

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331277-830

Luminaire Tested: **S122DIP-S290D1080U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331277-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D1080U830-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4862.0 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	25	24	19
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	21	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	41	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8995	8995	8995	8995
5°	10084	9054	8023	9054
10°	11555	8979	6943	8979
15°	12784	8816	6135	8816
20°	12589	8639	5593	8639
25°	11352	8402	5248	8402
30°	9380	8028	4998	8028
35°	6838	7634	4819	7634
40°	5461	7172	4719	7172
45°	4772	6635	4587	6635
50°	4486	6116	4496	6116
55°	4132	5588	4374	5588
60°	3788	5025	4191	5025
65°	3454	4523	4008	4523
70°	3135	4032	3744	4032
75°	2782	3487	3313	3487
80°	2390	2882	2669	2882
85°	2149	2149	1593	2149



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.1	1.1
10°-20°	154.2	3.2
20°-30°	223.9	4.6
30°-40°	236.2	4.9
40°-50°	209.2	4.3
50°-60°	166.9	3.4
60°-70°	113.4	2.3
70°-80°	58.2	1.2
80°-90°	19.2	0.4
90°-100°	82.2	1.7
100°-110°	255.3	5.3
110°-120°	436.4	9.0
120°-130°	573.9	11.8
130°-140°	644.2	13.2
140°-150°	631.6	13.0
150°-160°	529.8	10.9
160°-170°	351.4	7.2
170°-180°	122.8	2.5
0°-30°	431.2	8.9
0°-40°	667.4	13.7
0°-60°	1043.5	21.5
0°-90°	1234.3	25.4
90°-120°	774.0	15.9
90°-150°	2623.7	54.0
90°-180°	3628.0	74.6
0°-180°	4862.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	557	557	557	557	557	
5°	622	559	495	559	622	62
15°	765	527	367	527	765	211
25°	637	472	295	472	637	288
35°	347	387	244	387	347	226
45°	209	291	201	291	209	164
55°	147	198	155	198	147	132
65°	90	118	105	118	90	90
75°	45	56	53	56	45	48
85°	12	12	9	12	12	14
90°	37	1	37	1	37	17
95°	68	57	68	57	68	76
105°	243	235	243	235	243	256
115°	438	438	438	438	438	432
125°	639	637	639	637	639	570
135°	834	824	834	824	834	642
145°	1012	1001	1012	1001	1012	632
155°	1153	1144	1153	1144	1153	531
165°	1246	1245	1246	1245	1246	351
175°	1291	1295	1291	1295	1291	123
180°	1297	1297	1297	1297	1297	



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	582.8	583.0	583.3	580.6	580.2	580.2	577.9	575.8	573.3	570.1	570.5
5°	622.2	624.5	625.4	622.8	619.0	618.6	614.9	609.0	603.3	598.9	595.7
7.5°	669.2	670.1	668.1	664.7	661.9	656.7	649.9	643.3	634.0	625.5	619.2
10°	704.8	706.2	702.5	697.6	693.5	687.5	677.7	667.6	655.4	643.7	634.2
12.5°	731.9	735.1	730.4	729.8	722.8	714.5	702.9	697.8	680.6	664.2	654.0
15°	764.8	764.6	765.1	760.9	755.8	754.5	742.2	728.6	704.5	694.7	678.1
17.5°	755.3	758.6	760.1	760.0	759.9	759.0	755.1	746.6	734.4	718.8	699.6
20°	732.7	737.0	737.6	742.5	745.4	748.9	750.5	748.1	740.6	727.5	710.9
22.5°	697.8	699.0	701.0	708.6	714.6	723.8	728.5	736.5	733.6	727.2	713.2
25°	637.2	635.1	642.5	646.4	660.3	674.9	685.4	696.9	707.2	713.4	709.4
27.5°	564.5	561.3	572.5	582.8	594.0	609.8	626.1	645.5	661.5	681.6	688.5
30°	503.1	505.1	515.8	526.7	543.8	566.1	584.6	605.7	628.7	651.1	666.8
32.5°	437.1	444.4	451.2	468.0	483.1	507.8	534.9	561.4	589.9	615.5	639.7
35°	346.9	355.4	364.9	377.0	398.2	422.8	449.2	484.9	524.0	558.8	587.5
37.5°	292.0	290.6	296.0	304.8	322.0	341.9	372.2	407.5	453.4	494.4	534.9
40°	259.1	258.3	262.0	270.2	283.2	297.8	324.4	355.4	398.0	448.2	496.3
42.5°	236.5	237.0	239.1	244.9	253.8	265.8	285.7	312.1	351.1	398.3	450.1
45°	209.0	210.5	212.8	215.7	220.7	230.6	241.8	260.6	291.4	330.8	381.7
47.5°	189.2	189.3	191.6	194.1	197.1	202.6	211.8	223.6	245.3	277.4	321.2
50°	178.6	177.1	178.8	180.7	183.9	187.8	193.8	204.9	219.4	245.3	282.0
52.5°	165.5	165.6	167.1	167.9	170.7	174.6	180.0	187.8	201.0	221.2	251.3
55°	146.8	148.0	148.8	150.1	152.7	155.4	159.8	164.9	175.1	190.3	212.6
57.5°	129.3	129.7	130.5	133.0	134.6	137.1	141.2	145.9	152.6	163.8	180.6
60°	117.3	117.3	119.0	120.1	122.2	124.8	128.0	132.5	138.6	147.7	161.3
62.5°	106.4	106.2	106.9	108.7	110.3	112.6	115.8	119.7	125.4	133.6	144.6
65°	90.4	89.9	91.2	91.6	93.3	95.7	98.3	102.4	106.9	112.8	122.7
67.5°	74.9	75.5	76.2	76.9	77.9	80.4	82.1	84.9	88.8	93.8	100.4
70°	66.4	66.4	66.4	67.0	68.3	69.6	71.3	73.6	77.3	81.5	87.6
72.5°	56.7	57.5	58.2	57.8	59.4	60.1	62.2	63.5	67.0	69.7	75.0
75°	44.6	44.6	44.6	45.6	46.3	46.8	48.2	49.5	51.2	54.6	57.4
77.5°	33.3	33.2	33.4	33.6	34.3	35.1	35.4	36.6	38.2	39.8	42.1
80°	25.7	26.1	26.3	26.8	26.8	27.1	27.4	28.9	30.0	31.0	32.5
82.5°	19.9	20.0	20.0	20.1	20.3	20.5	21.1	21.6	22.0	22.8	23.9
85°	11.6	11.3	11.3	11.8	11.6	11.6	12.0	12.4	12.4	12.6	13.3
87.5°	11.9	11.9	12.0	11.8	11.7	11.9	12.0	11.9	12.2	12.4	11.6
90°	37.2	36.9	36.8	36.5	36.3	36.4	36.9	37.3	37.8	38.4	33.0
92.5°	35.4	35.4	35.3	35.3	35.3	35.3	35.1	35.0	34.9	34.8	33.6
95°	67.9	68.3	68.9	69.4	69.8	70.0	70.0	70.0	70.0	70.0	69.6
97.5°	117.6	117.6	117.7	117.7	117.8	117.8	117.8	117.8	117.8	117.8	116.9
100°	150.0	150.2	150.5	150.7	151.0	151.1	151.1	151.1	151.1	151.1	150.3
102.5°	186.8	187.0	187.3	187.5	187.8	187.8	187.6	187.4	187.2	187.0	186.1
105°	243.1	243.1	243.1	243.1	243.1	242.8	242.3	241.9	241.4	240.8	240.3
107.5°	296.1	297.2	298.3	299.4	300.5	301.0	300.8	300.6	300.4	300.2	300.2
110°	337.2	337.9	338.7	339.4	340.2	340.5	340.5	340.5	340.5	340.5	340.5



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	376.6	377.2	377.7	378.2	378.8	379.4	379.9	380.5	381.1	381.6	381.8
115°	437.9	438.7	439.4	440.2	440.8	441.3	441.6	441.9	442.1	442.3	442.8
117.5°	496.4	497.1	497.9	498.6	499.4	500.0	500.6	501.1	501.7	502.3	503.7
120°	537.5	538.3	539.0	539.8	540.5	540.8	540.8	540.8	540.8	540.8	542.8
122.5°	577.9	578.4	578.9	579.5	580.0	580.5	581.2	581.7	582.3	582.9	584.3
125°	639.4	639.6	639.9	640.1	640.4	640.8	641.6	642.3	643.0	643.8	644.5
127.5°	695.4	696.3	697.0	697.8	698.5	699.4	700.2	701.2	702.0	702.9	703.8
130°	735.7	736.7	737.6	738.7	739.6	740.4	740.8	741.3	741.8	742.3	742.8
132.5°	774.3	775.1	775.8	776.7	777.4	778.4	779.4	780.4	781.6	782.6	782.5
135°	834.2	835.0	835.8	836.4	837.2	837.6	837.9	838.2	838.4	838.7	838.2
137.5°	888.5	889.6	890.5	891.5	892.5	893.1	893.2	893.4	893.6	893.8	893.2
140°	926.2	927.2	928.2	929.2	930.1	930.6	930.6	930.6	930.6	930.6	929.4
142.5°	960.4	961.4	962.3	963.3	964.3	964.7	964.5	964.3	964.1	963.9	963.1
145°	1011.6	1012.6	1013.6	1014.6	1015.5	1015.9	1015.7	1015.4	1015.1	1014.9	1013.4
147.5°	1057.4	1058.3	1059.2	1060.2	1061.1	1061.3	1060.7	1060.3	1059.7	1059.1	1058.2
150°	1087.2	1087.9	1088.6	1089.4	1090.1	1090.1	1089.4	1088.6	1087.9	1087.2	1086.2
152.5°	1115.2	1116.2	1117.1	1117.9	1118.9	1118.9	1117.9	1117.1	1116.2	1115.2	1114.1
155°	1152.8	1153.6	1154.3	1155.1	1155.7	1155.6	1154.3	1153.1	1151.9	1150.7	1150.0
157.5°	1185.2	1186.5	1187.6	1188.7	1190.0	1189.7	1188.1	1186.4	1184.8	1183.1	1182.6
160°	1205.4	1206.4	1207.4	1208.3	1209.3	1209.1	1207.6	1206.2	1204.7	1203.2	1203.0
162.5°	1222.9	1224.1	1225.3	1226.4	1227.6	1227.4	1225.7	1224.1	1222.4	1220.8	1220.5
165°	1245.9	1247.2	1248.4	1249.6	1250.8	1250.6	1248.9	1247.2	1245.5	1243.8	1243.8
167.5°	1264.8	1266.0	1267.2	1268.6	1269.8	1269.6	1267.9	1266.2	1264.5	1262.8	1262.8
170°	1274.4	1275.8	1277.3	1278.7	1280.3	1280.1	1278.4	1276.7	1275.0	1273.3	1273.6
172.5°	1282.2	1283.7	1285.2	1286.7	1288.1	1288.0	1286.3	1284.6	1282.9	1281.2	1281.4
175°	1290.8	1292.3	1293.7	1295.2	1296.7	1296.6	1294.9	1293.2	1291.5	1289.7	1290.2
177.5°	1294.8	1295.9	1297.1	1298.3	1299.4	1299.4	1298.3	1297.1	1295.9	1294.8	1295.1
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	571.7	570.3	569.5	566.4	563.6	560.9	560.1	560.3	556.6	553.0	551.5
5°	594.0	589.7	585.6	579.9	573.0	565.4	561.7	558.6	551.1	543.0	538.3
7.5°	613.9	607.8	599.9	589.1	579.1	567.3	559.8	553.2	542.2	530.7	523.7
10°	626.0	617.7	607.7	594.4	582.2	567.8	557.8	547.7	534.9	521.1	512.6
12.5°	636.5	625.3	615.4	598.3	583.9	565.9	554.0	539.8	526.3	510.0	501.6
15°	661.4	640.6	621.8	602.5	584.8	559.7	546.4	527.4	509.6	489.5	479.8
17.5°	680.6	657.2	627.6	603.1	582.4	554.6	535.2	512.4	491.3	468.3	455.2
20°	691.5	664.8	632.9	603.8	579.0	547.2	526.0	502.8	478.2	452.2	438.1
22.5°	698.0	670.0	638.4	601.2	572.1	541.3	514.6	489.0	464.1	436.1	421.3
25°	700.1	674.5	641.0	599.1	563.5	528.7	496.5	471.6	441.5	415.4	393.8
27.5°	689.9	671.6	639.4	595.0	553.6	512.8	477.0	448.9	417.1	388.7	366.9
30°	677.4	666.8	635.5	591.0	545.7	501.9	462.5	430.6	398.9	370.2	347.9
32.5°	658.1	655.8	628.3	585.1	537.3	488.0	447.2	415.0	379.8	351.7	330.5
35°	620.1	630.4	613.0	572.1	521.6	468.3	424.1	387.3	350.9	324.0	304.1
37.5°	569.1	594.7	590.1	553.1	500.2	446.8	398.0	359.6	324.9	297.7	278.1
40°	534.0	566.6	571.3	538.5	485.2	430.2	378.5	340.3	306.4	281.5	261.8
42.5°	496.3	534.3	547.2	521.0	468.7	412.6	361.1	321.4	287.9	263.7	246.3
45°	433.2	483.4	506.8	491.8	441.3	383.9	330.8	290.6	260.1	237.4	223.9
47.5°	374.1	429.0	460.4	455.2	410.8	353.9	301.4	262.8	233.2	215.1	203.0
50°	332.3	388.8	426.7	428.5	388.8	332.5	279.8	243.5	216.2	199.3	189.5
52.5°	296.0	350.0	391.2	400.4	364.3	310.3	260.5	224.2	200.3	184.7	176.0
55°	248.5	294.2	340.0	356.8	327.8	276.4	230.4	198.5	176.0	165.3	157.6
57.5°	206.7	244.7	287.0	305.5	287.7	243.6	200.5	172.8	154.6	145.2	139.2
60°	184.5	214.5	252.2	274.3	258.8	219.7	182.0	155.6	140.6	132.3	126.8
62.5°	164.0	190.6	222.4	242.6	234.2	197.3	163.5	140.3	127.3	119.5	115.5
65°	135.3	156.3	181.0	199.5	194.0	166.0	138.3	118.4	108.1	101.9	98.7
67.5°	111.4	126.6	143.6	159.9	155.5	135.6	113.5	97.9	90.3	84.9	82.9
70°	96.3	107.9	123.1	136.2	132.5	116.3	98.7	85.4	78.8	74.3	72.4
72.5°	82.0	91.4	103.1	113.8	111.3	97.7	83.1	73.1	68.0	63.8	62.3
75°	61.9	69.2	76.3	83.3	82.7	72.2	63.6	55.9	51.8	48.6	48.0
77.5°	45.7	49.8	54.6	58.7	57.6	51.6	44.9	40.4	37.5	35.3	35.0
80°	34.9	37.2	40.7	43.6	42.2	39.6	34.2	31.0	28.9	26.8	25.9
82.5°	25.4	27.6	29.7	31.4	30.2	27.8	24.5	22.3	21.0	19.6	19.2
85°	13.3	14.5	15.5	15.8	15.5	13.9	12.4	11.6	10.5	9.8	9.6
87.5°	10.7	9.6	8.5	8.0	7.0	6.3	5.1	4.0	4.4	4.8	5.1
90°	27.6	22.2	16.9	12.8	9.9	7.0	4.1	1.1	4.1	7.0	9.9
92.5°	32.3	31.0	29.8	28.1	25.9	23.8	21.6	19.5	21.6	23.8	25.9
95°	69.1	68.6	68.1	66.6	64.2	61.8	59.4	56.9	59.4	61.8	64.2
97.5°	115.9	115.0	114.1	112.5	110.5	108.3	106.1	104.1	106.1	108.3	110.5
100°	149.6	148.9	148.2	146.8	144.9	143.0	141.0	139.0	141.0	143.0	144.9
102.5°	185.1	184.3	183.3	182.1	180.5	179.0	177.4	175.9	177.4	179.0	180.5
105°	239.9	239.4	238.9	238.3	237.6	236.9	236.1	235.4	236.1	236.9	237.6
107.5°	300.2	300.2	300.2	299.6	298.6	297.6	296.4	295.4	296.4	297.6	298.6
110°	340.5	340.5	340.5	339.8	338.3	336.9	335.4	333.9	335.4	336.9	338.3



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	382.0	382.2	382.5	381.8	380.3	378.9	377.4	376.0	377.4	378.9	380.3
115°	443.3	443.7	444.2	443.7	442.3	440.8	439.4	437.9	439.4	440.8	442.3
117.5°	505.0	506.4	507.7	507.5	505.5	503.6	501.6	499.6	501.6	503.6	505.5
120°	544.8	546.7	548.7	548.7	546.7	544.8	542.8	540.8	542.8	544.8	546.7
122.5°	585.6	587.0	588.3	587.9	585.5	583.2	580.9	578.5	580.9	583.2	585.5
125°	645.3	645.9	646.7	645.9	643.8	641.6	639.4	637.2	639.4	641.6	643.8
127.5°	704.6	705.5	706.4	705.4	702.7	699.9	697.1	694.4	697.1	699.9	702.7
130°	743.3	743.8	744.2	742.9	739.7	736.6	733.4	730.3	733.4	736.6	739.7
132.5°	782.4	782.3	782.2	780.9	778.3	775.7	773.2	770.5	773.2	775.7	778.3
135°	837.6	837.2	836.7	835.1	832.5	829.8	827.1	824.4	827.1	829.8	832.5
137.5°	892.6	891.9	891.3	889.9	887.7	885.5	883.4	881.1	883.4	885.5	887.7
140°	928.2	927.0	925.8	924.1	921.9	919.6	917.5	915.3	917.5	919.6	921.9
142.5°	962.2	961.4	960.5	959.0	956.9	954.7	952.5	950.4	952.5	954.7	956.9
145°	1012.0	1010.5	1009.1	1007.5	1005.8	1004.1	1002.4	1000.7	1002.4	1004.1	1005.8
147.5°	1057.2	1056.2	1055.3	1053.8	1051.7	1049.6	1047.6	1045.6	1047.6	1049.6	1051.7
150°	1085.2	1084.3	1083.3	1082.0	1080.6	1079.1	1077.7	1076.2	1077.7	1079.1	1080.6
152.5°	1112.9	1111.7	1110.5	1109.2	1107.8	1106.3	1104.8	1103.3	1104.8	1106.3	1107.8
155°	1149.2	1148.5	1147.7	1147.1	1146.3	1145.6	1144.8	1144.2	1144.8	1145.6	1146.3
157.5°	1182.2	1181.8	1181.3	1180.9	1180.3	1179.9	1179.4	1178.9	1179.4	1179.9	1180.3
160°	1202.8	1202.5	1202.2	1201.9	1201.4	1200.9	1200.4	1200.0	1200.4	1200.9	1201.4
162.5°	1220.2	1220.0	1219.7	1219.7	1219.5	1219.4	1219.3	1219.2	1219.3	1219.4	1219.5
165°	1243.8	1243.8	1243.8	1243.9	1244.1	1244.3	1244.6	1244.8	1244.6	1244.3	1244.1
167.5°	1262.9	1262.9	1263.0	1263.4	1264.1	1264.8	1265.6	1266.3	1265.6	1264.8	1264.1
170°	1273.8	1274.0	1274.3	1274.8	1275.4	1276.2	1277.0	1277.7	1277.0	1276.2	1275.4
172.5°	1281.7	1282.0	1282.1	1282.6	1283.4	1284.1	1284.9	1285.5	1284.9	1284.1	1283.4
175°	1290.7	1291.2	1291.7	1292.3	1293.0	1293.7	1294.5	1295.2	1294.5	1293.7	1293.0
177.5°	1295.5	1295.9	1296.3	1296.8	1297.4	1298.0	1298.5	1299.1	1298.5	1298.0	1297.4
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	549.8	548.7	545.2	543.3	540.2	537.2	535.4	536.2	536.9	536.6	536.0
5°	534.0	529.9	523.7	518.4	514.5	507.5	504.4	502.9	501.6	500.2	498.7
7.5°	515.2	508.8	499.9	492.3	485.1	476.3	471.3	468.3	465.2	461.8	458.8
10°	501.9	492.9	483.4	472.8	464.2	456.3	449.2	444.5	440.2	436.1	433.2
12.5°	487.9	477.5	465.8	451.2	441.8	430.4	429.3	421.0	414.3	411.8	408.3
15°	465.5	450.9	436.1	418.8	411.3	401.1	394.6	388.1	382.4	378.3	377.3
17.5°	440.1	421.2	406.5	394.1	381.8	371.3	365.3	360.2	355.4	350.1	349.3
20°	420.8	404.4	388.4	377.5	364.9	354.1	346.9	341.8	337.6	334.4	331.7
22.5°	402.4	384.6	369.9	358.0	345.5	336.9	331.1	326.1	322.7	319.2	316.6
25°	373.0	359.1	343.0	329.5	319.2	313.7	309.0	304.7	302.6	300.2	297.2
27.5°	347.2	331.8	316.8	306.3	297.3	292.4	289.0	286.1	284.1	282.7	281.0
30°	329.1	313.5	301.7	291.4	283.9	279.0	276.8	275.1	272.8	271.9	271.1
32.5°	311.6	297.6	287.5	278.5	271.5	268.2	266.3	264.7	262.9	262.0	260.2
35°	286.9	275.1	265.3	260.3	254.6	251.8	250.3	248.2	246.5	245.6	245.3
37.5°	263.6	253.4	246.9	240.6	238.2	236.5	234.4	233.0	232.4	232.3	232.1
40°	248.5	240.3	234.4	229.3	228.3	225.6	223.9	222.7	222.7	222.9	222.7
42.5°	234.9	227.3	222.3	217.8	216.6	215.1	213.3	213.3	213.6	214.3	213.6
45°	214.1	208.8	205.1	203.0	200.7	199.2	198.9	199.5	199.7	200.0	200.7
47.5°	195.0	191.4	188.1	185.8	184.7	184.5	184.3	185.4	186.4	186.8	187.8
50°	183.7	179.6	176.8	175.3	174.5	174.1	174.5	175.8	176.6	177.7	178.3
52.5°	171.1	168.1	166.3	165.0	164.8	165.0	165.0	166.5	167.9	168.3	168.6
55°	153.5	151.4	151.0	149.0	149.9	149.7	150.7	151.6	152.9	154.2	154.4
57.5°	136.0	134.3	133.2	133.4	133.7	134.6	135.4	137.0	138.3	139.7	139.8
60°	124.4	123.6	122.9	122.9	123.3	124.6	125.6	127.1	128.0	128.9	129.5
62.5°	113.8	112.9	112.3	112.6	113.8	114.5	115.7	116.6	117.4	118.3	118.6
65°	97.0	96.6	97.2	97.6	97.8	98.9	100.4	101.0	101.9	102.4	103.9
67.5°	81.5	81.6	81.5	82.1	83.4	83.6	85.0	86.5	86.7	87.6	88.5
70°	71.1	71.5	71.9	72.4	73.4	73.9	74.9	75.6	76.4	77.1	77.8
72.5°	61.5	61.5	62.0	61.9	62.9	63.7	64.7	65.3	66.2	67.0	67.6
75°	47.3	47.3	47.8	48.0	49.0	50.1	49.9	50.3	51.2	52.0	52.5
77.5°	34.6	34.1	34.6	34.8	35.2	36.0	36.2	36.8	37.8	37.5	38.0
80°	26.3	25.7	26.3	26.6	26.6	27.6	27.6	28.1	28.7	28.1	28.7
82.5°	18.8	18.5	18.9	19.0	19.3	19.4	19.7	19.8	20.5	20.2	20.5
85°	9.4	9.2	9.4	9.2	9.4	9.6	9.6	9.4	9.4	9.8	9.2
87.5°	5.5	6.1	7.0	8.1	9.0	9.9	9.6	9.5	9.4	9.0	9.0
90°	12.8	16.9	22.2	27.6	33.0	38.4	37.8	37.3	36.9	36.4	36.3
92.5°	28.1	29.8	31.0	32.3	33.6	34.8	34.9	35.0	35.1	35.3	35.3
95°	66.6	68.1	68.6	69.1	69.6	70.0	70.0	70.0	70.0	70.0	69.8
97.5°	112.5	114.1	115.0	115.9	116.9	117.8	117.8	117.8	117.8	117.8	117.8
100°	146.8	148.2	148.9	149.6	150.3	151.1	151.1	151.1	151.1	151.1	151.0
102.5°	182.1	183.3	184.3	185.1	186.1	187.0	187.2	187.4	187.6	187.8	187.8
105°	238.3	238.9	239.4	239.9	240.3	240.8	241.4	241.9	242.3	242.8	243.1
107.5°	299.6	300.2	300.2	300.2	300.2	300.2	300.4	300.6	300.8	301.0	300.5
110°	339.8	340.5	340.5	340.5	340.5	340.5	340.5	340.5	340.5	340.5	340.2



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	381.8	382.5	382.2	382.0	381.8	381.6	381.1	380.5	379.9	379.4	378.8
115°	443.7	444.2	443.7	443.3	442.8	442.3	442.1	441.9	441.6	441.3	440.8
117.5°	507.5	507.7	506.4	505.0	503.7	502.3	501.7	501.1	500.6	500.0	499.4
120°	548.7	548.7	546.7	544.8	542.8	540.8	540.8	540.8	540.8	540.8	540.5
122.5°	587.9	588.3	587.0	585.6	584.3	582.9	582.3	581.7	581.2	580.5	580.0
125°	645.9	646.7	645.9	645.3	644.5	643.8	643.0	642.3	641.6	640.8	640.4
127.5°	705.4	706.4	705.5	704.6	703.8	702.9	702.0	701.2	700.2	699.4	698.5
130°	742.9	744.2	743.8	743.3	742.8	742.3	741.8	741.3	740.8	740.4	739.6
132.5°	780.9	782.2	782.3	782.4	782.5	782.6	781.6	780.4	779.4	778.4	777.4
135°	835.1	836.7	837.2	837.6	838.2	838.7	838.4	838.2	837.9	837.6	837.2
137.5°	889.9	891.3	891.9	892.6	893.2	893.8	893.6	893.4	893.2	893.1	892.5
140°	924.1	925.8	927.0	928.2	929.4	930.6	930.6	930.6	930.6	930.6	930.1
142.5°	959.0	960.5	961.4	962.2	963.1	963.9	964.1	964.3	964.5	964.7	964.3
145°	1007.5	1009.1	1010.5	1012.0	1013.4	1014.9	1015.1	1015.4	1015.7	1015.9	1015.5
147.5°	1053.8	1055.3	1056.2	1057.2	1058.2	1059.1	1059.7	1060.3	1060.7	1061.3	1061.1
150°	1082.0	1083.3	1084.3	1085.2	1086.2	1087.2	1087.9	1088.6	1089.4	1090.1	1090.1
152.5°	1109.2	1110.5	1111.7	1112.9	1114.1	1115.2	1116.2	1117.1	1117.9	1118.9	1118.9
155°	1147.1	1147.7	1148.5	1149.2	1150.0	1150.7	1151.9	1153.1	1154.3	1155.6	1155.7
157.5°	1180.9	1181.3	1181.8	1182.2	1182.6	1183.1	1184.8	1186.4	1188.1	1189.7	1190.0
160°	1201.9	1202.2	1202.5	1202.8	1203.0	1203.2	1204.7	1206.2	1207.6	1209.1	1209.3
162.5°	1219.7	1219.7	1220.0	1220.2	1220.5	1220.8	1222.4	1224.1	1225.7	1227.4	1227.6
165°	1243.9	1243.8	1243.8	1243.8	1243.8	1243.8	1245.5	1247.2	1248.9	1250.6	1250.8
167.5°	1263.4	1263.0	1262.9	1262.9	1262.8	1262.8	1264.5	1266.2	1267.9	1269.6	1269.8
170°	1274.8	1274.3	1274.0	1273.8	1273.6	1273.3	1275.0	1276.7	1278.4	1280.1	1280.3
172.5°	1282.6	1282.1	1282.0	1281.7	1281.4	1281.2	1282.9	1284.6	1286.3	1288.0	1288.1
175°	1292.3	1291.7	1291.2	1290.7	1290.2	1289.7	1291.5	1293.2	1294.9	1296.6	1296.7
177.5°	1296.8	1296.3	1295.9	1295.5	1295.1	1294.8	1295.9	1297.1	1298.3	1299.4	1299.4
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	534.3	534.0	534.0	532.4	534.0	534.0	534.3	536.0	536.6	536.9	536.2
5°	495.7	495.0	494.0	495.0	494.0	495.0	495.7	498.7	500.2	501.6	502.9
7.5°	457.4	454.9	454.5	451.9	454.5	454.9	457.4	458.8	461.8	465.2	468.3
10°	429.5	427.8	427.5	423.5	427.5	427.8	429.5	433.2	436.1	440.2	444.5
12.5°	408.3	404.2	405.0	402.7	405.0	404.2	408.3	408.3	411.8	414.3	421.0
15°	371.5	371.5	370.6	367.0	370.6	371.5	371.5	377.3	378.3	382.4	388.1
17.5°	345.1	344.6	342.6	343.7	342.6	344.6	345.1	349.3	350.1	355.4	360.2
20°	329.3	328.0	325.5	325.5	325.5	328.0	329.3	331.7	334.4	337.6	341.8
22.5°	314.4	314.3	311.6	312.5	311.6	314.3	314.4	316.6	319.2	322.7	326.1
25°	297.0	295.3	294.0	294.6	294.0	295.3	297.0	297.2	300.2	302.6	304.7
27.5°	280.4	279.5	279.4	277.7	279.4	279.5	280.4	281.0	282.7	284.1	286.1
30°	270.9	268.7	269.1	268.1	269.1	268.7	270.9	271.1	271.9	272.8	275.1
32.5°	259.9	259.1	258.7	257.8	258.7	259.1	259.9	260.2	262.0	262.9	264.7
35°	245.0	245.2	244.1	244.5	244.1	245.2	245.0	245.3	245.6	246.5	248.2
37.5°	231.9	232.5	232.1	232.1	232.1	232.5	231.9	232.1	232.3	232.4	233.0
40°	223.3	223.3	223.3	223.9	223.3	223.3	223.3	222.7	222.9	222.7	222.7
42.5°	215.1	214.7	214.4	214.3	214.4	214.7	215.1	213.6	214.3	213.6	213.3
45°	201.0	201.7	201.9	200.9	201.9	201.7	201.0	200.7	200.0	199.7	199.5
47.5°	188.3	188.4	188.3	189.3	188.3	188.4	188.3	187.8	186.8	186.4	185.4
50°	179.5	179.0	179.5	179.0	179.5	179.0	179.5	178.3	177.7	176.6	175.8
52.5°	170.0	170.1	169.8	169.8	169.8	170.1	170.0	168.6	168.3	167.9	166.5
55°	155.2	155.6	155.4	155.4	155.4	155.6	155.2	154.4	154.2	152.9	151.6
57.5°	140.0	140.3	140.6	139.7	140.6	140.3	140.0	139.8	139.7	138.3	137.0
60°	129.3	130.4	130.2	129.8	130.2	130.4	129.3	129.5	128.9	128.0	127.1
62.5°	119.5	120.0	119.9	119.8	119.9	120.0	119.5	118.6	118.3	117.4	116.6
65°	104.5	104.9	104.2	104.9	104.2	104.9	104.5	103.9	102.4	101.9	101.0
67.5°	88.2	88.4	88.9	89.2	88.9	88.4	88.2	88.5	87.6	86.7	86.5
70°	78.1	77.9	78.6	79.3	78.6	77.9	78.1	77.8	77.1	76.4	75.6
72.5°	67.5	68.0	67.8	68.2	67.8	68.0	67.5	67.6	67.0	66.2	65.3
75°	52.0	52.7	52.5	53.1	52.5	52.7	52.0	52.5	52.0	51.2	50.3
77.5°	37.6	37.7	37.6	38.0	37.6	37.7	37.6	38.0	37.5	37.8	36.8
80°	28.7	28.3	27.8	28.7	27.8	28.3	28.7	28.7	28.1	28.7	28.1
82.5°	20.0	20.2	19.8	19.8	19.8	20.2	20.0	20.5	20.2	20.5	19.8
85°	9.2	9.0	8.6	8.6	8.6	9.0	9.2	9.2	9.8	9.4	9.4
87.5°	9.0	8.9	9.0	8.9	9.0	8.9	9.0	9.0	9.0	9.4	9.5
90°	36.5	36.8	36.9	37.2	36.9	36.8	36.5	36.3	36.4	36.9	37.3
92.5°	35.3	35.3	35.4	35.4	35.4	35.3	35.3	35.3	35.3	35.1	35.0
95°	69.4	68.9	68.3	67.9	68.3	68.9	69.4	69.8	70.0	70.0	70.0
97.5°	117.7	117.7	117.6	117.6	117.6	117.7	117.7	117.8	117.8	117.8	117.8
100°	150.7	150.5	150.2	150.0	150.2	150.5	150.7	151.0	151.1	151.1	151.1
102.5°	187.5	187.3	187.0	186.8	187.0	187.3	187.5	187.8	187.8	187.6	187.4
105°	243.1	243.1	243.1	243.1	243.1	243.1	243.1	243.1	242.8	242.3	241.9
107.5°	299.4	298.3	297.2	296.1	297.2	298.3	299.4	300.5	301.0	300.8	300.6
110°	339.4	338.7	337.9	337.2	337.9	338.7	339.4	340.2	340.5	340.5	340.5



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	378.2	377.7	377.2	376.6	377.2	377.7	378.2	378.8	379.4	379.9	380.5
115°	440.2	439.4	438.7	437.9	438.7	439.4	440.2	440.8	441.3	441.6	441.9
117.5°	498.6	497.9	497.1	496.4	497.1	497.9	498.6	499.4	500.0	500.6	501.1
120°	539.8	539.0	538.3	537.5	538.3	539.0	539.8	540.5	540.8	540.8	540.8
122.5°	579.5	578.9	578.4	577.9	578.4	578.9	579.5	580.0	580.5	581.2	581.7
125°	640.1	639.9	639.6	639.4	639.6	639.9	640.1	640.4	640.8	641.6	642.3
127.5°	697.8	697.0	696.3	695.4	696.3	697.0	697.8	698.5	699.4	700.2	701.2
130°	738.7	737.6	736.7	735.7	736.7	737.6	738.7	739.6	740.4	740.8	741.3
132.5°	776.7	775.8	775.1	774.3	775.1	775.8	776.7	777.4	778.4	779.4	780.4
135°	836.4	835.8	835.0	834.2	835.0	835.8	836.4	837.2	837.6	837.9	838.2
137.5°	891.5	890.5	889.6	888.5	889.6	890.5	891.5	892.5	893.1	893.2	893.4
140°	929.2	928.2	927.2	926.2	927.2	928.2	929.2	930.1	930.6	930.6	930.6
142.5°	963.3	962.3	961.4	960.4	961.4	962.3	963.3	964.3	964.7	964.5	964.3
145°	1014.6	1013.6	1012.6	1011.6	1012.6	1013.6	1014.6	1015.5	1015.9	1015.7	1015.4
147.5°	1060.2	1059.2	1058.3	1057.4	1058.3	1059.2	1060.2	1061.1	1061.3	1060.7	1060.3
150°	1089.4	1088.6	1087.9	1087.2	1087.9	1088.6	1089.4	1090.1	1090.1	1089.4	1088.6
152.5°	1117.9	1117.1	1116.2	1115.2	1116.2	1117.1	1117.9	1118.9	1118.9	1117.9	1117.1
155°	1155.1	1154.3	1153.6	1152.8	1153.6	1154.3	1155.1	1155.7	1155.6	1154.3	1153.1
157.5°	1188.7	1187.6	1186.5	1185.2	1186.5	1187.6	1188.7	1190.0	1189.7	1188.1	1186.4
160°	1208.3	1207.4	1206.4	1205.4	1206.4	1207.4	1208.3	1209.3	1209.1	1207.6	1206.2
162.5°	1226.4	1225.3	1224.1	1222.9	1224.1	1225.3	1226.4	1227.6	1227.4	1225.7	1224.1
165°	1249.6	1248.4	1247.2	1245.9	1247.2	1248.4	1249.6	1250.8	1250.6	1248.9	1247.2
167.5°	1268.6	1267.2	1266.0	1264.8	1266.0	1267.2	1268.6	1269.8	1269.6	1267.9	1266.2
170°	1278.7	1277.3	1275.8	1274.4	1275.8	1277.3	1278.7	1280.3	1280.1	1278.4	1276.7
172.5°	1286.7	1285.2	1283.7	1282.2	1283.7	1285.2	1286.7	1288.1	1288.0	1286.3	1284.6
175°	1295.2	1293.7	1292.3	1290.8	1292.3	1293.7	1295.2	1296.7	1296.6	1294.9	1293.2
177.5°	1298.3	1297.1	1295.9	1294.8	1295.9	1297.1	1298.3	1299.4	1299.4	1298.3	1297.1
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	535.4	537.2	540.2	543.3	545.2	548.7	549.8	551.5	553.0	556.6	560.3
5°	504.4	507.5	514.5	518.4	523.7	529.9	534.0	538.3	543.0	551.1	558.6
7.5°	471.3	476.3	485.1	492.3	499.9	508.8	515.2	523.7	530.7	542.2	553.2
10°	449.2	456.3	464.2	472.8	483.4	492.9	501.9	512.6	521.1	534.9	547.7
12.5°	429.3	430.4	441.8	451.2	465.8	477.5	487.9	501.6	510.0	526.3	539.8
15°	394.6	401.1	411.3	418.8	436.1	450.9	465.5	479.8	489.5	509.6	527.4
17.5°	365.3	371.3	381.8	394.1	406.5	421.2	440.1	455.2	468.3	491.3	512.4
20°	346.9	354.1	364.9	377.5	388.4	404.4	420.8	438.1	452.2	478.2	502.8
22.5°	331.1	336.9	345.5	358.0	369.9	384.6	402.4	421.3	436.1	464.1	489.0
25°	309.0	313.7	319.2	329.5	343.0	359.1	373.0	393.8	415.4	441.5	471.6
27.5°	289.0	292.4	297.3	306.3	316.8	331.8	347.2	366.9	388.7	417.1	448.9
30°	276.8	279.0	283.9	291.4	301.7	313.5	329.1	347.9	370.2	398.9	430.6
32.5°	266.3	268.2	271.5	278.5	287.5	297.6	311.6	330.5	351.7	379.8	415.0
35°	250.3	251.8	254.6	260.3	265.3	275.1	286.9	304.1	324.0	350.9	387.3
37.5°	234.4	236.5	238.2	240.6	246.9	253.4	263.6	278.1	297.7	324.9	359.6
40°	223.9	225.6	228.3	229.3	234.4	240.3	248.5	261.8	281.5	306.4	340.3
42.5°	213.3	215.1	216.6	217.8	222.3	227.3	234.9	246.3	263.7	287.9	321.4
45°	198.9	199.2	200.7	203.0	205.1	208.8	214.1	223.9	237.4	260.1	290.6
47.5°	184.3	184.5	184.7	185.8	188.1	191.4	195.0	203.0	215.1	233.2	262.8
50°	174.5	174.1	174.5	175.3	176.8	179.6	183.7	189.5	199.3	216.2	243.5
52.5°	165.0	165.0	164.8	165.0	166.3	168.1	171.1	176.0	184.7	200.3	224.2
55°	150.7	149.7	149.9	149.0	151.0	151.4	153.5	157.6	165.3	176.0	198.5
57.5°	135.4	134.6	133.7	133.4	133.2	134.3	136.0	139.2	145.2	154.6	172.8
60°	125.6	124.6	123.3	122.9	122.9	123.6	124.4	126.8	132.3	140.6	155.6
62.5°	115.7	114.5	113.8	112.6	112.3	112.9	113.8	115.5	119.5	127.3	140.3
65°	100.4	98.9	97.8	97.6	97.2	96.6	97.0	98.7	101.9	108.1	118.4
67.5°	85.0	83.6	83.4	82.1	81.5	81.6	81.5	82.9	84.9	90.3	97.9
70°	74.9	73.9	73.4	72.4	71.9	71.5	71.1	72.4	74.3	78.8	85.4
72.5°	64.7	63.7	62.9	61.9	62.0	61.5	61.5	62.3	63.8	68.0	73.1
75°	49.9	50.1	49.0	48.0	47.8	47.3	47.3	48.0	48.6	51.8	55.9
77.5°	36.2	36.0	35.2	34.8	34.6	34.1	34.6	35.0	35.3	37.5	40.4
80°	27.6	27.6	26.6	26.6	26.3	25.7	26.3	25.9	26.8	28.9	31.0
82.5°	19.7	19.4	19.3	19.0	18.9	18.5	18.8	19.2	19.6	21.0	22.3
85°	9.6	9.6	9.4	9.2	9.4	9.2	9.4	9.6	9.8	10.5	11.6
87.5°	9.6	9.9	9.0	8.1	7.0	6.1	5.5	5.1	4.8	4.4	4.0
90°	37.8	38.4	33.0	27.6	22.2	16.9	12.8	9.9	7.0	4.1	1.1
92.5°	34.9	34.8	33.6	32.3	31.0	29.8	28.1	25.9	23.8	21.6	19.5
95°	70.0	70.0	69.6	69.1	68.6	68.1	66.6	64.2	61.8	59.4	56.9
97.5°	117.8	117.8	116.9	115.9	115.0	114.1	112.5	110.5	108.3	106.1	104.1
100°	151.1	151.1	150.3	149.6	148.9	148.2	146.8	144.9	143.0	141.0	139.0
102.5°	187.2	187.0	186.1	185.1	184.3	183.3	182.1	180.5	179.0	177.4	175.9
105°	241.4	240.8	240.3	239.9	239.4	238.9	238.3	237.6	236.9	236.1	235.4
107.5°	300.4	300.2	300.2	300.2	300.2	300.2	299.6	298.6	297.6	296.4	295.4
110°	340.5	340.5	340.5	340.5	340.5	340.5	339.8	338.3	336.9	335.4	333.9



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	381.1	381.6	381.8	382.0	382.2	382.5	381.8	380.3	378.9	377.4	376.0
115°	442.1	442.3	442.8	443.3	443.7	444.2	443.7	442.3	440.8	439.4	437.9
117.5°	501.7	502.3	503.7	505.0	506.4	507.7	507.5	505.5	503.6	501.6	499.6
120°	540.8	540.8	542.8	544.8	546.7	548.7	548.7	546.7	544.8	542.8	540.8
122.5°	582.3	582.9	584.3	585.6	587.0	588.3	587.9	585.5	583.2	580.9	578.5
125°	643.0	643.8	644.5	645.3	645.9	646.7	645.9	643.8	641.6	639.4	637.2
127.5°	702.0	702.9	703.8	704.6	705.5	706.4	705.4	702.7	699.9	697.1	694.4
130°	741.8	742.3	742.8	743.3	743.8	744.2	742.9	739.7	736.6	733.4	730.3
132.5°	781.6	782.6	782.5	782.4	782.3	782.2	780.9	778.3	775.7	773.2	770.5
135°	838.4	838.7	838.2	837.6	837.2	836.7	835.1	832.5	829.8	827.1	824.4
137.5°	893.6	893.8	893.2	892.6	891.9	891.3	889.9	887.7	885.5	883.4	881.1
140°	930.6	930.6	929.4	928.2	927.0	925.8	924.1	921.9	919.6	917.5	915.3
142.5°	964.1	963.9	963.1	962.2	961.4	960.5	959.0	956.9	954.7	952.5	950.4
145°	1015.1	1014.9	1013.4	1012.0	1010.5	1009.1	1007.5	1005.8	1004.1	1002.4	1000.7
147.5°	1059.7	1059.1	1058.2	1057.2	1056.2	1055.3	1053.8	1051.7	1049.6	1047.6	1045.6
150°	1087.9	1087.2	1086.2	1085.2	1084.3	1083.3	1082.0	1080.6	1079.1	1077.7	1076.2
152.5°	1116.2	1115.2	1114.1	1112.9	1111.7	1110.5	1109.2	1107.8	1106.3	1104.8	1103.3
155°	1151.9	1150.7	1150.0	1149.2	1148.5	1147.7	1147.1	1146.3	1145.6	1144.8	1144.2
157.5°	1184.8	1183.1	1182.6	1182.2	1181.8	1181.3	1180.9	1180.3	1179.9	1179.4	1178.9
160°	1204.7	1203.2	1203.0	1202.8	1202.5	1202.2	1201.9	1201.4	1200.9	1200.4	1200.0
162.5°	1222.4	1220.8	1220.5	1220.2	1220.0	1219.7	1219.7	1219.5	1219.4	1219.3	1219.2
165°	1245.5	1243.8	1243.8	1243.8	1243.8	1243.8	1243.9	1244.1	1244.3	1244.6	1244.8
167.5°	1264.5	1262.8	1262.8	1262.9	1262.9	1263.0	1263.4	1264.1	1264.8	1265.6	1266.3
170°	1275.0	1273.3	1273.6	1273.8	1274.0	1274.3	1274.8	1275.4	1276.2	1277.0	1277.7
172.5°	1282.9	1281.2	1281.4	1281.7	1282.0	1282.1	1282.6	1283.4	1284.1	1284.9	1285.5
175°	1291.5	1289.7	1290.2	1290.7	1291.2	1291.7	1292.3	1293.0	1293.7	1294.5	1295.2
177.5°	1295.9	1294.8	1295.1	1295.5	1295.9	1296.3	1296.8	1297.4	1298.0	1298.5	1299.1
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	560.1	560.9	563.6	566.4	569.5	570.3	571.7	570.5	570.1	573.3	575.8
5°	561.7	565.4	573.0	579.9	585.6	589.7	594.0	595.7	598.9	603.3	609.0
7.5°	559.8	567.3	579.1	589.1	599.9	607.8	613.9	619.2	625.5	634.0	643.3
10°	557.8	567.8	582.2	594.4	607.7	617.7	626.0	634.2	643.7	655.4	667.6
12.5°	554.0	565.9	583.9	598.3	615.4	625.3	636.5	654.0	664.2	680.6	697.8
15°	546.4	559.7	584.8	602.5	621.8	640.6	661.4	678.1	694.7	704.5	728.6
17.5°	535.2	554.6	582.4	603.1	627.6	657.2	680.6	699.6	718.8	734.4	746.6
20°	526.0	547.2	579.0	603.8	632.9	664.8	691.5	710.9	727.5	740.6	748.1
22.5°	514.6	541.3	572.1	601.2	638.4	670.0	698.0	713.2	727.2	733.6	736.5
25°	496.5	528.7	563.5	599.1	641.0	674.5	700.1	709.4	713.4	707.2	696.9
27.5°	477.0	512.8	553.6	595.0	639.4	671.6	689.9	688.5	681.6	661.5	645.5
30°	462.5	501.9	545.7	591.0	635.5	666.8	677.4	666.8	651.1	628.7	605.7
32.5°	447.2	488.0	537.3	585.1	628.3	655.8	658.1	639.7	615.5	589.9	561.4
35°	424.1	468.3	521.6	572.1	613.0	630.4	620.1	587.5	558.8	524.0	484.9
37.5°	398.0	446.8	500.2	553.1	590.1	594.7	569.1	534.9	494.4	453.4	407.5
40°	378.5	430.2	485.2	538.5	571.3	566.6	534.0	496.3	448.2	398.0	355.4
42.5°	361.1	412.6	468.7	521.0	547.2	534.3	496.3	450.1	398.3	351.1	312.1
45°	330.8	383.9	441.3	491.8	506.8	483.4	433.2	381.7	330.8	291.4	260.6
47.5°	301.4	353.9	410.8	455.2	460.4	429.0	374.1	321.2	277.4	245.3	223.6
50°	279.8	332.5	388.8	428.5	426.7	388.8	332.3	282.0	245.3	219.4	204.9
52.5°	260.5	310.3	364.3	400.4	391.2	350.0	296.0	251.3	221.2	201.0	187.8
55°	230.4	276.4	327.8	356.8	340.0	294.2	248.5	212.6	190.3	175.1	164.9
57.5°	200.5	243.6	287.7	305.5	287.0	244.7	206.7	180.6	163.8	152.6	145.9
60°	182.0	219.7	258.8	274.3	252.2	214.5	184.5	161.3	147.7	138.6	132.5
62.5°	163.5	197.3	234.2	242.6	222.4	190.6	164.0	144.6	133.6	125.4	119.7
65°	138.3	166.0	194.0	199.5	181.0	156.3	135.3	122.7	112.8	106.9	102.4
67.5°	113.5	135.6	155.5	159.9	143.6	126.6	111.4	100.4	93.8	88.8	84.9
70°	98.7	116.3	132.5	136.2	123.1	107.9	96.3	87.6	81.5	77.3	73.6
72.5°	83.1	97.7	111.3	113.8	103.1	91.4	82.0	75.0	69.7	67.0	63.5
75°	63.6	72.2	82.7	83.3	76.3	69.2	61.9	57.4	54.6	51.2	49.5
77.5°	44.9	51.6	57.6	58.7	54.6	49.8	45.7	42.1	39.8	38.2	36.6
80°	34.2	39.6	42.2	43.6	40.7	37.2	34.9	32.5	31.0	30.0	28.9
82.5°	24.5	27.8	30.2	31.4	29.7	27.6	25.4	23.9	22.8	22.0	21.6
85°	12.4	13.9	15.5	15.8	15.5	14.5	13.3	13.3	12.6	12.4	12.4
87.5°	5.1	6.3	7.0	8.0	8.5	9.6	10.7	11.6	12.4	12.2	11.9
90°	4.1	7.0	9.9	12.8	16.9	22.2	27.6	33.0	38.4	37.8	37.3
92.5°	21.6	23.8	25.9	28.1	29.8	31.0	32.3	33.6	34.8	34.9	35.0
95°	59.4	61.8	64.2	66.6	68.1	68.6	69.1	69.6	70.0	70.0	70.0
97.5°	106.1	108.3	110.5	112.5	114.1	115.0	115.9	116.9	117.8	117.8	117.8
100°	141.0	143.0	144.9	146.8	148.2	148.9	149.6	150.3	151.1	151.1	151.1
102.5°	177.4	179.0	180.5	182.1	183.3	184.3	185.1	186.1	187.0	187.2	187.4
105°	236.1	236.9	237.6	238.3	238.9	239.4	239.9	240.3	240.8	241.4	241.9
107.5°	296.4	297.6	298.6	299.6	300.2	300.2	300.2	300.2	300.2	300.4	300.6
110°	335.4	336.9	338.3	339.8	340.5	340.5	340.5	340.5	340.5	340.5	340.5



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	377.4	378.9	380.3	381.8	382.5	382.2	382.0	381.8	381.6	381.1	380.5
115°	439.4	440.8	442.3	443.7	444.2	443.7	443.3	442.8	442.3	442.1	441.9
117.5°	501.6	503.6	505.5	507.5	507.7	506.4	505.0	503.7	502.3	501.7	501.1
120°	542.8	544.8	546.7	548.7	548.7	546.7	544.8	542.8	540.8	540.8	540.8
122.5°	580.9	583.2	585.5	587.9	588.3	587.0	585.6	584.3	582.9	582.3	581.7
125°	639.4	641.6	643.8	645.9	646.7	645.9	645.3	644.5	643.8	643.0	642.3
127.5°	697.1	699.9	702.7	705.4	706.4	705.5	704.6	703.8	702.9	702.0	701.2
130°	733.4	736.6	739.7	742.9	744.2	743.8	743.3	742.8	742.3	741.8	741.3
132.5°	773.2	775.7	778.3	780.9	782.2	782.3	782.4	782.5	782.6	781.6	780.4
135°	827.1	829.8	832.5	835.1	836.7	837.2	837.6	838.2	838.7	838.4	838.2
137.5°	883.4	885.5	887.7	889.9	891.3	891.9	892.6	893.2	893.8	893.6	893.4
140°	917.5	919.6	921.9	924.1	925.8	927.0	928.2	929.4	930.6	930.6	930.6
142.5°	952.5	954.7	956.9	959.0	960.5	961.4	962.2	963.1	963.9	964.1	964.3
145°	1002.4	1004.1	1005.8	1007.5	1009.1	1010.5	1012.0	1013.4	1014.9	1015.1	1015.4
147.5°	1047.6	1049.6	1051.7	1053.8	1055.3	1056.2	1057.2	1058.2	1059.1	1059.7	1060.3
150°	1077.7	1079.1	1080.6	1082.0	1083.3	1084.3	1085.2	1086.2	1087.2	1087.9	1088.6
152.5°	1104.8	1106.3	1107.8	1109.2	1110.5	1111.7	1112.9	1114.1	1115.2	1116.2	1117.1
155°	1144.8	1145.6	1146.3	1147.1	1147.7	1148.5	1149.2	1150.0	1150.7	1151.9	1153.1
157.5°	1179.4	1179.9	1180.3	1180.9	1181.3	1181.8	1182.2	1182.6	1183.1	1184.8	1186.4
160°	1200.4	1200.9	1201.4	1201.9	1202.2	1202.5	1202.8	1203.0	1203.2	1204.7	1206.2
162.5°	1219.3	1219.4	1219.5	1219.7	1219.7	1220.0	1220.2	1220.5	1220.8	1222.4	1224.1
165°	1244.6	1244.3	1244.1	1243.9	1243.8	1243.8	1243.8	1243.8	1243.8	1245.5	1247.2
167.5°	1265.6	1264.8	1264.1	1263.4	1263.0	1262.9	1262.9	1262.8	1262.8	1264.5	1266.2
170°	1277.0	1276.2	1275.4	1274.8	1274.3	1274.0	1273.8	1273.6	1273.3	1275.0	1276.7
172.5°	1284.9	1284.1	1283.4	1282.6	1282.1	1282.0	1281.7	1281.4	1281.2	1282.9	1284.6
175°	1294.5	1293.7	1293.0	1292.3	1291.7	1291.2	1290.7	1290.2	1289.7	1291.5	1293.2
177.5°	1298.5	1298.0	1297.4	1296.8	1296.3	1295.9	1295.5	1295.1	1294.8	1295.9	1297.1
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	577.9	580.2	580.2	580.6	583.3	583.0	582.8
5°	614.9	618.6	619.0	622.8	625.4	624.5	622.2
7.5°	649.9	656.7	661.9	664.7	668.1	670.1	669.2
10°	677.7	687.5	693.5	697.6	702.5	706.2	704.8
12.5°	702.9	714.5	722.8	729.8	730.4	735.1	731.9
15°	742.2	754.5	755.8	760.9	765.1	764.6	764.8
17.5°	755.1	759.0	759.9	760.0	760.1	758.6	755.3
20°	750.5	748.9	745.4	742.5	737.6	737.0	732.7
22.5°	728.5	723.8	714.6	708.6	701.0	699.0	697.8
25°	685.4	674.9	660.3	646.4	642.5	635.1	637.2
27.5°	626.1	609.8	594.0	582.8	572.5	561.3	564.5
30°	584.6	566.1	543.8	526.7	515.8	505.1	503.1
32.5°	534.9	507.8	483.1	468.0	451.2	444.4	437.1
35°	449.2	422.8	398.2	377.0	364.9	355.4	346.9
37.5°	372.2	341.9	322.0	304.8	296.0	290.6	292.0
40°	324.4	297.8	283.2	270.2	262.0	258.3	259.1
42.5°	285.7	265.8	253.8	244.9	239.1	237.0	236.5
45°	241.8	230.6	220.7	215.7	212.8	210.5	209.0
47.5°	211.8	202.6	197.1	194.1	191.6	189.3	189.2
50°	193.8	187.8	183.9	180.7	178.8	177.1	178.6
52.5°	180.0	174.6	170.7	167.9	167.1	165.6	165.5
55°	159.8	155.4	152.7	150.1	148.8	148.0	146.8
57.5°	141.2	137.1	134.6	133.0	130.5	129.7	129.3
60°	128.0	124.8	122.2	120.1	119.0	117.3	117.3
62.5°	115.8	112.6	110.3	108.7	106.9	106.2	106.4
65°	98.3	95.7	93.3	91.6	91.2	89.9	90.4
67.5°	82.1	80.4	77.9	76.9	76.2	75.5	74.9
70°	71.3	69.6	68.3	67.0	66.4	66.4	66.4
72.5°	62.2	60.1	59.4	57.8	58.2	57.5	56.7
75°	48.2	46.8	46.3	45.6	44.6	44.6	44.6
77.5°	35.4	35.1	34.3	33.6	33.4	33.2	33.3
80°	27.4	27.1	26.8	26.8	26.3	26.1	25.7
82.5°	21.1	20.5	20.3	20.1	20.0	20.0	19.9
85°	12.0	11.6	11.6	11.8	11.3	11.3	11.6
87.5°	12.0	11.9	11.7	11.8	12.0	11.9	11.9
90°	36.9	36.4	36.3	36.5	36.8	36.9	37.2
92.5°	35.1	35.3	35.3	35.3	35.3	35.4	35.4
95°	70.0	70.0	69.8	69.4	68.9	68.3	67.9
97.5°	117.8	117.8	117.8	117.7	117.7	117.6	117.6
100°	151.1	151.1	151.0	150.7	150.5	150.2	150.0
102.5°	187.6	187.8	187.8	187.5	187.3	187.0	186.8
105°	242.3	242.8	243.1	243.1	243.1	243.1	243.1
107.5°	300.8	301.0	300.5	299.4	298.3	297.2	296.1
110°	340.5	340.5	340.2	339.4	338.7	337.9	337.2



TEST NUMBER: P331277-830

CATALOG NUMBER: S122DIP-S290D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	379.9	379.4	378.8	378.2	377.7	377.2	376.6
115°	441.6	441.3	440.8	440.2	439.4	438.7	437.9
117.5°	500.6	500.0	499.4	498.6	497.9	497.1	496.4
120°	540.8	540.8	540.5	539.8	539.0	538.3	537.5
122.5°	581.2	580.5	580.0	579.5	578.9	578.4	577.9
125°	641.6	640.8	640.4	640.1	639.9	639.6	639.4
127.5°	700.2	699.4	698.5	697.8	697.0	696.3	695.4
130°	740.8	740.4	739.6	738.7	737.6	736.7	735.7
132.5°	779.4	778.4	777.4	776.7	775.8	775.1	774.3
135°	837.9	837.6	837.2	836.4	835.8	835.0	834.2
137.5°	893.2	893.1	892.5	891.5	890.5	889.6	888.5
140°	930.6	930.6	930.1	929.2	928.2	927.2	926.2
142.5°	964.5	964.7	964.3	963.3	962.3	961.4	960.4
145°	1015.7	1015.9	1015.5	1014.6	1013.6	1012.6	1011.6
147.5°	1060.7	1061.3	1061.1	1060.2	1059.2	1058.3	1057.4
150°	1089.4	1090.1	1090.1	1089.4	1088.6	1087.9	1087.2
152.5°	1117.9	1118.9	1118.9	1117.9	1117.1	1116.2	1115.2
155°	1154.3	1155.6	1155.7	1155.1	1154.3	1153.6	1152.8
157.5°	1188.1	1189.7	1190.0	1188.7	1187.6	1186.5	1185.2
160°	1207.6	1209.1	1209.3	1208.3	1207.4	1206.4	1205.4
162.5°	1225.7	1227.4	1227.6	1226.4	1225.3	1224.1	1222.9
165°	1248.9	1250.6	1250.8	1249.6	1248.4	1247.2	1245.9
167.5°	1267.9	1269.6	1269.8	1268.6	1267.2	1266.0	1264.8
170°	1278.4	1280.1	1280.3	1278.7	1277.3	1275.8	1274.4
172.5°	1286.3	1288.0	1288.1	1286.7	1285.2	1283.7	1282.2
175°	1294.9	1296.6	1296.7	1295.2	1293.7	1292.3	1290.8
177.5°	1298.3	1299.4	1299.4	1298.3	1297.1	1295.9	1294.8
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4

(END OF REPORT)