

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331267-830

Luminaire Tested: **S122DIP-S290D925U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331267-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D925U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4718.3 lumens
Efficiency: N/A
Efficacy: 126.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26				
1	93	89	85	82	83	79	76	73	62	60	58	45	44	43	31	30	29	22				
2	85	78	72	67	75	69	65	61	54	51	48	40	38	36	27	26	25	19				
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17				
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	14				
5	65	54	46	41	58	48	42	37	38	34	30	29	26	23	20	18	16	13				
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11				
7	55	44	36	31	49	39	33	28	31	26	23	24	20	18	16	15	13	10				
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12	9				
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8				
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8995	8995	8995	8995
5°	10084	9054	8023	9054
10°	11555	8979	6943	8979
15°	12784	8816	6135	8816
20°	12589	8639	5593	8639
25°	11352	8402	5248	8402
30°	9380	8028	4998	8028
35°	6838	7634	4819	7634
40°	5461	7172	4719	7172
45°	4772	6635	4587	6635
50°	4486	6116	4496	6116
55°	4132	5588	4374	5588
60°	3788	5025	4191	5025
65°	3454	4523	4008	4523
70°	3135	4032	3744	4032
75°	2782	3487	3313	3487
80°	2390	2882	2669	2882
85°	2149	2149	1593	2149



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.1	1.1
10°-20°	154.2	3.3
20°-30°	223.9	4.7
30°-40°	236.2	5.0
40°-50°	209.2	4.4
50°-60°	166.9	3.5
60°-70°	113.4	2.4
70°-80°	58.2	1.2
80°-90°	16.9	0.4
90°-100°	39.7	0.8
100°-110°	145.5	3.1
110°-120°	389.0	8.2
120°-130°	642.1	13.6
130°-140°	682.9	14.5
140°-150°	634.7	13.5
150°-160°	510.3	10.8
160°-170°	328.8	7.0
170°-180°	113.2	2.4
0°-30°	431.2	9.1
0°-40°	667.4	14.1
0°-60°	1043.5	22.1
0°-90°	1232.0	26.1
90°-120°	574.2	12.2
90°-150°	2533.9	53.7
90°-180°	3486.0	73.9
0°-180°	4718.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	557	557	557	557	557	
5°	622	559	495	559	622	62
15°	765	527	367	527	765	211
25°	637	472	295	472	637	288
35°	347	387	244	387	347	226
45°	209	291	201	291	209	164
55°	147	198	155	198	147	132
65°	90	118	105	118	90	90
75°	45	56	53	56	45	48
85°	12	12	9	12	12	13
90°	23	1	23	1	23	11
95°	37	56	37	56	37	35
105°	65	262	65	262	65	68
115°	71	495	71	495	71	177
125°	736	700	736	700	736	637
135°	894	866	894	866	894	689
145°	1020	1005	1020	1005	1020	638
155°	1107	1106	1107	1106	1107	511
165°	1163	1166	1163	1166	1163	328
175°	1185	1192	1185	1192	1185	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	582.8	583.0	583.3	580.6	580.2	580.2	577.9	575.8	573.3	570.1	570.5
5°	622.2	624.5	625.4	622.8	619.0	618.6	614.9	609.0	603.3	598.9	595.7
7.5°	669.2	670.1	668.1	664.7	661.9	656.7	649.9	643.3	634.0	625.5	619.2
10°	704.8	706.2	702.5	697.6	693.5	687.5	677.7	667.6	655.4	643.7	634.2
12.5°	731.9	735.1	730.4	729.8	722.8	714.5	702.9	697.8	680.6	664.2	654.0
15°	764.8	764.6	765.1	760.9	755.8	754.5	742.2	728.6	704.5	694.7	678.1
17.5°	755.3	758.6	760.1	760.0	759.9	759.0	755.1	746.6	734.4	718.8	699.6
20°	732.7	737.0	737.6	742.5	745.4	748.9	750.5	748.1	740.6	727.5	710.9
22.5°	697.8	699.0	701.0	708.6	714.6	723.8	728.5	736.5	733.6	727.2	713.2
25°	637.2	635.1	642.5	646.4	660.3	674.9	685.4	696.9	707.2	713.4	709.4
27.5°	564.5	561.3	572.5	582.8	594.0	609.8	626.1	645.5	661.5	681.6	688.5
30°	503.1	505.1	515.8	526.7	543.8	566.1	584.6	605.7	628.7	651.1	666.8
32.5°	437.1	444.4	451.2	468.0	483.1	507.8	534.9	561.4	589.9	615.5	639.7
35°	346.9	355.4	364.9	377.0	398.2	422.8	449.2	484.9	524.0	558.8	587.5
37.5°	292.0	290.6	296.0	304.8	322.0	341.9	372.2	407.5	453.4	494.4	534.9
40°	259.1	258.3	262.0	270.2	283.2	297.8	324.4	355.4	398.0	448.2	496.3
42.5°	236.5	237.0	239.1	244.9	253.8	265.8	285.7	312.1	351.1	398.3	450.1
45°	209.0	210.5	212.8	215.7	220.7	230.6	241.8	260.6	291.4	330.8	381.7
47.5°	189.2	189.3	191.6	194.1	197.1	202.6	211.8	223.6	245.3	277.4	321.2
50°	178.6	177.1	178.8	180.7	183.9	187.8	193.8	204.9	219.4	245.3	282.0
52.5°	165.5	165.6	167.1	167.9	170.7	174.6	180.0	187.8	201.0	221.2	251.3
55°	146.8	148.0	148.8	150.1	152.7	155.4	159.8	164.9	175.1	190.3	212.6
57.5°	129.3	129.7	130.5	133.0	134.6	137.1	141.2	145.9	152.6	163.8	180.6
60°	117.3	117.3	119.0	120.1	122.2	124.8	128.0	132.5	138.6	147.7	161.3
62.5°	106.4	106.2	106.9	108.7	110.3	112.6	115.8	119.7	125.4	133.6	144.6
65°	90.4	89.9	91.2	91.6	93.3	95.7	98.3	102.4	106.9	112.8	122.7
67.5°	74.9	75.5	76.2	76.9	77.9	80.4	82.1	84.9	88.8	93.8	100.4
70°	66.4	66.4	66.4	67.0	68.3	69.6	71.3	73.6	77.3	81.5	87.6
72.5°	56.7	57.5	58.2	57.8	59.4	60.1	62.2	63.5	67.0	69.7	75.0
75°	44.6	44.6	44.6	45.6	46.3	46.8	48.2	49.5	51.2	54.6	57.4
77.5°	33.3	33.2	33.4	33.6	34.3	35.1	35.4	36.6	38.2	39.8	42.1
80°	25.7	26.1	26.3	26.8	26.8	27.1	27.4	28.9	30.0	31.0	32.5
82.5°	19.9	20.0	20.0	20.1	20.3	20.5	21.1	21.6	22.0	22.8	23.9
85°	11.6	11.3	11.3	11.8	11.6	11.6	12.0	12.4	12.4	12.6	13.3
87.5°	9.1	9.0	9.1	8.9	8.8	8.9	8.7	8.3	8.3	8.2	8.1
90°	23.3	22.9	22.4	22.1	21.7	21.0	20.1	19.1	18.2	17.2	15.6
92.5°	23.3	23.0	22.8	22.5	22.3	22.0	21.5	20.9	20.5	20.0	19.2
95°	37.0	37.2	37.4	37.6	37.8	37.4	36.5	35.4	34.5	33.6	32.2
97.5°	49.4	49.2	48.9	48.7	48.4	48.0	47.2	46.5	45.7	45.0	41.8
100°	57.7	57.3	56.9	56.6	56.2	55.2	53.6	52.1	50.6	49.1	45.8
102.5°	61.8	61.3	60.7	60.2	59.7	58.4	56.5	54.4	52.4	50.4	47.7
105°	65.4	64.7	63.9	63.2	62.4	60.9	58.8	56.7	54.6	52.5	49.7
107.5°	67.3	66.5	65.8	65.0	64.3	64.9	67.1	69.2	71.4	73.5	76.1
110°	68.1	67.2	66.4	65.7	64.9	74.1	93.2	112.4	131.5	150.6	205.9



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	68.7	68.1	67.5	66.8	66.3	100.9	170.6	240.4	310.2	379.9	393.6
115°	70.6	84.4	98.1	111.9	125.6	176.8	265.4	354.0	442.5	531.1	526.3
117.5°	288.2	333.5	378.7	424.0	469.2	502.6	524.1	545.4	566.8	588.2	585.0
120°	525.1	550.9	576.7	602.6	628.4	640.2	637.9	635.6	633.3	630.9	627.5
122.5°	655.3	660.3	665.2	670.3	675.3	677.1	675.7	674.4	673.0	671.7	667.9
125°	736.0	735.5	734.8	734.2	733.7	732.7	731.4	730.1	728.8	727.4	723.8
127.5°	786.9	786.8	786.7	786.6	786.5	785.5	783.5	781.6	779.6	777.7	775.0
130°	818.6	818.8	819.0	819.3	819.4	818.4	816.3	814.3	812.1	810.0	807.9
132.5°	849.6	849.8	850.0	850.2	850.4	849.6	847.8	846.0	844.2	842.4	840.3
135°	894.4	894.8	895.1	895.5	895.9	895.1	893.2	891.4	889.4	887.5	885.8
137.5°	935.2	935.9	936.5	937.2	937.8	937.2	935.3	933.4	931.5	929.7	927.7
140°	960.6	961.7	962.6	963.6	964.5	964.1	962.4	960.6	958.9	957.2	955.2
142.5°	985.4	986.5	987.4	988.4	989.3	989.0	987.4	985.8	984.3	982.7	980.3
145°	1020.1	1021.1	1022.0	1022.9	1023.9	1023.7	1022.4	1021.1	1019.6	1018.3	1015.1
147.5°	1050.6	1051.3	1052.2	1052.9	1053.8	1053.7	1052.6	1051.7	1050.7	1049.7	1046.5
150°	1069.1	1070.1	1071.0	1072.0	1073.0	1072.9	1071.8	1070.5	1069.4	1068.3	1065.3
152.5°	1085.0	1086.3	1087.5	1088.7	1090.1	1090.1	1088.9	1087.8	1086.7	1085.5	1082.6
155°	1107.0	1108.5	1110.0	1111.6	1113.1	1113.3	1112.2	1111.1	1109.8	1108.7	1106.5
157.5°	1127.2	1128.6	1130.1	1131.6	1133.1	1133.2	1131.9	1130.6	1129.4	1128.0	1126.4
160°	1138.9	1140.2	1141.5	1142.8	1144.2	1144.3	1143.2	1142.0	1140.9	1139.7	1138.6
162.5°	1148.5	1150.2	1151.8	1153.5	1155.1	1155.3	1154.0	1152.6	1151.3	1150.1	1149.1
165°	1163.0	1164.3	1165.6	1167.0	1168.3	1168.3	1167.0	1165.6	1164.3	1163.0	1162.4
167.5°	1172.1	1173.8	1175.5	1177.2	1178.9	1179.2	1177.8	1176.5	1175.2	1173.8	1173.3
170°	1177.6	1179.3	1181.0	1182.8	1184.5	1184.7	1183.4	1182.0	1180.6	1179.3	1178.9
172.5°	1181.8	1183.5	1185.2	1186.8	1188.6	1188.8	1187.5	1186.1	1184.8	1183.5	1183.1
175°	1185.3	1187.2	1189.2	1191.1	1193.0	1193.3	1191.9	1190.6	1189.3	1187.9	1187.5
177.5°	1187.6	1188.9	1190.3	1191.8	1193.1	1193.3	1192.2	1191.1	1190.1	1188.9	1188.8
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	571.7	570.3	569.5	566.4	563.6	560.9	560.1	560.3	556.6	553.0	551.5
5°	594.0	589.7	585.6	579.9	573.0	565.4	561.7	558.6	551.1	543.0	538.3
7.5°	613.9	607.8	599.9	589.1	579.1	567.3	559.8	553.2	542.2	530.7	523.7
10°	626.0	617.7	607.7	594.4	582.2	567.8	557.8	547.7	534.9	521.1	512.6
12.5°	636.5	625.3	615.4	598.3	583.9	565.9	554.0	539.8	526.3	510.0	501.6
15°	661.4	640.6	621.8	602.5	584.8	559.7	546.4	527.4	509.6	489.5	479.8
17.5°	680.6	657.2	627.6	603.1	582.4	554.6	535.2	512.4	491.3	468.3	455.2
20°	691.5	664.8	632.9	603.8	579.0	547.2	526.0	502.8	478.2	452.2	438.1
22.5°	698.0	670.0	638.4	601.2	572.1	541.3	514.6	489.0	464.1	436.1	421.3
25°	700.1	674.5	641.0	599.1	563.5	528.7	496.5	471.6	441.5	415.4	393.8
27.5°	689.9	671.6	639.4	595.0	553.6	512.8	477.0	448.9	417.1	388.7	366.9
30°	677.4	666.8	635.5	591.0	545.7	501.9	462.5	430.6	398.9	370.2	347.9
32.5°	658.1	655.8	628.3	585.1	537.3	488.0	447.2	415.0	379.8	351.7	330.5
35°	620.1	630.4	613.0	572.1	521.6	468.3	424.1	387.3	350.9	324.0	304.1
37.5°	569.1	594.7	590.1	553.1	500.2	446.8	398.0	359.6	324.9	297.7	278.1
40°	534.0	566.6	571.3	538.5	485.2	430.2	378.5	340.3	306.4	281.5	261.8
42.5°	496.3	534.3	547.2	521.0	468.7	412.6	361.1	321.4	287.9	263.7	246.3
45°	433.2	483.4	506.8	491.8	441.3	383.9	330.8	290.6	260.1	237.4	223.9
47.5°	374.1	429.0	460.4	455.2	410.8	353.9	301.4	262.8	233.2	215.1	203.0
50°	332.3	388.8	426.7	428.5	388.8	332.5	279.8	243.5	216.2	199.3	189.5
52.5°	296.0	350.0	391.2	400.4	364.3	310.3	260.5	224.2	200.3	184.7	176.0
55°	248.5	294.2	340.0	356.8	327.8	276.4	230.4	198.5	176.0	165.3	157.6
57.5°	206.7	244.7	287.0	305.5	287.7	243.6	200.5	172.8	154.6	145.2	139.2
60°	184.5	214.5	252.2	274.3	258.8	219.7	182.0	155.6	140.6	132.3	126.8
62.5°	164.0	190.6	222.4	242.6	234.2	197.3	163.5	140.3	127.3	119.5	115.5
65°	135.3	156.3	181.0	199.5	194.0	166.0	138.3	118.4	108.1	101.9	98.7
67.5°	111.4	126.6	143.6	159.9	155.5	135.6	113.5	97.9	90.3	84.9	82.9
70°	96.3	107.9	123.1	136.2	132.5	116.3	98.7	85.4	78.8	74.3	72.4
72.5°	82.0	91.4	103.1	113.8	111.3	97.7	83.1	73.1	68.0	63.8	62.3
75°	61.9	69.2	76.3	83.3	82.7	72.2	63.6	55.9	51.8	48.6	48.0
77.5°	45.7	49.8	54.6	58.7	57.6	51.6	44.9	40.4	37.5	35.3	35.0
80°	34.9	37.2	40.7	43.6	42.2	39.6	34.2	31.0	28.9	26.8	25.9
82.5°	25.4	27.6	29.7	31.4	30.2	27.8	24.5	22.3	21.0	19.6	19.2
85°	13.3	14.5	15.5	15.8	15.5	13.9	12.4	11.6	10.5	9.8	9.6
87.5°	8.0	7.6	7.4	7.4	6.4	5.9	4.9	4.0	4.1	4.4	4.5
90°	14.1	12.6	11.1	9.2	7.2	5.1	2.9	0.8	2.9	5.1	7.2
92.5°	18.5	17.7	16.9	16.6	16.8	17.0	17.2	17.3	17.2	17.0	16.8
95°	30.9	29.6	28.2	30.7	37.0	43.4	49.7	56.0	49.7	43.4	37.0
97.5°	38.7	35.6	32.5	39.9	57.7	75.5	93.2	111.0	93.2	75.5	57.7
100°	42.6	39.3	36.1	47.5	73.7	99.9	126.1	152.4	126.1	99.9	73.7
102.5°	104.8	132.1	159.3	175.6	181.2	186.7	192.3	197.8	192.3	186.7	181.2
105°	156.9	209.2	261.4	284.6	278.9	273.1	267.4	261.6	267.4	273.1	278.9
107.5°	198.8	261.4	324.0	353.1	348.4	343.7	339.1	334.5	339.1	343.7	348.4
110°	261.2	316.5	371.7	397.4	393.4	389.4	385.4	381.4	385.4	389.4	393.4



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	407.3	420.9	434.6	439.6	436.1	432.5	429.0	425.4	429.0	432.5	436.1
115°	521.6	516.8	512.0	507.9	504.7	501.4	498.2	494.9	498.2	501.4	504.7
117.5°	581.7	578.4	575.1	571.7	568.1	564.4	560.7	557.1	560.7	564.4	568.1
120°	624.1	620.7	617.2	614.1	611.1	608.3	605.4	602.6	605.4	608.3	611.1
122.5°	664.1	660.3	656.6	653.2	650.2	647.1	644.1	641.1	644.1	647.1	650.2
125°	720.1	716.5	712.8	709.8	707.3	704.8	702.3	699.8	702.3	704.8	707.3
127.5°	772.2	769.5	766.8	764.0	761.3	758.6	755.8	753.0	755.8	758.6	761.3
130°	805.8	803.7	801.6	799.0	796.0	792.9	789.9	786.8	789.9	792.9	796.0
132.5°	838.2	836.1	834.0	831.6	829.1	826.4	823.8	821.2	823.8	826.4	829.1
135°	884.1	882.3	880.6	878.3	875.2	872.1	869.0	866.0	869.0	872.1	875.2
137.5°	925.8	923.8	921.9	919.8	917.7	915.6	913.4	911.3	913.4	915.6	917.7
140°	953.0	950.9	948.9	947.0	945.5	944.0	942.4	940.8	942.4	944.0	945.5
142.5°	977.9	975.4	973.1	971.2	969.8	968.5	967.0	965.6	967.0	968.5	969.8
145°	1011.8	1008.6	1005.3	1003.8	1004.0	1004.2	1004.4	1004.6	1004.4	1004.2	1004.0
147.5°	1043.3	1040.0	1036.8	1035.6	1036.3	1037.1	1037.7	1038.5	1037.7	1037.1	1036.3
150°	1062.2	1059.1	1056.0	1055.2	1056.5	1057.8	1059.2	1060.5	1059.2	1057.8	1056.5
152.5°	1079.7	1076.8	1073.8	1073.2	1074.7	1076.1	1077.6	1079.1	1077.6	1076.1	1074.7
155°	1104.2	1101.8	1099.6	1099.3	1101.0	1102.7	1104.5	1106.2	1104.5	1102.7	1101.0
157.5°	1124.8	1123.2	1121.6	1121.5	1122.9	1124.5	1125.9	1127.3	1125.9	1124.5	1122.9
160°	1137.5	1136.2	1135.1	1135.1	1136.2	1137.5	1138.6	1139.7	1138.6	1137.5	1136.2
162.5°	1148.0	1147.1	1146.0	1146.1	1147.3	1148.5	1149.6	1150.8	1149.6	1148.5	1147.3
165°	1161.8	1161.2	1160.6	1160.9	1162.1	1163.3	1164.4	1165.5	1164.4	1163.3	1162.1
167.5°	1172.7	1172.2	1171.7	1172.0	1173.1	1174.3	1175.4	1176.6	1175.4	1174.3	1173.1
170°	1178.6	1178.2	1177.8	1178.2	1179.3	1180.4	1181.6	1182.8	1181.6	1180.4	1179.3
172.5°	1182.7	1182.3	1181.9	1182.3	1183.5	1184.6	1185.7	1186.8	1185.7	1184.6	1183.5
175°	1187.1	1186.8	1186.4	1186.8	1188.2	1189.6	1190.9	1192.2	1190.9	1189.6	1188.2
177.5°	1188.6	1188.5	1188.4	1188.8	1189.9	1191.0	1192.0	1193.1	1192.0	1191.0	1189.9
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	549.8	548.7	545.2	543.3	540.2	537.2	535.4	536.2	536.9	536.6	536.0
5°	534.0	529.9	523.7	518.4	514.5	507.5	504.4	502.9	501.6	500.2	498.7
7.5°	515.2	508.8	499.9	492.3	485.1	476.3	471.3	468.3	465.2	461.8	458.8
10°	501.9	492.9	483.4	472.8	464.2	456.3	449.2	444.5	440.2	436.1	433.2
12.5°	487.9	477.5	465.8	451.2	441.8	430.4	429.3	421.0	414.3	411.8	408.3
15°	465.5	450.9	436.1	418.8	411.3	401.1	394.6	388.1	382.4	378.3	377.3
17.5°	440.1	421.2	406.5	394.1	381.8	371.3	365.3	360.2	355.4	350.1	349.3
20°	420.8	404.4	388.4	377.5	364.9	354.1	346.9	341.8	337.6	334.4	331.7
22.5°	402.4	384.6	369.9	358.0	345.5	336.9	331.1	326.1	322.7	319.2	316.6
25°	373.0	359.1	343.0	329.5	319.2	313.7	309.0	304.7	302.6	300.2	297.2
27.5°	347.2	331.8	316.8	306.3	297.3	292.4	289.0	286.1	284.1	282.7	281.0
30°	329.1	313.5	301.7	291.4	283.9	279.0	276.8	275.1	272.8	271.9	271.1
32.5°	311.6	297.6	287.5	278.5	271.5	268.2	266.3	264.7	262.9	262.0	260.2
35°	286.9	275.1	265.3	260.3	254.6	251.8	250.3	248.2	246.5	245.6	245.3
37.5°	263.6	253.4	246.9	240.6	238.2	236.5	234.4	233.0	232.4	232.3	232.1
40°	248.5	240.3	234.4	229.3	228.3	225.6	223.9	222.7	222.7	222.9	222.7
42.5°	234.9	227.3	222.3	217.8	216.6	215.1	213.3	213.3	213.6	214.3	213.6
45°	214.1	208.8	205.1	203.0	200.7	199.2	198.9	199.5	199.7	200.0	200.7
47.5°	195.0	191.4	188.1	185.8	184.7	184.5	184.3	185.4	186.4	186.8	187.8
50°	183.7	179.6	176.8	175.3	174.5	174.1	174.5	175.8	176.6	177.7	178.3
52.5°	171.1	168.1	166.3	165.0	164.8	165.0	165.0	166.5	167.9	168.3	168.6
55°	153.5	151.4	151.0	149.0	149.9	149.7	150.7	151.6	152.9	154.2	154.4
57.5°	136.0	134.3	133.2	133.4	133.7	134.6	135.4	137.0	138.3	139.7	139.8
60°	124.4	123.6	122.9	122.9	123.3	124.6	125.6	127.1	128.0	128.9	129.5
62.5°	113.8	112.9	112.3	112.6	113.8	114.5	115.7	116.6	117.4	118.3	118.6
65°	97.0	96.6	97.2	97.6	97.8	98.9	100.4	101.0	101.9	102.4	103.9
67.5°	81.5	81.6	81.5	82.1	83.4	83.6	85.0	86.5	86.7	87.6	88.5
70°	71.1	71.5	71.9	72.4	73.4	73.9	74.9	75.6	76.4	77.1	77.8
72.5°	61.5	61.5	62.0	61.9	62.9	63.7	64.7	65.3	66.2	67.0	67.6
75°	47.3	47.3	47.8	48.0	49.0	50.1	49.9	50.3	51.2	52.0	52.5
77.5°	34.6	34.1	34.6	34.8	35.2	36.0	36.2	36.8	37.8	37.5	38.0
80°	26.3	25.7	26.3	26.6	26.6	27.6	27.6	28.1	28.7	28.1	28.7
82.5°	18.8	18.5	18.9	19.0	19.3	19.4	19.7	19.8	20.5	20.2	20.5
85°	9.4	9.2	9.4	9.2	9.4	9.6	9.6	9.4	9.4	9.8	9.2
87.5°	4.8	5.0	5.1	5.4	5.6	5.7	5.7	5.8	6.0	5.9	6.0
90°	9.2	11.1	12.6	14.1	15.6	17.2	18.2	19.1	20.1	21.0	21.7
92.5°	16.6	16.9	17.7	18.5	19.2	20.0	20.5	20.9	21.5	22.0	22.3
95°	30.7	28.2	29.6	30.9	32.2	33.6	34.5	35.4	36.5	37.4	37.8
97.5°	39.9	32.5	35.6	38.7	41.8	45.0	45.7	46.5	47.2	48.0	48.4
100°	47.5	36.1	39.3	42.6	45.8	49.1	50.6	52.1	53.6	55.2	56.2
102.5°	175.6	159.3	132.1	104.8	77.7	50.4	52.4	54.4	56.5	58.4	59.7
105°	284.6	261.4	209.2	156.9	104.7	52.5	54.6	56.7	58.8	60.9	62.4
107.5°	353.1	324.0	261.4	198.8	136.1	73.5	71.4	69.2	67.1	64.9	64.3
110°	397.4	371.7	316.5	261.2	205.9	150.6	131.5	112.4	93.2	74.1	64.9



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	439.6	434.6	420.9	407.3	393.6	379.9	310.2	240.4	170.6	100.9	66.3
115°	507.9	512.0	516.8	521.6	526.3	531.1	442.5	354.0	265.4	176.8	125.6
117.5°	571.7	575.1	578.4	581.7	585.0	588.2	566.8	545.4	524.1	502.6	469.2
120°	614.1	617.2	620.7	624.1	627.5	630.9	633.3	635.6	637.9	640.2	628.4
122.5°	653.2	656.6	660.3	664.1	667.9	671.7	673.0	674.4	675.7	677.1	675.3
125°	709.8	712.8	716.5	720.1	723.8	727.4	728.8	730.1	731.4	732.7	733.7
127.5°	764.0	766.8	769.5	772.2	775.0	777.7	779.6	781.6	783.5	785.5	786.5
130°	799.0	801.6	803.7	805.8	807.9	810.0	812.1	814.3	816.3	818.4	819.4
132.5°	831.6	834.0	836.1	838.2	840.3	842.4	844.2	846.0	847.8	849.6	850.4
135°	878.3	880.6	882.3	884.1	885.8	887.5	889.4	891.4	893.2	895.1	895.9
137.5°	919.8	921.9	923.8	925.8	927.7	929.7	931.5	933.4	935.3	937.2	937.8
140°	947.0	948.9	950.9	953.0	955.2	957.2	958.9	960.6	962.4	964.1	964.5
142.5°	971.2	973.1	975.4	977.9	980.3	982.7	984.3	985.8	987.4	989.0	989.3
145°	1003.8	1005.3	1008.6	1011.8	1015.1	1018.3	1019.6	1021.1	1022.4	1023.7	1023.9
147.5°	1035.6	1036.8	1040.0	1043.3	1046.5	1049.7	1050.7	1051.7	1052.6	1053.7	1053.8
150°	1055.2	1056.0	1059.1	1062.2	1065.3	1068.3	1069.4	1070.5	1071.8	1072.9	1073.0
152.5°	1073.2	1073.8	1076.8	1079.7	1082.6	1085.5	1086.7	1087.8	1088.9	1090.1	1090.1
155°	1099.3	1099.6	1101.8	1104.2	1106.5	1108.7	1109.8	1111.1	1112.2	1113.3	1113.1
157.5°	1121.5	1121.6	1123.2	1124.8	1126.4	1128.0	1129.4	1130.6	1131.9	1133.2	1133.1
160°	1135.1	1135.1	1136.2	1137.5	1138.6	1139.7	1140.9	1142.0	1143.2	1144.3	1144.2
162.5°	1146.1	1146.0	1147.1	1148.0	1149.1	1150.1	1151.3	1152.6	1154.0	1155.3	1155.1
165°	1160.9	1160.6	1161.2	1161.8	1162.4	1163.0	1164.3	1165.6	1167.0	1168.3	1168.3
167.5°	1172.0	1171.7	1172.2	1172.7	1173.3	1173.8	1175.2	1176.5	1177.8	1179.2	1178.9
170°	1178.2	1177.8	1178.2	1178.6	1178.9	1179.3	1180.6	1182.0	1183.4	1184.7	1184.5
172.5°	1182.3	1181.9	1182.3	1182.7	1183.1	1183.5	1184.8	1186.1	1187.5	1188.8	1188.6
175°	1186.8	1186.4	1186.8	1187.1	1187.5	1187.9	1189.3	1190.6	1191.9	1193.3	1193.0
177.5°	1188.8	1188.4	1188.5	1188.6	1188.8	1188.9	1190.1	1191.1	1192.2	1193.3	1193.1
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	534.3	534.0	534.0	532.4	534.0	534.0	534.3	536.0	536.6	536.9	536.2
5°	495.7	495.0	494.0	495.0	494.0	495.0	495.7	498.7	500.2	501.6	502.9
7.5°	457.4	454.9	454.5	451.9	454.5	454.9	457.4	458.8	461.8	465.2	468.3
10°	429.5	427.8	427.5	423.5	427.5	427.8	429.5	433.2	436.1	440.2	444.5
12.5°	408.3	404.2	405.0	402.7	405.0	404.2	408.3	408.3	411.8	414.3	421.0
15°	371.5	371.5	370.6	367.0	370.6	371.5	371.5	377.3	378.3	382.4	388.1
17.5°	345.1	344.6	342.6	343.7	342.6	344.6	345.1	349.3	350.1	355.4	360.2
20°	329.3	328.0	325.5	325.5	325.5	328.0	329.3	331.7	334.4	337.6	341.8
22.5°	314.4	314.3	311.6	312.5	311.6	314.3	314.4	316.6	319.2	322.7	326.1
25°	297.0	295.3	294.0	294.6	294.0	295.3	297.0	297.2	300.2	302.6	304.7
27.5°	280.4	279.5	279.4	277.7	279.4	279.5	280.4	281.0	282.7	284.1	286.1
30°	270.9	268.7	269.1	268.1	269.1	268.7	270.9	271.1	271.9	272.8	275.1
32.5°	259.9	259.1	258.7	257.8	258.7	259.1	259.9	260.2	262.0	262.9	264.7
35°	245.0	245.2	244.1	244.5	244.1	245.2	245.0	245.3	245.6	246.5	248.2
37.5°	231.9	232.5	232.1	232.1	232.1	232.5	231.9	232.1	232.3	232.4	233.0
40°	223.3	223.3	223.3	223.9	223.3	223.3	223.3	222.7	222.9	222.7	222.7
42.5°	215.1	214.7	214.4	214.3	214.4	214.7	215.1	213.6	214.3	213.6	213.3
45°	201.0	201.7	201.9	200.9	201.9	201.7	201.0	200.7	200.0	199.7	199.5
47.5°	188.3	188.4	188.3	189.3	188.3	188.4	188.3	187.8	186.8	186.4	185.4
50°	179.5	179.0	179.5	179.0	179.5	179.0	179.5	178.3	177.7	176.6	175.8
52.5°	170.0	170.1	169.8	169.8	169.8	170.1	170.0	168.6	168.3	167.9	166.5
55°	155.2	155.6	155.4	155.4	155.4	155.6	155.2	154.4	154.2	152.9	151.6
57.5°	140.0	140.3	140.6	139.7	140.6	140.3	140.0	139.8	139.7	138.3	137.0
60°	129.3	130.4	130.2	129.8	130.2	130.4	129.3	129.5	128.9	128.0	127.1
62.5°	119.5	120.0	119.9	119.8	119.9	120.0	119.5	118.6	118.3	117.4	116.6
65°	104.5	104.9	104.2	104.9	104.2	104.9	104.5	103.9	102.4	101.9	101.0
67.5°	88.2	88.4	88.9	89.2	88.9	88.4	88.2	88.5	87.6	86.7	86.5
70°	78.1	77.9	78.6	79.3	78.6	77.9	78.1	77.8	77.1	76.4	75.6
72.5°	67.5	68.0	67.8	68.2	67.8	68.0	67.5	67.6	67.0	66.2	65.3
75°	52.0	52.7	52.5	53.1	52.5	52.7	52.0	52.5	52.0	51.2	50.3
77.5°	37.6	37.7	37.6	38.0	37.6	37.7	37.6	38.0	37.5	37.8	36.8
80°	28.7	28.3	27.8	28.7	27.8	28.3	28.7	28.7	28.1	28.7	28.1
82.5°	20.0	20.2	19.8	19.8	19.8	20.2	20.0	20.5	20.2	20.5	19.8
85°	9.2	9.0	8.6	8.6	8.6	9.0	9.2	9.2	9.8	9.4	9.4
87.5°	6.1	6.0	6.1	6.0	6.1	6.0	6.1	6.0	5.9	6.0	5.8
90°	22.1	22.4	22.9	23.3	22.9	22.4	22.1	21.7	21.0	20.1	19.1
92.5°	22.5	22.8	23.0	23.3	23.0	22.8	22.5	22.3	22.0	21.5	20.9
95°	37.6	37.4	37.2	37.0	37.2	37.4	37.6	37.8	37.4	36.5	35.4
97.5°	48.7	48.9	49.2	49.4	49.2	48.9	48.7	48.4	48.0	47.2	46.5
100°	56.6	56.9	57.3	57.7	57.3	56.9	56.6	56.2	55.2	53.6	52.1
102.5°	60.2	60.7	61.3	61.8	61.3	60.7	60.2	59.7	58.4	56.5	54.4
105°	63.2	63.9	64.7	65.4	64.7	63.9	63.2	62.4	60.9	58.8	56.7
107.5°	65.0	65.8	66.5	67.3	66.5	65.8	65.0	64.3	64.9	67.1	69.2
110°	65.7	66.4	67.2	68.1	67.2	66.4	65.7	64.9	74.1	93.2	112.4



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	66.8	67.5	68.1	68.7	68.1	67.5	66.8	66.3	100.9	170.6	240.4
115°	111.9	98.1	84.4	70.6	84.4	98.1	111.9	125.6	176.8	265.4	354.0
117.5°	424.0	378.7	333.5	288.2	333.5	378.7	424.0	469.2	502.6	524.1	545.4
120°	602.6	576.7	550.9	525.1	550.9	576.7	602.6	628.4	640.2	637.9	635.6
122.5°	670.3	665.2	660.3	655.3	660.3	665.2	670.3	675.3	677.1	675.7	674.4
125°	734.2	734.8	735.5	736.0	735.5	734.8	734.2	733.7	732.7	731.4	730.1
127.5°	786.6	786.7	786.8	786.9	786.8	786.7	786.6	786.5	785.5	783.5	781.6
130°	819.3	819.0	818.8	818.6	818.8	819.0	819.3	819.4	818.4	816.3	814.3
132.5°	850.2	850.0	849.8	849.6	849.8	850.0	850.2	850.4	849.6	847.8	846.0
135°	895.5	895.1	894.8	894.4	894.8	895.1	895.5	895.9	895.1	893.2	891.4
137.5°	937.2	936.5	935.9	935.2	935.9	936.5	937.2	937.8	937.2	935.3	933.4
140°	963.6	962.6	961.7	960.6	961.7	962.6	963.6	964.5	964.1	962.4	960.6
142.5°	988.4	987.4	986.5	985.4	986.5	987.4	988.4	989.3	989.0	987.4	985.8
145°	1022.9	1022.0	1021.1	1020.1	1021.1	1022.0	1022.9	1023.9	1023.7	1022.4	1021.1
147.5°	1052.9	1052.2	1051.3	1050.6	1051.3	1052.2	1052.9	1053.8	1053.7	1052.6	1051.7
150°	1072.0	1071.0	1070.1	1069.1	1070.1	1071.0	1072.0	1073.0	1072.9	1071.8	1070.5
152.5°	1088.7	1087.5	1086.3	1085.0	1086.3	1087.5	1088.7	1090.1	1090.1	1088.9	1087.8
155°	1111.6	1110.0	1108.5	1107.0	1108.5	1110.0	1111.6	1113.1	1113.3	1112.2	1111.1
157.5°	1131.6	1130.1	1128.6	1127.2	1128.6	1130.1	1131.6	1133.1	1133.2	1131.9	1130.6
160°	1142.8	1141.5	1140.2	1138.9	1140.2	1141.5	1142.8	1144.2	1144.3	1143.2	1142.0
162.5°	1153.5	1151.8	1150.2	1148.5	1150.2	1151.8	1153.5	1155.1	1155.3	1154.0	1152.6
165°	1167.0	1165.6	1164.3	1163.0	1164.3	1165.6	1167.0	1168.3	1168.3	1167.0	1165.6
167.5°	1177.2	1175.5	1173.8	1172.1	1173.8	1175.5	1177.2	1178.9	1179.2	1177.8	1176.5
170°	1182.8	1181.0	1179.3	1177.6	1179.3	1181.0	1182.8	1184.5	1184.7	1183.4	1182.0
172.5°	1186.8	1185.2	1183.5	1181.8	1183.5	1185.2	1186.8	1188.6	1188.8	1187.5	1186.1
175°	1191.1	1189.2	1187.2	1185.3	1187.2	1189.2	1191.1	1193.0	1193.3	1191.9	1190.6
177.5°	1191.8	1190.3	1188.9	1187.6	1188.9	1190.3	1191.8	1193.1	1193.3	1192.2	1191.1
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	535.4	537.2	540.2	543.3	545.2	548.7	549.8	551.5	553.0	556.6	560.3
5°	504.4	507.5	514.5	518.4	523.7	529.9	534.0	538.3	543.0	551.1	558.6
7.5°	471.3	476.3	485.1	492.3	499.9	508.8	515.2	523.7	530.7	542.2	553.2
10°	449.2	456.3	464.2	472.8	483.4	492.9	501.9	512.6	521.1	534.9	547.7
12.5°	429.3	430.4	441.8	451.2	465.8	477.5	487.9	501.6	510.0	526.3	539.8
15°	394.6	401.1	411.3	418.8	436.1	450.9	465.5	479.8	489.5	509.6	527.4
17.5°	365.3	371.3	381.8	394.1	406.5	421.2	440.1	455.2	468.3	491.3	512.4
20°	346.9	354.1	364.9	377.5	388.4	404.4	420.8	438.1	452.2	478.2	502.8
22.5°	331.1	336.9	345.5	358.0	369.9	384.6	402.4	421.3	436.1	464.1	489.0
25°	309.0	313.7	319.2	329.5	343.0	359.1	373.0	393.8	415.4	441.5	471.6
27.5°	289.0	292.4	297.3	306.3	316.8	331.8	347.2	366.9	388.7	417.1	448.9
30°	276.8	279.0	283.9	291.4	301.7	313.5	329.1	347.9	370.2	398.9	430.6
32.5°	266.3	268.2	271.5	278.5	287.5	297.6	311.6	330.5	351.7	379.8	415.0
35°	250.3	251.8	254.6	260.3	265.3	275.1	286.9	304.1	324.0	350.9	387.3
37.5°	234.4	236.5	238.2	240.6	246.9	253.4	263.6	278.1	297.7	324.9	359.6
40°	223.9	225.6	228.3	229.3	234.4	240.3	248.5	261.8	281.5	306.4	340.3
42.5°	213.3	215.1	216.6	217.8	222.3	227.3	234.9	246.3	263.7	287.9	321.4
45°	198.9	199.2	200.7	203.0	205.1	208.8	214.1	223.9	237.4	260.1	290.6
47.5°	184.3	184.5	184.7	185.8	188.1	191.4	195.0	203.0	215.1	233.2	262.8
50°	174.5	174.1	174.5	175.3	176.8	179.6	183.7	189.5	199.3	216.2	243.5
52.5°	165.0	165.0	164.8	165.0	166.3	168.1	171.1	176.0	184.7	200.3	224.2
55°	150.7	149.7	149.9	149.0	151.0	151.4	153.5	157.6	165.3	176.0	198.5
57.5°	135.4	134.6	133.7	133.4	133.2	134.3	136.0	139.2	145.2	154.6	172.8
60°	125.6	124.6	123.3	122.9	122.9	123.6	124.4	126.8	132.3	140.6	155.6
62.5°	115.7	114.5	113.8	112.6	112.3	112.9	113.8	115.5	119.5	127.3	140.3
65°	100.4	98.9	97.8	97.6	97.2	96.6	97.0	98.7	101.9	108.1	118.4
67.5°	85.0	83.6	83.4	82.1	81.5	81.6	81.5	82.9	84.9	90.3	97.9
70°	74.9	73.9	73.4	72.4	71.9	71.5	71.1	72.4	74.3	78.8	85.4
72.5°	64.7	63.7	62.9	61.9	62.0	61.5	61.5	62.3	63.8	68.0	73.1
75°	49.9	50.1	49.0	48.0	47.8	47.3	47.3	48.0	48.6	51.8	55.9
77.5°	36.2	36.0	35.2	34.8	34.6	34.1	34.6	35.0	35.3	37.5	40.4
80°	27.6	27.6	26.6	26.6	26.3	25.7	26.3	25.9	26.8	28.9	31.0
82.5°	19.7	19.4	19.3	19.0	18.9	18.5	18.8	19.2	19.6	21.0	22.3
85°	9.6	9.6	9.4	9.2	9.4	9.2	9.4	9.6	9.8	10.5	11.6
87.5°	5.7	5.7	5.6	5.4	5.1	5.0	4.8	4.5	4.4	4.1	4.0
90°	18.2	17.2	15.6	14.1	12.6	11.1	9.2	7.2	5.1	2.9	0.8
92.5°	20.5	20.0	19.2	18.5	17.7	16.9	16.6	16.8	17.0	17.2	17.3
95°	34.5	33.6	32.2	30.9	29.6	28.2	30.7	37.0	43.4	49.7	56.0
97.5°	45.7	45.0	41.8	38.7	35.6	32.5	39.9	57.7	75.5	93.2	111.0
100°	50.6	49.1	45.8	42.6	39.3	36.1	47.5	73.7	99.9	126.1	152.4
102.5°	52.4	50.4	77.7	104.8	132.1	159.3	175.6	181.2	186.7	192.3	197.8
105°	54.6	52.5	104.7	156.9	209.2	261.4	284.6	278.9	273.1	267.4	261.6
107.5°	71.4	73.5	136.1	198.8	261.4	324.0	353.1	348.4	343.7	339.1	334.5
110°	131.5	150.6	205.9	261.2	316.5	371.7	397.4	393.4	389.4	385.4	381.4



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	310.2	379.9	393.6	407.3	420.9	434.6	439.6	436.1	432.5	429.0	425.4
115°	442.5	531.1	526.3	521.6	516.8	512.0	507.9	504.7	501.4	498.2	494.9
117.5°	566.8	588.2	585.0	581.7	578.4	575.1	571.7	568.1	564.4	560.7	557.1
120°	633.3	630.9	627.5	624.1	620.7	617.2	614.1	611.1	608.3	605.4	602.6
122.5°	673.0	671.7	667.9	664.1	660.3	656.6	653.2	650.2	647.1	644.1	641.1
125°	728.8	727.4	723.8	720.1	716.5	712.8	709.8	707.3	704.8	702.3	699.8
127.5°	779.6	777.7	775.0	772.2	769.5	766.8	764.0	761.3	758.6	755.8	753.0
130°	812.1	810.0	807.9	805.8	803.7	801.6	799.0	796.0	792.9	789.9	786.8
132.5°	844.2	842.4	840.3	838.2	836.1	834.0	831.6	829.1	826.4	823.8	821.2
135°	889.4	887.5	885.8	884.1	882.3	880.6	878.3	875.2	872.1	869.0	866.0
137.5°	931.5	929.7	927.7	925.8	923.8	921.9	919.8	917.7	915.6	913.4	911.3
140°	958.9	957.2	955.2	953.0	950.9	948.9	947.0	945.5	944.0	942.4	940.8
142.5°	984.3	982.7	980.3	977.9	975.4	973.1	971.2	969.8	968.5	967.0	965.6
145°	1019.6	1018.3	1015.1	1011.8	1008.6	1005.3	1003.8	1004.0	1004.2	1004.4	1004.6
147.5°	1050.7	1049.7	1046.5	1043.3	1040.0	1036.8	1035.6	1036.3	1037.1	1037.7	1038.5
150°	1069.4	1068.3	1065.3	1062.2	1059.1	1056.0	1055.2	1056.5	1057.8	1059.2	1060.5
152.5°	1086.7	1085.5	1082.6	1079.7	1076.8	1073.8	1073.2	1074.7	1076.1	1077.6	1079.1
155°	1109.8	1108.7	1106.5	1104.2	1101.8	1099.6	1099.3	1101.0	1102.7	1104.5	1106.2
157.5°	1129.4	1128.0	1126.4	1124.8	1123.2	1121.6	1121.5	1122.9	1124.5	1125.9	1127.3
160°	1140.9	1139.7	1138.6	1137.5	1136.2	1135.1	1135.1	1136.2	1137.5	1138.6	1139.7
162.5°	1151.3	1150.1	1149.1	1148.0	1147.1	1146.0	1146.1	1147.3	1148.5	1149.6	1150.8
165°	1164.3	1163.0	1162.4	1161.8	1161.2	1160.6	1160.9	1162.1	1163.3	1164.4	1165.5
167.5°	1175.2	1173.8	1173.3	1172.7	1172.2	1171.7	1172.0	1173.1	1174.3	1175.4	1176.6
170°	1180.6	1179.3	1178.9	1178.6	1178.2	1177.8	1178.2	1179.3	1180.4	1181.6	1182.8
172.5°	1184.8	1183.5	1183.1	1182.7	1182.3	1181.9	1182.3	1183.5	1184.6	1185.7	1186.8
175°	1189.3	1187.9	1187.5	1187.1	1186.8	1186.4	1186.8	1188.2	1189.6	1190.9	1192.2
177.5°	1190.1	1188.9	1188.8	1188.6	1188.5	1188.4	1188.8	1189.9	1191.0	1192.0	1193.1
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	560.1	560.9	563.6	566.4	569.5	570.3	571.7	570.5	570.1	573.3	575.8
5°	561.7	565.4	573.0	579.9	585.6	589.7	594.0	595.7	598.9	603.3	609.0
7.5°	559.8	567.3	579.1	589.1	599.9	607.8	613.9	619.2	625.5	634.0	643.3
10°	557.8	567.8	582.2	594.4	607.7	617.7	626.0	634.2	643.7	655.4	667.6
12.5°	554.0	565.9	583.9	598.3	615.4	625.3	636.5	654.0	664.2	680.6	697.8
15°	546.4	559.7	584.8	602.5	621.8	640.6	661.4	678.1	694.7	704.5	728.6
17.5°	535.2	554.6	582.4	603.1	627.6	657.2	680.6	699.6	718.8	734.4	746.6
20°	526.0	547.2	579.0	603.8	632.9	664.8	691.5	710.9	727.5	740.6	748.1
22.5°	514.6	541.3	572.1	601.2	638.4	670.0	698.0	713.2	727.2	733.6	736.5
25°	496.5	528.7	563.5	599.1	641.0	674.5	700.1	709.4	713.4	707.2	696.9
27.5°	477.0	512.8	553.6	595.0	639.4	671.6	689.9	688.5	681.6	661.5	645.5
30°	462.5	501.9	545.7	591.0	635.5	666.8	677.4	666.8	651.1	628.7	605.7
32.5°	447.2	488.0	537.3	585.1	628.3	655.8	658.1	639.7	615.5	589.9	561.4
35°	424.1	468.3	521.6	572.1	613.0	630.4	620.1	587.5	558.8	524.0	484.9
37.5°	398.0	446.8	500.2	553.1	590.1	594.7	569.1	534.9	494.4	453.4	407.5
40°	378.5	430.2	485.2	538.5	571.3	566.6	534.0	496.3	448.2	398.0	355.4
42.5°	361.1	412.6	468.7	521.0	547.2	534.3	496.3	450.1	398.3	351.1	312.1
45°	330.8	383.9	441.3	491.8	506.8	483.4	433.2	381.7	330.8	291.4	260.6
47.5°	301.4	353.9	410.8	455.2	460.4	429.0	374.1	321.2	277.4	245.3	223.6
50°	279.8	332.5	388.8	428.5	426.7	388.8	332.3	282.0	245.3	219.4	204.9
52.5°	260.5	310.3	364.3	400.4	391.2	350.0	296.0	251.3	221.2	201.0	187.8
55°	230.4	276.4	327.8	356.8	340.0	294.2	248.5	212.6	190.3	175.1	164.9
57.5°	200.5	243.6	287.7	305.5	287.0	244.7	206.7	180.6	163.8	152.6	145.9
60°	182.0	219.7	258.8	274.3	252.2	214.5	184.5	161.3	147.7	138.6	132.5
62.5°	163.5	197.3	234.2	242.6	222.4	190.6	164.0	144.6	133.6	125.4	119.7
65°	138.3	166.0	194.0	199.5	181.0	156.3	135.3	122.7	112.8	106.9	102.4
67.5°	113.5	135.6	155.5	159.9	143.6	126.6	111.4	100.4	93.8	88.8	84.9
70°	98.7	116.3	132.5	136.2	123.1	107.9	96.3	87.6	81.5	77.3	73.6
72.5°	83.1	97.7	111.3	113.8	103.1	91.4	82.0	75.0	69.7	67.0	63.5
75°	63.6	72.2	82.7	83.3	76.3	69.2	61.9	57.4	54.6	51.2	49.5
77.5°	44.9	51.6	57.6	58.7	54.6	49.8	45.7	42.1	39.8	38.2	36.6
80°	34.2	39.6	42.2	43.6	40.7	37.2	34.9	32.5	31.0	30.0	28.9
82.5°	24.5	27.8	30.2	31.4	29.7	27.6	25.4	23.9	22.8	22.0	21.6
85°	12.4	13.9	15.5	15.8	15.5	14.5	13.3	13.3	12.6	12.4	12.4
87.5°	4.9	5.9	6.4	7.4	7.4	7.6	8.0	8.1	8.2	8.3	8.3
90°	2.9	5.1	7.2	9.2	11.1	12.6	14.1	15.6	17.2	18.2	19.1
92.5°	17.2	17.0	16.8	16.6	16.9	17.7	18.5	19.2	20.0	20.5	20.9
95°	49.7	43.4	37.0	30.7	28.2	29.6	30.9	32.2	33.6	34.5	35.4
97.5°	93.2	75.5	57.7	39.9	32.5	35.6	38.7	41.8	45.0	45.7	46.5
100°	126.1	99.9	73.7	47.5	36.1	39.3	42.6	45.8	49.1	50.6	52.1
102.5°	192.3	186.7	181.2	175.6	159.3	132.1	104.8	77.7	50.4	52.4	54.4
105°	267.4	273.1	278.9	284.6	261.4	209.2	156.9	104.7	52.5	54.6	56.7
107.5°	339.1	343.7	348.4	353.1	324.0	261.4	198.8	136.1	73.5	71.4	69.2
110°	385.4	389.4	393.4	397.4	371.7	316.5	261.2	205.9	150.6	131.5	112.4



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	429.0	432.5	436.1	439.6	434.6	420.9	407.3	393.6	379.9	310.2	240.4
115°	498.2	501.4	504.7	507.9	512.0	516.8	521.6	526.3	531.1	442.5	354.0
117.5°	560.7	564.4	568.1	571.7	575.1	578.4	581.7	585.0	588.2	566.8	545.4
120°	605.4	608.3	611.1	614.1	617.2	620.7	624.1	627.5	630.9	633.3	635.6
122.5°	644.1	647.1	650.2	653.2	656.6	660.3	664.1	667.9	671.7	673.0	674.4
125°	702.3	704.8	707.3	709.8	712.8	716.5	720.1	723.8	727.4	728.8	730.1
127.5°	755.8	758.6	761.3	764.0	766.8	769.5	772.2	775.0	777.7	779.6	781.6
130°	789.9	792.9	796.0	799.0	801.6	803.7	805.8	807.9	810.0	812.1	814.3
132.5°	823.8	826.4	829.1	831.6	834.0	836.1	838.2	840.3	842.4	844.2	846.0
135°	869.0	872.1	875.2	878.3	880.6	882.3	884.1	885.8	887.5	889.4	891.4
137.5°	913.4	915.6	917.7	919.8	921.9	923.8	925.8	927.7	929.7	931.5	933.4
140°	942.4	944.0	945.5	947.0	948.9	950.9	953.0	955.2	957.2	958.9	960.6
142.5°	967.0	968.5	969.8	971.2	973.1	975.4	977.9	980.3	982.7	984.3	985.8
145°	1004.4	1004.2	1004.0	1003.8	1005.3	1008.6	1011.8	1015.1	1018.3	1019.6	1021.1
147.5°	1037.7	1037.1	1036.3	1035.6	1036.8	1040.0	1043.3	1046.5	1049.7	1050.7	1051.7
150°	1059.2	1057.8	1056.5	1055.2	1056.0	1059.1	1062.2	1065.3	1068.3	1069.4	1070.5
152.5°	1077.6	1076.1	1074.7	1073.2	1073.8	1076.8	1079.7	1082.6	1085.5	1086.7	1087.8
155°	1104.5	1102.7	1101.0	1099.3	1099.6	1101.8	1104.2	1106.5	1108.7	1109.8	1111.1
157.5°	1125.9	1124.5	1122.9	1121.5	1121.6	1123.2	1124.8	1126.4	1128.0	1129.4	1130.6
160°	1138.6	1137.5	1136.2	1135.1	1135.1	1136.2	1137.5	1138.6	1139.7	1140.9	1142.0
162.5°	1149.6	1148.5	1147.3	1146.1	1146.0	1147.1	1148.0	1149.1	1150.1	1151.3	1152.6
165°	1164.4	1163.3	1162.1	1160.9	1160.6	1161.2	1161.8	1162.4	1163.0	1164.3	1165.6
167.5°	1175.4	1174.3	1173.1	1172.0	1171.7	1172.2	1172.7	1173.3	1173.8	1175.2	1176.5
170°	1181.6	1180.4	1179.3	1178.2	1177.8	1178.2	1178.6	1178.9	1179.3	1180.6	1182.0
172.5°	1185.7	1184.6	1183.5	1182.3	1181.9	1182.3	1182.7	1183.1	1183.5	1184.8	1186.1
175°	1190.9	1189.6	1188.2	1186.8	1186.4	1186.8	1187.1	1187.5	1187.9	1189.3	1190.6
177.5°	1192.0	1191.0	1189.9	1188.8	1188.4	1188.5	1188.6	1188.8	1188.9	1190.1	1191.1
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	557.1	557.1	557.1	557.1	557.1	557.1	557.1
2.5°	577.9	580.2	580.2	580.6	583.3	583.0	582.8
5°	614.9	618.6	619.0	622.8	625.4	624.5	622.2
7.5°	649.9	656.7	661.9	664.7	668.1	670.1	669.2
10°	677.7	687.5	693.5	697.6	702.5	706.2	704.8
12.5°	702.9	714.5	722.8	729.8	730.4	735.1	731.9
15°	742.2	754.5	755.8	760.9	765.1	764.6	764.8
17.5°	755.1	759.0	759.9	760.0	760.1	758.6	755.3
20°	750.5	748.9	745.4	742.5	737.6	737.0	732.7
22.5°	728.5	723.8	714.6	708.6	701.0	699.0	697.8
25°	685.4	674.9	660.3	646.4	642.5	635.1	637.2
27.5°	626.1	609.8	594.0	582.8	572.5	561.3	564.5
30°	584.6	566.1	543.8	526.7	515.8	505.1	503.1
32.5°	534.9	507.8	483.1	468.0	451.2	444.4	437.1
35°	449.2	422.8	398.2	377.0	364.9	355.4	346.9
37.5°	372.2	341.9	322.0	304.8	296.0	290.6	292.0
40°	324.4	297.8	283.2	270.2	262.0	258.3	259.1
42.5°	285.7	265.8	253.8	244.9	239.1	237.0	236.5
45°	241.8	230.6	220.7	215.7	212.8	210.5	209.0
47.5°	211.8	202.6	197.1	194.1	191.6	189.3	189.2
50°	193.8	187.8	183.9	180.7	178.8	177.1	178.6
52.5°	180.0	174.6	170.7	167.9	167.1	165.6	165.5
55°	159.8	155.4	152.7	150.1	148.8	148.0	146.8
57.5°	141.2	137.1	134.6	133.0	130.5	129.7	129.3
60°	128.0	124.8	122.2	120.1	119.0	117.3	117.3
62.5°	115.8	112.6	110.3	108.7	106.9	106.2	106.4
65°	98.3	95.7	93.3	91.6	91.2	89.9	90.4
67.5°	82.1	80.4	77.9	76.9	76.2	75.5	74.9
70°	71.3	69.6	68.3	67.0	66.4	66.4	66.4
72.5°	62.2	60.1	59.4	57.8	58.2	57.5	56.7
75°	48.2	46.8	46.3	45.6	44.6	44.6	44.6
77.5°	35.4	35.1	34.3	33.6	33.4	33.2	33.3
80°	27.4	27.1	26.8	26.8	26.3	26.1	25.7
82.5°	21.1	20.5	20.3	20.1	20.0	20.0	19.9
85°	12.0	11.6	11.6	11.8	11.3	11.3	11.6
87.5°	8.7	8.9	8.8	8.9	9.1	9.0	9.1
90°	20.1	21.0	21.7	22.1	22.4	22.9	23.3
92.5°	21.5	22.0	22.3	22.5	22.8	23.0	23.3
95°	36.5	37.4	37.8	37.6	37.4	37.2	37.0
97.5°	47.2	48.0	48.4	48.7	48.9	49.2	49.4
100°	53.6	55.2	56.2	56.6	56.9	57.3	57.7
102.5°	56.5	58.4	59.7	60.2	60.7	61.3	61.8
105°	58.8	60.9	62.4	63.2	63.9	64.7	65.4
107.5°	67.1	64.9	64.3	65.0	65.8	66.5	67.3
110°	93.2	74.1	64.9	65.7	66.4	67.2	68.1



TEST NUMBER: P331267-830

CATALOG NUMBER: S122DIP-S290D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	170.6	100.9	66.3	66.8	67.5	68.1	68.7
115°	265.4	176.8	125.6	111.9	98.1	84.4	70.6
117.5°	524.1	502.6	469.2	424.0	378.7	333.5	288.2
120°	637.9	640.2	628.4	602.6	576.7	550.9	525.1
122.5°	675.7	677.1	675.3	670.3	665.2	660.3	655.3
125°	731.4	732.7	733.7	734.2	734.8	735.5	736.0
127.5°	783.5	785.5	786.5	786.6	786.7	786.8	786.9
130°	816.3	818.4	819.4	819.3	819.0	818.8	818.6
132.5°	847.8	849.6	850.4	850.2	850.0	849.8	849.6
135°	893.2	895.1	895.9	895.5	895.1	894.8	894.4
137.5°	935.3	937.2	937.8	937.2	936.5	935.9	935.2
140°	962.4	964.1	964.5	963.6	962.6	961.7	960.6
142.5°	987.4	989.0	989.3	988.4	987.4	986.5	985.4
145°	1022.4	1023.7	1023.9	1022.9	1022.0	1021.1	1020.1
147.5°	1052.6	1053.7	1053.8	1052.9	1052.2	1051.3	1050.6
150°	1071.8	1072.9	1073.0	1072.0	1071.0	1070.1	1069.1
152.5°	1088.9	1090.1	1090.1	1088.7	1087.5	1086.3	1085.0
155°	1112.2	1113.3	1113.1	1111.6	1110.0	1108.5	1107.0
157.5°	1131.9	1133.2	1133.1	1131.6	1130.1	1128.6	1127.2
160°	1143.2	1144.3	1144.2	1142.8	1141.5	1140.2	1138.9
162.5°	1154.0	1155.3	1155.1	1153.5	1151.8	1150.2	1148.5
165°	1167.0	1168.3	1168.3	1167.0	1165.6	1164.3	1163.0
167.5°	1177.8	1179.2	1178.9	1177.2	1175.5	1173.8	1172.1
170°	1183.4	1184.7	1184.5	1182.8	1181.0	1179.3	1177.6
172.5°	1187.5	1188.8	1188.6	1186.8	1185.2	1183.5	1181.8
175°	1191.9	1193.3	1193.0	1191.1	1189.2	1187.2	1185.3
177.5°	1192.2	1193.3	1193.1	1191.8	1190.3	1188.9	1187.6
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7

(END OF REPORT)