

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331359-830

Luminaire Tested: **S122DIP-S675D925U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331359-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D925U830-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6170.3 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45					45			
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39					39			
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33					33			
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	28					28			
4	74	64	56	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25					25			
5	68	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22					22			
6	63	52	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19					19			
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17					17			
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16					16			
9	51	39	31	27	47	36	30	25	31	26	22	26	22	19	21	19	16	14					14			
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13					13			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20215	20215	20215	20215
5°	22663	20345	18029	20345
10°	25968	20179	15603	20179
15°	28727	19809	13785	19809
20°	28290	19411	12565	19411
25°	25509	18884	11794	18884
30°	21080	18040	11231	18040
35°	15364	17156	10831	17156
40°	12271	16115	10608	16115
45°	10723	14908	10305	14908
50°	10078	13742	10105	13742
55°	9292	12555	9833	12555
60°	8512	11296	9416	11296
65°	7755	10166	9005	10166
70°	7039	9064	8403	9064
75°	6245	7829	7442	7829
80°	5374	6481	5997	6481
85°	4817	4817	3557	4817



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.2	1.9
10°-20°	346.6	5.6
20°-30°	503.1	8.2
30°-40°	530.9	8.6
40°-50°	470.0	7.6
50°-60°	375.1	6.1
60°-70°	254.9	4.1
70°-80°	130.7	2.1
80°-90°	35.9	0.6
90°-100°	195.6	3.2
100°-110°	663.7	10.8
110°-120°	705.1	11.4
120°-130°	580.4	9.4
130°-140°	466.1	7.6
140°-150°	352.2	5.7
150°-160°	247.5	4.0
160°-170°	145.7	2.4
170°-180°	47.4	0.8
0°-30°	968.9	15.7
0°-40°	1499.8	24.3
0°-60°	2344.9	38.0
0°-90°	2766.5	44.8
90°-120°	1564.4	25.4
90°-150°	2963.2	48.0
90°-180°	3404.0	55.2
0°-180°	6170.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1252	1252	1252	1252	1252	
5°	1398	1255	1112	1255	1398	140
15°	1719	1185	825	1185	1719	474
25°	1432	1060	662	1060	1432	647
35°	780	870	550	870	780	507
45°	470	653	451	653	470	369
55°	330	446	349	446	330	296
65°	203	266	236	266	203	202
75°	100	126	119	126	100	107
85°	26	26	19	26	26	29
90°	31	1	31	1	31	18
95°	107	33	107	33	107	139
105°	1060	115	1060	115	1060	1026
115°	1395	202	1395	202	1395	1366
125°	1132	282	1132	282	1132	1023
135°	938	331	938	331	938	729
145°	749	378	749	378	749	476
155°	629	430	629	430	629	294
165°	552	468	552	468	552	158
175°	498	488	498	488	498	48
180°	489	489	489	489	489	



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1309.7	1310.0	1310.9	1304.7	1303.9	1303.9	1298.5	1293.9	1288.5	1281.2	1282.0
5°	1398.3	1403.5	1405.4	1399.7	1391.0	1390.1	1381.9	1368.4	1355.8	1345.8	1338.6
7.5°	1503.9	1506.0	1501.3	1493.6	1487.2	1475.7	1460.5	1445.6	1424.7	1405.5	1391.3
10°	1583.9	1586.9	1578.7	1567.6	1558.5	1545.0	1522.9	1500.2	1472.8	1446.3	1425.1
12.5°	1644.7	1651.9	1641.4	1639.9	1624.3	1605.8	1579.4	1568.0	1529.4	1492.5	1469.8
15°	1718.6	1718.2	1719.2	1710.1	1698.5	1695.5	1667.6	1637.4	1583.0	1561.3	1523.8
17.5°	1697.3	1704.6	1708.0	1707.9	1707.6	1705.8	1696.9	1677.7	1650.5	1615.3	1572.0
20°	1646.5	1656.1	1657.6	1668.7	1674.9	1683.1	1686.4	1681.1	1664.3	1634.9	1597.4
22.5°	1568.0	1570.7	1575.2	1592.4	1606.0	1626.5	1637.2	1655.0	1648.5	1634.2	1602.8
25°	1431.9	1427.1	1444.0	1452.6	1483.8	1516.6	1540.2	1566.1	1589.2	1603.2	1594.0
27.5°	1268.5	1261.3	1286.5	1309.5	1334.9	1370.4	1407.1	1450.5	1486.6	1531.7	1547.2
30°	1130.7	1135.0	1159.1	1183.6	1222.1	1272.1	1313.5	1361.2	1412.7	1463.2	1498.3
32.5°	982.1	998.8	1014.0	1051.6	1085.4	1141.3	1201.9	1261.5	1325.7	1383.1	1437.5
35°	779.5	798.7	819.9	847.3	894.9	950.3	1009.5	1089.8	1177.4	1255.8	1320.3
37.5°	656.1	653.0	665.2	684.9	723.6	768.2	836.3	915.8	1018.8	1111.0	1201.9
40°	582.2	580.2	588.9	607.2	636.6	669.3	729.0	798.7	894.5	1007.0	1115.3
42.5°	531.4	532.5	537.3	550.3	570.3	597.3	642.0	701.3	789.0	895.0	1011.3
45°	469.6	473.0	478.2	484.6	496.1	518.2	543.2	585.6	654.9	743.4	857.9
47.5°	425.2	425.3	430.6	436.1	443.0	455.4	475.9	502.4	551.3	623.4	721.8
50°	401.2	397.9	401.8	406.0	413.3	422.0	435.5	460.4	493.1	551.4	633.7
52.5°	372.0	372.1	375.6	377.2	383.7	392.3	404.6	422.0	451.6	497.1	564.8
55°	330.1	332.4	334.4	337.2	343.1	349.3	358.9	370.5	393.6	427.7	477.8
57.5°	290.6	291.3	293.3	298.8	302.5	308.2	317.4	327.8	342.9	368.2	405.8
60°	263.6	263.6	267.5	269.9	274.8	280.5	287.8	297.8	311.3	332.0	362.3
62.5°	239.0	238.7	240.2	244.1	247.8	253.2	260.4	269.0	281.6	300.0	325.0
65°	203.0	202.1	205.0	205.9	209.8	215.1	220.8	230.0	240.1	253.5	275.7
67.5°	168.4	169.6	171.1	173.0	175.0	180.6	184.5	191.0	199.4	210.7	225.6
70°	149.1	149.1	149.1	150.6	153.4	156.4	160.2	165.5	173.7	183.3	196.8
72.5°	127.6	129.1	130.6	129.8	133.5	135.2	139.8	142.8	150.6	156.7	168.7
75°	100.1	100.1	100.1	102.5	104.0	105.4	108.3	111.1	115.0	122.7	128.9
77.5°	74.6	74.5	74.9	75.5	77.1	78.8	79.6	82.3	85.9	89.4	94.7
80°	57.8	58.7	59.2	60.1	60.1	61.1	61.5	64.9	67.4	69.7	73.1
82.5°	44.7	44.9	45.0	45.1	45.5	46.1	47.3	48.4	49.3	51.3	53.9
85°	26.0	25.5	25.5	26.5	26.0	26.0	27.0	27.9	27.9	28.4	29.8
87.5°	16.2	16.2	16.6	16.2	16.2	16.4	16.0	16.0	16.6	17.2	17.3
90°	31.0	31.0	31.0	31.0	31.0	30.1	28.2	30.1	31.0	32.0	31.0
92.5°	52.1	53.6	52.9	55.9	56.6	62.5	70.4	82.0	103.3	122.2	120.6
95°	107.3	106.3	109.1	116.7	128.8	149.6	189.1	246.5	322.6	368.7	326.4
97.5°	211.1	219.0	232.7	255.9	300.9	368.7	470.5	575.1	660.3	629.5	474.1
100°	336.8	353.7	381.0	421.4	499.5	613.3	742.2	858.8	878.6	743.1	511.7
102.5°	592.7	615.6	649.6	718.7	803.5	924.2	1018.4	1044.7	959.9	746.9	497.5
105°	1060.2	1073.3	1113.8	1172.1	1230.4	1261.5	1249.2	1142.9	947.3	697.0	469.4
107.5°	1354.2	1371.7	1379.8	1383.0	1375.6	1330.1	1232.3	1072.2	864.7	643.7	455.4
110°	1443.0	1444.0	1435.5	1417.6	1377.1	1300.0	1179.6	1011.3	812.8	618.0	452.5



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1441.5	1436.4	1420.4	1390.5	1334.3	1245.9	1117.2	955.5	776.7	601.4	453.2
115°	1395.1	1386.6	1362.1	1318.8	1252.1	1155.2	1031.9	887.0	731.9	583.2	457.1
117.5°	1312.0	1305.0	1279.1	1233.4	1165.4	1074.4	962.7	835.5	703.6	574.4	463.9
120°	1258.7	1249.2	1221.9	1177.7	1111.9	1026.2	926.6	809.9	688.6	569.1	468.4
122.5°	1203.0	1195.0	1170.7	1127.3	1068.3	990.9	896.5	789.6	675.8	566.1	473.7
125°	1131.6	1124.1	1100.6	1064.9	1010.3	939.7	857.0	760.1	657.5	560.6	481.6
127.5°	1069.2	1063.2	1042.8	1009.4	961.8	896.6	818.6	730.9	640.6	557.4	489.7
130°	1033.8	1026.2	1007.5	975.5	929.4	867.3	793.0	712.1	629.3	555.9	495.8
132.5°	996.9	990.1	972.9	940.8	895.5	837.2	768.9	694.0	620.3	555.2	501.7
135°	937.8	934.1	917.2	886.1	845.6	793.0	730.9	668.8	607.7	554.0	508.9
137.5°	880.0	874.3	859.4	832.7	795.8	749.9	700.6	648.7	598.8	553.8	515.3
140°	840.0	834.4	820.3	795.8	765.7	724.3	681.1	635.9	593.6	553.1	518.3
142.5°	800.1	799.0	786.5	764.2	735.7	701.0	663.7	625.4	588.3	553.1	520.6
145°	748.8	745.9	736.6	720.6	698.0	670.7	641.6	610.5	581.4	551.2	523.0
147.5°	705.7	704.0	697.6	684.9	666.2	646.2	623.5	599.0	574.2	547.9	523.8
150°	680.1	679.2	673.5	662.2	648.1	631.2	611.4	590.8	568.2	545.6	523.0
152.5°	658.3	658.1	653.9	644.1	633.1	618.4	601.6	582.5	562.9	541.9	521.5
155°	629.3	631.2	627.5	620.9	610.5	600.1	586.1	571.0	553.1	535.3	519.2
157.5°	604.6	604.6	602.9	597.5	590.2	582.1	570.2	557.6	543.9	528.5	514.9
160°	588.9	588.9	588.0	583.2	576.6	570.0	559.7	549.3	537.2	524.0	512.6
162.5°	573.8	574.6	573.6	570.4	563.8	558.7	549.9	541.1	531.1	520.2	510.4
165°	552.1	553.1	553.1	549.3	545.6	541.9	535.3	528.7	521.1	512.6	506.1
167.5°	532.3	533.4	533.6	531.5	529.8	526.4	521.9	516.8	511.3	506.1	501.7
170°	520.2	522.1	523.0	520.2	519.2	517.4	513.6	510.8	506.1	502.3	499.5
172.5°	510.4	511.5	512.5	511.1	510.2	509.1	506.1	504.0	500.9	497.9	496.5
175°	497.7	499.5	500.5	499.5	499.5	498.6	497.7	496.7	493.9	492.9	492.0
177.5°	489.9	491.4	492.2	492.2	492.2	492.2	491.4	491.4	489.9	489.2	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1284.7	1281.6	1279.7	1272.7	1266.6	1260.5	1258.5	1259.2	1250.8	1242.7	1239.3
5°	1334.7	1325.1	1316.0	1303.0	1287.6	1270.7	1262.1	1255.3	1238.5	1220.2	1209.7
7.5°	1379.6	1365.8	1348.2	1323.7	1301.4	1274.9	1258.0	1243.1	1218.4	1192.7	1176.9
10°	1406.9	1388.1	1365.5	1335.7	1308.2	1276.0	1253.4	1230.8	1201.9	1171.1	1151.9
12.5°	1430.4	1405.0	1382.8	1344.5	1312.1	1271.8	1244.9	1213.1	1182.7	1146.1	1127.3
15°	1486.3	1439.6	1397.2	1354.0	1314.0	1257.7	1227.9	1185.1	1145.1	1099.9	1078.3
17.5°	1529.5	1477.1	1410.3	1355.3	1308.7	1246.4	1202.6	1151.3	1104.1	1052.3	1022.9
20°	1554.2	1493.9	1422.3	1356.9	1301.0	1229.8	1182.2	1129.7	1074.4	1016.2	984.4
22.5°	1568.8	1505.5	1434.6	1351.0	1285.6	1216.4	1156.4	1098.9	1042.8	980.1	946.7
25°	1573.4	1515.6	1440.6	1346.2	1266.4	1188.0	1115.8	1060.0	992.1	933.4	884.9
27.5°	1550.5	1509.1	1436.9	1337.2	1244.2	1152.4	1072.0	1008.8	937.2	873.5	824.6
30°	1522.4	1498.3	1428.0	1327.9	1226.4	1127.8	1039.2	967.6	896.4	831.9	781.8
32.5°	1478.8	1473.7	1411.9	1314.8	1207.6	1096.6	1005.0	932.6	853.7	790.3	742.6
35°	1393.5	1416.5	1377.5	1285.6	1172.1	1052.3	953.2	870.4	788.6	728.0	683.2
37.5°	1278.9	1336.2	1326.1	1242.8	1124.2	1004.0	894.6	808.0	730.1	668.9	625.0
40°	1200.0	1273.1	1283.7	1210.1	1090.3	966.7	850.6	764.6	688.5	632.7	588.4
42.5°	1115.3	1200.8	1229.8	1170.8	1053.3	927.4	811.4	722.2	647.0	592.7	553.5
45°	973.4	1086.5	1138.9	1105.2	991.6	862.7	743.4	652.9	584.6	533.6	503.3
47.5°	840.7	964.2	1034.7	1022.8	923.0	795.3	677.4	590.6	524.1	483.3	456.2
50°	746.8	873.7	958.9	962.8	873.7	747.2	628.9	547.1	486.0	448.0	425.8
52.5°	665.2	786.4	879.3	899.7	818.7	697.2	585.4	504.0	450.2	415.2	395.4
55°	558.6	661.1	764.0	801.6	736.6	621.1	517.7	446.0	395.5	371.5	354.1
57.5°	464.4	549.9	645.0	686.5	646.4	547.5	450.5	388.3	347.3	326.2	312.9
60°	414.7	482.1	566.8	616.3	581.7	493.7	409.0	349.8	316.1	297.4	284.8
62.5°	368.5	428.2	499.8	545.2	526.3	443.3	367.4	315.2	286.1	268.4	259.5
65°	304.1	351.3	406.6	448.5	435.9	372.9	310.9	266.1	243.0	229.0	221.8
67.5°	250.4	284.5	322.8	359.5	349.4	304.7	255.0	220.1	202.8	190.9	186.5
70°	216.5	242.5	276.6	306.0	297.8	261.3	221.8	192.0	177.1	166.9	162.6
72.5°	184.2	205.6	231.6	255.6	250.1	219.7	186.8	164.3	152.8	143.5	139.9
75°	139.0	155.4	171.3	187.2	185.7	162.1	142.9	125.5	116.4	109.2	107.7
77.5°	102.6	111.8	122.6	132.1	129.4	115.9	100.9	91.0	84.2	79.4	78.6
80°	78.4	83.7	91.4	98.1	94.8	89.0	77.0	69.7	64.9	60.1	58.2
82.5°	56.8	62.2	66.8	70.4	67.9	62.5	55.0	50.1	47.2	44.0	43.2
85°	29.8	32.7	34.7	35.6	34.7	31.3	27.9	26.0	23.6	22.1	21.7
87.5°	16.6	15.3	14.3	14.6	13.0	12.6	10.4	8.7	8.9	9.2	8.8
90°	25.4	18.9	14.1	11.3	9.4	7.5	3.8	0.9	3.8	7.5	9.4
92.5°	93.9	64.0	42.7	33.8	27.4	23.4	16.6	11.5	16.6	23.4	27.4
95°	217.3	135.4	92.2	69.7	54.6	46.1	36.7	32.9	36.7	46.1	54.6
97.5°	292.8	178.7	124.3	98.8	81.4	68.7	58.7	53.6	58.7	68.7	81.4
100°	308.6	193.8	143.9	117.6	98.8	83.7	75.2	72.4	75.2	83.7	98.8
102.5°	309.3	207.4	161.3	134.9	115.4	100.3	91.8	89.7	91.8	100.3	115.4
105°	314.1	230.5	186.2	159.9	139.2	125.1	118.6	114.8	118.6	125.1	139.2
107.5°	327.2	254.2	211.3	184.7	164.3	151.3	144.9	141.9	144.9	151.3	164.3
110°	337.7	269.9	228.6	201.3	181.5	169.3	163.7	159.9	163.7	169.3	181.5



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	349.0	285.0	245.2	217.1	198.1	186.6	180.2	176.4	180.2	186.6	198.1
115°	365.9	308.6	268.1	242.7	223.9	212.6	207.0	202.3	207.0	212.6	223.9
117.5°	384.0	330.2	292.8	266.4	248.4	238.4	232.7	228.9	232.7	238.4	248.4
120°	396.1	345.3	308.6	282.2	263.3	255.0	249.3	245.5	249.3	255.0	263.3
122.5°	406.5	359.5	325.1	298.0	279.2	269.9	264.3	261.4	264.3	269.9	279.2
125°	423.3	381.0	347.1	320.7	302.0	290.7	285.0	282.2	285.0	290.7	302.0
127.5°	438.9	401.0	368.0	340.9	322.8	310.4	302.6	298.8	302.6	310.4	322.8
130°	448.7	412.9	380.0	353.7	334.9	321.7	312.3	308.6	312.3	321.7	334.9
132.5°	458.5	423.5	392.1	365.7	346.2	332.2	322.1	317.5	322.1	332.2	346.2
135°	471.3	438.4	408.2	381.9	360.2	346.2	334.9	331.1	334.9	346.2	360.2
137.5°	481.1	450.4	420.7	396.2	374.8	359.7	348.5	343.9	348.5	359.7	374.8
140°	486.4	457.1	429.0	404.5	383.8	368.7	357.5	353.7	357.5	368.7	383.8
142.5°	490.9	462.4	435.0	412.0	392.1	377.0	366.5	363.4	366.5	377.0	392.1
145°	496.7	470.3	445.0	424.2	405.5	391.3	381.9	378.1	381.9	391.3	405.5
147.5°	499.9	476.7	452.9	434.4	418.8	405.8	396.8	394.0	396.8	405.8	418.8
150°	501.3	479.8	458.1	441.2	427.1	414.8	407.3	404.5	407.3	414.8	427.1
152.5°	502.1	482.8	463.4	448.0	434.6	423.9	416.3	415.0	416.3	423.9	434.6
155°	503.2	487.3	471.3	457.1	446.9	436.5	430.8	429.9	430.8	436.5	446.9
157.5°	503.2	490.5	476.9	465.1	456.8	447.8	443.3	442.3	443.3	447.8	456.8
160°	503.2	492.0	480.7	470.3	462.8	455.2	451.6	450.6	451.6	455.2	462.8
162.5°	502.5	492.8	483.0	474.9	468.1	462.0	458.3	458.8	458.3	462.0	468.1
165°	500.5	493.9	485.4	479.8	475.0	469.4	467.5	468.4	467.5	469.4	475.0
167.5°	499.2	493.7	487.5	483.9	480.5	476.9	475.2	476.4	475.2	476.9	480.5
170°	497.7	492.9	488.2	485.4	483.5	480.7	479.8	481.6	479.8	480.7	483.5
172.5°	495.4	492.2	489.0	486.9	485.8	483.0	483.5	484.7	483.5	483.0	485.8
175°	492.9	491.1	489.2	488.2	488.2	486.4	487.3	488.2	487.3	486.4	488.2
177.5°	491.4	489.9	489.2	489.2	489.2	487.7	488.4	489.9	488.4	487.7	489.2
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1235.4	1233.1	1225.0	1220.8	1213.8	1207.3	1203.1	1205.0	1206.5	1205.8	1204.6
5°	1200.0	1190.8	1176.9	1164.9	1156.2	1140.3	1133.6	1130.2	1127.4	1124.0	1120.6
7.5°	1157.8	1143.4	1123.4	1106.3	1090.1	1070.4	1059.1	1052.3	1045.5	1037.8	1031.1
10°	1127.8	1107.6	1086.5	1062.3	1043.1	1025.3	1009.5	998.9	989.3	980.1	973.4
12.5°	1096.3	1073.0	1046.8	1013.9	992.7	967.2	964.8	946.1	931.1	925.5	917.6
15°	1046.0	1013.3	980.1	941.1	924.3	901.2	886.7	872.3	859.3	850.2	847.8
17.5°	988.9	946.6	913.6	885.6	858.0	834.3	821.0	809.5	798.8	786.6	784.9
20°	945.5	908.9	872.8	848.3	819.9	795.8	779.5	767.9	758.7	751.6	745.3
22.5°	904.3	864.2	831.2	804.4	776.4	757.0	744.0	732.9	725.3	717.3	711.4
25°	838.2	806.9	770.8	740.5	717.4	704.9	694.3	684.7	679.9	674.6	667.9
27.5°	780.3	745.6	711.8	688.3	668.1	657.0	649.4	642.9	638.4	635.3	631.5
30°	739.5	704.4	678.0	654.9	638.0	627.0	622.2	618.3	613.0	611.1	609.2
32.5°	700.3	668.6	646.0	625.9	609.9	602.7	598.2	594.8	590.7	588.7	584.8
35°	644.7	618.3	596.2	585.0	572.1	565.8	562.5	557.6	553.8	551.9	551.4
37.5°	592.5	569.5	555.0	540.7	535.3	531.4	526.8	523.5	522.4	522.1	521.6
40°	558.6	539.9	526.9	515.3	512.9	507.1	503.3	500.4	500.4	500.9	500.4
42.5°	527.8	511.0	499.5	489.6	486.7	483.2	479.4	479.2	480.0	481.6	480.0
45°	481.2	469.1	460.9	456.1	450.8	447.4	447.0	448.5	448.9	449.4	450.8
47.5°	438.2	430.3	422.8	417.5	415.2	414.6	414.1	416.6	418.9	419.7	422.0
50°	412.8	403.7	397.5	394.1	392.1	391.2	392.1	395.0	396.9	399.4	400.8
52.5°	384.4	377.9	373.5	371.0	370.2	370.8	371.0	374.3	377.3	378.1	378.9
55°	345.0	340.2	339.2	334.9	336.8	336.3	338.7	340.6	343.6	346.4	346.9
57.5°	305.8	301.9	299.3	299.6	300.2	302.4	304.3	307.7	310.9	313.9	314.1
60°	279.6	277.6	276.2	276.2	277.1	280.0	282.5	285.8	287.8	289.6	291.1
62.5°	255.7	253.7	252.3	253.1	255.6	257.3	260.1	261.9	263.8	265.8	266.5
65°	217.9	217.0	218.5	219.4	219.9	222.3	225.6	227.1	229.0	230.0	233.4
67.5°	183.2	183.4	183.2	184.5	187.4	187.9	191.1	194.4	194.8	196.7	198.9
70°	159.8	160.7	161.6	162.6	165.0	166.0	168.4	169.8	171.7	173.2	174.7
72.5°	138.2	138.4	139.3	139.1	141.2	143.3	145.3	146.8	148.6	150.5	151.9
75°	106.3	106.3	107.3	107.7	110.2	112.6	112.1	113.1	115.0	116.9	117.9
77.5°	77.7	76.6	77.7	78.1	78.9	81.0	81.3	82.7	84.8	84.2	85.3
80°	59.2	57.8	59.2	59.7	59.7	62.1	62.1	63.1	64.5	63.1	64.5
82.5°	42.2	41.6	42.6	42.7	43.5	43.5	44.4	44.6	46.0	45.3	46.0
85°	21.2	20.7	21.2	20.7	21.2	21.7	21.7	21.2	21.2	22.1	20.7
87.5°	8.8	9.0	9.5	10.8	11.6	11.4	10.8	10.7	10.3	9.9	10.1
90°	11.3	14.1	18.9	25.4	31.0	32.0	31.0	30.1	28.2	30.1	31.0
92.5°	33.8	42.7	64.0	93.9	120.6	122.2	103.3	82.0	70.4	62.5	56.6
95°	69.7	92.2	135.4	217.3	326.4	368.7	322.6	246.5	189.1	149.6	128.8
97.5°	98.8	124.3	178.7	292.8	474.1	629.5	660.3	575.1	470.5	368.7	300.9
100°	117.6	143.9	193.8	308.6	511.7	743.1	878.6	858.8	742.2	613.3	499.5
102.5°	134.9	161.3	207.4	309.3	497.5	746.9	959.9	1044.7	1018.4	924.2	803.5
105°	159.9	186.2	230.5	314.1	469.4	697.0	947.3	1142.9	1249.2	1261.5	1230.4
107.5°	184.7	211.3	254.2	327.2	455.4	643.7	864.7	1072.2	1232.3	1330.1	1375.6
110°	201.3	228.6	269.9	337.7	452.5	618.0	812.8	1011.3	1179.6	1300.0	1377.1



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.1	245.2	285.0	349.0	453.2	601.4	776.7	955.5	1117.2	1245.9	1334.3
115°	242.7	268.1	308.6	365.9	457.1	583.2	731.9	887.0	1031.9	1155.2	1252.1
117.5°	266.4	292.8	330.2	384.0	463.9	574.4	703.6	835.5	962.7	1074.4	1165.4
120°	282.2	308.6	345.3	396.1	468.4	569.1	688.6	809.9	926.6	1026.2	1111.9
122.5°	298.0	325.1	359.5	406.5	473.7	566.1	675.8	789.6	896.5	990.9	1068.3
125°	320.7	347.1	381.0	423.3	481.6	560.6	657.5	760.1	857.0	939.7	1010.3
127.5°	340.9	368.0	401.0	438.9	489.7	557.4	640.6	730.9	818.6	896.6	961.8
130°	353.7	380.0	412.9	448.7	495.8	555.9	629.3	712.1	793.0	867.3	929.4
132.5°	365.7	392.1	423.5	458.5	501.7	555.2	620.3	694.0	768.9	837.2	895.5
135°	381.9	408.2	438.4	471.3	508.9	554.0	607.7	668.8	730.9	793.0	845.6
137.5°	396.2	420.7	450.4	481.1	515.3	553.8	598.8	648.7	700.6	749.9	795.8
140°	404.5	429.0	457.1	486.4	518.3	553.1	593.6	635.9	681.1	724.3	765.7
142.5°	412.0	435.0	462.4	490.9	520.6	553.1	588.3	625.4	663.7	701.0	735.7
145°	424.2	445.0	470.3	496.7	523.0	551.2	581.4	610.5	641.6	670.7	698.0
147.5°	434.4	452.9	476.7	499.9	523.8	547.9	574.2	599.0	623.5	646.2	666.2
150°	441.2	458.1	479.8	501.3	523.0	545.6	568.2	590.8	611.4	631.2	648.1
152.5°	448.0	463.4	482.8	502.1	521.5	541.9	562.9	582.5	601.6	618.4	633.1
155°	457.1	471.3	487.3	503.2	519.2	535.3	553.1	571.0	586.1	600.1	610.5
157.5°	465.1	476.9	490.5	503.2	514.9	528.5	543.9	557.6	570.2	582.1	590.2
160°	470.3	480.7	492.0	503.2	512.6	524.0	537.2	549.3	559.7	570.0	576.6
162.5°	474.9	483.0	492.8	502.5	510.4	520.2	531.1	541.1	549.9	558.7	563.8
165°	479.8	485.4	493.9	500.5	506.1	512.6	521.1	528.7	535.3	541.9	545.6
167.5°	483.9	487.5	493.7	499.2	501.7	506.1	511.3	516.8	521.9	526.4	529.8
170°	485.4	488.2	492.9	497.7	499.5	502.3	506.1	510.8	513.6	517.4	519.2
172.5°	486.9	489.0	492.2	495.4	496.5	497.9	500.9	504.0	506.1	509.1	510.2
175°	488.2	489.2	491.1	492.9	492.0	492.9	493.9	496.7	497.7	498.6	499.5
177.5°	489.2	489.2	489.9	491.4	489.9	489.2	489.9	491.4	491.4	492.2	492.2
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1200.8	1200.0	1200.0	1196.6	1200.0	1200.0	1200.8	1204.6	1205.8	1206.5	1205.0
5°	1113.9	1112.4	1110.0	1112.4	1110.0	1112.4	1113.9	1120.6	1124.0	1127.4	1130.2
7.5°	1027.9	1022.2	1021.3	1015.6	1021.3	1022.2	1027.9	1031.1	1037.8	1045.5	1052.3
10°	965.2	961.3	960.8	951.7	960.8	961.3	965.2	973.4	980.1	989.3	998.9
12.5°	917.5	908.2	910.0	904.7	910.0	908.2	917.5	917.6	925.5	931.1	946.1
15°	834.8	834.8	832.8	824.7	832.8	834.8	834.8	847.8	850.2	859.3	872.3
17.5°	775.4	774.5	769.9	772.1	769.9	774.5	775.4	784.9	786.6	798.8	809.5
20°	740.0	737.2	731.3	731.3	731.3	737.2	740.0	745.3	751.6	758.7	767.9
22.5°	706.5	706.3	700.2	702.1	700.2	706.3	706.5	711.4	717.3	725.3	732.9
25°	667.3	663.5	660.6	662.0	660.6	663.5	667.3	667.9	674.6	679.9	684.7
27.5°	630.2	628.1	627.9	624.0	627.9	628.1	630.2	631.5	635.3	638.4	642.9
30°	608.7	603.9	604.8	602.4	604.8	603.9	608.7	609.2	611.1	613.0	618.3
32.5°	584.0	582.3	581.4	579.3	581.4	582.3	584.0	584.8	588.7	590.7	594.8
35°	550.4	550.9	548.6	549.5	548.6	550.9	550.4	551.4	551.9	553.8	557.6
37.5°	521.1	522.6	521.5	521.8	521.5	522.6	521.1	521.6	522.1	522.4	523.5
40°	501.8	501.8	501.8	503.3	501.8	501.8	501.8	500.4	500.9	500.4	500.4
42.5°	483.3	482.6	481.8	481.7	481.8	482.6	483.3	480.0	481.6	480.0	479.2
45°	451.8	453.3	453.7	451.3	453.7	453.3	451.8	450.8	449.4	448.9	448.5
47.5°	423.2	423.4	423.2	425.4	423.2	423.4	423.2	422.0	419.7	418.9	416.6
50°	403.2	402.3	403.2	402.3	403.2	402.3	403.2	400.8	399.4	396.9	395.0
52.5°	382.0	382.2	381.6	381.4	381.6	382.2	382.0	378.9	378.1	377.3	374.3
55°	348.8	349.8	349.3	349.3	349.3	349.8	348.8	346.9	346.4	343.6	340.6
57.5°	314.5	315.4	316.0	313.9	316.0	315.4	314.5	314.1	313.9	310.9	307.7
60°	290.6	293.0	292.6	291.6	292.6	293.0	290.6	291.1	289.6	287.8	285.8
62.5°	268.7	269.6	269.5	269.3	269.5	269.6	268.7	266.5	265.8	263.8	261.9
65°	234.8	235.7	234.3	235.7	234.3	235.7	234.8	233.4	230.0	229.0	227.1
67.5°	198.3	198.6	199.7	200.4	199.7	198.6	198.3	198.9	196.7	194.8	194.4
70°	175.6	175.1	176.5	178.0	176.5	175.1	175.6	174.7	173.2	171.7	169.8
72.5°	151.7	152.8	152.3	153.4	152.3	152.8	151.7	151.9	150.5	148.6	146.8
75°	116.9	118.4	117.9	119.3	117.9	118.4	116.9	117.9	116.9	115.0	113.1
77.5°	84.5	84.6	84.5	85.3	84.5	84.6	84.5	85.3	84.2	84.8	82.7
80°	64.5	63.5	62.6	64.5	62.6	63.5	64.5	64.5	63.1	64.5	63.1
82.5°	44.9	45.4	44.5	44.5	44.5	45.4	44.9	46.0	45.3	46.0	44.6
85°	20.7	20.2	19.2	19.2	19.2	20.2	20.7	20.7	22.1	21.2	21.2
87.5°	10.1	9.7	9.7	9.3	9.7	9.7	10.1	10.1	9.9	10.3	10.7
90°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.0	30.1	28.2	30.1
92.5°	55.9	52.9	53.6	52.1	53.6	52.9	55.9	56.6	62.5	70.4	82.0
95°	116.7	109.1	106.3	107.3	106.3	109.1	116.7	128.8	149.6	189.1	246.5
97.5°	255.9	232.7	219.0	211.1	219.0	232.7	255.9	300.9	368.7	470.5	575.1
100°	421.4	381.0	353.7	336.8	353.7	381.0	421.4	499.5	613.3	742.2	858.8
102.5°	718.7	649.6	615.6	592.7	615.6	649.6	718.7	803.5	924.2	1018.4	1044.7
105°	1172.1	1113.8	1073.3	1060.2	1073.3	1113.8	1172.1	1230.4	1261.5	1249.2	1142.9
107.5°	1383.0	1379.8	1371.7	1354.2	1371.7	1379.8	1383.0	1375.6	1330.1	1232.3	1072.2
110°	1417.6	1435.5	1444.0	1443.0	1444.0	1435.5	1417.6	1377.1	1300.0	1179.6	1011.3



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1390.5	1420.4	1436.4	1441.5	1436.4	1420.4	1390.5	1334.3	1245.9	1117.2	955.5
115°	1318.8	1362.1	1386.6	1395.1	1386.6	1362.1	1318.8	1252.1	1155.2	1031.9	887.0
117.5°	1233.4	1279.1	1305.0	1312.0	1305.0	1279.1	1233.4	1165.4	1074.4	962.7	835.5
120°	1177.7	1221.9	1249.2	1258.7	1249.2	1221.9	1177.7	1111.9	1026.2	926.6	809.9
122.5°	1127.3	1170.7	1195.0	1203.0	1195.0	1170.7	1127.3	1068.3	990.9	896.5	789.6
125°	1064.9	1100.6	1124.1	1131.6	1124.1	1100.6	1064.9	1010.3	939.7	857.0	760.1
127.5°	1009.4	1042.8	1063.2	1069.2	1063.2	1042.8	1009.4	961.8	896.6	818.6	730.9
130°	975.5	1007.5	1026.2	1033.8	1026.2	1007.5	975.5	929.4	867.3	793.0	712.1
132.5°	940.8	972.9	990.1	996.9	990.1	972.9	940.8	895.5	837.2	768.9	694.0
135°	886.1	917.2	934.1	937.8	934.1	917.2	886.1	845.6	793.0	730.9	668.8
137.5°	832.7	859.4	874.3	880.0	874.3	859.4	832.7	795.8	749.9	700.6	648.7
140°	795.8	820.3	834.4	840.0	834.4	820.3	795.8	765.7	724.3	681.1	635.9
142.5°	764.2	786.5	799.0	800.1	799.0	786.5	764.2	735.7	701.0	663.7	625.4
145°	720.6	736.6	745.9	748.8	745.9	736.6	720.6	698.0	670.7	641.6	610.5
147.5°	684.9	697.6	704.0	705.7	704.0	697.6	684.9	666.2	646.2	623.5	599.0
150°	662.2	673.5	679.2	680.1	679.2	673.5	662.2	648.1	631.2	611.4	590.8
152.5°	644.1	653.9	658.1	658.3	658.1	653.9	644.1	633.1	618.4	601.6	582.5
155°	620.9	627.5	631.2	629.3	631.2	627.5	620.9	610.5	600.1	586.1	571.0
157.5°	597.5	602.9	604.6	604.6	604.6	602.9	597.5	590.2	582.1	570.2	557.6
160°	583.2	588.0	588.9	588.9	588.9	588.0	583.2	576.6	570.0	559.7	549.3
162.5°	570.4	573.6	574.6	573.8	574.6	573.6	570.4	563.8	558.7	549.9	541.1
165°	549.3	553.1	553.1	552.1	553.1	553.1	549.3	545.6	541.9	535.3	528.7
167.5°	531.5	533.6	533.4	532.3	533.4	533.6	531.5	529.8	526.4	521.9	516.8
170°	520.2	523.0	522.1	520.2	522.1	523.0	520.2	519.2	517.4	513.6	510.8
172.5°	511.1	512.5	511.5	510.4	511.5	512.5	511.1	510.2	509.1	506.1	504.0
175°	499.5	500.5	499.5	497.7	499.5	500.5	499.5	499.5	498.6	497.7	496.7
177.5°	492.2	492.2	491.4	489.9	491.4	492.2	492.2	492.2	492.2	491.4	491.4
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1203.1	1207.3	1213.8	1220.8	1225.0	1233.1	1235.4	1239.3	1242.7	1250.8	1259.2
5°	1133.6	1140.3	1156.2	1164.9	1176.9	1190.8	1200.0	1209.7	1220.2	1238.5	1255.3
7.5°	1059.1	1070.4	1090.1	1106.3	1123.4	1143.4	1157.8	1176.9	1192.7	1218.4	1243.1
10°	1009.5	1025.3	1043.1	1062.3	1086.5	1107.6	1127.8	1151.9	1171.1	1201.9	1230.8
12.5°	964.8	967.2	992.7	1013.9	1046.8	1073.0	1096.3	1127.3	1146.1	1182.7	1213.1
15°	886.7	901.2	924.3	941.1	980.1	1013.3	1046.0	1078.3	1099.9	1145.1	1185.1
17.5°	821.0	834.3	858.0	885.6	913.6	946.6	988.9	1022.9	1052.3	1104.1	1151.3
20°	779.5	795.8	819.9	848.3	872.8	908.9	945.5	984.4	1016.2	1074.4	1129.7
22.5°	744.0	757.0	776.4	804.4	831.2	864.2	904.3	946.7	980.1	1042.8	1098.9
25°	694.3	704.9	717.4	740.5	770.8	806.9	838.2	884.9	933.4	992.1	1060.0
27.5°	649.4	657.0	668.1	688.3	711.8	745.6	780.3	824.6	873.5	937.2	1008.8
30°	622.2	627.0	638.0	654.9	678.0	704.4	739.5	781.8	831.9	896.4	967.6
32.5°	598.2	602.7	609.9	625.9	646.0	668.6	700.3	742.6	790.3	853.7	932.6
35°	562.5	565.8	572.1	585.0	596.2	618.3	644.7	683.2	728.0	788.6	870.4
37.5°	526.8	531.4	535.3	540.7	555.0	569.5	592.5	625.0	668.9	730.1	808.0
40°	503.3	507.1	512.9	515.3	526.9	539.9	558.6	588.4	632.7	688.5	764.6
42.5°	479.4	483.2	486.7	489.6	499.5	511.0	527.8	553.5	592.7	647.0	722.2
45°	447.0	447.4	450.8	456.1	460.9	469.1	481.2	503.3	533.6	584.6	652.9
47.5°	414.1	414.6	415.2	417.5	422.8	430.3	438.2	456.2	483.3	524.1	590.6
50°	392.1	391.2	392.1	394.1	397.5	403.7	412.8	425.8	448.0	486.0	547.1
52.5°	371.0	370.8	370.2	371.0	373.5	377.9	384.4	395.4	415.2	450.2	504.0
55°	338.7	336.3	336.8	334.9	339.2	340.2	345.0	354.1	371.5	395.5	446.0
57.5°	304.3	302.4	300.2	299.6	299.3	301.9	305.8	312.9	326.2	347.3	388.3
60°	282.5	280.0	277.1	276.2	276.2	277.6	279.6	284.8	297.4	316.1	349.8
62.5°	260.1	257.3	255.6	253.1	252.3	253.7	255.7	259.5	268.4	286.1	315.2
65°	225.6	222.3	219.9	219.4	218.5	217.0	217.9	221.8	229.0	243.0	266.1
67.5°	191.1	187.9	187.4	184.5	183.2	183.4	183.2	186.5	190.9	202.8	220.1
70°	168.4	166.0	165.0	162.6	161.6	160.7	159.8	162.6	166.9	177.1	192.0
72.5°	145.3	143.3	141.2	139.1	139.3	138.4	138.2	139.9	143.5	152.8	164.3
75°	112.1	112.6	110.2	107.7	107.3	106.3	106.3	107.7	109.2	116.4	125.5
77.5°	81.3	81.0	78.9	78.1	77.7	76.6	77.7	78.6	79.4	84.2	91.0
80°	62.1	62.1	59.7	59.7	59.2	57.8	59.2	58.2	60.1	64.9	69.7
82.5°	44.4	43.5	43.5	42.7	42.6	41.6	42.2	43.2	44.0	47.2	50.1
85°	21.7	21.7	21.2	20.7	21.2	20.7	21.2	21.7	22.1	23.6	26.0
87.5°	10.8	11.4	11.6	10.8	9.5	9.0	8.8	8.8	9.2	8.9	8.7
90°	31.0	32.0	31.0	25.4	18.9	14.1	11.3	9.4	7.5	3.8	0.9
92.5°	103.3	122.2	120.6	93.9	64.0	42.7	33.8	27.4	23.4	16.6	11.5
95°	322.6	368.7	326.4	217.3	135.4	92.2	69.7	54.6	46.1	36.7	32.9
97.5°	660.3	629.5	474.1	292.8	178.7	124.3	98.8	81.4	68.7	58.7	53.6
100°	878.6	743.1	511.7	308.6	193.8	143.9	117.6	98.8	83.7	75.2	72.4
102.5°	959.9	746.9	497.5	309.3	207.4	161.3	134.9	115.4	100.3	91.8	89.7
105°	947.3	697.0	469.4	314.1	230.5	186.2	159.9	139.2	125.1	118.6	114.8
107.5°	864.7	643.7	455.4	327.2	254.2	211.3	184.7	164.3	151.3	144.9	141.9
110°	812.8	618.0	452.5	337.7	269.9	228.6	201.3	181.5	169.3	163.7	159.9



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	776.7	601.4	453.2	349.0	285.0	245.2	217.1	198.1	186.6	180.2	176.4
115°	731.9	583.2	457.1	365.9	308.6	268.1	242.7	223.9	212.6	207.0	202.3
117.5°	703.6	574.4	463.9	384.0	330.2	292.8	266.4	248.4	238.4	232.7	228.9
120°	688.6	569.1	468.4	396.1	345.3	308.6	282.2	263.3	255.0	249.3	245.5
122.5°	675.8	566.1	473.7	406.5	359.5	325.1	298.0	279.2	269.9	264.3	261.4
125°	657.5	560.6	481.6	423.3	381.0	347.1	320.7	302.0	290.7	285.0	282.2
127.5°	640.6	557.4	489.7	438.9	401.0	368.0	340.9	322.8	310.4	302.6	298.8
130°	629.3	555.9	495.8	448.7	412.9	380.0	353.7	334.9	321.7	312.3	308.6
132.5°	620.3	555.2	501.7	458.5	423.5	392.1	365.7	346.2	332.2	322.1	317.5
135°	607.7	554.0	508.9	471.3	438.4	408.2	381.9	360.2	346.2	334.9	331.1
137.5°	598.8	553.8	515.3	481.1	450.4	420.7	396.2	374.8	359.7	348.5	343.9
140°	593.6	553.1	518.3	486.4	457.1	429.0	404.5	383.8	368.7	357.5	353.7
142.5°	588.3	553.1	520.6	490.9	462.4	435.0	412.0	392.1	377.0	366.5	363.4
145°	581.4	551.2	523.0	496.7	470.3	445.0	424.2	405.5	391.3	381.9	378.1
147.5°	574.2	547.9	523.8	499.9	476.7	452.9	434.4	418.8	405.8	396.8	394.0
150°	568.2	545.6	523.0	501.3	479.8	458.1	441.2	427.1	414.8	407.3	404.5
152.5°	562.9	541.9	521.5	502.1	482.8	463.4	448.0	434.6	423.9	416.3	415.0
155°	553.1	535.3	519.2	503.2	487.3	471.3	457.1	446.9	436.5	430.8	429.9
157.5°	543.9	528.5	514.9	503.2	490.5	476.9	465.1	456.8	447.8	443.3	442.3
160°	537.2	524.0	512.6	503.2	492.0	480.7	470.3	462.8	455.2	451.6	450.6
162.5°	531.1	520.2	510.4	502.5	492.8	483.0	474.9	468.1	462.0	458.3	458.8
165°	521.1	512.6	506.1	500.5	493.9	485.4	479.8	475.0	469.4	467.5	468.4
167.5°	511.3	506.1	501.7	499.2	493.7	487.5	483.9	480.5	476.9	475.2	476.4
170°	506.1	502.3	499.5	497.7	492.9	488.2	485.4	483.5	480.7	479.8	481.6
172.5°	500.9	497.9	496.5	495.4	492.2	489.0	486.9	485.8	483.0	483.5	484.7
175°	493.9	492.9	492.0	492.9	491.1	489.2	488.2	488.2	486.4	487.3	488.2
177.5°	489.9	489.2	489.9	491.4	489.9	489.2	489.2	489.2	487.7	488.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1258.5	1260.5	1266.6	1272.7	1279.7	1281.6	1284.7	1282.0	1281.2	1288.5	1293.9
5°	1262.1	1270.7	1287.6	1303.0	1316.0	1325.1	1334.7	1338.6	1345.8	1355.8	1368.4
7.5°	1258.0	1274.9	1301.4	1323.7	1348.2	1365.8	1379.6	1391.3	1405.5	1424.7	1445.6
10°	1253.4	1276.0	1308.2	1335.7	1365.5	1388.1	1406.9	1425.1	1446.3	1472.8	1500.2
12.5°	1244.9	1271.8	1312.1	1344.5	1382.8	1405.0	1430.4	1469.8	1492.5	1529.4	1568.0
15°	1227.9	1257.7	1314.0	1354.0	1397.2	1439.6	1486.3	1523.8	1561.3	1583.0	1637.4
17.5°	1202.6	1246.4	1308.7	1355.3	1410.3	1477.1	1529.5	1572.0	1615.3	1650.5	1677.7
20°	1182.2	1229.8	1301.0	1356.9	1422.3	1493.9	1554.2	1597.4	1634.9	1664.3	1681.1
22.5°	1156.4	1216.4	1285.6	1351.0	1434.6	1505.5	1568.8	1602.8	1634.2	1648.5	1655.0
25°	1115.8	1188.0	1266.4	1346.2	1440.6	1515.6	1573.4	1594.0	1603.2	1589.2	1566.1
27.5°	1072.0	1152.4	1244.2	1337.2	1436.9	1509.1	1550.5	1547.2	1531.7	1486.6	1450.5
30°	1039.2	1127.8	1226.4	1327.9	1428.0	1498.3	1522.4	1498.3	1463.2	1412.7	1361.2
32.5°	1005.0	1096.6	1207.6	1314.8	1411.9	1473.7	1478.8	1437.5	1383.1	1325.7	1261.5
35°	953.2	1052.3	1172.1	1285.6	1377.5	1416.5	1393.5	1320.3	1255.8	1177.4	1089.8
37.5°	894.6	1004.0	1124.2	1242.8	1326.1	1336.2	1278.9	1201.9	1111.0	1018.8	915.8
40°	850.6	966.7	1090.3	1210.1	1283.7	1273.1	1200.0	1115.3	1007.0	894.5	798.7
42.5°	811.4	927.4	1053.3	1170.8	1229.8	1200.8	1115.3	1011.3	895.0	789.0	701.3
45°	743.4	862.7	991.6	1105.2	1138.9	1086.5	973.4	857.9	743.4	654.9	585.6
47.5°	677.4	795.3	923.0	1022.8	1034.7	964.2	840.7	721.8	623.4	551.3	502.4
50°	628.9	747.2	873.7	962.8	958.9	873.7	746.8	633.7	551.4	493.1	460.4
52.5°	585.4	697.2	818.7	899.7	879.3	786.4	665.2	564.8	497.1	451.6	422.0
55°	517.7	621.1	736.6	801.6	764.0	661.1	558.6	477.8	427.7	393.6	370.5
57.5°	450.5	547.5	646.4	686.5	645.0	549.9	464.4	405.8	368.2	342.9	327.8
60°	409.0	493.7	581.7	616.3	566.8	482.1	414.7	362.3	332.0	311.3	297.8
62.5°	367.4	443.3	526.3	545.2	499.8	428.2	368.5	325.0	300.0	281.6	269.0
65°	310.9	372.9	435.9	448.5	406.6	351.3	304.1	275.7	253.5	240.1	230.0
67.5°	255.0	304.7	349.4	359.5	322.8	284.5	250.4	225.6	210.7	199.4	191.0
70°	221.8	261.3	297.8	306.0	276.6	242.5	216.5	196.8	183.3	173.7	165.5
72.5°	186.8	219.7	250.1	255.6	231.6	205.6	184.2	168.7	156.7	150.6	142.8
75°	142.9	162.1	185.7	187.2	171.3	155.4	139.0	128.9	122.7	115.0	111.1
77.5°	100.9	115.9	129.4	132.1	122.6	111.8	102.6	94.7	89.4	85.9	82.3
80°	77.0	89.0	94.8	98.1	91.4	83.7	78.4	73.1	69.7	67.4	64.9
82.5°	55.0	62.5	67.9	70.4	66.8	62.2	56.8	53.9	51.3	49.3	48.4
85°	27.9	31.3	34.7	35.6	34.7	32.7	29.8	29.8	28.4	27.9	27.9
87.5°	10.4	12.6	13.0	14.6	14.3	15.3	16.6	17.3	17.2	16.6	16.0
90°	3.8	7.5	9.4	11.3	14.1	18.9	25.4	31.0	32.0	31.0	30.1
92.5°	16.6	23.4	27.4	33.8	42.7	64.0	93.9	120.6	122.2	103.3	82.0
95°	36.7	46.1	54.6	69.7	92.2	135.4	217.3	326.4	368.7	322.6	246.5
97.5°	58.7	68.7	81.4	98.8	124.3	178.7	292.8	474.1	629.5	660.3	575.1
100°	75.2	83.7	98.8	117.6	143.9	193.8	308.6	511.7	743.1	878.6	858.8
102.5°	91.8	100.3	115.4	134.9	161.3	207.4	309.3	497.5	746.9	959.9	1044.7
105°	118.6	125.1	139.2	159.9	186.2	230.5	314.1	469.4	697.0	947.3	1142.9
107.5°	144.9	151.3	164.3	184.7	211.3	254.2	327.2	455.4	643.7	864.7	1072.2
110°	163.7	169.3	181.5	201.3	228.6	269.9	337.7	452.5	618.0	812.8	1011.3



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	180.2	186.6	198.1	217.1	245.2	285.0	349.0	453.2	601.4	776.7	955.5
115°	207.0	212.6	223.9	242.7	268.1	308.6	365.9	457.1	583.2	731.9	887.0
117.5°	232.7	238.4	248.4	266.4	292.8	330.2	384.0	463.9	574.4	703.6	835.5
120°	249.3	255.0	263.3	282.2	308.6	345.3	396.1	468.4	569.1	688.6	809.9
122.5°	264.3	269.9	279.2	298.0	325.1	359.5	406.5	473.7	566.1	675.8	789.6
125°	285.0	290.7	302.0	320.7	347.1	381.0	423.3	481.6	560.6	657.5	760.1
127.5°	302.6	310.4	322.8	340.9	368.0	401.0	438.9	489.7	557.4	640.6	730.9
130°	312.3	321.7	334.9	353.7	380.0	412.9	448.7	495.8	555.9	629.3	712.1
132.5°	322.1	332.2	346.2	365.7	392.1	423.5	458.5	501.7	555.2	620.3	694.0
135°	334.9	346.2	360.2	381.9	408.2	438.4	471.3	508.9	554.0	607.7	668.8
137.5°	348.5	359.7	374.8	396.2	420.7	450.4	481.1	515.3	553.8	598.8	648.7
140°	357.5	368.7	383.8	404.5	429.0	457.1	486.4	518.3	553.1	593.6	635.9
142.5°	366.5	377.0	392.1	412.0	435.0	462.4	490.9	520.6	553.1	588.3	625.4
145°	381.9	391.3	405.5	424.2	445.0	470.3	496.7	523.0	551.2	581.4	610.5
147.5°	396.8	405.8	418.8	434.4	452.9	476.7	499.9	523.8	547.9	574.2	599.0
150°	407.3	414.8	427.1	441.2	458.1	479.8	501.3	523.0	545.6	568.2	590.8
152.5°	416.3	423.9	434.6	448.0	463.4	482.8	502.1	521.5	541.9	562.9	582.5
155°	430.8	436.5	446.9	457.1	471.3	487.3	503.2	519.2	535.3	553.1	571.0
157.5°	443.3	447.8	456.8	465.1	476.9	490.5	503.2	514.9	528.5	543.9	557.6
160°	451.6	455.2	462.8	470.3	480.7	492.0	503.2	512.6	524.0	537.2	549.3
162.5°	458.3	462.0	468.1	474.9	483.0	492.8	502.5	510.4	520.2	531.1	541.1
165°	467.5	469.4	475.0	479.8	485.4	493.9	500.5	506.1	512.6	521.1	528.7
167.5°	475.2	476.9	480.5	483.9	487.5	493.7	499.2	501.7	506.1	511.3	516.8
170°	479.8	480.7	483.5	485.4	488.2	492.9	497.7	499.5	502.3	506.1	510.8
172.5°	483.5	483.0	485.8	486.9	489.0	492.2	495.4	496.5	497.9	500.9	504.0
175°	487.3	486.4	488.2	488.2	489.2	491.1	492.9	492.0	492.9	493.9	496.7
177.5°	488.4	487.7	489.2	489.2	489.2	489.9	491.4	489.9	489.2	489.9	491.4
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1298.5	1303.9	1303.9	1304.7	1310.9	1310.0	1309.7
5°	1381.9	1390.1	1391.0	1399.7	1405.4	1403.5	1398.3
7.5°	1460.5	1475.7	1487.2	1493.6	1501.3	1506.0	1503.9
10°	1522.9	1545.0	1558.5	1567.6	1578.7	1586.9	1583.9
12.5°	1579.4	1605.8	1624.3	1639.9	1641.4	1651.9	1644.7
15°	1667.6	1695.5	1698.5	1710.1	1719.2	1718.2	1718.6
17.5°	1696.9	1705.8	1707.6	1707.9	1708.0	1704.6	1697.3
20°	1686.4	1683.1	1674.9	1668.7	1657.6	1656.1	1646.5
22.5°	1637.2	1626.5	1606.0	1592.4	1575.2	1570.7	1568.0
25°	1540.2	1516.6	1483.8	1452.6	1444.0	1427.1	1431.9
27.5°	1407.1	1370.4	1334.9	1309.5	1286.5	1261.3	1268.5
30°	1313.5	1272.1	1222.1	1183.6	1159.1	1135.0	1130.7
32.5°	1201.9	1141.3	1085.4	1051.6	1014.0	998.8	982.1
35°	1009.5	950.3	894.9	847.3	819.9	798.7	779.5
37.5°	836.3	768.2	723.6	684.9	665.2	653.0	656.1
40°	729.0	669.3	636.6	607.2	588.9	580.2	582.2
42.5°	642.0	597.3	570.3	550.3	537.3	532.5	531.4
45°	543.2	518.2	496.1	484.6	478.2	473.0	469.6
47.5°	475.9	455.4	443.0	436.1	430.6	425.3	425.2
50°	435.5	422.0	413.3	406.0	401.8	397.9	401.2
52.5°	404.6	392.3	383.7	377.2	375.6	372.1	372.0
55°	358.9	349.3	343.1	337.2	334.4	332.4	330.1
57.5°	317.4	308.2	302.5	298.8	293.3	291.3	290.6
60°	287.8	280.5	274.8	269.9	267.5	263.6	263.6
62.5°	260.4	253.2	247.8	244.1	240.2	238.7	239.0
65°	220.8	215.1	209.8	205.9	205.0	202.1	203.0
67.5°	184.5	180.6	175.0	173.0	171.1	169.6	168.4
70°	160.2	156.4	153.4	150.6	149.1	149.1	149.1
72.5°	139.8	135.2	133.5	129.8	130.6	129.1	127.6
75°	108.3	105.4	104.0	102.5	100.1	100.1	100.1
77.5°	79.6	78.8	77.1	75.5	74.9	74.5	74.6
80°	61.5	61.1	60.1	60.1	59.2	58.7	57.8
82.5°	47.3	46.1	45.5	45.1	45.0	44.9	44.7
85°	27.0	26.0	26.0	26.5	25.5	25.5	26.0
87.5°	16.0	16.4	16.2	16.2	16.6	16.2	16.2
90°	28.2	30.1	31.0	31.0	31.0	31.0	31.0
92.5°	70.4	62.5	56.6	55.9	52.9	53.6	52.1
95°	189.1	149.6	128.8	116.7	109.1	106.3	107.3
97.5°	470.5	368.7	300.9	255.9	232.7	219.0	211.1
100°	742.2	613.3	499.5	421.4	381.0	353.7	336.8
102.5°	1018.4	924.2	803.5	718.7	649.6	615.6	592.7
105°	1249.2	1261.5	1230.4	1172.1	1113.8	1073.3	1060.2
107.5°	1232.3	1330.1	1375.6	1383.0	1379.8	1371.7	1354.2
110°	1179.6	1300.0	1377.1	1417.6	1435.5	1444.0	1443.0



TEST NUMBER: P331359-830

CATALOG NUMBER: S122DIP-S675D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1117.2	1245.9	1334.3	1390.5	1420.4	1436.4	1441.5
115°	1031.9	1155.2	1252.1	1318.8	1362.1	1386.6	1395.1
117.5°	962.7	1074.4	1165.4	1233.4	1279.1	1305.0	1312.0
120°	926.6	1026.2	1111.9	1177.7	1221.9	1249.2	1258.7
122.5°	896.5	990.9	1068.3	1127.3	1170.7	1195.0	1203.0
125°	857.0	939.7	1010.3	1064.9	1100.6	1124.1	1131.6
127.5°	818.6	896.6	961.8	1009.4	1042.8	1063.2	1069.2
130°	793.0	867.3	929.4	975.5	1007.5	1026.2	1033.8
132.5°	768.9	837.2	895.5	940.8	972.9	990.1	996.9
135°	730.9	793.0	845.6	886.1	917.2	934.1	937.8
137.5°	700.6	749.9	795.8	832.7	859.4	874.3	880.0
140°	681.1	724.3	765.7	795.8	820.3	834.4	840.0
142.5°	663.7	701.0	735.7	764.2	786.5	799.0	800.1
145°	641.6	670.7	698.0	720.6	736.6	745.9	748.8
147.5°	623.5	646.2	666.2	684.9	697.6	704.0	705.7
150°	611.4	631.2	648.1	662.2	673.5	679.2	680.1
152.5°	601.6	618.4	633.1	644.1	653.9	658.1	658.3
155°	586.1	600.1	610.5	620.9	627.5	631.2	629.3
157.5°	570.2	582.1	590.2	597.5	602.9	604.6	604.6
160°	559.7	570.0	576.6	583.2	588.0	588.9	588.9
162.5°	549.9	558.7	563.8	570.4	573.6	574.6	573.8
165°	535.3	541.9	545.6	549.3	553.1	553.1	552.1
167.5°	521.9	526.4	529.8	531.5	533.6	533.4	532.3
170°	513.6	517.4	519.2	520.2	523.0	522.1	520.2
172.5°	506.1	509.1	510.2	511.1	512.5	511.5	510.4
175°	497.7	498.6	499.5	499.5	500.5	499.5	497.7
177.5°	491.4	492.2	492.2	492.2	492.2	491.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2

(END OF REPORT)