

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331629-830

Luminaire Tested: **S122RDIP-S290D725U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331629-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D725U830-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3734.4 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	89	86	83	84	80	77	75	63	61	59	47	46	45	33	32	32	25
2	85	79	73	68	76	71	66	62	56	53	50	42	40	38	29	28	27	22
3	78	69	63	57	70	63	57	52	50	46	42	38	35	33	27	25	24	19
4	72	62	54	49	64	56	49	45	44	40	36	34	31	29	24	22	21	17
5	66	55	48	42	59	50	43	38	40	35	32	31	27	25	22	20	19	15
6	61	49	42	36	54	45	38	34	36	31	28	28	25	22	20	18	17	13
7	56	45	37	32	50	41	34	30	33	28	25	25	22	20	18	16	15	12
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	14	11
9	49	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12	10
10	45	34	27	23	41	31	25	21	25	21	18	20	17	15	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9947	9947	9947	9947
5°	11110	10010	8877	10010
10°	12329	9940	7694	9940
15°	12933	9795	6063	9795
20°	11213	9579	5246	9579
25°	7352	9283	4684	9283
30°	4950	8925	4238	8925
35°	4009	8474	3824	8474
40°	3564	7982	3539	7982
45°	3226	7405	3158	7405
50°	2936	6835	2926	6835
55°	2759	6201	2725	6201
60°	2309	5622	2283	5622
65°	1948	5104	2208	5104
70°	1799	4556	2082	4556
75°	1684	3968	1921	3968
80°	1553	3273	1711	3273
85°	1426	2575	1501	2575



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.4	1.6
10°-20°	162.8	4.4
20°-30°	209.7	5.6
30°-40°	199.3	5.3
40°-50°	170.7	4.6
50°-60°	130.0	3.5
60°-70°	82.2	2.2
70°-80°	41.0	1.1
80°-90°	14.1	0.4
90°-100°	153.2	4.1
100°-110°	519.8	13.9
110°-120°	552.3	14.8
120°-130°	454.6	12.2
130°-140°	365.1	9.8
140°-150°	275.9	7.4
150°-160°	193.9	5.2
160°-170°	114.1	3.1
170°-180°	37.1	1.0
0°-30°	430.9	11.5
0°-40°	630.2	16.9
0°-60°	931.0	24.9
0°-90°	1068.3	28.6
90°-120°	1225.3	32.8
90°-150°	2320.9	62.1
90°-180°	2666.0	71.4
0°-180°	3734.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	616	616	616	616	616	
5°	686	618	548	618	686	68
15°	774	586	363	586	774	209
25°	413	521	263	521	413	196
35°	203	430	194	430	203	130
45°	141	324	138	324	141	109
55°	98	220	97	220	98	86
65°	51	134	58	134	51	52
75°	27	64	31	64	27	29
85°	8	14	8	14	8	9
90°	24	1	24	1	24	13
95°	84	26	84	26	84	109
105°	830	90	830	90	830	803
115°	1093	158	1093	158	1093	1070
125°	886	221	886	221	886	801
135°	735	259	735	259	735	571
145°	586	296	586	296	586	372
155°	493	337	493	337	493	230
165°	432	367	432	367	432	124
175°	390	382	390	382	390	38
180°	383	383	383	383	383	



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	641.2	641.7	642.2	641.0	641.0	640.0	637.7	636.0	631.2	630.6	630.6
5°	685.5	685.1	686.0	683.2	679.4	678.4	674.4	669.0	663.5	657.3	656.0
7.5°	729.6	729.0	727.3	726.8	723.9	717.4	710.9	703.9	694.7	685.6	681.1
10°	752.0	759.0	754.7	747.2	748.7	738.7	733.3	724.1	716.3	702.9	699.9
12.5°	773.8	776.7	775.2	771.0	769.1	762.1	754.9	746.9	732.6	720.6	710.0
15°	773.7	777.8	778.9	777.6	778.6	778.3	774.4	767.8	755.4	742.1	730.5
17.5°	716.6	719.4	726.5	731.2	737.3	749.9	756.2	758.6	756.8	749.1	741.0
20°	652.6	647.9	667.6	677.6	686.2	707.6	726.0	733.1	744.4	744.2	742.1
22.5°	561.8	562.9	581.5	593.5	618.5	640.0	660.9	687.5	709.5	724.0	732.4
25°	412.7	420.9	439.5	455.8	483.6	523.5	559.7	601.6	641.2	672.5	702.3
27.5°	310.0	310.7	325.4	340.4	356.9	389.6	435.2	485.2	541.7	588.3	641.9
30°	265.5	264.2	270.4	279.7	293.8	319.1	353.3	402.5	458.8	529.0	591.5
32.5°	233.9	234.0	238.7	245.5	257.2	274.3	297.7	337.8	391.0	460.1	533.3
35°	203.4	203.2	206.6	211.5	216.4	227.3	243.5	264.4	301.0	365.4	440.4
37.5°	181.4	182.4	184.1	187.2	192.6	198.7	208.3	222.4	248.5	286.6	349.6
40°	169.1	169.6	171.9	174.5	177.7	182.4	190.3	201.7	220.7	251.1	297.2
42.5°	157.9	158.3	159.9	162.3	164.9	169.6	176.2	186.0	201.4	225.1	263.1
45°	141.3	141.3	142.8	143.8	146.7	150.9	156.3	164.5	175.1	192.7	217.9
47.5°	125.8	125.8	126.9	128.7	130.4	133.7	139.0	145.7	153.4	167.0	188.6
50°	116.9	117.2	117.7	119.2	120.4	123.3	127.4	133.2	141.3	151.8	169.8
52.5°	109.7	109.6	110.4	111.0	111.8	113.9	117.0	122.1	129.3	138.5	153.4
55°	98.0	97.2	98.5	99.5	100.2	101.0	102.7	105.9	112.2	119.9	131.0
57.5°	83.5	83.1	84.1	85.0	87.1	89.4	90.9	92.8	96.0	101.6	112.6
60°	71.5	71.5	73.4	74.1	76.4	79.5	82.5	84.2	87.4	91.0	99.2
62.5°	60.9	61.1	61.9	62.6	63.9	67.6	71.8	75.6	78.6	82.1	87.5
65°	51.0	51.4	51.4	51.8	52.7	53.5	55.2	58.2	63.6	68.5	72.6
67.5°	43.3	43.4	43.5	43.9	44.1	45.1	45.8	47.1	48.4	53.0	58.1
70°	38.1	38.7	38.5	38.9	39.2	39.6	40.4	41.1	43.1	44.1	47.1
72.5°	33.3	33.7	33.7	34.0	34.6	34.7	35.3	36.0	37.2	38.1	39.8
75°	27.0	26.8	27.0	27.4	27.6	27.8	27.8	28.7	29.3	30.2	31.3
77.5°	20.8	21.0	21.0	21.0	21.1	21.5	21.4	21.8	22.4	22.9	23.4
80°	16.7	16.9	16.7	16.9	17.2	17.3	17.2	17.3	18.0	18.4	18.4
82.5°	12.9	13.0	13.1	13.1	13.2	13.2	13.6	13.6	14.0	13.9	14.1
85°	7.7	7.5	7.5	7.5	7.7	7.9	7.7	7.7	7.9	7.9	7.9
87.5°	7.6	7.7	7.7	7.7	7.7	7.6	7.4	7.8	7.7	8.1	7.7
90°	24.3	24.3	24.3	24.3	24.3	23.6	22.1	23.6	24.3	25.1	24.3
92.5°	40.8	42.0	41.4	43.7	44.4	48.9	55.1	64.3	80.9	95.8	94.4
95°	84.0	83.2	85.5	91.3	100.9	117.2	148.1	193.0	252.7	288.8	255.7
97.5°	165.3	171.5	182.3	200.4	235.6	288.8	368.5	450.4	517.3	493.0	371.4
100°	263.7	277.0	298.4	330.1	391.2	480.4	581.4	672.7	688.2	582.0	400.8
102.5°	464.2	482.1	508.8	562.9	629.3	723.8	797.7	818.3	751.8	585.0	389.6
105°	830.4	840.7	872.3	918.0	963.7	988.1	978.5	895.2	742.0	545.9	367.7
107.5°	1060.6	1074.4	1080.7	1083.3	1077.5	1041.8	965.2	839.8	677.2	504.1	356.8
110°	1130.2	1131.0	1124.4	1110.3	1078.6	1018.2	924.0	792.0	636.6	484.1	354.4



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1129.1	<i>1125.1</i>	1112.6	1089.1	1045.1	975.8	875.0	748.5	608.3	471.1	355.0
115°	1092.7	<i>1086.0</i>	1066.9	1032.9	980.6	904.7	808.2	694.7	573.3	456.9	358.1
117.5°	1027.7	<i>1022.1</i>	1001.9	966.1	912.8	841.6	754.0	654.4	551.1	449.9	363.4
120°	985.8	<i>978.5</i>	957.1	922.5	870.9	803.8	725.8	634.3	539.3	445.7	366.9
122.5°	942.2	<i>936.0</i>	917.0	883.0	836.7	776.1	702.2	618.5	529.3	443.4	371.1
125°	886.4	<i>880.4</i>	862.0	834.1	791.3	736.0	671.2	595.3	515.0	439.1	377.2
127.5°	837.4	<i>832.7</i>	816.8	790.6	753.3	702.3	641.1	572.5	501.7	436.6	383.6
130°	809.7	<i>803.8</i>	789.1	764.0	727.9	679.3	621.1	557.7	492.9	435.5	388.3
132.5°	780.8	<i>775.5</i>	762.0	737.0	701.4	655.7	602.3	543.6	485.9	434.9	393.0
135°	734.6	<i>731.6</i>	718.4	694.1	662.3	621.1	572.5	523.9	476.0	433.9	398.6
137.5°	689.2	<i>684.8</i>	673.2	652.2	623.3	587.4	548.7	508.1	469.0	433.9	403.6
140°	658.0	<i>653.6</i>	642.4	623.3	599.7	567.3	533.5	498.0	465.0	433.2	406.0
142.5°	626.7	<i>625.8</i>	616.0	598.6	576.2	549.0	519.9	489.8	460.8	433.2	407.7
145°	586.4	<i>584.3</i>	576.9	564.4	546.7	525.4	502.5	478.2	455.3	431.8	409.6
147.5°	552.7	<i>551.4</i>	546.4	536.4	521.8	506.1	488.3	469.2	449.8	429.1	410.3
150°	532.7	<i>532.0</i>	527.5	518.7	507.7	494.4	478.9	462.7	445.0	427.3	409.6
152.5°	515.6	<i>515.5</i>	512.2	504.5	495.9	484.4	471.3	456.2	440.9	424.4	408.5
155°	492.9	<i>494.4</i>	491.4	486.3	478.2	470.0	459.0	447.2	433.2	419.2	406.7
157.5°	473.6	<i>473.6</i>	472.3	468.0	462.2	455.9	446.7	436.8	426.0	414.0	403.3
160°	461.2	<i>461.2</i>	460.5	456.9	451.7	446.5	438.4	430.3	420.8	410.4	401.5
162.5°	449.4	<i>450.1</i>	449.3	446.8	441.7	437.6	430.7	423.8	415.9	407.5	399.8
165°	432.5	<i>433.2</i>	433.2	430.3	427.3	424.4	419.2	414.1	408.2	401.5	396.4
167.5°	416.9	<i>417.7</i>	417.9	416.3	415.0	412.3	408.8	404.8	400.5	396.4	393.0
170°	407.5	<i>408.9</i>	409.6	407.5	406.7	405.2	402.3	400.1	396.4	393.4	391.2
172.5°	399.8	<i>400.7</i>	401.4	400.4	399.6	398.8	396.4	394.7	392.3	389.9	388.9
175°	389.7	<i>391.2</i>	392.0	391.2	391.2	390.5	389.7	389.0	386.8	386.1	385.3
177.5°	383.7	<i>384.9</i>	385.5	385.5	385.5	385.5	384.9	384.9	383.7	383.1	383.7
180°	383.1	<i>383.1</i>	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	630.9	629.5	628.3	625.3	623.7	620.3	619.8	619.6	615.2	610.9	609.6
5°	652.6	649.1	644.0	638.0	631.8	625.4	621.1	617.6	609.1	601.0	596.3
7.5°	674.4	667.0	658.2	646.9	637.3	626.8	618.9	611.8	599.6	588.0	580.1
10°	690.7	678.7	666.9	651.3	639.0	627.1	616.0	606.3	592.7	577.2	566.3
12.5°	700.8	687.6	671.4	656.1	640.3	625.0	610.1	597.8	581.6	565.7	552.8
15°	714.4	700.3	680.6	658.7	638.5	618.5	601.4	586.0	565.1	545.9	530.1
17.5°	725.7	706.2	685.0	659.8	636.2	611.0	588.9	569.2	545.8	522.8	504.2
20°	729.2	709.9	685.5	660.3	632.4	602.7	578.9	557.5	532.4	507.4	486.0
22.5°	727.0	712.0	684.9	654.6	626.1	595.0	568.2	543.3	515.5	489.9	465.1
25°	711.9	706.7	681.1	648.1	615.6	579.4	548.3	521.1	489.5	462.0	435.1
27.5°	676.7	687.8	671.8	636.7	600.5	561.8	526.8	495.9	463.0	432.2	405.3
30°	642.7	668.2	661.4	628.8	588.3	550.3	511.0	478.7	443.7	411.9	385.4
32.5°	596.3	638.4	645.1	617.8	576.0	534.1	493.0	460.9	424.2	390.9	365.0
35°	522.4	585.3	614.3	596.9	555.0	509.7	467.4	429.9	393.0	360.1	334.4
37.5°	434.2	520.0	568.2	569.4	530.8	483.9	437.7	400.5	362.8	330.5	302.7
40°	377.0	470.0	532.7	546.6	514.1	463.4	416.6	378.7	342.0	310.2	278.3
42.5°	325.6	418.2	495.3	519.5	493.7	443.3	396.4	356.8	321.0	291.1	258.4
45°	263.3	344.3	429.2	472.5	458.2	411.5	362.0	324.3	290.8	264.9	233.6
47.5°	222.2	279.2	361.5	419.9	419.7	377.1	328.4	292.4	261.2	236.9	211.6
50°	198.7	248.4	317.9	384.3	389.8	354.1	307.8	272.1	243.0	217.5	197.2
52.5°	177.6	218.6	281.1	344.8	360.6	329.6	284.7	251.8	223.5	200.0	182.7
55°	150.1	181.8	229.3	288.8	312.8	291.0	251.1	220.3	197.4	177.7	162.7
57.5°	127.0	150.7	188.9	236.8	264.7	251.0	218.1	193.0	173.4	155.6	143.8
60°	112.4	131.9	164.2	204.2	235.1	225.5	197.4	174.1	157.4	141.9	130.8
62.5°	98.7	115.5	143.2	175.7	203.9	199.9	177.0	157.4	142.8	128.8	119.3
65°	79.5	91.6	113.3	138.7	161.5	163.3	146.8	133.6	120.6	109.4	101.0
67.5°	63.2	71.3	86.4	107.9	124.9	131.0	120.9	110.7	100.4	91.8	84.5
70°	53.3	59.8	70.9	88.2	103.9	110.3	104.4	96.5	87.6	80.5	74.3
72.5°	43.2	49.5	57.7	70.4	83.8	90.8	88.7	83.0	75.8	69.8	64.0
75°	32.5	34.5	40.1	48.6	59.1	65.1	66.5	63.6	57.8	53.3	49.9
77.5°	24.0	25.3	27.9	32.3	39.2	44.6	46.8	46.4	42.4	39.9	36.6
80°	19.2	19.9	21.2	23.1	28.3	33.6	35.2	35.2	32.3	31.3	28.1
82.5°	14.6	15.1	15.9	17.0	19.3	24.0	25.7	26.0	24.3	22.9	20.4
85°	8.4	8.1	8.6	9.2	9.6	10.9	13.5	13.9	13.5	11.8	11.1
87.5°	6.9	6.0	5.3	4.7	4.5	4.4	4.7	5.1	4.9	4.9	4.9
90°	19.9	14.7	11.0	8.9	7.4	5.9	2.9	0.8	2.9	5.9	7.4
92.5°	73.5	50.1	33.5	26.5	21.5	18.3	13.0	9.0	13.0	18.3	21.5
95°	170.2	106.1	72.2	54.5	42.7	36.1	28.7	25.8	28.7	36.1	42.7
97.5°	229.3	140.0	97.4	77.4	63.8	53.8	46.0	42.0	46.0	53.8	63.8
100°	241.7	151.7	112.7	92.1	77.4	65.6	58.9	56.7	58.9	65.6	77.4
102.5°	242.2	162.4	126.3	105.7	90.3	78.5	71.9	70.3	71.9	78.5	90.3
105°	246.1	180.5	145.9	125.3	109.1	98.0	92.8	89.9	92.8	98.0	109.1
107.5°	256.3	199.1	165.5	144.7	128.7	118.5	113.5	111.1	113.5	118.5	128.7
110°	264.5	211.4	179.1	157.7	142.2	132.6	128.2	125.3	128.2	132.6	142.2



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	273.3	223.3	192.0	170.0	155.1	146.2	141.2	138.2	141.2	146.2	155.1
115°	286.6	241.7	210.0	190.1	175.3	166.5	162.1	158.4	162.1	166.5	175.3
117.5°	300.8	258.6	229.3	208.7	194.5	186.7	182.3	179.4	182.3	186.7	194.5
120°	310.2	270.4	241.7	221.0	206.3	199.6	195.3	192.3	195.3	199.6	206.3
122.5°	318.5	281.6	254.7	233.4	218.7	211.4	207.1	204.7	207.1	211.4	218.7
125°	331.6	298.4	271.8	251.3	236.5	227.6	223.3	221.0	223.3	227.6	236.5
127.5°	343.7	314.1	288.2	267.0	252.9	243.2	237.0	234.0	237.0	243.2	252.9
130°	351.5	323.5	297.7	277.0	262.3	251.9	244.6	241.7	244.6	251.9	262.3
132.5°	359.1	331.7	307.1	286.4	271.2	260.2	252.3	248.7	252.3	260.2	271.2
135°	369.1	343.4	319.8	299.2	282.2	271.2	262.3	259.4	262.3	271.2	282.2
137.5°	376.8	352.8	329.5	310.4	293.5	281.7	272.9	269.4	272.9	281.7	293.5
140°	380.9	358.1	336.0	316.8	300.6	288.8	279.9	277.0	279.9	288.8	300.6
142.5°	384.5	362.2	340.7	322.7	307.1	295.3	287.1	284.6	287.1	295.3	307.1
145°	389.0	368.4	348.5	332.2	317.5	306.5	299.2	296.1	299.2	306.5	317.5
147.5°	391.5	373.4	354.7	340.3	328.0	317.8	310.8	308.6	310.8	317.8	328.0
150°	392.7	375.8	358.8	345.5	334.5	324.9	319.1	316.8	319.1	324.9	334.5
152.5°	393.3	378.1	363.0	350.8	340.4	332.0	326.1	325.1	326.1	332.0	340.4
155°	394.2	381.6	369.1	358.1	350.0	341.9	337.4	336.7	337.4	341.9	350.0
157.5°	394.2	384.2	373.5	364.3	357.8	350.7	347.1	346.5	347.1	350.7	357.8
160°	394.2	385.3	376.5	368.4	362.5	356.6	353.6	352.9	353.6	356.6	362.5
162.5°	393.6	386.0	378.2	371.9	366.6	361.9	358.9	359.4	358.9	361.9	366.6
165°	392.0	386.8	380.2	375.8	372.1	367.7	366.2	366.9	366.2	367.7	372.1
167.5°	391.0	386.6	381.8	379.0	376.4	373.5	372.2	373.2	372.2	373.5	376.4
170°	389.7	386.1	382.4	380.2	378.7	376.5	375.8	377.2	375.8	376.5	378.7
172.5°	388.0	385.5	383.0	381.4	380.5	378.2	378.7	379.6	378.7	378.2	380.5
175°	386.1	384.6	383.1	382.4	382.4	380.9	381.6	382.4	381.6	380.9	382.4
177.5°	384.9	383.7	383.1	383.1	383.1	381.9	382.6	383.7	382.6	381.9	383.1
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	607.5	606.2	604.0	600.6	598.5	594.9	592.6	593.9	594.3	593.9	593.6
5°	591.2	586.6	580.4	574.4	568.8	562.9	559.4	558.0	555.0	553.3	552.3
7.5°	571.4	563.6	554.9	544.4	535.6	526.2	521.5	519.2	513.0	509.7	506.8
10°	556.7	544.4	535.6	522.0	513.6	501.4	493.0	493.3	484.9	480.2	476.8
12.5°	540.4	527.0	512.4	500.0	488.4	478.6	468.5	464.5	455.6	451.1	441.9
15°	513.4	497.8	482.4	465.7	453.9	438.7	424.1	406.3	392.0	379.6	376.2
17.5°	484.0	464.6	449.1	429.5	409.3	383.8	366.9	356.6	348.0	341.4	336.5
20°	463.7	444.0	427.5	398.0	370.8	353.5	341.1	333.1	324.1	317.1	313.2
22.5°	442.5	422.0	399.4	366.5	345.3	331.4	320.4	311.2	305.1	299.6	296.1
25°	412.4	389.8	352.8	330.2	313.0	298.4	290.8	285.2	278.8	271.3	267.9
27.5°	380.5	344.8	318.1	301.2	284.9	275.5	268.5	260.2	254.5	251.1	247.5
30°	356.7	320.9	300.2	281.7	270.2	259.7	251.6	246.9	241.3	235.5	233.2
32.5°	330.2	301.6	281.6	266.4	254.6	245.6	239.2	231.6	227.6	224.0	219.1
35°	297.2	275.5	257.3	245.0	233.8	226.5	219.0	214.5	207.3	204.2	202.4
37.5°	269.3	250.5	237.0	223.9	215.0	207.0	202.4	195.2	192.1	187.8	183.8
40°	253.4	235.1	222.1	211.3	201.4	195.5	189.7	183.9	179.2	177.3	172.4
42.5°	237.4	222.4	209.3	197.7	191.1	184.6	177.4	173.1	168.2	165.1	162.1
45°	215.2	201.9	190.8	181.2	173.8	167.2	162.5	155.4	152.7	146.5	143.8
47.5°	195.7	183.3	172.7	163.5	156.5	152.1	145.2	139.7	135.3	131.4	128.1
50°	181.8	171.4	161.2	153.1	146.7	140.4	133.4	130.6	123.8	121.8	119.9
52.5°	169.1	159.3	150.0	141.9	135.5	129.5	123.3	119.6	115.0	113.1	111.7
55°	151.4	141.9	133.0	125.9	119.5	113.3	109.4	104.9	102.7	101.2	99.5
57.5°	133.6	125.1	118.2	111.0	104.5	99.6	95.2	92.5	90.3	88.3	86.2
60°	122.2	114.1	107.9	101.2	94.6	90.6	87.2	83.9	81.3	78.3	77.5
62.5°	110.3	103.1	97.5	91.0	85.2	81.5	78.2	75.2	72.1	67.8	66.5
65°	93.8	88.2	82.2	76.8	71.7	68.1	63.3	59.9	58.6	58.2	58.1
67.5°	78.9	73.6	68.4	63.0	58.3	55.0	52.5	52.0	51.1	50.9	50.2
70°	68.9	64.0	58.9	53.7	49.2	48.6	47.8	46.8	45.8	45.4	45.0
72.5°	60.0	55.0	49.8	45.7	43.7	43.0	42.1	41.2	40.5	40.1	39.9
75°	46.0	41.3	37.9	36.4	35.3	34.7	33.4	32.8	32.3	31.7	31.5
77.5°	33.2	30.4	28.9	28.0	26.9	26.2	25.4	24.8	24.3	24.2	23.8
80°	25.3	23.9	22.9	21.6	21.2	20.4	20.2	19.5	19.7	19.0	19.0
82.5°	19.6	18.0	17.1	16.5	16.0	15.4	15.2	14.9	14.9	14.4	14.4
85°	10.1	9.6	9.2	8.8	8.8	8.1	8.4	8.1	8.1	7.7	7.5
87.5°	5.0	5.3	5.7	6.7	7.6	7.5	7.4	7.1	6.8	7.1	7.1
90°	8.9	11.0	14.7	19.9	24.3	25.1	24.3	23.6	22.1	23.6	24.3
92.5°	26.5	33.5	50.1	73.5	94.4	95.8	80.9	64.3	55.1	48.9	44.4
95°	54.5	72.2	106.1	170.2	255.7	288.8	252.7	193.0	148.1	117.2	100.9
97.5°	77.4	97.4	140.0	229.3	371.4	493.0	517.3	450.4	368.5	288.8	235.6
100°	92.1	112.7	151.7	241.7	400.8	582.0	688.2	672.7	581.4	480.4	391.2
102.5°	105.7	126.3	162.4	242.2	389.6	585.0	751.8	818.3	797.7	723.8	629.3
105°	125.3	145.9	180.5	246.1	367.7	545.9	742.0	895.2	978.5	988.1	963.7
107.5°	144.7	165.5	199.1	256.3	356.8	504.1	677.2	839.8	965.2	1041.8	1077.5
110°	157.7	179.1	211.4	264.5	354.4	484.1	636.6	792.0	924.0	1018.2	1078.6



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.0	192.0	223.3	273.3	355.0	471.1	608.3	748.5	875.0	975.8	1045.1
115°	190.1	210.0	241.7	286.6	358.1	456.9	573.3	694.7	808.2	904.7	980.6
117.5°	208.7	229.3	258.6	300.8	363.4	449.9	551.1	654.4	754.0	841.6	912.8
120°	221.0	241.7	270.4	310.2	366.9	445.7	539.3	634.3	725.8	803.8	870.9
122.5°	233.4	254.7	281.6	318.5	371.1	443.4	529.3	618.5	702.2	776.1	836.7
125°	251.3	271.8	298.4	331.6	377.2	439.1	515.0	595.3	671.2	736.0	791.3
127.5°	267.0	288.2	314.1	343.7	383.6	436.6	501.7	572.5	641.1	702.3	753.3
130°	277.0	297.7	323.5	351.5	388.3	435.5	492.9	557.7	621.1	679.3	727.9
132.5°	286.4	307.1	331.7	359.1	393.0	434.9	485.9	543.6	602.3	655.7	701.4
135°	299.2	319.8	343.4	369.1	398.6	433.9	476.0	523.9	572.5	621.1	662.3
137.5°	310.4	329.5	352.8	376.8	403.6	433.9	469.0	508.1	548.7	587.4	623.3
140°	316.8	336.0	358.1	380.9	406.0	433.2	465.0	498.0	533.5	567.3	599.7
142.5°	322.7	340.7	362.2	384.5	407.7	433.2	460.8	489.8	519.9	549.0	576.2
145°	332.2	348.5	368.4	389.0	409.6	431.8	455.3	478.2	502.5	525.4	546.7
147.5°	340.3	354.7	373.4	391.5	410.3	429.1	449.8	469.2	488.3	506.1	521.8
150°	345.5	358.8	375.8	392.7	409.6	427.3	445.0	462.7	478.9	494.4	507.7
152.5°	350.8	363.0	378.1	393.3	408.5	424.4	440.9	456.2	471.3	484.4	495.9
155°	358.1	369.1	381.6	394.2	406.7	419.2	433.2	447.2	459.0	470.0	478.2
157.5°	364.3	373.5	384.2	394.2	403.3	414.0	426.0	436.8	446.7	455.9	462.2
160°	368.4	376.5	385.3	394.2	401.5	410.4	420.8	430.3	438.4	446.5	451.7
162.5°	371.9	378.2	386.0	393.6	399.8	407.5	415.9	423.8	430.7	437.6	441.7
165°	375.8	380.2	386.8	392.0	396.4	401.5	408.2	414.1	419.2	424.4	427.3
167.5°	379.0	381.8	386.6	391.0	393.0	396.4	400.5	404.8	408.8	412.3	415.0
170°	380.2	382.4	386.1	389.7	391.2	393.4	396.4	400.1	402.3	405.2	406.7
172.5°	381.4	383.0	385.5	388.0	388.9	389.9	392.3	394.7	396.4	398.8	399.6
175°	382.4	383.1	384.6	386.1	385.3	386.1	386.8	389.0	389.7	390.5	391.2
177.5°	383.1	383.1	383.7	384.9	383.7	383.1	383.7	384.9	384.9	385.5	385.5
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	591.7	592.0	591.5	591.8	591.5	592.0	591.7	593.6	593.9	594.3	593.9
5°	551.3	548.7	548.3	547.7	548.3	548.7	551.3	552.3	553.3	555.0	558.0
7.5°	503.1	502.8	501.6	500.1	501.6	502.8	503.1	506.8	509.7	513.0	519.2
10°	472.1	471.0	470.8	469.3	470.8	471.0	472.1	476.8	480.2	484.9	493.3
12.5°	435.7	428.9	428.2	424.4	428.2	428.9	435.7	441.9	451.1	455.6	464.5
15°	371.1	369.8	365.4	362.7	365.4	369.8	371.1	376.2	379.6	392.0	406.3
17.5°	334.0	329.8	328.5	327.9	328.5	329.8	334.0	336.5	341.4	348.0	356.6
20°	310.2	306.4	305.8	305.3	305.8	306.4	310.2	313.2	317.1	324.1	333.1
22.5°	293.8	289.7	288.1	286.8	288.1	289.7	293.8	296.1	299.6	305.1	311.2
25°	265.7	264.2	263.3	262.9	263.3	264.2	265.7	267.9	271.3	278.8	285.2
27.5°	243.7	240.4	239.8	238.7	239.8	240.4	243.7	247.5	251.1	254.5	260.2
30°	231.2	230.2	228.7	227.3	228.7	230.2	231.2	233.2	235.5	241.3	246.9
32.5°	216.5	215.6	214.2	213.7	214.2	215.6	216.5	219.1	224.0	227.6	231.6
35°	200.2	197.2	195.9	194.0	195.9	197.2	200.2	202.4	204.2	207.3	214.5
37.5°	182.9	181.3	179.6	180.2	179.6	181.3	182.9	183.8	187.8	192.1	195.2
40°	169.6	168.5	168.1	167.9	168.1	168.5	169.6	172.4	177.3	179.2	183.9
42.5°	158.9	156.0	154.9	154.9	154.9	156.0	158.9	162.1	165.1	168.2	173.1
45°	142.8	140.1	138.1	138.3	138.1	140.1	142.8	143.8	146.5	152.7	155.4
47.5°	126.3	126.2	125.0	125.4	125.0	126.2	126.3	128.1	131.4	135.3	139.7
50°	118.4	117.2	116.2	116.5	116.2	117.2	118.4	119.9	121.8	123.8	130.6
52.5°	110.8	109.7	109.1	110.0	109.1	109.7	110.8	111.7	113.1	115.0	119.6
55°	98.5	97.2	97.0	96.8	97.0	97.2	98.5	99.5	101.2	102.7	104.9
57.5°	84.6	83.8	82.5	82.0	82.5	83.8	84.6	86.2	88.3	90.3	92.5
60°	74.7	73.0	70.9	70.7	70.9	73.0	74.7	77.5	78.3	81.3	83.9
62.5°	65.6	65.3	64.8	64.8	64.8	65.3	65.6	66.5	67.8	72.1	75.2
65°	57.6	57.4	57.6	57.8	57.6	57.4	57.6	58.1	58.2	58.6	59.9
67.5°	50.1	49.8	49.4	49.6	49.4	49.8	50.1	50.2	50.9	51.1	52.0
70°	44.5	44.3	44.1	44.1	44.1	44.3	44.5	45.0	45.4	45.8	46.8
72.5°	39.0	39.0	38.8	38.6	38.8	39.0	39.0	39.9	40.1	40.5	41.2
75°	31.3	30.8	30.8	30.8	30.8	30.8	31.3	31.5	31.7	32.3	32.8
77.5°	23.8	23.6	23.4	23.2	23.4	23.6	23.8	23.8	24.2	24.3	24.8
80°	18.9	18.7	18.4	18.4	18.4	18.7	18.9	19.0	19.0	19.7	19.5
82.5°	14.4	14.1	14.1	13.9	14.1	14.1	14.4	14.4	14.4	14.9	14.9
85°	7.7	7.9	7.7	8.1	7.7	7.9	7.7	7.5	7.7	8.1	8.1
87.5°	7.1	6.9	7.1	6.9	7.1	6.9	7.1	7.1	7.1	6.8	7.1
90°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	23.6	22.1	23.6
92.5°	43.7	41.4	42.0	40.8	42.0	41.4	43.7	44.4	48.9	55.1	64.3
95°	91.3	85.5	83.2	84.0	83.2	85.5	91.3	100.9	117.2	148.1	193.0
97.5°	200.4	182.3	171.5	165.3	171.5	182.3	200.4	235.6	288.8	368.5	450.4
100°	330.1	298.4	277.0	263.7	277.0	298.4	330.1	391.2	480.4	581.4	672.7
102.5°	562.9	508.8	482.1	464.2	482.1	508.8	562.9	629.3	723.8	797.7	818.3
105°	918.0	872.3	840.7	830.4	840.7	872.3	918.0	963.7	988.1	978.5	895.2
107.5°	1083.3	1080.7	1074.4	1060.6	1074.4	1080.7	1083.3	1077.5	1041.8	965.2	839.8
110°	1110.3	1124.4	1131.0	1130.2	1131.0	1124.4	1110.3	1078.6	1018.2	924.0	792.0



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1089.1	1112.6	1125.1	1129.1	1125.1	1112.6	1089.1	1045.1	975.8	875.0	748.5
115°	1032.9	1066.9	1086.0	1092.7	1086.0	1066.9	1032.9	980.6	904.7	808.2	694.7
117.5°	966.1	1001.9	1022.1	1027.7	1022.1	1001.9	966.1	912.8	841.6	754.0	654.4
120°	922.5	957.1	978.5	985.8	978.5	957.1	922.5	870.9	803.8	725.8	634.3
122.5°	883.0	917.0	936.0	942.2	936.0	917.0	883.0	836.7	776.1	702.2	618.5
125°	834.1	862.0	880.4	886.4	880.4	862.0	834.1	791.3	736.0	671.2	595.3
127.5°	790.6	816.8	832.7	837.4	832.7	816.8	790.6	753.3	702.3	641.1	572.5
130°	764.0	789.1	803.8	809.7	803.8	789.1	764.0	727.9	679.3	621.1	557.7
132.5°	737.0	762.0	775.5	780.8	775.5	762.0	737.0	701.4	655.7	602.3	543.6
135°	694.1	718.4	731.6	734.6	731.6	718.4	694.1	662.3	621.1	572.5	523.9
137.5°	652.2	673.2	684.8	689.2	684.8	673.2	652.2	623.3	587.4	548.7	508.1
140°	623.3	642.4	653.6	658.0	653.6	642.4	623.3	599.7	567.3	533.5	498.0
142.5°	598.6	616.0	625.8	626.7	625.8	616.0	598.6	576.2	549.0	519.9	489.8
145°	564.4	576.9	584.3	586.4	584.3	576.9	564.4	546.7	525.4	502.5	478.2
147.5°	536.4	546.4	551.4	552.7	551.4	546.4	536.4	521.8	506.1	488.3	469.2
150°	518.7	527.5	532.0	532.7	532.0	527.5	518.7	507.7	494.4	478.9	462.7
152.5°	504.5	512.2	515.5	515.6	515.5	512.2	504.5	495.9	484.4	471.3	456.2
155°	486.3	491.4	494.4	492.9	494.4	491.4	486.3	478.2	470.0	459.0	447.2
157.5°	468.0	472.3	473.6	473.6	473.6	472.3	468.0	462.2	455.9	446.7	436.8
160°	456.9	460.5	461.2	461.2	461.2	460.5	456.9	451.7	446.5	438.4	430.3
162.5°	446.8	449.3	450.1	449.4	450.1	449.3	446.8	441.7	437.6	430.7	423.8
165°	430.3	433.2	433.2	432.5	433.2	433.2	430.3	427.3	424.4	419.2	414.1
167.5°	416.3	417.9	417.7	416.9	417.7	417.9	416.3	415.0	412.3	408.8	404.8
170°	407.5	409.6	408.9	407.5	408.9	409.6	407.5	406.7	405.2	402.3	400.1
172.5°	400.4	401.4	400.7	399.8	400.7	401.4	400.4	399.6	398.8	396.4	394.7
175°	391.2	392.0	391.2	389.7	391.2	392.0	391.2	391.2	390.5	389.7	389.0
177.5°	385.5	385.5	384.9	383.7	384.9	385.5	385.5	385.5	385.5	384.9	384.9
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	592.6	594.9	598.5	600.6	604.0	606.2	607.5	609.6	610.9	615.2	619.6
5°	559.4	562.9	568.8	574.4	580.4	586.6	591.2	596.3	601.0	609.1	617.6
7.5°	521.5	526.2	535.6	544.4	554.9	563.6	571.4	580.1	588.0	599.6	611.8
10°	493.0	501.4	513.6	522.0	535.6	544.4	556.7	566.3	577.2	592.7	606.3
12.5°	468.5	478.6	488.4	500.0	512.4	527.0	540.4	552.8	565.7	581.6	597.8
15°	424.1	438.7	453.9	465.7	482.4	497.8	513.4	530.1	545.9	565.1	586.0
17.5°	366.9	383.8	409.3	429.5	449.1	464.6	484.0	504.2	522.8	545.8	569.2
20°	341.1	353.5	370.8	398.0	427.5	444.0	463.7	486.0	507.4	532.4	557.5
22.5°	320.4	331.4	345.3	366.5	399.4	422.0	442.5	465.1	489.9	515.5	543.3
25°	290.8	298.4	313.0	330.2	352.8	389.8	412.4	435.1	462.0	489.5	521.1
27.5°	268.5	275.5	284.9	301.2	318.1	344.8	380.5	405.3	432.2	463.0	495.9
30°	251.6	259.7	270.2	281.7	300.2	320.9	356.7	385.4	411.9	443.7	478.7
32.5°	239.2	245.6	254.6	266.4	281.6	301.6	330.2	365.0	390.9	424.2	460.9
35°	219.0	226.5	233.8	245.0	257.3	275.5	297.2	334.4	360.1	393.0	429.9
37.5°	202.4	207.0	215.0	223.9	237.0	250.5	269.3	302.7	330.5	362.8	400.5
40°	189.7	195.5	201.4	211.3	222.1	235.1	253.4	278.3	310.2	342.0	378.7
42.5°	177.4	184.6	191.1	197.7	209.3	222.4	237.4	258.4	291.1	321.0	356.8
45°	162.5	167.2	173.8	181.2	190.8	201.9	215.2	233.6	264.9	290.8	324.3
47.5°	145.2	152.1	156.5	163.5	172.7	183.3	195.7	211.6	236.9	261.2	292.4
50°	133.4	140.4	146.7	153.1	161.2	171.4	181.8	197.2	217.5	243.0	272.1
52.5°	123.3	129.5	135.5	141.9	150.0	159.3	169.1	182.7	200.0	223.5	251.8
55°	109.4	113.3	119.5	125.9	133.0	141.9	151.4	162.7	177.7	197.4	220.3
57.5°	95.2	99.6	104.5	111.0	118.2	125.1	133.6	143.8	155.6	173.4	193.0
60°	87.2	90.6	94.6	101.2	107.9	114.1	122.2	130.8	141.9	157.4	174.1
62.5°	78.2	81.5	85.2	91.0	97.5	103.1	110.3	119.3	128.8	142.8	157.4
65°	63.3	68.1	71.7	76.8	82.2	88.2	93.8	101.0	109.4	120.6	133.6
67.5°	52.5	55.0	58.3	63.0	68.4	73.6	78.9	84.5	91.8	100.4	110.7
70°	47.8	48.6	49.2	53.7	58.9	64.0	68.9	74.3	80.5	87.6	96.5
72.5°	42.1	43.0	43.7	45.7	49.8	55.0	60.0	64.0	69.8	75.8	83.0
75°	33.4	34.7	35.3	36.4	37.9	41.3	46.0	49.9	53.3	57.8	63.6
77.5°	25.4	26.2	26.9	28.0	28.9	30.4	33.2	36.6	39.9	42.4	46.4
80°	20.2	20.4	21.2	21.6	22.9	23.9	25.3	28.1	31.3	32.3	35.2
82.5°	15.2	15.4	16.0	16.5	17.1	18.0	19.6	20.4	22.9	24.3	26.0
85°	8.4	8.1	8.8	8.8	9.2	9.6	10.1	11.1	11.8	13.5	13.9
87.5°	7.4	7.5	7.6	6.7	5.7	5.3	5.0	4.9	4.9	4.9	5.1
90°	24.3	25.1	24.3	19.9	14.7	11.0	8.9	7.4	5.9	2.9	0.8
92.5°	80.9	95.8	94.4	73.5	50.1	33.5	26.5	21.5	18.3	13.0	9.0
95°	252.7	288.8	255.7	170.2	106.1	72.2	54.5	42.7	36.1	28.7	25.8
97.5°	517.3	493.0	371.4	229.3	140.0	97.4	77.4	63.8	53.8	46.0	42.0
100°	688.2	582.0	400.8	241.7	151.7	112.7	92.1	77.4	65.6	58.9	56.7
102.5°	751.8	585.0	389.6	242.2	162.4	126.3	105.7	90.3	78.5	71.9	70.3
105°	742.0	545.9	367.7	246.1	180.5	145.9	125.3	109.1	98.0	92.8	89.9
107.5°	677.2	504.1	356.8	256.3	199.1	165.5	144.7	128.7	118.5	113.5	111.1
110°	636.6	484.1	354.4	264.5	211.4	179.1	157.7	142.2	132.6	128.2	125.3



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	608.3	471.1	355.0	273.3	223.3	192.0	170.0	155.1	146.2	141.2	138.2
115°	573.3	456.9	358.1	286.6	241.7	210.0	190.1	175.3	166.5	162.1	158.4
117.5°	551.1	449.9	363.4	300.8	258.6	229.3	208.7	194.5	186.7	182.3	179.4
120°	539.3	445.7	366.9	310.2	270.4	241.7	221.0	206.3	199.6	195.3	192.3
122.5°	529.3	443.4	371.1	318.5	281.6	254.7	233.4	218.7	211.4	207.1	204.7
125°	515.0	439.1	377.2	331.6	298.4	271.8	251.3	236.5	227.6	223.3	221.0
127.5°	501.7	436.6	383.6	343.7	314.1	288.2	267.0	252.9	243.2	237.0	234.0
130°	492.9	435.5	388.3	351.5	323.5	297.7	277.0	262.3	251.9	244.6	241.7
132.5°	485.9	434.9	393.0	359.1	331.7	307.1	286.4	271.2	260.2	252.3	248.7
135°	476.0	433.9	398.6	369.1	343.4	319.8	299.2	282.2	271.2	262.3	259.4
137.5°	469.0	433.9	403.6	376.8	352.8	329.5	310.4	293.5	281.7	272.9	269.4
140°	465.0	433.2	406.0	380.9	358.1	336.0	316.8	300.6	288.8	279.9	277.0
142.5°	460.8	433.2	407.7	384.5	362.2	340.7	322.7	307.1	295.3	287.1	284.6
145°	455.3	431.8	409.6	389.0	368.4	348.5	332.2	317.5	306.5	299.2	296.1
147.5°	449.8	429.1	410.3	391.5	373.4	354.7	340.3	328.0	317.8	310.8	308.6
150°	445.0	427.3	409.6	392.7	375.8	358.8	345.5	334.5	324.9	319.1	316.8
152.5°	440.9	424.4	408.5	393.3	378.1	363.0	350.8	340.4	332.0	326.1	325.1
155°	433.2	419.2	406.7	394.2	381.6	369.1	358.1	350.0	341.9	337.4	336.7
157.5°	426.0	414.0	403.3	394.2	384.2	373.5	364.3	357.8	350.7	347.1	346.5
160°	420.8	410.4	401.5	394.2	385.3	376.5	368.4	362.5	356.6	353.6	352.9
162.5°	415.9	407.5	399.8	393.6	386.0	378.2	371.9	366.6	361.9	358.9	359.4
165°	408.2	401.5	396.4	392.0	386.8	380.2	375.8	372.1	367.7	366.2	366.9
167.5°	400.5	396.4	393.0	391.0	386.6	381.8	379.0	376.4	373.5	372.2	373.2
170°	396.4	393.4	391.2	389.7	386.1	382.4	380.2	378.7	376.5	375.8	377.2
172.5°	392.3	389.9	388.9	388.0	385.5	383.0	381.4	380.5	378.2	378.7	379.6
175°	386.8	386.1	385.3	386.1	384.6	383.1	382.4	382.4	380.9	381.6	382.4
177.5°	383.7	383.1	383.7	384.9	383.7	383.1	383.1	383.1	381.9	382.6	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	619.8	620.3	623.7	625.3	628.3	629.5	630.9	630.6	630.6	631.2	636.0
5°	621.1	625.4	631.8	638.0	644.0	649.1	652.6	656.0	657.3	663.5	669.0
7.5°	618.9	626.8	637.3	646.9	658.2	667.0	674.4	681.1	685.6	694.7	703.9
10°	616.0	627.1	639.0	651.3	666.9	678.7	690.7	699.9	702.9	716.3	724.1
12.5°	610.1	625.0	640.3	656.1	671.4	687.6	700.8	710.0	720.6	732.6	746.9
15°	601.4	618.5	638.5	658.7	680.6	700.3	714.4	730.5	742.1	755.4	767.8
17.5°	588.9	611.0	636.2	659.8	685.0	706.2	725.7	741.0	749.1	756.8	758.6
20°	578.9	602.7	632.4	660.3	685.5	709.9	729.2	742.1	744.2	744.4	733.1
22.5°	568.2	595.0	626.1	654.6	684.9	712.0	727.0	732.4	724.0	709.5	687.5
25°	548.3	579.4	615.6	648.1	681.1	706.7	711.9	702.3	672.5	641.2	601.6
27.5°	526.8	561.8	600.5	636.7	671.8	687.8	676.7	641.9	588.3	541.7	485.2
30°	511.0	550.3	588.3	628.8	661.4	668.2	642.7	591.5	529.0	458.8	402.5
32.5°	493.0	534.1	576.0	617.8	645.1	638.4	596.3	533.3	460.1	391.0	337.8
35°	467.4	509.7	555.0	596.9	614.3	585.3	522.4	440.4	365.4	301.0	264.4
37.5°	437.7	483.9	530.8	569.4	568.2	520.0	434.2	349.6	286.6	248.5	222.4
40°	416.6	463.4	514.1	546.6	532.7	470.0	377.0	297.2	251.1	220.7	201.7
42.5°	396.4	443.3	493.7	519.5	495.3	418.2	325.6	263.1	225.1	201.4	186.0
45°	362.0	411.5	458.2	472.5	429.2	344.3	263.3	217.9	192.7	175.1	164.5
47.5°	328.4	377.1	419.7	419.9	361.5	279.2	222.2	188.6	167.0	153.4	145.7
50°	307.8	354.1	389.8	384.3	317.9	248.4	198.7	169.8	151.8	141.3	133.2
52.5°	284.7	329.6	360.6	344.8	281.1	218.6	177.6	153.4	138.5	129.3	122.1
55°	251.1	291.0	312.8	288.8	229.3	181.8	150.1	131.0	119.9	112.2	105.9
57.5°	218.1	251.0	264.7	236.8	188.9	150.7	127.0	112.6	101.6	96.0	92.8
60°	197.4	225.5	235.1	204.2	164.2	131.9	112.4	99.2	91.0	87.4	84.2
62.5°	177.0	199.9	203.9	175.7	143.2	115.5	98.7	87.5	82.1	78.6	75.6
65°	146.8	163.3	161.5	138.7	113.3	91.6	79.5	72.6	68.5	63.6	58.2
67.5°	120.9	131.0	124.9	107.9	86.4	71.3	63.2	58.1	53.0	48.4	47.1
70°	104.4	110.3	103.9	88.2	70.9	59.8	53.3	47.1	44.1	43.1	41.1
72.5°	88.7	90.8	83.8	70.4	57.7	49.5	43.2	39.8	38.1	37.2	36.0
75°	66.5	65.1	59.1	48.6	40.1	34.5	32.5	31.3	30.2	29.3	28.7
77.5°	46.8	44.6	39.2	32.3	27.9	25.3	24.0	23.4	22.9	22.4	21.8
80°	35.2	33.6	28.3	23.1	21.2	19.9	19.2	18.4	18.4	18.0	17.3
82.5°	25.7	24.0	19.3	17.0	15.9	15.1	14.6	14.1	13.9	14.0	13.6
85°	13.5	10.9	9.6	9.2	8.6	8.1	8.4	7.9	7.9	7.9	7.7
87.5°	4.7	4.4	4.5	4.7	5.3	6.0	6.9	7.7	8.1	7.7	7.8
90°	2.9	5.9	7.4	8.9	11.0	14.7	19.9	24.3	25.1	24.3	23.6
92.5°	13.0	18.3	21.5	26.5	33.5	50.1	73.5	94.4	95.8	80.9	64.3
95°	28.7	36.1	42.7	54.5	72.2	106.1	170.2	255.7	288.8	252.7	193.0
97.5°	46.0	53.8	63.8	77.4	97.4	140.0	229.3	371.4	493.0	517.3	450.4
100°	58.9	65.6	77.4	92.1	112.7	151.7	241.7	400.8	582.0	688.2	672.7
102.5°	71.9	78.5	90.3	105.7	126.3	162.4	242.2	389.6	585.0	751.8	818.3
105°	92.8	98.0	109.1	125.3	145.9	180.5	246.1	367.7	545.9	742.0	895.2
107.5°	113.5	118.5	128.7	144.7	165.5	199.1	256.3	356.8	504.1	677.2	839.8
110°	128.2	132.6	142.2	157.7	179.1	211.4	264.5	354.4	484.1	636.6	792.0



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	141.2	146.2	155.1	170.0	192.0	223.3	273.3	355.0	471.1	608.3	748.5
115°	162.1	166.5	175.3	190.1	210.0	241.7	286.6	358.1	456.9	573.3	694.7
117.5°	182.3	186.7	194.5	208.7	229.3	258.6	300.8	363.4	449.9	551.1	654.4
120°	195.3	199.6	206.3	221.0	241.7	270.4	310.2	366.9	445.7	539.3	634.3
122.5°	207.1	211.4	218.7	233.4	254.7	281.6	318.5	371.1	443.4	529.3	618.5
125°	223.3	227.6	236.5	251.3	271.8	298.4	331.6	377.2	439.1	515.0	595.3
127.5°	237.0	243.2	252.9	267.0	288.2	314.1	343.7	383.6	436.6	501.7	572.5
130°	244.6	251.9	262.3	277.0	297.7	323.5	351.5	388.3	435.5	492.9	557.7
132.5°	252.3	260.2	271.2	286.4	307.1	331.7	359.1	393.0	434.9	485.9	543.6
135°	262.3	271.2	282.2	299.2	319.8	343.4	369.1	398.6	433.9	476.0	523.9
137.5°	272.9	281.7	293.5	310.4	329.5	352.8	376.8	403.6	433.9	469.0	508.1
140°	279.9	288.8	300.6	316.8	336.0	358.1	380.9	406.0	433.2	465.0	498.0
142.5°	287.1	295.3	307.1	322.7	340.7	362.2	384.5	407.7	433.2	460.8	489.8
145°	299.2	306.5	317.5	332.2	348.5	368.4	389.0	409.6	431.8	455.3	478.2
147.5°	310.8	317.8	328.0	340.3	354.7	373.4	391.5	410.3	429.1	449.8	469.2
150°	319.1	324.9	334.5	345.5	358.8	375.8	392.7	409.6	427.3	445.0	462.7
152.5°	326.1	332.0	340.4	350.8	363.0	378.1	393.3	408.5	424.4	440.9	456.2
155°	337.4	341.9	350.0	358.1	369.1	381.6	394.2	406.7	419.2	433.2	447.2
157.5°	347.1	350.7	357.8	364.3	373.5	384.2	394.2	403.3	414.0	426.0	436.8
160°	353.6	356.6	362.5	368.4	376.5	385.3	394.2	401.5	410.4	420.8	430.3
162.5°	358.9	361.9	366.6	371.9	378.2	386.0	393.6	399.8	407.5	415.9	423.8
165°	366.2	367.7	372.1	375.8	380.2	386.8	392.0	396.4	401.5	408.2	414.1
167.5°	372.2	373.5	376.4	379.0	381.8	386.6	391.0	393.0	396.4	400.5	404.8
170°	375.8	376.5	378.7	380.2	382.4	386.1	389.7	391.2	393.4	396.4	400.1
172.5°	378.7	378.2	380.5	381.4	383.0	385.5	388.0	388.9	389.9	392.3	394.7
175°	381.6	380.9	382.4	382.4	383.1	384.6	386.1	385.3	386.1	386.8	389.0
177.5°	382.6	381.9	383.1	383.1	383.1	383.7	384.9	383.7	383.1	383.7	384.9
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	637.7	640.0	641.0	641.0	642.2	641.7	641.2
5°	674.4	678.4	679.4	683.2	686.0	685.1	685.5
7.5°	710.9	717.4	723.9	726.8	727.3	729.0	729.6
10°	733.3	738.7	748.7	747.2	754.7	759.0	752.0
12.5°	754.9	762.1	769.1	771.0	775.2	776.7	773.8
15°	774.4	778.3	778.6	777.6	778.9	777.8	773.7
17.5°	756.2	749.9	737.3	731.2	726.5	719.4	716.6
20°	726.0	707.6	686.2	677.6	667.6	647.9	652.6
22.5°	660.9	640.0	618.5	593.5	581.5	562.9	561.8
25°	559.7	523.5	483.6	455.8	439.5	420.9	412.7
27.5°	435.2	389.6	356.9	340.4	325.4	310.7	310.0
30°	353.3	319.1	293.8	279.7	270.4	264.2	265.5
32.5°	297.7	274.3	257.2	245.5	238.7	234.0	233.9
35°	243.5	227.3	216.4	211.5	206.6	203.2	203.4
37.5°	208.3	198.7	192.6	187.2	184.1	182.4	181.4
40°	190.3	182.4	177.7	174.5	171.9	169.6	169.1
42.5°	176.2	169.6	164.9	162.3	159.9	158.3	157.9
45°	156.3	150.9	146.7	143.8	142.8	141.3	141.3
47.5°	139.0	133.7	130.4	128.7	126.9	125.8	125.8
50°	127.4	123.3	120.4	119.2	117.7	117.2	116.9
52.5°	117.0	113.9	111.8	111.0	110.4	109.6	109.7
55°	102.7	101.0	100.2	99.5	98.5	97.2	98.0
57.5°	90.9	89.4	87.1	85.0	84.1	83.1	83.5
60°	82.5	79.5	76.4	74.1	73.4	71.5	71.5
62.5°	71.8	67.6	63.9	62.6	61.9	61.1	60.9
65°	55.2	53.5	52.7	51.8	51.4	51.4	51.0
67.5°	45.8	45.1	44.1	43.9	43.5	43.4	43.3
70°	40.4	39.6	39.2	38.9	38.5	38.7	38.1
72.5°	35.3	34.7	34.6	34.0	33.7	33.7	33.3
75°	27.8	27.8	27.6	27.4	27.0	26.8	27.0
77.5°	21.4	21.5	21.1	21.0	21.0	21.0	20.8
80°	17.2	17.3	17.2	16.9	16.7	16.9	16.7
82.5°	13.6	13.2	13.2	13.1	13.1	13.0	12.9
85°	7.7	7.9	7.7	7.5	7.5	7.5	7.7
87.5°	7.4	7.6	7.7	7.7	7.7	7.7	7.6
90°	22.1	23.6	24.3	24.3	24.3	24.3	24.3
92.5°	55.1	48.9	44.4	43.7	41.4	42.0	40.8
95°	148.1	117.2	100.9	91.3	85.5	83.2	84.0
97.5°	368.5	288.8	235.6	200.4	182.3	171.5	165.3
100°	581.4	480.4	391.2	330.1	298.4	277.0	263.7
102.5°	797.7	723.8	629.3	562.9	508.8	482.1	464.2
105°	978.5	988.1	963.7	918.0	872.3	840.7	830.4
107.5°	965.2	1041.8	1077.5	1083.3	1080.7	1074.4	1060.6
110°	924.0	1018.2	1078.6	1110.3	1124.4	1131.0	1130.2



TEST NUMBER: P331629-830

CATALOG NUMBER: S122RDIP-S290D725U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	875.0	975.8	1045.1	1089.1	1112.6	1125.1	1129.1
115°	808.2	904.7	980.6	1032.9	1066.9	1086.0	1092.7
117.5°	754.0	841.6	912.8	966.1	1001.9	1022.1	1027.7
120°	725.8	803.8	870.9	922.5	957.1	978.5	985.8
122.5°	702.2	776.1	836.7	883.0	917.0	936.0	942.2
125°	671.2	736.0	791.3	834.1	862.0	880.4	886.4
127.5°	641.1	702.3	753.3	790.6	816.8	832.7	837.4
130°	621.1	679.3	727.9	764.0	789.1	803.8	809.7
132.5°	602.3	655.7	701.4	737.0	762.0	775.5	780.8
135°	572.5	621.1	662.3	694.1	718.4	731.6	734.6
137.5°	548.7	587.4	623.3	652.2	673.2	684.8	689.2
140°	533.5	567.3	599.7	623.3	642.4	653.6	658.0
142.5°	519.9	549.0	576.2	598.6	616.0	625.8	626.7
145°	502.5	525.4	546.7	564.4	576.9	584.3	586.4
147.5°	488.3	506.1	521.8	536.4	546.4	551.4	552.7
150°	478.9	494.4	507.7	518.7	527.5	532.0	532.7
152.5°	471.3	484.4	495.9	504.5	512.2	515.5	515.6
155°	459.0	470.0	478.2	486.3	491.4	494.4	492.9
157.5°	446.7	455.9	462.2	468.0	472.3	473.6	473.6
160°	438.4	446.5	451.7	456.9	460.5	461.2	461.2
162.5°	430.7	437.6	441.7	446.8	449.3	450.1	449.4
165°	419.2	424.4	427.3	430.3	433.2	433.2	432.5
167.5°	408.8	412.3	415.0	416.3	417.9	417.7	416.9
170°	402.3	405.2	406.7	407.5	409.6	408.9	407.5
172.5°	396.4	398.8	399.6	400.4	401.4	400.7	399.8
175°	389.7	390.5	391.2	391.2	392.0	391.2	389.7
177.5°	384.9	385.5	385.5	385.5	385.5	384.9	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1

(END OF REPORT)