

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331651-830

Luminaire Tested: **S122RDIP-S485D530U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331651-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D530U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3744.5 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	94	90	87	90	86	83	81	73	70	68	60	58	57	48	47	46	41
2	90	83	77	72	82	76	71	67	64	61	58	53	51	49	43	42	40	35
3	82	73	67	61	75	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	52	69	61	54	49	52	47	43	43	40	37	35	33	31	27
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	32	30	28	24
6	65	53	45	40	59	49	43	38	42	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	33	39	34	30	33	29	26	27	25	22	20
8	56	44	37	32	51	41	35	30	36	30	27	30	26	23	25	23	20	18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19	16
10	49	37	30	26	45	35	29	24	30	25	22	26	22	20	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16356	16356	16356	16356
5°	18266	16459	14593	16459
10°	20266	16342	12650	16342
15°	21264	16104	9967	16104
20°	18433	15747	8624	15747
25°	12089	15262	7701	15262
30°	8138	14673	6969	14673
35°	6591	13931	6286	13931
40°	5861	13122	5817	13122
45°	5304	12177	5190	12177
50°	4828	11235	4808	11235
55°	4538	10196	4479	10196
60°	3794	9242	3749	9242
65°	3202	8390	3629	8390
70°	2960	7492	3423	7492
75°	2770	6519	3163	6519
80°	2548	5365	2817	5365
85°	2334	4242	2482	4242



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	2.6
10°-20°	267.6	7.1
20°-30°	344.8	9.2
30°-40°	327.7	8.8
40°-50°	280.7	7.5
50°-60°	213.8	5.7
60°-70°	135.1	3.6
70°-80°	67.5	1.8
80°-90°	19.2	0.5
90°-100°	22.7	0.6
100°-110°	83.2	2.2
110°-120°	222.3	5.9
120°-130°	366.9	9.8
130°-140°	390.2	10.4
140°-150°	362.7	9.7
150°-160°	291.6	7.8
160°-170°	187.9	5.0
170°-180°	64.7	1.7
0°-30°	708.4	18.9
0°-40°	1036.1	27.7
0°-60°	1530.5	40.9
0°-90°	1752.4	46.8
90°-120°	328.1	8.8
90°-150°	1447.9	38.7
90°-180°	1992.0	53.2
0°-180°	3744.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1013	1013	1013	1013	1013	
5°	1127	1016	900	1016	1127	111
15°	1272	963	596	963	1272	343
25°	679	857	432	857	679	322
35°	334	707	319	707	334	214
45°	232	533	227	533	232	180
55°	161	362	159	362	161	141
65°	84	220	95	220	84	85
75°	44	104	51	104	44	47
85°	13	23	13	23	13	14
90°	13	0	13	0	13	6
95°	21	32	21	32	21	20
105°	37	150	37	150	37	39
115°	40	283	40	283	40	101
125°	421	400	421	400	421	364
135°	511	495	511	495	511	394
145°	583	574	583	574	583	365
155°	632	632	632	632	632	292
165°	664	666	664	666	664	188
175°	677	681	677	681	677	65
180°	680	680	680	680	680	



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1054.1	1055.0	1055.8	1053.9	1053.9	1052.2	1048.5	1045.7	1037.7	1036.6	1036.6
5°	1127.0	1126.3	1127.8	1123.1	1116.8	1115.4	1108.7	1099.9	1090.8	1080.5	1078.5
7.5°	1199.6	1198.5	1195.7	1194.9	1190.1	1179.4	1168.7	1157.2	1142.0	1127.1	1119.6
10°	1236.1	1247.7	1240.8	1228.4	1230.9	1214.4	1205.5	1190.4	1177.7	1155.6	1150.7
12.5°	1272.1	1276.8	1274.5	1267.5	1264.4	1252.9	1241.0	1227.9	1204.5	1184.6	1167.2
15°	1272.1	1278.7	1280.5	1278.4	1280.2	1279.4	1273.1	1262.2	1241.8	1219.9	1201.0
17.5°	1178.2	1182.8	1194.3	1202.1	1212.0	1232.8	1243.1	1247.2	1244.1	1231.6	1218.2
20°	1072.8	1065.1	1097.5	1114.0	1128.1	1163.3	1193.5	1205.1	1223.8	1223.5	1219.9
22.5°	923.6	925.4	956.1	975.7	1016.9	1052.1	1086.6	1130.3	1166.4	1190.2	1204.2
25°	678.6	692.0	722.6	749.3	795.1	860.6	920.1	989.1	1054.1	1105.6	1154.5
27.5°	509.6	510.7	534.9	559.7	586.8	640.5	715.4	797.8	890.6	967.1	1055.3
30°	436.5	434.3	444.6	459.7	483.0	524.4	580.8	661.8	754.3	869.8	972.5
32.5°	384.7	384.7	392.5	403.7	422.9	450.9	489.6	555.3	642.8	756.3	876.8
35°	334.4	334.0	339.7	347.8	355.8	373.8	400.2	434.7	494.9	600.9	724.1
37.5°	298.3	299.9	302.7	307.7	316.6	326.6	342.5	365.6	408.5	471.2	574.7
40°	278.1	278.8	282.7	286.9	292.2	299.9	312.9	331.6	362.9	412.8	488.5
42.5°	259.5	260.1	263.0	266.8	271.0	278.8	289.5	305.7	331.1	370.0	432.5
45°	232.3	232.3	234.8	236.5	241.1	248.2	256.9	270.3	287.9	316.8	358.4
47.5°	206.8	206.9	208.5	211.5	214.4	219.9	228.6	239.5	252.3	274.7	310.1
50°	192.2	192.6	193.6	196.0	197.8	202.7	209.4	219.0	232.3	249.6	279.1
52.5°	180.3	180.1	181.4	182.6	183.7	187.3	192.3	200.7	212.6	227.6	252.1
55°	161.2	159.8	161.9	163.6	164.8	166.2	168.9	174.3	184.5	197.1	215.4
57.5°	137.2	136.7	138.2	139.8	143.1	146.9	149.3	152.7	158.0	167.0	185.2
60°	117.5	117.5	120.7	121.8	125.6	130.5	135.5	138.4	143.6	149.6	163.0
62.5°	100.1	100.4	101.9	102.9	105.1	111.1	118.1	124.2	129.2	135.0	143.8
65°	83.8	84.5	84.5	85.2	86.6	88.0	90.8	95.8	104.5	112.6	119.3
67.5°	71.1	71.4	71.5	72.2	72.6	74.1	75.2	77.5	79.5	87.2	95.5
70°	62.7	63.7	63.3	64.1	64.4	65.1	66.5	67.6	70.8	72.5	77.5
72.5°	54.8	55.5	55.5	55.9	56.8	56.9	58.1	59.1	61.2	62.7	65.3
75°	44.4	44.0	44.4	45.1	45.4	45.7	45.7	47.1	48.3	49.7	51.4
77.5°	34.2	34.6	34.5	34.6	34.6	35.3	35.2	35.8	36.9	37.6	38.5
80°	27.4	27.8	27.4	27.8	28.2	28.5	28.2	28.5	29.6	30.3	30.3
82.5°	21.3	21.3	21.6	21.6	21.7	21.8	22.2	22.3	23.1	22.9	23.2
85°	12.6	12.3	12.3	12.3	12.6	13.0	12.6	12.6	13.0	13.0	13.0
87.5°	7.2	7.4	7.4	7.4	7.3	7.2	7.1	7.3	6.9	7.1	6.6
90°	13.3	13.1	12.8	12.6	12.4	12.1	11.5	10.9	10.4	9.8	9.0
92.5°	13.3	13.2	13.0	12.9	12.7	12.5	12.3	12.0	11.7	11.4	10.9
95°	21.1	21.3	21.4	21.5	21.6	21.4	20.8	20.3	19.7	19.2	18.4
97.5°	28.3	28.1	28.0	27.8	27.7	27.4	27.0	26.6	26.1	25.6	23.9
100°	33.0	32.7	32.5	32.3	32.0	31.6	30.6	29.8	28.9	28.0	26.2
102.5°	35.3	35.0	34.7	34.4	34.1	33.4	32.2	31.1	30.0	28.8	44.4
105°	37.4	36.9	36.5	36.1	35.6	34.8	33.6	32.4	31.2	30.0	59.9
107.5°	38.5	38.0	37.6	37.1	36.8	37.1	38.4	39.6	40.8	42.0	77.8
110°	38.8	38.5	38.0	37.5	37.1	42.3	53.3	64.2	75.1	86.1	117.6



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	39.2	38.9	38.5	38.2	37.9	57.6	97.5	137.3	177.2	217.2	224.9
115°	40.3	48.2	56.1	63.9	71.8	101.0	151.7	202.3	252.9	303.5	300.8
117.5°	164.7	190.6	216.4	242.2	268.2	287.2	299.4	311.7	324.0	336.1	334.3
120°	300.0	314.8	329.6	344.3	359.1	365.8	364.5	363.2	361.8	360.5	358.5
122.5°	374.4	377.3	380.1	383.0	385.9	386.9	386.2	385.3	384.6	383.8	381.6
125°	420.6	420.3	419.9	419.6	419.2	418.7	417.9	417.2	416.4	415.7	413.6
127.5°	449.7	449.6	449.6	449.5	449.4	448.8	447.7	446.6	445.4	444.4	442.8
130°	467.8	467.9	468.0	468.1	468.3	467.7	466.5	465.2	464.1	462.9	461.7
132.5°	485.5	485.6	485.7	485.8	485.9	485.5	484.5	483.4	482.4	481.4	480.1
135°	511.0	511.3	511.5	511.7	512.0	511.5	510.4	509.3	508.2	507.1	506.1
137.5°	534.4	534.8	535.1	535.5	535.8	535.6	534.4	533.4	532.3	531.2	530.1
140°	548.9	549.5	550.1	550.5	551.1	550.9	549.9	548.9	548.0	547.0	545.7
142.5°	563.1	563.6	564.2	564.8	565.3	565.1	564.2	563.4	562.4	561.6	560.2
145°	582.9	583.4	584.0	584.6	585.0	584.9	584.2	583.4	582.7	581.9	580.0
147.5°	600.3	600.8	601.2	601.7	602.1	602.1	601.5	601.0	600.4	599.8	597.9
150°	611.0	611.4	612.0	612.6	613.1	613.0	612.4	611.7	611.1	610.4	608.7
152.5°	620.0	620.7	621.4	622.2	622.8	622.9	622.3	621.6	620.9	620.3	618.6
155°	632.5	633.5	634.3	635.2	636.0	636.2	635.6	634.9	634.2	633.6	632.3
157.5°	644.0	644.9	645.7	646.6	647.5	647.5	646.8	646.0	645.3	644.6	643.7
160°	650.7	651.5	652.3	653.1	653.8	653.8	653.2	652.5	652.0	651.3	650.6
162.5°	656.3	657.2	658.2	659.1	660.1	660.2	659.4	658.6	657.9	657.1	656.6
165°	664.5	665.3	666.1	666.8	667.6	667.6	666.8	666.1	665.3	664.5	664.2
167.5°	669.8	670.7	671.8	672.7	673.7	673.8	673.1	672.2	671.5	670.7	670.4
170°	672.9	673.9	674.9	675.8	676.8	676.9	676.2	675.4	674.7	673.9	673.6
172.5°	675.2	676.3	677.2	678.3	679.2	679.3	678.5	677.8	677.0	676.3	676.0
175°	677.3	678.4	679.5	680.6	681.7	681.8	681.1	680.3	679.6	678.8	678.5
177.5°	678.6	679.4	680.1	681.0	681.7	681.8	681.3	680.6	680.0	679.4	679.3
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1037.2	1035.0	1033.0	1027.9	1025.4	1019.7	1018.9	1018.6	1011.3	1004.3	1002.3
5°	1072.8	1067.2	1058.8	1048.9	1038.7	1028.1	1021.1	1015.5	1001.4	988.0	980.2
7.5°	1108.7	1096.6	1082.0	1063.4	1047.8	1030.4	1017.5	1005.8	985.8	966.7	953.8
10°	1135.5	1115.8	1096.5	1070.7	1050.7	1031.0	1012.7	996.8	974.3	949.0	930.9
12.5°	1152.1	1130.4	1103.7	1078.6	1052.6	1027.6	1003.1	982.7	956.3	930.1	908.7
15°	1174.6	1151.3	1119.0	1083.1	1049.6	1016.9	988.7	963.4	928.9	897.6	871.5
17.5°	1193.0	1160.9	1126.1	1084.7	1045.9	1004.4	968.1	935.7	897.3	859.5	828.9
20°	1198.8	1167.2	1127.0	1085.5	1039.7	990.8	951.8	916.5	875.3	834.2	799.0
22.5°	1195.1	1170.5	1125.9	1076.2	1029.4	978.2	934.1	893.2	847.5	805.5	764.7
25°	1170.4	1161.9	1119.6	1065.5	1011.9	952.4	901.4	856.7	804.6	759.6	715.2
27.5°	1112.4	1130.7	1104.5	1046.7	987.2	923.4	866.1	815.2	761.1	710.4	666.2
30°	1056.7	1098.5	1087.2	1033.8	967.2	904.6	840.2	787.0	729.3	677.2	633.6
32.5°	980.3	1049.5	1060.5	1015.8	947.0	878.1	810.6	757.7	697.5	642.5	600.0
35°	858.8	962.3	1009.8	981.3	912.3	838.1	768.4	706.8	646.2	592.0	549.8
37.5°	713.9	854.8	934.1	936.0	872.7	795.5	719.6	658.5	596.4	543.3	497.6
40°	619.8	772.6	875.7	898.6	845.1	761.7	684.9	622.6	562.1	510.0	457.6
42.5°	535.4	687.6	814.4	854.1	811.6	728.8	651.8	586.6	527.7	478.4	424.9
45°	432.9	566.0	705.7	776.8	753.3	676.5	595.2	533.3	478.0	435.4	384.0
47.5°	365.2	459.0	594.2	690.4	689.9	619.9	540.0	480.6	429.3	389.5	347.8
50°	326.6	408.3	522.7	631.8	640.9	582.2	506.1	447.3	399.5	357.6	324.1
52.5°	292.0	359.3	462.1	566.8	592.8	541.9	468.2	413.9	367.4	328.9	300.2
55°	246.8	298.8	377.0	474.9	514.3	478.3	412.8	362.2	324.5	292.2	267.5
57.5°	208.7	247.8	310.5	389.3	435.2	412.6	358.6	317.4	285.2	255.9	236.5
60°	184.8	216.8	269.9	335.8	386.4	370.6	324.5	286.2	258.7	233.4	215.1
62.5°	162.3	189.8	235.4	288.8	335.3	328.7	291.1	258.8	234.8	211.7	196.2
65°	130.5	150.6	186.2	228.1	265.4	268.5	241.5	219.6	198.1	179.8	166.2
67.5°	104.0	117.1	142.1	177.4	205.4	215.4	198.8	182.1	165.0	150.9	139.0
70°	87.7	98.2	116.5	145.1	170.7	181.3	171.7	158.7	143.9	132.3	122.2
72.5°	71.1	81.3	94.8	115.7	137.8	149.2	145.9	136.5	124.5	114.9	105.3
75°	53.5	56.6	65.8	79.9	97.2	107.0	109.4	104.5	95.0	87.7	82.0
77.5°	39.6	41.5	45.8	53.3	64.5	73.2	76.9	76.3	69.7	65.5	60.2
80°	31.7	32.7	34.9	38.0	46.5	55.2	57.7	57.7	53.2	51.4	46.1
82.5°	24.0	24.9	26.1	27.9	31.9	39.5	42.2	42.8	39.9	37.6	33.5
85°	13.8	13.4	14.0	15.2	15.8	17.9	22.1	22.9	22.1	19.3	18.3
87.5°	6.4	6.5	6.3	5.8	5.8	5.9	7.1	8.3	7.4	6.8	6.4
90°	8.1	7.3	6.3	5.3	4.1	2.9	1.7	0.5	1.7	2.9	4.1
92.5°	10.6	10.1	9.7	9.5	9.6	9.7	9.8	9.9	9.8	9.7	9.6
95°	17.6	16.9	16.1	17.5	21.1	24.8	28.4	32.0	28.4	24.8	21.1
97.5°	22.1	20.4	18.6	22.8	33.0	43.2	53.3	63.4	53.3	43.2	33.0
100°	24.3	22.4	20.6	27.1	42.1	57.1	72.1	87.1	72.1	57.1	42.1
102.5°	59.9	75.5	91.0	100.4	103.5	106.7	109.9	113.0	109.9	106.7	103.5
105°	89.7	119.5	149.4	162.7	159.4	156.1	152.8	149.5	152.8	156.1	159.4
107.5°	113.6	149.4	185.1	201.7	199.1	196.4	193.8	191.1	193.8	196.4	199.1
110°	149.3	180.9	212.4	227.1	224.8	222.5	220.2	217.9	220.2	222.5	224.8



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	232.7	240.5	248.4	251.2	249.2	247.1	245.2	243.1	245.2	247.1	249.2
115°	298.0	295.3	292.6	290.3	288.4	286.5	284.6	282.9	284.6	286.5	288.4
117.5°	332.4	330.5	328.7	326.7	324.6	322.5	320.5	318.4	320.5	322.5	324.6
120°	356.7	354.7	352.7	350.9	349.2	347.6	345.9	344.3	345.9	347.6	349.2
122.5°	379.5	377.3	375.2	373.2	371.6	369.9	368.1	366.4	368.1	369.9	371.6
125°	411.5	409.4	407.4	405.6	404.2	402.7	401.3	399.9	401.3	402.7	404.2
127.5°	441.3	439.7	438.2	436.6	435.0	433.5	431.9	430.3	431.9	433.5	435.0
130°	460.4	459.3	458.1	456.6	454.9	453.1	451.3	449.6	451.3	453.1	454.9
132.5°	479.0	477.8	476.5	475.2	473.7	472.2	470.7	469.3	470.7	472.2	473.7
135°	505.2	504.2	503.2	501.8	500.1	498.3	496.6	494.8	496.6	498.3	500.1
137.5°	529.0	527.9	526.8	525.6	524.3	523.1	521.9	520.8	521.9	523.1	524.3
140°	544.6	543.4	542.2	541.1	540.3	539.4	538.5	537.6	538.5	539.4	540.3
142.5°	558.7	557.4	556.0	555.0	554.1	553.4	552.6	551.8	552.6	553.4	554.1
145°	578.2	576.4	574.5	573.6	573.7	573.8	573.9	574.0	573.9	573.8	573.7
147.5°	596.2	594.3	592.5	591.7	592.2	592.6	593.0	593.4	593.0	592.6	592.2
150°	606.9	605.2	603.4	602.9	603.7	604.5	605.2	606.0	605.2	604.5	603.7
152.5°	617.0	615.3	613.6	613.2	614.1	614.9	615.8	616.6	615.8	614.9	614.1
155°	630.9	629.6	628.3	628.1	629.1	630.1	631.1	632.1	631.1	630.1	629.1
157.5°	642.7	641.8	640.9	640.8	641.7	642.5	643.4	644.1	643.4	642.5	641.7
160°	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3	650.6	650.0	649.3
162.5°	656.0	655.4	654.9	655.0	655.5	656.2	656.9	657.5	656.9	656.2	655.5
165°	663.8	663.5	663.3	663.4	664.0	664.7	665.3	666.0	665.3	664.7	664.0
167.5°	670.1	669.8	669.5	669.7	670.3	671.0	671.7	672.3	671.7	671.0	670.3
170°	673.4	673.3	673.0	673.3	673.9	674.6	675.2	675.8	675.2	674.6	673.9
172.5°	675.8	675.6	675.3	675.6	676.3	676.9	677.6	678.3	677.6	676.9	676.3
175°	678.3	678.2	678.0	678.2	679.0	679.8	680.5	681.3	680.5	679.8	679.0
177.5°	679.2	679.1	679.0	679.3	680.0	680.5	681.2	681.7	681.2	680.5	680.0
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	998.6	996.6	993.0	987.4	984.0	978.1	974.1	976.4	976.9	976.4	975.8
5°	971.9	964.4	954.2	944.3	935.2	925.4	919.7	917.3	912.3	909.6	908.1
7.5°	939.3	926.6	912.2	895.0	880.4	865.2	857.3	853.5	843.4	837.9	833.1
10°	915.1	895.0	880.6	858.1	844.4	824.3	810.6	811.0	797.2	789.5	783.8
12.5°	888.4	866.4	842.4	822.1	803.0	786.9	770.3	763.6	749.0	741.6	726.4
15°	844.0	818.3	793.1	765.5	746.2	721.2	697.3	668.1	644.5	624.1	618.4
17.5°	795.6	763.8	738.4	706.2	673.0	630.9	603.2	586.3	572.0	561.3	553.3
20°	762.4	730.0	702.9	654.3	609.6	581.1	560.7	547.7	532.9	521.3	514.9
22.5°	727.5	693.7	656.8	602.5	567.7	544.8	526.6	511.6	501.6	492.6	486.8
25°	677.9	640.9	580.0	542.7	514.6	490.7	478.0	468.8	458.3	445.9	440.4
27.5°	625.6	566.8	523.0	495.3	468.4	452.9	441.5	427.8	418.4	412.8	407.0
30°	586.4	527.6	493.5	463.2	444.2	427.0	413.6	405.9	396.7	387.2	383.3
32.5°	542.7	495.8	463.1	437.9	418.6	403.9	393.3	380.8	374.2	368.3	360.2
35°	488.5	453.0	423.1	402.7	384.4	372.4	360.1	352.7	340.7	335.8	332.6
37.5°	442.6	411.8	389.5	368.0	353.5	340.3	332.7	320.9	315.8	308.9	302.2
40°	416.7	386.4	365.0	347.4	331.2	321.3	311.9	302.4	294.6	291.4	283.3
42.5°	390.3	365.6	344.1	324.9	314.1	303.6	291.6	284.6	276.5	271.5	266.5
45°	353.7	332.0	313.6	297.7	285.8	274.9	267.1	255.5	251.0	240.7	236.5
47.5°	321.6	301.3	283.9	268.8	257.1	250.1	238.7	229.6	222.3	216.0	210.7
50°	298.8	281.9	265.0	251.7	241.1	230.9	219.3	214.7	203.4	200.3	197.1
52.5°	278.0	261.9	246.5	233.4	222.8	212.9	202.6	196.7	189.1	185.9	183.6
55°	248.8	233.4	218.6	207.0	196.4	186.2	179.8	172.5	168.9	166.5	163.6
57.5°	219.5	205.7	194.3	182.6	171.9	163.8	156.5	152.0	148.4	145.2	141.8
60°	201.0	187.6	177.4	166.5	155.6	148.9	143.3	138.0	133.7	128.8	127.4
62.5°	181.3	169.6	160.2	149.6	140.1	133.9	128.7	123.7	118.6	111.4	109.4
65°	154.2	145.1	135.2	126.4	117.9	112.0	104.2	98.6	96.4	95.8	95.4
67.5°	129.7	121.0	112.5	103.6	95.9	90.3	86.3	85.5	84.1	83.6	82.7
70°	113.3	105.3	96.8	88.3	81.0	79.9	78.5	77.1	75.3	74.6	73.9
72.5°	98.7	90.3	81.9	75.1	71.9	70.6	69.2	67.8	66.6	65.9	65.5
75°	75.7	68.0	62.3	59.9	58.1	57.0	55.0	53.8	53.2	52.1	51.7
77.5°	54.5	50.1	47.5	46.0	44.1	43.0	41.8	40.7	40.0	39.8	39.2
80°	41.6	39.4	37.7	35.5	34.9	33.5	33.1	32.0	32.4	31.3	31.3
82.5°	32.2	29.6	28.1	27.1	26.4	25.3	24.9	24.4	24.5	23.8	23.8
85°	16.6	15.8	15.2	14.4	14.4	13.4	13.8	13.4	13.4	12.6	12.3
87.5°	6.4	6.3	5.9	6.1	6.3	6.2	6.3	6.1	6.2	6.3	6.1
90°	5.3	6.3	7.3	8.1	9.0	9.8	10.4	10.9	11.5	12.1	12.4
92.5°	9.5	9.7	10.1	10.6	10.9	11.4	11.7	12.0	12.3	12.5	12.7
95°	17.5	16.1	16.9	17.6	18.4	19.2	19.7	20.3	20.8	21.4	21.6
97.5°	22.8	18.6	20.4	22.1	23.9	25.6	26.1	26.6	27.0	27.4	27.7
100°	27.1	20.6	22.4	24.3	26.2	28.0	28.9	29.8	30.6	31.6	32.0
102.5°	100.4	91.0	75.5	59.9	44.4	28.8	30.0	31.1	32.2	33.4	34.1
105°	162.7	149.4	119.5	89.7	59.9	30.0	31.2	32.4	33.6	34.8	35.6
107.5°	201.7	185.1	149.4	113.6	77.8	42.0	40.8	39.6	38.4	37.1	36.8
110°	227.1	212.4	180.9	149.3	117.6	86.1	75.1	64.2	53.3	42.3	37.1



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	251.2	248.4	240.5	232.7	224.9	217.2	177.2	137.3	97.5	57.6	37.9
115°	290.3	292.6	295.3	298.0	300.8	303.5	252.9	202.3	151.7	101.0	71.8
117.5°	326.7	328.7	330.5	332.4	334.3	336.1	324.0	311.7	299.4	287.2	268.2
120°	350.9	352.7	354.7	356.7	358.5	360.5	361.8	363.2	364.5	365.8	359.1
122.5°	373.2	375.2	377.3	379.5	381.6	383.8	384.6	385.3	386.2	386.9	385.9
125°	405.6	407.4	409.4	411.5	413.6	415.7	416.4	417.2	417.9	418.7	419.2
127.5°	436.6	438.2	439.7	441.3	442.8	444.4	445.4	446.6	447.7	448.8	449.4
130°	456.6	458.1	459.3	460.4	461.7	462.9	464.1	465.2	466.5	467.7	468.3
132.5°	475.2	476.5	477.8	479.0	480.1	481.4	482.4	483.4	484.5	485.5	485.9
135°	501.8	503.2	504.2	505.2	506.1	507.1	508.2	509.3	510.4	511.5	512.0
137.5°	525.6	526.8	527.9	529.0	530.1	531.2	532.3	533.4	534.4	535.6	535.8
140°	541.1	542.2	543.4	544.6	545.7	547.0	548.0	548.9	549.9	550.9	551.1
142.5°	555.0	556.0	557.4	558.7	560.2	561.6	562.4	563.4	564.2	565.1	565.3
145°	573.6	574.5	576.4	578.2	580.0	581.9	582.7	583.4	584.2	584.9	585.0
147.5°	591.7	592.5	594.3	596.2	597.9	599.8	600.4	601.0	601.5	602.1	602.1
150°	602.9	603.4	605.2	606.9	608.7	610.4	611.1	611.7	612.4	613.0	613.1
152.5°	613.2	613.6	615.3	617.0	618.6	620.3	620.9	621.6	622.3	622.9	622.8
155°	628.1	628.3	629.6	630.9	632.3	633.6	634.2	634.9	635.6	636.2	636.0
157.5°	640.8	640.9	641.8	642.7	643.7	644.6	645.3	646.0	646.8	647.5	647.5
160°	648.7	648.7	649.3	650.0	650.6	651.3	652.0	652.5	653.2	653.8	653.8
162.5°	655.0	654.9	655.4	656.0	656.6	657.1	657.9	658.6	659.4	660.2	660.1
165°	663.4	663.3	663.5	663.8	664.2	664.5	665.3	666.1	666.8	667.6	667.6
167.5°	669.7	669.5	669.8	670.1	670.4	670.7	671.5	672.2	673.1	673.8	673.7
170°	673.3	673.0	673.3	673.4	673.6	673.9	674.7	675.4	676.2	676.9	676.8
172.5°	675.6	675.3	675.6	675.8	676.0	676.3	677.0	677.8	678.5	679.3	679.2
175°	678.2	678.0	678.2	678.3	678.5	678.8	679.6	680.3	681.1	681.8	681.7
177.5°	679.3	679.0	679.1	679.2	679.3	679.4	680.0	680.6	681.3	681.8	681.7
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	972.7	973.3	972.4	973.0	972.4	973.3	972.7	975.8	976.4	976.9	976.4
5°	906.3	902.1	901.4	900.4	901.4	902.1	906.3	908.1	909.6	912.3	917.3
7.5°	827.1	826.4	824.7	822.2	824.7	826.4	827.1	833.1	837.9	843.4	853.5
10°	776.1	774.4	774.0	771.6	774.0	774.4	776.1	783.8	789.5	797.2	811.0
12.5°	716.4	705.1	703.9	697.8	703.9	705.1	716.4	726.4	741.6	749.0	763.6
15°	610.0	607.8	600.9	596.3	600.9	607.8	610.0	618.4	624.1	644.5	668.1
17.5°	549.1	542.2	540.1	539.1	540.1	542.2	549.1	553.3	561.3	572.0	586.3
20°	510.0	503.7	502.7	501.9	502.7	503.7	510.0	514.9	521.3	532.9	547.7
22.5°	483.0	476.4	473.6	471.6	473.6	476.4	483.0	486.8	492.6	501.6	511.6
25°	436.8	434.3	432.9	432.3	432.9	434.3	436.8	440.4	445.9	458.3	468.8
27.5°	400.7	395.3	394.2	392.4	394.2	395.3	400.7	407.0	412.8	418.4	427.8
30°	380.1	378.3	375.9	373.8	375.9	378.3	380.1	383.3	387.2	396.7	405.9
32.5°	355.9	354.5	352.2	351.3	352.2	354.5	355.9	360.2	368.3	374.2	380.8
35°	329.1	324.1	322.1	318.9	322.1	324.1	329.1	332.6	335.8	340.7	352.7
37.5°	300.8	298.1	295.2	296.2	295.2	298.1	300.8	302.2	308.9	315.8	320.9
40°	278.8	277.0	276.3	276.0	276.3	277.0	278.8	283.3	291.4	294.6	302.4
42.5°	261.3	256.5	254.6	254.6	254.6	256.5	261.3	266.5	271.5	276.5	284.6
45°	234.8	230.2	227.1	227.3	227.1	230.2	234.8	236.5	240.7	251.0	255.5
47.5°	207.6	207.5	205.5	206.1	205.5	207.5	207.6	210.7	216.0	222.3	229.6
50°	194.6	192.6	191.1	191.4	191.1	192.6	194.6	197.1	200.3	203.4	214.7
52.5°	182.3	180.4	179.3	180.8	179.3	180.4	182.3	183.6	185.9	189.1	196.7
55°	161.9	159.8	159.5	159.1	159.5	159.8	161.9	163.6	166.5	168.9	172.5
57.5°	139.2	137.8	135.6	134.8	135.6	137.8	139.2	141.8	145.2	148.4	152.0
60°	122.8	120.0	116.5	116.1	116.5	120.0	122.8	127.4	128.8	133.7	138.0
62.5°	107.9	107.4	106.7	106.6	106.7	107.4	107.9	109.4	111.4	118.6	123.7
65°	94.7	94.3	94.7	95.0	94.7	94.3	94.7	95.4	95.8	96.4	98.6
67.5°	82.5	81.9	81.2	81.5	81.2	81.9	82.5	82.7	83.6	84.1	85.5
70°	73.2	72.9	72.5	72.5	72.5	72.9	73.2	73.9	74.6	75.3	77.1
72.5°	64.2	64.1	63.8	63.5	63.8	64.1	64.2	65.5	65.9	66.6	67.8
75°	51.4	50.7	50.7	50.7	50.7	50.7	51.4	51.7	52.1	53.2	53.8
77.5°	39.1	38.8	38.5	38.2	38.5	38.8	39.1	39.2	39.8	40.0	40.7
80°	31.0	30.6	30.3	30.3	30.3	30.6	31.0	31.3	31.3	32.4	32.0
82.5°	23.7	23.3	23.2	22.9	23.2	23.3	23.7	23.8	23.8	24.5	24.4
85°	12.6	13.0	12.6	13.4	12.6	13.0	12.6	12.3	12.6	13.4	13.4
87.5°	6.2	5.9	6.3	6.0	6.3	5.9	6.2	6.1	6.3	6.2	6.1
90°	12.6	12.8	13.1	13.3	13.1	12.8	12.6	12.4	12.1	11.5	10.9
92.5°	12.9	13.0	13.2	13.3	13.2	13.0	12.9	12.7	12.5	12.3	12.0
95°	21.5	21.4	21.3	21.1	21.3	21.4	21.5	21.6	21.4	20.8	20.3
97.5°	27.8	28.0	28.1	28.3	28.1	28.0	27.8	27.7	27.4	27.0	26.6
100°	32.3	32.5	32.7	33.0	32.7	32.5	32.3	32.0	31.6	30.6	29.8
102.5°	34.4	34.7	35.0	35.3	35.0	34.7	34.4	34.1	33.4	32.2	31.1
105°	36.1	36.5	36.9	37.4	36.9	36.5	36.1	35.6	34.8	33.6	32.4
107.5°	37.1	37.6	38.0	38.5	38.0	37.6	37.1	36.8	37.1	38.4	39.6
110°	37.5	38.0	38.5	38.8	38.5	38.0	37.5	37.1	42.3	53.3	64.2



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	38.2	38.5	38.9	39.2	38.9	38.5	38.2	37.9	57.6	97.5	137.3
115°	63.9	56.1	48.2	40.3	48.2	56.1	63.9	71.8	101.0	151.7	202.3
117.5°	242.2	216.4	190.6	164.7	190.6	216.4	242.2	268.2	287.2	299.4	311.7
120°	344.3	329.6	314.8	300.0	314.8	329.6	344.3	359.1	365.8	364.5	363.2
122.5°	383.0	380.1	377.3	374.4	377.3	380.1	383.0	385.9	386.9	386.2	385.3
125°	419.6	419.9	420.3	420.6	420.3	419.9	419.6	419.2	418.7	417.9	417.2
127.5°	449.5	449.6	449.6	449.7	449.6	449.6	449.5	449.4	448.8	447.7	446.6
130°	468.1	468.0	467.9	467.8	467.9	468.0	468.1	468.3	467.7	466.5	465.2
132.5°	485.8	485.7	485.6	485.5	485.6	485.7	485.8	485.9	485.5	484.5	483.4
135°	511.7	511.5	511.3	511.0	511.3	511.5	511.7	512.0	511.5	510.4	509.3
137.5°	535.5	535.1	534.8	534.4	534.8	535.1	535.5	535.8	535.6	534.4	533.4
140°	550.5	550.1	549.5	548.9	549.5	550.1	550.5	551.1	550.9	549.9	548.9
142.5°	564.8	564.2	563.6	563.1	563.6	564.2	564.8	565.3	565.1	564.2	563.4
145°	584.6	584.0	583.4	582.9	583.4	584.0	584.6	585.0	584.9	584.2	583.4
147.5°	601.7	601.2	600.8	600.3	600.8	601.2	601.7	602.1	602.1	601.5	601.0
150°	612.6	612.0	611.4	611.0	611.4	612.0	612.6	613.1	613.0	612.4	611.7
152.5°	622.2	621.4	620.7	620.0	620.7	621.4	622.2	622.8	622.9	622.3	621.6
155°	635.2	634.3	633.5	632.5	633.5	634.3	635.2	636.0	636.2	635.6	634.9
157.5°	646.6	645.7	644.9	644.0	644.9	645.7	646.6	647.5	647.5	646.8	646.0
160°	653.1	652.3	651.5	650.7	651.5	652.3	653.1	653.8	653.8	653.2	652.5
162.5°	659.1	658.2	657.2	656.3	657.2	658.2	659.1	660.1	660.2	659.4	658.6
165°	666.8	666.1	665.3	664.5	665.3	666.1	666.8	667.6	667.6	666.8	666.1
167.5°	672.7	671.8	670.7	669.8	670.7	671.8	672.7	673.7	673.8	673.1	672.2
170°	675.8	674.9	673.9	672.9	673.9	674.9	675.8	676.8	676.9	676.2	675.4
172.5°	678.3	677.2	676.3	675.2	676.3	677.2	678.3	679.2	679.3	678.5	677.8
175°	680.6	679.5	678.4	677.3	678.4	679.5	680.6	681.7	681.8	681.1	680.3
177.5°	681.0	680.1	679.4	678.6	679.4	680.1	681.0	681.7	681.8	681.3	680.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	974.1	978.1	984.0	987.4	993.0	996.6	998.6	1002.3	1004.3	1011.3	1018.6
5°	919.7	925.4	935.2	944.3	954.2	964.4	971.9	980.2	988.0	1001.4	1015.5
7.5°	857.3	865.2	880.4	895.0	912.2	926.6	939.3	953.8	966.7	985.8	1005.8
10°	810.6	824.3	844.4	858.1	880.6	895.0	915.1	930.9	949.0	974.3	996.8
12.5°	770.3	786.9	803.0	822.1	842.4	866.4	888.4	908.7	930.1	956.3	982.7
15°	697.3	721.2	746.2	765.5	793.1	818.3	844.0	871.5	897.6	928.9	963.4
17.5°	603.2	630.9	673.0	706.2	738.4	763.8	795.6	828.9	859.5	897.3	935.7
20°	560.7	581.1	609.6	654.3	702.9	730.0	762.4	799.0	834.2	875.3	916.5
22.5°	526.6	544.8	567.7	602.5	656.8	693.7	727.5	764.7	805.5	847.5	893.2
25°	478.0	490.7	514.6	542.7	580.0	640.9	677.9	715.2	759.6	804.6	856.7
27.5°	441.5	452.9	468.4	495.3	523.0	566.8	625.6	666.2	710.4	761.1	815.2
30°	413.6	427.0	444.2	463.2	493.5	527.6	586.4	633.6	677.2	729.3	787.0
32.5°	393.3	403.9	418.6	437.9	463.1	495.8	542.7	600.0	642.5	697.5	757.7
35°	360.1	372.4	384.4	402.7	423.1	453.0	488.5	549.8	592.0	646.2	706.8
37.5°	332.7	340.3	353.5	368.0	389.5	411.8	442.6	497.6	543.3	596.4	658.5
40°	311.9	321.3	331.2	347.4	365.0	386.4	416.7	457.6	510.0	562.1	622.6
42.5°	291.6	303.6	314.1	324.9	344.1	365.6	390.3	424.9	478.4	527.7	586.6
45°	267.1	274.9	285.8	297.7	313.6	332.0	353.7	384.0	435.4	478.0	533.3
47.5°	238.7	250.1	257.1	268.8	283.9	301.3	321.6	347.8	389.5	429.3	480.6
50°	219.3	230.9	241.1	251.7	265.0	281.9	298.8	324.1	357.6	399.5	447.3
52.5°	202.6	212.9	222.8	233.4	246.5	261.9	278.0	300.2	328.9	367.4	413.9
55°	179.8	186.2	196.4	207.0	218.6	233.4	248.8	267.5	292.2	324.5	362.2
57.5°	156.5	163.8	171.9	182.6	194.3	205.7	219.5	236.5	255.9	285.2	317.4
60°	143.3	148.9	155.6	166.5	177.4	187.6	201.0	215.1	233.4	258.7	286.2
62.5°	128.7	133.9	140.1	149.6	160.2	169.6	181.3	196.2	211.7	234.8	258.8
65°	104.2	112.0	117.9	126.4	135.2	145.1	154.2	166.2	179.8	198.1	219.6
67.5°	86.3	90.3	95.9	103.6	112.5	121.0	129.7	139.0	150.9	165.0	182.1
70°	78.5	79.9	81.0	88.3	96.8	105.3	113.3	122.2	132.3	143.9	158.7
72.5°	69.2	70.6	71.9	75.1	81.9	90.3	98.7	105.3	114.9	124.5	136.5
75°	55.0	57.0	58.1	59.9	62.3	68.0	75.7	82.0	87.7	95.0	104.5
77.5°	41.8	43.0	44.1	46.0	47.5	50.1	54.5	60.2	65.5	69.7	76.3
80°	33.1	33.5	34.9	35.5	37.7	39.4	41.6	46.1	51.4	53.2	57.7
82.5°	24.9	25.3	26.4	27.1	28.1	29.6	32.2	33.5	37.6	39.9	42.8
85°	13.8	13.4	14.4	14.4	15.2	15.8	16.6	18.3	19.3	22.1	22.9
87.5°	6.3	6.2	6.3	6.1	5.9	6.3	6.4	6.4	6.8	7.4	8.3
90°	10.4	9.8	9.0	8.1	7.3	6.3	5.3	4.1	2.9	1.7	0.5
92.5°	11.7	11.4	10.9	10.6	10.1	9.7	9.5	9.6	9.7	9.8	9.9
95°	19.7	19.2	18.4	17.6	16.9	16.1	17.5	21.1	24.8	28.4	32.0
97.5°	26.1	25.6	23.9	22.1	20.4	18.6	22.8	33.0	43.2	53.3	63.4
100°	28.9	28.0	26.2	24.3	22.4	20.6	27.1	42.1	57.1	72.1	87.1
102.5°	30.0	28.8	44.4	59.9	75.5	91.0	100.4	103.5	106.7	109.9	113.0
105°	31.2	30.0	59.9	89.7	119.5	149.4	162.7	159.4	156.1	152.8	149.5
107.5°	40.8	42.0	77.8	113.6	149.4	185.1	201.7	199.1	196.4	193.8	191.1
110°	75.1	86.1	117.6	149.3	180.9	212.4	227.1	224.8	222.5	220.2	217.9



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	177.2	217.2	224.9	232.7	240.5	248.4	251.2	249.2	247.1	245.2	243.1
115°	252.9	303.5	300.8	298.0	295.3	292.6	290.3	288.4	286.5	284.6	282.9
117.5°	324.0	336.1	334.3	332.4	330.5	328.7	326.7	324.6	322.5	320.5	318.4
120°	361.8	360.5	358.5	356.7	354.7	352.7	350.9	349.2	347.6	345.9	344.3
122.5°	384.6	383.8	381.6	379.5	377.3	375.2	373.2	371.6	369.9	368.1	366.4
125°	416.4	415.7	413.6	411.5	409.4	407.4	405.6	404.2	402.7	401.3	399.9
127.5°	445.4	444.4	442.8	441.3	439.7	438.2	436.6	435.0	433.5	431.9	430.3
130°	464.1	462.9	461.7	460.4	459.3	458.1	456.6	454.9	453.1	451.3	449.6
132.5°	482.4	481.4	480.1	479.0	477.8	476.5	475.2	473.7	472.2	470.7	469.3
135°	508.2	507.1	506.1	505.2	504.2	503.2	501.8	500.1	498.3	496.6	494.8
137.5°	532.3	531.2	530.1	529.0	527.9	526.8	525.6	524.3	523.1	521.9	520.8
140°	548.0	547.0	545.7	544.6	543.4	542.2	541.1	540.3	539.4	538.5	537.6
142.5°	562.4	561.6	560.2	558.7	557.4	556.0	555.0	554.1	553.4	552.6	551.8
145°	582.7	581.9	580.0	578.2	576.4	574.5	573.6	573.7	573.8	573.9	574.0
147.5°	600.4	599.8	597.9	596.2	594.3	592.5	591.7	592.2	592.6	593.0	593.4
150°	611.1	610.4	608.7	606.9	605.2	603.4	602.9	603.7	604.5	605.2	606.0
152.5°	620.9	620.3	618.6	617.0	615.3	613.6	613.2	614.1	614.9	615.8	616.6
155°	634.2	633.6	632.3	630.9	629.6	628.3	628.1	629.1	630.1	631.1	632.1
157.5°	645.3	644.6	643.7	642.7	641.8	640.9	640.8	641.7	642.5	643.4	644.1
160°	652.0	651.3	650.6	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3
162.5°	657.9	657.1	656.6	656.0	655.4	654.9	655.0	655.5	656.2	656.9	657.5
165°	665.3	664.5	664.2	663.8	663.5	663.3	663.4	664.0	664.7	665.3	666.0
167.5°	671.5	670.7	670.4	670.1	669.8	669.5	669.7	670.3	671.0	671.7	672.3
170°	674.7	673.9	673.6	673.4	673.3	673.0	673.3	673.9	674.6	675.2	675.8
172.5°	677.0	676.3	676.0	675.8	675.6	675.3	675.6	676.3	676.9	677.6	678.3
175°	679.6	678.8	678.5	678.3	678.2	678.0	678.2	679.0	679.8	680.5	681.3
177.5°	680.0	679.4	679.3	679.2	679.1	679.0	679.3	680.0	680.5	681.2	681.7
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1018.9	1019.7	1025.4	1027.9	1033.0	1035.0	1037.2	1036.6	1036.6	1037.7	1045.7
5°	1021.1	1028.1	1038.7	1048.9	1058.8	1067.2	1072.8	1078.5	1080.5	1090.8	1099.9
7.5°	1017.5	1030.4	1047.8	1063.4	1082.0	1096.6	1108.7	1119.6	1127.1	1142.0	1157.2
10°	1012.7	1031.0	1050.7	1070.7	1096.5	1115.8	1135.5	1150.7	1155.6	1177.7	1190.4
12.5°	1003.1	1027.6	1052.6	1078.6	1103.7	1130.4	1152.1	1167.2	1184.6	1204.5	1227.9
15°	988.7	1016.9	1049.6	1083.1	1119.0	1151.3	1174.6	1201.0	1219.9	1241.8	1262.2
17.5°	968.1	1004.4	1045.9	1084.7	1126.1	1160.9	1193.0	1218.2	1231.6	1244.1	1247.2
20°	951.8	990.8	1039.7	1085.5	1127.0	1167.2	1198.8	1219.9	1223.5	1223.8	1205.1
22.5°	934.1	978.2	1029.4	1076.2	1125.9	1170.5	1195.1	1204.2	1190.2	1166.4	1130.3
25°	901.4	952.4	1011.9	1065.5	1119.6	1161.9	1170.4	1154.5	1105.6	1054.1	989.1
27.5°	866.1	923.4	987.2	1046.7	1104.5	1130.7	1112.4	1055.3	967.1	890.6	797.8
30°	840.2	904.6	967.2	1033.8	1087.2	1098.5	1056.7	972.5	869.8	754.3	661.8
32.5°	810.6	878.1	947.0	1015.8	1060.5	1049.5	980.3	876.8	756.3	642.8	555.3
35°	768.4	838.1	912.3	981.3	1009.8	962.3	858.8	724.1	600.9	494.9	434.7
37.5°	719.6	795.5	872.7	936.0	934.1	854.8	713.9	574.7	471.2	408.5	365.6
40°	684.9	761.7	845.1	898.6	875.7	772.6	619.8	488.5	412.8	362.9	331.6
42.5°	651.8	728.8	811.6	854.1	814.4	687.6	535.4	432.5	370.0	331.1	305.7
45°	595.2	676.5	753.3	776.8	705.7	566.0	432.9	358.4	316.8	287.9	270.3
47.5°	540.0	619.9	689.9	690.4	594.2	459.0	365.2	310.1	274.7	252.3	239.5
50°	506.1	582.2	640.9	631.8	522.7	408.3	326.6	279.1	249.6	232.3	219.0
52.5°	468.2	541.9	592.8	566.8	462.1	359.3	292.0	252.1	227.6	212.6	200.7
55°	412.8	478.3	514.3	474.9	377.0	298.8	246.8	215.4	197.1	184.5	174.3
57.5°	358.6	412.6	435.2	389.3	310.5	247.8	208.7	185.2	167.0	158.0	152.7
60°	324.5	370.6	386.4	335.8	269.9	216.8	184.8	163.0	149.6	143.6	138.4
62.5°	291.1	328.7	335.3	288.8	235.4	189.8	162.3	143.8	135.0	129.2	124.2
65°	241.5	268.5	265.4	228.1	186.2	150.6	130.5	119.3	112.6	104.5	95.8
67.5°	198.8	215.4	205.4	177.4	142.1	117.1	104.0	95.5	87.2	79.5	77.5
70°	171.7	181.3	170.7	145.1	116.5	98.2	87.7	77.5	72.5	70.8	67.6
72.5°	145.9	149.2	137.8	115.7	94.8	81.3	71.1	65.3	62.7	61.2	59.1
75°	109.4	107.0	97.2	79.9	65.8	56.6	53.5	51.4	49.7	48.3	47.1
77.5°	76.9	73.2	64.5	53.3	45.8	41.5	39.6	38.5	37.6	36.9	35.8
80°	57.7	55.2	46.5	38.0	34.9	32.7	31.7	30.3	30.3	29.6	28.5
82.5°	42.2	39.5	31.9	27.9	26.1	24.9	24.0	23.2	22.9	23.1	22.3
85°	22.1	17.9	15.8	15.2	14.0	13.4	13.8	13.0	13.0	13.0	12.6
87.5°	7.1	5.9	5.8	5.8	6.3	6.5	6.4	6.6	7.1	6.9	7.3
90°	1.7	2.9	4.1	5.3	6.3	7.3	8.1	9.0	9.8	10.4	10.9
92.5°	9.8	9.7	9.6	9.5	9.7	10.1	10.6	10.9	11.4	11.7	12.0
95°	28.4	24.8	21.1	17.5	16.1	16.9	17.6	18.4	19.2	19.7	20.3
97.5°	53.3	43.2	33.0	22.8	18.6	20.4	22.1	23.9	25.6	26.1	26.6
100°	72.1	57.1	42.1	27.1	20.6	22.4	24.3	26.2	28.0	28.9	29.8
102.5°	109.9	106.7	103.5	100.4	91.0	75.5	59.9	44.4	28.8	30.0	31.1
105°	152.8	156.1	159.4	162.7	149.4	119.5	89.7	59.9	30.0	31.2	32.4
107.5°	193.8	196.4	199.1	201.7	185.1	149.4	113.6	77.8	42.0	40.8	39.6
110°	220.2	222.5	224.8	227.1	212.4	180.9	149.3	117.6	86.1	75.1	64.2



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	245.2	247.1	249.2	251.2	248.4	240.5	232.7	224.9	217.2	177.2	137.3
115°	284.6	286.5	288.4	290.3	292.6	295.3	298.0	300.8	303.5	252.9	202.3
117.5°	320.5	322.5	324.6	326.7	328.7	330.5	332.4	334.3	336.1	324.0	311.7
120°	345.9	347.6	349.2	350.9	352.7	354.7	356.7	358.5	360.5	361.8	363.2
122.5°	368.1	369.9	371.6	373.2	375.2	377.3	379.5	381.6	383.8	384.6	385.3
125°	401.3	402.7	404.2	405.6	407.4	409.4	411.5	413.6	415.7	416.4	417.2
127.5°	431.9	433.5	435.0	436.6	438.2	439.7	441.3	442.8	444.4	445.4	446.6
130°	451.3	453.1	454.9	456.6	458.1	459.3	460.4	461.7	462.9	464.1	465.2
132.5°	470.7	472.2	473.7	475.2	476.5	477.8	479.0	480.1	481.4	482.4	483.4
135°	496.6	498.3	500.1	501.8	503.2	504.2	505.2	506.1	507.1	508.2	509.3
137.5°	521.9	523.1	524.3	525.6	526.8	527.9	529.0	530.1	531.2	532.3	533.4
140°	538.5	539.4	540.3	541.1	542.2	543.4	544.6	545.7	547.0	548.0	548.9
142.5°	552.6	553.4	554.1	555.0	556.0	557.4	558.7	560.2	561.6	562.4	563.4
145°	573.9	573.8	573.7	573.6	574.5	576.4	578.2	580.0	581.9	582.7	583.4
147.5°	593.0	592.6	592.2	591.7	592.5	594.3	596.2	597.9	599.8	600.4	601.0
150°	605.2	604.5	603.7	602.9	603.4	605.2	606.9	608.7	610.4	611.1	611.7
152.5°	615.8	614.9	614.1	613.2	613.6	615.3	617.0	618.6	620.3	620.9	621.6
155°	631.1	630.1	629.1	628.1	628.3	629.6	630.9	632.3	633.6	634.2	634.9
157.5°	643.4	642.5	641.7	640.8	640.9	641.8	642.7	643.7	644.6	645.3	646.0
160°	650.6	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3	652.0	652.5
162.5°	656.9	656.2	655.5	655.0	654.9	655.4	656.0	656.6	657.1	657.9	658.6
165°	665.3	664.7	664.0	663.4	663.3	663.5	663.8	664.2	664.5	665.3	666.1
167.5°	671.7	671.0	670.3	669.7	669.5	669.8	670.1	670.4	670.7	671.5	672.2
170°	675.2	674.6	673.9	673.3	673.0	673.3	673.4	673.6	673.9	674.7	675.4
172.5°	677.6	676.9	676.3	675.6	675.3	675.6	675.8	676.0	676.3	677.0	677.8
175°	680.5	679.8	679.0	678.2	678.0	678.2	678.3	678.5	678.8	679.6	680.3
177.5°	681.2	680.5	680.0	679.3	679.0	679.1	679.2	679.3	679.4	680.0	680.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1048.5	1052.2	1053.9	1053.9	1055.8	1055.0	1054.1
5°	1108.7	1115.4	1116.8	1123.1	1127.8	1126.3	1127.0
7.5°	1168.7	1179.4	1190.1	1194.9	1195.7	1198.5	1199.6
10°	1205.5	1214.4	1230.9	1228.4	1240.8	1247.7	1236.1
12.5°	1241.0	1252.9	1264.4	1267.5	1274.5	1276.8	1272.1
15°	1273.1	1279.4	1280.2	1278.4	1280.5	1278.7	1272.1
17.5°	1243.1	1232.8	1212.0	1202.1	1194.3	1182.8	1178.2
20°	1193.5	1163.3	1128.1	1114.0	1097.5	1065.1	1072.8
22.5°	1086.6	1052.1	1016.9	975.7	956.1	925.4	923.6
25°	920.1	860.6	795.1	749.3	722.6	692.0	678.6
27.5°	715.4	640.5	586.8	559.7	534.9	510.7	509.6
30°	580.8	524.4	483.0	459.7	444.6	434.3	436.5
32.5°	489.6	450.9	422.9	403.7	392.5	384.7	384.7
35°	400.2	373.8	355.8	347.8	339.7	334.0	334.4
37.5°	342.5	326.6	316.6	307.7	302.7	299.9	298.3
40°	312.9	299.9	292.2	286.9	282.7	278.8	278.1
42.5°	289.5	278.8	271.0	266.8	263.0	260.1	259.5
45°	256.9	248.2	241.1	236.5	234.8	232.3	232.3
47.5°	228.6	219.9	214.4	211.5	208.5	206.9	206.8
50°	209.4	202.7	197.8	196.0	193.6	192.6	192.2
52.5°	192.3	187.3	183.7	182.6	181.4	180.1	180.3
55°	168.9	166.2	164.8	163.6	161.9	159.8	161.2
57.5°	149.3	146.9	143.1	139.8	138.2	136.7	137.2
60°	135.5	130.5	125.6	121.8	120.7	117.5	117.5
62.5°	118.1	111.1	105.1	102.9	101.9	100.4	100.1
65°	90.8	88.0	86.6	85.2	84.5	84.5	83.8
67.5°	75.2	74.1	72.6	72.2	71.5	71.4	71.1
70°	66.5	65.1	64.4	64.1	63.3	63.7	62.7
72.5°	58.1	56.9	56.8	55.9	55.5	55.5	54.8
75°	45.7	45.7	45.4	45.1	44.4	44.0	44.4
77.5°	35.2	35.3	34.6	34.6	34.5	34.6	34.2
80°	28.2	28.5	28.2	27.8	27.4	27.8	27.4
82.5°	22.2	21.8	21.7	21.6	21.6	21.3	21.3
85°	12.6	13.0	12.6	12.3	12.3	12.3	12.6
87.5°	7.1	7.2	7.3	7.4	7.4	7.4	7.2
90°	11.5	12.1	12.4	12.6	12.8	13.1	13.3
92.5°	12.3	12.5	12.7	12.9	13.0	13.2	13.3
95°	20.8	21.4	21.6	21.5	21.4	21.3	21.1
97.5°	27.0	27.4	27.7	27.8	28.0	28.1	28.3
100°	30.6	31.6	32.0	32.3	32.5	32.7	33.0
102.5°	32.2	33.4	34.1	34.4	34.7	35.0	35.3
105°	33.6	34.8	35.6	36.1	36.5	36.9	37.4
107.5°	38.4	37.1	36.8	37.1	37.6	38.0	38.5
110°	53.3	42.3	37.1	37.5	38.0	38.5	38.8



TEST NUMBER: P331651-830

CATALOG NUMBER: S122RDIP-S485D530U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	97.5	57.6	37.9	38.2	38.5	38.9	39.2
115°	151.7	101.0	71.8	63.9	56.1	48.2	40.3
117.5°	299.4	287.2	268.2	242.2	216.4	190.6	164.7
120°	364.5	365.8	359.1	344.3	329.6	314.8	300.0
122.5°	386.2	386.9	385.9	383.0	380.1	377.3	374.4
125°	417.9	418.7	419.2	419.6	419.9	420.3	420.6
127.5°	447.7	448.8	449.4	449.5	449.6	449.6	449.7
130°	466.5	467.7	468.3	468.1	468.0	467.9	467.8
132.5°	484.5	485.5	485.9	485.8	485.7	485.6	485.5
135°	510.4	511.5	512.0	511.7	511.5	511.3	511.0
137.5°	534.4	535.6	535.8	535.5	535.1	534.8	534.4
140°	549.9	550.9	551.1	550.5	550.1	549.5	548.9
142.5°	564.2	565.1	565.3	564.8	564.2	563.6	563.1
145°	584.2	584.9	585.0	584.6	584.0	583.4	582.9
147.5°	601.5	602.1	602.1	601.7	601.2	600.8	600.3
150°	612.4	613.0	613.1	612.6	612.0	611.4	611.0
152.5°	622.3	622.9	622.8	622.2	621.4	620.7	620.0
155°	635.6	636.2	636.0	635.2	634.3	633.5	632.5
157.5°	646.8	647.5	647.5	646.6	645.7	644.9	644.0
160°	653.2	653.8	653.8	653.1	652.3	651.5	650.7
162.5°	659.4	660.2	660.1	659.1	658.2	657.2	656.3
165°	666.8	667.6	667.6	666.8	666.1	665.3	664.5
167.5°	673.1	673.8	673.7	672.7	671.8	670.7	669.8
170°	676.2	676.9	676.8	675.8	674.9	673.9	672.9
172.5°	678.5	679.3	679.2	678.3	677.2	676.3	675.2
175°	681.1	681.8	681.7	680.6	679.5	678.4	677.3
177.5°	681.3	681.8	681.7	681.0	680.1	679.4	678.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8

(END OF REPORT)