

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331665-830

Luminaire Tested: **S122RDIP-S485D925U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331665-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D925U830-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5159.0 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	37	37	36	30
2	87	80	74	69	78	72	68	63	58	55	52	45	43	41	34	32	31	26
3	79	71	64	58	72	64	58	54	52	48	45	41	38	36	30	29	27	22
4	73	63	55	50	66	57	51	46	47	42	38	37	34	31	27	25	24	20
5	67	56	49	43	60	51	45	40	42	37	33	33	30	27	25	23	21	18
6	62	51	43	38	56	46	40	35	38	33	29	30	27	24	23	21	19	16
7	57	46	38	33	52	42	35	31	35	30	26	28	24	22	21	19	17	14
8	53	42	34	29	48	38	32	27	32	27	23	25	22	19	20	17	16	13
9	50	38	31	26	45	35	29	24	29	24	21	23	20	18	18	16	14	12
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16356	16356	16356	16356
5°	18266	16459	14593	16459
10°	20266	16342	12650	16342
15°	21264	16104	9967	16104
20°	18433	15747	8624	15747
25°	12089	15262	7701	15262
30°	8138	14673	6969	14673
35°	6591	13931	6286	13931
40°	5861	13122	5817	13122
45°	5304	12177	5190	12177
50°	4828	11235	4808	11235
55°	4538	10196	4479	10196
60°	3794	9242	3749	9242
65°	3202	8390	3629	8390
70°	2960	7492	3423	7492
75°	2770	6519	3163	6519
80°	2548	5365	2817	5365
85°	2334	4242	2482	4242



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	1.9
10°-20°	267.6	5.2
20°-30°	344.8	6.7
30°-40°	327.7	6.4
40°-50°	280.7	5.4
50°-60°	213.8	4.1
60°-70°	135.1	2.6
70°-80°	67.5	1.3
80°-90°	22.0	0.4
90°-100°	195.6	3.8
100°-110°	663.7	12.9
110°-120°	705.1	13.7
120°-130°	580.4	11.3
130°-140°	466.1	9.0
140°-150°	352.2	6.8
150°-160°	247.5	4.8
160°-170°	145.7	2.8
170°-180°	47.4	0.9
0°-30°	708.4	13.7
0°-40°	1036.1	20.1
0°-60°	1530.5	29.7
0°-90°	1755.1	34.0
90°-120°	1564.4	30.3
90°-150°	2963.2	57.4
90°-180°	3404.0	66.0
0°-180°	5159.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1013	1013	1013	1013	1013	
5°	1127	1016	900	1016	1127	111
15°	1272	963	596	963	1272	343
25°	679	857	432	857	679	322
35°	334	707	319	707	334	214
45°	232	533	227	533	232	180
55°	161	362	159	362	161	141
65°	84	220	95	220	84	85
75°	44	104	51	104	44	47
85°	13	23	13	23	13	14
90°	31	1	31	1	31	17
95°	107	33	107	33	107	139
105°	1060	115	1060	115	1060	1026
115°	1395	202	1395	202	1395	1366
125°	1132	282	1132	282	1132	1023
135°	938	331	938	331	938	729
145°	749	378	749	378	749	476
155°	629	430	629	430	629	294
165°	552	468	552	468	552	158
175°	498	488	498	488	498	48
180°	489	489	489	489	489	



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1054.1	1055.0	1055.8	1053.9	1053.9	1052.2	1048.5	1045.7	1037.7	1036.6	1036.6
5°	1127.0	1126.3	1127.8	1123.1	1116.8	1115.4	1108.7	1099.9	1090.8	1080.5	1078.5
7.5°	1199.6	1198.5	1195.7	1194.9	1190.1	1179.4	1168.7	1157.2	1142.0	1127.1	1119.6
10°	1236.1	1247.7	1240.8	1228.4	1230.9	1214.4	1205.5	1190.4	1177.7	1155.6	1150.7
12.5°	1272.1	1276.8	1274.5	1267.5	1264.4	1252.9	1241.0	1227.9	1204.5	1184.6	1167.2
15°	1272.1	1278.7	1280.5	1278.4	1280.2	1279.4	1273.1	1262.2	1241.8	1219.9	1201.0
17.5°	1178.2	1182.8	1194.3	1202.1	1212.0	1232.8	1243.1	1247.2	1244.1	1231.6	1218.2
20°	1072.8	1065.1	1097.5	1114.0	1128.1	1163.3	1193.5	1205.1	1223.8	1223.5	1219.9
22.5°	923.6	925.4	956.1	975.7	1016.9	1052.1	1086.6	1130.3	1166.4	1190.2	1204.2
25°	678.6	692.0	722.6	749.3	795.1	860.6	920.1	989.1	1054.1	1105.6	1154.5
27.5°	509.6	510.7	534.9	559.7	586.8	640.5	715.4	797.8	890.6	967.1	1055.3
30°	436.5	434.3	444.6	459.7	483.0	524.4	580.8	661.8	754.3	869.8	972.5
32.5°	384.7	384.7	392.5	403.7	422.9	450.9	489.6	555.3	642.8	756.3	876.8
35°	334.4	334.0	339.7	347.8	355.8	373.8	400.2	434.7	494.9	600.9	724.1
37.5°	298.3	299.9	302.7	307.7	316.6	326.6	342.5	365.6	408.5	471.2	574.7
40°	278.1	278.8	282.7	286.9	292.2	299.9	312.9	331.6	362.9	412.8	488.5
42.5°	259.5	260.1	263.0	266.8	271.0	278.8	289.5	305.7	331.1	370.0	432.5
45°	232.3	232.3	234.8	236.5	241.1	248.2	256.9	270.3	287.9	316.8	358.4
47.5°	206.8	206.9	208.5	211.5	214.4	219.9	228.6	239.5	252.3	274.7	310.1
50°	192.2	192.6	193.6	196.0	197.8	202.7	209.4	219.0	232.3	249.6	279.1
52.5°	180.3	180.1	181.4	182.6	183.7	187.3	192.3	200.7	212.6	227.6	252.1
55°	161.2	159.8	161.9	163.6	164.8	166.2	168.9	174.3	184.5	197.1	215.4
57.5°	137.2	136.7	138.2	139.8	143.1	146.9	149.3	152.7	158.0	167.0	185.2
60°	117.5	117.5	120.7	121.8	125.6	130.5	135.5	138.4	143.6	149.6	163.0
62.5°	100.1	100.4	101.9	102.9	105.1	111.1	118.1	124.2	129.2	135.0	143.8
65°	83.8	84.5	84.5	85.2	86.6	88.0	90.8	95.8	104.5	112.6	119.3
67.5°	71.1	71.4	71.5	72.2	72.6	74.1	75.2	77.5	79.5	87.2	95.5
70°	62.7	63.7	63.3	64.1	64.4	65.1	66.5	67.6	70.8	72.5	77.5
72.5°	54.8	55.5	55.5	55.9	56.8	56.9	58.1	59.1	61.2	62.7	65.3
75°	44.4	44.0	44.4	45.1	45.4	45.7	45.7	47.1	48.3	49.7	51.4
77.5°	34.2	34.6	34.5	34.6	34.6	35.3	35.2	35.8	36.9	37.6	38.5
80°	27.4	27.8	27.4	27.8	28.2	28.5	28.2	28.5	29.6	30.3	30.3
82.5°	21.3	21.3	21.6	21.6	21.7	21.8	22.2	22.3	23.1	22.9	23.2
85°	12.6	12.3	12.3	12.3	12.6	13.0	12.6	12.6	13.0	13.0	13.0
87.5°	10.7	11.0	11.0	11.0	11.0	10.8	10.5	11.1	11.0	11.5	11.0
90°	31.0	31.0	31.0	31.0	31.0	30.1	28.2	30.1	31.0	32.0	31.0
92.5°	52.1	53.6	52.9	55.9	56.6	62.5	70.4	82.0	103.3	122.2	120.6
95°	107.3	106.3	109.1	116.7	128.8	149.6	189.1	246.5	322.6	368.7	326.4
97.5°	211.1	219.0	232.7	255.9	300.9	368.7	470.5	575.1	660.3	629.5	474.1
100°	336.8	353.7	381.0	421.4	499.5	613.3	742.2	858.8	878.6	743.1	511.7
102.5°	592.7	615.6	649.6	718.7	803.5	924.2	1018.4	1044.7	959.9	746.9	497.5
105°	1060.2	1073.3	1113.8	1172.1	1230.4	1261.5	1249.2	1142.9	947.3	697.0	469.4
107.5°	1354.2	1371.7	1379.8	1383.0	1375.6	1330.1	1232.3	1072.2	864.7	643.7	455.4
110°	1443.0	1444.0	1435.5	1417.6	1377.1	1300.0	1179.6	1011.3	812.8	618.0	452.5



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1441.5	1436.4	1420.4	1390.5	1334.3	1245.9	1117.2	955.5	776.7	601.4	453.2
115°	1395.1	1386.6	1362.1	1318.8	1252.1	1155.2	1031.9	887.0	731.9	583.2	457.1
117.5°	1312.0	1305.0	1279.1	1233.4	1165.4	1074.4	962.7	835.5	703.6	574.4	463.9
120°	1258.7	1249.2	1221.9	1177.7	1111.9	1026.2	926.6	809.9	688.6	569.1	468.4
122.5°	1203.0	1195.0	1170.7	1127.3	1068.3	990.9	896.5	789.6	675.8	566.1	473.7
125°	1131.6	1124.1	1100.6	1064.9	1010.3	939.7	857.0	760.1	657.5	560.6	481.6
127.5°	1069.2	1063.2	1042.8	1009.4	961.8	896.6	818.6	730.9	640.6	557.4	489.7
130°	1033.8	1026.2	1007.5	975.5	929.4	867.3	793.0	712.1	629.3	555.9	495.8
132.5°	996.9	990.1	972.9	940.8	895.5	837.2	768.9	694.0	620.3	555.2	501.7
135°	937.8	934.1	917.2	886.1	845.6	793.0	730.9	668.8	607.7	554.0	508.9
137.5°	880.0	874.3	859.4	832.7	795.8	749.9	700.6	648.7	598.8	553.8	515.3
140°	840.0	834.4	820.3	795.8	765.7	724.3	681.1	635.9	593.6	553.1	518.3
142.5°	800.1	799.0	786.5	764.2	735.7	701.0	663.7	625.4	588.3	553.1	520.6
145°	748.8	745.9	736.6	720.6	698.0	670.7	641.6	610.5	581.4	551.2	523.0
147.5°	705.7	704.0	697.6	684.9	666.2	646.2	623.5	599.0	574.2	547.9	523.8
150°	680.1	679.2	673.5	662.2	648.1	631.2	611.4	590.8	568.2	545.6	523.0
152.5°	658.3	658.1	653.9	644.1	633.1	618.4	601.6	582.5	562.9	541.9	521.5
155°	629.3	631.2	627.5	620.9	610.5	600.1	586.1	571.0	553.1	535.3	519.2
157.5°	604.6	604.6	602.9	597.5	590.2	582.1	570.2	557.6	543.9	528.5	514.9
160°	588.9	588.9	588.0	583.2	576.6	570.0	559.7	549.3	537.2	524.0	512.6
162.5°	573.8	574.6	573.6	570.4	563.8	558.7	549.9	541.1	531.1	520.2	510.4
165°	552.1	553.1	553.1	549.3	545.6	541.9	535.3	528.7	521.1	512.6	506.1
167.5°	532.3	533.4	533.6	531.5	529.8	526.4	521.9	516.8	511.3	506.1	501.7
170°	520.2	522.1	523.0	520.2	519.2	517.4	513.6	510.8	506.1	502.3	499.5
172.5°	510.4	511.5	512.5	511.1	510.2	509.1	506.1	504.0	500.9	497.9	496.5
175°	497.7	499.5	500.5	499.5	499.5	498.6	497.7	496.7	493.9	492.9	492.0
177.5°	489.9	491.4	492.2	492.2	492.2	492.2	491.4	491.4	489.9	489.2	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1037.2	1035.0	1033.0	1027.9	1025.4	1019.7	1018.9	1018.6	1011.3	1004.3	1002.3
5°	1072.8	1067.2	1058.8	1048.9	1038.7	1028.1	1021.1	1015.5	1001.4	988.0	980.2
7.5°	1108.7	1096.6	1082.0	1063.4	1047.8	1030.4	1017.5	1005.8	985.8	966.7	953.8
10°	1135.5	1115.8	1096.5	1070.7	1050.7	1031.0	1012.7	996.8	974.3	949.0	930.9
12.5°	1152.1	1130.4	1103.7	1078.6	1052.6	1027.6	1003.1	982.7	956.3	930.1	908.7
15°	1174.6	1151.3	1119.0	1083.1	1049.6	1016.9	988.7	963.4	928.9	897.6	871.5
17.5°	1193.0	1160.9	1126.1	1084.7	1045.9	1004.4	968.1	935.7	897.3	859.5	828.9
20°	1198.8	1167.2	1127.0	1085.5	1039.7	990.8	951.8	916.5	875.3	834.2	799.0
22.5°	1195.1	1170.5	1125.9	1076.2	1029.4	978.2	934.1	893.2	847.5	805.5	764.7
25°	1170.4	1161.9	1119.6	1065.5	1011.9	952.4	901.4	856.7	804.6	759.6	715.2
27.5°	1112.4	1130.7	1104.5	1046.7	987.2	923.4	866.1	815.2	761.1	710.4	666.2
30°	1056.7	1098.5	1087.2	1033.8	967.2	904.6	840.2	787.0	729.3	677.2	633.6
32.5°	980.3	1049.5	1060.5	1015.8	947.0	878.1	810.6	757.7	697.5	642.5	600.0
35°	858.8	962.3	1009.8	981.3	912.3	838.1	768.4	706.8	646.2	592.0	549.8
37.5°	713.9	854.8	934.1	936.0	872.7	795.5	719.6	658.5	596.4	543.3	497.6
40°	619.8	772.6	875.7	898.6	845.1	761.7	684.9	622.6	562.1	510.0	457.6
42.5°	535.4	687.6	814.4	854.1	811.6	728.8	651.8	586.6	527.7	478.4	424.9
45°	432.9	566.0	705.7	776.8	753.3	676.5	595.2	533.3	478.0	435.4	384.0
47.5°	365.2	459.0	594.2	690.4	689.9	619.9	540.0	480.6	429.3	389.5	347.8
50°	326.6	408.3	522.7	631.8	640.9	582.2	506.1	447.3	399.5	357.6	324.1
52.5°	292.0	359.3	462.1	566.8	592.8	541.9	468.2	413.9	367.4	328.9	300.2
55°	246.8	298.8	377.0	474.9	514.3	478.3	412.8	362.2	324.5	292.2	267.5
57.5°	208.7	247.8	310.5	389.3	435.2	412.6	358.6	317.4	285.2	255.9	236.5
60°	184.8	216.8	269.9	335.8	386.4	370.6	324.5	286.2	258.7	233.4	215.1
62.5°	162.3	189.8	235.4	288.8	335.3	328.7	291.1	258.8	234.8	211.7	196.2
65°	130.5	150.6	186.2	228.1	265.4	268.5	241.5	219.6	198.1	179.8	166.2
67.5°	104.0	117.1	142.1	177.4	205.4	215.4	198.8	182.1	165.0	150.9	139.0
70°	87.7	98.2	116.5	145.1	170.7	181.3	171.7	158.7	143.9	132.3	122.2
72.5°	71.1	81.3	94.8	115.7	137.8	149.2	145.9	136.5	124.5	114.9	105.3
75°	53.5	56.6	65.8	79.9	97.2	107.0	109.4	104.5	95.0	87.7	82.0
77.5°	39.6	41.5	45.8	53.3	64.5	73.2	76.9	76.3	69.7	65.5	60.2
80°	31.7	32.7	34.9	38.0	46.5	55.2	57.7	57.7	53.2	51.4	46.1
82.5°	24.0	24.9	26.1	27.9	31.9	39.5	42.2	42.8	39.9	37.6	33.5
85°	13.8	13.4	14.0	15.2	15.8	17.9	22.1	22.9	22.1	19.3	18.3
87.5°	9.9	8.9	7.9	7.1	7.0	6.9	7.5	8.4	7.8	7.7	7.5
90°	25.4	18.9	14.1	11.3	9.4	7.5	3.8	0.9	3.8	7.5	9.4
92.5°	93.9	64.0	42.7	33.8	27.4	23.4	16.6	11.5	16.6	23.4	27.4
95°	217.3	135.4	92.2	69.7	54.6	46.1	36.7	32.9	36.7	46.1	54.6
97.5°	292.8	178.7	124.3	98.8	81.4	68.7	58.7	53.6	58.7	68.7	81.4
100°	308.6	193.8	143.9	117.6	98.8	83.7	75.2	72.4	75.2	83.7	98.8
102.5°	309.3	207.4	161.3	134.9	115.4	100.3	91.8	89.7	91.8	100.3	115.4
105°	314.1	230.5	186.2	159.9	139.2	125.1	118.6	114.8	118.6	125.1	139.2
107.5°	327.2	254.2	211.3	184.7	164.3	151.3	144.9	141.9	144.9	151.3	164.3
110°	337.7	269.9	228.6	201.3	181.5	169.3	163.7	159.9	163.7	169.3	181.5



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	349.0	285.0	245.2	217.1	198.1	186.6	180.2	176.4	180.2	186.6	198.1
115°	365.9	308.6	268.1	242.7	223.9	212.6	207.0	202.3	207.0	212.6	223.9
117.5°	384.0	330.2	292.8	266.4	248.4	238.4	232.7	228.9	232.7	238.4	248.4
120°	396.1	345.3	308.6	282.2	263.3	255.0	249.3	245.5	249.3	255.0	263.3
122.5°	406.5	359.5	325.1	298.0	279.2	269.9	264.3	261.4	264.3	269.9	279.2
125°	423.3	381.0	347.1	320.7	302.0	290.7	285.0	282.2	285.0	290.7	302.0
127.5°	438.9	401.0	368.0	340.9	322.8	310.4	302.6	298.8	302.6	310.4	322.8
130°	448.7	412.9	380.0	353.7	334.9	321.7	312.3	308.6	312.3	321.7	334.9
132.5°	458.5	423.5	392.1	365.7	346.2	332.2	322.1	317.5	322.1	332.2	346.2
135°	471.3	438.4	408.2	381.9	360.2	346.2	334.9	331.1	334.9	346.2	360.2
137.5°	481.1	450.4	420.7	396.2	374.8	359.7	348.5	343.9	348.5	359.7	374.8
140°	486.4	457.1	429.0	404.5	383.8	368.7	357.5	353.7	357.5	368.7	383.8
142.5°	490.9	462.4	435.0	412.0	392.1	377.0	366.5	363.4	366.5	377.0	392.1
145°	496.7	470.3	445.0	424.2	405.5	391.3	381.9	378.1	381.9	391.3	405.5
147.5°	499.9	476.7	452.9	434.4	418.8	405.8	396.8	394.0	396.8	405.8	418.8
150°	501.3	479.8	458.1	441.2	427.1	414.8	407.3	404.5	407.3	414.8	427.1
152.5°	502.1	482.8	463.4	448.0	434.6	423.9	416.3	415.0	416.3	423.9	434.6
155°	503.2	487.3	471.3	457.1	446.9	436.5	430.8	429.9	430.8	436.5	446.9
157.5°	503.2	490.5	476.9	465.1	456.8	447.8	443.3	442.3	443.3	447.8	456.8
160°	503.2	492.0	480.7	470.3	462.8	455.2	451.6	450.6	451.6	455.2	462.8
162.5°	502.5	492.8	483.0	474.9	468.1	462.0	458.3	458.8	458.3	462.0	468.1
165°	500.5	493.9	485.4	479.8	475.0	469.4	467.5	468.4	467.5	469.4	475.0
167.5°	499.2	493.7	487.5	483.9	480.5	476.9	475.2	476.4	475.2	476.9	480.5
170°	497.7	492.9	488.2	485.4	483.5	480.7	479.8	481.6	479.8	480.7	483.5
172.5°	495.4	492.2	489.0	486.9	485.8	483.0	483.5	484.7	483.5	483.0	485.8
175°	492.9	491.1	489.2	488.2	488.2	486.4	487.3	488.2	487.3	486.4	488.2
177.5°	491.4	489.9	489.2	489.2	489.2	487.7	488.4	489.9	488.4	487.7	489.2
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	998.6	996.6	993.0	987.4	984.0	978.1	974.1	976.4	976.9	976.4	975.8
5°	971.9	964.4	954.2	944.3	935.2	925.4	919.7	917.3	912.3	909.6	908.1
7.5°	939.3	926.6	912.2	895.0	880.4	865.2	857.3	853.5	843.4	837.9	833.1
10°	915.1	895.0	880.6	858.1	844.4	824.3	810.6	811.0	797.2	789.5	783.8
12.5°	888.4	866.4	842.4	822.1	803.0	786.9	770.3	763.6	749.0	741.6	726.4
15°	844.0	818.3	793.1	765.5	746.2	721.2	697.3	668.1	644.5	624.1	618.4
17.5°	795.6	763.8	738.4	706.2	673.0	630.9	603.2	586.3	572.0	561.3	553.3
20°	762.4	730.0	702.9	654.3	609.6	581.1	560.7	547.7	532.9	521.3	514.9
22.5°	727.5	693.7	656.8	602.5	567.7	544.8	526.6	511.6	501.6	492.6	486.8
25°	677.9	640.9	580.0	542.7	514.6	490.7	478.0	468.8	458.3	445.9	440.4
27.5°	625.6	566.8	523.0	495.3	468.4	452.9	441.5	427.8	418.4	412.8	407.0
30°	586.4	527.6	493.5	463.2	444.2	427.0	413.6	405.9	396.7	387.2	383.3
32.5°	542.7	495.8	463.1	437.9	418.6	403.9	393.3	380.8	374.2	368.3	360.2
35°	488.5	453.0	423.1	402.7	384.4	372.4	360.1	352.7	340.7	335.8	332.6
37.5°	442.6	411.8	389.5	368.0	353.5	340.3	332.7	320.9	315.8	308.9	302.2
40°	416.7	386.4	365.0	347.4	331.2	321.3	311.9	302.4	294.6	291.4	283.3
42.5°	390.3	365.6	344.1	324.9	314.1	303.6	291.6	284.6	276.5	271.5	266.5
45°	353.7	332.0	313.6	297.7	285.8	274.9	267.1	255.5	251.0	240.7	236.5
47.5°	321.6	301.3	283.9	268.8	257.1	250.1	238.7	229.6	222.3	216.0	210.7
50°	298.8	281.9	265.0	251.7	241.1	230.9	219.3	214.7	203.4	200.3	197.1
52.5°	278.0	261.9	246.5	233.4	222.8	212.9	202.6	196.7	189.1	185.9	183.6
55°	248.8	233.4	218.6	207.0	196.4	186.2	179.8	172.5	168.9	166.5	163.6
57.5°	219.5	205.7	194.3	182.6	171.9	163.8	156.5	152.0	148.4	145.2	141.8
60°	201.0	187.6	177.4	166.5	155.6	148.9	143.3	138.0	133.7	128.8	127.4
62.5°	181.3	169.6	160.2	149.6	140.1	133.9	128.7	123.7	118.6	111.4	109.4
65°	154.2	145.1	135.2	126.4	117.9	112.0	104.2	98.6	96.4	95.8	95.4
67.5°	129.7	121.0	112.5	103.6	95.9	90.3	86.3	85.5	84.1	83.6	82.7
70°	113.3	105.3	96.8	88.3	81.0	79.9	78.5	77.1	75.3	74.6	73.9
72.5°	98.7	90.3	81.9	75.1	71.9	70.6	69.2	67.8	66.6	65.9	65.5
75°	75.7	68.0	62.3	59.9	58.1	57.0	55.0	53.8	53.2	52.1	51.7
77.5°	54.5	50.1	47.5	46.0	44.1	43.0	41.8	40.7	40.0	39.8	39.2
80°	41.6	39.4	37.7	35.5	34.9	33.5	33.1	32.0	32.4	31.3	31.3
82.5°	32.2	29.6	28.1	27.1	26.4	25.3	24.9	24.4	24.5	23.8	23.8
85°	16.6	15.8	15.2	14.4	14.4	13.4	13.8	13.4	13.4	12.6	12.3
87.5°	7.6	7.9	8.3	9.6	10.7	10.7	10.5	10.0	9.6	10.0	9.9
90°	11.3	14.1	18.9	25.4	31.0	32.0	31.0	30.1	28.2	30.1	31.0
92.5°	33.8	42.7	64.0	93.9	120.6	122.2	103.3	82.0	70.4	62.5	56.6
95°	69.7	92.2	135.4	217.3	326.4	368.7	322.6	246.5	189.1	149.6	128.8
97.5°	98.8	124.3	178.7	292.8	474.1	629.5	660.3	575.1	470.5	368.7	300.9
100°	117.6	143.9	193.8	308.6	511.7	743.1	878.6	858.8	742.2	613.3	499.5
102.5°	134.9	161.3	207.4	309.3	497.5	746.9	959.9	1044.7	1018.4	924.2	803.5
105°	159.9	186.2	230.5	314.1	469.4	697.0	947.3	1142.9	1249.2	1261.5	1230.4
107.5°	184.7	211.3	254.2	327.2	455.4	643.7	864.7	1072.2	1232.3	1330.1	1375.6
110°	201.3	228.6	269.9	337.7	452.5	618.0	812.8	1011.3	1179.6	1300.0	1377.1



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.1	245.2	285.0	349.0	453.2	601.4	776.7	955.5	1117.2	1245.9	1334.3
115°	242.7	268.1	308.6	365.9	457.1	583.2	731.9	887.0	1031.9	1155.2	1252.1
117.5°	266.4	292.8	330.2	384.0	463.9	574.4	703.6	835.5	962.7	1074.4	1165.4
120°	282.2	308.6	345.3	396.1	468.4	569.1	688.6	809.9	926.6	1026.2	1111.9
122.5°	298.0	325.1	359.5	406.5	473.7	566.1	675.8	789.6	896.5	990.9	1068.3
125°	320.7	347.1	381.0	423.3	481.6	560.6	657.5	760.1	857.0	939.7	1010.3
127.5°	340.9	368.0	401.0	438.9	489.7	557.4	640.6	730.9	818.6	896.6	961.8
130°	353.7	380.0	412.9	448.7	495.8	555.9	629.3	712.1	793.0	867.3	929.4
132.5°	365.7	392.1	423.5	458.5	501.7	555.2	620.3	694.0	768.9	837.2	895.5
135°	381.9	408.2	438.4	471.3	508.9	554.0	607.7	668.8	730.9	793.0	845.6
137.5°	396.2	420.7	450.4	481.1	515.3	553.8	598.8	648.7	700.6	749.9	795.8
140°	404.5	429.0	457.1	486.4	518.3	553.1	593.6	635.9	681.1	724.3	765.7
142.5°	412.0	435.0	462.4	490.9	520.6	553.1	588.3	625.4	663.7	701.0	735.7
145°	424.2	445.0	470.3	496.7	523.0	551.2	581.4	610.5	641.6	670.7	698.0
147.5°	434.4	452.9	476.7	499.9	523.8	547.9	574.2	599.0	623.5	646.2	666.2
150°	441.2	458.1	479.8	501.3	523.0	545.6	568.2	590.8	611.4	631.2	648.1
152.5°	448.0	463.4	482.8	502.1	521.5	541.9	562.9	582.5	601.6	618.4	633.1
155°	457.1	471.3	487.3	503.2	519.2	535.3	553.1	571.0	586.1	600.1	610.5
157.5°	465.1	476.9	490.5	503.2	514.9	528.5	543.9	557.6	570.2	582.1	590.2
160°	470.3	480.7	492.0	503.2	512.6	524.0	537.2	549.3	559.7	570.0	576.6
162.5°	474.9	483.0	492.8	502.5	510.4	520.2	531.1	541.1	549.9	558.7	563.8
165°	479.8	485.4	493.9	500.5	506.1	512.6	521.1	528.7	535.3	541.9	545.6
167.5°	483.9	487.5	493.7	499.2	501.7	506.1	511.3	516.8	521.9	526.4	529.8
170°	485.4	488.2	492.9	497.7	499.5	502.3	506.1	510.8	513.6	517.4	519.2
172.5°	486.9	489.0	492.2	495.4	496.5	497.9	500.9	504.0	506.1	509.1	510.2
175°	488.2	489.2	491.1	492.9	492.0	492.9	493.9	496.7	497.7	498.6	499.5
177.5°	489.2	489.2	489.9	491.4	489.9	489.2	489.9	491.4	491.4	492.2	492.2
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	972.7	973.3	972.4	973.0	972.4	973.3	972.7	975.8	976.4	976.9	976.4
5°	906.3	902.1	901.4	900.4	901.4	902.1	906.3	908.1	909.6	912.3	917.3
7.5°	827.1	826.4	824.7	822.2	824.7	826.4	827.1	833.1	837.9	843.4	853.5
10°	776.1	774.4	774.0	771.6	774.0	774.4	776.1	783.8	789.5	797.2	811.0
12.5°	716.4	705.1	703.9	697.8	703.9	705.1	716.4	726.4	741.6	749.0	763.6
15°	610.0	607.8	600.9	596.3	600.9	607.8	610.0	618.4	624.1	644.5	668.1
17.5°	549.1	542.2	540.1	539.1	540.1	542.2	549.1	553.3	561.3	572.0	586.3
20°	510.0	503.7	502.7	501.9	502.7	503.7	510.0	514.9	521.3	532.9	547.7
22.5°	483.0	476.4	473.6	471.6	473.6	476.4	483.0	486.8	492.6	501.6	511.6
25°	436.8	434.3	432.9	432.3	432.9	434.3	436.8	440.4	445.9	458.3	468.8
27.5°	400.7	395.3	394.2	392.4	394.2	395.3	400.7	407.0	412.8	418.4	427.8
30°	380.1	378.3	375.9	373.8	375.9	378.3	380.1	383.3	387.2	396.7	405.9
32.5°	355.9	354.5	352.2	351.3	352.2	354.5	355.9	360.2	368.3	374.2	380.8
35°	329.1	324.1	322.1	318.9	322.1	324.1	329.1	332.6	335.8	340.7	352.7
37.5°	300.8	298.1	295.2	296.2	295.2	298.1	300.8	302.2	308.9	315.8	320.9
40°	278.8	277.0	276.3	276.0	276.3	277.0	278.8	283.3	291.4	294.6	302.4
42.5°	261.3	256.5	254.6	254.6	254.6	256.5	261.3	266.5	271.5	276.5	284.6
45°	234.8	230.2	227.1	227.3	227.1	230.2	234.8	236.5	240.7	251.0	255.5
47.5°	207.6	207.5	205.5	206.1	205.5	207.5	207.6	210.7	216.0	222.3	229.6
50°	194.6	192.6	191.1	191.4	191.1	192.6	194.6	197.1	200.3	203.4	214.7
52.5°	182.3	180.4	179.3	180.8	179.3	180.4	182.3	183.6	185.9	189.1	196.7
55°	161.9	159.8	159.5	159.1	159.5	159.8	161.9	163.6	166.5	168.9	172.5
57.5°	139.2	137.8	135.6	134.8	135.6	137.8	139.2	141.8	145.2	148.4	152.0
60°	122.8	120.0	116.5	116.1	116.5	120.0	122.8	127.4	128.8	133.7	138.0
62.5°	107.9	107.4	106.7	106.6	106.7	107.4	107.9	109.4	111.4	118.6	123.7
65°	94.7	94.3	94.7	95.0	94.7	94.3	94.7	95.4	95.8	96.4	98.6
67.5°	82.5	81.9	81.2	81.5	81.2	81.9	82.5	82.7	83.6	84.1	85.5
70°	73.2	72.9	72.5	72.5	72.5	72.9	73.2	73.9	74.6	75.3	77.1
72.5°	64.2	64.1	63.8	63.5	63.8	64.1	64.2	65.5	65.9	66.6	67.8
75°	51.4	50.7	50.7	50.7	50.7	50.7	51.4	51.7	52.1	53.2	53.8
77.5°	39.1	38.8	38.5	38.2	38.5	38.8	39.1	39.2	39.8	40.0	40.7
80°	31.0	30.6	30.3	30.3	30.3	30.6	31.0	31.3	31.3	32.4	32.0
82.5°	23.7	23.3	23.2	22.9	23.2	23.3	23.7	23.8	23.8	24.5	24.4
85°	12.6	13.0	12.6	13.4	12.6	13.0	12.6	12.3	12.6	13.4	13.4
87.5°	9.9	9.6	9.9	9.6	9.9	9.6	9.9	9.9	10.0	9.6	10.0
90°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.0	30.1	28.2	30.1
92.5°	55.9	52.9	53.6	52.1	53.6	52.9	55.9	56.6	62.5	70.4	82.0
95°	116.7	109.1	106.3	107.3	106.3	109.1	116.7	128.8	149.6	189.1	246.5
97.5°	255.9	232.7	219.0	211.1	219.0	232.7	255.9	300.9	368.7	470.5	575.1
100°	421.4	381.0	353.7	336.8	353.7	381.0	421.4	499.5	613.3	742.2	858.8
102.5°	718.7	649.6	615.6	592.7	615.6	649.6	718.7	803.5	924.2	1018.4	1044.7
105°	1172.1	1113.8	1073.3	1060.2	1073.3	1113.8	1172.1	1230.4	1261.5	1249.2	1142.9
107.5°	1383.0	1379.8	1371.7	1354.2	1371.7	1379.8	1383.0	1375.6	1330.1	1232.3	1072.2
110°	1417.6	1435.5	1444.0	1443.0	1444.0	1435.5	1417.6	1377.1	1300.0	1179.6	1011.3



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1390.5	1420.4	1436.4	1441.5	1436.4	1420.4	1390.5	1334.3	1245.9	1117.2	955.5
115°	1318.8	1362.1	1386.6	1395.1	1386.6	1362.1	1318.8	1252.1	1155.2	1031.9	887.0
117.5°	1233.4	1279.1	1305.0	1312.0	1305.0	1279.1	1233.4	1165.4	1074.4	962.7	835.5
120°	1177.7	1221.9	1249.2	1258.7	1249.2	1221.9	1177.7	1111.9	1026.2	926.6	809.9
122.5°	1127.3	1170.7	1195.0	1203.0	1195.0	1170.7	1127.3	1068.3	990.9	896.5	789.6
125°	1064.9	1100.6	1124.1	1131.6	1124.1	1100.6	1064.9	1010.3	939.7	857.0	760.1
127.5°	1009.4	1042.8	1063.2	1069.2	1063.2	1042.8	1009.4	961.8	896.6	818.6	730.9
130°	975.5	1007.5	1026.2	1033.8	1026.2	1007.5	975.5	929.4	867.3	793.0	712.1
132.5°	940.8	972.9	990.1	996.9	990.1	972.9	940.8	895.5	837.2	768.9	694.0
135°	886.1	917.2	934.1	937.8	934.1	917.2	886.1	845.6	793.0	730.9	668.8
137.5°	832.7	859.4	874.3	880.0	874.3	859.4	832.7	795.8	749.9	700.6	648.7
140°	795.8	820.3	834.4	840.0	834.4	820.3	795.8	765.7	724.3	681.1	635.9
142.5°	764.2	786.5	799.0	800.1	799.0	786.5	764.2	735.7	701.0	663.7	625.4
145°	720.6	736.6	745.9	748.8	745.9	736.6	720.6	698.0	670.7	641.6	610.5
147.5°	684.9	697.6	704.0	705.7	704.0	697.6	684.9	666.2	646.2	623.5	599.0
150°	662.2	673.5	679.2	680.1	679.2	673.5	662.2	648.1	631.2	611.4	590.8
152.5°	644.1	653.9	658.1	658.3	658.1	653.9	644.1	633.1	618.4	601.6	582.5
155°	620.9	627.5	631.2	629.3	631.2	627.5	620.9	610.5	600.1	586.1	571.0
157.5°	597.5	602.9	604.6	604.6	604.6	602.9	597.5	590.2	582.1	570.2	557.6
160°	583.2	588.0	588.9	588.9	588.9	588.0	583.2	576.6	570.0	559.7	549.3
162.5°	570.4	573.6	574.6	573.8	574.6	573.6	570.4	563.8	558.7	549.9	541.1
165°	549.3	553.1	553.1	552.1	553.1	553.1	549.3	545.6	541.9	535.3	528.7
167.5°	531.5	533.6	533.4	532.3	533.4	533.6	531.5	529.8	526.4	521.9	516.8
170°	520.2	523.0	522.1	520.2	522.1	523.0	520.2	519.2	517.4	513.6	510.8
172.5°	511.1	512.5	511.5	510.4	511.5	512.5	511.1	510.2	509.1	506.1	504.0
175°	499.5	500.5	499.5	497.7	499.5	500.5	499.5	499.5	498.6	497.7	496.7
177.5°	492.2	492.2	491.4	489.9	491.4	492.2	492.2	492.2	492.2	491.4	491.4
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	974.1	978.1	984.0	987.4	993.0	996.6	998.6	1002.3	1004.3	1011.3	1018.6
5°	919.7	925.4	935.2	944.3	954.2	964.4	971.9	980.2	988.0	1001.4	1015.5
7.5°	857.3	865.2	880.4	895.0	912.2	926.6	939.3	953.8	966.7	985.8	1005.8
10°	810.6	824.3	844.4	858.1	880.6	895.0	915.1	930.9	949.0	974.3	996.8
12.5°	770.3	786.9	803.0	822.1	842.4	866.4	888.4	908.7	930.1	956.3	982.7
15°	697.3	721.2	746.2	765.5	793.1	818.3	844.0	871.5	897.6	928.9	963.4
17.5°	603.2	630.9	673.0	706.2	738.4	763.8	795.6	828.9	859.5	897.3	935.7
20°	560.7	581.1	609.6	654.3	702.9	730.0	762.4	799.0	834.2	875.3	916.5
22.5°	526.6	544.8	567.7	602.5	656.8	693.7	727.5	764.7	805.5	847.5	893.2
25°	478.0	490.7	514.6	542.7	580.0	640.9	677.9	715.2	759.6	804.6	856.7
27.5°	441.5	452.9	468.4	495.3	523.0	566.8	625.6	666.2	710.4	761.1	815.2
30°	413.6	427.0	444.2	463.2	493.5	527.6	586.4	633.6	677.2	729.3	787.0
32.5°	393.3	403.9	418.6	437.9	463.1	495.8	542.7	600.0	642.5	697.5	757.7
35°	360.1	372.4	384.4	402.7	423.1	453.0	488.5	549.8	592.0	646.2	706.8
37.5°	332.7	340.3	353.5	368.0	389.5	411.8	442.6	497.6	543.3	596.4	658.5
40°	311.9	321.3	331.2	347.4	365.0	386.4	416.7	457.6	510.0	562.1	622.6
42.5°	291.6	303.6	314.1	324.9	344.1	365.6	390.3	424.9	478.4	527.7	586.6
45°	267.1	274.9	285.8	297.7	313.6	332.0	353.7	384.0	435.4	478.0	533.3
47.5°	238.7	250.1	257.1	268.8	283.9	301.3	321.6	347.8	389.5	429.3	480.6
50°	219.3	230.9	241.1	251.7	265.0	281.9	298.8	324.1	357.6	399.5	447.3
52.5°	202.6	212.9	222.8	233.4	246.5	261.9	278.0	300.2	328.9	367.4	413.9
55°	179.8	186.2	196.4	207.0	218.6	233.4	248.8	267.5	292.2	324.5	362.2
57.5°	156.5	163.8	171.9	182.6	194.3	205.7	219.5	236.5	255.9	285.2	317.4
60°	143.3	148.9	155.6	166.5	177.4	187.6	201.0	215.1	233.4	258.7	286.2
62.5°	128.7	133.9	140.1	149.6	160.2	169.6	181.3	196.2	211.7	234.8	258.8
65°	104.2	112.0	117.9	126.4	135.2	145.1	154.2	166.2	179.8	198.1	219.6
67.5°	86.3	90.3	95.9	103.6	112.5	121.0	129.7	139.0	150.9	165.0	182.1
70°	78.5	79.9	81.0	88.3	96.8	105.3	113.3	122.2	132.3	143.9	158.7
72.5°	69.2	70.6	71.9	75.1	81.9	90.3	98.7	105.3	114.9	124.5	136.5
75°	55.0	57.0	58.1	59.9	62.3	68.0	75.7	82.0	87.7	95.0	104.5
77.5°	41.8	43.0	44.1	46.0	47.5	50.1	54.5	60.2	65.5	69.7	76.3
80°	33.1	33.5	34.9	35.5	37.7	39.4	41.6	46.1	51.4	53.2	57.7
82.5°	24.9	25.3	26.4	27.1	28.1	29.6	32.2	33.5	37.6	39.9	42.8
85°	13.8	13.4	14.4	14.4	15.2	15.8	16.6	18.3	19.3	22.1	22.9
87.5°	10.5	10.7	10.7	9.6	8.3	7.9	7.6	7.5	7.7	7.8	8.4
90°	31.0	32.0	31.0	25.4	18.9	14.1	11.3	9.4	7.5	3.8	0.9
92.5°	103.3	122.2	120.6	93.9	64.0	42.7	33.8	27.4	23.4	16.6	11.5
95°	322.6	368.7	326.4	217.3	135.4	92.2	69.7	54.6	46.1	36.7	32.9
97.5°	660.3	629.5	474.1	292.8	178.7	124.3	98.8	81.4	68.7	58.7	53.6
100°	878.6	743.1	511.7	308.6	193.8	143.9	117.6	98.8	83.7	75.2	72.4
102.5°	959.9	746.9	497.5	309.3	207.4	161.3	134.9	115.4	100.3	91.8	89.7
105°	947.3	697.0	469.4	314.1	230.5	186.2	159.9	139.2	125.1	118.6	114.8
107.5°	864.7	643.7	455.4	327.2	254.2	211.3	184.7	164.3	151.3	144.9	141.9
110°	812.8	618.0	452.5	337.7	269.9	228.6	201.3	181.5	169.3	163.7	159.9



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	776.7	601.4	453.2	349.0	285.0	245.2	217.1	198.1	186.6	180.2	176.4
115°	731.9	583.2	457.1	365.9	308.6	268.1	242.7	223.9	212.6	207.0	202.3
117.5°	703.6	574.4	463.9	384.0	330.2	292.8	266.4	248.4	238.4	232.7	228.9
120°	688.6	569.1	468.4	396.1	345.3	308.6	282.2	263.3	255.0	249.3	245.5
122.5°	675.8	566.1	473.7	406.5	359.5	325.1	298.0	279.2	269.9	264.3	261.4
125°	657.5	560.6	481.6	423.3	381.0	347.1	320.7	302.0	290.7	285.0	282.2
127.5°	640.6	557.4	489.7	438.9	401.0	368.0	340.9	322.8	310.4	302.6	298.8
130°	629.3	555.9	495.8	448.7	412.9	380.0	353.7	334.9	321.7	312.3	308.6
132.5°	620.3	555.2	501.7	458.5	423.5	392.1	365.7	346.2	332.2	322.1	317.5
135°	607.7	554.0	508.9	471.3	438.4	408.2	381.9	360.2	346.2	334.9	331.1
137.5°	598.8	553.8	515.3	481.1	450.4	420.7	396.2	374.8	359.7	348.5	343.9
140°	593.6	553.1	518.3	486.4	457.1	429.0	404.5	383.8	368.7	357.5	353.7
142.5°	588.3	553.1	520.6	490.9	462.4	435.0	412.0	392.1	377.0	366.5	363.4
145°	581.4	551.2	523.0	496.7	470.3	445.0	424.2	405.5	391.3	381.9	378.1
147.5°	574.2	547.9	523.8	499.9	476.7	452.9	434.4	418.8	405.8	396.8	394.0
150°	568.2	545.6	523.0	501.3	479.8	458.1	441.2	427.1	414.8	407.3	404.5
152.5°	562.9	541.9	521.5	502.1	482.8	463.4	448.0	434.6	423.9	416.3	415.0
155°	553.1	535.3	519.2	503.2	487.3	471.3	457.1	446.9	436.5	430.8	429.9
157.5°	543.9	528.5	514.9	503.2	490.5	476.9	465.1	456.8	447.8	443.3	442.3
160°	537.2	524.0	512.6	503.2	492.0	480.7	470.3	462.8	455.2	451.6	450.6
162.5°	531.1	520.2	510.4	502.5	492.8	483.0	474.9	468.1	462.0	458.3	458.8
165°	521.1	512.6	506.1	500.5	493.9	485.4	479.8	475.0	469.4	467.5	468.4
167.5°	511.3	506.1	501.7	499.2	493.7	487.5	483.9	480.5	476.9	475.2	476.4
170°	506.1	502.3	499.5	497.7	492.9	488.2	485.4	483.5	480.7	479.8	481.6
172.5°	500.9	497.9	496.5	495.4	492.2	489.0	486.9	485.8	483.0	483.5	484.7
175°	493.9	492.9	492.0	492.9	491.1	489.2	488.2	488.2	486.4	487.3	488.2
177.5°	489.9	489.2	489.9	491.4	489.9	489.2	489.2	489.2	487.7	488.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1018.9	1019.7	1025.4	1027.9	1033.0	1035.0	1037.2	1036.6	1036.6	1037.7	1045.7
5°	1021.1	1028.1	1038.7	1048.9	1058.8	1067.2	1072.8	1078.5	1080.5	1090.8	1099.9
7.5°	1017.5	1030.4	1047.8	1063.4	1082.0	1096.6	1108.7	1119.6	1127.1	1142.0	1157.2
10°	1012.7	1031.0	1050.7	1070.7	1096.5	1115.8	1135.5	1150.7	1155.6	1177.7	1190.4
12.5°	1003.1	1027.6	1052.6	1078.6	1103.7	1130.4	1152.1	1167.2	1184.6	1204.5	1227.9
15°	988.7	1016.9	1049.6	1083.1	1119.0	1151.3	1174.6	1201.0	1219.9	1241.8	1262.2
17.5°	968.1	1004.4	1045.9	1084.7	1126.1	1160.9	1193.0	1218.2	1231.6	1244.1	1247.2
20°	951.8	990.8	1039.7	1085.5	1127.0	1167.2	1198.8	1219.9	1223.5	1223.8	1205.1
22.5°	934.1	978.2	1029.4	1076.2	1125.9	1170.5	1195.1	1204.2	1190.2	1166.4	1130.3
25°	901.4	952.4	1011.9	1065.5	1119.6	1161.9	1170.4	1154.5	1105.6	1054.1	989.1
27.5°	866.1	923.4	987.2	1046.7	1104.5	1130.7	1112.4	1055.3	967.1	890.6	797.8
30°	840.2	904.6	967.2	1033.8	1087.2	1098.5	1056.7	972.5	869.8	754.3	661.8
32.5°	810.6	878.1	947.0	1015.8	1060.5	1049.5	980.3	876.8	756.3	642.8	555.3
35°	768.4	838.1	912.3	981.3	1009.8	962.3	858.8	724.1	600.9	494.9	434.7
37.5°	719.6	795.5	872.7	936.0	934.1	854.8	713.9	574.7	471.2	408.5	365.6
40°	684.9	761.7	845.1	898.6	875.7	772.6	619.8	488.5	412.8	362.9	331.6
42.5°	651.8	728.8	811.6	854.1	814.4	687.6	535.4	432.5	370.0	331.1	305.7
45°	595.2	676.5	753.3	776.8	705.7	566.0	432.9	358.4	316.8	287.9	270.3
47.5°	540.0	619.9	689.9	690.4	594.2	459.0	365.2	310.1	274.7	252.3	239.5
50°	506.1	582.2	640.9	631.8	522.7	408.3	326.6	279.1	249.6	232.3	219.0
52.5°	468.2	541.9	592.8	566.8	462.1	359.3	292.0	252.1	227.6	212.6	200.7
55°	412.8	478.3	514.3	474.9	377.0	298.8	246.8	215.4	197.1	184.5	174.3
57.5°	358.6	412.6	435.2	389.3	310.5	247.8	208.7	185.2	167.0	158.0	152.7
60°	324.5	370.6	386.4	335.8	269.9	216.8	184.8	163.0	149.6	143.6	138.4
62.5°	291.1	328.7	335.3	288.8	235.4	189.8	162.3	143.8	135.0	129.2	124.2
65°	241.5	268.5	265.4	228.1	186.2	150.6	130.5	119.3	112.6	104.5	95.8
67.5°	198.8	215.4	205.4	177.4	142.1	117.1	104.0	95.5	87.2	79.5	77.5
70°	171.7	181.3	170.7	145.1	116.5	98.2	87.7	77.5	72.5	70.8	67.6
72.5°	145.9	149.2	137.8	115.7	94.8	81.3	71.1	65.3	62.7	61.2	59.1
75°	109.4	107.0	97.2	79.9	65.8	56.6	53.5	51.4	49.7	48.3	47.1
77.5°	76.9	73.2	64.5	53.3	45.8	41.5	39.6	38.5	37.6	36.9	35.8
80°	57.7	55.2	46.5	38.0	34.9	32.7	31.7	30.3	30.3	29.6	28.5
82.5°	42.2	39.5	31.9	27.9	26.1	24.9	24.0	23.2	22.9	23.1	22.3
85°	22.1	17.9	15.8	15.2	14.0	13.4	13.8	13.0	13.0	13.0	12.6
87.5°	7.5	6.9	7.0	7.1	7.9	8.9	9.9	11.0	11.5	11.0	11.1
90°	3.8	7.5	9.4	11.3	14.1	18.9	25.4	31.0	32.0	31.0	30.1
92.5°	16.6	23.4	27.4	33.8	42.7	64.0	93.9	120.6	122.2	103.3	82.0
95°	36.7	46.1	54.6	69.7	92.2	135.4	217.3	326.4	368.7	322.6	246.5
97.5°	58.7	68.7	81.4	98.8	124.3	178.7	292.8	474.1	629.5	660.3	575.1
100°	75.2	83.7	98.8	117.6	143.9	193.8	308.6	511.7	743.1	878.6	858.8
102.5°	91.8	100.3	115.4	134.9	161.3	207.4	309.3	497.5	746.9	959.9	1044.7
105°	118.6	125.1	139.2	159.9	186.2	230.5	314.1	469.4	697.0	947.3	1142.9
107.5°	144.9	151.3	164.3	184.7	211.3	254.2	327.2	455.4	643.7	864.7	1072.2
110°	163.7	169.3	181.5	201.3	228.6	269.9	337.7	452.5	618.0	812.8	1011.3



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	180.2	186.6	198.1	217.1	245.2	285.0	349.0	453.2	601.4	776.7	955.5
115°	207.0	212.6	223.9	242.7	268.1	308.6	365.9	457.1	583.2	731.9	887.0
117.5°	232.7	238.4	248.4	266.4	292.8	330.2	384.0	463.9	574.4	703.6	835.5
120°	249.3	255.0	263.3	282.2	308.6	345.3	396.1	468.4	569.1	688.6	809.9
122.5°	264.3	269.9	279.2	298.0	325.1	359.5	406.5	473.7	566.1	675.8	789.6
125°	285.0	290.7	302.0	320.7	347.1	381.0	423.3	481.6	560.6	657.5	760.1
127.5°	302.6	310.4	322.8	340.9	368.0	401.0	438.9	489.7	557.4	640.6	730.9
130°	312.3	321.7	334.9	353.7	380.0	412.9	448.7	495.8	555.9	629.3	712.1
132.5°	322.1	332.2	346.2	365.7	392.1	423.5	458.5	501.7	555.2	620.3	694.0
135°	334.9	346.2	360.2	381.9	408.2	438.4	471.3	508.9	554.0	607.7	668.8
137.5°	348.5	359.7	374.8	396.2	420.7	450.4	481.1	515.3	553.8	598.8	648.7
140°	357.5	368.7	383.8	404.5	429.0	457.1	486.4	518.3	553.1	593.6	635.9
142.5°	366.5	377.0	392.1	412.0	435.0	462.4	490.9	520.6	553.1	588.3	625.4
145°	381.9	391.3	405.5	424.2	445.0	470.3	496.7	523.0	551.2	581.4	610.5
147.5°	396.8	405.8	418.8	434.4	452.9	476.7	499.9	523.8	547.9	574.2	599.0
150°	407.3	414.8	427.1	441.2	458.1	479.8	501.3	523.0	545.6	568.2	590.8
152.5°	416.3	423.9	434.6	448.0	463.4	482.8	502.1	521.5	541.9	562.9	582.5
155°	430.8	436.5	446.9	457.1	471.3	487.3	503.2	519.2	535.3	553.1	571.0
157.5°	443.3	447.8	456.8	465.1	476.9	490.5	503.2	514.9	528.5	543.9	557.6
160°	451.6	455.2	462.8	470.3	480.7	492.0	503.2	512.6	524.0	537.2	549.3
162.5°	458.3	462.0	468.1	474.9	483.0	492.8	502.5	510.4	520.2	531.1	541.1
165°	467.5	469.4	475.0	479.8	485.4	493.9	500.5	506.1	512.6	521.1	528.7
167.5°	475.2	476.9	480.5	483.9	487.5	493.7	499.2	501.7	506.1	511.3	516.8
170°	479.8	480.7	483.5	485.4	488.2	492.9	497.7	499.5	502.3	506.1	510.8
172.5°	483.5	483.0	485.8	486.9	489.0	492.2	495.4	496.5	497.9	500.9	504.0
175°	487.3	486.4	488.2	488.2	489.2	491.1	492.9	492.0	492.9	493.9	496.7
177.5°	488.4	487.7	489.2	489.2	489.2	489.9	491.4	489.9	489.2	489.9	491.4
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1048.5	1052.2	1053.9	1053.9	1055.8	1055.0	1054.1
5°	1108.7	1115.4	1116.8	1123.1	1127.8	1126.3	1127.0
7.5°	1168.7	1179.4	1190.1	1194.9	1195.7	1198.5	1199.6
10°	1205.5	1214.4	1230.9	1228.4	1240.8	1247.7	1236.1
12.5°	1241.0	1252.9	1264.4	1267.5	1274.5	1276.8	1272.1
15°	1273.1	1279.4	1280.2	1278.4	1280.5	1278.7	1272.1
17.5°	1243.1	1232.8	1212.0	1202.1	1194.3	1182.8	1178.2
20°	1193.5	1163.3	1128.1	1114.0	1097.5	1065.1	1072.8
22.5°	1086.6	1052.1	1016.9	975.7	956.1	925.4	923.6
25°	920.1	860.6	795.1	749.3	722.6	692.0	678.6
27.5°	715.4	640.5	586.8	559.7	534.9	510.7	509.6
30°	580.8	524.4	483.0	459.7	444.6	434.3	436.5
32.5°	489.6	450.9	422.9	403.7	392.5	384.7	384.7
35°	400.2	373.8	355.8	347.8	339.7	334.0	334.4
37.5°	342.5	326.6	316.6	307.7	302.7	299.9	298.3
40°	312.9	299.9	292.2	286.9	282.7	278.8	278.1
42.5°	289.5	278.8	271.0	266.8	263.0	260.1	259.5
45°	256.9	248.2	241.1	236.5	234.8	232.3	232.3
47.5°	228.6	219.9	214.4	211.5	208.5	206.9	206.8
50°	209.4	202.7	197.8	196.0	193.6	192.6	192.2
52.5°	192.3	187.3	183.7	182.6	181.4	180.1	180.3
55°	168.9	166.2	164.8	163.6	161.9	159.8	161.2
57.5°	149.3	146.9	143.1	139.8	138.2	136.7	137.2
60°	135.5	130.5	125.6	121.8	120.7	117.5	117.5
62.5°	118.1	111.1	105.1	102.9	101.9	100.4	100.1
65°	90.8	88.0	86.6	85.2	84.5	84.5	83.8
67.5°	75.2	74.1	72.6	72.2	71.5	71.4	71.1
70°	66.5	65.1	64.4	64.1	63.3	63.7	62.7
72.5°	58.1	56.9	56.8	55.9	55.5	55.5	54.8
75°	45.7	45.7	45.4	45.1	44.4	44.0	44.4
77.5°	35.2	35.3	34.6	34.6	34.5	34.6	34.2
80°	28.2	28.5	28.2	27.8	27.4	27.8	27.4
82.5°	22.2	21.8	21.7	21.6	21.6	21.3	21.3
85°	12.6	13.0	12.6	12.3	12.3	12.3	12.6
87.5°	10.5	10.8	11.0	11.0	11.0	11.0	10.7
90°	28.2	30.1	31.0	31.0	31.0	31.0	31.0
92.5°	70.4	62.5	56.6	55.9	52.9	53.6	52.1
95°	189.1	149.6	128.8	116.7	109.1	106.3	107.3
97.5°	470.5	368.7	300.9	255.9	232.7	219.0	211.1
100°	742.2	613.3	499.5	421.4	381.0	353.7	336.8
102.5°	1018.4	924.2	803.5	718.7	649.6	615.6	592.7
105°	1249.2	1261.5	1230.4	1172.1	1113.8	1073.3	1060.2
107.5°	1232.3	1330.1	1375.6	1383.0	1379.8	1371.7	1354.2
110°	1179.6	1300.0	1377.1	1417.6	1435.5	1444.0	1443.0



TEST NUMBER: P331665-830

CATALOG NUMBER: S122RDIP-S485D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1117.2	1245.9	1334.3	1390.5	1420.4	1436.4	1441.5
115°	1031.9	1155.2	1252.1	1318.8	1362.1	1386.6	1395.1
117.5°	962.7	1074.4	1165.4	1233.4	1279.1	1305.0	1312.0
120°	926.6	1026.2	1111.9	1177.7	1221.9	1249.2	1258.7
122.5°	896.5	990.9	1068.3	1127.3	1170.7	1195.0	1203.0
125°	857.0	939.7	1010.3	1064.9	1100.6	1124.1	1131.6
127.5°	818.6	896.6	961.8	1009.4	1042.8	1063.2	1069.2
130°	793.0	867.3	929.4	975.5	1007.5	1026.2	1033.8
132.5°	768.9	837.2	895.5	940.8	972.9	990.1	996.9
135°	730.9	793.0	845.6	886.1	917.2	934.1	937.8
137.5°	700.6	749.9	795.8	832.7	859.4	874.3	880.0
140°	681.1	724.3	765.7	795.8	820.3	834.4	840.0
142.5°	663.7	701.0	735.7	764.2	786.5	799.0	800.1
145°	641.6	670.7	698.0	720.6	736.6	745.9	748.8
147.5°	623.5	646.2	666.2	684.9	697.6	704.0	705.7
150°	611.4	631.2	648.1	662.2	673.5	679.2	680.1
152.5°	601.6	618.4	633.1	644.1	653.9	658.1	658.3
155°	586.1	600.1	610.5	620.9	627.5	631.2	629.3
157.5°	570.2	582.1	590.2	597.5	602.9	604.6	604.6
160°	559.7	570.0	576.6	583.2	588.0	588.9	588.9
162.5°	549.9	558.7	563.8	570.4	573.6	574.6	573.8
165°	535.3	541.9	545.6	549.3	553.1	553.1	552.1
167.5°	521.9	526.4	529.8	531.5	533.6	533.4	532.3
170°	513.6	517.4	519.2	520.2	523.0	522.1	520.2
172.5°	506.1	509.1	510.2	511.1	512.5	511.5	510.4
175°	497.7	498.6	499.5	499.5	500.5	499.5	497.7
177.5°	491.4	492.2	492.2	492.2	492.2	491.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2

(END OF REPORT)