

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331700-830

Luminaire Tested: **S122RDIP-S675D1080U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331700-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S675D1080U830-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6025.9 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	24	22	19
7	59	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	40	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22357	22357	22357	22357
5°	24969	22498	19947	22498
10°	27702	22338	17290	22338
15°	29065	22011	13623	22011
20°	25197	21526	11789	21526
25°	16527	20861	10525	20861
30°	11123	20057	9527	20057
35°	9008	19042	8592	19042
40°	8011	17939	7950	17939
45°	7250	16643	7099	16643
50°	6599	15360	6574	15360
55°	6204	13937	6120	13937
60°	5189	12633	5125	12633
65°	4374	11469	4963	11469
70°	4046	10244	4683	10244
75°	3780	8914	4323	8914
80°	3487	7336	3849	7336
85°	3205	5798	3390	5798



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.2
10°-20°	365.7	6.1
20°-30°	471.3	7.8
30°-40°	447.9	7.4
40°-50°	383.7	6.4
50°-60°	292.2	4.8
60°-70°	184.7	3.1
70°-80°	92.2	1.5
80°-90°	29.2	0.5
90°-100°	82.2	1.4
100°-110°	255.3	4.2
110°-120°	436.4	7.2
120°-130°	573.9	9.5
130°-140°	644.2	10.7
140°-150°	631.6	10.5
150°-160°	529.8	8.8
160°-170°	351.4	5.8
170°-180°	122.8	2.0
0°-30°	968.3	16.1
0°-40°	1416.2	23.5
0°-60°	2092.1	34.7
0°-90°	2398.2	39.8
90°-120°	774.0	12.8
90°-150°	2623.7	43.5
90°-180°	3628.0	60.2
0°-180°	6025.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1385	1385	1385	1385	1385	
5°	1541	1388	1231	1388	1541	152
15°	1739	1317	815	1317	1739	469
25°	928	1171	591	1171	928	440
35°	457	966	436	966	457	292
45°	318	729	311	729	318	246
55°	220	495	217	495	220	193
65°	114	300	130	300	114	117
75°	61	143	69	143	61	64
85°	17	31	18	31	17	20
90°	37	1	37	1	37	17
95°	68	57	68	57	68	76
105°	243	235	243	235	243	256
115°	438	438	438	438	438	432
125°	639	637	639	637	639	570
135°	834	824	834	824	834	642
145°	1012	1001	1012	1001	1012	632
155°	1153	1144	1153	1144	1153	531
165°	1246	1245	1246	1245	1246	351
175°	1291	1295	1291	1295	1291	123
180°	1297	1297	1297	1297	1297	



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1440.9	1442.0	1443.2	1440.5	1440.5	1438.1	1433.1	1429.4	1418.5	1417.0	1417.0
5°	1540.6	1539.5	1541.5	1535.3	1526.6	1524.7	1515.5	1503.5	1491.0	1477.1	1474.1
7.5°	1639.6	1638.2	1634.4	1633.3	1626.6	1612.1	1597.4	1581.8	1560.9	1540.7	1530.5
10°	1689.7	1705.6	1695.9	1679.1	1682.5	1659.9	1647.8	1627.2	1609.9	1579.5	1572.8
12.5°	1739.0	1745.2	1742.2	1732.6	1728.2	1712.6	1696.4	1678.4	1646.4	1619.2	1595.5
15°	1738.8	1747.9	1750.3	1747.5	1749.8	1748.9	1740.2	1725.3	1697.4	1667.5	1641.6
17.5°	1610.4	1616.7	1632.6	1643.2	1656.7	1685.2	1699.2	1704.7	1700.5	1683.6	1665.3
20°	1466.5	1455.9	1500.2	1522.8	1542.0	1590.1	1631.4	1647.4	1672.8	1672.4	1667.5
22.5°	1262.4	1265.0	1306.9	1333.8	1390.0	1438.0	1485.3	1545.0	1594.3	1626.9	1646.1
25°	927.7	945.9	987.8	1024.4	1086.8	1176.4	1257.6	1352.0	1441.0	1511.2	1578.1
27.5°	696.6	698.0	731.2	765.0	802.1	875.4	977.8	1090.4	1217.3	1322.0	1442.5
30°	596.6	593.7	607.7	628.4	660.1	716.9	793.8	904.6	1031.0	1188.8	1329.4
32.5°	525.8	525.9	536.5	551.8	578.2	616.4	669.1	759.0	878.6	1033.8	1198.4
35°	457.0	456.6	464.3	475.3	486.4	511.0	547.1	594.2	676.5	821.2	989.7
37.5°	407.8	409.9	413.7	420.6	432.8	446.5	468.2	499.8	558.4	644.0	785.6
40°	380.1	381.1	386.3	392.1	399.4	409.9	427.7	453.2	496.1	564.4	667.8
42.5°	354.7	355.6	359.4	364.8	370.4	381.1	395.8	417.8	452.5	505.9	591.2
45°	317.5	317.5	320.9	323.3	329.6	339.2	351.2	369.5	393.6	433.0	489.7
47.5°	282.7	282.8	285.0	289.2	293.1	300.6	312.5	327.3	344.9	375.4	423.9
50°	262.7	263.2	264.6	268.0	270.4	277.1	286.3	299.3	317.5	341.1	381.5
52.5°	246.6	246.2	248.1	249.5	251.2	256.0	262.8	274.3	290.6	311.1	344.6
55°	220.4	218.4	221.3	223.8	225.2	227.1	230.9	238.2	252.1	269.5	294.5
57.5°	187.7	186.9	188.9	191.1	195.7	200.9	204.1	208.7	215.9	228.4	253.2
60°	160.7	160.7	165.0	166.5	171.7	178.5	185.2	189.1	196.3	204.4	222.7
62.5°	136.9	137.2	139.2	140.7	143.6	151.9	161.4	169.8	176.6	184.5	196.6
65°	114.5	115.5	115.5	116.4	118.4	120.3	124.1	130.8	142.9	153.9	163.1
67.5°	97.2	97.5	97.7	98.7	99.2	101.3	102.8	105.8	108.7	119.1	130.4
70°	85.7	87.1	86.6	87.6	88.0	89.0	91.0	92.4	96.7	99.2	105.8
72.5°	74.8	75.9	75.8	76.4	77.7	77.9	79.4	80.9	83.6	85.7	89.3
75°	60.6	60.1	60.6	61.5	62.0	62.6	62.6	64.5	65.9	67.9	70.2
77.5°	46.8	47.2	47.1	47.2	47.3	48.2	48.1	49.0	50.4	51.4	52.5
80°	37.5	38.0	37.5	38.0	38.5	38.9	38.5	38.9	40.4	41.4	41.4
82.5°	29.0	29.1	29.4	29.5	29.6	29.7	30.4	30.5	31.6	31.4	31.8
85°	17.3	16.9	16.9	16.9	17.3	17.8	17.3	17.3	17.8	17.8	17.8
87.5°	13.6	13.9	13.9	13.9	13.8	13.9	13.9	14.4	14.1	14.6	13.1
90°	37.2	36.9	36.8	36.5	36.3	36.4	36.9	37.3	37.8	38.4	33.0
92.5°	35.4	35.4	35.3	35.3	35.3	35.3	35.1	35.0	34.9	34.8	33.6
95°	67.9	68.3	68.9	69.4	69.8	70.0	70.0	70.0	70.0	70.0	69.6
97.5°	117.6	117.6	117.7	117.7	117.8	117.8	117.8	117.8	117.8	117.8	116.9
100°	150.0	150.2	150.5	150.7	151.0	151.1	151.1	151.1	151.1	151.1	150.3
102.5°	186.8	187.0	187.3	187.5	187.8	187.8	187.6	187.4	187.2	187.0	186.1
105°	243.1	243.1	243.1	243.1	243.1	242.8	242.3	241.9	241.4	240.8	240.3
107.5°	296.1	297.2	298.3	299.4	300.5	301.0	300.8	300.6	300.4	300.2	300.2
110°	337.2	337.9	338.7	339.4	340.2	340.5	340.5	340.5	340.5	340.5	340.5



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	376.6	377.2	377.7	378.2	378.8	379.4	379.9	380.5	381.1	381.6	381.8
115°	437.9	438.7	439.4	440.2	440.8	441.3	441.6	441.9	442.1	442.3	442.8
117.5°	496.4	497.1	497.9	498.6	499.4	500.0	500.6	501.1	501.7	502.3	503.7
120°	537.5	538.3	539.0	539.8	540.5	540.8	540.8	540.8	540.8	540.8	542.8
122.5°	577.9	578.4	578.9	579.5	580.0	580.5	581.2	581.7	582.3	582.9	584.3
125°	639.4	639.6	639.9	640.1	640.4	640.8	641.6	642.3	643.0	643.8	644.5
127.5°	695.4	696.3	697.0	697.8	698.5	699.4	700.2	701.2	702.0	702.9	703.8
130°	735.7	736.7	737.6	738.7	739.6	740.4	740.8	741.3	741.8	742.3	742.8
132.5°	774.3	775.1	775.8	776.7	777.4	778.4	779.4	780.4	781.6	782.6	782.5
135°	834.2	835.0	835.8	836.4	837.2	837.6	837.9	838.2	838.4	838.7	838.2
137.5°	888.5	889.6	890.5	891.5	892.5	893.1	893.2	893.4	893.6	893.8	893.2
140°	926.2	927.2	928.2	929.2	930.1	930.6	930.6	930.6	930.6	930.6	929.4
142.5°	960.4	961.4	962.3	963.3	964.3	964.7	964.5	964.3	964.1	963.9	963.1
145°	1011.6	1012.6	1013.6	1014.6	1015.5	1015.9	1015.7	1015.4	1015.1	1014.9	1013.4
147.5°	1057.4	1058.3	1059.2	1060.2	1061.1	1061.3	1060.7	1060.3	1059.7	1059.1	1058.2
150°	1087.2	1087.9	1088.6	1089.4	1090.1	1090.1	1089.4	1088.6	1087.9	1087.2	1086.2
152.5°	1115.2	1116.2	1117.1	1117.9	1118.9	1118.9	1117.9	1117.1	1116.2	1115.2	1114.1
155°	1152.8	1153.6	1154.3	1155.1	1155.7	1155.6	1154.3	1153.1	1151.9	1150.7	1150.0
157.5°	1185.2	1186.5	1187.6	1188.7	1190.0	1189.7	1188.1	1186.4	1184.8	1183.1	1182.6
160°	1205.4	1206.4	1207.4	1208.3	1209.3	1209.1	1207.6	1206.2	1204.7	1203.2	1203.0
162.5°	1222.9	1224.1	1225.3	1226.4	1227.6	1227.4	1225.7	1224.1	1222.4	1220.8	1220.5
165°	1245.9	1247.2	1248.4	1249.6	1250.8	1250.6	1248.9	1247.2	1245.5	1243.8	1243.8
167.5°	1264.8	1266.0	1267.2	1268.6	1269.8	1269.6	1267.9	1266.2	1264.5	1262.8	1262.8
170°	1274.4	1275.8	1277.3	1278.7	1280.3	1280.1	1278.4	1276.7	1275.0	1273.3	1273.6
172.5°	1282.2	1283.7	1285.2	1286.7	1288.1	1288.0	1286.3	1284.6	1282.9	1281.2	1281.4
175°	1290.8	1292.3	1293.7	1295.2	1296.7	1296.6	1294.9	1293.2	1291.5	1289.7	1290.2
177.5°	1294.8	1295.9	1297.1	1298.3	1299.4	1299.4	1298.3	1297.1	1295.9	1294.8	1295.1
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1417.8	1414.7	1412.0	1405.0	1401.7	1393.9	1392.8	1392.4	1382.3	1372.7	1370.1
5°	1466.5	1458.8	1447.2	1433.7	1419.8	1405.3	1395.7	1388.1	1368.8	1350.5	1339.9
7.5°	1515.5	1499.0	1479.0	1453.6	1432.3	1408.4	1390.7	1374.9	1347.6	1321.4	1303.7
10°	1552.1	1525.1	1498.7	1463.6	1436.2	1409.2	1384.2	1362.5	1331.7	1297.1	1272.5
12.5°	1574.8	1545.2	1508.7	1474.3	1438.9	1404.6	1371.1	1343.3	1307.1	1271.3	1242.2
15°	1605.5	1573.8	1529.5	1480.5	1434.7	1390.0	1351.5	1316.8	1269.7	1226.9	1191.3
17.5°	1630.6	1587.0	1539.4	1482.6	1429.7	1372.8	1323.2	1279.0	1226.5	1174.9	1132.9
20°	1638.7	1595.4	1540.6	1483.8	1421.3	1354.3	1301.0	1252.8	1196.6	1140.3	1092.1
22.5°	1633.7	1600.1	1539.0	1471.1	1407.0	1337.0	1276.7	1220.9	1158.5	1101.0	1045.2
25°	1599.8	1588.2	1530.5	1456.3	1383.3	1301.9	1232.2	1171.0	1099.9	1038.3	977.6
27.5°	1520.5	1545.5	1509.7	1430.8	1349.4	1262.3	1183.8	1114.3	1040.4	971.1	910.7
30°	1444.4	1501.6	1486.2	1413.1	1322.1	1236.5	1148.5	1075.8	996.9	925.7	866.0
32.5°	1340.0	1434.6	1449.6	1388.5	1294.4	1200.3	1108.1	1035.8	953.4	878.4	820.2
35°	1173.9	1315.4	1380.4	1341.3	1247.1	1145.6	1050.3	966.1	883.4	809.3	751.5
37.5°	975.8	1168.5	1276.7	1279.5	1192.9	1087.3	983.6	900.0	815.3	742.5	680.1
40°	847.3	1056.0	1197.0	1228.3	1155.2	1041.1	936.2	851.1	768.4	697.1	625.5
42.5°	731.8	939.8	1113.1	1167.5	1109.4	996.1	890.9	801.8	721.4	654.0	580.8
45°	591.8	773.6	964.7	1061.9	1029.6	924.7	813.6	728.9	653.4	595.1	524.9
47.5°	499.2	627.4	812.2	943.7	943.1	847.3	738.0	657.0	586.9	532.3	475.4
50°	446.5	558.1	714.4	863.7	876.1	795.8	691.8	611.5	546.1	488.8	443.1
52.5°	399.2	491.2	631.7	774.7	810.3	740.7	639.9	565.7	502.2	449.6	410.4
55°	337.2	408.5	515.3	649.0	702.9	653.8	564.4	495.1	443.6	399.4	365.6
57.5°	285.3	338.7	424.4	532.2	594.8	564.0	490.1	433.9	389.8	349.8	323.2
60°	252.6	296.3	369.0	459.0	528.3	506.6	443.6	391.2	353.6	319.0	294.0
62.5°	221.8	259.4	321.7	394.7	458.3	449.3	397.8	353.8	320.9	289.4	268.2
65°	178.5	205.9	254.5	311.8	362.8	367.1	330.1	300.2	270.9	245.8	227.1
67.5°	142.1	160.0	194.3	242.5	280.7	294.4	271.7	248.9	225.6	206.3	190.0
70°	119.8	134.2	159.3	198.2	233.4	247.8	234.8	217.0	196.8	180.9	166.9
72.5°	97.1	111.1	129.6	158.2	188.3	203.9	199.3	186.6	170.2	157.0	143.8
75°	73.1	77.5	90.0	109.2	132.8	146.3	149.7	142.9	129.9	119.8	112.1
77.5°	54.1	56.6	62.7	72.8	88.1	100.2	105.1	104.3	95.4	89.4	82.3
80°	43.3	44.8	47.6	51.9	63.5	75.5	78.9	78.9	72.7	70.2	63.1
82.5°	32.9	33.9	35.7	38.1	43.5	54.0	57.8	58.5	54.6	51.4	45.7
85°	18.8	18.3	19.2	20.6	21.7	24.5	30.3	31.3	30.3	26.5	25.0
87.5°	12.1	11.4	10.3	9.1	8.9	8.7	10.1	11.4	10.5	9.9	9.7
90°	27.6	22.2	16.9	12.8	9.9	7.0	4.1	1.1	4.1	7.0	9.9
92.5°	32.3	31.0	29.8	28.1	25.9	23.8	21.6	19.5	21.6	23.8	25.9
95°	69.1	68.6	68.1	66.6	64.2	61.8	59.4	56.9	59.4	61.8	64.2
97.5°	115.9	115.0	114.1	112.5	110.5	108.3	106.1	104.1	106.1	108.3	110.5
100°	149.6	148.9	148.2	146.8	144.9	143.0	141.0	139.0	141.0	143.0	144.9
102.5°	185.1	184.3	183.3	182.1	180.5	179.0	177.4	175.9	177.4	179.0	180.5
105°	239.9	239.4	238.9	238.3	237.6	236.9	236.1	235.4	236.1	236.9	237.6
107.5°	300.2	300.2	300.2	299.6	298.6	297.6	296.4	295.4	296.4	297.6	298.6
110°	340.5	340.5	340.5	339.8	338.3	336.9	335.4	333.9	335.4	336.9	338.3



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	382.0	382.2	382.5	381.8	380.3	378.9	377.4	376.0	377.4	378.9	380.3
115°	443.3	443.7	444.2	443.7	442.3	440.8	439.4	437.9	439.4	440.8	442.3
117.5°	505.0	506.4	507.7	507.5	505.5	503.6	501.6	499.6	501.6	503.6	505.5
120°	544.8	546.7	548.7	548.7	546.7	544.8	542.8	540.8	542.8	544.8	546.7
122.5°	585.6	587.0	588.3	587.9	585.5	583.2	580.9	578.5	580.9	583.2	585.5
125°	645.3	645.9	646.7	645.9	643.8	641.6	639.4	637.2	639.4	641.6	643.8
127.5°	704.6	705.5	706.4	705.4	702.7	699.9	697.1	694.4	697.1	699.9	702.7
130°	743.3	743.8	744.2	742.9	739.7	736.6	733.4	730.3	733.4	736.6	739.7
132.5°	782.4	782.3	782.2	780.9	778.3	775.7	773.2	770.5	773.2	775.7	778.3
135°	837.6	837.2	836.7	835.1	832.5	829.8	827.1	824.4	827.1	829.8	832.5
137.5°	892.6	891.9	891.3	889.9	887.7	885.5	883.4	881.1	883.4	885.5	887.7
140°	928.2	927.0	925.8	924.1	921.9	919.6	917.5	915.3	917.5	919.6	921.9
142.5°	962.2	961.4	960.5	959.0	956.9	954.7	952.5	950.4	952.5	954.7	956.9
145°	1012.0	1010.5	1009.1	1007.5	1005.8	1004.1	1002.4	1000.7	1002.4	1004.1	1005.8
147.5°	1057.2	1056.2	1055.3	1053.8	1051.7	1049.6	1047.6	1045.6	1047.6	1049.6	1051.7
150°	1085.2	1084.3	1083.3	1082.0	1080.6	1079.1	1077.7	1076.2	1077.7	1079.1	1080.6
152.5°	1112.9	1111.7	1110.5	1109.2	1107.8	1106.3	1104.8	1103.3	1104.8	1106.3	1107.8
155°	1149.2	1148.5	1147.7	1147.1	1146.3	1145.6	1144.8	1144.2	1144.8	1145.6	1146.3
157.5°	1182.2	1181.8	1181.3	1180.9	1180.3	1179.9	1179.4	1178.9	1179.4	1179.9	1180.3
160°	1202.8	1202.5	1202.2	1201.9	1201.4	1200.9	1200.4	1200.0	1200.4	1200.9	1201.4
162.5°	1220.2	1220.0	1219.7	1219.7	1219.5	1219.4	1219.3	1219.2	1219.3	1219.4	1219.5
165°	1243.8	1243.8	1243.8	1243.9	1244.1	1244.3	1244.6	1244.8	1244.6	1244.3	1244.1
167.5°	1262.9	1262.9	1263.0	1263.4	1264.1	1264.8	1265.6	1266.3	1265.6	1264.8	1264.1
170°	1273.8	1274.0	1274.3	1274.8	1275.4	1276.2	1277.0	1277.7	1277.0	1276.2	1275.4
172.5°	1281.7	1282.0	1282.1	1282.6	1283.4	1284.1	1284.9	1285.5	1284.9	1284.1	1283.4
175°	1290.7	1291.2	1291.7	1292.3	1293.0	1293.7	1294.5	1295.2	1294.5	1293.7	1293.0
177.5°	1295.5	1295.9	1296.3	1296.8	1297.4	1298.0	1298.5	1299.1	1298.5	1298.0	1297.4
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1365.1	1362.4	1357.4	1349.6	1345.0	1336.9	1331.5	1334.6	1335.4	1334.6	1333.9
5°	1328.4	1318.2	1304.3	1290.8	1278.4	1264.9	1257.2	1253.8	1247.1	1243.2	1241.3
7.5°	1284.0	1266.6	1246.9	1223.4	1203.4	1182.6	1172.0	1166.6	1152.8	1145.4	1138.8
10°	1250.9	1223.5	1203.8	1173.0	1154.2	1126.8	1108.1	1108.5	1089.8	1079.1	1071.5
12.5°	1214.4	1184.2	1151.4	1123.7	1097.6	1075.6	1053.0	1043.9	1023.9	1013.7	993.0
15°	1153.8	1118.6	1084.0	1046.4	1020.0	985.8	953.1	913.1	880.9	853.0	845.4
17.5°	1087.5	1044.1	1009.3	965.3	919.9	862.4	824.5	801.3	781.9	767.2	756.2
20°	1042.1	997.9	960.8	894.4	833.3	794.4	766.5	748.7	728.4	712.6	703.9
22.5°	994.4	948.2	897.7	823.6	776.0	744.7	719.8	699.4	685.7	673.3	665.4
25°	926.6	876.1	792.9	741.9	703.4	670.7	653.4	640.8	626.4	609.5	601.9
27.5°	855.1	774.7	714.9	677.0	640.3	619.0	603.4	584.8	571.8	564.3	556.3
30°	801.5	721.2	674.6	633.2	607.2	583.6	565.3	554.8	542.2	529.2	524.0
32.5°	741.9	677.7	633.0	598.5	572.1	552.0	537.6	520.5	511.4	503.4	492.4
35°	667.8	619.3	578.3	550.4	525.4	509.1	492.2	482.1	465.7	459.0	454.7
37.5°	605.0	562.9	532.4	502.9	483.1	465.1	454.8	438.7	431.6	422.3	413.1
40°	569.7	528.3	498.9	474.9	452.7	439.2	426.3	413.3	402.7	398.4	387.3
42.5°	533.5	499.8	470.4	444.0	429.2	415.0	398.6	389.1	378.1	371.1	364.2
45°	483.5	453.7	428.7	407.0	390.7	375.8	365.1	349.3	343.1	329.0	323.3
47.5°	439.7	411.9	388.0	367.5	351.5	341.8	326.3	313.9	303.9	295.3	287.9
50°	408.5	385.4	362.3	344.0	329.6	315.7	299.7	293.5	278.1	273.7	269.5
52.5°	380.0	358.1	336.9	319.0	304.5	291.0	277.0	268.8	258.4	254.1	251.0
55°	340.2	319.0	298.8	282.9	268.4	254.5	245.8	235.7	230.9	227.5	223.8
57.5°	300.1	281.1	265.6	249.5	235.0	223.9	213.9	207.8	202.8	198.4	193.8
60°	274.8	256.5	242.5	227.5	212.6	203.5	195.9	188.6	182.9	176.1	174.2
62.5°	247.8	231.8	219.0	204.4	191.5	183.1	175.8	169.0	162.0	152.2	149.5
65°	210.8	198.2	184.7	172.8	161.2	153.0	142.4	134.7	131.9	130.8	130.4
67.5°	177.3	165.4	153.8	141.6	131.0	123.5	118.1	116.9	114.9	114.3	113.0
70°	155.0	143.8	132.3	120.7	110.7	109.2	107.3	105.4	102.9	102.0	101.0
72.5°	134.9	123.5	111.9	102.6	98.3	96.5	94.6	92.7	91.0	90.1	89.4
75°	103.4	92.8	85.2	81.8	79.4	77.9	75.0	73.6	72.7	71.2	70.7
77.5°	74.5	68.5	64.9	62.9	60.3	58.8	57.1	55.7	54.7	54.4	53.6
80°	56.7	53.9	51.5	48.6	47.6	45.7	45.2	43.8	44.3	42.8	42.8
82.5°	44.1	40.4	38.4	37.0	36.1	34.6	34.0	33.4	33.5	32.4	32.4
85°	22.6	21.7	20.6	19.7	19.7	18.3	18.8	18.3	18.3	17.3	16.9
87.5°	9.9	10.3	10.7	11.7	12.7	13.5	13.4	12.8	12.7	12.6	12.3
90°	12.8	16.9	22.2	27.6	33.0	38.4	37.8	37.3	36.9	36.4	36.3
92.5°	28.1	29.8	31.0	32.3	33.6	34.8	34.9	35.0	35.1	35.3	35.3
95°	66.6	68.1	68.6	69.1	69.6	70.0	70.0	70.0	70.0	70.0	69.8
97.5°	112.5	114.1	115.0	115.9	116.9	117.8	117.8	117.8	117.8	117.8	117.8
100°	146.8	148.2	148.9	149.6	150.3	151.1	151.1	151.1	151.1	151.1	151.0
102.5°	182.1	183.3	184.3	185.1	186.1	187.0	187.2	187.4	187.6	187.8	187.8
105°	238.3	238.9	239.4	239.9	240.3	240.8	241.4	241.9	242.3	242.8	243.1
107.5°	299.6	300.2	300.2	300.2	300.2	300.2	300.4	300.6	300.8	301.0	300.5
110°	339.8	340.5	340.5	340.5	340.5	340.5	340.5	340.5	340.5	340.5	340.2



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	381.8	382.5	382.2	382.0	381.8	381.6	381.1	380.5	379.9	379.4	378.8
115°	443.7	444.2	443.7	443.3	442.8	442.3	442.1	441.9	441.6	441.3	440.8
117.5°	507.5	507.7	506.4	505.0	503.7	502.3	501.7	501.1	500.6	500.0	499.4
120°	548.7	548.7	546.7	544.8	542.8	540.8	540.8	540.8	540.8	540.8	540.5
122.5°	587.9	588.3	587.0	585.6	584.3	582.9	582.3	581.7	581.2	580.5	580.0
125°	645.9	646.7	645.9	645.3	644.5	643.8	643.0	642.3	641.6	640.8	640.4
127.5°	705.4	706.4	705.5	704.6	703.8	702.9	702.0	701.2	700.2	699.4	698.5
130°	742.9	744.2	743.8	743.3	742.8	742.3	741.8	741.3	740.8	740.4	739.6
132.5°	780.9	782.2	782.3	782.4	782.5	782.6	781.6	780.4	779.4	778.4	777.4
135°	835.1	836.7	837.2	837.6	838.2	838.7	838.4	838.2	837.9	837.6	837.2
137.5°	889.9	891.3	891.9	892.6	893.2	893.8	893.6	893.4	893.2	893.1	892.5
140°	924.1	925.8	927.0	928.2	929.4	930.6	930.6	930.6	930.6	930.6	930.1
142.5°	959.0	960.5	961.4	962.2	963.1	963.9	964.1	964.3	964.5	964.7	964.3
145°	1007.5	1009.1	1010.5	1012.0	1013.4	1014.9	1015.1	1015.4	1015.7	1015.9	1015.5
147.5°	1053.8	1055.3	1056.2	1057.2	1058.2	1059.1	1059.7	1060.3	1060.7	1061.3	1061.1
150°	1082.0	1083.3	1084.3	1085.2	1086.2	1087.2	1087.9	1088.6	1089.4	1090.1	1090.1
152.5°	1109.2	1110.5	1111.7	1112.9	1114.1	1115.2	1116.2	1117.1	1117.9	1118.9	1118.9
155°	1147.1	1147.7	1148.5	1149.2	1150.0	1150.7	1151.9	1153.1	1154.3	1155.6	1155.7
157.5°	1180.9	1181.3	1181.8	1182.2	1182.6	1183.1	1184.8	1186.4	1188.1	1189.7	1190.0
160°	1201.9	1202.2	1202.5	1202.8	1203.0	1203.2	1204.7	1206.2	1207.6	1209.1	1209.3
162.5°	1219.7	1219.7	1220.0	1220.2	1220.5	1220.8	1222.4	1224.1	1225.7	1227.4	1227.6
165°	1243.9	1243.8	1243.8	1243.8	1243.8	1243.8	1245.5	1247.2	1248.9	1250.6	1250.8
167.5°	1263.4	1263.0	1262.9	1262.9	1262.8	1262.8	1264.5	1266.2	1267.9	1269.6	1269.8
170°	1274.8	1274.3	1274.0	1273.8	1273.6	1273.3	1275.0	1276.7	1278.4	1280.1	1280.3
172.5°	1282.6	1282.1	1282.0	1281.7	1281.4	1281.2	1282.9	1284.6	1286.3	1288.0	1288.1
175°	1292.3	1291.7	1291.2	1290.7	1290.2	1289.7	1291.5	1293.2	1294.9	1296.6	1296.7
177.5°	1296.8	1296.3	1295.9	1295.5	1295.1	1294.8	1295.9	1297.1	1298.3	1299.4	1299.4
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1329.6	1330.4	1329.3	1330.0	1329.3	1330.4	1329.6	1333.9	1334.6	1335.4	1334.6
5°	1238.9	1233.1	1232.2	1230.7	1232.2	1233.1	1238.9	1241.3	1243.2	1247.1	1253.8
7.5°	1130.6	1129.6	1127.3	1123.9	1127.3	1129.6	1130.6	1138.8	1145.4	1152.8	1166.6
10°	1060.8	1058.5	1058.0	1054.6	1058.0	1058.5	1060.8	1071.5	1079.1	1089.8	1108.5
12.5°	979.3	963.7	962.1	953.8	962.1	963.7	979.3	993.0	1013.7	1023.9	1043.9
15°	833.8	830.9	821.2	815.0	821.2	830.9	833.8	845.4	853.0	880.9	913.1
17.5°	750.6	741.2	738.2	736.9	738.2	741.2	750.6	756.2	767.2	781.9	801.3
20°	697.1	688.5	687.0	686.1	687.0	688.5	697.1	703.9	712.6	728.4	748.7
22.5°	660.2	651.1	647.4	644.5	647.4	651.1	660.2	665.4	673.3	685.7	699.4
25°	597.1	593.7	591.8	590.8	591.8	593.7	597.1	601.9	609.5	626.4	640.8
27.5°	547.7	540.3	538.9	536.4	538.9	540.3	547.7	556.3	564.3	571.8	584.8
30°	519.6	517.2	513.9	511.0	513.9	517.2	519.6	524.0	529.2	542.2	554.8
32.5°	486.5	484.5	481.5	480.1	481.5	484.5	486.5	492.4	503.4	511.4	520.5
35°	449.9	443.1	440.3	435.9	440.3	443.1	449.9	454.7	459.0	465.7	482.1
37.5°	411.0	407.6	403.5	404.9	403.5	407.6	411.0	413.1	422.3	431.6	438.7
40°	381.1	378.6	377.7	377.2	377.7	378.6	381.1	387.3	398.4	402.7	413.3
42.5°	357.2	350.5	348.1	348.0	348.1	350.5	357.2	364.2	371.1	378.1	389.1
45°	320.9	314.6	310.3	310.9	310.3	314.6	320.9	323.3	329.0	343.1	349.3
47.5°	283.8	283.6	280.9	281.7	280.9	283.6	283.8	287.9	295.3	303.9	313.9
50°	266.1	263.2	261.3	261.7	261.3	263.2	266.1	269.5	273.7	278.1	293.5
52.5°	249.1	246.7	245.1	247.1	245.1	246.7	249.1	251.0	254.1	258.4	268.8
55°	221.3	218.4	217.9	217.4	217.9	218.4	221.3	223.8	227.5	230.9	235.7
57.5°	190.2	188.3	185.4	184.2	185.4	188.3	190.2	193.8	198.4	202.8	207.8
60°	167.9	164.1	159.3	158.7	159.3	164.1	167.9	174.2	176.1	182.9	188.6
62.5°	147.5	146.8	145.8	145.7	145.8	146.8	147.5	149.5	152.2	162.0	169.0
65°	129.4	128.9	129.4	129.9	129.4	128.9	129.4	130.4	130.8	131.9	134.7
67.5°	112.8	111.9	111.0	111.4	111.0	111.9	112.8	113.0	114.3	114.9	116.9
70°	100.1	99.6	99.2	99.2	99.2	99.6	100.1	101.0	102.0	102.9	105.4
72.5°	87.8	87.7	87.2	86.8	87.2	87.7	87.8	89.4	90.1	91.0	92.7
75°	70.2	69.3	69.3	69.3	69.3	69.3	70.2	70.7	71.2	72.7	73.6
77.5°	53.5	53.1	52.5	52.1	52.5	53.1	53.5	53.6	54.4	54.7	55.7
80°	42.3	41.8	41.4	41.4	41.4	41.8	42.3	42.8	42.8	44.3	43.8
82.5°	32.3	31.9	31.8	31.4	31.8	31.9	32.3	32.4	32.4	33.5	33.4
85°	17.3	17.8	17.3	18.3	17.3	17.8	17.3	16.9	17.3	18.3	18.3
87.5°	12.3	12.0	12.4	12.1	12.4	12.0	12.3	12.3	12.6	12.7	12.8
90°	36.5	36.8	36.9	37.2	36.9	36.8	36.5	36.3	36.4	36.9	37.3
92.5°	35.3	35.3	35.4	35.4	35.4	35.3	35.3	35.3	35.3	35.1	35.0
95°	69.4	68.9	68.3	67.9	68.3	68.9	69.4	69.8	70.0	70.0	70.0
97.5°	117.7	117.7	117.6	117.6	117.6	117.7	117.7	117.8	117.8	117.8	117.8
100°	150.7	150.5	150.2	150.0	150.2	150.5	150.7	151.0	151.1	151.1	151.1
102.5°	187.5	187.3	187.0	186.8	187.0	187.3	187.5	187.8	187.8	187.6	187.4
105°	243.1	243.1	243.1	243.1	243.1	243.1	243.1	243.1	242.8	242.3	241.9
107.5°	299.4	298.3	297.2	296.1	297.2	298.3	299.4	300.5	301.0	300.8	300.6
110°	339.4	338.7	337.9	337.2	337.9	338.7	339.4	340.2	340.5	340.5	340.5



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	378.2	377.7	377.2	376.6	377.2	377.7	378.2	378.8	379.4	379.9	380.5
115°	440.2	439.4	438.7	437.9	438.7	439.4	440.2	440.8	441.3	441.6	441.9
117.5°	498.6	497.9	497.1	496.4	497.1	497.9	498.6	499.4	500.0	500.6	501.1
120°	539.8	539.0	538.3	537.5	538.3	539.0	539.8	540.5	540.8	540.8	540.8
122.5°	579.5	578.9	578.4	577.9	578.4	578.9	579.5	580.0	580.5	581.2	581.7
125°	640.1	639.9	639.6	639.4	639.6	639.9	640.1	640.4	640.8	641.6	642.3
127.5°	697.8	697.0	696.3	695.4	696.3	697.0	697.8	698.5	699.4	700.2	701.2
130°	738.7	737.6	736.7	735.7	736.7	737.6	738.7	739.6	740.4	740.8	741.3
132.5°	776.7	775.8	775.1	774.3	775.1	775.8	776.7	777.4	778.4	779.4	780.4
135°	836.4	835.8	835.0	834.2	835.0	835.8	836.4	837.2	837.6	837.9	838.2
137.5°	891.5	890.5	889.6	888.5	889.6	890.5	891.5	892.5	893.1	893.2	893.4
140°	929.2	928.2	927.2	926.2	927.2	928.2	929.2	930.1	930.6	930.6	930.6
142.5°	963.3	962.3	961.4	960.4	961.4	962.3	963.3	964.3	964.7	964.5	964.3
145°	1014.6	1013.6	1012.6	1011.6	1012.6	1013.6	1014.6	1015.5	1015.9	1015.7	1015.4
147.5°	1060.2	1059.2	1058.3	1057.4	1058.3	1059.2	1060.2	1061.1	1061.3	1060.7	1060.3
150°	1089.4	1088.6	1087.9	1087.2	1087.9	1088.6	1089.4	1090.1	1090.1	1089.4	1088.6
152.5°	1117.9	1117.1	1116.2	1115.2	1116.2	1117.1	1117.9	1118.9	1118.9	1117.9	1117.1
155°	1155.1	1154.3	1153.6	1152.8	1153.6	1154.3	1155.1	1155.7	1155.6	1154.3	1153.1
157.5°	1188.7	1187.6	1186.5	1185.2	1186.5	1187.6	1188.7	1190.0	1189.7	1188.1	1186.4
160°	1208.3	1207.4	1206.4	1205.4	1206.4	1207.4	1208.3	1209.3	1209.1	1207.6	1206.2
162.5°	1226.4	1225.3	1224.1	1222.9	1224.1	1225.3	1226.4	1227.6	1227.4	1225.7	1224.1
165°	1249.6	1248.4	1247.2	1245.9	1247.2	1248.4	1249.6	1250.8	1250.6	1248.9	1247.2
167.5°	1268.6	1267.2	1266.0	1264.8	1266.0	1267.2	1268.6	1269.8	1269.6	1267.9	1266.2
170°	1278.7	1277.3	1275.8	1274.4	1275.8	1277.3	1278.7	1280.3	1280.1	1278.4	1276.7
172.5°	1286.7	1285.2	1283.7	1282.2	1283.7	1285.2	1286.7	1288.1	1288.0	1286.3	1284.6
175°	1295.2	1293.7	1292.3	1290.8	1292.3	1293.7	1295.2	1296.7	1296.6	1294.9	1293.2
177.5°	1298.3	1297.1	1295.9	1294.8	1295.9	1297.1	1298.3	1299.4	1299.4	1298.3	1297.1
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1331.5	1336.9	1345.0	1349.6	1357.4	1362.4	1365.1	1370.1	1372.7	1382.3	1392.4
5°	1257.2	1264.9	1278.4	1290.8	1304.3	1318.2	1328.4	1339.9	1350.5	1368.8	1388.1
7.5°	1172.0	1182.6	1203.4	1223.4	1246.9	1266.6	1284.0	1303.7	1321.4	1347.6	1374.9
10°	1108.1	1126.8	1154.2	1173.0	1203.8	1223.5	1250.9	1272.5	1297.1	1331.7	1362.5
12.5°	1053.0	1075.6	1097.6	1123.7	1151.4	1184.2	1214.4	1242.2	1271.3	1307.1	1343.3
15°	953.1	985.8	1020.0	1046.4	1084.0	1118.6	1153.8	1191.3	1226.9	1269.7	1316.8
17.5°	824.5	862.4	919.9	965.3	1009.3	1044.1	1087.5	1132.9	1174.9	1226.5	1279.0
20°	766.5	794.4	833.3	894.4	960.8	997.9	1042.1	1092.1	1140.3	1196.6	1252.8
22.5°	719.8	744.7	776.0	823.6	897.7	948.2	994.4	1045.2	1101.0	1158.5	1220.9
25°	653.4	670.7	703.4	741.9	792.9	876.1	926.6	977.6	1038.3	1099.9	1171.0
27.5°	603.4	619.0	640.3	677.0	714.9	774.7	855.1	910.7	971.1	1040.4	1114.3
30°	565.3	583.6	607.2	633.2	674.6	721.2	801.5	866.0	925.7	996.9	1075.8
32.5°	537.6	552.0	572.1	598.5	633.0	677.7	741.9	820.2	878.4	953.4	1035.8
35°	492.2	509.1	525.4	550.4	578.3	619.3	667.8	751.5	809.3	883.4	966.1
37.5°	454.8	465.1	483.1	502.9	532.4	562.9	605.0	680.1	742.5	815.3	900.0
40°	426.3	439.2	452.7	474.9	498.9	528.3	569.7	625.5	697.1	768.4	851.1
42.5°	398.6	415.0	429.2	444.0	470.4	499.8	533.5	580.8	654.0	721.4	801.8
45°	365.1	375.8	390.7	407.0	428.7	453.7	483.5	524.9	595.1	653.4	728.9
47.5°	326.3	341.8	351.5	367.5	388.0	411.9	439.7	475.4	532.3	586.9	657.0
50°	299.7	315.7	329.6	344.0	362.3	385.4	408.5	443.1	488.8	546.1	611.5
52.5°	277.0	291.0	304.5	319.0	336.9	358.1	380.0	410.4	449.6	502.2	565.7
55°	245.8	254.5	268.4	282.9	298.8	319.0	340.2	365.6	399.4	443.6	495.1
57.5°	213.9	223.9	235.0	249.5	265.6	281.1	300.1	323.2	349.8	389.8	433.9
60°	195.9	203.5	212.6	227.5	242.5	256.5	274.8	294.0	319.0	353.6	391.2
62.5°	175.8	183.1	191.5	204.4	219.0	231.8	247.8	268.2	289.4	320.9	353.8
65°	142.4	153.0	161.2	172.8	184.7	198.2	210.8	227.1	245.8	270.9	300.2
67.5°	118.1	123.5	131.0	141.6	153.8	165.4	177.3	190.0	206.3	225.6	248.9
70°	107.3	109.2	110.7	120.7	132.3	143.8	155.0	166.9	180.9	196.8	217.0
72.5°	94.6	96.5	98.3	102.6	111.9	123.5	134.9	143.8	157.0	170.2	186.6
75°	75.0	77.9	79.4	81.8	85.2	92.8	103.4	112.1	119.8	129.9	142.9
77.5°	57.1	58.8	60.3	62.9	64.9	68.5	74.5	82.3	89.4	95.4	104.3
80°	45.2	45.7	47.6	48.6	51.5	53.9	56.7	63.1	70.2	72.7	78.9
82.5°	34.0	34.6	36.1	37.0	38.4	40.4	44.1	45.7	51.4	54.6	58.5
85°	18.8	18.3	19.7	19.7	20.6	21.7	22.6	25.0	26.5	30.3	31.3
87.5°	13.4	13.5	12.7	11.7	10.7	10.3	9.9	9.7	9.9	10.5	11.4
90°	37.8	38.4	33.0	27.6	22.2	16.9	12.8	9.9	7.0	4.1	1.1
92.5°	34.9	34.8	33.6	32.3	31.0	29.8	28.1	25.9	23.8	21.6	19.5
95°	70.0	70.0	69.6	69.1	68.6	68.1	66.6	64.2	61.8	59.4	56.9
97.5°	117.8	117.8	116.9	115.9	115.0	114.1	112.5	110.5	108.3	106.1	104.1
100°	151.1	151.1	150.3	149.6	148.9	148.2	146.8	144.9	143.0	141.0	139.0
102.5°	187.2	187.0	186.1	185.1	184.3	183.3	182.1	180.5	179.0	177.4	175.9
105°	241.4	240.8	240.3	239.9	239.4	238.9	238.3	237.6	236.9	236.1	235.4
107.5°	300.4	300.2	300.2	300.2	300.2	300.2	299.6	298.6	297.6	296.4	295.4
110°	340.5	340.5	340.5	340.5	340.5	340.5	339.8	338.3	336.9	335.4	333.9



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	381.1	381.6	381.8	382.0	382.2	382.5	381.8	380.3	378.9	377.4	376.0
115°	442.1	442.3	442.8	443.3	443.7	444.2	443.7	442.3	440.8	439.4	437.9
117.5°	501.7	502.3	503.7	505.0	506.4	507.7	507.5	505.5	503.6	501.6	499.6
120°	540.8	540.8	542.8	544.8	546.7	548.7	548.7	546.7	544.8	542.8	540.8
122.5°	582.3	582.9	584.3	585.6	587.0	588.3	587.9	585.5	583.2	580.9	578.5
125°	643.0	643.8	644.5	645.3	645.9	646.7	645.9	643.8	641.6	639.4	637.2
127.5°	702.0	702.9	703.8	704.6	705.5	706.4	705.4	702.7	699.9	697.1	694.4
130°	741.8	742.3	742.8	743.3	743.8	744.2	742.9	739.7	736.6	733.4	730.3
132.5°	781.6	782.6	782.5	782.4	782.3	782.2	780.9	778.3	775.7	773.2	770.5
135°	838.4	838.7	838.2	837.6	837.2	836.7	835.1	832.5	829.8	827.1	824.4
137.5°	893.6	893.8	893.2	892.6	891.9	891.3	889.9	887.7	885.5	883.4	881.1
140°	930.6	930.6	929.4	928.2	927.0	925.8	924.1	921.9	919.6	917.5	915.3
142.5°	964.1	963.9	963.1	962.2	961.4	960.5	959.0	956.9	954.7	952.5	950.4
145°	1015.1	1014.9	1013.4	1012.0	1010.5	1009.1	1007.5	1005.8	1004.1	1002.4	1000.7
147.5°	1059.7	1059.1	1058.2	1057.2	1056.2	1055.3	1053.8	1051.7	1049.6	1047.6	1045.6
150°	1087.9	1087.2	1086.2	1085.2	1084.3	1083.3	1082.0	1080.6	1079.1	1077.7	1076.2
152.5°	1116.2	1115.2	1114.1	1112.9	1111.7	1110.5	1109.2	1107.8	1106.3	1104.8	1103.3
155°	1151.9	1150.7	1150.0	1149.2	1148.5	1147.7	1147.1	1146.3	1145.6	1144.8	1144.2
157.5°	1184.8	1183.1	1182.6	1182.2	1181.8	1181.3	1180.9	1180.3	1179.9	1179.4	1178.9
160°	1204.7	1203.2	1203.0	1202.8	1202.5	1202.2	1201.9	1201.4	1200.9	1200.4	1200.0
162.5°	1222.4	1220.8	1220.5	1220.2	1220.0	1219.7	1219.7	1219.5	1219.4	1219.3	1219.2
165°	1245.5	1243.8	1243.8	1243.8	1243.8	1243.8	1243.9	1244.1	1244.3	1244.6	1244.8
167.5°	1264.5	1262.8	1262.8	1262.9	1262.9	1263.0	1263.4	1264.1	1264.8	1265.6	1266.3
170°	1275.0	1273.3	1273.6	1273.8	1274.0	1274.3	1274.8	1275.4	1276.2	1277.0	1277.7
172.5°	1282.9	1281.2	1281.4	1281.7	1282.0	1282.1	1282.6	1283.4	1284.1	1284.9	1285.5
175°	1291.5	1289.7	1290.2	1290.7	1291.2	1291.7	1292.3	1293.0	1293.7	1294.5	1295.2
177.5°	1295.9	1294.8	1295.1	1295.5	1295.9	1296.3	1296.8	1297.4	1298.0	1298.5	1299.1
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1392.8	1393.9	1401.7	1405.0	1412.0	1414.7	1417.8	1417.0	1417.0	1418.5	1429.4
5°	1395.7	1405.3	1419.8	1433.7	1447.2	1458.8	1466.5	1474.1	1477.1	1491.0	1503.5
7.5°	1390.7	1408.4	1432.3	1453.6	1479.0	1499.0	1515.5	1530.5	1540.7	1560.9	1581.8
10°	1384.2	1409.2	1436.2	1463.6	1498.7	1525.1	1552.1	1572.8	1579.5	1609.9	1627.2
12.5°	1371.1	1404.6	1438.9	1474.3	1508.7	1545.2	1574.8	1595.5	1619.2	1646.4	1678.4
15°	1351.5	1390.0	1434.7	1480.5	1529.5	1573.8	1605.5	1641.6	1667.5	1697.4	1725.3
17.5°	1323.2	1372.8	1429.7	1482.6	1539.4	1587.0	1630.6	1665.3	1683.6	1700.5	1704.7
20°	1301.0	1354.3	1421.3	1483.8	1540.6	1595.4	1638.7	1667.5	1672.4	1672.8	1647.4
22.5°	1276.7	1337.0	1407.0	1471.1	1539.0	1600.1	1633.7	1646.1	1626.9	1594.3	1545.0
25°	1232.2	1301.9	1383.3	1456.3	1530.5	1588.2	1599.8	1578.1	1511.2	1441.0	1352.0
27.5°	1183.8	1262.3	1349.4	1430.8	1509.7	1545.5	1520.5	1442.5	1322.0	1217.3	1090.4
30°	1148.5	1236.5	1322.1	1413.1	1486.2	1501.6	1444.4	1329.4	1188.8	1031.0	904.6
32.5°	1108.1	1200.3	1294.4	1388.5	1449.6	1434.6	1340.0	1198.4	1033.8	878.6	759.0
35°	1050.3	1145.6	1247.1	1341.3	1380.4	1315.4	1173.9	989.7	821.2	676.5	594.2
37.5°	983.6	1087.3	1192.9	1279.5	1276.7	1168.5	975.8	785.6	644.0	558.4	499.8
40°	936.2	1041.1	1155.2	1228.3	1197.0	1056.0	847.3	667.8	564.4	496.1	453.2
42.5°	890.9	996.1	1109.4	1167.5	1113.1	939.8	731.8	591.2	505.9	452.5	417.8
45°	813.6	924.7	1029.6	1061.9	964.7	773.6	591.8	489.7	433.0	393.6	369.5
47.5°	738.0	847.3	943.1	943.7	812.2	627.4	499.2	423.9	375.4	344.9	327.3
50°	691.8	795.8	876.1	863.7	714.4	558.1	446.5	381.5	341.1	317.5	299.3
52.5°	639.9	740.7	810.3	774.7	631.7	491.2	399.2	344.6	311.1	290.6	274.3
55°	564.4	653.8	702.9	649.0	515.3	408.5	337.2	294.5	269.5	252.1	238.2
57.5°	490.1	564.0	594.8	532.2	424.4	338.7	285.3	253.2	228.4	215.9	208.7
60°	443.6	506.6	528.3	459.0	369.0	296.3	252.6	222.7	204.4	196.3	189.1
62.5°	397.8	449.3	458.3	394.7	321.7	259.4	221.8	196.6	184.5	176.6	169.8
65°	330.1	367.1	362.8	311.8	254.5	205.9	178.5	163.1	153.9	142.9	130.8
67.5°	271.7	294.4	280.7	242.5	194.3	160.0	142.1	130.4	119.1	108.7	105.8
70°	234.8	247.8	233.4	198.2	159.3	134.2	119.8	105.8	99.2	96.7	92.4
72.5°	199.3	203.9	188.3	158.2	129.6	111.1	97.1	89.3	85.7	83.6	80.9
75°	149.7	146.3	132.8	109.2	90.0	77.5	73.1	70.2	67.9	65.9	64.5
77.5°	105.1	100.2	88.1	72.8	62.7	56.6	54.1	52.5	51.4	50.4	49.0
80°	78.9	75.5	63.5	51.9	47.6	44.8	43.3	41.4	41.4	40.4	38.9
82.5°	57.8	54.0	43.5	38.1	35.7	33.9	32.9	31.8	31.4	31.6	30.5
85°	30.3	24.5	21.7	20.6	19.2	18.3	18.8	17.8	17.8	17.8	17.3
87.5°	10.1	8.7	8.9	9.1	10.3	11.4	12.1	13.1	14.6	14.1	14.4
90°	4.1	7.0	9.9	12.8	16.9	22.2	27.6	33.0	38.4	37.8	37.3
92.5°	21.6	23.8	25.9	28.1	29.8	31.0	32.3	33.6	34.8	34.9	35.0
95°	59.4	61.8	64.2	66.6	68.1	68.6	69.1	69.6	70.0	70.0	70.0
97.5°	106.1	108.3	110.5	112.5	114.1	115.0	115.9	116.9	117.8	117.8	117.8
100°	141.0	143.0	144.9	146.8	148.2	148.9	149.6	150.3	151.1	151.1	151.1
102.5°	177.4	179.0	180.5	182.1	183.3	184.3	185.1	186.1	187.0	187.2	187.4
105°	236.1	236.9	237.6	238.3	238.9	239.4	239.9	240.3	240.8	241.4	241.9
107.5°	296.4	297.6	298.6	299.6	300.2	300.2	300.2	300.2	300.2	300.4	300.6
110°	335.4	336.9	338.3	339.8	340.5	340.5	340.5	340.5	340.5	340.5	340.5



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	377.4	378.9	380.3	381.8	382.5	382.2	382.0	381.8	381.6	381.1	380.5
115°	439.4	440.8	442.3	443.7	444.2	443.7	443.3	442.8	442.3	442.1	441.9
117.5°	501.6	503.6	505.5	507.5	507.7	506.4	505.0	503.7	502.3	501.7	501.1
120°	542.8	544.8	546.7	548.7	548.7	546.7	544.8	542.8	540.8	540.8	540.8
122.5°	580.9	583.2	585.5	587.9	588.3	587.0	585.6	584.3	582.9	582.3	581.7
125°	639.4	641.6	643.8	645.9	646.7	645.9	645.3	644.5	643.8	643.0	642.3
127.5°	697.1	699.9	702.7	705.4	706.4	705.5	704.6	703.8	702.9	702.0	701.2
130°	733.4	736.6	739.7	742.9	744.2	743.8	743.3	742.8	742.3	741.8	741.3
132.5°	773.2	775.7	778.3	780.9	782.2	782.3	782.4	782.5	782.6	781.6	780.4
135°	827.1	829.8	832.5	835.1	836.7	837.2	837.6	838.2	838.7	838.4	838.2
137.5°	883.4	885.5	887.7	889.9	891.3	891.9	892.6	893.2	893.8	893.6	893.4
140°	917.5	919.6	921.9	924.1	925.8	927.0	928.2	929.4	930.6	930.6	930.6
142.5°	952.5	954.7	956.9	959.0	960.5	961.4	962.2	963.1	963.9	964.1	964.3
145°	1002.4	1004.1	1005.8	1007.5	1009.1	1010.5	1012.0	1013.4	1014.9	1015.1	1015.4
147.5°	1047.6	1049.6	1051.7	1053.8	1055.3	1056.2	1057.2	1058.2	1059.1	1059.7	1060.3
150°	1077.7	1079.1	1080.6	1082.0	1083.3	1084.3	1085.2	1086.2	1087.2	1087.9	1088.6
152.5°	1104.8	1106.3	1107.8	1109.2	1110.5	1111.7	1112.9	1114.1	1115.2	1116.2	1117.1
155°	1144.8	1145.6	1146.3	1147.1	1147.7	1148.5	1149.2	1150.0	1150.7	1151.9	1153.1
157.5°	1179.4	1179.9	1180.3	1180.9	1181.3	1181.8	1182.2	1182.6	1183.1	1184.8	1186.4
160°	1200.4	1200.9	1201.4	1201.9	1202.2	1202.5	1202.8	1203.0	1203.2	1204.7	1206.2
162.5°	1219.3	1219.4	1219.5	1219.7	1219.7	1220.0	1220.2	1220.5	1220.8	1222.4	1224.1
165°	1244.6	1244.3	1244.1	1243.9	1243.8	1243.8	1243.8	1243.8	1243.8	1245.5	1247.2
167.5°	1265.6	1264.8	1264.1	1263.4	1263.0	1262.9	1262.9	1262.8	1262.8	1264.5	1266.2
170°	1277.0	1276.2	1275.4	1274.8	1274.3	1274.0	1273.8	1273.6	1273.3	1275.0	1276.7
172.5°	1284.9	1284.1	1283.4	1282.6	1282.1	1282.0	1281.7	1281.4	1281.2	1282.9	1284.6
175°	1294.5	1293.7	1293.0	1292.3	1291.7	1291.2	1290.7	1290.2	1289.7	1291.5	1293.2
177.5°	1298.5	1298.0	1297.4	1296.8	1296.3	1295.9	1295.5	1295.1	1294.8	1295.9	1297.1
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1433.1	1438.1	1440.5	1440.5	1443.2	1442.0	1440.9
5°	1515.5	1524.7	1526.6	1535.3	1541.5	1539.5	1540.6
7.5°	1597.4	1612.1	1626.6	1633.3	1634.4	1638.2	1639.6
10°	1647.8	1659.9	1682.5	1679.1	1695.9	1705.6	1689.7
12.5°	1696.4	1712.6	1728.2	1732.6	1742.2	1745.2	1739.0
15°	1740.2	1748.9	1749.8	1747.5	1750.3	1747.9	1738.8
17.5°	1699.2	1685.2	1656.7	1643.2	1632.6	1616.7	1610.4
20°	1631.4	1590.1	1542.0	1522.8	1500.2	1455.9	1466.5
22.5°	1485.3	1438.0	1390.0	1333.8	1306.9	1265.0	1262.4
25°	1257.6	1176.4	1086.8	1024.4	987.8	945.9	927.7
27.5°	977.8	875.4	802.1	765.0	731.2	698.0	696.6
30°	793.8	716.9	660.1	628.4	607.7	593.7	596.6
32.5°	669.1	616.4	578.2	551.8	536.5	525.9	525.8
35°	547.1	511.0	486.4	475.3	464.3	456.6	457.0
37.5°	468.2	446.5	432.8	420.6	413.7	409.9	407.8
40°	427.7	409.9	399.4	392.1	386.3	381.1	380.1
42.5°	395.8	381.1	370.4	364.8	359.4	355.6	354.7
45°	351.2	339.2	329.6	323.3	320.9	317.5	317.5
47.5°	312.5	300.6	293.1	289.2	285.0	282.8	282.7
50°	286.3	277.1	270.4	268.0	264.6	263.2	262.7
52.5°	262.8	256.0	251.2	249.5	248.1	246.2	246.6
55°	230.9	227.1	225.2	223.8	221.3	218.4	220.4
57.5°	204.1	200.9	195.7	191.1	188.9	186.9	187.7
60°	185.2	178.5	171.7	166.5	165.0	160.7	160.7
62.5°	161.4	151.9	143.6	140.7	139.2	137.2	136.9
65°	124.1	120.3	118.4	116.4	115.5	115.5	114.5
67.5°	102.8	101.3	99.2	98.7	97.7	97.5	97.2
70°	91.0	89.0	88.0	87.6	86.6	87.1	85.7
72.5°	79.4	77.9	77.7	76.4	75.8	75.9	74.8
75°	62.6	62.6	62.0	61.5	60.6	60.1	60.6
77.5°	48.1	48.2	47.3	47.2	47.1	47.2	46.8
80°	38.5	38.9	38.5	38.0	37.5	38.0	37.5
82.5°	30.4	29.7	29.6	29.5	29.4	29.1	29.0
85°	17.3	17.8	17.3	16.9	16.9	16.9	17.3
87.5°	13.9	13.9	13.8	13.9	13.9	13.9	13.6
90°	36.9	36.4	36.3	36.5	36.8	36.9	37.2
92.5°	35.1	35.3	35.3	35.3	35.3	35.4	35.4
95°	70.0	70.0	69.8	69.4	68.9	68.3	67.9
97.5°	117.8	117.8	117.8	117.7	117.7	117.6	117.6
100°	151.1	151.1	151.0	150.7	150.5	150.2	150.0
102.5°	187.6	187.8	187.8	187.5	187.3	187.0	186.8
105°	242.3	242.8	243.1	243.1	243.1	243.1	243.1
107.5°	300.8	301.0	300.5	299.4	298.3	297.2	296.1
110°	340.5	340.5	340.2	339.4	338.7	337.9	337.2



TEST NUMBER: P331700-830

CATALOG NUMBER: S122RDIP-S675D1080U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	379.9	379.4	378.8	378.2	377.7	377.2	376.6
115°	441.6	441.3	440.8	440.2	439.4	438.7	437.9
117.5°	500.6	500.0	499.4	498.6	497.9	497.1	496.4
120°	540.8	540.8	540.5	539.8	539.0	538.3	537.5
122.5°	581.2	580.5	580.0	579.5	578.9	578.4	577.9
125°	641.6	640.8	640.4	640.1	639.9	639.6	639.4
127.5°	700.2	699.4	698.5	697.8	697.0	696.3	695.4
130°	740.8	740.4	739.6	738.7	737.6	736.7	735.7
132.5°	779.4	778.4	777.4	776.7	775.8	775.1	774.3
135°	837.9	837.6	837.2	836.4	835.8	835.0	834.2
137.5°	893.2	893.1	892.5	891.5	890.5	889.6	888.5
140°	930.6	930.6	930.1	929.2	928.2	927.2	926.2
142.5°	964.5	964.7	964.3	963.3	962.3	961.4	960.4
145°	1015.7	1015.9	1015.5	1014.6	1013.6	1012.6	1011.6
147.5°	1060.7	1061.3	1061.1	1060.2	1059.2	1058.3	1057.4
150°	1089.4	1090.1	1090.1	1089.4	1088.6	1087.9	1087.2
152.5°	1117.9	1118.9	1118.9	1117.9	1117.1	1116.2	1115.2
155°	1154.3	1155.6	1155.7	1155.1	1154.3	1153.6	1152.8
157.5°	1188.1	1189.7	1190.0	1188.7	1187.6	1186.5	1185.2
160°	1207.6	1209.1	1209.3	1208.3	1207.4	1206.4	1205.4
162.5°	1225.7	1227.4	1227.6	1226.4	1225.3	1224.1	1222.9
165°	1248.9	1250.6	1250.8	1249.6	1248.4	1247.2	1245.9
167.5°	1267.9	1269.6	1269.8	1268.6	1267.2	1266.0	1264.8
170°	1278.4	1280.1	1280.3	1278.7	1277.3	1275.8	1274.4
172.5°	1286.3	1288.0	1288.1	1286.7	1285.2	1283.7	1282.2
175°	1294.9	1296.6	1296.7	1295.2	1293.7	1292.3	1290.8
177.5°	1298.3	1299.4	1299.4	1298.3	1297.1	1295.9	1294.8
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4

(END OF REPORT)