

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331694-830

Luminaire Tested: **S122RDIP-S675D925U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331694-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S675D925U830-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5514.2 lumens  
Efficiency: N/A  
Efficacy: 106.0 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	82	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	42	38	35	33	31	29	25
5	69	58	50	45	63	54	47	42	45	40	37	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	37	33	38	33	29	32	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	35	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	22357	22357	22357	22357
5°	24969	22498	19947	22498
10°	27702	22338	17290	22338
15°	29065	22011	13623	22011
20°	25197	21526	11789	21526
25°	16527	20861	10525	20861
30°	11123	20057	9527	20057
35°	9008	19042	8592	19042
40°	8011	17939	7950	17939
45°	7250	16643	7099	16643
50°	6599	15360	6574	15360
55°	6204	13937	6120	13937
60°	5189	12633	5125	12633
65°	4374	11469	4963	11469
70°	4046	10244	4683	10244
75°	3780	8914	4323	8914
80°	3487	7336	3849	7336
85°	3205	5798	3390	5798



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.3	2.4
10°-20°	365.7	6.6
20°-30°	471.3	8.5
30°-40°	447.9	8.1
40°-50°	383.7	7.0
50°-60°	292.2	5.3
60°-70°	184.7	3.3
70°-80°	92.2	1.7
80°-90°	28.5	0.5
90°-100°	70.6	1.3
100°-110°	219.4	4.0
110°-120°	375.0	6.8
120°-130°	493.1	8.9
130°-140°	553.4	10.0
140°-150°	542.7	9.8
150°-160°	455.2	8.3
160°-170°	301.9	5.5
170°-180°	105.5	1.9
0°-30°	968.3	17.6
0°-40°	1416.2	25.7
0°-60°	2092.1	37.9
0°-90°	2397.5	43.5
90°-120°	665.0	12.1
90°-150°	2254.1	40.9
90°-180°	3117.0	56.5
0°-180°	5514.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1385	1385	1385	1385	1385	
5°	1541	1388	1231	1388	1541	152
15°	1739	1317	815	1317	1739	469
25°	928	1171	591	1171	928	440
35°	457	966	436	966	457	292
45°	318	729	311	729	318	246
55°	220	495	217	495	220	193
65°	114	300	130	300	114	117
75°	61	143	69	143	61	64
85°	17	31	18	31	17	19
90°	32	1	32	1	32	15
95°	58	49	58	49	58	65
105°	209	202	209	202	209	220
115°	376	376	376	376	376	372
125°	549	547	549	547	549	490
135°	717	708	717	708	717	552
145°	869	860	869	860	869	543
155°	990	983	990	983	990	456
165°	1070	1070	1070	1070	1070	302
175°	1109	1113	1109	1113	1109	105
180°	1115	1115	1115	1115	1115	



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1440.9	1442.0	1443.2	1440.5	1440.5	1438.1	1433.1	1429.4	1418.5	1417.0	1417.0
5°	1540.6	1539.5	1541.5	1535.3	1526.6	1524.7	1515.5	1503.5	1491.0	1477.1	1474.1
7.5°	1639.6	1638.2	1634.4	1633.3	1626.6	1612.1	1597.4	1581.8	1560.9	1540.7	1530.5
10°	1689.7	1705.6	1695.9	1679.1	1682.5	1659.9	1647.8	1627.2	1609.9	1579.5	1572.8
12.5°	1739.0	1745.2	1742.2	1732.6	1728.2	1712.6	1696.4	1678.4	1646.4	1619.2	1595.5
15°	1738.8	1747.9	1750.3	1747.5	1749.8	1748.9	1740.2	1725.3	1697.4	1667.5	1641.6
17.5°	1610.4	1616.7	1632.6	1643.2	1656.7	1685.2	1699.2	1704.7	1700.5	1683.6	1665.3
20°	1466.5	1455.9	1500.2	1522.8	1542.0	1590.1	1631.4	1647.4	1672.8	1672.4	1667.5
22.5°	1262.4	1265.0	1306.9	1333.8	1390.0	1438.0	1485.3	1545.0	1594.3	1626.9	1646.1
25°	927.7	945.9	987.8	1024.4	1086.8	1176.4	1257.6	1352.0	1441.0	1511.2	1578.1
27.5°	696.6	698.0	731.2	765.0	802.1	875.4	977.8	1090.4	1217.3	1322.0	1442.5
30°	596.6	593.7	607.7	628.4	660.1	716.9	793.8	904.6	1031.0	1188.8	1329.4
32.5°	525.8	525.9	536.5	551.8	578.2	616.4	669.1	759.0	878.6	1033.8	1198.4
35°	457.0	456.6	464.3	475.3	486.4	511.0	547.1	594.2	676.5	821.2	989.7
37.5°	407.8	409.9	413.7	420.6	432.8	446.5	468.2	499.8	558.4	644.0	785.6
40°	380.1	381.1	386.3	392.1	399.4	409.9	427.7	453.2	496.1	564.4	667.8
42.5°	354.7	355.6	359.4	364.8	370.4	381.1	395.8	417.8	452.5	505.9	591.2
45°	317.5	317.5	320.9	323.3	329.6	339.2	351.2	369.5	393.6	433.0	489.7
47.5°	282.7	282.8	285.0	289.2	293.1	300.6	312.5	327.3	344.9	375.4	423.9
50°	262.7	263.2	264.6	268.0	270.4	277.1	286.3	299.3	317.5	341.1	381.5
52.5°	246.6	246.2	248.1	249.5	251.2	256.0	262.8	274.3	290.6	311.1	344.6
55°	220.4	218.4	221.3	223.8	225.2	227.1	230.9	238.2	252.1	269.5	294.5
57.5°	187.7	186.9	188.9	191.1	195.7	200.9	204.1	208.7	215.9	228.4	253.2
60°	160.7	160.7	165.0	166.5	171.7	178.5	185.2	189.1	196.3	204.4	222.7
62.5°	136.9	137.2	139.2	140.7	143.6	151.9	161.4	169.8	176.6	184.5	196.6
65°	114.5	115.5	115.5	116.4	118.4	120.3	124.1	130.8	142.9	153.9	163.1
67.5°	97.2	97.5	97.7	98.7	99.2	101.3	102.8	105.8	108.7	119.1	130.4
70°	85.7	87.1	86.6	87.6	88.0	89.0	91.0	92.4	96.7	99.2	105.8
72.5°	74.8	75.9	75.8	76.4	77.7	77.9	79.4	80.9	83.6	85.7	89.3
75°	60.6	60.1	60.6	61.5	62.0	62.6	62.6	64.5	65.9	67.9	70.2
77.5°	46.8	47.2	47.1	47.2	47.3	48.2	48.1	49.0	50.4	51.4	52.5
80°	37.5	38.0	37.5	38.0	38.5	38.9	38.5	38.9	40.4	41.4	41.4
82.5°	29.0	29.1	29.4	29.5	29.6	29.7	30.4	30.5	31.6	31.4	31.8
85°	17.3	16.9	16.9	16.9	17.3	17.8	17.3	17.3	17.8	17.8	17.8
87.5°	12.5	12.9	12.8	12.8	12.8	12.8	12.9	13.4	13.0	13.5	12.3
90°	32.0	31.8	31.6	31.4	31.1	31.3	31.7	32.0	32.5	32.9	28.3
92.5°	30.4	30.4	30.3	30.3	30.3	30.3	30.2	30.1	30.0	29.9	28.8
95°	58.3	58.7	59.2	59.6	59.9	60.2	60.2	60.2	60.2	60.2	59.8
97.5°	101.0	101.0	101.1	101.1	101.2	101.2	101.2	101.2	101.2	101.2	100.4
100°	128.8	129.0	129.3	129.5	129.7	129.8	129.8	129.8	129.8	129.8	129.2
102.5°	160.5	160.7	160.9	161.1	161.3	161.4	161.2	161.0	160.8	160.7	159.9
105°	208.8	208.8	208.8	208.8	208.8	208.6	208.2	207.7	207.4	206.9	206.5
107.5°	254.3	255.3	256.3	257.2	258.2	258.5	258.4	258.3	258.1	257.9	257.9
110°	289.7	290.3	291.0	291.6	292.2	292.6	292.6	292.6	292.6	292.6	292.6



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	323.6	324.0	324.5	325.0	325.4	325.9	326.4	326.9	327.4	327.9	328.1
115°	376.3	376.8	377.5	378.1	378.7	379.2	379.4	379.6	379.8	380.0	380.4
117.5°	426.5	427.1	427.7	428.4	429.0	429.5	430.1	430.6	431.0	431.6	432.7
120°	461.8	462.5	463.1	463.7	464.4	464.7	464.7	464.7	464.7	464.7	466.4
122.5°	496.4	496.9	497.4	497.9	498.3	498.8	499.3	499.7	500.3	500.8	502.0
125°	549.3	549.5	549.7	550.0	550.2	550.5	551.2	551.9	552.4	553.1	553.7
127.5°	597.5	598.1	598.8	599.5	600.1	600.9	601.6	602.4	603.1	603.9	604.6
130°	632.1	632.9	633.8	634.6	635.5	636.0	636.5	636.9	637.3	637.7	638.2
132.5°	665.2	665.9	666.6	667.2	667.9	668.6	669.6	670.5	671.5	672.3	672.2
135°	716.7	717.4	718.0	718.6	719.3	719.6	719.9	720.1	720.3	720.5	720.1
137.5°	763.4	764.2	765.1	765.9	766.8	767.2	767.4	767.6	767.8	767.9	767.4
140°	795.8	796.6	797.4	798.2	799.1	799.6	799.6	799.6	799.6	799.6	798.5
142.5°	825.1	826.0	826.8	827.6	828.5	828.8	828.6	828.5	828.3	828.1	827.4
145°	869.1	870.0	870.8	871.7	872.5	872.8	872.6	872.3	872.1	871.9	870.7
147.5°	908.4	909.3	910.0	910.9	911.6	911.8	911.3	910.9	910.4	909.9	909.1
150°	934.1	934.6	935.3	935.9	936.5	936.5	935.9	935.3	934.6	934.1	933.2
152.5°	958.1	958.9	959.7	960.5	961.3	961.3	960.5	959.7	958.9	958.1	957.1
155°	990.4	991.1	991.7	992.3	993.0	992.8	991.7	990.7	989.7	988.5	988.0
157.5°	1018.3	1019.3	1020.3	1021.3	1022.3	1022.1	1020.7	1019.3	1017.9	1016.4	1016.1
160°	1035.6	1036.4	1037.3	1038.1	1039.0	1038.8	1037.5	1036.2	1035.0	1033.7	1033.5
162.5°	1050.7	1051.7	1052.6	1053.7	1054.7	1054.4	1053.0	1051.6	1050.2	1048.8	1048.6
165°	1070.4	1071.5	1072.5	1073.6	1074.6	1074.4	1072.9	1071.5	1070.0	1068.6	1068.6
167.5°	1086.6	1087.7	1088.7	1089.9	1090.9	1090.7	1089.3	1087.8	1086.4	1084.9	1085.0
170°	1094.9	1096.1	1097.4	1098.6	1099.9	1099.8	1098.3	1096.8	1095.4	1093.9	1094.1
172.5°	1101.6	1102.9	1104.2	1105.4	1106.6	1106.5	1105.1	1103.6	1102.2	1100.7	1100.9
175°	1109.0	1110.2	1111.4	1112.8	1114.0	1113.9	1112.4	1111.0	1109.5	1108.1	1108.4
177.5°	1112.4	1113.3	1114.4	1115.4	1116.3	1116.3	1115.4	1114.4	1113.3	1112.4	1112.7
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1417.8	1414.7	1412.0	1405.0	1401.7	1393.9	1392.8	1392.4	1382.3	1372.7	1370.1
5°	1466.5	1458.8	1447.2	1433.7	1419.8	1405.3	1395.7	1388.1	1368.8	1350.5	1339.9
7.5°	1515.5	1499.0	1479.0	1453.6	1432.3	1408.4	1390.7	1374.9	1347.6	1321.4	1303.7
10°	1552.1	1525.1	1498.7	1463.6	1436.2	1409.2	1384.2	1362.5	1331.7	1297.1	1272.5
12.5°	1574.8	1545.2	1508.7	1474.3	1438.9	1404.6	1371.1	1343.3	1307.1	1271.3	1242.2
15°	1605.5	1573.8	1529.5	1480.5	1434.7	1390.0	1351.5	1316.8	1269.7	1226.9	1191.3
17.5°	1630.6	1587.0	1539.4	1482.6	1429.7	1372.8	1323.2	1279.0	1226.5	1174.9	1132.9
20°	1638.7	1595.4	1540.6	1483.8	1421.3	1354.3	1301.0	1252.8	1196.6	1140.3	1092.1
22.5°	1633.7	1600.1	1539.0	1471.1	1407.0	1337.0	1276.7	1220.9	1158.5	1101.0	1045.2
25°	1599.8	1588.2	1530.5	1456.3	1383.3	1301.9	1232.2	1171.0	1099.9	1038.3	977.6
27.5°	1520.5	1545.5	1509.7	1430.8	1349.4	1262.3	1183.8	1114.3	1040.4	971.1	910.7
30°	1444.4	1501.6	1486.2	1413.1	1322.1	1236.5	1148.5	1075.8	996.9	925.7	866.0
32.5°	1340.0	1434.6	1449.6	1388.5	1294.4	1200.3	1108.1	1035.8	953.4	878.4	820.2
35°	1173.9	1315.4	1380.4	1341.3	1247.1	1145.6	1050.3	966.1	883.4	809.3	751.5
37.5°	975.8	1168.5	1276.7	1279.5	1192.9	1087.3	983.6	900.0	815.3	742.5	680.1
40°	847.3	1056.0	1197.0	1228.3	1155.2	1041.1	936.2	851.1	768.4	697.1	625.5
42.5°	731.8	939.8	1113.1	1167.5	1109.4	996.1	890.9	801.8	721.4	654.0	580.8
45°	591.8	773.6	964.7	1061.9	1029.6	924.7	813.6	728.9	653.4	595.1	524.9
47.5°	499.2	627.4	812.2	943.7	943.1	847.3	738.0	657.0	586.9	532.3	475.4
50°	446.5	558.1	714.4	863.7	876.1	795.8	691.8	611.5	546.1	488.8	443.1
52.5°	399.2	491.2	631.7	774.7	810.3	740.7	639.9	565.7	502.2	449.6	410.4
55°	337.2	408.5	515.3	649.0	702.9	653.8	564.4	495.1	443.6	399.4	365.6
57.5°	285.3	338.7	424.4	532.2	594.8	564.0	490.1	433.9	389.8	349.8	323.2
60°	252.6	296.3	369.0	459.0	528.3	506.6	443.6	391.2	353.6	319.0	294.0
62.5°	221.8	259.4	321.7	394.7	458.3	449.3	397.8	353.8	320.9	289.4	268.2
65°	178.5	205.9	254.5	311.8	362.8	367.1	330.1	300.2	270.9	245.8	227.1
67.5°	142.1	160.0	194.3	242.5	280.7	294.4	271.7	248.9	225.6	206.3	190.0
70°	119.8	134.2	159.3	198.2	233.4	247.8	234.8	217.0	196.8	180.9	166.9
72.5°	97.1	111.1	129.6	158.2	188.3	203.9	199.3	186.6	170.2	157.0	143.8
75°	73.1	77.5	90.0	109.2	132.8	146.3	149.7	142.9	129.9	119.8	112.1
77.5°	54.1	56.6	62.7	72.8	88.1	100.2	105.1	104.3	95.4	89.4	82.3
80°	43.3	44.8	47.6	51.9	63.5	75.5	78.9	78.9	72.7	70.2	63.1
82.5°	32.9	33.9	35.7	38.1	43.5	54.0	57.8	58.5	54.6	51.4	45.7
85°	18.8	18.3	19.2	20.6	21.7	24.5	30.3	31.3	30.3	26.5	25.0
87.5°	11.3	10.7	9.8	8.8	8.6	8.5	9.9	11.3	10.3	9.6	9.4
90°	23.8	19.1	14.5	10.9	8.5	5.9	3.5	0.9	3.5	5.9	8.5
92.5°	27.7	26.7	25.5	24.1	22.2	20.5	18.6	16.8	18.6	20.5	22.2
95°	59.4	58.9	58.5	57.3	55.1	53.1	51.0	48.9	51.0	53.1	55.1
97.5°	99.6	98.9	98.0	96.7	94.9	93.0	91.2	89.4	91.2	93.0	94.9
100°	128.6	127.9	127.3	126.1	124.5	122.8	121.1	119.4	121.1	122.8	124.5
102.5°	159.1	158.3	157.5	156.4	155.0	153.7	152.4	151.1	152.4	153.7	155.0
105°	206.1	205.7	205.3	204.7	204.2	203.5	202.8	202.3	202.8	203.5	204.2
107.5°	257.9	257.9	257.9	257.5	256.6	255.6	254.7	253.7	254.7	255.6	256.6
110°	292.6	292.6	292.6	291.9	290.7	289.4	288.1	286.9	288.1	289.4	290.7





TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	328.2	328.4	328.6	328.0	326.8	325.6	324.2	323.0	324.2	325.6	326.8
115°	380.9	381.3	381.6	381.3	380.0	378.7	377.5	376.3	377.5	378.7	380.0
117.5°	433.9	435.1	436.2	436.0	434.3	432.6	430.9	429.3	430.9	432.6	434.3
120°	468.0	469.7	471.4	471.4	469.7	468.0	466.4	464.7	466.4	468.0	469.7
122.5°	503.1	504.3	505.5	505.0	503.0	501.1	499.0	497.0	499.0	501.1	503.0
125°	554.3	555.0	555.6	555.0	553.1	551.2	549.3	547.4	549.3	551.2	553.1
127.5°	605.4	606.1	606.9	606.1	603.7	601.3	598.9	596.5	598.9	601.3	603.7
130°	638.6	638.9	639.4	638.3	635.6	632.8	630.1	627.4	630.1	632.8	635.6
132.5°	672.2	672.1	672.0	670.9	668.6	666.5	664.2	662.0	664.2	666.5	668.6
135°	719.6	719.3	718.9	717.5	715.2	712.8	710.6	708.3	710.6	712.8	715.2
137.5°	766.9	766.3	765.7	764.5	762.6	760.7	758.8	757.1	758.8	760.7	762.6
140°	797.4	796.4	795.3	793.9	792.0	790.1	788.2	786.4	788.2	790.1	792.0
142.5°	826.7	826.0	825.3	824.0	822.1	820.2	818.3	816.4	818.3	820.2	822.1
145°	869.4	868.2	867.0	865.5	864.1	862.6	861.2	859.7	861.2	862.6	864.1
147.5°	908.2	907.5	906.6	905.3	903.5	901.8	900.0	898.2	900.0	901.8	903.5
150°	932.4	931.5	930.7	929.6	928.4	927.1	925.9	924.6	925.9	927.1	928.4
152.5°	956.1	955.1	954.1	953.0	951.7	950.5	949.2	947.9	949.2	950.5	951.7
155°	987.3	986.7	986.1	985.4	984.9	984.2	983.5	983.0	983.5	984.2	984.9
157.5°	1015.7	1015.3	1014.9	1014.6	1014.1	1013.7	1013.2	1012.9	1013.2	1013.7	1014.1
160°	1033.3	1033.1	1032.9	1032.6	1032.2	1031.7	1031.3	1031.0	1031.3	1031.7	1032.2
162.5°	1048.4	1048.2	1047.9	1047.8	1047.7	1047.6	1047.5	1047.4	1047.5	1047.6	1047.7
165°	1068.6	1068.6	1068.6	1068.7	1068.8	1069.0	1069.3	1069.5	1069.3	1069.0	1068.8
167.5°	1085.0	1085.1	1085.1	1085.4	1086.0	1086.7	1087.3	1087.9	1087.3	1086.7	1086.0
170°	1094.4	1094.6	1094.8	1095.1	1095.8	1096.5	1097.0	1097.7	1097.0	1096.5	1095.8
172.5°	1101.1	1101.4	1101.5	1101.9	1102.6	1103.2	1103.8	1104.5	1103.8	1103.2	1102.6
175°	1108.9	1109.3	1109.7	1110.2	1110.9	1111.4	1112.1	1112.8	1112.1	1111.4	1110.9
177.5°	1113.0	1113.3	1113.7	1114.1	1114.7	1115.1	1115.6	1116.2	1115.6	1115.1	1114.7
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1365.1	1362.4	1357.4	1349.6	1345.0	1336.9	1331.5	1334.6	1335.4	1334.6	1333.9
5°	1328.4	1318.2	1304.3	1290.8	1278.4	1264.9	1257.2	1253.8	1247.1	1243.2	1241.3
7.5°	1284.0	1266.6	1246.9	1223.4	1203.4	1182.6	1172.0	1166.6	1152.8	1145.4	1138.8
10°	1250.9	1223.5	1203.8	1173.0	1154.2	1126.8	1108.1	1108.5	1089.8	1079.1	1071.5
12.5°	1214.4	1184.2	1151.4	1123.7	1097.6	1075.6	1053.0	1043.9	1023.9	1013.7	993.0
15°	1153.8	1118.6	1084.0	1046.4	1020.0	985.8	953.1	913.1	880.9	853.0	845.4
17.5°	1087.5	1044.1	1009.3	965.3	919.9	862.4	824.5	801.3	781.9	767.2	756.2
20°	1042.1	997.9	960.8	894.4	833.3	794.4	766.5	748.7	728.4	712.6	703.9
22.5°	994.4	948.2	897.7	823.6	776.0	744.7	719.8	699.4	685.7	673.3	665.4
25°	926.6	876.1	792.9	741.9	703.4	670.7	653.4	640.8	626.4	609.5	601.9
27.5°	855.1	774.7	714.9	677.0	640.3	619.0	603.4	584.8	571.8	564.3	556.3
30°	801.5	721.2	674.6	633.2	607.2	583.6	565.3	554.8	542.2	529.2	524.0
32.5°	741.9	677.7	633.0	598.5	572.1	552.0	537.6	520.5	511.4	503.4	492.4
35°	667.8	619.3	578.3	550.4	525.4	509.1	492.2	482.1	465.7	459.0	454.7
37.5°	605.0	562.9	532.4	502.9	483.1	465.1	454.8	438.7	431.6	422.3	413.1
40°	569.7	528.3	498.9	474.9	452.7	439.2	426.3	413.3	402.7	398.4	387.3
42.5°	533.5	499.8	470.4	444.0	429.2	415.0	398.6	389.1	378.1	371.1	364.2
45°	483.5	453.7	428.7	407.0	390.7	375.8	365.1	349.3	343.1	329.0	323.3
47.5°	439.7	411.9	388.0	367.5	351.5	341.8	326.3	313.9	303.9	295.3	287.9
50°	408.5	385.4	362.3	344.0	329.6	315.7	299.7	293.5	278.1	273.7	269.5
52.5°	380.0	358.1	336.9	319.0	304.5	291.0	277.0	268.8	258.4	254.1	251.0
55°	340.2	319.0	298.8	282.9	268.4	254.5	245.8	235.7	230.9	227.5	223.8
57.5°	300.1	281.1	265.6	249.5	235.0	223.9	213.9	207.8	202.8	198.4	193.8
60°	274.8	256.5	242.5	227.5	212.6	203.5	195.9	188.6	182.9	176.1	174.2
62.5°	247.8	231.8	219.0	204.4	191.5	183.1	175.8	169.0	162.0	152.2	149.5
65°	210.8	198.2	184.7	172.8	161.2	153.0	142.4	134.7	131.9	130.8	130.4
67.5°	177.3	165.4	153.8	141.6	131.0	123.5	118.1	116.9	114.9	114.3	113.0
70°	155.0	143.8	132.3	120.7	110.7	109.2	107.3	105.4	102.9	102.0	101.0
72.5°	134.9	123.5	111.9	102.6	98.3	96.5	94.6	92.7	91.0	90.1	89.4
75°	103.4	92.8	85.2	81.8	79.4	77.9	75.0	73.6	72.7	71.2	70.7
77.5°	74.5	68.5	64.9	62.9	60.3	58.8	57.1	55.7	54.7	54.4	53.6
80°	56.7	53.9	51.5	48.6	47.6	45.7	45.2	43.8	44.3	42.8	42.8
82.5°	44.1	40.4	38.4	37.0	36.1	34.6	34.0	33.4	33.5	32.4	32.4
85°	22.6	21.7	20.6	19.7	19.7	18.3	18.8	18.3	18.3	17.3	16.9
87.5°	9.5	9.8	10.0	10.9	11.8	12.3	12.3	11.8	11.7	11.6	11.2
90°	10.9	14.5	19.1	23.8	28.3	32.9	32.5	32.0	31.7	31.3	31.1
92.5°	24.1	25.5	26.7	27.7	28.8	29.9	30.0	30.1	30.2	30.3	30.3
95°	57.3	58.5	58.9	59.4	59.8	60.2	60.2	60.2	60.2	60.2	59.9
97.5°	96.7	98.0	98.9	99.6	100.4	101.2	101.2	101.2	101.2	101.2	101.2
100°	126.1	127.3	127.9	128.6	129.2	129.8	129.8	129.8	129.8	129.8	129.7
102.5°	156.4	157.5	158.3	159.1	159.9	160.7	160.8	161.0	161.2	161.4	161.3
105°	204.7	205.3	205.7	206.1	206.5	206.9	207.4	207.7	208.2	208.6	208.8
107.5°	257.5	257.9	257.9	257.9	257.9	257.9	258.1	258.3	258.4	258.5	258.2
110°	291.9	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.2



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	328.0	328.6	328.4	328.2	328.1	327.9	327.4	326.9	326.4	325.9	325.4
115°	381.3	381.6	381.3	380.9	380.4	380.0	379.8	379.6	379.4	379.2	378.7
117.5°	436.0	436.2	435.1	433.9	432.7	431.6	431.0	430.6	430.1	429.5	429.0
120°	471.4	471.4	469.7	468.0	466.4	464.7	464.7	464.7	464.7	464.7	464.4
122.5°	505.0	505.5	504.3	503.1	502.0	500.8	500.3	499.7	499.3	498.8	498.3
125°	555.0	555.6	555.0	554.3	553.7	553.1	552.4	551.9	551.2	550.5	550.2
127.5°	606.1	606.9	606.1	605.4	604.6	603.9	603.1	602.4	601.6	600.9	600.1
130°	638.3	639.4	638.9	638.6	638.2	637.7	637.3	636.9	636.5	636.0	635.5
132.5°	670.9	672.0	672.1	672.2	672.2	672.3	671.5	670.5	669.6	668.6	667.9
135°	717.5	718.9	719.3	719.6	720.1	720.5	720.3	720.1	719.9	719.6	719.3
137.5°	764.5	765.7	766.3	766.9	767.4	767.9	767.8	767.6	767.4	767.2	766.8
140°	793.9	795.3	796.4	797.4	798.5	799.6	799.6	799.6	799.6	799.6	799.1
142.5°	824.0	825.3	826.0	826.7	827.4	828.1	828.3	828.5	828.6	828.8	828.5
145°	865.5	867.0	868.2	869.4	870.7	871.9	872.1	872.3	872.6	872.8	872.5
147.5°	905.3	906.6	907.5	908.2	909.1	909.9	910.4	910.9	911.3	911.8	911.6
150°	929.6	930.7	931.5	932.4	933.2	934.1	934.6	935.3	935.9	936.5	936.5
152.5°	953.0	954.1	955.1	956.1	957.1	958.1	958.9	959.7	960.5	961.3	961.3
155°	985.4	986.1	986.7	987.3	988.0	988.5	989.7	990.7	991.7	992.8	993.0
157.5°	1014.6	1014.9	1015.3	1015.7	1016.1	1016.4	1017.9	1019.3	1020.7	1022.1	1022.3
160°	1032.6	1032.9	1033.1	1033.3	1033.5	1033.7	1035.0	1036.2	1037.5	1038.8	1039.0
162.5°	1047.8	1047.9	1048.2	1048.4	1048.6	1048.8	1050.2	1051.6	1053.0	1054.4	1054.7
165°	1068.7	1068.6	1068.6	1068.6	1068.6	1068.6	1070.0	1071.5	1072.9	1074.4	1074.6
167.5°	1085.4	1085.1	1085.1	1085.0	1085.0	1084.9	1086.4	1087.8	1089.3	1090.7	1090.9
170°	1095.1	1094.8	1094.6	1094.4	1094.1	1093.9	1095.4	1096.8	1098.3	1099.8	1099.9
172.5°	1101.9	1101.5	1101.4	1101.1	1100.9	1100.7	1102.2	1103.6	1105.1	1106.5	1106.6
175°	1110.2	1109.7	1109.3	1108.9	1108.4	1108.1	1109.5	1111.0	1112.4	1113.9	1114.0
177.5°	1114.1	1113.7	1113.3	1113.0	1112.7	1112.4	1113.3	1114.4	1115.4	1116.3	1116.3
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1329.6	1330.4	1329.3	1330.0	1329.3	1330.4	1329.6	1333.9	1334.6	1335.4	1334.6
5°	1238.9	1233.1	1232.2	1230.7	1232.2	1233.1	1238.9	1241.3	1243.2	1247.1	1253.8
7.5°	1130.6	1129.6	1127.3	1123.9	1127.3	1129.6	1130.6	1138.8	1145.4	1152.8	1166.6
10°	1060.8	1058.5	1058.0	1054.6	1058.0	1058.5	1060.8	1071.5	1079.1	1089.8	1108.5
12.5°	979.3	963.7	962.1	953.8	962.1	963.7	979.3	993.0	1013.7	1023.9	1043.9
15°	833.8	830.9	821.2	815.0	821.2	830.9	833.8	845.4	853.0	880.9	913.1
17.5°	750.6	741.2	738.2	736.9	738.2	741.2	750.6	756.2	767.2	781.9	801.3
20°	697.1	688.5	687.0	686.1	687.0	688.5	697.1	703.9	712.6	728.4	748.7
22.5°	660.2	651.1	647.4	644.5	647.4	651.1	660.2	665.4	673.3	685.7	699.4
25°	597.1	593.7	591.8	590.8	591.8	593.7	597.1	601.9	609.5	626.4	640.8
27.5°	547.7	540.3	538.9	536.4	538.9	540.3	547.7	556.3	564.3	571.8	584.8
30°	519.6	517.2	513.9	511.0	513.9	517.2	519.6	524.0	529.2	542.2	554.8
32.5°	486.5	484.5	481.5	480.1	481.5	484.5	486.5	492.4	503.4	511.4	520.5
35°	449.9	443.1	440.3	435.9	440.3	443.1	449.9	454.7	459.0	465.7	482.1
37.5°	411.0	407.6	403.5	404.9	403.5	407.6	411.0	413.1	422.3	431.6	438.7
40°	381.1	378.6	377.7	377.2	377.7	378.6	381.1	387.3	398.4	402.7	413.3
42.5°	357.2	350.5	348.1	348.0	348.1	350.5	357.2	364.2	371.1	378.1	389.1
45°	320.9	314.6	310.3	310.9	310.3	314.6	320.9	323.3	329.0	343.1	349.3
47.5°	283.8	283.6	280.9	281.7	280.9	283.6	283.8	287.9	295.3	303.9	313.9
50°	266.1	263.2	261.3	261.7	261.3	263.2	266.1	269.5	273.7	278.1	293.5
52.5°	249.1	246.7	245.1	247.1	245.1	246.7	249.1	251.0	254.1	258.4	268.8
55°	221.3	218.4	217.9	217.4	217.9	218.4	221.3	223.8	227.5	230.9	235.7
57.5°	190.2	188.3	185.4	184.2	185.4	188.3	190.2	193.8	198.4	202.8	207.8
60°	167.9	164.1	159.3	158.7	159.3	164.1	167.9	174.2	176.1	182.9	188.6
62.5°	147.5	146.8	145.8	145.7	145.8	146.8	147.5	149.5	152.2	162.0	169.0
65°	129.4	128.9	129.4	129.9	129.4	128.9	129.4	130.4	130.8	131.9	134.7
67.5°	112.8	111.9	111.0	111.4	111.0	111.9	112.8	113.0	114.3	114.9	116.9
70°	100.1	99.6	99.2	99.2	99.2	99.6	100.1	101.0	102.0	102.9	105.4
72.5°	87.8	87.7	87.2	86.8	87.2	87.7	87.8	89.4	90.1	91.0	92.7
75°	70.2	69.3	69.3	69.3	69.3	69.3	70.2	70.7	71.2	72.7	73.6
77.5°	53.5	53.1	52.5	52.1	52.5	53.1	53.5	53.6	54.4	54.7	55.7
80°	42.3	41.8	41.4	41.4	41.4	41.8	42.3	42.8	42.8	44.3	43.8
82.5°	32.3	31.9	31.8	31.4	31.8	31.9	32.3	32.4	32.4	33.5	33.4
85°	17.3	17.8	17.3	18.3	17.3	17.8	17.3	16.9	17.3	18.3	18.3
87.5°	11.3	10.9	11.4	11.0	11.4	10.9	11.3	11.2	11.6	11.7	11.8
90°	31.4	31.6	31.8	32.0	31.8	31.6	31.4	31.1	31.3	31.7	32.0
92.5°	30.3	30.3	30.4	30.4	30.4	30.3	30.3	30.3	30.3	30.2	30.1
95°	59.6	59.2	58.7	58.3	58.7	59.2	59.6	59.9	60.2	60.2	60.2
97.5°	101.1	101.1	101.0	101.0	101.0	101.1	101.1	101.2	101.2	101.2	101.2
100°	129.5	129.3	129.0	128.8	129.0	129.3	129.5	129.7	129.8	129.8	129.8
102.5°	161.1	160.9	160.7	160.5	160.7	160.9	161.1	161.3	161.4	161.2	161.0
105°	208.8	208.8	208.8	208.8	208.8	208.8	208.8	208.8	208.6	208.2	207.7
107.5°	257.2	256.3	255.3	254.3	255.3	256.3	257.2	258.2	258.5	258.4	258.3
110°	291.6	291.0	290.3	289.7	290.3	291.0	291.6	292.2	292.6	292.6	292.6



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	325.0	324.5	324.0	323.6	324.0	324.5	325.0	325.4	325.9	326.4	326.9
115°	378.1	377.5	376.8	376.3	376.8	377.5	378.1	378.7	379.2	379.4	379.6
117.5°	428.4	427.7	427.1	426.5	427.1	427.7	428.4	429.0	429.5	430.1	430.6
120°	463.7	463.1	462.5	461.8	462.5	463.1	463.7	464.4	464.7	464.7	464.7
122.5°	497.9	497.4	496.9	496.4	496.9	497.4	497.9	498.3	498.8	499.3	499.7
125°	550.0	549.7	549.5	549.3	549.5	549.7	550.0	550.2	550.5	551.2	551.9
127.5°	599.5	598.8	598.1	597.5	598.1	598.8	599.5	600.1	600.9	601.6	602.4
130°	634.6	633.8	632.9	632.1	632.9	633.8	634.6	635.5	636.0	636.5	636.9
132.5°	667.2	666.6	665.9	665.2	665.9	666.6	667.2	667.9	668.6	669.6	670.5
135°	718.6	718.0	717.4	716.7	717.4	718.0	718.6	719.3	719.6	719.9	720.1
137.5°	765.9	765.1	764.2	763.4	764.2	765.1	765.9	766.8	767.2	767.4	767.6
140°	798.2	797.4	796.6	795.8	796.6	797.4	798.2	799.1	799.6	799.6	799.6
142.5°	827.6	826.8	826.0	825.1	826.0	826.8	827.6	828.5	828.8	828.6	828.5
145°	871.7	870.8	870.0	869.1	870.0	870.8	871.7	872.5	872.8	872.6	872.3
147.5°	910.9	910.0	909.3	908.4	909.3	910.0	910.9	911.6	911.8	911.3	910.9
150°	935.9	935.3	934.6	934.1	934.6	935.3	935.9	936.5	936.5	935.9	935.3
152.5°	960.5	959.7	958.9	958.1	958.9	959.7	960.5	961.3	961.3	960.5	959.7
155°	992.3	991.7	991.1	990.4	991.1	991.7	992.3	993.0	992.8	991.7	990.7
157.5°	1021.3	1020.3	1019.3	1018.3	1019.3	1020.3	1021.3	1022.3	1022.1	1020.7	1019.3
160°	1038.1	1037.3	1036.4	1035.6	1036.4	1037.3	1038.1	1039.0	1038.8	1037.5	1036.2
162.5°	1053.7	1052.6	1051.7	1050.7	1051.7	1052.6	1053.7	1054.7	1054.4	1053.0	1051.6
165°	1073.6	1072.5	1071.5	1070.4	1071.5	1072.5	1073.6	1074.6	1074.4	1072.9	1071.5
167.5°	1089.9	1088.7	1087.7	1086.6	1087.7	1088.7	1089.9	1090.9	1090.7	1089.3	1087.8
170°	1098.6	1097.4	1096.1	1094.9	1096.1	1097.4	1098.6	1099.9	1099.8	1098.3	1096.8
172.5°	1105.4	1104.2	1102.9	1101.6	1102.9	1104.2	1105.4	1106.6	1106.5	1105.1	1103.6
175°	1112.8	1111.4	1110.2	1109.0	1110.2	1111.4	1112.8	1114.0	1113.9	1112.4	1111.0
177.5°	1115.4	1114.4	1113.3	1112.4	1113.3	1114.4	1115.4	1116.3	1116.3	1115.4	1114.4
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1331.5	1336.9	1345.0	1349.6	1357.4	1362.4	1365.1	1370.1	1372.7	1382.3	1392.4
5°	1257.2	1264.9	1278.4	1290.8	1304.3	1318.2	1328.4	1339.9	1350.5	1368.8	1388.1
7.5°	1172.0	1182.6	1203.4	1223.4	1246.9	1266.6	1284.0	1303.7	1321.4	1347.6	1374.9
10°	1108.1	1126.8	1154.2	1173.0	1203.8	1223.5	1250.9	1272.5	1297.1	1331.7	1362.5
12.5°	1053.0	1075.6	1097.6	1123.7	1151.4	1184.2	1214.4	1242.2	1271.3	1307.1	1343.3
15°	953.1	985.8	1020.0	1046.4	1084.0	1118.6	1153.8	1191.3	1226.9	1269.7	1316.8
17.5°	824.5	862.4	919.9	965.3	1009.3	1044.1	1087.5	1132.9	1174.9	1226.5	1279.0
20°	766.5	794.4	833.3	894.4	960.8	997.9	1042.1	1092.1	1140.3	1196.6	1252.8
22.5°	719.8	744.7	776.0	823.6	897.7	948.2	994.4	1045.2	1101.0	1158.5	1220.9
25°	653.4	670.7	703.4	741.9	792.9	876.1	926.6	977.6	1038.3	1099.9	1171.0
27.5°	603.4	619.0	640.3	677.0	714.9	774.7	855.1	910.7	971.1	1040.4	1114.3
30°	565.3	583.6	607.2	633.2	674.6	721.2	801.5	866.0	925.7	996.9	1075.8
32.5°	537.6	552.0	572.1	598.5	633.0	677.7	741.9	820.2	878.4	953.4	1035.8
35°	492.2	509.1	525.4	550.4	578.3	619.3	667.8	751.5	809.3	883.4	966.1
37.5°	454.8	465.1	483.1	502.9	532.4	562.9	605.0	680.1	742.5	815.3	900.0
40°	426.3	439.2	452.7	474.9	498.9	528.3	569.7	625.5	697.1	768.4	851.1
42.5°	398.6	415.0	429.2	444.0	470.4	499.8	533.5	580.8	654.0	721.4	801.8
45°	365.1	375.8	390.7	407.0	428.7	453.7	483.5	524.9	595.1	653.4	728.9
47.5°	326.3	341.8	351.5	367.5	388.0	411.9	439.7	475.4	532.3	586.9	657.0
50°	299.7	315.7	329.6	344.0	362.3	385.4	408.5	443.1	488.8	546.1	611.5
52.5°	277.0	291.0	304.5	319.0	336.9	358.1	380.0	410.4	449.6	502.2	565.7
55°	245.8	254.5	268.4	282.9	298.8	319.0	340.2	365.6	399.4	443.6	495.1
57.5°	213.9	223.9	235.0	249.5	265.6	281.1	300.1	323.2	349.8	389.8	433.9
60°	195.9	203.5	212.6	227.5	242.5	256.5	274.8	294.0	319.0	353.6	391.2
62.5°	175.8	183.1	191.5	204.4	219.0	231.8	247.8	268.2	289.4	320.9	353.8
65°	142.4	153.0	161.2	172.8	184.7	198.2	210.8	227.1	245.8	270.9	300.2
67.5°	118.1	123.5	131.0	141.6	153.8	165.4	177.3	190.0	206.3	225.6	248.9
70°	107.3	109.2	110.7	120.7	132.3	143.8	155.0	166.9	180.9	196.8	217.0
72.5°	94.6	96.5	98.3	102.6	111.9	123.5	134.9	143.8	157.0	170.2	186.6
75°	75.0	77.9	79.4	81.8	85.2	92.8	103.4	112.1	119.8	129.9	142.9
77.5°	57.1	58.8	60.3	62.9	64.9	68.5	74.5	82.3	89.4	95.4	104.3
80°	45.2	45.7	47.6	48.6	51.5	53.9	56.7	63.1	70.2	72.7	78.9
82.5°	34.0	34.6	36.1	37.0	38.4	40.4	44.1	45.7	51.4	54.6	58.5
85°	18.8	18.3	19.7	19.7	20.6	21.7	22.6	25.0	26.5	30.3	31.3
87.5°	12.3	12.3	11.8	10.9	10.0	9.8	9.5	9.4	9.6	10.3	11.3
90°	32.5	32.9	28.3	23.8	19.1	14.5	10.9	8.5	5.9	3.5	0.9
92.5°	30.0	29.9	28.8	27.7	26.7	25.5	24.1	22.2	20.5	18.6	16.8
95°	60.2	60.2	59.8	59.4	58.9	58.5	57.3	55.1	53.1	51.0	48.9
97.5°	101.2	101.2	100.4	99.6	98.9	98.0	96.7	94.9	93.0	91.2	89.4
100°	129.8	129.8	129.2	128.6	127.9	127.3	126.1	124.5	122.8	121.1	119.4
102.5°	160.8	160.7	159.9	159.1	158.3	157.5	156.4	155.0	153.7	152.4	151.1
105°	207.4	206.9	206.5	206.1	205.7	205.3	204.7	204.2	203.5	202.8	202.3
107.5°	258.1	257.9	257.9	257.9	257.9	257.9	257.5	256.6	255.6	254.7	253.7
110°	292.6	292.6	292.6	292.6	292.6	292.6	291.9	290.7	289.4	288.1	286.9



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	327.4	327.9	328.1	328.2	328.4	328.6	328.0	326.8	325.6	324.2	323.0
115°	379.8	380.0	380.4	380.9	381.3	381.6	381.3	380.0	378.7	377.5	376.3
117.5°	431.0	431.6	432.7	433.9	435.1	436.2	436.0	434.3	432.6	430.9	429.3
120°	464.7	464.7	466.4	468.0	469.7	471.4	471.4	469.7	468.0	466.4	464.7
122.5°	500.3	500.8	502.0	503.1	504.3	505.5	505.0	503.0	501.1	499.0	497.0
125°	552.4	553.1	553.7	554.3	555.0	555.6	555.0	553.1	551.2	549.3	547.4
127.5°	603.1	603.9	604.6	605.4	606.1	606.9	606.1	603.7	601.3	598.9	596.5
130°	637.3	637.7	638.2	638.6	638.9	639.4	638.3	635.6	632.8	630.1	627.4
132.5°	671.5	672.3	672.2	672.2	672.1	672.0	670.9	668.6	666.5	664.2	662.0
135°	720.3	720.5	720.1	719.6	719.3	718.9	717.5	715.2	712.8	710.6	708.3
137.5°	767.8	767.9	767.4	766.9	766.3	765.7	764.5	762.6	760.7	758.8	757.1
140°	799.6	799.6	798.5	797.4	796.4	795.3	793.9	792.0	790.1	788.2	786.4
142.5°	828.3	828.1	827.4	826.7	826.0	825.3	824.0	822.1	820.2	818.3	816.4
145°	872.1	871.9	870.7	869.4	868.2	867.0	865.5	864.1	862.6	861.2	859.7
147.5°	910.4	909.9	909.1	908.2	907.5	906.6	905.3	903.5	901.8	900.0	898.2
150°	934.6	934.1	933.2	932.4	931.5	930.7	929.6	928.4	927.1	925.9	924.6
152.5°	958.9	958.1	957.1	956.1	955.1	954.1	953.0	951.7	950.5	949.2	947.9
155°	989.7	988.5	988.0	987.3	986.7	986.1	985.4	984.9	984.2	983.5	983.0
157.5°	1017.9	1016.4	1016.1	1015.7	1015.3	1014.9	1014.6	1014.1	1013.7	1013.2	1012.9
160°	1035.0	1033.7	1033.5	1033.3	1033.1	1032.9	1032.6	1032.2	1031.7	1031.3	1031.0
162.5°	1050.2	1048.8	1048.6	1048.4	1048.2	1047.9	1047.8	1047.7	1047.6	1047.5	1047.4
165°	1070.0	1068.6	1068.6	1068.6	1068.6	1068.6	1068.7	1068.8	1069.0	1069.3	1069.5
167.5°	1086.4	1084.9	1085.0	1085.0	1085.1	1085.1	1085.4	1086.0	1086.7	1087.3	1087.9
170°	1095.4	1093.9	1094.1	1094.4	1094.6	1094.8	1095.1	1095.8	1096.5	1097.0	1097.7
172.5°	1102.2	1100.7	1100.9	1101.1	1101.4	1101.5	1101.9	1102.6	1103.2	1103.8	1104.5
175°	1109.5	1108.1	1108.4	1108.9	1109.3	1109.7	1110.2	1110.9	1111.4	1112.1	1112.8
177.5°	1113.3	1112.4	1112.7	1113.0	1113.3	1113.7	1114.1	1114.7	1115.1	1115.6	1116.2
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1392.8	1393.9	1401.7	1405.0	1412.0	1414.7	1417.8	1417.0	1417.0	1418.5	1429.4
5°	1395.7	1405.3	1419.8	1433.7	1447.2	1458.8	1466.5	1474.1	1477.1	1491.0	1503.5
7.5°	1390.7	1408.4	1432.3	1453.6	1479.0	1499.0	1515.5	1530.5	1540.7	1560.9	1581.8
10°	1384.2	1409.2	1436.2	1463.6	1498.7	1525.1	1552.1	1572.8	1579.5	1609.9	1627.2
12.5°	1371.1	1404.6	1438.9	1474.3	1508.7	1545.2	1574.8	1595.5	1619.2	1646.4	1678.4
15°	1351.5	1390.0	1434.7	1480.5	1529.5	1573.8	1605.5	1641.6	1667.5	1697.4	1725.3
17.5°	1323.2	1372.8	1429.7	1482.6	1539.4	1587.0	1630.6	1665.3	1683.6	1700.5	1704.7
20°	1301.0	1354.3	1421.3	1483.8	1540.6	1595.4	1638.7	1667.5	1672.4	1672.8	1647.4
22.5°	1276.7	1337.0	1407.0	1471.1	1539.0	1600.1	1633.7	1646.1	1626.9	1594.3	1545.0
25°	1232.2	1301.9	1383.3	1456.3	1530.5	1588.2	1599.8	1578.1	1511.2	1441.0	1352.0
27.5°	1183.8	1262.3	1349.4	1430.8	1509.7	1545.5	1520.5	1442.5	1322.0	1217.3	1090.4
30°	1148.5	1236.5	1322.1	1413.1	1486.2	1501.6	1444.4	1329.4	1188.8	1031.0	904.6
32.5°	1108.1	1200.3	1294.4	1388.5	1449.6	1434.6	1340.0	1198.4	1033.8	878.6	759.0
35°	1050.3	1145.6	1247.1	1341.3	1380.4	1315.4	1173.9	989.7	821.2	676.5	594.2
37.5°	983.6	1087.3	1192.9	1279.5	1276.7	1168.5	975.8	785.6	644.0	558.4	499.8
40°	936.2	1041.1	1155.2	1228.3	1197.0	1056.0	847.3	667.8	564.4	496.1	453.2
42.5°	890.9	996.1	1109.4	1167.5	1113.1	939.8	731.8	591.2	505.9	452.5	417.8
45°	813.6	924.7	1029.6	1061.9	964.7	773.6	591.8	489.7	433.0	393.6	369.5
47.5°	738.0	847.3	943.1	943.7	812.2	627.4	499.2	423.9	375.4	344.9	327.3
50°	691.8	795.8	876.1	863.7	714.4	558.1	446.5	381.5	341.1	317.5	299.3
52.5°	639.9	740.7	810.3	774.7	631.7	491.2	399.2	344.6	311.1	290.6	274.3
55°	564.4	653.8	702.9	649.0	515.3	408.5	337.2	294.5	269.5	252.1	238.2
57.5°	490.1	564.0	594.8	532.2	424.4	338.7	285.3	253.2	228.4	215.9	208.7
60°	443.6	506.6	528.3	459.0	369.0	296.3	252.6	222.7	204.4	196.3	189.1
62.5°	397.8	449.3	458.3	394.7	321.7	259.4	221.8	196.6	184.5	176.6	169.8
65°	330.1	367.1	362.8	311.8	254.5	205.9	178.5	163.1	153.9	142.9	130.8
67.5°	271.7	294.4	280.7	242.5	194.3	160.0	142.1	130.4	119.1	108.7	105.8
70°	234.8	247.8	233.4	198.2	159.3	134.2	119.8	105.8	99.2	96.7	92.4
72.5°	199.3	203.9	188.3	158.2	129.6	111.1	97.1	89.3	85.7	83.6	80.9
75°	149.7	146.3	132.8	109.2	90.0	77.5	73.1	70.2	67.9	65.9	64.5
77.5°	105.1	100.2	88.1	72.8	62.7	56.6	54.1	52.5	51.4	50.4	49.0
80°	78.9	75.5	63.5	51.9	47.6	44.8	43.3	41.4	41.4	40.4	38.9
82.5°	57.8	54.0	43.5	38.1	35.7	33.9	32.9	31.8	31.4	31.6	30.5
85°	30.3	24.5	21.7	20.6	19.2	18.3	18.8	17.8	17.8	17.8	17.3
87.5°	9.9	8.5	8.6	8.8	9.8	10.7	11.3	12.3	13.5	13.0	13.4
90°	3.5	5.9	8.5	10.9	14.5	19.1	23.8	28.3	32.9	32.5	32.0
92.5°	18.6	20.5	22.2	24.1	25.5	26.7	27.7	28.8	29.9	30.0	30.1
95°	51.0	53.1	55.1	57.3	58.5	58.9	59.4	59.8	60.2	60.2	60.2
97.5°	91.2	93.0	94.9	96.7	98.0	98.9	99.6	100.4	101.2	101.2	101.2
100°	121.1	122.8	124.5	126.1	127.3	127.9	128.6	129.2	129.8	129.8	129.8
102.5°	152.4	153.7	155.0	156.4	157.5	158.3	159.1	159.9	160.7	160.8	161.0
105°	202.8	203.5	204.2	204.7	205.3	205.7	206.1	206.5	206.9	207.4	207.7
107.5°	254.7	255.6	256.6	257.5	257.9	257.9	257.9	257.9	257.9	258.1	258.3
110°	288.1	289.4	290.7	291.9	292.6	292.6	292.6	292.6	292.6	292.6	292.6





TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	324.2	325.6	326.8	328.0	328.6	328.4	328.2	328.1	327.9	327.4	326.9
115°	377.5	378.7	380.0	381.3	381.6	381.3	380.9	380.4	380.0	379.8	379.6
117.5°	430.9	432.6	434.3	436.0	436.2	435.1	433.9	432.7	431.6	431.0	430.6
120°	466.4	468.0	469.7	471.4	471.4	469.7	468.0	466.4	464.7	464.7	464.7
122.5°	499.0	501.1	503.0	505.0	505.5	504.3	503.1	502.0	500.8	500.3	499.7
125°	549.3	551.2	553.1	555.0	555.6	555.0	554.3	553.7	553.1	552.4	551.9
127.5°	598.9	601.3	603.7	606.1	606.9	606.1	605.4	604.6	603.9	603.1	602.4
130°	630.1	632.8	635.6	638.3	639.4	638.9	638.6	638.2	637.7	637.3	636.9
132.5°	664.2	666.5	668.6	670.9	672.0	672.1	672.2	672.2	672.3	671.5	670.5
135°	710.6	712.8	715.2	717.5	718.9	719.3	719.6	720.1	720.5	720.3	720.1
137.5°	758.8	760.7	762.6	764.5	765.7	766.3	766.9	767.4	767.9	767.8	767.6
140°	788.2	790.1	792.0	793.9	795.3	796.4	797.4	798.5	799.6	799.6	799.6
142.5°	818.3	820.2	822.1	824.0	825.3	826.0	826.7	827.4	828.1	828.3	828.5
145°	861.2	862.6	864.1	865.5	867.0	868.2	869.4	870.7	871.9	872.1	872.3
147.5°	900.0	901.8	903.5	905.3	906.6	907.5	908.2	909.1	909.9	910.4	910.9
150°	925.9	927.1	928.4	929.6	930.7	931.5	932.4	933.2	934.1	934.6	935.3
152.5°	949.2	950.5	951.7	953.0	954.1	955.1	956.1	957.1	958.1	958.9	959.7
155°	983.5	984.2	984.9	985.4	986.1	986.7	987.3	988.0	988.5	989.7	990.7
157.5°	1013.2	1013.7	1014.1	1014.6	1014.9	1015.3	1015.7	1016.1	1016.4	1017.9	1019.3
160°	1031.3	1031.7	1032.2	1032.6	1032.9	1033.1	1033.3	1033.5	1033.7	1035.0	1036.2
162.5°	1047.5	1047.6	1047.7	1047.8	1047.9	1048.2	1048.4	1048.6	1048.8	1050.2	1051.6
165°	1069.3	1069.0	1068.8	1068.7	1068.6	1068.6	1068.6	1068.6	1068.6	1070.0	1071.5
167.5°	1087.3	1086.7	1086.0	1085.4	1085.1	1085.1	1085.0	1085.0	1084.9	1086.4	1087.8
170°	1097.0	1096.5	1095.8	1095.1	1094.8	1094.6	1094.4	1094.1	1093.9	1095.4	1096.8
172.5°	1103.8	1103.2	1102.6	1101.9	1101.5	1101.4	1101.1	1100.9	1100.7	1102.2	1103.6
175°	1112.1	1111.4	1110.9	1110.2	1109.7	1109.3	1108.9	1108.4	1108.1	1109.5	1111.0
177.5°	1115.6	1115.1	1114.7	1114.1	1113.7	1113.3	1113.0	1112.7	1112.4	1113.3	1114.4
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1433.1	1438.1	1440.5	1440.5	1443.2	1442.0	1440.9
5°	1515.5	1524.7	1526.6	1535.3	1541.5	1539.5	1540.6
7.5°	1597.4	1612.1	1626.6	1633.3	1634.4	1638.2	1639.6
10°	1647.8	1659.9	1682.5	1679.1	1695.9	1705.6	1689.7
12.5°	1696.4	1712.6	1728.2	1732.6	1742.2	1745.2	1739.0
15°	1740.2	1748.9	1749.8	1747.5	1750.3	1747.9	1738.8
17.5°	1699.2	1685.2	1656.7	1643.2	1632.6	1616.7	1610.4
20°	1631.4	1590.1	1542.0	1522.8	1500.2	1455.9	1466.5
22.5°	1485.3	1438.0	1390.0	1333.8	1306.9	1265.0	1262.4
25°	1257.6	1176.4	1086.8	1024.4	987.8	945.9	927.7
27.5°	977.8	875.4	802.1	765.0	731.2	698.0	696.6
30°	793.8	716.9	660.1	628.4	607.7	593.7	596.6
32.5°	669.1	616.4	578.2	551.8	536.5	525.9	525.8
35°	547.1	511.0	486.4	475.3	464.3	456.6	457.0
37.5°	468.2	446.5	432.8	420.6	413.7	409.9	407.8
40°	427.7	409.9	399.4	392.1	386.3	381.1	380.1
42.5°	395.8	381.1	370.4	364.8	359.4	355.6	354.7
45°	351.2	339.2	329.6	323.3	320.9	317.5	317.5
47.5°	312.5	300.6	293.1	289.2	285.0	282.8	282.7
50°	286.3	277.1	270.4	268.0	264.6	263.2	262.7
52.5°	262.8	256.0	251.2	249.5	248.1	246.2	246.6
55°	230.9	227.1	225.2	223.8	221.3	218.4	220.4
57.5°	204.1	200.9	195.7	191.1	188.9	186.9	187.7
60°	185.2	178.5	171.7	166.5	165.0	160.7	160.7
62.5°	161.4	151.9	143.6	140.7	139.2	137.2	136.9
65°	124.1	120.3	118.4	116.4	115.5	115.5	114.5
67.5°	102.8	101.3	99.2	98.7	97.7	97.5	97.2
70°	91.0	89.0	88.0	87.6	86.6	87.1	85.7
72.5°	79.4	77.9	77.7	76.4	75.8	75.9	74.8
75°	62.6	62.6	62.0	61.5	60.6	60.1	60.6
77.5°	48.1	48.2	47.3	47.2	47.1	47.2	46.8
80°	38.5	38.9	38.5	38.0	37.5	38.0	37.5
82.5°	30.4	29.7	29.6	29.5	29.4	29.1	29.0
85°	17.3	17.8	17.3	16.9	16.9	16.9	17.3
87.5°	12.9	12.8	12.8	12.8	12.8	12.9	12.5
90°	31.7	31.3	31.1	31.4	31.6	31.8	32.0
92.5°	30.2	30.3	30.3	30.3	30.3	30.4	30.4
95°	60.2	60.2	59.9	59.6	59.2	58.7	58.3
97.5°	101.2	101.2	101.2	101.1	101.1	101.0	101.0
100°	129.8	129.8	129.7	129.5	129.3	129.0	128.8
102.5°	161.2	161.4	161.3	161.1	160.9	160.7	160.5
105°	208.2	208.6	208.8	208.8	208.8	208.8	208.8
107.5°	258.4	258.5	258.2	257.2	256.3	255.3	254.3
110°	292.6	292.6	292.2	291.6	291.0	290.3	289.7



TEST NUMBER: P331694-830

CATALOG NUMBER: S122RDIP-S675D925U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	326.4	325.9	325.4	325.0	324.5	324.0	323.6
115°	379.4	379.2	378.7	378.1	377.5	376.8	376.3
117.5°	430.1	429.5	429.0	428.4	427.7	427.1	426.5
120°	464.7	464.7	464.4	463.7	463.1	462.5	461.8
122.5°	499.3	498.8	498.3	497.9	497.4	496.9	496.4
125°	551.2	550.5	550.2	550.0	549.7	549.5	549.3
127.5°	601.6	600.9	600.1	599.5	598.8	598.1	597.5
130°	636.5	636.0	635.5	634.6	633.8	632.9	632.1
132.5°	669.6	668.6	667.9	667.2	666.6	665.9	665.2
135°	719.9	719.6	719.3	718.6	718.0	717.4	716.7
137.5°	767.4	767.2	766.8	765.9	765.1	764.2	763.4
140°	799.6	799.6	799.1	798.2	797.4	796.6	795.8
142.5°	828.6	828.8	828.5	827.6	826.8	826.0	825.1
145°	872.6	872.8	872.5	871.7	870.8	870.0	869.1
147.5°	911.3	911.8	911.6	910.9	910.0	909.3	908.4
150°	935.9	936.5	936.5	935.9	935.3	934.6	934.1
152.5°	960.5	961.3	961.3	960.5	959.7	958.9	958.1
155°	991.7	992.8	993.0	992.3	991.7	991.1	990.4
157.5°	1020.7	1022.1	1022.3	1021.3	1020.3	1019.3	1018.3
160°	1037.5	1038.8	1039.0	1038.1	1037.3	1036.4	1035.6
162.5°	1053.0	1054.4	1054.7	1053.7	1052.6	1051.7	1050.7
165°	1072.9	1074.4	1074.6	1073.6	1072.5	1071.5	1070.4
167.5°	1089.3	1090.7	1090.9	1089.9	1088.7	1087.7	1086.6
170°	1098.3	1099.8	1099.9	1098.6	1097.4	1096.1	1094.9
172.5°	1105.1	1106.5	1106.6	1105.4	1104.2	1102.9	1101.6
175°	1112.4	1113.9	1114.0	1112.8	1111.4	1110.2	1109.0
177.5°	1115.4	1116.3	1116.3	1115.4	1114.4	1113.3	1112.4
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7

(END OF REPORT)