

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331732-830

Luminaire Tested: **S122RDIP-S865D1080U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331732-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D1080U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6903.8 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331732-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331732-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23
5	68	57	49	43	62	52	45	40	44	38	34	36	32	29	28	26	23	20
6	63	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22315	22315	22315
5°	22400	22034	22156
10°	22228	21674	21489
15°	21972	21031	20425
20°	21618	20113	19105
25°	21257	19073	17826
30°	20752	18000	16183
35°	20262	16837	14741
40°	19770	15633	13076
45°	19192	14280	11565
50°	18600	12913	10083
55°	17990	11443	8659
60°	17286	9894	7188
65°	16485	8313	6548
70°	15526	6850	6019
75°	14361	6245	5614
80°	12673	5579	5114
85°	9967	4409	4409



TEST NUMBER: P331732-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.4	1.9
10°-20°	355.2	5.1
20°-30°	498.8	7.2
30°-40°	543.9	7.9
40°-50°	500.1	7.2
50°-60°	392.8	5.7
60°-70°	256.1	3.7
70°-80°	132.0	1.9
80°-90°	37.7	0.5
90°-100°	46.2	0.7
100°-110°	169.4	2.5
110°-120°	452.8	6.6
120°-130°	747.4	10.8
130°-140°	794.9	11.5
140°-150°	738.8	10.7
150°-160°	594.0	8.6
160°-170°	382.8	5.5
170°-180°	131.8	1.9
0°-30°	983.3	14.2
0°-40°	1527.2	22.1
0°-60°	2420.1	35.1
0°-90°	2845.9	41.2
90°-120°	668.4	9.7
90°-150°	2949.4	42.7
90°-180°	4058.0	58.8
0°-180°	6903.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1382	1382	1382	1382	1382	
5°	1382	1375	1360	1370	1367	131
15°	1314	1299	1258	1235	1222	370
25°	1193	1151	1071	1021	1001	548
35°	1028	962	854	778	748	643
45°	840	754	625	540	506	649
55°	639	539	406	334	308	571
65°	432	330	218	177	171	428
75°	230	145	100	92	90	244
85°	54	29	24	24	24	63
90°	1	12	20	25	27	5
95°	65	34	39	44	43	80
105°	305	318	61	72	76	325
115°	576	594	618	176	82	567
125°	815	828	847	853	857	726
135°	1008	1024	1033	1042	1041	778
145°	1169	1169	1185	1192	1187	731
155°	1288	1280	1290	1296	1288	593
165°	1357	1351	1354	1360	1354	383
175°	1388	1381	1383	1389	1380	132
180°	1385	1385	1385	1385	1385	



TEST NUMBER: P331732-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1
2.5°	1387.0	1385.9	1384.8	1383.7	1382.6	1380.8	1378.4	1375.9	1373.5	1371.0	1373.3
5°	1382.1	1380.6	1379.2	1377.8	1376.5	1373.9	1370.4	1366.8	1363.1	1359.5	1362.0
7.5°	1367.7	1366.0	1364.3	1362.6	1360.8	1357.9	1353.7	1349.4	1345.2	1341.0	1341.7
10°	1355.8	1353.8	1351.9	1349.9	1347.9	1344.3	1338.7	1333.1	1327.6	1322.0	1321.2
12.5°	1340.8	1338.3	1336.0	1333.6	1331.2	1326.4	1319.3	1312.2	1305.0	1298.0	1296.5
15°	1314.5	1311.5	1308.3	1305.3	1302.2	1296.0	1286.6	1277.1	1267.6	1258.2	1252.9
17.5°	1282.2	1277.5	1272.9	1268.2	1263.6	1255.2	1243.0	1230.9	1218.8	1206.6	1200.4
20°	1258.2	1252.6	1247.1	1241.5	1236.0	1226.2	1212.3	1198.4	1184.6	1170.6	1163.7
22.5°	1232.2	1226.0	1219.7	1213.5	1207.3	1196.4	1180.6	1165.0	1149.3	1133.6	1124.6
25°	1193.2	1184.3	1175.4	1166.5	1157.6	1144.0	1125.6	1107.3	1088.9	1070.6	1059.2
27.5°	1146.1	1136.4	1126.8	1117.1	1107.5	1092.3	1071.6	1050.9	1030.2	1009.6	996.3
30°	1113.1	1102.6	1092.0	1081.5	1070.9	1054.5	1032.3	1010.0	987.8	965.5	951.4
32.5°	1081.1	1068.7	1056.4	1044.1	1031.7	1014.3	991.6	968.8	946.2	923.5	907.4
35°	1028.0	1013.9	999.8	985.5	971.4	952.1	927.6	903.1	878.7	854.2	836.7
37.5°	975.1	959.5	944.0	928.3	912.8	891.9	865.9	839.8	813.8	787.7	768.4
40°	938.0	921.3	904.7	888.0	871.3	849.5	822.6	795.6	768.6	741.7	721.9
42.5°	900.0	882.4	864.9	847.3	829.7	807.0	779.2	751.3	723.5	695.6	675.2
45°	840.5	821.8	803.2	784.6	766.0	742.1	712.9	683.7	654.5	625.4	605.6
47.5°	782.4	762.7	743.0	723.2	703.5	678.5	648.5	618.3	588.1	558.1	538.5
50°	740.5	720.7	701.0	681.2	661.5	636.3	605.8	575.1	544.6	514.1	494.8
52.5°	699.4	678.7	658.2	637.5	616.9	591.6	561.8	531.8	501.9	472.0	453.5
55°	639.1	617.5	595.8	574.1	552.4	526.5	496.5	466.5	436.5	406.5	389.8
57.5°	577.3	555.1	532.8	510.6	488.4	462.9	433.9	405.1	376.3	347.4	332.2
60°	535.3	513.0	490.9	468.6	446.4	420.9	392.3	363.6	335.1	306.4	292.3
62.5°	494.3	472.0	449.8	427.5	405.3	380.6	353.3	326.0	298.7	271.4	257.9
65°	431.5	409.0	386.4	363.9	341.5	317.6	292.7	267.7	242.6	217.6	208.2
67.5°	371.0	348.6	326.3	303.9	281.5	259.1	236.7	214.1	191.6	169.1	164.8
70°	328.9	307.3	285.6	263.9	242.2	221.8	202.6	183.4	164.3	145.1	142.3
72.5°	288.9	268.2	247.3	226.6	205.8	187.7	172.3	156.8	141.5	126.1	123.8
75°	230.2	210.7	191.2	171.7	152.3	137.9	128.4	118.9	109.5	100.1	98.1
77.5°	172.4	155.2	138.2	121.1	104.1	93.3	88.7	84.2	79.6	75.0	73.9
80°	136.3	122.2	108.0	93.8	79.6	71.2	68.3	65.6	62.8	60.0	58.9
82.5°	103.3	92.3	81.2	70.1	59.1	52.6	50.7	48.8	46.9	45.1	44.4
85°	53.8	48.0	42.1	36.3	30.4	27.1	26.3	25.4	24.6	23.8	23.8
87.5°	16.2	14.9	13.7	12.3	11.0	10.6	10.9	11.3	11.7	12.0	12.0
90°	1.0	3.5	5.9	8.4	10.8	12.9	14.7	16.5	18.3	20.1	21.1
92.5°	20.3	20.0	19.8	19.6	19.3	19.7	20.5	21.5	22.3	23.3	23.8
95°	65.1	57.8	50.4	43.1	35.7	32.8	34.4	36.0	37.5	39.1	40.2
97.5°	129.2	108.6	87.8	67.1	46.5	37.9	41.5	45.1	48.7	52.3	53.2
100°	177.4	146.8	116.3	85.9	55.3	41.9	45.7	49.6	53.3	57.1	58.9
102.5°	230.3	223.8	217.4	210.8	204.4	185.4	153.7	122.1	90.4	58.7	61.1
105°	304.6	311.3	317.9	324.6	331.3	304.3	243.5	182.7	121.9	61.1	63.5
107.5°	389.4	394.7	400.1	405.5	410.9	377.2	304.3	231.4	158.4	85.6	83.0
110°	443.8	448.6	453.3	457.9	462.6	432.7	368.3	304.1	239.7	175.3	153.1



TEST NUMBER: P331732-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	495.2	499.4	503.4	507.6	511.7	505.9	489.9	474.1	458.2	442.2	361.1
115°	576.2	579.9	583.7	587.5	591.3	596.0	601.5	607.1	612.7	618.2	515.1
117.5°	648.5	652.7	657.0	661.2	665.4	669.4	673.3	677.1	680.9	684.8	659.8
120°	701.3	704.7	708.0	711.4	714.7	718.4	722.5	726.4	730.5	734.4	737.1
122.5°	746.3	749.8	753.3	756.9	760.3	764.3	768.6	773.0	777.4	781.7	783.3
125°	814.6	817.5	820.4	823.3	826.1	829.7	834.0	838.2	842.4	846.7	848.2
127.5°	876.6	879.8	883.0	886.2	889.4	892.5	895.7	898.8	902.0	905.2	907.5
130°	915.8	919.4	922.9	926.5	930.0	933.0	935.5	937.9	940.4	942.8	945.3
132.5°	955.8	958.9	962.0	965.0	968.0	970.7	973.2	975.6	978.1	980.5	982.6
135°	1008.0	1011.5	1015.1	1018.7	1022.2	1025.0	1027.0	1029.0	1031.0	1033.0	1035.3
137.5°	1060.6	1063.2	1065.6	1068.2	1070.6	1073.0	1075.3	1077.6	1079.9	1082.1	1084.3
140°	1095.1	1096.9	1098.7	1100.5	1102.3	1104.4	1106.8	1109.3	1111.7	1114.2	1116.2
142.5°	1124.0	1125.6	1127.2	1128.8	1130.4	1132.7	1135.4	1138.2	1141.0	1143.9	1145.7
145°	1169.3	1169.0	1168.8	1168.7	1168.4	1170.2	1173.9	1177.7	1181.6	1185.3	1186.8
147.5°	1208.8	1208.0	1207.1	1206.3	1205.4	1206.8	1210.6	1214.3	1218.0	1221.8	1222.9
150°	1234.4	1232.8	1231.3	1229.7	1228.2	1229.2	1232.8	1236.3	1239.9	1243.4	1244.8
152.5°	1256.0	1254.3	1252.5	1250.8	1249.2	1249.9	1253.3	1256.7	1260.1	1263.5	1264.8
155°	1287.5	1285.5	1283.6	1281.5	1279.5	1279.9	1282.5	1285.2	1287.9	1290.5	1291.8
157.5°	1312.2	1310.5	1308.8	1307.1	1305.4	1305.5	1307.4	1309.2	1311.1	1313.0	1314.5
160°	1326.6	1325.3	1323.9	1322.6	1321.3	1321.3	1322.6	1323.9	1325.3	1326.6	1327.9
162.5°	1339.4	1338.1	1336.7	1335.4	1334.1	1334.0	1335.1	1336.3	1337.5	1338.6	1340.1
165°	1356.7	1355.3	1354.0	1352.6	1351.3	1350.9	1351.6	1352.4	1353.0	1353.7	1355.2
167.5°	1369.5	1368.2	1366.8	1365.5	1364.1	1363.8	1364.4	1365.0	1365.6	1366.3	1367.8
170°	1376.7	1375.4	1374.0	1372.7	1371.4	1370.9	1371.4	1371.8	1372.2	1372.7	1374.2
172.5°	1381.5	1380.2	1378.8	1377.5	1376.2	1375.7	1376.2	1376.6	1377.1	1377.5	1379.0
175°	1387.7	1386.2	1384.6	1383.1	1381.5	1380.9	1381.4	1381.9	1382.2	1382.7	1384.3
177.5°	1388.7	1387.5	1386.2	1385.0	1383.7	1383.2	1383.4	1383.6	1383.7	1383.9	1385.2
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331732-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1
2.5°	1375.5	1377.7	1379.9	1380.8	1380.4	1379.9	1379.5	1379.0
5°	1364.5	1367.0	1369.5	1370.4	1369.5	1368.7	1367.8	1367.0
7.5°	1342.5	1343.1	1343.9	1343.5	1342.1	1340.7	1339.2	1337.8
10°	1320.3	1319.5	1318.6	1317.4	1315.7	1314.1	1312.4	1310.7
12.5°	1295.0	1293.5	1291.9	1289.9	1287.0	1284.3	1281.5	1278.7
15°	1247.6	1242.4	1237.1	1233.0	1230.3	1227.5	1224.7	1221.9
17.5°	1194.1	1187.8	1181.6	1176.0	1171.2	1166.5	1161.7	1156.9
20°	1156.8	1149.8	1142.8	1136.3	1130.2	1124.1	1117.9	1111.9
22.5°	1115.8	1106.8	1097.9	1091.1	1086.6	1081.9	1077.4	1072.9
25°	1047.8	1036.4	1025.0	1017.2	1013.0	1008.9	1004.8	1000.6
27.5°	983.0	969.7	956.4	946.5	939.9	933.2	926.6	920.0
30°	937.2	923.0	908.8	898.0	890.5	883.0	875.5	868.0
32.5°	891.2	875.0	858.8	847.2	840.2	833.1	826.0	819.0
35°	819.2	801.7	784.2	772.4	766.3	760.2	754.0	747.9
37.5°	749.1	729.8	710.6	697.4	690.4	683.3	676.4	669.4
40°	702.2	682.5	662.7	649.2	642.1	634.8	627.5	620.4
42.5°	654.9	634.4	614.1	600.3	593.3	586.4	579.3	572.3
45°	585.9	566.2	546.4	533.2	526.5	519.9	513.2	506.5
47.5°	518.8	499.2	479.6	466.7	460.7	454.6	448.6	442.5
50°	475.7	456.5	437.3	424.8	419.0	413.1	407.3	401.4
52.5°	435.0	416.5	397.9	386.1	380.6	375.2	369.9	364.5
55°	373.2	356.5	339.8	328.8	323.5	318.2	312.9	307.6
57.5°	316.9	301.6	286.3	276.4	272.0	267.5	263.1	258.6
60°	278.1	263.9	249.7	240.4	235.9	231.5	227.1	222.6
62.5°	244.4	230.9	217.4	209.2	206.6	204.0	201.2	198.6
65°	198.7	189.3	179.8	174.7	173.8	173.1	172.2	171.4
67.5°	160.4	156.1	151.7	149.1	148.3	147.3	146.5	145.6
70°	139.5	136.8	133.9	132.1	130.9	129.8	128.7	127.5
72.5°	121.4	119.0	116.7	115.3	114.5	113.9	113.2	112.5
75°	96.1	94.3	92.3	91.1	90.9	90.6	90.3	90.0
77.5°	72.9	71.7	70.6	69.8	69.4	68.9	68.5	68.1
80°	57.8	56.7	55.6	55.0	55.0	55.0	55.0	55.0
82.5°	43.7	43.0	42.3	42.0	42.0	42.0	42.0	42.0
85°	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.8
87.5°	12.0	12.0	12.0	12.1	12.2	12.3	12.3	12.4
90°	22.2	23.4	24.5	25.3	25.7	26.2	26.6	27.1
92.5°	24.4	25.0	25.5	26.0	26.3	26.5	26.8	27.1
95°	41.3	42.4	43.5	44.0	43.7	43.5	43.3	43.1
97.5°	54.1	55.0	55.9	56.5	56.7	57.0	57.2	57.5
100°	60.7	62.5	64.3	65.3	65.8	66.3	66.7	67.1
102.5°	63.3	65.7	68.0	69.5	70.0	70.7	71.4	71.9
105°	66.0	68.4	70.9	72.6	73.5	74.4	75.2	76.2
107.5°	80.6	78.0	75.6	74.8	75.7	76.5	77.5	78.3
110°	130.8	108.6	86.2	75.6	76.4	77.4	78.2	79.2



TEST NUMBER: P331732-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	279.8	198.6	117.3	77.1	77.9	78.5	79.3	79.9
115°	412.0	309.0	205.9	146.3	130.3	114.2	98.2	82.2
117.5°	634.9	609.9	585.0	546.2	493.5	440.8	388.1	335.5
120°	739.8	742.4	745.2	731.4	701.3	671.3	641.2	611.2
122.5°	784.9	786.6	788.2	786.0	780.2	774.4	768.5	762.7
125°	849.8	851.3	852.9	854.0	854.7	855.4	856.0	856.7
127.5°	909.7	912.0	914.3	915.5	915.6	915.8	915.9	916.0
130°	947.7	950.2	952.6	953.8	953.6	953.3	953.1	952.9
132.5°	984.7	986.8	988.9	989.9	989.6	989.4	989.2	988.9
135°	1037.5	1039.7	1041.9	1042.8	1042.4	1041.9	1041.5	1041.0
137.5°	1086.5	1088.6	1090.8	1091.6	1090.8	1090.1	1089.3	1088.5
140°	1118.2	1120.2	1122.2	1122.7	1121.5	1120.4	1119.3	1118.2
142.5°	1147.5	1149.3	1151.1	1151.5	1150.4	1149.2	1148.2	1147.1
145°	1188.5	1190.0	1191.6	1191.8	1190.7	1189.6	1188.5	1187.3
147.5°	1224.1	1225.3	1226.4	1226.5	1225.6	1224.6	1223.7	1222.8
150°	1246.1	1247.5	1248.8	1248.9	1247.7	1246.7	1245.6	1244.4
152.5°	1266.1	1267.5	1268.9	1268.8	1267.2	1265.8	1264.3	1262.9
155°	1293.2	1294.6	1295.9	1295.6	1293.8	1292.1	1290.3	1288.5
157.5°	1316.0	1317.5	1319.0	1318.9	1317.2	1315.4	1313.7	1311.9
160°	1329.3	1330.6	1331.9	1331.8	1330.3	1328.7	1327.2	1325.6
162.5°	1341.6	1343.1	1344.7	1344.4	1342.6	1340.7	1338.7	1336.8
165°	1356.8	1358.3	1359.9	1359.9	1358.3	1356.8	1355.2	1353.7
167.5°	1369.4	1370.9	1372.5	1372.2	1370.3	1368.3	1366.3	1364.2
170°	1375.8	1377.3	1378.9	1378.7	1376.7	1374.7	1372.7	1370.6
172.5°	1380.6	1382.1	1383.7	1383.6	1381.5	1379.5	1377.5	1375.5
175°	1385.8	1387.4	1388.9	1388.6	1386.4	1384.1	1382.0	1379.7
177.5°	1386.4	1387.6	1388.9	1388.7	1387.1	1385.5	1383.9	1382.3
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7

(END OF REPORT)