

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331734-830

Luminaire Tested: **S122RDIP-S865D1080U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331734-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D1080U830-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6809.6 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331734-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331734-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31
3	81	71	64	59	73	66	60	55	55	50	46	44	41	39	35	33	31	27
4	74	63	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27	23
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24	20
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21	18
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	15
9	50	38	31	26	46	35	29	25	30	25	22	25	21	18	20	17	15	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22315	22315	22315
5°	22400	22034	22156
10°	22228	21674	21489
15°	21972	21031	20425
20°	21618	20113	19105
25°	21257	19073	17826
30°	20752	18000	16183
35°	20262	16837	14741
40°	19770	15633	13076
45°	19192	14280	11565
50°	18600	12913	10083
55°	17990	11443	8659
60°	17286	9894	7188
65°	16485	8313	6548
70°	15526	6850	6019
75°	14361	6245	5614
80°	12673	5579	5114
85°	9967	4409	4409



TEST NUMBER: P331734-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.4	1.9
10°-20°	355.2	5.2
20°-30°	498.8	7.3
30°-40°	543.9	8.0
40°-50°	500.1	7.3
50°-60°	392.8	5.8
60°-70°	256.1	3.8
70°-80°	132.0	1.9
80°-90°	39.4	0.6
90°-100°	227.7	3.3
100°-110°	772.5	11.3
110°-120°	820.7	12.1
120°-130°	675.6	9.9
130°-140°	542.5	8.0
140°-150°	410.0	6.0
150°-160°	288.1	4.2
160°-170°	169.6	2.5
170°-180°	55.2	0.8
0°-30°	983.3	14.4
0°-40°	1527.2	22.4
0°-60°	2420.1	35.5
0°-90°	2847.6	41.8
90°-120°	1820.9	26.7
90°-150°	3449.0	50.6
90°-180°	3962.0	58.2
0°-180°	6809.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1382	1382	1382	1382	1382	
5°	1382	1375	1360	1370	1367	131
15°	1314	1299	1258	1235	1222	370
25°	1193	1151	1071	1021	1001	548
35°	1028	962	854	778	748	643
45°	840	754	625	540	506	649
55°	639	539	406	334	308	571
65°	432	330	218	177	171	428
75°	230	145	100	92	90	244
85°	54	29	24	24	24	63
90°	1	15	37	36	36	4
95°	38	94	429	162	125	41
105°	134	202	811	1450	1234	142
115°	235	297	679	1401	1624	233
125°	328	389	653	1135	1317	292
135°	385	460	645	954	1092	298
145°	440	506	642	797	872	276
155°	500	540	623	705	732	230
165°	545	562	597	633	643	154
175°	568	569	574	581	579	54
180°	569	569	569	569	569	



TEST NUMBER: P331734-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1
2.5°	1387.0	1385.9	1384.8	1383.7	1382.6	1380.8	1378.4	1375.9	1373.5	1371.0	1373.3
5°	1382.1	1380.6	1379.2	1377.8	1376.5	1373.9	1370.4	1366.8	1363.1	1359.5	1362.0
7.5°	1367.7	1366.0	1364.3	1362.6	1360.8	1357.9	1353.7	1349.4	1345.2	1341.0	1341.7
10°	1355.8	1353.8	1351.9	1349.9	1347.9	1344.3	1338.7	1333.1	1327.6	1322.0	1321.2
12.5°	1340.8	1338.3	1336.0	1333.6	1331.2	1326.4	1319.3	1312.2	1305.0	1298.0	1296.5
15°	1314.5	1311.5	1308.3	1305.3	1302.2	1296.0	1286.6	1277.1	1267.6	1258.2	1252.9
17.5°	1282.2	1277.5	1272.9	1268.2	1263.6	1255.2	1243.0	1230.9	1218.8	1206.6	1200.4
20°	1258.2	1252.6	1247.1	1241.5	1236.0	1226.2	1212.3	1198.4	1184.6	1170.6	1163.7
22.5°	1232.2	1226.0	1219.7	1213.5	1207.3	1196.4	1180.6	1165.0	1149.3	1133.6	1124.6
25°	1193.2	1184.3	1175.4	1166.5	1157.6	1144.0	1125.6	1107.3	1088.9	1070.6	1059.2
27.5°	1146.1	1136.4	1126.8	1117.1	1107.5	1092.3	1071.6	1050.9	1030.2	1009.6	996.3
30°	1113.1	1102.6	1092.0	1081.5	1070.9	1054.5	1032.3	1010.0	987.8	965.5	951.4
32.5°	1081.1	1068.7	1056.4	1044.1	1031.7	1014.3	991.6	968.8	946.2	923.5	907.4
35°	1028.0	1013.9	999.8	985.5	971.4	952.1	927.6	903.1	878.7	854.2	836.7
37.5°	975.1	959.5	944.0	928.3	912.8	891.9	865.9	839.8	813.8	787.7	768.4
40°	938.0	921.3	904.7	888.0	871.3	849.5	822.6	795.6	768.6	741.7	721.9
42.5°	900.0	882.4	864.9	847.3	829.7	807.0	779.2	751.3	723.5	695.6	675.2
45°	840.5	821.8	803.2	784.6	766.0	742.1	712.9	683.7	654.5	625.4	605.6
47.5°	782.4	762.7	743.0	723.2	703.5	678.5	648.5	618.3	588.1	558.1	538.5
50°	740.5	720.7	701.0	681.2	661.5	636.3	605.8	575.1	544.6	514.1	494.8
52.5°	699.4	678.7	658.2	637.5	616.9	591.6	561.8	531.8	501.9	472.0	453.5
55°	639.1	617.5	595.8	574.1	552.4	526.5	496.5	466.5	436.5	406.5	389.8
57.5°	577.3	555.1	532.8	510.6	488.4	462.9	433.9	405.1	376.3	347.4	332.2
60°	535.3	513.0	490.9	468.6	446.4	420.9	392.3	363.6	335.1	306.4	292.3
62.5°	494.3	472.0	449.8	427.5	405.3	380.6	353.3	326.0	298.7	271.4	257.9
65°	431.5	409.0	386.4	363.9	341.5	317.6	292.7	267.7	242.6	217.6	208.2
67.5°	371.0	348.6	326.3	303.9	281.5	259.1	236.7	214.1	191.6	169.1	164.8
70°	328.9	307.3	285.6	263.9	242.2	221.8	202.6	183.4	164.3	145.1	142.3
72.5°	288.9	268.2	247.3	226.6	205.8	187.7	172.3	156.8	141.5	126.1	123.8
75°	230.2	210.7	191.2	171.7	152.3	137.9	128.4	118.9	109.5	100.1	98.1
77.5°	172.4	155.2	138.2	121.1	104.1	93.3	88.7	84.2	79.6	75.0	73.9
80°	136.3	122.2	108.0	93.8	79.6	71.2	68.3	65.6	62.8	60.0	58.9
82.5°	103.3	92.3	81.2	70.1	59.1	52.6	50.7	48.8	46.9	45.1	44.4
85°	53.8	48.0	42.1	36.3	30.4	27.1	26.3	25.4	24.6	23.8	23.8
87.5°	16.2	15.1	14.2	12.8	11.5	11.3	12.3	13.9	15.3	15.5	15.0
90°	1.1	4.3	8.8	10.9	13.1	16.4	21.9	29.6	36.1	37.2	36.1
92.5°	13.4	19.2	27.1	32.0	39.4	49.7	74.5	109.2	140.3	142.3	120.3
95°	38.4	42.7	53.6	63.5	81.1	107.3	157.7	252.9	379.9	429.2	375.6
97.5°	62.4	68.3	79.9	94.8	115.0	144.8	208.0	340.7	551.9	732.7	768.6
100°	84.3	87.6	97.5	115.0	136.9	167.5	225.6	359.1	595.6	865.0	1022.7
102.5°	104.4	106.9	116.7	134.2	157.0	187.7	241.3	360.1	579.0	869.4	1117.3
105°	133.6	138.0	145.6	162.0	186.2	216.8	268.2	365.7	546.4	811.3	1102.6
107.5°	165.1	168.6	176.1	191.1	215.1	245.9	295.9	380.8	530.2	749.1	1006.4
110°	186.2	190.5	197.1	211.3	234.3	266.1	314.2	393.0	526.7	719.3	946.0



TEST NUMBER: P331734-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	205.4	209.8	217.3	230.5	252.7	285.3	331.8	406.2	527.5	700.1	904.0
115°	235.4	240.9	247.4	260.6	282.5	312.1	359.1	425.9	532.2	678.8	851.9
117.5°	266.6	270.9	277.5	289.1	310.1	340.7	384.3	447.0	540.0	668.5	819.0
120°	285.8	290.1	296.7	306.6	328.5	359.1	401.8	461.0	545.3	662.4	801.4
122.5°	304.2	307.6	314.2	325.0	346.9	378.4	418.5	473.3	551.4	658.9	786.6
125°	328.5	331.8	338.4	351.5	373.3	404.1	443.5	492.8	560.6	652.6	765.3
127.5°	347.7	352.1	361.4	375.8	396.8	428.3	466.7	510.9	570.0	648.8	745.6
130°	359.1	363.5	374.5	389.8	411.7	442.3	480.7	522.3	577.0	647.1	732.5
132.5°	369.7	374.9	386.7	402.9	425.7	456.4	492.9	533.7	584.0	646.2	722.0
135°	385.4	389.8	402.9	419.3	444.5	475.2	510.2	548.6	592.4	644.9	707.3
137.5°	400.3	405.6	418.7	436.2	461.2	489.7	524.2	560.0	599.8	644.7	697.0
140°	411.7	416.0	429.2	446.8	470.8	499.3	532.2	566.1	603.3	643.9	690.9
142.5°	423.1	426.6	438.8	456.4	479.6	506.3	538.3	571.4	606.0	643.9	684.8
145°	440.2	444.5	455.5	471.9	493.8	517.9	547.4	578.2	608.8	641.6	676.7
147.5°	458.5	461.8	472.3	487.5	505.7	527.1	554.9	581.8	609.6	637.7	668.4
150°	470.8	474.1	482.9	497.1	513.5	533.2	558.5	583.6	608.8	635.1	661.3
152.5°	483.1	484.7	493.3	505.9	521.4	539.3	561.9	584.5	607.0	630.7	655.2
155°	500.4	501.4	508.0	520.1	532.2	548.6	567.1	585.8	604.4	623.0	643.9
157.5°	514.8	515.9	521.2	531.7	541.3	555.2	570.9	585.8	599.4	615.1	633.1
160°	524.4	525.6	529.9	538.7	547.4	559.5	572.7	585.8	596.7	609.9	625.2
162.5°	534.1	533.5	537.8	544.8	552.7	562.1	573.5	584.9	594.1	605.5	618.2
165°	545.3	544.2	546.4	552.9	558.5	565.0	574.9	582.5	589.1	596.7	606.6
167.5°	554.5	553.2	555.2	559.3	563.3	567.4	574.6	581.0	584.0	589.1	595.2
170°	560.6	558.5	559.5	562.8	565.0	568.3	573.7	579.2	581.4	584.7	589.1
172.5°	564.1	562.8	562.1	565.4	566.8	569.1	572.9	576.6	577.9	579.5	583.0
175°	568.3	567.1	566.1	568.3	568.3	569.4	571.6	573.7	572.7	573.7	574.9
177.5°	570.2	568.4	567.6	569.4	569.4	569.4	570.2	572.0	570.2	569.4	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331734-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1
2.5°	1375.5	1377.7	1379.9	1380.8	1380.4	1379.9	1379.5	1379.0
5°	1364.5	1367.0	1369.5	1370.4	1369.5	1368.7	1367.8	1367.0
7.5°	1342.5	1343.1	1343.9	1343.5	1342.1	1340.7	1339.2	1337.8
10°	1320.3	1319.5	1318.6	1317.4	1315.7	1314.1	1312.4	1310.7
12.5°	1295.0	1293.5	1291.9	1289.9	1287.0	1284.3	1281.5	1278.7
15°	1247.6	1242.4	1237.1	1233.0	1230.3	1227.5	1224.7	1221.9
17.5°	1194.1	1187.8	1181.6	1176.0	1171.2	1166.5	1161.7	1156.9
20°	1156.8	1149.8	1142.8	1136.3	1130.2	1124.1	1117.9	1111.9
22.5°	1115.8	1106.8	1097.9	1091.1	1086.6	1081.9	1077.4	1072.9
25°	1047.8	1036.4	1025.0	1017.2	1013.0	1008.9	1004.8	1000.6
27.5°	983.0	969.7	956.4	946.5	939.9	933.2	926.6	920.0
30°	937.2	923.0	908.8	898.0	890.5	883.0	875.5	868.0
32.5°	891.2	875.0	858.8	847.2	840.2	833.1	826.0	819.0
35°	819.2	801.7	784.2	772.4	766.3	760.2	754.0	747.9
37.5°	749.1	729.8	710.6	697.4	690.4	683.3	676.4	669.4
40°	702.2	682.5	662.7	649.2	642.1	634.8	627.5	620.4
42.5°	654.9	634.4	614.1	600.3	593.3	586.4	579.3	572.3
45°	585.9	566.2	546.4	533.2	526.5	519.9	513.2	506.5
47.5°	518.8	499.2	479.6	466.7	460.7	454.6	448.6	442.5
50°	475.7	456.5	437.3	424.8	419.0	413.1	407.3	401.4
52.5°	435.0	416.5	397.9	386.1	380.6	375.2	369.9	364.5
55°	373.2	356.5	339.8	328.8	323.5	318.2	312.9	307.6
57.5°	316.9	301.6	286.3	276.4	272.0	267.5	263.1	258.6
60°	278.1	263.9	249.7	240.4	235.9	231.5	227.1	222.6
62.5°	244.4	230.9	217.4	209.2	206.6	204.0	201.2	198.6
65°	198.7	189.3	179.8	174.7	173.8	173.1	172.2	171.4
67.5°	160.4	156.1	151.7	149.1	148.3	147.3	146.5	145.6
70°	139.5	136.8	133.9	132.1	130.9	129.8	128.7	127.5
72.5°	121.4	119.0	116.7	115.3	114.5	113.9	113.2	112.5
75°	96.1	94.3	92.3	91.1	90.9	90.6	90.3	90.0
77.5°	72.9	71.7	70.6	69.8	69.4	68.9	68.5	68.1
80°	57.8	56.7	55.6	55.0	55.0	55.0	55.0	55.0
82.5°	43.7	43.0	42.3	42.0	42.0	42.0	42.0	42.0
85°	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.8
87.5°	14.6	13.9	14.1	14.2	14.2	14.2	14.2	14.2
90°	35.1	32.9	35.1	36.1	36.1	36.1	36.1	36.1
92.5°	95.5	81.9	72.7	65.9	65.0	61.5	62.4	60.7
95°	286.9	220.1	174.1	150.0	135.7	127.1	123.8	124.8
97.5°	669.4	547.7	429.2	350.2	297.8	270.9	254.9	245.7
100°	999.7	863.9	713.9	581.4	490.5	443.5	411.7	392.0
102.5°	1216.1	1185.3	1075.6	935.3	836.5	756.2	716.5	689.8
105°	1330.3	1454.1	1468.3	1432.2	1364.2	1296.4	1249.3	1234.0
107.5°	1248.0	1434.4	1548.2	1601.2	1609.8	1606.0	1596.6	1576.2
110°	1177.0	1373.0	1513.2	1603.0	1650.0	1670.8	1680.7	1679.6



TEST NUMBER: P331734-830

CATALOG NUMBER: S122RDIP-S865D1080U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1112.2	1300.3	1450.1	1553.0	1618.5	1653.3	1672.0	1677.8
115°	1032.6	1201.2	1344.5	1457.4	1535.1	1585.5	1613.9	1623.8
117.5°	972.5	1120.6	1250.7	1356.4	1435.7	1488.8	1518.9	1527.2
120°	942.7	1078.5	1194.6	1294.2	1370.8	1422.3	1454.1	1465.0
122.5°	919.1	1043.5	1153.4	1243.4	1312.1	1362.7	1391.0	1400.1
125°	884.7	997.5	1093.8	1175.9	1239.4	1281.1	1308.4	1317.2
127.5°	850.7	952.8	1043.7	1119.5	1174.9	1213.8	1237.5	1244.5
130°	828.9	923.0	1009.6	1081.8	1135.5	1172.7	1194.6	1203.3
132.5°	807.9	895.0	974.5	1042.4	1095.1	1132.4	1152.5	1160.4
135°	778.4	850.7	923.0	984.3	1031.4	1067.5	1087.2	1091.7
137.5°	755.1	815.5	872.9	926.3	969.2	1000.3	1017.7	1024.2
140°	740.2	792.8	843.1	891.3	926.3	954.8	971.2	977.8
142.5°	727.9	772.6	816.0	856.2	889.5	915.4	930.0	931.3
145°	710.6	746.8	780.7	812.5	838.7	857.3	868.3	871.6
147.5°	697.3	725.8	752.2	775.4	797.1	812.0	819.4	821.4
150°	687.6	711.7	734.7	754.4	770.8	784.0	790.5	791.6
152.5°	678.0	700.3	719.8	736.9	749.8	761.2	766.0	766.2
155°	664.6	682.1	698.5	710.6	722.6	730.3	734.7	732.5
157.5°	649.0	663.7	677.5	686.9	695.5	701.8	703.8	703.8
160°	639.4	651.5	663.5	671.2	678.8	684.3	685.4	685.4
162.5°	629.8	640.1	650.4	656.3	663.9	667.7	668.7	667.9
165°	615.4	623.0	630.7	635.1	639.4	643.9	643.9	642.7
167.5°	601.5	607.5	612.7	616.7	618.6	621.0	620.9	619.5
170°	594.6	597.9	602.2	604.4	605.5	608.8	607.7	605.5
172.5°	586.6	589.1	592.6	593.9	595.0	596.5	595.4	594.1
175°	578.2	579.2	580.3	581.4	581.4	582.5	581.4	579.2
177.5°	572.0	572.0	572.9	572.9	572.9	572.9	572.0	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4

(END OF REPORT)