

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331719-830

Luminaire Tested: **S122RDIP-S865D725U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331719-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S865D725U830-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5780.1 lumens  
Efficiency: N/A  
Efficacy: 106.3 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54				54
1	99	95	92	89	92	89	86	83	76	74	72	65	63	62	54	53	52				47	
2	91	84	79	74	85	79	74	69	68	64	61	58	55	53	49	47	45				41	
3	84	75	68	63	78	70	64	59	61	56	52	52	49	46	44	42	40				36	
4	77	67	60	54	72	63	56	51	55	49	45	47	43	40	40	37	35				31	
5	71	60	53	47	66	57	50	45	49	44	40	43	39	35	36	33	31				28	
6	66	55	47	41	61	51	44	39	45	39	35	39	35	32	33	30	28				25	
7	61	50	42	37	57	47	40	35	41	36	32	36	32	28	31	28	25				23	
8	57	45	38	33	53	43	36	31	38	32	29	33	29	26	29	25	23				21	
9	53	42	34	30	50	39	33	28	35	30	26	31	26	23	27	23	21				19	
10	50	38	32	27	47	36	30	26	32	27	24	29	24	21	25	22	19				17	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	29061	29061	29061	29061
5°	32456	29242	25929	29242
10°	36008	29037	22474	29037
15°	37778	28612	17708	28612
20°	32752	27981	15323	27981
25°	21480	27118	13682	27118
30°	14458	26071	12381	26071
35°	11710	24750	11168	24750
40°	10414	23317	10334	23317
45°	9423	21633	9225	21633
50°	8578	19964	8545	19964
55°	8062	18117	7958	18117
60°	6746	16417	6665	16417
65°	5685	14907	6449	14907
70°	5254	13312	6080	13312
75°	4916	11591	5614	11591
80°	4537	9530	5002	9530
85°	4168	7521	4409	7521



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.6	3.0
10°-20°	475.4	8.2
20°-30°	612.6	10.6
30°-40°	582.2	10.1
40°-50°	498.7	8.6
50°-60°	379.8	6.6
60°-70°	240.1	4.2
70°-80°	119.9	2.1
80°-90°	34.7	0.6
90°-100°	153.2	2.7
100°-110°	519.8	9.0
110°-120°	552.3	9.6
120°-130°	454.6	7.9
130°-140°	365.1	6.3
140°-150°	275.9	4.8
150°-160°	193.9	3.4
160°-170°	114.1	2.0
170°-180°	37.1	0.6
0°-30°	1258.6	21.8
0°-40°	1840.8	31.8
0°-60°	2719.4	47.0
0°-90°	3114.0	53.9
90°-120°	1225.3	21.2
90°-150°	2320.9	40.2
90°-180°	2666.0	46.1
0°-180°	5780.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1800	1800	1800	1800	1800	
5°	2002	1804	1600	1804	2002	198
15°	2260	1712	1059	1712	2260	610
25°	1206	1522	768	1522	1206	572
35°	594	1256	567	1256	594	380
45°	413	947	404	947	413	319
55°	286	644	283	644	286	251
65°	149	390	169	390	149	152
75°	79	186	90	186	79	84
85°	22	41	24	41	22	25
90°	24	1	24	1	24	14
95°	84	26	84	26	84	109
105°	830	90	830	90	830	803
115°	1093	158	1093	158	1093	1070
125°	886	221	886	221	886	801
135°	735	259	735	259	735	571
145°	586	296	586	296	586	372
155°	493	337	493	337	493	230
165°	432	367	432	367	432	124
175°	390	382	390	382	390	38
180°	383	383	383	383	383	



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1872.9	1874.4	1875.9	1872.4	1872.4	1869.4	1862.9	1857.9	1843.9	1841.9	1841.9
5°	2002.5	2001.2	2003.8	1995.6	1984.3	1981.9	1970.0	1954.4	1938.1	1920.0	1916.2
7.5°	2131.3	2129.4	2124.4	2123.1	2114.4	2095.6	2076.4	2056.1	2029.0	2002.6	1989.3
10°	2196.3	2217.0	2204.5	2182.6	2187.0	2157.6	2141.9	2115.1	2092.5	2053.1	2044.4
12.5°	2260.4	2268.5	2264.6	2252.1	2246.6	2226.1	2205.0	2181.6	2140.0	2104.7	2073.9
15°	2260.1	2272.0	2275.1	2271.4	2274.5	2273.3	2262.0	2242.6	2206.4	2167.6	2133.8
17.5°	2093.3	2101.6	2122.0	2135.9	2153.4	2190.5	2208.8	2215.8	2210.5	2188.3	2164.5
20°	1906.2	1892.4	1949.9	1979.3	2004.3	2066.9	2120.7	2141.4	2174.4	2173.9	2167.6
22.5°	1641.0	1644.3	1698.8	1733.7	1806.8	1869.3	1930.6	2008.3	2072.4	2114.8	2139.6
25°	1205.7	1229.5	1283.9	1331.4	1412.8	1529.1	1634.7	1757.4	1873.0	1964.4	2051.3
27.5°	905.6	907.3	950.5	994.4	1042.6	1137.9	1271.0	1417.4	1582.3	1718.4	1875.0
30°	775.5	771.8	789.9	816.7	858.0	931.8	1031.9	1175.7	1340.2	1545.3	1728.0
32.5°	683.4	683.6	697.3	717.2	751.5	801.3	869.8	986.7	1142.1	1343.7	1557.8
35°	594.1	593.5	603.5	617.8	632.3	664.1	711.1	772.3	879.3	1067.5	1286.4
37.5°	530.1	532.8	537.7	546.7	562.6	580.3	608.5	649.7	725.9	837.2	1021.2
40°	494.1	495.3	502.2	509.7	519.1	532.8	556.0	589.1	644.8	733.6	868.0
42.5°	461.0	462.3	467.1	474.2	481.5	495.3	514.4	543.1	588.2	657.5	768.5
45°	412.7	412.7	417.2	420.3	428.4	440.9	456.6	480.3	511.5	562.9	636.7
47.5°	367.5	367.6	370.5	375.9	381.0	390.8	406.1	425.6	448.3	488.0	551.0
50°	341.5	342.0	343.9	348.4	351.5	360.2	372.1	389.0	412.7	443.4	496.0
52.5°	320.5	320.1	322.4	324.3	326.5	332.7	341.6	356.5	377.8	404.4	447.9
55°	286.4	283.9	287.7	290.8	292.7	295.2	300.2	309.5	327.7	350.2	382.8
57.5°	243.9	242.9	245.5	248.4	254.3	261.0	265.3	271.3	280.7	296.8	329.0
60°	208.9	208.9	214.5	216.4	223.3	232.1	240.8	245.8	255.1	265.8	289.5
62.5°	177.9	178.3	181.0	182.9	186.7	197.5	209.7	220.7	229.6	239.8	255.5
65°	148.8	150.1	150.1	151.4	153.8	156.4	161.4	170.1	185.8	200.1	212.0
67.5°	126.3	126.7	127.1	128.4	128.9	131.7	133.7	137.6	141.2	154.9	169.6
70°	111.3	113.2	112.5	113.9	114.4	115.6	118.2	120.1	125.7	128.8	137.6
72.5°	97.3	98.7	98.6	99.3	100.9	101.2	103.2	105.1	108.7	111.3	116.0
75°	78.8	78.1	78.8	80.0	80.7	81.3	81.3	83.8	85.7	88.2	91.3
77.5°	60.8	61.5	61.3	61.5	61.5	62.7	62.6	63.6	65.5	66.8	68.3
80°	48.8	49.4	48.8	49.4	50.0	50.6	50.0	50.6	52.5	53.8	53.8
82.5°	37.8	37.9	38.3	38.4	38.5	38.6	39.5	39.7	41.0	40.8	41.3
85°	22.5	21.9	21.9	21.9	22.5	23.1	22.5	22.5	23.1	23.1	23.1
87.5°	12.9	13.4	13.4	13.4	13.4	13.2	12.9	13.8	13.4	14.0	13.4
90°	24.3	24.3	24.3	24.3	24.3	23.6	22.1	23.6	24.3	25.1	24.3
92.5°	40.8	42.0	41.4	43.7	44.4	48.9	55.1	64.3	80.9	95.8	94.4
95°	84.0	83.2	85.5	91.3	100.9	117.2	148.1	193.0	252.7	288.8	255.7
97.5°	165.3	171.5	182.3	200.4	235.6	288.8	368.5	450.4	517.3	493.0	371.4
100°	263.7	277.0	298.4	330.1	391.2	480.4	581.4	672.7	688.2	582.0	400.8
102.5°	464.2	482.1	508.8	562.9	629.3	723.8	797.7	818.3	751.8	585.0	389.6
105°	830.4	840.7	872.3	918.0	963.7	988.1	978.5	895.2	742.0	545.9	367.7
107.5°	1060.6	1074.4	1080.7	1083.3	1077.5	1041.8	965.2	839.8	677.2	504.1	356.8
110°	1130.2	1131.0	1124.4	1110.3	1078.6	1018.2	924.0	792.0	636.6	484.1	354.4



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1129.1	1125.1	1112.6	1089.1	1045.1	975.8	875.0	748.5	608.3	471.1	355.0
115°	1092.7	1086.0	1066.9	1032.9	980.6	904.7	808.2	694.7	573.3	456.9	358.1
117.5°	1027.7	1022.1	1001.9	966.1	912.8	841.6	754.0	654.4	551.1	449.9	363.4
120°	985.8	978.5	957.1	922.5	870.9	803.8	725.8	634.3	539.3	445.7	366.9
122.5°	942.2	936.0	917.0	883.0	836.7	776.1	702.2	618.5	529.3	443.4	371.1
125°	886.4	880.4	862.0	834.1	791.3	736.0	671.2	595.3	515.0	439.1	377.2
127.5°	837.4	832.7	816.8	790.6	753.3	702.3	641.1	572.5	501.7	436.6	383.6
130°	809.7	803.8	789.1	764.0	727.9	679.3	621.1	557.7	492.9	435.5	388.3
132.5°	780.8	775.5	762.0	737.0	701.4	655.7	602.3	543.6	485.9	434.9	393.0
135°	734.6	731.6	718.4	694.1	662.3	621.1	572.5	523.9	476.0	433.9	398.6
137.5°	689.2	684.8	673.2	652.2	623.3	587.4	548.7	508.1	469.0	433.9	403.6
140°	658.0	653.6	642.4	623.3	599.7	567.3	533.5	498.0	465.0	433.2	406.0
142.5°	626.7	625.8	616.0	598.6	576.2	549.0	519.9	489.8	460.8	433.2	407.7
145°	586.4	584.3	576.9	564.4	546.7	525.4	502.5	478.2	455.3	431.8	409.6
147.5°	552.7	551.4	546.4	536.4	521.8	506.1	488.3	469.2	449.8	429.1	410.3
150°	532.7	532.0	527.5	518.7	507.7	494.4	478.9	462.7	445.0	427.3	409.6
152.5°	515.6	515.5	512.2	504.5	495.9	484.4	471.3	456.2	440.9	424.4	408.5
155°	492.9	494.4	491.4	486.3	478.2	470.0	459.0	447.2	433.2	419.2	406.7
157.5°	473.6	473.6	472.3	468.0	462.2	455.9	446.7	436.8	426.0	414.0	403.3
160°	461.2	461.2	460.5	456.9	451.7	446.5	438.4	430.3	420.8	410.4	401.5
162.5°	449.4	450.1	449.3	446.8	441.7	437.6	430.7	423.8	415.9	407.5	399.8
165°	432.5	433.2	433.2	430.3	427.3	424.4	419.2	414.1	408.2	401.5	396.4
167.5°	416.9	417.7	417.9	416.3	415.0	412.3	408.8	404.8	400.5	396.4	393.0
170°	407.5	408.9	409.6	407.5	406.7	405.2	402.3	400.1	396.4	393.4	391.2
172.5°	399.8	400.7	401.4	400.4	399.6	398.8	396.4	394.7	392.3	389.9	388.9
175°	389.7	391.2	392.0	391.2	391.2	390.5	389.7	389.0	386.8	386.1	385.3
177.5°	383.7	384.9	385.5	385.5	385.5	385.5	384.9	384.9	383.7	383.1	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1842.9	1838.9	1835.4	1826.4	1821.8	1811.8	1810.3	1809.9	1796.9	1784.3	1780.8
5°	1906.2	1896.2	1881.1	1863.7	1845.5	1826.7	1814.2	1804.2	1779.2	1755.5	1741.7
7.5°	1970.0	1948.4	1922.6	1889.4	1861.8	1830.8	1807.7	1787.1	1751.6	1717.6	1694.7
10°	2017.5	1982.4	1948.0	1902.4	1866.8	1831.7	1799.2	1771.1	1731.1	1686.0	1654.2
12.5°	2047.0	2008.5	1961.1	1916.5	1870.3	1825.7	1782.3	1746.1	1699.0	1652.6	1614.6
15°	2086.9	2045.6	1988.1	1924.3	1864.9	1806.8	1756.7	1711.7	1650.4	1594.7	1548.4
17.5°	2119.6	2062.8	2001.0	1927.2	1858.4	1784.5	1720.0	1662.6	1594.3	1527.2	1472.6
20°	2130.1	2073.8	2002.5	1928.7	1847.4	1760.5	1691.0	1628.5	1555.3	1482.1	1419.7
22.5°	2123.5	2079.8	2000.5	1912.1	1828.9	1738.0	1659.5	1587.0	1505.8	1431.2	1358.6
25°	2079.4	2064.4	1989.3	1893.0	1798.0	1692.3	1601.6	1522.2	1429.6	1349.6	1270.7
27.5°	1976.5	2008.8	1962.4	1859.7	1754.1	1640.8	1538.8	1448.4	1352.4	1262.3	1183.7
30°	1877.5	1951.8	1931.8	1836.7	1718.5	1607.2	1492.8	1398.4	1295.8	1203.2	1125.7
32.5°	1741.8	1864.7	1884.3	1804.8	1682.5	1560.2	1440.3	1346.3	1239.3	1141.7	1066.1
35°	1526.0	1709.8	1794.2	1743.6	1621.0	1489.0	1365.2	1255.7	1148.2	1051.9	976.9
37.5°	1268.4	1518.8	1659.5	1663.1	1550.6	1413.3	1278.6	1169.9	1059.8	965.3	884.0
40°	1101.3	1372.7	1555.9	1596.6	1501.6	1353.3	1217.0	1106.3	998.7	906.2	813.0
42.5°	951.2	1221.6	1446.9	1517.6	1442.0	1294.8	1158.0	1042.3	937.7	850.2	755.0
45°	769.2	1005.6	1253.9	1380.3	1338.3	1202.0	1057.5	947.4	849.2	773.6	682.3
47.5°	648.9	815.5	1055.7	1226.6	1225.9	1101.5	959.3	853.9	762.8	691.9	618.0
50°	580.3	725.5	928.7	1122.6	1138.8	1034.3	899.3	794.8	709.8	635.4	576.0
52.5°	518.8	638.4	821.1	1007.0	1053.3	962.8	831.8	735.4	652.8	584.4	533.5
55°	438.4	530.9	669.8	843.7	913.7	849.9	733.6	643.6	576.6	519.1	475.3
57.5°	370.9	440.3	551.7	691.6	773.3	733.1	637.2	564.0	506.7	454.7	420.1
60°	328.3	385.2	479.7	596.6	686.6	658.6	576.6	508.4	459.7	414.6	382.1
62.5°	288.3	337.2	418.1	513.0	595.6	584.0	517.1	459.9	417.2	376.1	348.6
65°	232.1	267.7	330.8	405.3	471.6	477.2	429.0	390.2	352.1	319.6	295.2
67.5°	184.7	208.0	252.5	315.2	364.9	382.6	353.2	323.6	293.3	268.2	247.0
70°	155.7	174.5	207.0	257.7	303.3	322.1	305.2	282.0	255.8	235.2	217.0
72.5°	126.2	144.5	168.4	205.7	244.8	265.0	259.2	242.5	221.2	204.2	187.0
75°	95.1	100.7	117.0	141.9	172.6	190.1	194.5	185.8	168.8	155.7	145.7
77.5°	70.3	73.7	81.4	94.5	114.6	130.2	136.6	135.5	123.9	116.3	107.0
80°	56.3	58.2	61.9	67.6	82.6	98.2	102.5	102.5	94.4	91.3	81.9
82.5°	42.8	44.1	46.4	49.5	56.6	70.1	75.0	76.1	70.9	66.8	59.4
85°	24.4	23.8	25.0	26.9	28.2	31.9	39.4	40.6	39.4	34.4	32.5
87.5°	12.4	12.0	11.2	10.3	10.5	10.7	12.6	14.6	13.1	12.2	11.5
90°	19.9	14.7	11.0	8.9	7.4	5.9	2.9	0.8	2.9	5.9	7.4
92.5°	73.5	50.1	33.5	26.5	21.5	18.3	13.0	9.0	13.0	18.3	21.5
95°	170.2	106.1	72.2	54.5	42.7	36.1	28.7	25.8	28.7	36.1	42.7
97.5°	229.3	140.0	97.4	77.4	63.8	53.8	46.0	42.0	46.0	53.8	63.8
100°	241.7	151.7	112.7	92.1	77.4	65.6	58.9	56.7	58.9	65.6	77.4
102.5°	242.2	162.4	126.3	105.7	90.3	78.5	71.9	70.3	71.9	78.5	90.3
105°	246.1	180.5	145.9	125.3	109.1	98.0	92.8	89.9	92.8	98.0	109.1
107.5°	256.3	199.1	165.5	144.7	128.7	118.5	113.5	111.1	113.5	118.5	128.7
110°	264.5	211.4	179.1	157.7	142.2	132.6	128.2	125.3	128.2	132.6	142.2





TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	273.3	223.3	192.0	170.0	155.1	146.2	141.2	138.2	141.2	146.2	155.1
115°	286.6	241.7	210.0	190.1	175.3	166.5	162.1	158.4	162.1	166.5	175.3
117.5°	300.8	258.6	229.3	208.7	194.5	186.7	182.3	179.4	182.3	186.7	194.5
120°	310.2	270.4	241.7	221.0	206.3	199.6	195.3	192.3	195.3	199.6	206.3
122.5°	318.5	281.6	254.7	233.4	218.7	211.4	207.1	204.7	207.1	211.4	218.7
125°	331.6	298.4	271.8	251.3	236.5	227.6	223.3	221.0	223.3	227.6	236.5
127.5°	343.7	314.1	288.2	267.0	252.9	243.2	237.0	234.0	237.0	243.2	252.9
130°	351.5	323.5	297.7	277.0	262.3	251.9	244.6	241.7	244.6	251.9	262.3
132.5°	359.1	331.7	307.1	286.4	271.2	260.2	252.3	248.7	252.3	260.2	271.2
135°	369.1	343.4	319.8	299.2	282.2	271.2	262.3	259.4	262.3	271.2	282.2
137.5°	376.8	352.8	329.5	310.4	293.5	281.7	272.9	269.4	272.9	281.7	293.5
140°	380.9	358.1	336.0	316.8	300.6	288.8	279.9	277.0	279.9	288.8	300.6
142.5°	384.5	362.2	340.7	322.7	307.1	295.3	287.1	284.6	287.1	295.3	307.1
145°	389.0	368.4	348.5	332.2	317.5	306.5	299.2	296.1	299.2	306.5	317.5
147.5°	391.5	373.4	354.7	340.3	328.0	317.8	310.8	308.6	310.8	317.8	328.0
150°	392.7	375.8	358.8	345.5	334.5	324.9	319.1	316.8	319.1	324.9	334.5
152.5°	393.3	378.1	363.0	350.8	340.4	332.0	326.1	325.1	326.1	332.0	340.4
155°	394.2	381.6	369.1	358.1	350.0	341.9	337.4	336.7	337.4	341.9	350.0
157.5°	394.2	384.2	373.5	364.3	357.8	350.7	347.1	346.5	347.1	350.7	357.8
160°	394.2	385.3	376.5	368.4	362.5	356.6	353.6	352.9	353.6	356.6	362.5
162.5°	393.6	386.0	378.2	371.9	366.6	361.9	358.9	359.4	358.9	361.9	366.6
165°	392.0	386.8	380.2	375.8	372.1	367.7	366.2	366.9	366.2	367.7	372.1
167.5°	391.0	386.6	381.8	379.0	376.4	373.5	372.2	373.2	372.2	373.5	376.4
170°	389.7	386.1	382.4	380.2	378.7	376.5	375.8	377.2	375.8	376.5	378.7
172.5°	388.0	385.5	383.0	381.4	380.5	378.2	378.7	379.6	378.7	378.2	380.5
175°	386.1	384.6	383.1	382.4	382.4	380.9	381.6	382.4	381.6	380.9	382.4
177.5°	384.9	383.7	383.1	383.1	383.1	381.9	382.6	383.7	382.6	381.9	383.1
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1774.3	1770.8	1764.3	1754.4	1748.3	1737.9	1730.8	1734.8	1735.8	1734.8	1733.8
5°	1726.6	1713.5	1695.4	1677.9	1661.6	1644.2	1634.1	1629.8	1621.0	1616.0	1613.5
7.5°	1669.1	1646.4	1620.7	1590.3	1564.3	1537.2	1523.3	1516.5	1498.5	1488.7	1480.3
10°	1626.0	1590.4	1564.7	1524.7	1500.3	1464.6	1440.3	1440.9	1416.5	1402.7	1392.7
12.5°	1578.5	1539.4	1496.7	1460.7	1426.7	1398.1	1368.8	1356.8	1331.0	1317.7	1290.6
15°	1499.7	1454.1	1409.0	1360.2	1325.8	1281.4	1238.9	1186.9	1145.1	1108.8	1098.8
17.5°	1413.6	1357.1	1311.9	1254.6	1195.7	1121.1	1071.8	1041.6	1016.3	997.2	983.0
20°	1354.6	1297.0	1248.9	1162.6	1083.2	1032.6	996.3	973.1	946.9	926.2	914.9
22.5°	1292.5	1232.5	1166.9	1070.5	1008.6	968.0	935.7	909.1	891.3	875.2	864.9
25°	1204.5	1138.8	1030.7	964.3	914.3	871.8	849.2	833.0	814.3	792.4	782.3
27.5°	1111.4	1007.0	929.3	880.1	832.3	804.6	784.4	760.1	743.3	733.5	723.0
30°	1041.9	937.5	876.8	823.0	789.2	758.6	734.8	721.0	704.8	688.0	681.1
32.5°	964.3	880.9	822.7	778.0	743.7	717.6	698.8	676.6	664.8	654.4	640.0
35°	868.0	804.8	751.7	715.5	683.0	661.7	639.8	626.6	605.4	596.6	591.0
37.5°	786.5	731.7	692.0	653.7	628.0	604.5	591.1	570.2	561.0	548.8	537.0
40°	740.5	686.6	648.6	617.3	588.5	571.0	554.1	537.2	523.5	517.8	503.4
42.5°	693.4	649.7	611.5	577.2	558.0	539.4	518.1	505.7	491.4	482.3	473.4
45°	628.5	589.7	557.2	529.0	507.8	488.4	474.7	454.0	445.9	427.7	420.3
47.5°	571.5	535.5	504.4	477.7	456.9	444.3	424.1	408.0	395.0	383.9	374.2
50°	530.9	501.0	470.9	447.1	428.4	410.3	389.6	381.4	361.5	355.8	350.2
52.5°	493.9	465.4	437.9	414.6	395.9	378.2	360.1	349.5	335.9	330.4	326.2
55°	442.1	414.6	388.3	367.7	348.9	330.8	319.6	306.4	300.2	295.8	290.8
57.5°	390.1	365.3	345.3	324.3	305.5	291.1	278.1	270.1	263.6	257.9	251.9
60°	357.1	333.3	315.2	295.8	276.4	264.6	254.5	245.2	237.6	228.8	226.4
62.5°	322.1	301.3	284.6	265.8	248.9	238.0	228.5	219.6	210.7	197.8	194.4
65°	273.9	257.7	240.2	224.5	209.5	198.9	185.1	175.1	171.4	170.1	169.5
67.5°	230.4	215.0	200.0	184.0	170.3	160.5	153.4	151.9	149.3	148.5	146.8
70°	201.3	187.0	172.0	156.9	143.8	141.9	139.5	137.0	133.8	132.6	131.3
72.5°	175.3	160.5	145.4	133.5	127.8	125.5	122.9	120.5	118.3	117.1	116.3
75°	134.5	120.7	110.7	106.3	103.2	101.3	97.6	95.7	94.4	92.6	91.9
77.5°	96.8	89.1	84.5	81.7	78.4	76.4	74.3	72.4	71.1	70.7	69.7
80°	73.8	70.0	66.9	63.2	61.9	59.4	58.8	56.9	57.5	55.7	55.7
82.5°	57.3	52.5	49.9	48.2	46.9	44.9	44.3	43.4	43.5	42.1	42.1
85°	29.4	28.2	26.9	25.6	25.6	23.8	24.4	23.8	23.8	22.5	21.9
87.5°	11.3	11.2	10.9	12.0	12.9	12.5	12.3	11.7	11.4	11.7	11.4
90°	8.9	11.0	14.7	19.9	24.3	25.1	24.3	23.6	22.1	23.6	24.3
92.5°	26.5	33.5	50.1	73.5	94.4	95.8	80.9	64.3	55.1	48.9	44.4
95°	54.5	72.2	106.1	170.2	255.7	288.8	252.7	193.0	148.1	117.2	100.9
97.5°	77.4	97.4	140.0	229.3	371.4	493.0	517.3	450.4	368.5	288.8	235.6
100°	92.1	112.7	151.7	241.7	400.8	582.0	688.2	672.7	581.4	480.4	391.2
102.5°	105.7	126.3	162.4	242.2	389.6	585.0	751.8	818.3	797.7	723.8	629.3
105°	125.3	145.9	180.5	246.1	367.7	545.9	742.0	895.2	978.5	988.1	963.7
107.5°	144.7	165.5	199.1	256.3	356.8	504.1	677.2	839.8	965.2	1041.8	1077.5
110°	157.7	179.1	211.4	264.5	354.4	484.1	636.6	792.0	924.0	1018.2	1078.6



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.0	192.0	223.3	273.3	355.0	471.1	608.3	748.5	875.0	975.8	1045.1
115°	190.1	210.0	241.7	286.6	358.1	456.9	573.3	694.7	808.2	904.7	980.6
117.5°	208.7	229.3	258.6	300.8	363.4	449.9	551.1	654.4	754.0	841.6	912.8
120°	221.0	241.7	270.4	310.2	366.9	445.7	539.3	634.3	725.8	803.8	870.9
122.5°	233.4	254.7	281.6	318.5	371.1	443.4	529.3	618.5	702.2	776.1	836.7
125°	251.3	271.8	298.4	331.6	377.2	439.1	515.0	595.3	671.2	736.0	791.3
127.5°	267.0	288.2	314.1	343.7	383.6	436.6	501.7	572.5	641.1	702.3	753.3
130°	277.0	297.7	323.5	351.5	388.3	435.5	492.9	557.7	621.1	679.3	727.9
132.5°	286.4	307.1	331.7	359.1	393.0	434.9	485.9	543.6	602.3	655.7	701.4
135°	299.2	319.8	343.4	369.1	398.6	433.9	476.0	523.9	572.5	621.1	662.3
137.5°	310.4	329.5	352.8	376.8	403.6	433.9	469.0	508.1	548.7	587.4	623.3
140°	316.8	336.0	358.1	380.9	406.0	433.2	465.0	498.0	533.5	567.3	599.7
142.5°	322.7	340.7	362.2	384.5	407.7	433.2	460.8	489.8	519.9	549.0	576.2
145°	332.2	348.5	368.4	389.0	409.6	431.8	455.3	478.2	502.5	525.4	546.7
147.5°	340.3	354.7	373.4	391.5	410.3	429.1	449.8	469.2	488.3	506.1	521.8
150°	345.5	358.8	375.8	392.7	409.6	427.3	445.0	462.7	478.9	494.4	507.7
152.5°	350.8	363.0	378.1	393.3	408.5	424.4	440.9	456.2	471.3	484.4	495.9
155°	358.1	369.1	381.6	394.2	406.7	419.2	433.2	447.2	459.0	470.0	478.2
157.5°	364.3	373.5	384.2	394.2	403.3	414.0	426.0	436.8	446.7	455.9	462.2
160°	368.4	376.5	385.3	394.2	401.5	410.4	420.8	430.3	438.4	446.5	451.7
162.5°	371.9	378.2	386.0	393.6	399.8	407.5	415.9	423.8	430.7	437.6	441.7
165°	375.8	380.2	386.8	392.0	396.4	401.5	408.2	414.1	419.2	424.4	427.3
167.5°	379.0	381.8	386.6	391.0	393.0	396.4	400.5	404.8	408.8	412.3	415.0
170°	380.2	382.4	386.1	389.7	391.2	393.4	396.4	400.1	402.3	405.2	406.7
172.5°	381.4	383.0	385.5	388.0	388.9	389.9	392.3	394.7	396.4	398.8	399.6
175°	382.4	383.1	384.6	386.1	385.3	386.1	386.8	389.0	389.7	390.5	391.2
177.5°	383.1	383.1	383.7	384.9	383.7	383.1	383.7	384.9	384.9	385.5	385.5
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1728.3	1729.3	1727.8	1728.8	1727.8	1729.3	1728.3	1733.8	1734.8	1735.8	1734.8
5°	1610.3	1602.9	1601.6	1599.8	1601.6	1602.9	1610.3	1613.5	1616.0	1621.0	1629.8
7.5°	1469.5	1468.4	1465.3	1460.9	1465.3	1468.4	1469.5	1480.3	1488.7	1498.5	1516.5
10°	1378.9	1375.8	1375.3	1370.8	1375.3	1375.8	1378.9	1392.7	1402.7	1416.5	1440.9
12.5°	1272.9	1252.7	1250.7	1239.7	1250.7	1252.7	1272.9	1290.6	1317.7	1331.0	1356.8
15°	1083.8	1080.1	1067.5	1059.4	1067.5	1080.1	1083.8	1098.8	1108.8	1145.1	1186.9
17.5°	975.7	963.5	959.6	957.8	959.6	963.5	975.7	983.0	997.2	1016.3	1041.6
20°	906.2	894.9	893.1	891.8	893.1	894.9	906.2	914.9	926.2	946.9	973.1
22.5°	858.2	846.4	841.5	837.7	841.5	846.4	858.2	864.9	875.2	891.3	909.1
25°	776.1	771.8	769.2	768.0	769.2	771.8	776.1	782.3	792.4	814.3	833.0
27.5°	711.9	702.3	700.4	697.2	700.4	702.3	711.9	723.0	733.5	743.3	760.1
30°	675.4	672.3	667.9	664.1	667.9	672.3	675.4	681.1	688.0	704.8	721.0
32.5°	632.4	629.8	625.8	624.2	625.8	629.8	632.4	640.0	654.4	664.8	676.6
35°	584.8	576.0	572.2	566.6	572.2	576.0	584.8	591.0	596.6	605.4	626.6
37.5°	534.3	529.7	524.4	526.3	524.4	529.7	534.3	537.0	548.8	561.0	570.2
40°	495.3	492.2	491.0	490.3	491.0	492.2	495.3	503.4	517.8	523.5	537.2
42.5°	464.3	455.6	452.4	452.2	452.4	455.6	464.3	473.4	482.3	491.4	505.7
45°	417.2	409.0	403.4	404.0	403.4	409.0	417.2	420.3	427.7	445.9	454.0
47.5°	368.8	368.6	365.1	366.3	365.1	368.6	368.8	374.2	383.9	395.0	408.0
50°	345.8	342.0	339.6	340.2	339.6	342.0	345.8	350.2	355.8	361.5	381.4
52.5°	323.9	320.6	318.6	321.2	318.6	320.6	323.9	326.2	330.4	335.9	349.5
55°	287.7	283.9	283.3	282.7	283.3	283.9	287.7	290.8	295.8	300.2	306.4
57.5°	247.3	244.8	241.0	239.4	241.0	244.8	247.3	251.9	257.9	263.6	270.1
60°	218.3	213.3	207.0	206.4	207.0	213.3	218.3	226.4	228.8	237.6	245.2
62.5°	191.7	190.8	189.5	189.4	189.5	190.8	191.7	194.4	197.8	210.7	219.6
65°	168.2	167.6	168.2	168.8	168.2	167.6	168.2	169.5	170.1	171.4	175.1
67.5°	146.6	145.4	144.3	144.9	144.3	145.4	146.6	146.8	148.5	149.3	151.9
70°	130.1	129.4	128.8	128.8	128.8	129.4	130.1	131.3	132.6	133.8	137.0
72.5°	114.0	114.0	113.3	112.8	113.3	114.0	114.0	116.3	117.1	118.3	120.5
75°	91.3	90.0	90.0	90.0	90.0	90.0	91.3	91.9	92.6	94.4	95.7
77.5°	69.6	68.9	68.3	67.8	68.3	68.9	69.6	69.7	70.7	71.1	72.4
80°	55.0	54.4	53.8	53.8	53.8	54.4	55.0	55.7	55.7	57.5	56.9
82.5°	42.0	41.4	41.3	40.8	41.3	41.4	42.0	42.1	42.1	43.5	43.4
85°	22.5	23.1	22.5	23.8	22.5	23.1	22.5	21.9	22.5	23.8	23.8
87.5°	11.4	10.8	11.4	10.8	11.4	10.8	11.4	11.4	11.7	11.4	11.7
90°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	23.6	22.1	23.6
92.5°	43.7	41.4	42.0	40.8	42.0	41.4	43.7	44.4	48.9	55.1	64.3
95°	91.3	85.5	83.2	84.0	83.2	85.5	91.3	100.9	117.2	148.1	193.0
97.5°	200.4	182.3	171.5	165.3	171.5	182.3	200.4	235.6	288.8	368.5	450.4
100°	330.1	298.4	277.0	263.7	277.0	298.4	330.1	391.2	480.4	581.4	672.7
102.5°	562.9	508.8	482.1	464.2	482.1	508.8	562.9	629.3	723.8	797.7	818.3
105°	918.0	872.3	840.7	830.4	840.7	872.3	918.0	963.7	988.1	978.5	895.2
107.5°	1083.3	1080.7	1074.4	1060.6	1074.4	1080.7	1083.3	1077.5	1041.8	965.2	839.8
110°	1110.3	1124.4	1131.0	1130.2	1131.0	1124.4	1110.3	1078.6	1018.2	924.0	792.0



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1089.1	1112.6	1125.1	1129.1	1125.1	1112.6	1089.1	1045.1	975.8	875.0	748.5
115°	1032.9	1066.9	1086.0	1092.7	1086.0	1066.9	1032.9	980.6	904.7	808.2	694.7
117.5°	966.1	1001.9	1022.1	1027.7	1022.1	1001.9	966.1	912.8	841.6	754.0	654.4
120°	922.5	957.1	978.5	985.8	978.5	957.1	922.5	870.9	803.8	725.8	634.3
122.5°	883.0	917.0	936.0	942.2	936.0	917.0	883.0	836.7	776.1	702.2	618.5
125°	834.1	862.0	880.4	886.4	880.4	862.0	834.1	791.3	736.0	671.2	595.3
127.5°	790.6	816.8	832.7	837.4	832.7	816.8	790.6	753.3	702.3	641.1	572.5
130°	764.0	789.1	803.8	809.7	803.8	789.1	764.0	727.9	679.3	621.1	557.7
132.5°	737.0	762.0	775.5	780.8	775.5	762.0	737.0	701.4	655.7	602.3	543.6
135°	694.1	718.4	731.6	734.6	731.6	718.4	694.1	662.3	621.1	572.5	523.9
137.5°	652.2	673.2	684.8	689.2	684.8	673.2	652.2	623.3	587.4	548.7	508.1
140°	623.3	642.4	653.6	658.0	653.6	642.4	623.3	599.7	567.3	533.5	498.0
142.5°	598.6	616.0	625.8	626.7	625.8	616.0	598.6	576.2	549.0	519.9	489.8
145°	564.4	576.9	584.3	586.4	584.3	576.9	564.4	546.7	525.4	502.5	478.2
147.5°	536.4	546.4	551.4	552.7	551.4	546.4	536.4	521.8	506.1	488.3	469.2
150°	518.7	527.5	532.0	532.7	532.0	527.5	518.7	507.7	494.4	478.9	462.7
152.5°	504.5	512.2	515.5	515.6	515.5	512.2	504.5	495.9	484.4	471.3	456.2
155°	486.3	491.4	494.4	492.9	494.4	491.4	486.3	478.2	470.0	459.0	447.2
157.5°	468.0	472.3	473.6	473.6	473.6	472.3	468.0	462.2	455.9	446.7	436.8
160°	456.9	460.5	461.2	461.2	461.2	460.5	456.9	451.7	446.5	438.4	430.3
162.5°	446.8	449.3	450.1	449.4	450.1	449.3	446.8	441.7	437.6	430.7	423.8
165°	430.3	433.2	433.2	432.5	433.2	433.2	430.3	427.3	424.4	419.2	414.1
167.5°	416.3	417.9	417.7	416.9	417.7	417.9	416.3	415.0	412.3	408.8	404.8
170°	407.5	409.6	408.9	407.5	408.9	409.6	407.5	406.7	405.2	402.3	400.1
172.5°	400.4	401.4	400.7	399.8	400.7	401.4	400.4	399.6	398.8	396.4	394.7
175°	391.2	392.0	391.2	389.7	391.2	392.0	391.2	391.2	390.5	389.7	389.0
177.5°	385.5	385.5	384.9	383.7	384.9	385.5	385.5	385.5	385.5	384.9	384.9
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1730.8	1737.9	1748.3	1754.4	1764.3	1770.8	1774.3	1780.8	1784.3	1796.9	1809.9
5°	1634.1	1644.2	1661.6	1677.9	1695.4	1713.5	1726.6	1741.7	1755.5	1779.2	1804.2
7.5°	1523.3	1537.2	1564.3	1590.3	1620.7	1646.4	1669.1	1694.7	1717.6	1751.6	1787.1
10°	1440.3	1464.6	1500.3	1524.7	1564.7	1590.4	1626.0	1654.2	1686.0	1731.1	1771.1
12.5°	1368.8	1398.1	1426.7	1460.7	1496.7	1539.4	1578.5	1614.6	1652.6	1699.0	1746.1
15°	1238.9	1281.4	1325.8	1360.2	1409.0	1454.1	1499.7	1548.4	1594.7	1650.4	1711.7
17.5°	1071.8	1121.1	1195.7	1254.6	1311.9	1357.1	1413.6	1472.6	1527.2	1594.3	1662.6
20°	996.3	1032.6	1083.2	1162.6	1248.9	1297.0	1354.6	1419.7	1482.1	1555.3	1628.5
22.5°	935.7	968.0	1008.6	1070.5	1166.9	1232.5	1292.5	1358.6	1431.2	1505.8	1587.0
25°	849.2	871.8	914.3	964.3	1030.7	1138.8	1204.5	1270.7	1349.6	1429.6	1522.2
27.5°	784.4	804.6	832.3	880.1	929.3	1007.0	1111.4	1183.7	1262.3	1352.4	1448.4
30°	734.8	758.6	789.2	823.0	876.8	937.5	1041.9	1125.7	1203.2	1295.8	1398.4
32.5°	698.8	717.6	743.7	778.0	822.7	880.9	964.3	1066.1	1141.7	1239.3	1346.3
35°	639.8	661.7	683.0	715.5	751.7	804.8	868.0	976.9	1051.9	1148.2	1255.7
37.5°	591.1	604.5	628.0	653.7	692.0	731.7	786.5	884.0	965.3	1059.8	1169.9
40°	554.1	571.0	588.5	617.3	648.6	686.6	740.5	813.0	906.2	998.7	1106.3
42.5°	518.1	539.4	558.0	577.2	611.5	649.7	693.4	755.0	850.2	937.7	1042.3
45°	474.7	488.4	507.8	529.0	557.2	589.7	628.5	682.3	773.6	849.2	947.4
47.5°	424.1	444.3	456.9	477.7	504.4	535.5	571.5	618.0	691.9	762.8	853.9
50°	389.6	410.3	428.4	447.1	470.9	501.0	530.9	576.0	635.4	709.8	794.8
52.5°	360.1	378.2	395.9	414.6	437.9	465.4	493.9	533.5	584.4	652.8	735.4
55°	319.6	330.8	348.9	367.7	388.3	414.6	442.1	475.3	519.1	576.6	643.6
57.5°	278.1	291.1	305.5	324.3	345.3	365.3	390.1	420.1	454.7	506.7	564.0
60°	254.5	264.6	276.4	295.8	315.2	333.3	357.1	382.1	414.6	459.7	508.4
62.5°	228.5	238.0	248.9	265.8	284.6	301.3	322.1	348.6	376.1	417.2	459.9
65°	185.1	198.9	209.5	224.5	240.2	257.7	273.9	295.2	319.6	352.1	390.2
67.5°	153.4	160.5	170.3	184.0	200.0	215.0	230.4	247.0	268.2	293.3	323.6
70°	139.5	141.9	143.8	156.9	172.0	187.0	201.3	217.0	235.2	255.8	282.0
72.5°	122.9	125.5	127.8	133.5	145.4	160.5	175.3	187.0	204.2	221.2	242.5
75°	97.6	101.3	103.2	106.3	110.7	120.7	134.5	145.7	155.7	168.8	185.8
77.5°	74.3	76.4	78.4	81.7	84.5	89.1	96.8	107.0	116.3	123.9	135.5
80°	58.8	59.4	61.9	63.2	66.9	70.0	73.8	81.9	91.3	94.4	102.5
82.5°	44.3	44.9	46.9	48.2	49.9	52.5	57.3	59.4	66.8	70.9	76.1
85°	24.4	23.8	25.6	25.6	26.9	28.2	29.4	32.5	34.4	39.4	40.6
87.5°	12.3	12.5	12.9	12.0	10.9	11.2	11.3	11.5	12.2	13.1	14.6
90°	24.3	25.1	24.3	19.9	14.7	11.0	8.9	7.4	5.9	2.9	0.8
92.5°	80.9	95.8	94.4	73.5	50.1	33.5	26.5	21.5	18.3	13.0	9.0
95°	252.7	288.8	255.7	170.2	106.1	72.2	54.5	42.7	36.1	28.7	25.8
97.5°	517.3	493.0	371.4	229.3	140.0	97.4	77.4	63.8	53.8	46.0	42.0
100°	688.2	582.0	400.8	241.7	151.7	112.7	92.1	77.4	65.6	58.9	56.7
102.5°	751.8	585.0	389.6	242.2	162.4	126.3	105.7	90.3	78.5	71.9	70.3
105°	742.0	545.9	367.7	246.1	180.5	145.9	125.3	109.1	98.0	92.8	89.9
107.5°	677.2	504.1	356.8	256.3	199.1	165.5	144.7	128.7	118.5	113.5	111.1
110°	636.6	484.1	354.4	264.5	211.4	179.1	157.7	142.2	132.6	128.2	125.3



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	608.3	471.1	355.0	273.3	223.3	192.0	170.0	155.1	146.2	141.2	138.2
115°	573.3	456.9	358.1	286.6	241.7	210.0	190.1	175.3	166.5	162.1	158.4
117.5°	551.1	449.9	363.4	300.8	258.6	229.3	208.7	194.5	186.7	182.3	179.4
120°	539.3	445.7	366.9	310.2	270.4	241.7	221.0	206.3	199.6	195.3	192.3
122.5°	529.3	443.4	371.1	318.5	281.6	254.7	233.4	218.7	211.4	207.1	204.7
125°	515.0	439.1	377.2	331.6	298.4	271.8	251.3	236.5	227.6	223.3	221.0
127.5°	501.7	436.6	383.6	343.7	314.1	288.2	267.0	252.9	243.2	237.0	234.0
130°	492.9	435.5	388.3	351.5	323.5	297.7	277.0	262.3	251.9	244.6	241.7
132.5°	485.9	434.9	393.0	359.1	331.7	307.1	286.4	271.2	260.2	252.3	248.7
135°	476.0	433.9	398.6	369.1	343.4	319.8	299.2	282.2	271.2	262.3	259.4
137.5°	469.0	433.9	403.6	376.8	352.8	329.5	310.4	293.5	281.7	272.9	269.4
140°	465.0	433.2	406.0	380.9	358.1	336.0	316.8	300.6	288.8	279.9	277.0
142.5°	460.8	433.2	407.7	384.5	362.2	340.7	322.7	307.1	295.3	287.1	284.6
145°	455.3	431.8	409.6	389.0	368.4	348.5	332.2	317.5	306.5	299.2	296.1
147.5°	449.8	429.1	410.3	391.5	373.4	354.7	340.3	328.0	317.8	310.8	308.6
150°	445.0	427.3	409.6	392.7	375.8	358.8	345.5	334.5	324.9	319.1	316.8
152.5°	440.9	424.4	408.5	393.3	378.1	363.0	350.8	340.4	332.0	326.1	325.1
155°	433.2	419.2	406.7	394.2	381.6	369.1	358.1	350.0	341.9	337.4	336.7
157.5°	426.0	414.0	403.3	394.2	384.2	373.5	364.3	357.8	350.7	347.1	346.5
160°	420.8	410.4	401.5	394.2	385.3	376.5	368.4	362.5	356.6	353.6	352.9
162.5°	415.9	407.5	399.8	393.6	386.0	378.2	371.9	366.6	361.9	358.9	359.4
165°	408.2	401.5	396.4	392.0	386.8	380.2	375.8	372.1	367.7	366.2	366.9
167.5°	400.5	396.4	393.0	391.0	386.6	381.8	379.0	376.4	373.5	372.2	373.2
170°	396.4	393.4	391.2	389.7	386.1	382.4	380.2	378.7	376.5	375.8	377.2
172.5°	392.3	389.9	388.9	388.0	385.5	383.0	381.4	380.5	378.2	378.7	379.6
175°	386.8	386.1	385.3	386.1	384.6	383.1	382.4	382.4	380.9	381.6	382.4
177.5°	383.7	383.1	383.7	384.9	383.7	383.1	383.1	383.1	381.9	382.6	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1810.3	1811.8	1821.8	1826.4	1835.4	1838.9	1842.9	1841.9	1841.9	1843.9	1857.9
5°	1814.2	1826.7	1845.5	1863.7	1881.1	1896.2	1906.2	1916.2	1920.0	1938.1	1954.4
7.5°	1807.7	1830.8	1861.8	1889.4	1922.6	1948.4	1970.0	1989.3	2002.6	2029.0	2056.1
10°	1799.2	1831.7	1866.8	1902.4	1948.0	1982.4	2017.5	2044.4	2053.1	2092.5	2115.1
12.5°	1782.3	1825.7	1870.3	1916.5	1961.1	2008.5	2047.0	2073.9	2104.7	2140.0	2181.6
15°	1756.7	1806.8	1864.9	1924.3	1988.1	2045.6	2086.9	2133.8	2167.6	2206.4	2242.6
17.5°	1720.0	1784.5	1858.4	1927.2	2001.0	2062.8	2119.6	2164.5	2188.3	2210.5	2215.8
20°	1691.0	1760.5	1847.4	1928.7	2002.5	2073.8	2130.1	2167.6	2173.9	2174.4	2141.4
22.5°	1659.5	1738.0	1828.9	1912.1	2000.5	2079.8	2123.5	2139.6	2114.8	2072.4	2008.3
25°	1601.6	1692.3	1798.0	1893.0	1989.3	2064.4	2079.4	2051.3	1964.4	1873.0	1757.4
27.5°	1538.8	1640.8	1754.1	1859.7	1962.4	2008.8	1976.5	1875.0	1718.4	1582.3	1417.4
30°	1492.8	1607.2	1718.5	1836.7	1931.8	1951.8	1877.5	1728.0	1545.3	1340.2	1175.7
32.5°	1440.3	1560.2	1682.5	1804.8	1884.3	1864.7	1741.8	1557.8	1343.7	1142.1	986.7
35°	1365.2	1489.0	1621.0	1743.6	1794.2	1709.8	1526.0	1286.4	1067.5	879.3	772.3
37.5°	1278.6	1413.3	1550.6	1663.1	1659.5	1518.8	1268.4	1021.2	837.2	725.9	649.7
40°	1217.0	1353.3	1501.6	1596.6	1555.9	1372.7	1101.3	868.0	733.6	644.8	589.1
42.5°	1158.0	1294.8	1442.0	1517.6	1446.9	1221.6	951.2	768.5	657.5	588.2	543.1
45°	1057.5	1202.0	1338.3	1380.3	1253.9	1005.6	769.2	636.7	562.9	511.5	480.3
47.5°	959.3	1101.5	1225.9	1226.6	1055.7	815.5	648.9	551.0	488.0	448.3	425.6
50°	899.3	1034.3	1138.8	1122.6	928.7	725.5	580.3	496.0	443.4	412.7	389.0
52.5°	831.8	962.8	1053.3	1007.0	821.1	638.4	518.8	447.9	404.4	377.8	356.5
55°	733.6	849.9	913.7	843.7	669.8	530.9	438.4	382.8	350.2	327.7	309.5
57.5°	637.2	733.1	773.3	691.6	551.7	440.3	370.9	329.0	296.8	280.7	271.3
60°	576.6	658.6	686.6	596.6	479.7	385.2	328.3	289.5	265.8	255.1	245.8
62.5°	517.1	584.0	595.6	513.0	418.1	337.2	288.3	255.5	239.8	229.6	220.7
65°	429.0	477.2	471.6	405.3	330.8	267.7	232.1	212.0	200.1	185.8	170.1
67.5°	353.2	382.6	364.9	315.2	252.5	208.0	184.7	169.6	154.9	141.2	137.6
70°	305.2	322.1	303.3	257.7	207.0	174.5	155.7	137.6	128.8	125.7	120.1
72.5°	259.2	265.0	244.8	205.7	168.4	144.5	126.2	116.0	111.3	108.7	105.1
75°	194.5	190.1	172.6	141.9	117.0	100.7	95.1	91.3	88.2	85.7	83.8
77.5°	136.6	130.2	114.6	94.5	81.4	73.7	70.3	68.3	66.8	65.5	63.6
80°	102.5	98.2	82.6	67.6	61.9	58.2	56.3	53.8	53.8	52.5	50.6
82.5°	75.0	70.1	56.6	49.5	46.4	44.1	42.8	41.3	40.8	41.0	39.7
85°	39.4	31.9	28.2	26.9	25.0	23.8	24.4	23.1	23.1	23.1	22.5
87.5°	12.6	10.7	10.5	10.3	11.2	12.0	12.4	13.4	14.0	13.4	13.8
90°	2.9	5.9	7.4	8.9	11.0	14.7	19.9	24.3	25.1	24.3	23.6
92.5°	13.0	18.3	21.5	26.5	33.5	50.1	73.5	94.4	95.8	80.9	64.3
95°	28.7	36.1	42.7	54.5	72.2	106.1	170.2	255.7	288.8	252.7	193.0
97.5°	46.0	53.8	63.8	77.4	97.4	140.0	229.3	371.4	493.0	517.3	450.4
100°	58.9	65.6	77.4	92.1	112.7	151.7	241.7	400.8	582.0	688.2	672.7
102.5°	71.9	78.5	90.3	105.7	126.3	162.4	242.2	389.6	585.0	751.8	818.3
105°	92.8	98.0	109.1	125.3	145.9	180.5	246.1	367.7	545.9	742.0	895.2
107.5°	113.5	118.5	128.7	144.7	165.5	199.1	256.3	356.8	504.1	677.2	839.8
110°	128.2	132.6	142.2	157.7	179.1	211.4	264.5	354.4	484.1	636.6	792.0





TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	141.2	146.2	155.1	170.0	192.0	223.3	273.3	355.0	471.1	608.3	748.5
115°	162.1	166.5	175.3	190.1	210.0	241.7	286.6	358.1	456.9	573.3	694.7
117.5°	182.3	186.7	194.5	208.7	229.3	258.6	300.8	363.4	449.9	551.1	654.4
120°	195.3	199.6	206.3	221.0	241.7	270.4	310.2	366.9	445.7	539.3	634.3
122.5°	207.1	211.4	218.7	233.4	254.7	281.6	318.5	371.1	443.4	529.3	618.5
125°	223.3	227.6	236.5	251.3	271.8	298.4	331.6	377.2	439.1	515.0	595.3
127.5°	237.0	243.2	252.9	267.0	288.2	314.1	343.7	383.6	436.6	501.7	572.5
130°	244.6	251.9	262.3	277.0	297.7	323.5	351.5	388.3	435.5	492.9	557.7
132.5°	252.3	260.2	271.2	286.4	307.1	331.7	359.1	393.0	434.9	485.9	543.6
135°	262.3	271.2	282.2	299.2	319.8	343.4	369.1	398.6	433.9	476.0	523.9
137.5°	272.9	281.7	293.5	310.4	329.5	352.8	376.8	403.6	433.9	469.0	508.1
140°	279.9	288.8	300.6	316.8	336.0	358.1	380.9	406.0	433.2	465.0	498.0
142.5°	287.1	295.3	307.1	322.7	340.7	362.2	384.5	407.7	433.2	460.8	489.8
145°	299.2	306.5	317.5	332.2	348.5	368.4	389.0	409.6	431.8	455.3	478.2
147.5°	310.8	317.8	328.0	340.3	354.7	373.4	391.5	410.3	429.1	449.8	469.2
150°	319.1	324.9	334.5	345.5	358.8	375.8	392.7	409.6	427.3	445.0	462.7
152.5°	326.1	332.0	340.4	350.8	363.0	378.1	393.3	408.5	424.4	440.9	456.2
155°	337.4	341.9	350.0	358.1	369.1	381.6	394.2	406.7	419.2	433.2	447.2
157.5°	347.1	350.7	357.8	364.3	373.5	384.2	394.2	403.3	414.0	426.0	436.8
160°	353.6	356.6	362.5	368.4	376.5	385.3	394.2	401.5	410.4	420.8	430.3
162.5°	358.9	361.9	366.6	371.9	378.2	386.0	393.6	399.8	407.5	415.9	423.8
165°	366.2	367.7	372.1	375.8	380.2	386.8	392.0	396.4	401.5	408.2	414.1
167.5°	372.2	373.5	376.4	379.0	381.8	386.6	391.0	393.0	396.4	400.5	404.8
170°	375.8	376.5	378.7	380.2	382.4	386.1	389.7	391.2	393.4	396.4	400.1
172.5°	378.7	378.2	380.5	381.4	383.0	385.5	388.0	388.9	389.9	392.3	394.7
175°	381.6	380.9	382.4	382.4	383.1	384.6	386.1	385.3	386.1	386.8	389.0
177.5°	382.6	381.9	383.1	383.1	383.1	383.7	384.9	383.7	383.1	383.7	384.9
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1862.9	1869.4	1872.4	1872.4	1875.9	1874.4	1872.9
5°	1970.0	1981.9	1984.3	1995.6	2003.8	2001.2	2002.5
7.5°	2076.4	2095.6	2114.4	2123.1	2124.4	2129.4	2131.3
10°	2141.9	2157.6	2187.0	2182.6	2204.5	2217.0	2196.3
12.5°	2205.0	2226.1	2246.6	2252.1	2264.6	2268.5	2260.4
15°	2262.0	2273.3	2274.5	2271.4	2275.1	2272.0	2260.1
17.5°	2208.8	2190.5	2153.4	2135.9	2122.0	2101.6	2093.3
20°	2120.7	2066.9	2004.3	1979.3	1949.9	1892.4	1906.2
22.5°	1930.6	1869.3	1806.8	1733.7	1698.8	1644.3	1641.0
25°	1634.7	1529.1	1412.8	1331.4	1283.9	1229.5	1205.7
27.5°	1271.0	1137.9	1042.6	994.4	950.5	907.3	905.6
30°	1031.9	931.8	858.0	816.7	789.9	771.8	775.5
32.5°	869.8	801.3	751.5	717.2	697.3	683.6	683.4
35°	711.1	664.1	632.3	617.8	603.5	593.5	594.1
37.5°	608.5	580.3	562.6	546.7	537.7	532.8	530.1
40°	556.0	532.8	519.1	509.7	502.2	495.3	494.1
42.5°	514.4	495.3	481.5	474.2	467.1	462.3	461.0
45°	456.6	440.9	428.4	420.3	417.2	412.7	412.7
47.5°	406.1	390.8	381.0	375.9	370.5	367.6	367.5
50°	372.1	360.2	351.5	348.4	343.9	342.0	341.5
52.5°	341.6	332.7	326.5	324.3	322.4	320.1	320.5
55°	300.2	295.2	292.7	290.8	287.7	283.9	286.4
57.5°	265.3	261.0	254.3	248.4	245.5	242.9	243.9
60°	240.8	232.1	223.3	216.4	214.5	208.9	208.9
62.5°	209.7	197.5	186.7	182.9	181.0	178.3	177.9
65°	161.4	156.4	153.8	151.4	150.1	150.1	148.8
67.5°	133.7	131.7	128.9	128.4	127.1	126.7	126.3
70°	118.2	115.6	114.4	113.9	112.5	113.2	111.3
72.5°	103.2	101.2	100.9	99.3	98.6	98.7	97.3
75°	81.3	81.3	80.7	80.0	78.8	78.1	78.8
77.5°	62.6	62.7	61.5	61.5	61.3	61.5	60.8
80°	50.0	50.6	50.0	49.4	48.8	49.4	48.8
82.5°	39.5	38.6	38.5	38.4	38.3	37.9	37.8
85°	22.5	23.1	22.5	21.9	21.9	21.9	22.5
87.5°	12.9	13.2	13.4	13.4	13.4	13.4	12.9
90°	22.1	23.6	24.3	24.3	24.3	24.3	24.3
92.5°	55.1	48.9	44.4	43.7	41.4	42.0	40.8
95°	148.1	117.2	100.9	91.3	85.5	83.2	84.0
97.5°	368.5	288.8	235.6	200.4	182.3	171.5	165.3
100°	581.4	480.4	391.2	330.1	298.4	277.0	263.7
102.5°	797.7	723.8	629.3	562.9	508.8	482.1	464.2
105°	978.5	988.1	963.7	918.0	872.3	840.7	830.4
107.5°	965.2	1041.8	1077.5	1083.3	1080.7	1074.4	1060.6
110°	924.0	1018.2	1078.6	1110.3	1124.4	1131.0	1130.2



TEST NUMBER: P331719-830

CATALOG NUMBER: S122RDIP-S865D725U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	875.0	975.8	1045.1	1089.1	1112.6	1125.1	1129.1
115°	808.2	904.7	980.6	1032.9	1066.9	1086.0	1092.7
117.5°	754.0	841.6	912.8	966.1	1001.9	1022.1	1027.7
120°	725.8	803.8	870.9	922.5	957.1	978.5	985.8
122.5°	702.2	776.1	836.7	883.0	917.0	936.0	942.2
125°	671.2	736.0	791.3	834.1	862.0	880.4	886.4
127.5°	641.1	702.3	753.3	790.6	816.8	832.7	837.4
130°	621.1	679.3	727.9	764.0	789.1	803.8	809.7
132.5°	602.3	655.7	701.4	737.0	762.0	775.5	780.8
135°	572.5	621.1	662.3	694.1	718.4	731.6	734.6
137.5°	548.7	587.4	623.3	652.2	673.2	684.8	689.2
140°	533.5	567.3	599.7	623.3	642.4	653.6	658.0
142.5°	519.9	549.0	576.2	598.6	616.0	625.8	626.7
145°	502.5	525.4	546.7	564.4	576.9	584.3	586.4
147.5°	488.3	506.1	521.8	536.4	546.4	551.4	552.7
150°	478.9	494.4	507.7	518.7	527.5	532.0	532.7
152.5°	471.3	484.4	495.9	504.5	512.2	515.5	515.6
155°	459.0	470.0	478.2	486.3	491.4	494.4	492.9
157.5°	446.7	455.9	462.2	468.0	472.3	473.6	473.6
160°	438.4	446.5	451.7	456.9	460.5	461.2	461.2
162.5°	430.7	437.6	441.7	446.8	449.3	450.1	449.4
165°	419.2	424.4	427.3	430.3	433.2	433.2	432.5
167.5°	408.8	412.3	415.0	416.3	417.9	417.7	416.9
170°	402.3	405.2	406.7	407.5	409.6	408.9	407.5
172.5°	396.4	398.8	399.6	400.4	401.4	400.7	399.8
175°	389.7	390.5	391.2	391.2	392.0	391.2	389.7
177.5°	384.9	385.5	385.5	385.5	385.5	384.9	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1

(END OF REPORT)