

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331725-830

Luminaire Tested: **S122RDIP-S865D925U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331725-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D925U830-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6518.8 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	98	94	90	87	90	87	84	81	73	71	69	60	59	58	49	48	47	42
2	90	83	77	72	83	77	72	68	65	61	58	54	52	49	44	42	41	36
3	83	74	67	61	76	68	62	57	58	54	50	49	45	43	40	38	36	32
4	76	66	58	53	70	61	55	49	52	47	43	44	40	37	36	34	32	28
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28	25
6	65	53	46	40	60	50	43	38	43	38	34	36	32	29	30	27	25	22
7	60	48	41	36	55	45	38	34	39	34	30	33	29	26	28	25	23	20
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21	18
9	52	41	33	29	48	38	32	27	33	28	24	28	24	22	24	21	19	17
10	49	37	30	26	45	35	29	25	31	26	22	26	23	20	22	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	29061	29061	29061	29061
5°	32456	29242	25929	29242
10°	36008	29037	22474	29037
15°	37778	28612	17708	28612
20°	32752	27981	15323	27981
25°	21480	27118	13682	27118
30°	14458	26071	12381	26071
35°	11710	24750	11168	24750
40°	10414	23317	10334	23317
45°	9423	21633	9225	21633
50°	8578	19964	8545	19964
55°	8062	18117	7958	18117
60°	6746	16417	6665	16417
65°	5685	14907	6449	14907
70°	5254	13312	6080	13312
75°	4916	11591	5614	11591
80°	4537	9530	5002	9530
85°	4168	7521	4409	7521



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.6	2.6
10°-20°	475.4	7.3
20°-30°	612.6	9.4
30°-40°	582.2	8.9
40°-50°	498.7	7.7
50°-60°	379.8	5.8
60°-70°	240.1	3.7
70°-80°	119.9	1.8
80°-90°	35.6	0.5
90°-100°	195.6	3.0
100°-110°	663.7	10.2
110°-120°	705.1	10.8
120°-130°	580.4	8.9
130°-140°	466.1	7.2
140°-150°	352.2	5.4
150°-160°	247.5	3.8
160°-170°	145.7	2.2
170°-180°	47.4	0.7
0°-30°	1258.6	19.3
0°-40°	1840.8	28.2
0°-60°	2719.4	41.7
0°-90°	3115.0	47.8
90°-120°	1564.4	24.0
90°-150°	2963.2	45.5
90°-180°	3404.0	52.2
0°-180°	6518.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1800	1800	1800	1800	1800	
5°	2002	1804	1600	1804	2002	198
15°	2260	1712	1059	1712	2260	610
25°	1206	1522	768	1522	1206	572
35°	594	1256	567	1256	594	380
45°	413	947	404	947	413	319
55°	286	644	283	644	286	251
65°	149	390	169	390	149	152
75°	79	186	90	186	79	84
85°	22	41	24	41	22	25
90°	31	1	31	1	31	18
95°	107	33	107	33	107	139
105°	1060	115	1060	115	1060	1026
115°	1395	202	1395	202	1395	1366
125°	1132	282	1132	282	1132	1023
135°	938	331	938	331	938	729
145°	749	378	749	378	749	476
155°	629	430	629	430	629	294
165°	552	468	552	468	552	158
175°	498	488	498	488	498	48
180°	489	489	489	489	489	



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1872.9	1874.4	1875.9	1872.4	1872.4	1869.4	1862.9	1857.9	1843.9	1841.9	1841.9
5°	2002.5	2001.2	2003.8	1995.6	1984.3	1981.9	1970.0	1954.4	1938.1	1920.0	1916.2
7.5°	2131.3	2129.4	2124.4	2123.1	2114.4	2095.6	2076.4	2056.1	2029.0	2002.6	1989.3
10°	2196.3	2217.0	2204.5	2182.6	2187.0	2157.6	2141.9	2115.1	2092.5	2053.1	2044.4
12.5°	2260.4	2268.5	2264.6	2252.1	2246.6	2226.1	2205.0	2181.6	2140.0	2104.7	2073.9
15°	2260.1	2272.0	2275.1	2271.4	2274.5	2273.3	2262.0	2242.6	2206.4	2167.6	2133.8
17.5°	2093.3	2101.6	2122.0	2135.9	2153.4	2190.5	2208.8	2215.8	2210.5	2188.3	2164.5
20°	1906.2	1892.4	1949.9	1979.3	2004.3	2066.9	2120.7	2141.4	2174.4	2173.9	2167.6
22.5°	1641.0	1644.3	1698.8	1733.7	1806.8	1869.3	1930.6	2008.3	2072.4	2114.8	2139.6
25°	1205.7	1229.5	1283.9	1331.4	1412.8	1529.1	1634.7	1757.4	1873.0	1964.4	2051.3
27.5°	905.6	907.3	950.5	994.4	1042.6	1137.9	1271.0	1417.4	1582.3	1718.4	1875.0
30°	775.5	771.8	789.9	816.7	858.0	931.8	1031.9	1175.7	1340.2	1545.3	1728.0
32.5°	683.4	683.6	697.3	717.2	751.5	801.3	869.8	986.7	1142.1	1343.7	1557.8
35°	594.1	593.5	603.5	617.8	632.3	664.1	711.1	772.3	879.3	1067.5	1286.4
37.5°	530.1	532.8	537.7	546.7	562.6	580.3	608.5	649.7	725.9	837.2	1021.2
40°	494.1	495.3	502.2	509.7	519.1	532.8	556.0	589.1	644.8	733.6	868.0
42.5°	461.0	462.3	467.1	474.2	481.5	495.3	514.4	543.1	588.2	657.5	768.5
45°	412.7	412.7	417.2	420.3	428.4	440.9	456.6	480.3	511.5	562.9	636.7
47.5°	367.5	367.6	370.5	375.9	381.0	390.8	406.1	425.6	448.3	488.0	551.0
50°	341.5	342.0	343.9	348.4	351.5	360.2	372.1	389.0	412.7	443.4	496.0
52.5°	320.5	320.1	322.4	324.3	326.5	332.7	341.6	356.5	377.8	404.4	447.9
55°	286.4	283.9	287.7	290.8	292.7	295.2	300.2	309.5	327.7	350.2	382.8
57.5°	243.9	242.9	245.5	248.4	254.3	261.0	265.3	271.3	280.7	296.8	329.0
60°	208.9	208.9	214.5	216.4	223.3	232.1	240.8	245.8	255.1	265.8	289.5
62.5°	177.9	178.3	181.0	182.9	186.7	197.5	209.7	220.7	229.6	239.8	255.5
65°	148.8	150.1	150.1	151.4	153.8	156.4	161.4	170.1	185.8	200.1	212.0
67.5°	126.3	126.7	127.1	128.4	128.9	131.7	133.7	137.6	141.2	154.9	169.6
70°	111.3	113.2	112.5	113.9	114.4	115.6	118.2	120.1	125.7	128.8	137.6
72.5°	97.3	98.7	98.6	99.3	100.9	101.2	103.2	105.1	108.7	111.3	116.0
75°	78.8	78.1	78.8	80.0	80.7	81.3	81.3	83.8	85.7	88.2	91.3
77.5°	60.8	61.5	61.3	61.5	61.5	62.7	62.6	63.6	65.5	66.8	68.3
80°	48.8	49.4	48.8	49.4	50.0	50.6	50.0	50.6	52.5	53.8	53.8
82.5°	37.8	37.9	38.3	38.4	38.5	38.6	39.5	39.7	41.0	40.8	41.3
85°	22.5	21.9	21.9	21.9	22.5	23.1	22.5	22.5	23.1	23.1	23.1
87.5°	14.2	14.7	14.7	14.7	14.7	14.5	14.1	15.0	14.7	15.4	14.7
90°	31.0	31.0	31.0	31.0	31.0	30.1	28.2	30.1	31.0	32.0	31.0
92.5°	52.1	53.6	52.9	55.9	56.6	62.5	70.4	82.0	103.3	122.2	120.6
95°	107.3	106.3	109.1	116.7	128.8	149.6	189.1	246.5	322.6	368.7	326.4
97.5°	211.1	219.0	232.7	255.9	300.9	368.7	470.5	575.1	660.3	629.5	474.1
100°	336.8	353.7	381.0	421.4	499.5	613.3	742.2	858.8	878.6	743.1	511.7
102.5°	592.7	615.6	649.6	718.7	803.5	924.2	1018.4	1044.7	959.9	746.9	497.5
105°	1060.2	1073.3	1113.8	1172.1	1230.4	1261.5	1249.2	1142.9	947.3	697.0	469.4
107.5°	1354.2	1371.7	1379.8	1383.0	1375.6	1330.1	1232.3	1072.2	864.7	643.7	455.4
110°	1443.0	1444.0	1435.5	1417.6	1377.1	1300.0	1179.6	1011.3	812.8	618.0	452.5



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1441.5	1436.4	1420.4	1390.5	1334.3	1245.9	1117.2	955.5	776.7	601.4	453.2
115°	1395.1	1386.6	1362.1	1318.8	1252.1	1155.2	1031.9	887.0	731.9	583.2	457.1
117.5°	1312.0	1305.0	1279.1	1233.4	1165.4	1074.4	962.7	835.5	703.6	574.4	463.9
120°	1258.7	1249.2	1221.9	1177.7	1111.9	1026.2	926.6	809.9	688.6	569.1	468.4
122.5°	1203.0	1195.0	1170.7	1127.3	1068.3	990.9	896.5	789.6	675.8	566.1	473.7
125°	1131.6	1124.1	1100.6	1064.9	1010.3	939.7	857.0	760.1	657.5	560.6	481.6
127.5°	1069.2	1063.2	1042.8	1009.4	961.8	896.6	818.6	730.9	640.6	557.4	489.7
130°	1033.8	1026.2	1007.5	975.5	929.4	867.3	793.0	712.1	629.3	555.9	495.8
132.5°	996.9	990.1	972.9	940.8	895.5	837.2	768.9	694.0	620.3	555.2	501.7
135°	937.8	934.1	917.2	886.1	845.6	793.0	730.9	668.8	607.7	554.0	508.9
137.5°	880.0	874.3	859.4	832.7	795.8	749.9	700.6	648.7	598.8	553.8	515.3
140°	840.0	834.4	820.3	795.8	765.7	724.3	681.1	635.9	593.6	553.1	518.3
142.5°	800.1	799.0	786.5	764.2	735.7	701.0	663.7	625.4	588.3	553.1	520.6
145°	748.8	745.9	736.6	720.6	698.0	670.7	641.6	610.5	581.4	551.2	523.0
147.5°	705.7	704.0	697.6	684.9	666.2	646.2	623.5	599.0	574.2	547.9	523.8
150°	680.1	679.2	673.5	662.2	648.1	631.2	611.4	590.8	568.2	545.6	523.0
152.5°	658.3	658.1	653.9	644.1	633.1	618.4	601.6	582.5	562.9	541.9	521.5
155°	629.3	631.2	627.5	620.9	610.5	600.1	586.1	571.0	553.1	535.3	519.2
157.5°	604.6	604.6	602.9	597.5	590.2	582.1	570.2	557.6	543.9	528.5	514.9
160°	588.9	588.9	588.0	583.2	576.6	570.0	559.7	549.3	537.2	524.0	512.6
162.5°	573.8	574.6	573.6	570.4	563.8	558.7	549.9	541.1	531.1	520.2	510.4
165°	552.1	553.1	553.1	549.3	545.6	541.9	535.3	528.7	521.1	512.6	506.1
167.5°	532.3	533.4	533.6	531.5	529.8	526.4	521.9	516.8	511.3	506.1	501.7
170°	520.2	522.1	523.0	520.2	519.2	517.4	513.6	510.8	506.1	502.3	499.5
172.5°	510.4	511.5	512.5	511.1	510.2	509.1	506.1	504.0	500.9	497.9	496.5
175°	497.7	499.5	500.5	499.5	499.5	498.6	497.7	496.7	493.9	492.9	492.0
177.5°	489.9	491.4	492.2	492.2	492.2	492.2	491.4	491.4	489.9	489.2	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1842.9	1838.9	1835.4	1826.4	1821.8	1811.8	1810.3	1809.9	1796.9	1784.3	1780.8
5°	1906.2	1896.2	1881.1	1863.7	1845.5	1826.7	1814.2	1804.2	1779.2	1755.5	1741.7
7.5°	1970.0	1948.4	1922.6	1889.4	1861.8	1830.8	1807.7	1787.1	1751.6	1717.6	1694.7
10°	2017.5	1982.4	1948.0	1902.4	1866.8	1831.7	1799.2	1771.1	1731.1	1686.0	1654.2
12.5°	2047.0	2008.5	1961.1	1916.5	1870.3	1825.7	1782.3	1746.1	1699.0	1652.6	1614.6
15°	2086.9	2045.6	1988.1	1924.3	1864.9	1806.8	1756.7	1711.7	1650.4	1594.7	1548.4
17.5°	2119.6	2062.8	2001.0	1927.2	1858.4	1784.5	1720.0	1662.6	1594.3	1527.2	1472.6
20°	2130.1	2073.8	2002.5	1928.7	1847.4	1760.5	1691.0	1628.5	1555.3	1482.1	1419.7
22.5°	2123.5	2079.8	2000.5	1912.1	1828.9	1738.0	1659.5	1587.0	1505.8	1431.2	1358.6
25°	2079.4	2064.4	1989.3	1893.0	1798.0	1692.3	1601.6	1522.2	1429.6	1349.6	1270.7
27.5°	1976.5	2008.8	1962.4	1859.7	1754.1	1640.8	1538.8	1448.4	1352.4	1262.3	1183.7
30°	1877.5	1951.8	1931.8	1836.7	1718.5	1607.2	1492.8	1398.4	1295.8	1203.2	1125.7
32.5°	1741.8	1864.7	1884.3	1804.8	1682.5	1560.2	1440.3	1346.3	1239.3	1141.7	1066.1
35°	1526.0	1709.8	1794.2	1743.6	1621.0	1489.0	1365.2	1255.7	1148.2	1051.9	976.9
37.5°	1268.4	1518.8	1659.5	1663.1	1550.6	1413.3	1278.6	1169.9	1059.8	965.3	884.0
40°	1101.3	1372.7	1555.9	1596.6	1501.6	1353.3	1217.0	1106.3	998.7	906.2	813.0
42.5°	951.2	1221.6	1446.9	1517.6	1442.0	1294.8	1158.0	1042.3	937.7	850.2	755.0
45°	769.2	1005.6	1253.9	1380.3	1338.3	1202.0	1057.5	947.4	849.2	773.6	682.3
47.5°	648.9	815.5	1055.7	1226.6	1225.9	1101.5	959.3	853.9	762.8	691.9	618.0
50°	580.3	725.5	928.7	1122.6	1138.8	1034.3	899.3	794.8	709.8	635.4	576.0
52.5°	518.8	638.4	821.1	1007.0	1053.3	962.8	831.8	735.4	652.8	584.4	533.5
55°	438.4	530.9	669.8	843.7	913.7	849.9	733.6	643.6	576.6	519.1	475.3
57.5°	370.9	440.3	551.7	691.6	773.3	733.1	637.2	564.0	506.7	454.7	420.1
60°	328.3	385.2	479.7	596.6	686.6	658.6	576.6	508.4	459.7	414.6	382.1
62.5°	288.3	337.2	418.1	513.0	595.6	584.0	517.1	459.9	417.2	376.1	348.6
65°	232.1	267.7	330.8	405.3	471.6	477.2	429.0	390.2	352.1	319.6	295.2
67.5°	184.7	208.0	252.5	315.2	364.9	382.6	353.2	323.6	293.3	268.2	247.0
70°	155.7	174.5	207.0	257.7	303.3	322.1	305.2	282.0	255.8	235.2	217.0
72.5°	126.2	144.5	168.4	205.7	244.8	265.0	259.2	242.5	221.2	204.2	187.0
75°	95.1	100.7	117.0	141.9	172.6	190.1	194.5	185.8	168.8	155.7	145.7
77.5°	70.3	73.7	81.4	94.5	114.6	130.2	136.6	135.5	123.9	116.3	107.0
80°	56.3	58.2	61.9	67.6	82.6	98.2	102.5	102.5	94.4	91.3	81.9
82.5°	42.8	44.1	46.4	49.5	56.6	70.1	75.0	76.1	70.9	66.8	59.4
85°	24.4	23.8	25.0	26.9	28.2	31.9	39.4	40.6	39.4	34.4	32.5
87.5°	13.6	12.7	11.8	10.7	10.9	11.0	12.7	14.7	13.3	12.5	11.9
90°	25.4	18.9	14.1	11.3	9.4	7.5	3.8	0.9	3.8	7.5	9.4
92.5°	93.9	64.0	42.7	33.8	27.4	23.4	16.6	11.5	16.6	23.4	27.4
95°	217.3	135.4	92.2	69.7	54.6	46.1	36.7	32.9	36.7	46.1	54.6
97.5°	292.8	178.7	124.3	98.8	81.4	68.7	58.7	53.6	58.7	68.7	81.4
100°	308.6	193.8	143.9	117.6	98.8	83.7	75.2	72.4	75.2	83.7	98.8
102.5°	309.3	207.4	161.3	134.9	115.4	100.3	91.8	89.7	91.8	100.3	115.4
105°	314.1	230.5	186.2	159.9	139.2	125.1	118.6	114.8	118.6	125.1	139.2
107.5°	327.2	254.2	211.3	184.7	164.3	151.3	144.9	141.9	144.9	151.3	164.3
110°	337.7	269.9	228.6	201.3	181.5	169.3	163.7	159.9	163.7	169.3	181.5



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	349.0	285.0	245.2	217.1	198.1	186.6	180.2	176.4	180.2	186.6	198.1
115°	365.9	308.6	268.1	242.7	223.9	212.6	207.0	202.3	207.0	212.6	223.9
117.5°	384.0	330.2	292.8	266.4	248.4	238.4	232.7	228.9	232.7	238.4	248.4
120°	396.1	345.3	308.6	282.2	263.3	255.0	249.3	245.5	249.3	255.0	263.3
122.5°	406.5	359.5	325.1	298.0	279.2	269.9	264.3	261.4	264.3	269.9	279.2
125°	423.3	381.0	347.1	320.7	302.0	290.7	285.0	282.2	285.0	290.7	302.0
127.5°	438.9	401.0	368.0	340.9	322.8	310.4	302.6	298.8	302.6	310.4	322.8
130°	448.7	412.9	380.0	353.7	334.9	321.7	312.3	308.6	312.3	321.7	334.9
132.5°	458.5	423.5	392.1	365.7	346.2	332.2	322.1	317.5	322.1	332.2	346.2
135°	471.3	438.4	408.2	381.9	360.2	346.2	334.9	331.1	334.9	346.2	360.2
137.5°	481.1	450.4	420.7	396.2	374.8	359.7	348.5	343.9	348.5	359.7	374.8
140°	486.4	457.1	429.0	404.5	383.8	368.7	357.5	353.7	357.5	368.7	383.8
142.5°	490.9	462.4	435.0	412.0	392.1	377.0	366.5	363.4	366.5	377.0	392.1
145°	496.7	470.3	445.0	424.2	405.5	391.3	381.9	378.1	381.9	391.3	405.5
147.5°	499.9	476.7	452.9	434.4	418.8	405.8	396.8	394.0	396.8	405.8	418.8
150°	501.3	479.8	458.1	441.2	427.1	414.8	407.3	404.5	407.3	414.8	427.1
152.5°	502.1	482.8	463.4	448.0	434.6	423.9	416.3	415.0	416.3	423.9	434.6
155°	503.2	487.3	471.3	457.1	446.9	436.5	430.8	429.9	430.8	436.5	446.9
157.5°	503.2	490.5	476.9	465.1	456.8	447.8	443.3	442.3	443.3	447.8	456.8
160°	503.2	492.0	480.7	470.3	462.8	455.2	451.6	450.6	451.6	455.2	462.8
162.5°	502.5	492.8	483.0	474.9	468.1	462.0	458.3	458.8	458.3	462.0	468.1
165°	500.5	493.9	485.4	479.8	475.0	469.4	467.5	468.4	467.5	469.4	475.0
167.5°	499.2	493.7	487.5	483.9	480.5	476.9	475.2	476.4	475.2	476.9	480.5
170°	497.7	492.9	488.2	485.4	483.5	480.7	479.8	481.6	479.8	480.7	483.5
172.5°	495.4	492.2	489.0	486.9	485.8	483.0	483.5	484.7	483.5	483.0	485.8
175°	492.9	491.1	489.2	488.2	488.2	486.4	487.3	488.2	487.3	486.4	488.2
177.5°	491.4	489.9	489.2	489.2	489.2	487.7	488.4	489.9	488.4	487.7	489.2
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1774.3	1770.8	1764.3	1754.4	1748.3	1737.9	1730.8	1734.8	1735.8	1734.8	1733.8
5°	1726.6	1713.5	1695.4	1677.9	1661.6	1644.2	1634.1	1629.8	1621.0	1616.0	1613.5
7.5°	1669.1	1646.4	1620.7	1590.3	1564.3	1537.2	1523.3	1516.5	1498.5	1488.7	1480.3
10°	1626.0	1590.4	1564.7	1524.7	1500.3	1464.6	1440.3	1440.9	1416.5	1402.7	1392.7
12.5°	1578.5	1539.4	1496.7	1460.7	1426.7	1398.1	1368.8	1356.8	1331.0	1317.7	1290.6
15°	1499.7	1454.1	1409.0	1360.2	1325.8	1281.4	1238.9	1186.9	1145.1	1108.8	1098.8
17.5°	1413.6	1357.1	1311.9	1254.6	1195.7	1121.1	1071.8	1041.6	1016.3	997.2	983.0
20°	1354.6	1297.0	1248.9	1162.6	1083.2	1032.6	996.3	973.1	946.9	926.2	914.9
22.5°	1292.5	1232.5	1166.9	1070.5	1008.6	968.0	935.7	909.1	891.3	875.2	864.9
25°	1204.5	1138.8	1030.7	964.3	914.3	871.8	849.2	833.0	814.3	792.4	782.3
27.5°	1111.4	1007.0	929.3	880.1	832.3	804.6	784.4	760.1	743.3	733.5	723.0
30°	1041.9	937.5	876.8	823.0	789.2	758.6	734.8	721.0	704.8	688.0	681.1
32.5°	964.3	880.9	822.7	778.0	743.7	717.6	698.8	676.6	664.8	654.4	640.0
35°	868.0	804.8	751.7	715.5	683.0	661.7	639.8	626.6	605.4	596.6	591.0
37.5°	786.5	731.7	692.0	653.7	628.0	604.5	591.1	570.2	561.0	548.8	537.0
40°	740.5	686.6	648.6	617.3	588.5	571.0	554.1	537.2	523.5	517.8	503.4
42.5°	693.4	649.7	611.5	577.2	558.0	539.4	518.1	505.7	491.4	482.3	473.4
45°	628.5	589.7	557.2	529.0	507.8	488.4	474.7	454.0	445.9	427.7	420.3
47.5°	571.5	535.5	504.4	477.7	456.9	444.3	424.1	408.0	395.0	383.9	374.2
50°	530.9	501.0	470.9	447.1	428.4	410.3	389.6	381.4	361.5	355.8	350.2
52.5°	493.9	465.4	437.9	414.6	395.9	378.2	360.1	349.5	335.9	330.4	326.2
55°	442.1	414.6	388.3	367.7	348.9	330.8	319.6	306.4	300.2	295.8	290.8
57.5°	390.1	365.3	345.3	324.3	305.5	291.1	278.1	270.1	263.6	257.9	251.9
60°	357.1	333.3	315.2	295.8	276.4	264.6	254.5	245.2	237.6	228.8	226.4
62.5°	322.1	301.3	284.6	265.8	248.9	238.0	228.5	219.6	210.7	197.8	194.4
65°	273.9	257.7	240.2	224.5	209.5	198.9	185.1	175.1	171.4	170.1	169.5
67.5°	230.4	215.0	200.0	184.0	170.3	160.5	153.4	151.9	149.3	148.5	146.8
70°	201.3	187.0	172.0	156.9	143.8	141.9	139.5	137.0	133.8	132.6	131.3
72.5°	175.3	160.5	145.4	133.5	127.8	125.5	122.9	120.5	118.3	117.1	116.3
75°	134.5	120.7	110.7	106.3	103.2	101.3	97.6	95.7	94.4	92.6	91.9
77.5°	96.8	89.1	84.5	81.7	78.4	76.4	74.3	72.4	71.1	70.7	69.7
80°	73.8	70.0	66.9	63.2	61.9	59.4	58.8	56.9	57.5	55.7	55.7
82.5°	57.3	52.5	49.9	48.2	46.9	44.9	44.3	43.4	43.5	42.1	42.1
85°	29.4	28.2	26.9	25.6	25.6	23.8	24.4	23.8	23.8	22.5	21.9
87.5°	11.8	11.8	11.8	13.1	14.2	13.9	13.7	13.0	12.6	13.0	12.7
90°	11.3	14.1	18.9	25.4	31.0	32.0	31.0	30.1	28.2	30.1	31.0
92.5°	33.8	42.7	64.0	93.9	120.6	122.2	103.3	82.0	70.4	62.5	56.6
95°	69.7	92.2	135.4	217.3	326.4	368.7	322.6	246.5	189.1	149.6	128.8
97.5°	98.8	124.3	178.7	292.8	474.1	629.5	660.3	575.1	470.5	368.7	300.9
100°	117.6	143.9	193.8	308.6	511.7	743.1	878.6	858.8	742.2	613.3	499.5
102.5°	134.9	161.3	207.4	309.3	497.5	746.9	959.9	1044.7	1018.4	924.2	803.5
105°	159.9	186.2	230.5	314.1	469.4	697.0	947.3	1142.9	1249.2	1261.5	1230.4
107.5°	184.7	211.3	254.2	327.2	455.4	643.7	864.7	1072.2	1232.3	1330.1	1375.6
110°	201.3	228.6	269.9	337.7	452.5	618.0	812.8	1011.3	1179.6	1300.0	1377.1



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.1	245.2	285.0	349.0	453.2	601.4	776.7	955.5	1117.2	1245.9	1334.3
115°	242.7	268.1	308.6	365.9	457.1	583.2	731.9	887.0	1031.9	1155.2	1252.1
117.5°	266.4	292.8	330.2	384.0	463.9	574.4	703.6	835.5	962.7	1074.4	1165.4
120°	282.2	308.6	345.3	396.1	468.4	569.1	688.6	809.9	926.6	1026.2	1111.9
122.5°	298.0	325.1	359.5	406.5	473.7	566.1	675.8	789.6	896.5	990.9	1068.3
125°	320.7	347.1	381.0	423.3	481.6	560.6	657.5	760.1	857.0	939.7	1010.3
127.5°	340.9	368.0	401.0	438.9	489.7	557.4	640.6	730.9	818.6	896.6	961.8
130°	353.7	380.0	412.9	448.7	495.8	555.9	629.3	712.1	793.0	867.3	929.4
132.5°	365.7	392.1	423.5	458.5	501.7	555.2	620.3	694.0	768.9	837.2	895.5
135°	381.9	408.2	438.4	471.3	508.9	554.0	607.7	668.8	730.9	793.0	845.6
137.5°	396.2	420.7	450.4	481.1	515.3	553.8	598.8	648.7	700.6	749.9	795.8
140°	404.5	429.0	457.1	486.4	518.3	553.1	593.6	635.9	681.1	724.3	765.7
142.5°	412.0	435.0	462.4	490.9	520.6	553.1	588.3	625.4	663.7	701.0	735.7
145°	424.2	445.0	470.3	496.7	523.0	551.2	581.4	610.5	641.6	670.7	698.0
147.5°	434.4	452.9	476.7	499.9	523.8	547.9	574.2	599.0	623.5	646.2	666.2
150°	441.2	458.1	479.8	501.3	523.0	545.6	568.2	590.8	611.4	631.2	648.1
152.5°	448.0	463.4	482.8	502.1	521.5	541.9	562.9	582.5	601.6	618.4	633.1
155°	457.1	471.3	487.3	503.2	519.2	535.3	553.1	571.0	586.1	600.1	610.5
157.5°	465.1	476.9	490.5	503.2	514.9	528.5	543.9	557.6	570.2	582.1	590.2
160°	470.3	480.7	492.0	503.2	512.6	524.0	537.2	549.3	559.7	570.0	576.6
162.5°	474.9	483.0	492.8	502.5	510.4	520.2	531.1	541.1	549.9	558.7	563.8
165°	479.8	485.4	493.9	500.5	506.1	512.6	521.1	528.7	535.3	541.9	545.6
167.5°	483.9	487.5	493.7	499.2	501.7	506.1	511.3	516.8	521.9	526.4	529.8
170°	485.4	488.2	492.9	497.7	499.5	502.3	506.1	510.8	513.6	517.4	519.2
172.5°	486.9	489.0	492.2	495.4	496.5	497.9	500.9	504.0	506.1	509.1	510.2
175°	488.2	489.2	491.1	492.9	492.0	492.9	493.9	496.7	497.7	498.6	499.5
177.5°	489.2	489.2	489.9	491.4	489.9	489.2	489.9	491.4	491.4	492.2	492.2
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1728.3	1729.3	1727.8	1728.8	1727.8	1729.3	1728.3	1733.8	1734.8	1735.8	1734.8
5°	1610.3	1602.9	1601.6	1599.8	1601.6	1602.9	1610.3	1613.5	1616.0	1621.0	1629.8
7.5°	1469.5	1468.4	1465.3	1460.9	1465.3	1468.4	1469.5	1480.3	1488.7	1498.5	1516.5
10°	1378.9	1375.8	1375.3	1370.8	1375.3	1375.8	1378.9	1392.7	1402.7	1416.5	1440.9
12.5°	1272.9	1252.7	1250.7	1239.7	1250.7	1252.7	1272.9	1290.6	1317.7	1331.0	1356.8
15°	1083.8	1080.1	1067.5	1059.4	1067.5	1080.1	1083.8	1098.8	1108.8	1145.1	1186.9
17.5°	975.7	963.5	959.6	957.8	959.6	963.5	975.7	983.0	997.2	1016.3	1041.6
20°	906.2	894.9	893.1	891.8	893.1	894.9	906.2	914.9	926.2	946.9	973.1
22.5°	858.2	846.4	841.5	837.7	841.5	846.4	858.2	864.9	875.2	891.3	909.1
25°	776.1	771.8	769.2	768.0	769.2	771.8	776.1	782.3	792.4	814.3	833.0
27.5°	711.9	702.3	700.4	697.2	700.4	702.3	711.9	723.0	733.5	743.3	760.1
30°	675.4	672.3	667.9	664.1	667.9	672.3	675.4	681.1	688.0	704.8	721.0
32.5°	632.4	629.8	625.8	624.2	625.8	629.8	632.4	640.0	654.4	664.8	676.6
35°	584.8	576.0	572.2	566.6	572.2	576.0	584.8	591.0	596.6	605.4	626.6
37.5°	534.3	529.7	524.4	526.3	524.4	529.7	534.3	537.0	548.8	561.0	570.2
40°	495.3	492.2	491.0	490.3	491.0	492.2	495.3	503.4	517.8	523.5	537.2
42.5°	464.3	455.6	452.4	452.2	452.4	455.6	464.3	473.4	482.3	491.4	505.7
45°	417.2	409.0	403.4	404.0	403.4	409.0	417.2	420.3	427.7	445.9	454.0
47.5°	368.8	368.6	365.1	366.3	365.1	368.6	368.8	374.2	383.9	395.0	408.0
50°	345.8	342.0	339.6	340.2	339.6	342.0	345.8	350.2	355.8	361.5	381.4
52.5°	323.9	320.6	318.6	321.2	318.6	320.6	323.9	326.2	330.4	335.9	349.5
55°	287.7	283.9	283.3	282.7	283.3	283.9	287.7	290.8	295.8	300.2	306.4
57.5°	247.3	244.8	241.0	239.4	241.0	244.8	247.3	251.9	257.9	263.6	270.1
60°	218.3	213.3	207.0	206.4	207.0	213.3	218.3	226.4	228.8	237.6	245.2
62.5°	191.7	190.8	189.5	189.4	189.5	190.8	191.7	194.4	197.8	210.7	219.6
65°	168.2	167.6	168.2	168.8	168.2	167.6	168.2	169.5	170.1	171.4	175.1
67.5°	146.6	145.4	144.3	144.9	144.3	145.4	146.6	146.8	148.5	149.3	151.9
70°	130.1	129.4	128.8	128.8	128.8	129.4	130.1	131.3	132.6	133.8	137.0
72.5°	114.0	114.0	113.3	112.8	113.3	114.0	114.0	116.3	117.1	118.3	120.5
75°	91.3	90.0	90.0	90.0	90.0	90.0	91.3	91.9	92.6	94.4	95.7
77.5°	69.6	68.9	68.3	67.8	68.3	68.9	69.6	69.7	70.7	71.1	72.4
80°	55.0	54.4	53.8	53.8	53.8	54.4	55.0	55.7	55.7	57.5	56.9
82.5°	42.0	41.4	41.3	40.8	41.3	41.4	42.0	42.1	42.1	43.5	43.4
85°	22.5	23.1	22.5	23.8	22.5	23.1	22.5	21.9	22.5	23.8	23.8
87.5°	12.7	12.3	12.7	12.3	12.7	12.3	12.7	12.7	13.0	12.6	13.0
90°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.0	30.1	28.2	30.1
92.5°	55.9	52.9	53.6	52.1	53.6	52.9	55.9	56.6	62.5	70.4	82.0
95°	116.7	109.1	106.3	107.3	106.3	109.1	116.7	128.8	149.6	189.1	246.5
97.5°	255.9	232.7	219.0	211.1	219.0	232.7	255.9	300.9	368.7	470.5	575.1
100°	421.4	381.0	353.7	336.8	353.7	381.0	421.4	499.5	613.3	742.2	858.8
102.5°	718.7	649.6	615.6	592.7	615.6	649.6	718.7	803.5	924.2	1018.4	1044.7
105°	1172.1	1113.8	1073.3	1060.2	1073.3	1113.8	1172.1	1230.4	1261.5	1249.2	1142.9
107.5°	1383.0	1379.8	1371.7	1354.2	1371.7	1379.8	1383.0	1375.6	1330.1	1232.3	1072.2
110°	1417.6	1435.5	1444.0	1443.0	1444.0	1435.5	1417.6	1377.1	1300.0	1179.6	1011.3



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1390.5	1420.4	1436.4	1441.5	1436.4	1420.4	1390.5	1334.3	1245.9	1117.2	955.5
115°	1318.8	1362.1	1386.6	1395.1	1386.6	1362.1	1318.8	1252.1	1155.2	1031.9	887.0
117.5°	1233.4	1279.1	1305.0	1312.0	1305.0	1279.1	1233.4	1165.4	1074.4	962.7	835.5
120°	1177.7	1221.9	1249.2	1258.7	1249.2	1221.9	1177.7	1111.9	1026.2	926.6	809.9
122.5°	1127.3	1170.7	1195.0	1203.0	1195.0	1170.7	1127.3	1068.3	990.9	896.5	789.6
125°	1064.9	1100.6	1124.1	1131.6	1124.1	1100.6	1064.9	1010.3	939.7	857.0	760.1
127.5°	1009.4	1042.8	1063.2	1069.2	1063.2	1042.8	1009.4	961.8	896.6	818.6	730.9
130°	975.5	1007.5	1026.2	1033.8	1026.2	1007.5	975.5	929.4	867.3	793.0	712.1
132.5°	940.8	972.9	990.1	996.9	990.1	972.9	940.8	895.5	837.2	768.9	694.0
135°	886.1	917.2	934.1	937.8	934.1	917.2	886.1	845.6	793.0	730.9	668.8
137.5°	832.7	859.4	874.3	880.0	874.3	859.4	832.7	795.8	749.9	700.6	648.7
140°	795.8	820.3	834.4	840.0	834.4	820.3	795.8	765.7	724.3	681.1	635.9
142.5°	764.2	786.5	799.0	800.1	799.0	786.5	764.2	735.7	701.0	663.7	625.4
145°	720.6	736.6	745.9	748.8	745.9	736.6	720.6	698.0	670.7	641.6	610.5
147.5°	684.9	697.6	704.0	705.7	704.0	697.6	684.9	666.2	646.2	623.5	599.0
150°	662.2	673.5	679.2	680.1	679.2	673.5	662.2	648.1	631.2	611.4	590.8
152.5°	644.1	653.9	658.1	658.3	658.1	653.9	644.1	633.1	618.4	601.6	582.5
155°	620.9	627.5	631.2	629.3	631.2	627.5	620.9	610.5	600.1	586.1	571.0
157.5°	597.5	602.9	604.6	604.6	604.6	602.9	597.5	590.2	582.1	570.2	557.6
160°	583.2	588.0	588.9	588.9	588.9	588.0	583.2	576.6	570.0	559.7	549.3
162.5°	570.4	573.6	574.6	573.8	574.6	573.6	570.4	563.8	558.7	549.9	541.1
165°	549.3	553.1	553.1	552.1	553.1	553.1	549.3	545.6	541.9	535.3	528.7
167.5°	531.5	533.6	533.4	532.3	533.4	533.6	531.5	529.8	526.4	521.9	516.8
170°	520.2	523.0	522.1	520.2	522.1	523.0	520.2	519.2	517.4	513.6	510.8
172.5°	511.1	512.5	511.5	510.4	511.5	512.5	511.1	510.2	509.1	506.1	504.0
175°	499.5	500.5	499.5	497.7	499.5	500.5	499.5	499.5	498.6	497.7	496.7
177.5°	492.2	492.2	491.4	489.9	491.4	492.2	492.2	492.2	492.2	491.4	491.4
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1730.8	1737.9	1748.3	1754.4	1764.3	1770.8	1774.3	1780.8	1784.3	1796.9	1809.9
5°	1634.1	1644.2	1661.6	1677.9	1695.4	1713.5	1726.6	1741.7	1755.5	1779.2	1804.2
7.5°	1523.3	1537.2	1564.3	1590.3	1620.7	1646.4	1669.1	1694.7	1717.6	1751.6	1787.1
10°	1440.3	1464.6	1500.3	1524.7	1564.7	1590.4	1626.0	1654.2	1686.0	1731.1	1771.1
12.5°	1368.8	1398.1	1426.7	1460.7	1496.7	1539.4	1578.5	1614.6	1652.6	1699.0	1746.1
15°	1238.9	1281.4	1325.8	1360.2	1409.0	1454.1	1499.7	1548.4	1594.7	1650.4	1711.7
17.5°	1071.8	1121.1	1195.7	1254.6	1311.9	1357.1	1413.6	1472.6	1527.2	1594.3	1662.6
20°	996.3	1032.6	1083.2	1162.6	1248.9	1297.0	1354.6	1419.7	1482.1	1555.3	1628.5
22.5°	935.7	968.0	1008.6	1070.5	1166.9	1232.5	1292.5	1358.6	1431.2	1505.8	1587.0
25°	849.2	871.8	914.3	964.3	1030.7	1138.8	1204.5	1270.7	1349.6	1429.6	1522.2
27.5°	784.4	804.6	832.3	880.1	929.3	1007.0	1111.4	1183.7	1262.3	1352.4	1448.4
30°	734.8	758.6	789.2	823.0	876.8	937.5	1041.9	1125.7	1203.2	1295.8	1398.4
32.5°	698.8	717.6	743.7	778.0	822.7	880.9	964.3	1066.1	1141.7	1239.3	1346.3
35°	639.8	661.7	683.0	715.5	751.7	804.8	868.0	976.9	1051.9	1148.2	1255.7
37.5°	591.1	604.5	628.0	653.7	692.0	731.7	786.5	884.0	965.3	1059.8	1169.9
40°	554.1	571.0	588.5	617.3	648.6	686.6	740.5	813.0	906.2	998.7	1106.3
42.5°	518.1	539.4	558.0	577.2	611.5	649.7	693.4	755.0	850.2	937.7	1042.3
45°	474.7	488.4	507.8	529.0	557.2	589.7	628.5	682.3	773.6	849.2	947.4
47.5°	424.1	444.3	456.9	477.7	504.4	535.5	571.5	618.0	691.9	762.8	853.9
50°	389.6	410.3	428.4	447.1	470.9	501.0	530.9	576.0	635.4	709.8	794.8
52.5°	360.1	378.2	395.9	414.6	437.9	465.4	493.9	533.5	584.4	652.8	735.4
55°	319.6	330.8	348.9	367.7	388.3	414.6	442.1	475.3	519.1	576.6	643.6
57.5°	278.1	291.1	305.5	324.3	345.3	365.3	390.1	420.1	454.7	506.7	564.0
60°	254.5	264.6	276.4	295.8	315.2	333.3	357.1	382.1	414.6	459.7	508.4
62.5°	228.5	238.0	248.9	265.8	284.6	301.3	322.1	348.6	376.1	417.2	459.9
65°	185.1	198.9	209.5	224.5	240.2	257.7	273.9	295.2	319.6	352.1	390.2
67.5°	153.4	160.5	170.3	184.0	200.0	215.0	230.4	247.0	268.2	293.3	323.6
70°	139.5	141.9	143.8	156.9	172.0	187.0	201.3	217.0	235.2	255.8	282.0
72.5°	122.9	125.5	127.8	133.5	145.4	160.5	175.3	187.0	204.2	221.2	242.5
75°	97.6	101.3	103.2	106.3	110.7	120.7	134.5	145.7	155.7	168.8	185.8
77.5°	74.3	76.4	78.4	81.7	84.5	89.1	96.8	107.0	116.3	123.9	135.5
80°	58.8	59.4	61.9	63.2	66.9	70.0	73.8	81.9	91.3	94.4	102.5
82.5°	44.3	44.9	46.9	48.2	49.9	52.5	57.3	59.4	66.8	70.9	76.1
85°	24.4	23.8	25.6	25.6	26.9	28.2	29.4	32.5	34.4	39.4	40.6
87.5°	13.7	13.9	14.2	13.1	11.8	11.8	11.8	11.9	12.5	13.3	14.7
90°	31.0	32.0	31.0	25.4	18.9	14.1	11.3	9.4	7.5	3.8	0.9
92.5°	103.3	122.2	120.6	93.9	64.0	42.7	33.8	27.4	23.4	16.6	11.5
95°	322.6	368.7	326.4	217.3	135.4	92.2	69.7	54.6	46.1	36.7	32.9
97.5°	660.3	629.5	474.1	292.8	178.7	124.3	98.8	81.4	68.7	58.7	53.6
100°	878.6	743.1	511.7	308.6	193.8	143.9	117.6	98.8	83.7	75.2	72.4
102.5°	959.9	746.9	497.5	309.3	207.4	161.3	134.9	115.4	100.3	91.8	89.7
105°	947.3	697.0	469.4	314.1	230.5	186.2	159.9	139.2	125.1	118.6	114.8
107.5°	864.7	643.7	455.4	327.2	254.2	211.3	184.7	164.3	151.3	144.9	141.9
110°	812.8	618.0	452.5	337.7	269.9	228.6	201.3	181.5	169.3	163.7	159.9



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	776.7	601.4	453.2	349.0	285.0	245.2	217.1	198.1	186.6	180.2	176.4
115°	731.9	583.2	457.1	365.9	308.6	268.1	242.7	223.9	212.6	207.0	202.3
117.5°	703.6	574.4	463.9	384.0	330.2	292.8	266.4	248.4	238.4	232.7	228.9
120°	688.6	569.1	468.4	396.1	345.3	308.6	282.2	263.3	255.0	249.3	245.5
122.5°	675.8	566.1	473.7	406.5	359.5	325.1	298.0	279.2	269.9	264.3	261.4
125°	657.5	560.6	481.6	423.3	381.0	347.1	320.7	302.0	290.7	285.0	282.2
127.5°	640.6	557.4	489.7	438.9	401.0	368.0	340.9	322.8	310.4	302.6	298.8
130°	629.3	555.9	495.8	448.7	412.9	380.0	353.7	334.9	321.7	312.3	308.6
132.5°	620.3	555.2	501.7	458.5	423.5	392.1	365.7	346.2	332.2	322.1	317.5
135°	607.7	554.0	508.9	471.3	438.4	408.2	381.9	360.2	346.2	334.9	331.1
137.5°	598.8	553.8	515.3	481.1	450.4	420.7	396.2	374.8	359.7	348.5	343.9
140°	593.6	553.1	518.3	486.4	457.1	429.0	404.5	383.8	368.7	357.5	353.7
142.5°	588.3	553.1	520.6	490.9	462.4	435.0	412.0	392.1	377.0	366.5	363.4
145°	581.4	551.2	523.0	496.7	470.3	445.0	424.2	405.5	391.3	381.9	378.1
147.5°	574.2	547.9	523.8	499.9	476.7	452.9	434.4	418.8	405.8	396.8	394.0
150°	568.2	545.6	523.0	501.3	479.8	458.1	441.2	427.1	414.8	407.3	404.5
152.5°	562.9	541.9	521.5	502.1	482.8	463.4	448.0	434.6	423.9	416.3	415.0
155°	553.1	535.3	519.2	503.2	487.3	471.3	457.1	446.9	436.5	430.8	429.9
157.5°	543.9	528.5	514.9	503.2	490.5	476.9	465.1	456.8	447.8	443.3	442.3
160°	537.2	524.0	512.6	503.2	492.0	480.7	470.3	462.8	455.2	451.6	450.6
162.5°	531.1	520.2	510.4	502.5	492.8	483.0	474.9	468.1	462.0	458.3	458.8
165°	521.1	512.6	506.1	500.5	493.9	485.4	479.8	475.0	469.4	467.5	468.4
167.5°	511.3	506.1	501.7	499.2	493.7	487.5	483.9	480.5	476.9	475.2	476.4
170°	506.1	502.3	499.5	497.7	492.9	488.2	485.4	483.5	480.7	479.8	481.6
172.5°	500.9	497.9	496.5	495.4	492.2	489.0	486.9	485.8	483.0	483.5	484.7
175°	493.9	492.9	492.0	492.9	491.1	489.2	488.2	488.2	486.4	487.3	488.2
177.5°	489.9	489.2	489.9	491.4	489.9	489.2	489.2	489.2	487.7	488.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1810.3	1811.8	1821.8	1826.4	1835.4	1838.9	1842.9	1841.9	1841.9	1843.9	1857.9
5°	1814.2	1826.7	1845.5	1863.7	1881.1	1896.2	1906.2	1916.2	1920.0	1938.1	1954.4
7.5°	1807.7	1830.8	1861.8	1889.4	1922.6	1948.4	1970.0	1989.3	2002.6	2029.0	2056.1
10°	1799.2	1831.7	1866.8	1902.4	1948.0	1982.4	2017.5	2044.4	2053.1	2092.5	2115.1
12.5°	1782.3	1825.7	1870.3	1916.5	1961.1	2008.5	2047.0	2073.9	2104.7	2140.0	2181.6
15°	1756.7	1806.8	1864.9	1924.3	1988.1	2045.6	2086.9	2133.8	2167.6	2206.4	2242.6
17.5°	1720.0	1784.5	1858.4	1927.2	2001.0	2062.8	2119.6	2164.5	2188.3	2210.5	2215.8
20°	1691.0	1760.5	1847.4	1928.7	2002.5	2073.8	2130.1	2167.6	2173.9	2174.4	2141.4
22.5°	1659.5	1738.0	1828.9	1912.1	2000.5	2079.8	2123.5	2139.6	2114.8	2072.4	2008.3
25°	1601.6	1692.3	1798.0	1893.0	1989.3	2064.4	2079.4	2051.3	1964.4	1873.0	1757.4
27.5°	1538.8	1640.8	1754.1	1859.7	1962.4	2008.8	1976.5	1875.0	1718.4	1582.3	1417.4
30°	1492.8	1607.2	1718.5	1836.7	1931.8	1951.8	1877.5	1728.0	1545.3	1340.2	1175.7
32.5°	1440.3	1560.2	1682.5	1804.8	1884.3	1864.7	1741.8	1557.8	1343.7	1142.1	986.7
35°	1365.2	1489.0	1621.0	1743.6	1794.2	1709.8	1526.0	1286.4	1067.5	879.3	772.3
37.5°	1278.6	1413.3	1550.6	1663.1	1659.5	1518.8	1268.4	1021.2	837.2	725.9	649.7
40°	1217.0	1353.3	1501.6	1596.6	1555.9	1372.7	1101.3	868.0	733.6	644.8	589.1
42.5°	1158.0	1294.8	1442.0	1517.6	1446.9	1221.6	951.2	768.5	657.5	588.2	543.1
45°	1057.5	1202.0	1338.3	1380.3	1253.9	1005.6	769.2	636.7	562.9	511.5	480.3
47.5°	959.3	1101.5	1225.9	1226.6	1055.7	815.5	648.9	551.0	488.0	448.3	425.6
50°	899.3	1034.3	1138.8	1122.6	928.7	725.5	580.3	496.0	443.4	412.7	389.0
52.5°	831.8	962.8	1053.3	1007.0	821.1	638.4	518.8	447.9	404.4	377.8	356.5
55°	733.6	849.9	913.7	843.7	669.8	530.9	438.4	382.8	350.2	327.7	309.5
57.5°	637.2	733.1	773.3	691.6	551.7	440.3	370.9	329.0	296.8	280.7	271.3
60°	576.6	658.6	686.6	596.6	479.7	385.2	328.3	289.5	265.8	255.1	245.8
62.5°	517.1	584.0	595.6	513.0	418.1	337.2	288.3	255.5	239.8	229.6	220.7
65°	429.0	477.2	471.6	405.3	330.8	267.7	232.1	212.0	200.1	185.8	170.1
67.5°	353.2	382.6	364.9	315.2	252.5	208.0	184.7	169.6	154.9	141.2	137.6
70°	305.2	322.1	303.3	257.7	207.0	174.5	155.7	137.6	128.8	125.7	120.1
72.5°	259.2	265.0	244.8	205.7	168.4	144.5	126.2	116.0	111.3	108.7	105.1
75°	194.5	190.1	172.6	141.9	117.0	100.7	95.1	91.3	88.2	85.7	83.8
77.5°	136.6	130.2	114.6	94.5	81.4	73.7	70.3	68.3	66.8	65.5	63.6
80°	102.5	98.2	82.6	67.6	61.9	58.2	56.3	53.8	53.8	52.5	50.6
82.5°	75.0	70.1	56.6	49.5	46.4	44.1	42.8	41.3	40.8	41.0	39.7
85°	39.4	31.9	28.2	26.9	25.0	23.8	24.4	23.1	23.1	23.1	22.5
87.5°	12.7	11.0	10.9	10.7	11.8	12.7	13.6	14.7	15.4	14.7	15.0
90°	3.8	7.5	9.4	11.3	14.1	18.9	25.4	31.0	32.0	31.0	30.1
92.5°	16.6	23.4	27.4	33.8	42.7	64.0	93.9	120.6	122.2	103.3	82.0
95°	36.7	46.1	54.6	69.7	92.2	135.4	217.3	326.4	368.7	322.6	246.5
97.5°	58.7	68.7	81.4	98.8	124.3	178.7	292.8	474.1	629.5	660.3	575.1
100°	75.2	83.7	98.8	117.6	143.9	193.8	308.6	511.7	743.1	878.6	858.8
102.5°	91.8	100.3	115.4	134.9	161.3	207.4	309.3	497.5	746.9	959.9	1044.7
105°	118.6	125.1	139.2	159.9	186.2	230.5	314.1	469.4	697.0	947.3	1142.9
107.5°	144.9	151.3	164.3	184.7	211.3	254.2	327.2	455.4	643.7	864.7	1072.2
110°	163.7	169.3	181.5	201.3	228.6	269.9	337.7	452.5	618.0	812.8	1011.3



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	180.2	186.6	198.1	217.1	245.2	285.0	349.0	453.2	601.4	776.7	955.5
115°	207.0	212.6	223.9	242.7	268.1	308.6	365.9	457.1	583.2	731.9	887.0
117.5°	232.7	238.4	248.4	266.4	292.8	330.2	384.0	463.9	574.4	703.6	835.5
120°	249.3	255.0	263.3	282.2	308.6	345.3	396.1	468.4	569.1	688.6	809.9
122.5°	264.3	269.9	279.2	298.0	325.1	359.5	406.5	473.7	566.1	675.8	789.6
125°	285.0	290.7	302.0	320.7	347.1	381.0	423.3	481.6	560.6	657.5	760.1
127.5°	302.6	310.4	322.8	340.9	368.0	401.0	438.9	489.7	557.4	640.6	730.9
130°	312.3	321.7	334.9	353.7	380.0	412.9	448.7	495.8	555.9	629.3	712.1
132.5°	322.1	332.2	346.2	365.7	392.1	423.5	458.5	501.7	555.2	620.3	694.0
135°	334.9	346.2	360.2	381.9	408.2	438.4	471.3	508.9	554.0	607.7	668.8
137.5°	348.5	359.7	374.8	396.2	420.7	450.4	481.1	515.3	553.8	598.8	648.7
140°	357.5	368.7	383.8	404.5	429.0	457.1	486.4	518.3	553.1	593.6	635.9
142.5°	366.5	377.0	392.1	412.0	435.0	462.4	490.9	520.6	553.1	588.3	625.4
145°	381.9	391.3	405.5	424.2	445.0	470.3	496.7	523.0	551.2	581.4	610.5
147.5°	396.8	405.8	418.8	434.4	452.9	476.7	499.9	523.8	547.9	574.2	599.0
150°	407.3	414.8	427.1	441.2	458.1	479.8	501.3	523.0	545.6	568.2	590.8
152.5°	416.3	423.9	434.6	448.0	463.4	482.8	502.1	521.5	541.9	562.9	582.5
155°	430.8	436.5	446.9	457.1	471.3	487.3	503.2	519.2	535.3	553.1	571.0
157.5°	443.3	447.8	456.8	465.1	476.9	490.5	503.2	514.9	528.5	543.9	557.6
160°	451.6	455.2	462.8	470.3	480.7	492.0	503.2	512.6	524.0	537.2	549.3
162.5°	458.3	462.0	468.1	474.9	483.0	492.8	502.5	510.4	520.2	531.1	541.1
165°	467.5	469.4	475.0	479.8	485.4	493.9	500.5	506.1	512.6	521.1	528.7
167.5°	475.2	476.9	480.5	483.9	487.5	493.7	499.2	501.7	506.1	511.3	516.8
170°	479.8	480.7	483.5	485.4	488.2	492.9	497.7	499.5	502.3	506.1	510.8
172.5°	483.5	483.0	485.8	486.9	489.0	492.2	495.4	496.5	497.9	500.9	504.0
175°	487.3	486.4	488.2	488.2	489.2	491.1	492.9	492.0	492.9	493.9	496.7
177.5°	488.4	487.7	489.2	489.2	489.2	489.9	491.4	489.9	489.2	489.9	491.4
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1862.9	1869.4	1872.4	1872.4	1875.9	1874.4	1872.9
5°	1970.0	1981.9	1984.3	1995.6	2003.8	2001.2	2002.5
7.5°	2076.4	2095.6	2114.4	2123.1	2124.4	2129.4	2131.3
10°	2141.9	2157.6	2187.0	2182.6	2204.5	2217.0	2196.3
12.5°	2205.0	2226.1	2246.6	2252.1	2264.6	2268.5	2260.4
15°	2262.0	2273.3	2274.5	2271.4	2275.1	2272.0	2260.1
17.5°	2208.8	2190.5	2153.4	2135.9	2122.0	2101.6	2093.3
20°	2120.7	2066.9	2004.3	1979.3	1949.9	1892.4	1906.2
22.5°	1930.6	1869.3	1806.8	1733.7	1698.8	1644.3	1641.0
25°	1634.7	1529.1	1412.8	1331.4	1283.9	1229.5	1205.7
27.5°	1271.0	1137.9	1042.6	994.4	950.5	907.3	905.6
30°	1031.9	931.8	858.0	816.7	789.9	771.8	775.5
32.5°	869.8	801.3	751.5	717.2	697.3	683.6	683.4
35°	711.1	664.1	632.3	617.8	603.5	593.5	594.1
37.5°	608.5	580.3	562.6	546.7	537.7	532.8	530.1
40°	556.0	532.8	519.1	509.7	502.2	495.3	494.1
42.5°	514.4	495.3	481.5	474.2	467.1	462.3	461.0
45°	456.6	440.9	428.4	420.3	417.2	412.7	412.7
47.5°	406.1	390.8	381.0	375.9	370.5	367.6	367.5
50°	372.1	360.2	351.5	348.4	343.9	342.0	341.5
52.5°	341.6	332.7	326.5	324.3	322.4	320.1	320.5
55°	300.2	295.2	292.7	290.8	287.7	283.9	286.4
57.5°	265.3	261.0	254.3	248.4	245.5	242.9	243.9
60°	240.8	232.1	223.3	216.4	214.5	208.9	208.9
62.5°	209.7	197.5	186.7	182.9	181.0	178.3	177.9
65°	161.4	156.4	153.8	151.4	150.1	150.1	148.8
67.5°	133.7	131.7	128.9	128.4	127.1	126.7	126.3
70°	118.2	115.6	114.4	113.9	112.5	113.2	111.3
72.5°	103.2	101.2	100.9	99.3	98.6	98.7	97.3
75°	81.3	81.3	80.7	80.0	78.8	78.1	78.8
77.5°	62.6	62.7	61.5	61.5	61.3	61.5	60.8
80°	50.0	50.6	50.0	49.4	48.8	49.4	48.8
82.5°	39.5	38.6	38.5	38.4	38.3	37.9	37.8
85°	22.5	23.1	22.5	21.9	21.9	21.9	22.5
87.5°	14.1	14.5	14.7	14.7	14.7	14.7	14.2
90°	28.2	30.1	31.0	31.0	31.0	31.0	31.0
92.5°	70.4	62.5	56.6	55.9	52.9	53.6	52.1
95°	189.1	149.6	128.8	116.7	109.1	106.3	107.3
97.5°	470.5	368.7	300.9	255.9	232.7	219.0	211.1
100°	742.2	613.3	499.5	421.4	381.0	353.7	336.8
102.5°	1018.4	924.2	803.5	718.7	649.6	615.6	592.7
105°	1249.2	1261.5	1230.4	1172.1	1113.8	1073.3	1060.2
107.5°	1232.3	1330.1	1375.6	1383.0	1379.8	1371.7	1354.2
110°	1179.6	1300.0	1377.1	1417.6	1435.5	1444.0	1443.0



TEST NUMBER: P331725-830

CATALOG NUMBER: S122RDIP-S865D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1117.2	1245.9	1334.3	1390.5	1420.4	1436.4	1441.5
115°	1031.9	1155.2	1252.1	1318.8	1362.1	1386.6	1395.1
117.5°	962.7	1074.4	1165.4	1233.4	1279.1	1305.0	1312.0
120°	926.6	1026.2	1111.9	1177.7	1221.9	1249.2	1258.7
122.5°	896.5	990.9	1068.3	1127.3	1170.7	1195.0	1203.0
125°	857.0	939.7	1010.3	1064.9	1100.6	1124.1	1131.6
127.5°	818.6	896.6	961.8	1009.4	1042.8	1063.2	1069.2
130°	793.0	867.3	929.4	975.5	1007.5	1026.2	1033.8
132.5°	768.9	837.2	895.5	940.8	972.9	990.1	996.9
135°	730.9	793.0	845.6	886.1	917.2	934.1	937.8
137.5°	700.6	749.9	795.8	832.7	859.4	874.3	880.0
140°	681.1	724.3	765.7	795.8	820.3	834.4	840.0
142.5°	663.7	701.0	735.7	764.2	786.5	799.0	800.1
145°	641.6	670.7	698.0	720.6	736.6	745.9	748.8
147.5°	623.5	646.2	666.2	684.9	697.6	704.0	705.7
150°	611.4	631.2	648.1	662.2	673.5	679.2	680.1
152.5°	601.6	618.4	633.1	644.1	653.9	658.1	658.3
155°	586.1	600.1	610.5	620.9	627.5	631.2	629.3
157.5°	570.2	582.1	590.2	597.5	602.9	604.6	604.6
160°	559.7	570.0	576.6	583.2	588.0	588.9	588.9
162.5°	549.9	558.7	563.8	570.4	573.6	574.6	573.8
165°	535.3	541.9	545.6	549.3	553.1	553.1	552.1
167.5°	521.9	526.4	529.8	531.5	533.6	533.4	532.3
170°	513.6	517.4	519.2	520.2	523.0	522.1	520.2
172.5°	506.1	509.1	510.2	511.1	512.5	511.5	510.4
175°	497.7	498.6	499.5	499.5	500.5	499.5	497.7
177.5°	491.4	492.2	492.2	492.2	492.2	491.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2

(END OF REPORT)