

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331249-930

Luminaire Tested: **S122DIP-S290D530U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331249-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S290D530U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2787.8 lumens  
Efficiency: N/A  
Efficacy: 108.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



62% Up  
38% Dn



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24
4	73	63	55	50	66	57	51	46	47	43	39	38	35	32	29	27	25	21
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22	19
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	22	20	17
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7781	7781	7781	7781
5°	8723	7831	6940	7831
10°	9996	7768	6005	7768
15°	11057	7626	5307	7626
20°	10890	7472	4837	7472
25°	9818	7269	4541	7269
30°	8114	6943	4323	6943
35°	5913	6603	4169	6603
40°	4723	6203	4083	6203
45°	4128	5740	3966	5740
50°	3881	5290	3888	5290
55°	3575	4833	3783	4833
60°	3278	4346	3626	4346
65°	2988	3912	3465	3912
70°	2710	3489	3238	3489
75°	2408	3013	2863	3013
80°	2073	2492	2306	2492
85°	1853	1853	1371	1853



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.9	1.6
10°-20°	133.4	4.8
20°-30°	193.6	6.9
30°-40°	204.3	7.3
40°-50°	180.9	6.5
50°-60°	144.4	5.2
60°-70°	98.1	3.5
70°-80°	50.3	1.8
80°-90°	13.6	0.5
90°-100°	19.6	0.7
100°-110°	71.9	2.6
110°-120°	192.3	6.9
120°-130°	317.4	11.4
130°-140°	337.5	12.1
140°-150°	313.7	11.3
150°-160°	252.2	9.0
160°-170°	162.5	5.8
170°-180°	55.9	2.0
0°-30°	373.0	13.4
0°-40°	577.3	20.7
0°-60°	902.6	32.4
0°-90°	1064.6	38.2
90°-120°	283.8	10.2
90°-150°	1252.5	44.9
90°-180°	1723.0	61.8
0°-180°	2787.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	482	482	482	482	482	
5°	538	483	428	483	538	54
15°	662	456	318	456	662	183
25°	551	408	255	408	551	249
35°	300	335	212	335	300	195
45°	181	251	174	251	181	142
55°	127	172	134	172	127	114
65°	78	102	91	102	78	78
75°	39	48	46	48	39	41
85°	10	10	7	10	10	11
90°	12	0	12	0	12	6
95°	18	28	18	28	18	17
105°	32	129	32	129	32	34
115°	35	245	35	245	35	87
125°	364	346	364	346	364	315
135°	442	428	442	428	442	341
145°	504	496	504	496	504	315
155°	547	547	547	547	547	252
165°	575	576	575	576	575	162
175°	586	589	586	589	586	56
180°	588	588	588	588	588	



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	504.1	504.3	504.6	502.2	501.9	501.9	499.9	498.1	495.9	493.2	493.5
5°	538.2	540.2	541.0	538.7	535.4	535.1	531.9	526.8	521.9	518.0	515.3
7.5°	578.9	579.7	577.9	574.9	572.5	568.0	562.1	556.4	548.4	541.0	535.6
10°	609.7	610.8	607.6	603.4	599.9	594.7	586.2	577.5	567.0	556.8	548.6
12.5°	633.1	635.9	631.8	631.3	625.3	618.1	608.0	603.6	588.7	574.5	565.7
15°	661.5	661.4	661.8	658.2	653.8	652.6	642.0	630.2	609.4	601.0	586.5
17.5°	653.3	656.2	657.5	657.4	657.3	656.6	653.1	645.8	635.3	621.7	605.1
20°	633.8	637.5	638.1	642.3	644.7	647.8	649.1	647.1	640.7	629.3	614.9
22.5°	603.6	604.6	606.3	612.9	618.2	626.1	630.1	637.1	634.5	629.0	616.9
25°	551.1	549.3	555.8	559.1	571.2	583.8	592.9	602.8	611.7	617.1	613.6
27.5°	488.3	485.5	495.2	504.1	513.8	527.5	541.6	558.3	572.2	589.6	595.6
30°	435.2	436.9	446.1	455.6	470.4	489.7	505.6	523.9	543.8	563.2	576.7
32.5°	378.1	384.4	390.3	404.8	417.8	439.3	462.7	485.6	510.3	532.4	553.3
35°	300.0	307.4	315.6	326.1	344.5	365.7	388.6	419.5	453.2	483.4	508.2
37.5°	252.6	251.4	256.0	263.7	278.5	295.7	322.0	352.5	392.2	427.6	462.7
40°	224.1	223.4	226.7	233.7	245.0	257.6	280.6	307.4	344.3	387.7	429.3
42.5°	204.6	205.0	206.8	211.8	219.6	229.9	247.1	269.9	303.7	344.5	389.3
45°	180.8	182.1	184.1	186.5	190.9	199.5	209.1	225.4	252.1	286.2	330.2
47.5°	163.6	163.7	165.8	167.9	170.5	175.3	183.2	193.4	212.2	239.9	277.9
50°	154.5	153.2	154.7	156.3	159.1	162.4	167.6	177.2	189.8	212.2	243.9
52.5°	143.2	143.2	144.6	145.2	147.7	151.0	155.7	162.4	173.8	191.4	217.4
55°	127.0	128.0	128.7	129.8	132.1	134.4	138.2	142.6	151.5	164.6	183.9
57.5°	111.9	112.2	112.9	115.0	116.4	118.6	122.1	126.2	132.0	141.7	156.2
60°	101.5	101.5	103.0	103.9	105.7	107.9	110.7	114.6	119.8	127.8	139.5
62.5°	92.0	91.9	92.5	94.0	95.4	97.4	100.2	103.5	108.4	115.5	125.1
65°	78.2	77.8	78.9	79.2	80.7	82.8	85.0	88.5	92.5	97.6	106.2
67.5°	64.8	65.3	65.9	66.5	67.3	69.5	71.0	73.5	76.8	81.1	86.8
70°	57.4	57.4	57.4	58.0	59.1	60.2	61.6	63.7	66.9	70.5	75.7
72.5°	49.1	49.7	50.3	50.0	51.4	52.0	53.8	55.0	58.0	60.3	64.9
75°	38.6	38.6	38.6	39.5	40.0	40.5	41.7	42.8	44.3	47.2	49.7
77.5°	28.8	28.7	28.9	29.1	29.7	30.3	30.7	31.6	33.0	34.4	36.4
80°	22.3	22.6	22.7	23.2	23.2	23.5	23.7	25.0	25.9	26.8	28.1
82.5°	17.2	17.3	17.3	17.4	17.5	17.8	18.3	18.7	19.0	19.7	20.7
85°	10.0	9.8	9.8	10.2	10.0	10.0	10.4	10.8	10.8	10.9	11.5
87.5°	6.1	6.1	6.2	6.0	6.0	6.1	6.0	5.7	5.8	5.9	5.9
90°	11.5	11.3	11.1	10.9	10.8	10.4	9.9	9.5	9.0	8.5	7.7
92.5°	11.5	11.4	11.3	11.2	11.0	10.8	10.6	10.4	10.1	9.9	9.5
95°	18.3	18.4	18.5	18.6	18.7	18.5	18.0	17.5	17.0	16.6	15.9
97.5°	24.5	24.3	24.2	24.1	24.0	23.7	23.3	23.0	22.6	22.2	20.7
100°	28.5	28.3	28.1	28.0	27.7	27.3	26.5	25.8	25.0	24.2	22.7
102.5°	30.6	30.2	30.0	29.8	29.5	28.9	27.9	26.9	25.9	24.9	38.4
105°	32.4	32.0	31.6	31.2	30.8	30.1	29.1	28.0	27.0	25.9	51.8
107.5°	33.3	32.9	32.5	32.1	31.8	32.1	33.2	34.2	35.3	36.4	67.3
110°	33.6	33.3	32.9	32.4	32.1	36.6	46.1	55.5	65.0	74.4	101.7



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	33.9	33.7	33.3	33.0	32.8	49.8	84.3	118.8	153.3	187.8	194.5
115°	34.9	41.7	48.5	55.3	62.1	87.4	131.2	175.0	218.7	262.5	260.2
117.5°	142.4	164.9	187.2	209.5	232.0	248.4	259.0	269.6	280.2	290.7	289.2
120°	259.5	272.3	285.1	297.8	310.6	316.4	315.3	314.1	313.0	311.9	310.1
122.5°	323.8	326.4	328.8	331.3	333.8	334.7	334.0	333.3	332.6	332.0	330.1
125°	363.8	363.5	363.2	363.0	362.6	362.2	361.5	360.9	360.2	359.5	357.8
127.5°	389.0	388.9	388.9	388.8	388.7	388.2	387.3	386.3	385.3	384.4	383.0
130°	404.6	404.7	404.8	404.9	405.0	404.6	403.5	402.4	401.5	400.4	399.3
132.5°	420.0	420.0	420.1	420.2	420.3	420.0	419.1	418.2	417.3	416.4	415.3
135°	442.1	442.3	442.5	442.6	442.9	442.5	441.5	440.6	439.6	438.6	437.8
137.5°	462.3	462.6	462.8	463.2	463.5	463.3	462.3	461.4	460.5	459.5	458.5
140°	474.8	475.3	475.8	476.2	476.7	476.5	475.6	474.8	474.0	473.1	472.1
142.5°	487.1	487.5	488.0	488.5	489.0	488.9	488.0	487.3	486.5	485.8	484.5
145°	504.2	504.7	505.2	505.6	506.1	506.0	505.3	504.7	504.0	503.4	501.7
147.5°	519.3	519.7	520.1	520.5	520.8	520.8	520.3	519.8	519.3	518.9	517.2
150°	528.5	528.9	529.4	529.9	530.4	530.3	529.7	529.1	528.6	528.0	526.5
152.5°	536.3	536.9	537.5	538.2	538.7	538.8	538.3	537.7	537.1	536.5	535.1
155°	547.1	548.0	548.7	549.4	550.2	550.3	549.8	549.2	548.6	548.0	546.9
157.5°	557.1	557.8	558.6	559.3	560.1	560.1	559.5	558.8	558.2	557.6	556.8
160°	562.9	563.5	564.3	564.9	565.6	565.6	565.0	564.4	563.9	563.4	562.8
162.5°	567.7	568.5	569.3	570.1	571.0	571.0	570.4	569.7	569.1	568.4	567.9
165°	574.8	575.5	576.2	576.8	577.5	577.5	576.8	576.2	575.5	574.8	574.5
167.5°	579.4	580.2	581.1	581.9	582.8	582.9	582.2	581.5	580.8	580.2	579.9
170°	582.0	582.9	583.8	584.6	585.5	585.5	584.9	584.2	583.6	582.9	582.7
172.5°	584.1	585.0	585.8	586.7	587.5	587.6	586.9	586.3	585.6	585.0	584.7
175°	585.9	586.9	587.7	588.7	589.7	589.8	589.1	588.5	587.8	587.2	586.9
177.5°	587.0	587.7	588.3	589.1	589.7	589.8	589.3	588.7	588.2	587.7	587.6
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	494.5	493.3	492.6	489.9	487.5	485.2	484.5	484.7	481.4	478.3	477.0
5°	513.8	510.1	506.5	501.6	495.6	489.1	485.8	483.2	476.7	469.7	465.6
7.5°	531.0	525.7	518.9	509.6	500.9	490.7	484.2	478.5	469.0	459.1	453.0
10°	541.5	534.3	525.6	514.1	503.6	491.1	482.5	473.8	462.7	450.8	443.4
12.5°	550.6	540.9	532.3	517.6	505.1	489.5	479.2	466.9	455.3	441.2	433.9
15°	572.1	554.2	537.9	521.1	505.8	484.1	472.6	456.2	440.8	423.4	415.1
17.5°	588.7	568.5	542.9	521.7	503.8	479.7	462.9	443.2	425.0	405.1	393.8
20°	598.2	575.0	547.5	522.3	500.8	473.4	455.0	434.9	413.6	391.2	379.0
22.5°	603.8	579.5	552.2	520.1	494.9	468.2	445.2	423.0	401.5	377.2	364.4
25°	605.6	583.4	554.5	518.2	487.5	457.3	429.5	408.0	381.9	359.3	340.6
27.5°	596.8	580.9	553.1	514.7	478.9	443.6	412.6	388.3	360.8	336.2	317.4
30°	586.0	576.7	549.7	511.2	472.1	434.1	400.1	372.4	345.0	320.2	300.9
32.5°	569.2	567.3	543.5	506.1	464.8	422.2	386.9	359.0	328.6	304.2	285.8
35°	536.4	545.3	530.3	494.9	451.2	405.0	366.9	335.0	303.5	280.2	263.0
37.5°	492.3	514.4	510.5	478.4	432.7	386.5	344.3	311.0	281.0	257.5	240.6
40°	461.9	490.1	494.2	465.8	419.7	372.1	327.4	294.3	265.1	243.5	226.5
42.5°	429.3	462.2	473.4	450.7	405.4	356.9	312.3	278.0	249.0	228.1	213.0
45°	374.7	418.2	438.4	425.4	381.7	332.1	286.2	251.4	225.0	205.4	193.7
47.5°	323.6	371.1	398.3	393.7	355.3	306.1	260.7	227.3	201.7	186.1	175.6
50°	287.5	336.3	369.1	370.6	336.3	287.6	242.1	210.6	187.0	172.4	163.9
52.5°	256.0	302.7	338.4	346.3	315.1	268.4	225.3	194.0	173.3	159.8	152.2
55°	215.0	254.5	294.1	308.6	283.6	239.1	199.3	171.7	152.2	143.0	136.3
57.5°	178.8	211.7	248.3	264.2	248.8	210.8	173.4	149.4	133.7	125.6	120.4
60°	159.6	185.6	218.2	237.3	223.9	190.0	157.4	134.6	121.6	114.5	109.7
62.5°	141.9	164.9	192.4	209.9	202.6	170.6	141.5	121.3	110.1	103.4	99.9
65°	117.1	135.2	156.5	172.6	167.8	143.6	119.6	102.4	93.5	88.1	85.4
67.5°	96.4	109.5	124.3	138.4	134.5	117.3	98.2	84.7	78.1	73.5	71.7
70°	83.3	93.4	106.5	117.8	114.6	100.6	85.4	73.9	68.2	64.2	62.6
72.5°	70.9	79.1	89.2	98.4	96.3	84.5	71.9	63.3	58.8	55.2	53.9
75°	53.6	59.8	66.0	72.1	71.5	62.5	55.0	48.3	44.8	42.1	41.5
77.5°	39.5	43.0	47.2	50.8	49.8	44.6	38.8	35.0	32.4	30.6	30.2
80°	30.2	32.2	35.2	37.7	36.5	34.2	29.6	26.8	25.0	23.2	22.4
82.5°	21.9	23.9	25.7	27.1	26.1	24.1	21.2	19.3	18.2	17.0	16.6
85°	11.5	12.6	13.4	13.7	13.4	12.1	10.8	10.0	9.0	8.5	8.3
87.5°	5.9	5.7	5.5	5.6	5.0	4.8	4.0	3.3	3.4	3.4	3.3
90°	7.0	6.3	5.5	4.6	3.5	2.5	1.5	0.4	1.5	2.5	3.5
92.5°	9.1	8.7	8.4	8.2	8.3	8.4	8.5	8.6	8.5	8.4	8.3
95°	15.2	14.6	13.9	15.2	18.3	21.4	24.5	27.6	24.5	21.4	18.3
97.5°	19.2	17.6	16.1	19.7	28.5	37.3	46.1	54.9	46.1	37.3	28.5
100°	21.0	19.4	17.9	23.5	36.4	49.4	62.4	75.3	62.4	49.4	36.4
102.5°	51.9	65.3	78.7	86.8	89.5	92.3	95.1	97.8	95.1	92.3	89.5
105°	77.6	103.4	129.2	140.7	137.9	135.0	132.2	129.3	132.2	135.0	137.9
107.5°	98.2	129.2	160.1	174.5	172.2	169.9	167.6	165.3	167.6	169.9	172.2
110°	129.1	156.5	183.8	196.4	194.4	192.5	190.5	188.5	190.5	192.5	194.4





TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	201.3	208.1	214.8	217.3	215.6	213.8	212.1	210.3	212.1	213.8	215.6
115°	257.8	255.4	253.1	251.1	249.5	247.9	246.2	244.7	246.2	247.9	249.5
117.5°	287.6	285.9	284.3	282.6	280.8	279.0	277.2	275.4	277.2	279.0	280.8
120°	308.5	306.8	305.1	303.5	302.1	300.7	299.2	297.8	299.2	300.7	302.1
122.5°	328.2	326.4	324.6	322.9	321.4	319.9	318.4	316.9	318.4	319.9	321.4
125°	356.0	354.2	352.4	350.8	349.6	348.4	347.2	345.9	347.2	348.4	349.6
127.5°	381.7	380.3	379.0	377.6	376.3	375.0	373.6	372.2	373.6	375.0	376.3
130°	398.3	397.3	396.2	394.9	393.5	391.9	390.4	388.9	390.4	391.9	393.5
132.5°	414.3	413.3	412.2	411.1	409.8	408.5	407.2	405.9	407.2	408.5	409.8
135°	437.0	436.1	435.3	434.1	432.6	431.0	429.6	428.0	429.6	431.0	432.6
137.5°	457.6	456.6	455.7	454.6	453.6	452.5	451.4	450.5	451.4	452.5	453.6
140°	471.1	470.0	469.0	468.1	467.3	466.6	465.8	465.0	465.8	466.6	467.3
142.5°	483.3	482.2	480.9	480.0	479.3	478.7	478.0	477.3	478.0	478.7	479.3
145°	500.1	498.6	496.9	496.2	496.3	496.4	496.4	496.5	496.4	496.4	496.3
147.5°	515.7	514.0	512.5	511.8	512.3	512.6	512.9	513.3	512.9	512.6	512.3
150°	525.0	523.5	522.0	521.5	522.2	522.9	523.5	524.2	523.5	522.9	522.2
152.5°	533.7	532.2	530.8	530.4	531.2	531.9	532.6	533.4	532.6	531.9	531.2
155°	545.8	544.6	543.5	543.3	544.2	545.0	545.9	546.7	545.9	545.0	544.2
157.5°	556.0	555.1	554.4	554.3	555.1	555.8	556.5	557.2	556.5	555.8	555.1
160°	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	562.8	562.2	561.7
162.5°	567.4	567.0	566.5	566.6	567.0	567.6	568.2	568.8	568.2	567.6	567.0
165°	574.2	574.0	573.7	573.8	574.4	574.9	575.5	576.1	575.5	574.9	574.4
167.5°	579.7	579.4	579.1	579.3	579.8	580.4	581.0	581.6	581.0	580.4	579.8
170°	582.5	582.4	582.1	582.4	582.9	583.5	584.1	584.6	584.1	583.5	582.9
172.5°	584.6	584.4	584.2	584.4	585.0	585.5	586.1	586.7	586.1	585.5	585.0
175°	586.8	586.6	586.4	586.6	587.3	588.0	588.6	589.3	588.6	588.0	587.3
177.5°	587.5	587.4	587.3	587.6	588.2	588.6	589.2	589.7	589.2	588.6	588.2
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	475.6	474.7	471.6	469.9	467.2	464.7	463.1	463.8	464.4	464.1	463.7
5°	461.9	458.4	453.0	448.4	445.1	439.0	436.3	435.0	433.9	432.7	431.4
7.5°	445.6	440.1	432.4	425.8	419.6	412.0	407.6	405.1	402.4	399.5	396.9
10°	434.1	426.3	418.2	409.0	401.5	394.7	388.6	384.5	380.7	377.2	374.7
12.5°	422.0	413.0	402.9	390.3	382.1	372.3	371.4	364.2	358.4	356.2	353.2
15°	402.7	390.0	377.2	362.2	355.8	346.9	341.4	335.7	330.8	327.3	326.4
17.5°	380.7	364.4	351.6	340.9	330.3	321.1	316.0	311.6	307.4	302.8	302.1
20°	363.9	349.8	336.0	326.5	315.6	306.3	300.0	295.6	292.0	289.3	286.9
22.5°	348.1	332.6	319.9	309.7	298.9	291.4	286.4	282.1	279.2	276.1	273.9
25°	322.6	310.6	296.7	285.0	276.1	271.3	267.3	263.6	261.7	259.7	257.1
27.5°	300.4	287.0	274.0	265.0	257.1	252.9	250.0	247.4	245.7	244.5	243.0
30°	284.7	271.2	261.0	252.1	245.6	241.3	239.5	238.0	235.9	235.2	234.5
32.5°	269.5	257.4	248.7	240.9	234.8	232.0	230.3	228.9	227.4	226.7	225.1
35°	248.2	238.0	229.5	225.2	220.2	217.8	216.5	214.7	213.2	212.5	212.2
37.5°	228.0	219.2	213.6	208.1	206.0	204.6	202.8	201.5	201.1	201.0	200.7
40°	215.0	207.8	202.8	198.4	197.5	195.2	193.7	192.7	192.7	192.8	192.7
42.5°	203.2	196.7	192.2	188.4	187.4	186.1	184.5	184.5	184.7	185.4	184.7
45°	185.2	180.6	177.4	175.6	173.6	172.3	172.0	172.6	172.8	173.0	173.6
47.5°	168.7	165.6	162.7	160.7	159.8	159.6	159.4	160.4	161.3	161.6	162.4
50°	158.9	155.4	153.0	151.6	150.9	150.6	150.9	152.1	152.8	153.7	154.3
52.5°	148.0	145.4	143.8	142.8	142.5	142.8	142.8	144.1	145.2	145.6	145.9
55°	132.8	130.9	130.6	128.9	129.6	129.5	130.4	131.1	132.2	133.4	133.5
57.5°	117.6	116.2	115.2	115.4	115.6	116.4	117.2	118.5	119.6	120.8	120.9
60°	107.6	106.9	106.3	106.3	106.6	107.8	108.7	110.0	110.7	111.5	112.0
62.5°	98.4	97.7	97.1	97.4	98.4	99.1	100.1	100.9	101.6	102.3	102.6
65°	83.9	83.6	84.1	84.5	84.6	85.5	86.8	87.4	88.1	88.5	89.8
67.5°	70.5	70.6	70.5	71.0	72.2	72.3	73.5	74.8	75.0	75.7	76.6
70°	61.5	61.9	62.2	62.6	63.5	63.9	64.8	65.4	66.1	66.7	67.3
72.5°	53.2	53.2	53.6	53.6	54.4	55.1	55.9	56.5	57.2	58.0	58.5
75°	40.9	40.9	41.3	41.5	42.4	43.4	43.1	43.5	44.3	45.0	45.4
77.5°	29.9	29.5	29.9	30.1	30.4	31.1	31.3	31.8	32.7	32.4	32.9
80°	22.7	22.3	22.7	23.0	23.0	23.9	23.9	24.3	24.8	24.3	24.8
82.5°	16.2	16.0	16.4	16.5	16.7	16.8	17.0	17.1	17.7	17.4	17.7
85°	8.2	8.0	8.2	8.0	8.2	8.3	8.3	8.2	8.2	8.5	8.0
87.5°	3.4	3.5	3.5	3.6	3.6	3.6	3.6	3.7	3.8	3.6	3.6
90°	4.6	5.5	6.3	7.0	7.7	8.5	9.0	9.5	9.9	10.4	10.8
92.5°	8.2	8.4	8.7	9.1	9.5	9.9	10.1	10.4	10.6	10.8	11.0
95°	15.2	13.9	14.6	15.2	15.9	16.6	17.0	17.5	18.0	18.5	18.7
97.5°	19.7	16.1	17.6	19.2	20.7	22.2	22.6	23.0	23.3	23.7	24.0
100°	23.5	17.9	19.4	21.0	22.7	24.2	25.0	25.8	26.5	27.3	27.7
102.5°	86.8	78.7	65.3	51.9	38.4	24.9	25.9	26.9	27.9	28.9	29.5
105°	140.7	129.2	103.4	77.6	51.8	25.9	27.0	28.0	29.1	30.1	30.8
107.5°	174.5	160.1	129.2	98.2	67.3	36.4	35.3	34.2	33.2	32.1	31.8
110°	196.4	183.8	156.5	129.1	101.7	74.4	65.0	55.5	46.1	36.6	32.1



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.3	214.8	208.1	201.3	194.5	187.8	153.3	118.8	84.3	49.8	32.8
115°	251.1	253.1	255.4	257.8	260.2	262.5	218.7	175.0	131.2	87.4	62.1
117.5°	282.6	284.3	285.9	287.6	289.2	290.7	280.2	269.6	259.0	248.4	232.0
120°	303.5	305.1	306.8	308.5	310.1	311.9	313.0	314.1	315.3	316.4	310.6
122.5°	322.9	324.6	326.4	328.2	330.1	332.0	332.6	333.3	334.0	334.7	333.8
125°	350.8	352.4	354.2	356.0	357.8	359.5	360.2	360.9	361.5	362.2	362.6
127.5°	377.6	379.0	380.3	381.7	383.0	384.4	385.3	386.3	387.3	388.2	388.7
130°	394.9	396.2	397.3	398.3	399.3	400.4	401.5	402.4	403.5	404.6	405.0
132.5°	411.1	412.2	413.3	414.3	415.3	416.4	417.3	418.2	419.1	420.0	420.3
135°	434.1	435.3	436.1	437.0	437.8	438.6	439.6	440.6	441.5	442.5	442.9
137.5°	454.6	455.7	456.6	457.6	458.5	459.5	460.5	461.4	462.3	463.3	463.5
140°	468.1	469.0	470.0	471.1	472.1	473.1	474.0	474.8	475.6	476.5	476.7
142.5°	480.0	480.9	482.2	483.3	484.5	485.8	486.5	487.3	488.0	488.9	489.0
145°	496.2	496.9	498.6	500.1	501.7	503.4	504.0	504.7	505.3	506.0	506.1
147.5°	511.8	512.5	514.0	515.7	517.2	518.9	519.3	519.8	520.3	520.8	520.8
150°	521.5	522.0	523.5	525.0	526.5	528.0	528.6	529.1	529.7	530.3	530.4
152.5°	530.4	530.8	532.2	533.7	535.1	536.5	537.1	537.7	538.3	538.8	538.7
155°	543.3	543.5	544.6	545.8	546.9	548.0	548.6	549.2	549.8	550.3	550.2
157.5°	554.3	554.4	555.1	556.0	556.8	557.6	558.2	558.8	559.5	560.1	560.1
160°	561.1	561.1	561.7	562.2	562.8	563.4	563.9	564.4	565.0	565.6	565.6
162.5°	566.6	566.5	567.0	567.4	567.9	568.4	569.1	569.7	570.4	571.0	571.0
165°	573.8	573.7	574.0	574.2	574.5	574.8	575.5	576.2	576.8	577.5	577.5
167.5°	579.3	579.1	579.4	579.7	579.9	580.2	580.8	581.5	582.2	582.9	582.8
170°	582.4	582.1	582.4	582.5	582.7	582.9	583.6	584.2	584.9	585.5	585.5
172.5°	584.4	584.2	584.4	584.6	584.7	585.0	585.6	586.3	586.9	587.6	587.5
175°	586.6	586.4	586.6	586.8	586.9	587.2	587.8	588.5	589.1	589.8	589.7
177.5°	587.6	587.3	587.4	587.5	587.6	587.7	588.2	588.7	589.3	589.8	589.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	462.2	461.9	461.9	460.6	461.9	461.9	462.2	463.7	464.1	464.4	463.8
5°	428.8	428.2	427.3	428.2	427.3	428.2	428.8	431.4	432.7	433.9	435.0
7.5°	395.7	393.5	393.1	390.9	393.1	393.5	395.7	396.9	399.5	402.4	405.1
10°	371.5	370.1	369.8	366.3	369.8	370.1	371.5	374.7	377.2	380.7	384.5
12.5°	353.2	349.6	350.3	348.3	350.3	349.6	353.2	353.2	356.2	358.4	364.2
15°	321.3	321.3	320.6	317.5	320.6	321.3	321.3	326.4	327.3	330.8	335.7
17.5°	298.5	298.1	296.4	297.3	296.4	298.1	298.5	302.1	302.8	307.4	311.6
20°	284.9	283.7	281.5	281.5	281.5	283.7	284.9	286.9	289.3	292.0	295.6
22.5°	272.0	271.9	269.5	270.3	269.5	271.9	272.0	273.9	276.1	279.2	282.1
25°	256.9	255.4	254.3	254.9	254.3	255.4	256.9	257.1	259.7	261.7	263.6
27.5°	242.6	241.7	241.7	240.2	241.7	241.7	242.6	243.0	244.5	245.7	247.4
30°	234.3	232.4	232.8	231.9	232.8	232.4	234.3	234.5	235.2	235.9	238.0
32.5°	224.8	224.1	223.8	223.0	223.8	224.1	224.8	225.1	226.7	227.4	228.9
35°	211.9	212.1	211.2	211.5	211.2	212.1	211.9	212.2	212.5	213.2	214.7
37.5°	200.6	201.1	200.7	200.8	200.7	201.1	200.6	200.7	201.0	201.1	201.5
40°	193.1	193.1	193.1	193.7	193.1	193.1	193.1	192.7	192.8	192.7	192.7
42.5°	186.1	185.7	185.5	185.4	185.5	185.7	186.1	184.7	185.4	184.7	184.5
45°	173.9	174.5	174.6	173.7	174.6	174.5	173.9	173.6	173.0	172.8	172.6
47.5°	162.9	163.0	162.9	163.7	162.9	163.0	162.9	162.4	161.6	161.3	160.4
50°	155.2	154.8	155.2	154.8	155.2	154.8	155.2	154.3	153.7	152.8	152.1
52.5°	147.1	147.2	146.9	146.8	146.9	147.2	147.1	145.9	145.6	145.2	144.1
55°	134.3	134.6	134.4	134.4	134.4	134.6	134.3	133.5	133.4	132.2	131.1
57.5°	121.1	121.4	121.6	120.8	121.6	121.4	121.1	120.9	120.8	119.6	118.5
60°	111.9	112.8	112.6	112.3	112.6	112.8	111.9	112.0	111.5	110.7	110.0
62.5°	103.4	103.8	103.7	103.6	103.7	103.8	103.4	102.6	102.3	101.6	100.9
65°	90.4	90.7	90.2	90.7	90.2	90.7	90.4	89.8	88.5	88.1	87.4
67.5°	76.3	76.5	76.9	77.1	76.9	76.5	76.3	76.6	75.7	75.0	74.8
70°	67.6	67.4	68.0	68.6	68.0	67.4	67.6	67.3	66.7	66.1	65.4
72.5°	58.4	58.8	58.6	59.0	58.6	58.8	58.4	58.5	58.0	57.2	56.5
75°	45.0	45.6	45.4	45.9	45.4	45.6	45.0	45.4	45.0	44.3	43.5
77.5°	32.5	32.6	32.5	32.9	32.5	32.6	32.5	32.9	32.4	32.7	31.8
80°	24.8	24.5	24.1	24.8	24.1	24.5	24.8	24.8	24.3	24.8	24.3
82.5°	17.3	17.4	17.1	17.1	17.1	17.4	17.3	17.7	17.4	17.7	17.1
85°	8.0	7.7	7.4	7.4	7.4	7.7	8.0	8.0	8.5	8.2	8.2
87.5°	3.7	3.6	3.6	3.5	3.6	3.6	3.7	3.6	3.6	3.8	3.7
90°	10.9	11.1	11.3	11.5	11.3	11.1	10.9	10.8	10.4	9.9	9.5
92.5°	11.2	11.3	11.4	11.5	11.4	11.3	11.2	11.0	10.8	10.6	10.4
95°	18.6	18.5	18.4	18.3	18.4	18.5	18.6	18.7	18.5	18.0	17.5
97.5°	24.1	24.2	24.3	24.5	24.3	24.2	24.1	24.0	23.7	23.3	23.0
100°	28.0	28.1	28.3	28.5	28.3	28.1	28.0	27.7	27.3	26.5	25.8
102.5°	29.8	30.0	30.2	30.6	30.2	30.0	29.8	29.5	28.9	27.9	26.9
105°	31.2	31.6	32.0	32.4	32.0	31.6	31.2	30.8	30.1	29.1	28.0
107.5°	32.1	32.5	32.9	33.3	32.9	32.5	32.1	31.8	32.1	33.2	34.2
110°	32.4	32.9	33.3	33.6	33.3	32.9	32.4	32.1	36.6	46.1	55.5



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.0	33.3	33.7	33.9	33.7	33.3	33.0	32.8	49.8	84.3	118.8
115°	55.3	48.5	41.7	34.9	41.7	48.5	55.3	62.1	87.4	131.2	175.0
117.5°	209.5	187.2	164.9	142.4	164.9	187.2	209.5	232.0	248.4	259.0	269.6
120°	297.8	285.1	272.3	259.5	272.3	285.1	297.8	310.6	316.4	315.3	314.1
122.5°	331.3	328.8	326.4	323.8	326.4	328.8	331.3	333.8	334.7	334.0	333.3
125°	363.0	363.2	363.5	363.8	363.5	363.2	363.0	362.6	362.2	361.5	360.9
127.5°	388.8	388.9	388.9	389.0	388.9	388.9	388.8	388.7	388.2	387.3	386.3
130°	404.9	404.8	404.7	404.6	404.7	404.8	404.9	405.0	404.6	403.5	402.4
132.5°	420.2	420.1	420.0	420.0	420.0	420.1	420.2	420.3	420.0	419.1	418.2
135°	442.6	442.5	442.3	442.1	442.3	442.5	442.6	442.9	442.5	441.5	440.6
137.5°	463.2	462.8	462.6	462.3	462.6	462.8	463.2	463.5	463.3	462.3	461.4
140°	476.2	475.8	475.3	474.8	475.3	475.8	476.2	476.7	476.5	475.6	474.8
142.5°	488.5	488.0	487.5	487.1	487.5	488.0	488.5	489.0	488.9	488.0	487.3
145°	505.6	505.2	504.7	504.2	504.7	505.2	505.6	506.1	506.0	505.3	504.7
147.5°	520.5	520.1	519.7	519.3	519.7	520.1	520.5	520.8	520.8	520.3	519.8
150°	529.9	529.4	528.9	528.5	528.9	529.4	529.9	530.4	530.3	529.7	529.1
152.5°	538.2	537.5	536.9	536.3	536.9	537.5	538.2	538.7	538.8	538.3	537.7
155°	549.4	548.7	548.0	547.1	548.0	548.7	549.4	550.2	550.3	549.8	549.2
157.5°	559.3	558.6	557.8	557.1	557.8	558.6	559.3	560.1	560.1	559.5	558.8
160°	564.9	564.3	563.5	562.9	563.5	564.3	564.9	565.6	565.6	565.0	564.4
162.5°	570.1	569.3	568.5	567.7	568.5	569.3	570.1	571.0	571.0	570.4	569.7
165°	576.8	576.2	575.5	574.8	575.5	576.2	576.8	577.5	577.5	576.8	576.2
167.5°	581.9	581.1	580.2	579.4	580.2	581.1	581.9	582.8	582.9	582.2	581.5
170°	584.6	583.8	582.9	582.0	582.9	583.8	584.6	585.5	585.5	584.9	584.2
172.5°	586.7	585.8	585.0	584.1	585.0	585.8	586.7	587.5	587.6	586.9	586.3
175°	588.7	587.7	586.9	585.9	586.9	587.7	588.7	589.7	589.8	589.1	588.5
177.5°	589.1	588.3	587.7	587.0	587.7	588.3	589.1	589.7	589.8	589.3	588.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	463.1	464.7	467.2	469.9	471.6	474.7	475.6	477.0	478.3	481.4	484.7
5°	436.3	439.0	445.1	448.4	453.0	458.4	461.9	465.6	469.7	476.7	483.2
7.5°	407.6	412.0	419.6	425.8	432.4	440.1	445.6	453.0	459.1	469.0	478.5
10°	388.6	394.7	401.5	409.0	418.2	426.3	434.1	443.4	450.8	462.7	473.8
12.5°	371.4	372.3	382.1	390.3	402.9	413.0	422.0	433.9	441.2	455.3	466.9
15°	341.4	346.9	355.8	362.2	377.2	390.0	402.7	415.1	423.4	440.8	456.2
17.5°	316.0	321.1	330.3	340.9	351.6	364.4	380.7	393.8	405.1	425.0	443.2
20°	300.0	306.3	315.6	326.5	336.0	349.8	363.9	379.0	391.2	413.6	434.9
22.5°	286.4	291.4	298.9	309.7	319.9	332.6	348.1	364.4	377.2	401.5	423.0
25°	267.3	271.3	276.1	285.0	296.7	310.6	322.6	340.6	359.3	381.9	408.0
27.5°	250.0	252.9	257.1	265.0	274.0	287.0	300.4	317.4	336.2	360.8	388.3
30°	239.5	241.3	245.6	252.1	261.0	271.2	284.7	300.9	320.2	345.0	372.4
32.5°	230.3	232.0	234.8	240.9	248.7	257.4	269.5	285.8	304.2	328.6	359.0
35°	216.5	217.8	220.2	225.2	229.5	238.0	248.2	263.0	280.2	303.5	335.0
37.5°	202.8	204.6	206.0	208.1	213.6	219.2	228.0	240.6	257.5	281.0	311.0
40°	193.7	195.2	197.5	198.4	202.8	207.8	215.0	226.5	243.5	265.1	294.3
42.5°	184.5	186.1	187.4	188.4	192.2	196.7	203.2	213.0	228.1	249.0	278.0
45°	172.0	172.3	173.6	175.6	177.4	180.6	185.2	193.7	205.4	225.0	251.4
47.5°	159.4	159.6	159.8	160.7	162.7	165.6	168.7	175.6	186.1	201.7	227.3
50°	150.9	150.6	150.9	151.6	153.0	155.4	158.9	163.9	172.4	187.0	210.6
52.5°	142.8	142.8	142.5	142.8	143.8	145.4	148.0	152.2	159.8	173.3	194.0
55°	130.4	129.5	129.6	128.9	130.6	130.9	132.8	136.3	143.0	152.2	171.7
57.5°	117.2	116.4	115.6	115.4	115.2	116.2	117.6	120.4	125.6	133.7	149.4
60°	108.7	107.8	106.6	106.3	106.3	106.9	107.6	109.7	114.5	121.6	134.6
62.5°	100.1	99.1	98.4	97.4	97.1	97.7	98.4	99.9	103.4	110.1	121.3
65°	86.8	85.5	84.6	84.5	84.1	83.6	83.9	85.4	88.1	93.5	102.4
67.5°	73.5	72.3	72.2	71.0	70.5	70.6	70.5	71.7	73.5	78.1	84.7
70°	64.8	63.9	63.5	62.6	62.2	61.9	61.5	62.6	64.2	68.2	73.9
72.5°	55.9	55.1	54.4	53.6	53.6	53.2	53.2	53.9	55.2	58.8	63.3
75°	43.1	43.4	42.4	41.5	41.3	40.9	40.9	41.5	42.1	44.8	48.3
77.5°	31.3	31.1	30.4	30.1	29.9	29.5	29.9	30.2	30.6	32.4	35.0
80°	23.9	23.9	23.0	23.0	22.7	22.3	22.7	22.4	23.2	25.0	26.8
82.5°	17.0	16.8	16.7	16.5	16.4	16.0	16.2	16.6	17.0	18.2	19.3
85°	8.3	8.3	8.2	8.0	8.2	8.0	8.2	8.3	8.5	9.0	10.0
87.5°	3.6	3.6	3.6	3.6	3.5	3.5	3.4	3.3	3.4	3.4	3.3
90°	9.0	8.5	7.7	7.0	6.3	5.5	4.6	3.5	2.5	1.5	0.4
92.5°	10.1	9.9	9.5	9.1	8.7	8.4	8.2	8.3	8.4	8.5	8.6
95°	17.0	16.6	15.9	15.2	14.6	13.9	15.2	18.3	21.4	24.5	27.6
97.5°	22.6	22.2	20.7	19.2	17.6	16.1	19.7	28.5	37.3	46.1	54.9
100°	25.0	24.2	22.7	21.0	19.4	17.9	23.5	36.4	49.4	62.4	75.3
102.5°	25.9	24.9	38.4	51.9	65.3	78.7	86.8	89.5	92.3	95.1	97.8
105°	27.0	25.9	51.8	77.6	103.4	129.2	140.7	137.9	135.0	132.2	129.3
107.5°	35.3	36.4	67.3	98.2	129.2	160.1	174.5	172.2	169.9	167.6	165.3
110°	65.0	74.4	101.7	129.1	156.5	183.8	196.4	194.4	192.5	190.5	188.5



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	153.3	187.8	194.5	201.3	208.1	214.8	217.3	215.6	213.8	212.1	210.3
115°	218.7	262.5	260.2	257.8	255.4	253.1	251.1	249.5	247.9	246.2	244.7
117.5°	280.2	290.7	289.2	287.6	285.9	284.3	282.6	280.8	279.0	277.2	275.4
120°	313.0	311.9	310.1	308.5	306.8	305.1	303.5	302.1	300.7	299.2	297.8
122.5°	332.6	332.0	330.1	328.2	326.4	324.6	322.9	321.4	319.9	318.4	316.9
125°	360.2	359.5	357.8	356.0	354.2	352.4	350.8	349.6	348.4	347.2	345.9
127.5°	385.3	384.4	383.0	381.7	380.3	379.0	377.6	376.3	375.0	373.6	372.2
130°	401.5	400.4	399.3	398.3	397.3	396.2	394.9	393.5	391.9	390.4	388.9
132.5°	417.3	416.4	415.3	414.3	413.3	412.2	411.1	409.8	408.5	407.2	405.9
135°	439.6	438.6	437.8	437.0	436.1	435.3	434.1	432.6	431.0	429.6	428.0
137.5°	460.5	459.5	458.5	457.6	456.6	455.7	454.6	453.6	452.5	451.4	450.5
140°	474.0	473.1	472.1	471.1	470.0	469.0	468.1	467.3	466.6	465.8	465.0
142.5°	486.5	485.8	484.5	483.3	482.2	480.9	480.0	479.3	478.7	478.0	477.3
145°	504.0	503.4	501.7	500.1	498.6	496.9	496.2	496.3	496.4	496.4	496.5
147.5°	519.3	518.9	517.2	515.7	514.0	512.5	511.8	512.3	512.6	512.9	513.3
150°	528.6	528.0	526.5	525.0	523.5	522.0	521.5	522.2	522.9	523.5	524.2
152.5°	537.1	536.5	535.1	533.7	532.2	530.8	530.4	531.2	531.9	532.6	533.4
155°	548.6	548.0	546.9	545.8	544.6	543.5	543.3	544.2	545.0	545.9	546.7
157.5°	558.2	557.6	556.8	556.0	555.1	554.4	554.3	555.1	555.8	556.5	557.2
160°	563.9	563.4	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4
162.5°	569.1	568.4	567.9	567.4	567.0	566.5	566.6	567.0	567.6	568.2	568.8
165°	575.5	574.8	574.5	574.2	574.0	573.7	573.8	574.4	574.9	575.5	576.1
167.5°	580.8	580.2	579.9	579.7	579.4	579.1	579.3	579.8	580.4	581.0	581.6
170°	583.6	582.9	582.7	582.5	582.4	582.1	582.4	582.9	583.5	584.1	584.6
172.5°	585.6	585.0	584.7	584.6	584.4	584.2	584.4	585.0	585.5	586.1	586.7
175°	587.8	587.2	586.9	586.8	586.6	586.4	586.6	587.3	588.0	588.6	589.3
177.5°	588.2	587.7	587.6	587.5	587.4	587.3	587.6	588.2	588.6	589.2	589.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	484.5	485.2	487.5	489.9	492.6	493.3	494.5	493.5	493.2	495.9	498.1
5°	485.8	489.1	495.6	501.6	506.5	510.1	513.8	515.3	518.0	521.9	526.8
7.5°	484.2	490.7	500.9	509.6	518.9	525.7	531.0	535.6	541.0	548.4	556.4
10°	482.5	491.1	503.6	514.1	525.6	534.3	541.5	548.6	556.8	567.0	577.5
12.5°	479.2	489.5	505.1	517.6	532.3	540.9	550.6	565.7	574.5	588.7	603.6
15°	472.6	484.1	505.8	521.1	537.9	554.2	572.1	586.5	601.0	609.4	630.2
17.5°	462.9	479.7	503.8	521.7	542.9	568.5	588.7	605.1	621.7	635.3	645.8
20°	455.0	473.4	500.8	522.3	547.5	575.0	598.2	614.9	629.3	640.7	647.1
22.5°	445.2	468.2	494.9	520.1	552.2	579.5	603.8	616.9	629.0	634.5	637.1
25°	429.5	457.3	487.5	518.2	554.5	583.4	605.6	613.6	617.1	611.7	602.8
27.5°	412.6	443.6	478.9	514.7	553.1	580.9	596.8	595.6	589.6	572.2	558.3
30°	400.1	434.1	472.1	511.2	549.7	576.7	586.0	576.7	563.2	543.8	523.9
32.5°	386.9	422.2	464.8	506.1	543.5	567.3	569.2	553.3	532.4	510.3	485.6
35°	366.9	405.0	451.2	494.9	530.3	545.3	536.4	508.2	483.4	453.2	419.5
37.5°	344.3	386.5	432.7	478.4	510.5	514.4	492.3	462.7	427.6	392.2	352.5
40°	327.4	372.1	419.7	465.8	494.2	490.1	461.9	429.3	387.7	344.3	307.4
42.5°	312.3	356.9	405.4	450.7	473.4	462.2	429.3	389.3	344.5	303.7	269.9
45°	286.2	332.1	381.7	425.4	438.4	418.2	374.7	330.2	286.2	252.1	225.4
47.5°	260.7	306.1	355.3	393.7	398.3	371.1	323.6	277.9	239.9	212.2	193.4
50°	242.1	287.6	336.3	370.6	369.1	336.3	287.5	243.9	212.2	189.8	177.2
52.5°	225.3	268.4	315.1	346.3	338.4	302.7	256.0	217.4	191.4	173.8	162.4
55°	199.3	239.1	283.6	308.6	294.1	254.5	215.0	183.9	164.6	151.5	142.6
57.5°	173.4	210.8	248.8	264.2	248.3	211.7	178.8	156.2	141.7	132.0	126.2
60°	157.4	190.0	223.9	237.3	218.2	185.6	159.6	139.5	127.8	119.8	114.6
62.5°	141.5	170.6	202.6	209.9	192.4	164.9	141.9	125.1	115.5	108.4	103.5
65°	119.6	143.6	167.8	172.6	156.5	135.2	117.1	106.2	97.6	92.5	88.5
67.5°	98.2	117.3	134.5	138.4	124.3	109.5	96.4	86.8	81.1	76.8	73.5
70°	85.4	100.6	114.6	117.8	106.5	93.4	83.3	75.7	70.5	66.9	63.7
72.5°	71.9	84.5	96.3	98.4	89.2	79.1	70.9	64.9	60.3	58.0	55.0
75°	55.0	62.5	71.5	72.1	66.0	59.8	53.6	49.7	47.2	44.3	42.8
77.5°	38.8	44.6	49.8	50.8	47.2	43.0	39.5	36.4	34.4	33.0	31.6
80°	29.6	34.2	36.5	37.7	35.2	32.2	30.2	28.1	26.8	25.9	25.0
82.5°	21.2	24.1	26.1	27.1	25.7	23.9	21.9	20.7	19.7	19.0	18.7
85°	10.8	12.1	13.4	13.7	13.4	12.6	11.5	11.5	10.9	10.8	10.8
87.5°	4.0	4.8	5.0	5.6	5.5	5.7	5.9	5.9	5.9	5.8	5.7
90°	1.5	2.5	3.5	4.6	5.5	6.3	7.0	7.7	8.5	9.0	9.5
92.5°	8.5	8.4	8.3	8.2	8.4	8.7	9.1	9.5	9.9	10.1	10.4
95°	24.5	21.4	18.3	15.2	13.9	14.6	15.2	15.9	16.6	17.0	17.5
97.5°	46.1	37.3	28.5	19.7	16.1	17.6	19.2	20.7	22.2	22.6	23.0
100°	62.4	49.4	36.4	23.5	17.9	19.4	21.0	22.7	24.2	25.0	25.8
102.5°	95.1	92.3	89.5	86.8	78.7	65.3	51.9	38.4	24.9	25.9	26.9
105°	132.2	135.0	137.9	140.7	129.2	103.4	77.6	51.8	25.9	27.0	28.0
107.5°	167.6	169.9	172.2	174.5	160.1	129.2	98.2	67.3	36.4	35.3	34.2
110°	190.5	192.5	194.4	196.4	183.8	156.5	129.1	101.7	74.4	65.0	55.5





TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	212.1	213.8	215.6	217.3	214.8	208.1	201.3	194.5	187.8	153.3	118.8
115°	246.2	247.9	249.5	251.1	253.1	255.4	257.8	260.2	262.5	218.7	175.0
117.5°	277.2	279.0	280.8	282.6	284.3	285.9	287.6	289.2	290.7	280.2	269.6
120°	299.2	300.7	302.1	303.5	305.1	306.8	308.5	310.1	311.9	313.0	314.1
122.5°	318.4	319.9	321.4	322.9	324.6	326.4	328.2	330.1	332.0	332.6	333.3
125°	347.2	348.4	349.6	350.8	352.4	354.2	356.0	357.8	359.5	360.2	360.9
127.5°	373.6	375.0	376.3	377.6	379.0	380.3	381.7	383.0	384.4	385.3	386.3
130°	390.4	391.9	393.5	394.9	396.2	397.3	398.3	399.3	400.4	401.5	402.4
132.5°	407.2	408.5	409.8	411.1	412.2	413.3	414.3	415.3	416.4	417.3	418.2
135°	429.6	431.0	432.6	434.1	435.3	436.1	437.0	437.8	438.6	439.6	440.6
137.5°	451.4	452.5	453.6	454.6	455.7	456.6	457.6	458.5	459.5	460.5	461.4
140°	465.8	466.6	467.3	468.1	469.0	470.0	471.1	472.1	473.1	474.0	474.8
142.5°	478.0	478.7	479.3	480.0	480.9	482.2	483.3	484.5	485.8	486.5	487.3
145°	496.4	496.4	496.3	496.2	496.9	498.6	500.1	501.7	503.4	504.0	504.7
147.5°	512.9	512.6	512.3	511.8	512.5	514.0	515.7	517.2	518.9	519.3	519.8
150°	523.5	522.9	522.2	521.5	522.0	523.5	525.0	526.5	528.0	528.6	529.1
152.5°	532.6	531.9	531.2	530.4	530.8	532.2	533.7	535.1	536.5	537.1	537.7
155°	545.9	545.0	544.2	543.3	543.5	544.6	545.8	546.9	548.0	548.6	549.2
157.5°	556.5	555.8	555.1	554.3	554.4	555.1	556.0	556.8	557.6	558.2	558.8
160°	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	563.9	564.4
162.5°	568.2	567.6	567.0	566.6	566.5	567.0	567.4	567.9	568.4	569.1	569.7
165°	575.5	574.9	574.4	573.8	573.7	574.0	574.2	574.5	574.8	575.5	576.2
167.5°	581.0	580.4	579.8	579.3	579.1	579.4	579.7	579.9	580.2	580.8	581.5
170°	584.1	583.5	582.9	582.4	582.1	582.4	582.5	582.7	582.9	583.6	584.2
172.5°	586.1	585.5	585.0	584.4	584.2	584.4	584.6	584.7	585.0	585.6	586.3
175°	588.6	588.0	587.3	586.6	586.4	586.6	586.8	586.9	587.2	587.8	588.5
177.5°	589.2	588.6	588.2	587.6	587.3	587.4	587.5	587.6	587.7	588.2	588.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	499.9	501.9	501.9	502.2	504.6	504.3	504.1
5°	531.9	535.1	535.4	538.7	541.0	540.2	538.2
7.5°	562.1	568.0	572.5	574.9	577.9	579.7	578.9
10°	586.2	594.7	599.9	603.4	607.6	610.8	609.7
12.5°	608.0	618.1	625.3	631.3	631.8	635.9	633.1
15°	642.0	652.6	653.8	658.2	661.8	661.4	661.5
17.5°	653.1	656.6	657.3	657.4	657.5	656.2	653.3
20°	649.1	647.8	644.7	642.3	638.1	637.5	633.8
22.5°	630.1	626.1	618.2	612.9	606.3	604.6	603.6
25°	592.9	583.8	571.2	559.1	555.8	549.3	551.1
27.5°	541.6	527.5	513.8	504.1	495.2	485.5	488.3
30°	505.6	489.7	470.4	455.6	446.1	436.9	435.2
32.5°	462.7	439.3	417.8	404.8	390.3	384.4	378.1
35°	388.6	365.7	344.5	326.1	315.6	307.4	300.0
37.5°	322.0	295.7	278.5	263.7	256.0	251.4	252.6
40°	280.6	257.6	245.0	233.7	226.7	223.4	224.1
42.5°	247.1	229.9	219.6	211.8	206.8	205.0	204.6
45°	209.1	199.5	190.9	186.5	184.1	182.1	180.8
47.5°	183.2	175.3	170.5	167.9	165.8	163.7	163.6
50°	167.6	162.4	159.1	156.3	154.7	153.2	154.5
52.5°	155.7	151.0	147.7	145.2	144.6	143.2	143.2
55°	138.2	134.4	132.1	129.8	128.7	128.0	127.0
57.5°	122.1	118.6	116.4	115.0	112.9	112.2	111.9
60°	110.7	107.9	105.7	103.9	103.0	101.5	101.5
62.5°	100.2	97.4	95.4	94.0	92.5	91.9	92.0
65°	85.0	82.8	80.7	79.2	78.9	77.8	78.2
67.5°	71.0	69.5	67.3	66.5	65.9	65.3	64.8
70°	61.6	60.2	59.1	58.0	57.4	57.4	57.4
72.5°	53.8	52.0	51.4	50.0	50.3	49.7	49.1
75°	41.7	40.5	40.0	39.5	38.6	38.6	38.6
77.5°	30.7	30.3	29.7	29.1	28.9	28.7	28.8
80°	23.7	23.5	23.2	23.2	22.7	22.6	22.3
82.5°	18.3	17.8	17.5	17.4	17.3	17.3	17.2
85°	10.4	10.0	10.0	10.2	9.8	9.8	10.0
87.5°	6.0	6.1	6.0	6.0	6.2	6.1	6.1
90°	9.9	10.4	10.8	10.9	11.1	11.3	11.5
92.5°	10.6	10.8	11.0	11.2	11.3	11.4	11.5
95°	18.0	18.5	18.7	18.6	18.5	18.4	18.3
97.5°	23.3	23.7	24.0	24.1	24.2	24.3	24.5
100°	26.5	27.3	27.7	28.0	28.1	28.3	28.5
102.5°	27.9	28.9	29.5	29.8	30.0	30.2	30.6
105°	29.1	30.1	30.8	31.2	31.6	32.0	32.4
107.5°	33.2	32.1	31.8	32.1	32.5	32.9	33.3
110°	46.1	36.6	32.1	32.4	32.9	33.3	33.6



TEST NUMBER: P331249-930

CATALOG NUMBER: S122DIP-S290D530U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	84.3	49.8	32.8	33.0	33.3	33.7	33.9
115°	131.2	87.4	62.1	55.3	48.5	41.7	34.9
117.5°	259.0	248.4	232.0	209.5	187.2	164.9	142.4
120°	315.3	316.4	310.6	297.8	285.1	272.3	259.5
122.5°	334.0	334.7	333.8	331.3	328.8	326.4	323.8
125°	361.5	362.2	362.6	363.0	363.2	363.5	363.8
127.5°	387.3	388.2	388.7	388.8	388.9	388.9	389.0
130°	403.5	404.6	405.0	404.9	404.8	404.7	404.6
132.5°	419.1	420.0	420.3	420.2	420.1	420.0	420.0
135°	441.5	442.5	442.9	442.6	442.5	442.3	442.1
137.5°	462.3	463.3	463.5	463.2	462.8	462.6	462.3
140°	475.6	476.5	476.7	476.2	475.8	475.3	474.8
142.5°	488.0	488.9	489.0	488.5	488.0	487.5	487.1
145°	505.3	506.0	506.1	505.6	505.2	504.7	504.2
147.5°	520.3	520.8	520.8	520.5	520.1	519.7	519.3
150°	529.7	530.3	530.4	529.9	529.4	528.9	528.5
152.5°	538.3	538.8	538.7	538.2	537.5	536.9	536.3
155°	549.8	550.3	550.2	549.4	548.7	548.0	547.1
157.5°	559.5	560.1	560.1	559.3	558.6	557.8	557.1
160°	565.0	565.6	565.6	564.9	564.3	563.5	562.9
162.5°	570.4	571.0	571.0	570.1	569.3	568.5	567.7
165°	576.8	577.5	577.5	576.8	576.2	575.5	574.8
167.5°	582.2	582.9	582.8	581.9	581.1	580.2	579.4
170°	584.9	585.5	585.5	584.6	583.8	582.9	582.0
172.5°	586.9	587.6	587.5	586.7	585.8	585.0	584.1
175°	589.1	589.8	589.7	588.7	587.7	586.9	585.9
177.5°	589.3	589.8	589.7	589.1	588.3	587.7	587.0
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0

(END OF REPORT)