

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331268-930

Luminaire Tested: **S122DIP-S290D925U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331268-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D925U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3763.0 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18
4	71	61	53	48	63	55	49	44	44	39	36	33	30	28	23	21	20	16
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17	14
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	16	12
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7781	7781	7781	7781
5°	8723	7831	6940	7831
10°	9996	7768	6005	7768
15°	11057	7626	5307	7626
20°	10890	7472	4837	7472
25°	9818	7269	4541	7269
30°	8114	6943	4323	6943
35°	5913	6603	4169	6603
40°	4723	6203	4083	6203
45°	4128	5740	3966	5740
50°	3881	5290	3888	5290
55°	3575	4833	3783	4833
60°	3278	4346	3626	4346
65°	2988	3912	3465	3912
70°	2710	3489	3238	3489
75°	2408	3013	2863	3013
80°	2073	2492	2306	2492
85°	1853	1853	1371	1853



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.9	1.2
10°-20°	133.4	3.5
20°-30°	193.6	5.1
30°-40°	204.3	5.4
40°-50°	180.9	4.8
50°-60°	144.4	3.8
60°-70°	98.1	2.6
70°-80°	50.3	1.3
80°-90°	16.0	0.4
90°-100°	61.1	1.6
100°-110°	189.8	5.0
110°-120°	324.3	8.6
120°-130°	426.5	11.3
130°-140°	478.7	12.7
140°-150°	469.4	12.5
150°-160°	393.7	10.5
160°-170°	261.1	6.9
170°-180°	91.3	2.4
0°-30°	373.0	9.9
0°-40°	577.3	15.3
0°-60°	902.6	24.0
0°-90°	1067.0	28.4
90°-120°	575.2	15.3
90°-150°	1949.8	51.8
90°-180°	2696.0	71.6
0°-180°	3763.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	482	482	482	482	482	
5°	538	483	428	483	538	54
15°	662	456	318	456	662	183
25°	551	408	255	408	551	249
35°	300	335	212	335	300	195
45°	181	251	174	251	181	142
55°	127	172	134	172	127	114
65°	78	102	91	102	78	78
75°	39	48	46	48	39	41
85°	10	10	7	10	10	12
90°	28	1	28	1	28	12
95°	50	42	50	42	50	56
105°	181	175	181	175	181	190
115°	326	326	326	326	326	321
125°	475	474	475	474	475	424
135°	620	613	620	613	620	477
145°	752	744	752	744	752	469
155°	857	850	857	850	857	394
165°	926	925	926	925	926	261
175°	959	962	959	962	959	91
180°	964	964	964	964	964	



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	504.1	504.3	504.6	502.2	501.9	501.9	499.9	498.1	495.9	493.2	493.5
5°	538.2	540.2	541.0	538.7	535.4	535.1	531.9	526.8	521.9	518.0	515.3
7.5°	578.9	579.7	577.9	574.9	572.5	568.0	562.1	556.4	548.4	541.0	535.6
10°	609.7	610.8	607.6	603.4	599.9	594.7	586.2	577.5	567.0	556.8	548.6
12.5°	633.1	635.9	631.8	631.3	625.3	618.1	608.0	603.6	588.7	574.5	565.7
15°	661.5	661.4	661.8	658.2	653.8	652.6	642.0	630.2	609.4	601.0	586.5
17.5°	653.3	656.2	657.5	657.4	657.3	656.6	653.1	645.8	635.3	621.7	605.1
20°	633.8	637.5	638.1	642.3	644.7	647.8	649.1	647.1	640.7	629.3	614.9
22.5°	603.6	604.6	606.3	612.9	618.2	626.1	630.1	637.1	634.5	629.0	616.9
25°	551.1	549.3	555.8	559.1	571.2	583.8	592.9	602.8	611.7	617.1	613.6
27.5°	488.3	485.5	495.2	504.1	513.8	527.5	541.6	558.3	572.2	589.6	595.6
30°	435.2	436.9	446.1	455.6	470.4	489.7	505.6	523.9	543.8	563.2	576.7
32.5°	378.1	384.4	390.3	404.8	417.8	439.3	462.7	485.6	510.3	532.4	553.3
35°	300.0	307.4	315.6	326.1	344.5	365.7	388.6	419.5	453.2	483.4	508.2
37.5°	252.6	251.4	256.0	263.7	278.5	295.7	322.0	352.5	392.2	427.6	462.7
40°	224.1	223.4	226.7	233.7	245.0	257.6	280.6	307.4	344.3	387.7	429.3
42.5°	204.6	205.0	206.8	211.8	219.6	229.9	247.1	269.9	303.7	344.5	389.3
45°	180.8	182.1	184.1	186.5	190.9	199.5	209.1	225.4	252.1	286.2	330.2
47.5°	163.6	163.7	165.8	167.9	170.5	175.3	183.2	193.4	212.2	239.9	277.9
50°	154.5	153.2	154.7	156.3	159.1	162.4	167.6	177.2	189.8	212.2	243.9
52.5°	143.2	143.2	144.6	145.2	147.7	151.0	155.7	162.4	173.8	191.4	217.4
55°	127.0	128.0	128.7	129.8	132.1	134.4	138.2	142.6	151.5	164.6	183.9
57.5°	111.9	112.2	112.9	115.0	116.4	118.6	122.1	126.2	132.0	141.7	156.2
60°	101.5	101.5	103.0	103.9	105.7	107.9	110.7	114.6	119.8	127.8	139.5
62.5°	92.0	91.9	92.5	94.0	95.4	97.4	100.2	103.5	108.4	115.5	125.1
65°	78.2	77.8	78.9	79.2	80.7	82.8	85.0	88.5	92.5	97.6	106.2
67.5°	64.8	65.3	65.9	66.5	67.3	69.5	71.0	73.5	76.8	81.1	86.8
70°	57.4	57.4	57.4	58.0	59.1	60.2	61.6	63.7	66.9	70.5	75.7
72.5°	49.1	49.7	50.3	50.0	51.4	52.0	53.8	55.0	58.0	60.3	64.9
75°	38.6	38.6	38.6	39.5	40.0	40.5	41.7	42.8	44.3	47.2	49.7
77.5°	28.8	28.7	28.9	29.1	29.7	30.3	30.7	31.6	33.0	34.4	36.4
80°	22.3	22.6	22.7	23.2	23.2	23.5	23.7	25.0	25.9	26.8	28.1
82.5°	17.2	17.3	17.3	17.4	17.5	17.8	18.3	18.7	19.0	19.7	20.7
85°	10.0	9.8	9.8	10.2	10.0	10.0	10.4	10.8	10.8	10.9	11.5
87.5°	9.4	9.4	9.5	9.3	9.2	9.4	9.5	9.4	9.6	9.9	9.2
90°	27.6	27.5	27.3	27.1	26.9	27.1	27.4	27.7	28.1	28.5	24.5
92.5°	26.3	26.3	26.3	26.3	26.3	26.2	26.1	26.0	25.9	25.8	24.9
95°	50.5	50.8	51.2	51.5	51.9	52.1	52.1	52.1	52.1	52.1	51.7
97.5°	87.4	87.4	87.5	87.5	87.6	87.6	87.6	87.6	87.6	87.6	86.8
100°	111.5	111.6	111.9	112.0	112.2	112.3	112.3	112.3	112.3	112.3	111.8
102.5°	138.8	139.0	139.2	139.3	139.5	139.6	139.4	139.3	139.1	139.0	138.3
105°	180.6	180.6	180.6	180.6	180.6	180.4	180.1	179.7	179.4	179.0	178.6
107.5°	220.0	220.9	221.7	222.5	223.3	223.6	223.6	223.4	223.2	223.1	223.1
110°	250.6	251.1	251.7	252.3	252.7	253.1	253.1	253.1	253.1	253.1	253.1



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	279.9	280.3	280.7	281.1	281.4	281.9	282.3	282.7	283.2	283.6	283.8
115°	325.5	326.0	326.5	327.1	327.6	328.0	328.2	328.3	328.6	328.7	329.1
117.5°	368.9	369.4	370.0	370.6	371.0	371.5	372.0	372.4	372.8	373.3	374.3
120°	399.5	400.1	400.6	401.1	401.7	401.9	401.9	401.9	401.9	401.9	403.4
122.5°	429.4	429.8	430.2	430.6	431.0	431.5	431.9	432.3	432.8	433.2	434.2
125°	475.2	475.3	475.5	475.7	475.9	476.2	476.8	477.4	477.8	478.4	479.0
127.5°	516.8	517.4	518.0	518.5	519.1	519.8	520.4	521.1	521.7	522.4	523.0
130°	546.7	547.5	548.2	548.9	549.7	550.2	550.6	550.9	551.3	551.6	552.0
132.5°	575.4	576.0	576.6	577.2	577.7	578.4	579.2	580.0	580.8	581.6	581.5
135°	620.0	620.5	621.1	621.6	622.2	622.5	622.7	622.9	623.1	623.2	622.9
137.5°	660.3	661.0	661.8	662.5	663.2	663.7	663.8	664.0	664.1	664.2	663.8
140°	688.4	689.1	689.7	690.5	691.2	691.6	691.6	691.6	691.6	691.6	690.7
142.5°	713.7	714.4	715.2	715.9	716.6	716.9	716.7	716.6	716.5	716.3	715.7
145°	751.8	752.5	753.3	754.0	754.7	755.0	754.8	754.6	754.4	754.2	753.2
147.5°	785.8	786.5	787.2	787.9	788.6	788.7	788.3	787.9	787.5	787.1	786.4
150°	808.0	808.5	809.0	809.6	810.1	810.1	809.6	809.0	808.5	808.0	807.2
152.5°	828.8	829.5	830.1	830.8	831.5	831.5	830.8	830.1	829.5	828.8	827.9
155°	856.7	857.3	857.9	858.3	858.9	858.8	857.9	857.0	856.1	855.1	854.6
157.5°	880.8	881.7	882.6	883.5	884.3	884.1	882.9	881.7	880.4	879.2	878.9
160°	895.8	896.5	897.2	898.0	898.7	898.5	897.4	896.3	895.3	894.1	894.0
162.5°	908.8	909.7	910.5	911.4	912.3	912.1	910.9	909.6	908.4	907.2	907.0
165°	925.9	926.8	927.7	928.6	929.5	929.4	928.1	926.8	925.5	924.3	924.3
167.5°	939.9	940.9	941.8	942.7	943.6	943.5	942.2	940.9	939.7	938.4	938.5
170°	947.1	948.1	949.3	950.3	951.4	951.3	950.1	948.8	947.5	946.2	946.4
172.5°	952.9	954.0	955.1	956.2	957.2	957.2	955.9	954.6	953.4	952.1	952.3
175°	959.3	960.3	961.4	962.5	963.6	963.5	962.2	961.0	959.7	958.5	958.8
177.5°	962.2	963.0	963.9	964.8	965.6	965.6	964.8	963.9	963.0	962.2	962.5
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	494.5	493.3	492.6	489.9	487.5	485.2	484.5	484.7	481.4	478.3	477.0
5°	513.8	510.1	506.5	501.6	495.6	489.1	485.8	483.2	476.7	469.7	465.6
7.5°	531.0	525.7	518.9	509.6	500.9	490.7	484.2	478.5	469.0	459.1	453.0
10°	541.5	534.3	525.6	514.1	503.6	491.1	482.5	473.8	462.7	450.8	443.4
12.5°	550.6	540.9	532.3	517.6	505.1	489.5	479.2	466.9	455.3	441.2	433.9
15°	572.1	554.2	537.9	521.1	505.8	484.1	472.6	456.2	440.8	423.4	415.1
17.5°	588.7	568.5	542.9	521.7	503.8	479.7	462.9	443.2	425.0	405.1	393.8
20°	598.2	575.0	547.5	522.3	500.8	473.4	455.0	434.9	413.6	391.2	379.0
22.5°	603.8	579.5	552.2	520.1	494.9	468.2	445.2	423.0	401.5	377.2	364.4
25°	605.6	583.4	554.5	518.2	487.5	457.3	429.5	408.0	381.9	359.3	340.6
27.5°	596.8	580.9	553.1	514.7	478.9	443.6	412.6	388.3	360.8	336.2	317.4
30°	586.0	576.7	549.7	511.2	472.1	434.1	400.1	372.4	345.0	320.2	300.9
32.5°	569.2	567.3	543.5	506.1	464.8	422.2	386.9	359.0	328.6	304.2	285.8
35°	536.4	545.3	530.3	494.9	451.2	405.0	366.9	335.0	303.5	280.2	263.0
37.5°	492.3	514.4	510.5	478.4	432.7	386.5	344.3	311.0	281.0	257.5	240.6
40°	461.9	490.1	494.2	465.8	419.7	372.1	327.4	294.3	265.1	243.5	226.5
42.5°	429.3	462.2	473.4	450.7	405.4	356.9	312.3	278.0	249.0	228.1	213.0
45°	374.7	418.2	438.4	425.4	381.7	332.1	286.2	251.4	225.0	205.4	193.7
47.5°	323.6	371.1	398.3	393.7	355.3	306.1	260.7	227.3	201.7	186.1	175.6
50°	287.5	336.3	369.1	370.6	336.3	287.6	242.1	210.6	187.0	172.4	163.9
52.5°	256.0	302.7	338.4	346.3	315.1	268.4	225.3	194.0	173.3	159.8	152.2
55°	215.0	254.5	294.1	308.6	283.6	239.1	199.3	171.7	152.2	143.0	136.3
57.5°	178.8	211.7	248.3	264.2	248.8	210.8	173.4	149.4	133.7	125.6	120.4
60°	159.6	185.6	218.2	237.3	223.9	190.0	157.4	134.6	121.6	114.5	109.7
62.5°	141.9	164.9	192.4	209.9	202.6	170.6	141.5	121.3	110.1	103.4	99.9
65°	117.1	135.2	156.5	172.6	167.8	143.6	119.6	102.4	93.5	88.1	85.4
67.5°	96.4	109.5	124.3	138.4	134.5	117.3	98.2	84.7	78.1	73.5	71.7
70°	83.3	93.4	106.5	117.8	114.6	100.6	85.4	73.9	68.2	64.2	62.6
72.5°	70.9	79.1	89.2	98.4	96.3	84.5	71.9	63.3	58.8	55.2	53.9
75°	53.6	59.8	66.0	72.1	71.5	62.5	55.0	48.3	44.8	42.1	41.5
77.5°	39.5	43.0	47.2	50.8	49.8	44.6	38.8	35.0	32.4	30.6	30.2
80°	30.2	32.2	35.2	37.7	36.5	34.2	29.6	26.8	25.0	23.2	22.4
82.5°	21.9	23.9	25.7	27.1	26.1	24.1	21.2	19.3	18.2	17.0	16.6
85°	11.5	12.6	13.4	13.7	13.4	12.1	10.8	10.0	9.0	8.5	8.3
87.5°	8.6	7.7	6.9	6.6	5.8	5.3	4.3	3.4	3.7	4.0	4.2
90°	20.5	16.6	12.6	9.5	7.3	5.1	3.0	0.8	3.0	5.1	7.3
92.5°	24.0	23.1	22.1	20.9	19.2	17.7	16.1	14.5	16.1	17.7	19.2
95°	51.4	51.0	50.6	49.6	47.7	45.9	44.1	42.3	44.1	45.9	47.7
97.5°	86.2	85.5	84.8	83.6	82.1	80.5	78.9	77.3	78.9	80.5	82.1
100°	111.2	110.6	110.1	109.1	107.7	106.2	104.8	103.3	104.8	106.2	107.7
102.5°	137.6	136.9	136.2	135.3	134.1	133.0	131.8	130.7	131.8	133.0	134.1
105°	178.3	177.9	177.6	177.1	176.6	176.0	175.5	175.0	175.5	176.0	176.6
107.5°	223.1	223.1	223.1	222.7	221.9	221.1	220.3	219.5	220.3	221.1	221.9
110°	253.1	253.1	253.1	252.5	251.4	250.3	249.2	248.2	249.2	250.3	251.4



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	283.9	284.1	284.2	283.7	282.7	281.6	280.5	279.4	280.5	281.6	282.7
115°	329.5	329.8	330.1	329.8	328.7	327.6	326.5	325.5	326.5	327.6	328.7
117.5°	375.3	376.3	377.3	377.2	375.7	374.2	372.8	371.4	372.8	374.2	375.7
120°	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9	403.4	404.8	406.3
122.5°	435.2	436.2	437.2	436.8	435.1	433.4	431.6	429.9	431.6	433.4	435.1
125°	479.5	480.0	480.6	480.0	478.4	476.8	475.2	473.5	475.2	476.8	478.4
127.5°	523.7	524.3	525.0	524.2	522.2	520.2	518.0	516.0	518.0	520.2	522.2
130°	552.4	552.7	553.1	552.1	549.8	547.4	545.0	542.7	545.0	547.4	549.8
132.5°	581.5	581.4	581.3	580.3	578.4	576.5	574.5	572.7	574.5	576.5	578.4
135°	622.5	622.2	621.8	620.6	618.6	616.6	614.7	612.7	614.7	616.6	618.6
137.5°	663.3	662.8	662.3	661.3	659.7	658.0	656.4	654.8	656.4	658.0	659.7
140°	689.7	688.8	687.9	686.7	685.1	683.5	681.8	680.2	681.8	683.5	685.1
142.5°	715.1	714.4	713.9	712.7	711.1	709.5	707.8	706.2	707.8	709.5	711.1
145°	752.0	751.0	749.9	748.7	747.5	746.2	744.9	743.6	744.9	746.2	747.5
147.5°	785.6	785.0	784.2	783.1	781.5	780.1	778.5	777.0	778.5	780.1	781.5
150°	806.5	805.8	805.0	804.1	803.1	801.9	800.9	799.8	800.9	801.9	803.1
152.5°	827.0	826.1	825.3	824.3	823.2	822.1	821.1	819.9	821.1	822.1	823.2
155°	854.0	853.5	853.0	852.4	851.9	851.3	850.8	850.3	850.8	851.3	851.9
157.5°	878.6	878.2	877.9	877.6	877.2	876.9	876.4	876.1	876.4	876.9	877.2
160°	893.8	893.6	893.5	893.2	892.8	892.4	892.1	891.8	892.1	892.4	892.8
162.5°	906.9	906.7	906.4	906.4	906.3	906.2	906.1	906.0	906.1	906.2	906.3
165°	924.3	924.3	924.3	924.4	924.5	924.7	925.0	925.1	925.0	924.7	924.5
167.5°	938.5	938.6	938.6	938.9	939.4	940.0	940.5	941.0	940.5	940.0	939.4
170°	946.6	946.8	947.0	947.3	947.9	948.4	948.9	949.5	948.9	948.4	947.9
172.5°	952.4	952.7	952.8	953.2	953.7	954.3	954.8	955.4	954.8	954.3	953.7
175°	959.2	959.5	959.9	960.3	960.9	961.4	962.0	962.5	962.0	961.4	960.9
177.5°	962.8	963.0	963.4	963.7	964.2	964.6	965.0	965.5	965.0	964.6	964.2
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	475.6	474.7	471.6	469.9	467.2	464.7	463.1	463.8	464.4	464.1	463.7
5°	461.9	458.4	453.0	448.4	445.1	439.0	436.3	435.0	433.9	432.7	431.4
7.5°	445.6	440.1	432.4	425.8	419.6	412.0	407.6	405.1	402.4	399.5	396.9
10°	434.1	426.3	418.2	409.0	401.5	394.7	388.6	384.5	380.7	377.2	374.7
12.5°	422.0	413.0	402.9	390.3	382.1	372.3	371.4	364.2	358.4	356.2	353.2
15°	402.7	390.0	377.2	362.2	355.8	346.9	341.4	335.7	330.8	327.3	326.4
17.5°	380.7	364.4	351.6	340.9	330.3	321.1	316.0	311.6	307.4	302.8	302.1
20°	363.9	349.8	336.0	326.5	315.6	306.3	300.0	295.6	292.0	289.3	286.9
22.5°	348.1	332.6	319.9	309.7	298.9	291.4	286.4	282.1	279.2	276.1	273.9
25°	322.6	310.6	296.7	285.0	276.1	271.3	267.3	263.6	261.7	259.7	257.1
27.5°	300.4	287.0	274.0	265.0	257.1	252.9	250.0	247.4	245.7	244.5	243.0
30°	284.7	271.2	261.0	252.1	245.6	241.3	239.5	238.0	235.9	235.2	234.5
32.5°	269.5	257.4	248.7	240.9	234.8	232.0	230.3	228.9	227.4	226.7	225.1
35°	248.2	238.0	229.5	225.2	220.2	217.8	216.5	214.7	213.2	212.5	212.2
37.5°	228.0	219.2	213.6	208.1	206.0	204.6	202.8	201.5	201.1	201.0	200.7
40°	215.0	207.8	202.8	198.4	197.5	195.2	193.7	192.7	192.7	192.8	192.7
42.5°	203.2	196.7	192.2	188.4	187.4	186.1	184.5	184.5	184.7	185.4	184.7
45°	185.2	180.6	177.4	175.6	173.6	172.3	172.0	172.6	172.8	173.0	173.6
47.5°	168.7	165.6	162.7	160.7	159.8	159.6	159.4	160.4	161.3	161.6	162.4
50°	158.9	155.4	153.0	151.6	150.9	150.6	150.9	152.1	152.8	153.7	154.3
52.5°	148.0	145.4	143.8	142.8	142.5	142.8	142.8	144.1	145.2	145.6	145.9
55°	132.8	130.9	130.6	128.9	129.6	129.5	130.4	131.1	132.2	133.4	133.5
57.5°	117.6	116.2	115.2	115.4	115.6	116.4	117.2	118.5	119.6	120.8	120.9
60°	107.6	106.9	106.3	106.3	106.6	107.8	108.7	110.0	110.7	111.5	112.0
62.5°	98.4	97.7	97.1	97.4	98.4	99.1	100.1	100.9	101.6	102.3	102.6
65°	83.9	83.6	84.1	84.5	84.6	85.5	86.8	87.4	88.1	88.5	89.8
67.5°	70.5	70.6	70.5	71.0	72.2	72.3	73.5	74.8	75.0	75.7	76.6
70°	61.5	61.9	62.2	62.6	63.5	63.9	64.8	65.4	66.1	66.7	67.3
72.5°	53.2	53.2	53.6	53.6	54.4	55.1	55.9	56.5	57.2	58.0	58.5
75°	40.9	40.9	41.3	41.5	42.4	43.4	43.1	43.5	44.3	45.0	45.4
77.5°	29.9	29.5	29.9	30.1	30.4	31.1	31.3	31.8	32.7	32.4	32.9
80°	22.7	22.3	22.7	23.0	23.0	23.9	23.9	24.3	24.8	24.3	24.8
82.5°	16.2	16.0	16.4	16.5	16.7	16.8	17.0	17.1	17.7	17.4	17.7
85°	8.2	8.0	8.2	8.0	8.2	8.3	8.3	8.2	8.2	8.5	8.0
87.5°	4.4	4.9	5.5	6.4	7.0	7.6	7.4	7.3	7.3	6.8	6.8
90°	9.5	12.6	16.6	20.5	24.5	28.5	28.1	27.7	27.4	27.1	26.9
92.5°	20.9	22.1	23.1	24.0	24.9	25.8	25.9	26.0	26.1	26.2	26.3
95°	49.6	50.6	51.0	51.4	51.7	52.1	52.1	52.1	52.1	52.1	51.9
97.5°	83.6	84.8	85.5	86.2	86.8	87.6	87.6	87.6	87.6	87.6	87.6
100°	109.1	110.1	110.6	111.2	111.8	112.3	112.3	112.3	112.3	112.3	112.2
102.5°	135.3	136.2	136.9	137.6	138.3	139.0	139.1	139.3	139.4	139.6	139.5
105°	177.1	177.6	177.9	178.3	178.6	179.0	179.4	179.7	180.1	180.4	180.6
107.5°	222.7	223.1	223.1	223.1	223.1	223.1	223.2	223.4	223.6	223.6	223.3
110°	252.5	253.1	253.1	253.1	253.1	253.1	253.1	253.1	253.1	253.1	252.7



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	283.7	284.2	284.1	283.9	283.8	283.6	283.2	282.7	282.3	281.9	281.4
115°	329.8	330.1	329.8	329.5	329.1	328.7	328.6	328.3	328.2	328.0	327.6
117.5°	377.2	377.3	376.3	375.3	374.3	373.3	372.8	372.4	372.0	371.5	371.0
120°	407.7	407.7	406.3	404.8	403.4	401.9	401.9	401.9	401.9	401.9	401.7
122.5°	436.8	437.2	436.2	435.2	434.2	433.2	432.8	432.3	431.9	431.5	431.0
125°	480.0	480.6	480.0	479.5	479.0	478.4	477.8	477.4	476.8	476.2	475.9
127.5°	524.2	525.0	524.3	523.7	523.0	522.4	521.7	521.1	520.4	519.8	519.1
130°	552.1	553.1	552.7	552.4	552.0	551.6	551.3	550.9	550.6	550.2	549.7
132.5°	580.3	581.3	581.4	581.5	581.5	581.6	580.8	580.0	579.2	578.4	577.7
135°	620.6	621.8	622.2	622.5	622.9	623.2	623.1	622.9	622.7	622.5	622.2
137.5°	661.3	662.3	662.8	663.3	663.8	664.2	664.1	664.0	663.8	663.7	663.2
140°	686.7	687.9	688.8	689.7	690.7	691.6	691.6	691.6	691.6	691.6	691.2
142.5°	712.7	713.9	714.4	715.1	715.7	716.3	716.5	716.6	716.7	716.9	716.6
145°	748.7	749.9	751.0	752.0	753.2	754.2	754.4	754.6	754.8	755.0	754.7
147.5°	783.1	784.2	785.0	785.6	786.4	787.1	787.5	787.9	788.3	788.7	788.6
150°	804.1	805.0	805.8	806.5	807.2	808.0	808.5	809.0	809.6	810.1	810.1
152.5°	824.3	825.3	826.1	827.0	827.9	828.8	829.5	830.1	830.8	831.5	831.5
155°	852.4	853.0	853.5	854.0	854.6	855.1	856.1	857.0	857.9	858.8	858.9
157.5°	877.6	877.9	878.2	878.6	878.9	879.2	880.4	881.7	882.9	884.1	884.3
160°	893.2	893.5	893.6	893.8	894.0	894.1	895.3	896.3	897.4	898.5	898.7
162.5°	906.4	906.4	906.7	906.9	907.0	907.2	908.4	909.6	910.9	912.1	912.3
165°	924.4	924.3	924.3	924.3	924.3	924.3	925.5	926.8	928.1	929.4	929.5
167.5°	938.9	938.6	938.6	938.5	938.5	938.4	939.7	940.9	942.2	943.5	943.6
170°	947.3	947.0	946.8	946.6	946.4	946.2	947.5	948.8	950.1	951.3	951.4
172.5°	953.2	952.8	952.7	952.4	952.3	952.1	953.4	954.6	955.9	957.2	957.2
175°	960.3	959.9	959.5	959.2	958.8	958.5	959.7	961.0	962.2	963.5	963.6
177.5°	963.7	963.4	963.0	962.8	962.5	962.2	963.0	963.9	964.8	965.6	965.6
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	462.2	461.9	461.9	460.6	461.9	461.9	462.2	463.7	464.1	464.4	463.8
5°	428.8	428.2	427.3	428.2	427.3	428.2	428.8	431.4	432.7	433.9	435.0
7.5°	395.7	393.5	393.1	390.9	393.1	393.5	395.7	396.9	399.5	402.4	405.1
10°	371.5	370.1	369.8	366.3	369.8	370.1	371.5	374.7	377.2	380.7	384.5
12.5°	353.2	349.6	350.3	348.3	350.3	349.6	353.2	353.2	356.2	358.4	364.2
15°	321.3	321.3	320.6	317.5	320.6	321.3	321.3	326.4	327.3	330.8	335.7
17.5°	298.5	298.1	296.4	297.3	296.4	298.1	298.5	302.1	302.8	307.4	311.6
20°	284.9	283.7	281.5	281.5	281.5	283.7	284.9	286.9	289.3	292.0	295.6
22.5°	272.0	271.9	269.5	270.3	269.5	271.9	272.0	273.9	276.1	279.2	282.1
25°	256.9	255.4	254.3	254.9	254.3	255.4	256.9	257.1	259.7	261.7	263.6
27.5°	242.6	241.7	241.7	240.2	241.7	241.7	242.6	243.0	244.5	245.7	247.4
30°	234.3	232.4	232.8	231.9	232.8	232.4	234.3	234.5	235.2	235.9	238.0
32.5°	224.8	224.1	223.8	223.0	223.8	224.1	224.8	225.1	226.7	227.4	228.9
35°	211.9	212.1	211.2	211.5	211.2	212.1	211.9	212.2	212.5	213.2	214.7
37.5°	200.6	201.1	200.7	200.8	200.7	201.1	200.6	200.7	201.0	201.1	201.5
40°	193.1	193.1	193.1	193.7	193.1	193.1	193.1	192.7	192.8	192.7	192.7
42.5°	186.1	185.7	185.5	185.4	185.5	185.7	186.1	184.7	185.4	184.7	184.5
45°	173.9	174.5	174.6	173.7	174.6	174.5	173.9	173.6	173.0	172.8	172.6
47.5°	162.9	163.0	162.9	163.7	162.9	163.0	162.9	162.4	161.6	161.3	160.4
50°	155.2	154.8	155.2	154.8	155.2	154.8	155.2	154.3	153.7	152.8	152.1
52.5°	147.1	147.2	146.9	146.8	146.9	147.2	147.1	145.9	145.6	145.2	144.1
55°	134.3	134.6	134.4	134.4	134.4	134.6	134.3	133.5	133.4	132.2	131.1
57.5°	121.1	121.4	121.6	120.8	121.6	121.4	121.1	120.9	120.8	119.6	118.5
60°	111.9	112.8	112.6	112.3	112.6	112.8	111.9	112.0	111.5	110.7	110.0
62.5°	103.4	103.8	103.7	103.6	103.7	103.8	103.4	102.6	102.3	101.6	100.9
65°	90.4	90.7	90.2	90.7	90.2	90.7	90.4	89.8	88.5	88.1	87.4
67.5°	76.3	76.5	76.9	77.1	76.9	76.5	76.3	76.6	75.7	75.0	74.8
70°	67.6	67.4	68.0	68.6	68.0	67.4	67.6	67.3	66.7	66.1	65.4
72.5°	58.4	58.8	58.6	59.0	58.6	58.8	58.4	58.5	58.0	57.2	56.5
75°	45.0	45.6	45.4	45.9	45.4	45.6	45.0	45.4	45.0	44.3	43.5
77.5°	32.5	32.6	32.5	32.9	32.5	32.6	32.5	32.9	32.4	32.7	31.8
80°	24.8	24.5	24.1	24.8	24.1	24.5	24.8	24.8	24.3	24.8	24.3
82.5°	17.3	17.4	17.1	17.1	17.1	17.4	17.3	17.7	17.4	17.7	17.1
85°	8.0	7.7	7.4	7.4	7.4	7.7	8.0	8.0	8.5	8.2	8.2
87.5°	6.9	6.8	6.8	6.7	6.8	6.8	6.9	6.8	6.8	7.3	7.3
90°	27.1	27.3	27.5	27.6	27.5	27.3	27.1	26.9	27.1	27.4	27.7
92.5°	26.3	26.3	26.3	26.3	26.3	26.3	26.3	26.3	26.2	26.1	26.0
95°	51.5	51.2	50.8	50.5	50.8	51.2	51.5	51.9	52.1	52.1	52.1
97.5°	87.5	87.5	87.4	87.4	87.4	87.5	87.5	87.6	87.6	87.6	87.6
100°	112.0	111.9	111.6	111.5	111.6	111.9	112.0	112.2	112.3	112.3	112.3
102.5°	139.3	139.2	139.0	138.8	139.0	139.2	139.3	139.5	139.6	139.4	139.3
105°	180.6	180.6	180.6	180.6	180.6	180.6	180.6	180.6	180.4	180.1	179.7
107.5°	222.5	221.7	220.9	220.0	220.9	221.7	222.5	223.3	223.6	223.6	223.4
110°	252.3	251.7	251.1	250.6	251.1	251.7	252.3	252.7	253.1	253.1	253.1



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	281.1	280.7	280.3	279.9	280.3	280.7	281.1	281.4	281.9	282.3	282.7
115°	327.1	326.5	326.0	325.5	326.0	326.5	327.1	327.6	328.0	328.2	328.3
117.5°	370.6	370.0	369.4	368.9	369.4	370.0	370.6	371.0	371.5	372.0	372.4
120°	401.1	400.6	400.1	399.5	400.1	400.6	401.1	401.7	401.9	401.9	401.9
122.5°	430.6	430.2	429.8	429.4	429.8	430.2	430.6	431.0	431.5	431.9	432.3
125°	475.7	475.5	475.3	475.2	475.3	475.5	475.7	475.9	476.2	476.8	477.4
127.5°	518.5	518.0	517.4	516.8	517.4	518.0	518.5	519.1	519.8	520.4	521.1
130°	548.9	548.2	547.5	546.7	547.5	548.2	548.9	549.7	550.2	550.6	550.9
132.5°	577.2	576.6	576.0	575.4	576.0	576.6	577.2	577.7	578.4	579.2	580.0
135°	621.6	621.1	620.5	620.0	620.5	621.1	621.6	622.2	622.5	622.7	622.9
137.5°	662.5	661.8	661.0	660.3	661.0	661.8	662.5	663.2	663.7	663.8	664.0
140°	690.5	689.7	689.1	688.4	689.1	689.7	690.5	691.2	691.6	691.6	691.6
142.5°	715.9	715.2	714.4	713.7	714.4	715.2	715.9	716.6	716.9	716.7	716.6
145°	754.0	753.3	752.5	751.8	752.5	753.3	754.0	754.7	755.0	754.8	754.6
147.5°	787.9	787.2	786.5	785.8	786.5	787.2	787.9	788.6	788.7	788.3	787.9
150°	809.6	809.0	808.5	808.0	808.5	809.0	809.6	810.1	810.1	809.6	809.0
152.5°	830.8	830.1	829.5	828.8	829.5	830.1	830.8	831.5	831.5	830.8	830.1
155°	858.3	857.9	857.3	856.7	857.3	857.9	858.3	858.9	858.8	857.9	857.0
157.5°	883.5	882.6	881.7	880.8	881.7	882.6	883.5	884.3	884.1	882.9	881.7
160°	898.0	897.2	896.5	895.8	896.5	897.2	898.0	898.7	898.5	897.4	896.3
162.5°	911.4	910.5	909.7	908.8	909.7	910.5	911.4	912.3	912.1	910.9	909.6
165°	928.6	927.7	926.8	925.9	926.8	927.7	928.6	929.5	929.4	928.1	926.8
167.5°	942.7	941.8	940.9	939.9	940.9	941.8	942.7	943.6	943.5	942.2	940.9
170°	950.3	949.3	948.1	947.1	948.1	949.3	950.3	951.4	951.3	950.1	948.8
172.5°	956.2	955.1	954.0	952.9	954.0	955.1	956.2	957.2	957.2	955.9	954.6
175°	962.5	961.4	960.3	959.3	960.3	961.4	962.5	963.6	963.5	962.2	961.0
177.5°	964.8	963.9	963.0	962.2	963.0	963.9	964.8	965.6	965.6	964.8	963.9
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	463.1	464.7	467.2	469.9	471.6	474.7	475.6	477.0	478.3	481.4	484.7
5°	436.3	439.0	445.1	448.4	453.0	458.4	461.9	465.6	469.7	476.7	483.2
7.5°	407.6	412.0	419.6	425.8	432.4	440.1	445.6	453.0	459.1	469.0	478.5
10°	388.6	394.7	401.5	409.0	418.2	426.3	434.1	443.4	450.8	462.7	473.8
12.5°	371.4	372.3	382.1	390.3	402.9	413.0	422.0	433.9	441.2	455.3	466.9
15°	341.4	346.9	355.8	362.2	377.2	390.0	402.7	415.1	423.4	440.8	456.2
17.5°	316.0	321.1	330.3	340.9	351.6	364.4	380.7	393.8	405.1	425.0	443.2
20°	300.0	306.3	315.6	326.5	336.0	349.8	363.9	379.0	391.2	413.6	434.9
22.5°	286.4	291.4	298.9	309.7	319.9	332.6	348.1	364.4	377.2	401.5	423.0
25°	267.3	271.3	276.1	285.0	296.7	310.6	322.6	340.6	359.3	381.9	408.0
27.5°	250.0	252.9	257.1	265.0	274.0	287.0	300.4	317.4	336.2	360.8	388.3
30°	239.5	241.3	245.6	252.1	261.0	271.2	284.7	300.9	320.2	345.0	372.4
32.5°	230.3	232.0	234.8	240.9	248.7	257.4	269.5	285.8	304.2	328.6	359.0
35°	216.5	217.8	220.2	225.2	229.5	238.0	248.2	263.0	280.2	303.5	335.0
37.5°	202.8	204.6	206.0	208.1	213.6	219.2	228.0	240.6	257.5	281.0	311.0
40°	193.7	195.2	197.5	198.4	202.8	207.8	215.0	226.5	243.5	265.1	294.3
42.5°	184.5	186.1	187.4	188.4	192.2	196.7	203.2	213.0	228.1	249.0	278.0
45°	172.0	172.3	173.6	175.6	177.4	180.6	185.2	193.7	205.4	225.0	251.4
47.5°	159.4	159.6	159.8	160.7	162.7	165.6	168.7	175.6	186.1	201.7	227.3
50°	150.9	150.6	150.9	151.6	153.0	155.4	158.9	163.9	172.4	187.0	210.6
52.5°	142.8	142.8	142.5	142.8	143.8	145.4	148.0	152.2	159.8	173.3	194.0
55°	130.4	129.5	129.6	128.9	130.6	130.9	132.8	136.3	143.0	152.2	171.7
57.5°	117.2	116.4	115.6	115.4	115.2	116.2	117.6	120.4	125.6	133.7	149.4
60°	108.7	107.8	106.6	106.3	106.3	106.9	107.6	109.7	114.5	121.6	134.6
62.5°	100.1	99.1	98.4	97.4	97.1	97.7	98.4	99.9	103.4	110.1	121.3
65°	86.8	85.5	84.6	84.5	84.1	83.6	83.9	85.4	88.1	93.5	102.4
67.5°	73.5	72.3	72.2	71.0	70.5	70.6	70.5	71.7	73.5	78.1	84.7
70°	64.8	63.9	63.5	62.6	62.2	61.9	61.5	62.6	64.2	68.2	73.9
72.5°	55.9	55.1	54.4	53.6	53.6	53.2	53.2	53.9	55.2	58.8	63.3
75°	43.1	43.4	42.4	41.5	41.3	40.9	40.9	41.5	42.1	44.8	48.3
77.5°	31.3	31.1	30.4	30.1	29.9	29.5	29.9	30.2	30.6	32.4	35.0
80°	23.9	23.9	23.0	23.0	22.7	22.3	22.7	22.4	23.2	25.0	26.8
82.5°	17.0	16.8	16.7	16.5	16.4	16.0	16.2	16.6	17.0	18.2	19.3
85°	8.3	8.3	8.2	8.0	8.2	8.0	8.2	8.3	8.5	9.0	10.0
87.5°	7.4	7.6	7.0	6.4	5.5	4.9	4.4	4.2	4.0	3.7	3.4
90°	28.1	28.5	24.5	20.5	16.6	12.6	9.5	7.3	5.1	3.0	0.8
92.5°	25.9	25.8	24.9	24.0	23.1	22.1	20.9	19.2	17.7	16.1	14.5
95°	52.1	52.1	51.7	51.4	51.0	50.6	49.6	47.7	45.9	44.1	42.3
97.5°	87.6	87.6	86.8	86.2	85.5	84.8	83.6	82.1	80.5	78.9	77.3
100°	112.3	112.3	111.8	111.2	110.6	110.1	109.1	107.7	106.2	104.8	103.3
102.5°	139.1	139.0	138.3	137.6	136.9	136.2	135.3	134.1	133.0	131.8	130.7
105°	179.4	179.0	178.6	178.3	177.9	177.6	177.1	176.6	176.0	175.5	175.0
107.5°	223.2	223.1	223.1	223.1	223.1	223.1	222.7	221.9	221.1	220.3	219.5
110°	253.1	253.1	253.1	253.1	253.1	253.1	252.5	251.4	250.3	249.2	248.2



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.2	283.6	283.8	283.9	284.1	284.2	283.7	282.7	281.6	280.5	279.4
115°	328.6	328.7	329.1	329.5	329.8	330.1	329.8	328.7	327.6	326.5	325.5
117.5°	372.8	373.3	374.3	375.3	376.3	377.3	377.2	375.7	374.2	372.8	371.4
120°	401.9	401.9	403.4	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9
122.5°	432.8	433.2	434.2	435.2	436.2	437.2	436.8	435.1	433.4	431.6	429.9
125°	477.8	478.4	479.0	479.5	480.0	480.6	480.0	478.4	476.8	475.2	473.5
127.5°	521.7	522.4	523.0	523.7	524.3	525.0	524.2	522.2	520.2	518.0	516.0
130°	551.3	551.6	552.0	552.4	552.7	553.1	552.1	549.8	547.4	545.0	542.7
132.5°	580.8	581.6	581.5	581.5	581.4	581.3	580.3	578.4	576.5	574.5	572.7
135°	623.1	623.2	622.9	622.5	622.2	621.8	620.6	618.6	616.6	614.7	612.7
137.5°	664.1	664.2	663.8	663.3	662.8	662.3	661.3	659.7	658.0	656.4	654.8
140°	691.6	691.6	690.7	689.7	688.8	687.9	686.7	685.1	683.5	681.8	680.2
142.5°	716.5	716.3	715.7	715.1	714.4	713.9	712.7	711.1	709.5	707.8	706.2
145°	754.4	754.2	753.2	752.0	751.0	749.9	748.7	747.5	746.2	744.9	743.6
147.5°	787.5	787.1	786.4	785.6	785.0	784.2	783.1	781.5	780.1	778.5	777.0
150°	808.5	808.0	807.2	806.5	805.8	805.0	804.1	803.1	801.9	800.9	799.8
152.5°	829.5	828.8	827.9	827.0	826.1	825.3	824.3	823.2	822.1	821.1	819.9
155°	856.1	855.1	854.6	854.0	853.5	853.0	852.4	851.9	851.3	850.8	850.3
157.5°	880.4	879.2	878.9	878.6	878.2	877.9	877.6	877.2	876.9	876.4	876.1
160°	895.3	894.1	894.0	893.8	893.6	893.5	893.2	892.8	892.4	892.1	891.8
162.5°	908.4	907.2	907.0	906.9	906.7	906.4	906.4	906.3	906.2	906.1	906.0
165°	925.5	924.3	924.3	924.3	924.3	924.3	924.4	924.5	924.7	925.0	925.1
167.5°	939.7	938.4	938.5	938.5	938.6	938.6	938.9	939.4	940.0	940.5	941.0
170°	947.5	946.2	946.4	946.6	946.8	947.0	947.3	947.9	948.4	948.9	949.5
172.5°	953.4	952.1	952.3	952.4	952.7	952.8	953.2	953.7	954.3	954.8	955.4
175°	959.7	958.5	958.8	959.2	959.5	959.9	960.3	960.9	961.4	962.0	962.5
177.5°	963.0	962.2	962.5	962.8	963.0	963.4	963.7	964.2	964.6	965.0	965.5
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	484.5	485.2	487.5	489.9	492.6	493.3	494.5	493.5	493.2	495.9	498.1
5°	485.8	489.1	495.6	501.6	506.5	510.1	513.8	515.3	518.0	521.9	526.8
7.5°	484.2	490.7	500.9	509.6	518.9	525.7	531.0	535.6	541.0	548.4	556.4
10°	482.5	491.1	503.6	514.1	525.6	534.3	541.5	548.6	556.8	567.0	577.5
12.5°	479.2	489.5	505.1	517.6	532.3	540.9	550.6	565.7	574.5	588.7	603.6
15°	472.6	484.1	505.8	521.1	537.9	554.2	572.1	586.5	601.0	609.4	630.2
17.5°	462.9	479.7	503.8	521.7	542.9	568.5	588.7	605.1	621.7	635.3	645.8
20°	455.0	473.4	500.8	522.3	547.5	575.0	598.2	614.9	629.3	640.7	647.1
22.5°	445.2	468.2	494.9	520.1	552.2	579.5	603.8	616.9	629.0	634.5	637.1
25°	429.5	457.3	487.5	518.2	554.5	583.4	605.6	613.6	617.1	611.7	602.8
27.5°	412.6	443.6	478.9	514.7	553.1	580.9	596.8	595.6	589.6	572.2	558.3
30°	400.1	434.1	472.1	511.2	549.7	576.7	586.0	576.7	563.2	543.8	523.9
32.5°	386.9	422.2	464.8	506.1	543.5	567.3	569.2	553.3	532.4	510.3	485.6
35°	366.9	405.0	451.2	494.9	530.3	545.3	536.4	508.2	483.4	453.2	419.5
37.5°	344.3	386.5	432.7	478.4	510.5	514.4	492.3	462.7	427.6	392.2	352.5
40°	327.4	372.1	419.7	465.8	494.2	490.1	461.9	429.3	387.7	344.3	307.4
42.5°	312.3	356.9	405.4	450.7	473.4	462.2	429.3	389.3	344.5	303.7	269.9
45°	286.2	332.1	381.7	425.4	438.4	418.2	374.7	330.2	286.2	252.1	225.4
47.5°	260.7	306.1	355.3	393.7	398.3	371.1	323.6	277.9	239.9	212.2	193.4
50°	242.1	287.6	336.3	370.6	369.1	336.3	287.5	243.9	212.2	189.8	177.2
52.5°	225.3	268.4	315.1	346.3	338.4	302.7	256.0	217.4	191.4	173.8	162.4
55°	199.3	239.1	283.6	308.6	294.1	254.5	215.0	183.9	164.6	151.5	142.6
57.5°	173.4	210.8	248.8	264.2	248.3	211.7	178.8	156.2	141.7	132.0	126.2
60°	157.4	190.0	223.9	237.3	218.2	185.6	159.6	139.5	127.8	119.8	114.6
62.5°	141.5	170.6	202.6	209.9	192.4	164.9	141.9	125.1	115.5	108.4	103.5
65°	119.6	143.6	167.8	172.6	156.5	135.2	117.1	106.2	97.6	92.5	88.5
67.5°	98.2	117.3	134.5	138.4	124.3	109.5	96.4	86.8	81.1	76.8	73.5
70°	85.4	100.6	114.6	117.8	106.5	93.4	83.3	75.7	70.5	66.9	63.7
72.5°	71.9	84.5	96.3	98.4	89.2	79.1	70.9	64.9	60.3	58.0	55.0
75°	55.0	62.5	71.5	72.1	66.0	59.8	53.6	49.7	47.2	44.3	42.8
77.5°	38.8	44.6	49.8	50.8	47.2	43.0	39.5	36.4	34.4	33.0	31.6
80°	29.6	34.2	36.5	37.7	35.2	32.2	30.2	28.1	26.8	25.9	25.0
82.5°	21.2	24.1	26.1	27.1	25.7	23.9	21.9	20.7	19.7	19.0	18.7
85°	10.8	12.1	13.4	13.7	13.4	12.6	11.5	11.5	10.9	10.8	10.8
87.5°	4.3	5.3	5.8	6.6	6.9	7.7	8.6	9.2	9.9	9.6	9.4
90°	3.0	5.1	7.3	9.5	12.6	16.6	20.5	24.5	28.5	28.1	27.7
92.5°	16.1	17.7	19.2	20.9	22.1	23.1	24.0	24.9	25.8	25.9	26.0
95°	44.1	45.9	47.7	49.6	50.6	51.0	51.4	51.7	52.1	52.1	52.1
97.5°	78.9	80.5	82.1	83.6	84.8	85.5	86.2	86.8	87.6	87.6	87.6
100°	104.8	106.2	107.7	109.1	110.1	110.6	111.2	111.8	112.3	112.3	112.3
102.5°	131.8	133.0	134.1	135.3	136.2	136.9	137.6	138.3	139.0	139.1	139.3
105°	175.5	176.0	176.6	177.1	177.6	177.9	178.3	178.6	179.0	179.4	179.7
107.5°	220.3	221.1	221.9	222.7	223.1	223.1	223.1	223.1	223.1	223.2	223.4
110°	249.2	250.3	251.4	252.5	253.1	253.1	253.1	253.1	253.1	253.1	253.1



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	280.5	281.6	282.7	283.7	284.2	284.1	283.9	283.8	283.6	283.2	282.7
115°	326.5	327.6	328.7	329.8	330.1	329.8	329.5	329.1	328.7	328.6	328.3
117.5°	372.8	374.2	375.7	377.2	377.3	376.3	375.3	374.3	373.3	372.8	372.4
120°	403.4	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9	401.9	401.9
122.5°	431.6	433.4	435.1	436.8	437.2	436.2	435.2	434.2	433.2	432.8	432.3
125°	475.2	476.8	478.4	480.0	480.6	480.0	479.5	479.0	478.4	477.8	477.4
127.5°	518.0	520.2	522.2	524.2	525.0	524.3	523.7	523.0	522.4	521.7	521.1
130°	545.0	547.4	549.8	552.1	553.1	552.7	552.4	552.0	551.6	551.3	550.9
132.5°	574.5	576.5	578.4	580.3	581.3	581.4	581.5	581.5	581.6	580.8	580.0
135°	614.7	616.6	618.6	620.6	621.8	622.2	622.5	622.9	623.2	623.1	622.9
137.5°	656.4	658.0	659.7	661.3	662.3	662.8	663.3	663.8	664.2	664.1	664.0
140°	681.8	683.5	685.1	686.7	687.9	688.8	689.7	690.7	691.6	691.6	691.6
142.5°	707.8	709.5	711.1	712.7	713.9	714.4	715.1	715.7	716.3	716.5	716.6
145°	744.9	746.2	747.5	748.7	749.9	751.0	752.0	753.2	754.2	754.4	754.6
147.5°	778.5	780.1	781.5	783.1	784.2	785.0	785.6	786.4	787.1	787.5	787.9
150°	800.9	801.9	803.1	804.1	805.0	805.8	806.5	807.2	808.0	808.5	809.0
152.5°	821.1	822.1	823.2	824.3	825.3	826.1	827.0	827.9	828.8	829.5	830.1
155°	850.8	851.3	851.9	852.4	853.0	853.5	854.0	854.6	855.1	856.1	857.0
157.5°	876.4	876.9	877.2	877.6	877.9	878.2	878.6	878.9	879.2	880.4	881.7
160°	892.1	892.4	892.8	893.2	893.5	893.6	893.8	894.0	894.1	895.3	896.3
162.5°	906.1	906.2	906.3	906.4	906.4	906.7	906.9	907.0	907.2	908.4	909.6
165°	925.0	924.7	924.5	924.4	924.3	924.3	924.3	924.3	924.3	925.5	926.8
167.5°	940.5	940.0	939.4	938.9	938.6	938.6	938.5	938.5	938.4	939.7	940.9
170°	948.9	948.4	947.9	947.3	947.0	946.8	946.6	946.4	946.2	947.5	948.8
172.5°	954.8	954.3	953.7	953.2	952.8	952.7	952.4	952.3	952.1	953.4	954.6
175°	962.0	961.4	960.9	960.3	959.9	959.5	959.2	958.8	958.5	959.7	961.0
177.5°	965.0	964.6	964.2	963.7	963.4	963.0	962.8	962.5	962.2	963.0	963.9
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	499.9	501.9	501.9	502.2	504.6	504.3	504.1
5°	531.9	535.1	535.4	538.7	541.0	540.2	538.2
7.5°	562.1	568.0	572.5	574.9	577.9	579.7	578.9
10°	586.2	594.7	599.9	603.4	607.6	610.8	609.7
12.5°	608.0	618.1	625.3	631.3	631.8	635.9	633.1
15°	642.0	652.6	653.8	658.2	661.8	661.4	661.5
17.5°	653.1	656.6	657.3	657.4	657.5	656.2	653.3
20°	649.1	647.8	644.7	642.3	638.1	637.5	633.8
22.5°	630.1	626.1	618.2	612.9	606.3	604.6	603.6
25°	592.9	583.8	571.2	559.1	555.8	549.3	551.1
27.5°	541.6	527.5	513.8	504.1	495.2	485.5	488.3
30°	505.6	489.7	470.4	455.6	446.1	436.9	435.2
32.5°	462.7	439.3	417.8	404.8	390.3	384.4	378.1
35°	388.6	365.7	344.5	326.1	315.6	307.4	300.0
37.5°	322.0	295.7	278.5	263.7	256.0	251.4	252.6
40°	280.6	257.6	245.0	233.7	226.7	223.4	224.1
42.5°	247.1	229.9	219.6	211.8	206.8	205.0	204.6
45°	209.1	199.5	190.9	186.5	184.1	182.1	180.8
47.5°	183.2	175.3	170.5	167.9	165.8	163.7	163.6
50°	167.6	162.4	159.1	156.3	154.7	153.2	154.5
52.5°	155.7	151.0	147.7	145.2	144.6	143.2	143.2
55°	138.2	134.4	132.1	129.8	128.7	128.0	127.0
57.5°	122.1	118.6	116.4	115.0	112.9	112.2	111.9
60°	110.7	107.9	105.7	103.9	103.0	101.5	101.5
62.5°	100.2	97.4	95.4	94.0	92.5	91.9	92.0
65°	85.0	82.8	80.7	79.2	78.9	77.8	78.2
67.5°	71.0	69.5	67.3	66.5	65.9	65.3	64.8
70°	61.6	60.2	59.1	58.0	57.4	57.4	57.4
72.5°	53.8	52.0	51.4	50.0	50.3	49.7	49.1
75°	41.7	40.5	40.0	39.5	38.6	38.6	38.6
77.5°	30.7	30.3	29.7	29.1	28.9	28.7	28.8
80°	23.7	23.5	23.2	23.2	22.7	22.6	22.3
82.5°	18.3	17.8	17.5	17.4	17.3	17.3	17.2
85°	10.4	10.0	10.0	10.2	9.8	9.8	10.0
87.5°	9.5	9.4	9.2	9.3	9.5	9.4	9.4
90°	27.4	27.1	26.9	27.1	27.3	27.5	27.6
92.5°	26.1	26.2	26.3	26.3	26.3	26.3	26.3
95°	52.1	52.1	51.9	51.5	51.2	50.8	50.5
97.5°	87.6	87.6	87.6	87.5	87.5	87.4	87.4
100°	112.3	112.3	112.2	112.0	111.9	111.6	111.5
102.5°	139.4	139.6	139.5	139.3	139.2	139.0	138.8
105°	180.1	180.4	180.6	180.6	180.6	180.6	180.6
107.5°	223.6	223.6	223.3	222.5	221.7	220.9	220.0
110°	253.1	253.1	252.7	252.3	251.7	251.1	250.6



TEST NUMBER: P331268-930

CATALOG NUMBER: S122DIP-S290D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	282.3	281.9	281.4	281.1	280.7	280.3	279.9
115°	328.2	328.0	327.6	327.1	326.5	326.0	325.5
117.5°	372.0	371.5	371.0	370.6	370.0	369.4	368.9
120°	401.9	401.9	401.7	401.1	400.6	400.1	399.5
122.5°	431.9	431.5	431.0	430.6	430.2	429.8	429.4
125°	476.8	476.2	475.9	475.7	475.5	475.3	475.2
127.5°	520.4	519.8	519.1	518.5	518.0	517.4	516.8
130°	550.6	550.2	549.7	548.9	548.2	547.5	546.7
132.5°	579.2	578.4	577.7	577.2	576.6	576.0	575.4
135°	622.7	622.5	622.2	621.6	621.1	620.5	620.0
137.5°	663.8	663.7	663.2	662.5	661.8	661.0	660.3
140°	691.6	691.6	691.2	690.5	689.7	689.1	688.4
142.5°	716.7	716.9	716.6	715.9	715.2	714.4	713.7
145°	754.8	755.0	754.7	754.0	753.3	752.5	751.8
147.5°	788.3	788.7	788.6	787.9	787.2	786.5	785.8
150°	809.6	810.1	810.1	809.6	809.0	808.5	808.0
152.5°	830.8	831.5	831.5	830.8	830.1	829.5	828.8
155°	857.9	858.8	858.9	858.3	857.9	857.3	856.7
157.5°	882.9	884.1	884.3	883.5	882.6	881.7	880.8
160°	897.4	898.5	898.7	898.0	897.2	896.5	895.8
162.5°	910.9	912.1	912.3	911.4	910.5	909.7	908.8
165°	928.1	929.4	929.5	928.6	927.7	926.8	925.9
167.5°	942.2	943.5	943.6	942.7	941.8	940.9	939.9
170°	950.1	951.3	951.4	950.3	949.3	948.1	947.1
172.5°	955.9	957.2	957.2	956.2	955.1	954.0	952.9
175°	962.2	963.5	963.6	962.5	961.4	960.3	959.3
177.5°	964.8	965.6	965.6	964.8	963.9	963.0	962.2
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2

(END OF REPORT)