

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331314-930

Luminaire Tested: **S122DIP-S485D925U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331314-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S485D925U930-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4696.0 lumens  
Efficiency: N/A  
Efficacy: 105.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37				
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32				
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	35	34	33	27				
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24				
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	29	26	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	14				
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16	13				
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	18	16	14	12				
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12791	12791	12791	12791
5°	14340	12875	11408	12875
10°	16433	12770	9875	12770
15°	18180	12535	8724	12535
20°	17904	12283	7952	12283
25°	16142	11948	7464	11948
30°	13340	11415	7107	11415
35°	9723	10857	6853	10857
40°	7765	10197	6713	10197
45°	6786	9435	6521	9435
50°	6380	8696	6393	8696
55°	5880	7947	6221	7947
60°	5389	7149	5958	7149
65°	4909	6434	5700	6434
70°	4456	5736	5320	5736
75°	3949	4959	4710	4959
80°	3394	4110	3794	4110
85°	3057	3057	2242	3057



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.5	1.6
10°-20°	219.3	4.7
20°-30°	318.3	6.8
30°-40°	335.9	7.2
40°-50°	297.4	6.3
50°-60°	237.4	5.1
60°-70°	161.3	3.4
70°-80°	82.7	1.8
80°-90°	23.8	0.5
90°-100°	169.2	3.6
100°-110°	574.1	12.2
110°-120°	609.9	13.0
120°-130°	502.1	10.7
130°-140°	403.2	8.6
140°-150°	304.7	6.5
150°-160°	214.1	4.6
160°-170°	126.0	2.7
170°-180°	41.0	0.9
0°-30°	613.1	13.1
0°-40°	949.1	20.2
0°-60°	1483.9	31.6
0°-90°	1751.7	37.3
90°-120°	1353.2	28.8
90°-150°	2563.1	54.6
90°-180°	2944.0	62.7
0°-180°	4696.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	792	792	792	792	792	
5°	885	794	704	794	885	88
15°	1088	750	522	750	1088	300
25°	906	671	419	671	906	410
35°	493	551	348	551	493	321
45°	297	413	286	413	297	234
55°	209	282	221	282	209	187
65°	128	168	149	168	128	128
75°	63	80	76	80	63	68
85°	16	16	12	16	16	19
90°	27	1	27	1	27	15
95°	93	28	93	28	93	121
105°	917	99	917	99	917	887
115°	1207	175	1207	175	1207	1182
125°	979	244	979	244	979	885
135°	811	286	811	286	811	630
145°	648	327	648	327	648	411
155°	544	372	544	372	544	254
165°	478	405	478	405	478	137
175°	430	422	430	422	430	42
180°	423	423	423	423	423	



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	828.8	829.1	829.5	825.7	825.2	825.2	821.7	818.8	815.4	810.7	811.2
5°	884.8	888.2	889.4	885.7	880.3	879.6	874.5	865.9	858.0	851.7	847.1
7.5°	951.7	953.0	950.1	945.3	941.2	933.8	924.2	914.8	901.6	889.4	880.4
10°	1002.3	1004.2	999.0	992.0	986.2	977.7	963.7	949.3	932.1	915.3	901.9
12.5°	1040.8	1045.4	1038.7	1037.8	1027.8	1016.2	999.5	992.2	967.8	944.5	930.1
15°	1087.6	1087.3	1087.9	1082.1	1074.8	1073.0	1055.3	1036.2	1001.8	988.1	964.3
17.5°	1074.1	1078.7	1080.8	1080.8	1080.6	1079.5	1073.7	1061.7	1044.4	1022.2	994.8
20°	1042.0	1048.0	1049.0	1056.0	1059.9	1065.1	1067.2	1063.9	1053.2	1034.6	1010.9
22.5°	992.2	993.9	996.8	1007.7	1016.3	1029.2	1036.0	1047.3	1043.2	1034.1	1014.3
25°	906.1	903.1	913.7	919.2	939.0	959.7	974.6	991.1	1005.7	1014.6	1008.8
27.5°	802.7	798.2	814.2	828.7	844.7	867.2	890.4	917.9	940.7	969.3	979.1
30°	715.5	718.3	733.5	749.0	773.4	805.0	831.2	861.4	894.0	925.9	948.1
32.5°	621.5	632.0	641.6	665.4	686.9	722.2	760.6	798.3	838.9	875.2	909.6
35°	493.3	505.4	518.9	536.2	566.3	601.4	638.8	689.7	745.1	794.7	835.5
37.5°	415.2	413.3	420.9	433.5	457.9	486.2	529.2	579.5	644.7	703.0	760.6
40°	368.4	367.2	372.7	384.3	402.8	423.5	461.3	505.4	566.1	637.2	705.8
42.5°	336.2	337.0	340.1	348.2	360.9	378.0	406.3	443.8	499.3	566.4	640.0
45°	297.2	299.3	302.6	306.6	313.9	327.9	343.7	370.6	414.4	470.4	542.9
47.5°	269.0	269.1	272.5	276.0	280.3	288.2	301.2	318.0	348.9	394.5	456.8
50°	254.0	251.8	254.2	257.0	261.5	267.0	275.6	291.4	312.1	348.9	401.0
52.5°	235.5	235.5	237.7	238.7	242.8	248.3	256.1	267.0	285.8	314.6	357.4
55°	208.9	210.4	211.7	213.4	217.1	221.0	227.1	234.5	249.1	270.7	302.3
57.5°	183.9	184.4	185.6	189.1	191.4	195.0	200.8	207.5	217.0	233.0	256.8
60°	166.9	166.9	169.3	170.8	173.8	177.5	182.1	188.5	197.0	210.1	229.3
62.5°	151.2	151.0	152.0	154.5	156.8	160.2	164.8	170.2	178.2	189.9	205.6
65°	128.5	127.9	129.7	130.3	132.7	136.1	139.7	145.5	152.0	160.5	174.5
67.5°	106.6	107.3	108.3	109.4	110.8	114.3	116.8	120.8	126.2	133.3	142.8
70°	94.4	94.4	94.4	95.3	97.1	99.0	101.4	104.8	109.9	116.0	124.5
72.5°	80.7	81.7	82.7	82.2	84.5	85.5	88.5	90.3	95.3	99.2	106.7
75°	63.3	63.3	63.3	64.8	65.8	66.7	68.5	70.4	72.8	77.6	81.6
77.5°	47.3	47.1	47.5	47.8	48.8	49.9	50.4	52.1	54.3	56.6	59.9
80°	36.5	37.2	37.4	38.1	38.1	38.6	39.0	41.1	42.6	44.2	46.3
82.5°	28.3	28.4	28.5	28.5	28.8	29.2	29.9	30.7	31.1	32.4	34.1
85°	16.5	16.1	16.1	16.7	16.5	16.5	17.0	17.7	17.7	17.9	18.9
87.5°	11.7	11.7	12.0	11.7	11.7	11.8	11.5	11.6	12.0	12.4	12.5
90°	26.8	26.8	26.8	26.8	26.8	26.0	24.4	26.0	26.8	27.6	26.8
92.5°	45.1	46.4	45.7	48.3	49.0	54.1	60.9	70.9	89.4	105.7	104.3
95°	92.8	92.0	94.4	100.9	111.5	129.4	163.5	213.2	279.1	318.9	282.3
97.5°	182.6	189.4	201.3	221.4	260.2	318.9	407.0	497.5	571.2	544.5	410.1
100°	291.3	306.0	329.5	364.5	432.1	530.5	642.0	742.9	760.0	642.8	442.6
102.5°	512.7	532.5	561.9	621.7	695.0	799.4	880.9	903.7	830.3	646.0	430.3
105°	917.0	928.4	963.4	1013.8	1064.3	1091.2	1080.6	988.6	819.4	602.9	406.0
107.5°	1171.4	1186.5	1193.5	1196.3	1189.9	1150.6	1065.9	927.5	748.0	556.8	394.0
110°	1248.2	1249.0	1241.7	1226.2	1191.2	1124.5	1020.3	874.7	703.0	534.6	391.4



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1246.9	1242.5	1228.7	1202.8	1154.1	1077.7	966.4	826.6	671.8	520.2	392.0
115°	1206.7	1199.4	1178.2	1140.8	1083.0	999.2	892.6	767.3	633.1	504.5	395.4
117.5°	1134.9	1128.8	1106.4	1066.9	1008.0	929.4	832.7	722.7	608.6	496.8	401.3
120°	1088.8	1080.6	1057.0	1018.7	961.8	887.7	801.5	700.6	595.7	492.3	405.2
122.5°	1040.6	1033.7	1012.7	975.1	924.1	857.1	775.4	683.0	584.6	489.7	409.8
125°	978.8	972.3	952.0	921.1	873.9	812.9	741.3	657.5	568.8	484.9	416.6
127.5°	924.9	919.7	902.0	873.1	831.9	775.6	708.1	632.3	554.2	482.2	423.6
130°	894.2	887.7	871.5	843.8	804.0	750.2	685.9	616.0	544.4	480.9	428.8
132.5°	862.3	856.5	841.6	813.8	774.6	724.1	665.1	600.3	536.5	480.2	434.0
135°	811.2	808.0	793.4	766.5	731.5	685.9	632.3	578.5	525.6	479.2	440.2
137.5°	761.2	756.3	743.4	720.3	688.4	648.7	606.0	561.1	518.0	479.1	445.7
140°	726.6	721.8	709.6	688.4	662.3	626.6	589.1	550.1	513.5	478.4	448.3
142.5°	692.1	691.1	680.3	661.0	636.3	606.3	574.1	541.0	508.9	478.4	450.3
145°	647.7	645.2	637.2	623.3	603.7	580.2	555.0	528.1	502.9	476.8	452.4
147.5°	610.4	608.9	603.4	592.4	576.3	559.0	539.3	518.1	496.7	473.9	453.1
150°	588.3	587.5	582.6	572.8	560.6	546.0	528.9	511.0	491.5	472.0	452.4
152.5°	569.4	569.2	565.7	557.2	547.6	534.9	520.4	503.9	486.9	468.7	451.1
155°	544.4	546.0	542.7	537.0	528.1	519.1	507.0	493.9	478.4	463.0	449.1
157.5°	523.0	523.0	521.5	516.8	510.5	503.5	493.3	482.3	470.5	457.1	445.4
160°	509.4	509.4	508.6	504.5	498.8	493.1	484.1	475.2	464.6	453.2	443.4
162.5°	496.4	497.0	496.2	493.4	487.7	483.3	475.6	468.1	459.4	450.0	441.5
165°	477.6	478.4	478.4	475.2	472.0	468.7	463.0	457.3	450.8	443.4	437.7
167.5°	460.4	461.4	461.5	459.7	458.3	455.3	451.4	447.0	442.3	437.7	434.0
170°	450.0	451.6	452.4	450.0	449.1	447.5	444.3	441.8	437.7	434.5	432.1
172.5°	441.5	442.5	443.3	442.1	441.3	440.3	437.7	435.9	433.3	430.6	429.5
175°	430.5	432.1	432.9	432.1	432.1	431.3	430.5	429.7	427.2	426.4	425.6
177.5°	423.8	425.1	425.7	425.7	425.7	425.7	425.1	425.1	423.8	423.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	812.9	811.0	809.8	805.4	801.5	797.6	796.4	796.9	791.5	786.4	784.2
5°	844.7	838.5	832.7	824.5	814.8	804.1	798.7	794.4	783.7	772.2	765.5
7.5°	873.0	864.3	853.1	837.7	823.5	806.7	796.1	786.7	771.0	754.7	744.8
10°	890.3	878.4	864.1	845.2	827.9	807.5	793.2	778.9	760.6	741.1	729.0
12.5°	905.1	889.2	875.1	850.8	830.3	804.8	787.8	767.7	748.4	725.3	713.3
15°	940.5	911.0	884.2	856.8	831.5	795.9	777.1	749.9	724.6	696.0	682.3
17.5°	967.8	934.7	892.5	857.7	828.2	788.7	761.0	728.6	698.6	665.9	647.3
20°	983.5	945.4	900.0	858.7	823.3	778.3	748.1	714.9	679.9	643.0	623.0
22.5°	992.7	952.8	907.8	855.0	813.6	769.7	731.8	695.5	659.9	620.2	599.1
25°	995.6	959.1	911.6	851.9	801.4	751.8	706.0	670.7	627.9	590.7	559.9
27.5°	981.1	955.0	909.3	846.2	787.3	729.3	678.4	638.4	593.0	552.8	521.8
30°	963.4	948.1	903.7	840.3	776.1	713.7	657.7	612.3	567.3	526.4	494.8
32.5°	935.9	932.5	893.5	832.1	764.2	694.0	636.0	590.1	540.2	500.1	469.9
35°	881.7	896.4	871.7	813.6	741.7	665.9	603.2	550.8	499.0	460.6	432.4
37.5°	809.3	845.6	839.2	786.4	711.3	635.4	566.1	511.4	462.0	423.3	395.5
40°	759.4	805.7	812.4	765.7	690.0	611.7	538.3	483.8	435.7	400.4	372.3
42.5°	705.8	759.9	778.3	740.9	666.6	586.9	513.5	457.1	409.4	375.0	350.3
45°	616.0	687.5	720.7	699.4	627.5	545.9	470.4	413.2	370.0	337.7	318.5
47.5°	532.0	610.2	654.8	647.3	584.1	503.3	428.7	373.7	331.7	305.9	288.7
50°	472.5	552.9	606.8	609.3	552.9	472.9	397.9	346.2	307.5	283.5	269.5
52.5°	420.9	497.7	556.4	569.3	518.1	441.2	370.4	318.9	284.9	262.8	250.2
55°	353.5	418.3	483.6	507.3	466.2	393.1	327.6	282.3	250.3	235.1	224.1
57.5°	293.9	348.0	408.1	434.4	409.0	346.5	285.1	245.7	219.8	206.4	198.0
60°	262.4	305.1	358.7	390.0	368.1	312.4	258.8	221.4	200.1	188.2	180.3
62.5°	233.3	271.0	316.3	345.0	333.0	280.5	232.5	199.4	181.1	169.9	164.2
65°	192.4	222.3	257.3	283.8	275.9	235.9	196.7	168.4	153.8	145.0	140.4
67.5°	158.4	180.0	204.3	227.5	221.1	192.8	161.3	139.3	128.3	120.7	118.1
70°	137.1	153.4	175.0	193.6	188.5	165.3	140.4	121.5	112.0	105.7	102.9
72.5°	116.6	130.0	146.6	161.8	158.2	139.0	118.2	104.0	96.7	90.8	88.5
75°	88.0	98.3	108.4	118.5	117.6	102.6	90.4	79.5	73.7	69.1	68.2
77.5°	65.0	70.8	77.6	83.6	81.9	73.4	63.8	57.6	53.3	50.2	49.7
80°	49.7	53.0	57.9	62.1	60.0	56.3	48.8	44.2	41.1	38.1	36.9
82.5°	36.0	39.4	42.2	44.6	43.0	39.5	34.8	31.7	29.9	27.8	27.3
85°	18.9	20.7	21.9	22.5	21.9	19.8	17.7	16.5	14.9	14.0	13.7
87.5°	11.7	10.6	9.8	9.8	8.7	8.4	6.8	5.5	5.8	6.2	6.0
90°	21.9	16.3	12.2	9.8	8.2	6.5	3.3	0.8	3.3	6.5	8.2
92.5°	81.2	55.4	36.9	29.3	23.7	20.2	14.3	9.9	14.3	20.2	23.7
95°	187.9	117.2	79.7	60.3	47.2	39.9	31.7	28.5	31.7	39.9	47.2
97.5°	253.2	154.6	107.5	85.4	70.4	59.4	50.8	46.4	50.8	59.4	70.4
100°	266.9	167.6	124.5	101.7	85.4	72.4	65.1	62.6	65.1	72.4	85.4
102.5°	267.6	179.4	139.5	116.7	99.8	86.7	79.4	77.6	79.4	86.7	99.8
105°	271.7	199.3	161.1	138.4	120.4	108.2	102.6	99.3	102.6	108.2	120.4
107.5°	283.0	219.9	182.8	159.8	142.1	130.9	125.3	122.7	125.3	130.9	142.1
110°	292.1	233.5	197.7	174.1	157.0	146.4	141.6	138.4	141.6	146.4	157.0





TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	301.9	246.5	212.1	187.8	171.4	161.4	155.9	152.6	155.9	161.4	171.4
115°	316.5	266.9	231.9	209.9	193.6	183.9	179.0	175.0	179.0	183.9	193.6
117.5°	332.2	285.6	253.2	230.4	214.8	206.2	201.3	198.0	201.3	206.2	214.8
120°	342.6	298.6	266.9	244.1	227.8	220.5	215.6	212.4	215.6	220.5	227.8
122.5°	351.6	311.0	281.2	257.8	241.5	233.5	228.6	226.1	228.6	233.5	241.5
125°	366.2	329.5	300.3	277.4	261.2	251.4	246.5	244.1	246.5	251.4	261.2
127.5°	379.7	346.8	318.3	294.9	279.2	268.5	261.7	258.4	261.7	268.5	279.2
130°	388.2	357.2	328.7	306.0	289.7	278.3	270.1	266.9	270.1	278.3	289.7
132.5°	396.6	366.3	339.2	316.3	299.5	287.4	278.6	274.7	278.6	287.4	299.5
135°	407.6	379.2	353.1	330.4	311.6	299.5	289.7	286.4	289.7	299.5	311.6
137.5°	416.1	389.6	363.9	342.8	324.2	311.1	301.4	297.5	301.4	311.1	324.2
140°	420.7	395.4	371.0	349.9	332.0	318.9	309.2	306.0	309.2	318.9	332.0
142.5°	424.6	400.0	376.3	356.4	339.2	326.1	317.0	314.4	317.0	326.1	339.2
145°	429.7	406.8	384.9	367.0	350.7	338.5	330.4	327.1	330.4	338.5	350.7
147.5°	432.4	412.4	391.8	375.8	362.2	351.0	343.2	340.8	343.2	351.0	362.2
150°	433.7	415.0	396.2	381.6	369.4	358.8	352.3	349.9	352.3	358.8	369.4
152.5°	434.3	417.6	400.8	387.5	375.9	366.6	360.1	359.0	360.1	366.6	375.9
155°	435.3	421.5	407.6	395.4	386.5	377.6	372.7	371.9	372.7	377.6	386.5
157.5°	435.3	424.3	412.5	402.3	395.1	387.3	383.4	382.6	383.4	387.3	395.1
160°	435.3	425.6	415.8	406.8	400.3	393.8	390.6	389.8	390.6	393.8	400.3
162.5°	434.6	426.2	417.8	410.7	404.9	399.7	396.4	396.9	396.4	399.7	404.9
165°	432.9	427.2	419.9	415.0	410.9	406.0	404.4	405.2	404.4	406.0	410.9
167.5°	431.8	427.1	421.7	418.6	415.6	412.5	411.1	412.1	411.1	412.5	415.6
170°	430.5	426.4	422.3	419.9	418.2	415.8	415.0	416.6	415.0	415.8	418.2
172.5°	428.5	425.7	423.0	421.2	420.2	417.8	418.2	419.2	418.2	417.8	420.2
175°	426.4	424.8	423.1	422.3	422.3	420.7	421.5	422.3	421.5	420.7	422.3
177.5°	425.1	423.8	423.1	423.1	423.1	421.8	422.5	423.8	422.5	421.8	423.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	781.8	780.3	775.2	772.5	768.2	764.0	761.3	762.5	763.5	763.0	762.3
5°	759.4	753.6	744.8	737.1	731.6	721.6	717.4	715.3	713.4	711.3	709.1
7.5°	732.7	723.6	710.9	700.1	689.8	677.4	670.3	665.9	661.5	656.7	652.5
10°	713.7	700.9	687.5	672.3	660.1	648.8	638.8	632.1	626.0	620.2	616.0
12.5°	693.7	679.0	662.4	641.6	628.2	612.0	610.6	598.8	589.2	585.6	580.7
15°	661.9	641.2	620.2	595.6	584.9	570.3	561.2	552.0	543.8	538.0	536.5
17.5°	625.8	599.0	578.1	560.4	543.0	528.0	519.6	512.3	505.5	497.7	496.8
20°	598.3	575.2	552.4	536.8	518.9	503.6	493.3	485.9	480.1	475.6	471.7
22.5°	572.3	546.9	526.0	509.0	491.3	479.0	470.8	463.8	459.0	454.0	450.2
25°	530.4	510.6	487.8	468.6	454.0	446.1	439.4	433.3	430.2	426.9	422.7
27.5°	493.8	471.8	450.5	435.6	422.7	415.7	411.0	406.8	404.0	402.0	399.6
30°	468.0	445.7	429.0	414.4	403.7	396.7	393.7	391.3	387.9	386.7	385.5
32.5°	443.1	423.1	408.8	396.2	386.0	381.4	378.6	376.4	373.8	372.6	370.1
35°	408.0	391.3	377.2	370.2	362.0	358.1	356.0	352.9	350.5	349.3	348.9
37.5°	375.0	360.4	351.1	342.2	338.7	336.2	333.4	331.3	330.5	330.4	330.0
40°	353.5	341.6	333.4	326.1	324.6	320.9	318.5	316.7	316.7	317.0	316.7
42.5°	334.0	323.3	316.1	309.8	308.0	305.8	303.4	303.3	303.8	304.8	303.8
45°	304.5	296.9	291.7	288.6	285.3	283.2	282.8	283.8	284.1	284.4	285.3
47.5°	277.3	272.2	267.6	264.2	262.8	262.4	262.0	263.6	265.1	265.6	267.0
50°	261.2	255.4	251.5	249.4	248.2	247.5	248.2	250.0	251.2	252.7	253.6
52.5°	243.2	239.1	236.4	234.7	234.2	234.6	234.7	236.8	238.8	239.3	239.8
55°	218.3	215.2	214.7	211.9	213.1	212.8	214.3	215.6	217.4	219.2	219.6
57.5°	193.5	191.0	189.4	189.6	190.0	191.4	192.6	194.8	196.7	198.6	198.9
60°	176.9	175.7	174.8	174.8	175.4	177.2	178.7	180.8	182.1	183.3	184.2
62.5°	161.8	160.6	159.6	160.1	161.8	162.8	164.6	165.8	167.0	168.2	168.6
65°	137.9	137.3	138.3	138.8	139.2	140.6	142.8	143.7	145.0	145.5	147.7
67.5°	115.9	116.1	115.9	116.8	118.5	119.0	120.9	123.1	123.4	124.5	125.9
70°	101.1	101.7	102.3	102.9	104.4	105.0	106.6	107.5	108.7	109.6	110.6
72.5°	87.5	87.6	88.2	88.1	89.4	90.7	92.0	92.9	94.1	95.2	96.1
75°	67.3	67.3	67.9	68.2	69.7	71.3	70.9	71.6	72.8	74.0	74.6
77.5°	49.2	48.5	49.2	49.4	49.9	51.2	51.4	52.3	53.7	53.3	54.0
80°	37.4	36.5	37.4	37.7	37.7	39.3	39.3	39.9	40.8	39.9	40.8
82.5°	26.7	26.3	27.0	27.1	27.6	27.6	28.0	28.2	29.1	28.7	29.1
85°	13.4	13.1	13.4	13.1	13.4	13.7	13.7	13.4	13.4	14.0	13.1
87.5°	6.1	6.4	6.9	8.1	8.8	8.7	8.3	8.2	7.8	7.7	7.8
90°	9.8	12.2	16.3	21.9	26.8	27.6	26.8	26.0	24.4	26.0	26.8
92.5°	29.3	36.9	55.4	81.2	104.3	105.7	89.4	70.9	60.9	54.1	49.0
95°	60.3	79.7	117.2	187.9	282.3	318.9	279.1	213.2	163.5	129.4	111.5
97.5°	85.4	107.5	154.6	253.2	410.1	544.5	571.2	497.5	407.0	318.9	260.2
100°	101.7	124.5	167.6	266.9	442.6	642.8	760.0	742.9	642.0	530.5	432.1
102.5°	116.7	139.5	179.4	267.6	430.3	646.0	830.3	903.7	880.9	799.4	695.0
105°	138.4	161.1	199.3	271.7	406.0	602.9	819.4	988.6	1080.6	1091.2	1064.3
107.5°	159.8	182.8	219.9	283.0	394.0	556.8	748.0	927.5	1065.9	1150.6	1189.9
110°	174.1	197.7	233.5	292.1	391.4	534.6	703.0	874.7	1020.3	1124.5	1191.2



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	187.8	212.1	246.5	301.9	392.0	520.2	671.8	826.6	966.4	1077.7	1154.1
115°	209.9	231.9	266.9	316.5	395.4	504.5	633.1	767.3	892.6	999.2	1083.0
117.5°	230.4	253.2	285.6	332.2	401.3	496.8	608.6	722.7	832.7	929.4	1008.0
120°	244.1	266.9	298.6	342.6	405.2	492.3	595.7	700.6	801.5	887.7	961.8
122.5°	257.8	281.2	311.0	351.6	409.8	489.7	584.6	683.0	775.4	857.1	924.1
125°	277.4	300.3	329.5	366.2	416.6	484.9	568.8	657.5	741.3	812.9	873.9
127.5°	294.9	318.3	346.8	379.7	423.6	482.2	554.2	632.3	708.1	775.6	831.9
130°	306.0	328.7	357.2	388.2	428.8	480.9	544.4	616.0	685.9	750.2	804.0
132.5°	316.3	339.2	366.3	396.6	434.0	480.2	536.5	600.3	665.1	724.1	774.6
135°	330.4	353.1	379.2	407.6	440.2	479.2	525.6	578.5	632.3	685.9	731.5
137.5°	342.8	363.9	389.6	416.1	445.7	479.1	518.0	561.1	606.0	648.7	688.4
140°	349.9	371.0	395.4	420.7	448.3	478.4	513.5	550.1	589.1	626.6	662.3
142.5°	356.4	376.3	400.0	424.6	450.3	478.4	508.9	541.0	574.1	606.3	636.3
145°	367.0	384.9	406.8	429.7	452.4	476.8	502.9	528.1	555.0	580.2	603.7
147.5°	375.8	391.8	412.4	432.4	453.1	473.9	496.7	518.1	539.3	559.0	576.3
150°	381.6	396.2	415.0	433.7	452.4	472.0	491.5	511.0	528.9	546.0	560.6
152.5°	387.5	400.8	417.6	434.3	451.1	468.7	486.9	503.9	520.4	534.9	547.6
155°	395.4	407.6	421.5	435.3	449.1	463.0	478.4	493.9	507.0	519.1	528.1
157.5°	402.3	412.5	424.3	435.3	445.4	457.1	470.5	482.3	493.3	503.5	510.5
160°	406.8	415.8	425.6	435.3	443.4	453.2	464.6	475.2	484.1	493.1	498.8
162.5°	410.7	417.8	426.2	434.6	441.5	450.0	459.4	468.1	475.6	483.3	487.7
165°	415.0	419.9	427.2	432.9	437.7	443.4	450.8	457.3	463.0	468.7	472.0
167.5°	418.6	421.7	427.1	431.8	434.0	437.7	442.3	447.0	451.4	455.3	458.3
170°	419.9	422.3	426.4	430.5	432.1	434.5	437.7	441.8	444.3	447.5	449.1
172.5°	421.2	423.0	425.7	428.5	429.5	430.6	433.3	435.9	437.7	440.3	441.3
175°	422.3	423.1	424.8	426.4	425.6	426.4	427.2	429.7	430.5	431.3	432.1
177.5°	423.1	423.1	423.8	425.1	423.8	423.1	423.8	425.1	425.1	425.7	425.7
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	759.9	759.4	759.4	757.2	759.4	759.4	759.9	762.3	763.0	763.5	762.5
5°	704.9	703.9	702.5	703.9	702.5	703.9	704.9	709.1	711.3	713.4	715.3
7.5°	650.5	646.9	646.3	642.7	646.3	646.9	650.5	652.5	656.7	661.5	665.9
10°	610.8	608.4	608.1	602.3	608.1	608.4	610.8	616.0	620.2	626.0	632.1
12.5°	580.6	574.7	575.9	572.6	575.9	574.7	580.6	580.7	585.6	589.2	598.8
15°	528.2	528.2	527.1	521.9	527.1	528.2	528.2	536.5	538.0	543.8	552.0
17.5°	490.7	490.1	487.1	488.6	487.1	490.1	490.7	496.8	497.7	505.5	512.3
20°	468.3	466.4	462.8	462.8	462.8	466.4	468.3	471.7	475.6	480.1	485.9
22.5°	447.1	446.9	443.1	444.3	443.1	446.9	447.1	450.2	454.0	459.0	463.8
25°	422.3	419.9	418.1	419.0	418.1	419.9	422.3	422.7	426.9	430.2	433.3
27.5°	398.8	397.5	397.4	394.8	397.4	397.5	398.8	399.6	402.0	404.0	406.8
30°	385.1	382.1	382.7	381.2	382.7	382.1	385.1	385.5	386.7	387.9	391.3
32.5°	369.6	368.5	367.9	366.6	367.9	368.5	369.6	370.1	372.6	373.8	376.4
35°	348.3	348.6	347.1	347.7	347.1	348.6	348.3	348.9	349.3	350.5	352.9
37.5°	329.8	330.8	330.0	330.2	330.0	330.8	329.8	330.0	330.4	330.5	331.3
40°	317.6	317.6	317.6	318.5	317.6	317.6	317.6	316.7	317.0	316.7	316.7
42.5°	305.9	305.4	304.9	304.8	304.9	305.4	305.9	303.8	304.8	303.8	303.3
45°	285.9	286.8	287.1	285.6	287.1	286.8	285.9	285.3	284.4	284.1	283.8
47.5°	267.8	267.9	267.8	269.1	267.8	267.9	267.8	267.0	265.6	265.1	263.6
50°	255.2	254.5	255.2	254.5	255.2	254.5	255.2	253.6	252.7	251.2	250.0
52.5°	241.7	241.9	241.5	241.4	241.5	241.9	241.7	239.8	239.3	238.8	236.8
55°	220.8	221.4	221.0	221.0	221.0	221.4	220.8	219.6	219.2	217.4	215.6
57.5°	199.0	199.6	200.0	198.6	200.0	199.6	199.0	198.9	198.6	196.7	194.8
60°	183.9	185.4	185.2	184.5	185.2	185.4	183.9	184.2	183.3	182.1	180.8
62.5°	170.0	170.6	170.5	170.4	170.5	170.6	170.0	168.6	168.2	167.0	165.8
65°	148.5	149.2	148.3	149.2	148.3	149.2	148.5	147.7	145.5	145.0	143.7
67.5°	125.5	125.7	126.4	126.8	126.4	125.7	125.5	125.9	124.5	123.4	123.1
70°	111.1	110.8	111.8	112.7	111.8	110.8	111.1	110.6	109.6	108.7	107.5
72.5°	96.0	96.7	96.4	97.1	96.4	96.7	96.0	96.1	95.2	94.1	92.9
75°	74.0	74.9	74.6	75.5	74.6	74.9	74.0	74.6	74.0	72.8	71.6
77.5°	53.5	53.6	53.5	54.0	53.5	53.6	53.5	54.0	53.3	53.7	52.3
80°	40.8	40.2	39.5	40.8	39.5	40.2	40.8	40.8	39.9	40.8	39.9
82.5°	28.4	28.8	28.1	28.1	28.1	28.8	28.4	29.1	28.7	29.1	28.2
85°	13.1	12.8	12.1	12.1	12.1	12.8	13.1	13.1	14.0	13.4	13.4
87.5°	7.8	7.6	7.6	7.3	7.6	7.6	7.8	7.8	7.7	7.8	8.2
90°	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.0	24.4	26.0
92.5°	48.3	45.7	46.4	45.1	46.4	45.7	48.3	49.0	54.1	60.9	70.9
95°	100.9	94.4	92.0	92.8	92.0	94.4	100.9	111.5	129.4	163.5	213.2
97.5°	221.4	201.3	189.4	182.6	189.4	201.3	221.4	260.2	318.9	407.0	497.5
100°	364.5	329.5	306.0	291.3	306.0	329.5	364.5	432.1	530.5	642.0	742.9
102.5°	621.7	561.9	532.5	512.7	532.5	561.9	621.7	695.0	799.4	880.9	903.7
105°	1013.8	963.4	928.4	917.0	928.4	963.4	1013.8	1064.3	1091.2	1080.6	988.6
107.5°	1196.3	1193.5	1186.5	1171.4	1186.5	1193.5	1196.3	1189.9	1150.6	1065.9	927.5
110°	1226.2	1241.7	1249.0	1248.2	1249.0	1241.7	1226.2	1191.2	1124.5	1020.3	874.7



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1202.8	1228.7	1242.5	1246.9	1242.5	1228.7	1202.8	1154.1	1077.7	966.4	826.6
115°	1140.8	1178.2	1199.4	1206.7	1199.4	1178.2	1140.8	1083.0	999.2	892.6	767.3
117.5°	1066.9	1106.4	1128.8	1134.9	1128.8	1106.4	1066.9	1008.0	929.4	832.7	722.7
120°	1018.7	1057.0	1080.6	1088.8	1080.6	1057.0	1018.7	961.8	887.7	801.5	700.6
122.5°	975.1	1012.7	1033.7	1040.6	1033.7	1012.7	975.1	924.1	857.1	775.4	683.0
125°	921.1	952.0	972.3	978.8	972.3	952.0	921.1	873.9	812.9	741.3	657.5
127.5°	873.1	902.0	919.7	924.9	919.7	902.0	873.1	831.9	775.6	708.1	632.3
130°	843.8	871.5	887.7	894.2	887.7	871.5	843.8	804.0	750.2	685.9	616.0
132.5°	813.8	841.6	856.5	862.3	856.5	841.6	813.8	774.6	724.1	665.1	600.3
135°	766.5	793.4	808.0	811.2	808.0	793.4	766.5	731.5	685.9	632.3	578.5
137.5°	720.3	743.4	756.3	761.2	756.3	743.4	720.3	688.4	648.7	606.0	561.1
140°	688.4	709.6	721.8	726.6	721.8	709.6	688.4	662.3	626.6	589.1	550.1
142.5°	661.0	680.3	691.1	692.1	691.1	680.3	661.0	636.3	606.3	574.1	541.0
145°	623.3	637.2	645.2	647.7	645.2	637.2	623.3	603.7	580.2	555.0	528.1
147.5°	592.4	603.4	608.9	610.4	608.9	603.4	592.4	576.3	559.0	539.3	518.1
150°	572.8	582.6	587.5	588.3	587.5	582.6	572.8	560.6	546.0	528.9	511.0
152.5°	557.2	565.7	569.2	569.4	569.2	565.7	557.2	547.6	534.9	520.4	503.9
155°	537.0	542.7	546.0	544.4	546.0	542.7	537.0	528.1	519.1	507.0	493.9
157.5°	516.8	521.5	523.0	523.0	523.0	521.5	516.8	510.5	503.5	493.3	482.3
160°	504.5	508.6	509.4	509.4	509.4	508.6	504.5	498.8	493.1	484.1	475.2
162.5°	493.4	496.2	497.0	496.4	497.0	496.2	493.4	487.7	483.3	475.6	468.1
165°	475.2	478.4	478.4	477.6	478.4	478.4	475.2	472.0	468.7	463.0	457.3
167.5°	459.7	461.5	461.4	460.4	461.4	461.5	459.7	458.3	455.3	451.4	447.0
170°	450.0	452.4	451.6	450.0	451.6	452.4	450.0	449.1	447.5	444.3	441.8
172.5°	442.1	443.3	442.5	441.5	442.5	443.3	442.1	441.3	440.3	437.7	435.9
175°	432.1	432.9	432.1	430.5	432.1	432.9	432.1	432.1	431.3	430.5	429.7
177.5°	425.7	425.7	425.1	423.8	425.1	425.7	425.7	425.7	425.7	425.1	425.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	761.3	764.0	768.2	772.5	775.2	780.3	781.8	784.2	786.4	791.5	796.9
5°	717.4	721.6	731.6	737.1	744.8	753.6	759.4	765.5	772.2	783.7	794.4
7.5°	670.3	677.4	689.8	700.1	710.9	723.6	732.7	744.8	754.7	771.0	786.7
10°	638.8	648.8	660.1	672.3	687.5	700.9	713.7	729.0	741.1	760.6	778.9
12.5°	610.6	612.0	628.2	641.6	662.4	679.0	693.7	713.3	725.3	748.4	767.7
15°	561.2	570.3	584.9	595.6	620.2	641.2	661.9	682.3	696.0	724.6	749.9
17.5°	519.6	528.0	543.0	560.4	578.1	599.0	625.8	647.3	665.9	698.6	728.6
20°	493.3	503.6	518.9	536.8	552.4	575.2	598.3	623.0	643.0	679.9	714.9
22.5°	470.8	479.0	491.3	509.0	526.0	546.9	572.3	599.1	620.2	659.9	695.5
25°	439.4	446.1	454.0	468.6	487.8	510.6	530.4	559.9	590.7	627.9	670.7
27.5°	411.0	415.7	422.7	435.6	450.5	471.8	493.8	521.8	552.8	593.0	638.4
30°	393.7	396.7	403.7	414.4	429.0	445.7	468.0	494.8	526.4	567.3	612.3
32.5°	378.6	381.4	386.0	396.2	408.8	423.1	443.1	469.9	500.1	540.2	590.1
35°	356.0	358.1	362.0	370.2	377.2	391.3	408.0	432.4	460.6	499.0	550.8
37.5°	333.4	336.2	338.7	342.2	351.1	360.4	375.0	395.5	423.3	462.0	511.4
40°	318.5	320.9	324.6	326.1	333.4	341.6	353.5	372.3	400.4	435.7	483.8
42.5°	303.4	305.8	308.0	309.8	316.1	323.3	334.0	350.3	375.0	409.4	457.1
45°	282.8	283.2	285.3	288.6	291.7	296.9	304.5	318.5	337.7	370.0	413.2
47.5°	262.0	262.4	262.8	264.2	267.6	272.2	277.3	288.7	305.9	331.7	373.7
50°	248.2	247.5	248.2	249.4	251.5	255.4	261.2	269.5	283.5	307.5	346.2
52.5°	234.7	234.6	234.2	234.7	236.4	239.1	243.2	250.2	262.8	284.9	318.9
55°	214.3	212.8	213.1	211.9	214.7	215.2	218.3	224.1	235.1	250.3	282.3
57.5°	192.6	191.4	190.0	189.6	189.4	191.0	193.5	198.0	206.4	219.8	245.7
60°	178.7	177.2	175.4	174.8	174.8	175.7	176.9	180.3	188.2	200.1	221.4
62.5°	164.6	162.8	161.8	160.1	159.6	160.6	161.8	164.2	169.9	181.1	199.4
65°	142.8	140.6	139.2	138.8	138.3	137.3	137.9	140.4	145.0	153.8	168.4
67.5°	120.9	119.0	118.5	116.8	115.9	116.1	115.9	118.1	120.7	128.3	139.3
70°	106.6	105.0	104.4	102.9	102.3	101.7	101.1	102.9	105.7	112.0	121.5
72.5°	92.0	90.7	89.4	88.1	88.2	87.6	87.5	88.5	90.8	96.7	104.0
75°	70.9	71.3	69.7	68.2	67.9	67.3	67.3	68.2	69.1	73.7	79.5
77.5°	51.4	51.2	49.9	49.4	49.2	48.5	49.2	49.7	50.2	53.3	57.6
80°	39.3	39.3	37.7	37.7	37.4	36.5	37.4	36.9	38.1	41.1	44.2
82.5°	28.0	27.6	27.6	27.1	27.0	26.3	26.7	27.3	27.8	29.9	31.7
85°	13.7	13.7	13.4	13.1	13.4	13.1	13.4	13.7	14.0	14.9	16.5
87.5°	8.3	8.7	8.8	8.1	6.9	6.4	6.1	6.0	6.2	5.8	5.5
90°	26.8	27.6	26.8	21.9	16.3	12.2	9.8	8.2	6.5	3.3	0.8
92.5°	89.4	105.7	104.3	81.2	55.4	36.9	29.3	23.7	20.2	14.3	9.9
95°	279.1	318.9	282.3	187.9	117.2	79.7	60.3	47.2	39.9	31.7	28.5
97.5°	571.2	544.5	410.1	253.2	154.6	107.5	85.4	70.4	59.4	50.8	46.4
100°	760.0	642.8	442.6	266.9	167.6	124.5	101.7	85.4	72.4	65.1	62.6
102.5°	830.3	646.0	430.3	267.6	179.4	139.5	116.7	99.8	86.7	79.4	77.6
105°	819.4	602.9	406.0	271.7	199.3	161.1	138.4	120.4	108.2	102.6	99.3
107.5°	748.0	556.8	394.0	283.0	219.9	182.8	159.8	142.1	130.9	125.3	122.7
110°	703.0	534.6	391.4	292.1	233.5	197.7	174.1	157.0	146.4	141.6	138.4



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	671.8	520.2	392.0	301.9	246.5	212.1	187.8	171.4	161.4	155.9	152.6
115°	633.1	504.5	395.4	316.5	266.9	231.9	209.9	193.6	183.9	179.0	175.0
117.5°	608.6	496.8	401.3	332.2	285.6	253.2	230.4	214.8	206.2	201.3	198.0
120°	595.7	492.3	405.2	342.6	298.6	266.9	244.1	227.8	220.5	215.6	212.4
122.5°	584.6	489.7	409.8	351.6	311.0	281.2	257.8	241.5	233.5	228.6	226.1
125°	568.8	484.9	416.6	366.2	329.5	300.3	277.4	261.2	251.4	246.5	244.1
127.5°	554.2	482.2	423.6	379.7	346.8	318.3	294.9	279.2	268.5	261.7	258.4
130°	544.4	480.9	428.8	388.2	357.2	328.7	306.0	289.7	278.3	270.1	266.9
132.5°	536.5	480.2	434.0	396.6	366.3	339.2	316.3	299.5	287.4	278.6	274.7
135°	525.6	479.2	440.2	407.6	379.2	353.1	330.4	311.6	299.5	289.7	286.4
137.5°	518.0	479.1	445.7	416.1	389.6	363.9	342.8	324.2	311.1	301.4	297.5
140°	513.5	478.4	448.3	420.7	395.4	371.0	349.9	332.0	318.9	309.2	306.0
142.5°	508.9	478.4	450.3	424.6	400.0	376.3	356.4	339.2	326.1	317.0	314.4
145°	502.9	476.8	452.4	429.7	406.8	384.9	367.0	350.7	338.5	330.4	327.1
147.5°	496.7	473.9	453.1	432.4	412.4	391.8	375.8	362.2	351.0	343.2	340.8
150°	491.5	472.0	452.4	433.7	415.0	396.2	381.6	369.4	358.8	352.3	349.9
152.5°	486.9	468.7	451.1	434.3	417.6	400.8	387.5	375.9	366.6	360.1	359.0
155°	478.4	463.0	449.1	435.3	421.5	407.6	395.4	386.5	377.6	372.7	371.9
157.5°	470.5	457.1	445.4	435.3	424.3	412.5	402.3	395.1	387.3	383.4	382.6
160°	464.6	453.2	443.4	435.3	425.6	415.8	406.8	400.3	393.8	390.6	389.8
162.5°	459.4	450.0	441.5	434.6	426.2	417.8	410.7	404.9	399.7	396.4	396.9
165°	450.8	443.4	437.7	432.9	427.2	419.9	415.0	410.9	406.0	404.4	405.2
167.5°	442.3	437.7	434.0	431.8	427.1	421.7	418.6	415.6	412.5	411.1	412.1
170°	437.7	434.5	432.1	430.5	426.4	422.3	419.9	418.2	415.8	415.0	416.6
172.5°	433.3	430.6	429.5	428.5	425.7	423.0	421.2	420.2	417.8	418.2	419.2
175°	427.2	426.4	425.6	426.4	424.8	423.1	422.3	422.3	420.7	421.5	422.3
177.5°	423.8	423.1	423.8	425.1	423.8	423.1	423.1	423.1	421.8	422.5	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	796.4	797.6	801.5	805.4	809.8	811.0	812.9	811.2	810.7	815.4	818.8
5°	798.7	804.1	814.8	824.5	832.7	838.5	844.7	847.1	851.7	858.0	865.9
7.5°	796.1	806.7	823.5	837.7	853.1	864.3	873.0	880.4	889.4	901.6	914.8
10°	793.2	807.5	827.9	845.2	864.1	878.4	890.3	901.9	915.3	932.1	949.3
12.5°	787.8	804.8	830.3	850.8	875.1	889.2	905.1	930.1	944.5	967.8	992.2
15°	777.1	795.9	831.5	856.8	884.2	911.0	940.5	964.3	988.1	1001.8	1036.2
17.5°	761.0	788.7	828.2	857.7	892.5	934.7	967.8	994.8	1022.2	1044.4	1061.7
20°	748.1	778.3	823.3	858.7	900.0	945.4	983.5	1010.9	1034.6	1053.2	1063.9
22.5°	731.8	769.7	813.6	855.0	907.8	952.8	992.7	1014.3	1034.1	1043.2	1047.3
25°	706.0	751.8	801.4	851.9	911.6	959.1	995.6	1008.8	1014.6	1005.7	991.1
27.5°	678.4	729.3	787.3	846.2	909.3	955.0	981.1	979.1	969.3	940.7	917.9
30°	657.7	713.7	776.1	840.3	903.7	948.1	963.4	948.1	925.9	894.0	861.4
32.5°	636.0	694.0	764.2	832.1	893.5	932.5	935.9	909.6	875.2	838.9	798.3
35°	603.2	665.9	741.7	813.6	871.7	896.4	881.7	835.5	794.7	745.1	689.7
37.5°	566.1	635.4	711.3	786.4	839.2	845.6	809.3	760.6	703.0	644.7	579.5
40°	538.3	611.7	690.0	765.7	812.4	805.7	759.4	705.8	637.2	566.1	505.4
42.5°	513.5	586.9	666.6	740.9	778.3	759.9	705.8	640.0	566.4	499.3	443.8
45°	470.4	545.9	627.5	699.4	720.7	687.5	616.0	542.9	470.4	414.4	370.6
47.5°	428.7	503.3	584.1	647.3	654.8	610.2	532.0	456.8	394.5	348.9	318.0
50°	397.9	472.9	552.9	609.3	606.8	552.9	472.5	401.0	348.9	312.1	291.4
52.5°	370.4	441.2	518.1	569.3	556.4	497.7	420.9	357.4	314.6	285.8	267.0
55°	327.6	393.1	466.2	507.3	483.6	418.3	353.5	302.3	270.7	249.1	234.5
57.5°	285.1	346.5	409.0	434.4	408.1	348.0	293.9	256.8	233.0	217.0	207.5
60°	258.8	312.4	368.1	390.0	358.7	305.1	262.4	229.3	210.1	197.0	188.5
62.5°	232.5	280.5	333.0	345.0	316.3	271.0	233.3	205.6	189.9	178.2	170.2
65°	196.7	235.9	275.9	283.8	257.3	222.3	192.4	174.5	160.5	152.0	145.5
67.5°	161.3	192.8	221.1	227.5	204.3	180.0	158.4	142.8	133.3	126.2	120.8
70°	140.4	165.3	188.5	193.6	175.0	153.4	137.1	124.5	116.0	109.9	104.8
72.5°	118.2	139.0	158.2	161.8	146.6	130.0	116.6	106.7	99.2	95.3	90.3
75°	90.4	102.6	117.6	118.5	108.4	98.3	88.0	81.6	77.6	72.8	70.4
77.5°	63.8	73.4	81.9	83.6	77.6	70.8	65.0	59.9	56.6	54.3	52.1
80°	48.8	56.3	60.0	62.1	57.9	53.0	49.7	46.3	44.2	42.6	41.1
82.5°	34.8	39.5	43.0	44.6	42.2	39.4	36.0	34.1	32.4	31.1	30.7
85°	17.7	19.8	21.9	22.5	21.9	20.7	18.9	18.9	17.9	17.7	17.7
87.5°	6.8	8.4	8.7	9.8	9.8	10.6	11.7	12.5	12.4	12.0	11.6
90°	3.3	6.5	8.2	9.8	12.2	16.3	21.9	26.8	27.6	26.8	26.0
92.5°	14.3	20.2	23.7	29.3	36.9	55.4	81.2	104.3	105.7	89.4	70.9
95°	31.7	39.9	47.2	60.3	79.7	117.2	187.9	282.3	318.9	279.1	213.2
97.5°	50.8	59.4	70.4	85.4	107.5	154.6	253.2	410.1	544.5	571.2	497.5
100°	65.1	72.4	85.4	101.7	124.5	167.6	266.9	442.6	642.8	760.0	742.9
102.5°	79.4	86.7	99.8	116.7	139.5	179.4	267.6	430.3	646.0	830.3	903.7
105°	102.6	108.2	120.4	138.4	161.1	199.3	271.7	406.0	602.9	819.4	988.6
107.5°	125.3	130.9	142.1	159.8	182.8	219.9	283.0	394.0	556.8	748.0	927.5
110°	141.6	146.4	157.0	174.1	197.7	233.5	292.1	391.4	534.6	703.0	874.7





TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	155.9	161.4	171.4	187.8	212.1	246.5	301.9	392.0	520.2	671.8	826.6
115°	179.0	183.9	193.6	209.9	231.9	266.9	316.5	395.4	504.5	633.1	767.3
117.5°	201.3	206.2	214.8	230.4	253.2	285.6	332.2	401.3	496.8	608.6	722.7
120°	215.6	220.5	227.8	244.1	266.9	298.6	342.6	405.2	492.3	595.7	700.6
122.5°	228.6	233.5	241.5	257.8	281.2	311.0	351.6	409.8	489.7	584.6	683.0
125°	246.5	251.4	261.2	277.4	300.3	329.5	366.2	416.6	484.9	568.8	657.5
127.5°	261.7	268.5	279.2	294.9	318.3	346.8	379.7	423.6	482.2	554.2	632.3
130°	270.1	278.3	289.7	306.0	328.7	357.2	388.2	428.8	480.9	544.4	616.0
132.5°	278.6	287.4	299.5	316.3	339.2	366.3	396.6	434.0	480.2	536.5	600.3
135°	289.7	299.5	311.6	330.4	353.1	379.2	407.6	440.2	479.2	525.6	578.5
137.5°	301.4	311.1	324.2	342.8	363.9	389.6	416.1	445.7	479.1	518.0	561.1
140°	309.2	318.9	332.0	349.9	371.0	395.4	420.7	448.3	478.4	513.5	550.1
142.5°	317.0	326.1	339.2	356.4	376.3	400.0	424.6	450.3	478.4	508.9	541.0
145°	330.4	338.5	350.7	367.0	384.9	406.8	429.7	452.4	476.8	502.9	528.1
147.5°	343.2	351.0	362.2	375.8	391.8	412.4	432.4	453.1	473.9	496.7	518.1
150°	352.3	358.8	369.4	381.6	396.2	415.0	433.7	452.4	472.0	491.5	511.0
152.5°	360.1	366.6	375.9	387.5	400.8	417.6	434.3	451.1	468.7	486.9	503.9
155°	372.7	377.6	386.5	395.4	407.6	421.5	435.3	449.1	463.0	478.4	493.9
157.5°	383.4	387.3	395.1	402.3	412.5	424.3	435.3	445.4	457.1	470.5	482.3
160°	390.6	393.8	400.3	406.8	415.8	425.6	435.3	443.4	453.2	464.6	475.2
162.5°	396.4	399.7	404.9	410.7	417.8	426.2	434.6	441.5	450.0	459.4	468.1
165°	404.4	406.0	410.9	415.0	419.9	427.2	432.9	437.7	443.4	450.8	457.3
167.5°	411.1	412.5	415.6	418.6	421.7	427.1	431.8	434.0	437.7	442.3	447.0
170°	415.0	415.8	418.2	419.9	422.3	426.4	430.5	432.1	434.5	437.7	441.8
172.5°	418.2	417.8	420.2	421.2	423.0	425.7	428.5	429.5	430.6	433.3	435.9
175°	421.5	420.7	422.3	422.3	423.1	424.8	426.4	425.6	426.4	427.2	429.7
177.5°	422.5	421.8	423.1	423.1	423.1	423.8	425.1	423.8	423.1	423.8	425.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	821.7	825.2	825.2	825.7	829.5	829.1	828.8
5°	874.5	879.6	880.3	885.7	889.4	888.2	884.8
7.5°	924.2	933.8	941.2	945.3	950.1	953.0	951.7
10°	963.7	977.7	986.2	992.0	999.0	1004.2	1002.3
12.5°	999.5	1016.2	1027.8	1037.8	1038.7	1045.4	1040.8
15°	1055.3	1073.0	1074.8	1082.1	1087.9	1087.3	1087.6
17.5°	1073.7	1079.5	1080.6	1080.8	1080.8	1078.7	1074.1
20°	1067.2	1065.1	1059.9	1056.0	1049.0	1048.0	1042.0
22.5°	1036.0	1029.2	1016.3	1007.7	996.8	993.9	992.2
25°	974.6	959.7	939.0	919.2	913.7	903.1	906.1
27.5°	890.4	867.2	844.7	828.7	814.2	798.2	802.7
30°	831.2	805.0	773.4	749.0	733.5	718.3	715.5
32.5°	760.6	722.2	686.9	665.4	641.6	632.0	621.5
35°	638.8	601.4	566.3	536.2	518.9	505.4	493.3
37.5°	529.2	486.2	457.9	433.5	420.9	413.3	415.2
40°	461.3	423.5	402.8	384.3	372.7	367.2	368.4
42.5°	406.3	378.0	360.9	348.2	340.1	337.0	336.2
45°	343.7	327.9	313.9	306.6	302.6	299.3	297.2
47.5°	301.2	288.2	280.3	276.0	272.5	269.1	269.0
50°	275.6	267.0	261.5	257.0	254.2	251.8	254.0
52.5°	256.1	248.3	242.8	238.7	237.7	235.5	235.5
55°	227.1	221.0	217.1	213.4	211.7	210.4	208.9
57.5°	200.8	195.0	191.4	189.1	185.6	184.4	183.9
60°	182.1	177.5	173.8	170.8	169.3	166.9	166.9
62.5°	164.8	160.2	156.8	154.5	152.0	151.0	151.2
65°	139.7	136.1	132.7	130.3	129.7	127.9	128.5
67.5°	116.8	114.3	110.8	109.4	108.3	107.3	106.6
70°	101.4	99.0	97.1	95.3	94.4	94.4	94.4
72.5°	88.5	85.5	84.5	82.2	82.7	81.7	80.7
75°	68.5	66.7	65.8	64.8	63.3	63.3	63.3
77.5°	50.4	49.9	48.8	47.8	47.5	47.1	47.3
80°	39.0	38.6	38.1	38.1	37.4	37.2	36.5
82.5°	29.9	29.2	28.8	28.5	28.5	28.4	28.3
85°	17.0	16.5	16.5	16.7	16.1	16.1	16.5
87.5°	11.5	11.8	11.7	11.7	12.0	11.7	11.7
90°	24.4	26.0	26.8	26.8	26.8	26.8	26.8
92.5°	60.9	54.1	49.0	48.3	45.7	46.4	45.1
95°	163.5	129.4	111.5	100.9	94.4	92.0	92.8
97.5°	407.0	318.9	260.2	221.4	201.3	189.4	182.6
100°	642.0	530.5	432.1	364.5	329.5	306.0	291.3
102.5°	880.9	799.4	695.0	621.7	561.9	532.5	512.7
105°	1080.6	1091.2	1064.3	1013.8	963.4	928.4	917.0
107.5°	1065.9	1150.6	1189.9	1196.3	1193.5	1186.5	1171.4
110°	1020.3	1124.5	1191.2	1226.2	1241.7	1249.0	1248.2



TEST NUMBER: P331314-930

CATALOG NUMBER: S122DIP-S485D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	966.4	1077.7	1154.1	1202.8	1228.7	1242.5	1246.9
115°	892.6	999.2	1083.0	1140.8	1178.2	1199.4	1206.7
117.5°	832.7	929.4	1008.0	1066.9	1106.4	1128.8	1134.9
120°	801.5	887.7	961.8	1018.7	1057.0	1080.6	1088.8
122.5°	775.4	857.1	924.1	975.1	1012.7	1033.7	1040.6
125°	741.3	812.9	873.9	921.1	952.0	972.3	978.8
127.5°	708.1	775.6	831.9	873.1	902.0	919.7	924.9
130°	685.9	750.2	804.0	843.8	871.5	887.7	894.2
132.5°	665.1	724.1	774.6	813.8	841.6	856.5	862.3
135°	632.3	685.9	731.5	766.5	793.4	808.0	811.2
137.5°	606.0	648.7	688.4	720.3	743.4	756.3	761.2
140°	589.1	626.6	662.3	688.4	709.6	721.8	726.6
142.5°	574.1	606.3	636.3	661.0	680.3	691.1	692.1
145°	555.0	580.2	603.7	623.3	637.2	645.2	647.7
147.5°	539.3	559.0	576.3	592.4	603.4	608.9	610.4
150°	528.9	546.0	560.6	572.8	582.6	587.5	588.3
152.5°	520.4	534.9	547.6	557.2	565.7	569.2	569.4
155°	507.0	519.1	528.1	537.0	542.7	546.0	544.4
157.5°	493.3	503.5	510.5	516.8	521.5	523.0	523.0
160°	484.1	493.1	498.8	504.5	508.6	509.4	509.4
162.5°	475.6	483.3	487.7	493.4	496.2	497.0	496.4
165°	463.0	468.7	472.0	475.2	478.4	478.4	477.6
167.5°	451.4	455.3	458.3	459.7	461.5	461.4	460.4
170°	444.3	447.5	449.1	450.0	452.4	451.6	450.0
172.5°	437.7	440.3	441.3	442.1	443.3	442.5	441.5
175°	430.5	431.3	432.1	432.1	432.9	432.1	430.5
177.5°	425.1	425.7	425.7	425.7	425.7	425.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)