

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331633-930

Luminaire Tested: **S122RDIP-S290D925U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331633-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D925U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3939.3 lumens  
Efficiency: N/A  
Efficacy: 105.6 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	23
1	92	88	85	81	82	79	76	73	60	59	57	44	43	42	29	28	27	20
2	84	77	72	67	75	69	64	60	53	50	48	39	37	35	26	25	24	18
3	77	68	62	56	68	61	55	51	47	44	40	35	32	30	23	22	21	15
4	71	61	53	48	63	54	48	43	42	38	35	31	28	26	21	19	18	14
5	65	54	46	41	57	48	42	37	38	33	30	28	25	23	19	17	16	12
6	60	48	41	36	53	44	37	32	34	30	26	25	22	20	17	16	14	11
7	55	44	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	40	32	27	45	36	29	25	28	24	21	21	18	16	15	13	12	9
9	48	36	29	24	42	33	27	22	26	22	18	20	17	14	14	12	11	8
10	44	33	26	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8606	8606	8606	8606
5°	9611	8660	7679	8660
10°	10663	8599	6655	8599
15°	11188	8473	5244	8473
20°	9699	8285	4538	8285
25°	6360	8031	4051	8031
30°	4282	7720	3667	7720
35°	3467	7330	3307	7330
40°	3084	6905	3060	6905
45°	2790	6405	2731	6405
50°	2539	5913	2532	5913
55°	2387	5362	2356	5362
60°	1999	4863	1973	4863
65°	1685	4413	1910	4413
70°	1553	3942	1803	3942
75°	1454	3431	1666	3431
80°	1339	2827	1478	2827
85°	1241	2242	1297	2242



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.5	1.3
10°-20°	140.8	3.6
20°-30°	181.4	4.6
30°-40°	172.4	4.4
40°-50°	147.7	3.7
50°-60°	112.5	2.9
60°-70°	71.1	1.8
70°-80°	35.5	0.9
80°-90°	11.8	0.3
90°-100°	34.3	0.9
100°-110°	125.9	3.2
110°-120°	336.5	8.5
120°-130°	555.4	14.1
130°-140°	590.7	15.0
140°-150°	549.0	13.9
150°-160°	441.4	11.2
160°-170°	284.5	7.2
170°-180°	97.9	2.5
0°-30°	372.7	9.5
0°-40°	545.1	13.8
0°-60°	805.3	20.4
0°-90°	923.7	23.4
90°-120°	496.7	12.6
90°-150°	2191.9	55.6
90°-180°	3016.0	76.6
0°-180°	3939.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	533	533	533	533	533	
5°	593	534	474	534	593	59
15°	669	507	314	507	669	181
25°	357	451	227	451	357	169
35°	176	372	168	372	176	113
45°	122	280	120	280	122	95
55°	85	190	84	190	85	74
65°	44	116	50	116	44	45
75°	23	55	27	55	23	25
85°	7	12	7	12	7	8
90°	20	1	20	1	20	9
95°	32	48	32	48	32	30
105°	57	226	57	226	57	59
115°	61	428	61	428	61	153
125°	637	605	637	605	637	551
135°	774	749	774	749	774	596
145°	882	869	882	869	882	552
155°	958	957	958	957	958	442
165°	1006	1008	1006	1008	1006	284
175°	1025	1031	1025	1031	1025	98
180°	1029	1029	1029	1029	1029	



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	554.6	555.1	555.5	554.5	554.5	553.6	551.6	550.2	546.0	545.4	545.4
5°	593.0	592.6	593.4	590.9	587.7	586.9	583.3	578.7	573.9	568.6	567.4
7.5°	631.1	630.6	629.1	628.7	626.1	620.5	614.9	608.9	600.9	593.0	589.1
10°	650.4	656.6	652.8	646.4	647.6	639.0	634.3	626.3	619.6	608.0	605.4
12.5°	669.4	671.8	670.6	666.9	665.3	659.3	653.0	646.0	633.7	623.3	614.2
15°	669.3	672.8	673.8	672.6	673.5	673.2	669.8	664.1	653.4	641.9	631.9
17.5°	619.9	622.3	628.4	632.5	637.7	648.7	654.1	656.2	654.6	648.0	641.0
20°	564.5	560.4	577.5	586.1	593.5	612.0	628.0	634.1	643.9	643.8	641.9
22.5°	485.9	486.9	503.0	513.4	535.0	553.6	571.7	594.7	613.7	626.2	633.6
25°	357.0	364.1	380.2	394.3	418.3	452.8	484.1	520.4	554.6	581.7	607.5
27.5°	268.2	268.7	281.4	294.5	308.8	337.0	376.4	419.7	468.6	508.9	555.2
30°	229.7	228.5	233.9	241.9	254.1	276.0	305.6	348.1	396.9	457.6	511.7
32.5°	202.4	202.4	206.5	212.4	222.5	237.3	257.6	292.2	338.2	397.9	461.3
35°	175.9	175.8	178.7	183.0	187.2	196.7	210.6	228.7	260.4	316.1	380.9
37.5°	156.9	157.8	159.2	161.9	166.6	171.9	180.2	192.4	214.9	247.9	302.4
40°	146.3	146.7	148.7	150.9	153.7	157.8	164.6	174.5	190.9	217.2	257.1
42.5°	136.6	136.9	138.4	140.4	142.6	146.7	152.4	160.9	174.2	194.7	227.6
45°	122.2	122.2	123.5	124.4	126.9	130.5	135.2	142.3	151.5	166.6	188.5
47.5°	108.8	108.8	109.7	111.3	112.8	115.7	120.3	126.0	132.7	144.5	163.1
50°	101.1	101.3	101.8	103.1	104.1	106.6	110.2	115.2	122.2	131.3	146.8
52.5°	94.9	94.8	95.5	96.0	96.7	98.5	101.2	105.6	111.9	119.8	132.6
55°	84.8	84.1	85.2	86.1	86.7	87.4	88.9	91.6	97.0	103.7	113.3
57.5°	72.2	71.9	72.7	73.5	75.3	77.3	78.6	80.3	83.1	87.9	97.4
60°	61.9	61.9	63.5	64.1	66.1	68.7	71.3	72.8	75.6	78.7	85.8
62.5°	52.7	52.8	53.6	54.1	55.3	58.5	62.1	65.4	68.0	71.0	75.7
65°	44.1	44.4	44.4	44.8	45.6	46.3	47.8	50.4	55.0	59.3	62.8
67.5°	37.4	37.5	37.7	38.0	38.2	39.0	39.6	40.8	41.8	45.8	50.2
70°	32.9	33.5	33.3	33.7	33.9	34.2	35.0	35.5	37.3	38.2	40.8
72.5°	28.8	29.2	29.2	29.4	29.9	30.0	30.6	31.1	32.2	32.9	34.4
75°	23.3	23.2	23.3	23.7	23.9	24.1	24.1	24.8	25.4	26.1	27.1
77.5°	18.0	18.2	18.2	18.2	18.3	18.6	18.5	18.8	19.4	19.8	20.2
80°	14.4	14.6	14.4	14.6	14.8	15.0	14.8	15.0	15.6	15.9	15.9
82.5°	11.2	11.3	11.3	11.3	11.4	11.4	11.7	11.7	12.1	12.1	12.2
85°	6.7	6.5	6.5	6.5	6.7	6.8	6.7	6.7	6.8	6.8	6.8
87.5°	6.4	6.4	6.4	6.4	6.3	6.2	6.0	6.0	5.6	5.6	5.2
90°	20.1	19.8	19.4	19.1	18.8	18.2	17.4	16.6	15.7	14.9	13.5
92.5°	20.1	19.9	19.7	19.5	19.3	19.0	18.6	18.1	17.7	17.3	16.6
95°	32.0	32.2	32.4	32.5	32.7	32.4	31.6	30.7	29.8	29.0	27.9
97.5°	42.7	42.6	42.3	42.2	41.9	41.5	40.8	40.2	39.5	38.9	36.2
100°	49.9	49.6	49.2	48.9	48.6	47.8	46.4	45.1	43.8	42.5	39.6
102.5°	53.5	53.0	52.5	52.1	51.6	50.5	48.8	47.0	45.3	43.6	39.6
105°	56.6	55.9	55.3	54.6	54.0	52.7	50.9	49.1	47.2	45.4	39.6
107.5°	58.2	57.6	56.9	56.3	55.6	56.2	58.0	59.8	61.7	63.6	117.7
110°	58.9	58.1	57.5	56.8	56.2	64.1	80.6	97.2	113.7	130.3	178.1



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	59.4	58.9	58.4	57.8	57.3	87.2	147.6	208.0	268.3	328.6	340.5
115°	61.1	73.0	84.9	96.8	108.7	153.0	229.6	306.2	382.8	459.4	455.3
117.5°	249.3	288.5	327.6	366.7	405.9	434.7	453.3	471.8	490.3	508.8	506.1
120°	454.2	476.5	498.9	521.2	543.6	553.8	551.8	549.8	547.8	545.8	542.8
122.5°	566.8	571.1	575.4	579.8	584.2	585.7	584.5	583.3	582.1	581.0	577.7
125°	636.7	636.2	635.6	635.1	634.6	633.8	632.7	631.5	630.4	629.2	626.1
127.5°	680.7	680.6	680.5	680.4	680.3	679.5	677.8	676.0	674.3	672.7	670.3
130°	708.1	708.3	708.4	708.7	708.8	707.9	706.1	704.3	702.5	700.7	698.9
132.5°	734.9	735.1	735.2	735.4	735.6	734.9	733.4	731.8	730.3	728.6	726.8
135°	773.6	774.0	774.3	774.6	774.9	774.3	772.7	771.0	769.3	767.7	766.2
137.5°	808.9	809.5	810.1	810.7	811.2	810.7	809.0	807.4	805.8	804.2	802.5
140°	831.0	831.8	832.7	833.5	834.3	834.0	832.5	831.0	829.5	828.0	826.2
142.5°	852.4	853.3	854.1	854.9	855.7	855.5	854.1	852.7	851.4	850.0	848.0
145°	882.4	883.2	884.0	884.8	885.7	885.5	884.4	883.2	882.0	880.8	878.1
147.5°	908.7	909.4	910.1	910.8	911.5	911.4	910.5	909.7	908.8	908.0	905.2
150°	924.8	925.6	926.4	927.3	928.1	928.1	927.1	926.0	925.0	924.1	921.5
152.5°	938.5	939.6	940.7	941.8	942.9	942.9	941.9	940.9	940.0	939.0	936.5
155°	957.6	958.9	960.2	961.6	962.9	963.0	962.1	961.1	960.0	959.0	957.1
157.5°	975.0	976.2	977.5	978.8	980.2	980.2	979.1	978.0	976.9	975.8	974.4
160°	985.1	986.3	987.4	988.6	989.8	989.9	988.9	987.8	986.8	985.9	984.9
162.5°	993.4	994.9	996.3	997.8	999.1	999.3	998.2	997.0	995.9	994.8	993.9
165°	1006.0	1007.1	1008.3	1009.4	1010.6	1010.6	1009.4	1008.3	1007.1	1006.0	1005.5
167.5°	1013.8	1015.4	1016.8	1018.3	1019.8	1020.0	1018.8	1017.7	1016.5	1015.4	1014.9
170°	1018.6	1020.1	1021.6	1023.1	1024.6	1024.7	1023.6	1022.5	1021.2	1020.1	1019.8
172.5°	1022.2	1023.7	1025.2	1026.6	1028.2	1028.3	1027.2	1026.0	1024.8	1023.7	1023.4
175°	1025.3	1027.0	1028.7	1030.3	1031.9	1032.2	1031.0	1029.9	1028.7	1027.5	1027.2
177.5°	1027.3	1028.4	1029.6	1030.9	1032.0	1032.2	1031.3	1030.3	1029.4	1028.4	1028.3
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	545.8	544.5	543.5	540.9	539.5	536.5	536.1	536.0	532.1	528.4	527.3
5°	564.5	561.5	557.1	551.9	546.5	541.0	537.3	534.3	526.8	519.8	515.8
7.5°	583.3	577.0	569.3	559.5	551.3	542.2	535.3	529.2	518.7	508.6	501.8
10°	597.5	587.1	576.9	563.4	552.8	542.4	532.8	524.5	512.7	499.3	489.8
12.5°	606.2	594.8	580.7	567.5	553.8	540.6	527.7	517.1	503.1	489.3	478.2
15°	618.0	605.8	588.7	569.8	552.3	535.0	520.2	506.9	488.8	472.2	458.5
17.5°	627.7	610.8	592.6	570.7	550.3	528.5	509.4	492.4	472.1	452.2	436.1
20°	630.8	614.1	593.0	571.1	547.1	521.3	500.8	482.2	460.6	438.9	420.4
22.5°	628.8	615.9	592.4	566.2	541.6	514.7	491.5	469.9	445.9	423.8	402.4
25°	615.8	611.3	589.1	560.6	532.5	501.2	474.3	450.8	423.4	399.7	376.3
27.5°	585.3	594.9	581.1	550.7	519.4	485.9	455.7	428.9	400.5	373.8	350.6
30°	556.0	578.0	572.1	543.9	508.9	476.0	442.1	414.1	383.8	356.3	333.4
32.5°	515.8	552.2	558.0	534.4	498.2	462.0	426.5	398.7	367.0	338.1	315.7
35°	451.8	506.3	531.3	516.3	480.0	440.9	404.3	371.9	340.0	311.5	289.3
37.5°	375.6	449.8	491.5	492.5	459.2	418.6	378.6	346.4	313.8	285.8	261.8
40°	326.1	406.5	460.8	472.8	444.7	400.8	360.4	327.6	295.8	268.3	240.8
42.5°	281.7	361.7	428.4	449.4	427.1	383.4	342.9	308.7	277.7	251.8	223.6
45°	227.8	297.8	371.3	408.7	396.3	356.0	313.2	280.5	251.5	229.1	202.0
47.5°	192.2	241.5	312.7	363.2	363.1	326.2	284.1	252.9	225.9	204.9	183.0
50°	171.9	214.8	275.0	332.4	337.2	306.3	266.3	235.4	210.2	188.2	170.6
52.5°	153.6	189.1	243.1	298.2	311.9	285.1	246.3	217.8	193.3	173.0	158.0
55°	129.8	157.3	198.4	249.8	270.6	251.7	217.2	190.5	170.7	153.7	140.7
57.5°	109.8	130.4	163.4	204.8	228.9	217.1	188.7	167.0	150.0	134.6	124.4
60°	97.3	114.1	142.0	176.7	203.3	195.0	170.7	150.6	136.2	122.8	113.2
62.5°	85.4	99.9	123.8	152.0	176.3	172.9	153.1	136.2	123.5	111.4	103.2
65°	68.7	79.2	98.0	120.0	139.7	141.3	127.0	115.5	104.3	94.7	87.4
67.5°	54.7	61.6	74.8	93.4	108.0	113.3	104.6	95.8	86.8	79.4	73.1
70°	46.1	51.7	61.3	76.3	89.8	95.4	90.3	83.5	75.7	69.6	64.2
72.5°	37.3	42.8	49.9	60.9	72.5	78.5	76.7	71.8	65.6	60.4	55.4
75°	28.1	29.8	34.7	42.1	51.1	56.3	57.6	55.0	50.0	46.1	43.1
77.5°	20.8	21.9	24.1	28.0	33.9	38.6	40.4	40.1	36.7	34.5	31.6
80°	16.6	17.2	18.3	20.0	24.5	29.1	30.4	30.4	28.0	27.1	24.3
82.5°	12.6	13.0	13.8	14.7	16.7	20.8	22.3	22.5	21.0	19.8	17.6
85°	7.3	7.0	7.4	8.0	8.3	9.5	11.7	12.1	11.7	10.2	9.6
87.5°	5.0	4.8	4.6	4.2	3.9	3.7	4.1	4.5	4.2	4.2	4.2
90°	12.2	10.9	9.6	8.0	6.2	4.4	2.5	0.7	2.5	4.4	6.2
92.5°	16.0	15.3	14.6	14.3	14.5	14.7	14.8	15.0	14.8	14.7	14.5
95°	26.7	25.6	24.4	26.6	32.0	37.5	43.0	48.4	43.0	37.5	32.0
97.5°	33.5	30.8	28.1	34.5	49.9	65.3	80.6	96.0	80.6	65.3	49.9
100°	36.9	34.0	31.2	41.1	63.8	86.4	109.1	131.8	109.1	86.4	63.8
102.5°	90.7	114.2	137.8	151.9	156.7	161.5	166.3	171.1	166.3	161.5	156.7
105°	135.7	180.9	226.1	246.2	241.2	236.3	231.3	226.3	231.3	236.3	241.2
107.5°	171.9	226.1	280.3	305.4	301.3	297.3	293.3	289.3	293.3	297.3	301.3
110°	225.9	273.8	321.6	343.7	340.3	336.8	333.4	329.9	333.4	336.8	340.3





TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	352.3	364.1	375.9	380.3	377.2	374.1	371.0	367.9	371.0	374.1	377.2
115°	451.2	447.0	442.9	439.4	436.6	433.7	431.0	428.1	431.0	433.7	436.6
117.5°	503.2	500.3	497.5	494.5	491.4	488.2	485.0	481.9	485.0	488.2	491.4
120°	539.8	536.9	533.9	531.2	528.6	526.2	523.7	521.2	523.7	526.2	528.6
122.5°	574.5	571.2	567.9	565.0	562.4	559.8	557.2	554.6	557.2	559.8	562.4
125°	622.9	619.8	616.6	614.0	611.8	609.7	607.5	605.4	607.5	609.7	611.8
127.5°	668.0	665.6	663.2	660.9	658.5	656.2	653.8	651.3	653.8	656.2	658.5
130°	697.0	695.2	693.4	691.1	688.5	685.8	683.2	680.6	683.2	685.8	688.5
132.5°	725.0	723.3	721.4	719.3	717.1	714.9	712.6	710.4	712.6	714.9	717.1
135°	764.8	763.2	761.7	759.7	757.0	754.4	751.7	749.1	751.7	754.4	757.0
137.5°	800.8	799.1	797.4	795.7	793.8	792.0	790.1	788.2	790.1	792.0	793.8
140°	824.3	822.6	820.8	819.1	817.8	816.5	815.2	813.8	815.2	816.5	817.8
142.5°	845.9	843.8	841.7	840.1	838.9	837.7	836.5	835.3	836.5	837.7	838.9
145°	875.2	872.5	869.6	868.3	868.5	868.6	868.8	868.9	868.8	868.6	868.5
147.5°	902.5	899.6	896.8	895.8	896.4	897.1	897.6	898.3	897.6	897.1	896.4
150°	918.8	916.2	913.5	912.7	913.9	915.0	916.2	917.4	916.2	915.0	913.9
152.5°	933.9	931.4	928.9	928.3	929.6	930.8	932.1	933.4	932.1	930.8	929.6
155°	955.1	953.1	951.1	950.9	952.4	953.8	955.4	956.8	955.4	953.8	952.4
157.5°	973.0	971.6	970.2	970.1	971.3	972.7	973.9	975.1	973.9	972.7	971.3
160°	983.9	982.8	981.9	981.9	982.8	983.9	984.9	985.9	984.9	983.9	982.8
162.5°	993.0	992.2	991.3	991.4	992.4	993.4	994.4	995.4	994.4	993.4	992.4
165°	1004.9	1004.4	1004.0	1004.2	1005.2	1006.2	1007.2	1008.2	1007.2	1006.2	1005.2
167.5°	1014.4	1014.0	1013.5	1013.7	1014.7	1015.8	1016.8	1017.7	1016.8	1015.8	1014.7
170°	1019.5	1019.1	1018.8	1019.1	1020.1	1021.1	1022.1	1023.1	1022.1	1021.1	1020.1
172.5°	1023.0	1022.7	1022.4	1022.7	1023.7	1024.7	1025.6	1026.6	1025.6	1024.7	1023.7
175°	1026.9	1026.5	1026.2	1026.6	1027.8	1029.0	1030.1	1031.3	1030.1	1029.0	1027.8
177.5°	1028.2	1028.1	1027.9	1028.3	1029.2	1030.2	1031.1	1032.0	1031.1	1030.2	1029.2
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	525.5	524.4	522.4	519.5	517.7	514.6	512.6	513.7	514.0	513.7	513.5
5°	511.4	507.4	502.1	496.8	492.0	486.9	483.9	482.7	480.0	478.6	477.8
7.5°	494.2	487.5	480.0	470.9	463.3	455.2	451.1	449.1	443.8	440.9	438.4
10°	481.5	470.9	463.3	451.5	444.3	433.7	426.5	426.7	419.5	415.4	412.5
12.5°	467.4	455.8	443.2	432.5	422.5	414.0	405.3	401.8	394.1	390.2	382.2
15°	444.1	430.6	417.3	402.8	392.6	379.4	366.9	351.5	339.1	328.3	325.4
17.5°	418.7	401.9	388.5	371.5	354.1	332.0	317.4	308.4	301.0	295.3	291.1
20°	401.1	384.1	369.8	344.3	320.7	305.7	295.1	288.1	280.4	274.3	270.9
22.5°	382.8	365.0	345.5	317.0	298.6	286.7	277.1	269.2	263.9	259.2	256.1
25°	356.7	337.2	305.2	285.6	270.8	258.1	251.5	246.7	241.2	234.6	231.7
27.5°	329.1	298.2	275.2	260.6	246.5	238.3	232.3	225.1	220.1	217.2	214.1
30°	308.5	277.6	259.7	243.7	233.7	224.6	217.6	213.5	208.7	203.7	201.7
32.5°	285.6	260.9	243.6	230.4	220.2	212.5	206.9	200.3	196.9	193.8	189.6
35°	257.1	238.3	222.6	211.9	202.2	195.9	189.5	185.6	179.3	176.7	175.0
37.5°	232.9	216.7	205.0	193.6	186.0	179.0	175.0	168.8	166.2	162.5	159.0
40°	219.2	203.3	192.1	182.8	174.2	169.1	164.1	159.1	155.0	153.4	149.1
42.5°	205.4	192.4	181.1	171.0	165.3	159.7	153.4	149.8	145.5	142.8	140.2
45°	186.1	174.6	165.0	156.7	150.3	144.6	140.6	134.4	132.1	126.7	124.4
47.5°	169.3	158.6	149.4	141.5	135.3	131.6	125.6	120.8	117.0	113.7	110.8
50°	157.3	148.3	139.4	132.4	126.9	121.5	115.4	113.0	107.0	105.3	103.7
52.5°	146.3	137.8	129.7	122.8	117.2	112.0	106.6	103.5	99.5	97.8	96.6
55°	130.9	122.8	115.0	108.9	103.4	98.0	94.7	90.7	88.9	87.6	86.1
57.5°	115.5	108.2	102.2	96.0	90.4	86.2	82.3	80.0	78.1	76.4	74.6
60°	105.7	98.7	93.4	87.6	81.9	78.4	75.4	72.6	70.4	67.8	67.0
62.5°	95.4	89.2	84.3	78.7	73.7	70.5	67.7	65.1	62.4	58.6	57.6
65°	81.1	76.3	71.1	66.4	62.0	58.9	54.8	51.9	50.7	50.4	50.2
67.5°	68.2	63.7	59.2	54.5	50.5	47.5	45.4	45.0	44.2	44.0	43.5
70°	59.6	55.4	51.0	46.5	42.6	42.1	41.3	40.5	39.6	39.3	38.9
72.5°	51.9	47.5	43.0	39.5	37.8	37.2	36.4	35.6	35.1	34.7	34.5
75°	39.8	35.7	32.8	31.5	30.6	30.0	28.9	28.4	28.0	27.4	27.2
77.5°	28.7	26.3	25.0	24.2	23.2	22.7	22.0	21.4	21.0	21.0	20.6
80°	21.9	20.7	19.8	18.7	18.3	17.6	17.4	16.9	17.0	16.5	16.5
82.5°	17.0	15.6	14.8	14.3	13.9	13.3	13.1	12.9	12.9	12.5	12.5
85°	8.7	8.3	8.0	7.6	7.6	7.0	7.3	7.0	7.0	6.7	6.5
87.5°	4.4	4.6	4.6	4.8	5.1	5.2	5.4	5.4	5.5	5.7	5.7
90°	8.0	9.6	10.9	12.2	13.5	14.9	15.7	16.6	17.4	18.2	18.8
92.5°	14.3	14.6	15.3	16.0	16.6	17.3	17.7	18.1	18.6	19.0	19.3
95°	26.6	24.4	25.6	26.7	27.9	29.0	29.8	30.7	31.6	32.4	32.7
97.5°	34.5	28.1	30.8	33.5	36.2	38.9	39.5	40.2	40.8	41.5	41.9
100°	41.1	31.2	34.0	36.9	39.6	42.5	43.8	45.1	46.4	47.8	48.6
102.5°	151.9	137.8	114.2	90.7	67.2	43.6	45.3	47.0	48.8	50.5	51.6
105°	246.2	226.1	180.9	135.7	90.6	45.4	47.2	49.1	50.9	52.7	54.0
107.5°	305.4	280.3	226.1	171.9	117.7	63.6	61.7	59.8	58.0	56.2	55.6
110°	343.7	321.6	273.8	225.9	178.1	130.3	113.7	97.2	80.6	64.1	56.2



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	380.3	375.9	364.1	352.3	340.5	328.6	268.3	208.0	147.6	87.2	57.3
115°	439.4	442.9	447.0	451.2	455.3	459.4	382.8	306.2	229.6	153.0	108.7
117.5°	494.5	497.5	500.3	503.2	506.1	508.8	490.3	471.8	453.3	434.7	405.9
120°	531.2	533.9	536.9	539.8	542.8	545.8	547.8	549.8	551.8	553.8	543.6
122.5°	565.0	567.9	571.2	574.5	577.7	581.0	582.1	583.3	584.5	585.7	584.2
125°	614.0	616.6	619.8	622.9	626.1	629.2	630.4	631.5	632.7	633.8	634.6
127.5°	660.9	663.2	665.6	668.0	670.3	672.7	674.3	676.0	677.8	679.5	680.3
130°	691.1	693.4	695.2	697.0	698.9	700.7	702.5	704.3	706.1	707.9	708.8
132.5°	719.3	721.4	723.3	725.0	726.8	728.6	730.3	731.8	733.4	734.9	735.6
135°	759.7	761.7	763.2	764.8	766.2	767.7	769.3	771.0	772.7	774.3	774.9
137.5°	795.7	797.4	799.1	800.8	802.5	804.2	805.8	807.4	809.0	810.7	811.2
140°	819.1	820.8	822.6	824.3	826.2	828.0	829.5	831.0	832.5	834.0	834.3
142.5°	840.1	841.7	843.8	845.9	848.0	850.0	851.4	852.7	854.1	855.5	855.7
145°	868.3	869.6	872.5	875.2	878.1	880.8	882.0	883.2	884.4	885.5	885.7
147.5°	895.8	896.8	899.6	902.5	905.2	908.0	908.8	909.7	910.5	911.4	911.5
150°	912.7	913.5	916.2	918.8	921.5	924.1	925.0	926.0	927.1	928.1	928.1
152.5°	928.3	928.9	931.4	933.9	936.5	939.0	940.0	940.9	941.9	942.9	942.9
155°	950.9	951.1	953.1	955.1	957.1	959.0	960.0	961.1	962.1	963.0	962.9
157.5°	970.1	970.2	971.6	973.0	974.4	975.8	976.9	978.0	979.1	980.2	980.2
160°	981.9	981.9	982.8	983.9	984.9	985.9	986.8	987.8	988.9	989.9	989.8
162.5°	991.4	991.3	992.2	993.0	993.9	994.8	995.9	997.0	998.2	999.3	999.1
165°	1004.2	1004.0	1004.4	1004.9	1005.5	1006.0	1007.1	1008.3	1009.4	1010.6	1010.6
167.5°	1013.7	1013.5	1014.0	1014.4	1014.9	1015.4	1016.5	1017.7	1018.8	1020.0	1019.8
170°	1019.1	1018.8	1019.1	1019.5	1019.8	1020.1	1021.2	1022.5	1023.6	1024.7	1024.6
172.5°	1022.7	1022.4	1022.7	1023.0	1023.4	1023.7	1024.8	1026.0	1027.2	1028.3	1028.2
175°	1026.6	1026.2	1026.5	1026.9	1027.2	1027.5	1028.7	1029.9	1031.0	1032.2	1031.9
177.5°	1028.3	1027.9	1028.1	1028.2	1028.3	1028.4	1029.4	1030.3	1031.3	1032.2	1032.0
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	511.8	512.1	511.7	511.9	511.7	512.1	511.8	513.5	513.7	514.0	513.7
5°	476.9	474.7	474.3	473.8	474.3	474.7	476.9	477.8	478.6	480.0	482.7
7.5°	435.2	434.9	433.9	432.6	433.9	434.9	435.2	438.4	440.9	443.8	449.1
10°	408.4	407.4	407.2	405.9	407.2	407.4	408.4	412.5	415.4	419.5	426.7
12.5°	376.9	371.0	370.4	367.1	370.4	371.0	376.9	382.2	390.2	394.1	401.8
15°	321.0	319.8	316.1	313.7	316.1	319.8	321.0	325.4	328.3	339.1	351.5
17.5°	288.9	285.3	284.1	283.6	284.1	285.3	288.9	291.1	295.3	301.0	308.4
20°	268.3	265.1	264.5	264.1	264.5	265.1	268.3	270.9	274.3	280.4	288.1
22.5°	254.1	250.6	249.2	248.1	249.2	250.6	254.1	256.1	259.2	263.9	269.2
25°	229.8	228.5	227.8	227.4	227.8	228.5	229.8	231.7	234.6	241.2	246.7
27.5°	210.8	208.0	207.4	206.4	207.4	208.0	210.8	214.1	217.2	220.1	225.1
30°	200.0	199.1	197.8	196.7	197.8	199.1	200.0	201.7	203.7	208.7	213.5
32.5°	187.3	186.5	185.3	184.8	185.3	186.5	187.3	189.6	193.8	196.9	200.3
35°	173.2	170.6	169.4	167.8	169.4	170.6	173.2	175.0	176.7	179.3	185.6
37.5°	158.2	156.9	155.3	155.9	155.3	156.9	158.2	159.0	162.5	166.2	168.8
40°	146.7	145.8	145.4	145.2	145.4	145.8	146.7	149.1	153.4	155.0	159.1
42.5°	137.5	134.9	134.0	134.0	134.0	134.9	137.5	140.2	142.8	145.5	149.8
45°	123.5	121.2	119.4	119.6	119.4	121.2	123.5	124.4	126.7	132.1	134.4
47.5°	109.3	109.2	108.1	108.4	108.1	109.2	109.3	110.8	113.7	117.0	120.8
50°	102.4	101.3	100.5	100.8	100.5	101.3	102.4	103.7	105.3	107.0	113.0
52.5°	95.9	94.9	94.3	95.1	94.3	94.9	95.9	96.6	97.8	99.5	103.5
55°	85.2	84.1	83.9	83.7	83.9	84.1	85.2	86.1	87.6	88.9	90.7
57.5°	73.2	72.5	71.3	70.9	71.3	72.5	73.2	74.6	76.4	78.1	80.0
60°	64.7	63.2	61.3	61.1	61.3	63.2	64.7	67.0	67.8	70.4	72.6
62.5°	56.7	56.5	56.1	56.1	56.1	56.5	56.7	57.6	58.6	62.4	65.1
65°	49.8	49.7	49.8	50.0	49.8	49.7	49.8	50.2	50.4	50.7	51.9
67.5°	43.4	43.0	42.7	42.9	42.7	43.0	43.4	43.5	44.0	44.2	45.0
70°	38.5	38.3	38.2	38.2	38.2	38.3	38.5	38.9	39.3	39.6	40.5
72.5°	33.8	33.8	33.6	33.4	33.6	33.8	33.8	34.5	34.7	35.1	35.6
75°	27.1	26.7	26.7	26.7	26.7	26.7	27.1	27.2	27.4	28.0	28.4
77.5°	20.6	20.4	20.2	20.1	20.2	20.4	20.6	20.6	21.0	21.0	21.4
80°	16.3	16.1	15.9	15.9	15.9	16.1	16.3	16.5	16.5	17.0	16.9
82.5°	12.5	12.2	12.2	12.1	12.2	12.2	12.5	12.5	12.5	12.9	12.9
85°	6.7	6.8	6.7	7.0	6.7	6.8	6.7	6.5	6.7	7.0	7.0
87.5°	5.8	5.7	5.9	5.8	5.9	5.7	5.8	5.7	5.7	5.5	5.4
90°	19.1	19.4	19.8	20.1	19.8	19.4	19.1	18.8	18.2	17.4	16.6
92.5°	19.5	19.7	19.9	20.1	19.9	19.7	19.5	19.3	19.0	18.6	18.1
95°	32.5	32.4	32.2	32.0	32.2	32.4	32.5	32.7	32.4	31.6	30.7
97.5°	42.2	42.3	42.6	42.7	42.6	42.3	42.2	41.9	41.5	40.8	40.2
100°	48.9	49.2	49.6	49.9	49.6	49.2	48.9	48.6	47.8	46.4	45.1
102.5°	52.1	52.5	53.0	53.5	53.0	52.5	52.1	51.6	50.5	48.8	47.0
105°	54.6	55.3	55.9	56.6	55.9	55.3	54.6	54.0	52.7	50.9	49.1
107.5°	56.3	56.9	57.6	58.2	57.6	56.9	56.3	55.6	56.2	58.0	59.8
110°	56.8	57.5	58.1	58.9	58.1	57.5	56.8	56.2	64.1	80.6	97.2



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	57.8	58.4	58.9	59.4	58.9	58.4	57.8	57.3	87.2	147.6	208.0
115°	96.8	84.9	73.0	61.1	73.0	84.9	96.8	108.7	153.0	229.6	306.2
117.5°	366.7	327.6	288.5	249.3	288.5	327.6	366.7	405.9	434.7	453.3	471.8
120°	521.2	498.9	476.5	454.2	476.5	498.9	521.2	543.6	553.8	551.8	549.8
122.5°	579.8	575.4	571.1	566.8	571.1	575.4	579.8	584.2	585.7	584.5	583.3
125°	635.1	635.6	636.2	636.7	636.2	635.6	635.1	634.6	633.8	632.7	631.5
127.5°	680.4	680.5	680.6	680.7	680.6	680.5	680.4	680.3	679.5	677.8	676.0
130°	708.7	708.4	708.3	708.1	708.3	708.4	708.7	708.8	707.9	706.1	704.3
132.5°	735.4	735.2	735.1	734.9	735.1	735.2	735.4	735.6	734.9	733.4	731.8
135°	774.6	774.3	774.0	773.6	774.0	774.3	774.6	774.9	774.3	772.7	771.0
137.5°	810.7	810.1	809.5	808.9	809.5	810.1	810.7	811.2	810.7	809.0	807.4
140°	833.5	832.7	831.8	831.0	831.8	832.7	833.5	834.3	834.0	832.5	831.0
142.5°	854.9	854.1	853.3	852.4	853.3	854.1	854.9	855.7	855.5	854.1	852.7
145°	884.8	884.0	883.2	882.4	883.2	884.0	884.8	885.7	885.5	884.4	883.2
147.5°	910.8	910.1	909.4	908.7	909.4	910.1	910.8	911.5	911.4	910.5	909.7
150°	927.3	926.4	925.6	924.8	925.6	926.4	927.3	928.1	928.1	927.1	926.0
152.5°	941.8	940.7	939.6	938.5	939.6	940.7	941.8	942.9	942.9	941.9	940.9
155°	961.6	960.2	958.9	957.6	958.9	960.2	961.6	962.9	963.0	962.1	961.1
157.5°	978.8	977.5	976.2	975.0	976.2	977.5	978.8	980.2	980.2	979.1	978.0
160°	988.6	987.4	986.3	985.1	986.3	987.4	988.6	989.8	989.9	988.9	987.8
162.5°	997.8	996.3	994.9	993.4	994.9	996.3	997.8	999.1	999.3	998.2	997.0
165°	1009.4	1008.3	1007.1	1006.0	1007.1	1008.3	1009.4	1010.6	1010.6	1009.4	1008.3
167.5°	1018.3	1016.8	1015.4	1013.8	1015.4	1016.8	1018.3	1019.8	1020.0	1018.8	1017.7
170°	1023.1	1021.6	1020.1	1018.6	1020.1	1021.6	1023.1	1024.6	1024.7	1023.6	1022.5
172.5°	1026.6	1025.2	1023.7	1022.2	1023.7	1025.2	1026.6	1028.2	1028.3	1027.2	1026.0
175°	1030.3	1028.7	1027.0	1025.3	1027.0	1028.7	1030.3	1031.9	1032.2	1031.0	1029.9
177.5°	1030.9	1029.6	1028.4	1027.3	1028.4	1029.6	1030.9	1032.0	1032.2	1031.3	1030.3
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	512.6	514.6	517.7	519.5	522.4	524.4	525.5	527.3	528.4	532.1	536.0
5°	483.9	486.9	492.0	496.8	502.1	507.4	511.4	515.8	519.8	526.8	534.3
7.5°	451.1	455.2	463.3	470.9	480.0	487.5	494.2	501.8	508.6	518.7	529.2
10°	426.5	433.7	444.3	451.5	463.3	470.9	481.5	489.8	499.3	512.7	524.5
12.5°	405.3	414.0	422.5	432.5	443.2	455.8	467.4	478.2	489.3	503.1	517.1
15°	366.9	379.4	392.6	402.8	417.3	430.6	444.1	458.5	472.2	488.8	506.9
17.5°	317.4	332.0	354.1	371.5	388.5	401.9	418.7	436.1	452.2	472.1	492.4
20°	295.1	305.7	320.7	344.3	369.8	384.1	401.1	420.4	438.9	460.6	482.2
22.5°	277.1	286.7	298.6	317.0	345.5	365.0	382.8	402.4	423.8	445.9	469.9
25°	251.5	258.1	270.8	285.6	305.2	337.2	356.7	376.3	399.7	423.4	450.8
27.5°	232.3	238.3	246.5	260.6	275.2	298.2	329.1	350.6	373.8	400.5	428.9
30°	217.6	224.6	233.7	243.7	259.7	277.6	308.5	333.4	356.3	383.8	414.1
32.5°	206.9	212.5	220.2	230.4	243.6	260.9	285.6	315.7	338.1	367.0	398.7
35°	189.5	195.9	202.2	211.9	222.6	238.3	257.1	289.3	311.5	340.0	371.9
37.5°	175.0	179.0	186.0	193.6	205.0	216.7	232.9	261.8	285.8	313.8	346.4
40°	164.1	169.1	174.2	182.8	192.1	203.3	219.2	240.8	268.3	295.8	327.6
42.5°	153.4	159.7	165.3	171.0	181.1	192.4	205.4	223.6	251.8	277.7	308.7
45°	140.6	144.6	150.3	156.7	165.0	174.6	186.1	202.0	229.1	251.5	280.5
47.5°	125.6	131.6	135.3	141.5	149.4	158.6	169.3	183.0	204.9	225.9	252.9
50°	115.4	121.5	126.9	132.4	139.4	148.3	157.3	170.6	188.2	210.2	235.4
52.5°	106.6	112.0	117.2	122.8	129.7	137.8	146.3	158.0	173.0	193.3	217.8
55°	94.7	98.0	103.4	108.9	115.0	122.8	130.9	140.7	153.7	170.7	190.5
57.5°	82.3	86.2	90.4	96.0	102.2	108.2	115.5	124.4	134.6	150.0	167.0
60°	75.4	78.4	81.9	87.6	93.4	98.7	105.7	113.2	122.8	136.2	150.6
62.5°	67.7	70.5	73.7	78.7	84.3	89.2	95.4	103.2	111.4	123.5	136.2
65°	54.8	58.9	62.0	66.4	71.1	76.3	81.1	87.4	94.7	104.3	115.5
67.5°	45.4	47.5	50.5	54.5	59.2	63.7	68.2	73.1	79.4	86.8	95.8
70°	41.3	42.1	42.6	46.5	51.0	55.4	59.6	64.2	69.6	75.7	83.5
72.5°	36.4	37.2	37.8	39.5	43.0	47.5	51.9	55.4	60.4	65.6	71.8
75°	28.9	30.0	30.6	31.5	32.8	35.7	39.8	43.1	46.1	50.0	55.0
77.5°	22.0	22.7	23.2	24.2	25.0	26.3	28.7	31.6	34.5	36.7	40.1
80°	17.4	17.6	18.3	18.7	19.8	20.7	21.9	24.3	27.1	28.0	30.4
82.5°	13.1	13.3	13.9	14.3	14.8	15.6	17.0	17.6	19.8	21.0	22.5
85°	7.3	7.0	7.6	7.6	8.0	8.3	8.7	9.6	10.2	11.7	12.1
87.5°	5.4	5.2	5.1	4.8	4.6	4.6	4.4	4.2	4.2	4.2	4.5
90°	15.7	14.9	13.5	12.2	10.9	9.6	8.0	6.2	4.4	2.5	0.7
92.5°	17.7	17.3	16.6	16.0	15.3	14.6	14.3	14.5	14.7	14.8	15.0
95°	29.8	29.0	27.9	26.7	25.6	24.4	26.6	32.0	37.5	43.0	48.4
97.5°	39.5	38.9	36.2	33.5	30.8	28.1	34.5	49.9	65.3	80.6	96.0
100°	43.8	42.5	39.6	36.9	34.0	31.2	41.1	63.8	86.4	109.1	131.8
102.5°	45.3	43.6	67.2	90.7	114.2	137.8	151.9	156.7	161.5	166.3	171.1
105°	47.2	45.4	90.6	135.7	180.9	226.1	246.2	241.2	236.3	231.3	226.3
107.5°	61.7	63.6	117.7	171.9	226.1	280.3	305.4	301.3	297.3	293.3	289.3
110°	113.7	130.3	178.1	225.9	273.8	321.6	343.7	340.3	336.8	333.4	329.9



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	268.3	328.6	340.5	352.3	364.1	375.9	380.3	377.2	374.1	371.0	367.9
115°	382.8	459.4	455.3	451.2	447.0	442.9	439.4	436.6	433.7	431.0	428.1
117.5°	490.3	508.8	506.1	503.2	500.3	497.5	494.5	491.4	488.2	485.0	481.9
120°	547.8	545.8	542.8	539.8	536.9	533.9	531.2	528.6	526.2	523.7	521.2
122.5°	582.1	581.0	577.7	574.5	571.2	567.9	565.0	562.4	559.8	557.2	554.6
125°	630.4	629.2	626.1	622.9	619.8	616.6	614.0	611.8	609.7	607.5	605.4
127.5°	674.3	672.7	670.3	668.0	665.6	663.2	660.9	658.5	656.2	653.8	651.3
130°	702.5	700.7	698.9	697.0	695.2	693.4	691.1	688.5	685.8	683.2	680.6
132.5°	730.3	728.6	726.8	725.0	723.3	721.4	719.3	717.1	714.9	712.6	710.4
135°	769.3	767.7	766.2	764.8	763.2	761.7	759.7	757.0	754.4	751.7	749.1
137.5°	805.8	804.2	802.5	800.8	799.1	797.4	795.7	793.8	792.0	790.1	788.2
140°	829.5	828.0	826.2	824.3	822.6	820.8	819.1	817.8	816.5	815.2	813.8
142.5°	851.4	850.0	848.0	845.9	843.8	841.7	840.1	838.9	837.7	836.5	835.3
145°	882.0	880.8	878.1	875.2	872.5	869.6	868.3	868.5	868.6	868.8	868.9
147.5°	908.8	908.0	905.2	902.5	899.6	896.8	895.8	896.4	897.1	897.6	898.3
150°	925.0	924.1	921.5	918.8	916.2	913.5	912.7	913.9	915.0	916.2	917.4
152.5°	940.0	939.0	936.5	933.9	931.4	928.9	928.3	929.6	930.8	932.1	933.4
155°	960.0	959.0	957.1	955.1	953.1	951.1	950.9	952.4	953.8	955.4	956.8
157.5°	976.9	975.8	974.4	973.0	971.6	970.2	970.1	971.3	972.7	973.9	975.1
160°	986.8	985.9	984.9	983.9	982.8	981.9	981.9	982.8	983.9	984.9	985.9
162.5°	995.9	994.8	993.9	993.0	992.2	991.3	991.4	992.4	993.4	994.4	995.4
165°	1007.1	1006.0	1005.5	1004.9	1004.4	1004.0	1004.2	1005.2	1006.2	1007.2	1008.2
167.5°	1016.5	1015.4	1014.9	1014.4	1014.0	1013.5	1013.7	1014.7	1015.8	1016.8	1017.7
170°	1021.2	1020.1	1019.8	1019.5	1019.1	1018.8	1019.1	1020.1	1021.1	1022.1	1023.1
172.5°	1024.8	1023.7	1023.4	1023.0	1022.7	1022.4	1022.7	1023.7	1024.7	1025.6	1026.6
175°	1028.7	1027.5	1027.2	1026.9	1026.5	1026.2	1026.6	1027.8	1029.0	1030.1	1031.3
177.5°	1029.4	1028.4	1028.3	1028.2	1028.1	1027.9	1028.3	1029.2	1030.2	1031.1	1032.0
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	536.1	536.5	539.5	540.9	543.5	544.5	545.8	545.4	545.4	546.0	550.2
5°	537.3	541.0	546.5	551.9	557.1	561.5	564.5	567.4	568.6	573.9	578.7
7.5°	535.3	542.2	551.3	559.5	569.3	577.0	583.3	589.1	593.0	600.9	608.9
10°	532.8	542.4	552.8	563.4	576.9	587.1	597.5	605.4	608.0	619.6	626.3
12.5°	527.7	540.6	553.8	567.5	580.7	594.8	606.2	614.2	623.3	633.7	646.0
15°	520.2	535.0	552.3	569.8	588.7	605.8	618.0	631.9	641.9	653.4	664.1
17.5°	509.4	528.5	550.3	570.7	592.6	610.8	627.7	641.0	648.0	654.6	656.2
20°	500.8	521.3	547.1	571.1	593.0	614.1	630.8	641.9	643.8	643.9	634.1
22.5°	491.5	514.7	541.6	566.2	592.4	615.9	628.8	633.6	626.2	613.7	594.7
25°	474.3	501.2	532.5	560.6	589.1	611.3	615.8	607.5	581.7	554.6	520.4
27.5°	455.7	485.9	519.4	550.7	581.1	594.9	585.3	555.2	508.9	468.6	419.7
30°	442.1	476.0	508.9	543.9	572.1	578.0	556.0	511.7	457.6	396.9	348.1
32.5°	426.5	462.0	498.2	534.4	558.0	552.2	515.8	461.3	397.9	338.2	292.2
35°	404.3	440.9	480.0	516.3	531.3	506.3	451.8	380.9	316.1	260.4	228.7
37.5°	378.6	418.6	459.2	492.5	491.5	449.8	375.6	302.4	247.9	214.9	192.4
40°	360.4	400.8	444.7	472.8	460.8	406.5	326.1	257.1	217.2	190.9	174.5
42.5°	342.9	383.4	427.1	449.4	428.4	361.7	281.7	227.6	194.7	174.2	160.9
45°	313.2	356.0	396.3	408.7	371.3	297.8	227.8	188.5	166.6	151.5	142.3
47.5°	284.1	326.2	363.1	363.2	312.7	241.5	192.2	163.1	144.5	132.7	126.0
50°	266.3	306.3	337.2	332.4	275.0	214.8	171.9	146.8	131.3	122.2	115.2
52.5°	246.3	285.1	311.9	298.2	243.1	189.1	153.6	132.6	119.8	111.9	105.6
55°	217.2	251.7	270.6	249.8	198.4	157.3	129.8	113.3	103.7	97.0	91.6
57.5°	188.7	217.1	228.9	204.8	163.4	130.4	109.8	97.4	87.9	83.1	80.3
60°	170.7	195.0	203.3	176.7	142.0	114.1	97.3	85.8	78.7	75.6	72.8
62.5°	153.1	172.9	176.3	152.0	123.8	99.9	85.4	75.7	71.0	68.0	65.4
65°	127.0	141.3	139.7	120.0	98.0	79.2	68.7	62.8	59.3	55.0	50.4
67.5°	104.6	113.3	108.0	93.4	74.8	61.6	54.7	50.2	45.8	41.8	40.8
70°	90.3	95.4	89.8	76.3	61.3	51.7	46.1	40.8	38.2	37.3	35.5
72.5°	76.7	78.5	72.5	60.9	49.9	42.8	37.3	34.4	32.9	32.2	31.1
75°	57.6	56.3	51.1	42.1	34.7	29.8	28.1	27.1	26.1	25.4	24.8
77.5°	40.4	38.6	33.9	28.0	24.1	21.9	20.8	20.2	19.8	19.4	18.8
80°	30.4	29.1	24.5	20.0	18.3	17.2	16.6	15.9	15.9	15.6	15.0
82.5°	22.3	20.8	16.7	14.7	13.8	13.0	12.6	12.2	12.1	12.1	11.7
85°	11.7	9.5	8.3	8.0	7.4	7.0	7.3	6.8	6.8	6.8	6.7
87.5°	4.1	3.7	3.9	4.2	4.6	4.8	5.0	5.2	5.6	5.6	6.0
90°	2.5	4.4	6.2	8.0	9.6	10.9	12.2	13.5	14.9	15.7	16.6
92.5°	14.8	14.7	14.5	14.3	14.6	15.3	16.0	16.6	17.3	17.7	18.1
95°	43.0	37.5	32.0	26.6	24.4	25.6	26.7	27.9	29.0	29.8	30.7
97.5°	80.6	65.3	49.9	34.5	28.1	30.8	33.5	36.2	38.9	39.5	40.2
100°	109.1	86.4	63.8	41.1	31.2	34.0	36.9	39.6	42.5	43.8	45.1
102.5°	166.3	161.5	156.7	151.9	137.8	114.2	90.7	67.2	43.6	45.3	47.0
105°	231.3	236.3	241.2	246.2	226.1	180.9	135.7	90.6	45.4	47.2	49.1
107.5°	293.3	297.3	301.3	305.4	280.3	226.1	171.9	117.7	63.6	61.7	59.8
110°	333.4	336.8	340.3	343.7	321.6	273.8	225.9	178.1	130.3	113.7	97.2





TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	371.0	374.1	377.2	380.3	375.9	364.1	352.3	340.5	328.6	268.3	208.0
115°	431.0	433.7	436.6	439.4	442.9	447.0	451.2	455.3	459.4	382.8	306.2
117.5°	485.0	488.2	491.4	494.5	497.5	500.3	503.2	506.1	508.8	490.3	471.8
120°	523.7	526.2	528.6	531.2	533.9	536.9	539.8	542.8	545.8	547.8	549.8
122.5°	557.2	559.8	562.4	565.0	567.9	571.2	574.5	577.7	581.0	582.1	583.3
125°	607.5	609.7	611.8	614.0	616.6	619.8	622.9	626.1	629.2	630.4	631.5
127.5°	653.8	656.2	658.5	660.9	663.2	665.6	668.0	670.3	672.7	674.3	676.0
130°	683.2	685.8	688.5	691.1	693.4	695.2	697.0	698.9	700.7	702.5	704.3
132.5°	712.6	714.9	717.1	719.3	721.4	723.3	725.0	726.8	728.6	730.3	731.8
135°	751.7	754.4	757.0	759.7	761.7	763.2	764.8	766.2	767.7	769.3	771.0
137.5°	790.1	792.0	793.8	795.7	797.4	799.1	800.8	802.5	804.2	805.8	807.4
140°	815.2	816.5	817.8	819.1	820.8	822.6	824.3	826.2	828.0	829.5	831.0
142.5°	836.5	837.7	838.9	840.1	841.7	843.8	845.9	848.0	850.0	851.4	852.7
145°	868.8	868.6	868.5	868.3	869.6	872.5	875.2	878.1	880.8	882.0	883.2
147.5°	897.6	897.1	896.4	895.8	896.8	899.6	902.5	905.2	908.0	908.8	909.7
150°	916.2	915.0	913.9	912.7	913.5	916.2	918.8	921.5	924.1	925.0	926.0
152.5°	932.1	930.8	929.6	928.3	928.9	931.4	933.9	936.5	939.0	940.0	940.9
155°	955.4	953.8	952.4	950.9	951.1	953.1	955.1	957.1	959.0	960.0	961.1
157.5°	973.9	972.7	971.3	970.1	970.2	971.6	973.0	974.4	975.8	976.9	978.0
160°	984.9	983.9	982.8	981.9	981.9	982.8	983.9	984.9	985.9	986.8	987.8
162.5°	994.4	993.4	992.4	991.4	991.3	992.2	993.0	993.9	994.8	995.9	997.0
165°	1007.2	1006.2	1005.2	1004.2	1004.0	1004.4	1004.9	1005.5	1006.0	1007.1	1008.3
167.5°	1016.8	1015.8	1014.7	1013.7	1013.5	1014.0	1014.4	1014.9	1015.4	1016.5	1017.7
170°	1022.1	1021.1	1020.1	1019.1	1018.8	1019.1	1019.5	1019.8	1020.1	1021.2	1022.5
172.5°	1025.6	1024.7	1023.7	1022.7	1022.4	1022.7	1023.0	1023.4	1023.7	1024.8	1026.0
175°	1030.1	1029.0	1027.8	1026.6	1026.2	1026.5	1026.9	1027.2	1027.5	1028.7	1029.9
177.5°	1031.1	1030.2	1029.2	1028.3	1027.9	1028.1	1028.2	1028.3	1028.4	1029.4	1030.3
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	551.6	553.6	554.5	554.5	555.5	555.1	554.6
5°	583.3	586.9	587.7	590.9	593.4	592.6	593.0
7.5°	614.9	620.5	626.1	628.7	629.1	630.6	631.1
10°	634.3	639.0	647.6	646.4	652.8	656.6	650.4
12.5°	653.0	659.3	665.3	666.9	670.6	671.8	669.4
15°	669.8	673.2	673.5	672.6	673.8	672.8	669.3
17.5°	654.1	648.7	637.7	632.5	628.4	622.3	619.9
20°	628.0	612.0	593.5	586.1	577.5	560.4	564.5
22.5°	571.7	553.6	535.0	513.4	503.0	486.9	485.9
25°	484.1	452.8	418.3	394.3	380.2	364.1	357.0
27.5°	376.4	337.0	308.8	294.5	281.4	268.7	268.2
30°	305.6	276.0	254.1	241.9	233.9	228.5	229.7
32.5°	257.6	237.3	222.5	212.4	206.5	202.4	202.4
35°	210.6	196.7	187.2	183.0	178.7	175.8	175.9
37.5°	180.2	171.9	166.6	161.9	159.2	157.8	156.9
40°	164.6	157.8	153.7	150.9	148.7	146.7	146.3
42.5°	152.4	146.7	142.6	140.4	138.4	136.9	136.6
45°	135.2	130.5	126.9	124.4	123.5	122.2	122.2
47.5°	120.3	115.7	112.8	111.3	109.7	108.8	108.8
50°	110.2	106.6	104.1	103.1	101.8	101.3	101.1
52.5°	101.2	98.5	96.7	96.0	95.5	94.8	94.9
55°	88.9	87.4	86.7	86.1	85.2	84.1	84.8
57.5°	78.6	77.3	75.3	73.5	72.7	71.9	72.2
60°	71.3	68.7	66.1	64.1	63.5	61.9	61.9
62.5°	62.1	58.5	55.3	54.1	53.6	52.8	52.7
65°	47.8	46.3	45.6	44.8	44.4	44.4	44.1
67.5°	39.6	39.0	38.2	38.0	37.7	37.5	37.4
70°	35.0	34.2	33.9	33.7	33.3	33.5	32.9
72.5°	30.6	30.0	29.9	29.4	29.2	29.2	28.8
75°	24.1	24.1	23.9	23.7	23.3	23.2	23.3
77.5°	18.5	18.6	18.3	18.2	18.2	18.2	18.0
80°	14.8	15.0	14.8	14.6	14.4	14.6	14.4
82.5°	11.7	11.4	11.4	11.3	11.3	11.3	11.2
85°	6.7	6.8	6.7	6.5	6.5	6.5	6.7
87.5°	6.0	6.2	6.3	6.4	6.4	6.4	6.4
90°	17.4	18.2	18.8	19.1	19.4	19.8	20.1
92.5°	18.6	19.0	19.3	19.5	19.7	19.9	20.1
95°	31.6	32.4	32.7	32.5	32.4	32.2	32.0
97.5°	40.8	41.5	41.9	42.2	42.3	42.6	42.7
100°	46.4	47.8	48.6	48.9	49.2	49.6	49.9
102.5°	48.8	50.5	51.6	52.1	52.5	53.0	53.5
105°	50.9	52.7	54.0	54.6	55.3	55.9	56.6
107.5°	58.0	56.2	55.6	56.3	56.9	57.6	58.2
110°	80.6	64.1	56.2	56.8	57.5	58.1	58.9



TEST NUMBER: P331633-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	147.6	87.2	57.3	57.8	58.4	58.9	59.4
115°	229.6	153.0	108.7	96.8	84.9	73.0	61.1
117.5°	453.3	434.7	405.9	366.7	327.6	288.5	249.3
120°	551.8	553.8	543.6	521.2	498.9	476.5	454.2
122.5°	584.5	585.7	584.2	579.8	575.4	571.1	566.8
125°	632.7	633.8	634.6	635.1	635.6	636.2	636.7
127.5°	677.8	679.5	680.3	680.4	680.5	680.6	680.7
130°	706.1	707.9	708.8	708.7	708.4	708.3	708.1
132.5°	733.4	734.9	735.6	735.4	735.2	735.1	734.9
135°	772.7	774.3	774.9	774.6	774.3	774.0	773.6
137.5°	809.0	810.7	811.2	810.7	810.1	809.5	808.9
140°	832.5	834.0	834.3	833.5	832.7	831.8	831.0
142.5°	854.1	855.5	855.7	854.9	854.1	853.3	852.4
145°	884.4	885.5	885.7	884.8	884.0	883.2	882.4
147.5°	910.5	911.4	911.5	910.8	910.1	909.4	908.7
150°	927.1	928.1	928.1	927.3	926.4	925.6	924.8
152.5°	941.9	942.9	942.9	941.8	940.7	939.6	938.5
155°	962.1	963.0	962.9	961.6	960.2	958.9	957.6
157.5°	979.1	980.2	980.2	978.8	977.5	976.2	975.0
160°	988.9	989.9	989.8	988.6	987.4	986.3	985.1
162.5°	998.2	999.3	999.1	997.8	996.3	994.9	993.4
165°	1009.4	1010.6	1010.6	1009.4	1008.3	1007.1	1006.0
167.5°	1018.8	1020.0	1019.8	1018.3	1016.8	1015.4	1013.8
170°	1023.6	1024.7	1024.6	1023.1	1021.6	1020.1	1018.6
172.5°	1027.2	1028.3	1028.2	1026.6	1025.2	1023.7	1022.2
175°	1031.0	1032.2	1031.9	1030.3	1028.7	1027.0	1025.3
177.5°	1031.3	1032.2	1032.0	1030.9	1029.6	1028.4	1027.3
180°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1

(END OF REPORT)