

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331634-930

Luminaire Tested: **S122RDIP-S290D925U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331634-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D925U930-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3620.9 lumens  
Efficiency: N/A  
Efficacy: 97.1 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26				
1	93	89	85	82	82	79	76	74	61	60	58	45	44	43	30	30	29	22				
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19				
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22	17				
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	21	19	15				
5	65	54	47	41	58	49	43	38	39	34	31	29	26	24	20	18	17	13				
6	60	49	41	36	54	44	38	33	35	30	27	26	23	21	18	17	15	12				
7	56	44	37	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11				
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12	10				
9	48	37	30	25	43	33	27	23	27	22	19	20	17	15	15	13	11	9				
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8606	8606	8606	8606
5°	9611	8660	7679	8660
10°	10663	8599	6655	8599
15°	11188	8473	5244	8473
20°	9699	8285	4538	8285
25°	6360	8031	4051	8031
30°	4282	7720	3667	7720
35°	3467	7330	3307	7330
40°	3084	6905	3060	6905
45°	2790	6405	2731	6405
50°	2539	5913	2532	5913
55°	2387	5362	2356	5362
60°	1999	4863	1973	4863
65°	1685	4413	1910	4413
70°	1553	3942	1803	3942
75°	1454	3431	1666	3431
80°	1339	2827	1478	2827
85°	1241	2242	1297	2242



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.5	1.4
10°-20°	140.8	3.9
20°-30°	181.4	5.0
30°-40°	172.4	4.8
40°-50°	147.7	4.1
50°-60°	112.5	3.1
60°-70°	71.1	2.0
70°-80°	35.5	1.0
80°-90°	13.1	0.4
90°-100°	61.1	1.7
100°-110°	189.8	5.2
110°-120°	324.3	9.0
120°-130°	426.5	11.8
130°-140°	478.7	13.2
140°-150°	469.4	13.0
150°-160°	393.7	10.9
160°-170°	261.1	7.2
170°-180°	91.3	2.5
0°-30°	372.7	10.3
0°-40°	545.1	15.1
0°-60°	805.3	22.2
0°-90°	925.0	25.5
90°-120°	575.2	15.9
90°-150°	1949.8	53.8
90°-180°	2696.0	74.5
0°-180°	3620.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	533	533	533	533	533	
5°	593	534	474	534	593	59
15°	669	507	314	507	669	181
25°	357	451	227	451	357	169
35°	176	372	168	372	176	113
45°	122	280	120	280	122	95
55°	85	190	84	190	85	74
65°	44	116	50	116	44	45
75°	23	55	27	55	23	25
85°	7	12	7	12	7	8
90°	28	1	28	1	28	12
95°	50	42	50	42	50	56
105°	181	175	181	175	181	190
115°	326	326	326	326	326	321
125°	475	474	475	474	475	424
135°	620	613	620	613	620	477
145°	752	744	752	744	752	469
155°	857	850	857	850	857	394
165°	926	925	926	925	926	261
175°	959	962	959	962	959	91
180°	964	964	964	964	964	



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	554.6	555.1	555.5	554.5	554.5	553.6	551.6	550.2	546.0	545.4	545.4
5°	593.0	592.6	593.4	590.9	587.7	586.9	583.3	578.7	573.9	568.6	567.4
7.5°	631.1	630.6	629.1	628.7	626.1	620.5	614.9	608.9	600.9	593.0	589.1
10°	650.4	656.6	652.8	646.4	647.6	639.0	634.3	626.3	619.6	608.0	605.4
12.5°	669.4	671.8	670.6	666.9	665.3	659.3	653.0	646.0	633.7	623.3	614.2
15°	669.3	672.8	673.8	672.6	673.5	673.2	669.8	664.1	653.4	641.9	631.9
17.5°	619.9	622.3	628.4	632.5	637.7	648.7	654.1	656.2	654.6	648.0	641.0
20°	564.5	560.4	577.5	586.1	593.5	612.0	628.0	634.1	643.9	643.8	641.9
22.5°	485.9	486.9	503.0	513.4	535.0	553.6	571.7	594.7	613.7	626.2	633.6
25°	357.0	364.1	380.2	394.3	418.3	452.8	484.1	520.4	554.6	581.7	607.5
27.5°	268.2	268.7	281.4	294.5	308.8	337.0	376.4	419.7	468.6	508.9	555.2
30°	229.7	228.5	233.9	241.9	254.1	276.0	305.6	348.1	396.9	457.6	511.7
32.5°	202.4	202.4	206.5	212.4	222.5	237.3	257.6	292.2	338.2	397.9	461.3
35°	175.9	175.8	178.7	183.0	187.2	196.7	210.6	228.7	260.4	316.1	380.9
37.5°	156.9	157.8	159.2	161.9	166.6	171.9	180.2	192.4	214.9	247.9	302.4
40°	146.3	146.7	148.7	150.9	153.7	157.8	164.6	174.5	190.9	217.2	257.1
42.5°	136.6	136.9	138.4	140.4	142.6	146.7	152.4	160.9	174.2	194.7	227.6
45°	122.2	122.2	123.5	124.4	126.9	130.5	135.2	142.3	151.5	166.6	188.5
47.5°	108.8	108.8	109.7	111.3	112.8	115.7	120.3	126.0	132.7	144.5	163.1
50°	101.1	101.3	101.8	103.1	104.1	106.6	110.2	115.2	122.2	131.3	146.8
52.5°	94.9	94.8	95.5	96.0	96.7	98.5	101.2	105.6	111.9	119.8	132.6
55°	84.8	84.1	85.2	86.1	86.7	87.4	88.9	91.6	97.0	103.7	113.3
57.5°	72.2	71.9	72.7	73.5	75.3	77.3	78.6	80.3	83.1	87.9	97.4
60°	61.9	61.9	63.5	64.1	66.1	68.7	71.3	72.8	75.6	78.7	85.8
62.5°	52.7	52.8	53.6	54.1	55.3	58.5	62.1	65.4	68.0	71.0	75.7
65°	44.1	44.4	44.4	44.8	45.6	46.3	47.8	50.4	55.0	59.3	62.8
67.5°	37.4	37.5	37.7	38.0	38.2	39.0	39.6	40.8	41.8	45.8	50.2
70°	32.9	33.5	33.3	33.7	33.9	34.2	35.0	35.5	37.3	38.2	40.8
72.5°	28.8	29.2	29.2	29.4	29.9	30.0	30.6	31.1	32.2	32.9	34.4
75°	23.3	23.2	23.3	23.7	23.9	24.1	24.1	24.8	25.4	26.1	27.1
77.5°	18.0	18.2	18.2	18.2	18.3	18.6	18.5	18.8	19.4	19.8	20.2
80°	14.4	14.6	14.4	14.6	14.8	15.0	14.8	15.0	15.6	15.9	15.9
82.5°	11.2	11.3	11.3	11.3	11.4	11.4	11.7	11.7	12.1	12.1	12.2
85°	6.7	6.5	6.5	6.5	6.7	6.8	6.7	6.7	6.8	6.8	6.8
87.5°	7.9	8.0	8.0	7.9	7.9	7.9	8.0	8.2	8.2	8.4	7.4
90°	27.6	27.5	27.3	27.1	26.9	27.1	27.4	27.7	28.1	28.5	24.5
92.5°	26.3	26.3	26.3	26.3	26.3	26.2	26.1	26.0	25.9	25.8	24.9
95°	50.5	50.8	51.2	51.5	51.9	52.1	52.1	52.1	52.1	52.1	51.7
97.5°	87.4	87.4	87.5	87.5	87.6	87.6	87.6	87.6	87.6	87.6	86.8
100°	111.5	111.6	111.9	112.0	112.2	112.3	112.3	112.3	112.3	112.3	111.8
102.5°	138.8	139.0	139.2	139.3	139.5	139.6	139.4	139.3	139.1	139.0	138.3
105°	180.6	180.6	180.6	180.6	180.6	180.4	180.1	179.7	179.4	179.0	178.6
107.5°	220.0	220.9	221.7	222.5	223.3	223.6	223.6	223.4	223.2	223.1	223.1
110°	250.6	251.1	251.7	252.3	252.7	253.1	253.1	253.1	253.1	253.1	253.1



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	279.9	280.3	280.7	281.1	281.4	281.9	282.3	282.7	283.2	283.6	283.8
115°	325.5	326.0	326.5	327.1	327.6	328.0	328.2	328.3	328.6	328.7	329.1
117.5°	368.9	369.4	370.0	370.6	371.0	371.5	372.0	372.4	372.8	373.3	374.3
120°	399.5	400.1	400.6	401.1	401.7	401.9	401.9	401.9	401.9	401.9	403.4
122.5°	429.4	429.8	430.2	430.6	431.0	431.5	431.9	432.3	432.8	433.2	434.2
125°	475.2	475.3	475.5	475.7	475.9	476.2	476.8	477.4	477.8	478.4	479.0
127.5°	516.8	517.4	518.0	518.5	519.1	519.8	520.4	521.1	521.7	522.4	523.0
130°	546.7	547.5	548.2	548.9	549.7	550.2	550.6	550.9	551.3	551.6	552.0
132.5°	575.4	576.0	576.6	577.2	577.7	578.4	579.2	580.0	580.8	581.6	581.5
135°	620.0	620.5	621.1	621.6	622.2	622.5	622.7	622.9	623.1	623.2	622.9
137.5°	660.3	661.0	661.8	662.5	663.2	663.7	663.8	664.0	664.1	664.2	663.8
140°	688.4	689.1	689.7	690.5	691.2	691.6	691.6	691.6	691.6	691.6	690.7
142.5°	713.7	714.4	715.2	715.9	716.6	716.9	716.7	716.6	716.5	716.3	715.7
145°	751.8	752.5	753.3	754.0	754.7	755.0	754.8	754.6	754.4	754.2	753.2
147.5°	785.8	786.5	787.2	787.9	788.6	788.7	788.3	787.9	787.5	787.1	786.4
150°	808.0	808.5	809.0	809.6	810.1	810.1	809.6	809.0	808.5	808.0	807.2
152.5°	828.8	829.5	830.1	830.8	831.5	831.5	830.8	830.1	829.5	828.8	827.9
155°	856.7	857.3	857.9	858.3	858.9	858.8	857.9	857.0	856.1	855.1	854.6
157.5°	880.8	881.7	882.6	883.5	884.3	884.1	882.9	881.7	880.4	879.2	878.9
160°	895.8	896.5	897.2	898.0	898.7	898.5	897.4	896.3	895.3	894.1	894.0
162.5°	908.8	909.7	910.5	911.4	912.3	912.1	910.9	909.6	908.4	907.2	907.0
165°	925.9	926.8	927.7	928.6	929.5	929.4	928.1	926.8	925.5	924.3	924.3
167.5°	939.9	940.9	941.8	942.7	943.6	943.5	942.2	940.9	939.7	938.4	938.5
170°	947.1	948.1	949.3	950.3	951.4	951.3	950.1	948.8	947.5	946.2	946.4
172.5°	952.9	954.0	955.1	956.2	957.2	957.2	955.9	954.6	953.4	952.1	952.3
175°	959.3	960.3	961.4	962.5	963.6	963.5	962.2	961.0	959.7	958.5	958.8
177.5°	962.2	963.0	963.9	964.8	965.6	965.6	964.8	963.9	963.0	962.2	962.5
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	545.8	544.5	543.5	540.9	539.5	536.5	536.1	536.0	532.1	528.4	527.3
5°	564.5	561.5	557.1	551.9	546.5	541.0	537.3	534.3	526.8	519.8	515.8
7.5°	583.3	577.0	569.3	559.5	551.3	542.2	535.3	529.2	518.7	508.6	501.8
10°	597.5	587.1	576.9	563.4	552.8	542.4	532.8	524.5	512.7	499.3	489.8
12.5°	606.2	594.8	580.7	567.5	553.8	540.6	527.7	517.1	503.1	489.3	478.2
15°	618.0	605.8	588.7	569.8	552.3	535.0	520.2	506.9	488.8	472.2	458.5
17.5°	627.7	610.8	592.6	570.7	550.3	528.5	509.4	492.4	472.1	452.2	436.1
20°	630.8	614.1	593.0	571.1	547.1	521.3	500.8	482.2	460.6	438.9	420.4
22.5°	628.8	615.9	592.4	566.2	541.6	514.7	491.5	469.9	445.9	423.8	402.4
25°	615.8	611.3	589.1	560.6	532.5	501.2	474.3	450.8	423.4	399.7	376.3
27.5°	585.3	594.9	581.1	550.7	519.4	485.9	455.7	428.9	400.5	373.8	350.6
30°	556.0	578.0	572.1	543.9	508.9	476.0	442.1	414.1	383.8	356.3	333.4
32.5°	515.8	552.2	558.0	534.4	498.2	462.0	426.5	398.7	367.0	338.1	315.7
35°	451.8	506.3	531.3	516.3	480.0	440.9	404.3	371.9	340.0	311.5	289.3
37.5°	375.6	449.8	491.5	492.5	459.2	418.6	378.6	346.4	313.8	285.8	261.8
40°	326.1	406.5	460.8	472.8	444.7	400.8	360.4	327.6	295.8	268.3	240.8
42.5°	281.7	361.7	428.4	449.4	427.1	383.4	342.9	308.7	277.7	251.8	223.6
45°	227.8	297.8	371.3	408.7	396.3	356.0	313.2	280.5	251.5	229.1	202.0
47.5°	192.2	241.5	312.7	363.2	363.1	326.2	284.1	252.9	225.9	204.9	183.0
50°	171.9	214.8	275.0	332.4	337.2	306.3	266.3	235.4	210.2	188.2	170.6
52.5°	153.6	189.1	243.1	298.2	311.9	285.1	246.3	217.8	193.3	173.0	158.0
55°	129.8	157.3	198.4	249.8	270.6	251.7	217.2	190.5	170.7	153.7	140.7
57.5°	109.8	130.4	163.4	204.8	228.9	217.1	188.7	167.0	150.0	134.6	124.4
60°	97.3	114.1	142.0	176.7	203.3	195.0	170.7	150.6	136.2	122.8	113.2
62.5°	85.4	99.9	123.8	152.0	176.3	172.9	153.1	136.2	123.5	111.4	103.2
65°	68.7	79.2	98.0	120.0	139.7	141.3	127.0	115.5	104.3	94.7	87.4
67.5°	54.7	61.6	74.8	93.4	108.0	113.3	104.6	95.8	86.8	79.4	73.1
70°	46.1	51.7	61.3	76.3	89.8	95.4	90.3	83.5	75.7	69.6	64.2
72.5°	37.3	42.8	49.9	60.9	72.5	78.5	76.7	71.8	65.6	60.4	55.4
75°	28.1	29.8	34.7	42.1	51.1	56.3	57.6	55.0	50.0	46.1	43.1
77.5°	20.8	21.9	24.1	28.0	33.9	38.6	40.4	40.1	36.7	34.5	31.6
80°	16.6	17.2	18.3	20.0	24.5	29.1	30.4	30.4	28.0	27.1	24.3
82.5°	12.6	13.0	13.8	14.7	16.7	20.8	22.3	22.5	21.0	19.8	17.6
85°	7.3	7.0	7.4	8.0	8.3	9.5	11.7	12.1	11.7	10.2	9.6
87.5°	6.6	6.0	5.2	4.4	4.2	3.8	4.2	4.5	4.3	4.3	4.4
90°	20.5	16.6	12.6	9.5	7.3	5.1	3.0	0.8	3.0	5.1	7.3
92.5°	24.0	23.1	22.1	20.9	19.2	17.7	16.1	14.5	16.1	17.7	19.2
95°	51.4	51.0	50.6	49.6	47.7	45.9	44.1	42.3	44.1	45.9	47.7
97.5°	86.2	85.5	84.8	83.6	82.1	80.5	78.9	77.3	78.9	80.5	82.1
100°	111.2	110.6	110.1	109.1	107.7	106.2	104.8	103.3	104.8	106.2	107.7
102.5°	137.6	136.9	136.2	135.3	134.1	133.0	131.8	130.7	131.8	133.0	134.1
105°	178.3	177.9	177.6	177.1	176.6	176.0	175.5	175.0	175.5	176.0	176.6
107.5°	223.1	223.1	223.1	222.7	221.9	221.1	220.3	219.5	220.3	221.1	221.9
110°	253.1	253.1	253.1	252.5	251.4	250.3	249.2	248.2	249.2	250.3	251.4





TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	283.9	284.1	284.2	283.7	282.7	281.6	280.5	279.4	280.5	281.6	282.7
115°	329.5	329.8	330.1	329.8	328.7	327.6	326.5	325.5	326.5	327.6	328.7
117.5°	375.3	376.3	377.3	377.2	375.7	374.2	372.8	371.4	372.8	374.2	375.7
120°	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9	403.4	404.8	406.3
122.5°	435.2	436.2	437.2	436.8	435.1	433.4	431.6	429.9	431.6	433.4	435.1
125°	479.5	480.0	480.6	480.0	478.4	476.8	475.2	473.5	475.2	476.8	478.4
127.5°	523.7	524.3	525.0	524.2	522.2	520.2	518.0	516.0	518.0	520.2	522.2
130°	552.4	552.7	553.1	552.1	549.8	547.4	545.0	542.7	545.0	547.4	549.8
132.5°	581.5	581.4	581.3	580.3	578.4	576.5	574.5	572.7	574.5	576.5	578.4
135°	622.5	622.2	621.8	620.6	618.6	616.6	614.7	612.7	614.7	616.6	618.6
137.5°	663.3	662.8	662.3	661.3	659.7	658.0	656.4	654.8	656.4	658.0	659.7
140°	689.7	688.8	687.9	686.7	685.1	683.5	681.8	680.2	681.8	683.5	685.1
142.5°	715.1	714.4	713.9	712.7	711.1	709.5	707.8	706.2	707.8	709.5	711.1
145°	752.0	751.0	749.9	748.7	747.5	746.2	744.9	743.6	744.9	746.2	747.5
147.5°	785.6	785.0	784.2	783.1	781.5	780.1	778.5	777.0	778.5	780.1	781.5
150°	806.5	805.8	805.0	804.1	803.1	801.9	800.9	799.8	800.9	801.9	803.1
152.5°	827.0	826.1	825.3	824.3	823.2	822.1	821.1	819.9	821.1	822.1	823.2
155°	854.0	853.5	853.0	852.4	851.9	851.3	850.8	850.3	850.8	851.3	851.9
157.5°	878.6	878.2	877.9	877.6	877.2	876.9	876.4	876.1	876.4	876.9	877.2
160°	893.8	893.6	893.5	893.2	892.8	892.4	892.1	891.8	892.1	892.4	892.8
162.5°	906.9	906.7	906.4	906.4	906.3	906.2	906.1	906.0	906.1	906.2	906.3
165°	924.3	924.3	924.3	924.4	924.5	924.7	925.0	925.1	925.0	924.7	924.5
167.5°	938.5	938.6	938.6	938.9	939.4	940.0	940.5	941.0	940.5	940.0	939.4
170°	946.6	946.8	947.0	947.3	947.9	948.4	948.9	949.5	948.9	948.4	947.9
172.5°	952.4	952.7	952.8	953.2	953.7	954.3	954.8	955.4	954.8	954.3	953.7
175°	959.2	959.5	959.9	960.3	960.9	961.4	962.0	962.5	962.0	961.4	960.9
177.5°	962.8	963.0	963.4	963.7	964.2	964.6	965.0	965.5	965.0	964.6	964.2
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	525.5	524.4	522.4	519.5	517.7	514.6	512.6	513.7	514.0	513.7	513.5
5°	511.4	507.4	502.1	496.8	492.0	486.9	483.9	482.7	480.0	478.6	477.8
7.5°	494.2	487.5	480.0	470.9	463.3	455.2	451.1	449.1	443.8	440.9	438.4
10°	481.5	470.9	463.3	451.5	444.3	433.7	426.5	426.7	419.5	415.4	412.5
12.5°	467.4	455.8	443.2	432.5	422.5	414.0	405.3	401.8	394.1	390.2	382.2
15°	444.1	430.6	417.3	402.8	392.6	379.4	366.9	351.5	339.1	328.3	325.4
17.5°	418.7	401.9	388.5	371.5	354.1	332.0	317.4	308.4	301.0	295.3	291.1
20°	401.1	384.1	369.8	344.3	320.7	305.7	295.1	288.1	280.4	274.3	270.9
22.5°	382.8	365.0	345.5	317.0	298.6	286.7	277.1	269.2	263.9	259.2	256.1
25°	356.7	337.2	305.2	285.6	270.8	258.1	251.5	246.7	241.2	234.6	231.7
27.5°	329.1	298.2	275.2	260.6	246.5	238.3	232.3	225.1	220.1	217.2	214.1
30°	308.5	277.6	259.7	243.7	233.7	224.6	217.6	213.5	208.7	203.7	201.7
32.5°	285.6	260.9	243.6	230.4	220.2	212.5	206.9	200.3	196.9	193.8	189.6
35°	257.1	238.3	222.6	211.9	202.2	195.9	189.5	185.6	179.3	176.7	175.0
37.5°	232.9	216.7	205.0	193.6	186.0	179.0	175.0	168.8	166.2	162.5	159.0
40°	219.2	203.3	192.1	182.8	174.2	169.1	164.1	159.1	155.0	153.4	149.1
42.5°	205.4	192.4	181.1	171.0	165.3	159.7	153.4	149.8	145.5	142.8	140.2
45°	186.1	174.6	165.0	156.7	150.3	144.6	140.6	134.4	132.1	126.7	124.4
47.5°	169.3	158.6	149.4	141.5	135.3	131.6	125.6	120.8	117.0	113.7	110.8
50°	157.3	148.3	139.4	132.4	126.9	121.5	115.4	113.0	107.0	105.3	103.7
52.5°	146.3	137.8	129.7	122.8	117.2	112.0	106.6	103.5	99.5	97.8	96.6
55°	130.9	122.8	115.0	108.9	103.4	98.0	94.7	90.7	88.9	87.6	86.1
57.5°	115.5	108.2	102.2	96.0	90.4	86.2	82.3	80.0	78.1	76.4	74.6
60°	105.7	98.7	93.4	87.6	81.9	78.4	75.4	72.6	70.4	67.8	67.0
62.5°	95.4	89.2	84.3	78.7	73.7	70.5	67.7	65.1	62.4	58.6	57.6
65°	81.1	76.3	71.1	66.4	62.0	58.9	54.8	51.9	50.7	50.4	50.2
67.5°	68.2	63.7	59.2	54.5	50.5	47.5	45.4	45.0	44.2	44.0	43.5
70°	59.6	55.4	51.0	46.5	42.6	42.1	41.3	40.5	39.6	39.3	38.9
72.5°	51.9	47.5	43.0	39.5	37.8	37.2	36.4	35.6	35.1	34.7	34.5
75°	39.8	35.7	32.8	31.5	30.6	30.0	28.9	28.4	28.0	27.4	27.2
77.5°	28.7	26.3	25.0	24.2	23.2	22.7	22.0	21.4	21.0	21.0	20.6
80°	21.9	20.7	19.8	18.7	18.3	17.6	17.4	16.9	17.0	16.5	16.5
82.5°	17.0	15.6	14.8	14.3	13.9	13.3	13.1	12.9	12.9	12.5	12.5
85°	8.7	8.3	8.0	7.6	7.6	7.0	7.3	7.0	7.0	6.7	6.5
87.5°	4.7	5.2	5.7	6.4	7.3	7.9	7.8	7.7	7.6	7.5	7.3
90°	9.5	12.6	16.6	20.5	24.5	28.5	28.1	27.7	27.4	27.1	26.9
92.5°	20.9	22.1	23.1	24.0	24.9	25.8	25.9	26.0	26.1	26.2	26.3
95°	49.6	50.6	51.0	51.4	51.7	52.1	52.1	52.1	52.1	52.1	51.9
97.5°	83.6	84.8	85.5	86.2	86.8	87.6	87.6	87.6	87.6	87.6	87.6
100°	109.1	110.1	110.6	111.2	111.8	112.3	112.3	112.3	112.3	112.3	112.2
102.5°	135.3	136.2	136.9	137.6	138.3	139.0	139.1	139.3	139.4	139.6	139.5
105°	177.1	177.6	177.9	178.3	178.6	179.0	179.4	179.7	180.1	180.4	180.6
107.5°	222.7	223.1	223.1	223.1	223.1	223.1	223.2	223.4	223.6	223.6	223.3
110°	252.5	253.1	253.1	253.1	253.1	253.1	253.1	253.1	253.1	253.1	252.7



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	283.7	284.2	284.1	283.9	283.8	283.6	283.2	282.7	282.3	281.9	281.4
115°	329.8	330.1	329.8	329.5	329.1	328.7	328.6	328.3	328.2	328.0	327.6
117.5°	377.2	377.3	376.3	375.3	374.3	373.3	372.8	372.4	372.0	371.5	371.0
120°	407.7	407.7	406.3	404.8	403.4	401.9	401.9	401.9	401.9	401.9	401.7
122.5°	436.8	437.2	436.2	435.2	434.2	433.2	432.8	432.3	431.9	431.5	431.0
125°	480.0	480.6	480.0	479.5	479.0	478.4	477.8	477.4	476.8	476.2	475.9
127.5°	524.2	525.0	524.3	523.7	523.0	522.4	521.7	521.1	520.4	519.8	519.1
130°	552.1	553.1	552.7	552.4	552.0	551.6	551.3	550.9	550.6	550.2	549.7
132.5°	580.3	581.3	581.4	581.5	581.5	581.6	580.8	580.0	579.2	578.4	577.7
135°	620.6	621.8	622.2	622.5	622.9	623.2	623.1	622.9	622.7	622.5	622.2
137.5°	661.3	662.3	662.8	663.3	663.8	664.2	664.1	664.0	663.8	663.7	663.2
140°	686.7	687.9	688.8	689.7	690.7	691.6	691.6	691.6	691.6	691.6	691.2
142.5°	712.7	713.9	714.4	715.1	715.7	716.3	716.5	716.6	716.7	716.9	716.6
145°	748.7	749.9	751.0	752.0	753.2	754.2	754.4	754.6	754.8	755.0	754.7
147.5°	783.1	784.2	785.0	785.6	786.4	787.1	787.5	787.9	788.3	788.7	788.6
150°	804.1	805.0	805.8	806.5	807.2	808.0	808.5	809.0	809.6	810.1	810.1
152.5°	824.3	825.3	826.1	827.0	827.9	828.8	829.5	830.1	830.8	831.5	831.5
155°	852.4	853.0	853.5	854.0	854.6	855.1	856.1	857.0	857.9	858.8	858.9
157.5°	877.6	877.9	878.2	878.6	878.9	879.2	880.4	881.7	882.9	884.1	884.3
160°	893.2	893.5	893.6	893.8	894.0	894.1	895.3	896.3	897.4	898.5	898.7
162.5°	906.4	906.4	906.7	906.9	907.0	907.2	908.4	909.6	910.9	912.1	912.3
165°	924.4	924.3	924.3	924.3	924.3	924.3	925.5	926.8	928.1	929.4	929.5
167.5°	938.9	938.6	938.6	938.5	938.5	938.4	939.7	940.9	942.2	943.5	943.6
170°	947.3	947.0	946.8	946.6	946.4	946.2	947.5	948.8	950.1	951.3	951.4
172.5°	953.2	952.8	952.7	952.4	952.3	952.1	953.4	954.6	955.9	957.2	957.2
175°	960.3	959.9	959.5	959.2	958.8	958.5	959.7	961.0	962.2	963.5	963.6
177.5°	963.7	963.4	963.0	962.8	962.5	962.2	963.0	963.9	964.8	965.6	965.6
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	511.8	512.1	511.7	511.9	511.7	512.1	511.8	513.5	513.7	514.0	513.7
5°	476.9	474.7	474.3	473.8	474.3	474.7	476.9	477.8	478.6	480.0	482.7
7.5°	435.2	434.9	433.9	432.6	433.9	434.9	435.2	438.4	440.9	443.8	449.1
10°	408.4	407.4	407.2	405.9	407.2	407.4	408.4	412.5	415.4	419.5	426.7
12.5°	376.9	371.0	370.4	367.1	370.4	371.0	376.9	382.2	390.2	394.1	401.8
15°	321.0	319.8	316.1	313.7	316.1	319.8	321.0	325.4	328.3	339.1	351.5
17.5°	288.9	285.3	284.1	283.6	284.1	285.3	288.9	291.1	295.3	301.0	308.4
20°	268.3	265.1	264.5	264.1	264.5	265.1	268.3	270.9	274.3	280.4	288.1
22.5°	254.1	250.6	249.2	248.1	249.2	250.6	254.1	256.1	259.2	263.9	269.2
25°	229.8	228.5	227.8	227.4	227.8	228.5	229.8	231.7	234.6	241.2	246.7
27.5°	210.8	208.0	207.4	206.4	207.4	208.0	210.8	214.1	217.2	220.1	225.1
30°	200.0	199.1	197.8	196.7	197.8	199.1	200.0	201.7	203.7	208.7	213.5
32.5°	187.3	186.5	185.3	184.8	185.3	186.5	187.3	189.6	193.8	196.9	200.3
35°	173.2	170.6	169.4	167.8	169.4	170.6	173.2	175.0	176.7	179.3	185.6
37.5°	158.2	156.9	155.3	155.9	155.3	156.9	158.2	159.0	162.5	166.2	168.8
40°	146.7	145.8	145.4	145.2	145.4	145.8	146.7	149.1	153.4	155.0	159.1
42.5°	137.5	134.9	134.0	134.0	134.0	134.9	137.5	140.2	142.8	145.5	149.8
45°	123.5	121.2	119.4	119.6	119.4	121.2	123.5	124.4	126.7	132.1	134.4
47.5°	109.3	109.2	108.1	108.4	108.1	109.2	109.3	110.8	113.7	117.0	120.8
50°	102.4	101.3	100.5	100.8	100.5	101.3	102.4	103.7	105.3	107.0	113.0
52.5°	95.9	94.9	94.3	95.1	94.3	94.9	95.9	96.6	97.8	99.5	103.5
55°	85.2	84.1	83.9	83.7	83.9	84.1	85.2	86.1	87.6	88.9	90.7
57.5°	73.2	72.5	71.3	70.9	71.3	72.5	73.2	74.6	76.4	78.1	80.0
60°	64.7	63.2	61.3	61.1	61.3	63.2	64.7	67.0	67.8	70.4	72.6
62.5°	56.7	56.5	56.1	56.1	56.1	56.5	56.7	57.6	58.6	62.4	65.1
65°	49.8	49.7	49.8	50.0	49.8	49.7	49.8	50.2	50.4	50.7	51.9
67.5°	43.4	43.0	42.7	42.9	42.7	43.0	43.4	43.5	44.0	44.2	45.0
70°	38.5	38.3	38.2	38.2	38.2	38.3	38.5	38.9	39.3	39.6	40.5
72.5°	33.8	33.8	33.6	33.4	33.6	33.8	33.8	34.5	34.7	35.1	35.6
75°	27.1	26.7	26.7	26.7	26.7	26.7	27.1	27.2	27.4	28.0	28.4
77.5°	20.6	20.4	20.2	20.1	20.2	20.4	20.6	20.6	21.0	21.0	21.4
80°	16.3	16.1	15.9	15.9	15.9	16.1	16.3	16.5	16.5	17.0	16.9
82.5°	12.5	12.2	12.2	12.1	12.2	12.2	12.5	12.5	12.5	12.9	12.9
85°	6.7	6.8	6.7	7.0	6.7	6.8	6.7	6.5	6.7	7.0	7.0
87.5°	7.3	7.3	7.4	7.3	7.4	7.3	7.3	7.3	7.5	7.6	7.7
90°	27.1	27.3	27.5	27.6	27.5	27.3	27.1	26.9	27.1	27.4	27.7
92.5°	26.3	26.3	26.3	26.3	26.3	26.3	26.3	26.3	26.2	26.1	26.0
95°	51.5	51.2	50.8	50.5	50.8	51.2	51.5	51.9	52.1	52.1	52.1
97.5°	87.5	87.5	87.4	87.4	87.4	87.5	87.5	87.6	87.6	87.6	87.6
100°	112.0	111.9	111.6	111.5	111.6	111.9	112.0	112.2	112.3	112.3	112.3
102.5°	139.3	139.2	139.0	138.8	139.0	139.2	139.3	139.5	139.6	139.4	139.3
105°	180.6	180.6	180.6	180.6	180.6	180.6	180.6	180.6	180.4	180.1	179.7
107.5°	222.5	221.7	220.9	220.0	220.9	221.7	222.5	223.3	223.6	223.6	223.4
110°	252.3	251.7	251.1	250.6	251.1	251.7	252.3	252.7	253.1	253.1	253.1



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	281.1	280.7	280.3	279.9	280.3	280.7	281.1	281.4	281.9	282.3	282.7
115°	327.1	326.5	326.0	325.5	326.0	326.5	327.1	327.6	328.0	328.2	328.3
117.5°	370.6	370.0	369.4	368.9	369.4	370.0	370.6	371.0	371.5	372.0	372.4
120°	401.1	400.6	400.1	399.5	400.1	400.6	401.1	401.7	401.9	401.9	401.9
122.5°	430.6	430.2	429.8	429.4	429.8	430.2	430.6	431.0	431.5	431.9	432.3
125°	475.7	475.5	475.3	475.2	475.3	475.5	475.7	475.9	476.2	476.8	477.4
127.5°	518.5	518.0	517.4	516.8	517.4	518.0	518.5	519.1	519.8	520.4	521.1
130°	548.9	548.2	547.5	546.7	547.5	548.2	548.9	549.7	550.2	550.6	550.9
132.5°	577.2	576.6	576.0	575.4	576.0	576.6	577.2	577.7	578.4	579.2	580.0
135°	621.6	621.1	620.5	620.0	620.5	621.1	621.6	622.2	622.5	622.7	622.9
137.5°	662.5	661.8	661.0	660.3	661.0	661.8	662.5	663.2	663.7	663.8	664.0
140°	690.5	689.7	689.1	688.4	689.1	689.7	690.5	691.2	691.6	691.6	691.6
142.5°	715.9	715.2	714.4	713.7	714.4	715.2	715.9	716.6	716.9	716.7	716.6
145°	754.0	753.3	752.5	751.8	752.5	753.3	754.0	754.7	755.0	754.8	754.6
147.5°	787.9	787.2	786.5	785.8	786.5	787.2	787.9	788.6	788.7	788.3	787.9
150°	809.6	809.0	808.5	808.0	808.5	809.0	809.6	810.1	810.1	809.6	809.0
152.5°	830.8	830.1	829.5	828.8	829.5	830.1	830.8	831.5	831.5	830.8	830.1
155°	858.3	857.9	857.3	856.7	857.3	857.9	858.3	858.9	858.8	857.9	857.0
157.5°	883.5	882.6	881.7	880.8	881.7	882.6	883.5	884.3	884.1	882.9	881.7
160°	898.0	897.2	896.5	895.8	896.5	897.2	898.0	898.7	898.5	897.4	896.3
162.5°	911.4	910.5	909.7	908.8	909.7	910.5	911.4	912.3	912.1	910.9	909.6
165°	928.6	927.7	926.8	925.9	926.8	927.7	928.6	929.5	929.4	928.1	926.8
167.5°	942.7	941.8	940.9	939.9	940.9	941.8	942.7	943.6	943.5	942.2	940.9
170°	950.3	949.3	948.1	947.1	948.1	949.3	950.3	951.4	951.3	950.1	948.8
172.5°	956.2	955.1	954.0	952.9	954.0	955.1	956.2	957.2	957.2	955.9	954.6
175°	962.5	961.4	960.3	959.3	960.3	961.4	962.5	963.6	963.5	962.2	961.0
177.5°	964.8	963.9	963.0	962.2	963.0	963.9	964.8	965.6	965.6	964.8	963.9
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	512.6	514.6	517.7	519.5	522.4	524.4	525.5	527.3	528.4	532.1	536.0
5°	483.9	486.9	492.0	496.8	502.1	507.4	511.4	515.8	519.8	526.8	534.3
7.5°	451.1	455.2	463.3	470.9	480.0	487.5	494.2	501.8	508.6	518.7	529.2
10°	426.5	433.7	444.3	451.5	463.3	470.9	481.5	489.8	499.3	512.7	524.5
12.5°	405.3	414.0	422.5	432.5	443.2	455.8	467.4	478.2	489.3	503.1	517.1
15°	366.9	379.4	392.6	402.8	417.3	430.6	444.1	458.5	472.2	488.8	506.9
17.5°	317.4	332.0	354.1	371.5	388.5	401.9	418.7	436.1	452.2	472.1	492.4
20°	295.1	305.7	320.7	344.3	369.8	384.1	401.1	420.4	438.9	460.6	482.2
22.5°	277.1	286.7	298.6	317.0	345.5	365.0	382.8	402.4	423.8	445.9	469.9
25°	251.5	258.1	270.8	285.6	305.2	337.2	356.7	376.3	399.7	423.4	450.8
27.5°	232.3	238.3	246.5	260.6	275.2	298.2	329.1	350.6	373.8	400.5	428.9
30°	217.6	224.6	233.7	243.7	259.7	277.6	308.5	333.4	356.3	383.8	414.1
32.5°	206.9	212.5	220.2	230.4	243.6	260.9	285.6	315.7	338.1	367.0	398.7
35°	189.5	195.9	202.2	211.9	222.6	238.3	257.1	289.3	311.5	340.0	371.9
37.5°	175.0	179.0	186.0	193.6	205.0	216.7	232.9	261.8	285.8	313.8	346.4
40°	164.1	169.1	174.2	182.8	192.1	203.3	219.2	240.8	268.3	295.8	327.6
42.5°	153.4	159.7	165.3	171.0	181.1	192.4	205.4	223.6	251.8	277.7	308.7
45°	140.6	144.6	150.3	156.7	165.0	174.6	186.1	202.0	229.1	251.5	280.5
47.5°	125.6	131.6	135.3	141.5	149.4	158.6	169.3	183.0	204.9	225.9	252.9
50°	115.4	121.5	126.9	132.4	139.4	148.3	157.3	170.6	188.2	210.2	235.4
52.5°	106.6	112.0	117.2	122.8	129.7	137.8	146.3	158.0	173.0	193.3	217.8
55°	94.7	98.0	103.4	108.9	115.0	122.8	130.9	140.7	153.7	170.7	190.5
57.5°	82.3	86.2	90.4	96.0	102.2	108.2	115.5	124.4	134.6	150.0	167.0
60°	75.4	78.4	81.9	87.6	93.4	98.7	105.7	113.2	122.8	136.2	150.6
62.5°	67.7	70.5	73.7	78.7	84.3	89.2	95.4	103.2	111.4	123.5	136.2
65°	54.8	58.9	62.0	66.4	71.1	76.3	81.1	87.4	94.7	104.3	115.5
67.5°	45.4	47.5	50.5	54.5	59.2	63.7	68.2	73.1	79.4	86.8	95.8
70°	41.3	42.1	42.6	46.5	51.0	55.4	59.6	64.2	69.6	75.7	83.5
72.5°	36.4	37.2	37.8	39.5	43.0	47.5	51.9	55.4	60.4	65.6	71.8
75°	28.9	30.0	30.6	31.5	32.8	35.7	39.8	43.1	46.1	50.0	55.0
77.5°	22.0	22.7	23.2	24.2	25.0	26.3	28.7	31.6	34.5	36.7	40.1
80°	17.4	17.6	18.3	18.7	19.8	20.7	21.9	24.3	27.1	28.0	30.4
82.5°	13.1	13.3	13.9	14.3	14.8	15.6	17.0	17.6	19.8	21.0	22.5
85°	7.3	7.0	7.6	7.6	8.0	8.3	8.7	9.6	10.2	11.7	12.1
87.5°	7.8	7.9	7.3	6.4	5.7	5.2	4.7	4.4	4.3	4.3	4.5
90°	28.1	28.5	24.5	20.5	16.6	12.6	9.5	7.3	5.1	3.0	0.8
92.5°	25.9	25.8	24.9	24.0	23.1	22.1	20.9	19.2	17.7	16.1	14.5
95°	52.1	52.1	51.7	51.4	51.0	50.6	49.6	47.7	45.9	44.1	42.3
97.5°	87.6	87.6	86.8	86.2	85.5	84.8	83.6	82.1	80.5	78.9	77.3
100°	112.3	112.3	111.8	111.2	110.6	110.1	109.1	107.7	106.2	104.8	103.3
102.5°	139.1	139.0	138.3	137.6	136.9	136.2	135.3	134.1	133.0	131.8	130.7
105°	179.4	179.0	178.6	178.3	177.9	177.6	177.1	176.6	176.0	175.5	175.0
107.5°	223.2	223.1	223.1	223.1	223.1	223.1	222.7	221.9	221.1	220.3	219.5
110°	253.1	253.1	253.1	253.1	253.1	253.1	252.5	251.4	250.3	249.2	248.2



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.2	283.6	283.8	283.9	284.1	284.2	283.7	282.7	281.6	280.5	279.4
115°	328.6	328.7	329.1	329.5	329.8	330.1	329.8	328.7	327.6	326.5	325.5
117.5°	372.8	373.3	374.3	375.3	376.3	377.3	377.2	375.7	374.2	372.8	371.4
120°	401.9	401.9	403.4	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9
122.5°	432.8	433.2	434.2	435.2	436.2	437.2	436.8	435.1	433.4	431.6	429.9
125°	477.8	478.4	479.0	479.5	480.0	480.6	480.0	478.4	476.8	475.2	473.5
127.5°	521.7	522.4	523.0	523.7	524.3	525.0	524.2	522.2	520.2	518.0	516.0
130°	551.3	551.6	552.0	552.4	552.7	553.1	552.1	549.8	547.4	545.0	542.7
132.5°	580.8	581.6	581.5	581.5	581.4	581.3	580.3	578.4	576.5	574.5	572.7
135°	623.1	623.2	622.9	622.5	622.2	621.8	620.6	618.6	616.6	614.7	612.7
137.5°	664.1	664.2	663.8	663.3	662.8	662.3	661.3	659.7	658.0	656.4	654.8
140°	691.6	691.6	690.7	689.7	688.8	687.9	686.7	685.1	683.5	681.8	680.2
142.5°	716.5	716.3	715.7	715.1	714.4	713.9	712.7	711.1	709.5	707.8	706.2
145°	754.4	754.2	753.2	752.0	751.0	749.9	748.7	747.5	746.2	744.9	743.6
147.5°	787.5	787.1	786.4	785.6	785.0	784.2	783.1	781.5	780.1	778.5	777.0
150°	808.5	808.0	807.2	806.5	805.8	805.0	804.1	803.1	801.9	800.9	799.8
152.5°	829.5	828.8	827.9	827.0	826.1	825.3	824.3	823.2	822.1	821.1	819.9
155°	856.1	855.1	854.6	854.0	853.5	853.0	852.4	851.9	851.3	850.8	850.3
157.5°	880.4	879.2	878.9	878.6	878.2	877.9	877.6	877.2	876.9	876.4	876.1
160°	895.3	894.1	894.0	893.8	893.6	893.5	893.2	892.8	892.4	892.1	891.8
162.5°	908.4	907.2	907.0	906.9	906.7	906.4	906.4	906.3	906.2	906.1	906.0
165°	925.5	924.3	924.3	924.3	924.3	924.3	924.4	924.5	924.7	925.0	925.1
167.5°	939.7	938.4	938.5	938.5	938.6	938.6	938.9	939.4	940.0	940.5	941.0
170°	947.5	946.2	946.4	946.6	946.8	947.0	947.3	947.9	948.4	948.9	949.5
172.5°	953.4	952.1	952.3	952.4	952.7	952.8	953.2	953.7	954.3	954.8	955.4
175°	959.7	958.5	958.8	959.2	959.5	959.9	960.3	960.9	961.4	962.0	962.5
177.5°	963.0	962.2	962.5	962.8	963.0	963.4	963.7	964.2	964.6	965.0	965.5
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	536.1	536.5	539.5	540.9	543.5	544.5	545.8	545.4	545.4	546.0	550.2
5°	537.3	541.0	546.5	551.9	557.1	561.5	564.5	567.4	568.6	573.9	578.7
7.5°	535.3	542.2	551.3	559.5	569.3	577.0	583.3	589.1	593.0	600.9	608.9
10°	532.8	542.4	552.8	563.4	576.9	587.1	597.5	605.4	608.0	619.6	626.3
12.5°	527.7	540.6	553.8	567.5	580.7	594.8	606.2	614.2	623.3	633.7	646.0
15°	520.2	535.0	552.3	569.8	588.7	605.8	618.0	631.9	641.9	653.4	664.1
17.5°	509.4	528.5	550.3	570.7	592.6	610.8	627.7	641.0	648.0	654.6	656.2
20°	500.8	521.3	547.1	571.1	593.0	614.1	630.8	641.9	643.8	643.9	634.1
22.5°	491.5	514.7	541.6	566.2	592.4	615.9	628.8	633.6	626.2	613.7	594.7
25°	474.3	501.2	532.5	560.6	589.1	611.3	615.8	607.5	581.7	554.6	520.4
27.5°	455.7	485.9	519.4	550.7	581.1	594.9	585.3	555.2	508.9	468.6	419.7
30°	442.1	476.0	508.9	543.9	572.1	578.0	556.0	511.7	457.6	396.9	348.1
32.5°	426.5	462.0	498.2	534.4	558.0	552.2	515.8	461.3	397.9	338.2	292.2
35°	404.3	440.9	480.0	516.3	531.3	506.3	451.8	380.9	316.1	260.4	228.7
37.5°	378.6	418.6	459.2	492.5	491.5	449.8	375.6	302.4	247.9	214.9	192.4
40°	360.4	400.8	444.7	472.8	460.8	406.5	326.1	257.1	217.2	190.9	174.5
42.5°	342.9	383.4	427.1	449.4	428.4	361.7	281.7	227.6	194.7	174.2	160.9
45°	313.2	356.0	396.3	408.7	371.3	297.8	227.8	188.5	166.6	151.5	142.3
47.5°	284.1	326.2	363.1	363.2	312.7	241.5	192.2	163.1	144.5	132.7	126.0
50°	266.3	306.3	337.2	332.4	275.0	214.8	171.9	146.8	131.3	122.2	115.2
52.5°	246.3	285.1	311.9	298.2	243.1	189.1	153.6	132.6	119.8	111.9	105.6
55°	217.2	251.7	270.6	249.8	198.4	157.3	129.8	113.3	103.7	97.0	91.6
57.5°	188.7	217.1	228.9	204.8	163.4	130.4	109.8	97.4	87.9	83.1	80.3
60°	170.7	195.0	203.3	176.7	142.0	114.1	97.3	85.8	78.7	75.6	72.8
62.5°	153.1	172.9	176.3	152.0	123.8	99.9	85.4	75.7	71.0	68.0	65.4
65°	127.0	141.3	139.7	120.0	98.0	79.2	68.7	62.8	59.3	55.0	50.4
67.5°	104.6	113.3	108.0	93.4	74.8	61.6	54.7	50.2	45.8	41.8	40.8
70°	90.3	95.4	89.8	76.3	61.3	51.7	46.1	40.8	38.2	37.3	35.5
72.5°	76.7	78.5	72.5	60.9	49.9	42.8	37.3	34.4	32.9	32.2	31.1
75°	57.6	56.3	51.1	42.1	34.7	29.8	28.1	27.1	26.1	25.4	24.8
77.5°	40.4	38.6	33.9	28.0	24.1	21.9	20.8	20.2	19.8	19.4	18.8
80°	30.4	29.1	24.5	20.0	18.3	17.2	16.6	15.9	15.9	15.6	15.0
82.5°	22.3	20.8	16.7	14.7	13.8	13.0	12.6	12.2	12.1	12.1	11.7
85°	11.7	9.5	8.3	8.0	7.4	7.0	7.3	6.8	6.8	6.8	6.7
87.5°	4.2	3.8	4.2	4.4	5.2	6.0	6.6	7.4	8.4	8.2	8.2
90°	3.0	5.1	7.3	9.5	12.6	16.6	20.5	24.5	28.5	28.1	27.7
92.5°	16.1	17.7	19.2	20.9	22.1	23.1	24.0	24.9	25.8	25.9	26.0
95°	44.1	45.9	47.7	49.6	50.6	51.0	51.4	51.7	52.1	52.1	52.1
97.5°	78.9	80.5	82.1	83.6	84.8	85.5	86.2	86.8	87.6	87.6	87.6
100°	104.8	106.2	107.7	109.1	110.1	110.6	111.2	111.8	112.3	112.3	112.3
102.5°	131.8	133.0	134.1	135.3	136.2	136.9	137.6	138.3	139.0	139.1	139.3
105°	175.5	176.0	176.6	177.1	177.6	177.9	178.3	178.6	179.0	179.4	179.7
107.5°	220.3	221.1	221.9	222.7	223.1	223.1	223.1	223.1	223.1	223.2	223.4
110°	249.2	250.3	251.4	252.5	253.1	253.1	253.1	253.1	253.1	253.1	253.1





TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	280.5	281.6	282.7	283.7	284.2	284.1	283.9	283.8	283.6	283.2	282.7
115°	326.5	327.6	328.7	329.8	330.1	329.8	329.5	329.1	328.7	328.6	328.3
117.5°	372.8	374.2	375.7	377.2	377.3	376.3	375.3	374.3	373.3	372.8	372.4
120°	403.4	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9	401.9	401.9
122.5°	431.6	433.4	435.1	436.8	437.2	436.2	435.2	434.2	433.2	432.8	432.3
125°	475.2	476.8	478.4	480.0	480.6	480.0	479.5	479.0	478.4	477.8	477.4
127.5°	518.0	520.2	522.2	524.2	525.0	524.3	523.7	523.0	522.4	521.7	521.1
130°	545.0	547.4	549.8	552.1	553.1	552.7	552.4	552.0	551.6	551.3	550.9
132.5°	574.5	576.5	578.4	580.3	581.3	581.4	581.5	581.5	581.6	580.8	580.0
135°	614.7	616.6	618.6	620.6	621.8	622.2	622.5	622.9	623.2	623.1	622.9
137.5°	656.4	658.0	659.7	661.3	662.3	662.8	663.3	663.8	664.2	664.1	664.0
140°	681.8	683.5	685.1	686.7	687.9	688.8	689.7	690.7	691.6	691.6	691.6
142.5°	707.8	709.5	711.1	712.7	713.9	714.4	715.1	715.7	716.3	716.5	716.6
145°	744.9	746.2	747.5	748.7	749.9	751.0	752.0	753.2	754.2	754.4	754.6
147.5°	778.5	780.1	781.5	783.1	784.2	785.0	785.6	786.4	787.1	787.5	787.9
150°	800.9	801.9	803.1	804.1	805.0	805.8	806.5	807.2	808.0	808.5	809.0
152.5°	821.1	822.1	823.2	824.3	825.3	826.1	827.0	827.9	828.8	829.5	830.1
155°	850.8	851.3	851.9	852.4	853.0	853.5	854.0	854.6	855.1	856.1	857.0
157.5°	876.4	876.9	877.2	877.6	877.9	878.2	878.6	878.9	879.2	880.4	881.7
160°	892.1	892.4	892.8	893.2	893.5	893.6	893.8	894.0	894.1	895.3	896.3
162.5°	906.1	906.2	906.3	906.4	906.4	906.7	906.9	907.0	907.2	908.4	909.6
165°	925.0	924.7	924.5	924.4	924.3	924.3	924.3	924.3	924.3	925.5	926.8
167.5°	940.5	940.0	939.4	938.9	938.6	938.6	938.5	938.5	938.4	939.7	940.9
170°	948.9	948.4	947.9	947.3	947.0	946.8	946.6	946.4	946.2	947.5	948.8
172.5°	954.8	954.3	953.7	953.2	952.8	952.7	952.4	952.3	952.1	953.4	954.6
175°	962.0	961.4	960.9	960.3	959.9	959.5	959.2	958.8	958.5	959.7	961.0
177.5°	965.0	964.6	964.2	963.7	963.4	963.0	962.8	962.5	962.2	963.0	963.9
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	551.6	553.6	554.5	554.5	555.5	555.1	554.6
5°	583.3	586.9	587.7	590.9	593.4	592.6	593.0
7.5°	614.9	620.5	626.1	628.7	629.1	630.6	631.1
10°	634.3	639.0	647.6	646.4	652.8	656.6	650.4
12.5°	653.0	659.3	665.3	666.9	670.6	671.8	669.4
15°	669.8	673.2	673.5	672.6	673.8	672.8	669.3
17.5°	654.1	648.7	637.7	632.5	628.4	622.3	619.9
20°	628.0	612.0	593.5	586.1	577.5	560.4	564.5
22.5°	571.7	553.6	535.0	513.4	503.0	486.9	485.9
25°	484.1	452.8	418.3	394.3	380.2	364.1	357.0
27.5°	376.4	337.0	308.8	294.5	281.4	268.7	268.2
30°	305.6	276.0	254.1	241.9	233.9	228.5	229.7
32.5°	257.6	237.3	222.5	212.4	206.5	202.4	202.4
35°	210.6	196.7	187.2	183.0	178.7	175.8	175.9
37.5°	180.2	171.9	166.6	161.9	159.2	157.8	156.9
40°	164.6	157.8	153.7	150.9	148.7	146.7	146.3
42.5°	152.4	146.7	142.6	140.4	138.4	136.9	136.6
45°	135.2	130.5	126.9	124.4	123.5	122.2	122.2
47.5°	120.3	115.7	112.8	111.3	109.7	108.8	108.8
50°	110.2	106.6	104.1	103.1	101.8	101.3	101.1
52.5°	101.2	98.5	96.7	96.0	95.5	94.8	94.9
55°	88.9	87.4	86.7	86.1	85.2	84.1	84.8
57.5°	78.6	77.3	75.3	73.5	72.7	71.9	72.2
60°	71.3	68.7	66.1	64.1	63.5	61.9	61.9
62.5°	62.1	58.5	55.3	54.1	53.6	52.8	52.7
65°	47.8	46.3	45.6	44.8	44.4	44.4	44.1
67.5°	39.6	39.0	38.2	38.0	37.7	37.5	37.4
70°	35.0	34.2	33.9	33.7	33.3	33.5	32.9
72.5°	30.6	30.0	29.9	29.4	29.2	29.2	28.8
75°	24.1	24.1	23.9	23.7	23.3	23.2	23.3
77.5°	18.5	18.6	18.3	18.2	18.2	18.2	18.0
80°	14.8	15.0	14.8	14.6	14.4	14.6	14.4
82.5°	11.7	11.4	11.4	11.3	11.3	11.3	11.2
85°	6.7	6.8	6.7	6.5	6.5	6.5	6.7
87.5°	8.0	7.9	7.9	7.9	8.0	8.0	7.9
90°	27.4	27.1	26.9	27.1	27.3	27.5	27.6
92.5°	26.1	26.2	26.3	26.3	26.3	26.3	26.3
95°	52.1	52.1	51.9	51.5	51.2	50.8	50.5
97.5°	87.6	87.6	87.6	87.5	87.5	87.4	87.4
100°	112.3	112.3	112.2	112.0	111.9	111.6	111.5
102.5°	139.4	139.6	139.5	139.3	139.2	139.0	138.8
105°	180.1	180.4	180.6	180.6	180.6	180.6	180.6
107.5°	223.6	223.6	223.3	222.5	221.7	220.9	220.0
110°	253.1	253.1	252.7	252.3	251.7	251.1	250.6



TEST NUMBER: P331634-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	282.3	281.9	281.4	281.1	280.7	280.3	279.9
115°	328.2	328.0	327.6	327.1	326.5	326.0	325.5
117.5°	372.0	371.5	371.0	370.6	370.0	369.4	368.9
120°	401.9	401.9	401.7	401.1	400.6	400.1	399.5
122.5°	431.9	431.5	431.0	430.6	430.2	429.8	429.4
125°	476.8	476.2	475.9	475.7	475.5	475.3	475.2
127.5°	520.4	519.8	519.1	518.5	518.0	517.4	516.8
130°	550.6	550.2	549.7	548.9	548.2	547.5	546.7
132.5°	579.2	578.4	577.7	577.2	576.6	576.0	575.4
135°	622.7	622.5	622.2	621.6	621.1	620.5	620.0
137.5°	663.8	663.7	663.2	662.5	661.8	661.0	660.3
140°	691.6	691.6	691.2	690.5	689.7	689.1	688.4
142.5°	716.7	716.9	716.6	715.9	715.2	714.4	713.7
145°	754.8	755.0	754.7	754.0	753.3	752.5	751.8
147.5°	788.3	788.7	788.6	787.9	787.2	786.5	785.8
150°	809.6	810.1	810.1	809.6	809.0	808.5	808.0
152.5°	830.8	831.5	831.5	830.8	830.1	829.5	828.8
155°	857.9	858.8	858.9	858.3	857.9	857.3	856.7
157.5°	882.9	884.1	884.3	883.5	882.6	881.7	880.8
160°	897.4	898.5	898.7	898.0	897.2	896.5	895.8
162.5°	910.9	912.1	912.3	911.4	910.5	909.7	908.8
165°	928.1	929.4	929.5	928.6	927.7	926.8	925.9
167.5°	942.2	943.5	943.6	942.7	941.8	940.9	939.9
170°	950.1	951.3	951.4	950.3	949.3	948.1	947.1
172.5°	955.9	957.2	957.2	956.2	955.1	954.0	952.9
175°	962.2	963.5	963.6	962.5	961.4	960.3	959.3
177.5°	964.8	965.6	965.6	964.8	963.9	963.0	962.2
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2

(END OF REPORT)