

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331635-930

Luminaire Tested: **S122RDIP-S290D925U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331635-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D925U930-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3869.3 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21
2	84	77	72	67	75	69	64	60	54	50	48	39	37	36	26	25	24	18
3	77	68	62	56	68	61	55	51	48	44	41	35	33	30	23	22	21	16
4	71	61	53	48	63	54	48	43	42	38	35	31	29	26	21	20	18	14
5	65	54	47	41	58	49	42	37	38	34	30	28	25	23	19	18	16	12
6	60	49	41	36	53	44	37	32	34	30	26	26	23	20	18	16	14	11
7	55	44	36	31	49	39	33	29	31	27	23	23	20	18	16	14	13	10
8	51	40	33	28	46	36	30	25	28	24	21	21	18	16	15	13	12	9
9	48	36	29	24	42	33	27	22	26	22	19	20	17	15	14	12	11	8
10	44	33	26	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8606	8606	8606	8606
5°	9611	8660	7679	8660
10°	10663	8599	6655	8599
15°	11188	8473	5244	8473
20°	9699	8285	4538	8285
25°	6360	8031	4051	8031
30°	4282	7720	3667	7720
35°	3467	7330	3307	7330
40°	3084	6905	3060	6905
45°	2790	6405	2731	6405
50°	2539	5913	2532	5913
55°	2387	5362	2356	5362
60°	1999	4863	1973	4863
65°	1685	4413	1910	4413
70°	1553	3942	1803	3942
75°	1454	3431	1666	3431
80°	1339	2827	1478	2827
85°	1241	2242	1297	2242



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.5	1.3
10°-20°	140.8	3.6
20°-30°	181.4	4.7
30°-40°	172.4	4.5
40°-50°	147.7	3.8
50°-60°	112.5	2.9
60°-70°	71.1	1.8
70°-80°	35.5	0.9
80°-90°	13.0	0.3
90°-100°	169.2	4.4
100°-110°	574.1	14.8
110°-120°	609.9	15.8
120°-130°	502.1	13.0
130°-140°	403.2	10.4
140°-150°	304.7	7.9
150°-160°	214.1	5.5
160°-170°	126.0	3.3
170°-180°	41.0	1.1
0°-30°	372.7	9.6
0°-40°	545.1	14.1
0°-60°	805.3	20.8
0°-90°	924.9	23.9
90°-120°	1353.2	35.0
90°-150°	2563.1	66.2
90°-180°	2944.0	76.1
0°-180°	3869.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	533	533	533	533	533	
5°	593	534	474	534	593	59
15°	669	507	314	507	669	181
25°	357	451	227	451	357	169
35°	176	372	168	372	176	113
45°	122	280	120	280	122	95
55°	85	190	84	190	85	74
65°	44	116	50	116	44	45
75°	23	55	27	55	23	25
85°	7	12	7	12	7	8
90°	27	1	27	1	27	15
95°	93	28	93	28	93	121
105°	917	99	917	99	917	887
115°	1207	175	1207	175	1207	1182
125°	979	244	979	244	979	885
135°	811	286	811	286	811	630
145°	648	327	648	327	648	411
155°	544	372	544	372	544	254
165°	478	405	478	405	478	137
175°	430	422	430	422	430	42
180°	423	423	423	423	423	



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	554.6	555.1	555.5	554.5	554.5	553.6	551.6	550.2	546.0	545.4	545.4
5°	593.0	592.6	593.4	590.9	587.7	586.9	583.3	578.7	573.9	568.6	567.4
7.5°	631.1	630.6	629.1	628.7	626.1	620.5	614.9	608.9	600.9	593.0	589.1
10°	650.4	656.6	652.8	646.4	647.6	639.0	634.3	626.3	619.6	608.0	605.4
12.5°	669.4	671.8	670.6	666.9	665.3	659.3	653.0	646.0	633.7	623.3	614.2
15°	669.3	672.8	673.8	672.6	673.5	673.2	669.8	664.1	653.4	641.9	631.9
17.5°	619.9	622.3	628.4	632.5	637.7	648.7	654.1	656.2	654.6	648.0	641.0
20°	564.5	560.4	577.5	586.1	593.5	612.0	628.0	634.1	643.9	643.8	641.9
22.5°	485.9	486.9	503.0	513.4	535.0	553.6	571.7	594.7	613.7	626.2	633.6
25°	357.0	364.1	380.2	394.3	418.3	452.8	484.1	520.4	554.6	581.7	607.5
27.5°	268.2	268.7	281.4	294.5	308.8	337.0	376.4	419.7	468.6	508.9	555.2
30°	229.7	228.5	233.9	241.9	254.1	276.0	305.6	348.1	396.9	457.6	511.7
32.5°	202.4	202.4	206.5	212.4	222.5	237.3	257.6	292.2	338.2	397.9	461.3
35°	175.9	175.8	178.7	183.0	187.2	196.7	210.6	228.7	260.4	316.1	380.9
37.5°	156.9	157.8	159.2	161.9	166.6	171.9	180.2	192.4	214.9	247.9	302.4
40°	146.3	146.7	148.7	150.9	153.7	157.8	164.6	174.5	190.9	217.2	257.1
42.5°	136.6	136.9	138.4	140.4	142.6	146.7	152.4	160.9	174.2	194.7	227.6
45°	122.2	122.2	123.5	124.4	126.9	130.5	135.2	142.3	151.5	166.6	188.5
47.5°	108.8	108.8	109.7	111.3	112.8	115.7	120.3	126.0	132.7	144.5	163.1
50°	101.1	101.3	101.8	103.1	104.1	106.6	110.2	115.2	122.2	131.3	146.8
52.5°	94.9	94.8	95.5	96.0	96.7	98.5	101.2	105.6	111.9	119.8	132.6
55°	84.8	84.1	85.2	86.1	86.7	87.4	88.9	91.6	97.0	103.7	113.3
57.5°	72.2	71.9	72.7	73.5	75.3	77.3	78.6	80.3	83.1	87.9	97.4
60°	61.9	61.9	63.5	64.1	66.1	68.7	71.3	72.8	75.6	78.7	85.8
62.5°	52.7	52.8	53.6	54.1	55.3	58.5	62.1	65.4	68.0	71.0	75.7
65°	44.1	44.4	44.4	44.8	45.6	46.3	47.8	50.4	55.0	59.3	62.8
67.5°	37.4	37.5	37.7	38.0	38.2	39.0	39.6	40.8	41.8	45.8	50.2
70°	32.9	33.5	33.3	33.7	33.9	34.2	35.0	35.5	37.3	38.2	40.8
72.5°	28.8	29.2	29.2	29.4	29.9	30.0	30.6	31.1	32.2	32.9	34.4
75°	23.3	23.2	23.3	23.7	23.9	24.1	24.1	24.8	25.4	26.1	27.1
77.5°	18.0	18.2	18.2	18.2	18.3	18.6	18.5	18.8	19.4	19.8	20.2
80°	14.4	14.6	14.4	14.6	14.8	15.0	14.8	15.0	15.6	15.9	15.9
82.5°	11.2	11.3	11.3	11.3	11.4	11.4	11.7	11.7	12.1	12.1	12.2
85°	6.7	6.5	6.5	6.5	6.7	6.8	6.7	6.7	6.8	6.8	6.8
87.5°	7.7	7.9	7.9	7.9	7.9	7.7	7.4	7.9	7.9	8.2	7.9
90°	26.8	26.8	26.8	26.8	26.8	26.0	24.4	26.0	26.8	27.6	26.8
92.5°	45.1	46.4	45.7	48.3	49.0	54.1	60.9	70.9	89.4	105.7	104.3
95°	92.8	92.0	94.4	100.9	111.5	129.4	163.5	213.2	279.1	318.9	282.3
97.5°	182.6	189.4	201.3	221.4	260.2	318.9	407.0	497.5	571.2	544.5	410.1
100°	291.3	306.0	329.5	364.5	432.1	530.5	642.0	742.9	760.0	642.8	442.6
102.5°	512.7	532.5	561.9	621.7	695.0	799.4	880.9	903.7	830.3	646.0	430.3
105°	917.0	928.4	963.4	1013.8	1064.3	1091.2	1080.6	988.6	819.4	602.9	406.0
107.5°	1171.4	1186.5	1193.5	1196.3	1189.9	1150.6	1065.9	927.5	748.0	556.8	394.0
110°	1248.2	1249.0	1241.7	1226.2	1191.2	1124.5	1020.3	874.7	703.0	534.6	391.4



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1246.9	1242.5	1228.7	1202.8	1154.1	1077.7	966.4	826.6	671.8	520.2	392.0
115°	1206.7	1199.4	1178.2	1140.8	1083.0	999.2	892.6	767.3	633.1	504.5	395.4
117.5°	1134.9	1128.8	1106.4	1066.9	1008.0	929.4	832.7	722.7	608.6	496.8	401.3
120°	1088.8	1080.6	1057.0	1018.7	961.8	887.7	801.5	700.6	595.7	492.3	405.2
122.5°	1040.6	1033.7	1012.7	975.1	924.1	857.1	775.4	683.0	584.6	489.7	409.8
125°	978.8	972.3	952.0	921.1	873.9	812.9	741.3	657.5	568.8	484.9	416.6
127.5°	924.9	919.7	902.0	873.1	831.9	775.6	708.1	632.3	554.2	482.2	423.6
130°	894.2	887.7	871.5	843.8	804.0	750.2	685.9	616.0	544.4	480.9	428.8
132.5°	862.3	856.5	841.6	813.8	774.6	724.1	665.1	600.3	536.5	480.2	434.0
135°	811.2	808.0	793.4	766.5	731.5	685.9	632.3	578.5	525.6	479.2	440.2
137.5°	761.2	756.3	743.4	720.3	688.4	648.7	606.0	561.1	518.0	479.1	445.7
140°	726.6	721.8	709.6	688.4	662.3	626.6	589.1	550.1	513.5	478.4	448.3
142.5°	692.1	691.1	680.3	661.0	636.3	606.3	574.1	541.0	508.9	478.4	450.3
145°	647.7	645.2	637.2	623.3	603.7	580.2	555.0	528.1	502.9	476.8	452.4
147.5°	610.4	608.9	603.4	592.4	576.3	559.0	539.3	518.1	496.7	473.9	453.1
150°	588.3	587.5	582.6	572.8	560.6	546.0	528.9	511.0	491.5	472.0	452.4
152.5°	569.4	569.2	565.7	557.2	547.6	534.9	520.4	503.9	486.9	468.7	451.1
155°	544.4	546.0	542.7	537.0	528.1	519.1	507.0	493.9	478.4	463.0	449.1
157.5°	523.0	523.0	521.5	516.8	510.5	503.5	493.3	482.3	470.5	457.1	445.4
160°	509.4	509.4	508.6	504.5	498.8	493.1	484.1	475.2	464.6	453.2	443.4
162.5°	496.4	497.0	496.2	493.4	487.7	483.3	475.6	468.1	459.4	450.0	441.5
165°	477.6	478.4	478.4	475.2	472.0	468.7	463.0	457.3	450.8	443.4	437.7
167.5°	460.4	461.4	461.5	459.7	458.3	455.3	451.4	447.0	442.3	437.7	434.0
170°	450.0	451.6	452.4	450.0	449.1	447.5	444.3	441.8	437.7	434.5	432.1
172.5°	441.5	442.5	443.3	442.1	441.3	440.3	437.7	435.9	433.3	430.6	429.5
175°	430.5	432.1	432.9	432.1	432.1	431.3	430.5	429.7	427.2	426.4	425.6
177.5°	423.8	425.1	425.7	425.7	425.7	425.7	425.1	425.1	423.8	423.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	545.8	544.5	543.5	540.9	539.5	536.5	536.1	536.0	532.1	528.4	527.3
5°	564.5	561.5	557.1	551.9	546.5	541.0	537.3	534.3	526.8	519.8	515.8
7.5°	583.3	577.0	569.3	559.5	551.3	542.2	535.3	529.2	518.7	508.6	501.8
10°	597.5	587.1	576.9	563.4	552.8	542.4	532.8	524.5	512.7	499.3	489.8
12.5°	606.2	594.8	580.7	567.5	553.8	540.6	527.7	517.1	503.1	489.3	478.2
15°	618.0	605.8	588.7	569.8	552.3	535.0	520.2	506.9	488.8	472.2	458.5
17.5°	627.7	610.8	592.6	570.7	550.3	528.5	509.4	492.4	472.1	452.2	436.1
20°	630.8	614.1	593.0	571.1	547.1	521.3	500.8	482.2	460.6	438.9	420.4
22.5°	628.8	615.9	592.4	566.2	541.6	514.7	491.5	469.9	445.9	423.8	402.4
25°	615.8	611.3	589.1	560.6	532.5	501.2	474.3	450.8	423.4	399.7	376.3
27.5°	585.3	594.9	581.1	550.7	519.4	485.9	455.7	428.9	400.5	373.8	350.6
30°	556.0	578.0	572.1	543.9	508.9	476.0	442.1	414.1	383.8	356.3	333.4
32.5°	515.8	552.2	558.0	534.4	498.2	462.0	426.5	398.7	367.0	338.1	315.7
35°	451.8	506.3	531.3	516.3	480.0	440.9	404.3	371.9	340.0	311.5	289.3
37.5°	375.6	449.8	491.5	492.5	459.2	418.6	378.6	346.4	313.8	285.8	261.8
40°	326.1	406.5	460.8	472.8	444.7	400.8	360.4	327.6	295.8	268.3	240.8
42.5°	281.7	361.7	428.4	449.4	427.1	383.4	342.9	308.7	277.7	251.8	223.6
45°	227.8	297.8	371.3	408.7	396.3	356.0	313.2	280.5	251.5	229.1	202.0
47.5°	192.2	241.5	312.7	363.2	363.1	326.2	284.1	252.9	225.9	204.9	183.0
50°	171.9	214.8	275.0	332.4	337.2	306.3	266.3	235.4	210.2	188.2	170.6
52.5°	153.6	189.1	243.1	298.2	311.9	285.1	246.3	217.8	193.3	173.0	158.0
55°	129.8	157.3	198.4	249.8	270.6	251.7	217.2	190.5	170.7	153.7	140.7
57.5°	109.8	130.4	163.4	204.8	228.9	217.1	188.7	167.0	150.0	134.6	124.4
60°	97.3	114.1	142.0	176.7	203.3	195.0	170.7	150.6	136.2	122.8	113.2
62.5°	85.4	99.9	123.8	152.0	176.3	172.9	153.1	136.2	123.5	111.4	103.2
65°	68.7	79.2	98.0	120.0	139.7	141.3	127.0	115.5	104.3	94.7	87.4
67.5°	54.7	61.6	74.8	93.4	108.0	113.3	104.6	95.8	86.8	79.4	73.1
70°	46.1	51.7	61.3	76.3	89.8	95.4	90.3	83.5	75.7	69.6	64.2
72.5°	37.3	42.8	49.9	60.9	72.5	78.5	76.7	71.8	65.6	60.4	55.4
75°	28.1	29.8	34.7	42.1	51.1	56.3	57.6	55.0	50.0	46.1	43.1
77.5°	20.8	21.9	24.1	28.0	33.9	38.6	40.4	40.1	36.7	34.5	31.6
80°	16.6	17.2	18.3	20.0	24.5	29.1	30.4	30.4	28.0	27.1	24.3
82.5°	12.6	13.0	13.8	14.7	16.7	20.8	22.3	22.5	21.0	19.8	17.6
85°	7.3	7.0	7.4	8.0	8.3	9.5	11.7	12.1	11.7	10.2	9.6
87.5°	6.9	6.0	5.1	4.5	4.3	4.1	4.2	4.5	4.3	4.6	4.6
90°	21.9	16.3	12.2	9.8	8.2	6.5	3.3	0.8	3.3	6.5	8.2
92.5°	81.2	55.4	36.9	29.3	23.7	20.2	14.3	9.9	14.3	20.2	23.7
95°	187.9	117.2	79.7	60.3	47.2	39.9	31.7	28.5	31.7	39.9	47.2
97.5°	253.2	154.6	107.5	85.4	70.4	59.4	50.8	46.4	50.8	59.4	70.4
100°	266.9	167.6	124.5	101.7	85.4	72.4	65.1	62.6	65.1	72.4	85.4
102.5°	267.6	179.4	139.5	116.7	99.8	86.7	79.4	77.6	79.4	86.7	99.8
105°	271.7	199.3	161.1	138.4	120.4	108.2	102.6	99.3	102.6	108.2	120.4
107.5°	283.0	219.9	182.8	159.8	142.1	130.9	125.3	122.7	125.3	130.9	142.1
110°	292.1	233.5	197.7	174.1	157.0	146.4	141.6	138.4	141.6	146.4	157.0



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	301.9	246.5	212.1	187.8	171.4	161.4	155.9	152.6	155.9	161.4	171.4
115°	316.5	266.9	231.9	209.9	193.6	183.9	179.0	175.0	179.0	183.9	193.6
117.5°	332.2	285.6	253.2	230.4	214.8	206.2	201.3	198.0	201.3	206.2	214.8
120°	342.6	298.6	266.9	244.1	227.8	220.5	215.6	212.4	215.6	220.5	227.8
122.5°	351.6	311.0	281.2	257.8	241.5	233.5	228.6	226.1	228.6	233.5	241.5
125°	366.2	329.5	300.3	277.4	261.2	251.4	246.5	244.1	246.5	251.4	261.2
127.5°	379.7	346.8	318.3	294.9	279.2	268.5	261.7	258.4	261.7	268.5	279.2
130°	388.2	357.2	328.7	306.0	289.7	278.3	270.1	266.9	270.1	278.3	289.7
132.5°	396.6	366.3	339.2	316.3	299.5	287.4	278.6	274.7	278.6	287.4	299.5
135°	407.6	379.2	353.1	330.4	311.6	299.5	289.7	286.4	289.7	299.5	311.6
137.5°	416.1	389.6	363.9	342.8	324.2	311.1	301.4	297.5	301.4	311.1	324.2
140°	420.7	395.4	371.0	349.9	332.0	318.9	309.2	306.0	309.2	318.9	332.0
142.5°	424.6	400.0	376.3	356.4	339.2	326.1	317.0	314.4	317.0	326.1	339.2
145°	429.7	406.8	384.9	367.0	350.7	338.5	330.4	327.1	330.4	338.5	350.7
147.5°	432.4	412.4	391.8	375.8	362.2	351.0	343.2	340.8	343.2	351.0	362.2
150°	433.7	415.0	396.2	381.6	369.4	358.8	352.3	349.9	352.3	358.8	369.4
152.5°	434.3	417.6	400.8	387.5	375.9	366.6	360.1	359.0	360.1	366.6	375.9
155°	435.3	421.5	407.6	395.4	386.5	377.6	372.7	371.9	372.7	377.6	386.5
157.5°	435.3	424.3	412.5	402.3	395.1	387.3	383.4	382.6	383.4	387.3	395.1
160°	435.3	425.6	415.8	406.8	400.3	393.8	390.6	389.8	390.6	393.8	400.3
162.5°	434.6	426.2	417.8	410.7	404.9	399.7	396.4	396.9	396.4	399.7	404.9
165°	432.9	427.2	419.9	415.0	410.9	406.0	404.4	405.2	404.4	406.0	410.9
167.5°	431.8	427.1	421.7	418.6	415.6	412.5	411.1	412.1	411.1	412.5	415.6
170°	430.5	426.4	422.3	419.9	418.2	415.8	415.0	416.6	415.0	415.8	418.2
172.5°	428.5	425.7	423.0	421.2	420.2	417.8	418.2	419.2	418.2	417.8	420.2
175°	426.4	424.8	423.1	422.3	422.3	420.7	421.5	422.3	421.5	420.7	422.3
177.5°	425.1	423.8	423.1	423.1	423.1	421.8	422.5	423.8	422.5	421.8	423.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	525.5	524.4	522.4	519.5	517.7	514.6	512.6	513.7	514.0	513.7	513.5
5°	511.4	507.4	502.1	496.8	492.0	486.9	483.9	482.7	480.0	478.6	477.8
7.5°	494.2	487.5	480.0	470.9	463.3	455.2	451.1	449.1	443.8	440.9	438.4
10°	481.5	470.9	463.3	451.5	444.3	433.7	426.5	426.7	419.5	415.4	412.5
12.5°	467.4	455.8	443.2	432.5	422.5	414.0	405.3	401.8	394.1	390.2	382.2
15°	444.1	430.6	417.3	402.8	392.6	379.4	366.9	351.5	339.1	328.3	325.4
17.5°	418.7	401.9	388.5	371.5	354.1	332.0	317.4	308.4	301.0	295.3	291.1
20°	401.1	384.1	369.8	344.3	320.7	305.7	295.1	288.1	280.4	274.3	270.9
22.5°	382.8	365.0	345.5	317.0	298.6	286.7	277.1	269.2	263.9	259.2	256.1
25°	356.7	337.2	305.2	285.6	270.8	258.1	251.5	246.7	241.2	234.6	231.7
27.5°	329.1	298.2	275.2	260.6	246.5	238.3	232.3	225.1	220.1	217.2	214.1
30°	308.5	277.6	259.7	243.7	233.7	224.6	217.6	213.5	208.7	203.7	201.7
32.5°	285.6	260.9	243.6	230.4	220.2	212.5	206.9	200.3	196.9	193.8	189.6
35°	257.1	238.3	222.6	211.9	202.2	195.9	189.5	185.6	179.3	176.7	175.0
37.5°	232.9	216.7	205.0	193.6	186.0	179.0	175.0	168.8	166.2	162.5	159.0
40°	219.2	203.3	192.1	182.8	174.2	169.1	164.1	159.1	155.0	153.4	149.1
42.5°	205.4	192.4	181.1	171.0	165.3	159.7	153.4	149.8	145.5	142.8	140.2
45°	186.1	174.6	165.0	156.7	150.3	144.6	140.6	134.4	132.1	126.7	124.4
47.5°	169.3	158.6	149.4	141.5	135.3	131.6	125.6	120.8	117.0	113.7	110.8
50°	157.3	148.3	139.4	132.4	126.9	121.5	115.4	113.0	107.0	105.3	103.7
52.5°	146.3	137.8	129.7	122.8	117.2	112.0	106.6	103.5	99.5	97.8	96.6
55°	130.9	122.8	115.0	108.9	103.4	98.0	94.7	90.7	88.9	87.6	86.1
57.5°	115.5	108.2	102.2	96.0	90.4	86.2	82.3	80.0	78.1	76.4	74.6
60°	105.7	98.7	93.4	87.6	81.9	78.4	75.4	72.6	70.4	67.8	67.0
62.5°	95.4	89.2	84.3	78.7	73.7	70.5	67.7	65.1	62.4	58.6	57.6
65°	81.1	76.3	71.1	66.4	62.0	58.9	54.8	51.9	50.7	50.4	50.2
67.5°	68.2	63.7	59.2	54.5	50.5	47.5	45.4	45.0	44.2	44.0	43.5
70°	59.6	55.4	51.0	46.5	42.6	42.1	41.3	40.5	39.6	39.3	38.9
72.5°	51.9	47.5	43.0	39.5	37.8	37.2	36.4	35.6	35.1	34.7	34.5
75°	39.8	35.7	32.8	31.5	30.6	30.0	28.9	28.4	28.0	27.4	27.2
77.5°	28.7	26.3	25.0	24.2	23.2	22.7	22.0	21.4	21.0	21.0	20.6
80°	21.9	20.7	19.8	18.7	18.3	17.6	17.4	16.9	17.0	16.5	16.5
82.5°	17.0	15.6	14.8	14.3	13.9	13.3	13.1	12.9	12.9	12.5	12.5
85°	8.7	8.3	8.0	7.6	7.6	7.0	7.3	7.0	7.0	6.7	6.5
87.5°	4.7	5.1	5.6	6.8	7.7	7.7	7.6	7.3	6.9	7.3	7.3
90°	9.8	12.2	16.3	21.9	26.8	27.6	26.8	26.0	24.4	26.0	26.8
92.5°	29.3	36.9	55.4	81.2	104.3	105.7	89.4	70.9	60.9	54.1	49.0
95°	60.3	79.7	117.2	187.9	282.3	318.9	279.1	213.2	163.5	129.4	111.5
97.5°	85.4	107.5	154.6	253.2	410.1	544.5	571.2	497.5	407.0	318.9	260.2
100°	101.7	124.5	167.6	266.9	442.6	642.8	760.0	742.9	642.0	530.5	432.1
102.5°	116.7	139.5	179.4	267.6	430.3	646.0	830.3	903.7	880.9	799.4	695.0
105°	138.4	161.1	199.3	271.7	406.0	602.9	819.4	988.6	1080.6	1091.2	1064.3
107.5°	159.8	182.8	219.9	283.0	394.0	556.8	748.0	927.5	1065.9	1150.6	1189.9
110°	174.1	197.7	233.5	292.1	391.4	534.6	703.0	874.7	1020.3	1124.5	1191.2



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	187.8	212.1	246.5	301.9	392.0	520.2	671.8	826.6	966.4	1077.7	1154.1
115°	209.9	231.9	266.9	316.5	395.4	504.5	633.1	767.3	892.6	999.2	1083.0
117.5°	230.4	253.2	285.6	332.2	401.3	496.8	608.6	722.7	832.7	929.4	1008.0
120°	244.1	266.9	298.6	342.6	405.2	492.3	595.7	700.6	801.5	887.7	961.8
122.5°	257.8	281.2	311.0	351.6	409.8	489.7	584.6	683.0	775.4	857.1	924.1
125°	277.4	300.3	329.5	366.2	416.6	484.9	568.8	657.5	741.3	812.9	873.9
127.5°	294.9	318.3	346.8	379.7	423.6	482.2	554.2	632.3	708.1	775.6	831.9
130°	306.0	328.7	357.2	388.2	428.8	480.9	544.4	616.0	685.9	750.2	804.0
132.5°	316.3	339.2	366.3	396.6	434.0	480.2	536.5	600.3	665.1	724.1	774.6
135°	330.4	353.1	379.2	407.6	440.2	479.2	525.6	578.5	632.3	685.9	731.5
137.5°	342.8	363.9	389.6	416.1	445.7	479.1	518.0	561.1	606.0	648.7	688.4
140°	349.9	371.0	395.4	420.7	448.3	478.4	513.5	550.1	589.1	626.6	662.3
142.5°	356.4	376.3	400.0	424.6	450.3	478.4	508.9	541.0	574.1	606.3	636.3
145°	367.0	384.9	406.8	429.7	452.4	476.8	502.9	528.1	555.0	580.2	603.7
147.5°	375.8	391.8	412.4	432.4	453.1	473.9	496.7	518.1	539.3	559.0	576.3
150°	381.6	396.2	415.0	433.7	452.4	472.0	491.5	511.0	528.9	546.0	560.6
152.5°	387.5	400.8	417.6	434.3	451.1	468.7	486.9	503.9	520.4	534.9	547.6
155°	395.4	407.6	421.5	435.3	449.1	463.0	478.4	493.9	507.0	519.1	528.1
157.5°	402.3	412.5	424.3	435.3	445.4	457.1	470.5	482.3	493.3	503.5	510.5
160°	406.8	415.8	425.6	435.3	443.4	453.2	464.6	475.2	484.1	493.1	498.8
162.5°	410.7	417.8	426.2	434.6	441.5	450.0	459.4	468.1	475.6	483.3	487.7
165°	415.0	419.9	427.2	432.9	437.7	443.4	450.8	457.3	463.0	468.7	472.0
167.5°	418.6	421.7	427.1	431.8	434.0	437.7	442.3	447.0	451.4	455.3	458.3
170°	419.9	422.3	426.4	430.5	432.1	434.5	437.7	441.8	444.3	447.5	449.1
172.5°	421.2	423.0	425.7	428.5	429.5	430.6	433.3	435.9	437.7	440.3	441.3
175°	422.3	423.1	424.8	426.4	425.6	426.4	427.2	429.7	430.5	431.3	432.1
177.5°	423.1	423.1	423.8	425.1	423.8	423.1	423.8	425.1	425.1	425.7	425.7
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	511.8	512.1	511.7	511.9	511.7	512.1	511.8	513.5	513.7	514.0	513.7
5°	476.9	474.7	474.3	473.8	474.3	474.7	476.9	477.8	478.6	480.0	482.7
7.5°	435.2	434.9	433.9	432.6	433.9	434.9	435.2	438.4	440.9	443.8	449.1
10°	408.4	407.4	407.2	405.9	407.2	407.4	408.4	412.5	415.4	419.5	426.7
12.5°	376.9	371.0	370.4	367.1	370.4	371.0	376.9	382.2	390.2	394.1	401.8
15°	321.0	319.8	316.1	313.7	316.1	319.8	321.0	325.4	328.3	339.1	351.5
17.5°	288.9	285.3	284.1	283.6	284.1	285.3	288.9	291.1	295.3	301.0	308.4
20°	268.3	265.1	264.5	264.1	264.5	265.1	268.3	270.9	274.3	280.4	288.1
22.5°	254.1	250.6	249.2	248.1	249.2	250.6	254.1	256.1	259.2	263.9	269.2
25°	229.8	228.5	227.8	227.4	227.8	228.5	229.8	231.7	234.6	241.2	246.7
27.5°	210.8	208.0	207.4	206.4	207.4	208.0	210.8	214.1	217.2	220.1	225.1
30°	200.0	199.1	197.8	196.7	197.8	199.1	200.0	201.7	203.7	208.7	213.5
32.5°	187.3	186.5	185.3	184.8	185.3	186.5	187.3	189.6	193.8	196.9	200.3
35°	173.2	170.6	169.4	167.8	169.4	170.6	173.2	175.0	176.7	179.3	185.6
37.5°	158.2	156.9	155.3	155.9	155.3	156.9	158.2	159.0	162.5	166.2	168.8
40°	146.7	145.8	145.4	145.2	145.4	145.8	146.7	149.1	153.4	155.0	159.1
42.5°	137.5	134.9	134.0	134.0	134.0	134.9	137.5	140.2	142.8	145.5	149.8
45°	123.5	121.2	119.4	119.6	119.4	121.2	123.5	124.4	126.7	132.1	134.4
47.5°	109.3	109.2	108.1	108.4	108.1	109.2	109.3	110.8	113.7	117.0	120.8
50°	102.4	101.3	100.5	100.8	100.5	101.3	102.4	103.7	105.3	107.0	113.0
52.5°	95.9	94.9	94.3	95.1	94.3	94.9	95.9	96.6	97.8	99.5	103.5
55°	85.2	84.1	83.9	83.7	83.9	84.1	85.2	86.1	87.6	88.9	90.7
57.5°	73.2	72.5	71.3	70.9	71.3	72.5	73.2	74.6	76.4	78.1	80.0
60°	64.7	63.2	61.3	61.1	61.3	63.2	64.7	67.0	67.8	70.4	72.6
62.5°	56.7	56.5	56.1	56.1	56.1	56.5	56.7	57.6	58.6	62.4	65.1
65°	49.8	49.7	49.8	50.0	49.8	49.7	49.8	50.2	50.4	50.7	51.9
67.5°	43.4	43.0	42.7	42.9	42.7	43.0	43.4	43.5	44.0	44.2	45.0
70°	38.5	38.3	38.2	38.2	38.2	38.3	38.5	38.9	39.3	39.6	40.5
72.5°	33.8	33.8	33.6	33.4	33.6	33.8	33.8	34.5	34.7	35.1	35.6
75°	27.1	26.7	26.7	26.7	26.7	26.7	27.1	27.2	27.4	28.0	28.4
77.5°	20.6	20.4	20.2	20.1	20.2	20.4	20.6	20.6	21.0	21.0	21.4
80°	16.3	16.1	15.9	15.9	15.9	16.1	16.3	16.5	16.5	17.0	16.9
82.5°	12.5	12.2	12.2	12.1	12.2	12.2	12.5	12.5	12.5	12.9	12.9
85°	6.7	6.8	6.7	7.0	6.7	6.8	6.7	6.5	6.7	7.0	7.0
87.5°	7.3	7.2	7.3	7.2	7.3	7.2	7.3	7.3	7.3	6.9	7.3
90°	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.0	24.4	26.0
92.5°	48.3	45.7	46.4	45.1	46.4	45.7	48.3	49.0	54.1	60.9	70.9
95°	100.9	94.4	92.0	92.8	92.0	94.4	100.9	111.5	129.4	163.5	213.2
97.5°	221.4	201.3	189.4	182.6	189.4	201.3	221.4	260.2	318.9	407.0	497.5
100°	364.5	329.5	306.0	291.3	306.0	329.5	364.5	432.1	530.5	642.0	742.9
102.5°	621.7	561.9	532.5	512.7	532.5	561.9	621.7	695.0	799.4	880.9	903.7
105°	1013.8	963.4	928.4	917.0	928.4	963.4	1013.8	1064.3	1091.2	1080.6	988.6
107.5°	1196.3	1193.5	1186.5	1171.4	1186.5	1193.5	1196.3	1189.9	1150.6	1065.9	927.5
110°	1226.2	1241.7	1249.0	1248.2	1249.0	1241.7	1226.2	1191.2	1124.5	1020.3	874.7



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1202.8	1228.7	1242.5	1246.9	1242.5	1228.7	1202.8	1154.1	1077.7	966.4	826.6
115°	1140.8	1178.2	1199.4	1206.7	1199.4	1178.2	1140.8	1083.0	999.2	892.6	767.3
117.5°	1066.9	1106.4	1128.8	1134.9	1128.8	1106.4	1066.9	1008.0	929.4	832.7	722.7
120°	1018.7	1057.0	1080.6	1088.8	1080.6	1057.0	1018.7	961.8	887.7	801.5	700.6
122.5°	975.1	1012.7	1033.7	1040.6	1033.7	1012.7	975.1	924.1	857.1	775.4	683.0
125°	921.1	952.0	972.3	978.8	972.3	952.0	921.1	873.9	812.9	741.3	657.5
127.5°	873.1	902.0	919.7	924.9	919.7	902.0	873.1	831.9	775.6	708.1	632.3
130°	843.8	871.5	887.7	894.2	887.7	871.5	843.8	804.0	750.2	685.9	616.0
132.5°	813.8	841.6	856.5	862.3	856.5	841.6	813.8	774.6	724.1	665.1	600.3
135°	766.5	793.4	808.0	811.2	808.0	793.4	766.5	731.5	685.9	632.3	578.5
137.5°	720.3	743.4	756.3	761.2	756.3	743.4	720.3	688.4	648.7	606.0	561.1
140°	688.4	709.6	721.8	726.6	721.8	709.6	688.4	662.3	626.6	589.1	550.1
142.5°	661.0	680.3	691.1	692.1	691.1	680.3	661.0	636.3	606.3	574.1	541.0
145°	623.3	637.2	645.2	647.7	645.2	637.2	623.3	603.7	580.2	555.0	528.1
147.5°	592.4	603.4	608.9	610.4	608.9	603.4	592.4	576.3	559.0	539.3	518.1
150°	572.8	582.6	587.5	588.3	587.5	582.6	572.8	560.6	546.0	528.9	511.0
152.5°	557.2	565.7	569.2	569.4	569.2	565.7	557.2	547.6	534.9	520.4	503.9
155°	537.0	542.7	546.0	544.4	546.0	542.7	537.0	528.1	519.1	507.0	493.9
157.5°	516.8	521.5	523.0	523.0	523.0	521.5	516.8	510.5	503.5	493.3	482.3
160°	504.5	508.6	509.4	509.4	509.4	508.6	504.5	498.8	493.1	484.1	475.2
162.5°	493.4	496.2	497.0	496.4	497.0	496.2	493.4	487.7	483.3	475.6	468.1
165°	475.2	478.4	478.4	477.6	478.4	478.4	475.2	472.0	468.7	463.0	457.3
167.5°	459.7	461.5	461.4	460.4	461.4	461.5	459.7	458.3	455.3	451.4	447.0
170°	450.0	452.4	451.6	450.0	451.6	452.4	450.0	449.1	447.5	444.3	441.8
172.5°	442.1	443.3	442.5	441.5	442.5	443.3	442.1	441.3	440.3	437.7	435.9
175°	432.1	432.9	432.1	430.5	432.1	432.9	432.1	432.1	431.3	430.5	429.7
177.5°	425.7	425.7	425.1	423.8	425.1	425.7	425.7	425.7	425.7	425.1	425.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	512.6	514.6	517.7	519.5	522.4	524.4	525.5	527.3	528.4	532.1	536.0
5°	483.9	486.9	492.0	496.8	502.1	507.4	511.4	515.8	519.8	526.8	534.3
7.5°	451.1	455.2	463.3	470.9	480.0	487.5	494.2	501.8	508.6	518.7	529.2
10°	426.5	433.7	444.3	451.5	463.3	470.9	481.5	489.8	499.3	512.7	524.5
12.5°	405.3	414.0	422.5	432.5	443.2	455.8	467.4	478.2	489.3	503.1	517.1
15°	366.9	379.4	392.6	402.8	417.3	430.6	444.1	458.5	472.2	488.8	506.9
17.5°	317.4	332.0	354.1	371.5	388.5	401.9	418.7	436.1	452.2	472.1	492.4
20°	295.1	305.7	320.7	344.3	369.8	384.1	401.1	420.4	438.9	460.6	482.2
22.5°	277.1	286.7	298.6	317.0	345.5	365.0	382.8	402.4	423.8	445.9	469.9
25°	251.5	258.1	270.8	285.6	305.2	337.2	356.7	376.3	399.7	423.4	450.8
27.5°	232.3	238.3	246.5	260.6	275.2	298.2	329.1	350.6	373.8	400.5	428.9
30°	217.6	224.6	233.7	243.7	259.7	277.6	308.5	333.4	356.3	383.8	414.1
32.5°	206.9	212.5	220.2	230.4	243.6	260.9	285.6	315.7	338.1	367.0	398.7
35°	189.5	195.9	202.2	211.9	222.6	238.3	257.1	289.3	311.5	340.0	371.9
37.5°	175.0	179.0	186.0	193.6	205.0	216.7	232.9	261.8	285.8	313.8	346.4
40°	164.1	169.1	174.2	182.8	192.1	203.3	219.2	240.8	268.3	295.8	327.6
42.5°	153.4	159.7	165.3	171.0	181.1	192.4	205.4	223.6	251.8	277.7	308.7
45°	140.6	144.6	150.3	156.7	165.0	174.6	186.1	202.0	229.1	251.5	280.5
47.5°	125.6	131.6	135.3	141.5	149.4	158.6	169.3	183.0	204.9	225.9	252.9
50°	115.4	121.5	126.9	132.4	139.4	148.3	157.3	170.6	188.2	210.2	235.4
52.5°	106.6	112.0	117.2	122.8	129.7	137.8	146.3	158.0	173.0	193.3	217.8
55°	94.7	98.0	103.4	108.9	115.0	122.8	130.9	140.7	153.7	170.7	190.5
57.5°	82.3	86.2	90.4	96.0	102.2	108.2	115.5	124.4	134.6	150.0	167.0
60°	75.4	78.4	81.9	87.6	93.4	98.7	105.7	113.2	122.8	136.2	150.6
62.5°	67.7	70.5	73.7	78.7	84.3	89.2	95.4	103.2	111.4	123.5	136.2
65°	54.8	58.9	62.0	66.4	71.1	76.3	81.1	87.4	94.7	104.3	115.5
67.5°	45.4	47.5	50.5	54.5	59.2	63.7	68.2	73.1	79.4	86.8	95.8
70°	41.3	42.1	42.6	46.5	51.0	55.4	59.6	64.2	69.6	75.7	83.5
72.5°	36.4	37.2	37.8	39.5	43.0	47.5	51.9	55.4	60.4	65.6	71.8
75°	28.9	30.0	30.6	31.5	32.8	35.7	39.8	43.1	46.1	50.0	55.0
77.5°	22.0	22.7	23.2	24.2	25.0	26.3	28.7	31.6	34.5	36.7	40.1
80°	17.4	17.6	18.3	18.7	19.8	20.7	21.9	24.3	27.1	28.0	30.4
82.5°	13.1	13.3	13.9	14.3	14.8	15.6	17.0	17.6	19.8	21.0	22.5
85°	7.3	7.0	7.6	7.6	8.0	8.3	8.7	9.6	10.2	11.7	12.1
87.5°	7.6	7.7	7.7	6.8	5.6	5.1	4.7	4.6	4.6	4.3	4.5
90°	26.8	27.6	26.8	21.9	16.3	12.2	9.8	8.2	6.5	3.3	0.8
92.5°	89.4	105.7	104.3	81.2	55.4	36.9	29.3	23.7	20.2	14.3	9.9
95°	279.1	318.9	282.3	187.9	117.2	79.7	60.3	47.2	39.9	31.7	28.5
97.5°	571.2	544.5	410.1	253.2	154.6	107.5	85.4	70.4	59.4	50.8	46.4
100°	760.0	642.8	442.6	266.9	167.6	124.5	101.7	85.4	72.4	65.1	62.6
102.5°	830.3	646.0	430.3	267.6	179.4	139.5	116.7	99.8	86.7	79.4	77.6
105°	819.4	602.9	406.0	271.7	199.3	161.1	138.4	120.4	108.2	102.6	99.3
107.5°	748.0	556.8	394.0	283.0	219.9	182.8	159.8	142.1	130.9	125.3	122.7
110°	703.0	534.6	391.4	292.1	233.5	197.7	174.1	157.0	146.4	141.6	138.4



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	671.8	520.2	392.0	301.9	246.5	212.1	187.8	171.4	161.4	155.9	152.6
115°	633.1	504.5	395.4	316.5	266.9	231.9	209.9	193.6	183.9	179.0	175.0
117.5°	608.6	496.8	401.3	332.2	285.6	253.2	230.4	214.8	206.2	201.3	198.0
120°	595.7	492.3	405.2	342.6	298.6	266.9	244.1	227.8	220.5	215.6	212.4
122.5°	584.6	489.7	409.8	351.6	311.0	281.2	257.8	241.5	233.5	228.6	226.1
125°	568.8	484.9	416.6	366.2	329.5	300.3	277.4	261.2	251.4	246.5	244.1
127.5°	554.2	482.2	423.6	379.7	346.8	318.3	294.9	279.2	268.5	261.7	258.4
130°	544.4	480.9	428.8	388.2	357.2	328.7	306.0	289.7	278.3	270.1	266.9
132.5°	536.5	480.2	434.0	396.6	366.3	339.2	316.3	299.5	287.4	278.6	274.7
135°	525.6	479.2	440.2	407.6	379.2	353.1	330.4	311.6	299.5	289.7	286.4
137.5°	518.0	479.1	445.7	416.1	389.6	363.9	342.8	324.2	311.1	301.4	297.5
140°	513.5	478.4	448.3	420.7	395.4	371.0	349.9	332.0	318.9	309.2	306.0
142.5°	508.9	478.4	450.3	424.6	400.0	376.3	356.4	339.2	326.1	317.0	314.4
145°	502.9	476.8	452.4	429.7	406.8	384.9	367.0	350.7	338.5	330.4	327.1
147.5°	496.7	473.9	453.1	432.4	412.4	391.8	375.8	362.2	351.0	343.2	340.8
150°	491.5	472.0	452.4	433.7	415.0	396.2	381.6	369.4	358.8	352.3	349.9
152.5°	486.9	468.7	451.1	434.3	417.6	400.8	387.5	375.9	366.6	360.1	359.0
155°	478.4	463.0	449.1	435.3	421.5	407.6	395.4	386.5	377.6	372.7	371.9
157.5°	470.5	457.1	445.4	435.3	424.3	412.5	402.3	395.1	387.3	383.4	382.6
160°	464.6	453.2	443.4	435.3	425.6	415.8	406.8	400.3	393.8	390.6	389.8
162.5°	459.4	450.0	441.5	434.6	426.2	417.8	410.7	404.9	399.7	396.4	396.9
165°	450.8	443.4	437.7	432.9	427.2	419.9	415.0	410.9	406.0	404.4	405.2
167.5°	442.3	437.7	434.0	431.8	427.1	421.7	418.6	415.6	412.5	411.1	412.1
170°	437.7	434.5	432.1	430.5	426.4	422.3	419.9	418.2	415.8	415.0	416.6
172.5°	433.3	430.6	429.5	428.5	425.7	423.0	421.2	420.2	417.8	418.2	419.2
175°	427.2	426.4	425.6	426.4	424.8	423.1	422.3	422.3	420.7	421.5	422.3
177.5°	423.8	423.1	423.8	425.1	423.8	423.1	423.1	423.1	421.8	422.5	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	536.1	536.5	539.5	540.9	543.5	544.5	545.8	545.4	545.4	546.0	550.2
5°	537.3	541.0	546.5	551.9	557.1	561.5	564.5	567.4	568.6	573.9	578.7
7.5°	535.3	542.2	551.3	559.5	569.3	577.0	583.3	589.1	593.0	600.9	608.9
10°	532.8	542.4	552.8	563.4	576.9	587.1	597.5	605.4	608.0	619.6	626.3
12.5°	527.7	540.6	553.8	567.5	580.7	594.8	606.2	614.2	623.3	633.7	646.0
15°	520.2	535.0	552.3	569.8	588.7	605.8	618.0	631.9	641.9	653.4	664.1
17.5°	509.4	528.5	550.3	570.7	592.6	610.8	627.7	641.0	648.0	654.6	656.2
20°	500.8	521.3	547.1	571.1	593.0	614.1	630.8	641.9	643.8	643.9	634.1
22.5°	491.5	514.7	541.6	566.2	592.4	615.9	628.8	633.6	626.2	613.7	594.7
25°	474.3	501.2	532.5	560.6	589.1	611.3	615.8	607.5	581.7	554.6	520.4
27.5°	455.7	485.9	519.4	550.7	581.1	594.9	585.3	555.2	508.9	468.6	419.7
30°	442.1	476.0	508.9	543.9	572.1	578.0	556.0	511.7	457.6	396.9	348.1
32.5°	426.5	462.0	498.2	534.4	558.0	552.2	515.8	461.3	397.9	338.2	292.2
35°	404.3	440.9	480.0	516.3	531.3	506.3	451.8	380.9	316.1	260.4	228.7
37.5°	378.6	418.6	459.2	492.5	491.5	449.8	375.6	302.4	247.9	214.9	192.4
40°	360.4	400.8	444.7	472.8	460.8	406.5	326.1	257.1	217.2	190.9	174.5
42.5°	342.9	383.4	427.1	449.4	428.4	361.7	281.7	227.6	194.7	174.2	160.9
45°	313.2	356.0	396.3	408.7	371.3	297.8	227.8	188.5	166.6	151.5	142.3
47.5°	284.1	326.2	363.1	363.2	312.7	241.5	192.2	163.1	144.5	132.7	126.0
50°	266.3	306.3	337.2	332.4	275.0	214.8	171.9	146.8	131.3	122.2	115.2
52.5°	246.3	285.1	311.9	298.2	243.1	189.1	153.6	132.6	119.8	111.9	105.6
55°	217.2	251.7	270.6	249.8	198.4	157.3	129.8	113.3	103.7	97.0	91.6
57.5°	188.7	217.1	228.9	204.8	163.4	130.4	109.8	97.4	87.9	83.1	80.3
60°	170.7	195.0	203.3	176.7	142.0	114.1	97.3	85.8	78.7	75.6	72.8
62.5°	153.1	172.9	176.3	152.0	123.8	99.9	85.4	75.7	71.0	68.0	65.4
65°	127.0	141.3	139.7	120.0	98.0	79.2	68.7	62.8	59.3	55.0	50.4
67.5°	104.6	113.3	108.0	93.4	74.8	61.6	54.7	50.2	45.8	41.8	40.8
70°	90.3	95.4	89.8	76.3	61.3	51.7	46.1	40.8	38.2	37.3	35.5
72.5°	76.7	78.5	72.5	60.9	49.9	42.8	37.3	34.4	32.9	32.2	31.1
75°	57.6	56.3	51.1	42.1	34.7	29.8	28.1	27.1	26.1	25.4	24.8
77.5°	40.4	38.6	33.9	28.0	24.1	21.9	20.8	20.2	19.8	19.4	18.8
80°	30.4	29.1	24.5	20.0	18.3	17.2	16.6	15.9	15.9	15.6	15.0
82.5°	22.3	20.8	16.7	14.7	13.8	13.0	12.6	12.2	12.1	12.1	11.7
85°	11.7	9.5	8.3	8.0	7.4	7.0	7.3	6.8	6.8	6.8	6.7
87.5°	4.2	4.1	4.3	4.5	5.1	6.0	6.9	7.9	8.2	7.9	7.9
90°	3.3	6.5	8.2	9.8	12.2	16.3	21.9	26.8	27.6	26.8	26.0
92.5°	14.3	20.2	23.7	29.3	36.9	55.4	81.2	104.3	105.7	89.4	70.9
95°	31.7	39.9	47.2	60.3	79.7	117.2	187.9	282.3	318.9	279.1	213.2
97.5°	50.8	59.4	70.4	85.4	107.5	154.6	253.2	410.1	544.5	571.2	497.5
100°	65.1	72.4	85.4	101.7	124.5	167.6	266.9	442.6	642.8	760.0	742.9
102.5°	79.4	86.7	99.8	116.7	139.5	179.4	267.6	430.3	646.0	830.3	903.7
105°	102.6	108.2	120.4	138.4	161.1	199.3	271.7	406.0	602.9	819.4	988.6
107.5°	125.3	130.9	142.1	159.8	182.8	219.9	283.0	394.0	556.8	748.0	927.5
110°	141.6	146.4	157.0	174.1	197.7	233.5	292.1	391.4	534.6	703.0	874.7



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	155.9	161.4	171.4	187.8	212.1	246.5	301.9	392.0	520.2	671.8	826.6
115°	179.0	183.9	193.6	209.9	231.9	266.9	316.5	395.4	504.5	633.1	767.3
117.5°	201.3	206.2	214.8	230.4	253.2	285.6	332.2	401.3	496.8	608.6	722.7
120°	215.6	220.5	227.8	244.1	266.9	298.6	342.6	405.2	492.3	595.7	700.6
122.5°	228.6	233.5	241.5	257.8	281.2	311.0	351.6	409.8	489.7	584.6	683.0
125°	246.5	251.4	261.2	277.4	300.3	329.5	366.2	416.6	484.9	568.8	657.5
127.5°	261.7	268.5	279.2	294.9	318.3	346.8	379.7	423.6	482.2	554.2	632.3
130°	270.1	278.3	289.7	306.0	328.7	357.2	388.2	428.8	480.9	544.4	616.0
132.5°	278.6	287.4	299.5	316.3	339.2	366.3	396.6	434.0	480.2	536.5	600.3
135°	289.7	299.5	311.6	330.4	353.1	379.2	407.6	440.2	479.2	525.6	578.5
137.5°	301.4	311.1	324.2	342.8	363.9	389.6	416.1	445.7	479.1	518.0	561.1
140°	309.2	318.9	332.0	349.9	371.0	395.4	420.7	448.3	478.4	513.5	550.1
142.5°	317.0	326.1	339.2	356.4	376.3	400.0	424.6	450.3	478.4	508.9	541.0
145°	330.4	338.5	350.7	367.0	384.9	406.8	429.7	452.4	476.8	502.9	528.1
147.5°	343.2	351.0	362.2	375.8	391.8	412.4	432.4	453.1	473.9	496.7	518.1
150°	352.3	358.8	369.4	381.6	396.2	415.0	433.7	452.4	472.0	491.5	511.0
152.5°	360.1	366.6	375.9	387.5	400.8	417.6	434.3	451.1	468.7	486.9	503.9
155°	372.7	377.6	386.5	395.4	407.6	421.5	435.3	449.1	463.0	478.4	493.9
157.5°	383.4	387.3	395.1	402.3	412.5	424.3	435.3	445.4	457.1	470.5	482.3
160°	390.6	393.8	400.3	406.8	415.8	425.6	435.3	443.4	453.2	464.6	475.2
162.5°	396.4	399.7	404.9	410.7	417.8	426.2	434.6	441.5	450.0	459.4	468.1
165°	404.4	406.0	410.9	415.0	419.9	427.2	432.9	437.7	443.4	450.8	457.3
167.5°	411.1	412.5	415.6	418.6	421.7	427.1	431.8	434.0	437.7	442.3	447.0
170°	415.0	415.8	418.2	419.9	422.3	426.4	430.5	432.1	434.5	437.7	441.8
172.5°	418.2	417.8	420.2	421.2	423.0	425.7	428.5	429.5	430.6	433.3	435.9
175°	421.5	420.7	422.3	422.3	423.1	424.8	426.4	425.6	426.4	427.2	429.7
177.5°	422.5	421.8	423.1	423.1	423.1	423.8	425.1	423.8	423.1	423.8	425.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	551.6	553.6	554.5	554.5	555.5	555.1	554.6
5°	583.3	586.9	587.7	590.9	593.4	592.6	593.0
7.5°	614.9	620.5	626.1	628.7	629.1	630.6	631.1
10°	634.3	639.0	647.6	646.4	652.8	656.6	650.4
12.5°	653.0	659.3	665.3	666.9	670.6	671.8	669.4
15°	669.8	673.2	673.5	672.6	673.8	672.8	669.3
17.5°	654.1	648.7	637.7	632.5	628.4	622.3	619.9
20°	628.0	612.0	593.5	586.1	577.5	560.4	564.5
22.5°	571.7	553.6	535.0	513.4	503.0	486.9	485.9
25°	484.1	452.8	418.3	394.3	380.2	364.1	357.0
27.5°	376.4	337.0	308.8	294.5	281.4	268.7	268.2
30°	305.6	276.0	254.1	241.9	233.9	228.5	229.7
32.5°	257.6	237.3	222.5	212.4	206.5	202.4	202.4
35°	210.6	196.7	187.2	183.0	178.7	175.8	175.9
37.5°	180.2	171.9	166.6	161.9	159.2	157.8	156.9
40°	164.6	157.8	153.7	150.9	148.7	146.7	146.3
42.5°	152.4	146.7	142.6	140.4	138.4	136.9	136.6
45°	135.2	130.5	126.9	124.4	123.5	122.2	122.2
47.5°	120.3	115.7	112.8	111.3	109.7	108.8	108.8
50°	110.2	106.6	104.1	103.1	101.8	101.3	101.1
52.5°	101.2	98.5	96.7	96.0	95.5	94.8	94.9
55°	88.9	87.4	86.7	86.1	85.2	84.1	84.8
57.5°	78.6	77.3	75.3	73.5	72.7	71.9	72.2
60°	71.3	68.7	66.1	64.1	63.5	61.9	61.9
62.5°	62.1	58.5	55.3	54.1	53.6	52.8	52.7
65°	47.8	46.3	45.6	44.8	44.4	44.4	44.1
67.5°	39.6	39.0	38.2	38.0	37.7	37.5	37.4
70°	35.0	34.2	33.9	33.7	33.3	33.5	32.9
72.5°	30.6	30.0	29.9	29.4	29.2	29.2	28.8
75°	24.1	24.1	23.9	23.7	23.3	23.2	23.3
77.5°	18.5	18.6	18.3	18.2	18.2	18.2	18.0
80°	14.8	15.0	14.8	14.6	14.4	14.6	14.4
82.5°	11.7	11.4	11.4	11.3	11.3	11.3	11.2
85°	6.7	6.8	6.7	6.5	6.5	6.5	6.7
87.5°	7.4	7.7	7.9	7.9	7.9	7.9	7.7
90°	24.4	26.0	26.8	26.8	26.8	26.8	26.8
92.5°	60.9	54.1	49.0	48.3	45.7	46.4	45.1
95°	163.5	129.4	111.5	100.9	94.4	92.0	92.8
97.5°	407.0	318.9	260.2	221.4	201.3	189.4	182.6
100°	642.0	530.5	432.1	364.5	329.5	306.0	291.3
102.5°	880.9	799.4	695.0	621.7	561.9	532.5	512.7
105°	1080.6	1091.2	1064.3	1013.8	963.4	928.4	917.0
107.5°	1065.9	1150.6	1189.9	1196.3	1193.5	1186.5	1171.4
110°	1020.3	1124.5	1191.2	1226.2	1241.7	1249.0	1248.2



TEST NUMBER: P331635-930

CATALOG NUMBER: S122RDIP-S290D925U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	966.4	1077.7	1154.1	1202.8	1228.7	1242.5	1246.9
115°	892.6	999.2	1083.0	1140.8	1178.2	1199.4	1206.7
117.5°	832.7	929.4	1008.0	1066.9	1106.4	1128.8	1134.9
120°	801.5	887.7	961.8	1018.7	1057.0	1080.6	1088.8
122.5°	775.4	857.1	924.1	975.1	1012.7	1033.7	1040.6
125°	741.3	812.9	873.9	921.1	952.0	972.3	978.8
127.5°	708.1	775.6	831.9	873.1	902.0	919.7	924.9
130°	685.9	750.2	804.0	843.8	871.5	887.7	894.2
132.5°	665.1	724.1	774.6	813.8	841.6	856.5	862.3
135°	632.3	685.9	731.5	766.5	793.4	808.0	811.2
137.5°	606.0	648.7	688.4	720.3	743.4	756.3	761.2
140°	589.1	626.6	662.3	688.4	709.6	721.8	726.6
142.5°	574.1	606.3	636.3	661.0	680.3	691.1	692.1
145°	555.0	580.2	603.7	623.3	637.2	645.2	647.7
147.5°	539.3	559.0	576.3	592.4	603.4	608.9	610.4
150°	528.9	546.0	560.6	572.8	582.6	587.5	588.3
152.5°	520.4	534.9	547.6	557.2	565.7	569.2	569.4
155°	507.0	519.1	528.1	537.0	542.7	546.0	544.4
157.5°	493.3	503.5	510.5	516.8	521.5	523.0	523.0
160°	484.1	493.1	498.8	504.5	508.6	509.4	509.4
162.5°	475.6	483.3	487.7	493.4	496.2	497.0	496.4
165°	463.0	468.7	472.0	475.2	478.4	478.4	477.6
167.5°	451.4	455.3	458.3	459.7	461.5	461.4	460.4
170°	444.3	447.5	449.1	450.0	452.4	451.6	450.0
172.5°	437.7	440.3	441.3	442.1	443.3	442.5	441.5
175°	430.5	431.3	432.1	432.1	432.9	432.1	430.5
177.5°	425.1	425.7	425.7	425.7	425.7	425.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)