

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331671-930

Luminaire Tested: **S122RDIP-S485D1080U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331671-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D1080U930-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4945.9 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31				
1	94	90	86	83	84	81	78	75	64	62	60	49	48	46	35	34	33	27				
2	86	79	73	69	77	71	67	62	57	54	51	43	41	39	31	30	29	23				
3	79	70	63	58	70	63	57	53	51	47	43	39	36	34	28	26	25	20				
4	72	62	55	49	65	56	50	45	45	41	37	35	32	30	25	24	22	18				
5	66	56	48	42	60	50	44	39	41	36	32	32	28	26	23	21	20	16				
6	61	50	42	37	55	45	39	34	37	32	28	29	25	23	21	19	17	14				
7	57	45	38	32	51	41	35	30	33	29	25	26	23	20	19	17	16	13				
8	53	41	34	29	47	37	31	27	31	26	22	24	21	18	18	16	14	12				
9	49	37	30	26	44	34	28	24	28	23	20	22	19	17	17	15	13	11				
10	46	34	28	23	41	31	25	21	26	21	18	21	17	15	16	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14149	14149	14149	14149
5°	15801	14237	12624	14237
10°	17531	14137	10942	14137
15°	18392	13929	8622	13929
20°	15945	13622	7459	13622
25°	10457	13201	6661	13201
30°	7040	12693	6027	12693
35°	5702	12051	5436	12051
40°	5069	11352	5031	11352
45°	4590	10533	4491	10533
50°	4175	9718	4160	9718
55°	3924	8819	3873	8819
60°	3284	7992	3242	7992
65°	2770	7259	3140	7259
70°	2559	6482	2960	6482
75°	2395	5639	2739	5639
80°	2204	4640	2436	4640
85°	2019	3668	2149	3668



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.1	1.7
10°-20°	231.5	4.7
20°-30°	298.2	6.0
30°-40°	283.4	5.7
40°-50°	242.8	4.9
50°-60°	184.9	3.7
60°-70°	116.9	2.4
70°-80°	58.4	1.2
80°-90°	19.6	0.4
90°-100°	196.9	4.0
100°-110°	668.2	13.5
110°-120°	709.9	14.4
120°-130°	584.4	11.8
130°-140°	469.3	9.5
140°-150°	354.6	7.2
150°-160°	249.2	5.0
160°-170°	146.7	3.0
170°-180°	47.8	1.0
0°-30°	612.8	12.4
0°-40°	896.2	18.1
0°-60°	1323.9	26.8
0°-90°	1518.8	30.7
90°-120°	1575.1	31.8
90°-150°	2983.4	60.3
90°-180°	3427.0	69.3
0°-180°	4945.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	876	876	876	876	876	
5°	975	878	779	878	975	96
15°	1100	833	516	833	1100	297
25°	587	741	374	741	587	279
35°	289	611	276	611	289	185
45°	201	461	197	461	201	156
55°	139	313	138	313	139	122
65°	72	190	82	190	72	74
75°	38	90	44	90	38	41
85°	11	20	12	20	11	13
90°	31	1	31	1	31	17
95°	108	33	108	33	108	140
105°	1067	116	1067	116	1067	1033
115°	1405	204	1405	204	1405	1375
125°	1139	284	1139	284	1139	1030
135°	944	333	944	333	944	734
145°	754	381	754	381	754	479
155°	634	433	634	433	634	296
165°	556	472	556	472	556	159
175°	501	492	501	492	501	49
180°	492	492	492	492	492	



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	911.8	912.6	913.3	911.6	911.6	910.1	906.9	904.5	897.6	896.7	896.7
5°	974.9	974.3	975.5	971.5	966.0	964.8	959.0	951.5	943.5	934.7	932.9
7.5°	1037.6	1036.7	1034.3	1033.6	1029.4	1020.2	1010.9	1000.9	987.8	974.9	968.5
10°	1069.3	1079.3	1073.3	1062.6	1064.7	1050.4	1042.8	1029.7	1018.7	999.6	995.3
12.5°	1100.4	1104.4	1102.4	1096.4	1093.7	1083.8	1073.5	1062.1	1041.9	1024.7	1009.7
15°	1100.3	1106.1	1107.7	1105.8	1107.3	1106.7	1101.2	1091.8	1074.2	1055.2	1038.9
17.5°	1019.1	1023.1	1033.1	1039.8	1048.4	1066.4	1075.3	1078.8	1076.1	1065.4	1053.8
20°	928.0	921.3	949.3	963.6	975.8	1006.2	1032.4	1042.4	1058.6	1058.3	1055.2
22.5°	798.9	800.5	827.0	844.0	879.6	910.0	939.9	977.7	1008.9	1029.6	1041.6
25°	587.0	598.6	625.1	648.2	687.8	744.4	795.9	855.6	911.8	956.3	998.7
27.5°	440.8	441.7	462.7	484.1	507.6	554.0	618.8	690.1	770.4	836.6	912.8
30°	377.6	375.7	384.6	397.6	417.8	453.6	502.4	572.4	652.5	752.4	841.2
32.5°	332.7	332.8	339.5	349.2	365.8	390.0	423.5	480.3	556.0	654.2	758.4
35°	289.3	288.9	293.8	300.8	307.8	323.3	346.2	376.0	428.1	519.8	626.3
37.5°	258.0	259.4	261.8	266.2	273.9	282.5	296.3	316.3	353.4	407.6	497.1
40°	240.5	241.2	244.5	248.2	252.7	259.4	270.7	286.8	313.9	357.1	422.6
42.5°	224.5	225.0	227.5	230.8	234.4	241.2	250.5	264.4	286.4	320.1	374.1
45°	201.0	201.0	203.1	204.6	208.6	214.7	222.3	233.8	249.1	274.0	310.0
47.5°	178.9	179.0	180.3	183.0	185.5	190.2	197.7	207.2	218.3	237.6	268.2
50°	166.2	166.6	167.5	169.6	171.1	175.4	181.2	189.4	201.0	215.9	241.4
52.5°	156.0	155.8	156.9	157.9	158.9	162.0	166.3	173.6	183.9	196.9	218.1
55°	139.4	138.2	140.1	141.5	142.5	143.7	146.1	150.7	159.6	170.5	186.3
57.5°	118.7	118.2	119.5	120.9	123.8	127.1	129.1	132.1	136.6	144.5	160.2
60°	101.7	101.7	104.4	105.3	108.7	112.9	117.2	119.7	124.3	129.4	141.0
62.5°	86.6	86.8	88.1	89.0	90.9	96.1	102.2	107.5	111.8	116.8	124.4
65°	72.5	73.1	73.1	73.7	74.9	76.1	78.5	82.8	90.4	97.4	103.2
67.5°	61.5	61.7	61.9	62.5	62.8	64.1	65.1	67.0	68.7	75.4	82.6
70°	54.2	55.1	54.8	55.4	55.7	56.3	57.6	58.5	61.2	62.7	67.0
72.5°	47.4	48.0	48.0	48.3	49.2	49.2	50.2	51.1	52.9	54.2	56.5
75°	38.4	38.1	38.4	39.0	39.3	39.5	39.5	40.8	41.7	43.0	44.4
77.5°	29.6	29.9	29.8	29.9	29.9	30.5	30.4	31.0	31.9	32.5	33.3
80°	23.7	24.1	23.7	24.1	24.4	24.6	24.4	24.6	25.6	26.2	26.2
82.5°	18.4	18.4	18.7	18.7	18.8	18.8	19.2	19.3	20.0	19.8	20.1
85°	10.9	10.7	10.7	10.7	10.9	11.3	10.9	10.9	11.3	11.3	11.3
87.5°	10.1	10.4	10.4	10.4	10.4	10.2	9.8	10.4	10.4	10.8	10.4
90°	31.2	31.2	31.2	31.2	31.2	30.3	28.5	30.3	31.2	32.2	31.2
92.5°	52.5	54.0	53.2	56.3	57.0	62.9	70.8	82.6	104.0	123.1	121.4
95°	107.9	107.0	109.9	117.4	129.7	150.6	190.4	248.2	324.9	371.3	328.6
97.5°	212.5	220.5	234.3	257.6	302.9	371.3	473.8	579.0	664.9	633.8	477.4
100°	339.1	356.1	383.6	424.3	502.9	617.5	747.3	864.7	884.6	748.2	515.2
102.5°	596.7	619.8	654.1	723.6	809.0	930.4	1025.3	1051.9	966.5	752.0	500.8
105°	1067.4	1080.7	1121.4	1180.1	1238.8	1270.1	1257.8	1150.7	953.7	701.8	472.6
107.5°	1363.4	1381.0	1389.2	1392.4	1385.0	1339.2	1240.7	1079.5	870.6	648.0	458.6
110°	1452.9	1453.8	1445.3	1427.3	1386.6	1308.9	1187.6	1018.1	818.3	622.2	455.6



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1451.3	1446.3	1430.1	1400.0	1343.4	1254.3	1124.8	962.1	782.0	605.6	456.3
115°	1404.6	1396.0	1371.4	1327.9	1260.6	1163.0	1039.0	893.2	736.9	587.2	460.3
117.5°	1321.0	1313.9	1287.8	1241.9	1173.3	1081.8	969.3	841.2	708.4	578.3	467.1
120°	1267.2	1257.8	1230.3	1185.8	1119.5	1033.3	932.9	815.5	693.2	573.0	471.7
122.5°	1211.1	1203.2	1178.8	1135.0	1075.5	997.7	902.6	795.0	680.4	570.0	477.0
125°	1139.4	1131.8	1108.2	1072.1	1017.2	946.2	862.8	765.2	662.0	564.5	484.9
127.5°	1076.5	1070.4	1049.9	1016.3	968.3	902.8	824.2	735.9	645.0	561.3	493.1
130°	1040.9	1033.3	1014.4	982.2	935.7	873.3	798.4	717.0	633.7	559.7	499.1
132.5°	1003.7	996.9	979.5	947.3	901.6	842.9	774.2	698.8	624.5	559.0	505.2
135°	944.3	940.4	923.4	892.2	851.4	798.4	735.9	673.4	611.8	557.8	512.4
137.5°	885.9	880.3	865.3	838.4	801.3	755.0	705.4	653.1	602.9	557.7	518.9
140°	845.8	840.1	825.9	801.3	770.9	729.3	685.7	640.3	597.6	556.9	521.9
142.5°	805.6	804.5	791.8	769.4	740.6	705.8	668.3	629.7	592.3	556.9	524.2
145°	753.9	751.1	741.6	725.5	702.8	675.3	646.0	614.7	585.3	555.0	526.6
147.5°	710.5	708.8	702.4	689.5	670.7	650.7	627.8	603.2	578.1	551.6	527.3
150°	684.8	683.8	678.2	666.8	652.6	635.5	615.6	594.8	572.0	549.3	526.6
152.5°	662.8	662.6	658.4	648.6	637.4	622.6	605.8	586.4	566.7	545.5	525.1
155°	633.7	635.5	631.7	625.1	614.7	604.2	590.0	574.9	556.9	538.9	522.8
157.5°	608.8	608.8	607.1	601.6	594.2	586.0	574.1	561.4	547.6	532.1	518.4
160°	592.9	592.9	591.9	587.2	580.6	574.0	563.5	553.1	540.8	527.6	516.2
162.5°	577.7	578.5	577.6	574.3	567.7	562.6	553.7	544.8	534.8	523.7	513.9
165°	556.0	556.9	556.9	553.1	549.3	545.5	538.9	532.3	524.7	516.2	509.6
167.5°	535.9	537.0	537.2	535.1	533.5	530.0	525.5	520.3	514.9	509.6	505.2
170°	523.7	525.6	526.6	523.7	522.8	520.9	517.1	514.3	509.6	505.7	502.9
172.5°	513.9	515.0	516.0	514.7	513.7	512.6	509.6	507.4	504.3	501.2	499.9
175°	501.0	502.9	503.9	502.9	502.9	502.0	501.0	500.1	497.3	496.3	495.4
177.5°	493.3	494.8	495.5	495.5	495.5	495.5	494.8	494.8	493.3	492.5	493.3
180°	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	897.2	895.3	893.6	889.2	887.0	882.1	881.3	881.1	874.8	868.7	867.0
5°	928.0	923.2	915.8	907.3	898.5	889.3	883.2	878.4	866.2	854.6	847.9
7.5°	959.0	948.6	936.0	919.8	906.4	891.3	880.1	870.0	852.7	836.2	825.0
10°	982.2	965.2	948.4	926.2	908.8	891.8	876.0	862.3	842.8	820.8	805.3
12.5°	996.5	977.8	954.7	933.0	910.5	888.8	867.6	850.0	827.2	804.5	786.0
15°	1016.0	995.9	967.9	936.9	907.9	879.6	855.2	833.3	803.5	776.4	753.8
17.5°	1031.9	1004.2	974.1	938.2	904.7	868.8	837.4	809.3	776.2	743.5	717.0
20°	1037.0	1009.6	974.9	939.0	899.4	857.0	823.3	792.8	757.2	721.5	691.1
22.5°	1033.8	1012.5	973.9	930.9	890.4	846.1	808.0	772.6	733.1	696.8	661.5
25°	1012.4	1005.0	968.5	921.6	875.3	823.9	779.8	741.0	696.0	657.0	618.6
27.5°	962.2	978.0	955.4	905.4	853.9	798.7	749.2	705.2	658.4	614.5	576.3
30°	914.0	950.2	940.4	894.2	836.7	782.4	726.8	680.8	630.9	585.8	548.0
32.5°	848.0	907.8	917.4	878.6	819.1	759.5	701.2	655.4	603.3	555.8	519.0
35°	742.9	832.4	873.5	848.8	789.1	725.0	664.6	611.4	559.0	512.1	475.6
37.5°	617.5	739.4	808.0	809.7	754.9	688.1	622.5	569.6	515.9	469.9	430.4
40°	536.1	668.3	757.5	777.3	731.0	658.8	592.5	538.6	486.2	441.2	395.8
42.5°	463.1	594.8	704.4	738.8	702.1	630.4	563.8	507.4	456.5	413.8	367.5
45°	374.5	489.6	610.4	672.0	651.6	585.1	514.9	461.3	413.4	376.6	332.2
47.5°	315.9	397.1	514.0	597.2	596.8	536.2	467.1	415.7	371.4	336.9	300.8
50°	282.5	353.2	452.2	546.5	554.4	503.6	437.8	386.9	345.6	309.3	280.4
52.5°	252.6	310.8	399.7	490.2	512.7	468.7	405.0	358.0	317.8	284.5	259.7
55°	213.4	258.4	326.1	410.7	444.8	413.8	357.1	313.3	280.7	252.7	231.4
57.5°	180.5	214.3	268.6	336.7	376.4	356.9	310.2	274.6	246.7	221.4	204.6
60°	159.9	187.5	233.5	290.5	334.3	320.6	280.7	247.5	223.8	201.9	186.1
62.5°	140.4	164.2	203.6	249.8	290.0	284.3	251.8	223.9	203.1	183.1	169.7
65°	112.9	130.3	161.0	197.3	229.6	232.3	208.9	190.0	171.4	155.6	143.7
67.5°	89.9	101.3	122.9	153.4	177.7	186.3	171.9	157.5	142.8	130.5	120.3
70°	75.8	85.0	100.8	125.5	147.7	156.8	148.5	137.3	124.5	114.5	105.7
72.5°	61.5	70.4	82.0	100.1	119.2	129.1	126.2	118.1	107.7	99.4	91.1
75°	46.3	49.0	56.9	69.1	84.1	92.5	94.7	90.4	82.2	75.8	70.9
77.5°	34.2	35.9	39.6	46.1	55.8	63.3	66.5	66.0	60.3	56.7	52.1
80°	27.4	28.3	30.2	32.9	40.2	47.8	49.9	49.9	46.0	44.4	39.9
82.5°	20.8	21.5	22.6	24.1	27.6	34.2	36.5	37.0	34.5	32.5	28.9
85°	11.9	11.6	12.1	13.1	13.7	15.5	19.2	19.8	19.2	16.7	15.8
87.5°	9.3	8.2	7.3	6.4	6.3	6.1	6.6	7.3	6.8	6.8	6.8
90°	25.6	18.9	14.2	11.3	9.5	7.6	3.8	1.0	3.8	7.6	9.5
92.5°	94.5	64.4	43.0	34.1	27.6	23.5	16.6	11.6	16.6	23.5	27.6
95°	218.7	136.4	92.8	70.1	55.0	46.4	36.9	33.2	36.9	46.4	55.0
97.5°	294.7	179.9	125.2	99.5	82.0	69.1	59.1	54.0	59.1	69.1	82.0
100°	310.6	195.1	144.9	118.4	99.5	84.3	75.7	72.9	75.7	84.3	99.5
102.5°	311.4	208.7	162.3	135.8	116.1	100.9	92.5	90.3	92.5	100.9	116.1
105°	316.3	232.0	187.5	161.0	140.1	126.0	119.4	115.5	119.4	126.0	140.1
107.5°	329.4	255.9	212.7	186.1	165.3	152.3	145.9	142.8	145.9	152.3	165.3
110°	340.0	271.8	230.2	202.7	182.8	170.5	164.8	161.0	164.8	170.5	182.8



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	351.4	287.0	246.8	218.6	199.4	187.9	181.5	177.7	181.5	187.9	199.4
115°	368.4	310.6	269.9	244.3	225.4	214.0	208.4	203.7	208.4	214.0	225.4
117.5°	386.6	332.4	294.7	268.2	250.1	240.0	234.3	230.6	234.3	240.0	250.1
120°	398.8	347.6	310.6	284.1	265.2	256.7	250.9	247.2	250.9	256.7	265.2
122.5°	409.4	362.0	327.3	300.0	281.1	271.8	266.1	263.1	266.1	271.8	281.1
125°	426.2	383.6	349.5	322.9	304.0	292.7	287.0	284.1	287.0	292.7	304.0
127.5°	441.9	403.7	370.5	343.2	325.1	312.6	304.6	300.8	304.6	312.6	325.1
130°	451.8	415.8	382.6	356.1	337.2	323.9	314.5	310.6	314.5	323.9	337.2
132.5°	461.6	426.4	394.8	368.3	348.5	334.5	324.3	319.8	324.3	334.5	348.5
135°	474.5	441.3	411.1	384.5	362.7	348.5	337.2	333.4	337.2	348.5	362.7
137.5°	484.4	453.5	423.5	398.9	377.3	362.2	350.8	346.3	350.8	362.2	377.3
140°	489.7	460.3	431.9	407.2	386.5	371.3	359.9	356.1	359.9	371.3	386.5
142.5°	494.2	465.6	438.0	414.8	394.8	379.6	369.0	366.0	369.0	379.6	394.8
145°	500.1	473.5	448.0	427.1	408.2	394.0	384.5	380.7	384.5	394.0	408.2
147.5°	503.3	480.0	455.9	437.4	421.7	408.5	399.5	396.6	399.5	408.5	421.7
150°	504.8	483.1	461.2	444.2	430.0	417.7	410.1	407.2	410.1	417.7	430.0
152.5°	505.6	486.1	466.5	451.0	437.6	426.7	419.2	417.8	419.2	426.7	437.6
155°	506.7	490.6	474.5	460.3	449.9	439.4	433.7	432.8	433.7	439.4	449.9
157.5°	506.7	493.8	480.2	468.2	459.9	450.9	446.3	445.3	446.3	450.9	459.9
160°	506.7	495.4	484.0	473.5	465.9	458.4	454.6	453.6	454.6	458.4	465.9
162.5°	506.0	496.1	486.2	478.1	471.2	465.2	461.5	462.0	461.5	465.2	471.2
165°	503.9	497.3	488.7	483.1	478.3	472.6	470.8	471.7	470.8	472.6	478.3
167.5°	502.6	497.0	490.8	487.2	483.8	480.2	478.5	479.6	478.5	480.2	483.8
170°	501.0	496.3	491.5	488.7	486.8	484.0	483.1	484.9	483.1	484.0	486.8
172.5°	498.7	495.5	492.3	490.2	489.1	486.2	486.8	488.0	486.8	486.2	489.1
175°	496.3	494.4	492.5	491.5	491.5	489.7	490.6	491.5	490.6	489.7	491.5
177.5°	494.8	493.3	492.5	492.5	492.5	491.0	491.7	493.3	491.7	491.0	492.5
180°	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	863.8	862.1	858.9	854.1	851.2	846.0	842.6	844.6	845.1	844.6	844.1
5°	840.7	834.2	825.4	816.8	808.9	800.5	795.6	793.4	789.1	786.8	785.5
7.5°	812.5	801.5	789.0	774.2	761.6	748.4	741.6	738.3	729.5	724.8	720.6
10°	791.6	774.2	761.7	742.2	730.4	713.1	701.2	701.5	689.6	682.9	678.0
12.5°	768.5	749.4	728.6	711.1	694.6	680.7	666.3	660.6	647.9	641.5	628.4
15°	730.1	707.8	686.0	662.2	645.5	623.9	603.2	577.9	557.5	539.8	534.9
17.5°	688.2	660.7	638.7	610.8	582.1	545.8	521.8	507.1	494.8	485.5	478.6
20°	659.5	631.4	608.1	566.0	527.3	502.6	485.0	473.8	461.0	450.9	445.4
22.5°	629.2	600.1	568.1	521.1	491.1	471.2	455.5	442.5	433.9	426.1	421.1
25°	586.4	554.4	501.7	469.4	445.2	424.4	413.4	405.5	396.4	385.7	380.9
27.5°	541.1	490.2	452.4	428.4	405.2	391.8	381.9	370.1	361.9	357.1	352.0
30°	507.2	456.4	426.9	400.6	384.3	369.3	357.8	351.1	343.2	334.9	331.6
32.5°	469.4	428.8	400.6	378.8	362.1	349.4	340.2	329.4	323.7	318.6	311.6
35°	422.6	391.8	366.0	348.3	332.5	322.1	311.4	305.1	294.7	290.5	287.7
37.5°	382.9	356.2	336.9	318.3	305.7	294.3	287.8	277.6	273.1	267.2	261.4
40°	360.4	334.3	315.8	300.5	286.5	277.9	269.8	261.5	254.9	252.1	245.1
42.5°	337.6	316.3	297.7	281.0	271.7	262.6	252.3	246.2	239.2	234.8	230.5
45°	306.0	287.1	271.3	257.6	247.2	237.8	231.1	221.0	217.1	208.2	204.6
47.5°	278.2	260.7	245.6	232.5	222.4	216.3	206.5	198.6	192.3	186.9	182.2
50°	258.4	243.9	229.3	217.7	208.6	199.7	189.7	185.7	175.9	173.3	170.5
52.5°	240.4	226.6	213.2	201.9	192.7	184.2	175.3	170.2	163.5	160.8	158.8
55°	215.2	201.9	189.1	179.0	169.9	161.0	155.6	149.2	146.1	144.0	141.5
57.5°	189.9	177.9	168.0	157.9	148.7	141.7	135.3	131.5	128.3	125.6	122.6
60°	173.8	162.2	153.4	144.0	134.6	128.8	123.9	119.4	115.7	111.5	110.2
62.5°	156.8	146.7	138.6	129.4	121.2	115.9	111.3	107.0	102.6	96.4	94.7
65°	133.4	125.5	116.9	109.3	102.0	96.9	90.1	85.3	83.4	82.8	82.5
67.5°	112.2	104.7	97.3	89.6	82.9	78.1	74.7	73.9	72.7	72.3	71.5
70°	98.0	91.1	83.7	76.4	70.0	69.1	67.9	66.7	65.1	64.6	63.9
72.5°	85.4	78.1	70.8	65.0	62.2	61.1	59.8	58.6	57.6	57.0	56.7
75°	65.5	58.8	53.9	51.8	50.2	49.3	47.5	46.6	46.0	45.1	44.8
77.5°	47.1	43.4	41.1	39.8	38.2	37.2	36.2	35.2	34.6	34.4	33.9
80°	36.0	34.1	32.6	30.7	30.2	28.9	28.6	27.7	28.0	27.1	27.1
82.5°	27.9	25.6	24.3	23.5	22.8	21.9	21.5	21.1	21.2	20.5	20.5
85°	14.3	13.7	13.1	12.5	12.5	11.6	11.9	11.6	11.6	10.9	10.7
87.5°	6.9	7.3	7.7	9.0	10.1	10.1	9.9	9.5	9.1	9.5	9.5
90°	11.3	14.2	18.9	25.6	31.2	32.2	31.2	30.3	28.5	30.3	31.2
92.5°	34.1	43.0	64.4	94.5	121.4	123.1	104.0	82.6	70.8	62.9	57.0
95°	70.1	92.8	136.4	218.7	328.6	371.3	324.9	248.2	190.4	150.6	129.7
97.5°	99.5	125.2	179.9	294.7	477.4	633.8	664.9	579.0	473.8	371.3	302.9
100°	118.4	144.9	195.1	310.6	515.2	748.2	884.6	864.7	747.3	617.5	502.9
102.5°	135.8	162.3	208.7	311.4	500.8	752.0	966.5	1051.9	1025.3	930.4	809.0
105°	161.0	187.5	232.0	316.3	472.6	701.8	953.7	1150.7	1257.8	1270.1	1238.8
107.5°	186.1	212.7	255.9	329.4	458.6	648.0	870.6	1079.5	1240.7	1339.2	1385.0
110°	202.7	230.2	271.8	340.0	455.6	622.2	818.3	1018.1	1187.6	1308.9	1386.6



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	218.6	246.8	287.0	351.4	456.3	605.6	782.0	962.1	1124.8	1254.3	1343.4
115°	244.3	269.9	310.6	368.4	460.3	587.2	736.9	893.2	1039.0	1163.0	1260.6
117.5°	268.2	294.7	332.4	386.6	467.1	578.3	708.4	841.2	969.3	1081.8	1173.3
120°	284.1	310.6	347.6	398.8	471.7	573.0	693.2	815.5	932.9	1033.3	1119.5
122.5°	300.0	327.3	362.0	409.4	477.0	570.0	680.4	795.0	902.6	997.7	1075.5
125°	322.9	349.5	383.6	426.2	484.9	564.5	662.0	765.2	862.8	946.2	1017.2
127.5°	343.2	370.5	403.7	441.9	493.1	561.3	645.0	735.9	824.2	902.8	968.3
130°	356.1	382.6	415.8	451.8	499.1	559.7	633.7	717.0	798.4	873.3	935.7
132.5°	368.3	394.8	426.4	461.6	505.2	559.0	624.5	698.8	774.2	842.9	901.6
135°	384.5	411.1	441.3	474.5	512.4	557.8	611.8	673.4	735.9	798.4	851.4
137.5°	398.9	423.5	453.5	484.4	518.9	557.7	602.9	653.1	705.4	755.0	801.3
140°	407.2	431.9	460.3	489.7	521.9	556.9	597.6	640.3	685.7	729.3	770.9
142.5°	414.8	438.0	465.6	494.2	524.2	556.9	592.3	629.7	668.3	705.8	740.6
145°	427.1	448.0	473.5	500.1	526.6	555.0	585.3	614.7	646.0	675.3	702.8
147.5°	437.4	455.9	480.0	503.3	527.3	551.6	578.1	603.2	627.8	650.7	670.7
150°	444.2	461.2	483.1	504.8	526.6	549.3	572.0	594.8	615.6	635.5	652.6
152.5°	451.0	466.5	486.1	505.6	525.1	545.5	566.7	586.4	605.8	622.6	637.4
155°	460.3	474.5	490.6	506.7	522.8	538.9	556.9	574.9	590.0	604.2	614.7
157.5°	468.2	480.2	493.8	506.7	518.4	532.1	547.6	561.4	574.1	586.0	594.2
160°	473.5	484.0	495.4	506.7	516.2	527.6	540.8	553.1	563.5	574.0	580.6
162.5°	478.1	486.2	496.1	506.0	513.9	523.7	534.8	544.8	553.7	562.6	567.7
165°	483.1	488.7	497.3	503.9	509.6	516.2	524.7	532.3	538.9	545.5	549.3
167.5°	487.2	490.8	497.0	502.6	505.2	509.6	514.9	520.3	525.5	530.0	533.5
170°	488.7	491.5	496.3	501.0	502.9	505.7	509.6	514.3	517.1	520.9	522.8
172.5°	490.2	492.3	495.5	498.7	499.9	501.2	504.3	507.4	509.6	512.6	513.7
175°	491.5	492.5	494.4	496.3	495.4	496.3	497.3	500.1	501.0	502.0	502.9
177.5°	492.5	492.5	493.3	494.8	493.3	492.5	493.3	494.8	494.8	495.5	495.5
180°	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	841.4	841.9	841.1	841.6	841.1	841.9	841.4	844.1	844.6	845.1	844.6
5°	784.0	780.3	779.8	778.9	779.8	780.3	784.0	785.5	786.8	789.1	793.4
7.5°	715.4	714.9	713.4	711.2	713.4	714.9	715.4	720.6	724.8	729.5	738.3
10°	671.3	669.8	669.5	667.4	669.5	669.8	671.3	678.0	682.9	689.6	701.5
12.5°	619.7	609.9	608.9	603.6	608.9	609.9	619.7	628.4	641.5	647.9	660.6
15°	527.7	525.8	519.8	515.8	519.8	525.8	527.7	534.9	539.8	557.5	577.9
17.5°	475.0	469.0	467.2	466.4	467.2	469.0	475.0	478.6	485.5	494.8	507.1
20°	441.2	435.7	434.8	434.1	434.8	435.7	441.2	445.4	450.9	461.0	473.8
22.5°	417.8	412.1	409.7	407.9	409.7	412.1	417.8	421.1	426.1	433.9	442.5
25°	377.8	375.7	374.5	373.9	374.5	375.7	377.8	380.9	385.7	396.4	405.5
27.5°	346.6	341.9	341.0	339.4	341.0	341.9	346.6	352.0	357.1	361.9	370.1
30°	328.8	327.3	325.1	323.3	325.1	327.3	328.8	331.6	334.9	343.2	351.1
32.5°	307.9	306.6	304.7	303.9	304.7	306.6	307.9	311.6	318.6	323.7	329.4
35°	284.7	280.4	278.6	275.8	278.6	280.4	284.7	287.7	290.5	294.7	305.1
37.5°	260.2	257.9	255.4	256.2	255.4	257.9	260.2	261.4	267.2	273.1	277.6
40°	241.2	239.6	239.0	238.7	239.0	239.6	241.2	245.1	252.1	254.9	261.5
42.5°	226.0	221.8	220.2	220.2	220.2	221.8	226.0	230.5	234.8	239.2	246.2
45°	203.1	199.1	196.4	196.7	196.4	199.1	203.1	204.6	208.2	217.1	221.0
47.5°	179.6	179.4	177.7	178.3	177.7	179.4	179.6	182.2	186.9	192.3	198.6
50°	168.4	166.6	165.3	165.6	165.3	166.6	168.4	170.5	173.3	175.9	185.7
52.5°	157.7	156.0	155.1	156.4	155.1	156.0	157.7	158.8	160.8	163.5	170.2
55°	140.1	138.2	137.9	137.6	137.9	138.2	140.1	141.5	144.0	146.1	149.2
57.5°	120.4	119.2	117.3	116.6	117.3	119.2	120.4	122.6	125.6	128.3	131.5
60°	106.2	103.8	100.8	100.4	100.8	103.8	106.2	110.2	111.5	115.7	119.4
62.5°	93.4	92.9	92.3	92.2	92.3	92.9	93.4	94.7	96.4	102.6	107.0
65°	81.9	81.6	81.9	82.2	81.9	81.6	81.9	82.5	82.8	83.4	85.3
67.5°	71.3	70.8	70.3	70.5	70.3	70.8	71.3	71.5	72.3	72.7	73.9
70°	63.3	63.0	62.7	62.7	62.7	63.0	63.3	63.9	64.6	65.1	66.7
72.5°	55.5	55.4	55.2	55.0	55.2	55.4	55.5	56.7	57.0	57.6	58.6
75°	44.4	43.9	43.9	43.9	43.9	43.9	44.4	44.8	45.1	46.0	46.6
77.5°	33.8	33.6	33.3	33.0	33.3	33.6	33.8	33.9	34.4	34.6	35.2
80°	26.8	26.5	26.2	26.2	26.2	26.5	26.8	27.1	27.1	28.0	27.7
82.5°	20.5	20.1	20.1	19.8	20.1	20.1	20.5	20.5	20.5	21.2	21.1
85°	10.9	11.3	10.9	11.6	10.9	11.3	10.9	10.7	10.9	11.6	11.6
87.5°	9.5	9.2	9.5	9.2	9.5	9.2	9.5	9.5	9.5	9.1	9.5
90°	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	30.3	28.5	30.3
92.5°	56.3	53.2	54.0	52.5	54.0	53.2	56.3	57.0	62.9	70.8	82.6
95°	117.4	109.9	107.0	107.9	107.0	109.9	117.4	129.7	150.6	190.4	248.2
97.5°	257.6	234.3	220.5	212.5	220.5	234.3	257.6	302.9	371.3	473.8	579.0
100°	424.3	383.6	356.1	339.1	356.1	383.6	424.3	502.9	617.5	747.3	864.7
102.5°	723.6	654.1	619.8	596.7	619.8	654.1	723.6	809.0	930.4	1025.3	1051.9
105°	1180.1	1121.4	1080.7	1067.4	1080.7	1121.4	1180.1	1238.8	1270.1	1257.8	1150.7
107.5°	1392.4	1389.2	1381.0	1363.4	1381.0	1389.2	1392.4	1385.0	1339.2	1240.7	1079.5
110°	1427.3	1445.3	1453.8	1452.9	1453.8	1445.3	1427.3	1386.6	1308.9	1187.6	1018.1



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1400.0	1430.1	1446.3	1451.3	1446.3	1430.1	1400.0	1343.4	1254.3	1124.8	962.1
115°	1327.9	1371.4	1396.0	1404.6	1396.0	1371.4	1327.9	1260.6	1163.0	1039.0	893.2
117.5°	1241.9	1287.8	1313.9	1321.0	1313.9	1287.8	1241.9	1173.3	1081.8	969.3	841.2
120°	1185.8	1230.3	1257.8	1267.2	1257.8	1230.3	1185.8	1119.5	1033.3	932.9	815.5
122.5°	1135.0	1178.8	1203.2	1211.1	1203.2	1178.8	1135.0	1075.5	997.7	902.6	795.0
125°	1072.1	1108.2	1131.8	1139.4	1131.8	1108.2	1072.1	1017.2	946.2	862.8	765.2
127.5°	1016.3	1049.9	1070.4	1076.5	1070.4	1049.9	1016.3	968.3	902.8	824.2	735.9
130°	982.2	1014.4	1033.3	1040.9	1033.3	1014.4	982.2	935.7	873.3	798.4	717.0
132.5°	947.3	979.5	996.9	1003.7	996.9	979.5	947.3	901.6	842.9	774.2	698.8
135°	892.2	923.4	940.4	944.3	940.4	923.4	892.2	851.4	798.4	735.9	673.4
137.5°	838.4	865.3	880.3	885.9	880.3	865.3	838.4	801.3	755.0	705.4	653.1
140°	801.3	825.9	840.1	845.8	840.1	825.9	801.3	770.9	729.3	685.7	640.3
142.5°	769.4	791.8	804.5	805.6	804.5	791.8	769.4	740.6	705.8	668.3	629.7
145°	725.5	741.6	751.1	753.9	751.1	741.6	725.5	702.8	675.3	646.0	614.7
147.5°	689.5	702.4	708.8	710.5	708.8	702.4	689.5	670.7	650.7	627.8	603.2
150°	666.8	678.2	683.8	684.8	683.8	678.2	666.8	652.6	635.5	615.6	594.8
152.5°	648.6	658.4	662.6	662.8	662.6	658.4	648.6	637.4	622.6	605.8	586.4
155°	625.1	631.7	635.5	633.7	635.5	631.7	625.1	614.7	604.2	590.0	574.9
157.5°	601.6	607.1	608.8	608.8	608.8	607.1	601.6	594.2	586.0	574.1	561.4
160°	587.2	591.9	592.9	592.9	592.9	591.9	587.2	580.6	574.0	563.5	553.1
162.5°	574.3	577.6	578.5	577.7	578.5	577.6	574.3	567.7	562.6	553.7	544.8
165°	553.1	556.9	556.9	556.0	556.9	556.9	553.1	549.3	545.5	538.9	532.3
167.5°	535.1	537.2	537.0	535.9	537.0	537.2	535.1	533.5	530.0	525.5	520.3
170°	523.7	526.6	525.6	523.7	525.6	526.6	523.7	522.8	520.9	517.1	514.3
172.5°	514.7	516.0	515.0	513.9	515.0	516.0	514.7	513.7	512.6	509.6	507.4
175°	502.9	503.9	502.9	501.0	502.9	503.9	502.9	502.9	502.0	501.0	500.1
177.5°	495.5	495.5	494.8	493.3	494.8	495.5	495.5	495.5	495.5	494.8	494.8
180°	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	842.6	846.0	851.2	854.1	858.9	862.1	863.8	867.0	868.7	874.8	881.1
5°	795.6	800.5	808.9	816.8	825.4	834.2	840.7	847.9	854.6	866.2	878.4
7.5°	741.6	748.4	761.6	774.2	789.0	801.5	812.5	825.0	836.2	852.7	870.0
10°	701.2	713.1	730.4	742.2	761.7	774.2	791.6	805.3	820.8	842.8	862.3
12.5°	666.3	680.7	694.6	711.1	728.6	749.4	768.5	786.0	804.5	827.2	850.0
15°	603.2	623.9	645.5	662.2	686.0	707.8	730.1	753.8	776.4	803.5	833.3
17.5°	521.8	545.8	582.1	610.8	638.7	660.7	688.2	717.0	743.5	776.2	809.3
20°	485.0	502.6	527.3	566.0	608.1	631.4	659.5	691.1	721.5	757.2	792.8
22.5°	455.5	471.2	491.1	521.1	568.1	600.1	629.2	661.5	696.8	733.1	772.6
25°	413.4	424.4	445.2	469.4	501.7	554.4	586.4	618.6	657.0	696.0	741.0
27.5°	381.9	391.8	405.2	428.4	452.4	490.2	541.1	576.3	614.5	658.4	705.2
30°	357.8	369.3	384.3	400.6	426.9	456.4	507.2	548.0	585.8	630.9	680.8
32.5°	340.2	349.4	362.1	378.8	400.6	428.8	469.4	519.0	555.8	603.3	655.4
35°	311.4	322.1	332.5	348.3	366.0	391.8	422.6	475.6	512.1	559.0	611.4
37.5°	287.8	294.3	305.7	318.3	336.9	356.2	382.9	430.4	469.9	515.9	569.6
40°	269.8	277.9	286.5	300.5	315.8	334.3	360.4	395.8	441.2	486.2	538.6
42.5°	252.3	262.6	271.7	281.0	297.7	316.3	337.6	367.5	413.8	456.5	507.4
45°	231.1	237.8	247.2	257.6	271.3	287.1	306.0	332.2	376.6	413.4	461.3
47.5°	206.5	216.3	222.4	232.5	245.6	260.7	278.2	300.8	336.9	371.4	415.7
50°	189.7	199.7	208.6	217.7	229.3	243.9	258.4	280.4	309.3	345.6	386.9
52.5°	175.3	184.2	192.7	201.9	213.2	226.6	240.4	259.7	284.5	317.8	358.0
55°	155.6	161.0	169.9	179.0	189.1	201.9	215.2	231.4	252.7	280.7	313.3
57.5°	135.3	141.7	148.7	157.9	168.0	177.9	189.9	204.6	221.4	246.7	274.6
60°	123.9	128.8	134.6	144.0	153.4	162.2	173.8	186.1	201.9	223.8	247.5
62.5°	111.3	115.9	121.2	129.4	138.6	146.7	156.8	169.7	183.1	203.1	223.9
65°	90.1	96.9	102.0	109.3	116.9	125.5	133.4	143.7	155.6	171.4	190.0
67.5°	74.7	78.1	82.9	89.6	97.3	104.7	112.2	120.3	130.5	142.8	157.5
70°	67.9	69.1	70.0	76.4	83.7	91.1	98.0	105.7	114.5	124.5	137.3
72.5°	59.8	61.1	62.2	65.0	70.8	78.1	85.4	91.1	99.4	107.7	118.1
75°	47.5	49.3	50.2	51.8	53.9	58.8	65.5	70.9	75.8	82.2	90.4
77.5°	36.2	37.2	38.2	39.8	41.1	43.4	47.1	52.1	56.7	60.3	66.0
80°	28.6	28.9	30.2	30.7	32.6	34.1	36.0	39.9	44.4	46.0	49.9
82.5°	21.5	21.9	22.8	23.5	24.3	25.6	27.9	28.9	32.5	34.5	37.0
85°	11.9	11.6	12.5	12.5	13.1	13.7	14.3	15.8	16.7	19.2	19.8
87.5°	9.9	10.1	10.1	9.0	7.7	7.3	6.9	6.8	6.8	6.8	7.3
90°	31.2	32.2	31.2	25.6	18.9	14.2	11.3	9.5	7.6	3.8	1.0
92.5°	104.0	123.1	121.4	94.5	64.4	43.0	34.1	27.6	23.5	16.6	11.6
95°	324.9	371.3	328.6	218.7	136.4	92.8	70.1	55.0	46.4	36.9	33.2
97.5°	664.9	633.8	477.4	294.7	179.9	125.2	99.5	82.0	69.1	59.1	54.0
100°	884.6	748.2	515.2	310.6	195.1	144.9	118.4	99.5	84.3	75.7	72.9
102.5°	966.5	752.0	500.8	311.4	208.7	162.3	135.8	116.1	100.9	92.5	90.3
105°	953.7	701.8	472.6	316.3	232.0	187.5	161.0	140.1	126.0	119.4	115.5
107.5°	870.6	648.0	458.6	329.4	255.9	212.7	186.1	165.3	152.3	145.9	142.8
110°	818.3	622.2	455.6	340.0	271.8	230.2	202.7	182.8	170.5	164.8	161.0



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	782.0	605.6	456.3	351.4	287.0	246.8	218.6	199.4	187.9	181.5	177.7
115°	736.9	587.2	460.3	368.4	310.6	269.9	244.3	225.4	214.0	208.4	203.7
117.5°	708.4	578.3	467.1	386.6	332.4	294.7	268.2	250.1	240.0	234.3	230.6
120°	693.2	573.0	471.7	398.8	347.6	310.6	284.1	265.2	256.7	250.9	247.2
122.5°	680.4	570.0	477.0	409.4	362.0	327.3	300.0	281.1	271.8	266.1	263.1
125°	662.0	564.5	484.9	426.2	383.6	349.5	322.9	304.0	292.7	287.0	284.1
127.5°	645.0	561.3	493.1	441.9	403.7	370.5	343.2	325.1	312.6	304.6	300.8
130°	633.7	559.7	499.1	451.8	415.8	382.6	356.1	337.2	323.9	314.5	310.6
132.5°	624.5	559.0	505.2	461.6	426.4	394.8	368.3	348.5	334.5	324.3	319.8
135°	611.8	557.8	512.4	474.5	441.3	411.1	384.5	362.7	348.5	337.2	333.4
137.5°	602.9	557.7	518.9	484.4	453.5	423.5	398.9	377.3	362.2	350.8	346.3
140°	597.6	556.9	521.9	489.7	460.3	431.9	407.2	386.5	371.3	359.9	356.1
142.5°	592.3	556.9	524.2	494.2	465.6	438.0	414.8	394.8	379.6	369.0	366.0
145°	585.3	555.0	526.6	500.1	473.5	448.0	427.1	408.2	394.0	384.5	380.7
147.5°	578.1	551.6	527.3	503.3	480.0	455.9	437.4	421.7	408.5	399.5	396.6
150°	572.0	549.3	526.6	504.8	483.1	461.2	444.2	430.0	417.7	410.1	407.2
152.5°	566.7	545.5	525.1	505.6	486.1	466.5	451.0	437.6	426.7	419.2	417.8
155°	556.9	538.9	522.8	506.7	490.6	474.5	460.3	449.9	439.4	433.7	432.8
157.5°	547.6	532.1	518.4	506.7	493.8	480.2	468.2	459.9	450.9	446.3	445.3
160°	540.8	527.6	516.2	506.7	495.4	484.0	473.5	465.9	458.4	454.6	453.6
162.5°	534.8	523.7	513.9	506.0	496.1	486.2	478.1	471.2	465.2	461.5	462.0
165°	524.7	516.2	509.6	503.9	497.3	488.7	483.1	478.3	472.6	470.8	471.7
167.5°	514.9	509.6	505.2	502.6	497.0	490.8	487.2	483.8	480.2	478.5	479.6
170°	509.6	505.7	502.9	501.0	496.3	491.5	488.7	486.8	484.0	483.1	484.9
172.5°	504.3	501.2	499.9	498.7	495.5	492.3	490.2	489.1	486.2	486.8	488.0
175°	497.3	496.3	495.4	496.3	494.4	492.5	491.5	491.5	489.7	490.6	491.5
177.5°	493.3	492.5	493.3	494.8	493.3	492.5	492.5	492.5	491.0	491.7	493.3
180°	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	881.3	882.1	887.0	889.2	893.6	895.3	897.2	896.7	896.7	897.6	904.5
5°	883.2	889.3	898.5	907.3	915.8	923.2	928.0	932.9	934.7	943.5	951.5
7.5°	880.1	891.3	906.4	919.8	936.0	948.6	959.0	968.5	974.9	987.8	1000.9
10°	876.0	891.8	908.8	926.2	948.4	965.2	982.2	995.3	999.6	1018.7	1029.7
12.5°	867.6	888.8	910.5	933.0	954.7	977.8	996.5	1009.7	1024.7	1041.9	1062.1
15°	855.2	879.6	907.9	936.9	967.9	995.9	1016.0	1038.9	1055.2	1074.2	1091.8
17.5°	837.4	868.8	904.7	938.2	974.1	1004.2	1031.9	1053.8	1065.4	1076.1	1078.8
20°	823.3	857.0	899.4	939.0	974.9	1009.6	1037.0	1055.2	1058.3	1058.6	1042.4
22.5°	808.0	846.1	890.4	930.9	973.9	1012.5	1033.8	1041.6	1029.6	1008.9	977.7
25°	779.8	823.9	875.3	921.6	968.5	1005.0	1012.4	998.7	956.3	911.8	855.6
27.5°	749.2	798.7	853.9	905.4	955.4	978.0	962.2	912.8	836.6	770.4	690.1
30°	726.8	782.4	836.7	894.2	940.4	950.2	914.0	841.2	752.4	652.5	572.4
32.5°	701.2	759.5	819.1	878.6	917.4	907.8	848.0	758.4	654.2	556.0	480.3
35°	664.6	725.0	789.1	848.8	873.5	832.4	742.9	626.3	519.8	428.1	376.0
37.5°	622.5	688.1	754.9	809.7	808.0	739.4	617.5	497.1	407.6	353.4	316.3
40°	592.5	658.8	731.0	777.3	757.5	668.3	536.1	422.6	357.1	313.9	286.8
42.5°	563.8	630.4	702.1	738.8	704.4	594.8	463.1	374.1	320.1	286.4	264.4
45°	514.9	585.1	651.6	672.0	610.4	489.6	374.5	310.0	274.0	249.1	233.8
47.5°	467.1	536.2	596.8	597.2	514.0	397.1	315.9	268.2	237.6	218.3	207.2
50°	437.8	503.6	554.4	546.5	452.2	353.2	282.5	241.4	215.9	201.0	189.4
52.5°	405.0	468.7	512.7	490.2	399.7	310.8	252.6	218.1	196.9	183.9	173.6
55°	357.1	413.8	444.8	410.7	326.1	258.4	213.4	186.3	170.5	159.6	150.7
57.5°	310.2	356.9	376.4	336.7	268.6	214.3	180.5	160.2	144.5	136.6	132.1
60°	280.7	320.6	334.3	290.5	233.5	187.5	159.9	141.0	129.4	124.3	119.7
62.5°	251.8	284.3	290.0	249.8	203.6	164.2	140.4	124.4	116.8	111.8	107.5
65°	208.9	232.3	229.6	197.3	161.0	130.3	112.9	103.2	97.4	90.4	82.8
67.5°	171.9	186.3	177.7	153.4	122.9	101.3	89.9	82.6	75.4	68.7	67.0
70°	148.5	156.8	147.7	125.5	100.8	85.0	75.8	67.0	62.7	61.2	58.5
72.5°	126.2	129.1	119.2	100.1	82.0	70.4	61.5	56.5	54.2	52.9	51.1
75°	94.7	92.5	84.1	69.1	56.9	49.0	46.3	44.4	43.0	41.7	40.8
77.5°	66.5	63.3	55.8	46.1	39.6	35.9	34.2	33.3	32.5	31.9	31.0
80°	49.9	47.8	40.2	32.9	30.2	28.3	27.4	26.2	26.2	25.6	24.6
82.5°	36.5	34.2	27.6	24.1	22.6	21.5	20.8	20.1	19.8	20.0	19.3
85°	19.2	15.5	13.7	13.1	12.1	11.6	11.9	11.3	11.3	11.3	10.9
87.5°	6.6	6.1	6.3	6.4	7.3	8.2	9.3	10.4	10.8	10.4	10.4
90°	3.8	7.6	9.5	11.3	14.2	18.9	25.6	31.2	32.2	31.2	30.3
92.5°	16.6	23.5	27.6	34.1	43.0	64.4	94.5	121.4	123.1	104.0	82.6
95°	36.9	46.4	55.0	70.1	92.8	136.4	218.7	328.6	371.3	324.9	248.2
97.5°	59.1	69.1	82.0	99.5	125.2	179.9	294.7	477.4	633.8	664.9	579.0
100°	75.7	84.3	99.5	118.4	144.9	195.1	310.6	515.2	748.2	884.6	864.7
102.5°	92.5	100.9	116.1	135.8	162.3	208.7	311.4	500.8	752.0	966.5	1051.9
105°	119.4	126.0	140.1	161.0	187.5	232.0	316.3	472.6	701.8	953.7	1150.7
107.5°	145.9	152.3	165.3	186.1	212.7	255.9	329.4	458.6	648.0	870.6	1079.5
110°	164.8	170.5	182.8	202.7	230.2	271.8	340.0	455.6	622.2	818.3	1018.1



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	181.5	187.9	199.4	218.6	246.8	287.0	351.4	456.3	605.6	782.0	962.1
115°	208.4	214.0	225.4	244.3	269.9	310.6	368.4	460.3	587.2	736.9	893.2
117.5°	234.3	240.0	250.1	268.2	294.7	332.4	386.6	467.1	578.3	708.4	841.2
120°	250.9	256.7	265.2	284.1	310.6	347.6	398.8	471.7	573.0	693.2	815.5
122.5°	266.1	271.8	281.1	300.0	327.3	362.0	409.4	477.0	570.0	680.4	795.0
125°	287.0	292.7	304.0	322.9	349.5	383.6	426.2	484.9	564.5	662.0	765.2
127.5°	304.6	312.6	325.1	343.2	370.5	403.7	441.9	493.1	561.3	645.0	735.9
130°	314.5	323.9	337.2	356.1	382.6	415.8	451.8	499.1	559.7	633.7	717.0
132.5°	324.3	334.5	348.5	368.3	394.8	426.4	461.6	505.2	559.0	624.5	698.8
135°	337.2	348.5	362.7	384.5	411.1	441.3	474.5	512.4	557.8	611.8	673.4
137.5°	350.8	362.2	377.3	398.9	423.5	453.5	484.4	518.9	557.7	602.9	653.1
140°	359.9	371.3	386.5	407.2	431.9	460.3	489.7	521.9	556.9	597.6	640.3
142.5°	369.0	379.6	394.8	414.8	438.0	465.6	494.2	524.2	556.9	592.3	629.7
145°	384.5	394.0	408.2	427.1	448.0	473.5	500.1	526.6	555.0	585.3	614.7
147.5°	399.5	408.5	421.7	437.4	455.9	480.0	503.3	527.3	551.6	578.1	603.2
150°	410.1	417.7	430.0	444.2	461.2	483.1	504.8	526.6	549.3	572.0	594.8
152.5°	419.2	426.7	437.6	451.0	466.5	486.1	505.6	525.1	545.5	566.7	586.4
155°	433.7	439.4	449.9	460.3	474.5	490.6	506.7	522.8	538.9	556.9	574.9
157.5°	446.3	450.9	459.9	468.2	480.2	493.8	506.7	518.4	532.1	547.6	561.4
160°	454.6	458.4	465.9	473.5	484.0	495.4	506.7	516.2	527.6	540.8	553.1
162.5°	461.5	465.2	471.2	478.1	486.2	496.1	506.0	513.9	523.7	534.8	544.8
165°	470.8	472.6	478.3	483.1	488.7	497.3	503.9	509.6	516.2	524.7	532.3
167.5°	478.5	480.2	483.8	487.2	490.8	497.0	502.6	505.2	509.6	514.9	520.3
170°	483.1	484.0	486.8	488.7	491.5	496.3	501.0	502.9	505.7	509.6	514.3
172.5°	486.8	486.2	489.1	490.2	492.3	495.5	498.7	499.9	501.2	504.3	507.4
175°	490.6	489.7	491.5	491.5	492.5	494.4	496.3	495.4	496.3	497.3	500.1
177.5°	491.7	491.0	492.5	492.5	492.5	493.3	494.8	493.3	492.5	493.3	494.8
180°	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5	492.5



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	906.9	910.1	911.6	911.6	913.3	912.6	911.8
5°	959.0	964.8	966.0	971.5	975.5	974.3	974.9
7.5°	1010.9	1020.2	1029.4	1033.6	1034.3	1036.7	1037.6
10°	1042.8	1050.4	1064.7	1062.6	1073.3	1079.3	1069.3
12.5°	1073.5	1083.8	1093.7	1096.4	1102.4	1104.4	1100.4
15°	1101.2	1106.7	1107.3	1105.8	1107.7	1106.1	1100.3
17.5°	1075.3	1066.4	1048.4	1039.8	1033.1	1023.1	1019.1
20°	1032.4	1006.2	975.8	963.6	949.3	921.3	928.0
22.5°	939.9	910.0	879.6	844.0	827.0	800.5	798.9
25°	795.9	744.4	687.8	648.2	625.1	598.6	587.0
27.5°	618.8	554.0	507.6	484.1	462.7	441.7	440.8
30°	502.4	453.6	417.8	397.6	384.6	375.7	377.6
32.5°	423.5	390.0	365.8	349.2	339.5	332.8	332.7
35°	346.2	323.3	307.8	300.8	293.8	288.9	289.3
37.5°	296.3	282.5	273.9	266.2	261.8	259.4	258.0
40°	270.7	259.4	252.7	248.2	244.5	241.2	240.5
42.5°	250.5	241.2	234.4	230.8	227.5	225.0	224.5
45°	222.3	214.7	208.6	204.6	203.1	201.0	201.0
47.5°	197.7	190.2	185.5	183.0	180.3	179.0	178.9
50°	181.2	175.4	171.1	169.6	167.5	166.6	166.2
52.5°	166.3	162.0	158.9	157.9	156.9	155.8	156.0
55°	146.1	143.7	142.5	141.5	140.1	138.2	139.4
57.5°	129.1	127.1	123.8	120.9	119.5	118.2	118.7
60°	117.2	112.9	108.7	105.3	104.4	101.7	101.7
62.5°	102.2	96.1	90.9	89.0	88.1	86.8	86.6
65°	78.5	76.1	74.9	73.7	73.1	73.1	72.5
67.5°	65.1	64.1	62.8	62.5	61.9	61.7	61.5
70°	57.6	56.3	55.7	55.4	54.8	55.1	54.2
72.5°	50.2	49.2	49.2	48.3	48.0	48.0	47.4
75°	39.5	39.5	39.3	39.0	38.4	38.1	38.4
77.5°	30.4	30.5	29.9	29.9	29.8	29.9	29.6
80°	24.4	24.6	24.4	24.1	23.7	24.1	23.7
82.5°	19.2	18.8	18.8	18.7	18.7	18.4	18.4
85°	10.9	11.3	10.9	10.7	10.7	10.7	10.9
87.5°	9.8	10.2	10.4	10.4	10.4	10.4	10.1
90°	28.5	30.3	31.2	31.2	31.2	31.2	31.2
92.5°	70.8	62.9	57.0	56.3	53.2	54.0	52.5
95°	190.4	150.6	129.7	117.4	109.9	107.0	107.9
97.5°	473.8	371.3	302.9	257.6	234.3	220.5	212.5
100°	747.3	617.5	502.9	424.3	383.6	356.1	339.1
102.5°	1025.3	930.4	809.0	723.6	654.1	619.8	596.7
105°	1257.8	1270.1	1238.8	1180.1	1121.4	1080.7	1067.4
107.5°	1240.7	1339.2	1385.0	1392.4	1389.2	1381.0	1363.4
110°	1187.6	1308.9	1386.6	1427.3	1445.3	1453.8	1452.9



TEST NUMBER: P331671-930

CATALOG NUMBER: S122RDIP-S485D1080U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1124.8	1254.3	1343.4	1400.0	1430.1	1446.3	1451.3
115°	1039.0	1163.0	1260.6	1327.9	1371.4	1396.0	1404.6
117.5°	969.3	1081.8	1173.3	1241.9	1287.8	1313.9	1321.0
120°	932.9	1033.3	1119.5	1185.8	1230.3	1257.8	1267.2
122.5°	902.6	997.7	1075.5	1135.0	1178.8	1203.2	1211.1
125°	862.8	946.2	1017.2	1072.1	1108.2	1131.8	1139.4
127.5°	824.2	902.8	968.3	1016.3	1049.9	1070.4	1076.5
130°	798.4	873.3	935.7	982.2	1014.4	1033.3	1040.9
132.5°	774.2	842.9	901.6	947.3	979.5	996.9	1003.7
135°	735.9	798.4	851.4	892.2	923.4	940.4	944.3
137.5°	705.4	755.0	801.3	838.4	865.3	880.3	885.9
140°	685.7	729.3	770.9	801.3	825.9	840.1	845.8
142.5°	668.3	705.8	740.6	769.4	791.8	804.5	805.6
145°	646.0	675.3	702.8	725.5	741.6	751.1	753.9
147.5°	627.8	650.7	670.7	689.5	702.4	708.8	710.5
150°	615.6	635.5	652.6	666.8	678.2	683.8	684.8
152.5°	605.8	622.6	637.4	648.6	658.4	662.6	662.8
155°	590.0	604.2	614.7	625.1	631.7	635.5	633.7
157.5°	574.1	586.0	594.2	601.6	607.1	608.8	608.8
160°	563.5	574.0	580.6	587.2	591.9	592.9	592.9
162.5°	553.7	562.6	567.7	574.3	577.6	578.5	577.7
165°	538.9	545.5	549.3	553.1	556.9	556.9	556.0
167.5°	525.5	530.0	533.5	535.1	537.2	537.0	535.9
170°	517.1	520.9	522.8	523.7	526.6	525.6	523.7
172.5°	509.6	512.6	513.7	514.7	516.0	515.0	513.9
175°	501.0	502.0	502.9	502.9	503.9	502.9	501.0
177.5°	494.8	495.5	495.5	495.5	495.5	494.8	493.3
180°	492.5	492.5	492.5	492.5	492.5	492.5	492.5

(END OF REPORT)