

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331652-930

Luminaire Tested: **S122RDIP-S485D530U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331652-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D530U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3057.1 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	91	88	91	87	84	81	74	72	70	62	60	59	50	49	49	43
2	90	83	78	73	83	77	72	68	66	62	59	55	53	50	45	44	42	38
3	83	74	67	62	76	69	63	58	59	54	51	50	46	44	41	39	37	33
4	76	66	59	53	70	62	55	50	53	48	44	45	41	38	37	35	33	29
5	70	59	52	46	65	55	49	44	48	43	39	41	37	34	34	31	29	26
6	65	54	46	40	60	50	43	38	43	38	34	37	33	30	31	28	26	23
7	61	49	41	36	56	46	39	34	40	34	30	34	30	27	29	26	23	21
8	56	45	37	32	52	42	35	31	36	31	27	31	27	24	27	24	21	19
9	53	41	34	29	49	38	32	28	34	28	25	29	25	22	25	22	20	17
10	49	38	31	26	46	35	29	25	31	26	23	27	23	20	23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14149	14149	14149	14149
5°	15801	14237	12624	14237
10°	17531	14137	10942	14137
15°	18392	13929	8622	13929
20°	15945	13622	7459	13622
25°	10457	13201	6661	13201
30°	7040	12693	6027	12693
35°	5702	12051	5436	12051
40°	5069	11352	5031	11352
45°	4590	10533	4491	10533
50°	4175	9718	4160	9718
55°	3924	8819	3873	8819
60°	3284	7992	3242	7992
65°	2770	7259	3140	7259
70°	2559	6482	2960	6482
75°	2395	5639	2739	5639
80°	2204	4640	2436	4640
85°	2019	3668	2149	3668



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.1	2.7
10°-20°	231.5	7.6
20°-30°	298.2	9.8
30°-40°	283.4	9.3
40°-50°	242.8	7.9
50°-60°	184.9	6.0
60°-70°	116.9	3.8
70°-80°	58.4	1.9
80°-90°	17.4	0.6
90°-100°	34.9	1.1
100°-110°	108.4	3.5
110°-120°	185.3	6.1
120°-130°	243.7	8.0
130°-140°	273.5	8.9
140°-150°	268.2	8.8
150°-160°	225.0	7.4
160°-170°	149.2	4.9
170°-180°	52.2	1.7
0°-30°	612.8	20.0
0°-40°	896.2	29.3
0°-60°	1323.9	43.3
0°-90°	1516.6	49.6
90°-120°	328.7	10.8
90°-150°	1114.2	36.4
90°-180°	1540.0	50.4
0°-180°	3057.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	876	876	876	876	876	
5°	975	878	779	878	975	96
15°	1100	833	516	833	1100	297
25°	587	741	374	741	587	279
35°	289	611	276	611	289	185
45°	201	461	197	461	201	156
55°	139	313	138	313	139	122
65°	72	190	82	190	72	74
75°	38	90	44	90	38	41
85°	11	20	12	20	11	12
90°	16	0	16	0	16	7
95°	29	24	29	24	29	32
105°	103	100	103	100	103	109
115°	186	186	186	186	186	184
125°	272	271	272	271	272	242
135°	354	350	354	350	354	273
145°	430	425	430	425	430	268
155°	490	486	490	486	490	225
165°	529	529	529	529	529	149
175°	548	550	548	550	548	52
180°	551	551	551	551	551	



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	911.8	912.6	913.3	911.6	911.6	910.1	906.9	904.5	897.6	896.7	896.7
5°	974.9	974.3	975.5	971.5	966.0	964.8	959.0	951.5	943.5	934.7	932.9
7.5°	1037.6	1036.7	1034.3	1033.6	1029.4	1020.2	1010.9	1000.9	987.8	974.9	968.5
10°	1069.3	1079.3	1073.3	1062.6	1064.7	1050.4	1042.8	1029.7	1018.7	999.6	995.3
12.5°	1100.4	1104.4	1102.4	1096.4	1093.7	1083.8	1073.5	1062.1	1041.9	1024.7	1009.7
15°	1100.3	1106.1	1107.7	1105.8	1107.3	1106.7	1101.2	1091.8	1074.2	1055.2	1038.9
17.5°	1019.1	1023.1	1033.1	1039.8	1048.4	1066.4	1075.3	1078.8	1076.1	1065.4	1053.8
20°	928.0	921.3	949.3	963.6	975.8	1006.2	1032.4	1042.4	1058.6	1058.3	1055.2
22.5°	798.9	800.5	827.0	844.0	879.6	910.0	939.9	977.7	1008.9	1029.6	1041.6
25°	587.0	598.6	625.1	648.2	687.8	744.4	795.9	855.6	911.8	956.3	998.7
27.5°	440.8	441.7	462.7	484.1	507.6	554.0	618.8	690.1	770.4	836.6	912.8
30°	377.6	375.7	384.6	397.6	417.8	453.6	502.4	572.4	652.5	752.4	841.2
32.5°	332.7	332.8	339.5	349.2	365.8	390.0	423.5	480.3	556.0	654.2	758.4
35°	289.3	288.9	293.8	300.8	307.8	323.3	346.2	376.0	428.1	519.8	626.3
37.5°	258.0	259.4	261.8	266.2	273.9	282.5	296.3	316.3	353.4	407.6	497.1
40°	240.5	241.2	244.5	248.2	252.7	259.4	270.7	286.8	313.9	357.1	422.6
42.5°	224.5	225.0	227.5	230.8	234.4	241.2	250.5	264.4	286.4	320.1	374.1
45°	201.0	201.0	203.1	204.6	208.6	214.7	222.3	233.8	249.1	274.0	310.0
47.5°	178.9	179.0	180.3	183.0	185.5	190.2	197.7	207.2	218.3	237.6	268.2
50°	166.2	166.6	167.5	169.6	171.1	175.4	181.2	189.4	201.0	215.9	241.4
52.5°	156.0	155.8	156.9	157.9	158.9	162.0	166.3	173.6	183.9	196.9	218.1
55°	139.4	138.2	140.1	141.5	142.5	143.7	146.1	150.7	159.6	170.5	186.3
57.5°	118.7	118.2	119.5	120.9	123.8	127.1	129.1	132.1	136.6	144.5	160.2
60°	101.7	101.7	104.4	105.3	108.7	112.9	117.2	119.7	124.3	129.4	141.0
62.5°	86.6	86.8	88.1	89.0	90.9	96.1	102.2	107.5	111.8	116.8	124.4
65°	72.5	73.1	73.1	73.7	74.9	76.1	78.5	82.8	90.4	97.4	103.2
67.5°	61.5	61.7	61.9	62.5	62.8	64.1	65.1	67.0	68.7	75.4	82.6
70°	54.2	55.1	54.8	55.4	55.7	56.3	57.6	58.5	61.2	62.7	67.0
72.5°	47.4	48.0	48.0	48.3	49.2	49.2	50.2	51.1	52.9	54.2	56.5
75°	38.4	38.1	38.4	39.0	39.3	39.5	39.5	40.8	41.7	43.0	44.4
77.5°	29.6	29.9	29.8	29.9	29.9	30.5	30.4	31.0	31.9	32.5	33.3
80°	23.7	24.1	23.7	24.1	24.4	24.6	24.4	24.6	25.6	26.2	26.2
82.5°	18.4	18.4	18.7	18.7	18.8	18.8	19.2	19.3	20.0	19.8	20.1
85°	10.9	10.7	10.7	10.7	10.9	11.3	10.9	10.9	11.3	11.3	11.3
87.5°	7.1	7.3	7.3	7.3	7.3	7.3	7.3	7.6	7.3	7.7	6.9
90°	15.8	15.7	15.6	15.5	15.4	15.4	15.7	15.9	16.1	16.3	14.0
92.5°	15.1	15.1	15.0	15.0	15.0	14.9	14.9	14.8	14.8	14.8	14.3
95°	28.9	29.0	29.3	29.4	29.7	29.8	29.8	29.8	29.8	29.8	29.5
97.5°	49.9	50.0	50.0	50.0	50.0	50.1	50.1	50.1	50.1	50.1	49.7
100°	63.7	63.8	63.9	64.0	64.1	64.2	64.2	64.2	64.2	64.2	63.8
102.5°	79.3	79.4	79.5	79.7	79.7	79.7	79.7	79.6	79.5	79.4	79.0
105°	103.2	103.2	103.2	103.2	103.2	103.1	102.9	102.7	102.5	102.3	102.1
107.5°	125.7	126.2	126.7	127.1	127.6	127.8	127.8	127.7	127.6	127.5	127.5
110°	143.2	143.5	143.8	144.1	144.5	144.6	144.6	144.6	144.6	144.6	144.6



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	160.0	160.1	160.4	160.6	160.9	161.1	161.3	161.6	161.8	162.1	162.2
115°	186.0	186.3	186.6	186.9	187.2	187.4	187.5	187.6	187.8	187.8	188.0
117.5°	210.8	211.1	211.4	211.7	212.1	212.3	212.5	212.8	213.0	213.3	213.9
120°	228.3	228.6	228.9	229.2	229.5	229.7	229.7	229.7	229.7	229.7	230.5
122.5°	245.4	245.6	245.8	246.1	246.3	246.5	246.8	247.0	247.3	247.5	248.1
125°	271.5	271.6	271.7	271.8	271.9	272.1	272.5	272.7	273.0	273.4	273.7
127.5°	295.3	295.6	296.0	296.3	296.6	297.0	297.3	297.7	298.1	298.5	298.9
130°	312.4	312.8	313.2	313.6	314.1	314.4	314.6	314.8	315.0	315.2	315.4
132.5°	328.8	329.1	329.5	329.8	330.1	330.5	330.9	331.4	331.9	332.3	332.3
135°	354.2	354.6	354.9	355.2	355.5	355.7	355.8	356.0	356.0	356.1	356.0
137.5°	377.3	377.7	378.1	378.5	379.0	379.2	379.3	379.4	379.4	379.5	379.3
140°	393.3	393.7	394.1	394.5	395.0	395.2	395.2	395.2	395.2	395.2	394.7
142.5°	407.8	408.2	408.6	409.0	409.4	409.6	409.5	409.4	409.4	409.3	409.0
145°	429.6	430.0	430.4	430.8	431.2	431.4	431.3	431.2	431.0	431.0	430.4
147.5°	449.0	449.4	449.8	450.2	450.6	450.7	450.5	450.2	450.0	449.8	449.3
150°	461.7	461.9	462.3	462.6	462.9	462.9	462.6	462.3	461.9	461.7	461.2
152.5°	473.6	473.9	474.3	474.7	475.2	475.2	474.7	474.3	473.9	473.6	473.0
155°	489.6	489.8	490.2	490.5	490.8	490.7	490.2	489.7	489.2	488.6	488.3
157.5°	503.3	503.9	504.3	504.8	505.3	505.2	504.5	503.8	503.1	502.4	502.2
160°	511.8	512.3	512.7	513.1	513.6	513.4	512.8	512.2	511.6	510.9	510.9
162.5°	519.3	519.8	520.3	520.8	521.3	521.2	520.5	519.8	519.1	518.4	518.3
165°	529.0	529.6	530.1	530.6	531.2	531.0	530.4	529.6	528.9	528.2	528.2
167.5°	537.0	537.6	538.2	538.7	539.2	539.2	538.4	537.7	537.0	536.2	536.2
170°	541.2	541.8	542.4	543.0	543.6	543.6	542.9	542.2	541.4	540.7	540.8
172.5°	544.5	545.1	545.8	546.4	547.0	546.9	546.3	545.5	544.8	544.0	544.1
175°	548.1	548.8	549.3	550.0	550.7	550.6	549.8	549.1	548.4	547.6	547.9
177.5°	549.8	550.3	550.8	551.3	551.8	551.8	551.3	550.8	550.3	549.8	550.0
180°	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	897.2	895.3	893.6	889.2	887.0	882.1	881.3	881.1	874.8	868.7	867.0
5°	928.0	923.2	915.8	907.3	898.5	889.3	883.2	878.4	866.2	854.6	847.9
7.5°	959.0	948.6	936.0	919.8	906.4	891.3	880.1	870.0	852.7	836.2	825.0
10°	982.2	965.2	948.4	926.2	908.8	891.8	876.0	862.3	842.8	820.8	805.3
12.5°	996.5	977.8	954.7	933.0	910.5	888.8	867.6	850.0	827.2	804.5	786.0
15°	1016.0	995.9	967.9	936.9	907.9	879.6	855.2	833.3	803.5	776.4	753.8
17.5°	1031.9	1004.2	974.1	938.2	904.7	868.8	837.4	809.3	776.2	743.5	717.0
20°	1037.0	1009.6	974.9	939.0	899.4	857.0	823.3	792.8	757.2	721.5	691.1
22.5°	1033.8	1012.5	973.9	930.9	890.4	846.1	808.0	772.6	733.1	696.8	661.5
25°	1012.4	1005.0	968.5	921.6	875.3	823.9	779.8	741.0	696.0	657.0	618.6
27.5°	962.2	978.0	955.4	905.4	853.9	798.7	749.2	705.2	658.4	614.5	576.3
30°	914.0	950.2	940.4	894.2	836.7	782.4	726.8	680.8	630.9	585.8	548.0
32.5°	848.0	907.8	917.4	878.6	819.1	759.5	701.2	655.4	603.3	555.8	519.0
35°	742.9	832.4	873.5	848.8	789.1	725.0	664.6	611.4	559.0	512.1	475.6
37.5°	617.5	739.4	808.0	809.7	754.9	688.1	622.5	569.6	515.9	469.9	430.4
40°	536.1	668.3	757.5	777.3	731.0	658.8	592.5	538.6	486.2	441.2	395.8
42.5°	463.1	594.8	704.4	738.8	702.1	630.4	563.8	507.4	456.5	413.8	367.5
45°	374.5	489.6	610.4	672.0	651.6	585.1	514.9	461.3	413.4	376.6	332.2
47.5°	315.9	397.1	514.0	597.2	596.8	536.2	467.1	415.7	371.4	336.9	300.8
50°	282.5	353.2	452.2	546.5	554.4	503.6	437.8	386.9	345.6	309.3	280.4
52.5°	252.6	310.8	399.7	490.2	512.7	468.7	405.0	358.0	317.8	284.5	259.7
55°	213.4	258.4	326.1	410.7	444.8	413.8	357.1	313.3	280.7	252.7	231.4
57.5°	180.5	214.3	268.6	336.7	376.4	356.9	310.2	274.6	246.7	221.4	204.6
60°	159.9	187.5	233.5	290.5	334.3	320.6	280.7	247.5	223.8	201.9	186.1
62.5°	140.4	164.2	203.6	249.8	290.0	284.3	251.8	223.9	203.1	183.1	169.7
65°	112.9	130.3	161.0	197.3	229.6	232.3	208.9	190.0	171.4	155.6	143.7
67.5°	89.9	101.3	122.9	153.4	177.7	186.3	171.9	157.5	142.8	130.5	120.3
70°	75.8	85.0	100.8	125.5	147.7	156.8	148.5	137.3	124.5	114.5	105.7
72.5°	61.5	70.4	82.0	100.1	119.2	129.1	126.2	118.1	107.7	99.4	91.1
75°	46.3	49.0	56.9	69.1	84.1	92.5	94.7	90.4	82.2	75.8	70.9
77.5°	34.2	35.9	39.6	46.1	55.8	63.3	66.5	66.0	60.3	56.7	52.1
80°	27.4	28.3	30.2	32.9	40.2	47.8	49.9	49.9	46.0	44.4	39.9
82.5°	20.8	21.5	22.6	24.1	27.6	34.2	36.5	37.0	34.5	32.5	28.9
85°	11.9	11.6	12.1	13.1	13.7	15.5	19.2	19.8	19.2	16.7	15.8
87.5°	6.5	6.3	5.8	5.2	5.2	5.2	6.2	7.2	6.4	6.0	5.7
90°	11.7	9.5	7.2	5.5	4.2	2.9	1.7	0.5	1.7	2.9	4.2
92.5°	13.7	13.2	12.6	11.9	11.0	10.1	9.2	8.3	9.2	10.1	11.0
95°	29.4	29.1	28.9	28.3	27.3	26.3	25.2	24.2	25.2	26.3	27.3
97.5°	49.2	48.8	48.4	47.8	46.9	46.0	45.1	44.2	45.1	46.0	46.9
100°	63.5	63.3	62.9	62.4	61.6	60.7	59.8	59.0	59.8	60.7	61.6
102.5°	78.6	78.3	77.9	77.3	76.6	76.0	75.3	74.7	75.3	76.0	76.6
105°	101.8	101.7	101.4	101.2	100.9	100.6	100.3	100.0	100.3	100.6	100.9
107.5°	127.5	127.5	127.5	127.3	126.8	126.4	125.9	125.5	125.9	126.4	126.8
110°	144.6	144.6	144.6	144.3	143.7	143.0	142.4	141.8	142.4	143.0	143.7



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	162.2	162.3	162.4	162.2	161.5	160.9	160.3	159.6	160.3	160.9	161.5
115°	188.3	188.4	188.7	188.4	187.8	187.2	186.6	186.0	186.6	187.2	187.8
117.5°	214.4	215.1	215.6	215.5	214.7	213.9	213.0	212.2	213.0	213.9	214.7
120°	231.3	232.1	233.0	233.0	232.1	231.3	230.5	229.7	230.5	231.3	232.1
122.5°	248.7	249.2	249.8	249.6	248.7	247.7	246.6	245.6	246.6	247.7	248.7
125°	274.0	274.3	274.6	274.3	273.4	272.5	271.5	270.6	271.5	272.5	273.4
127.5°	299.2	299.6	299.9	299.5	298.4	297.2	296.0	294.8	296.0	297.2	298.4
130°	315.6	315.8	316.0	315.4	314.1	312.7	311.4	310.1	311.4	312.7	314.1
132.5°	332.2	332.2	332.2	331.6	330.5	329.4	328.3	327.2	328.3	329.4	330.5
135°	355.7	355.5	355.3	354.7	353.5	352.4	351.2	350.1	351.2	352.4	353.5
137.5°	379.0	378.8	378.5	377.9	377.0	376.0	375.1	374.1	375.1	376.0	377.0
140°	394.1	393.6	393.1	392.4	391.4	390.5	389.6	388.7	389.6	390.5	391.4
142.5°	408.6	408.3	407.9	407.2	406.3	405.4	404.5	403.6	404.5	405.4	406.3
145°	429.7	429.1	428.5	427.9	427.1	426.4	425.7	424.9	425.7	426.4	427.1
147.5°	448.9	448.5	448.1	447.4	446.6	445.7	444.8	444.0	444.8	445.7	446.6
150°	460.8	460.4	460.0	459.5	458.9	458.3	457.6	457.1	457.6	458.3	458.9
152.5°	472.5	472.1	471.6	471.0	470.4	469.8	469.2	468.6	469.2	469.8	470.4
155°	488.0	487.7	487.4	487.1	486.7	486.5	486.2	485.8	486.2	486.5	486.7
157.5°	502.1	501.8	501.7	501.5	501.2	501.0	500.8	500.6	500.8	501.0	501.2
160°	510.7	510.6	510.5	510.4	510.1	510.0	509.7	509.6	509.7	510.0	510.1
162.5°	518.2	518.0	518.0	517.9	517.9	517.8	517.8	517.7	517.8	517.8	517.9
165°	528.2	528.2	528.2	528.2	528.3	528.4	528.5	528.6	528.5	528.4	528.3
167.5°	536.3	536.3	536.3	536.5	536.8	537.1	537.4	537.7	537.4	537.1	536.8
170°	540.9	541.0	541.1	541.4	541.6	541.9	542.3	542.6	542.3	541.9	541.6
172.5°	544.3	544.4	544.5	544.7	544.9	545.3	545.6	545.9	545.6	545.3	544.9
175°	548.1	548.3	548.5	548.8	549.1	549.3	549.7	550.0	549.7	549.3	549.1
177.5°	550.2	550.3	550.5	550.7	550.9	551.1	551.4	551.7	551.4	551.1	550.9
180°	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	863.8	862.1	858.9	854.1	851.2	846.0	842.6	844.6	845.1	844.6	844.1
5°	840.7	834.2	825.4	816.8	808.9	800.5	795.6	793.4	789.1	786.8	785.5
7.5°	812.5	801.5	789.0	774.2	761.6	748.4	741.6	738.3	729.5	724.8	720.6
10°	791.6	774.2	761.7	742.2	730.4	713.1	701.2	701.5	689.6	682.9	678.0
12.5°	768.5	749.4	728.6	711.1	694.6	680.7	666.3	660.6	647.9	641.5	628.4
15°	730.1	707.8	686.0	662.2	645.5	623.9	603.2	577.9	557.5	539.8	534.9
17.5°	688.2	660.7	638.7	610.8	582.1	545.8	521.8	507.1	494.8	485.5	478.6
20°	659.5	631.4	608.1	566.0	527.3	502.6	485.0	473.8	461.0	450.9	445.4
22.5°	629.2	600.1	568.1	521.1	491.1	471.2	455.5	442.5	433.9	426.1	421.1
25°	586.4	554.4	501.7	469.4	445.2	424.4	413.4	405.5	396.4	385.7	380.9
27.5°	541.1	490.2	452.4	428.4	405.2	391.8	381.9	370.1	361.9	357.1	352.0
30°	507.2	456.4	426.9	400.6	384.3	369.3	357.8	351.1	343.2	334.9	331.6
32.5°	469.4	428.8	400.6	378.8	362.1	349.4	340.2	329.4	323.7	318.6	311.6
35°	422.6	391.8	366.0	348.3	332.5	322.1	311.4	305.1	294.7	290.5	287.7
37.5°	382.9	356.2	336.9	318.3	305.7	294.3	287.8	277.6	273.1	267.2	261.4
40°	360.4	334.3	315.8	300.5	286.5	277.9	269.8	261.5	254.9	252.1	245.1
42.5°	337.6	316.3	297.7	281.0	271.7	262.6	252.3	246.2	239.2	234.8	230.5
45°	306.0	287.1	271.3	257.6	247.2	237.8	231.1	221.0	217.1	208.2	204.6
47.5°	278.2	260.7	245.6	232.5	222.4	216.3	206.5	198.6	192.3	186.9	182.2
50°	258.4	243.9	229.3	217.7	208.6	199.7	189.7	185.7	175.9	173.3	170.5
52.5°	240.4	226.6	213.2	201.9	192.7	184.2	175.3	170.2	163.5	160.8	158.8
55°	215.2	201.9	189.1	179.0	169.9	161.0	155.6	149.2	146.1	144.0	141.5
57.5°	189.9	177.9	168.0	157.9	148.7	141.7	135.3	131.5	128.3	125.6	122.6
60°	173.8	162.2	153.4	144.0	134.6	128.8	123.9	119.4	115.7	111.5	110.2
62.5°	156.8	146.7	138.6	129.4	121.2	115.9	111.3	107.0	102.6	96.4	94.7
65°	133.4	125.5	116.9	109.3	102.0	96.9	90.1	85.3	83.4	82.8	82.5
67.5°	112.2	104.7	97.3	89.6	82.9	78.1	74.7	73.9	72.7	72.3	71.5
70°	98.0	91.1	83.7	76.4	70.0	69.1	67.9	66.7	65.1	64.6	63.9
72.5°	85.4	78.1	70.8	65.0	62.2	61.1	59.8	58.6	57.6	57.0	56.7
75°	65.5	58.8	53.9	51.8	50.2	49.3	47.5	46.6	46.0	45.1	44.8
77.5°	47.1	43.4	41.1	39.8	38.2	37.2	36.2	35.2	34.6	34.4	33.9
80°	36.0	34.1	32.6	30.7	30.2	28.9	28.6	27.7	28.0	27.1	27.1
82.5°	27.9	25.6	24.3	23.5	22.8	21.9	21.5	21.1	21.2	20.5	20.5
85°	14.3	13.7	13.1	12.5	12.5	11.6	11.9	11.6	11.6	10.9	10.7
87.5°	5.7	5.8	5.8	6.3	6.7	6.9	6.8	6.6	6.5	6.5	6.3
90°	5.5	7.2	9.5	11.7	14.0	16.3	16.1	15.9	15.7	15.4	15.4
92.5°	11.9	12.6	13.2	13.7	14.3	14.8	14.8	14.8	14.9	14.9	15.0
95°	28.3	28.9	29.1	29.4	29.5	29.8	29.8	29.8	29.8	29.8	29.7
97.5°	47.8	48.4	48.8	49.2	49.7	50.1	50.1	50.1	50.1	50.1	50.0
100°	62.4	62.9	63.3	63.5	63.8	64.2	64.2	64.2	64.2	64.2	64.1
102.5°	77.3	77.9	78.3	78.6	79.0	79.4	79.5	79.6	79.7	79.7	79.7
105°	101.2	101.4	101.7	101.8	102.1	102.3	102.5	102.7	102.9	103.1	103.2
107.5°	127.3	127.5	127.5	127.5	127.5	127.5	127.6	127.7	127.8	127.8	127.6
110°	144.3	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.6	144.5



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	162.2	162.4	162.3	162.2	162.2	162.1	161.8	161.6	161.3	161.1	160.9
115°	188.4	188.7	188.4	188.3	188.0	187.8	187.8	187.6	187.5	187.4	187.2
117.5°	215.5	215.6	215.1	214.4	213.9	213.3	213.0	212.8	212.5	212.3	212.1
120°	233.0	233.0	232.1	231.3	230.5	229.7	229.7	229.7	229.7	229.7	229.5
122.5°	249.6	249.8	249.2	248.7	248.1	247.5	247.3	247.0	246.8	246.5	246.3
125°	274.3	274.6	274.3	274.0	273.7	273.4	273.0	272.7	272.5	272.1	271.9
127.5°	299.5	299.9	299.6	299.2	298.9	298.5	298.1	297.7	297.3	297.0	296.6
130°	315.4	316.0	315.8	315.6	315.4	315.2	315.0	314.8	314.6	314.4	314.1
132.5°	331.6	332.2	332.2	332.2	332.3	332.3	331.9	331.4	330.9	330.5	330.1
135°	354.7	355.3	355.5	355.7	356.0	356.1	356.0	356.0	355.8	355.7	355.5
137.5°	377.9	378.5	378.8	379.0	379.3	379.5	379.4	379.4	379.3	379.2	379.0
140°	392.4	393.1	393.6	394.1	394.7	395.2	395.2	395.2	395.2	395.2	395.0
142.5°	407.2	407.9	408.3	408.6	409.0	409.3	409.4	409.4	409.5	409.6	409.4
145°	427.9	428.5	429.1	429.7	430.4	431.0	431.0	431.2	431.3	431.4	431.2
147.5°	447.4	448.1	448.5	448.9	449.3	449.8	450.0	450.2	450.5	450.7	450.6
150°	459.5	460.0	460.4	460.8	461.2	461.7	461.9	462.3	462.6	462.9	462.9
152.5°	471.0	471.6	472.1	472.5	473.0	473.6	473.9	474.3	474.7	475.2	475.2
155°	487.1	487.4	487.7	488.0	488.3	488.6	489.2	489.7	490.2	490.7	490.8
157.5°	501.5	501.7	501.8	502.1	502.2	502.4	503.1	503.8	504.5	505.2	505.3
160°	510.4	510.5	510.6	510.7	510.9	510.9	511.6	512.2	512.8	513.4	513.6
162.5°	517.9	518.0	518.0	518.2	518.3	518.4	519.1	519.8	520.5	521.2	521.3
165°	528.2	528.2	528.2	528.2	528.2	528.2	528.9	529.6	530.4	531.0	531.2
167.5°	536.5	536.3	536.3	536.3	536.2	536.2	537.0	537.7	538.4	539.2	539.2
170°	541.4	541.1	541.0	540.9	540.8	540.7	541.4	542.2	542.9	543.6	543.6
172.5°	544.7	544.5	544.4	544.3	544.1	544.0	544.8	545.5	546.3	546.9	547.0
175°	548.8	548.5	548.3	548.1	547.9	547.6	548.4	549.1	549.8	550.6	550.7
177.5°	550.7	550.5	550.3	550.2	550.0	549.8	550.3	550.8	551.3	551.8	551.8
180°	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	841.4	841.9	841.1	841.6	841.1	841.9	841.4	844.1	844.6	845.1	844.6
5°	784.0	780.3	779.8	778.9	779.8	780.3	784.0	785.5	786.8	789.1	793.4
7.5°	715.4	714.9	713.4	711.2	713.4	714.9	715.4	720.6	724.8	729.5	738.3
10°	671.3	669.8	669.5	667.4	669.5	669.8	671.3	678.0	682.9	689.6	701.5
12.5°	619.7	609.9	608.9	603.6	608.9	609.9	619.7	628.4	641.5	647.9	660.6
15°	527.7	525.8	519.8	515.8	519.8	525.8	527.7	534.9	539.8	557.5	577.9
17.5°	475.0	469.0	467.2	466.4	467.2	469.0	475.0	478.6	485.5	494.8	507.1
20°	441.2	435.7	434.8	434.1	434.8	435.7	441.2	445.4	450.9	461.0	473.8
22.5°	417.8	412.1	409.7	407.9	409.7	412.1	417.8	421.1	426.1	433.9	442.5
25°	377.8	375.7	374.5	373.9	374.5	375.7	377.8	380.9	385.7	396.4	405.5
27.5°	346.6	341.9	341.0	339.4	341.0	341.9	346.6	352.0	357.1	361.9	370.1
30°	328.8	327.3	325.1	323.3	325.1	327.3	328.8	331.6	334.9	343.2	351.1
32.5°	307.9	306.6	304.7	303.9	304.7	306.6	307.9	311.6	318.6	323.7	329.4
35°	284.7	280.4	278.6	275.8	278.6	280.4	284.7	287.7	290.5	294.7	305.1
37.5°	260.2	257.9	255.4	256.2	255.4	257.9	260.2	261.4	267.2	273.1	277.6
40°	241.2	239.6	239.0	238.7	239.0	239.6	241.2	245.1	252.1	254.9	261.5
42.5°	226.0	221.8	220.2	220.2	220.2	221.8	226.0	230.5	234.8	239.2	246.2
45°	203.1	199.1	196.4	196.7	196.4	199.1	203.1	204.6	208.2	217.1	221.0
47.5°	179.6	179.4	177.7	178.3	177.7	179.4	179.6	182.2	186.9	192.3	198.6
50°	168.4	166.6	165.3	165.6	165.3	166.6	168.4	170.5	173.3	175.9	185.7
52.5°	157.7	156.0	155.1	156.4	155.1	156.0	157.7	158.8	160.8	163.5	170.2
55°	140.1	138.2	137.9	137.6	137.9	138.2	140.1	141.5	144.0	146.1	149.2
57.5°	120.4	119.2	117.3	116.6	117.3	119.2	120.4	122.6	125.6	128.3	131.5
60°	106.2	103.8	100.8	100.4	100.8	103.8	106.2	110.2	111.5	115.7	119.4
62.5°	93.4	92.9	92.3	92.2	92.3	92.9	93.4	94.7	96.4	102.6	107.0
65°	81.9	81.6	81.9	82.2	81.9	81.6	81.9	82.5	82.8	83.4	85.3
67.5°	71.3	70.8	70.3	70.5	70.3	70.8	71.3	71.5	72.3	72.7	73.9
70°	63.3	63.0	62.7	62.7	62.7	63.0	63.3	63.9	64.6	65.1	66.7
72.5°	55.5	55.4	55.2	55.0	55.2	55.4	55.5	56.7	57.0	57.6	58.6
75°	44.4	43.9	43.9	43.9	43.9	43.9	44.4	44.8	45.1	46.0	46.6
77.5°	33.8	33.6	33.3	33.0	33.3	33.6	33.8	33.9	34.4	34.6	35.2
80°	26.8	26.5	26.2	26.2	26.2	26.5	26.8	27.1	27.1	28.0	27.7
82.5°	20.5	20.1	20.1	19.8	20.1	20.1	20.5	20.5	20.5	21.2	21.1
85°	10.9	11.3	10.9	11.6	10.9	11.3	10.9	10.7	10.9	11.6	11.6
87.5°	6.3	6.0	6.3	6.1	6.3	6.0	6.3	6.3	6.5	6.5	6.6
90°	15.5	15.6	15.7	15.8	15.7	15.6	15.5	15.4	15.4	15.7	15.9
92.5°	15.0	15.0	15.1	15.1	15.1	15.0	15.0	15.0	14.9	14.9	14.8
95°	29.4	29.3	29.0	28.9	29.0	29.3	29.4	29.7	29.8	29.8	29.8
97.5°	50.0	50.0	50.0	49.9	50.0	50.0	50.0	50.0	50.1	50.1	50.1
100°	64.0	63.9	63.8	63.7	63.8	63.9	64.0	64.1	64.2	64.2	64.2
102.5°	79.7	79.5	79.4	79.3	79.4	79.5	79.7	79.7	79.7	79.7	79.6
105°	103.2	103.2	103.2	103.2	103.2	103.2	103.2	103.2	103.1	102.9	102.7
107.5°	127.1	126.7	126.2	125.7	126.2	126.7	127.1	127.6	127.8	127.8	127.7
110°	144.1	143.8	143.5	143.2	143.5	143.8	144.1	144.5	144.6	144.6	144.6



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	160.6	160.4	160.1	160.0	160.1	160.4	160.6	160.9	161.1	161.3	161.6
115°	186.9	186.6	186.3	186.0	186.3	186.6	186.9	187.2	187.4	187.5	187.6
117.5°	211.7	211.4	211.1	210.8	211.1	211.4	211.7	212.1	212.3	212.5	212.8
120°	229.2	228.9	228.6	228.3	228.6	228.9	229.2	229.5	229.7	229.7	229.7
122.5°	246.1	245.8	245.6	245.4	245.6	245.8	246.1	246.3	246.5	246.8	247.0
125°	271.8	271.7	271.6	271.5	271.6	271.7	271.8	271.9	272.1	272.5	272.7
127.5°	296.3	296.0	295.6	295.3	295.6	296.0	296.3	296.6	297.0	297.3	297.7
130°	313.6	313.2	312.8	312.4	312.8	313.2	313.6	314.1	314.4	314.6	314.8
132.5°	329.8	329.5	329.1	328.8	329.1	329.5	329.8	330.1	330.5	330.9	331.4
135°	355.2	354.9	354.6	354.2	354.6	354.9	355.2	355.5	355.7	355.8	356.0
137.5°	378.5	378.1	377.7	377.3	377.7	378.1	378.5	379.0	379.2	379.3	379.4
140°	394.5	394.1	393.7	393.3	393.7	394.1	394.5	395.0	395.2	395.2	395.2
142.5°	409.0	408.6	408.2	407.8	408.2	408.6	409.0	409.4	409.6	409.5	409.4
145°	430.8	430.4	430.0	429.6	430.0	430.4	430.8	431.2	431.4	431.3	431.2
147.5°	450.2	449.8	449.4	449.0	449.4	449.8	450.2	450.6	450.7	450.5	450.2
150°	462.6	462.3	461.9	461.7	461.9	462.3	462.6	462.9	462.9	462.6	462.3
152.5°	474.7	474.3	473.9	473.6	473.9	474.3	474.7	475.2	475.2	474.7	474.3
155°	490.5	490.2	489.8	489.6	489.8	490.2	490.5	490.8	490.7	490.2	489.7
157.5°	504.8	504.3	503.9	503.3	503.9	504.3	504.8	505.3	505.2	504.5	503.8
160°	513.1	512.7	512.3	511.8	512.3	512.7	513.1	513.6	513.4	512.8	512.2
162.5°	520.8	520.3	519.8	519.3	519.8	520.3	520.8	521.3	521.2	520.5	519.8
165°	530.6	530.1	529.6	529.0	529.6	530.1	530.6	531.2	531.0	530.4	529.6
167.5°	538.7	538.2	537.6	537.0	537.6	538.2	538.7	539.2	539.2	538.4	537.7
170°	543.0	542.4	541.8	541.2	541.8	542.4	543.0	543.6	543.6	542.9	542.2
172.5°	546.4	545.8	545.1	544.5	545.1	545.8	546.4	547.0	546.9	546.3	545.5
175°	550.0	549.3	548.8	548.1	548.8	549.3	550.0	550.7	550.6	549.8	549.1
177.5°	551.3	550.8	550.3	549.8	550.3	550.8	551.3	551.8	551.8	551.3	550.8
180°	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	842.6	846.0	851.2	854.1	858.9	862.1	863.8	867.0	868.7	874.8	881.1
5°	795.6	800.5	808.9	816.8	825.4	834.2	840.7	847.9	854.6	866.2	878.4
7.5°	741.6	748.4	761.6	774.2	789.0	801.5	812.5	825.0	836.2	852.7	870.0
10°	701.2	713.1	730.4	742.2	761.7	774.2	791.6	805.3	820.8	842.8	862.3
12.5°	666.3	680.7	694.6	711.1	728.6	749.4	768.5	786.0	804.5	827.2	850.0
15°	603.2	623.9	645.5	662.2	686.0	707.8	730.1	753.8	776.4	803.5	833.3
17.5°	521.8	545.8	582.1	610.8	638.7	660.7	688.2	717.0	743.5	776.2	809.3
20°	485.0	502.6	527.3	566.0	608.1	631.4	659.5	691.1	721.5	757.2	792.8
22.5°	455.5	471.2	491.1	521.1	568.1	600.1	629.2	661.5	696.8	733.1	772.6
25°	413.4	424.4	445.2	469.4	501.7	554.4	586.4	618.6	657.0	696.0	741.0
27.5°	381.9	391.8	405.2	428.4	452.4	490.2	541.1	576.3	614.5	658.4	705.2
30°	357.8	369.3	384.3	400.6	426.9	456.4	507.2	548.0	585.8	630.9	680.8
32.5°	340.2	349.4	362.1	378.8	400.6	428.8	469.4	519.0	555.8	603.3	655.4
35°	311.4	322.1	332.5	348.3	366.0	391.8	422.6	475.6	512.1	559.0	611.4
37.5°	287.8	294.3	305.7	318.3	336.9	356.2	382.9	430.4	469.9	515.9	569.6
40°	269.8	277.9	286.5	300.5	315.8	334.3	360.4	395.8	441.2	486.2	538.6
42.5°	252.3	262.6	271.7	281.0	297.7	316.3	337.6	367.5	413.8	456.5	507.4
45°	231.1	237.8	247.2	257.6	271.3	287.1	306.0	332.2	376.6	413.4	461.3
47.5°	206.5	216.3	222.4	232.5	245.6	260.7	278.2	300.8	336.9	371.4	415.7
50°	189.7	199.7	208.6	217.7	229.3	243.9	258.4	280.4	309.3	345.6	386.9
52.5°	175.3	184.2	192.7	201.9	213.2	226.6	240.4	259.7	284.5	317.8	358.0
55°	155.6	161.0	169.9	179.0	189.1	201.9	215.2	231.4	252.7	280.7	313.3
57.5°	135.3	141.7	148.7	157.9	168.0	177.9	189.9	204.6	221.4	246.7	274.6
60°	123.9	128.8	134.6	144.0	153.4	162.2	173.8	186.1	201.9	223.8	247.5
62.5°	111.3	115.9	121.2	129.4	138.6	146.7	156.8	169.7	183.1	203.1	223.9
65°	90.1	96.9	102.0	109.3	116.9	125.5	133.4	143.7	155.6	171.4	190.0
67.5°	74.7	78.1	82.9	89.6	97.3	104.7	112.2	120.3	130.5	142.8	157.5
70°	67.9	69.1	70.0	76.4	83.7	91.1	98.0	105.7	114.5	124.5	137.3
72.5°	59.8	61.1	62.2	65.0	70.8	78.1	85.4	91.1	99.4	107.7	118.1
75°	47.5	49.3	50.2	51.8	53.9	58.8	65.5	70.9	75.8	82.2	90.4
77.5°	36.2	37.2	38.2	39.8	41.1	43.4	47.1	52.1	56.7	60.3	66.0
80°	28.6	28.9	30.2	30.7	32.6	34.1	36.0	39.9	44.4	46.0	49.9
82.5°	21.5	21.9	22.8	23.5	24.3	25.6	27.9	28.9	32.5	34.5	37.0
85°	11.9	11.6	12.5	12.5	13.1	13.7	14.3	15.8	16.7	19.2	19.8
87.5°	6.8	6.9	6.7	6.3	5.8	5.8	5.7	5.7	6.0	6.4	7.2
90°	16.1	16.3	14.0	11.7	9.5	7.2	5.5	4.2	2.9	1.7	0.5
92.5°	14.8	14.8	14.3	13.7	13.2	12.6	11.9	11.0	10.1	9.2	8.3
95°	29.8	29.8	29.5	29.4	29.1	28.9	28.3	27.3	26.3	25.2	24.2
97.5°	50.1	50.1	49.7	49.2	48.8	48.4	47.8	46.9	46.0	45.1	44.2
100°	64.2	64.2	63.8	63.5	63.3	62.9	62.4	61.6	60.7	59.8	59.0
102.5°	79.5	79.4	79.0	78.6	78.3	77.9	77.3	76.6	76.0	75.3	74.7
105°	102.5	102.3	102.1	101.8	101.7	101.4	101.2	100.9	100.6	100.3	100.0
107.5°	127.6	127.5	127.5	127.5	127.5	127.5	127.3	126.8	126.4	125.9	125.5
110°	144.6	144.6	144.6	144.6	144.6	144.6	144.3	143.7	143.0	142.4	141.8



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	161.8	162.1	162.2	162.2	162.3	162.4	162.2	161.5	160.9	160.3	159.6
115°	187.8	187.8	188.0	188.3	188.4	188.7	188.4	187.8	187.2	186.6	186.0
117.5°	213.0	213.3	213.9	214.4	215.1	215.6	215.5	214.7	213.9	213.0	212.2
120°	229.7	229.7	230.5	231.3	232.1	233.0	233.0	232.1	231.3	230.5	229.7
122.5°	247.3	247.5	248.1	248.7	249.2	249.8	249.6	248.7	247.7	246.6	245.6
125°	273.0	273.4	273.7	274.0	274.3	274.6	274.3	273.4	272.5	271.5	270.6
127.5°	298.1	298.5	298.9	299.2	299.6	299.9	299.5	298.4	297.2	296.0	294.8
130°	315.0	315.2	315.4	315.6	315.8	316.0	315.4	314.1	312.7	311.4	310.1
132.5°	331.9	332.3	332.3	332.2	332.2	332.2	331.6	330.5	329.4	328.3	327.2
135°	356.0	356.1	356.0	355.7	355.5	355.3	354.7	353.5	352.4	351.2	350.1
137.5°	379.4	379.5	379.3	379.0	378.8	378.5	377.9	377.0	376.0	375.1	374.1
140°	395.2	395.2	394.7	394.1	393.6	393.1	392.4	391.4	390.5	389.6	388.7
142.5°	409.4	409.3	409.0	408.6	408.3	407.9	407.2	406.3	405.4	404.5	403.6
145°	431.0	431.0	430.4	429.7	429.1	428.5	427.9	427.1	426.4	425.7	424.9
147.5°	450.0	449.8	449.3	448.9	448.5	448.1	447.4	446.6	445.7	444.8	444.0
150°	461.9	461.7	461.2	460.8	460.4	460.0	459.5	458.9	458.3	457.6	457.1
152.5°	473.9	473.6	473.0	472.5	472.1	471.6	471.0	470.4	469.8	469.2	468.6
155°	489.2	488.6	488.3	488.0	487.7	487.4	487.1	486.7	486.5	486.2	485.8
157.5°	503.1	502.4	502.2	502.1	501.8	501.7	501.5	501.2	501.0	500.8	500.6
160°	511.6	510.9	510.9	510.7	510.6	510.5	510.4	510.1	510.0	509.7	509.6
162.5°	519.1	518.4	518.3	518.2	518.0	518.0	517.9	517.9	517.8	517.8	517.7
165°	528.9	528.2	528.2	528.2	528.2	528.2	528.2	528.3	528.4	528.5	528.6
167.5°	537.0	536.2	536.2	536.3	536.3	536.3	536.5	536.8	537.1	537.4	537.7
170°	541.4	540.7	540.8	540.9	541.0	541.1	541.4	541.6	541.9	542.3	542.6
172.5°	544.8	544.0	544.1	544.3	544.4	544.5	544.7	544.9	545.3	545.6	545.9
175°	548.4	547.6	547.9	548.1	548.3	548.5	548.8	549.1	549.3	549.7	550.0
177.5°	550.3	549.8	550.0	550.2	550.3	550.5	550.7	550.9	551.1	551.4	551.7
180°	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	881.3	882.1	887.0	889.2	893.6	895.3	897.2	896.7	896.7	897.6	904.5
5°	883.2	889.3	898.5	907.3	915.8	923.2	928.0	932.9	934.7	943.5	951.5
7.5°	880.1	891.3	906.4	919.8	936.0	948.6	959.0	968.5	974.9	987.8	1000.9
10°	876.0	891.8	908.8	926.2	948.4	965.2	982.2	995.3	999.6	1018.7	1029.7
12.5°	867.6	888.8	910.5	933.0	954.7	977.8	996.5	1009.7	1024.7	1041.9	1062.1
15°	855.2	879.6	907.9	936.9	967.9	995.9	1016.0	1038.9	1055.2	1074.2	1091.8
17.5°	837.4	868.8	904.7	938.2	974.1	1004.2	1031.9	1053.8	1065.4	1076.1	1078.8
20°	823.3	857.0	899.4	939.0	974.9	1009.6	1037.0	1055.2	1058.3	1058.6	1042.4
22.5°	808.0	846.1	890.4	930.9	973.9	1012.5	1033.8	1041.6	1029.6	1008.9	977.7
25°	779.8	823.9	875.3	921.6	968.5	1005.0	1012.4	998.7	956.3	911.8	855.6
27.5°	749.2	798.7	853.9	905.4	955.4	978.0	962.2	912.8	836.6	770.4	690.1
30°	726.8	782.4	836.7	894.2	940.4	950.2	914.0	841.2	752.4	652.5	572.4
32.5°	701.2	759.5	819.1	878.6	917.4	907.8	848.0	758.4	654.2	556.0	480.3
35°	664.6	725.0	789.1	848.8	873.5	832.4	742.9	626.3	519.8	428.1	376.0
37.5°	622.5	688.1	754.9	809.7	808.0	739.4	617.5	497.1	407.6	353.4	316.3
40°	592.5	658.8	731.0	777.3	757.5	668.3	536.1	422.6	357.1	313.9	286.8
42.5°	563.8	630.4	702.1	738.8	704.4	594.8	463.1	374.1	320.1	286.4	264.4
45°	514.9	585.1	651.6	672.0	610.4	489.6	374.5	310.0	274.0	249.1	233.8
47.5°	467.1	536.2	596.8	597.2	514.0	397.1	315.9	268.2	237.6	218.3	207.2
50°	437.8	503.6	554.4	546.5	452.2	353.2	282.5	241.4	215.9	201.0	189.4
52.5°	405.0	468.7	512.7	490.2	399.7	310.8	252.6	218.1	196.9	183.9	173.6
55°	357.1	413.8	444.8	410.7	326.1	258.4	213.4	186.3	170.5	159.6	150.7
57.5°	310.2	356.9	376.4	336.7	268.6	214.3	180.5	160.2	144.5	136.6	132.1
60°	280.7	320.6	334.3	290.5	233.5	187.5	159.9	141.0	129.4	124.3	119.7
62.5°	251.8	284.3	290.0	249.8	203.6	164.2	140.4	124.4	116.8	111.8	107.5
65°	208.9	232.3	229.6	197.3	161.0	130.3	112.9	103.2	97.4	90.4	82.8
67.5°	171.9	186.3	177.7	153.4	122.9	101.3	89.9	82.6	75.4	68.7	67.0
70°	148.5	156.8	147.7	125.5	100.8	85.0	75.8	67.0	62.7	61.2	58.5
72.5°	126.2	129.1	119.2	100.1	82.0	70.4	61.5	56.5	54.2	52.9	51.1
75°	94.7	92.5	84.1	69.1	56.9	49.0	46.3	44.4	43.0	41.7	40.8
77.5°	66.5	63.3	55.8	46.1	39.6	35.9	34.2	33.3	32.5	31.9	31.0
80°	49.9	47.8	40.2	32.9	30.2	28.3	27.4	26.2	26.2	25.6	24.6
82.5°	36.5	34.2	27.6	24.1	22.6	21.5	20.8	20.1	19.8	20.0	19.3
85°	19.2	15.5	13.7	13.1	12.1	11.6	11.9	11.3	11.3	11.3	10.9
87.5°	6.2	5.2	5.2	5.2	5.8	6.3	6.5	6.9	7.7	7.3	7.6
90°	1.7	2.9	4.2	5.5	7.2	9.5	11.7	14.0	16.3	16.1	15.9
92.5°	9.2	10.1	11.0	11.9	12.6	13.2	13.7	14.3	14.8	14.8	14.8
95°	25.2	26.3	27.3	28.3	28.9	29.1	29.4	29.5	29.8	29.8	29.8
97.5°	45.1	46.0	46.9	47.8	48.4	48.8	49.2	49.7	50.1	50.1	50.1
100°	59.8	60.7	61.6	62.4	62.9	63.3	63.5	63.8	64.2	64.2	64.2
102.5°	75.3	76.0	76.6	77.3	77.9	78.3	78.6	79.0	79.4	79.5	79.6
105°	100.3	100.6	100.9	101.2	101.4	101.7	101.8	102.1	102.3	102.5	102.7
107.5°	125.9	126.4	126.8	127.3	127.5	127.5	127.5	127.5	127.5	127.6	127.7
110°	142.4	143.0	143.7	144.3	144.6	144.6	144.6	144.6	144.6	144.6	144.6



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	160.3	160.9	161.5	162.2	162.4	162.3	162.2	162.2	162.1	161.8	161.6
115°	186.6	187.2	187.8	188.4	188.7	188.4	188.3	188.0	187.8	187.8	187.6
117.5°	213.0	213.9	214.7	215.5	215.6	215.1	214.4	213.9	213.3	213.0	212.8
120°	230.5	231.3	232.1	233.0	233.0	232.1	231.3	230.5	229.7	229.7	229.7
122.5°	246.6	247.7	248.7	249.6	249.8	249.2	248.7	248.1	247.5	247.3	247.0
125°	271.5	272.5	273.4	274.3	274.6	274.3	274.0	273.7	273.4	273.0	272.7
127.5°	296.0	297.2	298.4	299.5	299.9	299.6	299.2	298.9	298.5	298.1	297.7
130°	311.4	312.7	314.1	315.4	316.0	315.8	315.6	315.4	315.2	315.0	314.8
132.5°	328.3	329.4	330.5	331.6	332.2	332.2	332.2	332.3	332.3	331.9	331.4
135°	351.2	352.4	353.5	354.7	355.3	355.5	355.7	356.0	356.1	356.0	356.0
137.5°	375.1	376.0	377.0	377.9	378.5	378.8	379.0	379.3	379.5	379.4	379.4
140°	389.6	390.5	391.4	392.4	393.1	393.6	394.1	394.7	395.2	395.2	395.2
142.5°	404.5	405.4	406.3	407.2	407.9	408.3	408.6	409.0	409.3	409.4	409.4
145°	425.7	426.4	427.1	427.9	428.5	429.1	429.7	430.4	431.0	431.0	431.2
147.5°	444.8	445.7	446.6	447.4	448.1	448.5	448.9	449.3	449.8	450.0	450.2
150°	457.6	458.3	458.9	459.5	460.0	460.4	460.8	461.2	461.7	461.9	462.3
152.5°	469.2	469.8	470.4	471.0	471.6	472.1	472.5	473.0	473.6	473.9	474.3
155°	486.2	486.5	486.7	487.1	487.4	487.7	488.0	488.3	488.6	489.2	489.7
157.5°	500.8	501.0	501.2	501.5	501.7	501.8	502.1	502.2	502.4	503.1	503.8
160°	509.7	510.0	510.1	510.4	510.5	510.6	510.7	510.9	510.9	511.6	512.2
162.5°	517.8	517.8	517.9	517.9	518.0	518.0	518.2	518.3	518.4	519.1	519.8
165°	528.5	528.4	528.3	528.2	528.2	528.2	528.2	528.2	528.2	528.9	529.6
167.5°	537.4	537.1	536.8	536.5	536.3	536.3	536.3	536.2	536.2	537.0	537.7
170°	542.3	541.9	541.6	541.4	541.1	541.0	540.9	540.8	540.7	541.4	542.2
172.5°	545.6	545.3	544.9	544.7	544.5	544.4	544.3	544.1	544.0	544.8	545.5
175°	549.7	549.3	549.1	548.8	548.5	548.3	548.1	547.9	547.6	548.4	549.1
177.5°	551.4	551.1	550.9	550.7	550.5	550.3	550.2	550.0	549.8	550.3	550.8
180°	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9	550.9



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	906.9	910.1	911.6	911.6	913.3	912.6	911.8
5°	959.0	964.8	966.0	971.5	975.5	974.3	974.9
7.5°	1010.9	1020.2	1029.4	1033.6	1034.3	1036.7	1037.6
10°	1042.8	1050.4	1064.7	1062.6	1073.3	1079.3	1069.3
12.5°	1073.5	1083.8	1093.7	1096.4	1102.4	1104.4	1100.4
15°	1101.2	1106.7	1107.3	1105.8	1107.7	1106.1	1100.3
17.5°	1075.3	1066.4	1048.4	1039.8	1033.1	1023.1	1019.1
20°	1032.4	1006.2	975.8	963.6	949.3	921.3	928.0
22.5°	939.9	910.0	879.6	844.0	827.0	800.5	798.9
25°	795.9	744.4	687.8	648.2	625.1	598.6	587.0
27.5°	618.8	554.0	507.6	484.1	462.7	441.7	440.8
30°	502.4	453.6	417.8	397.6	384.6	375.7	377.6
32.5°	423.5	390.0	365.8	349.2	339.5	332.8	332.7
35°	346.2	323.3	307.8	300.8	293.8	288.9	289.3
37.5°	296.3	282.5	273.9	266.2	261.8	259.4	258.0
40°	270.7	259.4	252.7	248.2	244.5	241.2	240.5
42.5°	250.5	241.2	234.4	230.8	227.5	225.0	224.5
45°	222.3	214.7	208.6	204.6	203.1	201.0	201.0
47.5°	197.7	190.2	185.5	183.0	180.3	179.0	178.9
50°	181.2	175.4	171.1	169.6	167.5	166.6	166.2
52.5°	166.3	162.0	158.9	157.9	156.9	155.8	156.0
55°	146.1	143.7	142.5	141.5	140.1	138.2	139.4
57.5°	129.1	127.1	123.8	120.9	119.5	118.2	118.7
60°	117.2	112.9	108.7	105.3	104.4	101.7	101.7
62.5°	102.2	96.1	90.9	89.0	88.1	86.8	86.6
65°	78.5	76.1	74.9	73.7	73.1	73.1	72.5
67.5°	65.1	64.1	62.8	62.5	61.9	61.7	61.5
70°	57.6	56.3	55.7	55.4	54.8	55.1	54.2
72.5°	50.2	49.2	49.2	48.3	48.0	48.0	47.4
75°	39.5	39.5	39.3	39.0	38.4	38.1	38.4
77.5°	30.4	30.5	29.9	29.9	29.8	29.9	29.6
80°	24.4	24.6	24.4	24.1	23.7	24.1	23.7
82.5°	19.2	18.8	18.8	18.7	18.7	18.4	18.4
85°	10.9	11.3	10.9	10.7	10.7	10.7	10.9
87.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.1
90°	15.7	15.4	15.4	15.5	15.6	15.7	15.8
92.5°	14.9	14.9	15.0	15.0	15.0	15.1	15.1
95°	29.8	29.8	29.7	29.4	29.3	29.0	28.9
97.5°	50.1	50.1	50.0	50.0	50.0	50.0	49.9
100°	64.2	64.2	64.1	64.0	63.9	63.8	63.7
102.5°	79.7	79.7	79.7	79.7	79.5	79.4	79.3
105°	102.9	103.1	103.2	103.2	103.2	103.2	103.2
107.5°	127.8	127.8	127.6	127.1	126.7	126.2	125.7
110°	144.6	144.6	144.5	144.1	143.8	143.5	143.2



TEST NUMBER: P331652-930

CATALOG NUMBER: S122RDIP-S485D530U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	161.3	161.1	160.9	160.6	160.4	160.1	160.0
115°	187.5	187.4	187.2	186.9	186.6	186.3	186.0
117.5°	212.5	212.3	212.1	211.7	211.4	211.1	210.8
120°	229.7	229.7	229.5	229.2	228.9	228.6	228.3
122.5°	246.8	246.5	246.3	246.1	245.8	245.6	245.4
125°	272.5	272.1	271.9	271.8	271.7	271.6	271.5
127.5°	297.3	297.0	296.6	296.3	296.0	295.6	295.3
130°	314.6	314.4	314.1	313.6	313.2	312.8	312.4
132.5°	330.9	330.5	330.1	329.8	329.5	329.1	328.8
135°	355.8	355.7	355.5	355.2	354.9	354.6	354.2
137.5°	379.3	379.2	379.0	378.5	378.1	377.7	377.3
140°	395.2	395.2	395.0	394.5	394.1	393.7	393.3
142.5°	409.5	409.6	409.4	409.0	408.6	408.2	407.8
145°	431.3	431.4	431.2	430.8	430.4	430.0	429.6
147.5°	450.5	450.7	450.6	450.2	449.8	449.4	449.0
150°	462.6	462.9	462.9	462.6	462.3	461.9	461.7
152.5°	474.7	475.2	475.2	474.7	474.3	473.9	473.6
155°	490.2	490.7	490.8	490.5	490.2	489.8	489.6
157.5°	504.5	505.2	505.3	504.8	504.3	503.9	503.3
160°	512.8	513.4	513.6	513.1	512.7	512.3	511.8
162.5°	520.5	521.2	521.3	520.8	520.3	519.8	519.3
165°	530.4	531.0	531.2	530.6	530.1	529.6	529.0
167.5°	538.4	539.2	539.2	538.7	538.2	537.6	537.0
170°	542.9	543.6	543.6	543.0	542.4	541.8	541.2
172.5°	546.3	546.9	547.0	546.4	545.8	545.1	544.5
175°	549.8	550.6	550.7	550.0	549.3	548.8	548.1
177.5°	551.3	551.8	551.8	551.3	550.8	550.3	549.8
180°	550.9	550.9	550.9	550.9	550.9	550.9	550.9

(END OF REPORT)