

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331659-930

Luminaire Tested: **S122RDIP-S485D725U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331659-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D725U930-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3823.5 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	19
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14149	14149	14149	14149
5°	15801	14237	12624	14237
10°	17531	14137	10942	14137
15°	18392	13929	8622	13929
20°	15945	13622	7459	13622
25°	10457	13201	6661	13201
30°	7040	12693	6027	12693
35°	5702	12051	5436	12051
40°	5069	11352	5031	11352
45°	4590	10533	4491	10533
50°	4175	9718	4160	9718
55°	3924	8819	3873	8819
60°	3284	7992	3242	7992
65°	2770	7259	3140	7259
70°	2559	6482	2960	6482
75°	2395	5639	2739	5639
80°	2204	4640	2436	4640
85°	2019	3668	2149	3668



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.1	2.2
10°-20°	231.5	6.1
20°-30°	298.2	7.8
30°-40°	283.4	7.4
40°-50°	242.8	6.4
50°-60°	184.9	4.8
60°-70°	116.9	3.1
70°-80°	58.4	1.5
80°-90°	18.2	0.5
90°-100°	132.5	3.5
100°-110°	449.7	11.8
110°-120°	477.7	12.5
120°-130°	393.2	10.3
130°-140°	315.8	8.3
140°-150°	238.6	6.2
150°-160°	167.7	4.4
160°-170°	98.7	2.6
170°-180°	32.1	0.8
0°-30°	612.8	16.0
0°-40°	896.2	23.4
0°-60°	1323.9	34.6
0°-90°	1517.3	39.7
90°-120°	1059.9	27.7
90°-150°	2007.6	52.5
90°-180°	2306.0	60.3
0°-180°	3823.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	876	876	876	876	876	
5°	975	878	779	878	975	96
15°	1100	833	516	833	1100	297
25°	587	741	374	741	587	279
35°	289	611	276	611	289	185
45°	201	461	197	461	201	156
55°	139	313	138	313	139	122
65°	72	190	82	190	72	74
75°	38	90	44	90	38	41
85°	11	20	12	20	11	12
90°	21	1	21	1	21	12
95°	73	22	73	22	73	94
105°	718	78	718	78	718	695
115°	945	137	945	137	945	926
125°	767	191	767	191	767	693
135°	635	224	635	224	635	494
145°	507	256	507	256	507	322
155°	426	291	426	291	426	199
165°	374	317	374	317	374	107
175°	337	331	337	331	337	33
180°	331	331	331	331	331	



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	911.8	912.6	913.3	911.6	911.6	910.1	906.9	904.5	897.6	896.7	896.7
5°	974.9	974.3	975.5	971.5	966.0	964.8	959.0	951.5	943.5	934.7	932.9
7.5°	1037.6	1036.7	1034.3	1033.6	1029.4	1020.2	1010.9	1000.9	987.8	974.9	968.5
10°	1069.3	1079.3	1073.3	1062.6	1064.7	1050.4	1042.8	1029.7	1018.7	999.6	995.3
12.5°	1100.4	1104.4	1102.4	1096.4	1093.7	1083.8	1073.5	1062.1	1041.9	1024.7	1009.7
15°	1100.3	1106.1	1107.7	1105.8	1107.3	1106.7	1101.2	1091.8	1074.2	1055.2	1038.9
17.5°	1019.1	1023.1	1033.1	1039.8	1048.4	1066.4	1075.3	1078.8	1076.1	1065.4	1053.8
20°	928.0	921.3	949.3	963.6	975.8	1006.2	1032.4	1042.4	1058.6	1058.3	1055.2
22.5°	798.9	800.5	827.0	844.0	879.6	910.0	939.9	977.7	1008.9	1029.6	1041.6
25°	587.0	598.6	625.1	648.2	687.8	744.4	795.9	855.6	911.8	956.3	998.7
27.5°	440.8	441.7	462.7	484.1	507.6	554.0	618.8	690.1	770.4	836.6	912.8
30°	377.6	375.7	384.6	397.6	417.8	453.6	502.4	572.4	652.5	752.4	841.2
32.5°	332.7	332.8	339.5	349.2	365.8	390.0	423.5	480.3	556.0	654.2	758.4
35°	289.3	288.9	293.8	300.8	307.8	323.3	346.2	376.0	428.1	519.8	626.3
37.5°	258.0	259.4	261.8	266.2	273.9	282.5	296.3	316.3	353.4	407.6	497.1
40°	240.5	241.2	244.5	248.2	252.7	259.4	270.7	286.8	313.9	357.1	422.6
42.5°	224.5	225.0	227.5	230.8	234.4	241.2	250.5	264.4	286.4	320.1	374.1
45°	201.0	201.0	203.1	204.6	208.6	214.7	222.3	233.8	249.1	274.0	310.0
47.5°	178.9	179.0	180.3	183.0	185.5	190.2	197.7	207.2	218.3	237.6	268.2
50°	166.2	166.6	167.5	169.6	171.1	175.4	181.2	189.4	201.0	215.9	241.4
52.5°	156.0	155.8	156.9	157.9	158.9	162.0	166.3	173.6	183.9	196.9	218.1
55°	139.4	138.2	140.1	141.5	142.5	143.7	146.1	150.7	159.6	170.5	186.3
57.5°	118.7	118.2	119.5	120.9	123.8	127.1	129.1	132.1	136.6	144.5	160.2
60°	101.7	101.7	104.4	105.3	108.7	112.9	117.2	119.7	124.3	129.4	141.0
62.5°	86.6	86.8	88.1	89.0	90.9	96.1	102.2	107.5	111.8	116.8	124.4
65°	72.5	73.1	73.1	73.7	74.9	76.1	78.5	82.8	90.4	97.4	103.2
67.5°	61.5	61.7	61.9	62.5	62.8	64.1	65.1	67.0	68.7	75.4	82.6
70°	54.2	55.1	54.8	55.4	55.7	56.3	57.6	58.5	61.2	62.7	67.0
72.5°	47.4	48.0	48.0	48.3	49.2	49.2	50.2	51.1	52.9	54.2	56.5
75°	38.4	38.1	38.4	39.0	39.3	39.5	39.5	40.8	41.7	43.0	44.4
77.5°	29.6	29.9	29.8	29.9	29.9	30.5	30.4	31.0	31.9	32.5	33.3
80°	23.7	24.1	23.7	24.1	24.4	24.6	24.4	24.6	25.6	26.2	26.2
82.5°	18.4	18.4	18.7	18.7	18.8	18.8	19.2	19.3	20.0	19.8	20.1
85°	10.9	10.7	10.7	10.7	10.9	11.3	10.9	10.9	11.3	11.3	11.3
87.5°	8.1	8.3	8.3	8.3	8.3	8.2	8.0	8.5	8.3	8.7	8.3
90°	21.0	21.0	21.0	21.0	21.0	20.4	19.2	20.4	21.0	21.7	21.0
92.5°	35.3	36.4	35.8	37.8	38.4	42.3	47.7	55.6	70.0	82.8	81.7
95°	72.6	72.0	73.9	79.0	87.3	101.3	128.1	167.0	218.6	249.8	221.2
97.5°	143.0	148.4	157.7	173.3	203.8	249.8	318.8	389.6	447.4	426.5	321.2
100°	228.1	239.6	258.1	285.5	338.4	415.6	502.9	581.9	595.3	503.4	346.7
102.5°	401.5	417.0	440.1	486.9	544.4	626.1	690.0	707.8	650.3	506.1	337.0
105°	718.3	727.2	754.6	794.1	833.6	854.7	846.4	774.4	641.8	472.2	318.0
107.5°	917.5	929.4	934.8	937.0	932.1	901.2	834.9	726.4	585.8	436.0	308.6
110°	977.6	978.3	972.6	960.4	933.0	880.8	799.2	685.1	550.7	418.7	306.6



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	976.6	973.2	962.4	942.1	904.0	844.1	756.8	647.4	526.2	407.5	307.0
115°	945.2	939.4	922.8	893.5	848.2	782.6	699.1	601.0	495.9	395.2	309.7
117.5°	888.9	884.1	866.7	835.7	789.5	728.0	652.2	566.1	476.7	389.1	314.3
120°	852.7	846.4	827.9	797.9	753.3	695.3	627.8	548.7	466.5	385.6	317.4
122.5°	815.0	809.7	793.2	763.8	723.7	671.3	607.4	535.0	457.9	383.5	321.0
125°	766.7	761.6	745.7	721.5	684.4	636.7	580.6	514.9	445.5	379.8	326.3
127.5°	724.4	720.3	706.5	683.9	651.6	607.5	554.6	495.2	434.0	377.6	331.8
130°	700.4	695.3	682.6	660.9	629.7	587.6	537.3	482.4	426.4	376.7	335.9
132.5°	675.4	670.8	659.1	637.5	606.7	567.2	521.0	470.2	420.3	376.2	340.0
135°	635.4	632.8	621.4	600.4	572.9	537.3	495.2	453.1	411.7	375.4	344.8
137.5°	596.1	592.3	582.3	564.2	539.2	508.1	474.7	439.5	405.7	375.3	349.1
140°	569.2	565.3	555.7	539.2	518.8	490.7	461.5	430.8	402.2	374.7	351.1
142.5°	542.1	541.4	532.8	517.8	498.4	474.9	449.7	423.7	398.6	374.7	352.7
145°	507.3	505.4	499.0	488.2	472.9	454.4	434.6	413.6	393.9	373.5	354.3
147.5°	478.1	477.0	472.6	464.0	451.3	437.8	422.4	405.9	389.1	371.2	354.9
150°	460.8	460.2	456.3	448.7	439.1	427.6	414.3	400.2	384.9	369.7	354.3
152.5°	446.0	445.9	443.0	436.4	428.9	419.0	407.6	394.6	381.4	367.1	353.4
155°	426.4	427.6	425.1	420.6	413.6	406.6	397.1	386.9	374.7	362.6	351.8
157.5°	409.7	409.7	408.5	404.8	399.8	394.4	386.4	377.8	368.5	358.1	348.9
160°	398.9	398.9	398.4	395.2	390.7	386.2	379.2	372.2	363.9	355.0	347.3
162.5°	388.7	389.3	388.7	386.5	382.0	378.5	372.6	366.6	359.8	352.5	345.8
165°	374.1	374.7	374.7	372.2	369.7	367.1	362.6	358.2	353.1	347.3	342.9
167.5°	360.6	361.3	361.5	360.1	359.0	356.6	353.6	350.2	346.4	342.9	340.0
170°	352.5	353.7	354.3	352.5	351.8	350.5	348.0	346.1	342.9	340.3	338.4
172.5°	345.8	346.6	347.2	346.3	345.7	345.0	342.9	341.4	339.3	337.3	336.4
175°	337.1	338.4	339.1	338.4	338.4	337.8	337.1	336.5	334.6	333.9	333.3
177.5°	331.9	333.0	333.5	333.5	333.5	333.5	333.0	333.0	331.9	331.4	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	897.2	895.3	893.6	889.2	887.0	882.1	881.3	881.1	874.8	868.7	867.0
5°	928.0	923.2	915.8	907.3	898.5	889.3	883.2	878.4	866.2	854.6	847.9
7.5°	959.0	948.6	936.0	919.8	906.4	891.3	880.1	870.0	852.7	836.2	825.0
10°	982.2	965.2	948.4	926.2	908.8	891.8	876.0	862.3	842.8	820.8	805.3
12.5°	996.5	977.8	954.7	933.0	910.5	888.8	867.6	850.0	827.2	804.5	786.0
15°	1016.0	995.9	967.9	936.9	907.9	879.6	855.2	833.3	803.5	776.4	753.8
17.5°	1031.9	1004.2	974.1	938.2	904.7	868.8	837.4	809.3	776.2	743.5	717.0
20°	1037.0	1009.6	974.9	939.0	899.4	857.0	823.3	792.8	757.2	721.5	691.1
22.5°	1033.8	1012.5	973.9	930.9	890.4	846.1	808.0	772.6	733.1	696.8	661.5
25°	1012.4	1005.0	968.5	921.6	875.3	823.9	779.8	741.0	696.0	657.0	618.6
27.5°	962.2	978.0	955.4	905.4	853.9	798.7	749.2	705.2	658.4	614.5	576.3
30°	914.0	950.2	940.4	894.2	836.7	782.4	726.8	680.8	630.9	585.8	548.0
32.5°	848.0	907.8	917.4	878.6	819.1	759.5	701.2	655.4	603.3	555.8	519.0
35°	742.9	832.4	873.5	848.8	789.1	725.0	664.6	611.4	559.0	512.1	475.6
37.5°	617.5	739.4	808.0	809.7	754.9	688.1	622.5	569.6	515.9	469.9	430.4
40°	536.1	668.3	757.5	777.3	731.0	658.8	592.5	538.6	486.2	441.2	395.8
42.5°	463.1	594.8	704.4	738.8	702.1	630.4	563.8	507.4	456.5	413.8	367.5
45°	374.5	489.6	610.4	672.0	651.6	585.1	514.9	461.3	413.4	376.6	332.2
47.5°	315.9	397.1	514.0	597.2	596.8	536.2	467.1	415.7	371.4	336.9	300.8
50°	282.5	353.2	452.2	546.5	554.4	503.6	437.8	386.9	345.6	309.3	280.4
52.5°	252.6	310.8	399.7	490.2	512.7	468.7	405.0	358.0	317.8	284.5	259.7
55°	213.4	258.4	326.1	410.7	444.8	413.8	357.1	313.3	280.7	252.7	231.4
57.5°	180.5	214.3	268.6	336.7	376.4	356.9	310.2	274.6	246.7	221.4	204.6
60°	159.9	187.5	233.5	290.5	334.3	320.6	280.7	247.5	223.8	201.9	186.1
62.5°	140.4	164.2	203.6	249.8	290.0	284.3	251.8	223.9	203.1	183.1	169.7
65°	112.9	130.3	161.0	197.3	229.6	232.3	208.9	190.0	171.4	155.6	143.7
67.5°	89.9	101.3	122.9	153.4	177.7	186.3	171.9	157.5	142.8	130.5	120.3
70°	75.8	85.0	100.8	125.5	147.7	156.8	148.5	137.3	124.5	114.5	105.7
72.5°	61.5	70.4	82.0	100.1	119.2	129.1	126.2	118.1	107.7	99.4	91.1
75°	46.3	49.0	56.9	69.1	84.1	92.5	94.7	90.4	82.2	75.8	70.9
77.5°	34.2	35.9	39.6	46.1	55.8	63.3	66.5	66.0	60.3	56.7	52.1
80°	27.4	28.3	30.2	32.9	40.2	47.8	49.9	49.9	46.0	44.4	39.9
82.5°	20.8	21.5	22.6	24.1	27.6	34.2	36.5	37.0	34.5	32.5	28.9
85°	11.9	11.6	12.1	13.1	13.7	15.5	19.2	19.8	19.2	16.7	15.8
87.5°	7.6	6.9	6.3	5.7	5.6	5.6	6.4	7.2	6.6	6.4	6.1
90°	17.2	12.7	9.5	7.7	6.4	5.1	2.5	0.7	2.5	5.1	6.4
92.5°	63.6	43.4	28.9	22.9	18.6	15.8	11.3	7.7	11.3	15.8	18.6
95°	147.2	91.8	62.5	47.1	36.9	31.2	24.9	22.3	24.9	31.2	36.9
97.5°	198.4	121.1	84.2	66.9	55.2	46.6	39.8	36.4	39.8	46.6	55.2
100°	209.0	131.3	97.5	79.7	66.9	56.7	51.0	49.1	51.0	56.7	66.9
102.5°	209.5	140.5	109.3	91.4	78.1	67.9	62.2	60.8	62.2	67.9	78.1
105°	212.9	156.1	126.2	108.4	94.3	84.8	80.3	77.8	80.3	84.8	94.3
107.5°	221.7	172.2	143.2	125.1	111.3	102.5	98.2	96.1	98.2	102.5	111.3
110°	228.8	182.9	154.9	136.4	123.0	114.7	110.9	108.4	110.9	114.7	123.0



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	236.4	193.1	166.1	147.1	134.2	126.5	122.1	119.5	122.1	126.5	134.2
115°	247.9	209.0	181.6	164.4	151.6	144.1	140.2	137.1	140.2	144.1	151.6
117.5°	260.2	223.7	198.4	180.5	168.3	161.5	157.7	155.2	157.7	161.5	168.3
120°	268.3	233.9	209.0	191.2	178.5	172.7	168.9	166.3	168.9	172.7	178.5
122.5°	275.5	243.6	220.3	201.9	189.1	182.9	179.1	177.1	179.1	182.9	189.1
125°	286.8	258.1	235.1	217.4	204.6	196.9	193.1	191.2	193.1	196.9	204.6
127.5°	297.3	271.7	249.3	231.0	218.7	210.3	205.0	202.4	205.0	210.3	218.7
130°	304.0	279.8	257.5	239.6	226.9	217.9	211.6	209.0	211.6	217.9	226.9
132.5°	310.6	286.9	265.6	247.8	234.6	225.1	218.3	215.2	218.3	225.1	234.6
135°	319.3	297.0	276.6	258.8	244.1	234.6	226.9	224.4	226.9	234.6	244.1
137.5°	326.0	305.2	285.0	268.5	253.9	243.7	236.0	233.0	236.0	243.7	253.9
140°	329.5	309.7	290.7	274.0	260.0	249.8	242.1	239.6	242.1	249.8	260.0
142.5°	332.6	313.3	294.7	279.2	265.6	255.4	248.3	246.2	248.3	255.4	265.6
145°	336.5	318.7	301.4	287.4	274.7	265.1	258.8	256.2	258.8	265.1	274.7
147.5°	338.7	323.0	306.8	294.3	283.7	274.9	268.8	266.9	268.8	274.9	283.7
150°	339.7	325.1	310.4	298.9	289.3	281.0	276.0	274.0	276.0	281.0	289.3
152.5°	340.2	327.1	314.0	303.5	294.4	287.1	282.1	281.2	282.1	287.1	294.4
155°	341.0	330.1	319.3	309.7	302.7	295.7	291.9	291.2	291.9	295.7	302.7
157.5°	341.0	332.3	323.1	315.1	309.5	303.4	300.3	299.7	300.3	303.4	309.5
160°	341.0	333.3	325.6	318.7	313.6	308.4	305.9	305.2	305.9	308.4	313.6
162.5°	340.5	333.9	327.2	321.7	317.2	313.1	310.5	310.9	310.5	313.1	317.2
165°	339.1	334.6	328.9	325.1	321.9	318.0	316.7	317.4	316.7	318.0	321.9
167.5°	338.2	334.4	330.3	327.8	325.5	323.1	322.0	322.8	322.0	323.1	325.5
170°	337.1	333.9	330.8	328.9	327.6	325.6	325.1	326.3	325.1	325.6	327.6
172.5°	335.6	333.5	331.3	329.9	329.1	327.2	327.6	328.3	327.6	327.2	329.1
175°	333.9	332.6	331.4	330.8	330.8	329.5	330.1	330.8	330.1	329.5	330.8
177.5°	333.0	331.9	331.4	331.4	331.4	330.4	330.9	331.9	330.9	330.4	331.4
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	863.8	862.1	858.9	854.1	851.2	846.0	842.6	844.6	845.1	844.6	844.1
5°	840.7	834.2	825.4	816.8	808.9	800.5	795.6	793.4	789.1	786.8	785.5
7.5°	812.5	801.5	789.0	774.2	761.6	748.4	741.6	738.3	729.5	724.8	720.6
10°	791.6	774.2	761.7	742.2	730.4	713.1	701.2	701.5	689.6	682.9	678.0
12.5°	768.5	749.4	728.6	711.1	694.6	680.7	666.3	660.6	647.9	641.5	628.4
15°	730.1	707.8	686.0	662.2	645.5	623.9	603.2	577.9	557.5	539.8	534.9
17.5°	688.2	660.7	638.7	610.8	582.1	545.8	521.8	507.1	494.8	485.5	478.6
20°	659.5	631.4	608.1	566.0	527.3	502.6	485.0	473.8	461.0	450.9	445.4
22.5°	629.2	600.1	568.1	521.1	491.1	471.2	455.5	442.5	433.9	426.1	421.1
25°	586.4	554.4	501.7	469.4	445.2	424.4	413.4	405.5	396.4	385.7	380.9
27.5°	541.1	490.2	452.4	428.4	405.2	391.8	381.9	370.1	361.9	357.1	352.0
30°	507.2	456.4	426.9	400.6	384.3	369.3	357.8	351.1	343.2	334.9	331.6
32.5°	469.4	428.8	400.6	378.8	362.1	349.4	340.2	329.4	323.7	318.6	311.6
35°	422.6	391.8	366.0	348.3	332.5	322.1	311.4	305.1	294.7	290.5	287.7
37.5°	382.9	356.2	336.9	318.3	305.7	294.3	287.8	277.6	273.1	267.2	261.4
40°	360.4	334.3	315.8	300.5	286.5	277.9	269.8	261.5	254.9	252.1	245.1
42.5°	337.6	316.3	297.7	281.0	271.7	262.6	252.3	246.2	239.2	234.8	230.5
45°	306.0	287.1	271.3	257.6	247.2	237.8	231.1	221.0	217.1	208.2	204.6
47.5°	278.2	260.7	245.6	232.5	222.4	216.3	206.5	198.6	192.3	186.9	182.2
50°	258.4	243.9	229.3	217.7	208.6	199.7	189.7	185.7	175.9	173.3	170.5
52.5°	240.4	226.6	213.2	201.9	192.7	184.2	175.3	170.2	163.5	160.8	158.8
55°	215.2	201.9	189.1	179.0	169.9	161.0	155.6	149.2	146.1	144.0	141.5
57.5°	189.9	177.9	168.0	157.9	148.7	141.7	135.3	131.5	128.3	125.6	122.6
60°	173.8	162.2	153.4	144.0	134.6	128.8	123.9	119.4	115.7	111.5	110.2
62.5°	156.8	146.7	138.6	129.4	121.2	115.9	111.3	107.0	102.6	96.4	94.7
65°	133.4	125.5	116.9	109.3	102.0	96.9	90.1	85.3	83.4	82.8	82.5
67.5°	112.2	104.7	97.3	89.6	82.9	78.1	74.7	73.9	72.7	72.3	71.5
70°	98.0	91.1	83.7	76.4	70.0	69.1	67.9	66.7	65.1	64.6	63.9
72.5°	85.4	78.1	70.8	65.0	62.2	61.1	59.8	58.6	57.6	57.0	56.7
75°	65.5	58.8	53.9	51.8	50.2	49.3	47.5	46.6	46.0	45.1	44.8
77.5°	47.1	43.4	41.1	39.8	38.2	37.2	36.2	35.2	34.6	34.4	33.9
80°	36.0	34.1	32.6	30.7	30.2	28.9	28.6	27.7	28.0	27.1	27.1
82.5°	27.9	25.6	24.3	23.5	22.8	21.9	21.5	21.1	21.2	20.5	20.5
85°	14.3	13.7	13.1	12.5	12.5	11.6	11.9	11.6	11.6	10.9	10.7
87.5°	6.2	6.3	6.4	7.3	8.1	8.0	7.8	7.5	7.3	7.5	7.3
90°	7.7	9.5	12.7	17.2	21.0	21.7	21.0	20.4	19.2	20.4	21.0
92.5°	22.9	28.9	43.4	63.6	81.7	82.8	70.0	55.6	47.7	42.3	38.4
95°	47.1	62.5	91.8	147.2	221.2	249.8	218.6	167.0	128.1	101.3	87.3
97.5°	66.9	84.2	121.1	198.4	321.2	426.5	447.4	389.6	318.8	249.8	203.8
100°	79.7	97.5	131.3	209.0	346.7	503.4	595.3	581.9	502.9	415.6	338.4
102.5°	91.4	109.3	140.5	209.5	337.0	506.1	650.3	707.8	690.0	626.1	544.4
105°	108.4	126.2	156.1	212.9	318.0	472.2	641.8	774.4	846.4	854.7	833.6
107.5°	125.1	143.2	172.2	221.7	308.6	436.0	585.8	726.4	834.9	901.2	932.1
110°	136.4	154.9	182.9	228.8	306.6	418.7	550.7	685.1	799.2	880.8	933.0



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	147.1	166.1	193.1	236.4	307.0	407.5	526.2	647.4	756.8	844.1	904.0
115°	164.4	181.6	209.0	247.9	309.7	395.2	495.9	601.0	699.1	782.6	848.2
117.5°	180.5	198.4	223.7	260.2	314.3	389.1	476.7	566.1	652.2	728.0	789.5
120°	191.2	209.0	233.9	268.3	317.4	385.6	466.5	548.7	627.8	695.3	753.3
122.5°	201.9	220.3	243.6	275.5	321.0	383.5	457.9	535.0	607.4	671.3	723.7
125°	217.4	235.1	258.1	286.8	326.3	379.8	445.5	514.9	580.6	636.7	684.4
127.5°	231.0	249.3	271.7	297.3	331.8	377.6	434.0	495.2	554.6	607.5	651.6
130°	239.6	257.5	279.8	304.0	335.9	376.7	426.4	482.4	537.3	587.6	629.7
132.5°	247.8	265.6	286.9	310.6	340.0	376.2	420.3	470.2	521.0	567.2	606.7
135°	258.8	276.6	297.0	319.3	344.8	375.4	411.7	453.1	495.2	537.3	572.9
137.5°	268.5	285.0	305.2	326.0	349.1	375.3	405.7	439.5	474.7	508.1	539.2
140°	274.0	290.7	309.7	329.5	351.1	374.7	402.2	430.8	461.5	490.7	518.8
142.5°	279.2	294.7	313.3	332.6	352.7	374.7	398.6	423.7	449.7	474.9	498.4
145°	287.4	301.4	318.7	336.5	354.3	373.5	393.9	413.6	434.6	454.4	472.9
147.5°	294.3	306.8	323.0	338.7	354.9	371.2	389.1	405.9	422.4	437.8	451.3
150°	298.9	310.4	325.1	339.7	354.3	369.7	384.9	400.2	414.3	427.6	439.1
152.5°	303.5	314.0	327.1	340.2	353.4	367.1	381.4	394.6	407.6	419.0	428.9
155°	309.7	319.3	330.1	341.0	351.8	362.6	374.7	386.9	397.1	406.6	413.6
157.5°	315.1	323.1	332.3	341.0	348.9	358.1	368.5	377.8	386.4	394.4	399.8
160°	318.7	325.6	333.3	341.0	347.3	355.0	363.9	372.2	379.2	386.2	390.7
162.5°	321.7	327.2	333.9	340.5	345.8	352.5	359.8	366.6	372.6	378.5	382.0
165°	325.1	328.9	334.6	339.1	342.9	347.3	353.1	358.2	362.6	367.1	369.7
167.5°	327.8	330.3	334.4	338.2	340.0	342.9	346.4	350.2	353.6	356.6	359.0
170°	328.9	330.8	333.9	337.1	338.4	340.3	342.9	346.1	348.0	350.5	351.8
172.5°	329.9	331.3	333.5	335.6	336.4	337.3	339.3	341.4	342.9	345.0	345.7
175°	330.8	331.4	332.6	333.9	333.3	333.9	334.6	336.5	337.1	337.8	338.4
177.5°	331.4	331.4	331.9	333.0	331.9	331.4	331.9	333.0	333.0	333.5	333.5
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	841.4	841.9	841.1	841.6	841.1	841.9	841.4	844.1	844.6	845.1	844.6
5°	784.0	780.3	779.8	778.9	779.8	780.3	784.0	785.5	786.8	789.1	793.4
7.5°	715.4	714.9	713.4	711.2	713.4	714.9	715.4	720.6	724.8	729.5	738.3
10°	671.3	669.8	669.5	667.4	669.5	669.8	671.3	678.0	682.9	689.6	701.5
12.5°	619.7	609.9	608.9	603.6	608.9	609.9	619.7	628.4	641.5	647.9	660.6
15°	527.7	525.8	519.8	515.8	519.8	525.8	527.7	534.9	539.8	557.5	577.9
17.5°	475.0	469.0	467.2	466.4	467.2	469.0	475.0	478.6	485.5	494.8	507.1
20°	441.2	435.7	434.8	434.1	434.8	435.7	441.2	445.4	450.9	461.0	473.8
22.5°	417.8	412.1	409.7	407.9	409.7	412.1	417.8	421.1	426.1	433.9	442.5
25°	377.8	375.7	374.5	373.9	374.5	375.7	377.8	380.9	385.7	396.4	405.5
27.5°	346.6	341.9	341.0	339.4	341.0	341.9	346.6	352.0	357.1	361.9	370.1
30°	328.8	327.3	325.1	323.3	325.1	327.3	328.8	331.6	334.9	343.2	351.1
32.5°	307.9	306.6	304.7	303.9	304.7	306.6	307.9	311.6	318.6	323.7	329.4
35°	284.7	280.4	278.6	275.8	278.6	280.4	284.7	287.7	290.5	294.7	305.1
37.5°	260.2	257.9	255.4	256.2	255.4	257.9	260.2	261.4	267.2	273.1	277.6
40°	241.2	239.6	239.0	238.7	239.0	239.6	241.2	245.1	252.1	254.9	261.5
42.5°	226.0	221.8	220.2	220.2	220.2	221.8	226.0	230.5	234.8	239.2	246.2
45°	203.1	199.1	196.4	196.7	196.4	199.1	203.1	204.6	208.2	217.1	221.0
47.5°	179.6	179.4	177.7	178.3	177.7	179.4	179.6	182.2	186.9	192.3	198.6
50°	168.4	166.6	165.3	165.6	165.3	166.6	168.4	170.5	173.3	175.9	185.7
52.5°	157.7	156.0	155.1	156.4	155.1	156.0	157.7	158.8	160.8	163.5	170.2
55°	140.1	138.2	137.9	137.6	137.9	138.2	140.1	141.5	144.0	146.1	149.2
57.5°	120.4	119.2	117.3	116.6	117.3	119.2	120.4	122.6	125.6	128.3	131.5
60°	106.2	103.8	100.8	100.4	100.8	103.8	106.2	110.2	111.5	115.7	119.4
62.5°	93.4	92.9	92.3	92.2	92.3	92.9	93.4	94.7	96.4	102.6	107.0
65°	81.9	81.6	81.9	82.2	81.9	81.6	81.9	82.5	82.8	83.4	85.3
67.5°	71.3	70.8	70.3	70.5	70.3	70.8	71.3	71.5	72.3	72.7	73.9
70°	63.3	63.0	62.7	62.7	62.7	63.0	63.3	63.9	64.6	65.1	66.7
72.5°	55.5	55.4	55.2	55.0	55.2	55.4	55.5	56.7	57.0	57.6	58.6
75°	44.4	43.9	43.9	43.9	43.9	43.9	44.4	44.8	45.1	46.0	46.6
77.5°	33.8	33.6	33.3	33.0	33.3	33.6	33.8	33.9	34.4	34.6	35.2
80°	26.8	26.5	26.2	26.2	26.2	26.5	26.8	27.1	27.1	28.0	27.7
82.5°	20.5	20.1	20.1	19.8	20.1	20.1	20.5	20.5	20.5	21.2	21.1
85°	10.9	11.3	10.9	11.6	10.9	11.3	10.9	10.7	10.9	11.6	11.6
87.5°	7.3	7.1	7.3	7.1	7.3	7.1	7.3	7.3	7.5	7.3	7.5
90°	21.0	21.0	21.0	21.0	21.0	21.0	21.0	21.0	20.4	19.2	20.4
92.5°	37.8	35.8	36.4	35.3	36.4	35.8	37.8	38.4	42.3	47.7	55.6
95°	79.0	73.9	72.0	72.6	72.0	73.9	79.0	87.3	101.3	128.1	167.0
97.5°	173.3	157.7	148.4	143.0	148.4	157.7	173.3	203.8	249.8	318.8	389.6
100°	285.5	258.1	239.6	228.1	239.6	258.1	285.5	338.4	415.6	502.9	581.9
102.5°	486.9	440.1	417.0	401.5	417.0	440.1	486.9	544.4	626.1	690.0	707.8
105°	794.1	754.6	727.2	718.3	727.2	754.6	794.1	833.6	854.7	846.4	774.4
107.5°	937.0	934.8	929.4	917.5	929.4	934.8	937.0	932.1	901.2	834.9	726.4
110°	960.4	972.6	978.3	977.6	978.3	972.6	960.4	933.0	880.8	799.2	685.1



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	942.1	962.4	973.2	976.6	973.2	962.4	942.1	904.0	844.1	756.8	647.4
115°	893.5	922.8	939.4	945.2	939.4	922.8	893.5	848.2	782.6	699.1	601.0
117.5°	835.7	866.7	884.1	888.9	884.1	866.7	835.7	789.5	728.0	652.2	566.1
120°	797.9	827.9	846.4	852.7	846.4	827.9	797.9	753.3	695.3	627.8	548.7
122.5°	763.8	793.2	809.7	815.0	809.7	793.2	763.8	723.7	671.3	607.4	535.0
125°	721.5	745.7	761.6	766.7	761.6	745.7	721.5	684.4	636.7	580.6	514.9
127.5°	683.9	706.5	720.3	724.4	720.3	706.5	683.9	651.6	607.5	554.6	495.2
130°	660.9	682.6	695.3	700.4	695.3	682.6	660.9	629.7	587.6	537.3	482.4
132.5°	637.5	659.1	670.8	675.4	670.8	659.1	637.5	606.7	567.2	521.0	470.2
135°	600.4	621.4	632.8	635.4	632.8	621.4	600.4	572.9	537.3	495.2	453.1
137.5°	564.2	582.3	592.3	596.1	592.3	582.3	564.2	539.2	508.1	474.7	439.5
140°	539.2	555.7	565.3	569.2	565.3	555.7	539.2	518.8	490.7	461.5	430.8
142.5°	517.8	532.8	541.4	542.1	541.4	532.8	517.8	498.4	474.9	449.7	423.7
145°	488.2	499.0	505.4	507.3	505.4	499.0	488.2	472.9	454.4	434.6	413.6
147.5°	464.0	472.6	477.0	478.1	477.0	472.6	464.0	451.3	437.8	422.4	405.9
150°	448.7	456.3	460.2	460.8	460.2	456.3	448.7	439.1	427.6	414.3	400.2
152.5°	436.4	443.0	445.9	446.0	445.9	443.0	436.4	428.9	419.0	407.6	394.6
155°	420.6	425.1	427.6	426.4	427.6	425.1	420.6	413.6	406.6	397.1	386.9
157.5°	404.8	408.5	409.7	409.7	409.7	408.5	404.8	399.8	394.4	386.4	377.8
160°	395.2	398.4	398.9	398.9	398.9	398.4	395.2	390.7	386.2	379.2	372.2
162.5°	386.5	388.7	389.3	388.7	389.3	388.7	386.5	382.0	378.5	372.6	366.6
165°	372.2	374.7	374.7	374.1	374.7	374.7	372.2	369.7	367.1	362.6	358.2
167.5°	360.1	361.5	361.3	360.6	361.3	361.5	360.1	359.0	356.6	353.6	350.2
170°	352.5	354.3	353.7	352.5	353.7	354.3	352.5	351.8	350.5	348.0	346.1
172.5°	346.3	347.2	346.6	345.8	346.6	347.2	346.3	345.7	345.0	342.9	341.4
175°	338.4	339.1	338.4	337.1	338.4	339.1	338.4	338.4	337.8	337.1	336.5
177.5°	333.5	333.5	333.0	331.9	333.0	333.5	333.5	333.5	333.5	333.0	333.0
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	842.6	846.0	851.2	854.1	858.9	862.1	863.8	867.0	868.7	874.8	881.1
5°	795.6	800.5	808.9	816.8	825.4	834.2	840.7	847.9	854.6	866.2	878.4
7.5°	741.6	748.4	761.6	774.2	789.0	801.5	812.5	825.0	836.2	852.7	870.0
10°	701.2	713.1	730.4	742.2	761.7	774.2	791.6	805.3	820.8	842.8	862.3
12.5°	666.3	680.7	694.6	711.1	728.6	749.4	768.5	786.0	804.5	827.2	850.0
15°	603.2	623.9	645.5	662.2	686.0	707.8	730.1	753.8	776.4	803.5	833.3
17.5°	521.8	545.8	582.1	610.8	638.7	660.7	688.2	717.0	743.5	776.2	809.3
20°	485.0	502.6	527.3	566.0	608.1	631.4	659.5	691.1	721.5	757.2	792.8
22.5°	455.5	471.2	491.1	521.1	568.1	600.1	629.2	661.5	696.8	733.1	772.6
25°	413.4	424.4	445.2	469.4	501.7	554.4	586.4	618.6	657.0	696.0	741.0
27.5°	381.9	391.8	405.2	428.4	452.4	490.2	541.1	576.3	614.5	658.4	705.2
30°	357.8	369.3	384.3	400.6	426.9	456.4	507.2	548.0	585.8	630.9	680.8
32.5°	340.2	349.4	362.1	378.8	400.6	428.8	469.4	519.0	555.8	603.3	655.4
35°	311.4	322.1	332.5	348.3	366.0	391.8	422.6	475.6	512.1	559.0	611.4
37.5°	287.8	294.3	305.7	318.3	336.9	356.2	382.9	430.4	469.9	515.9	569.6
40°	269.8	277.9	286.5	300.5	315.8	334.3	360.4	395.8	441.2	486.2	538.6
42.5°	252.3	262.6	271.7	281.0	297.7	316.3	337.6	367.5	413.8	456.5	507.4
45°	231.1	237.8	247.2	257.6	271.3	287.1	306.0	332.2	376.6	413.4	461.3
47.5°	206.5	216.3	222.4	232.5	245.6	260.7	278.2	300.8	336.9	371.4	415.7
50°	189.7	199.7	208.6	217.7	229.3	243.9	258.4	280.4	309.3	345.6	386.9
52.5°	175.3	184.2	192.7	201.9	213.2	226.6	240.4	259.7	284.5	317.8	358.0
55°	155.6	161.0	169.9	179.0	189.1	201.9	215.2	231.4	252.7	280.7	313.3
57.5°	135.3	141.7	148.7	157.9	168.0	177.9	189.9	204.6	221.4	246.7	274.6
60°	123.9	128.8	134.6	144.0	153.4	162.2	173.8	186.1	201.9	223.8	247.5
62.5°	111.3	115.9	121.2	129.4	138.6	146.7	156.8	169.7	183.1	203.1	223.9
65°	90.1	96.9	102.0	109.3	116.9	125.5	133.4	143.7	155.6	171.4	190.0
67.5°	74.7	78.1	82.9	89.6	97.3	104.7	112.2	120.3	130.5	142.8	157.5
70°	67.9	69.1	70.0	76.4	83.7	91.1	98.0	105.7	114.5	124.5	137.3
72.5°	59.8	61.1	62.2	65.0	70.8	78.1	85.4	91.1	99.4	107.7	118.1
75°	47.5	49.3	50.2	51.8	53.9	58.8	65.5	70.9	75.8	82.2	90.4
77.5°	36.2	37.2	38.2	39.8	41.1	43.4	47.1	52.1	56.7	60.3	66.0
80°	28.6	28.9	30.2	30.7	32.6	34.1	36.0	39.9	44.4	46.0	49.9
82.5°	21.5	21.9	22.8	23.5	24.3	25.6	27.9	28.9	32.5	34.5	37.0
85°	11.9	11.6	12.5	12.5	13.1	13.7	14.3	15.8	16.7	19.2	19.8
87.5°	7.8	8.0	8.1	7.3	6.4	6.3	6.2	6.1	6.4	6.6	7.2
90°	21.0	21.7	21.0	17.2	12.7	9.5	7.7	6.4	5.1	2.5	0.7
92.5°	70.0	82.8	81.7	63.6	43.4	28.9	22.9	18.6	15.8	11.3	7.7
95°	218.6	249.8	221.2	147.2	91.8	62.5	47.1	36.9	31.2	24.9	22.3
97.5°	447.4	426.5	321.2	198.4	121.1	84.2	66.9	55.2	46.6	39.8	36.4
100°	595.3	503.4	346.7	209.0	131.3	97.5	79.7	66.9	56.7	51.0	49.1
102.5°	650.3	506.1	337.0	209.5	140.5	109.3	91.4	78.1	67.9	62.2	60.8
105°	641.8	472.2	318.0	212.9	156.1	126.2	108.4	94.3	84.8	80.3	77.8
107.5°	585.8	436.0	308.6	221.7	172.2	143.2	125.1	111.3	102.5	98.2	96.1
110°	550.7	418.7	306.6	228.8	182.9	154.9	136.4	123.0	114.7	110.9	108.4



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	526.2	407.5	307.0	236.4	193.1	166.1	147.1	134.2	126.5	122.1	119.5
115°	495.9	395.2	309.7	247.9	209.0	181.6	164.4	151.6	144.1	140.2	137.1
117.5°	476.7	389.1	314.3	260.2	223.7	198.4	180.5	168.3	161.5	157.7	155.2
120°	466.5	385.6	317.4	268.3	233.9	209.0	191.2	178.5	172.7	168.9	166.3
122.5°	457.9	383.5	321.0	275.5	243.6	220.3	201.9	189.1	182.9	179.1	177.1
125°	445.5	379.8	326.3	286.8	258.1	235.1	217.4	204.6	196.9	193.1	191.2
127.5°	434.0	377.6	331.8	297.3	271.7	249.3	231.0	218.7	210.3	205.0	202.4
130°	426.4	376.7	335.9	304.0	279.8	257.5	239.6	226.9	217.9	211.6	209.0
132.5°	420.3	376.2	340.0	310.6	286.9	265.6	247.8	234.6	225.1	218.3	215.2
135°	411.7	375.4	344.8	319.3	297.0	276.6	258.8	244.1	234.6	226.9	224.4
137.5°	405.7	375.3	349.1	326.0	305.2	285.0	268.5	253.9	243.7	236.0	233.0
140°	402.2	374.7	351.1	329.5	309.7	290.7	274.0	260.0	249.8	242.1	239.6
142.5°	398.6	374.7	352.7	332.6	313.3	294.7	279.2	265.6	255.4	248.3	246.2
145°	393.9	373.5	354.3	336.5	318.7	301.4	287.4	274.7	265.1	258.8	256.2
147.5°	389.1	371.2	354.9	338.7	323.0	306.8	294.3	283.7	274.9	268.8	266.9
150°	384.9	369.7	354.3	339.7	325.1	310.4	298.9	289.3	281.0	276.0	274.0
152.5°	381.4	367.1	353.4	340.2	327.1	314.0	303.5	294.4	287.1	282.1	281.2
155°	374.7	362.6	351.8	341.0	330.1	319.3	309.7	302.7	295.7	291.9	291.2
157.5°	368.5	358.1	348.9	341.0	332.3	323.1	315.1	309.5	303.4	300.3	299.7
160°	363.9	355.0	347.3	341.0	333.3	325.6	318.7	313.6	308.4	305.9	305.2
162.5°	359.8	352.5	345.8	340.5	333.9	327.2	321.7	317.2	313.1	310.5	310.9
165°	353.1	347.3	342.9	339.1	334.6	328.9	325.1	321.9	318.0	316.7	317.4
167.5°	346.4	342.9	340.0	338.2	334.4	330.3	327.8	325.5	323.1	322.0	322.8
170°	342.9	340.3	338.4	337.1	333.9	330.8	328.9	327.6	325.6	325.1	326.3
172.5°	339.3	337.3	336.4	335.6	333.5	331.3	329.9	329.1	327.2	327.6	328.3
175°	334.6	333.9	333.3	333.9	332.6	331.4	330.8	330.8	329.5	330.1	330.8
177.5°	331.9	331.4	331.9	333.0	331.9	331.4	331.4	331.4	330.4	330.9	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	881.3	882.1	887.0	889.2	893.6	895.3	897.2	896.7	896.7	897.6	904.5
5°	883.2	889.3	898.5	907.3	915.8	923.2	928.0	932.9	934.7	943.5	951.5
7.5°	880.1	891.3	906.4	919.8	936.0	948.6	959.0	968.5	974.9	987.8	1000.9
10°	876.0	891.8	908.8	926.2	948.4	965.2	982.2	995.3	999.6	1018.7	1029.7
12.5°	867.6	888.8	910.5	933.0	954.7	977.8	996.5	1009.7	1024.7	1041.9	1062.1
15°	855.2	879.6	907.9	936.9	967.9	995.9	1016.0	1038.9	1055.2	1074.2	1091.8
17.5°	837.4	868.8	904.7	938.2	974.1	1004.2	1031.9	1053.8	1065.4	1076.1	1078.8
20°	823.3	857.0	899.4	939.0	974.9	1009.6	1037.0	1055.2	1058.3	1058.6	1042.4
22.5°	808.0	846.1	890.4	930.9	973.9	1012.5	1033.8	1041.6	1029.6	1008.9	977.7
25°	779.8	823.9	875.3	921.6	968.5	1005.0	1012.4	998.7	956.3	911.8	855.6
27.5°	749.2	798.7	853.9	905.4	955.4	978.0	962.2	912.8	836.6	770.4	690.1
30°	726.8	782.4	836.7	894.2	940.4	950.2	914.0	841.2	752.4	652.5	572.4
32.5°	701.2	759.5	819.1	878.6	917.4	907.8	848.0	758.4	654.2	556.0	480.3
35°	664.6	725.0	789.1	848.8	873.5	832.4	742.9	626.3	519.8	428.1	376.0
37.5°	622.5	688.1	754.9	809.7	808.0	739.4	617.5	497.1	407.6	353.4	316.3
40°	592.5	658.8	731.0	777.3	757.5	668.3	536.1	422.6	357.1	313.9	286.8
42.5°	563.8	630.4	702.1	738.8	704.4	594.8	463.1	374.1	320.1	286.4	264.4
45°	514.9	585.1	651.6	672.0	610.4	489.6	374.5	310.0	274.0	249.1	233.8
47.5°	467.1	536.2	596.8	597.2	514.0	397.1	315.9	268.2	237.6	218.3	207.2
50°	437.8	503.6	554.4	546.5	452.2	353.2	282.5	241.4	215.9	201.0	189.4
52.5°	405.0	468.7	512.7	490.2	399.7	310.8	252.6	218.1	196.9	183.9	173.6
55°	357.1	413.8	444.8	410.7	326.1	258.4	213.4	186.3	170.5	159.6	150.7
57.5°	310.2	356.9	376.4	336.7	268.6	214.3	180.5	160.2	144.5	136.6	132.1
60°	280.7	320.6	334.3	290.5	233.5	187.5	159.9	141.0	129.4	124.3	119.7
62.5°	251.8	284.3	290.0	249.8	203.6	164.2	140.4	124.4	116.8	111.8	107.5
65°	208.9	232.3	229.6	197.3	161.0	130.3	112.9	103.2	97.4	90.4	82.8
67.5°	171.9	186.3	177.7	153.4	122.9	101.3	89.9	82.6	75.4	68.7	67.0
70°	148.5	156.8	147.7	125.5	100.8	85.0	75.8	67.0	62.7	61.2	58.5
72.5°	126.2	129.1	119.2	100.1	82.0	70.4	61.5	56.5	54.2	52.9	51.1
75°	94.7	92.5	84.1	69.1	56.9	49.0	46.3	44.4	43.0	41.7	40.8
77.5°	66.5	63.3	55.8	46.1	39.6	35.9	34.2	33.3	32.5	31.9	31.0
80°	49.9	47.8	40.2	32.9	30.2	28.3	27.4	26.2	26.2	25.6	24.6
82.5°	36.5	34.2	27.6	24.1	22.6	21.5	20.8	20.1	19.8	20.0	19.3
85°	19.2	15.5	13.7	13.1	12.1	11.6	11.9	11.3	11.3	11.3	10.9
87.5°	6.4	5.6	5.6	5.7	6.3	6.9	7.6	8.3	8.7	8.3	8.5
90°	2.5	5.1	6.4	7.7	9.5	12.7	17.2	21.0	21.7	21.0	20.4
92.5°	11.3	15.8	18.6	22.9	28.9	43.4	63.6	81.7	82.8	70.0	55.6
95°	24.9	31.2	36.9	47.1	62.5	91.8	147.2	221.2	249.8	218.6	167.0
97.5°	39.8	46.6	55.2	66.9	84.2	121.1	198.4	321.2	426.5	447.4	389.6
100°	51.0	56.7	66.9	79.7	97.5	131.3	209.0	346.7	503.4	595.3	581.9
102.5°	62.2	67.9	78.1	91.4	109.3	140.5	209.5	337.0	506.1	650.3	707.8
105°	80.3	84.8	94.3	108.4	126.2	156.1	212.9	318.0	472.2	641.8	774.4
107.5°	98.2	102.5	111.3	125.1	143.2	172.2	221.7	308.6	436.0	585.8	726.4
110°	110.9	114.7	123.0	136.4	154.9	182.9	228.8	306.6	418.7	550.7	685.1



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	122.1	126.5	134.2	147.1	166.1	193.1	236.4	307.0	407.5	526.2	647.4
115°	140.2	144.1	151.6	164.4	181.6	209.0	247.9	309.7	395.2	495.9	601.0
117.5°	157.7	161.5	168.3	180.5	198.4	223.7	260.2	314.3	389.1	476.7	566.1
120°	168.9	172.7	178.5	191.2	209.0	233.9	268.3	317.4	385.6	466.5	548.7
122.5°	179.1	182.9	189.1	201.9	220.3	243.6	275.5	321.0	383.5	457.9	535.0
125°	193.1	196.9	204.6	217.4	235.1	258.1	286.8	326.3	379.8	445.5	514.9
127.5°	205.0	210.3	218.7	231.0	249.3	271.7	297.3	331.8	377.6	434.0	495.2
130°	211.6	217.9	226.9	239.6	257.5	279.8	304.0	335.9	376.7	426.4	482.4
132.5°	218.3	225.1	234.6	247.8	265.6	286.9	310.6	340.0	376.2	420.3	470.2
135°	226.9	234.6	244.1	258.8	276.6	297.0	319.3	344.8	375.4	411.7	453.1
137.5°	236.0	243.7	253.9	268.5	285.0	305.2	326.0	349.1	375.3	405.7	439.5
140°	242.1	249.8	260.0	274.0	290.7	309.7	329.5	351.1	374.7	402.2	430.8
142.5°	248.3	255.4	265.6	279.2	294.7	313.3	332.6	352.7	374.7	398.6	423.7
145°	258.8	265.1	274.7	287.4	301.4	318.7	336.5	354.3	373.5	393.9	413.6
147.5°	268.8	274.9	283.7	294.3	306.8	323.0	338.7	354.9	371.2	389.1	405.9
150°	276.0	281.0	289.3	298.9	310.4	325.1	339.7	354.3	369.7	384.9	400.2
152.5°	282.1	287.1	294.4	303.5	314.0	327.1	340.2	353.4	367.1	381.4	394.6
155°	291.9	295.7	302.7	309.7	319.3	330.1	341.0	351.8	362.6	374.7	386.9
157.5°	300.3	303.4	309.5	315.1	323.1	332.3	341.0	348.9	358.1	368.5	377.8
160°	305.9	308.4	313.6	318.7	325.6	333.3	341.0	347.3	355.0	363.9	372.2
162.5°	310.5	313.1	317.2	321.7	327.2	333.9	340.5	345.8	352.5	359.8	366.6
165°	316.7	318.0	321.9	325.1	328.9	334.6	339.1	342.9	347.3	353.1	358.2
167.5°	322.0	323.1	325.5	327.8	330.3	334.4	338.2	340.0	342.9	346.4	350.2
170°	325.1	325.6	327.6	328.9	330.8	333.9	337.1	338.4	340.3	342.9	346.1
172.5°	327.6	327.2	329.1	329.9	331.3	333.5	335.6	336.4	337.3	339.3	341.4
175°	330.1	329.5	330.8	330.8	331.4	332.6	333.9	333.3	333.9	334.6	336.5
177.5°	330.9	330.4	331.4	331.4	331.4	331.9	333.0	331.9	331.4	331.9	333.0
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	906.9	910.1	911.6	911.6	913.3	912.6	911.8
5°	959.0	964.8	966.0	971.5	975.5	974.3	974.9
7.5°	1010.9	1020.2	1029.4	1033.6	1034.3	1036.7	1037.6
10°	1042.8	1050.4	1064.7	1062.6	1073.3	1079.3	1069.3
12.5°	1073.5	1083.8	1093.7	1096.4	1102.4	1104.4	1100.4
15°	1101.2	1106.7	1107.3	1105.8	1107.7	1106.1	1100.3
17.5°	1075.3	1066.4	1048.4	1039.8	1033.1	1023.1	1019.1
20°	1032.4	1006.2	975.8	963.6	949.3	921.3	928.0
22.5°	939.9	910.0	879.6	844.0	827.0	800.5	798.9
25°	795.9	744.4	687.8	648.2	625.1	598.6	587.0
27.5°	618.8	554.0	507.6	484.1	462.7	441.7	440.8
30°	502.4	453.6	417.8	397.6	384.6	375.7	377.6
32.5°	423.5	390.0	365.8	349.2	339.5	332.8	332.7
35°	346.2	323.3	307.8	300.8	293.8	288.9	289.3
37.5°	296.3	282.5	273.9	266.2	261.8	259.4	258.0
40°	270.7	259.4	252.7	248.2	244.5	241.2	240.5
42.5°	250.5	241.2	234.4	230.8	227.5	225.0	224.5
45°	222.3	214.7	208.6	204.6	203.1	201.0	201.0
47.5°	197.7	190.2	185.5	183.0	180.3	179.0	178.9
50°	181.2	175.4	171.1	169.6	167.5	166.6	166.2
52.5°	166.3	162.0	158.9	157.9	156.9	155.8	156.0
55°	146.1	143.7	142.5	141.5	140.1	138.2	139.4
57.5°	129.1	127.1	123.8	120.9	119.5	118.2	118.7
60°	117.2	112.9	108.7	105.3	104.4	101.7	101.7
62.5°	102.2	96.1	90.9	89.0	88.1	86.8	86.6
65°	78.5	76.1	74.9	73.7	73.1	73.1	72.5
67.5°	65.1	64.1	62.8	62.5	61.9	61.7	61.5
70°	57.6	56.3	55.7	55.4	54.8	55.1	54.2
72.5°	50.2	49.2	49.2	48.3	48.0	48.0	47.4
75°	39.5	39.5	39.3	39.0	38.4	38.1	38.4
77.5°	30.4	30.5	29.9	29.9	29.8	29.9	29.6
80°	24.4	24.6	24.4	24.1	23.7	24.1	23.7
82.5°	19.2	18.8	18.8	18.7	18.7	18.4	18.4
85°	10.9	11.3	10.9	10.7	10.7	10.7	10.9
87.5°	8.0	8.2	8.3	8.3	8.3	8.3	8.1
90°	19.2	20.4	21.0	21.0	21.0	21.0	21.0
92.5°	47.7	42.3	38.4	37.8	35.8	36.4	35.3
95°	128.1	101.3	87.3	79.0	73.9	72.0	72.6
97.5°	318.8	249.8	203.8	173.3	157.7	148.4	143.0
100°	502.9	415.6	338.4	285.5	258.1	239.6	228.1
102.5°	690.0	626.1	544.4	486.9	440.1	417.0	401.5
105°	846.4	854.7	833.6	794.1	754.6	727.2	718.3
107.5°	834.9	901.2	932.1	937.0	934.8	929.4	917.5
110°	799.2	880.8	933.0	960.4	972.6	978.3	977.6



TEST NUMBER: P331659-930

CATALOG NUMBER: S122RDIP-S485D725U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	756.8	844.1	904.0	942.1	962.4	973.2	976.6
115°	699.1	782.6	848.2	893.5	922.8	939.4	945.2
117.5°	652.2	728.0	789.5	835.7	866.7	884.1	888.9
120°	627.8	695.3	753.3	797.9	827.9	846.4	852.7
122.5°	607.4	671.3	723.7	763.8	793.2	809.7	815.0
125°	580.6	636.7	684.4	721.5	745.7	761.6	766.7
127.5°	554.6	607.5	651.6	683.9	706.5	720.3	724.4
130°	537.3	587.6	629.7	660.9	682.6	695.3	700.4
132.5°	521.0	567.2	606.7	637.5	659.1	670.8	675.4
135°	495.2	537.3	572.9	600.4	621.4	632.8	635.4
137.5°	474.7	508.1	539.2	564.2	582.3	592.3	596.1
140°	461.5	490.7	518.8	539.2	555.7	565.3	569.2
142.5°	449.7	474.9	498.4	517.8	532.8	541.4	542.1
145°	434.6	454.4	472.9	488.2	499.0	505.4	507.3
147.5°	422.4	437.8	451.3	464.0	472.6	477.0	478.1
150°	414.3	427.6	439.1	448.7	456.3	460.2	460.8
152.5°	407.6	419.0	428.9	436.4	443.0	445.9	446.0
155°	397.1	406.6	413.6	420.6	425.1	427.6	426.4
157.5°	386.4	394.4	399.8	404.8	408.5	409.7	409.7
160°	379.2	386.2	390.7	395.2	398.4	398.9	398.9
162.5°	372.6	378.5	382.0	386.5	388.7	389.3	388.7
165°	362.6	367.1	369.7	372.2	374.7	374.7	374.1
167.5°	353.6	356.6	359.0	360.1	361.5	361.3	360.6
170°	348.0	350.5	351.8	352.5	354.3	353.7	352.5
172.5°	342.9	345.0	345.7	346.3	347.2	346.6	345.8
175°	337.1	337.8	338.4	338.4	339.1	338.4	337.1
177.5°	333.0	333.5	333.5	333.5	333.5	333.0	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4

(END OF REPORT)