

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331686-930

Luminaire Tested: **S122RDIP-S675D530U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331686-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S675D530U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3576.2 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331686-930

CATALOG NUMBER: S122RDIP-S675D530U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331686-930

CATALOG NUMBER: S122RDIP-S675D530U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53				
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51	46				
2	91	83	77	72	84	78	72	68	67	63	59	56	54	51	47	45	43	39				
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38	34				
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29				
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	34	31	29	26				
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	31	28	26	23				
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21				
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	27	23	21	19				
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19	17				
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14849	14849	14849
5°	14906	14663	14744
10°	14791	14423	14300
15°	14621	13996	13593
20°	14387	13385	12713
25°	14145	12691	11863
30°	13811	11979	10769
35°	13484	11203	9810
40°	13156	10404	8701
45°	12771	9501	7695
50°	12376	8593	6712
55°	11972	7614	5762
60°	11502	6584	4782
65°	10968	5532	4359
70°	10334	4556	4008
75°	9551	4155	3737
80°	8433	3710	3403
85°	6632	2927	2927



TEST NUMBER: P331686-930

CATALOG NUMBER: S122RDIP-S675D530U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.1	2.4
10°-20°	236.4	6.6
20°-30°	331.9	9.3
30°-40°	361.9	10.1
40°-50°	332.8	9.3
50°-60°	261.4	7.3
60°-70°	170.4	4.8
70°-80°	87.9	2.5
80°-90°	25.0	0.7
90°-100°	96.7	2.7
100°-110°	328.1	9.2
110°-120°	348.5	9.7
120°-130°	286.9	8.0
130°-140°	230.4	6.4
140°-150°	174.1	4.9
150°-160°	122.4	3.4
160°-170°	72.0	2.0
170°-180°	23.4	0.7
0°-30°	654.4	18.3
0°-40°	1016.3	28.4
0°-60°	1610.5	45.0
0°-90°	1893.7	53.0
90°-120°	773.2	21.6
90°-150°	1464.6	41.0
90°-180°	1682.0	47.0
0°-180°	3576.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	920	915	905	912	910	87
15°	875	864	837	822	813	246
25°	794	766	712	680	666	365
35°	684	640	568	518	498	428
45°	559	502	416	359	337	432
55°	425	359	270	222	205	380
65°	287	219	145	118	114	285
75°	153	96	67	61	60	162
85°	36	19	16	16	16	42
90°	0	6	16	15	15	2
95°	16	40	182	69	53	17
105°	57	86	344	616	524	60
115°	100	126	288	595	690	99
125°	140	165	277	482	559	124
135°	164	195	274	405	464	126
145°	187	215	272	338	370	117
155°	212	229	265	299	311	98
165°	232	238	253	269	273	65
175°	241	242	244	247	246	23
180°	242	242	242	242	242	



TEST NUMBER: P331686-930

CATALOG NUMBER: S122RDIP-S675D530U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	923.0	922.3	921.5	920.8	920.1	918.8	917.2	915.6	914.0	912.4	913.9
5°	919.7	918.8	917.9	916.9	916.0	914.4	911.9	909.5	907.1	904.7	906.4
7.5°	910.2	909.1	907.9	906.8	905.6	903.6	900.8	898.1	895.2	892.4	892.8
10°	902.2	900.9	899.6	898.3	897.0	894.5	890.8	887.1	883.5	879.7	879.2
12.5°	892.2	890.6	889.0	887.5	885.8	882.7	878.0	873.3	868.5	863.7	862.7
15°	874.7	872.7	870.7	868.6	866.6	862.4	856.1	849.9	843.6	837.3	833.8
17.5°	853.3	850.2	847.1	843.9	840.8	835.3	827.2	819.1	811.1	803.0	798.8
20°	837.3	833.6	829.9	826.2	822.5	816.0	806.7	797.5	788.3	779.0	774.4
22.5°	819.9	815.9	811.7	807.6	803.4	796.1	785.7	775.3	764.8	754.4	748.4
25°	794.0	788.1	782.2	776.2	770.4	761.2	749.1	736.9	724.6	712.4	704.8
27.5°	762.7	756.3	749.8	743.4	736.9	726.8	713.1	699.4	685.6	671.8	663.0
30°	740.8	733.7	726.7	719.7	712.7	701.7	686.9	672.1	657.3	642.5	633.1
32.5°	719.4	711.2	703.0	694.8	686.6	674.9	659.8	644.7	629.7	614.6	603.8
35°	684.1	674.7	665.3	655.8	646.5	633.6	617.3	601.0	584.7	568.4	556.8
37.5°	648.9	638.5	628.1	617.8	607.4	593.5	576.3	558.9	541.5	524.2	511.4
40°	624.2	613.1	602.0	590.9	579.8	565.3	547.4	529.5	511.5	493.6	480.5
42.5°	598.9	587.3	575.5	563.9	552.2	537.0	518.5	500.0	481.4	462.9	449.3
45°	559.3	546.9	534.5	522.1	509.7	493.8	474.4	455.0	435.5	416.1	403.0
47.5°	520.7	507.5	494.4	481.3	468.1	451.6	431.5	411.5	391.4	371.4	358.3
50°	492.7	479.6	466.4	453.3	440.2	423.5	403.1	382.8	362.4	342.1	329.3
52.5°	465.5	451.7	438.0	424.3	410.5	393.7	373.8	353.9	334.0	314.1	301.8
55°	425.3	410.9	396.5	382.0	367.6	350.4	330.4	310.5	290.5	270.5	259.4
57.5°	384.2	369.4	354.6	339.8	325.0	308.0	288.8	269.6	250.4	231.2	221.0
60°	356.2	341.4	326.6	311.9	297.0	280.1	261.1	242.0	223.0	203.9	194.4
62.5°	328.9	314.1	299.3	284.5	269.7	253.2	235.1	217.0	198.8	180.6	171.6
65°	287.1	272.1	257.1	242.2	227.2	211.4	194.8	178.1	161.4	144.8	138.5
67.5°	246.9	232.0	217.1	202.3	187.4	172.4	157.4	142.5	127.5	112.5	109.7
70°	218.9	204.5	190.0	175.6	161.2	147.6	134.9	122.1	109.3	96.5	94.7
72.5°	192.2	178.4	164.6	150.7	136.9	124.9	114.6	104.4	94.2	83.9	82.3
75°	153.1	140.2	127.3	114.3	101.3	91.7	85.4	79.2	72.9	66.6	65.3
77.5°	114.7	103.3	92.0	80.6	69.3	62.0	59.0	56.0	53.0	50.0	49.2
80°	90.7	81.3	71.8	62.5	53.0	47.4	45.5	43.6	41.8	39.9	39.2
82.5°	68.7	61.4	54.1	46.6	39.3	35.0	33.8	32.4	31.2	30.0	29.5
85°	35.8	31.9	28.0	24.1	20.2	18.0	17.4	17.0	16.4	15.8	15.8
87.5°	10.8	9.9	9.0	8.1	7.0	6.7	7.2	7.8	8.4	8.5	8.2
90°	0.5	1.9	3.8	4.6	5.5	7.0	9.3	12.6	15.3	15.8	15.3
92.5°	5.7	8.2	11.5	13.6	16.7	21.1	31.6	46.4	59.6	60.4	51.0
95°	16.3	18.1	22.7	27.0	34.4	45.6	66.9	107.4	161.3	182.3	159.5
97.5°	26.5	29.0	33.9	40.3	48.8	61.5	88.4	144.7	234.3	311.1	326.4
100°	35.8	37.2	41.4	48.8	58.1	71.2	95.8	152.5	252.9	367.3	434.2
102.5°	44.4	45.4	49.6	57.0	66.7	79.7	102.5	152.9	245.9	369.2	474.4
105°	56.7	58.6	61.8	68.8	79.0	92.0	113.9	155.3	232.0	344.5	468.2
107.5°	70.1	71.6	74.8	81.2	91.3	104.4	125.6	161.7	225.1	318.1	427.4
110°	79.0	80.9	83.7	89.8	99.5	113.0	133.5	166.9	223.6	305.5	401.7



TEST NUMBER: P331686-930

CATALOG NUMBER: S122RDIP-S675D530U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	87.2	89.1	92.2	97.9	107.3	121.2	140.9	172.5	224.0	297.3	383.8
115°	100.0	102.3	105.1	110.6	119.9	132.5	152.5	180.8	226.0	288.3	361.7
117.5°	113.2	115.0	117.8	122.8	131.7	144.7	163.2	189.8	229.3	283.9	347.8
120°	121.3	123.2	126.0	130.2	139.5	152.5	170.6	195.8	231.5	281.3	340.4
122.5°	129.1	130.7	133.5	138.0	147.3	160.7	177.7	201.0	234.2	279.8	334.0
125°	139.5	140.9	143.7	149.3	158.6	171.5	188.3	209.2	238.1	277.1	325.0
127.5°	147.7	149.5	153.4	159.6	168.5	181.9	198.2	217.0	242.1	275.6	316.7
130°	152.5	154.3	159.0	165.5	174.8	187.8	204.2	221.8	245.0	274.8	311.0
132.5°	156.9	159.2	164.2	171.1	180.8	193.8	209.3	226.7	248.0	274.4	306.6
135°	163.6	165.5	171.1	178.1	188.7	201.8	216.7	232.9	251.5	273.9	300.4
137.5°	170.0	172.2	177.8	185.2	195.8	207.9	222.7	237.7	254.7	273.8	296.0
140°	174.8	176.7	182.3	189.7	199.9	212.1	226.0	240.4	256.2	273.4	293.4
142.5°	179.7	181.2	186.4	193.8	203.7	215.0	228.6	242.6	257.3	273.4	290.8
145°	186.9	188.7	193.4	200.4	209.7	219.9	232.4	245.5	258.5	272.5	287.3
147.5°	194.7	196.1	200.6	207.0	214.7	223.8	235.6	247.1	258.9	270.8	283.8
150°	199.9	201.3	205.0	211.1	218.1	226.4	237.1	247.9	258.5	269.7	280.9
152.5°	205.1	205.8	209.5	214.8	221.4	229.0	238.6	248.2	257.8	267.8	278.3
155°	212.5	213.0	215.7	220.9	226.0	232.9	240.8	248.7	256.7	264.6	273.4
157.5°	218.6	219.1	221.4	225.8	229.9	235.7	242.4	248.7	254.5	261.2	268.8
160°	222.7	223.1	225.0	228.8	232.4	237.6	243.2	248.7	253.4	259.0	265.5
162.5°	226.8	226.5	228.4	231.4	234.7	238.7	243.5	248.3	252.3	257.1	262.5
165°	231.5	231.1	232.0	234.8	237.1	239.9	244.1	247.4	250.1	253.4	257.6
167.5°	235.5	234.9	235.7	237.5	239.2	240.9	244.0	246.7	248.0	250.1	252.7
170°	238.1	237.1	237.6	239.0	239.9	241.3	243.6	246.0	246.9	248.3	250.1
172.5°	239.5	239.0	238.7	240.1	240.7	241.7	243.3	244.8	245.4	246.1	247.5
175°	241.3	240.8	240.4	241.3	241.3	241.7	242.7	243.6	243.2	243.6	244.1
177.5°	242.1	241.4	241.0	241.7	241.7	241.7	242.1	242.9	242.1	241.7	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331686-930

CATALOG NUMBER: S122RDIP-S675D530U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	915.3	916.8	918.3	918.8	918.6	918.3	918.0	917.7
5°	908.0	909.7	911.3	911.9	911.3	910.8	910.3	909.7
7.5°	893.3	893.8	894.3	894.1	893.1	892.2	891.2	890.2
10°	878.6	878.1	877.5	876.7	875.5	874.5	873.3	872.2
12.5°	861.8	860.8	859.7	858.3	856.5	854.7	852.8	850.9
15°	830.3	826.7	823.2	820.5	818.7	816.8	815.0	813.2
17.5°	794.7	790.4	786.3	782.6	779.4	776.2	773.1	769.9
20°	769.8	765.2	760.5	756.2	752.1	748.0	744.0	739.9
22.5°	742.5	736.5	730.6	726.1	723.0	720.0	717.0	714.0
25°	697.2	689.7	682.1	676.9	674.2	671.4	668.6	665.9
27.5°	654.1	645.3	636.5	629.8	625.4	621.0	616.6	612.2
30°	623.7	614.2	604.8	597.6	592.6	587.6	582.6	577.6
32.5°	593.0	582.3	571.5	563.8	559.1	554.4	549.7	545.0
35°	545.2	533.5	521.9	514.0	509.9	505.8	501.8	497.7
37.5°	498.5	485.7	472.9	464.1	459.4	454.8	450.1	445.5
40°	467.2	454.1	441.0	432.0	427.2	422.4	417.6	412.8
42.5°	435.8	422.2	408.6	399.5	394.8	390.2	385.6	380.8
45°	389.9	376.7	363.6	354.8	350.4	345.9	341.5	337.0
47.5°	345.3	332.2	319.1	310.6	306.6	302.6	298.5	294.5
50°	316.6	303.8	291.1	282.7	278.8	274.9	271.1	267.2
52.5°	289.5	277.1	264.8	256.9	253.3	249.7	246.1	242.6
55°	248.3	237.2	226.1	218.8	215.3	211.7	208.2	204.7
57.5°	210.8	200.7	190.5	183.9	181.0	178.1	175.0	172.1
60°	185.1	175.6	166.2	160.0	157.0	154.1	151.1	148.1
62.5°	162.7	153.6	144.6	139.3	137.5	135.7	134.0	132.2
65°	132.2	126.0	119.7	116.3	115.7	115.1	114.5	114.1
67.5°	106.7	103.9	101.0	99.2	98.7	98.1	97.5	96.9
70°	92.9	91.0	89.1	87.9	87.1	86.3	85.6	84.9
72.5°	80.8	79.2	77.7	76.7	76.2	75.8	75.3	74.9
75°	64.0	62.7	61.4	60.7	60.5	60.3	60.1	59.9
77.5°	48.4	47.7	47.0	46.5	46.1	45.9	45.6	45.2
80°	38.5	37.7	37.0	36.6	36.6	36.6	36.6	36.6
82.5°	29.1	28.6	28.2	28.0	28.0	28.0	28.0	28.0
85°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
87.5°	8.0	7.7	7.7	7.7	7.7	7.7	7.7	7.7
90°	14.8	13.9	14.8	15.3	15.3	15.3	15.3	15.3
92.5°	40.5	34.8	30.9	28.0	27.6	26.2	26.5	25.8
95°	121.8	93.4	73.9	63.7	57.6	54.0	52.5	53.0
97.5°	284.3	232.6	182.3	148.7	126.5	115.0	108.3	104.4
100°	424.5	366.9	303.1	246.9	208.3	188.3	174.8	166.5
102.5°	516.4	503.4	456.8	397.1	355.2	321.1	304.3	292.9
105°	564.9	617.4	623.5	608.1	579.4	550.5	530.5	524.0
107.5°	529.9	609.1	657.5	680.0	683.5	682.0	678.0	669.4
110°	499.9	583.0	642.5	680.7	700.7	709.6	713.7	713.2



TEST NUMBER: P331686-930

CATALOG NUMBER: S122RDIP-S675D530U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	472.3	552.2	615.8	659.5	687.3	702.1	710.0	712.5
115°	438.5	510.1	571.0	618.9	651.8	673.3	685.3	689.5
117.5°	412.9	475.8	531.1	576.0	609.7	632.3	645.0	648.5
120°	400.3	458.0	507.3	549.6	582.1	604.0	617.4	622.1
122.5°	390.3	443.1	489.8	528.0	557.2	578.7	590.7	594.6
125°	375.7	423.5	464.5	499.4	526.4	544.0	555.6	559.4
127.5°	361.3	404.6	443.2	475.4	498.9	515.4	525.5	528.5
130°	352.0	392.0	428.7	459.3	482.2	498.0	507.3	510.9
132.5°	343.1	380.1	413.8	442.6	465.0	480.9	489.4	492.8
135°	330.6	361.3	392.0	418.0	438.0	453.3	461.7	463.6
137.5°	320.7	346.3	370.6	393.4	411.6	424.8	432.1	434.9
140°	314.3	336.6	358.0	378.5	393.4	405.4	412.4	415.2
142.5°	309.1	328.1	346.5	363.6	377.7	388.7	394.9	395.5
145°	301.7	317.1	331.5	345.0	356.1	364.0	368.7	370.1
147.5°	296.1	308.2	319.4	329.3	338.5	344.8	348.0	348.8
150°	292.0	302.2	312.0	320.3	327.3	332.9	335.7	336.1
152.5°	287.9	297.4	305.7	312.9	318.4	323.3	325.3	325.4
155°	282.3	289.7	296.6	301.7	306.9	310.1	312.0	311.0
157.5°	275.7	281.8	287.7	291.7	295.3	298.1	298.9	298.9
160°	271.5	276.6	281.8	285.0	288.3	290.6	291.1	291.1
162.5°	267.4	271.8	276.2	278.7	281.9	283.6	284.0	283.6
165°	261.3	264.6	267.8	269.7	271.5	273.4	273.4	273.0
167.5°	255.4	258.0	260.2	261.9	262.7	263.7	263.7	263.1
170°	252.5	253.9	255.8	256.7	257.1	258.5	258.0	257.1
172.5°	249.2	250.1	251.6	252.2	252.7	253.3	252.8	252.3
175°	245.5	246.0	246.5	246.9	246.9	247.4	246.9	246.0
177.5°	242.9	242.9	243.3	243.3	243.3	243.3	242.9	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7

(END OF REPORT)