

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331711-930

Luminaire Tested: **S122RDIP-S865D530U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331711-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D530U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4415.3 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	94	90	95	91	88	85	80	78	75	70	68	66	60	59	58	53
2	93	86	80	75	87	81	76	72	71	67	64	62	59	57	54	52	50	46
3	86	77	70	64	80	72	66	61	64	59	55	56	52	49	49	46	44	40
4	79	69	61	55	74	65	58	53	57	52	48	51	47	43	44	41	39	36
5	73	62	54	48	68	58	51	46	52	47	42	46	42	38	41	37	35	32
6	68	56	48	43	63	53	46	41	47	42	38	42	38	34	37	34	31	28
7	63	51	43	38	59	48	41	37	43	38	34	39	34	31	34	31	28	26
8	59	47	39	34	55	44	38	33	40	34	30	36	31	28	32	28	26	23
9	55	43	36	31	52	41	34	30	37	31	28	33	29	26	30	26	23	21
10	51	40	33	28	48	38	31	27	34	29	25	31	27	23	28	24	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25137	25137	25137	25137
5°	28075	25293	22428	25293
10°	31147	25117	19441	25117
15°	32679	24749	15318	24749
20°	28331	24204	13254	24204
25°	18579	23457	11834	23457
30°	12506	22551	10711	22551
35°	10129	21409	9660	21409
40°	9008	20168	8939	20168
45°	8152	18712	7978	18712
50°	7420	17269	7390	17269
55°	6975	15671	6883	15671
60°	5835	14202	5767	14202
65°	4917	12894	5578	12894
70°	4546	11514	5264	11514
75°	4255	10025	4860	10025
80°	3924	8247	4333	8247
85°	3612	6502	3798	6502



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.6	3.3
10°-20°	411.2	9.3
20°-30°	529.9	12.0
30°-40°	503.6	11.4
40°-50°	431.4	9.8
50°-60°	328.5	7.4
60°-70°	207.7	4.7
70°-80°	103.7	2.3
80°-90°	28.4	0.6
90°-100°	19.6	0.4
100°-110°	71.9	1.6
110°-120°	192.3	4.4
120°-130°	317.4	7.2
130°-140°	337.5	7.6
140°-150°	313.7	7.1
150°-160°	252.2	5.7
160°-170°	162.5	3.7
170°-180°	55.9	1.3
0°-30°	1088.7	24.7
0°-40°	1592.3	36.1
0°-60°	2352.3	53.3
0°-90°	2692.1	61.0
90°-120°	283.8	6.4
90°-150°	1252.5	28.4
90°-180°	1723.0	39.0
0°-180°	4415.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1557	1557	1557	1557	1557	
5°	1732	1561	1384	1561	1732	171
15°	1955	1481	916	1481	1955	527
25°	1043	1317	664	1317	1043	495
35°	514	1086	490	1086	514	329
45°	357	820	349	820	357	276
55°	248	557	244	557	248	217
65°	129	338	146	338	129	131
75°	68	161	78	161	68	72
85°	20	35	20	35	20	21
90°	12	0	12	0	12	6
95°	18	28	18	28	18	17
105°	32	129	32	129	32	34
115°	35	245	35	245	35	87
125°	364	346	364	346	364	315
135°	442	428	442	428	442	341
145°	504	496	504	496	504	315
155°	547	547	547	547	547	252
165°	575	576	575	576	575	162
175°	586	589	586	589	586	56
180°	588	588	588	588	588	



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1620.1	1621.4	1622.7	1619.6	1619.6	1617.1	1611.4	1607.1	1595.0	1593.3	1593.3
5°	1732.2	1731.0	1733.2	1726.2	1716.4	1714.3	1704.1	1690.5	1676.4	1660.8	1657.5
7.5°	1843.6	1841.9	1837.6	1836.5	1829.0	1812.7	1796.1	1778.5	1755.1	1732.3	1720.8
10°	1899.8	1917.7	1906.9	1887.9	1891.7	1866.3	1852.8	1829.5	1810.0	1776.0	1768.4
12.5°	1955.3	1962.3	1958.8	1948.1	1943.3	1925.6	1907.3	1887.1	1851.1	1820.6	1793.9
15°	1955.0	1965.3	1968.0	1964.8	1967.5	1966.4	1956.6	1939.8	1908.5	1874.9	1845.8
17.5°	1810.7	1817.9	1835.6	1847.5	1862.7	1894.8	1910.6	1916.7	1912.0	1892.9	1872.3
20°	1648.9	1637.0	1686.7	1712.1	1733.7	1787.9	1834.4	1852.3	1880.9	1880.4	1874.9
22.5°	1419.4	1422.3	1469.5	1499.7	1562.8	1616.9	1670.0	1737.2	1792.6	1829.3	1850.7
25°	1042.9	1063.6	1110.6	1151.7	1222.1	1322.7	1414.1	1520.1	1620.2	1699.2	1774.3
27.5°	783.3	784.8	822.1	860.1	901.9	984.3	1099.4	1226.0	1368.7	1486.5	1621.9
30°	670.8	667.6	683.2	706.5	742.2	806.0	892.6	1017.0	1159.3	1336.7	1494.7
32.5°	591.2	591.3	603.2	620.4	650.0	693.1	752.4	853.5	987.9	1162.3	1347.5
35°	513.9	513.4	522.0	534.4	546.9	574.5	615.1	668.1	760.6	923.4	1112.7
37.5°	458.5	460.9	465.1	472.9	486.7	502.0	526.4	562.0	627.9	724.1	883.3
40°	427.4	428.4	434.4	440.9	449.0	460.9	480.9	509.6	557.7	634.5	750.8
42.5°	398.8	399.9	404.1	410.2	416.5	428.4	445.0	469.8	508.8	568.8	664.7
45°	357.0	357.0	360.9	363.5	370.6	381.4	394.9	415.5	442.5	486.9	550.7
47.5°	317.9	318.0	320.5	325.1	329.5	338.0	351.3	368.1	387.8	422.1	476.6
50°	295.4	295.9	297.5	301.3	304.0	311.6	321.9	336.5	357.0	383.5	429.0
52.5°	277.2	276.9	278.9	280.5	282.4	287.8	295.5	308.3	326.8	349.8	387.4
55°	247.8	245.6	248.8	251.5	253.2	255.4	259.7	267.7	283.5	303.0	331.1
57.5°	211.0	210.1	212.4	214.8	220.0	225.8	229.5	234.6	242.8	256.7	284.6
60°	180.7	180.7	185.6	187.2	193.1	200.7	208.3	212.6	220.7	229.9	250.5
62.5°	153.8	154.3	156.5	158.2	161.5	170.8	181.4	190.9	198.6	207.4	221.0
65°	128.7	129.8	129.8	130.9	133.1	135.3	139.6	147.2	160.7	173.1	183.4
67.5°	109.3	109.6	109.9	111.0	111.5	113.9	115.7	119.0	122.1	134.0	146.7
70°	96.3	97.9	97.3	98.5	99.0	100.0	102.2	103.9	108.8	111.5	119.0
72.5°	84.1	85.4	85.3	85.9	87.3	87.6	89.3	90.9	94.0	96.3	100.4
75°	68.2	67.6	68.2	69.2	69.8	70.4	70.4	72.5	74.1	76.3	79.0
77.5°	52.6	53.2	53.0	53.2	53.2	54.2	54.1	55.0	56.7	57.8	59.1
80°	42.2	42.7	42.2	42.7	43.3	43.8	43.3	43.8	45.4	46.6	46.6
82.5°	32.7	32.8	33.1	33.2	33.3	33.4	34.2	34.3	35.5	35.3	35.7
85°	19.5	18.9	18.9	18.9	19.5	20.0	19.5	19.5	20.0	20.0	20.0
87.5°	9.2	9.6	9.5	9.5	9.5	9.5	9.4	9.7	9.1	9.5	8.9
90°	11.5	11.3	11.1	10.9	10.8	10.4	9.9	9.5	9.0	8.5	7.7
92.5°	11.5	11.4	11.3	11.2	11.0	10.8	10.6	10.4	10.1	9.9	9.5
95°	18.3	18.4	18.5	18.6	18.7	18.5	18.0	17.5	17.0	16.6	15.9
97.5°	24.5	24.3	24.2	24.1	24.0	23.7	23.3	23.0	22.6	22.2	20.7
100°	28.5	28.3	28.1	28.0	27.7	27.3	26.5	25.8	25.0	24.2	22.7
102.5°	30.6	30.2	30.0	29.8	29.5	28.9	27.9	26.9	25.9	24.9	38.4
105°	32.4	32.0	31.6	31.2	30.8	30.1	29.1	28.0	27.0	25.9	51.8
107.5°	33.3	32.9	32.5	32.1	31.8	32.1	33.2	34.2	35.3	36.4	67.3
110°	33.6	33.3	32.9	32.4	32.1	36.6	46.1	55.5	65.0	74.4	101.7



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	33.9	33.7	33.3	33.0	32.8	49.8	84.3	118.8	153.3	187.8	194.5
115°	34.9	41.7	48.5	55.3	62.1	87.4	131.2	175.0	218.7	262.5	260.2
117.5°	142.4	164.9	187.2	209.5	232.0	248.4	259.0	269.6	280.2	290.7	289.2
120°	259.5	272.3	285.1	297.8	310.6	316.4	315.3	314.1	313.0	311.9	310.1
122.5°	323.8	326.4	328.8	331.3	333.8	334.7	334.0	333.3	332.6	332.0	330.1
125°	363.8	363.5	363.2	363.0	362.6	362.2	361.5	360.9	360.2	359.5	357.8
127.5°	389.0	388.9	388.9	388.8	388.7	388.2	387.3	386.3	385.3	384.4	383.0
130°	404.6	404.7	404.8	404.9	405.0	404.6	403.5	402.4	401.5	400.4	399.3
132.5°	420.0	420.0	420.1	420.2	420.3	420.0	419.1	418.2	417.3	416.4	415.3
135°	442.1	442.3	442.5	442.6	442.9	442.5	441.5	440.6	439.6	438.6	437.8
137.5°	462.3	462.6	462.8	463.2	463.5	463.3	462.3	461.4	460.5	459.5	458.5
140°	474.8	475.3	475.8	476.2	476.7	476.5	475.6	474.8	474.0	473.1	472.1
142.5°	487.1	487.5	488.0	488.5	489.0	488.9	488.0	487.3	486.5	485.8	484.5
145°	504.2	504.7	505.2	505.6	506.1	506.0	505.3	504.7	504.0	503.4	501.7
147.5°	519.3	519.7	520.1	520.5	520.8	520.8	520.3	519.8	519.3	518.9	517.2
150°	528.5	528.9	529.4	529.9	530.4	530.3	529.7	529.1	528.6	528.0	526.5
152.5°	536.3	536.9	537.5	538.2	538.7	538.8	538.3	537.7	537.1	536.5	535.1
155°	547.1	548.0	548.7	549.4	550.2	550.3	549.8	549.2	548.6	548.0	546.9
157.5°	557.1	557.8	558.6	559.3	560.1	560.1	559.5	558.8	558.2	557.6	556.8
160°	562.9	563.5	564.3	564.9	565.6	565.6	565.0	564.4	563.9	563.4	562.8
162.5°	567.7	568.5	569.3	570.1	571.0	571.0	570.4	569.7	569.1	568.4	567.9
165°	574.8	575.5	576.2	576.8	577.5	577.5	576.8	576.2	575.5	574.8	574.5
167.5°	579.4	580.2	581.1	581.9	582.8	582.9	582.2	581.5	580.8	580.2	579.9
170°	582.0	582.9	583.8	584.6	585.5	585.5	584.9	584.2	583.6	582.9	582.7
172.5°	584.1	585.0	585.8	586.7	587.5	587.6	586.9	586.3	585.6	585.0	584.7
175°	585.9	586.9	587.7	588.7	589.7	589.8	589.1	588.5	587.8	587.2	586.9
177.5°	587.0	587.7	588.3	589.1	589.7	589.8	589.3	588.7	588.2	587.7	587.6
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1594.1	1590.6	1587.6	1579.8	1575.9	1567.2	1565.9	1565.5	1554.3	1543.4	1540.4
5°	1648.9	1640.2	1627.2	1612.1	1596.4	1580.1	1569.3	1560.6	1539.0	1518.5	1506.6
7.5°	1704.1	1685.4	1663.0	1634.3	1610.5	1583.6	1563.7	1545.8	1515.2	1485.7	1465.9
10°	1745.1	1714.8	1685.1	1645.6	1614.8	1584.5	1556.3	1532.0	1497.4	1458.4	1430.9
12.5°	1770.7	1737.3	1696.3	1657.7	1617.8	1579.2	1541.6	1510.3	1469.7	1429.5	1396.6
15°	1805.2	1769.4	1719.7	1664.5	1613.2	1562.8	1519.6	1480.6	1427.6	1379.4	1339.4
17.5°	1833.4	1784.3	1730.9	1667.0	1607.5	1543.6	1487.8	1438.1	1379.1	1321.0	1273.8
20°	1842.5	1793.8	1732.2	1668.3	1598.0	1522.8	1462.7	1408.7	1345.3	1282.1	1228.0
22.5°	1836.9	1799.0	1730.4	1654.0	1582.0	1503.3	1435.5	1372.7	1302.5	1238.0	1175.2
25°	1798.7	1785.7	1720.8	1637.4	1555.3	1463.9	1385.4	1316.7	1236.6	1167.4	1099.2
27.5°	1709.7	1737.6	1697.5	1608.7	1517.3	1419.3	1331.1	1252.9	1169.8	1091.8	1023.9
30°	1624.0	1688.3	1671.0	1588.8	1486.5	1390.2	1291.3	1209.6	1120.9	1040.8	973.7
32.5°	1506.7	1613.0	1629.9	1561.1	1455.4	1349.6	1245.9	1164.6	1072.0	987.6	922.2
35°	1320.0	1479.0	1552.0	1508.2	1402.2	1288.0	1180.9	1086.2	993.2	909.9	845.0
37.5°	1097.1	1313.8	1435.5	1438.6	1341.2	1222.5	1106.0	1011.9	916.7	834.9	764.7
40°	952.6	1187.4	1345.9	1381.0	1298.9	1170.6	1052.7	956.9	863.9	783.8	703.3
42.5°	822.8	1056.7	1251.6	1312.7	1247.3	1120.0	1001.7	901.6	811.1	735.4	653.1
45°	665.4	869.8	1084.6	1193.9	1157.6	1039.8	914.8	819.5	734.6	669.2	590.2
47.5°	561.3	705.4	913.2	1061.0	1060.4	952.8	829.8	738.7	659.8	598.5	534.6
50°	502.0	627.5	803.3	971.0	985.0	894.7	777.9	687.5	614.0	549.6	498.2
52.5°	448.7	552.2	710.3	871.1	911.1	832.8	719.5	636.1	564.7	505.5	461.5
55°	379.2	459.3	579.4	729.8	790.4	735.2	634.5	556.7	498.8	449.0	411.2
57.5°	320.8	380.8	477.2	598.3	668.9	634.1	551.1	487.9	438.3	393.3	363.4
60°	284.0	333.2	414.9	516.1	593.9	569.6	498.8	439.8	397.6	358.7	330.5
62.5°	249.4	291.7	361.7	443.8	515.2	505.2	447.3	397.8	360.9	325.3	301.5
65°	200.7	231.5	286.2	350.6	407.9	412.8	371.1	337.5	304.6	276.5	255.4
67.5°	159.8	179.9	218.4	272.6	315.6	330.9	305.5	279.9	253.7	232.0	213.7
70°	134.7	150.9	179.0	222.9	262.4	278.6	264.0	243.9	221.3	203.4	187.7
72.5°	109.2	125.0	145.7	177.9	211.7	229.3	224.2	209.8	191.4	176.6	161.8
75°	82.3	87.1	101.2	122.8	149.3	164.4	168.3	160.7	146.0	134.7	126.0
77.5°	60.8	63.8	70.4	81.8	99.1	112.6	118.1	117.2	107.2	100.6	92.5
80°	48.7	50.3	53.6	58.5	71.4	85.0	88.7	88.7	81.7	79.0	70.8
82.5°	37.0	38.2	40.1	42.8	48.9	60.7	64.9	65.8	61.3	57.8	51.4
85°	21.1	20.5	21.6	23.2	24.4	27.6	34.1	35.1	34.1	29.8	28.1
87.5°	8.7	9.0	8.9	8.2	8.5	8.7	10.7	12.6	11.1	10.0	9.4
90°	7.0	6.3	5.5	4.6	3.5	2.5	1.5	0.4	1.5	2.5	3.5
92.5°	9.1	8.7	8.4	8.2	8.3	8.4	8.5	8.6	8.5	8.4	8.3
95°	15.2	14.6	13.9	15.2	18.3	21.4	24.5	27.6	24.5	21.4	18.3
97.5°	19.2	17.6	16.1	19.7	28.5	37.3	46.1	54.9	46.1	37.3	28.5
100°	21.0	19.4	17.9	23.5	36.4	49.4	62.4	75.3	62.4	49.4	36.4
102.5°	51.9	65.3	78.7	86.8	89.5	92.3	95.1	97.8	95.1	92.3	89.5
105°	77.6	103.4	129.2	140.7	137.9	135.0	132.2	129.3	132.2	135.0	137.9
107.5°	98.2	129.2	160.1	174.5	172.2	169.9	167.6	165.3	167.6	169.9	172.2
110°	129.1	156.5	183.8	196.4	194.4	192.5	190.5	188.5	190.5	192.5	194.4



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	201.3	208.1	214.8	217.3	215.6	213.8	212.1	210.3	212.1	213.8	215.6
115°	257.8	255.4	253.1	251.1	249.5	247.9	246.2	244.7	246.2	247.9	249.5
117.5°	287.6	285.9	284.3	282.6	280.8	279.0	277.2	275.4	277.2	279.0	280.8
120°	308.5	306.8	305.1	303.5	302.1	300.7	299.2	297.8	299.2	300.7	302.1
122.5°	328.2	326.4	324.6	322.9	321.4	319.9	318.4	316.9	318.4	319.9	321.4
125°	356.0	354.2	352.4	350.8	349.6	348.4	347.2	345.9	347.2	348.4	349.6
127.5°	381.7	380.3	379.0	377.6	376.3	375.0	373.6	372.2	373.6	375.0	376.3
130°	398.3	397.3	396.2	394.9	393.5	391.9	390.4	388.9	390.4	391.9	393.5
132.5°	414.3	413.3	412.2	411.1	409.8	408.5	407.2	405.9	407.2	408.5	409.8
135°	437.0	436.1	435.3	434.1	432.6	431.0	429.6	428.0	429.6	431.0	432.6
137.5°	457.6	456.6	455.7	454.6	453.6	452.5	451.4	450.5	451.4	452.5	453.6
140°	471.1	470.0	469.0	468.1	467.3	466.6	465.8	465.0	465.8	466.6	467.3
142.5°	483.3	482.2	480.9	480.0	479.3	478.7	478.0	477.3	478.0	478.7	479.3
145°	500.1	498.6	496.9	496.2	496.3	496.4	496.4	496.5	496.4	496.4	496.3
147.5°	515.7	514.0	512.5	511.8	512.3	512.6	512.9	513.3	512.9	512.6	512.3
150°	525.0	523.5	522.0	521.5	522.2	522.9	523.5	524.2	523.5	522.9	522.2
152.5°	533.7	532.2	530.8	530.4	531.2	531.9	532.6	533.4	532.6	531.9	531.2
155°	545.8	544.6	543.5	543.3	544.2	545.0	545.9	546.7	545.9	545.0	544.2
157.5°	556.0	555.1	554.4	554.3	555.1	555.8	556.5	557.2	556.5	555.8	555.1
160°	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	562.8	562.2	561.7
162.5°	567.4	567.0	566.5	566.6	567.0	567.6	568.2	568.8	568.2	567.6	567.0
165°	574.2	574.0	573.7	573.8	574.4	574.9	575.5	576.1	575.5	574.9	574.4
167.5°	579.7	579.4	579.1	579.3	579.8	580.4	581.0	581.6	581.0	580.4	579.8
170°	582.5	582.4	582.1	582.4	582.9	583.5	584.1	584.6	584.1	583.5	582.9
172.5°	584.6	584.4	584.2	584.4	585.0	585.5	586.1	586.7	586.1	585.5	585.0
175°	586.8	586.6	586.4	586.6	587.3	588.0	588.6	589.3	588.6	588.0	587.3
177.5°	587.5	587.4	587.3	587.6	588.2	588.6	589.2	589.7	589.2	588.6	588.2
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1534.8	1531.8	1526.2	1517.5	1512.3	1503.2	1497.1	1500.6	1501.5	1500.6	1499.7
5°	1493.5	1482.2	1466.6	1451.4	1437.3	1422.2	1413.5	1409.7	1402.2	1397.8	1395.7
7.5°	1443.7	1424.2	1401.9	1375.6	1353.2	1329.7	1317.7	1311.7	1296.2	1287.8	1280.4
10°	1406.5	1375.7	1353.5	1318.8	1297.8	1266.9	1245.9	1246.3	1225.2	1213.3	1204.7
12.5°	1365.4	1331.5	1294.6	1263.5	1234.1	1209.3	1184.0	1173.6	1151.3	1139.8	1116.4
15°	1297.2	1257.8	1218.8	1176.6	1146.8	1108.4	1071.6	1026.7	990.5	959.1	950.5
17.5°	1222.8	1173.9	1134.8	1085.2	1034.3	969.7	927.1	901.0	879.1	862.6	850.3
20°	1171.7	1121.9	1080.3	1005.7	936.9	893.2	861.8	841.7	819.0	801.2	791.4
22.5°	1118.0	1066.1	1009.3	926.0	872.5	837.3	809.3	786.4	770.9	757.0	748.1
25°	1041.9	985.0	891.5	834.1	790.8	754.1	734.6	720.6	704.3	685.4	676.7
27.5°	961.4	871.1	803.9	761.2	719.9	696.0	678.5	657.5	642.9	634.5	625.4
30°	901.2	810.9	758.4	711.9	682.7	656.2	635.6	623.7	609.7	595.1	589.1
32.5°	834.1	762.0	711.7	672.9	643.3	620.7	604.5	585.2	575.0	566.1	553.6
35°	750.8	696.2	650.2	618.9	590.8	572.3	553.4	542.0	523.7	516.1	511.2
37.5°	680.3	632.9	598.6	565.5	543.2	522.9	511.3	493.3	485.3	474.7	464.5
40°	640.5	593.9	561.0	533.9	509.1	493.9	479.3	464.7	452.8	447.9	435.5
42.5°	599.8	562.0	529.0	499.3	482.7	466.6	448.2	437.4	425.1	417.2	409.5
45°	543.6	510.1	482.0	457.6	439.3	422.5	410.6	392.7	385.7	370.0	363.5
47.5°	494.3	463.2	436.3	413.2	395.3	384.3	366.9	352.9	341.7	332.1	323.7
50°	459.3	433.3	407.3	386.8	370.6	354.9	337.0	330.0	312.7	307.8	303.0
52.5°	427.2	402.6	378.8	358.7	342.4	327.2	311.4	302.3	290.6	285.8	282.2
55°	382.5	358.7	335.9	318.0	301.8	286.2	276.5	265.1	259.7	255.8	251.5
57.5°	337.5	316.0	298.6	280.5	264.2	251.8	240.5	233.7	228.0	223.1	217.9
60°	308.9	288.3	272.6	255.8	239.1	228.9	220.1	212.1	205.5	198.0	195.8
62.5°	278.6	260.7	246.2	229.9	215.3	205.9	197.6	190.0	182.2	171.1	168.1
65°	236.9	222.9	207.7	194.2	181.2	172.0	160.1	151.5	148.2	147.2	146.6
67.5°	199.3	186.0	173.0	159.1	147.3	138.8	132.7	131.4	129.1	128.5	127.0
70°	174.1	161.8	148.8	135.7	124.4	122.8	120.7	118.5	115.8	114.7	113.6
72.5°	151.6	138.8	125.8	115.4	110.6	108.5	106.3	104.2	102.3	101.3	100.6
75°	116.3	104.4	95.7	92.0	89.3	87.6	84.4	82.8	81.7	80.1	79.5
77.5°	83.7	77.0	73.1	70.7	67.8	66.1	64.2	62.6	61.5	61.1	60.3
80°	63.8	60.6	57.9	54.6	53.6	51.4	50.9	49.2	49.7	48.2	48.2
82.5°	49.6	45.4	43.1	41.7	40.6	38.8	38.3	37.5	37.7	36.4	36.4
85°	25.4	24.4	23.2	22.2	22.2	20.5	21.1	20.5	20.5	19.5	18.9
87.5°	9.1	8.9	8.2	8.3	8.5	8.2	8.3	8.0	8.1	8.2	7.7
90°	4.6	5.5	6.3	7.0	7.7	8.5	9.0	9.5	9.9	10.4	10.8
92.5°	8.2	8.4	8.7	9.1	9.5	9.9	10.1	10.4	10.6	10.8	11.0
95°	15.2	13.9	14.6	15.2	15.9	16.6	17.0	17.5	18.0	18.5	18.7
97.5°	19.7	16.1	17.6	19.2	20.7	22.2	22.6	23.0	23.3	23.7	24.0
100°	23.5	17.9	19.4	21.0	22.7	24.2	25.0	25.8	26.5	27.3	27.7
102.5°	86.8	78.7	65.3	51.9	38.4	24.9	25.9	26.9	27.9	28.9	29.5
105°	140.7	129.2	103.4	77.6	51.8	25.9	27.0	28.0	29.1	30.1	30.8
107.5°	174.5	160.1	129.2	98.2	67.3	36.4	35.3	34.2	33.2	32.1	31.8
110°	196.4	183.8	156.5	129.1	101.7	74.4	65.0	55.5	46.1	36.6	32.1



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.3	214.8	208.1	201.3	194.5	187.8	153.3	118.8	84.3	49.8	32.8
115°	251.1	253.1	255.4	257.8	260.2	262.5	218.7	175.0	131.2	87.4	62.1
117.5°	282.6	284.3	285.9	287.6	289.2	290.7	280.2	269.6	259.0	248.4	232.0
120°	303.5	305.1	306.8	308.5	310.1	311.9	313.0	314.1	315.3	316.4	310.6
122.5°	322.9	324.6	326.4	328.2	330.1	332.0	332.6	333.3	334.0	334.7	333.8
125°	350.8	352.4	354.2	356.0	357.8	359.5	360.2	360.9	361.5	362.2	362.6
127.5°	377.6	379.0	380.3	381.7	383.0	384.4	385.3	386.3	387.3	388.2	388.7
130°	394.9	396.2	397.3	398.3	399.3	400.4	401.5	402.4	403.5	404.6	405.0
132.5°	411.1	412.2	413.3	414.3	415.3	416.4	417.3	418.2	419.1	420.0	420.3
135°	434.1	435.3	436.1	437.0	437.8	438.6	439.6	440.6	441.5	442.5	442.9
137.5°	454.6	455.7	456.6	457.6	458.5	459.5	460.5	461.4	462.3	463.3	463.5
140°	468.1	469.0	470.0	471.1	472.1	473.1	474.0	474.8	475.6	476.5	476.7
142.5°	480.0	480.9	482.2	483.3	484.5	485.8	486.5	487.3	488.0	488.9	489.0
145°	496.2	496.9	498.6	500.1	501.7	503.4	504.0	504.7	505.3	506.0	506.1
147.5°	511.8	512.5	514.0	515.7	517.2	518.9	519.3	519.8	520.3	520.8	520.8
150°	521.5	522.0	523.5	525.0	526.5	528.0	528.6	529.1	529.7	530.3	530.4
152.5°	530.4	530.8	532.2	533.7	535.1	536.5	537.1	537.7	538.3	538.8	538.7
155°	543.3	543.5	544.6	545.8	546.9	548.0	548.6	549.2	549.8	550.3	550.2
157.5°	554.3	554.4	555.1	556.0	556.8	557.6	558.2	558.8	559.5	560.1	560.1
160°	561.1	561.1	561.7	562.2	562.8	563.4	563.9	564.4	565.0	565.6	565.6
162.5°	566.6	566.5	567.0	567.4	567.9	568.4	569.1	569.7	570.4	571.0	571.0
165°	573.8	573.7	574.0	574.2	574.5	574.8	575.5	576.2	576.8	577.5	577.5
167.5°	579.3	579.1	579.4	579.7	579.9	580.2	580.8	581.5	582.2	582.9	582.8
170°	582.4	582.1	582.4	582.5	582.7	582.9	583.6	584.2	584.9	585.5	585.5
172.5°	584.4	584.2	584.4	584.6	584.7	585.0	585.6	586.3	586.9	587.6	587.5
175°	586.6	586.4	586.6	586.8	586.9	587.2	587.8	588.5	589.1	589.8	589.7
177.5°	587.6	587.3	587.4	587.5	587.6	587.7	588.2	588.7	589.3	589.8	589.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1495.0	1495.8	1494.5	1495.4	1494.5	1495.8	1495.0	1499.7	1500.6	1501.5	1500.6
5°	1392.9	1386.5	1385.4	1383.8	1385.4	1386.5	1392.9	1395.7	1397.8	1402.2	1409.7
7.5°	1271.1	1270.2	1267.5	1263.7	1267.5	1270.2	1271.1	1280.4	1287.8	1296.2	1311.7
10°	1192.8	1190.1	1189.6	1185.8	1189.6	1190.1	1192.8	1204.7	1213.3	1225.2	1246.3
12.5°	1101.1	1083.6	1081.8	1072.4	1081.8	1083.6	1101.1	1116.4	1139.8	1151.3	1173.6
15°	937.5	934.3	923.4	916.4	923.4	934.3	937.5	950.5	959.1	990.5	1026.7
17.5°	844.0	833.4	830.1	828.5	830.1	833.4	844.0	850.3	862.6	879.1	901.0
20°	783.8	774.1	772.5	771.4	772.5	774.1	783.8	791.4	801.2	819.0	841.7
22.5°	742.3	732.1	727.9	724.6	727.9	732.1	742.3	748.1	757.0	770.9	786.4
25°	671.3	667.6	665.4	664.3	665.4	667.6	671.3	676.7	685.4	704.3	720.6
27.5°	615.8	607.5	605.8	603.1	605.8	607.5	615.8	625.4	634.5	642.9	657.5
30°	584.2	581.6	577.7	574.5	577.7	581.6	584.2	589.1	595.1	609.7	623.7
32.5°	547.0	544.8	541.4	539.9	541.4	544.8	547.0	553.6	566.1	575.0	585.2
35°	505.8	498.2	495.0	490.1	495.0	498.2	505.8	511.2	516.1	523.7	542.0
37.5°	462.2	458.2	453.6	455.3	453.6	458.2	462.2	464.5	474.7	485.3	493.3
40°	428.4	425.7	424.7	424.1	424.7	425.7	428.4	435.5	447.9	452.8	464.7
42.5°	401.6	394.1	391.3	391.2	391.3	394.1	401.6	409.5	417.2	425.1	437.4
45°	360.9	353.8	348.9	349.4	348.9	353.8	360.9	363.5	370.0	385.7	392.7
47.5°	319.0	318.9	315.8	316.8	315.8	318.9	319.0	323.7	332.1	341.7	352.9
50°	299.1	295.9	293.8	294.2	293.8	295.9	299.1	303.0	307.8	312.7	330.0
52.5°	280.1	277.3	275.6	277.9	275.6	277.3	280.1	282.2	285.8	290.6	302.3
55°	248.8	245.6	245.1	244.5	245.1	245.6	248.8	251.5	255.8	259.7	265.1
57.5°	213.9	211.7	208.5	207.1	208.5	211.7	213.9	217.9	223.1	228.0	233.7
60°	188.8	184.5	179.0	178.6	179.0	184.5	188.8	195.8	198.0	205.5	212.1
62.5°	165.8	165.0	163.9	163.8	163.9	165.0	165.8	168.1	171.1	182.2	190.0
65°	145.5	145.0	145.5	146.0	145.5	145.0	145.5	146.6	147.2	148.2	151.5
67.5°	126.8	125.8	124.8	125.3	124.8	125.8	126.8	127.0	128.5	129.1	131.4
70°	112.5	111.9	111.5	111.5	111.5	111.9	112.5	113.6	114.7	115.8	118.5
72.5°	98.7	98.6	98.0	97.6	98.0	98.6	98.7	100.6	101.3	102.3	104.2
75°	79.0	77.9	77.9	77.9	77.9	77.9	79.0	79.5	80.1	81.7	82.8
77.5°	60.2	59.6	59.1	58.6	59.1	59.6	60.2	60.3	61.1	61.5	62.6
80°	47.6	47.0	46.6	46.6	46.6	47.0	47.6	48.2	48.2	49.7	49.2
82.5°	36.4	35.8	35.7	35.3	35.7	35.8	36.4	36.4	36.4	37.7	37.5
85°	19.5	20.0	19.5	20.5	19.5	20.0	19.5	18.9	19.5	20.5	20.5
87.5°	7.8	7.4	7.9	7.5	7.9	7.4	7.8	7.7	8.2	8.1	8.0
90°	10.9	11.1	11.3	11.5	11.3	11.1	10.9	10.8	10.4	9.9	9.5
92.5°	11.2	11.3	11.4	11.5	11.4	11.3	11.2	11.0	10.8	10.6	10.4
95°	18.6	18.5	18.4	18.3	18.4	18.5	18.6	18.7	18.5	18.0	17.5
97.5°	24.1	24.2	24.3	24.5	24.3	24.2	24.1	24.0	23.7	23.3	23.0
100°	28.0	28.1	28.3	28.5	28.3	28.1	28.0	27.7	27.3	26.5	25.8
102.5°	29.8	30.0	30.2	30.6	30.2	30.0	29.8	29.5	28.9	27.9	26.9
105°	31.2	31.6	32.0	32.4	32.0	31.6	31.2	30.8	30.1	29.1	28.0
107.5°	32.1	32.5	32.9	33.3	32.9	32.5	32.1	31.8	32.1	33.2	34.2
110°	32.4	32.9	33.3	33.6	33.3	32.9	32.4	32.1	36.6	46.1	55.5



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.0	33.3	33.7	33.9	33.7	33.3	33.0	32.8	49.8	84.3	118.8
115°	55.3	48.5	41.7	34.9	41.7	48.5	55.3	62.1	87.4	131.2	175.0
117.5°	209.5	187.2	164.9	142.4	164.9	187.2	209.5	232.0	248.4	259.0	269.6
120°	297.8	285.1	272.3	259.5	272.3	285.1	297.8	310.6	316.4	315.3	314.1
122.5°	331.3	328.8	326.4	323.8	326.4	328.8	331.3	333.8	334.7	334.0	333.3
125°	363.0	363.2	363.5	363.8	363.5	363.2	363.0	362.6	362.2	361.5	360.9
127.5°	388.8	388.9	388.9	389.0	388.9	388.9	388.8	388.7	388.2	387.3	386.3
130°	404.9	404.8	404.7	404.6	404.7	404.8	404.9	405.0	404.6	403.5	402.4
132.5°	420.2	420.1	420.0	420.0	420.0	420.1	420.2	420.3	420.0	419.1	418.2
135°	442.6	442.5	442.3	442.1	442.3	442.5	442.6	442.9	442.5	441.5	440.6
137.5°	463.2	462.8	462.6	462.3	462.6	462.8	463.2	463.5	463.3	462.3	461.4
140°	476.2	475.8	475.3	474.8	475.3	475.8	476.2	476.7	476.5	475.6	474.8
142.5°	488.5	488.0	487.5	487.1	487.5	488.0	488.5	489.0	488.9	488.0	487.3
145°	505.6	505.2	504.7	504.2	504.7	505.2	505.6	506.1	506.0	505.3	504.7
147.5°	520.5	520.1	519.7	519.3	519.7	520.1	520.5	520.8	520.8	520.3	519.8
150°	529.9	529.4	528.9	528.5	528.9	529.4	529.9	530.4	530.3	529.7	529.1
152.5°	538.2	537.5	536.9	536.3	536.9	537.5	538.2	538.7	538.8	538.3	537.7
155°	549.4	548.7	548.0	547.1	548.0	548.7	549.4	550.2	550.3	549.8	549.2
157.5°	559.3	558.6	557.8	557.1	557.8	558.6	559.3	560.1	560.1	559.5	558.8
160°	564.9	564.3	563.5	562.9	563.5	564.3	564.9	565.6	565.6	565.0	564.4
162.5°	570.1	569.3	568.5	567.7	568.5	569.3	570.1	571.0	571.0	570.4	569.7
165°	576.8	576.2	575.5	574.8	575.5	576.2	576.8	577.5	577.5	576.8	576.2
167.5°	581.9	581.1	580.2	579.4	580.2	581.1	581.9	582.8	582.9	582.2	581.5
170°	584.6	583.8	582.9	582.0	582.9	583.8	584.6	585.5	585.5	584.9	584.2
172.5°	586.7	585.8	585.0	584.1	585.0	585.8	586.7	587.5	587.6	586.9	586.3
175°	588.7	587.7	586.9	585.9	586.9	587.7	588.7	589.7	589.8	589.1	588.5
177.5°	589.1	588.3	587.7	587.0	587.7	588.3	589.1	589.7	589.8	589.3	588.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1497.1	1503.2	1512.3	1517.5	1526.2	1531.8	1534.8	1540.4	1543.4	1554.3	1565.5
5°	1413.5	1422.2	1437.3	1451.4	1466.6	1482.2	1493.5	1506.6	1518.5	1539.0	1560.6
7.5°	1317.7	1329.7	1353.2	1375.6	1401.9	1424.2	1443.7	1465.9	1485.7	1515.2	1545.8
10°	1245.9	1266.9	1297.8	1318.8	1353.5	1375.7	1406.5	1430.9	1458.4	1497.4	1532.0
12.5°	1184.0	1209.3	1234.1	1263.5	1294.6	1331.5	1365.4	1396.6	1429.5	1469.7	1510.3
15°	1071.6	1108.4	1146.8	1176.6	1218.8	1257.8	1297.2	1339.4	1379.4	1427.6	1480.6
17.5°	927.1	969.7	1034.3	1085.2	1134.8	1173.9	1222.8	1273.8	1321.0	1379.1	1438.1
20°	861.8	893.2	936.9	1005.7	1080.3	1121.9	1171.7	1228.0	1282.1	1345.3	1408.7
22.5°	809.3	837.3	872.5	926.0	1009.3	1066.1	1118.0	1175.2	1238.0	1302.5	1372.7
25°	734.6	754.1	790.8	834.1	891.5	985.0	1041.9	1099.2	1167.4	1236.6	1316.7
27.5°	678.5	696.0	719.9	761.2	803.9	871.1	961.4	1023.9	1091.8	1169.8	1252.9
30°	635.6	656.2	682.7	711.9	758.4	810.9	901.2	973.7	1040.8	1120.9	1209.6
32.5°	604.5	620.7	643.3	672.9	711.7	762.0	834.1	922.2	987.6	1072.0	1164.6
35°	553.4	572.3	590.8	618.9	650.2	696.2	750.8	845.0	909.9	993.2	1086.2
37.5°	511.3	522.9	543.2	565.5	598.6	632.9	680.3	764.7	834.9	916.7	1011.9
40°	479.3	493.9	509.1	533.9	561.0	593.9	640.5	703.3	783.8	863.9	956.9
42.5°	448.2	466.6	482.7	499.3	529.0	562.0	599.8	653.1	735.4	811.1	901.6
45°	410.6	422.5	439.3	457.6	482.0	510.1	543.6	590.2	669.2	734.6	819.5
47.5°	366.9	384.3	395.3	413.2	436.3	463.2	494.3	534.6	598.5	659.8	738.7
50°	337.0	354.9	370.6	386.8	407.3	433.3	459.3	498.2	549.6	614.0	687.5
52.5°	311.4	327.2	342.4	358.7	378.8	402.6	427.2	461.5	505.5	564.7	636.1
55°	276.5	286.2	301.8	318.0	335.9	358.7	382.5	411.2	449.0	498.8	556.7
57.5°	240.5	251.8	264.2	280.5	298.6	316.0	337.5	363.4	393.3	438.3	487.9
60°	220.1	228.9	239.1	255.8	272.6	288.3	308.9	330.5	358.7	397.6	439.8
62.5°	197.6	205.9	215.3	229.9	246.2	260.7	278.6	301.5	325.3	360.9	397.8
65°	160.1	172.0	181.2	194.2	207.7	222.9	236.9	255.4	276.5	304.6	337.5
67.5°	132.7	138.8	147.3	159.1	173.0	186.0	199.3	213.7	232.0	253.7	279.9
70°	120.7	122.8	124.4	135.7	148.8	161.8	174.1	187.7	203.4	221.3	243.9
72.5°	106.3	108.5	110.6	115.4	125.8	138.8	151.6	161.8	176.6	191.4	209.8
75°	84.4	87.6	89.3	92.0	95.7	104.4	116.3	126.0	134.7	146.0	160.7
77.5°	64.2	66.1	67.8	70.7	73.1	77.0	83.7	92.5	100.6	107.2	117.2
80°	50.9	51.4	53.6	54.6	57.9	60.6	63.8	70.8	79.0	81.7	88.7
82.5°	38.3	38.8	40.6	41.7	43.1	45.4	49.6	51.4	57.8	61.3	65.8
85°	21.1	20.5	22.2	22.2	23.2	24.4	25.4	28.1	29.8	34.1	35.1
87.5°	8.3	8.2	8.5	8.3	8.2	8.9	9.1	9.4	10.0	11.1	12.6
90°	9.0	8.5	7.7	7.0	6.3	5.5	4.6	3.5	2.5	1.5	0.4
92.5°	10.1	9.9	9.5	9.1	8.7	8.4	8.2	8.3	8.4	8.5	8.6
95°	17.0	16.6	15.9	15.2	14.6	13.9	15.2	18.3	21.4	24.5	27.6
97.5°	22.6	22.2	20.7	19.2	17.6	16.1	19.7	28.5	37.3	46.1	54.9
100°	25.0	24.2	22.7	21.0	19.4	17.9	23.5	36.4	49.4	62.4	75.3
102.5°	25.9	24.9	38.4	51.9	65.3	78.7	86.8	89.5	92.3	95.1	97.8
105°	27.0	25.9	51.8	77.6	103.4	129.2	140.7	137.9	135.0	132.2	129.3
107.5°	35.3	36.4	67.3	98.2	129.2	160.1	174.5	172.2	169.9	167.6	165.3
110°	65.0	74.4	101.7	129.1	156.5	183.8	196.4	194.4	192.5	190.5	188.5



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	153.3	187.8	194.5	201.3	208.1	214.8	217.3	215.6	213.8	212.1	210.3
115°	218.7	262.5	260.2	257.8	255.4	253.1	251.1	249.5	247.9	246.2	244.7
117.5°	280.2	290.7	289.2	287.6	285.9	284.3	282.6	280.8	279.0	277.2	275.4
120°	313.0	311.9	310.1	308.5	306.8	305.1	303.5	302.1	300.7	299.2	297.8
122.5°	332.6	332.0	330.1	328.2	326.4	324.6	322.9	321.4	319.9	318.4	316.9
125°	360.2	359.5	357.8	356.0	354.2	352.4	350.8	349.6	348.4	347.2	345.9
127.5°	385.3	384.4	383.0	381.7	380.3	379.0	377.6	376.3	375.0	373.6	372.2
130°	401.5	400.4	399.3	398.3	397.3	396.2	394.9	393.5	391.9	390.4	388.9
132.5°	417.3	416.4	415.3	414.3	413.3	412.2	411.1	409.8	408.5	407.2	405.9
135°	439.6	438.6	437.8	437.0	436.1	435.3	434.1	432.6	431.0	429.6	428.0
137.5°	460.5	459.5	458.5	457.6	456.6	455.7	454.6	453.6	452.5	451.4	450.5
140°	474.0	473.1	472.1	471.1	470.0	469.0	468.1	467.3	466.6	465.8	465.0
142.5°	486.5	485.8	484.5	483.3	482.2	480.9	480.0	479.3	478.7	478.0	477.3
145°	504.0	503.4	501.7	500.1	498.6	496.9	496.2	496.3	496.4	496.4	496.5
147.5°	519.3	518.9	517.2	515.7	514.0	512.5	511.8	512.3	512.6	512.9	513.3
150°	528.6	528.0	526.5	525.0	523.5	522.0	521.5	522.2	522.9	523.5	524.2
152.5°	537.1	536.5	535.1	533.7	532.2	530.8	530.4	531.2	531.9	532.6	533.4
155°	548.6	548.0	546.9	545.8	544.6	543.5	543.3	544.2	545.0	545.9	546.7
157.5°	558.2	557.6	556.8	556.0	555.1	554.4	554.3	555.1	555.8	556.5	557.2
160°	563.9	563.4	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4
162.5°	569.1	568.4	567.9	567.4	567.0	566.5	566.6	567.0	567.6	568.2	568.8
165°	575.5	574.8	574.5	574.2	574.0	573.7	573.8	574.4	574.9	575.5	576.1
167.5°	580.8	580.2	579.9	579.7	579.4	579.1	579.3	579.8	580.4	581.0	581.6
170°	583.6	582.9	582.7	582.5	582.4	582.1	582.4	582.9	583.5	584.1	584.6
172.5°	585.6	585.0	584.7	584.6	584.4	584.2	584.4	585.0	585.5	586.1	586.7
175°	587.8	587.2	586.9	586.8	586.6	586.4	586.6	587.3	588.0	588.6	589.3
177.5°	588.2	587.7	587.6	587.5	587.4	587.3	587.6	588.2	588.6	589.2	589.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1565.9	1567.2	1575.9	1579.8	1587.6	1590.6	1594.1	1593.3	1593.3	1595.0	1607.1
5°	1569.3	1580.1	1596.4	1612.1	1627.2	1640.2	1648.9	1657.5	1660.8	1676.4	1690.5
7.5°	1563.7	1583.6	1610.5	1634.3	1663.0	1685.4	1704.1	1720.8	1732.3	1755.1	1778.5
10°	1556.3	1584.5	1614.8	1645.6	1685.1	1714.8	1745.1	1768.4	1776.0	1810.0	1829.5
12.5°	1541.6	1579.2	1617.8	1657.7	1696.3	1737.3	1770.7	1793.9	1820.6	1851.1	1887.1
15°	1519.6	1562.8	1613.2	1664.5	1719.7	1769.4	1805.2	1845.8	1874.9	1908.5	1939.8
17.5°	1487.8	1543.6	1607.5	1667.0	1730.9	1784.3	1833.4	1872.3	1892.9	1912.0	1916.7
20°	1462.7	1522.8	1598.0	1668.3	1732.2	1793.8	1842.5	1874.9	1880.4	1880.9	1852.3
22.5°	1435.5	1503.3	1582.0	1654.0	1730.4	1799.0	1836.9	1850.7	1829.3	1792.6	1737.2
25°	1385.4	1463.9	1555.3	1637.4	1720.8	1785.7	1798.7	1774.3	1699.2	1620.2	1520.1
27.5°	1331.1	1419.3	1517.3	1608.7	1697.5	1737.6	1709.7	1621.9	1486.5	1368.7	1226.0
30°	1291.3	1390.2	1486.5	1588.8	1671.0	1688.3	1624.0	1494.7	1336.7	1159.3	1017.0
32.5°	1245.9	1349.6	1455.4	1561.1	1629.9	1613.0	1506.7	1347.5	1162.3	987.9	853.5
35°	1180.9	1288.0	1402.2	1508.2	1552.0	1479.0	1320.0	1112.7	923.4	760.6	668.1
37.5°	1106.0	1222.5	1341.2	1438.6	1435.5	1313.8	1097.1	883.3	724.1	627.9	562.0
40°	1052.7	1170.6	1298.9	1381.0	1345.9	1187.4	952.6	750.8	634.5	557.7	509.6
42.5°	1001.7	1120.0	1247.3	1312.7	1251.6	1056.7	822.8	664.7	568.8	508.8	469.8
45°	914.8	1039.8	1157.6	1193.9	1084.6	869.8	665.4	550.7	486.9	442.5	415.5
47.5°	829.8	952.8	1060.4	1061.0	913.2	705.4	561.3	476.6	422.1	387.8	368.1
50°	777.9	894.7	985.0	971.0	803.3	627.5	502.0	429.0	383.5	357.0	336.5
52.5°	719.5	832.8	911.1	871.1	710.3	552.2	448.7	387.4	349.8	326.8	308.3
55°	634.5	735.2	790.4	729.8	579.4	459.3	379.2	331.1	303.0	283.5	267.7
57.5°	551.1	634.1	668.9	598.3	477.2	380.8	320.8	284.6	256.7	242.8	234.6
60°	498.8	569.6	593.9	516.1	414.9	333.2	284.0	250.5	229.9	220.7	212.6
62.5°	447.3	505.2	515.2	443.8	361.7	291.7	249.4	221.0	207.4	198.6	190.9
65°	371.1	412.8	407.9	350.6	286.2	231.5	200.7	183.4	173.1	160.7	147.2
67.5°	305.5	330.9	315.6	272.6	218.4	179.9	159.8	146.7	134.0	122.1	119.0
70°	264.0	278.6	262.4	222.9	179.0	150.9	134.7	119.0	111.5	108.8	103.9
72.5°	224.2	229.3	211.7	177.9	145.7	125.0	109.2	100.4	96.3	94.0	90.9
75°	168.3	164.4	149.3	122.8	101.2	87.1	82.3	79.0	76.3	74.1	72.5
77.5°	118.1	112.6	99.1	81.8	70.4	63.8	60.8	59.1	57.8	56.7	55.0
80°	88.7	85.0	71.4	58.5	53.6	50.3	48.7	46.6	46.6	45.4	43.8
82.5°	64.9	60.7	48.9	42.8	40.1	38.2	37.0	35.7	35.3	35.5	34.3
85°	34.1	27.6	24.4	23.2	21.6	20.5	21.1	20.0	20.0	20.0	19.5
87.5°	10.7	8.7	8.5	8.2	8.9	9.0	8.7	8.9	9.5	9.1	9.7
90°	1.5	2.5	3.5	4.6	5.5	6.3	7.0	7.7	8.5	9.0	9.5
92.5°	8.5	8.4	8.3	8.2	8.4	8.7	9.1	9.5	9.9	10.1	10.4
95°	24.5	21.4	18.3	15.2	13.9	14.6	15.2	15.9	16.6	17.0	17.5
97.5°	46.1	37.3	28.5	19.7	16.1	17.6	19.2	20.7	22.2	22.6	23.0
100°	62.4	49.4	36.4	23.5	17.9	19.4	21.0	22.7	24.2	25.0	25.8
102.5°	95.1	92.3	89.5	86.8	78.7	65.3	51.9	38.4	24.9	25.9	26.9
105°	132.2	135.0	137.9	140.7	129.2	103.4	77.6	51.8	25.9	27.0	28.0
107.5°	167.6	169.9	172.2	174.5	160.1	129.2	98.2	67.3	36.4	35.3	34.2
110°	190.5	192.5	194.4	196.4	183.8	156.5	129.1	101.7	74.4	65.0	55.5



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	212.1	213.8	215.6	217.3	214.8	208.1	201.3	194.5	187.8	153.3	118.8
115°	246.2	247.9	249.5	251.1	253.1	255.4	257.8	260.2	262.5	218.7	175.0
117.5°	277.2	279.0	280.8	282.6	284.3	285.9	287.6	289.2	290.7	280.2	269.6
120°	299.2	300.7	302.1	303.5	305.1	306.8	308.5	310.1	311.9	313.0	314.1
122.5°	318.4	319.9	321.4	322.9	324.6	326.4	328.2	330.1	332.0	332.6	333.3
125°	347.2	348.4	349.6	350.8	352.4	354.2	356.0	357.8	359.5	360.2	360.9
127.5°	373.6	375.0	376.3	377.6	379.0	380.3	381.7	383.0	384.4	385.3	386.3
130°	390.4	391.9	393.5	394.9	396.2	397.3	398.3	399.3	400.4	401.5	402.4
132.5°	407.2	408.5	409.8	411.1	412.2	413.3	414.3	415.3	416.4	417.3	418.2
135°	429.6	431.0	432.6	434.1	435.3	436.1	437.0	437.8	438.6	439.6	440.6
137.5°	451.4	452.5	453.6	454.6	455.7	456.6	457.6	458.5	459.5	460.5	461.4
140°	465.8	466.6	467.3	468.1	469.0	470.0	471.1	472.1	473.1	474.0	474.8
142.5°	478.0	478.7	479.3	480.0	480.9	482.2	483.3	484.5	485.8	486.5	487.3
145°	496.4	496.4	496.3	496.2	496.9	498.6	500.1	501.7	503.4	504.0	504.7
147.5°	512.9	512.6	512.3	511.8	512.5	514.0	515.7	517.2	518.9	519.3	519.8
150°	523.5	522.9	522.2	521.5	522.0	523.5	525.0	526.5	528.0	528.6	529.1
152.5°	532.6	531.9	531.2	530.4	530.8	532.2	533.7	535.1	536.5	537.1	537.7
155°	545.9	545.0	544.2	543.3	543.5	544.6	545.8	546.9	548.0	548.6	549.2
157.5°	556.5	555.8	555.1	554.3	554.4	555.1	556.0	556.8	557.6	558.2	558.8
160°	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	563.9	564.4
162.5°	568.2	567.6	567.0	566.6	566.5	567.0	567.4	567.9	568.4	569.1	569.7
165°	575.5	574.9	574.4	573.8	573.7	574.0	574.2	574.5	574.8	575.5	576.2
167.5°	581.0	580.4	579.8	579.3	579.1	579.4	579.7	579.9	580.2	580.8	581.5
170°	584.1	583.5	582.9	582.4	582.1	582.4	582.5	582.7	582.9	583.6	584.2
172.5°	586.1	585.5	585.0	584.4	584.2	584.4	584.6	584.7	585.0	585.6	586.3
175°	588.6	588.0	587.3	586.6	586.4	586.6	586.8	586.9	587.2	587.8	588.5
177.5°	589.2	588.6	588.2	587.6	587.3	587.4	587.5	587.6	587.7	588.2	588.7
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1611.4	1617.1	1619.6	1619.6	1622.7	1621.4	1620.1
5°	1704.1	1714.3	1716.4	1726.2	1733.2	1731.0	1732.2
7.5°	1796.1	1812.7	1829.0	1836.5	1837.6	1841.9	1843.6
10°	1852.8	1866.3	1891.7	1887.9	1906.9	1917.7	1899.8
12.5°	1907.3	1925.6	1943.3	1948.1	1958.8	1962.3	1955.3
15°	1956.6	1966.4	1967.5	1964.8	1968.0	1965.3	1955.0
17.5°	1910.6	1894.8	1862.7	1847.5	1835.6	1817.9	1810.7
20°	1834.4	1787.9	1733.7	1712.1	1686.7	1637.0	1648.9
22.5°	1670.0	1616.9	1562.8	1499.7	1469.5	1422.3	1419.4
25°	1414.1	1322.7	1222.1	1151.7	1110.6	1063.6	1042.9
27.5°	1099.4	984.3	901.9	860.1	822.1	784.8	783.3
30°	892.6	806.0	742.2	706.5	683.2	667.6	670.8
32.5°	752.4	693.1	650.0	620.4	603.2	591.3	591.2
35°	615.1	574.5	546.9	534.4	522.0	513.4	513.9
37.5°	526.4	502.0	486.7	472.9	465.1	460.9	458.5
40°	480.9	460.9	449.0	440.9	434.4	428.4	427.4
42.5°	445.0	428.4	416.5	410.2	404.1	399.9	398.8
45°	394.9	381.4	370.6	363.5	360.9	357.0	357.0
47.5°	351.3	338.0	329.5	325.1	320.5	318.0	317.9
50°	321.9	311.6	304.0	301.3	297.5	295.9	295.4
52.5°	295.5	287.8	282.4	280.5	278.9	276.9	277.2
55°	259.7	255.4	253.2	251.5	248.8	245.6	247.8
57.5°	229.5	225.8	220.0	214.8	212.4	210.1	211.0
60°	208.3	200.7	193.1	187.2	185.6	180.7	180.7
62.5°	181.4	170.8	161.5	158.2	156.5	154.3	153.8
65°	139.6	135.3	133.1	130.9	129.8	129.8	128.7
67.5°	115.7	113.9	111.5	111.0	109.9	109.6	109.3
70°	102.2	100.0	99.0	98.5	97.3	97.9	96.3
72.5°	89.3	87.6	87.3	85.9	85.3	85.4	84.1
75°	70.4	70.4	69.8	69.2	68.2	67.6	68.2
77.5°	54.1	54.2	53.2	53.2	53.0	53.2	52.6
80°	43.3	43.8	43.3	42.7	42.2	42.7	42.2
82.5°	34.2	33.4	33.3	33.2	33.1	32.8	32.7
85°	19.5	20.0	19.5	18.9	18.9	18.9	19.5
87.5°	9.4	9.5	9.5	9.5	9.5	9.6	9.2
90°	9.9	10.4	10.8	10.9	11.1	11.3	11.5
92.5°	10.6	10.8	11.0	11.2	11.3	11.4	11.5
95°	18.0	18.5	18.7	18.6	18.5	18.4	18.3
97.5°	23.3	23.7	24.0	24.1	24.2	24.3	24.5
100°	26.5	27.3	27.7	28.0	28.1	28.3	28.5
102.5°	27.9	28.9	29.5	29.8	30.0	30.2	30.6
105°	29.1	30.1	30.8	31.2	31.6	32.0	32.4
107.5°	33.2	32.1	31.8	32.1	32.5	32.9	33.3
110°	46.1	36.6	32.1	32.4	32.9	33.3	33.6



TEST NUMBER: P331711-930

CATALOG NUMBER: S122RDIP-S865D530U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	84.3	49.8	32.8	33.0	33.3	33.7	33.9
115°	131.2	87.4	62.1	55.3	48.5	41.7	34.9
117.5°	259.0	248.4	232.0	209.5	187.2	164.9	142.4
120°	315.3	316.4	310.6	297.8	285.1	272.3	259.5
122.5°	334.0	334.7	333.8	331.3	328.8	326.4	323.8
125°	361.5	362.2	362.6	363.0	363.2	363.5	363.8
127.5°	387.3	388.2	388.7	388.8	388.9	388.9	389.0
130°	403.5	404.6	405.0	404.9	404.8	404.7	404.6
132.5°	419.1	420.0	420.3	420.2	420.1	420.0	420.0
135°	441.5	442.5	442.9	442.6	442.5	442.3	442.1
137.5°	462.3	463.3	463.5	463.2	462.8	462.6	462.3
140°	475.6	476.5	476.7	476.2	475.8	475.3	474.8
142.5°	488.0	488.9	489.0	488.5	488.0	487.5	487.1
145°	505.3	506.0	506.1	505.6	505.2	504.7	504.2
147.5°	520.3	520.8	520.8	520.5	520.1	519.7	519.3
150°	529.7	530.3	530.4	529.9	529.4	528.9	528.5
152.5°	538.3	538.8	538.7	538.2	537.5	536.9	536.3
155°	549.8	550.3	550.2	549.4	548.7	548.0	547.1
157.5°	559.5	560.1	560.1	559.3	558.6	557.8	557.1
160°	565.0	565.6	565.6	564.9	564.3	563.5	562.9
162.5°	570.4	571.0	571.0	570.1	569.3	568.5	567.7
165°	576.8	577.5	577.5	576.8	576.2	575.5	574.8
167.5°	582.2	582.9	582.8	581.9	581.1	580.2	579.4
170°	584.9	585.5	585.5	584.6	583.8	582.9	582.0
172.5°	586.9	587.6	587.5	586.7	585.8	585.0	584.1
175°	589.1	589.8	589.7	588.7	587.7	586.9	585.9
177.5°	589.3	589.8	589.7	589.1	588.3	587.7	587.0
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0

(END OF REPORT)