

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331725-930

Luminaire Tested: **S122RDIP-S865D925U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331725-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S865D925U930-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5638.8 lumens  
Efficiency: N/A  
Efficacy: 93.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	98	94	90	87	90	87	84	81	73	71	69	60	59	58	49	48	47	42
2	90	83	77	72	83	77	72	68	65	61	58	54	52	49	44	42	41	36
3	83	74	67	61	76	68	62	57	58	54	50	49	45	43	40	38	36	32
4	76	66	58	53	70	61	55	49	52	47	43	44	40	37	36	34	32	28
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28	25
6	65	53	46	40	60	50	43	38	43	38	34	36	32	29	30	27	25	22
7	60	48	41	36	55	45	38	34	39	34	30	33	29	26	28	25	23	20
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21	18
9	52	41	33	29	48	38	32	27	33	28	24	28	24	22	24	21	19	17
10	49	37	30	26	45	35	29	25	31	26	22	26	23	20	22	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	25137	25137	25137	25137
5°	28075	25293	22428	25293
10°	31147	25117	19441	25117
15°	32679	24749	15318	24749
20°	28331	24204	13254	24204
25°	18579	23457	11834	23457
30°	12506	22551	10711	22551
35°	10129	21409	9660	21409
40°	9008	20168	8939	20168
45°	8152	18712	7978	18712
50°	7420	17269	7390	17269
55°	6975	15671	6883	15671
60°	5835	14202	5767	14202
65°	4917	12894	5578	12894
70°	4546	11514	5264	11514
75°	4255	10025	4860	10025
80°	3924	8247	4333	8247
85°	3612	6502	3798	6502



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.6	2.6
10°-20°	411.2	7.3
20°-30°	529.9	9.4
30°-40°	503.6	8.9
40°-50°	431.4	7.7
50°-60°	328.5	5.8
60°-70°	207.7	3.7
70°-80°	103.7	1.8
80°-90°	30.8	0.5
90°-100°	169.2	3.0
100°-110°	574.1	10.2
110°-120°	609.9	10.8
120°-130°	502.1	8.9
130°-140°	403.2	7.2
140°-150°	304.7	5.4
150°-160°	214.1	3.8
160°-170°	126.0	2.2
170°-180°	41.0	0.7
0°-30°	1088.7	19.3
0°-40°	1592.3	28.2
0°-60°	2352.3	41.7
0°-90°	2694.4	47.8
90°-120°	1353.2	24.0
90°-150°	2563.1	45.5
90°-180°	2944.0	52.2
0°-180°	5638.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1557	1557	1557	1557	1557	
5°	1732	1561	1384	1561	1732	171
15°	1955	1481	916	1481	1955	527
25°	1043	1317	664	1317	1043	495
35°	514	1086	490	1086	514	329
45°	357	820	349	820	357	276
55°	248	557	244	557	248	217
65°	129	338	146	338	129	131
75°	68	161	78	161	68	72
85°	20	35	20	35	20	22
90°	27	1	27	1	27	15
95°	93	28	93	28	93	121
105°	917	99	917	99	917	887
115°	1207	175	1207	175	1207	1182
125°	979	244	979	244	979	885
135°	811	286	811	286	811	630
145°	648	327	648	327	648	411
155°	544	372	544	372	544	254
165°	478	405	478	405	478	137
175°	430	422	430	422	430	42
180°	423	423	423	423	423	



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1620.1	1621.4	1622.7	1619.6	1619.6	1617.1	1611.4	1607.1	1595.0	1593.3	1593.3
5°	1732.2	1731.0	1733.2	1726.2	1716.4	1714.3	1704.1	1690.5	1676.4	1660.8	1657.5
7.5°	1843.6	1841.9	1837.6	1836.5	1829.0	1812.7	1796.1	1778.5	1755.1	1732.3	1720.8
10°	1899.8	1917.7	1906.9	1887.9	1891.7	1866.3	1852.8	1829.5	1810.0	1776.0	1768.4
12.5°	1955.3	1962.3	1958.8	1948.1	1943.3	1925.6	1907.3	1887.1	1851.1	1820.6	1793.9
15°	1955.0	1965.3	1968.0	1964.8	1967.5	1966.4	1956.6	1939.8	1908.5	1874.9	1845.8
17.5°	1810.7	1817.9	1835.6	1847.5	1862.7	1894.8	1910.6	1916.7	1912.0	1892.9	1872.3
20°	1648.9	1637.0	1686.7	1712.1	1733.7	1787.9	1834.4	1852.3	1880.9	1880.4	1874.9
22.5°	1419.4	1422.3	1469.5	1499.7	1562.8	1616.9	1670.0	1737.2	1792.6	1829.3	1850.7
25°	1042.9	1063.6	1110.6	1151.7	1222.1	1322.7	1414.1	1520.1	1620.2	1699.2	1774.3
27.5°	783.3	784.8	822.1	860.1	901.9	984.3	1099.4	1226.0	1368.7	1486.5	1621.9
30°	670.8	667.6	683.2	706.5	742.2	806.0	892.6	1017.0	1159.3	1336.7	1494.7
32.5°	591.2	591.3	603.2	620.4	650.0	693.1	752.4	853.5	987.9	1162.3	1347.5
35°	513.9	513.4	522.0	534.4	546.9	574.5	615.1	668.1	760.6	923.4	1112.7
37.5°	458.5	460.9	465.1	472.9	486.7	502.0	526.4	562.0	627.9	724.1	883.3
40°	427.4	428.4	434.4	440.9	449.0	460.9	480.9	509.6	557.7	634.5	750.8
42.5°	398.8	399.9	404.1	410.2	416.5	428.4	445.0	469.8	508.8	568.8	664.7
45°	357.0	357.0	360.9	363.5	370.6	381.4	394.9	415.5	442.5	486.9	550.7
47.5°	317.9	318.0	320.5	325.1	329.5	338.0	351.3	368.1	387.8	422.1	476.6
50°	295.4	295.9	297.5	301.3	304.0	311.6	321.9	336.5	357.0	383.5	429.0
52.5°	277.2	276.9	278.9	280.5	282.4	287.8	295.5	308.3	326.8	349.8	387.4
55°	247.8	245.6	248.8	251.5	253.2	255.4	259.7	267.7	283.5	303.0	331.1
57.5°	211.0	210.1	212.4	214.8	220.0	225.8	229.5	234.6	242.8	256.7	284.6
60°	180.7	180.7	185.6	187.2	193.1	200.7	208.3	212.6	220.7	229.9	250.5
62.5°	153.8	154.3	156.5	158.2	161.5	170.8	181.4	190.9	198.6	207.4	221.0
65°	128.7	129.8	129.8	130.9	133.1	135.3	139.6	147.2	160.7	173.1	183.4
67.5°	109.3	109.6	109.9	111.0	111.5	113.9	115.7	119.0	122.1	134.0	146.7
70°	96.3	97.9	97.3	98.5	99.0	100.0	102.2	103.9	108.8	111.5	119.0
72.5°	84.1	85.4	85.3	85.9	87.3	87.6	89.3	90.9	94.0	96.3	100.4
75°	68.2	67.6	68.2	69.2	69.8	70.4	70.4	72.5	74.1	76.3	79.0
77.5°	52.6	53.2	53.0	53.2	53.2	54.2	54.1	55.0	56.7	57.8	59.1
80°	42.2	42.7	42.2	42.7	43.3	43.8	43.3	43.8	45.4	46.6	46.6
82.5°	32.7	32.8	33.1	33.2	33.3	33.4	34.2	34.3	35.5	35.3	35.7
85°	19.5	18.9	18.9	18.9	19.5	20.0	19.5	19.5	20.0	20.0	20.0
87.5°	12.3	12.7	12.7	12.7	12.7	12.6	12.2	13.0	12.7	13.3	12.7
90°	26.8	26.8	26.8	26.8	26.8	26.0	24.4	26.0	26.8	27.6	26.8
92.5°	45.1	46.4	45.7	48.3	49.0	54.1	60.9	70.9	89.4	105.7	104.3
95°	92.8	92.0	94.4	100.9	111.5	129.4	163.5	213.2	279.1	318.9	282.3
97.5°	182.6	189.4	201.3	221.4	260.2	318.9	407.0	497.5	571.2	544.5	410.1
100°	291.3	306.0	329.5	364.5	432.1	530.5	642.0	742.9	760.0	642.8	442.6
102.5°	512.7	532.5	561.9	621.7	695.0	799.4	880.9	903.7	830.3	646.0	430.3
105°	917.0	928.4	963.4	1013.8	1064.3	1091.2	1080.6	988.6	819.4	602.9	406.0
107.5°	1171.4	1186.5	1193.5	1196.3	1189.9	1150.6	1065.9	927.5	748.0	556.8	394.0
110°	1248.2	1249.0	1241.7	1226.2	1191.2	1124.5	1020.3	874.7	703.0	534.6	391.4



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1246.9	1242.5	1228.7	1202.8	1154.1	1077.7	966.4	826.6	671.8	520.2	392.0
115°	1206.7	1199.4	1178.2	1140.8	1083.0	999.2	892.6	767.3	633.1	504.5	395.4
117.5°	1134.9	1128.8	1106.4	1066.9	1008.0	929.4	832.7	722.7	608.6	496.8	401.3
120°	1088.8	1080.6	1057.0	1018.7	961.8	887.7	801.5	700.6	595.7	492.3	405.2
122.5°	1040.6	1033.7	1012.7	975.1	924.1	857.1	775.4	683.0	584.6	489.7	409.8
125°	978.8	972.3	952.0	921.1	873.9	812.9	741.3	657.5	568.8	484.9	416.6
127.5°	924.9	919.7	902.0	873.1	831.9	775.6	708.1	632.3	554.2	482.2	423.6
130°	894.2	887.7	871.5	843.8	804.0	750.2	685.9	616.0	544.4	480.9	428.8
132.5°	862.3	856.5	841.6	813.8	774.6	724.1	665.1	600.3	536.5	480.2	434.0
135°	811.2	808.0	793.4	766.5	731.5	685.9	632.3	578.5	525.6	479.2	440.2
137.5°	761.2	756.3	743.4	720.3	688.4	648.7	606.0	561.1	518.0	479.1	445.7
140°	726.6	721.8	709.6	688.4	662.3	626.6	589.1	550.1	513.5	478.4	448.3
142.5°	692.1	691.1	680.3	661.0	636.3	606.3	574.1	541.0	508.9	478.4	450.3
145°	647.7	645.2	637.2	623.3	603.7	580.2	555.0	528.1	502.9	476.8	452.4
147.5°	610.4	608.9	603.4	592.4	576.3	559.0	539.3	518.1	496.7	473.9	453.1
150°	588.3	587.5	582.6	572.8	560.6	546.0	528.9	511.0	491.5	472.0	452.4
152.5°	569.4	569.2	565.7	557.2	547.6	534.9	520.4	503.9	486.9	468.7	451.1
155°	544.4	546.0	542.7	537.0	528.1	519.1	507.0	493.9	478.4	463.0	449.1
157.5°	523.0	523.0	521.5	516.8	510.5	503.5	493.3	482.3	470.5	457.1	445.4
160°	509.4	509.4	508.6	504.5	498.8	493.1	484.1	475.2	464.6	453.2	443.4
162.5°	496.4	497.0	496.2	493.4	487.7	483.3	475.6	468.1	459.4	450.0	441.5
165°	477.6	478.4	478.4	475.2	472.0	468.7	463.0	457.3	450.8	443.4	437.7
167.5°	460.4	461.4	461.5	459.7	458.3	455.3	451.4	447.0	442.3	437.7	434.0
170°	450.0	451.6	452.4	450.0	449.1	447.5	444.3	441.8	437.7	434.5	432.1
172.5°	441.5	442.5	443.3	442.1	441.3	440.3	437.7	435.9	433.3	430.6	429.5
175°	430.5	432.1	432.9	432.1	432.1	431.3	430.5	429.7	427.2	426.4	425.6
177.5°	423.8	425.1	425.7	425.7	425.7	425.7	425.1	425.1	423.8	423.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1594.1	1590.6	1587.6	1579.8	1575.9	1567.2	1565.9	1565.5	1554.3	1543.4	1540.4
5°	1648.9	1640.2	1627.2	1612.1	1596.4	1580.1	1569.3	1560.6	1539.0	1518.5	1506.6
7.5°	1704.1	1685.4	1663.0	1634.3	1610.5	1583.6	1563.7	1545.8	1515.2	1485.7	1465.9
10°	1745.1	1714.8	1685.1	1645.6	1614.8	1584.5	1556.3	1532.0	1497.4	1458.4	1430.9
12.5°	1770.7	1737.3	1696.3	1657.7	1617.8	1579.2	1541.6	1510.3	1469.7	1429.5	1396.6
15°	1805.2	1769.4	1719.7	1664.5	1613.2	1562.8	1519.6	1480.6	1427.6	1379.4	1339.4
17.5°	1833.4	1784.3	1730.9	1667.0	1607.5	1543.6	1487.8	1438.1	1379.1	1321.0	1273.8
20°	1842.5	1793.8	1732.2	1668.3	1598.0	1522.8	1462.7	1408.7	1345.3	1282.1	1228.0
22.5°	1836.9	1799.0	1730.4	1654.0	1582.0	1503.3	1435.5	1372.7	1302.5	1238.0	1175.2
25°	1798.7	1785.7	1720.8	1637.4	1555.3	1463.9	1385.4	1316.7	1236.6	1167.4	1099.2
27.5°	1709.7	1737.6	1697.5	1608.7	1517.3	1419.3	1331.1	1252.9	1169.8	1091.8	1023.9
30°	1624.0	1688.3	1671.0	1588.8	1486.5	1390.2	1291.3	1209.6	1120.9	1040.8	973.7
32.5°	1506.7	1613.0	1629.9	1561.1	1455.4	1349.6	1245.9	1164.6	1072.0	987.6	922.2
35°	1320.0	1479.0	1552.0	1508.2	1402.2	1288.0	1180.9	1086.2	993.2	909.9	845.0
37.5°	1097.1	1313.8	1435.5	1438.6	1341.2	1222.5	1106.0	1011.9	916.7	834.9	764.7
40°	952.6	1187.4	1345.9	1381.0	1298.9	1170.6	1052.7	956.9	863.9	783.8	703.3
42.5°	822.8	1056.7	1251.6	1312.7	1247.3	1120.0	1001.7	901.6	811.1	735.4	653.1
45°	665.4	869.8	1084.6	1193.9	1157.6	1039.8	914.8	819.5	734.6	669.2	590.2
47.5°	561.3	705.4	913.2	1061.0	1060.4	952.8	829.8	738.7	659.8	598.5	534.6
50°	502.0	627.5	803.3	971.0	985.0	894.7	777.9	687.5	614.0	549.6	498.2
52.5°	448.7	552.2	710.3	871.1	911.1	832.8	719.5	636.1	564.7	505.5	461.5
55°	379.2	459.3	579.4	729.8	790.4	735.2	634.5	556.7	498.8	449.0	411.2
57.5°	320.8	380.8	477.2	598.3	668.9	634.1	551.1	487.9	438.3	393.3	363.4
60°	284.0	333.2	414.9	516.1	593.9	569.6	498.8	439.8	397.6	358.7	330.5
62.5°	249.4	291.7	361.7	443.8	515.2	505.2	447.3	397.8	360.9	325.3	301.5
65°	200.7	231.5	286.2	350.6	407.9	412.8	371.1	337.5	304.6	276.5	255.4
67.5°	159.8	179.9	218.4	272.6	315.6	330.9	305.5	279.9	253.7	232.0	213.7
70°	134.7	150.9	179.0	222.9	262.4	278.6	264.0	243.9	221.3	203.4	187.7
72.5°	109.2	125.0	145.7	177.9	211.7	229.3	224.2	209.8	191.4	176.6	161.8
75°	82.3	87.1	101.2	122.8	149.3	164.4	168.3	160.7	146.0	134.7	126.0
77.5°	60.8	63.8	70.4	81.8	99.1	112.6	118.1	117.2	107.2	100.6	92.5
80°	48.7	50.3	53.6	58.5	71.4	85.0	88.7	88.7	81.7	79.0	70.8
82.5°	37.0	38.2	40.1	42.8	48.9	60.7	64.9	65.8	61.3	57.8	51.4
85°	21.1	20.5	21.6	23.2	24.4	27.6	34.1	35.1	34.1	29.8	28.1
87.5°	11.7	11.0	10.2	9.3	9.5	9.5	11.0	12.7	11.5	10.8	10.3
90°	21.9	16.3	12.2	9.8	8.2	6.5	3.3	0.8	3.3	6.5	8.2
92.5°	81.2	55.4	36.9	29.3	23.7	20.2	14.3	9.9	14.3	20.2	23.7
95°	187.9	117.2	79.7	60.3	47.2	39.9	31.7	28.5	31.7	39.9	47.2
97.5°	253.2	154.6	107.5	85.4	70.4	59.4	50.8	46.4	50.8	59.4	70.4
100°	266.9	167.6	124.5	101.7	85.4	72.4	65.1	62.6	65.1	72.4	85.4
102.5°	267.6	179.4	139.5	116.7	99.8	86.7	79.4	77.6	79.4	86.7	99.8
105°	271.7	199.3	161.1	138.4	120.4	108.2	102.6	99.3	102.6	108.2	120.4
107.5°	283.0	219.9	182.8	159.8	142.1	130.9	125.3	122.7	125.3	130.9	142.1
110°	292.1	233.5	197.7	174.1	157.0	146.4	141.6	138.4	141.6	146.4	157.0





TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	301.9	246.5	212.1	187.8	171.4	161.4	155.9	152.6	155.9	161.4	171.4
115°	316.5	266.9	231.9	209.9	193.6	183.9	179.0	175.0	179.0	183.9	193.6
117.5°	332.2	285.6	253.2	230.4	214.8	206.2	201.3	198.0	201.3	206.2	214.8
120°	342.6	298.6	266.9	244.1	227.8	220.5	215.6	212.4	215.6	220.5	227.8
122.5°	351.6	311.0	281.2	257.8	241.5	233.5	228.6	226.1	228.6	233.5	241.5
125°	366.2	329.5	300.3	277.4	261.2	251.4	246.5	244.1	246.5	251.4	261.2
127.5°	379.7	346.8	318.3	294.9	279.2	268.5	261.7	258.4	261.7	268.5	279.2
130°	388.2	357.2	328.7	306.0	289.7	278.3	270.1	266.9	270.1	278.3	289.7
132.5°	396.6	366.3	339.2	316.3	299.5	287.4	278.6	274.7	278.6	287.4	299.5
135°	407.6	379.2	353.1	330.4	311.6	299.5	289.7	286.4	289.7	299.5	311.6
137.5°	416.1	389.6	363.9	342.8	324.2	311.1	301.4	297.5	301.4	311.1	324.2
140°	420.7	395.4	371.0	349.9	332.0	318.9	309.2	306.0	309.2	318.9	332.0
142.5°	424.6	400.0	376.3	356.4	339.2	326.1	317.0	314.4	317.0	326.1	339.2
145°	429.7	406.8	384.9	367.0	350.7	338.5	330.4	327.1	330.4	338.5	350.7
147.5°	432.4	412.4	391.8	375.8	362.2	351.0	343.2	340.8	343.2	351.0	362.2
150°	433.7	415.0	396.2	381.6	369.4	358.8	352.3	349.9	352.3	358.8	369.4
152.5°	434.3	417.6	400.8	387.5	375.9	366.6	360.1	359.0	360.1	366.6	375.9
155°	435.3	421.5	407.6	395.4	386.5	377.6	372.7	371.9	372.7	377.6	386.5
157.5°	435.3	424.3	412.5	402.3	395.1	387.3	383.4	382.6	383.4	387.3	395.1
160°	435.3	425.6	415.8	406.8	400.3	393.8	390.6	389.8	390.6	393.8	400.3
162.5°	434.6	426.2	417.8	410.7	404.9	399.7	396.4	396.9	396.4	399.7	404.9
165°	432.9	427.2	419.9	415.0	410.9	406.0	404.4	405.2	404.4	406.0	410.9
167.5°	431.8	427.1	421.7	418.6	415.6	412.5	411.1	412.1	411.1	412.5	415.6
170°	430.5	426.4	422.3	419.9	418.2	415.8	415.0	416.6	415.0	415.8	418.2
172.5°	428.5	425.7	423.0	421.2	420.2	417.8	418.2	419.2	418.2	417.8	420.2
175°	426.4	424.8	423.1	422.3	422.3	420.7	421.5	422.3	421.5	420.7	422.3
177.5°	425.1	423.8	423.1	423.1	423.1	421.8	422.5	423.8	422.5	421.8	423.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1534.8	1531.8	1526.2	1517.5	1512.3	1503.2	1497.1	1500.6	1501.5	1500.6	1499.7
5°	1493.5	1482.2	1466.6	1451.4	1437.3	1422.2	1413.5	1409.7	1402.2	1397.8	1395.7
7.5°	1443.7	1424.2	1401.9	1375.6	1353.2	1329.7	1317.7	1311.7	1296.2	1287.8	1280.4
10°	1406.5	1375.7	1353.5	1318.8	1297.8	1266.9	1245.9	1246.3	1225.2	1213.3	1204.7
12.5°	1365.4	1331.5	1294.6	1263.5	1234.1	1209.3	1184.0	1173.6	1151.3	1139.8	1116.4
15°	1297.2	1257.8	1218.8	1176.6	1146.8	1108.4	1071.6	1026.7	990.5	959.1	950.5
17.5°	1222.8	1173.9	1134.8	1085.2	1034.3	969.7	927.1	901.0	879.1	862.6	850.3
20°	1171.7	1121.9	1080.3	1005.7	936.9	893.2	861.8	841.7	819.0	801.2	791.4
22.5°	1118.0	1066.1	1009.3	926.0	872.5	837.3	809.3	786.4	770.9	757.0	748.1
25°	1041.9	985.0	891.5	834.1	790.8	754.1	734.6	720.6	704.3	685.4	676.7
27.5°	961.4	871.1	803.9	761.2	719.9	696.0	678.5	657.5	642.9	634.5	625.4
30°	901.2	810.9	758.4	711.9	682.7	656.2	635.6	623.7	609.7	595.1	589.1
32.5°	834.1	762.0	711.7	672.9	643.3	620.7	604.5	585.2	575.0	566.1	553.6
35°	750.8	696.2	650.2	618.9	590.8	572.3	553.4	542.0	523.7	516.1	511.2
37.5°	680.3	632.9	598.6	565.5	543.2	522.9	511.3	493.3	485.3	474.7	464.5
40°	640.5	593.9	561.0	533.9	509.1	493.9	479.3	464.7	452.8	447.9	435.5
42.5°	599.8	562.0	529.0	499.3	482.7	466.6	448.2	437.4	425.1	417.2	409.5
45°	543.6	510.1	482.0	457.6	439.3	422.5	410.6	392.7	385.7	370.0	363.5
47.5°	494.3	463.2	436.3	413.2	395.3	384.3	366.9	352.9	341.7	332.1	323.7
50°	459.3	433.3	407.3	386.8	370.6	354.9	337.0	330.0	312.7	307.8	303.0
52.5°	427.2	402.6	378.8	358.7	342.4	327.2	311.4	302.3	290.6	285.8	282.2
55°	382.5	358.7	335.9	318.0	301.8	286.2	276.5	265.1	259.7	255.8	251.5
57.5°	337.5	316.0	298.6	280.5	264.2	251.8	240.5	233.7	228.0	223.1	217.9
60°	308.9	288.3	272.6	255.8	239.1	228.9	220.1	212.1	205.5	198.0	195.8
62.5°	278.6	260.7	246.2	229.9	215.3	205.9	197.6	190.0	182.2	171.1	168.1
65°	236.9	222.9	207.7	194.2	181.2	172.0	160.1	151.5	148.2	147.2	146.6
67.5°	199.3	186.0	173.0	159.1	147.3	138.8	132.7	131.4	129.1	128.5	127.0
70°	174.1	161.8	148.8	135.7	124.4	122.8	120.7	118.5	115.8	114.7	113.6
72.5°	151.6	138.8	125.8	115.4	110.6	108.5	106.3	104.2	102.3	101.3	100.6
75°	116.3	104.4	95.7	92.0	89.3	87.6	84.4	82.8	81.7	80.1	79.5
77.5°	83.7	77.0	73.1	70.7	67.8	66.1	64.2	62.6	61.5	61.1	60.3
80°	63.8	60.6	57.9	54.6	53.6	51.4	50.9	49.2	49.7	48.2	48.2
82.5°	49.6	45.4	43.1	41.7	40.6	38.8	38.3	37.5	37.7	36.4	36.4
85°	25.4	24.4	23.2	22.2	22.2	20.5	21.1	20.5	20.5	19.5	18.9
87.5°	10.2	10.2	10.2	11.3	12.3	12.0	11.8	11.3	10.9	11.3	11.0
90°	9.8	12.2	16.3	21.9	26.8	27.6	26.8	26.0	24.4	26.0	26.8
92.5°	29.3	36.9	55.4	81.2	104.3	105.7	89.4	70.9	60.9	54.1	49.0
95°	60.3	79.7	117.2	187.9	282.3	318.9	279.1	213.2	163.5	129.4	111.5
97.5°	85.4	107.5	154.6	253.2	410.1	544.5	571.2	497.5	407.0	318.9	260.2
100°	101.7	124.5	167.6	266.9	442.6	642.8	760.0	742.9	642.0	530.5	432.1
102.5°	116.7	139.5	179.4	267.6	430.3	646.0	830.3	903.7	880.9	799.4	695.0
105°	138.4	161.1	199.3	271.7	406.0	602.9	819.4	988.6	1080.6	1091.2	1064.3
107.5°	159.8	182.8	219.9	283.0	394.0	556.8	748.0	927.5	1065.9	1150.6	1189.9
110°	174.1	197.7	233.5	292.1	391.4	534.6	703.0	874.7	1020.3	1124.5	1191.2



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	187.8	212.1	246.5	301.9	392.0	520.2	671.8	826.6	966.4	1077.7	1154.1
115°	209.9	231.9	266.9	316.5	395.4	504.5	633.1	767.3	892.6	999.2	1083.0
117.5°	230.4	253.2	285.6	332.2	401.3	496.8	608.6	722.7	832.7	929.4	1008.0
120°	244.1	266.9	298.6	342.6	405.2	492.3	595.7	700.6	801.5	887.7	961.8
122.5°	257.8	281.2	311.0	351.6	409.8	489.7	584.6	683.0	775.4	857.1	924.1
125°	277.4	300.3	329.5	366.2	416.6	484.9	568.8	657.5	741.3	812.9	873.9
127.5°	294.9	318.3	346.8	379.7	423.6	482.2	554.2	632.3	708.1	775.6	831.9
130°	306.0	328.7	357.2	388.2	428.8	480.9	544.4	616.0	685.9	750.2	804.0
132.5°	316.3	339.2	366.3	396.6	434.0	480.2	536.5	600.3	665.1	724.1	774.6
135°	330.4	353.1	379.2	407.6	440.2	479.2	525.6	578.5	632.3	685.9	731.5
137.5°	342.8	363.9	389.6	416.1	445.7	479.1	518.0	561.1	606.0	648.7	688.4
140°	349.9	371.0	395.4	420.7	448.3	478.4	513.5	550.1	589.1	626.6	662.3
142.5°	356.4	376.3	400.0	424.6	450.3	478.4	508.9	541.0	574.1	606.3	636.3
145°	367.0	384.9	406.8	429.7	452.4	476.8	502.9	528.1	555.0	580.2	603.7
147.5°	375.8	391.8	412.4	432.4	453.1	473.9	496.7	518.1	539.3	559.0	576.3
150°	381.6	396.2	415.0	433.7	452.4	472.0	491.5	511.0	528.9	546.0	560.6
152.5°	387.5	400.8	417.6	434.3	451.1	468.7	486.9	503.9	520.4	534.9	547.6
155°	395.4	407.6	421.5	435.3	449.1	463.0	478.4	493.9	507.0	519.1	528.1
157.5°	402.3	412.5	424.3	435.3	445.4	457.1	470.5	482.3	493.3	503.5	510.5
160°	406.8	415.8	425.6	435.3	443.4	453.2	464.6	475.2	484.1	493.1	498.8
162.5°	410.7	417.8	426.2	434.6	441.5	450.0	459.4	468.1	475.6	483.3	487.7
165°	415.0	419.9	427.2	432.9	437.7	443.4	450.8	457.3	463.0	468.7	472.0
167.5°	418.6	421.7	427.1	431.8	434.0	437.7	442.3	447.0	451.4	455.3	458.3
170°	419.9	422.3	426.4	430.5	432.1	434.5	437.7	441.8	444.3	447.5	449.1
172.5°	421.2	423.0	425.7	428.5	429.5	430.6	433.3	435.9	437.7	440.3	441.3
175°	422.3	423.1	424.8	426.4	425.6	426.4	427.2	429.7	430.5	431.3	432.1
177.5°	423.1	423.1	423.8	425.1	423.8	423.1	423.8	425.1	425.1	425.7	425.7
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1495.0	1495.8	1494.5	1495.4	1494.5	1495.8	1495.0	1499.7	1500.6	1501.5	1500.6
5°	1392.9	1386.5	1385.4	1383.8	1385.4	1386.5	1392.9	1395.7	1397.8	1402.2	1409.7
7.5°	1271.1	1270.2	1267.5	1263.7	1267.5	1270.2	1271.1	1280.4	1287.8	1296.2	1311.7
10°	1192.8	1190.1	1189.6	1185.8	1189.6	1190.1	1192.8	1204.7	1213.3	1225.2	1246.3
12.5°	1101.1	1083.6	1081.8	1072.4	1081.8	1083.6	1101.1	1116.4	1139.8	1151.3	1173.6
15°	937.5	934.3	923.4	916.4	923.4	934.3	937.5	950.5	959.1	990.5	1026.7
17.5°	844.0	833.4	830.1	828.5	830.1	833.4	844.0	850.3	862.6	879.1	901.0
20°	783.8	774.1	772.5	771.4	772.5	774.1	783.8	791.4	801.2	819.0	841.7
22.5°	742.3	732.1	727.9	724.6	727.9	732.1	742.3	748.1	757.0	770.9	786.4
25°	671.3	667.6	665.4	664.3	665.4	667.6	671.3	676.7	685.4	704.3	720.6
27.5°	615.8	607.5	605.8	603.1	605.8	607.5	615.8	625.4	634.5	642.9	657.5
30°	584.2	581.6	577.7	574.5	577.7	581.6	584.2	589.1	595.1	609.7	623.7
32.5°	547.0	544.8	541.4	539.9	541.4	544.8	547.0	553.6	566.1	575.0	585.2
35°	505.8	498.2	495.0	490.1	495.0	498.2	505.8	511.2	516.1	523.7	542.0
37.5°	462.2	458.2	453.6	455.3	453.6	458.2	462.2	464.5	474.7	485.3	493.3
40°	428.4	425.7	424.7	424.1	424.7	425.7	428.4	435.5	447.9	452.8	464.7
42.5°	401.6	394.1	391.3	391.2	391.3	394.1	401.6	409.5	417.2	425.1	437.4
45°	360.9	353.8	348.9	349.4	348.9	353.8	360.9	363.5	370.0	385.7	392.7
47.5°	319.0	318.9	315.8	316.8	315.8	318.9	319.0	323.7	332.1	341.7	352.9
50°	299.1	295.9	293.8	294.2	293.8	295.9	299.1	303.0	307.8	312.7	330.0
52.5°	280.1	277.3	275.6	277.9	275.6	277.3	280.1	282.2	285.8	290.6	302.3
55°	248.8	245.6	245.1	244.5	245.1	245.6	248.8	251.5	255.8	259.7	265.1
57.5°	213.9	211.7	208.5	207.1	208.5	211.7	213.9	217.9	223.1	228.0	233.7
60°	188.8	184.5	179.0	178.6	179.0	184.5	188.8	195.8	198.0	205.5	212.1
62.5°	165.8	165.0	163.9	163.8	163.9	165.0	165.8	168.1	171.1	182.2	190.0
65°	145.5	145.0	145.5	146.0	145.5	145.0	145.5	146.6	147.2	148.2	151.5
67.5°	126.8	125.8	124.8	125.3	124.8	125.8	126.8	127.0	128.5	129.1	131.4
70°	112.5	111.9	111.5	111.5	111.5	111.9	112.5	113.6	114.7	115.8	118.5
72.5°	98.7	98.6	98.0	97.6	98.0	98.6	98.7	100.6	101.3	102.3	104.2
75°	79.0	77.9	77.9	77.9	77.9	77.9	79.0	79.5	80.1	81.7	82.8
77.5°	60.2	59.6	59.1	58.6	59.1	59.6	60.2	60.3	61.1	61.5	62.6
80°	47.6	47.0	46.6	46.6	46.6	47.0	47.6	48.2	48.2	49.7	49.2
82.5°	36.4	35.8	35.7	35.3	35.7	35.8	36.4	36.4	36.4	37.7	37.5
85°	19.5	20.0	19.5	20.5	19.5	20.0	19.5	18.9	19.5	20.5	20.5
87.5°	11.0	10.6	11.0	10.6	11.0	10.6	11.0	11.0	11.3	10.9	11.3
90°	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.0	24.4	26.0
92.5°	48.3	45.7	46.4	45.1	46.4	45.7	48.3	49.0	54.1	60.9	70.9
95°	100.9	94.4	92.0	92.8	92.0	94.4	100.9	111.5	129.4	163.5	213.2
97.5°	221.4	201.3	189.4	182.6	189.4	201.3	221.4	260.2	318.9	407.0	497.5
100°	364.5	329.5	306.0	291.3	306.0	329.5	364.5	432.1	530.5	642.0	742.9
102.5°	621.7	561.9	532.5	512.7	532.5	561.9	621.7	695.0	799.4	880.9	903.7
105°	1013.8	963.4	928.4	917.0	928.4	963.4	1013.8	1064.3	1091.2	1080.6	988.6
107.5°	1196.3	1193.5	1186.5	1171.4	1186.5	1193.5	1196.3	1189.9	1150.6	1065.9	927.5
110°	1226.2	1241.7	1249.0	1248.2	1249.0	1241.7	1226.2	1191.2	1124.5	1020.3	874.7



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1202.8	1228.7	1242.5	1246.9	1242.5	1228.7	1202.8	1154.1	1077.7	966.4	826.6
115°	1140.8	1178.2	1199.4	1206.7	1199.4	1178.2	1140.8	1083.0	999.2	892.6	767.3
117.5°	1066.9	1106.4	1128.8	1134.9	1128.8	1106.4	1066.9	1008.0	929.4	832.7	722.7
120°	1018.7	1057.0	1080.6	1088.8	1080.6	1057.0	1018.7	961.8	887.7	801.5	700.6
122.5°	975.1	1012.7	1033.7	1040.6	1033.7	1012.7	975.1	924.1	857.1	775.4	683.0
125°	921.1	952.0	972.3	978.8	972.3	952.0	921.1	873.9	812.9	741.3	657.5
127.5°	873.1	902.0	919.7	924.9	919.7	902.0	873.1	831.9	775.6	708.1	632.3
130°	843.8	871.5	887.7	894.2	887.7	871.5	843.8	804.0	750.2	685.9	616.0
132.5°	813.8	841.6	856.5	862.3	856.5	841.6	813.8	774.6	724.1	665.1	600.3
135°	766.5	793.4	808.0	811.2	808.0	793.4	766.5	731.5	685.9	632.3	578.5
137.5°	720.3	743.4	756.3	761.2	756.3	743.4	720.3	688.4	648.7	606.0	561.1
140°	688.4	709.6	721.8	726.6	721.8	709.6	688.4	662.3	626.6	589.1	550.1
142.5°	661.0	680.3	691.1	692.1	691.1	680.3	661.0	636.3	606.3	574.1	541.0
145°	623.3	637.2	645.2	647.7	645.2	637.2	623.3	603.7	580.2	555.0	528.1
147.5°	592.4	603.4	608.9	610.4	608.9	603.4	592.4	576.3	559.0	539.3	518.1
150°	572.8	582.6	587.5	588.3	587.5	582.6	572.8	560.6	546.0	528.9	511.0
152.5°	557.2	565.7	569.2	569.4	569.2	565.7	557.2	547.6	534.9	520.4	503.9
155°	537.0	542.7	546.0	544.4	546.0	542.7	537.0	528.1	519.1	507.0	493.9
157.5°	516.8	521.5	523.0	523.0	523.0	521.5	516.8	510.5	503.5	493.3	482.3
160°	504.5	508.6	509.4	509.4	509.4	508.6	504.5	498.8	493.1	484.1	475.2
162.5°	493.4	496.2	497.0	496.4	497.0	496.2	493.4	487.7	483.3	475.6	468.1
165°	475.2	478.4	478.4	477.6	478.4	478.4	475.2	472.0	468.7	463.0	457.3
167.5°	459.7	461.5	461.4	460.4	461.4	461.5	459.7	458.3	455.3	451.4	447.0
170°	450.0	452.4	451.6	450.0	451.6	452.4	450.0	449.1	447.5	444.3	441.8
172.5°	442.1	443.3	442.5	441.5	442.5	443.3	442.1	441.3	440.3	437.7	435.9
175°	432.1	432.9	432.1	430.5	432.1	432.9	432.1	432.1	431.3	430.5	429.7
177.5°	425.7	425.7	425.1	423.8	425.1	425.7	425.7	425.7	425.7	425.1	425.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1497.1	1503.2	1512.3	1517.5	1526.2	1531.8	1534.8	1540.4	1543.4	1554.3	1565.5
5°	1413.5	1422.2	1437.3	1451.4	1466.6	1482.2	1493.5	1506.6	1518.5	1539.0	1560.6
7.5°	1317.7	1329.7	1353.2	1375.6	1401.9	1424.2	1443.7	1465.9	1485.7	1515.2	1545.8
10°	1245.9	1266.9	1297.8	1318.8	1353.5	1375.7	1406.5	1430.9	1458.4	1497.4	1532.0
12.5°	1184.0	1209.3	1234.1	1263.5	1294.6	1331.5	1365.4	1396.6	1429.5	1469.7	1510.3
15°	1071.6	1108.4	1146.8	1176.6	1218.8	1257.8	1297.2	1339.4	1379.4	1427.6	1480.6
17.5°	927.1	969.7	1034.3	1085.2	1134.8	1173.9	1222.8	1273.8	1321.0	1379.1	1438.1
20°	861.8	893.2	936.9	1005.7	1080.3	1121.9	1171.7	1228.0	1282.1	1345.3	1408.7
22.5°	809.3	837.3	872.5	926.0	1009.3	1066.1	1118.0	1175.2	1238.0	1302.5	1372.7
25°	734.6	754.1	790.8	834.1	891.5	985.0	1041.9	1099.2	1167.4	1236.6	1316.7
27.5°	678.5	696.0	719.9	761.2	803.9	871.1	961.4	1023.9	1091.8	1169.8	1252.9
30°	635.6	656.2	682.7	711.9	758.4	810.9	901.2	973.7	1040.8	1120.9	1209.6
32.5°	604.5	620.7	643.3	672.9	711.7	762.0	834.1	922.2	987.6	1072.0	1164.6
35°	553.4	572.3	590.8	618.9	650.2	696.2	750.8	845.0	909.9	993.2	1086.2
37.5°	511.3	522.9	543.2	565.5	598.6	632.9	680.3	764.7	834.9	916.7	1011.9
40°	479.3	493.9	509.1	533.9	561.0	593.9	640.5	703.3	783.8	863.9	956.9
42.5°	448.2	466.6	482.7	499.3	529.0	562.0	599.8	653.1	735.4	811.1	901.6
45°	410.6	422.5	439.3	457.6	482.0	510.1	543.6	590.2	669.2	734.6	819.5
47.5°	366.9	384.3	395.3	413.2	436.3	463.2	494.3	534.6	598.5	659.8	738.7
50°	337.0	354.9	370.6	386.8	407.3	433.3	459.3	498.2	549.6	614.0	687.5
52.5°	311.4	327.2	342.4	358.7	378.8	402.6	427.2	461.5	505.5	564.7	636.1
55°	276.5	286.2	301.8	318.0	335.9	358.7	382.5	411.2	449.0	498.8	556.7
57.5°	240.5	251.8	264.2	280.5	298.6	316.0	337.5	363.4	393.3	438.3	487.9
60°	220.1	228.9	239.1	255.8	272.6	288.3	308.9	330.5	358.7	397.6	439.8
62.5°	197.6	205.9	215.3	229.9	246.2	260.7	278.6	301.5	325.3	360.9	397.8
65°	160.1	172.0	181.2	194.2	207.7	222.9	236.9	255.4	276.5	304.6	337.5
67.5°	132.7	138.8	147.3	159.1	173.0	186.0	199.3	213.7	232.0	253.7	279.9
70°	120.7	122.8	124.4	135.7	148.8	161.8	174.1	187.7	203.4	221.3	243.9
72.5°	106.3	108.5	110.6	115.4	125.8	138.8	151.6	161.8	176.6	191.4	209.8
75°	84.4	87.6	89.3	92.0	95.7	104.4	116.3	126.0	134.7	146.0	160.7
77.5°	64.2	66.1	67.8	70.7	73.1	77.0	83.7	92.5	100.6	107.2	117.2
80°	50.9	51.4	53.6	54.6	57.9	60.6	63.8	70.8	79.0	81.7	88.7
82.5°	38.3	38.8	40.6	41.7	43.1	45.4	49.6	51.4	57.8	61.3	65.8
85°	21.1	20.5	22.2	22.2	23.2	24.4	25.4	28.1	29.8	34.1	35.1
87.5°	11.8	12.0	12.3	11.3	10.2	10.2	10.2	10.3	10.8	11.5	12.7
90°	26.8	27.6	26.8	21.9	16.3	12.2	9.8	8.2	6.5	3.3	0.8
92.5°	89.4	105.7	104.3	81.2	55.4	36.9	29.3	23.7	20.2	14.3	9.9
95°	279.1	318.9	282.3	187.9	117.2	79.7	60.3	47.2	39.9	31.7	28.5
97.5°	571.2	544.5	410.1	253.2	154.6	107.5	85.4	70.4	59.4	50.8	46.4
100°	760.0	642.8	442.6	266.9	167.6	124.5	101.7	85.4	72.4	65.1	62.6
102.5°	830.3	646.0	430.3	267.6	179.4	139.5	116.7	99.8	86.7	79.4	77.6
105°	819.4	602.9	406.0	271.7	199.3	161.1	138.4	120.4	108.2	102.6	99.3
107.5°	748.0	556.8	394.0	283.0	219.9	182.8	159.8	142.1	130.9	125.3	122.7
110°	703.0	534.6	391.4	292.1	233.5	197.7	174.1	157.0	146.4	141.6	138.4



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	671.8	520.2	392.0	301.9	246.5	212.1	187.8	171.4	161.4	155.9	152.6
115°	633.1	504.5	395.4	316.5	266.9	231.9	209.9	193.6	183.9	179.0	175.0
117.5°	608.6	496.8	401.3	332.2	285.6	253.2	230.4	214.8	206.2	201.3	198.0
120°	595.7	492.3	405.2	342.6	298.6	266.9	244.1	227.8	220.5	215.6	212.4
122.5°	584.6	489.7	409.8	351.6	311.0	281.2	257.8	241.5	233.5	228.6	226.1
125°	568.8	484.9	416.6	366.2	329.5	300.3	277.4	261.2	251.4	246.5	244.1
127.5°	554.2	482.2	423.6	379.7	346.8	318.3	294.9	279.2	268.5	261.7	258.4
130°	544.4	480.9	428.8	388.2	357.2	328.7	306.0	289.7	278.3	270.1	266.9
132.5°	536.5	480.2	434.0	396.6	366.3	339.2	316.3	299.5	287.4	278.6	274.7
135°	525.6	479.2	440.2	407.6	379.2	353.1	330.4	311.6	299.5	289.7	286.4
137.5°	518.0	479.1	445.7	416.1	389.6	363.9	342.8	324.2	311.1	301.4	297.5
140°	513.5	478.4	448.3	420.7	395.4	371.0	349.9	332.0	318.9	309.2	306.0
142.5°	508.9	478.4	450.3	424.6	400.0	376.3	356.4	339.2	326.1	317.0	314.4
145°	502.9	476.8	452.4	429.7	406.8	384.9	367.0	350.7	338.5	330.4	327.1
147.5°	496.7	473.9	453.1	432.4	412.4	391.8	375.8	362.2	351.0	343.2	340.8
150°	491.5	472.0	452.4	433.7	415.0	396.2	381.6	369.4	358.8	352.3	349.9
152.5°	486.9	468.7	451.1	434.3	417.6	400.8	387.5	375.9	366.6	360.1	359.0
155°	478.4	463.0	449.1	435.3	421.5	407.6	395.4	386.5	377.6	372.7	371.9
157.5°	470.5	457.1	445.4	435.3	424.3	412.5	402.3	395.1	387.3	383.4	382.6
160°	464.6	453.2	443.4	435.3	425.6	415.8	406.8	400.3	393.8	390.6	389.8
162.5°	459.4	450.0	441.5	434.6	426.2	417.8	410.7	404.9	399.7	396.4	396.9
165°	450.8	443.4	437.7	432.9	427.2	419.9	415.0	410.9	406.0	404.4	405.2
167.5°	442.3	437.7	434.0	431.8	427.1	421.7	418.6	415.6	412.5	411.1	412.1
170°	437.7	434.5	432.1	430.5	426.4	422.3	419.9	418.2	415.8	415.0	416.6
172.5°	433.3	430.6	429.5	428.5	425.7	423.0	421.2	420.2	417.8	418.2	419.2
175°	427.2	426.4	425.6	426.4	424.8	423.1	422.3	422.3	420.7	421.5	422.3
177.5°	423.8	423.1	423.8	425.1	423.8	423.1	423.1	423.1	421.8	422.5	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1565.9	1567.2	1575.9	1579.8	1587.6	1590.6	1594.1	1593.3	1593.3	1595.0	1607.1
5°	1569.3	1580.1	1596.4	1612.1	1627.2	1640.2	1648.9	1657.5	1660.8	1676.4	1690.5
7.5°	1563.7	1583.6	1610.5	1634.3	1663.0	1685.4	1704.1	1720.8	1732.3	1755.1	1778.5
10°	1556.3	1584.5	1614.8	1645.6	1685.1	1714.8	1745.1	1768.4	1776.0	1810.0	1829.5
12.5°	1541.6	1579.2	1617.8	1657.7	1696.3	1737.3	1770.7	1793.9	1820.6	1851.1	1887.1
15°	1519.6	1562.8	1613.2	1664.5	1719.7	1769.4	1805.2	1845.8	1874.9	1908.5	1939.8
17.5°	1487.8	1543.6	1607.5	1667.0	1730.9	1784.3	1833.4	1872.3	1892.9	1912.0	1916.7
20°	1462.7	1522.8	1598.0	1668.3	1732.2	1793.8	1842.5	1874.9	1880.4	1880.9	1852.3
22.5°	1435.5	1503.3	1582.0	1654.0	1730.4	1799.0	1836.9	1850.7	1829.3	1792.6	1737.2
25°	1385.4	1463.9	1555.3	1637.4	1720.8	1785.7	1798.7	1774.3	1699.2	1620.2	1520.1
27.5°	1331.1	1419.3	1517.3	1608.7	1697.5	1737.6	1709.7	1621.9	1486.5	1368.7	1226.0
30°	1291.3	1390.2	1486.5	1588.8	1671.0	1688.3	1624.0	1494.7	1336.7	1159.3	1017.0
32.5°	1245.9	1349.6	1455.4	1561.1	1629.9	1613.0	1506.7	1347.5	1162.3	987.9	853.5
35°	1180.9	1288.0	1402.2	1508.2	1552.0	1479.0	1320.0	1112.7	923.4	760.6	668.1
37.5°	1106.0	1222.5	1341.2	1438.6	1435.5	1313.8	1097.1	883.3	724.1	627.9	562.0
40°	1052.7	1170.6	1298.9	1381.0	1345.9	1187.4	952.6	750.8	634.5	557.7	509.6
42.5°	1001.7	1120.0	1247.3	1312.7	1251.6	1056.7	822.8	664.7	568.8	508.8	469.8
45°	914.8	1039.8	1157.6	1193.9	1084.6	869.8	665.4	550.7	486.9	442.5	415.5
47.5°	829.8	952.8	1060.4	1061.0	913.2	705.4	561.3	476.6	422.1	387.8	368.1
50°	777.9	894.7	985.0	971.0	803.3	627.5	502.0	429.0	383.5	357.0	336.5
52.5°	719.5	832.8	911.1	871.1	710.3	552.2	448.7	387.4	349.8	326.8	308.3
55°	634.5	735.2	790.4	729.8	579.4	459.3	379.2	331.1	303.0	283.5	267.7
57.5°	551.1	634.1	668.9	598.3	477.2	380.8	320.8	284.6	256.7	242.8	234.6
60°	498.8	569.6	593.9	516.1	414.9	333.2	284.0	250.5	229.9	220.7	212.6
62.5°	447.3	505.2	515.2	443.8	361.7	291.7	249.4	221.0	207.4	198.6	190.9
65°	371.1	412.8	407.9	350.6	286.2	231.5	200.7	183.4	173.1	160.7	147.2
67.5°	305.5	330.9	315.6	272.6	218.4	179.9	159.8	146.7	134.0	122.1	119.0
70°	264.0	278.6	262.4	222.9	179.0	150.9	134.7	119.0	111.5	108.8	103.9
72.5°	224.2	229.3	211.7	177.9	145.7	125.0	109.2	100.4	96.3	94.0	90.9
75°	168.3	164.4	149.3	122.8	101.2	87.1	82.3	79.0	76.3	74.1	72.5
77.5°	118.1	112.6	99.1	81.8	70.4	63.8	60.8	59.1	57.8	56.7	55.0
80°	88.7	85.0	71.4	58.5	53.6	50.3	48.7	46.6	46.6	45.4	43.8
82.5°	64.9	60.7	48.9	42.8	40.1	38.2	37.0	35.7	35.3	35.5	34.3
85°	34.1	27.6	24.4	23.2	21.6	20.5	21.1	20.0	20.0	20.0	19.5
87.5°	11.0	9.5	9.5	9.3	10.2	11.0	11.7	12.7	13.3	12.7	13.0
90°	3.3	6.5	8.2	9.8	12.2	16.3	21.9	26.8	27.6	26.8	26.0
92.5°	14.3	20.2	23.7	29.3	36.9	55.4	81.2	104.3	105.7	89.4	70.9
95°	31.7	39.9	47.2	60.3	79.7	117.2	187.9	282.3	318.9	279.1	213.2
97.5°	50.8	59.4	70.4	85.4	107.5	154.6	253.2	410.1	544.5	571.2	497.5
100°	65.1	72.4	85.4	101.7	124.5	167.6	266.9	442.6	642.8	760.0	742.9
102.5°	79.4	86.7	99.8	116.7	139.5	179.4	267.6	430.3	646.0	830.3	903.7
105°	102.6	108.2	120.4	138.4	161.1	199.3	271.7	406.0	602.9	819.4	988.6
107.5°	125.3	130.9	142.1	159.8	182.8	219.9	283.0	394.0	556.8	748.0	927.5
110°	141.6	146.4	157.0	174.1	197.7	233.5	292.1	391.4	534.6	703.0	874.7





TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	155.9	161.4	171.4	187.8	212.1	246.5	301.9	392.0	520.2	671.8	826.6
115°	179.0	183.9	193.6	209.9	231.9	266.9	316.5	395.4	504.5	633.1	767.3
117.5°	201.3	206.2	214.8	230.4	253.2	285.6	332.2	401.3	496.8	608.6	722.7
120°	215.6	220.5	227.8	244.1	266.9	298.6	342.6	405.2	492.3	595.7	700.6
122.5°	228.6	233.5	241.5	257.8	281.2	311.0	351.6	409.8	489.7	584.6	683.0
125°	246.5	251.4	261.2	277.4	300.3	329.5	366.2	416.6	484.9	568.8	657.5
127.5°	261.7	268.5	279.2	294.9	318.3	346.8	379.7	423.6	482.2	554.2	632.3
130°	270.1	278.3	289.7	306.0	328.7	357.2	388.2	428.8	480.9	544.4	616.0
132.5°	278.6	287.4	299.5	316.3	339.2	366.3	396.6	434.0	480.2	536.5	600.3
135°	289.7	299.5	311.6	330.4	353.1	379.2	407.6	440.2	479.2	525.6	578.5
137.5°	301.4	311.1	324.2	342.8	363.9	389.6	416.1	445.7	479.1	518.0	561.1
140°	309.2	318.9	332.0	349.9	371.0	395.4	420.7	448.3	478.4	513.5	550.1
142.5°	317.0	326.1	339.2	356.4	376.3	400.0	424.6	450.3	478.4	508.9	541.0
145°	330.4	338.5	350.7	367.0	384.9	406.8	429.7	452.4	476.8	502.9	528.1
147.5°	343.2	351.0	362.2	375.8	391.8	412.4	432.4	453.1	473.9	496.7	518.1
150°	352.3	358.8	369.4	381.6	396.2	415.0	433.7	452.4	472.0	491.5	511.0
152.5°	360.1	366.6	375.9	387.5	400.8	417.6	434.3	451.1	468.7	486.9	503.9
155°	372.7	377.6	386.5	395.4	407.6	421.5	435.3	449.1	463.0	478.4	493.9
157.5°	383.4	387.3	395.1	402.3	412.5	424.3	435.3	445.4	457.1	470.5	482.3
160°	390.6	393.8	400.3	406.8	415.8	425.6	435.3	443.4	453.2	464.6	475.2
162.5°	396.4	399.7	404.9	410.7	417.8	426.2	434.6	441.5	450.0	459.4	468.1
165°	404.4	406.0	410.9	415.0	419.9	427.2	432.9	437.7	443.4	450.8	457.3
167.5°	411.1	412.5	415.6	418.6	421.7	427.1	431.8	434.0	437.7	442.3	447.0
170°	415.0	415.8	418.2	419.9	422.3	426.4	430.5	432.1	434.5	437.7	441.8
172.5°	418.2	417.8	420.2	421.2	423.0	425.7	428.5	429.5	430.6	433.3	435.9
175°	421.5	420.7	422.3	422.3	423.1	424.8	426.4	425.6	426.4	427.2	429.7
177.5°	422.5	421.8	423.1	423.1	423.1	423.8	425.1	423.8	423.1	423.8	425.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1611.4	1617.1	1619.6	1619.6	1622.7	1621.4	1620.1
5°	1704.1	1714.3	1716.4	1726.2	1733.2	1731.0	1732.2
7.5°	1796.1	1812.7	1829.0	1836.5	1837.6	1841.9	1843.6
10°	1852.8	1866.3	1891.7	1887.9	1906.9	1917.7	1899.8
12.5°	1907.3	1925.6	1943.3	1948.1	1958.8	1962.3	1955.3
15°	1956.6	1966.4	1967.5	1964.8	1968.0	1965.3	1955.0
17.5°	1910.6	1894.8	1862.7	1847.5	1835.6	1817.9	1810.7
20°	1834.4	1787.9	1733.7	1712.1	1686.7	1637.0	1648.9
22.5°	1670.0	1616.9	1562.8	1499.7	1469.5	1422.3	1419.4
25°	1414.1	1322.7	1222.1	1151.7	1110.6	1063.6	1042.9
27.5°	1099.4	984.3	901.9	860.1	822.1	784.8	783.3
30°	892.6	806.0	742.2	706.5	683.2	667.6	670.8
32.5°	752.4	693.1	650.0	620.4	603.2	591.3	591.2
35°	615.1	574.5	546.9	534.4	522.0	513.4	513.9
37.5°	526.4	502.0	486.7	472.9	465.1	460.9	458.5
40°	480.9	460.9	449.0	440.9	434.4	428.4	427.4
42.5°	445.0	428.4	416.5	410.2	404.1	399.9	398.8
45°	394.9	381.4	370.6	363.5	360.9	357.0	357.0
47.5°	351.3	338.0	329.5	325.1	320.5	318.0	317.9
50°	321.9	311.6	304.0	301.3	297.5	295.9	295.4
52.5°	295.5	287.8	282.4	280.5	278.9	276.9	277.2
55°	259.7	255.4	253.2	251.5	248.8	245.6	247.8
57.5°	229.5	225.8	220.0	214.8	212.4	210.1	211.0
60°	208.3	200.7	193.1	187.2	185.6	180.7	180.7
62.5°	181.4	170.8	161.5	158.2	156.5	154.3	153.8
65°	139.6	135.3	133.1	130.9	129.8	129.8	128.7
67.5°	115.7	113.9	111.5	111.0	109.9	109.6	109.3
70°	102.2	100.0	99.0	98.5	97.3	97.9	96.3
72.5°	89.3	87.6	87.3	85.9	85.3	85.4	84.1
75°	70.4	70.4	69.8	69.2	68.2	67.6	68.2
77.5°	54.1	54.2	53.2	53.2	53.0	53.2	52.6
80°	43.3	43.8	43.3	42.7	42.2	42.7	42.2
82.5°	34.2	33.4	33.3	33.2	33.1	32.8	32.7
85°	19.5	20.0	19.5	18.9	18.9	18.9	19.5
87.5°	12.2	12.6	12.7	12.7	12.7	12.7	12.3
90°	24.4	26.0	26.8	26.8	26.8	26.8	26.8
92.5°	60.9	54.1	49.0	48.3	45.7	46.4	45.1
95°	163.5	129.4	111.5	100.9	94.4	92.0	92.8
97.5°	407.0	318.9	260.2	221.4	201.3	189.4	182.6
100°	642.0	530.5	432.1	364.5	329.5	306.0	291.3
102.5°	880.9	799.4	695.0	621.7	561.9	532.5	512.7
105°	1080.6	1091.2	1064.3	1013.8	963.4	928.4	917.0
107.5°	1065.9	1150.6	1189.9	1196.3	1193.5	1186.5	1171.4
110°	1020.3	1124.5	1191.2	1226.2	1241.7	1249.0	1248.2



TEST NUMBER: P331725-930

CATALOG NUMBER: S122RDIP-S865D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	966.4	1077.7	1154.1	1202.8	1228.7	1242.5	1246.9
115°	892.6	999.2	1083.0	1140.8	1178.2	1199.4	1206.7
117.5°	832.7	929.4	1008.0	1066.9	1106.4	1128.8	1134.9
120°	801.5	887.7	961.8	1018.7	1057.0	1080.6	1088.8
122.5°	775.4	857.1	924.1	975.1	1012.7	1033.7	1040.6
125°	741.3	812.9	873.9	921.1	952.0	972.3	978.8
127.5°	708.1	775.6	831.9	873.1	902.0	919.7	924.9
130°	685.9	750.2	804.0	843.8	871.5	887.7	894.2
132.5°	665.1	724.1	774.6	813.8	841.6	856.5	862.3
135°	632.3	685.9	731.5	766.5	793.4	808.0	811.2
137.5°	606.0	648.7	688.4	720.3	743.4	756.3	761.2
140°	589.1	626.6	662.3	688.4	709.6	721.8	726.6
142.5°	574.1	606.3	636.3	661.0	680.3	691.1	692.1
145°	555.0	580.2	603.7	623.3	637.2	645.2	647.7
147.5°	539.3	559.0	576.3	592.4	603.4	608.9	610.4
150°	528.9	546.0	560.6	572.8	582.6	587.5	588.3
152.5°	520.4	534.9	547.6	557.2	565.7	569.2	569.4
155°	507.0	519.1	528.1	537.0	542.7	546.0	544.4
157.5°	493.3	503.5	510.5	516.8	521.5	523.0	523.0
160°	484.1	493.1	498.8	504.5	508.6	509.4	509.4
162.5°	475.6	483.3	487.7	493.4	496.2	497.0	496.4
165°	463.0	468.7	472.0	475.2	478.4	478.4	477.6
167.5°	451.4	455.3	458.3	459.7	461.5	461.4	460.4
170°	444.3	447.5	449.1	450.0	452.4	451.6	450.0
172.5°	437.7	440.3	441.3	442.1	443.3	442.5	441.5
175°	430.5	431.3	432.1	432.1	432.9	432.1	430.5
177.5°	425.1	425.7	425.7	425.7	425.7	425.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)