

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331250

Luminaire Tested: **S122DIP-S290D530U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331250
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D530U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3196.2 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26	23
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9544	9544	9544	9544
5°	10699	9606	8512	9606
10°	12260	9527	7366	9527
15°	13563	9352	6509	9352
20°	13357	9165	5933	9165
25°	12043	8915	5569	8915
30°	9952	8516	5302	8516
35°	7253	8099	5113	8099
40°	5794	7609	5008	7609
45°	5062	7040	4866	7040
50°	4760	6488	4770	6488
55°	4386	5928	4642	5928
60°	4020	5331	4447	5331
65°	3664	4798	4252	4798
70°	3323	4277	3970	4277
75°	2951	3699	3512	3699
80°	2538	3059	2827	3059
85°	2279	2279	1686	2279



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	1.8
10°-20°	163.7	5.1
20°-30°	237.5	7.4
30°-40°	250.6	7.8
40°-50°	221.9	6.9
50°-60°	177.1	5.5
60°-70°	120.4	3.8
70°-80°	61.7	1.9
80°-90°	17.6	0.5
90°-100°	42.8	1.3
100°-110°	133.0	4.2
110°-120°	227.3	7.1
120°-130°	298.9	9.4
130°-140°	335.5	10.5
140°-150°	329.0	10.3
150°-160°	275.9	8.6
160°-170°	183.0	5.7
170°-180°	64.0	2.0
0°-30°	457.5	14.3
0°-40°	708.1	22.2
0°-60°	1107.1	34.6
0°-90°	1306.7	40.9
90°-120°	403.1	12.6
90°-150°	1366.6	42.8
90°-180°	1889.0	59.1
0°-180°	3196.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	591	591	591	591	591	
5°	660	593	525	593	660	66
15°	811	560	389	560	811	224
25°	676	500	313	500	676	306
35°	368	411	259	411	368	239
45°	222	308	213	308	222	174
55°	156	211	165	211	156	140
65°	96	126	111	126	96	95
75°	47	59	56	59	47	51
85°	12	12	9	12	12	14
90°	19	1	19	1	19	9
95°	35	30	35	30	35	39
105°	127	123	127	123	127	133
115°	228	228	228	228	228	225
125°	333	332	333	332	333	297
135°	434	429	434	429	434	334
145°	527	521	527	521	527	329
155°	600	596	600	596	600	276
165°	649	648	649	648	649	183
175°	672	675	672	675	672	64
180°	676	676	676	676	676	



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	618.3	618.5	618.9	616.0	615.6	615.6	613.1	610.9	608.3	604.9	605.3
5°	660.1	662.6	663.5	660.8	656.7	656.3	652.4	646.1	640.1	635.4	632.0
7.5°	710.0	711.0	708.8	705.2	702.2	696.7	689.5	682.5	672.6	663.6	656.9
10°	747.8	749.2	745.3	740.1	735.8	729.4	719.0	708.3	695.4	682.9	672.9
12.5°	776.5	779.9	774.9	774.3	766.9	758.1	745.7	740.3	722.1	704.7	693.9
15°	811.4	811.2	811.7	807.3	801.9	800.5	787.4	773.0	747.4	737.1	719.4
17.5°	801.3	804.8	806.4	806.3	806.2	805.3	801.1	792.1	779.2	762.6	742.2
20°	777.4	781.9	782.6	787.8	790.8	794.6	796.2	793.7	785.8	771.9	754.2
22.5°	740.3	741.6	743.7	751.8	758.2	767.9	772.9	781.4	778.3	771.5	756.7
25°	676.0	673.8	681.7	685.8	700.6	716.0	727.2	739.4	750.3	756.9	752.6
27.5°	598.9	595.5	607.4	618.3	630.2	647.0	664.3	684.8	701.8	723.2	730.5
30°	533.8	535.9	547.2	558.8	577.0	600.6	620.2	642.6	667.0	690.8	707.4
32.5°	463.7	471.5	478.7	496.5	512.5	538.8	567.5	595.6	625.9	653.0	678.7
35°	368.0	377.1	387.1	400.0	422.5	448.6	476.6	514.5	555.9	592.9	623.3
37.5°	309.8	308.3	314.0	323.4	341.6	362.7	394.9	432.3	481.0	524.5	567.5
40°	274.9	274.0	278.0	286.7	300.5	316.0	344.2	377.1	422.3	475.5	526.6
42.5°	250.9	251.4	253.7	259.8	269.3	282.0	303.1	331.1	372.5	422.6	477.5
45°	221.7	223.3	225.8	228.8	234.2	244.7	256.5	276.5	309.2	351.0	405.0
47.5°	200.7	200.8	203.3	205.9	209.1	215.0	224.7	237.2	260.3	294.3	340.8
50°	189.5	187.9	189.7	191.7	195.1	199.2	205.6	217.4	232.8	260.3	299.2
52.5°	175.6	175.7	177.3	178.1	181.1	185.2	191.0	199.2	213.2	234.7	266.6
55°	155.8	157.0	157.9	159.2	162.0	164.9	169.5	174.9	185.8	201.9	225.6
57.5°	137.2	137.6	138.5	141.1	142.8	145.5	149.8	154.8	161.9	173.8	191.6
60°	124.5	124.5	126.3	127.4	129.7	132.4	135.8	140.6	147.0	156.7	171.1
62.5°	112.9	112.7	113.4	115.3	117.0	119.5	122.9	127.0	133.0	141.7	153.4
65°	95.9	95.4	96.8	97.2	99.0	101.5	104.3	108.6	113.4	119.7	130.2
67.5°	79.5	80.1	80.8	81.6	82.6	85.3	87.1	90.1	94.2	99.5	106.5
70°	70.4	70.4	70.4	71.1	72.5	73.8	75.6	78.1	82.0	86.5	92.9
72.5°	60.2	61.0	61.7	61.3	63.0	63.8	66.0	67.4	71.1	74.0	79.6
75°	47.3	47.3	47.3	48.4	49.1	49.7	51.1	52.5	54.3	57.9	60.9
77.5°	35.3	35.2	35.4	35.7	36.4	37.2	37.6	38.8	40.5	42.2	44.7
80°	27.3	27.7	27.9	28.4	28.4	28.8	29.1	30.7	31.8	32.9	34.5
82.5°	21.1	21.2	21.2	21.3	21.5	21.8	22.4	22.9	23.3	24.2	25.4
85°	12.3	12.0	12.0	12.5	12.3	12.3	12.7	13.2	13.2	13.4	14.1
87.5°	8.6	8.6	8.7	8.5	8.5	8.7	8.7	8.6	8.8	9.1	8.7
90°	19.4	19.3	19.1	19.0	18.9	18.9	19.2	19.5	19.7	20.0	17.2
92.5°	18.5	18.5	18.4	18.4	18.4	18.3	18.3	18.2	18.2	18.1	17.5
95°	35.4	35.6	35.9	36.1	36.4	36.5	36.5	36.5	36.5	36.5	36.2
97.5°	61.2	61.3	61.3	61.3	61.3	61.4	61.4	61.4	61.4	61.4	60.9
100°	78.1	78.3	78.4	78.5	78.6	78.7	78.7	78.7	78.7	78.7	78.3
102.5°	97.3	97.4	97.5	97.7	97.8	97.8	97.7	97.6	97.5	97.4	96.9
105°	126.6	126.6	126.6	126.6	126.6	126.5	126.2	126.0	125.7	125.5	125.2
107.5°	154.2	154.8	155.4	155.9	156.5	156.8	156.7	156.6	156.5	156.4	156.4
110°	175.6	176.0	176.4	176.8	177.2	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.2	196.4	196.7	197.0	197.3	197.6	197.9	198.2	198.5	198.8	198.9
115°	228.1	228.5	228.9	229.2	229.6	229.9	230.0	230.1	230.3	230.4	230.6
117.5°	258.5	258.9	259.3	259.7	260.1	260.4	260.7	261.0	261.3	261.6	262.3
120°	280.0	280.4	280.8	281.1	281.5	281.7	281.7	281.7	281.7	281.7	282.7
122.5°	301.0	301.3	301.5	301.8	302.1	302.4	302.7	303.0	303.3	303.6	304.3
125°	333.0	333.1	333.3	333.4	333.5	333.8	334.2	334.5	334.9	335.3	335.7
127.5°	362.2	362.6	363.0	363.4	363.8	364.3	364.7	365.2	365.6	366.1	366.6
130°	383.2	383.7	384.2	384.7	385.2	385.6	385.9	386.1	386.4	386.6	386.9
132.5°	403.3	403.7	404.1	404.5	404.9	405.4	405.9	406.5	407.1	407.6	407.6
135°	434.5	434.9	435.3	435.7	436.0	436.3	436.4	436.6	436.7	436.8	436.6
137.5°	462.8	463.3	463.8	464.3	464.8	465.1	465.2	465.3	465.4	465.5	465.2
140°	482.4	482.9	483.4	483.9	484.5	484.7	484.7	484.7	484.7	484.7	484.1
142.5°	500.2	500.7	501.2	501.7	502.2	502.4	502.3	502.2	502.1	502.0	501.6
145°	526.9	527.4	527.9	528.4	528.9	529.1	529.0	528.9	528.7	528.6	527.9
147.5°	550.7	551.2	551.7	552.2	552.7	552.8	552.5	552.2	551.9	551.7	551.1
150°	566.3	566.6	567.0	567.4	567.8	567.8	567.4	567.0	566.6	566.3	565.7
152.5°	580.9	581.3	581.8	582.3	582.8	582.8	582.3	581.8	581.3	580.9	580.2
155°	600.5	600.8	601.2	601.6	602.0	601.9	601.2	600.6	600.0	599.3	598.9
157.5°	617.3	618.0	618.6	619.2	619.8	619.7	618.8	617.9	617.1	616.2	616.0
160°	627.8	628.3	628.9	629.4	629.9	629.7	629.0	628.2	627.5	626.7	626.6
162.5°	637.0	637.6	638.2	638.8	639.4	639.3	638.4	637.5	636.7	635.8	635.7
165°	648.9	649.6	650.2	650.8	651.5	651.3	650.5	649.6	648.7	647.8	647.8
167.5°	658.7	659.4	660.1	660.7	661.4	661.3	660.4	659.5	658.6	657.7	657.7
170°	663.8	664.5	665.3	666.0	666.8	666.7	665.9	665.0	664.1	663.2	663.3
172.5°	667.9	668.6	669.4	670.2	670.9	670.8	670.0	669.1	668.2	667.3	667.4
175°	672.3	673.1	673.8	674.6	675.4	675.3	674.4	673.5	672.6	671.7	672.0
177.5°	674.4	675.0	675.6	676.2	676.8	676.8	676.2	675.6	675.0	674.4	674.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	606.5	605.1	604.2	600.9	598.0	595.1	594.2	594.5	590.5	586.7	585.1
5°	630.2	625.6	621.3	615.2	607.9	599.9	595.9	592.7	584.7	576.1	571.1
7.5°	651.3	644.8	636.5	625.0	614.4	601.9	593.9	586.9	575.3	563.1	555.6
10°	664.2	655.4	644.7	630.6	617.7	602.4	591.8	581.1	567.5	552.9	543.8
12.5°	675.3	663.4	652.9	634.8	619.5	600.4	587.8	572.7	558.4	541.1	532.2
15°	701.7	679.7	659.7	639.2	620.4	593.8	579.7	559.5	540.7	519.3	509.1
17.5°	722.1	697.3	665.9	639.9	617.9	588.4	567.8	543.6	521.3	496.9	483.0
20°	733.7	705.3	671.5	640.6	614.3	580.6	558.1	533.4	507.3	479.8	464.8
22.5°	740.6	710.8	677.3	637.9	607.0	574.3	546.0	518.8	492.4	462.7	447.0
25°	742.8	715.6	680.1	635.6	597.9	560.9	526.8	500.4	468.4	440.7	417.8
27.5°	732.0	712.5	678.4	631.3	587.4	544.1	506.1	476.3	442.5	412.4	389.3
30°	718.7	707.4	674.2	627.0	579.0	532.5	490.7	456.8	423.2	392.8	369.1
32.5°	698.2	695.8	666.6	620.8	570.1	517.8	474.5	440.3	403.0	373.1	350.6
35°	657.9	668.8	650.4	607.0	553.4	496.8	450.0	410.9	372.3	343.7	322.6
37.5°	603.8	630.9	626.1	586.8	530.7	474.0	422.3	381.5	344.7	315.8	295.1
40°	566.5	601.1	606.1	571.3	514.8	456.4	401.6	361.0	325.1	298.7	277.8
42.5°	526.6	566.9	580.6	552.8	497.3	437.8	383.1	341.0	305.4	279.8	261.3
45°	459.6	512.9	537.7	521.8	468.2	407.3	351.0	308.3	276.0	251.9	237.6
47.5°	396.9	455.2	488.5	482.9	435.8	375.5	319.8	278.8	247.4	228.2	215.4
50°	352.6	412.5	452.7	454.6	412.5	352.8	296.9	258.3	229.4	211.5	201.0
52.5°	314.0	371.3	415.1	424.8	386.5	329.2	276.4	237.9	212.5	196.0	186.7
55°	263.7	312.1	360.7	378.5	347.8	293.3	244.4	210.6	186.7	175.4	167.2
57.5°	219.3	259.6	304.5	324.1	305.2	258.5	212.7	183.3	164.0	154.0	147.7
60°	195.8	227.6	267.6	291.0	274.6	233.1	193.1	165.1	149.2	140.4	134.5
62.5°	174.0	202.2	236.0	257.4	248.5	209.3	173.5	148.8	135.1	126.8	122.5
65°	143.6	165.8	192.0	211.7	205.8	176.1	146.7	125.6	114.7	108.1	104.7
67.5°	118.2	134.3	152.4	169.7	165.0	143.9	120.4	103.9	95.8	90.1	88.0
70°	102.2	114.5	130.6	144.5	140.6	123.4	104.7	90.6	83.6	78.8	76.8
72.5°	87.0	97.0	109.4	120.7	118.1	103.7	88.2	77.6	72.1	67.7	66.1
75°	65.7	73.4	80.9	88.4	87.7	76.6	67.5	59.3	55.0	51.6	50.9
77.5°	48.5	52.8	57.9	62.3	61.1	54.7	47.6	42.9	39.8	37.5	37.1
80°	37.0	39.5	43.2	46.3	44.8	42.0	36.3	32.9	30.7	28.4	27.5
82.5°	26.9	29.3	31.5	33.3	32.0	29.5	26.0	23.7	22.3	20.8	20.4
85°	14.1	15.4	16.4	16.8	16.4	14.8	13.2	12.3	11.1	10.4	10.2
87.5°	8.3	7.8	7.2	7.1	6.3	6.0	5.0	4.1	4.2	4.4	4.3
90°	14.4	11.6	8.8	6.7	5.1	3.6	2.1	0.6	2.1	3.6	5.1
92.5°	16.8	16.2	15.5	14.6	13.5	12.4	11.3	10.2	11.3	12.4	13.5
95°	36.0	35.7	35.5	34.7	33.5	32.2	30.9	29.7	30.9	32.2	33.5
97.5°	60.4	59.9	59.4	58.6	57.5	56.4	55.3	54.2	55.3	56.4	57.5
100°	77.9	77.6	77.2	76.5	75.5	74.4	73.4	72.4	73.4	74.4	75.5
102.5°	96.4	96.0	95.5	94.8	94.0	93.2	92.4	91.6	92.4	93.2	94.0
105°	124.9	124.7	124.4	124.1	123.7	123.4	123.0	122.6	123.0	123.4	123.7
107.5°	156.4	156.4	156.4	156.1	155.5	155.0	154.4	153.9	154.4	155.0	155.5
110°	177.3	177.3	177.3	177.0	176.2	175.4	174.7	173.9	174.7	175.4	176.2



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	199.0	199.1	199.2	198.9	198.1	197.3	196.6	195.8	196.6	197.3	198.1
115°	230.9	231.1	231.4	231.1	230.4	229.6	228.9	228.1	228.9	229.6	230.4
117.5°	263.0	263.8	264.5	264.3	263.3	262.3	261.3	260.3	261.3	262.3	263.3
120°	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	282.7	283.7	284.7
122.5°	305.0	305.7	306.4	306.2	305.0	303.8	302.5	301.3	302.5	303.8	305.0
125°	336.1	336.4	336.8	336.4	335.3	334.2	333.0	331.9	333.0	334.2	335.3
127.5°	367.0	367.5	367.9	367.4	366.0	364.5	363.1	361.6	363.1	364.5	366.0
130°	387.1	387.4	387.6	386.9	385.3	383.6	382.0	380.4	382.0	383.6	385.3
132.5°	407.5	407.5	407.4	406.7	405.4	404.0	402.7	401.3	402.7	404.0	405.4
135°	436.3	436.0	435.8	435.0	433.6	432.2	430.8	429.4	430.8	432.2	433.6
137.5°	464.9	464.6	464.2	463.5	462.4	461.2	460.1	458.9	460.1	461.2	462.4
140°	483.4	482.8	482.2	481.3	480.1	479.0	477.9	476.7	477.9	479.0	480.1
142.5°	501.2	500.8	500.3	499.5	498.4	497.3	496.1	495.0	496.1	497.3	498.4
145°	527.1	526.3	525.6	524.8	523.9	523.0	522.1	521.2	522.1	523.0	523.9
147.5°	550.6	550.1	549.6	548.8	547.8	546.7	545.6	544.6	545.6	546.7	547.8
150°	565.2	564.7	564.2	563.6	562.8	562.1	561.3	560.6	561.3	562.1	562.8
152.5°	579.6	579.0	578.4	577.7	577.0	576.2	575.5	574.7	575.5	576.2	577.0
155°	598.6	598.2	597.8	597.4	597.0	596.7	596.3	595.9	596.3	596.7	597.0
157.5°	615.8	615.5	615.3	615.1	614.8	614.5	614.3	614.0	614.3	614.5	614.8
160°	626.4	626.3	626.2	626.0	625.7	625.5	625.2	625.0	625.2	625.5	625.7
162.5°	635.6	635.4	635.3	635.2	635.2	635.1	635.1	635.0	635.1	635.1	635.2
165°	647.8	647.8	647.8	647.9	648.0	648.1	648.2	648.4	648.2	648.1	648.0
167.5°	657.8	657.8	657.8	658.0	658.4	658.8	659.2	659.5	659.2	658.8	658.4
170°	663.4	663.6	663.7	664.0	664.3	664.7	665.1	665.5	665.1	664.7	664.3
172.5°	667.6	667.7	667.8	668.1	668.4	668.8	669.2	669.6	669.2	668.8	668.4
175°	672.3	672.5	672.8	673.1	673.5	673.8	674.2	674.6	674.2	673.8	673.5
177.5°	674.8	675.0	675.2	675.4	675.7	676.0	676.3	676.7	676.3	676.0	675.7
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	583.3	582.2	578.4	576.4	573.1	570.0	568.0	568.9	569.6	569.3	568.7
5°	566.5	562.2	555.6	550.0	545.9	538.4	535.2	533.6	532.2	530.7	529.1
7.5°	546.6	539.8	530.4	522.3	514.7	505.3	500.0	496.9	493.6	490.0	486.8
10°	532.5	522.9	512.9	501.6	492.5	484.1	476.6	471.6	467.0	462.7	459.6
12.5°	517.6	506.6	494.2	478.7	468.7	456.6	455.5	446.7	439.6	436.9	433.2
15°	493.9	478.4	462.7	444.3	436.4	425.5	418.7	411.8	405.7	401.4	400.3
17.5°	466.9	446.9	431.3	418.1	405.1	393.9	387.6	382.2	377.1	371.4	370.6
20°	446.4	429.1	412.1	400.5	387.1	375.7	368.0	362.6	358.2	354.8	351.9
22.5°	426.9	408.0	392.4	379.8	366.6	357.4	351.3	346.0	342.4	338.7	335.9
25°	395.7	381.0	363.9	349.6	338.7	332.8	327.8	323.3	321.0	318.5	315.3
27.5°	368.4	352.0	336.1	325.0	315.4	310.2	306.6	303.5	301.4	299.9	298.1
30°	349.2	332.6	320.1	309.2	301.2	296.0	293.7	291.9	289.4	288.5	287.6
32.5°	330.6	315.7	305.0	295.5	288.0	284.5	282.5	280.8	278.9	278.0	276.1
35°	304.4	291.9	281.5	276.2	270.1	267.1	265.6	263.3	261.5	260.6	260.3
37.5°	279.7	268.9	262.0	255.3	252.7	250.9	248.7	247.2	246.6	246.5	246.2
40°	263.7	254.9	248.7	243.3	242.2	239.4	237.6	236.3	236.3	236.5	236.3
42.5°	249.2	241.2	235.8	231.1	229.8	228.2	226.3	226.3	226.6	227.4	226.6
45°	227.2	221.5	217.6	215.4	212.9	211.3	211.0	211.7	211.9	212.2	212.9
47.5°	206.9	203.1	199.6	197.1	196.0	195.8	195.5	196.7	197.8	198.2	199.2
50°	194.9	190.6	187.6	186.0	185.1	184.7	185.1	186.5	187.4	188.5	189.2
52.5°	181.5	178.4	176.4	175.1	174.8	175.1	175.1	176.7	178.1	178.6	178.9
55°	162.9	160.6	160.2	158.1	159.0	158.8	159.9	160.8	162.2	163.6	163.8
57.5°	144.3	142.5	141.3	141.5	141.8	142.8	143.7	145.3	146.7	148.2	148.3
60°	132.0	131.1	130.4	130.4	130.8	132.2	133.3	134.9	135.8	136.8	137.4
62.5°	120.7	119.8	119.1	119.5	120.7	121.5	122.8	123.7	124.6	125.5	125.8
65°	102.9	102.5	103.1	103.6	103.8	104.9	106.5	107.2	108.1	108.6	110.2
67.5°	86.5	86.6	86.5	87.1	88.5	88.7	90.2	91.8	92.0	92.9	93.9
70°	75.4	75.9	76.3	76.8	77.9	78.4	79.5	80.2	81.1	81.8	82.5
72.5°	65.2	65.3	65.8	65.7	66.7	67.6	68.6	69.3	70.2	71.1	71.7
75°	50.2	50.2	50.7	50.9	52.0	53.2	52.9	53.4	54.3	55.2	55.7
77.5°	36.7	36.2	36.7	36.9	37.3	38.2	38.4	39.0	40.1	39.8	40.3
80°	27.9	27.3	27.9	28.2	28.2	29.3	29.3	29.8	30.4	29.8	30.4
82.5°	19.9	19.6	20.1	20.2	20.5	20.6	20.9	21.0	21.7	21.4	21.7
85°	10.0	9.8	10.0	9.8	10.0	10.2	10.2	10.0	10.0	10.4	9.8
87.5°	4.4	4.7	5.0	5.6	6.0	6.4	6.1	6.1	6.0	5.6	5.6
90°	6.7	8.8	11.6	14.4	17.2	20.0	19.7	19.5	19.2	18.9	18.9
92.5°	14.6	15.5	16.2	16.8	17.5	18.1	18.2	18.2	18.3	18.3	18.4
95°	34.7	35.5	35.7	36.0	36.2	36.5	36.5	36.5	36.5	36.5	36.4
97.5°	58.6	59.4	59.9	60.4	60.9	61.4	61.4	61.4	61.4	61.4	61.3
100°	76.5	77.2	77.6	77.9	78.3	78.7	78.7	78.7	78.7	78.7	78.6
102.5°	94.8	95.5	96.0	96.4	96.9	97.4	97.5	97.6	97.7	97.8	97.8
105°	124.1	124.4	124.7	124.9	125.2	125.5	125.7	126.0	126.2	126.5	126.6
107.5°	156.1	156.4	156.4	156.4	156.4	156.4	156.5	156.6	156.7	156.8	156.5
110°	177.0	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.2



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	198.9	199.2	199.1	199.0	198.9	198.8	198.5	198.2	197.9	197.6	197.3
115°	231.1	231.4	231.1	230.9	230.6	230.4	230.3	230.1	230.0	229.9	229.6
117.5°	264.3	264.5	263.8	263.0	262.3	261.6	261.3	261.0	260.7	260.4	260.1
120°	285.8	285.8	284.7	283.7	282.7	281.7	281.7	281.7	281.7	281.7	281.5
122.5°	306.2	306.4	305.7	305.0	304.3	303.6	303.3	303.0	302.7	302.4	302.1
125°	336.4	336.8	336.4	336.1	335.7	335.3	334.9	334.5	334.2	333.8	333.5
127.5°	367.4	367.9	367.5	367.0	366.6	366.1	365.6	365.2	364.7	364.3	363.8
130°	386.9	387.6	387.4	387.1	386.9	386.6	386.4	386.1	385.9	385.6	385.2
132.5°	406.7	407.4	407.5	407.5	407.6	407.6	407.1	406.5	405.9	405.4	404.9
135°	435.0	435.8	436.0	436.3	436.6	436.8	436.7	436.6	436.4	436.3	436.0
137.5°	463.5	464.2	464.6	464.9	465.2	465.5	465.4	465.3	465.2	465.1	464.8
140°	481.3	482.2	482.8	483.4	484.1	484.7	484.7	484.7	484.7	484.7	484.5
142.5°	499.5	500.3	500.8	501.2	501.6	502.0	502.1	502.2	502.3	502.4	502.2
145°	524.8	525.6	526.3	527.1	527.9	528.6	528.7	528.9	529.0	529.1	528.9
147.5°	548.8	549.6	550.1	550.6	551.1	551.7	551.9	552.2	552.5	552.8	552.7
150°	563.6	564.2	564.7	565.2	565.7	566.3	566.6	567.0	567.4	567.8	567.8
152.5°	577.7	578.4	579.0	579.6	580.2	580.9	581.3	581.8	582.3	582.8	582.8
155°	597.4	597.8	598.2	598.6	598.9	599.3	600.0	600.6	601.2	601.9	602.0
157.5°	615.1	615.3	615.5	615.8	616.0	616.2	617.1	617.9	618.8	619.7	619.8
160°	626.0	626.2	626.3	626.4	626.6	626.7	627.5	628.2	629.0	629.7	629.9
162.5°	635.2	635.3	635.4	635.6	635.7	635.8	636.7	637.5	638.4	639.3	639.4
165°	647.9	647.8	647.8	647.8	647.8	647.8	648.7	649.6	650.5	651.3	651.5
167.5°	658.0	657.8	657.8	657.8	657.7	657.7	658.6	659.5	660.4	661.3	661.4
170°	664.0	663.7	663.6	663.4	663.3	663.2	664.1	665.0	665.9	666.7	666.8
172.5°	668.1	667.8	667.7	667.6	667.4	667.3	668.2	669.1	670.0	670.8	670.9
175°	673.1	672.8	672.5	672.3	672.0	671.7	672.6	673.5	674.4	675.3	675.4
177.5°	675.4	675.2	675.0	674.8	674.6	674.4	675.0	675.6	676.2	676.8	676.8
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	566.9	566.5	566.5	564.9	566.5	566.5	566.9	568.7	569.3	569.6	568.9
5°	525.9	525.2	524.1	525.2	524.1	525.2	525.9	529.1	530.7	532.2	533.6
7.5°	485.3	482.6	482.2	479.5	482.2	482.6	485.3	486.8	490.0	493.6	496.9
10°	455.7	453.9	453.6	449.3	453.6	453.9	455.7	459.6	462.7	467.0	471.6
12.5°	433.2	428.8	429.7	427.2	429.7	428.8	433.2	433.2	436.9	439.6	446.7
15°	394.1	394.1	393.2	389.4	393.2	394.1	394.1	400.3	401.4	405.7	411.8
17.5°	366.1	365.6	363.5	364.6	363.5	365.6	366.1	370.6	371.4	377.1	382.2
20°	349.4	348.0	345.3	345.3	345.3	348.0	349.4	351.9	354.8	358.2	362.6
22.5°	333.6	333.5	330.6	331.5	330.6	333.5	333.6	335.9	338.7	342.4	346.0
25°	315.1	313.3	311.9	312.6	311.9	313.3	315.1	315.3	318.5	321.0	323.3
27.5°	297.5	296.5	296.4	294.6	296.4	296.5	297.5	298.1	299.9	301.4	303.5
30°	287.4	285.1	285.5	284.4	285.5	285.1	287.4	287.6	288.5	289.4	291.9
32.5°	275.7	274.9	274.5	273.5	274.5	274.9	275.7	276.1	278.0	278.9	280.8
35°	259.9	260.1	259.0	259.4	259.0	260.1	259.9	260.3	260.6	261.5	263.3
37.5°	246.0	246.7	246.2	246.3	246.2	246.7	246.0	246.2	246.5	246.6	247.2
40°	236.9	236.9	236.9	237.6	236.9	236.9	236.9	236.3	236.5	236.3	236.3
42.5°	228.2	227.8	227.5	227.4	227.5	227.8	228.2	226.6	227.4	226.6	226.3
45°	213.3	214.0	214.2	213.1	214.2	214.0	213.3	212.9	212.2	211.9	211.7
47.5°	199.8	199.9	199.8	200.8	199.8	199.9	199.8	199.2	198.2	197.8	196.7
50°	190.4	189.9	190.4	189.9	190.4	189.9	190.4	189.2	188.5	187.4	186.5
52.5°	180.4	180.5	180.2	180.1	180.2	180.5	180.4	178.9	178.6	178.1	176.7
55°	164.7	165.1	164.9	164.9	164.9	165.1	164.7	163.8	163.6	162.2	160.8
57.5°	148.5	148.9	149.2	148.2	149.2	148.9	148.5	148.3	148.2	146.7	145.3
60°	137.2	138.3	138.1	137.7	138.1	138.3	137.2	137.4	136.8	135.8	134.9
62.5°	126.8	127.3	127.2	127.1	127.2	127.3	126.8	125.8	125.5	124.6	123.7
65°	110.9	111.3	110.6	111.3	110.6	111.3	110.9	110.2	108.6	108.1	107.2
67.5°	93.6	93.8	94.3	94.6	94.3	93.8	93.6	93.9	92.9	92.0	91.8
70°	82.9	82.7	83.4	84.1	83.4	82.7	82.9	82.5	81.8	81.1	80.2
72.5°	71.6	72.1	71.9	72.4	71.9	72.1	71.6	71.7	71.1	70.2	69.3
75°	55.2	55.9	55.7	56.3	55.7	55.9	55.2	55.7	55.2	54.3	53.4
77.5°	39.9	40.0	39.9	40.3	39.9	40.0	39.9	40.3	39.8	40.1	39.0
80°	30.4	30.0	29.5	30.4	29.5	30.0	30.4	30.4	29.8	30.4	29.8
82.5°	21.2	21.4	21.0	21.0	21.0	21.4	21.2	21.7	21.4	21.7	21.0
85°	9.8	9.5	9.1	9.1	9.1	9.5	9.8	9.8	10.4	10.0	10.0
87.5°	5.6	5.5	5.5	5.3	5.5	5.5	5.6	5.6	5.6	6.0	6.1
90°	19.0	19.1	19.3	19.4	19.3	19.1	19.0	18.9	18.9	19.2	19.5
92.5°	18.4	18.4	18.5	18.5	18.5	18.4	18.4	18.4	18.3	18.3	18.2
95°	36.1	35.9	35.6	35.4	35.6	35.9	36.1	36.4	36.5	36.5	36.5
97.5°	61.3	61.3	61.3	61.2	61.3	61.3	61.3	61.3	61.4	61.4	61.4
100°	78.5	78.4	78.3	78.1	78.3	78.4	78.5	78.6	78.7	78.7	78.7
102.5°	97.7	97.5	97.4	97.3	97.4	97.5	97.7	97.8	97.8	97.7	97.6
105°	126.6	126.6	126.6	126.6	126.6	126.6	126.6	126.6	126.5	126.2	126.0
107.5°	155.9	155.4	154.8	154.2	154.8	155.4	155.9	156.5	156.8	156.7	156.6
110°	176.8	176.4	176.0	175.6	176.0	176.4	176.8	177.2	177.3	177.3	177.3



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	197.0	196.7	196.4	196.2	196.4	196.7	197.0	197.3	197.6	197.9	198.2
115°	229.2	228.9	228.5	228.1	228.5	228.9	229.2	229.6	229.9	230.0	230.1
117.5°	259.7	259.3	258.9	258.5	258.9	259.3	259.7	260.1	260.4	260.7	261.0
120°	281.1	280.8	280.4	280.0	280.4	280.8	281.1	281.5	281.7	281.7	281.7
122.5°	301.8	301.5	301.3	301.0	301.3	301.5	301.8	302.1	302.4	302.7	303.0
125°	333.4	333.3	333.1	333.0	333.1	333.3	333.4	333.5	333.8	334.2	334.5
127.5°	363.4	363.0	362.6	362.2	362.6	363.0	363.4	363.8	364.3	364.7	365.2
130°	384.7	384.2	383.7	383.2	383.7	384.2	384.7	385.2	385.6	385.9	386.1
132.5°	404.5	404.1	403.7	403.3	403.7	404.1	404.5	404.9	405.4	405.9	406.5
135°	435.7	435.3	434.9	434.5	434.9	435.3	435.7	436.0	436.3	436.4	436.6
137.5°	464.3	463.8	463.3	462.8	463.3	463.8	464.3	464.8	465.1	465.2	465.3
140°	483.9	483.4	482.9	482.4	482.9	483.4	483.9	484.5	484.7	484.7	484.7
142.5°	501.7	501.2	500.7	500.2	500.7	501.2	501.7	502.2	502.4	502.3	502.2
145°	528.4	527.9	527.4	526.9	527.4	527.9	528.4	528.9	529.1	529.0	528.9
147.5°	552.2	551.7	551.2	550.7	551.2	551.7	552.2	552.7	552.8	552.5	552.2
150°	567.4	567.0	566.6	566.3	566.6	567.0	567.4	567.8	567.8	567.4	567.0
152.5°	582.3	581.8	581.3	580.9	581.3	581.8	582.3	582.8	582.8	582.3	581.8
155°	601.6	601.2	600.8	600.5	600.8	601.2	601.6	602.0	601.9	601.2	600.6
157.5°	619.2	618.6	618.0	617.3	618.0	618.6	619.2	619.8	619.7	618.8	617.9
160°	629.4	628.9	628.3	627.8	628.3	628.9	629.4	629.9	629.7	629.0	628.2
162.5°	638.8	638.2	637.6	637.0	637.6	638.2	638.8	639.4	639.3	638.4	637.5
165°	650.8	650.2	649.6	648.9	649.6	650.2	650.8	651.5	651.3	650.5	649.6
167.5°	660.7	660.1	659.4	658.7	659.4	660.1	660.7	661.4	661.3	660.4	659.5
170°	666.0	665.3	664.5	663.8	664.5	665.3	666.0	666.8	666.7	665.9	665.0
172.5°	670.2	669.4	668.6	667.9	668.6	669.4	670.2	670.9	670.8	670.0	669.1
175°	674.6	673.8	673.1	672.3	673.1	673.8	674.6	675.4	675.3	674.4	673.5
177.5°	676.2	675.6	675.0	674.4	675.0	675.6	676.2	676.8	676.8	676.2	675.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	568.0	570.0	573.1	576.4	578.4	582.2	583.3	585.1	586.7	590.5	594.5
5°	535.2	538.4	545.9	550.0	555.6	562.2	566.5	571.1	576.1	584.7	592.7
7.5°	500.0	505.3	514.7	522.3	530.4	539.8	546.6	555.6	563.1	575.3	586.9
10°	476.6	484.1	492.5	501.6	512.9	522.9	532.5	543.8	552.9	567.5	581.1
12.5°	455.5	456.6	468.7	478.7	494.2	506.6	517.6	532.2	541.1	558.4	572.7
15°	418.7	425.5	436.4	444.3	462.7	478.4	493.9	509.1	519.3	540.7	559.5
17.5°	387.6	393.9	405.1	418.1	431.3	446.9	466.9	483.0	496.9	521.3	543.6
20°	368.0	375.7	387.1	400.5	412.1	429.1	446.4	464.8	479.8	507.3	533.4
22.5°	351.3	357.4	366.6	379.8	392.4	408.0	426.9	447.0	462.7	492.4	518.8
25°	327.8	332.8	338.7	349.6	363.9	381.0	395.7	417.8	440.7	468.4	500.4
27.5°	306.6	310.2	315.4	325.0	336.1	352.0	368.4	389.3	412.4	442.5	476.3
30°	293.7	296.0	301.2	309.2	320.1	332.6	349.2	369.1	392.8	423.2	456.8
32.5°	282.5	284.5	288.0	295.5	305.0	315.7	330.6	350.6	373.1	403.0	440.3
35°	265.6	267.1	270.1	276.2	281.5	291.9	304.4	322.6	343.7	372.3	410.9
37.5°	248.7	250.9	252.7	255.3	262.0	268.9	279.7	295.1	315.8	344.7	381.5
40°	237.6	239.4	242.2	243.3	248.7	254.9	263.7	277.8	298.7	325.1	361.0
42.5°	226.3	228.2	229.8	231.1	235.8	241.2	249.2	261.3	279.8	305.4	341.0
45°	211.0	211.3	212.9	215.4	217.6	221.5	227.2	237.6	251.9	276.0	308.3
47.5°	195.5	195.8	196.0	197.1	199.6	203.1	206.9	215.4	228.2	247.4	278.8
50°	185.1	184.7	185.1	186.0	187.6	190.6	194.9	201.0	211.5	229.4	258.3
52.5°	175.1	175.1	174.8	175.1	176.4	178.4	181.5	186.7	196.0	212.5	237.9
55°	159.9	158.8	159.0	158.1	160.2	160.6	162.9	167.2	175.4	186.7	210.6
57.5°	143.7	142.8	141.8	141.5	141.3	142.5	144.3	147.7	154.0	164.0	183.3
60°	133.3	132.2	130.8	130.4	130.4	131.1	132.0	134.5	140.4	149.2	165.1
62.5°	122.8	121.5	120.7	119.5	119.1	119.8	120.7	122.5	126.8	135.1	148.8
65°	106.5	104.9	103.8	103.6	103.1	102.5	102.9	104.7	108.1	114.7	125.6
67.5°	90.2	88.7	88.5	87.1	86.5	86.6	86.5	88.0	90.1	95.8	103.9
70°	79.5	78.4	77.9	76.8	76.3	75.9	75.4	76.8	78.8	83.6	90.6
72.5°	68.6	67.6	66.7	65.7	65.8	65.3	65.2	66.1	67.7	72.1	77.6
75°	52.9	53.2	52.0	50.9	50.7	50.2	50.2	50.9	51.6	55.0	59.3
77.5°	38.4	38.2	37.3	36.9	36.7	36.2	36.7	37.1	37.5	39.8	42.9
80°	29.3	29.3	28.2	28.2	27.9	27.3	27.9	27.5	28.4	30.7	32.9
82.5°	20.9	20.6	20.5	20.2	20.1	19.6	19.9	20.4	20.8	22.3	23.7
85°	10.2	10.2	10.0	9.8	10.0	9.8	10.0	10.2	10.4	11.1	12.3
87.5°	6.1	6.4	6.0	5.6	5.0	4.7	4.4	4.3	4.4	4.2	4.1
90°	19.7	20.0	17.2	14.4	11.6	8.8	6.7	5.1	3.6	2.1	0.6
92.5°	18.2	18.1	17.5	16.8	16.2	15.5	14.6	13.5	12.4	11.3	10.2
95°	36.5	36.5	36.2	36.0	35.7	35.5	34.7	33.5	32.2	30.9	29.7
97.5°	61.4	61.4	60.9	60.4	59.9	59.4	58.6	57.5	56.4	55.3	54.2
100°	78.7	78.7	78.3	77.9	77.6	77.2	76.5	75.5	74.4	73.4	72.4
102.5°	97.5	97.4	96.9	96.4	96.0	95.5	94.8	94.0	93.2	92.4	91.6
105°	125.7	125.5	125.2	124.9	124.7	124.4	124.1	123.7	123.4	123.0	122.6
107.5°	156.5	156.4	156.4	156.4	156.4	156.4	156.1	155.5	155.0	154.4	153.9
110°	177.3	177.3	177.3	177.3	177.3	177.3	177.0	176.2	175.4	174.7	173.9



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	198.5	198.8	198.9	199.0	199.1	199.2	198.9	198.1	197.3	196.6	195.8
115°	230.3	230.4	230.6	230.9	231.1	231.4	231.1	230.4	229.6	228.9	228.1
117.5°	261.3	261.6	262.3	263.0	263.8	264.5	264.3	263.3	262.3	261.3	260.3
120°	281.7	281.7	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7
122.5°	303.3	303.6	304.3	305.0	305.7	306.4	306.2	305.0	303.8	302.5	301.3
125°	334.9	335.3	335.7	336.1	336.4	336.8	336.4	335.3	334.2	333.0	331.9
127.5°	365.6	366.1	366.6	367.0	367.5	367.9	367.4	366.0	364.5	363.1	361.6
130°	386.4	386.6	386.9	387.1	387.4	387.6	386.9	385.3	383.6	382.0	380.4
132.5°	407.1	407.6	407.6	407.5	407.5	407.4	406.7	405.4	404.0	402.7	401.3
135°	436.7	436.8	436.6	436.3	436.0	435.8	435.0	433.6	432.2	430.8	429.4
137.5°	465.4	465.5	465.2	464.9	464.6	464.2	463.5	462.4	461.2	460.1	458.9
140°	484.7	484.7	484.1	483.4	482.8	482.2	481.3	480.1	479.0	477.9	476.7
142.5°	502.1	502.0	501.6	501.2	500.8	500.3	499.5	498.4	497.3	496.1	495.0
145°	528.7	528.6	527.9	527.1	526.3	525.6	524.8	523.9	523.0	522.1	521.2
147.5°	551.9	551.7	551.1	550.6	550.1	549.6	548.8	547.8	546.7	545.6	544.6
150°	566.6	566.3	565.7	565.2	564.7	564.2	563.6	562.8	562.1	561.3	560.6
152.5°	581.3	580.9	580.2	579.6	579.0	578.4	577.7	577.0	576.2	575.5	574.7
155°	600.0	599.3	598.9	598.6	598.2	597.8	597.4	597.0	596.7	596.3	595.9
157.5°	617.1	616.2	616.0	615.8	615.5	615.3	615.1	614.8	614.5	614.3	614.0
160°	627.5	626.7	626.6	626.4	626.3	626.2	626.0	625.7	625.5	625.2	625.0
162.5°	636.7	635.8	635.7	635.6	635.4	635.3	635.2	635.2	635.1	635.1	635.0
165°	648.7	647.8	647.8	647.8	647.8	647.8	647.9	648.0	648.1	648.2	648.4
167.5°	658.6	657.7	657.7	657.8	657.8	657.8	658.0	658.4	658.8	659.2	659.5
170°	664.1	663.2	663.3	663.4	663.6	663.7	664.0	664.3	664.7	665.1	665.5
172.5°	668.2	667.3	667.4	667.6	667.7	667.8	668.1	668.4	668.8	669.2	669.6
175°	672.6	671.7	672.0	672.3	672.5	672.8	673.1	673.5	673.8	674.2	674.6
177.5°	675.0	674.4	674.6	674.8	675.0	675.2	675.4	675.7	676.0	676.3	676.7
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	594.2	595.1	598.0	600.9	604.2	605.1	606.5	605.3	604.9	608.3	610.9
5°	595.9	599.9	607.9	615.2	621.3	625.6	630.2	632.0	635.4	640.1	646.1
7.5°	593.9	601.9	614.4	625.0	636.5	644.8	651.3	656.9	663.6	672.6	682.5
10°	591.8	602.4	617.7	630.6	644.7	655.4	664.2	672.9	682.9	695.4	708.3
12.5°	587.8	600.4	619.5	634.8	652.9	663.4	675.3	693.9	704.7	722.1	740.3
15°	579.7	593.8	620.4	639.2	659.7	679.7	701.7	719.4	737.1	747.4	773.0
17.5°	567.8	588.4	617.9	639.9	665.9	697.3	722.1	742.2	762.6	779.2	792.1
20°	558.1	580.6	614.3	640.6	671.5	705.3	733.7	754.2	771.9	785.8	793.7
22.5°	546.0	574.3	607.0	637.9	677.3	710.8	740.6	756.7	771.5	778.3	781.4
25°	526.8	560.9	597.9	635.6	680.1	715.6	742.8	752.6	756.9	750.3	739.4
27.5°	506.1	544.1	587.4	631.3	678.4	712.5	732.0	730.5	723.2	701.8	684.8
30°	490.7	532.5	579.0	627.0	674.2	707.4	718.7	707.4	690.8	667.0	642.6
32.5°	474.5	517.8	570.1	620.8	666.6	695.8	698.2	678.7	653.0	625.9	595.6
35°	450.0	496.8	553.4	607.0	650.4	668.8	657.9	623.3	592.9	555.9	514.5
37.5°	422.3	474.0	530.7	586.8	626.1	630.9	603.8	567.5	524.5	481.0	432.3
40°	401.6	456.4	514.8	571.3	606.1	601.1	566.5	526.6	475.5	422.3	377.1
42.5°	383.1	437.8	497.3	552.8	580.6	566.9	526.6	477.5	422.6	372.5	331.1
45°	351.0	407.3	468.2	521.8	537.7	512.9	459.6	405.0	351.0	309.2	276.5
47.5°	319.8	375.5	435.8	482.9	488.5	455.2	396.9	340.8	294.3	260.3	237.2
50°	296.9	352.8	412.5	454.6	452.7	412.5	352.6	299.2	260.3	232.8	217.4
52.5°	276.4	329.2	386.5	424.8	415.1	371.3	314.0	266.6	234.7	213.2	199.2
55°	244.4	293.3	347.8	378.5	360.7	312.1	263.7	225.6	201.9	185.8	174.9
57.5°	212.7	258.5	305.2	324.1	304.5	259.6	219.3	191.6	173.8	161.9	154.8
60°	193.1	233.1	274.6	291.0	267.6	227.6	195.8	171.1	156.7	147.0	140.6
62.5°	173.5	209.3	248.5	257.4	236.0	202.2	174.0	153.4	141.7	133.0	127.0
65°	146.7	176.1	205.8	211.7	192.0	165.8	143.6	130.2	119.7	113.4	108.6
67.5°	120.4	143.9	165.0	169.7	152.4	134.3	118.2	106.5	99.5	94.2	90.1
70°	104.7	123.4	140.6	144.5	130.6	114.5	102.2	92.9	86.5	82.0	78.1
72.5°	88.2	103.7	118.1	120.7	109.4	97.0	87.0	79.6	74.0	71.1	67.4
75°	67.5	76.6	87.7	88.4	80.9	73.4	65.7	60.9	57.9	54.3	52.5
77.5°	47.6	54.7	61.1	62.3	57.9	52.8	48.5	44.7	42.2	40.5	38.8
80°	36.3	42.0	44.8	46.3	43.2	39.5	37.0	34.5	32.9	31.8	30.7
82.5°	26.0	29.5	32.0	33.3	31.5	29.3	26.9	25.4	24.2	23.3	22.9
85°	13.2	14.8	16.4	16.8	16.4	15.4	14.1	14.1	13.4	13.2	13.2
87.5°	5.0	6.0	6.3	7.1	7.2	7.8	8.3	8.7	9.1	8.8	8.6
90°	2.1	3.6	5.1	6.7	8.8	11.6	14.4	17.2	20.0	19.7	19.5
92.5°	11.3	12.4	13.5	14.6	15.5	16.2	16.8	17.5	18.1	18.2	18.2
95°	30.9	32.2	33.5	34.7	35.5	35.7	36.0	36.2	36.5	36.5	36.5
97.5°	55.3	56.4	57.5	58.6	59.4	59.9	60.4	60.9	61.4	61.4	61.4
100°	73.4	74.4	75.5	76.5	77.2	77.6	77.9	78.3	78.7	78.7	78.7
102.5°	92.4	93.2	94.0	94.8	95.5	96.0	96.4	96.9	97.4	97.5	97.6
105°	123.0	123.4	123.7	124.1	124.4	124.7	124.9	125.2	125.5	125.7	126.0
107.5°	154.4	155.0	155.5	156.1	156.4	156.4	156.4	156.4	156.4	156.5	156.6
110°	174.7	175.4	176.2	177.0	177.3	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	196.6	197.3	198.1	198.9	199.2	199.1	199.0	198.9	198.8	198.5	198.2
115°	228.9	229.6	230.4	231.1	231.4	231.1	230.9	230.6	230.4	230.3	230.1
117.5°	261.3	262.3	263.3	264.3	264.5	263.8	263.0	262.3	261.6	261.3	261.0
120°	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	281.7	281.7
122.5°	302.5	303.8	305.0	306.2	306.4	305.7	305.0	304.3	303.6	303.3	303.0
125°	333.0	334.2	335.3	336.4	336.8	336.4	336.1	335.7	335.3	334.9	334.5
127.5°	363.1	364.5	366.0	367.4	367.9	367.5	367.0	366.6	366.1	365.6	365.2
130°	382.0	383.6	385.3	386.9	387.6	387.4	387.1	386.9	386.6	386.4	386.1
132.5°	402.7	404.0	405.4	406.7	407.4	407.5	407.5	407.6	407.6	407.1	406.5
135°	430.8	432.2	433.6	435.0	435.8	436.0	436.3	436.6	436.8	436.7	436.6
137.5°	460.1	461.2	462.4	463.5	464.2	464.6	464.9	465.2	465.5	465.4	465.3
140°	477.9	479.0	480.1	481.3	482.2	482.8	483.4	484.1	484.7	484.7	484.7
142.5°	496.1	497.3	498.4	499.5	500.3	500.8	501.2	501.6	502.0	502.1	502.2
145°	522.1	523.0	523.9	524.8	525.6	526.3	527.1	527.9	528.6	528.7	528.9
147.5°	545.6	546.7	547.8	548.8	549.6	550.1	550.6	551.1	551.7	551.9	552.2
150°	561.3	562.1	562.8	563.6	564.2	564.7	565.2	565.7	566.3	566.6	567.0
152.5°	575.5	576.2	577.0	577.7	578.4	579.0	579.6	580.2	580.9	581.3	581.8
155°	596.3	596.7	597.0	597.4	597.8	598.2	598.6	598.9	599.3	600.0	600.6
157.5°	614.3	614.5	614.8	615.1	615.3	615.5	615.8	616.0	616.2	617.1	617.9
160°	625.2	625.5	625.7	626.0	626.2	626.3	626.4	626.6	626.7	627.5	628.2
162.5°	635.1	635.1	635.2	635.2	635.3	635.4	635.6	635.7	635.8	636.7	637.5
165°	648.2	648.1	648.0	647.9	647.8	647.8	647.8	647.8	647.8	648.7	649.6
167.5°	659.2	658.8	658.4	658.0	657.8	657.8	657.8	657.7	657.7	658.6	659.5
170°	665.1	664.7	664.3	664.0	663.7	663.6	663.4	663.3	663.2	664.1	665.0
172.5°	669.2	668.8	668.4	668.1	667.8	667.7	667.6	667.4	667.3	668.2	669.1
175°	674.2	673.8	673.5	673.1	672.8	672.5	672.3	672.0	671.7	672.6	673.5
177.5°	676.3	676.0	675.7	675.4	675.2	675.0	674.8	674.6	674.4	675.0	675.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	613.1	615.6	615.6	616.0	618.9	618.5	618.3
5°	652.4	656.3	656.7	660.8	663.5	662.6	660.1
7.5°	689.5	696.7	702.2	705.2	708.8	711.0	710.0
10°	719.0	729.4	735.8	740.1	745.3	749.2	747.8
12.5°	745.7	758.1	766.9	774.3	774.9	779.9	776.5
15°	787.4	800.5	801.9	807.3	811.7	811.2	811.4
17.5°	801.1	805.3	806.2	806.3	806.4	804.8	801.3
20°	796.2	794.6	790.8	787.8	782.6	781.9	777.4
22.5°	772.9	767.9	758.2	751.8	743.7	741.6	740.3
25°	727.2	716.0	700.6	685.8	681.7	673.8	676.0
27.5°	664.3	647.0	630.2	618.3	607.4	595.5	598.9
30°	620.2	600.6	577.0	558.8	547.2	535.9	533.8
32.5°	567.5	538.8	512.5	496.5	478.7	471.5	463.7
35°	476.6	448.6	422.5	400.0	387.1	377.1	368.0
37.5°	394.9	362.7	341.6	323.4	314.0	308.3	309.8
40°	344.2	316.0	300.5	286.7	278.0	274.0	274.9
42.5°	303.1	282.0	269.3	259.8	253.7	251.4	250.9
45°	256.5	244.7	234.2	228.8	225.8	223.3	221.7
47.5°	224.7	215.0	209.1	205.9	203.3	200.8	200.7
50°	205.6	199.2	195.1	191.7	189.7	187.9	189.5
52.5°	191.0	185.2	181.1	178.1	177.3	175.7	175.6
55°	169.5	164.9	162.0	159.2	157.9	157.0	155.8
57.5°	149.8	145.5	142.8	141.1	138.5	137.6	137.2
60°	135.8	132.4	129.7	127.4	126.3	124.5	124.5
62.5°	122.9	119.5	117.0	115.3	113.4	112.7	112.9
65°	104.3	101.5	99.0	97.2	96.8	95.4	95.9
67.5°	87.1	85.3	82.6	81.6	80.8	80.1	79.5
70°	75.6	73.8	72.5	71.1	70.4	70.4	70.4
72.5°	66.0	63.8	63.0	61.3	61.7	61.0	60.2
75°	51.1	49.7	49.1	48.4	47.3	47.3	47.3
77.5°	37.6	37.2	36.4	35.7	35.4	35.2	35.3
80°	29.1	28.8	28.4	28.4	27.9	27.7	27.3
82.5°	22.4	21.8	21.5	21.3	21.2	21.2	21.1
85°	12.7	12.3	12.3	12.5	12.0	12.0	12.3
87.5°	8.7	8.7	8.5	8.5	8.7	8.6	8.6
90°	19.2	18.9	18.9	19.0	19.1	19.3	19.4
92.5°	18.3	18.3	18.4	18.4	18.4	18.5	18.5
95°	36.5	36.5	36.4	36.1	35.9	35.6	35.4
97.5°	61.4	61.4	61.3	61.3	61.3	61.3	61.2
100°	78.7	78.7	78.6	78.5	78.4	78.3	78.1
102.5°	97.7	97.8	97.8	97.7	97.5	97.4	97.3
105°	126.2	126.5	126.6	126.6	126.6	126.6	126.6
107.5°	156.7	156.8	156.5	155.9	155.4	154.8	154.2
110°	177.3	177.3	177.2	176.8	176.4	176.0	175.6



TEST NUMBER: P331250

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	197.9	197.6	197.3	197.0	196.7	196.4	196.2
115°	230.0	229.9	229.6	229.2	228.9	228.5	228.1
117.5°	260.7	260.4	260.1	259.7	259.3	258.9	258.5
120°	281.7	281.7	281.5	281.1	280.8	280.4	280.0
122.5°	302.7	302.4	302.1	301.8	301.5	301.3	301.0
125°	334.2	333.8	333.5	333.4	333.3	333.1	333.0
127.5°	364.7	364.3	363.8	363.4	363.0	362.6	362.2
130°	385.9	385.6	385.2	384.7	384.2	383.7	383.2
132.5°	405.9	405.4	404.9	404.5	404.1	403.7	403.3
135°	436.4	436.3	436.0	435.7	435.3	434.9	434.5
137.5°	465.2	465.1	464.8	464.3	463.8	463.3	462.8
140°	484.7	484.7	484.5	483.9	483.4	482.9	482.4
142.5°	502.3	502.4	502.2	501.7	501.2	500.7	500.2
145°	529.0	529.1	528.9	528.4	527.9	527.4	526.9
147.5°	552.5	552.8	552.7	552.2	551.7	551.2	550.7
150°	567.4	567.8	567.8	567.4	567.0	566.6	566.3
152.5°	582.3	582.8	582.8	582.3	581.8	581.3	580.9
155°	601.2	601.9	602.0	601.6	601.2	600.8	600.5
157.5°	618.8	619.7	619.8	619.2	618.6	618.0	617.3
160°	629.0	629.7	629.9	629.4	628.9	628.3	627.8
162.5°	638.4	639.3	639.4	638.8	638.2	637.6	637.0
165°	650.5	651.3	651.5	650.8	650.2	649.6	648.9
167.5°	660.4	661.3	661.4	660.7	660.1	659.4	658.7
170°	665.9	666.7	666.8	666.0	665.3	664.5	663.8
172.5°	670.0	670.8	670.9	670.2	669.4	668.6	667.9
175°	674.4	675.3	675.4	674.6	673.8	673.1	672.3
177.5°	676.2	676.8	676.8	676.2	675.6	675.0	674.4
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7

(END OF REPORT)