

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331251

Luminaire Tested: **S122DIP-S290D530U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331251
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D530U835-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3370.3 lumens
Efficiency: N/A
Efficacy: 131.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	84	87	83	80	77	68	66	64	54	53	51	41	40	39	33
2	87	80	74	70	79	73	68	64	60	57	53	48	45	43	37	35	34	29
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	29	27	25	21
5	67	56	48	43	61	51	45	40	43	38	34	34	31	28	27	24	22	19
6	62	50	43	37	56	46	40	35	39	33	30	31	27	25	24	22	20	17
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18	15
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	21	18	16	14
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	15	12
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9544	9544	9544	9544
5°	10699	9606	8512	9606
10°	12260	9527	7366	9527
15°	13563	9352	6509	9352
20°	13357	9165	5933	9165
25°	12043	8915	5569	8915
30°	9952	8516	5302	8516
35°	7253	8099	5113	8099
40°	5794	7609	5008	7609
45°	5062	7040	4866	7040
50°	4760	6488	4770	6488
55°	4386	5928	4642	5928
60°	4020	5331	4447	5331
65°	3664	4798	4252	4798
70°	3323	4277	3970	4277
75°	2951	3699	3512	3699
80°	2538	3059	2827	3059
85°	2279	2279	1686	2279



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	1.7
10°-20°	163.7	4.9
20°-30°	237.5	7.0
30°-40°	250.6	7.4
40°-50°	221.9	6.6
50°-60°	177.1	5.3
60°-70°	120.4	3.6
70°-80°	61.7	1.8
80°-90°	17.5	0.5
90°-100°	118.6	3.5
100°-110°	402.4	11.9
110°-120°	427.5	12.7
120°-130°	351.9	10.4
130°-140°	282.6	8.4
140°-150°	213.5	6.3
150°-160°	150.1	4.5
160°-170°	88.3	2.6
170°-180°	28.8	0.9
0°-30°	457.5	13.6
0°-40°	708.1	21.0
0°-60°	1107.1	32.8
0°-90°	1306.7	38.8
90°-120°	948.4	28.1
90°-150°	1796.4	53.3
90°-180°	2064.0	61.2
0°-180°	3370.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	591	591	591	591	591	
5°	660	593	525	593	660	66
15°	811	560	389	560	811	224
25°	676	500	313	500	676	306
35°	368	411	259	411	368	239
45°	222	308	213	308	222	174
55°	156	211	165	211	156	140
65°	96	126	111	126	96	95
75°	47	59	56	59	47	51
85°	12	12	9	12	12	14
90°	19	1	19	1	19	11
95°	65	20	65	20	65	85
105°	643	70	643	70	643	622
115°	846	123	846	123	846	828
125°	686	171	686	171	686	620
135°	569	201	569	201	569	442
145°	454	229	454	229	454	288
155°	382	261	382	261	382	178
165°	335	284	335	284	335	96
175°	302	296	302	296	302	29
180°	296	296	296	296	296	



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	618.3	618.5	618.9	616.0	615.6	615.6	613.1	610.9	608.3	604.9	605.3
5°	660.1	662.6	663.5	660.8	656.7	656.3	652.4	646.1	640.1	635.4	632.0
7.5°	710.0	711.0	708.8	705.2	702.2	696.7	689.5	682.5	672.6	663.6	656.9
10°	747.8	749.2	745.3	740.1	735.8	729.4	719.0	708.3	695.4	682.9	672.9
12.5°	776.5	779.9	774.9	774.3	766.9	758.1	745.7	740.3	722.1	704.7	693.9
15°	811.4	811.2	811.7	807.3	801.9	800.5	787.4	773.0	747.4	737.1	719.4
17.5°	801.3	804.8	806.4	806.3	806.2	805.3	801.1	792.1	779.2	762.6	742.2
20°	777.4	781.9	782.6	787.8	790.8	794.6	796.2	793.7	785.8	771.9	754.2
22.5°	740.3	741.6	743.7	751.8	758.2	767.9	772.9	781.4	778.3	771.5	756.7
25°	676.0	673.8	681.7	685.8	700.6	716.0	727.2	739.4	750.3	756.9	752.6
27.5°	598.9	595.5	607.4	618.3	630.2	647.0	664.3	684.8	701.8	723.2	730.5
30°	533.8	535.9	547.2	558.8	577.0	600.6	620.2	642.6	667.0	690.8	707.4
32.5°	463.7	471.5	478.7	496.5	512.5	538.8	567.5	595.6	625.9	653.0	678.7
35°	368.0	377.1	387.1	400.0	422.5	448.6	476.6	514.5	555.9	592.9	623.3
37.5°	309.8	308.3	314.0	323.4	341.6	362.7	394.9	432.3	481.0	524.5	567.5
40°	274.9	274.0	278.0	286.7	300.5	316.0	344.2	377.1	422.3	475.5	526.6
42.5°	250.9	251.4	253.7	259.8	269.3	282.0	303.1	331.1	372.5	422.6	477.5
45°	221.7	223.3	225.8	228.8	234.2	244.7	256.5	276.5	309.2	351.0	405.0
47.5°	200.7	200.8	203.3	205.9	209.1	215.0	224.7	237.2	260.3	294.3	340.8
50°	189.5	187.9	189.7	191.7	195.1	199.2	205.6	217.4	232.8	260.3	299.2
52.5°	175.6	175.7	177.3	178.1	181.1	185.2	191.0	199.2	213.2	234.7	266.6
55°	155.8	157.0	157.9	159.2	162.0	164.9	169.5	174.9	185.8	201.9	225.6
57.5°	137.2	137.6	138.5	141.1	142.8	145.5	149.8	154.8	161.9	173.8	191.6
60°	124.5	124.5	126.3	127.4	129.7	132.4	135.8	140.6	147.0	156.7	171.1
62.5°	112.9	112.7	113.4	115.3	117.0	119.5	122.9	127.0	133.0	141.7	153.4
65°	95.9	95.4	96.8	97.2	99.0	101.5	104.3	108.6	113.4	119.7	130.2
67.5°	79.5	80.1	80.8	81.6	82.6	85.3	87.1	90.1	94.2	99.5	106.5
70°	70.4	70.4	70.4	71.1	72.5	73.8	75.6	78.1	82.0	86.5	92.9
72.5°	60.2	61.0	61.7	61.3	63.0	63.8	66.0	67.4	71.1	74.0	79.6
75°	47.3	47.3	47.3	48.4	49.1	49.7	51.1	52.5	54.3	57.9	60.9
77.5°	35.3	35.2	35.4	35.7	36.4	37.2	37.6	38.8	40.5	42.2	44.7
80°	27.3	27.7	27.9	28.4	28.4	28.8	29.1	30.7	31.8	32.9	34.5
82.5°	21.1	21.2	21.2	21.3	21.5	21.8	22.4	22.9	23.3	24.2	25.4
85°	12.3	12.0	12.0	12.5	12.3	12.3	12.7	13.2	13.2	13.4	14.1
87.5°	8.5	8.5	8.7	8.5	8.5	8.6	8.3	8.4	8.7	9.0	9.0
90°	18.8	18.8	18.8	18.8	18.8	18.2	17.1	18.2	18.8	19.4	18.8
92.5°	31.6	32.5	32.1	33.9	34.3	37.9	42.7	49.7	62.6	74.1	73.1
95°	65.0	64.4	66.2	70.7	78.1	90.7	114.6	149.4	195.6	223.6	197.9
97.5°	128.0	132.8	141.1	155.1	182.4	223.6	285.3	348.7	400.3	381.6	287.4
100°	204.2	214.4	231.0	255.5	302.8	371.8	450.0	520.7	532.6	450.5	310.2
102.5°	359.3	373.2	393.8	435.7	487.1	560.3	617.4	633.4	581.9	452.8	301.6
105°	642.7	650.7	675.2	710.6	745.9	764.8	757.3	692.9	574.3	422.6	284.6
107.5°	821.0	831.6	836.5	838.4	834.0	806.4	747.1	650.0	524.2	390.2	276.1
110°	874.8	875.4	870.3	859.4	834.9	788.1	715.1	613.1	492.7	374.7	274.3



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	873.9	870.8	861.1	843.0	808.9	755.3	677.3	579.3	470.8	364.6	274.8
115°	845.7	840.6	825.8	799.5	759.1	700.3	625.6	537.8	443.7	353.6	277.2
117.5°	795.4	791.1	775.5	747.8	706.5	651.4	583.6	506.5	426.6	348.2	281.3
120°	763.0	757.3	740.8	714.0	674.1	622.2	561.7	491.0	417.5	345.0	284.0
122.5°	729.3	724.5	709.8	683.4	647.6	600.7	543.5	478.7	409.7	343.2	287.2
125°	686.1	681.5	667.2	645.6	612.5	569.7	519.5	460.8	398.6	339.9	292.0
127.5°	648.2	644.5	632.2	611.9	583.1	543.6	496.3	443.1	388.4	338.0	296.9
130°	626.7	622.2	610.8	591.4	563.4	525.8	480.8	431.7	381.5	337.0	300.5
132.5°	604.4	600.3	589.8	570.4	542.9	507.6	466.2	420.8	376.0	336.6	304.2
135°	568.6	566.3	556.0	537.2	512.7	480.8	443.1	405.5	368.4	335.9	308.5
137.5°	533.4	530.0	521.0	504.8	482.5	454.6	424.8	393.3	363.0	335.8	312.4
140°	509.3	505.8	497.3	482.5	464.2	439.1	412.9	385.5	359.9	335.3	314.2
142.5°	485.1	484.4	476.8	463.3	446.0	425.0	402.4	379.1	356.7	335.3	315.6
145°	453.9	452.2	446.5	436.8	423.2	406.6	388.9	370.1	352.4	334.2	317.1
147.5°	427.8	426.8	422.9	415.2	403.9	391.8	378.0	363.2	348.1	332.1	317.5
150°	412.3	411.7	408.3	401.5	392.9	382.7	370.7	358.1	344.5	330.8	317.1
152.5°	399.1	399.0	396.5	390.5	383.8	374.9	364.8	353.1	341.3	328.5	316.2
155°	381.5	382.7	380.4	376.4	370.1	363.8	355.3	346.2	335.3	324.5	314.8
157.5°	366.6	366.6	365.6	362.2	357.8	352.9	345.7	338.1	329.7	320.4	312.2
160°	357.0	357.0	356.4	353.6	349.6	345.6	339.3	333.0	325.6	317.7	310.8
162.5°	347.9	348.3	347.8	345.8	341.8	338.8	333.4	328.0	322.0	315.4	309.4
165°	334.8	335.3	335.3	333.0	330.8	328.5	324.5	320.5	315.9	310.8	306.8
167.5°	322.7	323.4	323.5	322.2	321.2	319.1	316.4	313.3	310.0	306.8	304.2
170°	315.4	316.5	317.1	315.4	314.8	313.7	311.4	309.7	306.8	304.5	302.8
172.5°	309.4	310.1	310.7	309.9	309.3	308.6	306.8	305.6	303.6	301.8	301.0
175°	301.7	302.8	303.4	302.8	302.8	302.3	301.7	301.1	299.4	298.8	298.3
177.5°	297.0	297.9	298.4	298.4	298.4	298.4	297.9	297.9	297.0	296.5	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	606.5	605.1	604.2	600.9	598.0	595.1	594.2	594.5	590.5	586.7	585.1
5°	630.2	625.6	621.3	615.2	607.9	599.9	595.9	592.7	584.7	576.1	571.1
7.5°	651.3	644.8	636.5	625.0	614.4	601.9	593.9	586.9	575.3	563.1	555.6
10°	664.2	655.4	644.7	630.6	617.7	602.4	591.8	581.1	567.5	552.9	543.8
12.5°	675.3	663.4	652.9	634.8	619.5	600.4	587.8	572.7	558.4	541.1	532.2
15°	701.7	679.7	659.7	639.2	620.4	593.8	579.7	559.5	540.7	519.3	509.1
17.5°	722.1	697.3	665.9	639.9	617.9	588.4	567.8	543.6	521.3	496.9	483.0
20°	733.7	705.3	671.5	640.6	614.3	580.6	558.1	533.4	507.3	479.8	464.8
22.5°	740.6	710.8	677.3	637.9	607.0	574.3	546.0	518.8	492.4	462.7	447.0
25°	742.8	715.6	680.1	635.6	597.9	560.9	526.8	500.4	468.4	440.7	417.8
27.5°	732.0	712.5	678.4	631.3	587.4	544.1	506.1	476.3	442.5	412.4	389.3
30°	718.7	707.4	674.2	627.0	579.0	532.5	490.7	456.8	423.2	392.8	369.1
32.5°	698.2	695.8	666.6	620.8	570.1	517.8	474.5	440.3	403.0	373.1	350.6
35°	657.9	668.8	650.4	607.0	553.4	496.8	450.0	410.9	372.3	343.7	322.6
37.5°	603.8	630.9	626.1	586.8	530.7	474.0	422.3	381.5	344.7	315.8	295.1
40°	566.5	601.1	606.1	571.3	514.8	456.4	401.6	361.0	325.1	298.7	277.8
42.5°	526.6	566.9	580.6	552.8	497.3	437.8	383.1	341.0	305.4	279.8	261.3
45°	459.6	512.9	537.7	521.8	468.2	407.3	351.0	308.3	276.0	251.9	237.6
47.5°	396.9	455.2	488.5	482.9	435.8	375.5	319.8	278.8	247.4	228.2	215.4
50°	352.6	412.5	452.7	454.6	412.5	352.8	296.9	258.3	229.4	211.5	201.0
52.5°	314.0	371.3	415.1	424.8	386.5	329.2	276.4	237.9	212.5	196.0	186.7
55°	263.7	312.1	360.7	378.5	347.8	293.3	244.4	210.6	186.7	175.4	167.2
57.5°	219.3	259.6	304.5	324.1	305.2	258.5	212.7	183.3	164.0	154.0	147.7
60°	195.8	227.6	267.6	291.0	274.6	233.1	193.1	165.1	149.2	140.4	134.5
62.5°	174.0	202.2	236.0	257.4	248.5	209.3	173.5	148.8	135.1	126.8	122.5
65°	143.6	165.8	192.0	211.7	205.8	176.1	146.7	125.6	114.7	108.1	104.7
67.5°	118.2	134.3	152.4	169.7	165.0	143.9	120.4	103.9	95.8	90.1	88.0
70°	102.2	114.5	130.6	144.5	140.6	123.4	104.7	90.6	83.6	78.8	76.8
72.5°	87.0	97.0	109.4	120.7	118.1	103.7	88.2	77.6	72.1	67.7	66.1
75°	65.7	73.4	80.9	88.4	87.7	76.6	67.5	59.3	55.0	51.6	50.9
77.5°	48.5	52.8	57.9	62.3	61.1	54.7	47.6	42.9	39.8	37.5	37.1
80°	37.0	39.5	43.2	46.3	44.8	42.0	36.3	32.9	30.7	28.4	27.5
82.5°	26.9	29.3	31.5	33.3	32.0	29.5	26.0	23.7	22.3	20.8	20.4
85°	14.1	15.4	16.4	16.8	16.4	14.8	13.2	12.3	11.1	10.4	10.2
87.5°	8.5	7.7	7.2	7.2	6.4	6.2	5.0	4.1	4.3	4.5	4.4
90°	15.4	11.4	8.6	6.8	5.7	4.6	2.3	0.6	2.3	4.6	5.7
92.5°	56.9	38.8	25.9	20.5	16.7	14.1	10.0	7.0	10.0	14.1	16.7
95°	131.7	82.1	55.9	42.2	33.1	27.9	22.2	20.0	22.2	27.9	33.1
97.5°	177.5	108.4	75.4	59.9	49.4	41.6	35.6	32.5	35.6	41.6	49.4
100°	187.1	117.5	87.3	71.3	59.9	50.8	45.6	43.9	45.6	50.8	59.9
102.5°	187.5	125.7	97.7	81.8	69.9	60.8	55.7	54.4	55.7	60.8	69.9
105°	190.5	139.7	112.9	96.9	84.4	75.8	71.9	69.6	71.9	75.8	84.4
107.5°	198.3	154.1	128.1	112.0	99.6	91.7	87.8	86.0	87.8	91.7	99.6
110°	204.7	163.7	138.6	122.0	110.1	102.7	99.2	96.9	99.2	102.7	110.1



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	211.6	172.8	148.6	131.6	120.1	113.1	109.3	107.0	109.3	113.1	120.1
115°	221.8	187.1	162.5	147.1	135.7	128.9	125.5	122.6	125.5	128.9	135.7
117.5°	232.8	200.2	177.5	161.5	150.6	144.5	141.1	138.8	141.1	144.5	150.6
120°	240.1	209.3	187.1	171.1	159.7	154.5	151.1	148.8	151.1	154.5	159.7
122.5°	246.5	218.0	197.1	180.7	169.3	163.7	160.3	158.4	160.3	163.7	169.3
125°	256.6	231.0	210.4	194.5	183.1	176.2	172.8	171.1	172.8	176.2	183.1
127.5°	266.1	243.1	223.1	206.7	195.7	188.2	183.4	181.1	183.4	188.2	195.7
130°	272.0	250.4	230.4	214.4	203.0	195.0	189.3	187.1	189.3	195.0	203.0
132.5°	278.0	256.7	237.7	221.7	209.9	201.4	195.3	192.5	195.3	201.4	209.9
135°	285.7	265.8	247.5	231.5	218.4	209.9	203.0	200.7	203.0	209.9	218.4
137.5°	291.6	273.1	255.0	240.2	227.2	218.1	211.2	208.5	211.2	218.1	227.2
140°	294.8	277.2	260.1	245.2	232.7	223.6	216.7	214.4	216.7	223.6	232.7
142.5°	297.6	280.4	263.7	249.8	237.7	228.6	222.2	220.4	222.2	228.6	237.7
145°	301.1	285.1	269.7	257.2	245.8	237.2	231.5	229.3	231.5	237.2	245.8
147.5°	303.1	289.0	274.5	263.4	253.9	246.0	240.5	238.8	240.5	246.0	253.9
150°	304.0	290.8	277.7	267.5	258.9	251.5	246.9	245.2	246.9	251.5	258.9
152.5°	304.4	292.7	280.9	271.6	263.5	257.0	252.4	251.6	252.4	257.0	263.5
155°	305.1	295.4	285.7	277.2	270.9	264.6	261.2	260.6	261.2	264.6	270.9
157.5°	305.1	297.3	289.1	282.0	276.9	271.5	268.7	268.1	268.7	271.5	276.9
160°	305.1	298.3	291.4	285.1	280.6	276.0	273.7	273.2	273.7	276.0	280.6
162.5°	304.6	298.7	292.8	287.9	283.8	280.1	277.8	278.2	277.8	280.1	283.8
165°	303.4	299.4	294.3	290.8	288.0	284.6	283.4	284.0	283.4	284.6	288.0
167.5°	302.6	299.3	295.5	293.4	291.3	289.1	288.1	288.8	288.1	289.1	291.3
170°	301.7	298.8	296.0	294.3	293.1	291.4	290.8	292.0	290.8	291.4	293.1
172.5°	300.3	298.4	296.4	295.2	294.5	292.8	293.1	293.8	293.1	292.8	294.5
175°	298.8	297.7	296.5	296.0	296.0	294.8	295.4	296.0	295.4	294.8	296.0
177.5°	297.9	297.0	296.5	296.5	296.5	295.6	296.1	297.0	296.1	295.6	296.5
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	583.3	582.2	578.4	576.4	573.1	570.0	568.0	568.9	569.6	569.3	568.7
5°	566.5	562.2	555.6	550.0	545.9	538.4	535.2	533.6	532.2	530.7	529.1
7.5°	546.6	539.8	530.4	522.3	514.7	505.3	500.0	496.9	493.6	490.0	486.8
10°	532.5	522.9	512.9	501.6	492.5	484.1	476.6	471.6	467.0	462.7	459.6
12.5°	517.6	506.6	494.2	478.7	468.7	456.6	455.5	446.7	439.6	436.9	433.2
15°	493.9	478.4	462.7	444.3	436.4	425.5	418.7	411.8	405.7	401.4	400.3
17.5°	466.9	446.9	431.3	418.1	405.1	393.9	387.6	382.2	377.1	371.4	370.6
20°	446.4	429.1	412.1	400.5	387.1	375.7	368.0	362.6	358.2	354.8	351.9
22.5°	426.9	408.0	392.4	379.8	366.6	357.4	351.3	346.0	342.4	338.7	335.9
25°	395.7	381.0	363.9	349.6	338.7	332.8	327.8	323.3	321.0	318.5	315.3
27.5°	368.4	352.0	336.1	325.0	315.4	310.2	306.6	303.5	301.4	299.9	298.1
30°	349.2	332.6	320.1	309.2	301.2	296.0	293.7	291.9	289.4	288.5	287.6
32.5°	330.6	315.7	305.0	295.5	288.0	284.5	282.5	280.8	278.9	278.0	276.1
35°	304.4	291.9	281.5	276.2	270.1	267.1	265.6	263.3	261.5	260.6	260.3
37.5°	279.7	268.9	262.0	255.3	252.7	250.9	248.7	247.2	246.6	246.5	246.2
40°	263.7	254.9	248.7	243.3	242.2	239.4	237.6	236.3	236.3	236.5	236.3
42.5°	249.2	241.2	235.8	231.1	229.8	228.2	226.3	226.3	226.6	227.4	226.6
45°	227.2	221.5	217.6	215.4	212.9	211.3	211.0	211.7	211.9	212.2	212.9
47.5°	206.9	203.1	199.6	197.1	196.0	195.8	195.5	196.7	197.8	198.2	199.2
50°	194.9	190.6	187.6	186.0	185.1	184.7	185.1	186.5	187.4	188.5	189.2
52.5°	181.5	178.4	176.4	175.1	174.8	175.1	175.1	176.7	178.1	178.6	178.9
55°	162.9	160.6	160.2	158.1	159.0	158.8	159.9	160.8	162.2	163.6	163.8
57.5°	144.3	142.5	141.3	141.5	141.8	142.8	143.7	145.3	146.7	148.2	148.3
60°	132.0	131.1	130.4	130.4	130.8	132.2	133.3	134.9	135.8	136.8	137.4
62.5°	120.7	119.8	119.1	119.5	120.7	121.5	122.8	123.7	124.6	125.5	125.8
65°	102.9	102.5	103.1	103.6	103.8	104.9	106.5	107.2	108.1	108.6	110.2
67.5°	86.5	86.6	86.5	87.1	88.5	88.7	90.2	91.8	92.0	92.9	93.9
70°	75.4	75.9	76.3	76.8	77.9	78.4	79.5	80.2	81.1	81.8	82.5
72.5°	65.2	65.3	65.8	65.7	66.7	67.6	68.6	69.3	70.2	71.1	71.7
75°	50.2	50.2	50.7	50.9	52.0	53.2	52.9	53.4	54.3	55.2	55.7
77.5°	36.7	36.2	36.7	36.9	37.3	38.2	38.4	39.0	40.1	39.8	40.3
80°	27.9	27.3	27.9	28.2	28.2	29.3	29.3	29.8	30.4	29.8	30.4
82.5°	19.9	19.6	20.1	20.2	20.5	20.6	20.9	21.0	21.7	21.4	21.7
85°	10.0	9.8	10.0	9.8	10.0	10.2	10.2	10.0	10.0	10.4	9.8
87.5°	4.5	4.6	5.0	5.8	6.3	6.2	5.9	5.8	5.6	5.5	5.6
90°	6.8	8.6	11.4	15.4	18.8	19.4	18.8	18.2	17.1	18.2	18.8
92.5°	20.5	25.9	38.8	56.9	73.1	74.1	62.6	49.7	42.7	37.9	34.3
95°	42.2	55.9	82.1	131.7	197.9	223.6	195.6	149.4	114.6	90.7	78.1
97.5°	59.9	75.4	108.4	177.5	287.4	381.6	400.3	348.7	285.3	223.6	182.4
100°	71.3	87.3	117.5	187.1	310.2	450.5	532.6	520.7	450.0	371.8	302.8
102.5°	81.8	97.7	125.7	187.5	301.6	452.8	581.9	633.4	617.4	560.3	487.1
105°	96.9	112.9	139.7	190.5	284.6	422.6	574.3	692.9	757.3	764.8	745.9
107.5°	112.0	128.1	154.1	198.3	276.1	390.2	524.2	650.0	747.1	806.4	834.0
110°	122.0	138.6	163.7	204.7	274.3	374.7	492.7	613.1	715.1	788.1	834.9



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	131.6	148.6	172.8	211.6	274.8	364.6	470.8	579.3	677.3	755.3	808.9
115°	147.1	162.5	187.1	221.8	277.2	353.6	443.7	537.8	625.6	700.3	759.1
117.5°	161.5	177.5	200.2	232.8	281.3	348.2	426.6	506.5	583.6	651.4	706.5
120°	171.1	187.1	209.3	240.1	284.0	345.0	417.5	491.0	561.7	622.2	674.1
122.5°	180.7	197.1	218.0	246.5	287.2	343.2	409.7	478.7	543.5	600.7	647.6
125°	194.5	210.4	231.0	256.6	292.0	339.9	398.6	460.8	519.5	569.7	612.5
127.5°	206.7	223.1	243.1	266.1	296.9	338.0	388.4	443.1	496.3	543.6	583.1
130°	214.4	230.4	250.4	272.0	300.5	337.0	381.5	431.7	480.8	525.8	563.4
132.5°	221.7	237.7	256.7	278.0	304.2	336.6	376.0	420.8	466.2	507.6	542.9
135°	231.5	247.5	265.8	285.7	308.5	335.9	368.4	405.5	443.1	480.8	512.7
137.5°	240.2	255.0	273.1	291.6	312.4	335.8	363.0	393.3	424.8	454.6	482.5
140°	245.2	260.1	277.2	294.8	314.2	335.3	359.9	385.5	412.9	439.1	464.2
142.5°	249.8	263.7	280.4	297.6	315.6	335.3	356.7	379.1	402.4	425.0	446.0
145°	257.2	269.7	285.1	301.1	317.1	334.2	352.4	370.1	388.9	406.6	423.2
147.5°	263.4	274.5	289.0	303.1	317.5	332.1	348.1	363.2	378.0	391.8	403.9
150°	267.5	277.7	290.8	304.0	317.1	330.8	344.5	358.1	370.7	382.7	392.9
152.5°	271.6	280.9	292.7	304.4	316.2	328.5	341.3	353.1	364.8	374.9	383.8
155°	277.2	285.7	295.4	305.1	314.8	324.5	335.3	346.2	355.3	363.8	370.1
157.5°	282.0	289.1	297.3	305.1	312.2	320.4	329.7	338.1	345.7	352.9	357.8
160°	285.1	291.4	298.3	305.1	310.8	317.7	325.6	333.0	339.3	345.6	349.6
162.5°	287.9	292.8	298.7	304.6	309.4	315.4	322.0	328.0	333.4	338.8	341.8
165°	290.8	294.3	299.4	303.4	306.8	310.8	315.9	320.5	324.5	328.5	330.8
167.5°	293.4	295.5	299.3	302.6	304.2	306.8	310.0	313.3	316.4	319.1	321.2
170°	294.3	296.0	298.8	301.7	302.8	304.5	306.8	309.7	311.4	313.7	314.8
172.5°	295.2	296.4	298.4	300.3	301.0	301.8	303.6	305.6	306.8	308.6	309.3
175°	296.0	296.5	297.7	298.8	298.3	298.8	299.4	301.1	301.7	302.3	302.8
177.5°	296.5	296.5	297.0	297.9	297.0	296.5	297.0	297.9	297.9	298.4	298.4
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	566.9	566.5	566.5	564.9	566.5	566.5	566.9	568.7	569.3	569.6	568.9
5°	525.9	525.2	524.1	525.2	524.1	525.2	525.9	529.1	530.7	532.2	533.6
7.5°	485.3	482.6	482.2	479.5	482.2	482.6	485.3	486.8	490.0	493.6	496.9
10°	455.7	453.9	453.6	449.3	453.6	453.9	455.7	459.6	462.7	467.0	471.6
12.5°	433.2	428.8	429.7	427.2	429.7	428.8	433.2	433.2	436.9	439.6	446.7
15°	394.1	394.1	393.2	389.4	393.2	394.1	394.1	400.3	401.4	405.7	411.8
17.5°	366.1	365.6	363.5	364.6	363.5	365.6	366.1	370.6	371.4	377.1	382.2
20°	349.4	348.0	345.3	345.3	345.3	348.0	349.4	351.9	354.8	358.2	362.6
22.5°	333.6	333.5	330.6	331.5	330.6	333.5	333.6	335.9	338.7	342.4	346.0
25°	315.1	313.3	311.9	312.6	311.9	313.3	315.1	315.3	318.5	321.0	323.3
27.5°	297.5	296.5	296.4	294.6	296.4	296.5	297.5	298.1	299.9	301.4	303.5
30°	287.4	285.1	285.5	284.4	285.5	285.1	287.4	287.6	288.5	289.4	291.9
32.5°	275.7	274.9	274.5	273.5	274.5	274.9	275.7	276.1	278.0	278.9	280.8
35°	259.9	260.1	259.0	259.4	259.0	260.1	259.9	260.3	260.6	261.5	263.3
37.5°	246.0	246.7	246.2	246.3	246.2	246.7	246.0	246.2	246.5	246.6	247.2
40°	236.9	236.9	236.9	237.6	236.9	236.9	236.9	236.3	236.5	236.3	236.3
42.5°	228.2	227.8	227.5	227.4	227.5	227.8	228.2	226.6	227.4	226.6	226.3
45°	213.3	214.0	214.2	213.1	214.2	214.0	213.3	212.9	212.2	211.9	211.7
47.5°	199.8	199.9	199.8	200.8	199.8	199.9	199.8	199.2	198.2	197.8	196.7
50°	190.4	189.9	190.4	189.9	190.4	189.9	190.4	189.2	188.5	187.4	186.5
52.5°	180.4	180.5	180.2	180.1	180.2	180.5	180.4	178.9	178.6	178.1	176.7
55°	164.7	165.1	164.9	164.9	164.9	165.1	164.7	163.8	163.6	162.2	160.8
57.5°	148.5	148.9	149.2	148.2	149.2	148.9	148.5	148.3	148.2	146.7	145.3
60°	137.2	138.3	138.1	137.7	138.1	138.3	137.2	137.4	136.8	135.8	134.9
62.5°	126.8	127.3	127.2	127.1	127.2	127.3	126.8	125.8	125.5	124.6	123.7
65°	110.9	111.3	110.6	111.3	110.6	111.3	110.9	110.2	108.6	108.1	107.2
67.5°	93.6	93.8	94.3	94.6	94.3	93.8	93.6	93.9	92.9	92.0	91.8
70°	82.9	82.7	83.4	84.1	83.4	82.7	82.9	82.5	81.8	81.1	80.2
72.5°	71.6	72.1	71.9	72.4	71.9	72.1	71.6	71.7	71.1	70.2	69.3
75°	55.2	55.9	55.7	56.3	55.7	55.9	55.2	55.7	55.2	54.3	53.4
77.5°	39.9	40.0	39.9	40.3	39.9	40.0	39.9	40.3	39.8	40.1	39.0
80°	30.4	30.0	29.5	30.4	29.5	30.0	30.4	30.4	29.8	30.4	29.8
82.5°	21.2	21.4	21.0	21.0	21.0	21.4	21.2	21.7	21.4	21.7	21.0
85°	9.8	9.5	9.1	9.1	9.1	9.5	9.8	9.8	10.4	10.0	10.0
87.5°	5.6	5.4	5.4	5.2	5.4	5.4	5.6	5.6	5.5	5.6	5.8
90°	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.2	17.1	18.2
92.5°	33.9	32.1	32.5	31.6	32.5	32.1	33.9	34.3	37.9	42.7	49.7
95°	70.7	66.2	64.4	65.0	64.4	66.2	70.7	78.1	90.7	114.6	149.4
97.5°	155.1	141.1	132.8	128.0	132.8	141.1	155.1	182.4	223.6	285.3	348.7
100°	255.5	231.0	214.4	204.2	214.4	231.0	255.5	302.8	371.8	450.0	520.7
102.5°	435.7	393.8	373.2	359.3	373.2	393.8	435.7	487.1	560.3	617.4	633.4
105°	710.6	675.2	650.7	642.7	650.7	675.2	710.6	745.9	764.8	757.3	692.9
107.5°	838.4	836.5	831.6	821.0	831.6	836.5	838.4	834.0	806.4	747.1	650.0
110°	859.4	870.3	875.4	874.8	875.4	870.3	859.4	834.9	788.1	715.1	613.1



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	843.0	861.1	870.8	873.9	870.8	861.1	843.0	808.9	755.3	677.3	579.3
115°	799.5	825.8	840.6	845.7	840.6	825.8	799.5	759.1	700.3	625.6	537.8
117.5°	747.8	775.5	791.1	795.4	791.1	775.5	747.8	706.5	651.4	583.6	506.5
120°	714.0	740.8	757.3	763.0	757.3	740.8	714.0	674.1	622.2	561.7	491.0
122.5°	683.4	709.8	724.5	729.3	724.5	709.8	683.4	647.6	600.7	543.5	478.7
125°	645.6	667.2	681.5	686.1	681.5	667.2	645.6	612.5	569.7	519.5	460.8
127.5°	611.9	632.2	644.5	648.2	644.5	632.2	611.9	583.1	543.6	496.3	443.1
130°	591.4	610.8	622.2	626.7	622.2	610.8	591.4	563.4	525.8	480.8	431.7
132.5°	570.4	589.8	600.3	604.4	600.3	589.8	570.4	542.9	507.6	466.2	420.8
135°	537.2	556.0	566.3	568.6	566.3	556.0	537.2	512.7	480.8	443.1	405.5
137.5°	504.8	521.0	530.0	533.4	530.0	521.0	504.8	482.5	454.6	424.8	393.3
140°	482.5	497.3	505.8	509.3	505.8	497.3	482.5	464.2	439.1	412.9	385.5
142.5°	463.3	476.8	484.4	485.1	484.4	476.8	463.3	446.0	425.0	402.4	379.1
145°	436.8	446.5	452.2	453.9	452.2	446.5	436.8	423.2	406.6	388.9	370.1
147.5°	415.2	422.9	426.8	427.8	426.8	422.9	415.2	403.9	391.8	378.0	363.2
150°	401.5	408.3	411.7	412.3	411.7	408.3	401.5	392.9	382.7	370.7	358.1
152.5°	390.5	396.5	399.0	399.1	399.0	396.5	390.5	383.8	374.9	364.8	353.1
155°	376.4	380.4	382.7	381.5	382.7	380.4	376.4	370.1	363.8	355.3	346.2
157.5°	362.2	365.6	366.6	366.6	366.6	365.6	362.2	357.8	352.9	345.7	338.1
160°	353.6	356.4	357.0	357.0	357.0	356.4	353.6	349.6	345.6	339.3	333.0
162.5°	345.8	347.8	348.3	347.9	348.3	347.8	345.8	341.8	338.8	333.4	328.0
165°	333.0	335.3	335.3	334.8	335.3	335.3	333.0	330.8	328.5	324.5	320.5
167.5°	322.2	323.5	323.4	322.7	323.4	323.5	322.2	321.2	319.1	316.4	313.3
170°	315.4	317.1	316.5	315.4	316.5	317.1	315.4	314.8	313.7	311.4	309.7
172.5°	309.9	310.7	310.1	309.4	310.1	310.7	309.9	309.3	308.6	306.8	305.6
175°	302.8	303.4	302.8	301.7	302.8	303.4	302.8	302.8	302.3	301.7	301.1
177.5°	298.4	298.4	297.9	297.0	297.9	298.4	298.4	298.4	298.4	297.9	297.9
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	568.0	570.0	573.1	576.4	578.4	582.2	583.3	585.1	586.7	590.5	594.5
5°	535.2	538.4	545.9	550.0	555.6	562.2	566.5	571.1	576.1	584.7	592.7
7.5°	500.0	505.3	514.7	522.3	530.4	539.8	546.6	555.6	563.1	575.3	586.9
10°	476.6	484.1	492.5	501.6	512.9	522.9	532.5	543.8	552.9	567.5	581.1
12.5°	455.5	456.6	468.7	478.7	494.2	506.6	517.6	532.2	541.1	558.4	572.7
15°	418.7	425.5	436.4	444.3	462.7	478.4	493.9	509.1	519.3	540.7	559.5
17.5°	387.6	393.9	405.1	418.1	431.3	446.9	466.9	483.0	496.9	521.3	543.6
20°	368.0	375.7	387.1	400.5	412.1	429.1	446.4	464.8	479.8	507.3	533.4
22.5°	351.3	357.4	366.6	379.8	392.4	408.0	426.9	447.0	462.7	492.4	518.8
25°	327.8	332.8	338.7	349.6	363.9	381.0	395.7	417.8	440.7	468.4	500.4
27.5°	306.6	310.2	315.4	325.0	336.1	352.0	368.4	389.3	412.4	442.5	476.3
30°	293.7	296.0	301.2	309.2	320.1	332.6	349.2	369.1	392.8	423.2	456.8
32.5°	282.5	284.5	288.0	295.5	305.0	315.7	330.6	350.6	373.1	403.0	440.3
35°	265.6	267.1	270.1	276.2	281.5	291.9	304.4	322.6	343.7	372.3	410.9
37.5°	248.7	250.9	252.7	255.3	262.0	268.9	279.7	295.1	315.8	344.7	381.5
40°	237.6	239.4	242.2	243.3	248.7	254.9	263.7	277.8	298.7	325.1	361.0
42.5°	226.3	228.2	229.8	231.1	235.8	241.2	249.2	261.3	279.8	305.4	341.0
45°	211.0	211.3	212.9	215.4	217.6	221.5	227.2	237.6	251.9	276.0	308.3
47.5°	195.5	195.8	196.0	197.1	199.6	203.1	206.9	215.4	228.2	247.4	278.8
50°	185.1	184.7	185.1	186.0	187.6	190.6	194.9	201.0	211.5	229.4	258.3
52.5°	175.1	175.1	174.8	175.1	176.4	178.4	181.5	186.7	196.0	212.5	237.9
55°	159.9	158.8	159.0	158.1	160.2	160.6	162.9	167.2	175.4	186.7	210.6
57.5°	143.7	142.8	141.8	141.5	141.3	142.5	144.3	147.7	154.0	164.0	183.3
60°	133.3	132.2	130.8	130.4	130.4	131.1	132.0	134.5	140.4	149.2	165.1
62.5°	122.8	121.5	120.7	119.5	119.1	119.8	120.7	122.5	126.8	135.1	148.8
65°	106.5	104.9	103.8	103.6	103.1	102.5	102.9	104.7	108.1	114.7	125.6
67.5°	90.2	88.7	88.5	87.1	86.5	86.6	86.5	88.0	90.1	95.8	103.9
70°	79.5	78.4	77.9	76.8	76.3	75.9	75.4	76.8	78.8	83.6	90.6
72.5°	68.6	67.6	66.7	65.7	65.8	65.3	65.2	66.1	67.7	72.1	77.6
75°	52.9	53.2	52.0	50.9	50.7	50.2	50.2	50.9	51.6	55.0	59.3
77.5°	38.4	38.2	37.3	36.9	36.7	36.2	36.7	37.1	37.5	39.8	42.9
80°	29.3	29.3	28.2	28.2	27.9	27.3	27.9	27.5	28.4	30.7	32.9
82.5°	20.9	20.6	20.5	20.2	20.1	19.6	19.9	20.4	20.8	22.3	23.7
85°	10.2	10.2	10.0	9.8	10.0	9.8	10.0	10.2	10.4	11.1	12.3
87.5°	5.9	6.2	6.3	5.8	5.0	4.6	4.5	4.4	4.5	4.3	4.1
90°	18.8	19.4	18.8	15.4	11.4	8.6	6.8	5.7	4.6	2.3	0.6
92.5°	62.6	74.1	73.1	56.9	38.8	25.9	20.5	16.7	14.1	10.0	7.0
95°	195.6	223.6	197.9	131.7	82.1	55.9	42.2	33.1	27.9	22.2	20.0
97.5°	400.3	381.6	287.4	177.5	108.4	75.4	59.9	49.4	41.6	35.6	32.5
100°	532.6	450.5	310.2	187.1	117.5	87.3	71.3	59.9	50.8	45.6	43.9
102.5°	581.9	452.8	301.6	187.5	125.7	97.7	81.8	69.9	60.8	55.7	54.4
105°	574.3	422.6	284.6	190.5	139.7	112.9	96.9	84.4	75.8	71.9	69.6
107.5°	524.2	390.2	276.1	198.3	154.1	128.1	112.0	99.6	91.7	87.8	86.0
110°	492.7	374.7	274.3	204.7	163.7	138.6	122.0	110.1	102.7	99.2	96.9



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	470.8	364.6	274.8	211.6	172.8	148.6	131.6	120.1	113.1	109.3	107.0
115°	443.7	353.6	277.2	221.8	187.1	162.5	147.1	135.7	128.9	125.5	122.6
117.5°	426.6	348.2	281.3	232.8	200.2	177.5	161.5	150.6	144.5	141.1	138.8
120°	417.5	345.0	284.0	240.1	209.3	187.1	171.1	159.7	154.5	151.1	148.8
122.5°	409.7	343.2	287.2	246.5	218.0	197.1	180.7	169.3	163.7	160.3	158.4
125°	398.6	339.9	292.0	256.6	231.0	210.4	194.5	183.1	176.2	172.8	171.1
127.5°	388.4	338.0	296.9	266.1	243.1	223.1	206.7	195.7	188.2	183.4	181.1
130°	381.5	337.0	300.5	272.0	250.4	230.4	214.4	203.0	195.0	189.3	187.1
132.5°	376.0	336.6	304.2	278.0	256.7	237.7	221.7	209.9	201.4	195.3	192.5
135°	368.4	335.9	308.5	285.7	265.8	247.5	231.5	218.4	209.9	203.0	200.7
137.5°	363.0	335.8	312.4	291.6	273.1	255.0	240.2	227.2	218.1	211.2	208.5
140°	359.9	335.3	314.2	294.8	277.2	260.1	245.2	232.7	223.6	216.7	214.4
142.5°	356.7	335.3	315.6	297.6	280.4	263.7	249.8	237.7	228.6	222.2	220.4
145°	352.4	334.2	317.1	301.1	285.1	269.7	257.2	245.8	237.2	231.5	229.3
147.5°	348.1	332.1	317.5	303.1	289.0	274.5	263.4	253.9	246.0	240.5	238.8
150°	344.5	330.8	317.1	304.0	290.8	277.7	267.5	258.9	251.5	246.9	245.2
152.5°	341.3	328.5	316.2	304.4	292.7	280.9	271.6	263.5	257.0	252.4	251.6
155°	335.3	324.5	314.8	305.1	295.4	285.7	277.2	270.9	264.6	261.2	260.6
157.5°	329.7	320.4	312.2	305.1	297.3	289.1	282.0	276.9	271.5	268.7	268.1
160°	325.6	317.7	310.8	305.1	298.3	291.4	285.1	280.6	276.0	273.7	273.2
162.5°	322.0	315.4	309.4	304.6	298.7	292.8	287.9	283.8	280.1	277.8	278.2
165°	315.9	310.8	306.8	303.4	299.4	294.3	290.8	288.0	284.6	283.4	284.0
167.5°	310.0	306.8	304.2	302.6	299.3	295.5	293.4	291.3	289.1	288.1	288.8
170°	306.8	304.5	302.8	301.7	298.8	296.0	294.3	293.1	291.4	290.8	292.0
172.5°	303.6	301.8	301.0	300.3	298.4	296.4	295.2	294.5	292.8	293.1	293.8
175°	299.4	298.8	298.3	298.8	297.7	296.5	296.0	296.0	294.8	295.4	296.0
177.5°	297.0	296.5	297.0	297.9	297.0	296.5	296.5	296.5	295.6	296.1	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	594.2	595.1	598.0	600.9	604.2	605.1	606.5	605.3	604.9	608.3	610.9
5°	595.9	599.9	607.9	615.2	621.3	625.6	630.2	632.0	635.4	640.1	646.1
7.5°	593.9	601.9	614.4	625.0	636.5	644.8	651.3	656.9	663.6	672.6	682.5
10°	591.8	602.4	617.7	630.6	644.7	655.4	664.2	672.9	682.9	695.4	708.3
12.5°	587.8	600.4	619.5	634.8	652.9	663.4	675.3	693.9	704.7	722.1	740.3
15°	579.7	593.8	620.4	639.2	659.7	679.7	701.7	719.4	737.1	747.4	773.0
17.5°	567.8	588.4	617.9	639.9	665.9	697.3	722.1	742.2	762.6	779.2	792.1
20°	558.1	580.6	614.3	640.6	671.5	705.3	733.7	754.2	771.9	785.8	793.7
22.5°	546.0	574.3	607.0	637.9	677.3	710.8	740.6	756.7	771.5	778.3	781.4
25°	526.8	560.9	597.9	635.6	680.1	715.6	742.8	752.6	756.9	750.3	739.4
27.5°	506.1	544.1	587.4	631.3	678.4	712.5	732.0	730.5	723.2	701.8	684.8
30°	490.7	532.5	579.0	627.0	674.2	707.4	718.7	707.4	690.8	667.0	642.6
32.5°	474.5	517.8	570.1	620.8	666.6	695.8	698.2	678.7	653.0	625.9	595.6
35°	450.0	496.8	553.4	607.0	650.4	668.8	657.9	623.3	592.9	555.9	514.5
37.5°	422.3	474.0	530.7	586.8	626.1	630.9	603.8	567.5	524.5	481.0	432.3
40°	401.6	456.4	514.8	571.3	606.1	601.1	566.5	526.6	475.5	422.3	377.1
42.5°	383.1	437.8	497.3	552.8	580.6	566.9	526.6	477.5	422.6	372.5	331.1
45°	351.0	407.3	468.2	521.8	537.7	512.9	459.6	405.0	351.0	309.2	276.5
47.5°	319.8	375.5	435.8	482.9	488.5	455.2	396.9	340.8	294.3	260.3	237.2
50°	296.9	352.8	412.5	454.6	452.7	412.5	352.6	299.2	260.3	232.8	217.4
52.5°	276.4	329.2	386.5	424.8	415.1	371.3	314.0	266.6	234.7	213.2	199.2
55°	244.4	293.3	347.8	378.5	360.7	312.1	263.7	225.6	201.9	185.8	174.9
57.5°	212.7	258.5	305.2	324.1	304.5	259.6	219.3	191.6	173.8	161.9	154.8
60°	193.1	233.1	274.6	291.0	267.6	227.6	195.8	171.1	156.7	147.0	140.6
62.5°	173.5	209.3	248.5	257.4	236.0	202.2	174.0	153.4	141.7	133.0	127.0
65°	146.7	176.1	205.8	211.7	192.0	165.8	143.6	130.2	119.7	113.4	108.6
67.5°	120.4	143.9	165.0	169.7	152.4	134.3	118.2	106.5	99.5	94.2	90.1
70°	104.7	123.4	140.6	144.5	130.6	114.5	102.2	92.9	86.5	82.0	78.1
72.5°	88.2	103.7	118.1	120.7	109.4	97.0	87.0	79.6	74.0	71.1	67.4
75°	67.5	76.6	87.7	88.4	80.9	73.4	65.7	60.9	57.9	54.3	52.5
77.5°	47.6	54.7	61.1	62.3	57.9	52.8	48.5	44.7	42.2	40.5	38.8
80°	36.3	42.0	44.8	46.3	43.2	39.5	37.0	34.5	32.9	31.8	30.7
82.5°	26.0	29.5	32.0	33.3	31.5	29.3	26.9	25.4	24.2	23.3	22.9
85°	13.2	14.8	16.4	16.8	16.4	15.4	14.1	14.1	13.4	13.2	13.2
87.5°	5.0	6.2	6.4	7.2	7.2	7.7	8.5	9.0	9.0	8.7	8.4
90°	2.3	4.6	5.7	6.8	8.6	11.4	15.4	18.8	19.4	18.8	18.2
92.5°	10.0	14.1	16.7	20.5	25.9	38.8	56.9	73.1	74.1	62.6	49.7
95°	22.2	27.9	33.1	42.2	55.9	82.1	131.7	197.9	223.6	195.6	149.4
97.5°	35.6	41.6	49.4	59.9	75.4	108.4	177.5	287.4	381.6	400.3	348.7
100°	45.6	50.8	59.9	71.3	87.3	117.5	187.1	310.2	450.5	532.6	520.7
102.5°	55.7	60.8	69.9	81.8	97.7	125.7	187.5	301.6	452.8	581.9	633.4
105°	71.9	75.8	84.4	96.9	112.9	139.7	190.5	284.6	422.6	574.3	692.9
107.5°	87.8	91.7	99.6	112.0	128.1	154.1	198.3	276.1	390.2	524.2	650.0
110°	99.2	102.7	110.1	122.0	138.6	163.7	204.7	274.3	374.7	492.7	613.1



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	109.3	113.1	120.1	131.6	148.6	172.8	211.6	274.8	364.6	470.8	579.3
115°	125.5	128.9	135.7	147.1	162.5	187.1	221.8	277.2	353.6	443.7	537.8
117.5°	141.1	144.5	150.6	161.5	177.5	200.2	232.8	281.3	348.2	426.6	506.5
120°	151.1	154.5	159.7	171.1	187.1	209.3	240.1	284.0	345.0	417.5	491.0
122.5°	160.3	163.7	169.3	180.7	197.1	218.0	246.5	287.2	343.2	409.7	478.7
125°	172.8	176.2	183.1	194.5	210.4	231.0	256.6	292.0	339.9	398.6	460.8
127.5°	183.4	188.2	195.7	206.7	223.1	243.1	266.1	296.9	338.0	388.4	443.1
130°	189.3	195.0	203.0	214.4	230.4	250.4	272.0	300.5	337.0	381.5	431.7
132.5°	195.3	201.4	209.9	221.7	237.7	256.7	278.0	304.2	336.6	376.0	420.8
135°	203.0	209.9	218.4	231.5	247.5	265.8	285.7	308.5	335.9	368.4	405.5
137.5°	211.2	218.1	227.2	240.2	255.0	273.1	291.6	312.4	335.8	363.0	393.3
140°	216.7	223.6	232.7	245.2	260.1	277.2	294.8	314.2	335.3	359.9	385.5
142.5°	222.2	228.6	237.7	249.8	263.7	280.4	297.6	315.6	335.3	356.7	379.1
145°	231.5	237.2	245.8	257.2	269.7	285.1	301.1	317.1	334.2	352.4	370.1
147.5°	240.5	246.0	253.9	263.4	274.5	289.0	303.1	317.5	332.1	348.1	363.2
150°	246.9	251.5	258.9	267.5	277.7	290.8	304.0	317.1	330.8	344.5	358.1
152.5°	252.4	257.0	263.5	271.6	280.9	292.7	304.4	316.2	328.5	341.3	353.1
155°	261.2	264.6	270.9	277.2	285.7	295.4	305.1	314.8	324.5	335.3	346.2
157.5°	268.7	271.5	276.9	282.0	289.1	297.3	305.1	312.2	320.4	329.7	338.1
160°	273.7	276.0	280.6	285.1	291.4	298.3	305.1	310.8	317.7	325.6	333.0
162.5°	277.8	280.1	283.8	287.9	292.8	298.7	304.6	309.4	315.4	322.0	328.0
165°	283.4	284.6	288.0	290.8	294.3	299.4	303.4	306.8	310.8	315.9	320.5
167.5°	288.1	289.1	291.3	293.4	295.5	299.3	302.6	304.2	306.8	310.0	313.3
170°	290.8	291.4	293.1	294.3	296.0	298.8	301.7	302.8	304.5	306.8	309.7
172.5°	293.1	292.8	294.5	295.2	296.4	298.4	300.3	301.0	301.8	303.6	305.6
175°	295.4	294.8	296.0	296.0	296.5	297.7	298.8	298.3	298.8	299.4	301.1
177.5°	296.1	295.6	296.5	296.5	296.5	297.0	297.9	297.0	296.5	297.0	297.9
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	613.1	615.6	615.6	616.0	618.9	618.5	618.3
5°	652.4	656.3	656.7	660.8	663.5	662.6	660.1
7.5°	689.5	696.7	702.2	705.2	708.8	711.0	710.0
10°	719.0	729.4	735.8	740.1	745.3	749.2	747.8
12.5°	745.7	758.1	766.9	774.3	774.9	779.9	776.5
15°	787.4	800.5	801.9	807.3	811.7	811.2	811.4
17.5°	801.1	805.3	806.2	806.3	806.4	804.8	801.3
20°	796.2	794.6	790.8	787.8	782.6	781.9	777.4
22.5°	772.9	767.9	758.2	751.8	743.7	741.6	740.3
25°	727.2	716.0	700.6	685.8	681.7	673.8	676.0
27.5°	664.3	647.0	630.2	618.3	607.4	595.5	598.9
30°	620.2	600.6	577.0	558.8	547.2	535.9	533.8
32.5°	567.5	538.8	512.5	496.5	478.7	471.5	463.7
35°	476.6	448.6	422.5	400.0	387.1	377.1	368.0
37.5°	394.9	362.7	341.6	323.4	314.0	308.3	309.8
40°	344.2	316.0	300.5	286.7	278.0	274.0	274.9
42.5°	303.1	282.0	269.3	259.8	253.7	251.4	250.9
45°	256.5	244.7	234.2	228.8	225.8	223.3	221.7
47.5°	224.7	215.0	209.1	205.9	203.3	200.8	200.7
50°	205.6	199.2	195.1	191.7	189.7	187.9	189.5
52.5°	191.0	185.2	181.1	178.1	177.3	175.7	175.6
55°	169.5	164.9	162.0	159.2	157.9	157.0	155.8
57.5°	149.8	145.5	142.8	141.1	138.5	137.6	137.2
60°	135.8	132.4	129.7	127.4	126.3	124.5	124.5
62.5°	122.9	119.5	117.0	115.3	113.4	112.7	112.9
65°	104.3	101.5	99.0	97.2	96.8	95.4	95.9
67.5°	87.1	85.3	82.6	81.6	80.8	80.1	79.5
70°	75.6	73.8	72.5	71.1	70.4	70.4	70.4
72.5°	66.0	63.8	63.0	61.3	61.7	61.0	60.2
75°	51.1	49.7	49.1	48.4	47.3	47.3	47.3
77.5°	37.6	37.2	36.4	35.7	35.4	35.2	35.3
80°	29.1	28.8	28.4	28.4	27.9	27.7	27.3
82.5°	22.4	21.8	21.5	21.3	21.2	21.2	21.1
85°	12.7	12.3	12.3	12.5	12.0	12.0	12.3
87.5°	8.3	8.6	8.5	8.5	8.7	8.5	8.5
90°	17.1	18.2	18.8	18.8	18.8	18.8	18.8
92.5°	42.7	37.9	34.3	33.9	32.1	32.5	31.6
95°	114.6	90.7	78.1	70.7	66.2	64.4	65.0
97.5°	285.3	223.6	182.4	155.1	141.1	132.8	128.0
100°	450.0	371.8	302.8	255.5	231.0	214.4	204.2
102.5°	617.4	560.3	487.1	435.7	393.8	373.2	359.3
105°	757.3	764.8	745.9	710.6	675.2	650.7	642.7
107.5°	747.1	806.4	834.0	838.4	836.5	831.6	821.0
110°	715.1	788.1	834.9	859.4	870.3	875.4	874.8



TEST NUMBER: P331251

CATALOG NUMBER: S122DIP-S290D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	677.3	755.3	808.9	843.0	861.1	870.8	873.9
115°	625.6	700.3	759.1	799.5	825.8	840.6	845.7
117.5°	583.6	651.4	706.5	747.8	775.5	791.1	795.4
120°	561.7	622.2	674.1	714.0	740.8	757.3	763.0
122.5°	543.5	600.7	647.6	683.4	709.8	724.5	729.3
125°	519.5	569.7	612.5	645.6	667.2	681.5	686.1
127.5°	496.3	543.6	583.1	611.9	632.2	644.5	648.2
130°	480.8	525.8	563.4	591.4	610.8	622.2	626.7
132.5°	466.2	507.6	542.9	570.4	589.8	600.3	604.4
135°	443.1	480.8	512.7	537.2	556.0	566.3	568.6
137.5°	424.8	454.6	482.5	504.8	521.0	530.0	533.4
140°	412.9	439.1	464.2	482.5	497.3	505.8	509.3
142.5°	402.4	425.0	446.0	463.3	476.8	484.4	485.1
145°	388.9	406.6	423.2	436.8	446.5	452.2	453.9
147.5°	378.0	391.8	403.9	415.2	422.9	426.8	427.8
150°	370.7	382.7	392.9	401.5	408.3	411.7	412.3
152.5°	364.8	374.9	383.8	390.5	396.5	399.0	399.1
155°	355.3	363.8	370.1	376.4	380.4	382.7	381.5
157.5°	345.7	352.9	357.8	362.2	365.6	366.6	366.6
160°	339.3	345.6	349.6	353.6	356.4	357.0	357.0
162.5°	333.4	338.8	341.8	345.8	347.8	348.3	347.9
165°	324.5	328.5	330.8	333.0	335.3	335.3	334.8
167.5°	316.4	319.1	321.2	322.2	323.5	323.4	322.7
170°	311.4	313.7	314.8	315.4	317.1	316.5	315.4
172.5°	306.8	308.6	309.3	309.9	310.7	310.1	309.4
175°	301.7	302.3	302.8	302.8	303.4	302.8	301.7
177.5°	297.9	298.4	298.4	298.4	298.4	297.9	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5

(END OF REPORT)