

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331755

Luminaire Tested: **S122RDIP-S1005D925U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331755
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S1005D925U835-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7427.5 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	95	91	88	91	88	85	82	75	73	71	63	61	60	52	51	50	45
2	91	84	78	73	84	78	73	69	67	63	60	56	54	51	47	45	43	39
3	83	74	68	62	77	69	63	58	60	55	51	51	47	45	42	40	38	34
4	77	67	59	53	71	62	55	50	54	49	45	46	42	39	38	36	34	30
5	71	60	52	46	65	56	49	44	48	43	39	41	38	34	35	32	30	27
6	66	54	46	41	61	51	44	39	44	39	35	38	34	31	32	29	27	24
7	61	49	42	36	56	46	39	34	40	35	31	35	31	28	30	27	24	22
8	57	45	37	32	53	42	36	31	37	32	28	32	28	25	28	24	22	20
9	53	41	34	29	49	39	32	28	34	29	25	30	26	23	26	22	20	18
10	50	38	31	26	46	36	30	25	32	27	23	28	24	21	24	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	35608	35608	35608	35608
5°	39768	35832	31770	35832
10°	44124	35580	27539	35580
15°	46292	35059	21698	35059
20°	40132	34287	18777	34287
25°	26320	33228	16764	33228
30°	17715	31946	15172	31946
35°	14349	30328	13685	30328
40°	12760	28572	12663	28572
45°	11549	26510	11303	26510
50°	10510	24465	10472	24465
55°	9880	22196	9751	22196
60°	8263	20118	8167	20118
65°	6968	18269	7904	18269
70°	6439	16315	7454	16315
75°	6026	14198	6881	14198
80°	5560	11688	6127	11688
85°	5113	9226	5391	9226



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.1	2.8
10°-20°	582.5	7.8
20°-30°	750.7	10.1
30°-40°	713.4	9.6
40°-50°	611.1	8.2
50°-60°	465.4	6.3
60°-70°	294.2	4.0
70°-80°	146.9	2.0
80°-90°	42.9	0.6
90°-100°	207.5	2.8
100°-110°	704.2	9.5
110°-120°	748.1	10.1
120°-130°	615.8	8.3
130°-140°	494.5	6.7
140°-150°	373.7	5.0
150°-160°	262.6	3.5
160°-170°	154.6	2.1
170°-180°	50.3	0.7
0°-30°	1542.3	20.8
0°-40°	2255.7	30.4
0°-60°	3332.1	44.9
0°-90°	3816.2	51.4
90°-120°	1659.8	22.3
90°-150°	3143.8	42.3
90°-180°	3611.0	48.6
0°-180°	7427.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2205	2205	2205	2205	2205	
5°	2454	2211	1960	2211	2454	242
15°	2769	2097	1298	2097	2769	747
25°	1477	1865	941	1865	1477	701
35°	728	1539	694	1539	728	466
45°	506	1161	495	1161	506	391
55°	351	788	346	788	351	308
65°	182	478	207	478	182	186
75°	97	228	110	228	97	102
85°	28	50	29	50	28	30
90°	33	1	33	1	33	19
95°	114	35	114	35	114	148
105°	1125	122	1125	122	1125	1088
115°	1480	215	1480	215	1480	1449
125°	1201	299	1201	299	1201	1085
135°	995	351	995	351	995	773
145°	794	401	794	401	794	505
155°	668	456	668	456	668	312
165°	586	497	586	497	586	168
175°	528	518	528	518	528	51
180°	519	519	519	519	519	



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2294.9	2296.8	2298.6	2294.3	2294.3	2290.6	2282.7	2276.5	2259.4	2256.9	2256.9
5°	2453.7	2452.2	2455.2	2445.3	2431.5	2428.4	2413.9	2394.7	2374.8	2352.6	2348.0
7.5°	2611.6	2609.3	2603.1	2601.5	2590.9	2567.7	2544.3	2519.3	2486.2	2453.9	2437.6
10°	2691.3	2716.6	2701.2	2674.4	2679.8	2643.8	2624.6	2591.7	2564.1	2515.8	2505.1
12.5°	2769.7	2779.7	2774.8	2759.6	2752.7	2727.7	2701.8	2673.2	2622.3	2578.9	2541.2
15°	2769.4	2784.0	2787.8	2783.2	2787.1	2785.5	2771.7	2748.0	2703.5	2656.0	2614.6
17.5°	2565.0	2575.1	2600.2	2617.2	2638.7	2684.1	2706.4	2715.2	2708.6	2681.5	2652.3
20°	2335.7	2318.8	2389.3	2425.4	2456.0	2532.6	2598.5	2623.8	2664.4	2663.7	2656.0
22.5°	2010.8	2014.8	2081.6	2124.4	2213.9	2290.5	2365.6	2460.8	2539.4	2591.3	2621.7
25°	1477.4	1506.6	1573.2	1631.5	1731.1	1873.6	2003.1	2153.3	2295.1	2407.0	2513.5
27.5°	1109.6	1111.8	1164.6	1218.4	1277.6	1394.4	1557.4	1736.8	1938.9	2105.7	2297.5
30°	950.2	945.6	967.8	1000.8	1051.4	1141.8	1264.4	1440.7	1642.2	1893.5	2117.3
32.5°	837.4	837.7	854.4	878.8	920.8	981.8	1065.8	1208.9	1399.4	1646.5	1908.9
35°	728.0	727.2	739.5	757.1	774.7	813.8	871.3	946.4	1077.4	1308.1	1576.3
37.5°	649.5	652.9	658.9	669.9	689.4	711.1	745.6	796.0	889.4	1025.8	1251.2
40°	605.4	606.9	615.3	624.5	636.0	652.9	681.2	721.9	790.1	898.9	1063.6
42.5°	564.9	566.5	572.4	581.0	590.1	606.9	630.4	665.5	720.8	805.7	941.6
45°	505.8	505.8	511.1	515.0	524.9	540.2	559.4	588.5	626.8	689.7	780.1
47.5°	450.3	450.4	454.0	460.6	466.8	478.8	497.6	521.4	549.3	597.9	675.1
50°	418.4	419.2	421.5	426.8	430.7	441.4	456.0	476.6	505.8	543.3	607.7
52.5°	392.7	392.2	395.1	397.4	400.0	407.7	418.6	436.8	462.8	495.5	548.8
55°	351.0	347.9	352.5	356.3	358.6	361.7	367.8	379.3	401.5	429.1	469.0
57.5°	298.9	297.6	300.9	304.4	311.6	319.9	325.1	332.4	343.9	363.7	403.2
60°	255.9	255.9	262.8	265.1	273.6	284.3	295.0	301.2	312.7	325.7	354.8
62.5°	217.9	218.6	221.8	224.1	228.8	242.0	257.0	270.5	281.4	293.8	313.1
65°	182.4	183.9	183.9	185.4	188.5	191.6	197.7	208.4	227.6	245.2	259.8
67.5°	154.8	155.3	155.7	157.2	158.0	161.4	163.8	168.6	173.0	189.7	207.8
70°	136.4	138.7	137.9	139.5	140.2	141.8	144.8	147.1	154.0	157.9	168.6
72.5°	119.2	120.9	120.8	121.7	123.7	124.0	126.4	128.7	133.2	136.4	142.2
75°	96.6	95.8	96.6	98.1	98.9	99.6	99.6	102.7	105.0	108.0	111.9
77.5°	74.5	75.3	75.1	75.3	75.4	76.8	76.6	78.0	80.3	81.8	83.7
80°	59.8	60.5	59.8	60.5	61.3	62.1	61.3	62.1	64.4	65.9	65.9
82.5°	46.3	46.4	46.9	47.1	47.2	47.4	48.4	48.6	50.3	50.0	50.6
85°	27.6	26.8	26.8	26.8	27.6	28.4	27.6	27.6	28.4	28.4	28.4
87.5°	16.4	17.0	17.0	17.0	17.0	16.8	16.4	17.4	17.0	17.8	17.0
90°	32.9	32.9	32.9	32.9	32.9	31.9	29.9	31.9	32.9	33.9	32.9
92.5°	55.3	56.9	56.1	59.3	60.1	66.3	74.7	87.0	109.6	129.7	127.9
95°	113.8	112.8	115.8	123.8	136.7	158.7	200.6	261.5	342.3	391.2	346.3
97.5°	224.0	232.3	246.9	271.5	319.2	391.2	499.2	610.2	700.6	667.9	503.0
100°	357.3	375.3	404.2	447.1	530.0	650.7	787.4	911.2	932.2	788.4	542.9
102.5°	628.8	653.1	689.2	762.5	852.5	980.5	1080.5	1108.4	1018.4	792.4	527.8
105°	1124.8	1138.7	1181.7	1243.5	1305.4	1338.4	1325.4	1212.6	1005.0	739.5	498.0
107.5°	1436.8	1455.3	1463.9	1467.3	1459.5	1411.2	1307.4	1137.6	917.4	682.9	483.2
110°	1531.0	1532.0	1523.0	1504.0	1461.1	1379.3	1251.5	1072.9	862.3	655.7	480.1



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1529.4	1524.0	1507.0	1475.3	1415.6	1321.8	1185.3	1013.8	824.0	638.1	480.8
115°	1480.1	1471.1	1445.1	1399.2	1328.4	1225.6	1094.8	941.1	776.5	618.8	485.0
117.5°	1392.0	1384.5	1357.1	1308.6	1236.4	1139.9	1021.4	886.4	746.5	609.4	492.2
120°	1335.4	1325.4	1296.4	1249.5	1179.7	1088.8	983.1	859.3	730.6	603.8	497.0
122.5°	1276.3	1267.9	1242.1	1196.0	1133.4	1051.3	951.1	837.7	717.0	600.6	502.6
125°	1200.6	1192.6	1167.7	1129.8	1071.9	997.0	909.2	806.4	697.6	594.8	511.0
127.5°	1134.4	1128.0	1106.4	1070.9	1020.4	951.3	868.5	775.5	679.7	591.4	519.6
130°	1096.8	1088.8	1068.9	1035.0	986.1	920.2	841.3	755.5	667.7	589.8	526.0
132.5°	1057.7	1050.5	1032.2	998.2	950.1	888.2	815.8	736.3	658.1	589.0	532.3
135°	995.0	991.0	973.1	940.1	897.2	841.3	775.5	709.6	644.7	587.8	539.9
137.5°	933.6	927.6	911.8	883.5	844.3	795.6	743.3	688.2	635.3	587.6	546.7
140°	891.2	885.3	870.3	844.3	812.4	768.5	722.6	674.7	629.8	586.8	549.9
142.5°	848.9	847.7	834.4	810.8	780.5	743.7	704.2	663.5	624.2	586.8	552.3
145°	794.4	791.4	781.5	764.5	740.5	711.6	680.7	647.7	616.8	584.8	554.9
147.5°	748.7	746.9	740.1	726.6	706.8	685.6	661.5	635.5	609.2	581.3	555.7
150°	721.6	720.6	714.6	702.6	687.6	669.7	648.7	626.8	602.8	578.9	554.9
152.5°	698.4	698.2	693.8	683.4	671.7	656.1	638.3	618.0	597.2	574.9	553.3
155°	667.7	669.7	665.7	658.7	647.7	636.7	621.8	605.8	586.8	567.9	550.9
157.5°	641.5	641.5	639.7	633.9	626.2	617.6	605.0	591.6	577.1	560.7	546.3
160°	624.8	624.8	623.8	618.8	611.8	604.8	593.8	582.8	569.9	555.9	543.9
162.5°	608.8	609.6	608.6	605.2	598.2	592.8	583.4	574.1	563.5	551.9	541.5
165°	585.8	586.8	586.8	582.8	578.9	574.9	567.9	560.9	552.9	543.9	536.9
167.5°	564.7	565.9	566.1	563.9	562.1	558.5	553.7	548.3	542.5	536.9	532.3
170°	551.9	553.9	554.9	551.9	550.9	548.9	544.9	541.9	536.9	532.9	530.0
172.5°	541.5	542.7	543.7	542.3	541.3	540.1	536.9	534.7	531.4	528.2	526.8
175°	528.0	530.0	531.0	530.0	530.0	529.0	528.0	527.0	524.0	523.0	522.0
177.5°	519.8	521.4	522.2	522.2	522.2	522.2	521.4	521.4	519.8	519.0	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2258.2	2253.2	2249.0	2237.9	2232.4	2220.1	2218.3	2217.7	2201.8	2186.4	2182.1
5°	2335.7	2323.4	2305.1	2283.6	2261.4	2238.4	2223.1	2210.8	2180.1	2151.0	2134.2
7.5°	2413.9	2387.5	2355.8	2315.2	2281.3	2243.3	2215.1	2189.8	2146.3	2104.6	2076.5
10°	2472.1	2429.2	2387.0	2331.1	2287.4	2244.5	2204.7	2170.2	2121.1	2066.0	2026.9
12.5°	2508.3	2461.1	2403.0	2348.3	2291.7	2237.2	2183.8	2139.5	2081.9	2024.9	1978.5
15°	2557.2	2506.6	2436.1	2357.9	2285.1	2213.9	2152.6	2097.4	2022.3	1954.1	1897.4
17.5°	2597.2	2527.6	2451.9	2361.5	2277.2	2186.6	2107.7	2037.2	1953.6	1871.3	1804.5
20°	2610.0	2541.1	2453.7	2363.3	2263.7	2157.2	2072.1	1995.5	1905.8	1816.1	1739.5
22.5°	2602.1	2548.4	2451.3	2343.1	2241.0	2129.6	2033.5	1944.6	1845.1	1753.6	1664.7
25°	2548.0	2529.6	2437.6	2319.6	2203.1	2073.6	1962.5	1865.2	1751.8	1653.7	1557.1
27.5°	2421.8	2461.5	2404.5	2278.8	2149.3	2010.5	1885.6	1774.8	1657.1	1546.7	1450.5
30°	2300.5	2391.6	2367.1	2250.6	2105.8	1969.4	1829.2	1713.5	1587.8	1474.4	1379.4
32.5°	2134.3	2285.0	2308.9	2211.4	2061.7	1911.8	1764.8	1649.7	1518.5	1399.0	1306.4
35°	1869.8	2095.1	2198.5	2136.5	1986.3	1824.6	1672.8	1538.7	1406.9	1288.9	1197.0
37.5°	1554.2	1861.1	2033.5	2037.9	1900.0	1731.9	1566.6	1433.5	1298.6	1182.7	1083.3
40°	1349.5	1682.0	1906.6	1956.4	1839.9	1658.3	1491.2	1355.6	1223.8	1110.4	996.2
42.5°	1165.6	1496.9	1772.9	1859.5	1767.0	1586.6	1418.9	1277.1	1149.0	1041.7	925.1
45°	942.6	1232.2	1536.4	1691.2	1639.9	1472.8	1295.8	1161.0	1040.6	947.9	836.0
47.5°	795.1	999.3	1293.7	1503.0	1502.1	1349.6	1175.5	1046.3	934.7	847.8	757.3
50°	711.1	888.9	1138.0	1375.5	1395.4	1267.5	1101.9	974.0	869.8	778.6	705.8
52.5°	635.7	782.2	1006.2	1233.9	1290.6	1179.8	1019.2	901.0	799.9	716.0	653.7
55°	537.2	650.6	820.7	1033.7	1119.6	1041.4	898.9	788.5	706.5	636.0	582.4
57.5°	454.4	539.5	676.0	847.5	947.5	898.3	780.7	691.1	620.9	557.1	514.8
60°	402.3	472.0	587.8	731.1	841.4	806.9	706.5	623.0	563.2	508.1	468.2
62.5°	353.3	413.2	512.4	628.7	729.8	715.6	633.6	563.5	511.1	460.9	427.1
65°	284.3	328.0	405.4	496.6	577.8	584.7	525.7	478.2	431.4	391.6	361.7
67.5°	226.4	254.9	309.4	386.2	447.1	468.8	432.8	396.5	359.4	328.6	302.7
70°	190.8	213.8	253.6	315.7	371.7	394.6	374.0	345.6	313.4	288.1	265.9
72.5°	154.6	177.0	206.4	252.0	299.9	324.8	317.6	297.2	271.1	250.1	229.1
75°	116.5	123.4	143.3	174.0	211.5	233.0	238.3	227.6	206.9	190.8	178.5
77.5°	86.1	90.3	99.8	115.9	140.4	159.5	167.4	166.1	151.9	142.5	131.0
80°	69.0	71.3	75.9	82.8	101.2	120.3	125.7	125.7	115.7	111.9	100.4
82.5°	52.4	54.1	56.9	60.7	69.3	86.0	92.0	93.2	86.9	81.8	72.8
85°	29.9	29.1	30.7	33.0	34.5	39.1	48.3	49.8	48.3	42.1	39.8
87.5°	15.8	15.0	14.0	12.8	13.0	13.2	15.5	18.0	16.1	15.1	14.3
90°	26.9	20.0	15.0	12.0	10.0	8.0	4.0	1.0	4.0	8.0	10.0
92.5°	99.6	67.9	45.3	35.9	29.1	24.8	17.6	12.2	17.6	24.8	29.1
95°	230.5	143.7	97.8	73.9	57.9	48.9	38.9	34.9	38.9	48.9	57.9
97.5°	310.6	189.6	131.9	104.8	86.4	72.9	62.3	56.9	62.3	72.9	86.4
100°	327.4	205.6	152.7	124.8	104.8	88.8	79.8	76.8	79.8	88.8	104.8
102.5°	328.2	220.0	171.1	143.1	122.4	106.4	97.4	95.2	97.4	106.4	122.4
105°	333.3	244.5	197.6	169.7	147.7	132.7	125.8	121.8	125.8	132.7	147.7
107.5°	347.1	269.7	224.2	196.0	174.3	160.5	153.7	150.5	153.7	160.5	174.3
110°	358.3	286.4	242.5	213.6	192.6	179.6	173.7	169.7	173.7	179.6	192.6



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	370.3	302.4	260.1	230.3	210.2	198.0	191.2	187.2	191.2	198.0	210.2
115°	388.2	327.4	284.4	257.5	237.5	225.6	219.6	214.6	219.6	225.6	237.5
117.5°	407.4	350.3	310.6	282.6	263.5	252.9	246.9	242.9	246.9	252.9	263.5
120°	420.2	366.3	327.4	299.4	279.4	270.5	264.5	260.5	264.5	270.5	279.4
122.5°	431.3	381.4	344.9	316.2	296.2	286.4	280.4	277.3	280.4	286.4	296.2
125°	449.1	404.2	368.3	340.3	320.4	308.4	302.4	299.4	302.4	308.4	320.4
127.5°	465.7	425.4	390.4	361.7	342.5	329.3	321.0	317.0	321.0	329.3	342.5
130°	476.1	438.1	403.2	375.3	355.3	341.3	331.3	327.4	331.3	341.3	355.3
132.5°	486.4	449.3	416.0	388.0	367.3	352.5	341.7	336.9	341.7	352.5	367.3
135°	500.0	465.1	433.1	405.2	382.2	367.3	355.3	351.3	355.3	367.3	382.2
137.5°	510.4	477.9	446.3	420.4	397.6	381.6	369.7	364.9	369.7	381.6	397.6
140°	516.0	485.0	455.1	429.2	407.2	391.2	379.3	375.3	379.3	391.2	407.2
142.5°	520.8	490.6	461.5	437.1	416.0	400.0	388.8	385.6	388.8	400.0	416.0
145°	527.0	499.0	472.1	450.1	430.2	415.2	405.2	401.2	405.2	415.2	430.2
147.5°	530.4	505.8	480.5	460.9	444.3	430.5	421.0	418.0	421.0	430.5	444.3
150°	531.9	509.0	486.0	468.1	453.1	440.1	432.1	429.2	432.1	440.1	453.1
152.5°	532.7	512.2	491.6	475.3	461.1	449.7	441.7	440.3	441.7	449.7	461.1
155°	533.9	517.0	500.0	485.0	474.1	463.1	457.1	456.1	457.1	463.1	474.1
157.5°	533.9	520.4	506.0	493.4	484.6	475.1	470.3	469.3	470.3	475.1	484.6
160°	533.9	522.0	510.0	499.0	491.0	483.0	479.1	478.1	479.1	483.0	491.0
162.5°	533.1	522.8	512.4	503.8	496.6	490.2	486.2	486.8	486.2	490.2	496.6
165°	531.0	524.0	515.0	509.0	504.0	498.0	496.0	497.0	496.0	498.0	504.0
167.5°	529.6	523.8	517.2	513.4	509.8	506.0	504.2	505.4	504.2	506.0	509.8
170°	528.0	523.0	518.0	515.0	513.0	510.0	509.0	511.0	509.0	510.0	513.0
172.5°	525.6	522.2	518.8	516.6	515.4	512.4	513.0	514.2	513.0	512.4	515.4
175°	523.0	521.0	519.0	518.0	518.0	516.0	517.0	518.0	517.0	516.0	518.0
177.5°	521.4	519.8	519.0	519.0	519.0	517.4	518.2	519.8	518.2	517.4	519.0
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2174.2	2169.9	2161.9	2149.6	2142.3	2129.4	2120.8	2125.7	2127.0	2125.7	2124.5
5°	2115.8	2099.7	2077.5	2056.0	2036.1	2014.6	2002.4	1997.0	1986.3	1980.1	1977.1
7.5°	2045.1	2017.4	1986.0	1948.6	1916.8	1883.6	1866.6	1858.1	1836.2	1824.3	1813.8
10°	1992.4	1948.7	1917.3	1868.3	1838.4	1794.7	1764.8	1765.6	1735.7	1718.8	1706.6
12.5°	1934.2	1886.2	1833.9	1789.8	1748.3	1713.2	1677.1	1662.6	1630.9	1614.6	1581.5
15°	1837.6	1781.7	1726.5	1666.7	1624.6	1570.2	1518.1	1454.5	1403.1	1358.7	1346.4
17.5°	1732.2	1662.9	1607.6	1537.4	1465.2	1373.7	1313.3	1276.4	1245.4	1222.0	1204.5
20°	1659.8	1589.3	1530.3	1424.6	1327.2	1265.2	1220.7	1192.4	1160.2	1134.9	1121.1
22.5°	1583.8	1510.2	1429.8	1311.8	1235.9	1186.1	1146.5	1113.9	1092.1	1072.4	1059.8
25°	1475.9	1395.4	1262.9	1181.6	1120.3	1068.2	1040.6	1020.7	997.7	970.9	958.7
27.5°	1361.9	1233.9	1138.7	1078.3	1019.8	985.9	961.1	931.4	910.8	898.7	886.0
30°	1276.7	1148.7	1074.4	1008.5	967.1	929.5	900.4	883.6	863.6	842.9	834.5
32.5°	1181.6	1079.4	1008.2	953.3	911.3	879.3	856.3	829.0	814.6	801.9	784.2
35°	1063.6	986.2	921.1	876.7	836.8	810.8	783.9	767.8	741.8	731.1	724.2
37.5°	963.7	896.6	848.0	801.1	769.5	740.7	724.3	698.7	687.4	672.5	658.0
40°	907.3	841.4	794.7	756.3	721.1	699.6	678.9	658.3	641.4	634.5	616.9
42.5°	849.7	796.0	749.3	707.3	683.7	661.0	634.8	619.6	602.2	591.0	580.1
45°	770.1	722.6	682.8	648.3	622.2	598.5	581.6	556.3	546.4	524.2	515.0
47.5°	700.3	656.1	618.1	585.3	559.9	544.4	519.7	499.9	484.0	470.4	458.6
50°	650.6	613.8	577.0	547.9	524.9	502.7	477.4	467.4	442.9	436.0	429.1
52.5°	605.2	570.3	536.6	508.1	485.1	463.5	441.2	428.2	411.7	404.8	399.7
55°	541.8	508.1	475.9	450.6	427.6	405.4	391.6	375.5	367.8	362.5	356.3
57.5°	478.0	447.7	423.0	397.4	374.3	356.6	340.7	331.0	323.1	316.0	308.7
60°	437.6	408.4	386.2	362.5	338.7	324.1	311.9	300.4	291.2	280.5	277.4
62.5°	394.6	369.2	348.8	325.7	305.0	291.7	280.0	269.1	258.1	242.5	238.2
65°	335.6	315.7	294.3	275.1	256.7	243.7	226.8	214.6	210.0	208.4	207.7
67.5°	282.3	263.5	245.1	225.4	208.7	196.6	188.1	186.2	183.0	182.1	179.9
70°	246.8	229.1	210.7	192.3	176.3	174.0	170.9	167.8	164.0	162.5	160.9
72.5°	214.9	196.6	178.2	163.5	156.6	153.7	150.7	147.6	145.0	143.5	142.5
75°	164.8	147.9	135.6	130.3	126.4	124.1	119.5	117.2	115.7	113.4	112.6
77.5°	118.6	109.1	103.5	100.1	96.1	93.6	91.0	88.7	87.1	86.6	85.4
80°	90.4	85.8	82.0	77.4	75.9	72.8	72.0	69.7	70.5	68.2	68.2
82.5°	70.2	64.4	61.2	59.0	57.5	55.0	54.3	53.2	53.3	51.6	51.6
85°	36.0	34.5	33.0	31.4	31.4	29.1	29.9	29.1	29.1	27.6	26.8
87.5°	14.0	14.0	13.8	15.2	16.4	16.0	15.8	15.0	14.6	15.0	14.6
90°	12.0	15.0	20.0	26.9	32.9	33.9	32.9	31.9	29.9	31.9	32.9
92.5°	35.9	45.3	67.9	99.6	127.9	129.7	109.6	87.0	74.7	66.3	60.1
95°	73.9	97.8	143.7	230.5	346.3	391.2	342.3	261.5	200.6	158.7	136.7
97.5°	104.8	131.9	189.6	310.6	503.0	667.9	700.6	610.2	499.2	391.2	319.2
100°	124.8	152.7	205.6	327.4	542.9	788.4	932.2	911.2	787.4	650.7	530.0
102.5°	143.1	171.1	220.0	328.2	527.8	792.4	1018.4	1108.4	1080.5	980.5	852.5
105°	169.7	197.6	244.5	333.3	498.0	739.5	1005.0	1212.6	1325.4	1338.4	1305.4
107.5°	196.0	224.2	269.7	347.1	483.2	682.9	917.4	1137.6	1307.4	1411.2	1459.5
110°	213.6	242.5	286.4	358.3	480.1	655.7	862.3	1072.9	1251.5	1379.3	1461.1



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.3	260.1	302.4	370.3	480.8	638.1	824.0	1013.8	1185.3	1321.8	1415.6
115°	257.5	284.4	327.4	388.2	485.0	618.8	776.5	941.1	1094.8	1225.6	1328.4
117.5°	282.6	310.6	350.3	407.4	492.2	609.4	746.5	886.4	1021.4	1139.9	1236.4
120°	299.4	327.4	366.3	420.2	497.0	603.8	730.6	859.3	983.1	1088.8	1179.7
122.5°	316.2	344.9	381.4	431.3	502.6	600.6	717.0	837.7	951.1	1051.3	1133.4
125°	340.3	368.3	404.2	449.1	511.0	594.8	697.6	806.4	909.2	997.0	1071.9
127.5°	361.7	390.4	425.4	465.7	519.6	591.4	679.7	775.5	868.5	951.3	1020.4
130°	375.3	403.2	438.1	476.1	526.0	589.8	667.7	755.5	841.3	920.2	986.1
132.5°	388.0	416.0	449.3	486.4	532.3	589.0	658.1	736.3	815.8	888.2	950.1
135°	405.2	433.1	465.1	500.0	539.9	587.8	644.7	709.6	775.5	841.3	897.2
137.5°	420.4	446.3	477.9	510.4	546.7	587.6	635.3	688.2	743.3	795.6	844.3
140°	429.2	455.1	485.0	516.0	549.9	586.8	629.8	674.7	722.6	768.5	812.4
142.5°	437.1	461.5	490.6	520.8	552.3	586.8	624.2	663.5	704.2	743.7	780.5
145°	450.1	472.1	499.0	527.0	554.9	584.8	616.8	647.7	680.7	711.6	740.5
147.5°	460.9	480.5	505.8	530.4	555.7	581.3	609.2	635.5	661.5	685.6	706.8
150°	468.1	486.0	509.0	531.9	554.9	578.9	602.8	626.8	648.7	669.7	687.6
152.5°	475.3	491.6	512.2	532.7	553.3	574.9	597.2	618.0	638.3	656.1	671.7
155°	485.0	500.0	517.0	533.9	550.9	567.9	586.8	605.8	621.8	636.7	647.7
157.5°	493.4	506.0	520.4	533.9	546.3	560.7	577.1	591.6	605.0	617.6	626.2
160°	499.0	510.0	522.0	533.9	543.9	555.9	569.9	582.8	593.8	604.8	611.8
162.5°	503.8	512.4	522.8	533.1	541.5	551.9	563.5	574.1	583.4	592.8	598.2
165°	509.0	515.0	524.0	531.0	536.9	543.9	552.9	560.9	567.9	574.9	578.9
167.5°	513.4	517.2	523.8	529.6	532.3	536.9	542.5	548.3	553.7	558.5	562.1
170°	515.0	518.0	523.0	528.0	530.0	532.9	536.9	541.9	544.9	548.9	550.9
172.5°	516.6	518.8	522.2	525.6	526.8	528.2	531.4	534.7	536.9	540.1	541.3
175°	518.0	519.0	521.0	523.0	522.0	523.0	524.0	527.0	528.0	529.0	530.0
177.5°	519.0	519.0	519.8	521.4	519.8	519.0	519.8	521.4	521.4	522.2	522.2
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2117.8	2119.0	2117.2	2118.4	2117.2	2119.0	2117.8	2124.5	2125.7	2127.0	2125.7
5°	1973.2	1964.0	1962.5	1960.2	1962.5	1964.0	1973.2	1977.1	1980.1	1986.3	1997.0
7.5°	1800.7	1799.3	1795.5	1790.1	1795.5	1799.3	1800.7	1813.8	1824.3	1836.2	1858.1
10°	1689.7	1685.9	1685.1	1679.7	1685.1	1685.9	1689.7	1706.6	1718.8	1735.7	1765.6
12.5°	1559.7	1535.1	1532.5	1519.1	1532.5	1535.1	1559.7	1581.5	1614.6	1630.9	1662.6
15°	1328.0	1323.4	1308.1	1298.1	1308.1	1323.4	1328.0	1346.4	1358.7	1403.1	1454.5
17.5°	1195.6	1180.6	1175.8	1173.7	1175.8	1180.6	1195.6	1204.5	1222.0	1245.4	1276.4
20°	1110.4	1096.6	1094.3	1092.8	1094.3	1096.6	1110.4	1121.1	1134.9	1160.2	1192.4
22.5°	1051.5	1037.1	1031.1	1026.5	1031.1	1037.1	1051.5	1059.8	1072.4	1092.1	1113.9
25°	951.0	945.6	942.6	941.0	942.6	945.6	951.0	958.7	970.9	997.7	1020.7
27.5°	872.4	860.6	858.3	854.3	858.3	860.6	872.4	886.0	898.7	910.8	931.4
30°	827.6	823.8	818.4	813.8	818.4	823.8	827.6	834.5	842.9	863.6	883.6
32.5°	774.9	771.7	766.9	764.8	766.9	771.7	774.9	784.2	801.9	814.6	829.0
35°	716.5	705.8	701.2	694.3	701.2	705.8	716.5	724.2	731.1	741.8	767.8
37.5°	654.7	649.1	642.6	644.9	642.6	649.1	654.7	658.0	672.5	687.4	698.7
40°	606.9	603.1	601.6	600.8	601.6	603.1	606.9	616.9	634.5	641.4	658.3
42.5°	568.9	558.3	554.3	554.2	554.3	558.3	568.9	580.1	591.0	602.2	619.6
45°	511.1	501.2	494.3	495.0	494.3	501.2	511.1	515.0	524.2	546.4	556.3
47.5°	452.0	451.7	447.4	448.7	447.4	451.7	452.0	458.6	470.4	484.0	499.9
50°	423.8	419.2	416.1	416.9	416.1	419.2	423.8	429.1	436.0	442.9	467.4
52.5°	396.8	392.8	390.4	393.6	390.4	392.8	396.8	399.7	404.8	411.7	428.2
55°	352.5	347.9	347.1	346.4	347.1	347.9	352.5	356.3	362.5	367.8	375.5
57.5°	303.0	299.9	295.3	293.3	295.3	299.9	303.0	308.7	316.0	323.1	331.0
60°	267.4	261.3	253.6	252.9	253.6	261.3	267.4	277.4	280.5	291.2	300.4
62.5°	234.9	233.7	232.2	232.0	232.2	233.7	234.9	238.2	242.5	258.1	269.1
65°	206.1	205.4	206.1	206.9	206.1	205.4	206.1	207.7	208.4	210.0	214.6
67.5°	179.6	178.2	176.9	177.5	176.9	178.2	179.6	179.9	182.1	183.0	186.2
70°	159.4	158.6	157.9	157.9	157.9	158.6	159.4	160.9	162.5	164.0	167.8
72.5°	139.8	139.6	138.9	138.2	138.9	139.6	139.8	142.5	143.5	145.0	147.6
75°	111.9	110.3	110.3	110.3	110.3	110.3	111.9	112.6	113.4	115.7	117.2
77.5°	85.2	84.4	83.7	83.1	83.7	84.4	85.2	85.4	86.6	87.1	88.7
80°	67.4	66.7	65.9	65.9	65.9	66.7	67.4	68.2	68.2	70.5	69.7
82.5°	51.5	50.7	50.6	50.0	50.6	50.7	51.5	51.6	51.6	53.3	53.2
85°	27.6	28.4	27.6	29.1	27.6	28.4	27.6	26.8	27.6	29.1	29.1
87.5°	14.6	13.9	14.6	13.9	14.6	13.9	14.6	14.6	15.0	14.6	15.0
90°	32.9	32.9	32.9	32.9	32.9	32.9	32.9	32.9	31.9	29.9	31.9
92.5°	59.3	56.1	56.9	55.3	56.9	56.1	59.3	60.1	66.3	74.7	87.0
95°	123.8	115.8	112.8	113.8	112.8	115.8	123.8	136.7	158.7	200.6	261.5
97.5°	271.5	246.9	232.3	224.0	232.3	246.9	271.5	319.2	391.2	499.2	610.2
100°	447.1	404.2	375.3	357.3	375.3	404.2	447.1	530.0	650.7	787.4	911.2
102.5°	762.5	689.2	653.1	628.8	653.1	689.2	762.5	852.5	980.5	1080.5	1108.4
105°	1243.5	1181.7	1138.7	1124.8	1138.7	1181.7	1243.5	1305.4	1338.4	1325.4	1212.6
107.5°	1467.3	1463.9	1455.3	1436.8	1455.3	1463.9	1467.3	1459.5	1411.2	1307.4	1137.6
110°	1504.0	1523.0	1532.0	1531.0	1532.0	1523.0	1504.0	1461.1	1379.3	1251.5	1072.9



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1475.3	1507.0	1524.0	1529.4	1524.0	1507.0	1475.3	1415.6	1321.8	1185.3	1013.8
115°	1399.2	1445.1	1471.1	1480.1	1471.1	1445.1	1399.2	1328.4	1225.6	1094.8	941.1
117.5°	1308.6	1357.1	1384.5	1392.0	1384.5	1357.1	1308.6	1236.4	1139.9	1021.4	886.4
120°	1249.5	1296.4	1325.4	1335.4	1325.4	1296.4	1249.5	1179.7	1088.8	983.1	859.3
122.5°	1196.0	1242.1	1267.9	1276.3	1267.9	1242.1	1196.0	1133.4	1051.3	951.1	837.7
125°	1129.8	1167.7	1192.6	1200.6	1192.6	1167.7	1129.8	1071.9	997.0	909.2	806.4
127.5°	1070.9	1106.4	1128.0	1134.4	1128.0	1106.4	1070.9	1020.4	951.3	868.5	775.5
130°	1035.0	1068.9	1088.8	1096.8	1088.8	1068.9	1035.0	986.1	920.2	841.3	755.5
132.5°	998.2	1032.2	1050.5	1057.7	1050.5	1032.2	998.2	950.1	888.2	815.8	736.3
135°	940.1	973.1	991.0	995.0	991.0	973.1	940.1	897.2	841.3	775.5	709.6
137.5°	883.5	911.8	927.6	933.6	927.6	911.8	883.5	844.3	795.6	743.3	688.2
140°	844.3	870.3	885.3	891.2	885.3	870.3	844.3	812.4	768.5	722.6	674.7
142.5°	810.8	834.4	847.7	848.9	847.7	834.4	810.8	780.5	743.7	704.2	663.5
145°	764.5	781.5	791.4	794.4	791.4	781.5	764.5	740.5	711.6	680.7	647.7
147.5°	726.6	740.1	746.9	748.7	746.9	740.1	726.6	706.8	685.6	661.5	635.5
150°	702.6	714.6	720.6	721.6	720.6	714.6	702.6	687.6	669.7	648.7	626.8
152.5°	683.4	693.8	698.2	698.4	698.2	693.8	683.4	671.7	656.1	638.3	618.0
155°	658.7	665.7	669.7	667.7	669.7	665.7	658.7	647.7	636.7	621.8	605.8
157.5°	633.9	639.7	641.5	641.5	641.5	639.7	633.9	626.2	617.6	605.0	591.6
160°	618.8	623.8	624.8	624.8	624.8	623.8	618.8	611.8	604.8	593.8	582.8
162.5°	605.2	608.6	609.6	608.8	609.6	608.6	605.2	598.2	592.8	583.4	574.1
165°	582.8	586.8	586.8	585.8	586.8	586.8	582.8	578.9	574.9	567.9	560.9
167.5°	563.9	566.1	565.9	564.7	565.9	566.1	563.9	562.1	558.5	553.7	548.3
170°	551.9	554.9	553.9	551.9	553.9	554.9	551.9	550.9	548.9	544.9	541.9
172.5°	542.3	543.7	542.7	541.5	542.7	543.7	542.3	541.3	540.1	536.9	534.7
175°	530.0	531.0	530.0	528.0	530.0	531.0	530.0	530.0	529.0	528.0	527.0
177.5°	522.2	522.2	521.4	519.8	521.4	522.2	522.2	522.2	522.2	521.4	521.4
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2120.8	2129.4	2142.3	2149.6	2161.9	2169.9	2174.2	2182.1	2186.4	2201.8	2217.7
5°	2002.4	2014.6	2036.1	2056.0	2077.5	2099.7	2115.8	2134.2	2151.0	2180.1	2210.8
7.5°	1866.6	1883.6	1916.8	1948.6	1986.0	2017.4	2045.1	2076.5	2104.6	2146.3	2189.8
10°	1764.8	1794.7	1838.4	1868.3	1917.3	1948.7	1992.4	2026.9	2066.0	2121.1	2170.2
12.5°	1677.1	1713.2	1748.3	1789.8	1833.9	1886.2	1934.2	1978.5	2024.9	2081.9	2139.5
15°	1518.1	1570.2	1624.6	1666.7	1726.5	1781.7	1837.6	1897.4	1954.1	2022.3	2097.4
17.5°	1313.3	1373.7	1465.2	1537.4	1607.6	1662.9	1732.2	1804.5	1871.3	1953.6	2037.2
20°	1220.7	1265.2	1327.2	1424.6	1530.3	1589.3	1659.8	1739.5	1816.1	1905.8	1995.5
22.5°	1146.5	1186.1	1235.9	1311.8	1429.8	1510.2	1583.8	1664.7	1753.6	1845.1	1944.6
25°	1040.6	1068.2	1120.3	1181.6	1262.9	1395.4	1475.9	1557.1	1653.7	1751.8	1865.2
27.5°	961.1	985.9	1019.8	1078.3	1138.7	1233.9	1361.9	1450.5	1546.7	1657.1	1774.8
30°	900.4	929.5	967.1	1008.5	1074.4	1148.7	1276.7	1379.4	1474.4	1587.8	1713.5
32.5°	856.3	879.3	911.3	953.3	1008.2	1079.4	1181.6	1306.4	1399.0	1518.5	1649.7
35°	783.9	810.8	836.8	876.7	921.1	986.2	1063.6	1197.0	1288.9	1406.9	1538.7
37.5°	724.3	740.7	769.5	801.1	848.0	896.6	963.7	1083.3	1182.7	1298.6	1433.5
40°	678.9	699.6	721.1	756.3	794.7	841.4	907.3	996.2	1110.4	1223.8	1355.6
42.5°	634.8	661.0	683.7	707.3	749.3	796.0	849.7	925.1	1041.7	1149.0	1277.1
45°	581.6	598.5	622.2	648.3	682.8	722.6	770.1	836.0	947.9	1040.6	1161.0
47.5°	519.7	544.4	559.9	585.3	618.1	656.1	700.3	757.3	847.8	934.7	1046.3
50°	477.4	502.7	524.9	547.9	577.0	613.8	650.6	705.8	778.6	869.8	974.0
52.5°	441.2	463.5	485.1	508.1	536.6	570.3	605.2	653.7	716.0	799.9	901.0
55°	391.6	405.4	427.6	450.6	475.9	508.1	541.8	582.4	636.0	706.5	788.5
57.5°	340.7	356.6	374.3	397.4	423.0	447.7	478.0	514.8	557.1	620.9	691.1
60°	311.9	324.1	338.7	362.5	386.2	408.4	437.6	468.2	508.1	563.2	623.0
62.5°	280.0	291.7	305.0	325.7	348.8	369.2	394.6	427.1	460.9	511.1	563.5
65°	226.8	243.7	256.7	275.1	294.3	315.7	335.6	361.7	391.6	431.4	478.2
67.5°	188.1	196.6	208.7	225.4	245.1	263.5	282.3	302.7	328.6	359.4	396.5
70°	170.9	174.0	176.3	192.3	210.7	229.1	246.8	265.9	288.1	313.4	345.6
72.5°	150.7	153.7	156.6	163.5	178.2	196.6	214.9	229.1	250.1	271.1	297.2
75°	119.5	124.1	126.4	130.3	135.6	147.9	164.8	178.5	190.8	206.9	227.6
77.5°	91.0	93.6	96.1	100.1	103.5	109.1	118.6	131.0	142.5	151.9	166.1
80°	72.0	72.8	75.9	77.4	82.0	85.8	90.4	100.4	111.9	115.7	125.7
82.5°	54.3	55.0	57.5	59.0	61.2	64.4	70.2	72.8	81.8	86.9	93.2
85°	29.9	29.1	31.4	31.4	33.0	34.5	36.0	39.8	42.1	48.3	49.8
87.5°	15.8	16.0	16.4	15.2	13.8	14.0	14.0	14.3	15.1	16.1	18.0
90°	32.9	33.9	32.9	26.9	20.0	15.0	12.0	10.0	8.0	4.0	1.0
92.5°	109.6	129.7	127.9	99.6	67.9	45.3	35.9	29.1	24.8	17.6	12.2
95°	342.3	391.2	346.3	230.5	143.7	97.8	73.9	57.9	48.9	38.9	34.9
97.5°	700.6	667.9	503.0	310.6	189.6	131.9	104.8	86.4	72.9	62.3	56.9
100°	932.2	788.4	542.9	327.4	205.6	152.7	124.8	104.8	88.8	79.8	76.8
102.5°	1018.4	792.4	527.8	328.2	220.0	171.1	143.1	122.4	106.4	97.4	95.2
105°	1005.0	739.5	498.0	333.3	244.5	197.6	169.7	147.7	132.7	125.8	121.8
107.5°	917.4	682.9	483.2	347.1	269.7	224.2	196.0	174.3	160.5	153.7	150.5
110°	862.3	655.7	480.1	358.3	286.4	242.5	213.6	192.6	179.6	173.7	169.7



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	824.0	638.1	480.8	370.3	302.4	260.1	230.3	210.2	198.0	191.2	187.2
115°	776.5	618.8	485.0	388.2	327.4	284.4	257.5	237.5	225.6	219.6	214.6
117.5°	746.5	609.4	492.2	407.4	350.3	310.6	282.6	263.5	252.9	246.9	242.9
120°	730.6	603.8	497.0	420.2	366.3	327.4	299.4	279.4	270.5	264.5	260.5
122.5°	717.0	600.6	502.6	431.3	381.4	344.9	316.2	296.2	286.4	280.4	277.3
125°	697.6	594.8	511.0	449.1	404.2	368.3	340.3	320.4	308.4	302.4	299.4
127.5°	679.7	591.4	519.6	465.7	425.4	390.4	361.7	342.5	329.3	321.0	317.0
130°	667.7	589.8	526.0	476.1	438.1	403.2	375.3	355.3	341.3	331.3	327.4
132.5°	658.1	589.0	532.3	486.4	449.3	416.0	388.0	367.3	352.5	341.7	336.9
135°	644.7	587.8	539.9	500.0	465.1	433.1	405.2	382.2	367.3	355.3	351.3
137.5°	635.3	587.6	546.7	510.4	477.9	446.3	420.4	397.6	381.6	369.7	364.9
140°	629.8	586.8	549.9	516.0	485.0	455.1	429.2	407.2	391.2	379.3	375.3
142.5°	624.2	586.8	552.3	520.8	490.6	461.5	437.1	416.0	400.0	388.8	385.6
145°	616.8	584.8	554.9	527.0	499.0	472.1	450.1	430.2	415.2	405.2	401.2
147.5°	609.2	581.3	555.7	530.4	505.8	480.5	460.9	444.3	430.5	421.0	418.0
150°	602.8	578.9	554.9	531.9	509.0	486.0	468.1	453.1	440.1	432.1	429.2
152.5°	597.2	574.9	553.3	532.7	512.2	491.6	475.3	461.1	449.7	441.7	440.3
155°	586.8	567.9	550.9	533.9	517.0	500.0	485.0	474.1	463.1	457.1	456.1
157.5°	577.1	560.7	546.3	533.9	520.4	506.0	493.4	484.6	475.1	470.3	469.3
160°	569.9	555.9	543.9	533.9	522.0	510.0	499.0	491.0	483.0	479.1	478.1
162.5°	563.5	551.9	541.5	533.1	522.8	512.4	503.8	496.6	490.2	486.2	486.8
165°	552.9	543.9	536.9	531.0	524.0	515.0	509.0	504.0	498.0	496.0	497.0
167.5°	542.5	536.9	532.3	529.6	523.8	517.2	513.4	509.8	506.0	504.2	505.4
170°	536.9	532.9	530.0	528.0	523.0	518.0	515.0	513.0	510.0	509.0	511.0
172.5°	531.4	528.2	526.8	525.6	522.2	518.8	516.6	515.4	512.4	513.0	514.2
175°	524.0	523.0	522.0	523.0	521.0	519.0	518.0	518.0	516.0	517.0	518.0
177.5°	519.8	519.0	519.8	521.4	519.8	519.0	519.0	519.0	517.4	518.2	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2218.3	2220.1	2232.4	2237.9	2249.0	2253.2	2258.2	2256.9	2256.9	2259.4	2276.5
5°	2223.1	2238.4	2261.4	2283.6	2305.1	2323.4	2335.7	2348.0	2352.6	2374.8	2394.7
7.5°	2215.1	2243.3	2281.3	2315.2	2355.8	2387.5	2413.9	2437.6	2453.9	2486.2	2519.3
10°	2204.7	2244.5	2287.4	2331.1	2387.0	2429.2	2472.1	2505.1	2515.8	2564.1	2591.7
12.5°	2183.8	2237.2	2291.7	2348.3	2403.0	2461.1	2508.3	2541.2	2578.9	2622.3	2673.2
15°	2152.6	2213.9	2285.1	2357.9	2436.1	2506.6	2557.2	2614.6	2656.0	2703.5	2748.0
17.5°	2107.7	2186.6	2277.2	2361.5	2451.9	2527.6	2597.2	2652.3	2681.5	2708.6	2715.2
20°	2072.1	2157.2	2263.7	2363.3	2453.7	2541.1	2610.0	2656.0	2663.7	2664.4	2623.8
22.5°	2033.5	2129.6	2241.0	2343.1	2451.3	2548.4	2602.1	2621.7	2591.3	2539.4	2460.8
25°	1962.5	2073.6	2203.1	2319.6	2437.6	2529.6	2548.0	2513.5	2407.0	2295.1	2153.3
27.5°	1885.6	2010.5	2149.3	2278.8	2404.5	2461.5	2421.8	2297.5	2105.7	1938.9	1736.8
30°	1829.2	1969.4	2105.8	2250.6	2367.1	2391.6	2300.5	2117.3	1893.5	1642.2	1440.7
32.5°	1764.8	1911.8	2061.7	2211.4	2308.9	2285.0	2134.3	1908.9	1646.5	1399.4	1208.9
35°	1672.8	1824.6	1986.3	2136.5	2198.5	2095.1	1869.8	1576.3	1308.1	1077.4	946.4
37.5°	1566.6	1731.9	1900.0	2037.9	2033.5	1861.1	1554.2	1251.2	1025.8	889.4	796.0
40°	1491.2	1658.3	1839.9	1956.4	1906.6	1682.0	1349.5	1063.6	898.9	790.1	721.9
42.5°	1418.9	1586.6	1767.0	1859.5	1772.9	1496.9	1165.6	941.6	805.7	720.8	665.5
45°	1295.8	1472.8	1639.9	1691.2	1536.4	1232.2	942.6	780.1	689.7	626.8	588.5
47.5°	1175.5	1349.6	1502.1	1503.0	1293.7	999.3	795.1	675.1	597.9	549.3	521.4
50°	1101.9	1267.5	1395.4	1375.5	1138.0	888.9	711.1	607.7	543.3	505.8	476.6
52.5°	1019.2	1179.8	1290.6	1233.9	1006.2	782.2	635.7	548.8	495.5	462.8	436.8
55°	898.9	1041.4	1119.6	1033.7	820.7	650.6	537.2	469.0	429.1	401.5	379.3
57.5°	780.7	898.3	947.5	847.5	676.0	539.5	454.4	403.2	363.7	343.9	332.4
60°	706.5	806.9	841.4	731.1	587.8	472.0	402.3	354.8	325.7	312.7	301.2
62.5°	633.6	715.6	729.8	628.7	512.4	413.2	353.3	313.1	293.8	281.4	270.5
65°	525.7	584.7	577.8	496.6	405.4	328.0	284.3	259.8	245.2	227.6	208.4
67.5°	432.8	468.8	447.1	386.2	309.4	254.9	226.4	207.8	189.7	173.0	168.6
70°	374.0	394.6	371.7	315.7	253.6	213.8	190.8	168.6	157.9	154.0	147.1
72.5°	317.6	324.8	299.9	252.0	206.4	177.0	154.6	142.2	136.4	133.2	128.7
75°	238.3	233.0	211.5	174.0	143.3	123.4	116.5	111.9	108.0	105.0	102.7
77.5°	167.4	159.5	140.4	115.9	99.8	90.3	86.1	83.7	81.8	80.3	78.0
80°	125.7	120.3	101.2	82.8	75.9	71.3	69.0	65.9	65.9	64.4	62.1
82.5°	92.0	86.0	69.3	60.7	56.9	54.1	52.4	50.6	50.0	50.3	48.6
85°	48.3	39.1	34.5	33.0	30.7	29.1	29.9	28.4	28.4	28.4	27.6
87.5°	15.5	13.2	13.0	12.8	14.0	15.0	15.8	17.0	17.8	17.0	17.4
90°	4.0	8.0	10.0	12.0	15.0	20.0	26.9	32.9	33.9	32.9	31.9
92.5°	17.6	24.8	29.1	35.9	45.3	67.9	99.6	127.9	129.7	109.6	87.0
95°	38.9	48.9	57.9	73.9	97.8	143.7	230.5	346.3	391.2	342.3	261.5
97.5°	62.3	72.9	86.4	104.8	131.9	189.6	310.6	503.0	667.9	700.6	610.2
100°	79.8	88.8	104.8	124.8	152.7	205.6	327.4	542.9	788.4	932.2	911.2
102.5°	97.4	106.4	122.4	143.1	171.1	220.0	328.2	527.8	792.4	1018.4	1108.4
105°	125.8	132.7	147.7	169.7	197.6	244.5	333.3	498.0	739.5	1005.0	1212.6
107.5°	153.7	160.5	174.3	196.0	224.2	269.7	347.1	483.2	682.9	917.4	1137.6
110°	173.7	179.6	192.6	213.6	242.5	286.4	358.3	480.1	655.7	862.3	1072.9



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	191.2	198.0	210.2	230.3	260.1	302.4	370.3	480.8	638.1	824.0	1013.8
115°	219.6	225.6	237.5	257.5	284.4	327.4	388.2	485.0	618.8	776.5	941.1
117.5°	246.9	252.9	263.5	282.6	310.6	350.3	407.4	492.2	609.4	746.5	886.4
120°	264.5	270.5	279.4	299.4	327.4	366.3	420.2	497.0	603.8	730.6	859.3
122.5°	280.4	286.4	296.2	316.2	344.9	381.4	431.3	502.6	600.6	717.0	837.7
125°	302.4	308.4	320.4	340.3	368.3	404.2	449.1	511.0	594.8	697.6	806.4
127.5°	321.0	329.3	342.5	361.7	390.4	425.4	465.7	519.6	591.4	679.7	775.5
130°	331.3	341.3	355.3	375.3	403.2	438.1	476.1	526.0	589.8	667.7	755.5
132.5°	341.7	352.5	367.3	388.0	416.0	449.3	486.4	532.3	589.0	658.1	736.3
135°	355.3	367.3	382.2	405.2	433.1	465.1	500.0	539.9	587.8	644.7	709.6
137.5°	369.7	381.6	397.6	420.4	446.3	477.9	510.4	546.7	587.6	635.3	688.2
140°	379.3	391.2	407.2	429.2	455.1	485.0	516.0	549.9	586.8	629.8	674.7
142.5°	388.8	400.0	416.0	437.1	461.5	490.6	520.8	552.3	586.8	624.2	663.5
145°	405.2	415.2	430.2	450.1	472.1	499.0	527.0	554.9	584.8	616.8	647.7
147.5°	421.0	430.5	444.3	460.9	480.5	505.8	530.4	555.7	581.3	609.2	635.5
150°	432.1	440.1	453.1	468.1	486.0	509.0	531.9	554.9	578.9	602.8	626.8
152.5°	441.7	449.7	461.1	475.3	491.6	512.2	532.7	553.3	574.9	597.2	618.0
155°	457.1	463.1	474.1	485.0	500.0	517.0	533.9	550.9	567.9	586.8	605.8
157.5°	470.3	475.1	484.6	493.4	506.0	520.4	533.9	546.3	560.7	577.1	591.6
160°	479.1	483.0	491.0	499.0	510.0	522.0	533.9	543.9	555.9	569.9	582.8
162.5°	486.2	490.2	496.6	503.8	512.4	522.8	533.1	541.5	551.9	563.5	574.1
165°	496.0	498.0	504.0	509.0	515.0	524.0	531.0	536.9	543.9	552.9	560.9
167.5°	504.2	506.0	509.8	513.4	517.2	523.8	529.6	532.3	536.9	542.5	548.3
170°	509.0	510.0	513.0	515.0	518.0	523.0	528.0	530.0	532.9	536.9	541.9
172.5°	513.0	512.4	515.4	516.6	518.8	522.2	525.6	526.8	528.2	531.4	534.7
175°	517.0	516.0	518.0	518.0	519.0	521.0	523.0	522.0	523.0	524.0	527.0
177.5°	518.2	517.4	519.0	519.0	519.0	519.8	521.4	519.8	519.0	519.8	521.4
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2282.7	2290.6	2294.3	2294.3	2298.6	2296.8	2294.9
5°	2413.9	2428.4	2431.5	2445.3	2455.2	2452.2	2453.7
7.5°	2544.3	2567.7	2590.9	2601.5	2603.1	2609.3	2611.6
10°	2624.6	2643.8	2679.8	2674.4	2701.2	2716.6	2691.3
12.5°	2701.8	2727.7	2752.7	2759.6	2774.8	2779.7	2769.7
15°	2771.7	2785.5	2787.1	2783.2	2787.8	2784.0	2769.4
17.5°	2706.4	2684.1	2638.7	2617.2	2600.2	2575.1	2565.0
20°	2598.5	2532.6	2456.0	2425.4	2389.3	2318.8	2335.7
22.5°	2365.6	2290.5	2213.9	2124.4	2081.6	2014.8	2010.8
25°	2003.1	1873.6	1731.1	1631.5	1573.2	1506.6	1477.4
27.5°	1557.4	1394.4	1277.6	1218.4	1164.6	1111.8	1109.6
30°	1264.4	1141.8	1051.4	1000.8	967.8	945.6	950.2
32.5°	1065.8	981.8	920.8	878.8	854.4	837.7	837.4
35°	871.3	813.8	774.7	757.1	739.5	727.2	728.0
37.5°	745.6	711.1	689.4	669.9	658.9	652.9	649.5
40°	681.2	652.9	636.0	624.5	615.3	606.9	605.4
42.5°	630.4	606.9	590.1	581.0	572.4	566.5	564.9
45°	559.4	540.2	524.9	515.0	511.1	505.8	505.8
47.5°	497.6	478.8	466.8	460.6	454.0	450.4	450.3
50°	456.0	441.4	430.7	426.8	421.5	419.2	418.4
52.5°	418.6	407.7	400.0	397.4	395.1	392.2	392.7
55°	367.8	361.7	358.6	356.3	352.5	347.9	351.0
57.5°	325.1	319.9	311.6	304.4	300.9	297.6	298.9
60°	295.0	284.3	273.6	265.1	262.8	255.9	255.9
62.5°	257.0	242.0	228.8	224.1	221.8	218.6	217.9
65°	197.7	191.6	188.5	185.4	183.9	183.9	182.4
67.5°	163.8	161.4	158.0	157.2	155.7	155.3	154.8
70°	144.8	141.8	140.2	139.5	137.9	138.7	136.4
72.5°	126.4	124.0	123.7	121.7	120.8	120.9	119.2
75°	99.6	99.6	98.9	98.1	96.6	95.8	96.6
77.5°	76.6	76.8	75.4	75.3	75.1	75.3	74.5
80°	61.3	62.1	61.3	60.5	59.8	60.5	59.8
82.5°	48.4	47.4	47.2	47.1	46.9	46.4	46.3
85°	27.6	28.4	27.6	26.8	26.8	26.8	27.6
87.5°	16.4	16.8	17.0	17.0	17.0	17.0	16.4
90°	29.9	31.9	32.9	32.9	32.9	32.9	32.9
92.5°	74.7	66.3	60.1	59.3	56.1	56.9	55.3
95°	200.6	158.7	136.7	123.8	115.8	112.8	113.8
97.5°	499.2	391.2	319.2	271.5	246.9	232.3	224.0
100°	787.4	650.7	530.0	447.1	404.2	375.3	357.3
102.5°	1080.5	980.5	852.5	762.5	689.2	653.1	628.8
105°	1325.4	1338.4	1305.4	1243.5	1181.7	1138.7	1124.8
107.5°	1307.4	1411.2	1459.5	1467.3	1463.9	1455.3	1436.8
110°	1251.5	1379.3	1461.1	1504.0	1523.0	1532.0	1531.0



TEST NUMBER: P331755

CATALOG NUMBER: S122RDIP-S1005D925U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1185.3	1321.8	1415.6	1475.3	1507.0	1524.0	1529.4
115°	1094.8	1225.6	1328.4	1399.2	1445.1	1471.1	1480.1
117.5°	1021.4	1139.9	1236.4	1308.6	1357.1	1384.5	1392.0
120°	983.1	1088.8	1179.7	1249.5	1296.4	1325.4	1335.4
122.5°	951.1	1051.3	1133.4	1196.0	1242.1	1267.9	1276.3
125°	909.2	997.0	1071.9	1129.8	1167.7	1192.6	1200.6
127.5°	868.5	951.3	1020.4	1070.9	1106.4	1128.0	1134.4
130°	841.3	920.2	986.1	1035.0	1068.9	1088.8	1096.8
132.5°	815.8	888.2	950.1	998.2	1032.2	1050.5	1057.7
135°	775.5	841.3	897.2	940.1	973.1	991.0	995.0
137.5°	743.3	795.6	844.3	883.5	911.8	927.6	933.6
140°	722.6	768.5	812.4	844.3	870.3	885.3	891.2
142.5°	704.2	743.7	780.5	810.8	834.4	847.7	848.9
145°	680.7	711.6	740.5	764.5	781.5	791.4	794.4
147.5°	661.5	685.6	706.8	726.6	740.1	746.9	748.7
150°	648.7	669.7	687.6	702.6	714.6	720.6	721.6
152.5°	638.3	656.1	671.7	683.4	693.8	698.2	698.4
155°	621.8	636.7	647.7	658.7	665.7	669.7	667.7
157.5°	605.0	617.6	626.2	633.9	639.7	641.5	641.5
160°	593.8	604.8	611.8	618.8	623.8	624.8	624.8
162.5°	583.4	592.8	598.2	605.2	608.6	609.6	608.8
165°	567.9	574.9	578.9	582.8	586.8	586.8	585.8
167.5°	553.7	558.5	562.1	563.9	566.1	565.9	564.7
170°	544.9	548.9	550.9	551.9	554.9	553.9	551.9
172.5°	536.9	540.1	541.3	542.3	543.7	542.7	541.5
175°	528.0	529.0	530.0	530.0	531.0	530.0	528.0
177.5°	521.4	522.2	522.2	522.2	522.2	521.4	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0

(END OF REPORT)