

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331623

Luminaire Tested: **S122RDIP-S290D530U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331623  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D530U835-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3196.1 lumens  
Efficiency: N/A  
Efficacy: 124.8 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35																												
1	95	91	87	84	86	83	80	77	67	65	63	52	51	49	39	38	37	31																												
2	87	80	74	70	79	73	68	64	59	56	53	46	44	42	35	33	32	27																												
3	80	71	64	59	72	65	59	54	53	48	45	42	39	36	31	29	28	23																												
4	73	63	56	50	66	58	51	46	47	43	39	37	34	32	28	26	25	21																												
5	67	56	49	43	61	52	45	40	42	38	34	34	30	28	26	24	22	18																												
6	62	51	43	38	56	47	40	35	38	34	30	31	27	25	24	21	20	17																												
7	58	46	39	33	52	42	36	31	35	30	27	28	25	22	22	19	18	15																												
8	54	42	35	30	49	39	32	28	32	27	24	26	22	20	20	18	16	14																												
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	19	16	15	12																												
10	47	35	28	24	42	32	26	22	27	23	19	22	19	16	18	15	13	11																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10555	10555	10555	10555
5°	11788	10621	9418	10621
10°	13080	10547	8163	10547
15°	13722	10392	6432	10392
20°	11897	10163	5565	10163
25°	7801	9850	4969	9850
30°	5252	9469	4497	9469
35°	4254	8990	4056	8990
40°	3781	8469	3754	8469
45°	3423	7857	3350	7857
50°	3115	7252	3105	7252
55°	2928	6579	2891	6579
60°	2451	5964	2422	5964
65°	2067	5414	2342	5414
70°	1907	4834	2209	4834
75°	1784	4211	2040	4211
80°	1646	3468	1813	3468
85°	1519	2742	1593	2742



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.0	1.9
10°-20°	172.7	5.4
20°-30°	222.5	7.0
30°-40°	211.5	6.6
40°-50°	181.1	5.7
50°-60°	137.9	4.3
60°-70°	87.2	2.7
70°-80°	43.5	1.4
80°-90°	14.0	0.4
90°-100°	118.6	3.7
100°-110°	402.4	12.6
110°-120°	427.5	13.4
120°-130°	351.9	11.0
130°-140°	282.6	8.8
140°-150°	213.5	6.7
150°-160°	150.1	4.7
160°-170°	88.3	2.8
170°-180°	28.8	0.9
0°-30°	457.2	14.3
0°-40°	668.6	20.9
0°-60°	987.7	30.9
0°-90°	1132.5	35.4
90°-120°	948.4	29.7
90°-150°	1796.4	56.2
90°-180°	2064.0	64.6
0°-180°	3196.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	654	654	654	654	654	
5°	727	655	581	655	727	72
15°	821	622	385	622	821	221
25°	438	553	279	553	438	208
35°	216	456	206	456	216	138
45°	150	344	147	344	150	116
55°	104	234	103	234	104	91
65°	54	142	61	142	54	55
75°	29	68	33	68	29	30
85°	8	15	9	15	8	9
90°	19	1	19	1	19	10
95°	65	20	65	20	65	85
105°	643	70	643	70	643	622
115°	846	123	846	123	846	828
125°	686	171	686	171	686	620
135°	569	201	569	201	569	442
145°	454	229	454	229	454	288
155°	382	261	382	261	382	178
165°	335	284	335	284	335	96
175°	302	296	302	296	302	29
180°	296	296	296	296	296	



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	680.3	680.8	681.4	680.1	680.1	679.0	676.6	674.8	669.7	669.0	669.0
5°	727.3	726.9	727.8	724.8	720.8	719.8	715.5	709.8	703.9	697.4	696.0
7.5°	774.1	773.4	771.6	771.1	768.0	761.1	754.2	746.8	737.0	727.4	722.6
10°	797.8	805.3	800.7	792.8	794.3	783.7	778.0	768.2	760.0	745.7	742.6
12.5°	821.0	824.0	822.5	818.0	816.0	808.6	800.9	792.4	777.3	764.5	753.3
15°	820.9	825.2	826.4	825.0	826.1	825.7	821.6	814.6	801.4	787.3	775.0
17.5°	760.3	763.3	770.8	775.8	782.2	795.6	802.3	804.8	802.9	794.8	786.2
20°	692.4	687.4	708.3	718.9	728.0	750.7	770.3	777.8	789.8	789.6	787.3
22.5°	596.0	597.2	617.0	629.7	656.2	679.0	701.2	729.4	752.7	768.1	777.1
25°	437.9	446.6	466.3	483.6	513.1	555.4	593.8	638.3	680.3	713.5	745.1
27.5°	328.9	329.6	345.2	361.2	378.7	413.3	461.7	514.8	574.7	624.2	681.0
30°	281.7	280.3	286.9	296.7	311.7	338.5	374.8	427.0	486.8	561.3	627.6
32.5°	248.2	248.3	253.3	260.5	272.9	291.0	315.9	358.4	414.8	488.1	565.8
35°	215.8	215.6	219.2	224.4	229.6	241.2	258.3	280.5	319.4	387.7	467.2
37.5°	192.5	193.5	195.3	198.6	204.3	210.8	221.0	236.0	263.6	304.1	370.9
40°	179.4	179.9	182.4	185.1	188.5	193.5	201.9	214.0	234.2	266.4	315.3
42.5°	167.5	167.9	169.7	172.2	174.9	179.9	186.9	197.3	213.7	238.8	279.1
45°	149.9	149.9	151.5	152.6	155.6	160.1	165.8	174.5	185.8	204.4	231.2
47.5°	133.5	133.5	134.6	136.5	138.4	141.9	147.5	154.6	162.8	177.2	200.1
50°	124.0	124.3	124.9	126.5	127.7	130.8	135.2	141.3	149.9	161.1	180.1
52.5°	116.4	116.3	117.1	117.8	118.6	120.8	124.1	129.5	137.2	146.9	162.7
55°	104.0	103.1	104.5	105.6	106.3	107.2	109.0	112.4	119.0	127.2	139.0
57.5°	88.6	88.2	89.2	90.2	92.4	94.8	96.4	98.5	101.9	107.8	119.5
60°	75.9	75.9	77.9	78.6	81.1	84.3	87.5	89.3	92.7	96.5	105.2
62.5°	64.6	64.8	65.7	66.4	67.8	71.7	76.2	80.2	83.4	87.1	92.8
65°	54.1	54.5	54.5	55.0	55.9	56.8	58.6	61.8	67.5	72.7	77.0
67.5°	45.9	46.0	46.2	46.6	46.8	47.8	48.6	50.0	51.3	56.2	61.6
70°	40.4	41.1	40.9	41.3	41.6	42.0	42.9	43.6	45.7	46.8	50.0
72.5°	35.3	35.8	35.8	36.1	36.7	36.8	37.5	38.2	39.5	40.4	42.2
75°	28.6	28.4	28.6	29.1	29.3	29.5	29.5	30.4	31.1	32.0	33.2
77.5°	22.1	22.3	22.3	22.3	22.4	22.8	22.7	23.1	23.8	24.3	24.8
80°	17.7	17.9	17.7	17.9	18.2	18.4	18.2	18.4	19.1	19.5	19.5
82.5°	13.7	13.8	13.9	13.9	14.0	14.0	14.4	14.4	14.9	14.8	15.0
85°	8.2	8.0	8.0	8.0	8.2	8.4	8.2	8.2	8.4	8.4	8.4
87.5°	6.7	6.9	6.9	6.9	6.9	6.7	6.5	6.9	6.9	7.1	6.9
90°	18.8	18.8	18.8	18.8	18.8	18.2	17.1	18.2	18.8	19.4	18.8
92.5°	31.6	32.5	32.1	33.9	34.3	37.9	42.7	49.7	62.6	74.1	73.1
95°	65.0	64.4	66.2	70.7	78.1	90.7	114.6	149.4	195.6	223.6	197.9
97.5°	128.0	132.8	141.1	155.1	182.4	223.6	285.3	348.7	400.3	381.6	287.4
100°	204.2	214.4	231.0	255.5	302.8	371.8	450.0	520.7	532.6	450.5	310.2
102.5°	359.3	373.2	393.8	435.7	487.1	560.3	617.4	633.4	581.9	452.8	301.6
105°	642.7	650.7	675.2	710.6	745.9	764.8	757.3	692.9	574.3	422.6	284.6
107.5°	821.0	831.6	836.5	838.4	834.0	806.4	747.1	650.0	524.2	390.2	276.1
110°	874.8	875.4	870.3	859.4	834.9	788.1	715.1	613.1	492.7	374.7	274.3



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	873.9	870.8	861.1	843.0	808.9	755.3	677.3	579.3	470.8	364.6	274.8
115°	845.7	840.6	825.8	799.5	759.1	700.3	625.6	537.8	443.7	353.6	277.2
117.5°	795.4	791.1	775.5	747.8	706.5	651.4	583.6	506.5	426.6	348.2	281.3
120°	763.0	757.3	740.8	714.0	674.1	622.2	561.7	491.0	417.5	345.0	284.0
122.5°	729.3	724.5	709.8	683.4	647.6	600.7	543.5	478.7	409.7	343.2	287.2
125°	686.1	681.5	667.2	645.6	612.5	569.7	519.5	460.8	398.6	339.9	292.0
127.5°	648.2	644.5	632.2	611.9	583.1	543.6	496.3	443.1	388.4	338.0	296.9
130°	626.7	622.2	610.8	591.4	563.4	525.8	480.8	431.7	381.5	337.0	300.5
132.5°	604.4	600.3	589.8	570.4	542.9	507.6	466.2	420.8	376.0	336.6	304.2
135°	568.6	566.3	556.0	537.2	512.7	480.8	443.1	405.5	368.4	335.9	308.5
137.5°	533.4	530.0	521.0	504.8	482.5	454.6	424.8	393.3	363.0	335.8	312.4
140°	509.3	505.8	497.3	482.5	464.2	439.1	412.9	385.5	359.9	335.3	314.2
142.5°	485.1	484.4	476.8	463.3	446.0	425.0	402.4	379.1	356.7	335.3	315.6
145°	453.9	452.2	446.5	436.8	423.2	406.6	388.9	370.1	352.4	334.2	317.1
147.5°	427.8	426.8	422.9	415.2	403.9	391.8	378.0	363.2	348.1	332.1	317.5
150°	412.3	411.7	408.3	401.5	392.9	382.7	370.7	358.1	344.5	330.8	317.1
152.5°	399.1	399.0	396.5	390.5	383.8	374.9	364.8	353.1	341.3	328.5	316.2
155°	381.5	382.7	380.4	376.4	370.1	363.8	355.3	346.2	335.3	324.5	314.8
157.5°	366.6	366.6	365.6	362.2	357.8	352.9	345.7	338.1	329.7	320.4	312.2
160°	357.0	357.0	356.4	353.6	349.6	345.6	339.3	333.0	325.6	317.7	310.8
162.5°	347.9	348.3	347.8	345.8	341.8	338.8	333.4	328.0	322.0	315.4	309.4
165°	334.8	335.3	335.3	333.0	330.8	328.5	324.5	320.5	315.9	310.8	306.8
167.5°	322.7	323.4	323.5	322.2	321.2	319.1	316.4	313.3	310.0	306.8	304.2
170°	315.4	316.5	317.1	315.4	314.8	313.7	311.4	309.7	306.8	304.5	302.8
172.5°	309.4	310.1	310.7	309.9	309.3	308.6	306.8	305.6	303.6	301.8	301.0
175°	301.7	302.8	303.4	302.8	302.8	302.3	301.7	301.1	299.4	298.8	298.3
177.5°	297.0	297.9	298.4	298.4	298.4	298.4	297.9	297.9	297.0	296.5	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	669.4	667.9	666.6	663.4	661.7	658.1	657.6	657.4	652.7	648.1	646.8
5°	692.4	688.7	683.3	676.9	670.3	663.5	659.0	655.3	646.2	637.6	632.6
7.5°	715.5	707.7	698.3	686.3	676.2	665.0	656.6	649.1	636.2	623.8	615.5
10°	732.8	720.1	707.6	691.0	678.0	665.3	653.5	643.3	628.8	612.4	600.8
12.5°	743.5	729.5	712.3	696.1	679.3	663.1	647.3	634.2	617.1	600.2	586.5
15°	758.0	743.0	722.1	698.9	677.4	656.2	638.1	621.7	599.5	579.2	562.4
17.5°	769.9	749.2	726.8	700.0	675.0	648.2	624.8	603.9	579.1	554.7	534.9
20°	773.7	753.2	727.3	700.5	671.0	639.4	614.2	591.5	564.9	538.3	515.6
22.5°	771.3	755.4	726.6	694.5	664.3	631.3	602.8	576.4	546.9	519.8	493.5
25°	755.3	749.8	722.6	687.6	653.1	614.7	581.7	552.9	519.3	490.2	461.6
27.5°	717.9	729.7	712.8	675.5	637.1	596.0	558.9	526.1	491.2	458.5	430.0
30°	681.9	708.9	701.7	667.1	624.2	583.8	542.2	507.9	470.7	437.0	408.9
32.5°	632.7	677.3	684.4	655.5	611.1	566.7	523.1	489.0	450.1	414.7	387.2
35°	554.2	621.0	651.7	633.3	588.8	540.8	495.9	456.1	417.0	382.1	354.8
37.5°	460.7	551.7	602.8	604.1	563.2	513.4	464.4	424.9	384.9	350.6	321.1
40°	400.0	498.6	565.2	579.9	545.4	491.6	442.0	401.8	362.8	329.1	295.3
42.5°	345.5	443.7	525.5	551.2	523.8	470.3	420.6	378.6	340.6	308.8	274.2
45°	279.4	365.3	455.4	501.3	486.1	436.6	384.1	344.1	308.5	281.0	247.8
47.5°	235.7	296.2	383.5	445.5	445.3	400.1	348.4	310.2	277.1	251.3	224.5
50°	210.8	263.5	337.3	407.7	413.6	375.7	326.6	288.7	257.8	230.8	209.2
52.5°	188.4	231.9	298.2	365.8	382.6	349.7	302.1	267.1	237.1	212.2	193.8
55°	159.2	192.9	243.3	306.4	331.9	308.7	266.4	233.7	209.4	188.5	172.6
57.5°	134.7	159.9	200.4	251.2	280.8	266.3	231.4	204.8	184.0	165.1	152.6
60°	119.3	139.9	174.2	216.7	249.4	239.2	209.4	184.7	167.0	150.6	138.8
62.5°	104.7	122.5	151.9	186.4	216.3	212.1	187.8	167.0	151.5	136.6	126.6
65°	84.3	97.2	120.2	147.2	171.3	173.3	155.8	141.7	127.9	116.1	107.2
67.5°	67.1	75.6	91.7	114.5	132.5	139.0	128.3	117.5	106.5	97.4	89.7
70°	56.6	63.4	75.2	93.6	110.2	117.0	110.8	102.4	92.9	85.4	78.8
72.5°	45.8	52.5	61.2	74.7	88.9	96.3	94.1	88.1	80.4	74.1	67.9
75°	34.5	36.6	42.5	51.6	62.7	69.1	70.6	67.5	61.3	56.6	52.9
77.5°	25.5	26.8	29.6	34.3	41.6	47.3	49.6	49.2	45.0	42.3	38.8
80°	20.4	21.1	22.5	24.5	30.0	35.7	37.3	37.3	34.3	33.2	29.8
82.5°	15.5	16.0	16.9	18.0	20.5	25.5	27.3	27.6	25.8	24.3	21.6
85°	8.9	8.6	9.1	9.8	10.2	11.6	14.3	14.8	14.3	12.5	11.8
87.5°	6.2	5.6	5.0	4.5	4.4	4.4	4.8	5.4	5.0	4.9	4.8
90°	15.4	11.4	8.6	6.8	5.7	4.6	2.3	0.6	2.3	4.6	5.7
92.5°	56.9	38.8	25.9	20.5	16.7	14.1	10.0	7.0	10.0	14.1	16.7
95°	131.7	82.1	55.9	42.2	33.1	27.9	22.2	20.0	22.2	27.9	33.1
97.5°	177.5	108.4	75.4	59.9	49.4	41.6	35.6	32.5	35.6	41.6	49.4
100°	187.1	117.5	87.3	71.3	59.9	50.8	45.6	43.9	45.6	50.8	59.9
102.5°	187.5	125.7	97.7	81.8	69.9	60.8	55.7	54.4	55.7	60.8	69.9
105°	190.5	139.7	112.9	96.9	84.4	75.8	71.9	69.6	71.9	75.8	84.4
107.5°	198.3	154.1	128.1	112.0	99.6	91.7	87.8	86.0	87.8	91.7	99.6
110°	204.7	163.7	138.6	122.0	110.1	102.7	99.2	96.9	99.2	102.7	110.1





TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	211.6	172.8	148.6	131.6	120.1	113.1	109.3	107.0	109.3	113.1	120.1
115°	221.8	187.1	162.5	147.1	135.7	128.9	125.5	122.6	125.5	128.9	135.7
117.5°	232.8	200.2	177.5	161.5	150.6	144.5	141.1	138.8	141.1	144.5	150.6
120°	240.1	209.3	187.1	171.1	159.7	154.5	151.1	148.8	151.1	154.5	159.7
122.5°	246.5	218.0	197.1	180.7	169.3	163.7	160.3	158.4	160.3	163.7	169.3
125°	256.6	231.0	210.4	194.5	183.1	176.2	172.8	171.1	172.8	176.2	183.1
127.5°	266.1	243.1	223.1	206.7	195.7	188.2	183.4	181.1	183.4	188.2	195.7
130°	272.0	250.4	230.4	214.4	203.0	195.0	189.3	187.1	189.3	195.0	203.0
132.5°	278.0	256.7	237.7	221.7	209.9	201.4	195.3	192.5	195.3	201.4	209.9
135°	285.7	265.8	247.5	231.5	218.4	209.9	203.0	200.7	203.0	209.9	218.4
137.5°	291.6	273.1	255.0	240.2	227.2	218.1	211.2	208.5	211.2	218.1	227.2
140°	294.8	277.2	260.1	245.2	232.7	223.6	216.7	214.4	216.7	223.6	232.7
142.5°	297.6	280.4	263.7	249.8	237.7	228.6	222.2	220.4	222.2	228.6	237.7
145°	301.1	285.1	269.7	257.2	245.8	237.2	231.5	229.3	231.5	237.2	245.8
147.5°	303.1	289.0	274.5	263.4	253.9	246.0	240.5	238.8	240.5	246.0	253.9
150°	304.0	290.8	277.7	267.5	258.9	251.5	246.9	245.2	246.9	251.5	258.9
152.5°	304.4	292.7	280.9	271.6	263.5	257.0	252.4	251.6	252.4	257.0	263.5
155°	305.1	295.4	285.7	277.2	270.9	264.6	261.2	260.6	261.2	264.6	270.9
157.5°	305.1	297.3	289.1	282.0	276.9	271.5	268.7	268.1	268.7	271.5	276.9
160°	305.1	298.3	291.4	285.1	280.6	276.0	273.7	273.2	273.7	276.0	280.6
162.5°	304.6	298.7	292.8	287.9	283.8	280.1	277.8	278.2	277.8	280.1	283.8
165°	303.4	299.4	294.3	290.8	288.0	284.6	283.4	284.0	283.4	284.6	288.0
167.5°	302.6	299.3	295.5	293.4	291.3	289.1	288.1	288.8	288.1	289.1	291.3
170°	301.7	298.8	296.0	294.3	293.1	291.4	290.8	292.0	290.8	291.4	293.1
172.5°	300.3	298.4	296.4	295.2	294.5	292.8	293.1	293.8	293.1	292.8	294.5
175°	298.8	297.7	296.5	296.0	296.0	294.8	295.4	296.0	295.4	294.8	296.0
177.5°	297.9	297.0	296.5	296.5	296.5	295.6	296.1	297.0	296.1	295.6	296.5
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	644.5	643.2	640.8	637.2	635.0	631.2	628.7	630.1	630.5	630.1	629.8
5°	627.2	622.4	615.8	609.4	603.5	597.2	593.5	592.0	588.8	587.0	586.0
7.5°	606.2	598.0	588.7	577.6	568.2	558.3	553.3	550.8	544.3	540.8	537.7
10°	590.6	577.6	568.3	553.8	544.9	532.0	523.1	523.4	514.5	509.5	505.9
12.5°	573.3	559.1	543.6	530.5	518.2	507.8	497.1	492.8	483.4	478.6	468.8
15°	544.7	528.1	511.8	494.1	481.6	465.4	450.0	431.1	415.9	402.7	399.1
17.5°	513.5	492.9	476.5	455.7	434.3	407.2	389.3	378.3	369.2	362.2	357.0
20°	492.0	471.1	453.6	422.3	393.4	375.0	361.9	353.4	343.9	336.4	332.3
22.5°	469.5	447.7	423.8	388.8	366.3	351.6	339.9	330.2	323.7	317.9	314.1
25°	437.5	413.6	374.3	350.3	332.1	316.6	308.5	302.6	295.8	287.8	284.2
27.5°	403.7	365.8	337.5	319.6	302.3	292.3	284.9	276.1	270.0	266.4	262.6
30°	378.4	340.5	318.5	298.9	286.7	275.5	266.9	261.9	256.0	249.9	247.4
32.5°	350.3	320.0	298.8	282.6	270.1	260.6	253.8	245.7	241.5	237.7	232.5
35°	315.3	292.3	273.0	259.9	248.0	240.3	232.4	227.6	219.9	216.7	214.7
37.5°	285.7	265.8	251.4	237.5	228.1	219.6	214.7	207.1	203.8	199.3	195.0
40°	268.9	249.4	235.6	224.2	213.7	207.4	201.3	195.1	190.1	188.1	182.9
42.5°	251.9	236.0	222.1	209.7	202.7	195.9	188.2	183.7	178.5	175.2	172.0
45°	228.3	214.2	202.4	192.2	184.4	177.4	172.4	164.9	162.0	155.4	152.6
47.5°	207.6	194.5	183.2	173.5	166.0	161.4	154.1	148.2	143.5	139.4	135.9
50°	192.9	181.9	171.0	162.4	155.6	149.0	141.5	138.6	131.3	129.2	127.2
52.5°	179.4	169.0	159.1	150.6	143.8	137.4	130.8	126.9	122.0	120.0	118.5
55°	160.6	150.6	141.1	133.6	126.8	120.2	116.1	111.3	109.0	107.4	105.6
57.5°	141.7	132.7	125.4	117.8	110.9	105.7	101.0	98.1	95.8	93.7	91.5
60°	129.7	121.1	114.5	107.4	100.4	96.1	92.5	89.0	86.3	83.1	82.2
62.5°	117.0	109.4	103.4	96.5	90.4	86.5	83.0	79.8	76.5	71.9	70.6
65°	99.5	93.6	87.2	81.5	76.1	72.2	67.2	63.6	62.2	61.8	61.6
67.5°	83.7	78.1	72.6	66.8	61.9	58.3	55.7	55.2	54.2	54.0	53.3
70°	73.1	67.9	62.5	57.0	52.2	51.6	50.7	49.7	48.6	48.2	47.7
72.5°	63.7	58.3	52.8	48.5	46.4	45.6	44.7	43.7	43.0	42.5	42.3
75°	48.8	43.8	40.2	38.6	37.5	36.8	35.4	34.8	34.3	33.6	33.4
77.5°	35.2	32.3	30.7	29.7	28.5	27.8	27.0	26.3	25.8	25.7	25.3
80°	26.8	25.4	24.3	22.9	22.5	21.6	21.4	20.7	20.9	20.2	20.2
82.5°	20.8	19.1	18.1	17.5	17.0	16.3	16.1	15.8	15.8	15.3	15.3
85°	10.7	10.2	9.8	9.3	9.3	8.6	8.9	8.6	8.6	8.2	8.0
87.5°	4.8	5.0	5.2	6.0	6.7	6.6	6.5	6.2	6.0	6.2	6.1
90°	6.8	8.6	11.4	15.4	18.8	19.4	18.8	18.2	17.1	18.2	18.8
92.5°	20.5	25.9	38.8	56.9	73.1	74.1	62.6	49.7	42.7	37.9	34.3
95°	42.2	55.9	82.1	131.7	197.9	223.6	195.6	149.4	114.6	90.7	78.1
97.5°	59.9	75.4	108.4	177.5	287.4	381.6	400.3	348.7	285.3	223.6	182.4
100°	71.3	87.3	117.5	187.1	310.2	450.5	532.6	520.7	450.0	371.8	302.8
102.5°	81.8	97.7	125.7	187.5	301.6	452.8	581.9	633.4	617.4	560.3	487.1
105°	96.9	112.9	139.7	190.5	284.6	422.6	574.3	692.9	757.3	764.8	745.9
107.5°	112.0	128.1	154.1	198.3	276.1	390.2	524.2	650.0	747.1	806.4	834.0
110°	122.0	138.6	163.7	204.7	274.3	374.7	492.7	613.1	715.1	788.1	834.9



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	131.6	148.6	172.8	211.6	274.8	364.6	470.8	579.3	677.3	755.3	808.9
115°	147.1	162.5	187.1	221.8	277.2	353.6	443.7	537.8	625.6	700.3	759.1
117.5°	161.5	177.5	200.2	232.8	281.3	348.2	426.6	506.5	583.6	651.4	706.5
120°	171.1	187.1	209.3	240.1	284.0	345.0	417.5	491.0	561.7	622.2	674.1
122.5°	180.7	197.1	218.0	246.5	287.2	343.2	409.7	478.7	543.5	600.7	647.6
125°	194.5	210.4	231.0	256.6	292.0	339.9	398.6	460.8	519.5	569.7	612.5
127.5°	206.7	223.1	243.1	266.1	296.9	338.0	388.4	443.1	496.3	543.6	583.1
130°	214.4	230.4	250.4	272.0	300.5	337.0	381.5	431.7	480.8	525.8	563.4
132.5°	221.7	237.7	256.7	278.0	304.2	336.6	376.0	420.8	466.2	507.6	542.9
135°	231.5	247.5	265.8	285.7	308.5	335.9	368.4	405.5	443.1	480.8	512.7
137.5°	240.2	255.0	273.1	291.6	312.4	335.8	363.0	393.3	424.8	454.6	482.5
140°	245.2	260.1	277.2	294.8	314.2	335.3	359.9	385.5	412.9	439.1	464.2
142.5°	249.8	263.7	280.4	297.6	315.6	335.3	356.7	379.1	402.4	425.0	446.0
145°	257.2	269.7	285.1	301.1	317.1	334.2	352.4	370.1	388.9	406.6	423.2
147.5°	263.4	274.5	289.0	303.1	317.5	332.1	348.1	363.2	378.0	391.8	403.9
150°	267.5	277.7	290.8	304.0	317.1	330.8	344.5	358.1	370.7	382.7	392.9
152.5°	271.6	280.9	292.7	304.4	316.2	328.5	341.3	353.1	364.8	374.9	383.8
155°	277.2	285.7	295.4	305.1	314.8	324.5	335.3	346.2	355.3	363.8	370.1
157.5°	282.0	289.1	297.3	305.1	312.2	320.4	329.7	338.1	345.7	352.9	357.8
160°	285.1	291.4	298.3	305.1	310.8	317.7	325.6	333.0	339.3	345.6	349.6
162.5°	287.9	292.8	298.7	304.6	309.4	315.4	322.0	328.0	333.4	338.8	341.8
165°	290.8	294.3	299.4	303.4	306.8	310.8	315.9	320.5	324.5	328.5	330.8
167.5°	293.4	295.5	299.3	302.6	304.2	306.8	310.0	313.3	316.4	319.1	321.2
170°	294.3	296.0	298.8	301.7	302.8	304.5	306.8	309.7	311.4	313.7	314.8
172.5°	295.2	296.4	298.4	300.3	301.0	301.8	303.6	305.6	306.8	308.6	309.3
175°	296.0	296.5	297.7	298.8	298.3	298.8	299.4	301.1	301.7	302.3	302.8
177.5°	296.5	296.5	297.0	297.9	297.0	296.5	297.0	297.9	297.9	298.4	298.4
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	627.8	628.1	627.6	627.9	627.6	628.1	627.8	629.8	630.1	630.5	630.1
5°	584.9	582.2	581.7	581.1	581.7	582.2	584.9	586.0	587.0	588.8	592.0
7.5°	533.8	533.4	532.2	530.6	532.2	533.4	533.8	537.7	540.8	544.3	550.8
10°	500.9	499.7	499.5	497.9	499.5	499.7	500.9	505.9	509.5	514.5	523.4
12.5°	462.3	455.0	454.3	450.3	454.3	455.0	462.3	468.8	478.6	483.4	492.8
15°	393.7	392.3	387.7	384.8	387.7	392.3	393.7	399.1	402.7	415.9	431.1
17.5°	354.4	349.9	348.5	347.9	348.5	349.9	354.4	357.0	362.2	369.2	378.3
20°	329.1	325.1	324.4	323.9	324.4	325.1	329.1	332.3	336.4	343.9	353.4
22.5°	311.7	307.4	305.7	304.3	305.7	307.4	311.7	314.1	317.9	323.7	330.2
25°	281.9	280.3	279.4	278.9	279.4	280.3	281.9	284.2	287.8	295.8	302.6
27.5°	258.6	255.1	254.4	253.2	254.4	255.1	258.6	262.6	266.4	270.0	276.1
30°	245.3	244.2	242.6	241.2	242.6	244.2	245.3	247.4	249.9	256.0	261.9
32.5°	229.7	228.7	227.3	226.7	227.3	228.7	229.7	232.5	237.7	241.5	245.7
35°	212.4	209.2	207.8	205.8	207.8	209.2	212.4	214.7	216.7	219.9	227.6
37.5°	194.1	192.4	190.5	191.2	190.5	192.4	194.1	195.0	199.3	203.8	207.1
40°	179.9	178.8	178.3	178.1	178.3	178.8	179.9	182.9	188.1	190.1	195.1
42.5°	168.6	165.5	164.3	164.3	164.3	165.5	168.6	172.0	175.2	178.5	183.7
45°	151.5	148.6	146.5	146.7	146.5	148.6	151.5	152.6	155.4	162.0	164.9
47.5°	134.0	133.9	132.6	133.0	132.6	133.9	134.0	135.9	139.4	143.5	148.2
50°	125.6	124.3	123.3	123.6	123.3	124.3	125.6	127.2	129.2	131.3	138.6
52.5°	117.6	116.4	115.7	116.7	115.7	116.4	117.6	118.5	120.0	122.0	126.9
55°	104.5	103.1	102.9	102.7	102.9	103.1	104.5	105.6	107.4	109.0	111.3
57.5°	89.8	88.9	87.5	87.0	87.5	88.9	89.8	91.5	93.7	95.8	98.1
60°	79.3	77.5	75.2	75.0	75.2	77.5	79.3	82.2	83.1	86.3	89.0
62.5°	69.6	69.3	68.8	68.8	68.8	69.3	69.6	70.6	71.9	76.5	79.8
65°	61.1	60.9	61.1	61.3	61.1	60.9	61.1	61.6	61.8	62.2	63.6
67.5°	53.2	52.8	52.4	52.6	52.4	52.8	53.2	53.3	54.0	54.2	55.2
70°	47.2	47.0	46.8	46.8	46.8	47.0	47.2	47.7	48.2	48.6	49.7
72.5°	41.4	41.4	41.2	41.0	41.2	41.4	41.4	42.3	42.5	43.0	43.7
75°	33.2	32.7	32.7	32.7	32.7	32.7	33.2	33.4	33.6	34.3	34.8
77.5°	25.3	25.0	24.8	24.6	24.8	25.0	25.3	25.3	25.7	25.8	26.3
80°	20.0	19.8	19.5	19.5	19.5	19.8	20.0	20.2	20.2	20.9	20.7
82.5°	15.3	15.0	15.0	14.8	15.0	15.0	15.3	15.3	15.3	15.8	15.8
85°	8.2	8.4	8.2	8.6	8.2	8.4	8.2	8.0	8.2	8.6	8.6
87.5°	6.1	5.9	6.1	5.9	6.1	5.9	6.1	6.1	6.2	6.0	6.2
90°	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.2	17.1	18.2
92.5°	33.9	32.1	32.5	31.6	32.5	32.1	33.9	34.3	37.9	42.7	49.7
95°	70.7	66.2	64.4	65.0	64.4	66.2	70.7	78.1	90.7	114.6	149.4
97.5°	155.1	141.1	132.8	128.0	132.8	141.1	155.1	182.4	223.6	285.3	348.7
100°	255.5	231.0	214.4	204.2	214.4	231.0	255.5	302.8	371.8	450.0	520.7
102.5°	435.7	393.8	373.2	359.3	373.2	393.8	435.7	487.1	560.3	617.4	633.4
105°	710.6	675.2	650.7	642.7	650.7	675.2	710.6	745.9	764.8	757.3	692.9
107.5°	838.4	836.5	831.6	821.0	831.6	836.5	838.4	834.0	806.4	747.1	650.0
110°	859.4	870.3	875.4	874.8	875.4	870.3	859.4	834.9	788.1	715.1	613.1



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	843.0	861.1	870.8	873.9	870.8	861.1	843.0	808.9	755.3	677.3	579.3
115°	799.5	825.8	840.6	845.7	840.6	825.8	799.5	759.1	700.3	625.6	537.8
117.5°	747.8	775.5	791.1	795.4	791.1	775.5	747.8	706.5	651.4	583.6	506.5
120°	714.0	740.8	757.3	763.0	757.3	740.8	714.0	674.1	622.2	561.7	491.0
122.5°	683.4	709.8	724.5	729.3	724.5	709.8	683.4	647.6	600.7	543.5	478.7
125°	645.6	667.2	681.5	686.1	681.5	667.2	645.6	612.5	569.7	519.5	460.8
127.5°	611.9	632.2	644.5	648.2	644.5	632.2	611.9	583.1	543.6	496.3	443.1
130°	591.4	610.8	622.2	626.7	622.2	610.8	591.4	563.4	525.8	480.8	431.7
132.5°	570.4	589.8	600.3	604.4	600.3	589.8	570.4	542.9	507.6	466.2	420.8
135°	537.2	556.0	566.3	568.6	566.3	556.0	537.2	512.7	480.8	443.1	405.5
137.5°	504.8	521.0	530.0	533.4	530.0	521.0	504.8	482.5	454.6	424.8	393.3
140°	482.5	497.3	505.8	509.3	505.8	497.3	482.5	464.2	439.1	412.9	385.5
142.5°	463.3	476.8	484.4	485.1	484.4	476.8	463.3	446.0	425.0	402.4	379.1
145°	436.8	446.5	452.2	453.9	452.2	446.5	436.8	423.2	406.6	388.9	370.1
147.5°	415.2	422.9	426.8	427.8	426.8	422.9	415.2	403.9	391.8	378.0	363.2
150°	401.5	408.3	411.7	412.3	411.7	408.3	401.5	392.9	382.7	370.7	358.1
152.5°	390.5	396.5	399.0	399.1	399.0	396.5	390.5	383.8	374.9	364.8	353.1
155°	376.4	380.4	382.7	381.5	382.7	380.4	376.4	370.1	363.8	355.3	346.2
157.5°	362.2	365.6	366.6	366.6	366.6	365.6	362.2	357.8	352.9	345.7	338.1
160°	353.6	356.4	357.0	357.0	357.0	356.4	353.6	349.6	345.6	339.3	333.0
162.5°	345.8	347.8	348.3	347.9	348.3	347.8	345.8	341.8	338.8	333.4	328.0
165°	333.0	335.3	335.3	334.8	335.3	335.3	333.0	330.8	328.5	324.5	320.5
167.5°	322.2	323.5	323.4	322.7	323.4	323.5	322.2	321.2	319.1	316.4	313.3
170°	315.4	317.1	316.5	315.4	316.5	317.1	315.4	314.8	313.7	311.4	309.7
172.5°	309.9	310.7	310.1	309.4	310.1	310.7	309.9	309.3	308.6	306.8	305.6
175°	302.8	303.4	302.8	301.7	302.8	303.4	302.8	302.8	302.3	301.7	301.1
177.5°	298.4	298.4	297.9	297.0	297.9	298.4	298.4	298.4	298.4	297.9	297.9
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	628.7	631.2	635.0	637.2	640.8	643.2	644.5	646.8	648.1	652.7	657.4
5°	593.5	597.2	603.5	609.4	615.8	622.4	627.2	632.6	637.6	646.2	655.3
7.5°	553.3	558.3	568.2	577.6	588.7	598.0	606.2	615.5	623.8	636.2	649.1
10°	523.1	532.0	544.9	553.8	568.3	577.6	590.6	600.8	612.4	628.8	643.3
12.5°	497.1	507.8	518.2	530.5	543.6	559.1	573.3	586.5	600.2	617.1	634.2
15°	450.0	465.4	481.6	494.1	511.8	528.1	544.7	562.4	579.2	599.5	621.7
17.5°	389.3	407.2	434.3	455.7	476.5	492.9	513.5	534.9	554.7	579.1	603.9
20°	361.9	375.0	393.4	422.3	453.6	471.1	492.0	515.6	538.3	564.9	591.5
22.5°	339.9	351.6	366.3	388.8	423.8	447.7	469.5	493.5	519.8	546.9	576.4
25°	308.5	316.6	332.1	350.3	374.3	413.6	437.5	461.6	490.2	519.3	552.9
27.5°	284.9	292.3	302.3	319.6	337.5	365.8	403.7	430.0	458.5	491.2	526.1
30°	266.9	275.5	286.7	298.9	318.5	340.5	378.4	408.9	437.0	470.7	507.9
32.5°	253.8	260.6	270.1	282.6	298.8	320.0	350.3	387.2	414.7	450.1	489.0
35°	232.4	240.3	248.0	259.9	273.0	292.3	315.3	354.8	382.1	417.0	456.1
37.5°	214.7	219.6	228.1	237.5	251.4	265.8	285.7	321.1	350.6	384.9	424.9
40°	201.3	207.4	213.7	224.2	235.6	249.4	268.9	295.3	329.1	362.8	401.8
42.5°	188.2	195.9	202.7	209.7	222.1	236.0	251.9	274.2	308.8	340.6	378.6
45°	172.4	177.4	184.4	192.2	202.4	214.2	228.3	247.8	281.0	308.5	344.1
47.5°	154.1	161.4	166.0	173.5	183.2	194.5	207.6	224.5	251.3	277.1	310.2
50°	141.5	149.0	155.6	162.4	171.0	181.9	192.9	209.2	230.8	257.8	288.7
52.5°	130.8	137.4	143.8	150.6	159.1	169.0	179.4	193.8	212.2	237.1	267.1
55°	116.1	120.2	126.8	133.6	141.1	150.6	160.6	172.6	188.5	209.4	233.7
57.5°	101.0	105.7	110.9	117.8	125.4	132.7	141.7	152.6	165.1	184.0	204.8
60°	92.5	96.1	100.4	107.4	114.5	121.1	129.7	138.8	150.6	167.0	184.7
62.5°	83.0	86.5	90.4	96.5	103.4	109.4	117.0	126.6	136.6	151.5	167.0
65°	67.2	72.2	76.1	81.5	87.2	93.6	99.5	107.2	116.1	127.9	141.7
67.5°	55.7	58.3	61.9	66.8	72.6	78.1	83.7	89.7	97.4	106.5	117.5
70°	50.7	51.6	52.2	57.0	62.5	67.9	73.1	78.8	85.4	92.9	102.4
72.5°	44.7	45.6	46.4	48.5	52.8	58.3	63.7	67.9	74.1	80.4	88.1
75°	35.4	36.8	37.5	38.6	40.2	43.8	48.8	52.9	56.6	61.3	67.5
77.5°	27.0	27.8	28.5	29.7	30.7	32.3	35.2	38.8	42.3	45.0	49.2
80°	21.4	21.6	22.5	22.9	24.3	25.4	26.8	29.8	33.2	34.3	37.3
82.5°	16.1	16.3	17.0	17.5	18.1	19.1	20.8	21.6	24.3	25.8	27.6
85°	8.9	8.6	9.3	9.3	9.8	10.2	10.7	11.8	12.5	14.3	14.8
87.5°	6.5	6.6	6.7	6.0	5.2	5.0	4.8	4.8	4.9	5.0	5.4
90°	18.8	19.4	18.8	15.4	11.4	8.6	6.8	5.7	4.6	2.3	0.6
92.5°	62.6	74.1	73.1	56.9	38.8	25.9	20.5	16.7	14.1	10.0	7.0
95°	195.6	223.6	197.9	131.7	82.1	55.9	42.2	33.1	27.9	22.2	20.0
97.5°	400.3	381.6	287.4	177.5	108.4	75.4	59.9	49.4	41.6	35.6	32.5
100°	532.6	450.5	310.2	187.1	117.5	87.3	71.3	59.9	50.8	45.6	43.9
102.5°	581.9	452.8	301.6	187.5	125.7	97.7	81.8	69.9	60.8	55.7	54.4
105°	574.3	422.6	284.6	190.5	139.7	112.9	96.9	84.4	75.8	71.9	69.6
107.5°	524.2	390.2	276.1	198.3	154.1	128.1	112.0	99.6	91.7	87.8	86.0
110°	492.7	374.7	274.3	204.7	163.7	138.6	122.0	110.1	102.7	99.2	96.9



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	470.8	364.6	274.8	211.6	172.8	148.6	131.6	120.1	113.1	109.3	107.0
115°	443.7	353.6	277.2	221.8	187.1	162.5	147.1	135.7	128.9	125.5	122.6
117.5°	426.6	348.2	281.3	232.8	200.2	177.5	161.5	150.6	144.5	141.1	138.8
120°	417.5	345.0	284.0	240.1	209.3	187.1	171.1	159.7	154.5	151.1	148.8
122.5°	409.7	343.2	287.2	246.5	218.0	197.1	180.7	169.3	163.7	160.3	158.4
125°	398.6	339.9	292.0	256.6	231.0	210.4	194.5	183.1	176.2	172.8	171.1
127.5°	388.4	338.0	296.9	266.1	243.1	223.1	206.7	195.7	188.2	183.4	181.1
130°	381.5	337.0	300.5	272.0	250.4	230.4	214.4	203.0	195.0	189.3	187.1
132.5°	376.0	336.6	304.2	278.0	256.7	237.7	221.7	209.9	201.4	195.3	192.5
135°	368.4	335.9	308.5	285.7	265.8	247.5	231.5	218.4	209.9	203.0	200.7
137.5°	363.0	335.8	312.4	291.6	273.1	255.0	240.2	227.2	218.1	211.2	208.5
140°	359.9	335.3	314.2	294.8	277.2	260.1	245.2	232.7	223.6	216.7	214.4
142.5°	356.7	335.3	315.6	297.6	280.4	263.7	249.8	237.7	228.6	222.2	220.4
145°	352.4	334.2	317.1	301.1	285.1	269.7	257.2	245.8	237.2	231.5	229.3
147.5°	348.1	332.1	317.5	303.1	289.0	274.5	263.4	253.9	246.0	240.5	238.8
150°	344.5	330.8	317.1	304.0	290.8	277.7	267.5	258.9	251.5	246.9	245.2
152.5°	341.3	328.5	316.2	304.4	292.7	280.9	271.6	263.5	257.0	252.4	251.6
155°	335.3	324.5	314.8	305.1	295.4	285.7	277.2	270.9	264.6	261.2	260.6
157.5°	329.7	320.4	312.2	305.1	297.3	289.1	282.0	276.9	271.5	268.7	268.1
160°	325.6	317.7	310.8	305.1	298.3	291.4	285.1	280.6	276.0	273.7	273.2
162.5°	322.0	315.4	309.4	304.6	298.7	292.8	287.9	283.8	280.1	277.8	278.2
165°	315.9	310.8	306.8	303.4	299.4	294.3	290.8	288.0	284.6	283.4	284.0
167.5°	310.0	306.8	304.2	302.6	299.3	295.5	293.4	291.3	289.1	288.1	288.8
170°	306.8	304.5	302.8	301.7	298.8	296.0	294.3	293.1	291.4	290.8	292.0
172.5°	303.6	301.8	301.0	300.3	298.4	296.4	295.2	294.5	292.8	293.1	293.8
175°	299.4	298.8	298.3	298.8	297.7	296.5	296.0	296.0	294.8	295.4	296.0
177.5°	297.0	296.5	297.0	297.9	297.0	296.5	296.5	296.5	295.6	296.1	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	657.6	658.1	661.7	663.4	666.6	667.9	669.4	669.0	669.0	669.7	674.8
5°	659.0	663.5	670.3	676.9	683.3	688.7	692.4	696.0	697.4	703.9	709.8
7.5°	656.6	665.0	676.2	686.3	698.3	707.7	715.5	722.6	727.4	737.0	746.8
10°	653.5	665.3	678.0	691.0	707.6	720.1	732.8	742.6	745.7	760.0	768.2
12.5°	647.3	663.1	679.3	696.1	712.3	729.5	743.5	753.3	764.5	777.3	792.4
15°	638.1	656.2	677.4	698.9	722.1	743.0	758.0	775.0	787.3	801.4	814.6
17.5°	624.8	648.2	675.0	700.0	726.8	749.2	769.9	786.2	794.8	802.9	804.8
20°	614.2	639.4	671.0	700.5	727.3	753.2	773.7	787.3	789.6	789.8	777.8
22.5°	602.8	631.3	664.3	694.5	726.6	755.4	771.3	777.1	768.1	752.7	729.4
25°	581.7	614.7	653.1	687.6	722.6	749.8	755.3	745.1	713.5	680.3	638.3
27.5°	558.9	596.0	637.1	675.5	712.8	729.7	717.9	681.0	624.2	574.7	514.8
30°	542.2	583.8	624.2	667.1	701.7	708.9	681.9	627.6	561.3	486.8	427.0
32.5°	523.1	566.7	611.1	655.5	684.4	677.3	632.7	565.8	488.1	414.8	358.4
35°	495.9	540.8	588.8	633.3	651.7	621.0	554.2	467.2	387.7	319.4	280.5
37.5°	464.4	513.4	563.2	604.1	602.8	551.7	460.7	370.9	304.1	263.6	236.0
40°	442.0	491.6	545.4	579.9	565.2	498.6	400.0	315.3	266.4	234.2	214.0
42.5°	420.6	470.3	523.8	551.2	525.5	443.7	345.5	279.1	238.8	213.7	197.3
45°	384.1	436.6	486.1	501.3	455.4	365.3	279.4	231.2	204.4	185.8	174.5
47.5°	348.4	400.1	445.3	445.5	383.5	296.2	235.7	200.1	177.2	162.8	154.6
50°	326.6	375.7	413.6	407.7	337.3	263.5	210.8	180.1	161.1	149.9	141.3
52.5°	302.1	349.7	382.6	365.8	298.2	231.9	188.4	162.7	146.9	137.2	129.5
55°	266.4	308.7	331.9	306.4	243.3	192.9	159.2	139.0	127.2	119.0	112.4
57.5°	231.4	266.3	280.8	251.2	200.4	159.9	134.7	119.5	107.8	101.9	98.5
60°	209.4	239.2	249.4	216.7	174.2	139.9	119.3	105.2	96.5	92.7	89.3
62.5°	187.8	212.1	216.3	186.4	151.9	122.5	104.7	92.8	87.1	83.4	80.2
65°	155.8	173.3	171.3	147.2	120.2	97.2	84.3	77.0	72.7	67.5	61.8
67.5°	128.3	139.0	132.5	114.5	91.7	75.6	67.1	61.6	56.2	51.3	50.0
70°	110.8	117.0	110.2	93.6	75.2	63.4	56.6	50.0	46.8	45.7	43.6
72.5°	94.1	96.3	88.9	74.7	61.2	52.5	45.8	42.2	40.4	39.5	38.2
75°	70.6	69.1	62.7	51.6	42.5	36.6	34.5	33.2	32.0	31.1	30.4
77.5°	49.6	47.3	41.6	34.3	29.6	26.8	25.5	24.8	24.3	23.8	23.1
80°	37.3	35.7	30.0	24.5	22.5	21.1	20.4	19.5	19.5	19.1	18.4
82.5°	27.3	25.5	20.5	18.0	16.9	16.0	15.5	15.0	14.8	14.9	14.4
85°	14.3	11.6	10.2	9.8	9.1	8.6	8.9	8.4	8.4	8.4	8.2
87.5°	4.8	4.4	4.4	4.5	5.0	5.6	6.2	6.9	7.1	6.9	6.9
90°	2.3	4.6	5.7	6.8	8.6	11.4	15.4	18.8	19.4	18.8	18.2
92.5°	10.0	14.1	16.7	20.5	25.9	38.8	56.9	73.1	74.1	62.6	49.7
95°	22.2	27.9	33.1	42.2	55.9	82.1	131.7	197.9	223.6	195.6	149.4
97.5°	35.6	41.6	49.4	59.9	75.4	108.4	177.5	287.4	381.6	400.3	348.7
100°	45.6	50.8	59.9	71.3	87.3	117.5	187.1	310.2	450.5	532.6	520.7
102.5°	55.7	60.8	69.9	81.8	97.7	125.7	187.5	301.6	452.8	581.9	633.4
105°	71.9	75.8	84.4	96.9	112.9	139.7	190.5	284.6	422.6	574.3	692.9
107.5°	87.8	91.7	99.6	112.0	128.1	154.1	198.3	276.1	390.2	524.2	650.0
110°	99.2	102.7	110.1	122.0	138.6	163.7	204.7	274.3	374.7	492.7	613.1





TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	109.3	113.1	120.1	131.6	148.6	172.8	211.6	274.8	364.6	470.8	579.3
115°	125.5	128.9	135.7	147.1	162.5	187.1	221.8	277.2	353.6	443.7	537.8
117.5°	141.1	144.5	150.6	161.5	177.5	200.2	232.8	281.3	348.2	426.6	506.5
120°	151.1	154.5	159.7	171.1	187.1	209.3	240.1	284.0	345.0	417.5	491.0
122.5°	160.3	163.7	169.3	180.7	197.1	218.0	246.5	287.2	343.2	409.7	478.7
125°	172.8	176.2	183.1	194.5	210.4	231.0	256.6	292.0	339.9	398.6	460.8
127.5°	183.4	188.2	195.7	206.7	223.1	243.1	266.1	296.9	338.0	388.4	443.1
130°	189.3	195.0	203.0	214.4	230.4	250.4	272.0	300.5	337.0	381.5	431.7
132.5°	195.3	201.4	209.9	221.7	237.7	256.7	278.0	304.2	336.6	376.0	420.8
135°	203.0	209.9	218.4	231.5	247.5	265.8	285.7	308.5	335.9	368.4	405.5
137.5°	211.2	218.1	227.2	240.2	255.0	273.1	291.6	312.4	335.8	363.0	393.3
140°	216.7	223.6	232.7	245.2	260.1	277.2	294.8	314.2	335.3	359.9	385.5
142.5°	222.2	228.6	237.7	249.8	263.7	280.4	297.6	315.6	335.3	356.7	379.1
145°	231.5	237.2	245.8	257.2	269.7	285.1	301.1	317.1	334.2	352.4	370.1
147.5°	240.5	246.0	253.9	263.4	274.5	289.0	303.1	317.5	332.1	348.1	363.2
150°	246.9	251.5	258.9	267.5	277.7	290.8	304.0	317.1	330.8	344.5	358.1
152.5°	252.4	257.0	263.5	271.6	280.9	292.7	304.4	316.2	328.5	341.3	353.1
155°	261.2	264.6	270.9	277.2	285.7	295.4	305.1	314.8	324.5	335.3	346.2
157.5°	268.7	271.5	276.9	282.0	289.1	297.3	305.1	312.2	320.4	329.7	338.1
160°	273.7	276.0	280.6	285.1	291.4	298.3	305.1	310.8	317.7	325.6	333.0
162.5°	277.8	280.1	283.8	287.9	292.8	298.7	304.6	309.4	315.4	322.0	328.0
165°	283.4	284.6	288.0	290.8	294.3	299.4	303.4	306.8	310.8	315.9	320.5
167.5°	288.1	289.1	291.3	293.4	295.5	299.3	302.6	304.2	306.8	310.0	313.3
170°	290.8	291.4	293.1	294.3	296.0	298.8	301.7	302.8	304.5	306.8	309.7
172.5°	293.1	292.8	294.5	295.2	296.4	298.4	300.3	301.0	301.8	303.6	305.6
175°	295.4	294.8	296.0	296.0	296.5	297.7	298.8	298.3	298.8	299.4	301.1
177.5°	296.1	295.6	296.5	296.5	296.5	297.0	297.9	297.0	296.5	297.0	297.9
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	676.6	679.0	680.1	680.1	681.4	680.8	680.3
5°	715.5	719.8	720.8	724.8	727.8	726.9	727.3
7.5°	754.2	761.1	768.0	771.1	771.6	773.4	774.1
10°	778.0	783.7	794.3	792.8	800.7	805.3	797.8
12.5°	800.9	808.6	816.0	818.0	822.5	824.0	821.0
15°	821.6	825.7	826.1	825.0	826.4	825.2	820.9
17.5°	802.3	795.6	782.2	775.8	770.8	763.3	760.3
20°	770.3	750.7	728.0	718.9	708.3	687.4	692.4
22.5°	701.2	679.0	656.2	629.7	617.0	597.2	596.0
25°	593.8	555.4	513.1	483.6	466.3	446.6	437.9
27.5°	461.7	413.3	378.7	361.2	345.2	329.6	328.9
30°	374.8	338.5	311.7	296.7	286.9	280.3	281.7
32.5°	315.9	291.0	272.9	260.5	253.3	248.3	248.2
35°	258.3	241.2	229.6	224.4	219.2	215.6	215.8
37.5°	221.0	210.8	204.3	198.6	195.3	193.5	192.5
40°	201.9	193.5	188.5	185.1	182.4	179.9	179.4
42.5°	186.9	179.9	174.9	172.2	169.7	167.9	167.5
45°	165.8	160.1	155.6	152.6	151.5	149.9	149.9
47.5°	147.5	141.9	138.4	136.5	134.6	133.5	133.5
50°	135.2	130.8	127.7	126.5	124.9	124.3	124.0
52.5°	124.1	120.8	118.6	117.8	117.1	116.3	116.4
55°	109.0	107.2	106.3	105.6	104.5	103.1	104.0
57.5°	96.4	94.8	92.4	90.2	89.2	88.2	88.6
60°	87.5	84.3	81.1	78.6	77.9	75.9	75.9
62.5°	76.2	71.7	67.8	66.4	65.7	64.8	64.6
65°	58.6	56.8	55.9	55.0	54.5	54.5	54.1
67.5°	48.6	47.8	46.8	46.6	46.2	46.0	45.9
70°	42.9	42.0	41.6	41.3	40.9	41.1	40.4
72.5°	37.5	36.8	36.7	36.1	35.8	35.8	35.3
75°	29.5	29.5	29.3	29.1	28.6	28.4	28.6
77.5°	22.7	22.8	22.4	22.3	22.3	22.3	22.1
80°	18.2	18.4	18.2	17.9	17.7	17.9	17.7
82.5°	14.4	14.0	14.0	13.9	13.9	13.8	13.7
85°	8.2	8.4	8.2	8.0	8.0	8.0	8.2
87.5°	6.5	6.7	6.9	6.9	6.9	6.9	6.7
90°	17.1	18.2	18.8	18.8	18.8	18.8	18.8
92.5°	42.7	37.9	34.3	33.9	32.1	32.5	31.6
95°	114.6	90.7	78.1	70.7	66.2	64.4	65.0
97.5°	285.3	223.6	182.4	155.1	141.1	132.8	128.0
100°	450.0	371.8	302.8	255.5	231.0	214.4	204.2
102.5°	617.4	560.3	487.1	435.7	393.8	373.2	359.3
105°	757.3	764.8	745.9	710.6	675.2	650.7	642.7
107.5°	747.1	806.4	834.0	838.4	836.5	831.6	821.0
110°	715.1	788.1	834.9	859.4	870.3	875.4	874.8



TEST NUMBER: P331623

CATALOG NUMBER: S122RDIP-S290D530U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	677.3	755.3	808.9	843.0	861.1	870.8	873.9
115°	625.6	700.3	759.1	799.5	825.8	840.6	845.7
117.5°	583.6	651.4	706.5	747.8	775.5	791.1	795.4
120°	561.7	622.2	674.1	714.0	740.8	757.3	763.0
122.5°	543.5	600.7	647.6	683.4	709.8	724.5	729.3
125°	519.5	569.7	612.5	645.6	667.2	681.5	686.1
127.5°	496.3	543.6	583.1	611.9	632.2	644.5	648.2
130°	480.8	525.8	563.4	591.4	610.8	622.2	626.7
132.5°	466.2	507.6	542.9	570.4	589.8	600.3	604.4
135°	443.1	480.8	512.7	537.2	556.0	566.3	568.6
137.5°	424.8	454.6	482.5	504.8	521.0	530.0	533.4
140°	412.9	439.1	464.2	482.5	497.3	505.8	509.3
142.5°	402.4	425.0	446.0	463.3	476.8	484.4	485.1
145°	388.9	406.6	423.2	436.8	446.5	452.2	453.9
147.5°	378.0	391.8	403.9	415.2	422.9	426.8	427.8
150°	370.7	382.7	392.9	401.5	408.3	411.7	412.3
152.5°	364.8	374.9	383.8	390.5	396.5	399.0	399.1
155°	355.3	363.8	370.1	376.4	380.4	382.7	381.5
157.5°	345.7	352.9	357.8	362.2	365.6	366.6	366.6
160°	339.3	345.6	349.6	353.6	356.4	357.0	357.0
162.5°	333.4	338.8	341.8	345.8	347.8	348.3	347.9
165°	324.5	328.5	330.8	333.0	335.3	335.3	334.8
167.5°	316.4	319.1	321.2	322.2	323.5	323.4	322.7
170°	311.4	313.7	314.8	315.4	317.1	316.5	315.4
172.5°	306.8	308.6	309.3	309.9	310.7	310.1	309.4
175°	301.7	302.3	302.8	302.8	303.4	302.8	301.7
177.5°	297.9	298.4	298.4	298.4	298.4	297.9	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5

(END OF REPORT)