

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331634

Luminaire Tested: **S122RDIP-S290D925U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331634  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D925U835-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4441.2 lumens  
Efficiency: N/A  
Efficacy: 119.1 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26				
1	93	89	85	82	82	79	76	74	61	60	58	45	44	43	30	30	29	22				
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19				
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22	17				
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	21	19	15				
5	65	54	47	41	58	49	43	38	39	34	31	29	26	24	20	18	17	13				
6	60	49	41	36	54	44	38	33	35	30	27	26	23	21	18	17	15	12				
7	56	44	37	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11				
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12	10				
9	48	37	30	25	43	33	27	23	27	22	19	20	17	15	15	13	11	9				
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10555	10555	10555	10555
5°	11788	10621	9418	10621
10°	13080	10547	8163	10547
15°	13722	10392	6432	10392
20°	11897	10163	5565	10163
25°	7801	9850	4969	9850
30°	5252	9469	4497	9469
35°	4254	8990	4056	8990
40°	3781	8469	3754	8469
45°	3423	7857	3350	7857
50°	3115	7252	3105	7252
55°	2928	6579	2891	6579
60°	2451	5964	2422	5964
65°	2067	5414	2342	5414
70°	1907	4834	2209	4834
75°	1784	4211	2040	4211
80°	1646	3468	1813	3468
85°	1519	2742	1593	2742



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.0	1.4
10°-20°	172.7	3.9
20°-30°	222.5	5.0
30°-40°	211.5	4.8
40°-50°	181.1	4.1
50°-60°	137.9	3.1
60°-70°	87.2	2.0
70°-80°	43.5	1.0
80°-90°	16.1	0.4
90°-100°	74.9	1.7
100°-110°	232.7	5.2
110°-120°	397.8	9.0
120°-130°	523.2	11.8
130°-140°	587.2	13.2
140°-150°	575.7	13.0
150°-160°	482.9	10.9
160°-170°	320.3	7.2
170°-180°	111.9	2.5
0°-30°	457.2	10.3
0°-40°	668.6	15.1
0°-60°	987.7	22.2
0°-90°	1134.5	25.5
90°-120°	705.5	15.9
90°-150°	2391.6	53.8
90°-180°	3307.0	74.5
0°-180°	4441.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	654	654	654	654	654	
5°	727	655	581	655	727	72
15°	821	622	385	622	821	221
25°	438	553	279	553	438	208
35°	216	456	206	456	216	138
45°	150	344	147	344	150	116
55°	104	234	103	234	104	91
65°	54	142	61	142	54	55
75°	29	68	33	68	29	30
85°	8	15	9	15	8	10
90°	34	1	34	1	34	15
95°	62	52	62	52	62	69
105°	222	215	222	215	222	233
115°	399	399	399	399	399	394
125°	583	581	583	581	583	520
135°	760	752	760	752	760	585
145°	922	912	922	912	922	576
155°	1051	1043	1051	1043	1051	484
165°	1136	1135	1136	1135	1136	320
175°	1177	1181	1177	1181	1177	112
180°	1183	1183	1183	1183	1183	



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	680.3	680.8	681.4	680.1	680.1	679.0	676.6	674.8	669.7	669.0	669.0
5°	727.3	726.9	727.8	724.8	720.8	719.8	715.5	709.8	703.9	697.4	696.0
7.5°	774.1	773.4	771.6	771.1	768.0	761.1	754.2	746.8	737.0	727.4	722.6
10°	797.8	805.3	800.7	792.8	794.3	783.7	778.0	768.2	760.0	745.7	742.6
12.5°	821.0	824.0	822.5	818.0	816.0	808.6	800.9	792.4	777.3	764.5	753.3
15°	820.9	825.2	826.4	825.0	826.1	825.7	821.6	814.6	801.4	787.3	775.0
17.5°	760.3	763.3	770.8	775.8	782.2	795.6	802.3	804.8	802.9	794.8	786.2
20°	692.4	687.4	708.3	718.9	728.0	750.7	770.3	777.8	789.8	789.6	787.3
22.5°	596.0	597.2	617.0	629.7	656.2	679.0	701.2	729.4	752.7	768.1	777.1
25°	437.9	446.6	466.3	483.6	513.1	555.4	593.8	638.3	680.3	713.5	745.1
27.5°	328.9	329.6	345.2	361.2	378.7	413.3	461.7	514.8	574.7	624.2	681.0
30°	281.7	280.3	286.9	296.7	311.7	338.5	374.8	427.0	486.8	561.3	627.6
32.5°	248.2	248.3	253.3	260.5	272.9	291.0	315.9	358.4	414.8	488.1	565.8
35°	215.8	215.6	219.2	224.4	229.6	241.2	258.3	280.5	319.4	387.7	467.2
37.5°	192.5	193.5	195.3	198.6	204.3	210.8	221.0	236.0	263.6	304.1	370.9
40°	179.4	179.9	182.4	185.1	188.5	193.5	201.9	214.0	234.2	266.4	315.3
42.5°	167.5	167.9	169.7	172.2	174.9	179.9	186.9	197.3	213.7	238.8	279.1
45°	149.9	149.9	151.5	152.6	155.6	160.1	165.8	174.5	185.8	204.4	231.2
47.5°	133.5	133.5	134.6	136.5	138.4	141.9	147.5	154.6	162.8	177.2	200.1
50°	124.0	124.3	124.9	126.5	127.7	130.8	135.2	141.3	149.9	161.1	180.1
52.5°	116.4	116.3	117.1	117.8	118.6	120.8	124.1	129.5	137.2	146.9	162.7
55°	104.0	103.1	104.5	105.6	106.3	107.2	109.0	112.4	119.0	127.2	139.0
57.5°	88.6	88.2	89.2	90.2	92.4	94.8	96.4	98.5	101.9	107.8	119.5
60°	75.9	75.9	77.9	78.6	81.1	84.3	87.5	89.3	92.7	96.5	105.2
62.5°	64.6	64.8	65.7	66.4	67.8	71.7	76.2	80.2	83.4	87.1	92.8
65°	54.1	54.5	54.5	55.0	55.9	56.8	58.6	61.8	67.5	72.7	77.0
67.5°	45.9	46.0	46.2	46.6	46.8	47.8	48.6	50.0	51.3	56.2	61.6
70°	40.4	41.1	40.9	41.3	41.6	42.0	42.9	43.6	45.7	46.8	50.0
72.5°	35.3	35.8	35.8	36.1	36.7	36.8	37.5	38.2	39.5	40.4	42.2
75°	28.6	28.4	28.6	29.1	29.3	29.5	29.5	30.4	31.1	32.0	33.2
77.5°	22.1	22.3	22.3	22.3	22.4	22.8	22.7	23.1	23.8	24.3	24.8
80°	17.7	17.9	17.7	17.9	18.2	18.4	18.2	18.4	19.1	19.5	19.5
82.5°	13.7	13.8	13.9	13.9	14.0	14.0	14.4	14.4	14.9	14.8	15.0
85°	8.2	8.0	8.0	8.0	8.2	8.4	8.2	8.2	8.4	8.4	8.4
87.5°	9.7	9.8	9.8	9.7	9.7	9.7	9.8	10.1	10.0	10.3	9.1
90°	33.9	33.7	33.5	33.3	33.0	33.2	33.6	34.0	34.5	34.9	30.0
92.5°	32.3	32.3	32.2	32.2	32.2	32.1	32.0	31.9	31.8	31.7	30.6
95°	61.9	62.3	62.8	63.2	63.6	63.9	63.9	63.9	63.9	63.9	63.4
97.5°	107.2	107.2	107.3	107.3	107.4	107.4	107.4	107.4	107.4	107.4	106.5
100°	136.7	136.9	137.2	137.4	137.6	137.7	137.7	137.7	137.7	137.7	137.1
102.5°	170.3	170.5	170.7	170.9	171.1	171.2	171.0	170.8	170.6	170.5	169.6
105°	221.5	221.5	221.5	221.5	221.5	221.3	220.9	220.4	220.0	219.5	219.1
107.5°	269.8	270.9	271.9	272.9	273.9	274.3	274.2	274.0	273.8	273.6	273.6
110°	307.4	308.0	308.7	309.4	310.0	310.4	310.4	310.4	310.4	310.4	310.4



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.3	343.8	344.3	344.8	345.2	345.8	346.3	346.8	347.4	347.9	348.1
115°	399.2	399.8	400.5	401.2	401.8	402.3	402.5	402.7	403.0	403.2	403.6
117.5°	452.5	453.1	453.8	454.5	455.1	455.7	456.3	456.8	457.3	457.9	459.1
120°	490.0	490.7	491.3	492.0	492.7	493.0	493.0	493.0	493.0	493.0	494.8
122.5°	526.7	527.2	527.7	528.2	528.7	529.2	529.7	530.2	530.8	531.3	532.6
125°	582.8	583.0	583.2	583.5	583.7	584.1	584.8	585.5	586.1	586.8	587.5
127.5°	633.9	634.6	635.3	636.0	636.7	637.5	638.3	639.1	639.9	640.7	641.5
130°	670.6	671.5	672.4	673.3	674.2	674.8	675.3	675.7	676.2	676.6	677.1
132.5°	705.8	706.5	707.2	707.9	708.6	709.4	710.4	711.4	712.4	713.3	713.2
135°	760.4	761.1	761.8	762.4	763.1	763.5	763.8	764.0	764.2	764.4	764.0
137.5°	809.9	810.8	811.7	812.6	813.5	814.0	814.2	814.4	814.6	814.7	814.2
140°	844.3	845.2	846.0	846.9	847.8	848.3	848.3	848.3	848.3	848.3	847.2
142.5°	875.4	876.3	877.2	878.1	879.0	879.3	879.1	879.0	878.8	878.6	877.8
145°	922.1	923.0	923.9	924.8	925.7	926.0	925.8	925.5	925.3	925.1	923.8
147.5°	963.8	964.7	965.5	966.4	967.2	967.4	966.9	966.4	965.9	965.4	964.5
150°	991.0	991.6	992.3	993.0	993.6	993.6	993.0	992.3	991.6	991.0	990.1
152.5°	1016.5	1017.4	1018.2	1019.0	1019.9	1019.9	1019.0	1018.2	1017.4	1016.5	1015.4
155°	1050.8	1051.5	1052.2	1052.8	1053.5	1053.3	1052.2	1051.1	1050.0	1048.8	1048.2
157.5°	1080.4	1081.4	1082.5	1083.6	1084.6	1084.4	1082.9	1081.4	1079.9	1078.4	1078.0
160°	1098.7	1099.6	1100.5	1101.4	1102.3	1102.1	1100.7	1099.4	1098.1	1096.7	1096.5
162.5°	1114.7	1115.8	1116.8	1117.9	1119.0	1118.7	1117.2	1115.7	1114.2	1112.7	1112.5
165°	1135.7	1136.8	1137.9	1139.0	1140.1	1139.9	1138.3	1136.8	1135.2	1133.7	1133.7
167.5°	1152.8	1154.0	1155.1	1156.3	1157.4	1157.2	1155.7	1154.1	1152.6	1151.0	1151.1
170°	1161.6	1162.9	1164.3	1165.6	1166.9	1166.8	1165.3	1163.7	1162.2	1160.6	1160.8
172.5°	1168.8	1170.1	1171.5	1172.8	1174.1	1174.0	1172.5	1170.9	1169.4	1167.8	1168.0
175°	1176.6	1177.9	1179.2	1180.6	1181.9	1181.8	1180.2	1178.7	1177.1	1175.6	1176.0
177.5°	1180.2	1181.2	1182.3	1183.4	1184.4	1184.4	1183.4	1182.3	1181.2	1180.2	1180.5
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	669.4	667.9	666.6	663.4	661.7	658.1	657.6	657.4	652.7	648.1	646.8
5°	692.4	688.7	683.3	676.9	670.3	663.5	659.0	655.3	646.2	637.6	632.6
7.5°	715.5	707.7	698.3	686.3	676.2	665.0	656.6	649.1	636.2	623.8	615.5
10°	732.8	720.1	707.6	691.0	678.0	665.3	653.5	643.3	628.8	612.4	600.8
12.5°	743.5	729.5	712.3	696.1	679.3	663.1	647.3	634.2	617.1	600.2	586.5
15°	758.0	743.0	722.1	698.9	677.4	656.2	638.1	621.7	599.5	579.2	562.4
17.5°	769.9	749.2	726.8	700.0	675.0	648.2	624.8	603.9	579.1	554.7	534.9
20°	773.7	753.2	727.3	700.5	671.0	639.4	614.2	591.5	564.9	538.3	515.6
22.5°	771.3	755.4	726.6	694.5	664.3	631.3	602.8	576.4	546.9	519.8	493.5
25°	755.3	749.8	722.6	687.6	653.1	614.7	581.7	552.9	519.3	490.2	461.6
27.5°	717.9	729.7	712.8	675.5	637.1	596.0	558.9	526.1	491.2	458.5	430.0
30°	681.9	708.9	701.7	667.1	624.2	583.8	542.2	507.9	470.7	437.0	408.9
32.5°	632.7	677.3	684.4	655.5	611.1	566.7	523.1	489.0	450.1	414.7	387.2
35°	554.2	621.0	651.7	633.3	588.8	540.8	495.9	456.1	417.0	382.1	354.8
37.5°	460.7	551.7	602.8	604.1	563.2	513.4	464.4	424.9	384.9	350.6	321.1
40°	400.0	498.6	565.2	579.9	545.4	491.6	442.0	401.8	362.8	329.1	295.3
42.5°	345.5	443.7	525.5	551.2	523.8	470.3	420.6	378.6	340.6	308.8	274.2
45°	279.4	365.3	455.4	501.3	486.1	436.6	384.1	344.1	308.5	281.0	247.8
47.5°	235.7	296.2	383.5	445.5	445.3	400.1	348.4	310.2	277.1	251.3	224.5
50°	210.8	263.5	337.3	407.7	413.6	375.7	326.6	288.7	257.8	230.8	209.2
52.5°	188.4	231.9	298.2	365.8	382.6	349.7	302.1	267.1	237.1	212.2	193.8
55°	159.2	192.9	243.3	306.4	331.9	308.7	266.4	233.7	209.4	188.5	172.6
57.5°	134.7	159.9	200.4	251.2	280.8	266.3	231.4	204.8	184.0	165.1	152.6
60°	119.3	139.9	174.2	216.7	249.4	239.2	209.4	184.7	167.0	150.6	138.8
62.5°	104.7	122.5	151.9	186.4	216.3	212.1	187.8	167.0	151.5	136.6	126.6
65°	84.3	97.2	120.2	147.2	171.3	173.3	155.8	141.7	127.9	116.1	107.2
67.5°	67.1	75.6	91.7	114.5	132.5	139.0	128.3	117.5	106.5	97.4	89.7
70°	56.6	63.4	75.2	93.6	110.2	117.0	110.8	102.4	92.9	85.4	78.8
72.5°	45.8	52.5	61.2	74.7	88.9	96.3	94.1	88.1	80.4	74.1	67.9
75°	34.5	36.6	42.5	51.6	62.7	69.1	70.6	67.5	61.3	56.6	52.9
77.5°	25.5	26.8	29.6	34.3	41.6	47.3	49.6	49.2	45.0	42.3	38.8
80°	20.4	21.1	22.5	24.5	30.0	35.7	37.3	37.3	34.3	33.2	29.8
82.5°	15.5	16.0	16.9	18.0	20.5	25.5	27.3	27.6	25.8	24.3	21.6
85°	8.9	8.6	9.1	9.8	10.2	11.6	14.3	14.8	14.3	12.5	11.8
87.5°	8.1	7.3	6.4	5.4	5.1	4.7	5.1	5.5	5.3	5.3	5.4
90°	25.2	20.3	15.4	11.6	9.0	6.3	3.7	1.0	3.7	6.3	9.0
92.5°	29.4	28.3	27.1	25.6	23.6	21.7	19.7	17.8	19.7	21.7	23.6
95°	63.0	62.5	62.1	60.8	58.5	56.3	54.1	51.9	54.1	56.3	58.5
97.5°	105.7	104.9	104.0	102.6	100.7	98.7	96.8	94.8	96.8	98.7	100.7
100°	136.4	135.7	135.1	133.8	132.1	130.3	128.5	126.7	128.5	130.3	132.1
102.5°	168.8	167.9	167.1	165.9	164.5	163.1	161.7	160.3	161.7	163.1	164.5
105°	218.7	218.2	217.8	217.2	216.6	215.9	215.2	214.6	215.2	215.9	216.6
107.5°	273.6	273.6	273.6	273.2	272.2	271.2	270.2	269.2	270.2	271.2	272.2
110°	310.4	310.4	310.4	309.7	308.4	307.0	305.7	304.4	305.7	307.0	308.4





TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	348.2	348.4	348.6	348.0	346.7	345.4	344.0	342.7	344.0	345.4	346.7
115°	404.1	404.5	404.9	404.5	403.2	401.8	400.5	399.2	400.5	401.8	403.2
117.5°	460.3	461.6	462.8	462.6	460.8	459.0	457.2	455.5	457.2	459.0	460.8
120°	496.5	498.3	500.1	500.1	498.3	496.5	494.8	493.0	494.8	496.5	498.3
122.5°	533.8	535.0	536.3	535.8	533.7	531.6	529.4	527.3	529.4	531.6	533.7
125°	588.1	588.8	589.5	588.8	586.8	584.8	582.8	580.8	582.8	584.8	586.8
127.5°	642.3	643.1	643.9	643.0	640.5	638.0	635.4	632.9	635.4	638.0	640.5
130°	677.5	677.9	678.4	677.2	674.3	671.4	668.5	665.6	668.5	671.4	674.3
132.5°	713.2	713.1	713.0	711.8	709.4	707.1	704.7	702.4	704.7	707.1	709.4
135°	763.5	763.1	762.7	761.2	758.8	756.3	753.9	751.5	753.9	756.3	758.8
137.5°	813.6	813.0	812.4	811.1	809.1	807.1	805.1	803.2	805.1	807.1	809.1
140°	846.0	844.9	843.8	842.3	840.3	838.3	836.3	834.3	836.3	838.3	840.3
142.5°	877.1	876.3	875.6	874.2	872.2	870.2	868.2	866.2	868.2	870.2	872.2
145°	922.4	921.1	919.8	918.3	916.8	915.2	913.7	912.1	913.7	915.2	916.8
147.5°	963.6	962.8	961.9	960.5	958.6	956.8	954.9	953.0	954.9	956.8	958.6
150°	989.2	988.3	987.4	986.3	985.0	983.6	982.3	981.0	982.3	983.6	985.0
152.5°	1014.4	1013.3	1012.3	1011.1	1009.7	1008.4	1007.1	1005.7	1007.1	1008.4	1009.7
155°	1047.5	1046.9	1046.2	1045.5	1044.9	1044.2	1043.5	1042.9	1043.5	1044.2	1044.9
157.5°	1077.6	1077.2	1076.8	1076.4	1075.9	1075.5	1075.0	1074.6	1075.0	1075.5	1075.9
160°	1096.3	1096.1	1095.9	1095.5	1095.1	1094.6	1094.2	1093.8	1094.2	1094.6	1095.1
162.5°	1112.3	1112.1	1111.8	1111.7	1111.6	1111.5	1111.4	1111.3	1111.4	1111.5	1111.6
165°	1133.7	1133.7	1133.7	1133.8	1134.0	1134.2	1134.5	1134.7	1134.5	1134.2	1134.0
167.5°	1151.1	1151.2	1151.2	1151.6	1152.2	1152.9	1153.6	1154.2	1153.6	1152.9	1152.2
170°	1161.1	1161.3	1161.5	1161.9	1162.6	1163.3	1163.9	1164.6	1163.9	1163.3	1162.6
172.5°	1168.2	1168.5	1168.7	1169.1	1169.8	1170.5	1171.1	1171.8	1171.1	1170.5	1169.8
175°	1176.5	1176.9	1177.4	1177.9	1178.6	1179.2	1179.9	1180.6	1179.9	1179.2	1178.6
177.5°	1180.9	1181.2	1181.6	1182.0	1182.6	1183.1	1183.6	1184.2	1183.6	1183.1	1182.6
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	644.5	643.2	640.8	637.2	635.0	631.2	628.7	630.1	630.5	630.1	629.8
5°	627.2	622.4	615.8	609.4	603.5	597.2	593.5	592.0	588.8	587.0	586.0
7.5°	606.2	598.0	588.7	577.6	568.2	558.3	553.3	550.8	544.3	540.8	537.7
10°	590.6	577.6	568.3	553.8	544.9	532.0	523.1	523.4	514.5	509.5	505.9
12.5°	573.3	559.1	543.6	530.5	518.2	507.8	497.1	492.8	483.4	478.6	468.8
15°	544.7	528.1	511.8	494.1	481.6	465.4	450.0	431.1	415.9	402.7	399.1
17.5°	513.5	492.9	476.5	455.7	434.3	407.2	389.3	378.3	369.2	362.2	357.0
20°	492.0	471.1	453.6	422.3	393.4	375.0	361.9	353.4	343.9	336.4	332.3
22.5°	469.5	447.7	423.8	388.8	366.3	351.6	339.9	330.2	323.7	317.9	314.1
25°	437.5	413.6	374.3	350.3	332.1	316.6	308.5	302.6	295.8	287.8	284.2
27.5°	403.7	365.8	337.5	319.6	302.3	292.3	284.9	276.1	270.0	266.4	262.6
30°	378.4	340.5	318.5	298.9	286.7	275.5	266.9	261.9	256.0	249.9	247.4
32.5°	350.3	320.0	298.8	282.6	270.1	260.6	253.8	245.7	241.5	237.7	232.5
35°	315.3	292.3	273.0	259.9	248.0	240.3	232.4	227.6	219.9	216.7	214.7
37.5°	285.7	265.8	251.4	237.5	228.1	219.6	214.7	207.1	203.8	199.3	195.0
40°	268.9	249.4	235.6	224.2	213.7	207.4	201.3	195.1	190.1	188.1	182.9
42.5°	251.9	236.0	222.1	209.7	202.7	195.9	188.2	183.7	178.5	175.2	172.0
45°	228.3	214.2	202.4	192.2	184.4	177.4	172.4	164.9	162.0	155.4	152.6
47.5°	207.6	194.5	183.2	173.5	166.0	161.4	154.1	148.2	143.5	139.4	135.9
50°	192.9	181.9	171.0	162.4	155.6	149.0	141.5	138.6	131.3	129.2	127.2
52.5°	179.4	169.0	159.1	150.6	143.8	137.4	130.8	126.9	122.0	120.0	118.5
55°	160.6	150.6	141.1	133.6	126.8	120.2	116.1	111.3	109.0	107.4	105.6
57.5°	141.7	132.7	125.4	117.8	110.9	105.7	101.0	98.1	95.8	93.7	91.5
60°	129.7	121.1	114.5	107.4	100.4	96.1	92.5	89.0	86.3	83.1	82.2
62.5°	117.0	109.4	103.4	96.5	90.4	86.5	83.0	79.8	76.5	71.9	70.6
65°	99.5	93.6	87.2	81.5	76.1	72.2	67.2	63.6	62.2	61.8	61.6
67.5°	83.7	78.1	72.6	66.8	61.9	58.3	55.7	55.2	54.2	54.0	53.3
70°	73.1	67.9	62.5	57.0	52.2	51.6	50.7	49.7	48.6	48.2	47.7
72.5°	63.7	58.3	52.8	48.5	46.4	45.6	44.7	43.7	43.0	42.5	42.3
75°	48.8	43.8	40.2	38.6	37.5	36.8	35.4	34.8	34.3	33.6	33.4
77.5°	35.2	32.3	30.7	29.7	28.5	27.8	27.0	26.3	25.8	25.7	25.3
80°	26.8	25.4	24.3	22.9	22.5	21.6	21.4	20.7	20.9	20.2	20.2
82.5°	20.8	19.1	18.1	17.5	17.0	16.3	16.1	15.8	15.8	15.3	15.3
85°	10.7	10.2	9.8	9.3	9.3	8.6	8.9	8.6	8.6	8.2	8.0
87.5°	5.8	6.4	7.0	7.9	8.9	9.7	9.6	9.4	9.3	9.2	9.0
90°	11.6	15.4	20.3	25.2	30.0	34.9	34.5	34.0	33.6	33.2	33.0
92.5°	25.6	27.1	28.3	29.4	30.6	31.7	31.8	31.9	32.0	32.1	32.2
95°	60.8	62.1	62.5	63.0	63.4	63.9	63.9	63.9	63.9	63.9	63.6
97.5°	102.6	104.0	104.9	105.7	106.5	107.4	107.4	107.4	107.4	107.4	107.4
100°	133.8	135.1	135.7	136.4	137.1	137.7	137.7	137.7	137.7	137.7	137.6
102.5°	165.9	167.1	167.9	168.8	169.6	170.5	170.6	170.8	171.0	171.2	171.1
105°	217.2	217.8	218.2	218.7	219.1	219.5	220.0	220.4	220.9	221.3	221.5
107.5°	273.2	273.6	273.6	273.6	273.6	273.6	273.8	274.0	274.2	274.3	273.9
110°	309.7	310.4	310.4	310.4	310.4	310.4	310.4	310.4	310.4	310.4	310.0



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	348.0	348.6	348.4	348.2	348.1	347.9	347.4	346.8	346.3	345.8	345.2
115°	404.5	404.9	404.5	404.1	403.6	403.2	403.0	402.7	402.5	402.3	401.8
117.5°	462.6	462.8	461.6	460.3	459.1	457.9	457.3	456.8	456.3	455.7	455.1
120°	500.1	500.1	498.3	496.5	494.8	493.0	493.0	493.0	493.0	493.0	492.7
122.5°	535.8	536.3	535.0	533.8	532.6	531.3	530.8	530.2	529.7	529.2	528.7
125°	588.8	589.5	588.8	588.1	587.5	586.8	586.1	585.5	584.8	584.1	583.7
127.5°	643.0	643.9	643.1	642.3	641.5	640.7	639.9	639.1	638.3	637.5	636.7
130°	677.2	678.4	677.9	677.5	677.1	676.6	676.2	675.7	675.3	674.8	674.2
132.5°	711.8	713.0	713.1	713.2	713.2	713.3	712.4	711.4	710.4	709.4	708.6
135°	761.2	762.7	763.1	763.5	764.0	764.4	764.2	764.0	763.8	763.5	763.1
137.5°	811.1	812.4	813.0	813.6	814.2	814.7	814.6	814.4	814.2	814.0	813.5
140°	842.3	843.8	844.9	846.0	847.2	848.3	848.3	848.3	848.3	848.3	847.8
142.5°	874.2	875.6	876.3	877.1	877.8	878.6	878.8	879.0	879.1	879.3	879.0
145°	918.3	919.8	921.1	922.4	923.8	925.1	925.3	925.5	925.8	926.0	925.7
147.5°	960.5	961.9	962.8	963.6	964.5	965.4	965.9	966.4	966.9	967.4	967.2
150°	986.3	987.4	988.3	989.2	990.1	991.0	991.6	992.3	993.0	993.6	993.6
152.5°	1011.1	1012.3	1013.3	1014.4	1015.4	1016.5	1017.4	1018.2	1019.0	1019.9	1019.9
155°	1045.5	1046.2	1046.9	1047.5	1048.2	1048.8	1050.0	1051.1	1052.2	1053.3	1053.5
157.5°	1076.4	1076.8	1077.2	1077.6	1078.0	1078.4	1079.9	1081.4	1082.9	1084.4	1084.6
160°	1095.5	1095.9	1096.1	1096.3	1096.5	1096.7	1098.1	1099.4	1100.7	1102.1	1102.3
162.5°	1111.7	1111.8	1112.1	1112.3	1112.5	1112.7	1114.2	1115.7	1117.2	1118.7	1119.0
165°	1133.8	1133.7	1133.7	1133.7	1133.7	1133.7	1135.2	1136.8	1138.3	1139.9	1140.1
167.5°	1151.6	1151.2	1151.2	1151.1	1151.1	1151.0	1152.6	1154.1	1155.7	1157.2	1157.4
170°	1161.9	1161.5	1161.3	1161.1	1160.8	1160.6	1162.2	1163.7	1165.3	1166.8	1166.9
172.5°	1169.1	1168.7	1168.5	1168.2	1168.0	1167.8	1169.4	1170.9	1172.5	1174.0	1174.1
175°	1177.9	1177.4	1176.9	1176.5	1176.0	1175.6	1177.1	1178.7	1180.2	1181.8	1181.9
177.5°	1182.0	1181.6	1181.2	1180.9	1180.5	1180.2	1181.2	1182.3	1183.4	1184.4	1184.4
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	627.8	628.1	627.6	627.9	627.6	628.1	627.8	629.8	630.1	630.5	630.1
5°	584.9	582.2	581.7	581.1	581.7	582.2	584.9	586.0	587.0	588.8	592.0
7.5°	533.8	533.4	532.2	530.6	532.2	533.4	533.8	537.7	540.8	544.3	550.8
10°	500.9	499.7	499.5	497.9	499.5	499.7	500.9	505.9	509.5	514.5	523.4
12.5°	462.3	455.0	454.3	450.3	454.3	455.0	462.3	468.8	478.6	483.4	492.8
15°	393.7	392.3	387.7	384.8	387.7	392.3	393.7	399.1	402.7	415.9	431.1
17.5°	354.4	349.9	348.5	347.9	348.5	349.9	354.4	357.0	362.2	369.2	378.3
20°	329.1	325.1	324.4	323.9	324.4	325.1	329.1	332.3	336.4	343.9	353.4
22.5°	311.7	307.4	305.7	304.3	305.7	307.4	311.7	314.1	317.9	323.7	330.2
25°	281.9	280.3	279.4	278.9	279.4	280.3	281.9	284.2	287.8	295.8	302.6
27.5°	258.6	255.1	254.4	253.2	254.4	255.1	258.6	262.6	266.4	270.0	276.1
30°	245.3	244.2	242.6	241.2	242.6	244.2	245.3	247.4	249.9	256.0	261.9
32.5°	229.7	228.7	227.3	226.7	227.3	228.7	229.7	232.5	237.7	241.5	245.7
35°	212.4	209.2	207.8	205.8	207.8	209.2	212.4	214.7	216.7	219.9	227.6
37.5°	194.1	192.4	190.5	191.2	190.5	192.4	194.1	195.0	199.3	203.8	207.1
40°	179.9	178.8	178.3	178.1	178.3	178.8	179.9	182.9	188.1	190.1	195.1
42.5°	168.6	165.5	164.3	164.3	164.3	165.5	168.6	172.0	175.2	178.5	183.7
45°	151.5	148.6	146.5	146.7	146.5	148.6	151.5	152.6	155.4	162.0	164.9
47.5°	134.0	133.9	132.6	133.0	132.6	133.9	134.0	135.9	139.4	143.5	148.2
50°	125.6	124.3	123.3	123.6	123.3	124.3	125.6	127.2	129.2	131.3	138.6
52.5°	117.6	116.4	115.7	116.7	115.7	116.4	117.6	118.5	120.0	122.0	126.9
55°	104.5	103.1	102.9	102.7	102.9	103.1	104.5	105.6	107.4	109.0	111.3
57.5°	89.8	88.9	87.5	87.0	87.5	88.9	89.8	91.5	93.7	95.8	98.1
60°	79.3	77.5	75.2	75.0	75.2	77.5	79.3	82.2	83.1	86.3	89.0
62.5°	69.6	69.3	68.8	68.8	68.8	69.3	69.6	70.6	71.9	76.5	79.8
65°	61.1	60.9	61.1	61.3	61.1	60.9	61.1	61.6	61.8	62.2	63.6
67.5°	53.2	52.8	52.4	52.6	52.4	52.8	53.2	53.3	54.0	54.2	55.2
70°	47.2	47.0	46.8	46.8	46.8	47.0	47.2	47.7	48.2	48.6	49.7
72.5°	41.4	41.4	41.2	41.0	41.2	41.4	41.4	42.3	42.5	43.0	43.7
75°	33.2	32.7	32.7	32.7	32.7	32.7	33.2	33.4	33.6	34.3	34.8
77.5°	25.3	25.0	24.8	24.6	24.8	25.0	25.3	25.3	25.7	25.8	26.3
80°	20.0	19.8	19.5	19.5	19.5	19.8	20.0	20.2	20.2	20.9	20.7
82.5°	15.3	15.0	15.0	14.8	15.0	15.0	15.3	15.3	15.3	15.8	15.8
85°	8.2	8.4	8.2	8.6	8.2	8.4	8.2	8.0	8.2	8.6	8.6
87.5°	9.0	8.9	9.1	9.0	9.1	8.9	9.0	9.0	9.2	9.3	9.4
90°	33.3	33.5	33.7	33.9	33.7	33.5	33.3	33.0	33.2	33.6	34.0
92.5°	32.2	32.2	32.3	32.3	32.3	32.2	32.2	32.2	32.1	32.0	31.9
95°	63.2	62.8	62.3	61.9	62.3	62.8	63.2	63.6	63.9	63.9	63.9
97.5°	107.3	107.3	107.2	107.2	107.2	107.3	107.3	107.4	107.4	107.4	107.4
100°	137.4	137.2	136.9	136.7	136.9	137.2	137.4	137.6	137.7	137.7	137.7
102.5°	170.9	170.7	170.5	170.3	170.5	170.7	170.9	171.1	171.2	171.0	170.8
105°	221.5	221.5	221.5	221.5	221.5	221.5	221.5	221.5	221.3	220.9	220.4
107.5°	272.9	271.9	270.9	269.8	270.9	271.9	272.9	273.9	274.3	274.2	274.0
110°	309.4	308.7	308.0	307.4	308.0	308.7	309.4	310.0	310.4	310.4	310.4



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	344.8	344.3	343.8	343.3	343.8	344.3	344.8	345.2	345.8	346.3	346.8
115°	401.2	400.5	399.8	399.2	399.8	400.5	401.2	401.8	402.3	402.5	402.7
117.5°	454.5	453.8	453.1	452.5	453.1	453.8	454.5	455.1	455.7	456.3	456.8
120°	492.0	491.3	490.7	490.0	490.7	491.3	492.0	492.7	493.0	493.0	493.0
122.5°	528.2	527.7	527.2	526.7	527.2	527.7	528.2	528.7	529.2	529.7	530.2
125°	583.5	583.2	583.0	582.8	583.0	583.2	583.5	583.7	584.1	584.8	585.5
127.5°	636.0	635.3	634.6	633.9	634.6	635.3	636.0	636.7	637.5	638.3	639.1
130°	673.3	672.4	671.5	670.6	671.5	672.4	673.3	674.2	674.8	675.3	675.7
132.5°	707.9	707.2	706.5	705.8	706.5	707.2	707.9	708.6	709.4	710.4	711.4
135°	762.4	761.8	761.1	760.4	761.1	761.8	762.4	763.1	763.5	763.8	764.0
137.5°	812.6	811.7	810.8	809.9	810.8	811.7	812.6	813.5	814.0	814.2	814.4
140°	846.9	846.0	845.2	844.3	845.2	846.0	846.9	847.8	848.3	848.3	848.3
142.5°	878.1	877.2	876.3	875.4	876.3	877.2	878.1	879.0	879.3	879.1	879.0
145°	924.8	923.9	923.0	922.1	923.0	923.9	924.8	925.7	926.0	925.8	925.5
147.5°	966.4	965.5	964.7	963.8	964.7	965.5	966.4	967.2	967.4	966.9	966.4
150°	993.0	992.3	991.6	991.0	991.6	992.3	993.0	993.6	993.6	993.0	992.3
152.5°	1019.0	1018.2	1017.4	1016.5	1017.4	1018.2	1019.0	1019.9	1019.9	1019.0	1018.2
155°	1052.8	1052.2	1051.5	1050.8	1051.5	1052.2	1052.8	1053.5	1053.3	1052.2	1051.1
157.5°	1083.6	1082.5	1081.4	1080.4	1081.4	1082.5	1083.6	1084.6	1084.4	1082.9	1081.4
160°	1101.4	1100.5	1099.6	1098.7	1099.6	1100.5	1101.4	1102.3	1102.1	1100.7	1099.4
162.5°	1117.9	1116.8	1115.8	1114.7	1115.8	1116.8	1117.9	1119.0	1118.7	1117.2	1115.7
165°	1139.0	1137.9	1136.8	1135.7	1136.8	1137.9	1139.0	1140.1	1139.9	1138.3	1136.8
167.5°	1156.3	1155.1	1154.0	1152.8	1154.0	1155.1	1156.3	1157.4	1157.2	1155.7	1154.1
170°	1165.6	1164.3	1162.9	1161.6	1162.9	1164.3	1165.6	1166.9	1166.8	1165.3	1163.7
172.5°	1172.8	1171.5	1170.1	1168.8	1170.1	1171.5	1172.8	1174.1	1174.0	1172.5	1170.9
175°	1180.6	1179.2	1177.9	1176.6	1177.9	1179.2	1180.6	1181.9	1181.8	1180.2	1178.7
177.5°	1183.4	1182.3	1181.2	1180.2	1181.2	1182.3	1183.4	1184.4	1184.4	1183.4	1182.3
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	628.7	631.2	635.0	637.2	640.8	643.2	644.5	646.8	648.1	652.7	657.4
5°	593.5	597.2	603.5	609.4	615.8	622.4	627.2	632.6	637.6	646.2	655.3
7.5°	553.3	558.3	568.2	577.6	588.7	598.0	606.2	615.5	623.8	636.2	649.1
10°	523.1	532.0	544.9	553.8	568.3	577.6	590.6	600.8	612.4	628.8	643.3
12.5°	497.1	507.8	518.2	530.5	543.6	559.1	573.3	586.5	600.2	617.1	634.2
15°	450.0	465.4	481.6	494.1	511.8	528.1	544.7	562.4	579.2	599.5	621.7
17.5°	389.3	407.2	434.3	455.7	476.5	492.9	513.5	534.9	554.7	579.1	603.9
20°	361.9	375.0	393.4	422.3	453.6	471.1	492.0	515.6	538.3	564.9	591.5
22.5°	339.9	351.6	366.3	388.8	423.8	447.7	469.5	493.5	519.8	546.9	576.4
25°	308.5	316.6	332.1	350.3	374.3	413.6	437.5	461.6	490.2	519.3	552.9
27.5°	284.9	292.3	302.3	319.6	337.5	365.8	403.7	430.0	458.5	491.2	526.1
30°	266.9	275.5	286.7	298.9	318.5	340.5	378.4	408.9	437.0	470.7	507.9
32.5°	253.8	260.6	270.1	282.6	298.8	320.0	350.3	387.2	414.7	450.1	489.0
35°	232.4	240.3	248.0	259.9	273.0	292.3	315.3	354.8	382.1	417.0	456.1
37.5°	214.7	219.6	228.1	237.5	251.4	265.8	285.7	321.1	350.6	384.9	424.9
40°	201.3	207.4	213.7	224.2	235.6	249.4	268.9	295.3	329.1	362.8	401.8
42.5°	188.2	195.9	202.7	209.7	222.1	236.0	251.9	274.2	308.8	340.6	378.6
45°	172.4	177.4	184.4	192.2	202.4	214.2	228.3	247.8	281.0	308.5	344.1
47.5°	154.1	161.4	166.0	173.5	183.2	194.5	207.6	224.5	251.3	277.1	310.2
50°	141.5	149.0	155.6	162.4	171.0	181.9	192.9	209.2	230.8	257.8	288.7
52.5°	130.8	137.4	143.8	150.6	159.1	169.0	179.4	193.8	212.2	237.1	267.1
55°	116.1	120.2	126.8	133.6	141.1	150.6	160.6	172.6	188.5	209.4	233.7
57.5°	101.0	105.7	110.9	117.8	125.4	132.7	141.7	152.6	165.1	184.0	204.8
60°	92.5	96.1	100.4	107.4	114.5	121.1	129.7	138.8	150.6	167.0	184.7
62.5°	83.0	86.5	90.4	96.5	103.4	109.4	117.0	126.6	136.6	151.5	167.0
65°	67.2	72.2	76.1	81.5	87.2	93.6	99.5	107.2	116.1	127.9	141.7
67.5°	55.7	58.3	61.9	66.8	72.6	78.1	83.7	89.7	97.4	106.5	117.5
70°	50.7	51.6	52.2	57.0	62.5	67.9	73.1	78.8	85.4	92.9	102.4
72.5°	44.7	45.6	46.4	48.5	52.8	58.3	63.7	67.9	74.1	80.4	88.1
75°	35.4	36.8	37.5	38.6	40.2	43.8	48.8	52.9	56.6	61.3	67.5
77.5°	27.0	27.8	28.5	29.7	30.7	32.3	35.2	38.8	42.3	45.0	49.2
80°	21.4	21.6	22.5	22.9	24.3	25.4	26.8	29.8	33.2	34.3	37.3
82.5°	16.1	16.3	17.0	17.5	18.1	19.1	20.8	21.6	24.3	25.8	27.6
85°	8.9	8.6	9.3	9.3	9.8	10.2	10.7	11.8	12.5	14.3	14.8
87.5°	9.6	9.7	8.9	7.9	7.0	6.4	5.8	5.4	5.3	5.3	5.5
90°	34.5	34.9	30.0	25.2	20.3	15.4	11.6	9.0	6.3	3.7	1.0
92.5°	31.8	31.7	30.6	29.4	28.3	27.1	25.6	23.6	21.7	19.7	17.8
95°	63.9	63.9	63.4	63.0	62.5	62.1	60.8	58.5	56.3	54.1	51.9
97.5°	107.4	107.4	106.5	105.7	104.9	104.0	102.6	100.7	98.7	96.8	94.8
100°	137.7	137.7	137.1	136.4	135.7	135.1	133.8	132.1	130.3	128.5	126.7
102.5°	170.6	170.5	169.6	168.8	167.9	167.1	165.9	164.5	163.1	161.7	160.3
105°	220.0	219.5	219.1	218.7	218.2	217.8	217.2	216.6	215.9	215.2	214.6
107.5°	273.8	273.6	273.6	273.6	273.6	273.6	273.2	272.2	271.2	270.2	269.2
110°	310.4	310.4	310.4	310.4	310.4	310.4	309.7	308.4	307.0	305.7	304.4



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	347.4	347.9	348.1	348.2	348.4	348.6	348.0	346.7	345.4	344.0	342.7
115°	403.0	403.2	403.6	404.1	404.5	404.9	404.5	403.2	401.8	400.5	399.2
117.5°	457.3	457.9	459.1	460.3	461.6	462.8	462.6	460.8	459.0	457.2	455.5
120°	493.0	493.0	494.8	496.5	498.3	500.1	500.1	498.3	496.5	494.8	493.0
122.5°	530.8	531.3	532.6	533.8	535.0	536.3	535.8	533.7	531.6	529.4	527.3
125°	586.1	586.8	587.5	588.1	588.8	589.5	588.8	586.8	584.8	582.8	580.8
127.5°	639.9	640.7	641.5	642.3	643.1	643.9	643.0	640.5	638.0	635.4	632.9
130°	676.2	676.6	677.1	677.5	677.9	678.4	677.2	674.3	671.4	668.5	665.6
132.5°	712.4	713.3	713.2	713.2	713.1	713.0	711.8	709.4	707.1	704.7	702.4
135°	764.2	764.4	764.0	763.5	763.1	762.7	761.2	758.8	756.3	753.9	751.5
137.5°	814.6	814.7	814.2	813.6	813.0	812.4	811.1	809.1	807.1	805.1	803.2
140°	848.3	848.3	847.2	846.0	844.9	843.8	842.3	840.3	838.3	836.3	834.3
142.5°	878.8	878.6	877.8	877.1	876.3	875.6	874.2	872.2	870.2	868.2	866.2
145°	925.3	925.1	923.8	922.4	921.1	919.8	918.3	916.8	915.2	913.7	912.1
147.5°	965.9	965.4	964.5	963.6	962.8	961.9	960.5	958.6	956.8	954.9	953.0
150°	991.6	991.0	990.1	989.2	988.3	987.4	986.3	985.0	983.6	982.3	981.0
152.5°	1017.4	1016.5	1015.4	1014.4	1013.3	1012.3	1011.1	1009.7	1008.4	1007.1	1005.7
155°	1050.0	1048.8	1048.2	1047.5	1046.9	1046.2	1045.5	1044.9	1044.2	1043.5	1042.9
157.5°	1079.9	1078.4	1078.0	1077.6	1077.2	1076.8	1076.4	1075.9	1075.5	1075.0	1074.6
160°	1098.1	1096.7	1096.5	1096.3	1096.1	1095.9	1095.5	1095.1	1094.6	1094.2	1093.8
162.5°	1114.2	1112.7	1112.5	1112.3	1112.1	1111.8	1111.7	1111.6	1111.5	1111.4	1111.3
165°	1135.2	1133.7	1133.7	1133.7	1133.7	1133.7	1133.8	1134.0	1134.2	1134.5	1134.7
167.5°	1152.6	1151.0	1151.1	1151.1	1151.2	1151.2	1151.6	1152.2	1152.9	1153.6	1154.2
170°	1162.2	1160.6	1160.8	1161.1	1161.3	1161.5	1161.9	1162.6	1163.3	1163.9	1164.6
172.5°	1169.4	1167.8	1168.0	1168.2	1168.5	1168.7	1169.1	1169.8	1170.5	1171.1	1171.8
175°	1177.1	1175.6	1176.0	1176.5	1176.9	1177.4	1177.9	1178.6	1179.2	1179.9	1180.6
177.5°	1181.2	1180.2	1180.5	1180.9	1181.2	1181.6	1182.0	1182.6	1183.1	1183.6	1184.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	657.6	658.1	661.7	663.4	666.6	667.9	669.4	669.0	669.0	669.7	674.8
5°	659.0	663.5	670.3	676.9	683.3	688.7	692.4	696.0	697.4	703.9	709.8
7.5°	656.6	665.0	676.2	686.3	698.3	707.7	715.5	722.6	727.4	737.0	746.8
10°	653.5	665.3	678.0	691.0	707.6	720.1	732.8	742.6	745.7	760.0	768.2
12.5°	647.3	663.1	679.3	696.1	712.3	729.5	743.5	753.3	764.5	777.3	792.4
15°	638.1	656.2	677.4	698.9	722.1	743.0	758.0	775.0	787.3	801.4	814.6
17.5°	624.8	648.2	675.0	700.0	726.8	749.2	769.9	786.2	794.8	802.9	804.8
20°	614.2	639.4	671.0	700.5	727.3	753.2	773.7	787.3	789.6	789.8	777.8
22.5°	602.8	631.3	664.3	694.5	726.6	755.4	771.3	777.1	768.1	752.7	729.4
25°	581.7	614.7	653.1	687.6	722.6	749.8	755.3	745.1	713.5	680.3	638.3
27.5°	558.9	596.0	637.1	675.5	712.8	729.7	717.9	681.0	624.2	574.7	514.8
30°	542.2	583.8	624.2	667.1	701.7	708.9	681.9	627.6	561.3	486.8	427.0
32.5°	523.1	566.7	611.1	655.5	684.4	677.3	632.7	565.8	488.1	414.8	358.4
35°	495.9	540.8	588.8	633.3	651.7	621.0	554.2	467.2	387.7	319.4	280.5
37.5°	464.4	513.4	563.2	604.1	602.8	551.7	460.7	370.9	304.1	263.6	236.0
40°	442.0	491.6	545.4	579.9	565.2	498.6	400.0	315.3	266.4	234.2	214.0
42.5°	420.6	470.3	523.8	551.2	525.5	443.7	345.5	279.1	238.8	213.7	197.3
45°	384.1	436.6	486.1	501.3	455.4	365.3	279.4	231.2	204.4	185.8	174.5
47.5°	348.4	400.1	445.3	445.5	383.5	296.2	235.7	200.1	177.2	162.8	154.6
50°	326.6	375.7	413.6	407.7	337.3	263.5	210.8	180.1	161.1	149.9	141.3
52.5°	302.1	349.7	382.6	365.8	298.2	231.9	188.4	162.7	146.9	137.2	129.5
55°	266.4	308.7	331.9	306.4	243.3	192.9	159.2	139.0	127.2	119.0	112.4
57.5°	231.4	266.3	280.8	251.2	200.4	159.9	134.7	119.5	107.8	101.9	98.5
60°	209.4	239.2	249.4	216.7	174.2	139.9	119.3	105.2	96.5	92.7	89.3
62.5°	187.8	212.1	216.3	186.4	151.9	122.5	104.7	92.8	87.1	83.4	80.2
65°	155.8	173.3	171.3	147.2	120.2	97.2	84.3	77.0	72.7	67.5	61.8
67.5°	128.3	139.0	132.5	114.5	91.7	75.6	67.1	61.6	56.2	51.3	50.0
70°	110.8	117.0	110.2	93.6	75.2	63.4	56.6	50.0	46.8	45.7	43.6
72.5°	94.1	96.3	88.9	74.7	61.2	52.5	45.8	42.2	40.4	39.5	38.2
75°	70.6	69.1	62.7	51.6	42.5	36.6	34.5	33.2	32.0	31.1	30.4
77.5°	49.6	47.3	41.6	34.3	29.6	26.8	25.5	24.8	24.3	23.8	23.1
80°	37.3	35.7	30.0	24.5	22.5	21.1	20.4	19.5	19.5	19.1	18.4
82.5°	27.3	25.5	20.5	18.0	16.9	16.0	15.5	15.0	14.8	14.9	14.4
85°	14.3	11.6	10.2	9.8	9.1	8.6	8.9	8.4	8.4	8.4	8.2
87.5°	5.1	4.7	5.1	5.4	6.4	7.3	8.1	9.1	10.3	10.0	10.1
90°	3.7	6.3	9.0	11.6	15.4	20.3	25.2	30.0	34.9	34.5	34.0
92.5°	19.7	21.7	23.6	25.6	27.1	28.3	29.4	30.6	31.7	31.8	31.9
95°	54.1	56.3	58.5	60.8	62.1	62.5	63.0	63.4	63.9	63.9	63.9
97.5°	96.8	98.7	100.7	102.6	104.0	104.9	105.7	106.5	107.4	107.4	107.4
100°	128.5	130.3	132.1	133.8	135.1	135.7	136.4	137.1	137.7	137.7	137.7
102.5°	161.7	163.1	164.5	165.9	167.1	167.9	168.8	169.6	170.5	170.6	170.8
105°	215.2	215.9	216.6	217.2	217.8	218.2	218.7	219.1	219.5	220.0	220.4
107.5°	270.2	271.2	272.2	273.2	273.6	273.6	273.6	273.6	273.6	273.8	274.0
110°	305.7	307.0	308.4	309.7	310.4	310.4	310.4	310.4	310.4	310.4	310.4





TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	344.0	345.4	346.7	348.0	348.6	348.4	348.2	348.1	347.9	347.4	346.8
115°	400.5	401.8	403.2	404.5	404.9	404.5	404.1	403.6	403.2	403.0	402.7
117.5°	457.2	459.0	460.8	462.6	462.8	461.6	460.3	459.1	457.9	457.3	456.8
120°	494.8	496.5	498.3	500.1	500.1	498.3	496.5	494.8	493.0	493.0	493.0
122.5°	529.4	531.6	533.7	535.8	536.3	535.0	533.8	532.6	531.3	530.8	530.2
125°	582.8	584.8	586.8	588.8	589.5	588.8	588.1	587.5	586.8	586.1	585.5
127.5°	635.4	638.0	640.5	643.0	643.9	643.1	642.3	641.5	640.7	639.9	639.1
130°	668.5	671.4	674.3	677.2	678.4	677.9	677.5	677.1	676.6	676.2	675.7
132.5°	704.7	707.1	709.4	711.8	713.0	713.1	713.2	713.2	713.3	712.4	711.4
135°	753.9	756.3	758.8	761.2	762.7	763.1	763.5	764.0	764.4	764.2	764.0
137.5°	805.1	807.1	809.1	811.1	812.4	813.0	813.6	814.2	814.7	814.6	814.4
140°	836.3	838.3	840.3	842.3	843.8	844.9	846.0	847.2	848.3	848.3	848.3
142.5°	868.2	870.2	872.2	874.2	875.6	876.3	877.1	877.8	878.6	878.8	879.0
145°	913.7	915.2	916.8	918.3	919.8	921.1	922.4	923.8	925.1	925.3	925.5
147.5°	954.9	956.8	958.6	960.5	961.9	962.8	963.6	964.5	965.4	965.9	966.4
150°	982.3	983.6	985.0	986.3	987.4	988.3	989.2	990.1	991.0	991.6	992.3
152.5°	1007.1	1008.4	1009.7	1011.1	1012.3	1013.3	1014.4	1015.4	1016.5	1017.4	1018.2
155°	1043.5	1044.2	1044.9	1045.5	1046.2	1046.9	1047.5	1048.2	1048.8	1050.0	1051.1
157.5°	1075.0	1075.5	1075.9	1076.4	1076.8	1077.2	1077.6	1078.0	1078.4	1079.9	1081.4
160°	1094.2	1094.6	1095.1	1095.5	1095.9	1096.1	1096.3	1096.5	1096.7	1098.1	1099.4
162.5°	1111.4	1111.5	1111.6	1111.7	1111.8	1112.1	1112.3	1112.5	1112.7	1114.2	1115.7
165°	1134.5	1134.2	1134.0	1133.8	1133.7	1133.7	1133.7	1133.7	1133.7	1135.2	1136.8
167.5°	1153.6	1152.9	1152.2	1151.6	1151.2	1151.2	1151.1	1151.1	1151.0	1152.6	1154.1
170°	1163.9	1163.3	1162.6	1161.9	1161.5	1161.3	1161.1	1160.8	1160.6	1162.2	1163.7
172.5°	1171.1	1170.5	1169.8	1169.1	1168.7	1168.5	1168.2	1168.0	1167.8	1169.4	1170.9
175°	1179.9	1179.2	1178.6	1177.9	1177.4	1176.9	1176.5	1176.0	1175.6	1177.1	1178.7
177.5°	1183.6	1183.1	1182.6	1182.0	1181.6	1181.2	1180.9	1180.5	1180.2	1181.2	1182.3
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	676.6	679.0	680.1	680.1	681.4	680.8	680.3
5°	715.5	719.8	720.8	724.8	727.8	726.9	727.3
7.5°	754.2	761.1	768.0	771.1	771.6	773.4	774.1
10°	778.0	783.7	794.3	792.8	800.7	805.3	797.8
12.5°	800.9	808.6	816.0	818.0	822.5	824.0	821.0
15°	821.6	825.7	826.1	825.0	826.4	825.2	820.9
17.5°	802.3	795.6	782.2	775.8	770.8	763.3	760.3
20°	770.3	750.7	728.0	718.9	708.3	687.4	692.4
22.5°	701.2	679.0	656.2	629.7	617.0	597.2	596.0
25°	593.8	555.4	513.1	483.6	466.3	446.6	437.9
27.5°	461.7	413.3	378.7	361.2	345.2	329.6	328.9
30°	374.8	338.5	311.7	296.7	286.9	280.3	281.7
32.5°	315.9	291.0	272.9	260.5	253.3	248.3	248.2
35°	258.3	241.2	229.6	224.4	219.2	215.6	215.8
37.5°	221.0	210.8	204.3	198.6	195.3	193.5	192.5
40°	201.9	193.5	188.5	185.1	182.4	179.9	179.4
42.5°	186.9	179.9	174.9	172.2	169.7	167.9	167.5
45°	165.8	160.1	155.6	152.6	151.5	149.9	149.9
47.5°	147.5	141.9	138.4	136.5	134.6	133.5	133.5
50°	135.2	130.8	127.7	126.5	124.9	124.3	124.0
52.5°	124.1	120.8	118.6	117.8	117.1	116.3	116.4
55°	109.0	107.2	106.3	105.6	104.5	103.1	104.0
57.5°	96.4	94.8	92.4	90.2	89.2	88.2	88.6
60°	87.5	84.3	81.1	78.6	77.9	75.9	75.9
62.5°	76.2	71.7	67.8	66.4	65.7	64.8	64.6
65°	58.6	56.8	55.9	55.0	54.5	54.5	54.1
67.5°	48.6	47.8	46.8	46.6	46.2	46.0	45.9
70°	42.9	42.0	41.6	41.3	40.9	41.1	40.4
72.5°	37.5	36.8	36.7	36.1	35.8	35.8	35.3
75°	29.5	29.5	29.3	29.1	28.6	28.4	28.6
77.5°	22.7	22.8	22.4	22.3	22.3	22.3	22.1
80°	18.2	18.4	18.2	17.9	17.7	17.9	17.7
82.5°	14.4	14.0	14.0	13.9	13.9	13.8	13.7
85°	8.2	8.4	8.2	8.0	8.0	8.0	8.2
87.5°	9.8	9.7	9.7	9.7	9.8	9.8	9.7
90°	33.6	33.2	33.0	33.3	33.5	33.7	33.9
92.5°	32.0	32.1	32.2	32.2	32.2	32.3	32.3
95°	63.9	63.9	63.6	63.2	62.8	62.3	61.9
97.5°	107.4	107.4	107.4	107.3	107.3	107.2	107.2
100°	137.7	137.7	137.6	137.4	137.2	136.9	136.7
102.5°	171.0	171.2	171.1	170.9	170.7	170.5	170.3
105°	220.9	221.3	221.5	221.5	221.5	221.5	221.5
107.5°	274.2	274.3	273.9	272.9	271.9	270.9	269.8
110°	310.4	310.4	310.0	309.4	308.7	308.0	307.4



TEST NUMBER: P331634

CATALOG NUMBER: S122RDIP-S290D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	346.3	345.8	345.2	344.8	344.3	343.8	343.3
115°	402.5	402.3	401.8	401.2	400.5	399.8	399.2
117.5°	456.3	455.7	455.1	454.5	453.8	453.1	452.5
120°	493.0	493.0	492.7	492.0	491.3	490.7	490.0
122.5°	529.7	529.2	528.7	528.2	527.7	527.2	526.7
125°	584.8	584.1	583.7	583.5	583.2	583.0	582.8
127.5°	638.3	637.5	636.7	636.0	635.3	634.6	633.9
130°	675.3	674.8	674.2	673.3	672.4	671.5	670.6
132.5°	710.4	709.4	708.6	707.9	707.2	706.5	705.8
135°	763.8	763.5	763.1	762.4	761.8	761.1	760.4
137.5°	814.2	814.0	813.5	812.6	811.7	810.8	809.9
140°	848.3	848.3	847.8	846.9	846.0	845.2	844.3
142.5°	879.1	879.3	879.0	878.1	877.2	876.3	875.4
145°	925.8	926.0	925.7	924.8	923.9	923.0	922.1
147.5°	966.9	967.4	967.2	966.4	965.5	964.7	963.8
150°	993.0	993.6	993.6	993.0	992.3	991.6	991.0
152.5°	1019.0	1019.9	1019.9	1019.0	1018.2	1017.4	1016.5
155°	1052.2	1053.3	1053.5	1052.8	1052.2	1051.5	1050.8
157.5°	1082.9	1084.4	1084.6	1083.6	1082.5	1081.4	1080.4
160°	1100.7	1102.1	1102.3	1101.4	1100.5	1099.6	1098.7
162.5°	1117.2	1118.7	1119.0	1117.9	1116.8	1115.8	1114.7
165°	1138.3	1139.9	1140.1	1139.0	1137.9	1136.8	1135.7
167.5°	1155.7	1157.2	1157.4	1156.3	1155.1	1154.0	1152.8
170°	1165.3	1166.8	1166.9	1165.6	1164.3	1162.9	1161.6
172.5°	1172.5	1174.0	1174.1	1172.8	1171.5	1170.1	1168.8
175°	1180.2	1181.8	1181.9	1180.6	1179.2	1177.9	1176.6
177.5°	1183.4	1184.4	1184.4	1183.4	1182.3	1181.2	1180.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6

(END OF REPORT)