

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331647

Luminaire Tested: **S122RDIP-S485D330U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331647  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S485D330U835-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3137.6 lumens  
Efficiency: N/A  
Efficacy: 114.1 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	101	97	93	90	94	91	87	85	79	77	75	68	67	65	59	57	56	52
2	93	86	80	75	86	80	75	71	70	67	63	61	58	56	53	51	49	45
3	85	76	69	64	79	72	66	61	63	58	54	55	52	49	48	45	43	39
4	78	68	61	55	73	64	58	52	57	52	47	50	46	43	43	40	38	35
5	72	61	54	48	68	58	51	46	51	46	42	45	41	38	40	36	34	31
6	67	56	48	42	63	53	46	41	47	41	37	41	37	34	36	33	30	28
7	62	51	43	38	58	48	41	36	43	37	33	38	34	30	34	30	27	25
8	58	46	39	34	55	44	37	33	39	34	30	35	31	27	31	28	25	23
9	55	43	35	31	51	41	34	29	36	31	27	33	28	25	29	25	23	21
10	51	39	32	28	48	38	31	27	34	29	25	30	26	23	27	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17354	17354	17354	17354
5°	19379	17462	15483	17462
10°	21502	17339	13421	17339
15°	22559	17085	10574	17085
20°	19557	16708	9149	16708
25°	12827	16192	8170	16192
30°	8634	15567	7394	15567
35°	6993	14781	6668	14781
40°	6218	13923	6171	13923
45°	5628	12919	5507	12919
50°	5122	11921	5102	11921
55°	4814	10818	4752	10818
60°	4027	9804	3978	9804
65°	3396	8902	3851	8902
70°	3139	7950	3630	7950
75°	2938	6918	3356	6918
80°	2706	5690	2985	5690
85°	2482	4502	2631	4502



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.9	3.2
10°-20°	283.9	9.0
20°-30°	365.8	11.7
30°-40°	347.6	11.1
40°-50°	297.8	9.5
50°-60°	226.8	7.2
60°-70°	143.4	4.6
70°-80°	71.6	2.3
80°-90°	20.3	0.6
90°-100°	73.5	2.3
100°-110°	249.3	7.9
110°-120°	264.8	8.4
120°-130°	218.0	6.9
130°-140°	175.1	5.6
140°-150°	132.3	4.2
150°-160°	93.0	3.0
160°-170°	54.7	1.7
170°-180°	17.8	0.6
0°-30°	751.6	24.0
0°-40°	1099.2	35.0
0°-60°	1623.8	51.8
0°-90°	1859.1	59.3
90°-120°	587.6	18.7
90°-150°	1113.0	35.5
90°-180°	1279.0	40.8
0°-180°	3137.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1075	1075	1075	1075	1075	
5°	1196	1077	955	1077	1196	118
15°	1350	1022	633	1022	1350	364
25°	720	909	459	909	720	342
35°	355	750	338	750	355	227
45°	246	566	241	566	246	191
55°	171	384	169	384	171	150
65°	89	233	101	233	89	90
75°	47	111	54	111	47	50
85°	13	24	14	24	13	15
90°	12	0	12	0	12	7
95°	40	12	40	12	40	52
105°	398	43	398	43	398	385
115°	524	76	524	76	524	513
125°	425	106	425	106	425	384
135°	352	124	352	124	352	274
145°	281	142	281	142	281	179
155°	236	162	236	162	236	110
165°	207	176	207	176	207	59
175°	187	183	187	183	187	18
180°	184	184	184	184	184	



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1118.4	1119.3	1120.2	1118.1	1118.1	1116.3	1112.4	1109.4	1101.0	1099.8	1099.8
5°	1195.7	1195.0	1196.5	1191.6	1184.9	1183.4	1176.3	1167.0	1157.3	1146.4	1144.2
7.5°	1272.7	1271.6	1268.6	1267.7	1262.6	1251.3	1239.9	1227.7	1211.6	1195.8	1187.9
10°	1311.5	1323.8	1316.4	1303.3	1305.9	1288.4	1279.0	1263.0	1249.5	1226.0	1220.8
12.5°	1349.7	1354.6	1352.2	1344.8	1341.5	1329.3	1316.7	1302.7	1277.9	1256.8	1238.4
15°	1349.6	1356.7	1358.6	1356.3	1358.2	1357.4	1350.7	1339.1	1317.5	1294.3	1274.2
17.5°	1250.0	1254.9	1267.1	1275.4	1285.9	1308.0	1318.9	1323.2	1319.9	1306.7	1292.5
20°	1138.2	1130.0	1164.4	1181.9	1196.9	1234.2	1266.3	1278.6	1298.4	1298.1	1294.3
22.5°	979.9	981.8	1014.4	1035.2	1078.9	1116.2	1152.8	1199.2	1237.5	1262.8	1277.6
25°	720.0	734.2	766.7	795.0	843.6	913.1	976.2	1049.4	1118.4	1173.0	1224.9
27.5°	540.7	541.8	567.5	593.8	622.6	679.5	759.0	846.4	944.9	1026.1	1119.6
30°	463.1	460.8	471.7	487.7	512.4	556.4	616.2	702.1	800.3	922.8	1031.8
32.5°	408.1	408.2	416.4	428.3	448.7	478.4	519.4	589.1	682.0	802.4	930.2
35°	354.8	354.4	360.4	369.0	377.5	396.6	424.6	461.2	525.1	637.5	768.2
37.5°	316.5	318.2	321.1	326.5	335.9	346.5	363.4	387.9	433.4	499.9	609.7
40°	295.0	295.8	299.9	304.4	310.0	318.2	332.0	351.8	385.0	438.0	518.3
42.5°	275.3	276.0	279.0	283.1	287.5	295.8	307.2	324.3	351.3	392.6	458.9
45°	246.5	246.5	249.1	250.9	255.8	263.3	272.6	286.8	305.5	336.1	380.2
47.5°	219.4	219.5	221.2	224.4	227.5	233.3	242.5	254.1	267.7	291.4	329.0
50°	203.9	204.3	205.4	208.0	209.9	215.1	222.2	232.3	246.5	264.8	296.1
52.5°	191.3	191.1	192.5	193.7	194.9	198.7	204.0	212.9	225.6	241.5	267.5
55°	171.0	169.5	171.8	173.6	174.8	176.3	179.2	184.9	195.7	209.1	228.5
57.5°	145.6	145.0	146.6	148.3	151.8	155.9	158.4	162.0	167.6	177.2	196.5
60°	124.7	124.7	128.1	129.2	133.3	138.5	143.8	146.8	152.4	158.7	172.9
62.5°	106.2	106.5	108.1	109.2	111.5	117.9	125.3	131.8	137.1	143.2	152.6
65°	88.9	89.6	89.6	90.4	91.9	93.4	96.3	101.6	110.9	119.5	126.6
67.5°	75.4	75.7	75.9	76.6	77.0	78.6	79.8	82.2	84.3	92.5	101.3
70°	66.5	67.6	67.2	68.0	68.3	69.1	70.6	71.7	75.1	76.9	82.2
72.5°	58.1	58.9	58.9	59.3	60.3	60.4	61.6	62.7	64.9	66.5	69.3
75°	47.1	46.7	47.1	47.8	48.2	48.5	48.5	50.0	51.2	52.7	54.5
77.5°	36.3	36.7	36.6	36.7	36.7	37.4	37.3	38.0	39.1	39.9	40.8
80°	29.1	29.5	29.1	29.5	29.9	30.2	29.9	30.2	31.4	32.1	32.1
82.5°	22.6	22.6	22.9	22.9	23.0	23.1	23.6	23.7	24.5	24.3	24.6
85°	13.4	13.1	13.1	13.1	13.4	13.8	13.4	13.4	13.8	13.8	13.8
87.5°	7.1	7.4	7.4	7.4	7.4	7.3	7.2	7.6	7.4	7.8	7.4
90°	11.7	11.7	11.7	11.7	11.7	11.3	10.6	11.3	11.7	12.0	11.7
92.5°	19.6	20.1	19.9	21.0	21.3	23.5	26.4	30.8	38.8	45.9	45.3
95°	40.3	39.9	41.0	43.8	48.4	56.2	71.0	92.6	121.2	138.5	122.6
97.5°	79.3	82.3	87.4	96.1	113.0	138.5	176.7	216.0	248.0	236.4	178.1
100°	126.5	132.9	143.1	158.3	187.6	230.4	278.8	322.6	330.0	279.1	192.2
102.5°	222.6	231.2	244.0	269.9	301.8	347.1	382.5	392.4	360.5	280.5	186.8
105°	398.2	403.1	418.3	440.2	462.2	473.8	469.2	429.3	355.8	261.8	176.3
107.5°	508.7	515.2	518.3	519.5	516.7	499.6	462.9	402.7	324.8	241.7	171.1
110°	542.0	542.4	539.2	532.5	517.3	488.3	443.1	379.8	305.3	232.1	170.0



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	541.4	539.5	533.5	522.3	501.2	467.9	419.6	358.9	291.7	225.9	170.2
115°	524.0	520.8	511.6	495.4	470.3	433.9	387.6	333.2	274.9	219.1	171.7
117.5°	492.8	490.1	480.5	463.3	437.7	403.6	361.6	313.8	264.3	215.7	174.3
120°	472.8	469.2	459.0	442.4	417.6	385.5	348.0	304.2	258.6	213.8	176.0
122.5°	451.8	448.9	439.8	423.4	401.2	372.2	336.7	296.6	253.8	212.6	177.9
125°	425.1	422.2	413.4	400.0	379.5	353.0	321.9	285.5	247.0	210.6	180.9
127.5°	401.6	399.3	391.7	379.1	361.2	336.8	307.5	274.5	240.6	209.4	183.9
130°	388.3	385.5	378.4	366.4	349.1	325.8	297.9	267.5	236.4	208.8	186.2
132.5°	374.5	371.9	365.4	353.4	336.4	314.5	288.8	260.7	233.0	208.5	188.5
135°	352.3	350.9	344.5	332.8	317.6	297.9	274.5	251.2	228.2	208.1	191.2
137.5°	330.5	328.4	322.8	312.8	298.9	281.7	263.2	243.7	224.9	208.0	193.6
140°	315.5	313.4	308.1	298.9	287.6	272.1	255.8	238.8	222.9	207.8	194.7
142.5°	300.5	300.1	295.4	287.0	276.3	263.3	249.3	234.9	221.0	207.8	195.5
145°	281.2	280.2	276.7	270.6	262.2	251.9	241.0	229.3	218.4	207.0	196.4
147.5°	265.1	264.4	262.0	257.2	250.2	242.7	234.2	225.0	215.7	205.8	196.7
150°	255.5	255.1	253.0	248.7	243.4	237.1	229.7	221.9	213.4	204.9	196.4
152.5°	247.3	247.2	245.6	242.0	237.8	232.3	226.0	218.8	211.4	203.5	195.9
155°	236.4	237.1	235.7	233.2	229.3	225.4	220.1	214.5	207.8	201.0	195.0
157.5°	227.1	227.1	226.5	224.4	221.7	218.6	214.2	209.5	204.3	198.5	193.4
160°	221.2	221.2	220.8	219.1	216.6	214.1	210.2	206.3	201.7	196.8	192.6
162.5°	215.5	215.8	215.5	214.3	211.8	209.9	206.6	203.2	199.5	195.4	191.7
165°	207.4	207.8	207.8	206.3	204.9	203.5	201.0	198.6	195.7	192.6	190.1
167.5°	199.9	200.3	200.4	199.6	199.0	197.7	196.0	194.1	192.1	190.1	188.5
170°	195.4	196.1	196.4	195.4	195.0	194.3	192.9	191.9	190.1	188.7	187.6
172.5°	191.7	192.1	192.5	192.0	191.6	191.2	190.1	189.3	188.1	187.0	186.5
175°	186.9	187.6	188.0	187.6	187.6	187.3	186.9	186.6	185.5	185.1	184.8
177.5°	184.0	184.6	184.9	184.9	184.9	184.9	184.6	184.6	184.0	183.7	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1100.4	1098.1	1096.0	1090.6	1087.9	1081.9	1081.0	1080.7	1073.0	1065.5	1063.4
5°	1138.2	1132.3	1123.3	1112.8	1102.0	1090.8	1083.3	1077.4	1062.4	1048.2	1040.0
7.5°	1176.3	1163.5	1148.0	1128.2	1111.7	1093.2	1079.5	1067.1	1045.9	1025.6	1011.9
10°	1204.7	1183.8	1163.3	1136.0	1114.7	1093.8	1074.4	1057.6	1033.7	1006.8	987.7
12.5°	1222.3	1199.3	1171.0	1144.4	1116.8	1090.2	1064.2	1042.6	1014.6	986.8	964.1
15°	1246.2	1221.5	1187.2	1149.1	1113.6	1078.9	1049.0	1022.1	985.5	952.3	924.6
17.5°	1265.7	1231.7	1194.8	1150.8	1109.7	1065.6	1027.1	992.7	952.0	911.9	879.4
20°	1271.9	1238.3	1195.7	1151.7	1103.1	1051.2	1009.8	972.4	928.7	885.0	847.7
22.5°	1268.0	1241.9	1194.5	1141.8	1092.1	1037.8	991.0	947.6	899.2	854.6	811.3
25°	1241.7	1232.7	1187.9	1130.4	1073.6	1010.5	956.4	908.9	853.7	805.9	758.8
27.5°	1180.2	1199.6	1171.8	1110.5	1047.4	979.7	918.9	864.9	807.5	753.7	706.8
30°	1121.1	1165.5	1153.5	1096.8	1026.2	959.7	891.4	835.0	773.8	718.5	672.2
32.5°	1040.1	1113.5	1125.2	1077.7	1004.7	931.6	860.0	803.9	740.0	681.7	636.6
35°	911.2	1021.0	1071.4	1041.1	967.9	889.2	815.2	749.9	685.6	628.1	583.3
37.5°	757.4	906.9	991.0	993.1	925.9	844.0	763.5	698.6	632.8	576.4	527.9
40°	657.6	819.7	929.1	953.4	896.6	808.1	726.7	660.6	596.4	541.1	485.5
42.5°	568.0	729.5	864.0	906.2	861.1	773.2	691.5	622.4	559.9	507.6	450.8
45°	459.3	600.5	748.7	824.2	799.2	717.7	631.5	565.8	507.1	461.9	407.4
47.5°	387.5	487.0	630.4	732.5	732.0	657.7	572.9	509.9	455.5	413.2	369.0
50°	346.5	433.2	554.6	670.3	680.0	617.7	537.0	474.6	423.9	379.4	343.9
52.5°	309.8	381.2	490.3	601.3	628.9	574.9	496.7	439.1	389.8	348.9	318.5
55°	261.8	317.0	400.0	503.8	545.6	507.5	438.0	384.3	344.3	310.0	283.8
57.5°	221.4	262.9	329.4	413.0	461.7	437.7	380.5	336.8	302.6	271.5	250.9
60°	196.1	230.0	286.4	356.3	410.0	393.2	344.3	303.6	274.5	247.6	228.2
62.5°	172.2	201.4	249.7	306.4	355.7	348.7	308.8	274.6	249.1	224.6	208.2
65°	138.5	159.8	197.5	242.0	281.6	284.9	256.2	233.0	210.2	190.8	176.3
67.5°	110.3	124.2	150.8	188.2	217.9	228.5	210.9	193.2	175.1	160.1	147.5
70°	93.0	104.2	123.6	153.9	181.1	192.3	182.2	168.4	152.7	140.4	129.6
72.5°	75.4	86.3	100.6	122.8	146.2	158.3	154.8	144.8	132.1	121.9	111.7
75°	56.8	60.1	69.8	84.8	103.1	113.5	116.1	110.9	100.8	93.0	87.0
77.5°	42.0	44.0	48.6	56.5	68.4	77.7	81.6	81.0	74.0	69.5	63.9
80°	33.6	34.7	37.0	40.3	49.3	58.6	61.2	61.2	56.4	54.5	48.9
82.5°	25.5	26.4	27.7	29.6	33.8	41.9	44.8	45.4	42.3	39.9	35.5
85°	14.6	14.2	14.9	16.1	16.8	19.0	23.5	24.3	23.5	20.5	19.4
87.5°	7.0	6.8	6.4	5.9	6.1	6.2	7.5	8.7	7.8	7.1	6.7
90°	9.5	7.1	5.3	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	35.3	24.0	16.0	12.7	10.3	8.8	6.2	4.3	6.2	8.8	10.3
95°	81.6	50.9	34.6	26.1	20.5	17.3	13.8	12.4	13.8	17.3	20.5
97.5°	110.0	67.1	46.7	37.1	30.6	25.8	22.0	20.1	22.0	25.8	30.6
100°	115.9	72.8	54.1	44.2	37.1	31.4	28.3	27.2	28.3	31.4	37.1
102.5°	116.2	77.9	60.6	50.7	43.3	37.7	34.5	33.7	34.5	37.7	43.3
105°	118.0	86.6	70.0	60.1	52.3	47.0	44.5	43.1	44.5	47.0	52.3
107.5°	122.9	95.5	79.4	69.4	61.7	56.8	54.4	53.3	54.4	56.8	61.7
110°	126.8	101.4	85.9	75.6	68.2	63.6	61.5	60.1	61.5	63.6	68.2





TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	131.1	107.1	92.1	81.5	74.4	70.1	67.7	66.3	67.7	70.1	74.4
115°	137.4	115.9	100.7	91.2	84.1	79.9	77.7	76.0	77.7	79.9	84.1
117.5°	144.2	124.0	110.0	100.1	93.3	89.5	87.4	86.0	87.4	89.5	93.3
120°	148.8	129.7	115.9	106.0	98.9	95.8	93.6	92.2	93.6	95.8	98.9
122.5°	152.7	135.0	122.1	111.9	104.9	101.4	99.3	98.2	99.3	101.4	104.9
125°	159.0	143.1	130.4	120.5	113.4	109.2	107.1	106.0	107.1	109.2	113.4
127.5°	164.9	150.6	138.2	128.0	121.3	116.6	113.6	112.2	113.6	116.6	121.3
130°	168.5	155.1	142.7	132.9	125.8	120.8	117.3	115.9	117.3	120.8	125.8
132.5°	172.2	159.1	147.3	137.4	130.0	124.8	121.0	119.3	121.0	124.8	130.0
135°	177.0	164.7	153.3	143.5	135.3	130.0	125.8	124.4	125.8	130.0	135.3
137.5°	180.7	169.2	158.0	148.8	140.8	135.1	130.9	129.2	130.9	135.1	140.8
140°	182.7	171.7	161.1	151.9	144.2	138.5	134.3	132.9	134.3	138.5	144.2
142.5°	184.4	173.7	163.4	154.8	147.3	141.6	137.7	136.5	137.7	141.6	147.3
145°	186.6	176.7	167.1	159.4	152.3	147.0	143.5	142.0	143.5	147.0	152.3
147.5°	187.8	179.1	170.1	163.2	157.3	152.4	149.0	148.0	149.0	152.4	157.3
150°	188.3	180.2	172.1	165.7	160.4	155.8	153.0	151.9	153.0	155.8	160.4
152.5°	188.6	181.3	174.0	168.3	163.2	159.2	156.4	155.9	156.4	159.2	163.2
155°	189.0	183.0	177.0	171.7	167.8	163.9	161.8	161.5	161.8	163.9	167.8
157.5°	189.0	184.2	179.1	174.7	171.6	168.2	166.5	166.1	166.5	168.2	171.6
160°	189.0	184.8	180.6	176.7	173.8	171.0	169.6	169.2	169.6	171.0	173.8
162.5°	188.7	185.1	181.4	178.4	175.8	173.6	172.1	172.4	172.1	173.6	175.8
165°	188.0	185.5	182.3	180.2	178.4	176.3	175.6	176.0	175.6	176.3	178.4
167.5°	187.5	185.4	183.1	181.8	180.5	179.1	178.5	178.9	178.5	179.1	180.5
170°	186.9	185.1	183.4	182.3	181.6	180.6	180.2	180.9	180.2	180.6	181.6
172.5°	186.1	184.9	183.7	182.9	182.5	181.4	181.6	182.0	181.6	181.4	182.5
175°	185.1	184.4	183.7	183.4	183.4	182.7	183.0	183.4	183.0	182.7	183.4
177.5°	184.6	184.0	183.7	183.7	183.7	183.2	183.4	184.0	183.4	183.2	183.7
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1059.5	1057.4	1053.5	1047.6	1044.0	1037.7	1033.5	1035.9	1036.5	1035.9	1035.3
5°	1031.1	1023.2	1012.4	1001.9	992.2	981.8	975.8	973.2	967.9	965.0	963.5
7.5°	996.6	983.1	967.8	949.6	934.1	917.9	909.6	905.5	894.8	889.0	883.9
10°	970.9	949.6	934.3	910.4	895.9	874.6	860.0	860.4	845.8	837.6	831.6
12.5°	942.6	919.2	893.7	872.2	852.0	834.9	817.3	810.2	794.7	786.8	770.7
15°	895.5	868.2	841.4	812.2	791.7	765.2	739.8	708.8	683.8	662.1	656.1
17.5°	844.1	810.4	783.4	749.2	714.0	669.4	640.0	622.0	606.9	595.5	587.0
20°	808.9	774.5	745.8	694.2	646.8	616.5	594.9	581.1	565.4	553.1	546.3
22.5°	771.8	736.0	696.8	639.2	602.3	578.0	558.7	542.8	532.2	522.6	516.5
25°	719.2	680.0	615.4	575.8	546.0	520.6	507.1	497.4	486.2	473.1	467.2
27.5°	663.7	601.3	554.9	525.5	497.0	480.5	468.4	453.9	443.9	438.0	431.8
30°	622.1	559.8	523.6	491.4	471.3	453.0	438.8	430.6	420.9	410.8	406.7
32.5°	575.8	526.0	491.3	464.6	444.1	428.5	417.3	404.0	397.0	390.8	382.2
35°	518.3	480.6	448.9	427.2	407.8	395.1	382.0	374.2	361.5	356.3	352.9
37.5°	469.6	436.9	413.2	390.4	375.0	361.0	353.0	340.5	335.0	327.7	320.6
40°	442.1	410.0	387.3	368.6	351.4	340.9	330.9	320.8	312.6	309.2	300.6
42.5°	414.1	387.9	365.1	344.7	333.2	322.1	309.4	302.0	293.4	288.0	282.7
45°	375.3	352.2	332.7	315.9	303.2	291.7	283.4	271.1	266.3	255.4	250.9
47.5°	341.2	319.7	301.2	285.2	272.8	265.3	253.3	243.6	235.9	229.2	223.5
50°	317.0	299.1	281.2	267.0	255.8	245.0	232.7	227.8	215.8	212.5	209.1
52.5°	294.9	277.9	261.5	247.6	236.4	225.9	215.0	208.7	200.6	197.2	194.8
55°	264.0	247.6	231.9	219.6	208.4	197.5	190.8	183.0	179.2	176.6	173.6
57.5°	232.9	218.2	206.1	193.7	182.4	173.8	166.0	161.3	157.4	154.0	150.4
60°	213.2	199.0	188.2	176.6	165.1	158.0	152.0	146.4	141.9	136.7	135.2
62.5°	192.3	179.9	170.0	158.7	148.6	142.1	136.5	131.2	125.8	118.2	116.1
65°	163.6	153.9	143.4	134.1	125.1	118.8	110.5	104.6	102.3	101.6	101.2
67.5°	137.6	128.4	119.4	109.9	101.7	95.8	91.6	90.7	89.2	88.7	87.7
70°	120.2	111.7	102.7	93.7	85.9	84.8	83.3	81.8	79.9	79.2	78.4
72.5°	104.7	95.8	86.9	79.7	76.3	74.9	73.4	71.9	70.7	69.9	69.5
75°	80.3	72.1	66.1	63.5	61.6	60.5	58.3	57.1	56.4	55.3	54.9
77.5°	57.8	53.2	50.4	48.8	46.8	45.6	44.4	43.2	42.4	42.2	41.6
80°	44.1	41.8	40.0	37.7	37.0	35.5	35.1	34.0	34.4	33.2	33.2
82.5°	34.2	31.4	29.8	28.8	28.0	26.8	26.4	25.9	26.0	25.2	25.2
85°	17.6	16.8	16.1	15.3	15.3	14.2	14.6	14.2	14.2	13.4	13.1
87.5°	6.5	6.4	6.2	6.7	7.1	6.9	6.8	6.4	6.3	6.4	6.2
90°	4.2	5.3	7.1	9.5	11.7	12.0	11.7	11.3	10.6	11.3	11.7
92.5°	12.7	16.0	24.0	35.3	45.3	45.9	38.8	30.8	26.4	23.5	21.3
95°	26.1	34.6	50.9	81.6	122.6	138.5	121.2	92.6	71.0	56.2	48.4
97.5°	37.1	46.7	67.1	110.0	178.1	236.4	248.0	216.0	176.7	138.5	113.0
100°	44.2	54.1	72.8	115.9	192.2	279.1	330.0	322.6	278.8	230.4	187.6
102.5°	50.7	60.6	77.9	116.2	186.8	280.5	360.5	392.4	382.5	347.1	301.8
105°	60.1	70.0	86.6	118.0	176.3	261.8	355.8	429.3	469.2	473.8	462.2
107.5°	69.4	79.4	95.5	122.9	171.1	241.7	324.8	402.7	462.9	499.6	516.7
110°	75.6	85.9	101.4	126.8	170.0	232.1	305.3	379.8	443.1	488.3	517.3



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	81.5	92.1	107.1	131.1	170.2	225.9	291.7	358.9	419.6	467.9	501.2
115°	91.2	100.7	115.9	137.4	171.7	219.1	274.9	333.2	387.6	433.9	470.3
117.5°	100.1	110.0	124.0	144.2	174.3	215.7	264.3	313.8	361.6	403.6	437.7
120°	106.0	115.9	129.7	148.8	176.0	213.8	258.6	304.2	348.0	385.5	417.6
122.5°	111.9	122.1	135.0	152.7	177.9	212.6	253.8	296.6	336.7	372.2	401.2
125°	120.5	130.4	143.1	159.0	180.9	210.6	247.0	285.5	321.9	353.0	379.5
127.5°	128.0	138.2	150.6	164.9	183.9	209.4	240.6	274.5	307.5	336.8	361.2
130°	132.9	142.7	155.1	168.5	186.2	208.8	236.4	267.5	297.9	325.8	349.1
132.5°	137.4	147.3	159.1	172.2	188.5	208.5	233.0	260.7	288.8	314.5	336.4
135°	143.5	153.3	164.7	177.0	191.2	208.1	228.2	251.2	274.5	297.9	317.6
137.5°	148.8	158.0	169.2	180.7	193.6	208.0	224.9	243.7	263.2	281.7	298.9
140°	151.9	161.1	171.7	182.7	194.7	207.8	222.9	238.8	255.8	272.1	287.6
142.5°	154.8	163.4	173.7	184.4	195.5	207.8	221.0	234.9	249.3	263.3	276.3
145°	159.4	167.1	176.7	186.6	196.4	207.0	218.4	229.3	241.0	251.9	262.2
147.5°	163.2	170.1	179.1	187.8	196.7	205.8	215.7	225.0	234.2	242.7	250.2
150°	165.7	172.1	180.2	188.3	196.4	204.9	213.4	221.9	229.7	237.1	243.4
152.5°	168.3	174.0	181.3	188.6	195.9	203.5	211.4	218.8	226.0	232.3	237.8
155°	171.7	177.0	183.0	189.0	195.0	201.0	207.8	214.5	220.1	225.4	229.3
157.5°	174.7	179.1	184.2	189.0	193.4	198.5	204.3	209.5	214.2	218.6	221.7
160°	176.7	180.6	184.8	189.0	192.6	196.8	201.7	206.3	210.2	214.1	216.6
162.5°	178.4	181.4	185.1	188.7	191.7	195.4	199.5	203.2	206.6	209.9	211.8
165°	180.2	182.3	185.5	188.0	190.1	192.6	195.7	198.6	201.0	203.5	204.9
167.5°	181.8	183.1	185.4	187.5	188.5	190.1	192.1	194.1	196.0	197.7	199.0
170°	182.3	183.4	185.1	186.9	187.6	188.7	190.1	191.9	192.9	194.3	195.0
172.5°	182.9	183.7	184.9	186.1	186.5	187.0	188.1	189.3	190.1	191.2	191.6
175°	183.4	183.7	184.4	185.1	184.8	185.1	185.5	186.6	186.9	187.3	187.6
177.5°	183.7	183.7	184.0	184.6	184.0	183.7	184.0	184.6	184.6	184.9	184.9
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1032.0	1032.6	1031.7	1032.3	1031.7	1032.6	1032.0	1035.3	1035.9	1036.5	1035.9
5°	961.6	957.1	956.4	955.3	956.4	957.1	961.6	963.5	965.0	967.9	973.2
7.5°	877.5	876.8	875.0	872.3	875.0	876.8	877.5	883.9	889.0	894.8	905.5
10°	823.4	821.6	821.2	818.6	821.2	821.6	823.4	831.6	837.6	845.8	860.4
12.5°	760.1	748.1	746.8	740.3	746.8	748.1	760.1	770.7	786.8	794.7	810.2
15°	647.2	644.9	637.5	632.6	637.5	644.9	647.2	656.1	662.1	683.8	708.8
17.5°	582.6	575.3	573.0	572.0	573.0	575.3	582.6	587.0	595.5	606.9	622.0
20°	541.1	534.4	533.3	532.5	533.3	534.4	541.1	546.3	553.1	565.4	581.1
22.5°	512.4	505.4	502.5	500.3	502.5	505.4	512.4	516.5	522.6	532.2	542.8
25°	463.4	460.8	459.3	458.6	459.3	460.8	463.4	467.2	473.1	486.2	497.4
27.5°	425.1	419.4	418.2	416.3	418.2	419.4	425.1	431.8	438.0	443.9	453.9
30°	403.3	401.4	398.8	396.6	398.8	401.4	403.3	406.7	410.8	420.9	430.6
32.5°	377.6	376.1	373.7	372.7	373.7	376.1	377.6	382.2	390.8	397.0	404.0
35°	349.2	343.9	341.7	338.3	341.7	343.9	349.2	352.9	356.3	361.5	374.2
37.5°	319.1	316.3	313.2	314.3	313.2	316.3	319.1	320.6	327.7	335.0	340.5
40°	295.8	293.9	293.1	292.8	293.1	293.9	295.8	300.6	309.2	312.6	320.8
42.5°	277.2	272.1	270.1	270.1	270.1	272.1	277.2	282.7	288.0	293.4	302.0
45°	249.1	244.2	240.9	241.2	240.9	244.2	249.1	250.9	255.4	266.3	271.1
47.5°	220.3	220.1	218.0	218.7	218.0	220.1	220.3	223.5	229.2	235.9	243.6
50°	206.5	204.3	202.8	203.1	202.8	204.3	206.5	209.1	212.5	215.8	227.8
52.5°	193.4	191.4	190.2	191.8	190.2	191.4	193.4	194.8	197.2	200.6	208.7
55°	171.8	169.5	169.2	168.8	169.2	169.5	171.8	173.6	176.6	179.2	183.0
57.5°	147.7	146.2	143.9	143.0	143.9	146.2	147.7	150.4	154.0	157.4	161.3
60°	130.3	127.3	123.6	123.2	123.6	127.3	130.3	135.2	136.7	141.9	146.4
62.5°	114.5	113.9	113.2	113.1	113.2	113.9	114.5	116.1	118.2	125.8	131.2
65°	100.5	100.1	100.5	100.8	100.5	100.1	100.5	101.2	101.6	102.3	104.6
67.5°	87.5	86.9	86.2	86.5	86.2	86.9	87.5	87.7	88.7	89.2	90.7
70°	77.7	77.3	76.9	76.9	76.9	77.3	77.7	78.4	79.2	79.9	81.8
72.5°	68.1	68.0	67.7	67.4	67.7	68.0	68.1	69.5	69.9	70.7	71.9
75°	54.5	53.8	53.8	53.8	53.8	53.8	54.5	54.9	55.3	56.4	57.1
77.5°	41.5	41.2	40.8	40.5	40.8	41.2	41.5	41.6	42.2	42.4	43.2
80°	32.9	32.5	32.1	32.1	32.1	32.5	32.9	33.2	33.2	34.4	34.0
82.5°	25.1	24.7	24.6	24.3	24.6	24.7	25.1	25.2	25.2	26.0	25.9
85°	13.4	13.8	13.4	14.2	13.4	13.8	13.4	13.1	13.4	14.2	14.2
87.5°	6.2	5.9	6.2	5.9	6.2	5.9	6.2	6.2	6.4	6.3	6.4
90°	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.3	10.6	11.3
92.5°	21.0	19.9	20.1	19.6	20.1	19.9	21.0	21.3	23.5	26.4	30.8
95°	43.8	41.0	39.9	40.3	39.9	41.0	43.8	48.4	56.2	71.0	92.6
97.5°	96.1	87.4	82.3	79.3	82.3	87.4	96.1	113.0	138.5	176.7	216.0
100°	158.3	143.1	132.9	126.5	132.9	143.1	158.3	187.6	230.4	278.8	322.6
102.5°	269.9	244.0	231.2	222.6	231.2	244.0	269.9	301.8	347.1	382.5	392.4
105°	440.2	418.3	403.1	398.2	403.1	418.3	440.2	462.2	473.8	469.2	429.3
107.5°	519.5	518.3	515.2	508.7	515.2	518.3	519.5	516.7	499.6	462.9	402.7
110°	532.5	539.2	542.4	542.0	542.4	539.2	532.5	517.3	488.3	443.1	379.8



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	522.3	533.5	539.5	541.4	539.5	533.5	522.3	501.2	467.9	419.6	358.9
115°	495.4	511.6	520.8	524.0	520.8	511.6	495.4	470.3	433.9	387.6	333.2
117.5°	463.3	480.5	490.1	492.8	490.1	480.5	463.3	437.7	403.6	361.6	313.8
120°	442.4	459.0	469.2	472.8	469.2	459.0	442.4	417.6	385.5	348.0	304.2
122.5°	423.4	439.8	448.9	451.8	448.9	439.8	423.4	401.2	372.2	336.7	296.6
125°	400.0	413.4	422.2	425.1	422.2	413.4	400.0	379.5	353.0	321.9	285.5
127.5°	379.1	391.7	399.3	401.6	399.3	391.7	379.1	361.2	336.8	307.5	274.5
130°	366.4	378.4	385.5	388.3	385.5	378.4	366.4	349.1	325.8	297.9	267.5
132.5°	353.4	365.4	371.9	374.5	371.9	365.4	353.4	336.4	314.5	288.8	260.7
135°	332.8	344.5	350.9	352.3	350.9	344.5	332.8	317.6	297.9	274.5	251.2
137.5°	312.8	322.8	328.4	330.5	328.4	322.8	312.8	298.9	281.7	263.2	243.7
140°	298.9	308.1	313.4	315.5	313.4	308.1	298.9	287.6	272.1	255.8	238.8
142.5°	287.0	295.4	300.1	300.5	300.1	295.4	287.0	276.3	263.3	249.3	234.9
145°	270.6	276.7	280.2	281.2	280.2	276.7	270.6	262.2	251.9	241.0	229.3
147.5°	257.2	262.0	264.4	265.1	264.4	262.0	257.2	250.2	242.7	234.2	225.0
150°	248.7	253.0	255.1	255.5	255.1	253.0	248.7	243.4	237.1	229.7	221.9
152.5°	242.0	245.6	247.2	247.3	247.2	245.6	242.0	237.8	232.3	226.0	218.8
155°	233.2	235.7	237.1	236.4	237.1	235.7	233.2	229.3	225.4	220.1	214.5
157.5°	224.4	226.5	227.1	227.1	227.1	226.5	224.4	221.7	218.6	214.2	209.5
160°	219.1	220.8	221.2	221.2	221.2	220.8	219.1	216.6	214.1	210.2	206.3
162.5°	214.3	215.5	215.8	215.5	215.8	215.5	214.3	211.8	209.9	206.6	203.2
165°	206.3	207.8	207.8	207.4	207.8	207.8	206.3	204.9	203.5	201.0	198.6
167.5°	199.6	200.4	200.3	199.9	200.3	200.4	199.6	199.0	197.7	196.0	194.1
170°	195.4	196.4	196.1	195.4	196.1	196.4	195.4	195.0	194.3	192.9	191.9
172.5°	192.0	192.5	192.1	191.7	192.1	192.5	192.0	191.6	191.2	190.1	189.3
175°	187.6	188.0	187.6	186.9	187.6	188.0	187.6	187.6	187.3	186.9	186.6
177.5°	184.9	184.9	184.6	184.0	184.6	184.9	184.9	184.9	184.9	184.6	184.6
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1033.5	1037.7	1044.0	1047.6	1053.5	1057.4	1059.5	1063.4	1065.5	1073.0	1080.7
5°	975.8	981.8	992.2	1001.9	1012.4	1023.2	1031.1	1040.0	1048.2	1062.4	1077.4
7.5°	909.6	917.9	934.1	949.6	967.8	983.1	996.6	1011.9	1025.6	1045.9	1067.1
10°	860.0	874.6	895.9	910.4	934.3	949.6	970.9	987.7	1006.8	1033.7	1057.6
12.5°	817.3	834.9	852.0	872.2	893.7	919.2	942.6	964.1	986.8	1014.6	1042.6
15°	739.8	765.2	791.7	812.2	841.4	868.2	895.5	924.6	952.3	985.5	1022.1
17.5°	640.0	669.4	714.0	749.2	783.4	810.4	844.1	879.4	911.9	952.0	992.7
20°	594.9	616.5	646.8	694.2	745.8	774.5	808.9	847.7	885.0	928.7	972.4
22.5°	558.7	578.0	602.3	639.2	696.8	736.0	771.8	811.3	854.6	899.2	947.6
25°	507.1	520.6	546.0	575.8	615.4	680.0	719.2	758.8	805.9	853.7	908.9
27.5°	468.4	480.5	497.0	525.5	554.9	601.3	663.7	706.8	753.7	807.5	864.9
30°	438.8	453.0	471.3	491.4	523.6	559.8	622.1	672.2	718.5	773.8	835.0
32.5°	417.3	428.5	444.1	464.6	491.3	526.0	575.8	636.6	681.7	740.0	803.9
35°	382.0	395.1	407.8	427.2	448.9	480.6	518.3	583.3	628.1	685.6	749.9
37.5°	353.0	361.0	375.0	390.4	413.2	436.9	469.6	527.9	576.4	632.8	698.6
40°	330.9	340.9	351.4	368.6	387.3	410.0	442.1	485.5	541.1	596.4	660.6
42.5°	309.4	322.1	333.2	344.7	365.1	387.9	414.1	450.8	507.6	559.9	622.4
45°	283.4	291.7	303.2	315.9	332.7	352.2	375.3	407.4	461.9	507.1	565.8
47.5°	253.3	265.3	272.8	285.2	301.2	319.7	341.2	369.0	413.2	455.5	509.9
50°	232.7	245.0	255.8	267.0	281.2	299.1	317.0	343.9	379.4	423.9	474.6
52.5°	215.0	225.9	236.4	247.6	261.5	277.9	294.9	318.5	348.9	389.8	439.1
55°	190.8	197.5	208.4	219.6	231.9	247.6	264.0	283.8	310.0	344.3	384.3
57.5°	166.0	173.8	182.4	193.7	206.1	218.2	232.9	250.9	271.5	302.6	336.8
60°	152.0	158.0	165.1	176.6	188.2	199.0	213.2	228.2	247.6	274.5	303.6
62.5°	136.5	142.1	148.6	158.7	170.0	179.9	192.3	208.2	224.6	249.1	274.6
65°	110.5	118.8	125.1	134.1	143.4	153.9	163.6	176.3	190.8	210.2	233.0
67.5°	91.6	95.8	101.7	109.9	119.4	128.4	137.6	147.5	160.1	175.1	193.2
70°	83.3	84.8	85.9	93.7	102.7	111.7	120.2	129.6	140.4	152.7	168.4
72.5°	73.4	74.9	76.3	79.7	86.9	95.8	104.7	111.7	121.9	132.1	144.8
75°	58.3	60.5	61.6	63.5	66.1	72.1	80.3	87.0	93.0	100.8	110.9
77.5°	44.4	45.6	46.8	48.8	50.4	53.2	57.8	63.9	69.5	74.0	81.0
80°	35.1	35.5	37.0	37.7	40.0	41.8	44.1	48.9	54.5	56.4	61.2
82.5°	26.4	26.8	28.0	28.8	29.8	31.4	34.2	35.5	39.9	42.3	45.4
85°	14.6	14.2	15.3	15.3	16.1	16.8	17.6	19.4	20.5	23.5	24.3
87.5°	6.8	6.9	7.1	6.7	6.2	6.4	6.5	6.7	7.1	7.8	8.7
90°	11.7	12.0	11.7	9.5	7.1	5.3	4.2	3.5	2.8	1.4	0.4
92.5°	38.8	45.9	45.3	35.3	24.0	16.0	12.7	10.3	8.8	6.2	4.3
95°	121.2	138.5	122.6	81.6	50.9	34.6	26.1	20.5	17.3	13.8	12.4
97.5°	248.0	236.4	178.1	110.0	67.1	46.7	37.1	30.6	25.8	22.0	20.1
100°	330.0	279.1	192.2	115.9	72.8	54.1	44.2	37.1	31.4	28.3	27.2
102.5°	360.5	280.5	186.8	116.2	77.9	60.6	50.7	43.3	37.7	34.5	33.7
105°	355.8	261.8	176.3	118.0	86.6	70.0	60.1	52.3	47.0	44.5	43.1
107.5°	324.8	241.7	171.1	122.9	95.5	79.4	69.4	61.7	56.8	54.4	53.3
110°	305.3	232.1	170.0	126.8	101.4	85.9	75.6	68.2	63.6	61.5	60.1



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	291.7	225.9	170.2	131.1	107.1	92.1	81.5	74.4	70.1	67.7	66.3
115°	274.9	219.1	171.7	137.4	115.9	100.7	91.2	84.1	79.9	77.7	76.0
117.5°	264.3	215.7	174.3	144.2	124.0	110.0	100.1	93.3	89.5	87.4	86.0
120°	258.6	213.8	176.0	148.8	129.7	115.9	106.0	98.9	95.8	93.6	92.2
122.5°	253.8	212.6	177.9	152.7	135.0	122.1	111.9	104.9	101.4	99.3	98.2
125°	247.0	210.6	180.9	159.0	143.1	130.4	120.5	113.4	109.2	107.1	106.0
127.5°	240.6	209.4	183.9	164.9	150.6	138.2	128.0	121.3	116.6	113.6	112.2
130°	236.4	208.8	186.2	168.5	155.1	142.7	132.9	125.8	120.8	117.3	115.9
132.5°	233.0	208.5	188.5	172.2	159.1	147.3	137.4	130.0	124.8	121.0	119.3
135°	228.2	208.1	191.2	177.0	164.7	153.3	143.5	135.3	130.0	125.8	124.4
137.5°	224.9	208.0	193.6	180.7	169.2	158.0	148.8	140.8	135.1	130.9	129.2
140°	222.9	207.8	194.7	182.7	171.7	161.1	151.9	144.2	138.5	134.3	132.9
142.5°	221.0	207.8	195.5	184.4	173.7	163.4	154.8	147.3	141.6	137.7	136.5
145°	218.4	207.0	196.4	186.6	176.7	167.1	159.4	152.3	147.0	143.5	142.0
147.5°	215.7	205.8	196.7	187.8	179.1	170.1	163.2	157.3	152.4	149.0	148.0
150°	213.4	204.9	196.4	188.3	180.2	172.1	165.7	160.4	155.8	153.0	151.9
152.5°	211.4	203.5	195.9	188.6	181.3	174.0	168.3	163.2	159.2	156.4	155.9
155°	207.8	201.0	195.0	189.0	183.0	177.0	171.7	167.8	163.9	161.8	161.5
157.5°	204.3	198.5	193.4	189.0	184.2	179.1	174.7	171.6	168.2	166.5	166.1
160°	201.7	196.8	192.6	189.0	184.8	180.6	176.7	173.8	171.0	169.6	169.2
162.5°	199.5	195.4	191.7	188.7	185.1	181.4	178.4	175.8	173.6	172.1	172.4
165°	195.7	192.6	190.1	188.0	185.5	182.3	180.2	178.4	176.3	175.6	176.0
167.5°	192.1	190.1	188.5	187.5	185.4	183.1	181.8	180.5	179.1	178.5	178.9
170°	190.1	188.7	187.6	186.9	185.1	183.4	182.3	181.6	180.6	180.2	180.9
172.5°	188.1	187.0	186.5	186.1	184.9	183.7	182.9	182.5	181.4	181.6	182.0
175°	185.5	185.1	184.8	185.1	184.4	183.7	183.4	183.4	182.7	183.0	183.4
177.5°	184.0	183.7	184.0	184.6	184.0	183.7	183.7	183.7	183.2	183.4	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1081.0	1081.9	1087.9	1090.6	1096.0	1098.1	1100.4	1099.8	1099.8	1101.0	1109.4
5°	1083.3	1090.8	1102.0	1112.8	1123.3	1132.3	1138.2	1144.2	1146.4	1157.3	1167.0
7.5°	1079.5	1093.2	1111.7	1128.2	1148.0	1163.5	1176.3	1187.9	1195.8	1211.6	1227.7
10°	1074.4	1093.8	1114.7	1136.0	1163.3	1183.8	1204.7	1220.8	1226.0	1249.5	1263.0
12.5°	1064.2	1090.2	1116.8	1144.4	1171.0	1199.3	1222.3	1238.4	1256.8	1277.9	1302.7
15°	1049.0	1078.9	1113.6	1149.1	1187.2	1221.5	1246.2	1274.2	1294.3	1317.5	1339.1
17.5°	1027.1	1065.6	1109.7	1150.8	1194.8	1231.7	1265.7	1292.5	1306.7	1319.9	1323.2
20°	1009.8	1051.2	1103.1	1151.7	1195.7	1238.3	1271.9	1294.3	1298.1	1298.4	1278.6
22.5°	991.0	1037.8	1092.1	1141.8	1194.5	1241.9	1268.0	1277.6	1262.8	1237.5	1199.2
25°	956.4	1010.5	1073.6	1130.4	1187.9	1232.7	1241.7	1224.9	1173.0	1118.4	1049.4
27.5°	918.9	979.7	1047.4	1110.5	1171.8	1199.6	1180.2	1119.6	1026.1	944.9	846.4
30°	891.4	959.7	1026.2	1096.8	1153.5	1165.5	1121.1	1031.8	922.8	800.3	702.1
32.5°	860.0	931.6	1004.7	1077.7	1125.2	1113.5	1040.1	930.2	802.4	682.0	589.1
35°	815.2	889.2	967.9	1041.1	1071.4	1021.0	911.2	768.2	637.5	525.1	461.2
37.5°	763.5	844.0	925.9	993.1	991.0	906.9	757.4	609.7	499.9	433.4	387.9
40°	726.7	808.1	896.6	953.4	929.1	819.7	657.6	518.3	438.0	385.0	351.8
42.5°	691.5	773.2	861.1	906.2	864.0	729.5	568.0	458.9	392.6	351.3	324.3
45°	631.5	717.7	799.2	824.2	748.7	600.5	459.3	380.2	336.1	305.5	286.8
47.5°	572.9	657.7	732.0	732.5	630.4	487.0	387.5	329.0	291.4	267.7	254.1
50°	537.0	617.7	680.0	670.3	554.6	433.2	346.5	296.1	264.8	246.5	232.3
52.5°	496.7	574.9	628.9	601.3	490.3	381.2	309.8	267.5	241.5	225.6	212.9
55°	438.0	507.5	545.6	503.8	400.0	317.0	261.8	228.5	209.1	195.7	184.9
57.5°	380.5	437.7	461.7	413.0	329.4	262.9	221.4	196.5	177.2	167.6	162.0
60°	344.3	393.2	410.0	356.3	286.4	230.0	196.1	172.9	158.7	152.4	146.8
62.5°	308.8	348.7	355.7	306.4	249.7	201.4	172.2	152.6	143.2	137.1	131.8
65°	256.2	284.9	281.6	242.0	197.5	159.8	138.5	126.6	119.5	110.9	101.6
67.5°	210.9	228.5	217.9	188.2	150.8	124.2	110.3	101.3	92.5	84.3	82.2
70°	182.2	192.3	181.1	153.9	123.6	104.2	93.0	82.2	76.9	75.1	71.7
72.5°	154.8	158.3	146.2	122.8	100.6	86.3	75.4	69.3	66.5	64.9	62.7
75°	116.1	113.5	103.1	84.8	69.8	60.1	56.8	54.5	52.7	51.2	50.0
77.5°	81.6	77.7	68.4	56.5	48.6	44.0	42.0	40.8	39.9	39.1	38.0
80°	61.2	58.6	49.3	40.3	37.0	34.7	33.6	32.1	32.1	31.4	30.2
82.5°	44.8	41.9	33.8	29.6	27.7	26.4	25.5	24.6	24.3	24.5	23.7
85°	23.5	19.0	16.8	16.1	14.9	14.2	14.6	13.8	13.8	13.8	13.4
87.5°	7.5	6.2	6.1	5.9	6.4	6.8	7.0	7.4	7.8	7.4	7.6
90°	1.4	2.8	3.5	4.2	5.3	7.1	9.5	11.7	12.0	11.7	11.3
92.5°	6.2	8.8	10.3	12.7	16.0	24.0	35.3	45.3	45.9	38.8	30.8
95°	13.8	17.3	20.5	26.1	34.6	50.9	81.6	122.6	138.5	121.2	92.6
97.5°	22.0	25.8	30.6	37.1	46.7	67.1	110.0	178.1	236.4	248.0	216.0
100°	28.3	31.4	37.1	44.2	54.1	72.8	115.9	192.2	279.1	330.0	322.6
102.5°	34.5	37.7	43.3	50.7	60.6	77.9	116.2	186.8	280.5	360.5	392.4
105°	44.5	47.0	52.3	60.1	70.0	86.6	118.0	176.3	261.8	355.8	429.3
107.5°	54.4	56.8	61.7	69.4	79.4	95.5	122.9	171.1	241.7	324.8	402.7
110°	61.5	63.6	68.2	75.6	85.9	101.4	126.8	170.0	232.1	305.3	379.8





TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	67.7	70.1	74.4	81.5	92.1	107.1	131.1	170.2	225.9	291.7	358.9
115°	77.7	79.9	84.1	91.2	100.7	115.9	137.4	171.7	219.1	274.9	333.2
117.5°	87.4	89.5	93.3	100.1	110.0	124.0	144.2	174.3	215.7	264.3	313.8
120°	93.6	95.8	98.9	106.0	115.9	129.7	148.8	176.0	213.8	258.6	304.2
122.5°	99.3	101.4	104.9	111.9	122.1	135.0	152.7	177.9	212.6	253.8	296.6
125°	107.1	109.2	113.4	120.5	130.4	143.1	159.0	180.9	210.6	247.0	285.5
127.5°	113.6	116.6	121.3	128.0	138.2	150.6	164.9	183.9	209.4	240.6	274.5
130°	117.3	120.8	125.8	132.9	142.7	155.1	168.5	186.2	208.8	236.4	267.5
132.5°	121.0	124.8	130.0	137.4	147.3	159.1	172.2	188.5	208.5	233.0	260.7
135°	125.8	130.0	135.3	143.5	153.3	164.7	177.0	191.2	208.1	228.2	251.2
137.5°	130.9	135.1	140.8	148.8	158.0	169.2	180.7	193.6	208.0	224.9	243.7
140°	134.3	138.5	144.2	151.9	161.1	171.7	182.7	194.7	207.8	222.9	238.8
142.5°	137.7	141.6	147.3	154.8	163.4	173.7	184.4	195.5	207.8	221.0	234.9
145°	143.5	147.0	152.3	159.4	167.1	176.7	186.6	196.4	207.0	218.4	229.3
147.5°	149.0	152.4	157.3	163.2	170.1	179.1	187.8	196.7	205.8	215.7	225.0
150°	153.0	155.8	160.4	165.7	172.1	180.2	188.3	196.4	204.9	213.4	221.9
152.5°	156.4	159.2	163.2	168.3	174.0	181.3	188.6	195.9	203.5	211.4	218.8
155°	161.8	163.9	167.8	171.7	177.0	183.0	189.0	195.0	201.0	207.8	214.5
157.5°	166.5	168.2	171.6	174.7	179.1	184.2	189.0	193.4	198.5	204.3	209.5
160°	169.6	171.0	173.8	176.7	180.6	184.8	189.0	192.6	196.8	201.7	206.3
162.5°	172.1	173.6	175.8	178.4	181.4	185.1	188.7	191.7	195.4	199.5	203.2
165°	175.6	176.3	178.4	180.2	182.3	185.5	188.0	190.1	192.6	195.7	198.6
167.5°	178.5	179.1	180.5	181.8	183.1	185.4	187.5	188.5	190.1	192.1	194.1
170°	180.2	180.6	181.6	182.3	183.4	185.1	186.9	187.6	188.7	190.1	191.9
172.5°	181.6	181.4	182.5	182.9	183.7	184.9	186.1	186.5	187.0	188.1	189.3
175°	183.0	182.7	183.4	183.4	183.7	184.4	185.1	184.8	185.1	185.5	186.6
177.5°	183.4	183.2	183.7	183.7	183.7	184.0	184.6	184.0	183.7	184.0	184.6
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8	1074.8
2.5°	1112.4	1116.3	1118.1	1118.1	1120.2	1119.3	1118.4
5°	1176.3	1183.4	1184.9	1191.6	1196.5	1195.0	1195.7
7.5°	1239.9	1251.3	1262.6	1267.7	1268.6	1271.6	1272.7
10°	1279.0	1288.4	1305.9	1303.3	1316.4	1323.8	1311.5
12.5°	1316.7	1329.3	1341.5	1344.8	1352.2	1354.6	1349.7
15°	1350.7	1357.4	1358.2	1356.3	1358.6	1356.7	1349.6
17.5°	1318.9	1308.0	1285.9	1275.4	1267.1	1254.9	1250.0
20°	1266.3	1234.2	1196.9	1181.9	1164.4	1130.0	1138.2
22.5°	1152.8	1116.2	1078.9	1035.2	1014.4	981.8	979.9
25°	976.2	913.1	843.6	795.0	766.7	734.2	720.0
27.5°	759.0	679.5	622.6	593.8	567.5	541.8	540.7
30°	616.2	556.4	512.4	487.7	471.7	460.8	463.1
32.5°	519.4	478.4	448.7	428.3	416.4	408.2	408.1
35°	424.6	396.6	377.5	369.0	360.4	354.4	354.8
37.5°	363.4	346.5	335.9	326.5	321.1	318.2	316.5
40°	332.0	318.2	310.0	304.4	299.9	295.8	295.0
42.5°	307.2	295.8	287.5	283.1	279.0	276.0	275.3
45°	272.6	263.3	255.8	250.9	249.1	246.5	246.5
47.5°	242.5	233.3	227.5	224.4	221.2	219.5	219.4
50°	222.2	215.1	209.9	208.0	205.4	204.3	203.9
52.5°	204.0	198.7	194.9	193.7	192.5	191.1	191.3
55°	179.2	176.3	174.8	173.6	171.8	169.5	171.0
57.5°	158.4	155.9	151.8	148.3	146.6	145.0	145.6
60°	143.8	138.5	133.3	129.2	128.1	124.7	124.7
62.5°	125.3	117.9	111.5	109.2	108.1	106.5	106.2
65°	96.3	93.4	91.9	90.4	89.6	89.6	88.9
67.5°	79.8	78.6	77.0	76.6	75.9	75.7	75.4
70°	70.6	69.1	68.3	68.0	67.2	67.6	66.5
72.5°	61.6	60.4	60.3	59.3	58.9	58.9	58.1
75°	48.5	48.5	48.2	47.8	47.1	46.7	47.1
77.5°	37.3	37.4	36.7	36.7	36.6	36.7	36.3
80°	29.9	30.2	29.9	29.5	29.1	29.5	29.1
82.5°	23.6	23.1	23.0	22.9	22.9	22.6	22.6
85°	13.4	13.8	13.4	13.1	13.1	13.1	13.4
87.5°	7.2	7.3	7.4	7.4	7.4	7.4	7.1
90°	10.6	11.3	11.7	11.7	11.7	11.7	11.7
92.5°	26.4	23.5	21.3	21.0	19.9	20.1	19.6
95°	71.0	56.2	48.4	43.8	41.0	39.9	40.3
97.5°	176.7	138.5	113.0	96.1	87.4	82.3	79.3
100°	278.8	230.4	187.6	158.3	143.1	132.9	126.5
102.5°	382.5	347.1	301.8	269.9	244.0	231.2	222.6
105°	469.2	473.8	462.2	440.2	418.3	403.1	398.2
107.5°	462.9	499.6	516.7	519.5	518.3	515.2	508.7
110°	443.1	488.3	517.3	532.5	539.2	542.4	542.0



TEST NUMBER: P331647

CATALOG NUMBER: S122RDIP-S485D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	419.6	467.9	501.2	522.3	533.5	539.5	541.4
115°	387.6	433.9	470.3	495.4	511.6	520.8	524.0
117.5°	361.6	403.6	437.7	463.3	480.5	490.1	492.8
120°	348.0	385.5	417.6	442.4	459.0	469.2	472.8
122.5°	336.7	372.2	401.2	423.4	439.8	448.9	451.8
125°	321.9	353.0	379.5	400.0	413.4	422.2	425.1
127.5°	307.5	336.8	361.2	379.1	391.7	399.3	401.6
130°	297.9	325.8	349.1	366.4	378.4	385.5	388.3
132.5°	288.8	314.5	336.4	353.4	365.4	371.9	374.5
135°	274.5	297.9	317.6	332.8	344.5	350.9	352.3
137.5°	263.2	281.7	298.9	312.8	322.8	328.4	330.5
140°	255.8	272.1	287.6	298.9	308.1	313.4	315.5
142.5°	249.3	263.3	276.3	287.0	295.4	300.1	300.5
145°	241.0	251.9	262.2	270.6	276.7	280.2	281.2
147.5°	234.2	242.7	250.2	257.2	262.0	264.4	265.1
150°	229.7	237.1	243.4	248.7	253.0	255.1	255.5
152.5°	226.0	232.3	237.8	242.0	245.6	247.2	247.3
155°	220.1	225.4	229.3	233.2	235.7	237.1	236.4
157.5°	214.2	218.6	221.7	224.4	226.5	227.1	227.1
160°	210.2	214.1	216.6	219.1	220.8	221.2	221.2
162.5°	206.6	209.9	211.8	214.3	215.5	215.8	215.5
165°	201.0	203.5	204.9	206.3	207.8	207.8	207.4
167.5°	196.0	197.7	199.0	199.6	200.4	200.3	199.9
170°	192.9	194.3	195.0	195.4	196.4	196.1	195.4
172.5°	190.1	191.2	191.6	192.0	192.5	192.1	191.7
175°	186.9	187.3	187.6	187.6	188.0	187.6	186.9
177.5°	184.6	184.9	184.9	184.9	184.9	184.6	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7

(END OF REPORT)