

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331242-935

Luminaire Tested: **S122DIP-S290D330U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331242-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D330U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2225.0 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	57	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	44	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	2.2
10°-20°	140.9	6.3
20°-30°	204.5	9.2
30°-40°	215.8	9.7
40°-50°	191.1	8.6
50°-60°	152.5	6.9
60°-70°	103.6	4.7
70°-80°	53.1	2.4
80°-90°	14.2	0.6
90°-100°	63.3	2.8
100°-110°	214.7	9.6
110°-120°	228.0	10.2
120°-130°	187.7	8.4
130°-140°	150.7	6.8
140°-150°	113.9	5.1
150°-160°	80.1	3.6
160°-170°	47.1	2.1
170°-180°	15.3	0.7
0°-30°	393.9	17.7
0°-40°	609.7	27.4
0°-60°	953.2	42.8
0°-90°	1124.2	50.5
90°-120°	505.9	22.7
90°-150°	958.3	43.1
90°-180°	1101.0	49.5
0°-180°	2225.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	12
90°	10	0	10	0	10	6
95°	35	11	35	11	35	45
105°	343	37	343	37	343	332
115°	451	65	451	65	451	442
125°	366	91	366	91	366	331
135°	303	107	303	107	303	236
145°	242	122	242	122	242	154
155°	204	139	204	139	204	95
165°	179	152	179	152	179	51
175°	161	158	161	158	161	16
180°	158	158	158	158	158	



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	6.1	6.1	6.2	6.1	6.1	6.2	6.0	6.0	6.2	6.5	6.5
90°	10.1	10.1	10.1	10.1	10.1	9.7	9.1	9.7	10.1	10.3	10.1
92.5°	16.9	17.3	17.1	18.1	18.3	20.2	22.7	26.5	33.4	39.5	39.0
95°	34.7	34.4	35.3	37.7	41.7	48.4	61.1	79.7	104.4	119.2	105.6
97.5°	68.3	70.9	75.3	82.7	97.3	119.2	152.1	186.0	213.5	203.5	153.3
100°	108.9	114.4	123.2	136.3	161.5	198.4	240.0	277.8	284.1	240.3	165.5
102.5°	191.7	199.1	210.1	232.4	259.8	298.9	329.3	337.9	310.4	241.5	160.8
105°	342.9	347.1	360.2	379.0	398.0	407.9	404.0	369.6	306.3	225.4	151.8
107.5°	438.0	443.6	446.3	447.3	444.9	430.2	398.6	346.7	279.7	208.1	147.3
110°	466.7	467.0	464.3	458.5	445.4	420.4	381.5	327.0	262.9	199.8	146.4



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	466.1	464.5	459.3	449.7	431.5	402.9	361.3	309.0	251.2	194.5	146.5
115°	451.2	448.4	440.5	426.5	404.9	373.6	333.7	286.9	236.7	188.6	147.8
117.5°	424.3	422.0	413.7	398.9	376.9	347.5	311.3	270.2	227.6	185.7	150.1
120°	407.1	404.0	395.2	380.9	359.6	331.9	299.6	261.9	222.7	184.1	151.5
122.5°	389.0	386.5	378.7	364.5	345.4	320.5	289.9	255.4	218.5	183.0	153.2
125°	366.0	363.5	355.9	344.4	326.7	303.9	277.2	245.8	212.7	181.3	155.8
127.5°	345.8	343.8	337.3	326.4	311.0	290.0	264.8	236.3	207.2	180.3	158.3
130°	334.3	331.9	325.8	315.5	300.6	280.5	256.5	230.3	203.5	179.8	160.3
132.5°	322.4	320.2	314.6	304.3	289.6	270.8	248.7	224.5	200.6	179.5	162.3
135°	303.3	302.1	296.6	286.5	273.5	256.5	236.3	216.3	196.5	179.2	164.6
137.5°	284.6	282.8	277.9	269.3	257.4	242.5	226.6	209.8	193.6	179.1	166.7
140°	271.6	269.8	265.3	257.4	247.6	234.3	220.2	205.6	191.9	178.9	167.6
142.5°	258.7	258.4	254.3	247.1	237.9	226.7	214.6	202.2	190.3	178.9	168.3
145°	242.1	241.3	238.2	233.0	225.8	216.9	207.5	197.4	188.0	178.2	169.1
147.5°	228.3	227.6	225.6	221.4	215.4	209.0	201.6	193.7	185.7	177.2	169.4
150°	220.0	219.6	217.8	214.1	209.6	204.1	197.8	191.1	183.7	176.4	169.1
152.5°	212.9	212.8	211.5	208.4	204.7	200.0	194.6	188.4	182.0	175.2	168.7
155°	203.5	204.1	202.9	200.8	197.4	194.1	189.5	184.7	178.9	173.1	167.9
157.5°	195.5	195.5	195.0	193.2	190.9	188.2	184.4	180.4	175.9	170.9	166.5
160°	190.5	190.5	190.1	188.6	186.5	184.3	181.0	177.6	173.7	169.4	165.8
162.5°	185.5	185.8	185.5	184.5	182.4	180.7	177.9	175.0	171.8	168.2	165.1
165°	178.6	178.9	178.9	177.6	176.4	175.2	173.1	171.0	168.5	165.8	163.7
167.5°	172.1	172.5	172.5	171.9	171.3	170.2	168.8	167.1	165.4	163.7	162.3
170°	168.2	168.8	169.1	168.2	167.9	167.3	166.1	165.2	163.7	162.5	161.5
172.5°	165.1	165.4	165.7	165.3	165.0	164.6	163.7	163.0	162.0	161.0	160.6
175°	160.9	161.5	161.9	161.5	161.5	161.3	160.9	160.7	159.7	159.4	159.1
177.5°	158.4	158.9	159.2	159.2	159.2	159.2	158.9	158.9	158.4	158.2	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	6.4	5.9	5.6	5.8	5.2	5.0	4.1	3.5	3.5	3.6	3.4
90°	8.2	6.1	4.6	3.6	3.0	2.4	1.2	0.3	1.2	2.4	3.0
92.5°	30.4	20.7	13.8	10.9	8.9	7.6	5.3	3.7	5.3	7.6	8.9
95°	70.3	43.8	29.8	22.5	17.7	14.9	11.9	10.7	11.9	14.9	17.7
97.5°	94.7	57.8	40.2	31.9	26.3	22.2	18.9	17.3	18.9	22.2	26.3
100°	99.8	62.7	46.6	38.1	31.9	27.0	24.4	23.4	24.4	27.0	31.9
102.5°	100.0	67.1	52.2	43.7	37.3	32.5	29.7	29.0	29.7	32.5	37.3
105°	101.6	74.6	60.3	51.7	45.0	40.5	38.3	37.1	38.3	40.5	45.0
107.5°	105.8	82.2	68.4	59.8	53.1	48.9	46.8	45.9	46.8	48.9	53.1
110°	109.2	87.3	74.0	65.1	58.7	54.8	53.0	51.7	53.0	54.8	58.7



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	112.9	92.2	79.3	70.2	64.1	60.4	58.3	57.1	58.3	60.4	64.1
115°	118.3	99.8	86.7	78.5	72.4	68.8	66.9	65.4	66.9	68.8	72.4
117.5°	124.2	106.8	94.7	86.2	80.3	77.1	75.3	74.0	75.3	77.1	80.3
120°	128.1	111.7	99.8	91.3	85.2	82.5	80.6	79.4	80.6	82.5	85.2
122.5°	131.5	116.2	105.1	96.3	90.3	87.3	85.5	84.6	85.5	87.3	90.3
125°	136.9	123.2	112.3	103.8	97.6	94.0	92.2	91.3	92.2	94.0	97.6
127.5°	142.0	129.7	119.0	110.2	104.4	100.4	97.8	96.6	97.8	100.4	104.4
130°	145.1	133.5	122.9	114.4	108.3	104.0	101.0	99.8	101.0	104.0	108.3
132.5°	148.3	137.0	126.8	118.3	111.9	107.5	104.2	102.7	104.2	107.5	111.9
135°	152.4	141.8	132.0	123.6	116.5	111.9	108.3	107.1	108.3	111.9	116.5
137.5°	155.6	145.7	136.0	128.1	121.2	116.3	112.7	111.2	112.7	116.3	121.2
140°	157.3	147.8	138.7	130.8	124.2	119.2	115.6	114.4	115.6	119.2	124.2
142.5°	158.8	149.6	140.7	133.3	126.8	121.9	118.6	117.5	118.6	121.9	126.8
145°	160.7	152.1	143.9	137.2	131.1	126.6	123.6	122.3	123.6	126.6	131.1
147.5°	161.7	154.2	146.5	140.5	135.4	131.2	128.3	127.4	128.3	131.2	135.4
150°	162.1	155.2	148.2	142.7	138.1	134.1	131.7	130.8	131.7	134.1	138.1
152.5°	162.4	156.1	149.8	144.9	140.5	137.1	134.7	134.2	134.7	137.1	140.5
155°	162.7	157.6	152.4	147.8	144.5	141.1	139.3	139.1	139.3	141.1	144.5
157.5°	162.7	158.6	154.2	150.4	147.7	144.8	143.4	143.0	143.4	144.8	147.7
160°	162.7	159.1	155.5	152.1	149.6	147.2	146.0	145.7	146.0	147.2	149.6
162.5°	162.5	159.4	156.2	153.6	151.4	149.5	148.2	148.4	148.2	149.5	151.4
165°	161.9	159.7	157.0	155.2	153.6	151.8	151.2	151.5	151.2	151.8	153.6
167.5°	161.4	159.6	157.6	156.5	155.4	154.2	153.7	154.0	153.7	154.2	155.4
170°	160.9	159.4	157.9	157.0	156.4	155.5	155.2	155.8	155.2	155.5	156.4
172.5°	160.2	159.2	158.2	157.5	157.1	156.2	156.4	156.7	156.4	156.2	157.1
175°	159.4	158.8	158.2	157.9	157.9	157.3	157.6	157.9	157.6	157.3	157.9
177.5°	158.9	158.4	158.2	158.2	158.2	157.7	157.9	158.4	157.9	157.7	158.2
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	3.4	3.4	3.5	4.0	4.2	4.1	3.9	3.8	3.7	3.5	3.5
90°	3.6	4.6	6.1	8.2	10.1	10.3	10.1	9.7	9.1	9.7	10.1
92.5°	10.9	13.8	20.7	30.4	39.0	39.5	33.4	26.5	22.7	20.2	18.3
95°	22.5	29.8	43.8	70.3	105.6	119.2	104.4	79.7	61.1	48.4	41.7
97.5°	31.9	40.2	57.8	94.7	153.3	203.5	213.5	186.0	152.1	119.2	97.3
100°	38.1	46.6	62.7	99.8	165.5	240.3	284.1	277.8	240.0	198.4	161.5
102.5°	43.7	52.2	67.1	100.0	160.8	241.5	310.4	337.9	329.3	298.9	259.8
105°	51.7	60.3	74.6	101.6	151.8	225.4	306.3	369.6	404.0	407.9	398.0
107.5°	59.8	68.4	82.2	105.8	147.3	208.1	279.7	346.7	398.6	430.2	444.9
110°	65.1	74.0	87.3	109.2	146.4	199.8	262.9	327.0	381.5	420.4	445.4



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	70.2	79.3	92.2	112.9	146.5	194.5	251.2	309.0	361.3	402.9	431.5
115°	78.5	86.7	99.8	118.3	147.8	188.6	236.7	286.9	333.7	373.6	404.9
117.5°	86.2	94.7	106.8	124.2	150.1	185.7	227.6	270.2	311.3	347.5	376.9
120°	91.3	99.8	111.7	128.1	151.5	184.1	222.7	261.9	299.6	331.9	359.6
122.5°	96.3	105.1	116.2	131.5	153.2	183.0	218.5	255.4	289.9	320.5	345.4
125°	103.8	112.3	123.2	136.9	155.8	181.3	212.7	245.8	277.2	303.9	326.7
127.5°	110.2	119.0	129.7	142.0	158.3	180.3	207.2	236.3	264.8	290.0	311.0
130°	114.4	122.9	133.5	145.1	160.3	179.8	203.5	230.3	256.5	280.5	300.6
132.5°	118.3	126.8	137.0	148.3	162.3	179.5	200.6	224.5	248.7	270.8	289.6
135°	123.6	132.0	141.8	152.4	164.6	179.2	196.5	216.3	236.3	256.5	273.5
137.5°	128.1	136.0	145.7	155.6	166.7	179.1	193.6	209.8	226.6	242.5	257.4
140°	130.8	138.7	147.8	157.3	167.6	178.9	191.9	205.6	220.2	234.3	247.6
142.5°	133.3	140.7	149.6	158.8	168.3	178.9	190.3	202.2	214.6	226.7	237.9
145°	137.2	143.9	152.1	160.7	169.1	178.2	188.0	197.4	207.5	216.9	225.8
147.5°	140.5	146.5	154.2	161.7	169.4	177.2	185.7	193.7	201.6	209.0	215.4
150°	142.7	148.2	155.2	162.1	169.1	176.4	183.7	191.1	197.8	204.1	209.6
152.5°	144.9	149.8	156.1	162.4	168.7	175.2	182.0	188.4	194.6	200.0	204.7
155°	147.8	152.4	157.6	162.7	167.9	173.1	178.9	184.7	189.5	194.1	197.4
157.5°	150.4	154.2	158.6	162.7	166.5	170.9	175.9	180.4	184.4	188.2	190.9
160°	152.1	155.5	159.1	162.7	165.8	169.4	173.7	177.6	181.0	184.3	186.5
162.5°	153.6	156.2	159.4	162.5	165.1	168.2	171.8	175.0	177.9	180.7	182.4
165°	155.2	157.0	159.7	161.9	163.7	165.8	168.5	171.0	173.1	175.2	176.4
167.5°	156.5	157.6	159.6	161.4	162.3	163.7	165.4	167.1	168.8	170.2	171.3
170°	157.0	157.9	159.4	160.9	161.5	162.5	163.7	165.2	166.1	167.3	167.9
172.5°	157.5	158.2	159.2	160.2	160.6	161.0	162.0	163.0	163.7	164.6	165.0
175°	157.9	158.2	158.8	159.4	159.1	159.4	159.7	160.7	160.9	161.3	161.5
177.5°	158.2	158.2	158.4	158.9	158.4	158.2	158.4	158.9	158.9	159.2	159.2
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	3.5	3.4	3.4	3.3	3.4	3.4	3.5	3.5	3.5	3.7	3.8
90°	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	9.7	9.1	9.7
92.5°	18.1	17.1	17.3	16.9	17.3	17.1	18.1	18.3	20.2	22.7	26.5
95°	37.7	35.3	34.4	34.7	34.4	35.3	37.7	41.7	48.4	61.1	79.7
97.5°	82.7	75.3	70.9	68.3	70.9	75.3	82.7	97.3	119.2	152.1	186.0
100°	136.3	123.2	114.4	108.9	114.4	123.2	136.3	161.5	198.4	240.0	277.8
102.5°	232.4	210.1	199.1	191.7	199.1	210.1	232.4	259.8	298.9	329.3	337.9
105°	379.0	360.2	347.1	342.9	347.1	360.2	379.0	398.0	407.9	404.0	369.6
107.5°	447.3	446.3	443.6	438.0	443.6	446.3	447.3	444.9	430.2	398.6	346.7
110°	458.5	464.3	467.0	466.7	467.0	464.3	458.5	445.4	420.4	381.5	327.0



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	449.7	459.3	464.5	466.1	464.5	459.3	449.7	431.5	402.9	361.3	309.0
115°	426.5	440.5	448.4	451.2	448.4	440.5	426.5	404.9	373.6	333.7	286.9
117.5°	398.9	413.7	422.0	424.3	422.0	413.7	398.9	376.9	347.5	311.3	270.2
120°	380.9	395.2	404.0	407.1	404.0	395.2	380.9	359.6	331.9	299.6	261.9
122.5°	364.5	378.7	386.5	389.0	386.5	378.7	364.5	345.4	320.5	289.9	255.4
125°	344.4	355.9	363.5	366.0	363.5	355.9	344.4	326.7	303.9	277.2	245.8
127.5°	326.4	337.3	343.8	345.8	343.8	337.3	326.4	311.0	290.0	264.8	236.3
130°	315.5	325.8	331.9	334.3	331.9	325.8	315.5	300.6	280.5	256.5	230.3
132.5°	304.3	314.6	320.2	322.4	320.2	314.6	304.3	289.6	270.8	248.7	224.5
135°	286.5	296.6	302.1	303.3	302.1	296.6	286.5	273.5	256.5	236.3	216.3
137.5°	269.3	277.9	282.8	284.6	282.8	277.9	269.3	257.4	242.5	226.6	209.8
140°	257.4	265.3	269.8	271.6	269.8	265.3	257.4	247.6	234.3	220.2	205.6
142.5°	247.1	254.3	258.4	258.7	258.4	254.3	247.1	237.9	226.7	214.6	202.2
145°	233.0	238.2	241.3	242.1	241.3	238.2	233.0	225.8	216.9	207.5	197.4
147.5°	221.4	225.6	227.6	228.3	227.6	225.6	221.4	215.4	209.0	201.6	193.7
150°	214.1	217.8	219.6	220.0	219.6	217.8	214.1	209.6	204.1	197.8	191.1
152.5°	208.4	211.5	212.8	212.9	212.8	211.5	208.4	204.7	200.0	194.6	188.4
155°	200.8	202.9	204.1	203.5	204.1	202.9	200.8	197.4	194.1	189.5	184.7
157.5°	193.2	195.0	195.5	195.5	195.5	195.0	193.2	190.9	188.2	184.4	180.4
160°	188.6	190.1	190.5	190.5	190.5	190.1	188.6	186.5	184.3	181.0	177.6
162.5°	184.5	185.5	185.8	185.5	185.8	185.5	184.5	182.4	180.7	177.9	175.0
165°	177.6	178.9	178.9	178.6	178.9	178.9	177.6	176.4	175.2	173.1	171.0
167.5°	171.9	172.5	172.5	172.1	172.5	172.5	171.9	171.3	170.2	168.8	167.1
170°	168.2	169.1	168.8	168.2	168.8	169.1	168.2	167.9	167.3	166.1	165.2
172.5°	165.3	165.7	165.4	165.1	165.4	165.7	165.3	165.0	164.6	163.7	163.0
175°	161.5	161.9	161.5	160.9	161.5	161.9	161.5	161.5	161.3	160.9	160.7
177.5°	159.2	159.2	158.9	158.4	158.9	159.2	159.2	159.2	159.2	158.9	158.9
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	3.9	4.1	4.2	4.0	3.5	3.4	3.4	3.4	3.6	3.5	3.5
90°	10.1	10.3	10.1	8.2	6.1	4.6	3.6	3.0	2.4	1.2	0.3
92.5°	33.4	39.5	39.0	30.4	20.7	13.8	10.9	8.9	7.6	5.3	3.7
95°	104.4	119.2	105.6	70.3	43.8	29.8	22.5	17.7	14.9	11.9	10.7
97.5°	213.5	203.5	153.3	94.7	57.8	40.2	31.9	26.3	22.2	18.9	17.3
100°	284.1	240.3	165.5	99.8	62.7	46.6	38.1	31.9	27.0	24.4	23.4
102.5°	310.4	241.5	160.8	100.0	67.1	52.2	43.7	37.3	32.5	29.7	29.0
105°	306.3	225.4	151.8	101.6	74.6	60.3	51.7	45.0	40.5	38.3	37.1
107.5°	279.7	208.1	147.3	105.8	82.2	68.4	59.8	53.1	48.9	46.8	45.9
110°	262.9	199.8	146.4	109.2	87.3	74.0	65.1	58.7	54.8	53.0	51.7



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	251.2	194.5	146.5	112.9	92.2	79.3	70.2	64.1	60.4	58.3	57.1
115°	236.7	188.6	147.8	118.3	99.8	86.7	78.5	72.4	68.8	66.9	65.4
117.5°	227.6	185.7	150.1	124.2	106.8	94.7	86.2	80.3	77.1	75.3	74.0
120°	222.7	184.1	151.5	128.1	111.7	99.8	91.3	85.2	82.5	80.6	79.4
122.5°	218.5	183.0	153.2	131.5	116.2	105.1	96.3	90.3	87.3	85.5	84.6
125°	212.7	181.3	155.8	136.9	123.2	112.3	103.8	97.6	94.0	92.2	91.3
127.5°	207.2	180.3	158.3	142.0	129.7	119.0	110.2	104.4	100.4	97.8	96.6
130°	203.5	179.8	160.3	145.1	133.5	122.9	114.4	108.3	104.0	101.0	99.8
132.5°	200.6	179.5	162.3	148.3	137.0	126.8	118.3	111.9	107.5	104.2	102.7
135°	196.5	179.2	164.6	152.4	141.8	132.0	123.6	116.5	111.9	108.3	107.1
137.5°	193.6	179.1	166.7	155.6	145.7	136.0	128.1	121.2	116.3	112.7	111.2
140°	191.9	178.9	167.6	157.3	147.8	138.7	130.8	124.2	119.2	115.6	114.4
142.5°	190.3	178.9	168.3	158.8	149.6	140.7	133.3	126.8	121.9	118.6	117.5
145°	188.0	178.2	169.1	160.7	152.1	143.9	137.2	131.1	126.6	123.6	122.3
147.5°	185.7	177.2	169.4	161.7	154.2	146.5	140.5	135.4	131.2	128.3	127.4
150°	183.7	176.4	169.1	162.1	155.2	148.2	142.7	138.1	134.1	131.7	130.8
152.5°	182.0	175.2	168.7	162.4	156.1	149.8	144.9	140.5	137.1	134.7	134.2
155°	178.9	173.1	167.9	162.7	157.6	152.4	147.8	144.5	141.1	139.3	139.1
157.5°	175.9	170.9	166.5	162.7	158.6	154.2	150.4	147.7	144.8	143.4	143.0
160°	173.7	169.4	165.8	162.7	159.1	155.5	152.1	149.6	147.2	146.0	145.7
162.5°	171.8	168.2	165.1	162.5	159.4	156.2	153.6	151.4	149.5	148.2	148.4
165°	168.5	165.8	163.7	161.9	159.7	157.0	155.2	153.6	151.8	151.2	151.5
167.5°	165.4	163.7	162.3	161.4	159.6	157.6	156.5	155.4	154.2	153.7	154.0
170°	163.7	162.5	161.5	160.9	159.4	157.9	157.0	156.4	155.5	155.2	155.8
172.5°	162.0	161.0	160.6	160.2	159.2	158.2	157.5	157.1	156.2	156.4	156.7
175°	159.7	159.4	159.1	159.4	158.8	158.2	157.9	157.9	157.3	157.6	157.9
177.5°	158.4	158.2	158.4	158.9	158.4	158.2	158.2	158.2	157.7	157.9	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.1	5.0	5.2	5.8	5.6	5.9	6.4	6.5	6.5	6.2	6.0
90°	1.2	2.4	3.0	3.6	4.6	6.1	8.2	10.1	10.3	10.1	9.7
92.5°	5.3	7.6	8.9	10.9	13.8	20.7	30.4	39.0	39.5	33.4	26.5
95°	11.9	14.9	17.7	22.5	29.8	43.8	70.3	105.6	119.2	104.4	79.7
97.5°	18.9	22.2	26.3	31.9	40.2	57.8	94.7	153.3	203.5	213.5	186.0
100°	24.4	27.0	31.9	38.1	46.6	62.7	99.8	165.5	240.3	284.1	277.8
102.5°	29.7	32.5	37.3	43.7	52.2	67.1	100.0	160.8	241.5	310.4	337.9
105°	38.3	40.5	45.0	51.7	60.3	74.6	101.6	151.8	225.4	306.3	369.6
107.5°	46.8	48.9	53.1	59.8	68.4	82.2	105.8	147.3	208.1	279.7	346.7
110°	53.0	54.8	58.7	65.1	74.0	87.3	109.2	146.4	199.8	262.9	327.0



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	58.3	60.4	64.1	70.2	79.3	92.2	112.9	146.5	194.5	251.2	309.0
115°	66.9	68.8	72.4	78.5	86.7	99.8	118.3	147.8	188.6	236.7	286.9
117.5°	75.3	77.1	80.3	86.2	94.7	106.8	124.2	150.1	185.7	227.6	270.2
120°	80.6	82.5	85.2	91.3	99.8	111.7	128.1	151.5	184.1	222.7	261.9
122.5°	85.5	87.3	90.3	96.3	105.1	116.2	131.5	153.2	183.0	218.5	255.4
125°	92.2	94.0	97.6	103.8	112.3	123.2	136.9	155.8	181.3	212.7	245.8
127.5°	97.8	100.4	104.4	110.2	119.0	129.7	142.0	158.3	180.3	207.2	236.3
130°	101.0	104.0	108.3	114.4	122.9	133.5	145.1	160.3	179.8	203.5	230.3
132.5°	104.2	107.5	111.9	118.3	126.8	137.0	148.3	162.3	179.5	200.6	224.5
135°	108.3	111.9	116.5	123.6	132.0	141.8	152.4	164.6	179.2	196.5	216.3
137.5°	112.7	116.3	121.2	128.1	136.0	145.7	155.6	166.7	179.1	193.6	209.8
140°	115.6	119.2	124.2	130.8	138.7	147.8	157.3	167.6	178.9	191.9	205.6
142.5°	118.6	121.9	126.8	133.3	140.7	149.6	158.8	168.3	178.9	190.3	202.2
145°	123.6	126.6	131.1	137.2	143.9	152.1	160.7	169.1	178.2	188.0	197.4
147.5°	128.3	131.2	135.4	140.5	146.5	154.2	161.7	169.4	177.2	185.7	193.7
150°	131.7	134.1	138.1	142.7	148.2	155.2	162.1	169.1	176.4	183.7	191.1
152.5°	134.7	137.1	140.5	144.9	149.8	156.1	162.4	168.7	175.2	182.0	188.4
155°	139.3	141.1	144.5	147.8	152.4	157.6	162.7	167.9	173.1	178.9	184.7
157.5°	143.4	144.8	147.7	150.4	154.2	158.6	162.7	166.5	170.9	175.9	180.4
160°	146.0	147.2	149.6	152.1	155.5	159.1	162.7	165.8	169.4	173.7	177.6
162.5°	148.2	149.5	151.4	153.6	156.2	159.4	162.5	165.1	168.2	171.8	175.0
165°	151.2	151.8	153.6	155.2	157.0	159.7	161.9	163.7	165.8	168.5	171.0
167.5°	153.7	154.2	155.4	156.5	157.6	159.6	161.4	162.3	163.7	165.4	167.1
170°	155.2	155.5	156.4	157.0	157.9	159.4	160.9	161.5	162.5	163.7	165.2
172.5°	156.4	156.2	157.1	157.5	158.2	159.2	160.2	160.6	161.0	162.0	163.0
175°	157.6	157.3	157.9	157.9	158.2	158.8	159.4	159.1	159.4	159.7	160.7
177.5°	157.9	157.7	158.2	158.2	158.2	158.4	158.9	158.4	158.2	158.4	158.9
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	6.0	6.2	6.1	6.1	6.2	6.1	6.1
90°	9.1	9.7	10.1	10.1	10.1	10.1	10.1
92.5°	22.7	20.2	18.3	18.1	17.1	17.3	16.9
95°	61.1	48.4	41.7	37.7	35.3	34.4	34.7
97.5°	152.1	119.2	97.3	82.7	75.3	70.9	68.3
100°	240.0	198.4	161.5	136.3	123.2	114.4	108.9
102.5°	329.3	298.9	259.8	232.4	210.1	199.1	191.7
105°	404.0	407.9	398.0	379.0	360.2	347.1	342.9
107.5°	398.6	430.2	444.9	447.3	446.3	443.6	438.0
110°	381.5	420.4	445.4	458.5	464.3	467.0	466.7



TEST NUMBER: P331242-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	361.3	402.9	431.5	449.7	459.3	464.5	466.1
115°	333.7	373.6	404.9	426.5	440.5	448.4	451.2
117.5°	311.3	347.5	376.9	398.9	413.7	422.0	424.3
120°	299.6	331.9	359.6	380.9	395.2	404.0	407.1
122.5°	289.9	320.5	345.4	364.5	378.7	386.5	389.0
125°	277.2	303.9	326.7	344.4	355.9	363.5	366.0
127.5°	264.8	290.0	311.0	326.4	337.3	343.8	345.8
130°	256.5	280.5	300.6	315.5	325.8	331.9	334.3
132.5°	248.7	270.8	289.6	304.3	314.6	320.2	322.4
135°	236.3	256.5	273.5	286.5	296.6	302.1	303.3
137.5°	226.6	242.5	257.4	269.3	277.9	282.8	284.6
140°	220.2	234.3	247.6	257.4	265.3	269.8	271.6
142.5°	214.6	226.7	237.9	247.1	254.3	258.4	258.7
145°	207.5	216.9	225.8	233.0	238.2	241.3	242.1
147.5°	201.6	209.0	215.4	221.4	225.6	227.6	228.3
150°	197.8	204.1	209.6	214.1	217.8	219.6	220.0
152.5°	194.6	200.0	204.7	208.4	211.5	212.8	212.9
155°	189.5	194.1	197.4	200.8	202.9	204.1	203.5
157.5°	184.4	188.2	190.9	193.2	195.0	195.5	195.5
160°	181.0	184.3	186.5	188.6	190.1	190.5	190.5
162.5°	177.9	180.7	182.4	184.5	185.5	185.8	185.5
165°	173.1	175.2	176.4	177.6	178.9	178.9	178.6
167.5°	168.8	170.2	171.3	171.9	172.5	172.5	172.1
170°	166.1	167.3	167.9	168.2	169.1	168.8	168.2
172.5°	163.7	164.6	165.0	165.3	165.7	165.4	165.1
175°	160.9	161.3	161.5	161.5	161.9	161.5	160.9
177.5°	158.9	159.2	159.2	159.2	159.2	158.9	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2

(END OF REPORT)