

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331251-935

Luminaire Tested: **S122DIP-S290D530U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331251-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D530U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2901.8 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	84	87	83	80	77	68	66	64	54	53	51	41	40	39	33
2	87	80	74	70	79	73	68	64	60	57	53	48	45	43	37	35	34	29
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	29	27	25	21
5	67	56	48	43	61	51	45	40	43	38	34	34	31	28	27	24	22	19
6	62	50	43	37	56	46	40	35	39	33	30	31	27	25	24	22	20	17
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18	15
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	21	18	16	14
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	15	12
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	1.7
10°-20°	140.9	4.9
20°-30°	204.5	7.0
30°-40°	215.8	7.4
40°-50°	191.1	6.6
50°-60°	152.5	5.3
60°-70°	103.6	3.6
70°-80°	53.1	1.8
80°-90°	15.1	0.5
90°-100°	102.1	3.5
100°-110°	346.4	11.9
110°-120°	368.0	12.7
120°-130°	303.0	10.4
130°-140°	243.3	8.4
140°-150°	183.9	6.3
150°-160°	129.2	4.5
160°-170°	76.1	2.6
170°-180°	24.8	0.9
0°-30°	393.9	13.6
0°-40°	609.7	21.0
0°-60°	953.2	32.8
0°-90°	1125.1	38.8
90°-120°	816.6	28.1
90°-150°	1546.7	53.3
90°-180°	1777.0	61.2
0°-180°	2901.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	12
90°	16	0	16	0	16	9
95°	56	17	56	17	56	73
105°	553	60	553	60	553	535
115°	728	106	728	106	728	713
125°	591	147	591	147	591	534
135°	490	173	490	173	490	380
145°	391	197	391	197	391	248
155°	328	224	328	224	328	153
165°	288	244	288	244	288	82
175°	260	255	260	255	260	25
180°	255	255	255	255	255	



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	7.3	7.3	7.5	7.3	7.3	7.4	7.1	7.2	7.5	7.7	7.7
90°	16.2	16.2	16.2	16.2	16.2	15.7	14.7	15.7	16.2	16.7	16.2
92.5°	27.2	28.0	27.6	29.2	29.5	32.6	36.8	42.8	53.9	63.8	62.9
95°	56.0	55.4	57.0	60.9	67.2	78.1	98.7	128.6	168.4	192.5	170.4
97.5°	110.2	114.3	121.5	133.5	157.0	192.5	245.6	300.2	344.7	328.6	247.5
100°	175.8	184.6	198.9	220.0	260.7	320.1	387.4	448.3	458.6	387.9	267.1
102.5°	309.4	321.3	339.1	375.1	419.4	482.4	531.6	545.4	501.0	389.9	259.7
105°	553.4	560.3	581.3	611.8	642.2	658.5	652.0	596.6	494.5	363.9	245.0
107.5°	706.9	716.0	720.2	721.9	718.1	694.3	643.3	559.6	451.3	336.0	237.7
110°	753.2	753.7	749.3	739.9	718.8	678.6	615.7	527.9	424.2	322.6	236.2



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	752.4	749.8	741.4	725.8	696.5	650.3	583.2	498.8	405.4	313.9	236.6
115°	728.1	723.8	711.0	688.4	653.6	603.0	538.6	463.0	382.0	304.4	238.7
117.5°	684.8	681.1	667.7	643.9	608.3	560.9	502.5	436.1	367.3	299.8	242.2
120°	656.9	652.0	637.8	614.8	580.4	535.7	483.6	422.8	359.5	297.0	244.5
122.5°	627.9	623.8	611.1	588.4	557.6	517.2	468.0	412.2	352.8	295.5	247.3
125°	590.7	586.8	574.5	555.9	527.4	490.5	447.3	396.7	343.2	292.7	251.4
127.5°	558.1	554.9	544.3	526.8	502.0	468.0	427.3	381.5	334.4	291.0	255.6
130°	539.6	535.7	525.9	509.2	485.1	452.7	414.0	371.7	328.5	290.2	258.7
132.5°	520.4	516.9	507.8	491.1	467.4	437.0	401.4	362.3	323.7	289.8	261.9
135°	489.6	487.6	478.7	462.5	441.4	414.0	381.5	349.1	317.2	289.2	265.6
137.5°	459.3	456.3	448.6	434.6	415.4	391.4	365.8	338.6	312.5	289.1	269.0
140°	438.5	435.5	428.2	415.4	399.7	378.1	355.5	331.9	309.9	288.7	270.5
142.5°	417.7	417.1	410.5	398.9	384.0	365.9	346.5	326.4	307.1	288.7	271.7
145°	390.8	389.3	384.4	376.1	364.4	350.1	334.8	318.7	303.4	287.7	273.0
147.5°	368.3	367.5	364.1	357.5	347.8	337.3	325.5	312.7	299.7	285.9	273.4
150°	355.0	354.5	351.5	345.7	338.3	329.5	319.2	308.3	296.6	284.8	273.0
152.5°	343.6	343.5	341.4	336.2	330.5	322.8	314.1	304.0	293.9	282.8	272.2
155°	328.5	329.5	327.5	324.1	318.7	313.2	305.9	298.1	288.7	279.4	271.0
157.5°	315.6	315.6	314.8	311.9	308.1	303.8	297.6	291.1	283.9	275.9	268.8
160°	307.4	307.4	306.9	304.4	301.0	297.6	292.1	286.7	280.3	273.5	267.6
162.5°	299.5	299.9	299.5	297.7	294.3	291.7	287.1	282.4	277.2	271.6	266.4
165°	288.3	288.7	288.7	286.7	284.8	282.8	279.4	276.0	272.0	267.6	264.2
167.5°	277.8	278.4	278.5	277.4	276.6	274.7	272.4	269.8	266.9	264.2	261.9
170°	271.6	272.5	273.0	271.6	271.0	270.1	268.1	266.7	264.2	262.2	260.7
172.5°	266.4	267.0	267.5	266.8	266.3	265.7	264.2	263.1	261.4	259.8	259.2
175°	259.8	260.7	261.2	260.7	260.7	260.3	259.8	259.2	257.8	257.3	256.8
177.5°	255.7	256.5	256.9	256.9	256.9	256.9	256.5	256.5	255.7	255.3	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	7.3	6.6	6.2	6.2	5.5	5.3	4.3	3.5	3.7	3.9	3.8
90°	13.3	9.8	7.4	5.9	4.9	4.0	2.0	0.5	2.0	4.0	4.9
92.5°	49.0	33.4	22.3	17.7	14.4	12.1	8.6	6.0	8.6	12.1	14.4
95°	113.4	70.7	48.1	36.3	28.5	24.0	19.1	17.2	19.1	24.0	28.5
97.5°	152.8	93.3	64.9	51.6	42.5	35.8	30.7	28.0	30.7	35.8	42.5
100°	161.1	101.2	75.2	61.4	51.6	43.7	39.3	37.8	39.3	43.7	51.6
102.5°	161.4	108.2	84.1	70.4	60.2	52.3	48.0	46.8	48.0	52.3	60.2
105°	164.0	120.3	97.2	83.4	72.7	65.3	61.9	59.9	61.9	65.3	72.7
107.5°	170.7	132.7	110.3	96.4	85.8	79.0	75.6	74.0	75.6	79.0	85.8
110°	176.2	140.9	119.3	105.0	94.8	88.4	85.4	83.4	85.4	88.4	94.8



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	182.2	148.8	127.9	113.3	103.4	97.4	94.1	92.1	94.1	97.4	103.4
115°	191.0	161.1	139.9	126.7	116.8	111.0	108.1	105.6	108.1	111.0	116.8
117.5°	200.4	172.4	152.8	139.1	129.7	124.4	121.5	119.5	121.5	124.4	129.7
120°	206.7	180.2	161.1	147.3	137.5	133.0	130.1	128.1	130.1	133.0	137.5
122.5°	212.2	187.7	169.7	155.6	145.8	140.9	138.0	136.4	138.0	140.9	145.8
125°	220.9	198.9	181.2	167.5	157.6	151.7	148.8	147.3	148.8	151.7	157.6
127.5°	229.1	209.3	192.1	178.0	168.5	162.0	157.9	155.9	157.9	162.0	168.5
130°	234.2	215.6	198.4	184.6	174.8	167.9	163.0	161.1	163.0	167.9	174.8
132.5°	239.4	221.0	204.7	190.9	180.7	173.4	168.2	165.7	168.2	173.4	180.7
135°	246.0	228.9	213.1	199.3	188.0	180.7	174.8	172.8	174.8	180.7	188.0
137.5°	251.1	235.1	219.6	206.8	195.6	187.8	181.8	179.5	181.8	187.8	195.6
140°	253.8	238.7	223.9	211.1	200.4	192.5	186.6	184.6	186.6	192.5	200.4
142.5°	256.2	241.4	227.0	215.1	204.7	196.8	191.3	189.8	191.3	196.8	204.7
145°	259.2	245.5	232.2	221.4	211.6	204.2	199.3	197.4	199.3	204.2	211.6
147.5°	261.0	248.8	236.3	226.8	218.6	211.8	207.1	205.6	207.1	211.8	218.6
150°	261.7	250.4	239.1	230.3	222.9	216.5	212.6	211.1	212.6	216.5	222.9
152.5°	262.1	252.0	241.9	233.8	226.9	221.3	217.3	216.6	217.3	221.3	226.9
155°	262.7	254.3	246.0	238.7	233.2	227.8	224.9	224.4	224.9	227.8	233.2
157.5°	262.7	256.0	248.9	242.8	238.4	233.8	231.4	230.8	231.4	233.8	238.4
160°	262.7	256.8	250.9	245.5	241.6	237.6	235.7	235.2	235.7	237.6	241.6
162.5°	262.3	257.2	252.1	247.9	244.4	241.2	239.2	239.5	239.2	241.2	244.4
165°	261.2	257.8	253.4	250.4	248.0	245.0	244.0	244.5	244.0	245.0	248.0
167.5°	260.5	257.7	254.4	252.6	250.8	248.9	248.1	248.7	248.1	248.9	250.8
170°	259.8	257.3	254.9	253.4	252.4	250.9	250.4	251.4	250.4	250.9	252.4
172.5°	258.6	256.9	255.2	254.2	253.6	252.1	252.4	253.0	252.4	252.1	253.6
175°	257.3	256.3	255.3	254.9	254.9	253.8	254.3	254.9	254.3	253.8	254.9
177.5°	256.5	255.7	255.3	255.3	255.3	254.5	254.9	255.7	254.9	254.5	255.3
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	3.9	4.0	4.3	5.0	5.4	5.3	5.1	5.0	4.8	4.7	4.8
90°	5.9	7.4	9.8	13.3	16.2	16.7	16.2	15.7	14.7	15.7	16.2
92.5°	17.7	22.3	33.4	49.0	62.9	63.8	53.9	42.8	36.8	32.6	29.5
95°	36.3	48.1	70.7	113.4	170.4	192.5	168.4	128.6	98.7	78.1	67.2
97.5°	51.6	64.9	93.3	152.8	247.5	328.6	344.7	300.2	245.6	192.5	157.0
100°	61.4	75.2	101.2	161.1	267.1	387.9	458.6	448.3	387.4	320.1	260.7
102.5°	70.4	84.1	108.2	161.4	259.7	389.9	501.0	545.4	531.6	482.4	419.4
105°	83.4	97.2	120.3	164.0	245.0	363.9	494.5	596.6	652.0	658.5	642.2
107.5°	96.4	110.3	132.7	170.7	237.7	336.0	451.3	559.6	643.3	694.3	718.1
110°	105.0	119.3	140.9	176.2	236.2	322.6	424.2	527.9	615.7	678.6	718.8



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	113.3	127.9	148.8	182.2	236.6	313.9	405.4	498.8	583.2	650.3	696.5
115°	126.7	139.9	161.1	191.0	238.7	304.4	382.0	463.0	538.6	603.0	653.6
117.5°	139.1	152.8	172.4	200.4	242.2	299.8	367.3	436.1	502.5	560.9	608.3
120°	147.3	161.1	180.2	206.7	244.5	297.0	359.5	422.8	483.6	535.7	580.4
122.5°	155.6	169.7	187.7	212.2	247.3	295.5	352.8	412.2	468.0	517.2	557.6
125°	167.5	181.2	198.9	220.9	251.4	292.7	343.2	396.7	447.3	490.5	527.4
127.5°	178.0	192.1	209.3	229.1	255.6	291.0	334.4	381.5	427.3	468.0	502.0
130°	184.6	198.4	215.6	234.2	258.7	290.2	328.5	371.7	414.0	452.7	485.1
132.5°	190.9	204.7	221.0	239.4	261.9	289.8	323.7	362.3	401.4	437.0	467.4
135°	199.3	213.1	228.9	246.0	265.6	289.2	317.2	349.1	381.5	414.0	441.4
137.5°	206.8	219.6	235.1	251.1	269.0	289.1	312.5	338.6	365.8	391.4	415.4
140°	211.1	223.9	238.7	253.8	270.5	288.7	309.9	331.9	355.5	378.1	399.7
142.5°	215.1	227.0	241.4	256.2	271.7	288.7	307.1	326.4	346.5	365.9	384.0
145°	221.4	232.2	245.5	259.2	273.0	287.7	303.4	318.7	334.8	350.1	364.4
147.5°	226.8	236.3	248.8	261.0	273.4	285.9	299.7	312.7	325.5	337.3	347.8
150°	230.3	239.1	250.4	261.7	273.0	284.8	296.6	308.3	319.2	329.5	338.3
152.5°	233.8	241.9	252.0	262.1	272.2	282.8	293.9	304.0	314.1	322.8	330.5
155°	238.7	246.0	254.3	262.7	271.0	279.4	288.7	298.1	305.9	313.2	318.7
157.5°	242.8	248.9	256.0	262.7	268.8	275.9	283.9	291.1	297.6	303.8	308.1
160°	245.5	250.9	256.8	262.7	267.6	273.5	280.3	286.7	292.1	297.6	301.0
162.5°	247.9	252.1	257.2	262.3	266.4	271.6	277.2	282.4	287.1	291.7	294.3
165°	250.4	253.4	257.8	261.2	264.2	267.6	272.0	276.0	279.4	282.8	284.8
167.5°	252.6	254.4	257.7	260.5	261.9	264.2	266.9	269.8	272.4	274.7	276.6
170°	253.4	254.9	257.3	259.8	260.7	262.2	264.2	266.7	268.1	270.1	271.0
172.5°	254.2	255.2	256.9	258.6	259.2	259.8	261.4	263.1	264.2	265.7	266.3
175°	254.9	255.3	256.3	257.3	256.8	257.3	257.8	259.2	259.8	260.3	260.7
177.5°	255.3	255.3	255.7	256.5	255.7	255.3	255.7	256.5	256.5	256.9	256.9
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	4.8	4.6	4.6	4.5	4.6	4.6	4.8	4.8	4.7	4.8	5.0
90°	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2	15.7	14.7	15.7
92.5°	29.2	27.6	28.0	27.2	28.0	27.6	29.2	29.5	32.6	36.8	42.8
95°	60.9	57.0	55.4	56.0	55.4	57.0	60.9	67.2	78.1	98.7	128.6
97.5°	133.5	121.5	114.3	110.2	114.3	121.5	133.5	157.0	192.5	245.6	300.2
100°	220.0	198.9	184.6	175.8	184.6	198.9	220.0	260.7	320.1	387.4	448.3
102.5°	375.1	339.1	321.3	309.4	321.3	339.1	375.1	419.4	482.4	531.6	545.4
105°	611.8	581.3	560.3	553.4	560.3	581.3	611.8	642.2	658.5	652.0	596.6
107.5°	721.9	720.2	716.0	706.9	716.0	720.2	721.9	718.1	694.3	643.3	559.6
110°	739.9	749.3	753.7	753.2	753.7	749.3	739.9	718.8	678.6	615.7	527.9



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	725.8	741.4	749.8	752.4	749.8	741.4	725.8	696.5	650.3	583.2	498.8
115°	688.4	711.0	723.8	728.1	723.8	711.0	688.4	653.6	603.0	538.6	463.0
117.5°	643.9	667.7	681.1	684.8	681.1	667.7	643.9	608.3	560.9	502.5	436.1
120°	614.8	637.8	652.0	656.9	652.0	637.8	614.8	580.4	535.7	483.6	422.8
122.5°	588.4	611.1	623.8	627.9	623.8	611.1	588.4	557.6	517.2	468.0	412.2
125°	555.9	574.5	586.8	590.7	586.8	574.5	555.9	527.4	490.5	447.3	396.7
127.5°	526.8	544.3	554.9	558.1	554.9	544.3	526.8	502.0	468.0	427.3	381.5
130°	509.2	525.9	535.7	539.6	535.7	525.9	509.2	485.1	452.7	414.0	371.7
132.5°	491.1	507.8	516.9	520.4	516.9	507.8	491.1	467.4	437.0	401.4	362.3
135°	462.5	478.7	487.6	489.6	487.6	478.7	462.5	441.4	414.0	381.5	349.1
137.5°	434.6	448.6	456.3	459.3	456.3	448.6	434.6	415.4	391.4	365.8	338.6
140°	415.4	428.2	435.5	438.5	435.5	428.2	415.4	399.7	378.1	355.5	331.9
142.5°	398.9	410.5	417.1	417.7	417.1	410.5	398.9	384.0	365.9	346.5	326.4
145°	376.1	384.4	389.3	390.8	389.3	384.4	376.1	364.4	350.1	334.8	318.7
147.5°	357.5	364.1	367.5	368.3	367.5	364.1	357.5	347.8	337.3	325.5	312.7
150°	345.7	351.5	354.5	355.0	354.5	351.5	345.7	338.3	329.5	319.2	308.3
152.5°	336.2	341.4	343.5	343.6	343.5	341.4	336.2	330.5	322.8	314.1	304.0
155°	324.1	327.5	329.5	328.5	329.5	327.5	324.1	318.7	313.2	305.9	298.1
157.5°	311.9	314.8	315.6	315.6	315.6	314.8	311.9	308.1	303.8	297.6	291.1
160°	304.4	306.9	307.4	307.4	307.4	306.9	304.4	301.0	297.6	292.1	286.7
162.5°	297.7	299.5	299.9	299.5	299.9	299.5	297.7	294.3	291.7	287.1	282.4
165°	286.7	288.7	288.7	288.3	288.7	288.7	286.7	284.8	282.8	279.4	276.0
167.5°	277.4	278.5	278.4	277.8	278.4	278.5	277.4	276.6	274.7	272.4	269.8
170°	271.6	273.0	272.5	271.6	272.5	273.0	271.6	271.0	270.1	268.1	266.7
172.5°	266.8	267.5	267.0	266.4	267.0	267.5	266.8	266.3	265.7	264.2	263.1
175°	260.7	261.2	260.7	259.8	260.7	261.2	260.7	260.7	260.3	259.8	259.2
177.5°	256.9	256.9	256.5	255.7	256.5	256.9	256.9	256.9	256.9	256.5	256.5
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	5.1	5.3	5.4	5.0	4.3	4.0	3.9	3.8	3.9	3.7	3.5
90°	16.2	16.7	16.2	13.3	9.8	7.4	5.9	4.9	4.0	2.0	0.5
92.5°	53.9	63.8	62.9	49.0	33.4	22.3	17.7	14.4	12.1	8.6	6.0
95°	168.4	192.5	170.4	113.4	70.7	48.1	36.3	28.5	24.0	19.1	17.2
97.5°	344.7	328.6	247.5	152.8	93.3	64.9	51.6	42.5	35.8	30.7	28.0
100°	458.6	387.9	267.1	161.1	101.2	75.2	61.4	51.6	43.7	39.3	37.8
102.5°	501.0	389.9	259.7	161.4	108.2	84.1	70.4	60.2	52.3	48.0	46.8
105°	494.5	363.9	245.0	164.0	120.3	97.2	83.4	72.7	65.3	61.9	59.9
107.5°	451.3	336.0	237.7	170.7	132.7	110.3	96.4	85.8	79.0	75.6	74.0
110°	424.2	322.6	236.2	176.2	140.9	119.3	105.0	94.8	88.4	85.4	83.4



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	405.4	313.9	236.6	182.2	148.8	127.9	113.3	103.4	97.4	94.1	92.1
115°	382.0	304.4	238.7	191.0	161.1	139.9	126.7	116.8	111.0	108.1	105.6
117.5°	367.3	299.8	242.2	200.4	172.4	152.8	139.1	129.7	124.4	121.5	119.5
120°	359.5	297.0	244.5	206.7	180.2	161.1	147.3	137.5	133.0	130.1	128.1
122.5°	352.8	295.5	247.3	212.2	187.7	169.7	155.6	145.8	140.9	138.0	136.4
125°	343.2	292.7	251.4	220.9	198.9	181.2	167.5	157.6	151.7	148.8	147.3
127.5°	334.4	291.0	255.6	229.1	209.3	192.1	178.0	168.5	162.0	157.9	155.9
130°	328.5	290.2	258.7	234.2	215.6	198.4	184.6	174.8	167.9	163.0	161.1
132.5°	323.7	289.8	261.9	239.4	221.0	204.7	190.9	180.7	173.4	168.2	165.7
135°	317.2	289.2	265.6	246.0	228.9	213.1	199.3	188.0	180.7	174.8	172.8
137.5°	312.5	289.1	269.0	251.1	235.1	219.6	206.8	195.6	187.8	181.8	179.5
140°	309.9	288.7	270.5	253.8	238.7	223.9	211.1	200.4	192.5	186.6	184.6
142.5°	307.1	288.7	271.7	256.2	241.4	227.0	215.1	204.7	196.8	191.3	189.8
145°	303.4	287.7	273.0	259.2	245.5	232.2	221.4	211.6	204.2	199.3	197.4
147.5°	299.7	285.9	273.4	261.0	248.8	236.3	226.8	218.6	211.8	207.1	205.6
150°	296.6	284.8	273.0	261.7	250.4	239.1	230.3	222.9	216.5	212.6	211.1
152.5°	293.9	282.8	272.2	262.1	252.0	241.9	233.8	226.9	221.3	217.3	216.6
155°	288.7	279.4	271.0	262.7	254.3	246.0	238.7	233.2	227.8	224.9	224.4
157.5°	283.9	275.9	268.8	262.7	256.0	248.9	242.8	238.4	233.8	231.4	230.8
160°	280.3	273.5	267.6	262.7	256.8	250.9	245.5	241.6	237.6	235.7	235.2
162.5°	277.2	271.6	266.4	262.3	257.2	252.1	247.9	244.4	241.2	239.2	239.5
165°	272.0	267.6	264.2	261.2	257.8	253.4	250.4	248.0	245.0	244.0	244.5
167.5°	266.9	264.2	261.9	260.5	257.7	254.4	252.6	250.8	248.9	248.1	248.7
170°	264.2	262.2	260.7	259.8	257.3	254.9	253.4	252.4	250.9	250.4	251.4
172.5°	261.4	259.8	259.2	258.6	256.9	255.2	254.2	253.6	252.1	252.4	253.0
175°	257.8	257.3	256.8	257.3	256.3	255.3	254.9	254.9	253.8	254.3	254.9
177.5°	255.7	255.3	255.7	256.5	255.7	255.3	255.3	255.3	254.5	254.9	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.3	5.3	5.5	6.2	6.2	6.6	7.3	7.7	7.7	7.5	7.2
90°	2.0	4.0	4.9	5.9	7.4	9.8	13.3	16.2	16.7	16.2	15.7
92.5°	8.6	12.1	14.4	17.7	22.3	33.4	49.0	62.9	63.8	53.9	42.8
95°	19.1	24.0	28.5	36.3	48.1	70.7	113.4	170.4	192.5	168.4	128.6
97.5°	30.7	35.8	42.5	51.6	64.9	93.3	152.8	247.5	328.6	344.7	300.2
100°	39.3	43.7	51.6	61.4	75.2	101.2	161.1	267.1	387.9	458.6	448.3
102.5°	48.0	52.3	60.2	70.4	84.1	108.2	161.4	259.7	389.9	501.0	545.4
105°	61.9	65.3	72.7	83.4	97.2	120.3	164.0	245.0	363.9	494.5	596.6
107.5°	75.6	79.0	85.8	96.4	110.3	132.7	170.7	237.7	336.0	451.3	559.6
110°	85.4	88.4	94.8	105.0	119.3	140.9	176.2	236.2	322.6	424.2	527.9



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	94.1	97.4	103.4	113.3	127.9	148.8	182.2	236.6	313.9	405.4	498.8
115°	108.1	111.0	116.8	126.7	139.9	161.1	191.0	238.7	304.4	382.0	463.0
117.5°	121.5	124.4	129.7	139.1	152.8	172.4	200.4	242.2	299.8	367.3	436.1
120°	130.1	133.0	137.5	147.3	161.1	180.2	206.7	244.5	297.0	359.5	422.8
122.5°	138.0	140.9	145.8	155.6	169.7	187.7	212.2	247.3	295.5	352.8	412.2
125°	148.8	151.7	157.6	167.5	181.2	198.9	220.9	251.4	292.7	343.2	396.7
127.5°	157.9	162.0	168.5	178.0	192.1	209.3	229.1	255.6	291.0	334.4	381.5
130°	163.0	167.9	174.8	184.6	198.4	215.6	234.2	258.7	290.2	328.5	371.7
132.5°	168.2	173.4	180.7	190.9	204.7	221.0	239.4	261.9	289.8	323.7	362.3
135°	174.8	180.7	188.0	199.3	213.1	228.9	246.0	265.6	289.2	317.2	349.1
137.5°	181.8	187.8	195.6	206.8	219.6	235.1	251.1	269.0	289.1	312.5	338.6
140°	186.6	192.5	200.4	211.1	223.9	238.7	253.8	270.5	288.7	309.9	331.9
142.5°	191.3	196.8	204.7	215.1	227.0	241.4	256.2	271.7	288.7	307.1	326.4
145°	199.3	204.2	211.6	221.4	232.2	245.5	259.2	273.0	287.7	303.4	318.7
147.5°	207.1	211.8	218.6	226.8	236.3	248.8	261.0	273.4	285.9	299.7	312.7
150°	212.6	216.5	222.9	230.3	239.1	250.4	261.7	273.0	284.8	296.6	308.3
152.5°	217.3	221.3	226.9	233.8	241.9	252.0	262.1	272.2	282.8	293.9	304.0
155°	224.9	227.8	233.2	238.7	246.0	254.3	262.7	271.0	279.4	288.7	298.1
157.5°	231.4	233.8	238.4	242.8	248.9	256.0	262.7	268.8	275.9	283.9	291.1
160°	235.7	237.6	241.6	245.5	250.9	256.8	262.7	267.6	273.5	280.3	286.7
162.5°	239.2	241.2	244.4	247.9	252.1	257.2	262.3	266.4	271.6	277.2	282.4
165°	244.0	245.0	248.0	250.4	253.4	257.8	261.2	264.2	267.6	272.0	276.0
167.5°	248.1	248.9	250.8	252.6	254.4	257.7	260.5	261.9	264.2	266.9	269.8
170°	250.4	250.9	252.4	253.4	254.9	257.3	259.8	260.7	262.2	264.2	266.7
172.5°	252.4	252.1	253.6	254.2	255.2	256.9	258.6	259.2	259.8	261.4	263.1
175°	254.3	253.8	254.9	254.9	255.3	256.3	257.3	256.8	257.3	257.8	259.2
177.5°	254.9	254.5	255.3	255.3	255.3	255.7	256.5	255.7	255.3	255.7	256.5
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	7.1	7.4	7.3	7.3	7.5	7.3	7.3
90°	14.7	15.7	16.2	16.2	16.2	16.2	16.2
92.5°	36.8	32.6	29.5	29.2	27.6	28.0	27.2
95°	98.7	78.1	67.2	60.9	57.0	55.4	56.0
97.5°	245.6	192.5	157.0	133.5	121.5	114.3	110.2
100°	387.4	320.1	260.7	220.0	198.9	184.6	175.8
102.5°	531.6	482.4	419.4	375.1	339.1	321.3	309.4
105°	652.0	658.5	642.2	611.8	581.3	560.3	553.4
107.5°	643.3	694.3	718.1	721.9	720.2	716.0	706.9
110°	615.7	678.6	718.8	739.9	749.3	753.7	753.2



TEST NUMBER: P331251-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	583.2	650.3	696.5	725.8	741.4	749.8	752.4
115°	538.6	603.0	653.6	688.4	711.0	723.8	728.1
117.5°	502.5	560.9	608.3	643.9	667.7	681.1	684.8
120°	483.6	535.7	580.4	614.8	637.8	652.0	656.9
122.5°	468.0	517.2	557.6	588.4	611.1	623.8	627.9
125°	447.3	490.5	527.4	555.9	574.5	586.8	590.7
127.5°	427.3	468.0	502.0	526.8	544.3	554.9	558.1
130°	414.0	452.7	485.1	509.2	525.9	535.7	539.6
132.5°	401.4	437.0	467.4	491.1	507.8	516.9	520.4
135°	381.5	414.0	441.4	462.5	478.7	487.6	489.6
137.5°	365.8	391.4	415.4	434.6	448.6	456.3	459.3
140°	355.5	378.1	399.7	415.4	428.2	435.5	438.5
142.5°	346.5	365.9	384.0	398.9	410.5	417.1	417.7
145°	334.8	350.1	364.4	376.1	384.4	389.3	390.8
147.5°	325.5	337.3	347.8	357.5	364.1	367.5	368.3
150°	319.2	329.5	338.3	345.7	351.5	354.5	355.0
152.5°	314.1	322.8	330.5	336.2	341.4	343.5	343.6
155°	305.9	313.2	318.7	324.1	327.5	329.5	328.5
157.5°	297.6	303.8	308.1	311.9	314.8	315.6	315.6
160°	292.1	297.6	301.0	304.4	306.9	307.4	307.4
162.5°	287.1	291.7	294.3	297.7	299.5	299.9	299.5
165°	279.4	282.8	284.8	286.7	288.7	288.7	288.3
167.5°	272.4	274.7	276.6	277.4	278.5	278.4	277.8
170°	268.1	270.1	271.0	271.6	273.0	272.5	271.6
172.5°	264.2	265.7	266.3	266.8	267.5	267.0	266.4
175°	259.8	260.3	260.7	260.7	261.2	260.7	259.8
177.5°	256.5	256.9	256.9	256.9	256.9	256.5	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3

(END OF REPORT)