

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331257-935

Luminaire Tested: **S122DIP-S290D530U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331257-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S290D530U935-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2813.9 lumens  
Efficiency: N/A  
Efficacy: 109.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331257-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331257-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		59	59	59		44	44	44	37
1	95	91	87	83	86	82	79	76	67	64	62		52	51	49		39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52		46	43	41		34	33	31	26
3	79	69	62	57	71	63	57	52	51	47	43		40	37	35		30	28	27	22
4	72	61	54	48	65	56	49	44	46	41	37		36	33	30		27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32		32	29	26		24	22	20	16
6	61	49	41	35	55	45	38	33	37	31	28		29	25	22		22	20	18	14
7	56	44	36	31	51	40	33	29	33	28	24		26	23	20		20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21		24	20	18		19	16	14	11
9	48	36	29	24	44	33	27	22	28	23	19		22	18	16		17	14	13	10
10	45	33	26	22	41	31	24	20	25	20	17		20	17	14		16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6567	6567	6567
5°	6592	6498	6536
10°	6555	6432	6465
15°	6472	6349	6342
20°	6357	6223	6216
25°	6242	6070	6070
30°	6096	5929	5876
35°	5960	5757	5673
40°	5788	5590	5482
45°	5617	5421	5286
50°	5433	5247	5061
55°	5239	5044	4856
60°	5028	4799	4624
65°	4795	4558	4348
70°	4504	4263	4060
75°	4099	3924	3830
80°	3636	3533	3347
85°	2964	2816	2538



TEST NUMBER: P331257-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.3	1.4
10°-20°	107.6	3.8
20°-30°	158.2	5.6
30°-40°	183.8	6.5
40°-50°	183.6	6.5
50°-60°	160.1	5.7
60°-70°	118.4	4.2
70°-80°	67.0	2.4
80°-90°	20.3	0.7
90°-100°	102.1	3.6
100°-110°	346.4	12.3
110°-120°	368.0	13.1
120°-130°	303.0	10.8
130°-140°	243.3	8.6
140°-150°	183.9	6.5
150°-160°	129.2	4.6
160°-170°	76.1	2.7
170°-180°	24.8	0.9
0°-30°	304.1	10.8
0°-40°	487.8	17.3
0°-60°	831.5	29.5
0°-90°	1037.2	36.9
90°-120°	816.6	29.0
90°-150°	1546.7	55.0
90°-180°	1777.0	63.2
0°-180°	2813.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	407	407	407	407	407	
5°	407	405	401	404	403	39
15°	387	385	380	381	379	109
25°	350	347	341	341	341	161
35°	302	298	292	290	288	189
45°	246	243	237	233	232	190
55°	186	184	179	175	172	166
65°	126	123	119	116	114	124
75°	66	65	63	61	61	70
85°	16	16	15	14	14	18
90°	0	7	17	16	16	2
95°	17	42	192	73	56	18
105°	60	90	364	650	553	64
115°	106	133	304	628	728	105
125°	147	174	293	509	591	131
135°	173	206	289	428	490	133
145°	197	227	288	357	391	124
155°	224	242	279	316	328	103
165°	244	252	268	284	288	69
175°	255	255	257	260	260	24
180°	255	255	255	255	255	



TEST NUMBER: P331257-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	408.6	408.3	407.9	407.6	407.3	406.7	406.0	405.2	404.4	403.6	404.3
5°	406.7	406.4	406.0	405.7	405.4	404.8	403.8	402.9	401.8	400.9	401.6
7.5°	403.2	402.6	402.1	401.6	401.1	400.3	399.3	398.3	397.4	396.4	397.1
10°	399.8	399.2	398.6	398.0	397.3	396.5	395.5	394.4	393.4	392.3	393.0
12.5°	395.0	394.5	394.0	393.4	392.9	392.1	391.1	390.0	389.0	388.0	388.4
15°	387.2	386.7	386.2	385.6	385.1	384.4	383.1	382.0	380.9	379.8	380.1
17.5°	377.2	376.7	376.2	375.7	375.1	374.3	373.2	372.0	370.8	369.7	370.1
20°	370.0	369.5	368.9	368.4	367.9	367.0	365.8	364.6	363.4	362.2	362.5
22.5°	362.8	362.1	361.4	360.6	359.9	359.0	357.8	356.6	355.5	354.4	354.4
25°	350.4	349.7	349.0	348.4	347.7	346.6	345.1	343.6	342.2	340.7	340.9
27.5°	336.4	335.8	335.1	334.5	333.9	332.9	331.8	330.6	329.5	328.3	328.0
30°	327.0	326.3	325.6	324.9	324.2	323.2	321.9	320.6	319.3	318.0	317.7
32.5°	316.9	316.4	315.9	315.3	314.8	313.7	312.4	311.1	309.7	308.3	307.8
35°	302.4	301.4	300.6	299.7	298.9	297.7	296.4	295.0	293.6	292.1	291.6
37.5°	285.9	285.1	284.3	283.5	282.8	281.7	280.3	279.0	277.5	276.1	275.5
40°	274.6	273.9	273.2	272.5	271.8	270.8	269.3	267.9	266.6	265.2	264.4
42.5°	263.6	262.9	262.3	261.6	260.9	259.8	258.4	257.0	255.6	254.3	253.4
45°	246.0	245.4	244.8	244.2	243.6	242.6	241.3	240.0	238.8	237.4	236.4
47.5°	228.5	227.9	227.4	226.8	226.2	225.2	223.9	222.6	221.2	219.8	218.8
50°	216.3	215.9	215.4	215.0	214.6	213.7	212.5	211.3	210.1	208.9	207.7
52.5°	204.4	203.8	203.3	202.7	202.1	201.2	200.1	199.0	197.8	196.7	195.6
55°	186.1	185.6	185.1	184.6	184.1	183.3	182.3	181.2	180.2	179.2	178.1
57.5°	167.9	167.5	167.0	166.6	166.2	165.4	164.3	163.2	162.0	160.8	159.8
60°	155.7	155.3	155.0	154.6	154.3	153.5	152.3	151.1	149.8	148.6	147.7
62.5°	143.8	143.2	142.7	142.2	141.5	140.8	139.8	139.0	138.0	137.1	136.1
65°	125.5	125.0	124.5	124.0	123.5	122.8	121.9	121.1	120.2	119.3	118.5
67.5°	107.0	106.6	106.2	105.7	105.4	104.8	103.9	103.1	102.4	101.6	101.0
70°	95.4	95.1	94.7	94.4	94.0	93.5	92.7	92.0	91.1	90.3	89.7
72.5°	83.5	83.2	82.8	82.5	82.1	81.7	81.2	80.8	80.2	79.7	79.1
75°	65.7	65.5	65.3	65.2	65.0	64.7	64.3	63.8	63.4	62.9	62.4
77.5°	49.8	49.4	49.2	48.9	48.6	48.3	48.1	48.0	47.8	47.6	47.4
80°	39.1	39.0	38.9	38.8	38.7	38.7	38.5	38.3	38.1	38.0	37.7
82.5°	29.1	29.1	29.1	29.0	29.0	28.9	28.8	28.8	28.7	28.6	28.2
85°	16.0	15.9	15.8	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.0
87.5°	5.8	5.9	6.1	6.2	6.3	6.4	6.8	7.3	7.7	7.7	7.4
90°	0.5	2.0	4.0	4.9	5.9	7.4	9.8	13.3	16.2	16.7	16.2
92.5°	6.0	8.6	12.1	14.4	17.7	22.3	33.4	49.0	62.9	63.8	53.9
95°	17.2	19.1	24.0	28.5	36.3	48.1	70.7	113.4	170.4	192.5	168.4
97.5°	28.0	30.7	35.8	42.5	51.6	64.9	93.3	152.8	247.5	328.6	344.7
100°	37.8	39.3	43.7	51.6	61.4	75.2	101.2	161.1	267.1	387.9	458.6
102.5°	46.8	48.0	52.3	60.2	70.4	84.1	108.2	161.4	259.7	389.9	501.0
105°	59.9	61.9	65.3	72.7	83.4	97.2	120.3	164.0	245.0	363.9	494.5
107.5°	74.0	75.6	79.0	85.8	96.4	110.3	132.7	170.7	237.7	336.0	451.3
110°	83.4	85.4	88.4	94.8	105.0	119.3	140.9	176.2	236.2	322.6	424.2



TEST NUMBER: P331257-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	92.1	94.1	97.4	103.4	113.3	127.9	148.8	182.2	236.6	313.9	405.4
115°	105.6	108.1	111.0	116.8	126.7	139.9	161.1	191.0	238.7	304.4	382.0
117.5°	119.5	121.5	124.4	129.7	139.1	152.8	172.4	200.4	242.2	299.8	367.3
120°	128.1	130.1	133.0	137.5	147.3	161.1	180.2	206.7	244.5	297.0	359.5
122.5°	136.4	138.0	140.9	145.8	155.6	169.7	187.7	212.2	247.3	295.5	352.8
125°	147.3	148.8	151.7	157.6	167.5	181.2	198.9	220.9	251.4	292.7	343.2
127.5°	155.9	157.9	162.0	168.5	178.0	192.1	209.3	229.1	255.6	291.0	334.4
130°	161.1	163.0	167.9	174.8	184.6	198.4	215.6	234.2	258.7	290.2	328.5
132.5°	165.7	168.2	173.4	180.7	190.9	204.7	221.0	239.4	261.9	289.8	323.7
135°	172.8	174.8	180.7	188.0	199.3	213.1	228.9	246.0	265.6	289.2	317.2
137.5°	179.5	181.8	187.8	195.6	206.8	219.6	235.1	251.1	269.0	289.1	312.5
140°	184.6	186.6	192.5	200.4	211.1	223.9	238.7	253.8	270.5	288.7	309.9
142.5°	189.8	191.3	196.8	204.7	215.1	227.0	241.4	256.2	271.7	288.7	307.1
145°	197.4	199.3	204.2	211.6	221.4	232.2	245.5	259.2	273.0	287.7	303.4
147.5°	205.6	207.1	211.8	218.6	226.8	236.3	248.8	261.0	273.4	285.9	299.7
150°	211.1	212.6	216.5	222.9	230.3	239.1	250.4	261.7	273.0	284.8	296.6
152.5°	216.6	217.3	221.3	226.9	233.8	241.9	252.0	262.1	272.2	282.8	293.9
155°	224.4	224.9	227.8	233.2	238.7	246.0	254.3	262.7	271.0	279.4	288.7
157.5°	230.8	231.4	233.8	238.4	242.8	248.9	256.0	262.7	268.8	275.9	283.9
160°	235.2	235.7	237.6	241.6	245.5	250.9	256.8	262.7	267.6	273.5	280.3
162.5°	239.5	239.2	241.2	244.4	247.9	252.1	257.2	262.3	266.4	271.6	277.2
165°	244.5	244.0	245.0	248.0	250.4	253.4	257.8	261.2	264.2	267.6	272.0
167.5°	248.7	248.1	248.9	250.8	252.6	254.4	257.7	260.5	261.9	264.2	266.9
170°	251.4	250.4	250.9	252.4	253.4	254.9	257.3	259.8	260.7	262.2	264.2
172.5°	253.0	252.4	252.1	253.6	254.2	255.2	256.9	258.6	259.2	259.8	261.4
175°	254.9	254.3	253.8	254.9	254.9	255.3	256.3	257.3	256.8	257.3	257.8
177.5°	255.7	254.9	254.5	255.3	255.3	255.3	255.7	256.5	255.7	255.3	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331257-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	405.0	405.7	406.4	406.7	406.6	406.4	406.3	406.1
5°	402.3	403.0	403.7	404.0	403.8	403.6	403.5	403.3
7.5°	397.8	398.5	399.2	399.4	399.2	399.0	398.8	398.6
10°	393.7	394.4	395.1	395.3	395.0	394.8	394.5	394.3
12.5°	388.9	389.3	389.9	390.0	389.9	389.6	389.4	389.3
15°	380.5	380.8	381.2	381.2	380.7	380.3	379.9	379.4
17.5°	370.5	370.9	371.3	371.3	370.8	370.5	370.1	369.6
20°	362.7	363.0	363.3	363.2	362.8	362.5	362.1	361.8
22.5°	354.5	354.6	354.6	354.5	354.3	354.0	353.9	353.7
25°	341.0	341.2	341.4	341.4	341.2	341.0	340.9	340.7
27.5°	327.8	327.5	327.3	326.9	326.5	326.1	325.7	325.3
30°	317.5	317.2	316.9	316.7	316.3	316.0	315.6	315.2
32.5°	307.4	306.9	306.4	306.0	305.7	305.3	305.0	304.6
35°	291.1	290.6	290.1	289.6	289.2	288.8	288.3	287.8
37.5°	274.8	274.2	273.5	273.0	272.6	272.2	271.8	271.4
40°	263.6	262.9	262.1	261.5	261.1	260.8	260.5	260.1
42.5°	252.5	251.7	250.8	250.1	249.7	249.2	248.7	248.2
45°	235.5	234.5	233.6	232.9	232.6	232.2	231.9	231.5
47.5°	217.8	216.8	215.8	215.0	214.6	214.0	213.5	213.0
50°	206.5	205.2	204.0	203.2	202.8	202.3	201.9	201.5
52.5°	194.7	193.6	192.6	191.8	191.2	190.7	190.1	189.5
55°	177.0	176.0	175.0	174.3	173.8	173.3	172.9	172.5
57.5°	158.8	157.7	156.7	156.0	155.8	155.4	155.1	154.7
60°	146.7	145.8	144.8	144.2	144.0	143.7	143.4	143.2
62.5°	135.3	134.4	133.5	132.9	132.6	132.2	131.9	131.6
65°	117.7	116.9	116.1	115.5	115.1	114.7	114.3	113.8
67.5°	100.4	99.8	99.2	98.7	98.3	98.0	97.6	97.3
70°	89.1	88.5	87.9	87.5	87.1	86.7	86.4	86.0
72.5°	78.5	77.9	77.3	76.8	76.5	76.3	76.0	75.7
75°	61.9	61.4	60.9	60.7	60.9	61.0	61.2	61.4
77.5°	47.1	46.8	46.6	46.3	46.1	45.9	45.6	45.4
80°	37.5	37.2	36.9	36.7	36.5	36.3	36.2	36.0
82.5°	27.9	27.6	27.2	27.0	27.0	26.9	26.9	26.9
85°	14.7	14.5	14.2	14.0	13.9	13.9	13.8	13.7
87.5°	7.1	6.7	6.7	6.6	6.5	6.5	6.5	6.4
90°	15.7	14.7	15.7	16.2	16.2	16.2	16.2	16.2
92.5°	42.8	36.8	32.6	29.5	29.2	27.6	28.0	27.2
95°	128.6	98.7	78.1	67.2	60.9	57.0	55.4	56.0
97.5°	300.2	245.6	192.5	157.0	133.5	121.5	114.3	110.2
100°	448.3	387.4	320.1	260.7	220.0	198.9	184.6	175.8
102.5°	545.4	531.6	482.4	419.4	375.1	339.1	321.3	309.4
105°	596.6	652.0	658.5	642.2	611.8	581.3	560.3	553.4
107.5°	559.6	643.3	694.3	718.1	721.9	720.2	716.0	706.9
110°	527.9	615.7	678.6	718.8	739.9	749.3	753.7	753.2





TEST NUMBER: P331257-935

CATALOG NUMBER: S122DIP-S290D530U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	498.8	583.2	650.3	696.5	725.8	741.4	749.8	752.4
115°	463.0	538.6	603.0	653.6	688.4	711.0	723.8	728.1
117.5°	436.1	502.5	560.9	608.3	643.9	667.7	681.1	684.8
120°	422.8	483.6	535.7	580.4	614.8	637.8	652.0	656.9
122.5°	412.2	468.0	517.2	557.6	588.4	611.1	623.8	627.9
125°	396.7	447.3	490.5	527.4	555.9	574.5	586.8	590.7
127.5°	381.5	427.3	468.0	502.0	526.8	544.3	554.9	558.1
130°	371.7	414.0	452.7	485.1	509.2	525.9	535.7	539.6
132.5°	362.3	401.4	437.0	467.4	491.1	507.8	516.9	520.4
135°	349.1	381.5	414.0	441.4	462.5	478.7	487.6	489.6
137.5°	338.6	365.8	391.4	415.4	434.6	448.6	456.3	459.3
140°	331.9	355.5	378.1	399.7	415.4	428.2	435.5	438.5
142.5°	326.4	346.5	365.9	384.0	398.9	410.5	417.1	417.7
145°	318.7	334.8	350.1	364.4	376.1	384.4	389.3	390.8
147.5°	312.7	325.5	337.3	347.8	357.5	364.1	367.5	368.3
150°	308.3	319.2	329.5	338.3	345.7	351.5	354.5	355.0
152.5°	304.0	314.1	322.8	330.5	336.2	341.4	343.5	343.6
155°	298.1	305.9	313.2	318.7	324.1	327.5	329.5	328.5
157.5°	291.1	297.6	303.8	308.1	311.9	314.8	315.6	315.6
160°	286.7	292.1	297.6	301.0	304.4	306.9	307.4	307.4
162.5°	282.4	287.1	291.7	294.3	297.7	299.5	299.9	299.5
165°	276.0	279.4	282.8	284.8	286.7	288.7	288.7	288.3
167.5°	269.8	272.4	274.7	276.6	277.4	278.5	278.4	277.8
170°	266.7	268.1	270.1	271.0	271.6	273.0	272.5	271.6
172.5°	263.1	264.2	265.7	266.3	266.8	267.5	267.0	266.4
175°	259.2	259.8	260.3	260.7	260.7	261.2	260.7	259.8
177.5°	256.5	256.5	256.9	256.9	256.9	256.9	256.5	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3

(END OF REPORT)