

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331296-935

Luminaire Tested: **S122DIP-S485D530U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331296-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D530U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3624.9 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	53	50	46	44	42	38
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	42	37	40	36	33	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	31	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	23	28	24	21	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13508	13508	13508	13508
5°	15144	13598	12049	13598
10°	17354	13485	10427	13485
15°	19199	13237	9212	13237
20°	18907	12972	8399	12972
25°	17047	12618	7883	12618
30°	14087	12055	7506	12055
35°	10267	11466	7238	11466
40°	8201	10768	7088	10768
45°	7165	9965	6887	9965
50°	6737	9183	6752	9183
55°	6210	8391	6570	8391
60°	5690	7550	6290	7550
65°	5184	6793	6021	6793
70°	4707	6057	5618	6057
75°	4173	5234	4972	5234
80°	3589	4342	3998	4342
85°	3223	3223	2371	3223



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	2.2
10°-20°	231.6	6.4
20°-30°	336.2	9.3
30°-40°	354.8	9.8
40°-50°	314.1	8.7
50°-60°	250.7	6.9
60°-70°	170.4	4.7
70°-80°	87.4	2.4
80°-90°	23.4	0.6
90°-100°	102.1	2.8
100°-110°	346.4	9.6
110°-120°	368.0	10.2
120°-130°	303.0	8.4
130°-140°	243.3	6.7
140°-150°	183.9	5.1
150°-160°	129.2	3.6
160°-170°	76.1	2.1
170°-180°	24.8	0.7
0°-30°	647.5	17.9
0°-40°	1002.3	27.6
0°-60°	1567.1	43.2
0°-90°	1848.2	51.0
90°-120°	816.6	22.5
90°-150°	1546.7	42.7
90°-180°	1777.0	49.0
0°-180°	3624.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	837	837	837	837	837	
5°	934	839	743	839	934	93
15°	1149	792	551	792	1149	317
25°	957	708	442	708	957	432
35°	521	582	367	582	521	339
45°	314	436	302	436	314	247
55°	221	298	233	298	221	198
65°	136	178	158	178	136	135
75°	67	84	80	84	67	71
85°	17	17	13	17	17	19
90°	16	0	16	0	16	10
95°	56	17	56	17	56	73
105°	553	60	553	60	553	535
115°	728	106	728	106	728	713
125°	591	147	591	147	591	534
135°	490	173	490	173	490	380
145°	391	197	391	197	391	248
155°	328	224	328	224	328	153
165°	288	244	288	244	288	82
175°	260	255	260	255	260	25
180°	255	255	255	255	255	



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	875.3	875.6	876.0	871.9	871.4	871.4	867.8	864.7	861.1	856.2	856.7
5°	934.4	938.0	939.3	935.4	929.6	928.9	923.5	914.5	906.1	899.4	894.6
7.5°	1005.0	1006.4	1003.3	998.2	993.9	986.2	976.0	966.0	952.1	939.3	929.8
10°	1058.5	1060.5	1055.0	1047.6	1041.5	1032.5	1017.7	1002.5	984.3	966.6	952.4
12.5°	1099.2	1104.0	1096.9	1096.0	1085.5	1073.2	1055.5	1047.8	1022.1	997.5	982.2
15°	1148.6	1148.2	1148.9	1142.8	1135.1	1133.2	1114.5	1094.2	1057.9	1043.4	1018.3
17.5°	1134.3	1139.2	1141.4	1141.3	1141.2	1140.0	1133.9	1121.2	1102.9	1079.5	1050.6
20°	1100.4	1106.7	1107.8	1115.2	1119.3	1124.8	1127.0	1123.5	1112.2	1092.6	1067.6
22.5°	1047.8	1049.6	1052.7	1064.2	1073.2	1086.9	1094.1	1106.0	1101.6	1092.1	1071.2
25°	956.9	953.7	964.9	970.8	991.6	1013.5	1029.2	1046.6	1062.0	1071.4	1065.3
27.5°	847.7	842.9	859.8	875.1	892.1	915.8	940.3	969.3	993.4	1023.6	1034.0
30°	755.6	758.5	774.6	791.0	816.7	850.2	877.8	909.6	944.1	977.8	1001.3
32.5°	656.3	667.4	677.6	702.7	725.4	762.7	803.2	843.0	886.0	924.3	960.6
35°	520.9	533.7	547.9	566.3	598.1	635.1	674.6	728.3	786.9	839.2	882.4
37.5°	438.4	436.4	444.5	457.8	483.5	513.4	558.9	612.0	680.9	742.4	803.2
40°	389.1	387.8	393.6	405.8	425.4	447.3	487.2	533.7	597.8	673.0	745.4
42.5°	355.1	355.9	359.1	367.7	381.2	399.2	429.0	468.7	527.3	598.1	675.9
45°	313.8	316.1	319.6	323.8	331.5	346.3	363.0	391.3	437.6	496.8	573.3
47.5°	284.1	284.2	287.7	291.4	296.0	304.4	318.1	335.8	368.4	416.6	482.4
50°	268.2	265.9	268.5	271.4	276.2	282.0	291.0	307.7	329.6	368.5	423.4
52.5°	248.7	248.7	251.0	252.1	256.4	262.2	270.4	282.0	301.8	332.3	377.5
55°	220.6	222.2	223.5	225.4	229.3	233.4	239.9	247.6	263.0	285.9	319.3
57.5°	194.2	194.8	196.0	199.7	202.2	206.0	212.1	219.1	229.1	246.1	271.2
60°	176.2	176.2	178.7	180.4	183.6	187.4	192.3	199.1	208.0	221.9	242.1
62.5°	159.7	159.5	160.5	163.2	165.6	169.2	174.0	179.8	188.2	200.5	217.1
65°	135.7	135.1	137.0	137.6	140.2	143.7	147.6	153.7	160.5	169.4	184.3
67.5°	112.5	113.3	114.3	115.5	117.0	120.7	123.3	127.6	133.3	140.8	150.8
70°	99.7	99.7	99.7	100.7	102.5	104.5	107.1	110.6	116.1	122.5	131.5
72.5°	85.2	86.3	87.3	86.8	89.2	90.3	93.4	95.4	100.7	104.8	112.7
75°	66.9	66.9	66.9	68.4	69.5	70.4	72.3	74.3	76.9	82.0	86.2
77.5°	49.9	49.8	50.1	50.5	51.5	52.7	53.2	55.0	57.3	59.8	63.3
80°	38.6	39.3	39.5	40.2	40.2	40.8	41.2	43.4	45.0	46.7	48.9
82.5°	29.9	30.0	30.0	30.1	30.4	30.8	31.6	32.4	32.9	34.3	36.0
85°	17.4	17.0	17.0	17.7	17.4	17.4	18.0	18.7	18.7	18.9	20.0
87.5°	9.9	9.9	10.2	9.9	9.9	10.1	9.9	9.8	10.2	10.5	10.7
90°	16.2	16.2	16.2	16.2	16.2	15.7	14.7	15.7	16.2	16.7	16.2
92.5°	27.2	28.0	27.6	29.2	29.5	32.6	36.8	42.8	53.9	63.8	62.9
95°	56.0	55.4	57.0	60.9	67.2	78.1	98.7	128.6	168.4	192.5	170.4
97.5°	110.2	114.3	121.5	133.5	157.0	192.5	245.6	300.2	344.7	328.6	247.5
100°	175.8	184.6	198.9	220.0	260.7	320.1	387.4	448.3	458.6	387.9	267.1
102.5°	309.4	321.3	339.1	375.1	419.4	482.4	531.6	545.4	501.0	389.9	259.7
105°	553.4	560.3	581.3	611.8	642.2	658.5	652.0	596.6	494.5	363.9	245.0
107.5°	706.9	716.0	720.2	721.9	718.1	694.3	643.3	559.6	451.3	336.0	237.7
110°	753.2	753.7	749.3	739.9	718.8	678.6	615.7	527.9	424.2	322.6	236.2



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	752.4	749.8	741.4	725.8	696.5	650.3	583.2	498.8	405.4	313.9	236.6
115°	728.1	723.8	711.0	688.4	653.6	603.0	538.6	463.0	382.0	304.4	238.7
117.5°	684.8	681.1	667.7	643.9	608.3	560.9	502.5	436.1	367.3	299.8	242.2
120°	656.9	652.0	637.8	614.8	580.4	535.7	483.6	422.8	359.5	297.0	244.5
122.5°	627.9	623.8	611.1	588.4	557.6	517.2	468.0	412.2	352.8	295.5	247.3
125°	590.7	586.8	574.5	555.9	527.4	490.5	447.3	396.7	343.2	292.7	251.4
127.5°	558.1	554.9	544.3	526.8	502.0	468.0	427.3	381.5	334.4	291.0	255.6
130°	539.6	535.7	525.9	509.2	485.1	452.7	414.0	371.7	328.5	290.2	258.7
132.5°	520.4	516.9	507.8	491.1	467.4	437.0	401.4	362.3	323.7	289.8	261.9
135°	489.6	487.6	478.7	462.5	441.4	414.0	381.5	349.1	317.2	289.2	265.6
137.5°	459.3	456.3	448.6	434.6	415.4	391.4	365.8	338.6	312.5	289.1	269.0
140°	438.5	435.5	428.2	415.4	399.7	378.1	355.5	331.9	309.9	288.7	270.5
142.5°	417.7	417.1	410.5	398.9	384.0	365.9	346.5	326.4	307.1	288.7	271.7
145°	390.8	389.3	384.4	376.1	364.4	350.1	334.8	318.7	303.4	287.7	273.0
147.5°	368.3	367.5	364.1	357.5	347.8	337.3	325.5	312.7	299.7	285.9	273.4
150°	355.0	354.5	351.5	345.7	338.3	329.5	319.2	308.3	296.6	284.8	273.0
152.5°	343.6	343.5	341.4	336.2	330.5	322.8	314.1	304.0	293.9	282.8	272.2
155°	328.5	329.5	327.5	324.1	318.7	313.2	305.9	298.1	288.7	279.4	271.0
157.5°	315.6	315.6	314.8	311.9	308.1	303.8	297.6	291.1	283.9	275.9	268.8
160°	307.4	307.4	306.9	304.4	301.0	297.6	292.1	286.7	280.3	273.5	267.6
162.5°	299.5	299.9	299.5	297.7	294.3	291.7	287.1	282.4	277.2	271.6	266.4
165°	288.3	288.7	288.7	286.7	284.8	282.8	279.4	276.0	272.0	267.6	264.2
167.5°	277.8	278.4	278.5	277.4	276.6	274.7	272.4	269.8	266.9	264.2	261.9
170°	271.6	272.5	273.0	271.6	271.0	270.1	268.1	266.7	264.2	262.2	260.7
172.5°	266.4	267.0	267.5	266.8	266.3	265.7	264.2	263.1	261.4	259.8	259.2
175°	259.8	260.7	261.2	260.7	260.7	260.3	259.8	259.2	257.8	257.3	256.8
177.5°	255.7	256.5	256.9	256.9	256.9	256.9	256.5	256.5	255.7	255.3	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	858.5	856.4	855.1	850.6	846.4	842.3	841.0	841.5	835.9	830.5	828.2
5°	892.0	885.5	879.4	870.7	860.5	849.2	843.4	839.0	827.7	815.5	808.4
7.5°	922.0	912.7	901.0	884.7	869.7	852.0	840.7	830.8	814.2	797.0	786.5
10°	940.2	927.6	912.6	892.6	874.3	852.7	837.7	822.5	803.2	782.6	769.8
12.5°	955.9	939.0	924.1	898.5	876.8	849.9	832.0	810.7	790.4	765.9	753.3
15°	993.2	962.1	933.8	904.8	878.1	840.5	820.6	791.9	765.3	735.0	720.6
17.5°	1022.1	987.1	942.5	905.8	874.6	832.9	803.7	769.4	737.8	703.3	683.6
20°	1038.6	998.4	950.5	906.8	869.4	821.9	790.1	755.0	718.0	679.1	657.9
22.5°	1048.4	1006.2	958.7	902.9	859.2	812.9	772.8	734.4	696.9	655.0	632.7
25°	1051.5	1012.9	962.7	899.7	846.3	793.9	745.6	708.3	663.1	623.8	591.3
27.5°	1036.1	1008.5	960.3	893.6	831.5	770.2	716.4	674.2	626.3	583.8	551.0
30°	1017.4	1001.3	954.3	887.4	819.6	753.7	694.6	646.6	599.1	555.9	522.5
32.5°	988.3	984.8	943.6	878.7	807.0	732.9	671.7	623.2	570.5	528.1	496.3
35°	931.2	946.7	920.6	859.2	783.3	703.3	637.0	581.7	527.0	486.5	456.6
37.5°	854.7	893.0	886.2	830.5	751.2	671.0	597.8	540.0	487.9	447.0	417.7
40°	801.9	850.8	857.9	808.7	728.7	646.0	568.5	510.9	460.1	422.8	393.2
42.5°	745.4	802.5	821.9	782.5	704.0	619.7	542.3	482.7	432.4	396.1	369.9
45°	650.5	726.1	761.1	738.6	662.7	576.5	496.8	436.4	390.7	356.6	336.3
47.5°	561.8	644.4	691.6	683.5	616.8	531.5	452.7	394.7	350.3	323.0	304.9
50°	499.0	583.9	640.8	643.4	583.9	499.4	420.3	365.6	324.8	299.4	284.6
52.5°	444.5	525.6	587.6	601.2	547.2	465.9	391.2	336.8	300.8	277.5	264.2
55°	373.3	441.8	510.7	535.7	492.3	415.1	345.9	298.1	264.3	248.2	236.7
57.5°	310.4	367.5	431.0	458.7	432.0	365.9	301.1	259.5	232.1	218.0	209.1
60°	277.2	322.2	378.8	411.9	388.7	329.9	273.3	233.8	211.3	198.7	190.4
62.5°	246.3	286.2	334.0	364.3	351.7	296.2	245.6	210.6	191.2	179.4	173.4
65°	203.2	234.7	271.7	299.7	291.4	249.2	207.8	177.8	162.4	153.1	148.3
67.5°	167.3	190.1	215.8	240.2	233.5	203.6	170.4	147.1	135.5	127.5	124.7
70°	144.7	162.0	184.9	204.5	199.1	174.6	148.3	128.3	118.3	111.6	108.7
72.5°	123.1	137.3	154.8	170.8	167.1	146.8	124.8	109.8	102.1	95.9	93.5
75°	92.9	103.8	114.5	125.1	124.2	108.4	95.5	83.9	77.8	73.0	72.1
77.5°	68.6	74.7	82.0	88.3	86.5	77.5	67.4	60.8	56.3	53.0	52.5
80°	52.4	56.0	61.1	65.6	63.4	59.5	51.5	46.7	43.4	40.2	38.9
82.5°	38.0	41.6	44.6	47.1	45.4	41.8	36.8	33.5	31.6	29.4	28.8
85°	20.0	21.9	23.2	23.8	23.2	20.9	18.7	17.4	15.8	14.8	14.5
87.5°	10.3	9.6	9.2	9.4	8.4	8.3	6.8	5.8	5.8	5.9	5.6
90°	13.3	9.8	7.4	5.9	4.9	4.0	2.0	0.5	2.0	4.0	4.9
92.5°	49.0	33.4	22.3	17.7	14.4	12.1	8.6	6.0	8.6	12.1	14.4
95°	113.4	70.7	48.1	36.3	28.5	24.0	19.1	17.2	19.1	24.0	28.5
97.5°	152.8	93.3	64.9	51.6	42.5	35.8	30.7	28.0	30.7	35.8	42.5
100°	161.1	101.2	75.2	61.4	51.6	43.7	39.3	37.8	39.3	43.7	51.6
102.5°	161.4	108.2	84.1	70.4	60.2	52.3	48.0	46.8	48.0	52.3	60.2
105°	164.0	120.3	97.2	83.4	72.7	65.3	61.9	59.9	61.9	65.3	72.7
107.5°	170.7	132.7	110.3	96.4	85.8	79.0	75.6	74.0	75.6	79.0	85.8
110°	176.2	140.9	119.3	105.0	94.8	88.4	85.4	83.4	85.4	88.4	94.8



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	182.2	148.8	127.9	113.3	103.4	97.4	94.1	92.1	94.1	97.4	103.4
115°	191.0	161.1	139.9	126.7	116.8	111.0	108.1	105.6	108.1	111.0	116.8
117.5°	200.4	172.4	152.8	139.1	129.7	124.4	121.5	119.5	121.5	124.4	129.7
120°	206.7	180.2	161.1	147.3	137.5	133.0	130.1	128.1	130.1	133.0	137.5
122.5°	212.2	187.7	169.7	155.6	145.8	140.9	138.0	136.4	138.0	140.9	145.8
125°	220.9	198.9	181.2	167.5	157.6	151.7	148.8	147.3	148.8	151.7	157.6
127.5°	229.1	209.3	192.1	178.0	168.5	162.0	157.9	155.9	157.9	162.0	168.5
130°	234.2	215.6	198.4	184.6	174.8	167.9	163.0	161.1	163.0	167.9	174.8
132.5°	239.4	221.0	204.7	190.9	180.7	173.4	168.2	165.7	168.2	173.4	180.7
135°	246.0	228.9	213.1	199.3	188.0	180.7	174.8	172.8	174.8	180.7	188.0
137.5°	251.1	235.1	219.6	206.8	195.6	187.8	181.8	179.5	181.8	187.8	195.6
140°	253.8	238.7	223.9	211.1	200.4	192.5	186.6	184.6	186.6	192.5	200.4
142.5°	256.2	241.4	227.0	215.1	204.7	196.8	191.3	189.8	191.3	196.8	204.7
145°	259.2	245.5	232.2	221.4	211.6	204.2	199.3	197.4	199.3	204.2	211.6
147.5°	261.0	248.8	236.3	226.8	218.6	211.8	207.1	205.6	207.1	211.8	218.6
150°	261.7	250.4	239.1	230.3	222.9	216.5	212.6	211.1	212.6	216.5	222.9
152.5°	262.1	252.0	241.9	233.8	226.9	221.3	217.3	216.6	217.3	221.3	226.9
155°	262.7	254.3	246.0	238.7	233.2	227.8	224.9	224.4	224.9	227.8	233.2
157.5°	262.7	256.0	248.9	242.8	238.4	233.8	231.4	230.8	231.4	233.8	238.4
160°	262.7	256.8	250.9	245.5	241.6	237.6	235.7	235.2	235.7	237.6	241.6
162.5°	262.3	257.2	252.1	247.9	244.4	241.2	239.2	239.5	239.2	241.2	244.4
165°	261.2	257.8	253.4	250.4	248.0	245.0	244.0	244.5	244.0	245.0	248.0
167.5°	260.5	257.7	254.4	252.6	250.8	248.9	248.1	248.7	248.1	248.9	250.8
170°	259.8	257.3	254.9	253.4	252.4	250.9	250.4	251.4	250.4	250.9	252.4
172.5°	258.6	256.9	255.2	254.2	253.6	252.1	252.4	253.0	252.4	252.1	253.6
175°	257.3	256.3	255.3	254.9	254.9	253.8	254.3	254.9	254.3	253.8	254.9
177.5°	256.5	255.7	255.3	255.3	255.3	254.5	254.9	255.7	254.9	254.5	255.3
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	825.6	824.1	818.6	815.8	811.2	806.8	804.0	805.3	806.3	805.8	805.0
5°	801.9	795.8	786.5	778.4	772.7	762.1	757.6	755.4	753.4	751.1	748.9
7.5°	773.8	764.1	750.8	739.3	728.5	715.3	707.8	703.3	698.6	693.5	689.1
10°	753.7	740.2	726.1	710.0	697.2	685.2	674.6	667.5	661.1	655.0	650.5
12.5°	732.6	717.0	699.6	677.6	663.4	646.4	644.8	632.3	622.2	618.5	613.2
15°	699.0	677.2	655.0	629.0	617.7	602.3	592.6	583.0	574.3	568.2	566.5
17.5°	660.9	632.6	610.5	591.9	573.4	557.6	548.7	541.0	533.8	525.6	524.6
20°	631.8	607.4	583.3	566.9	547.9	531.8	520.9	513.2	507.0	502.2	498.1
22.5°	604.3	577.6	555.5	537.5	518.8	505.8	497.2	489.8	484.7	479.4	475.4
25°	560.2	539.2	515.1	494.9	479.4	471.1	464.0	457.5	454.3	450.8	446.3
27.5°	521.5	498.3	475.7	460.0	446.4	439.0	434.0	429.6	426.6	424.6	422.0
30°	494.2	470.7	453.1	437.6	426.4	419.0	415.8	413.2	409.7	408.4	407.1
32.5°	468.0	446.9	431.7	418.4	407.6	402.8	399.8	397.5	394.8	393.5	390.9
35°	430.8	413.2	398.4	391.0	382.3	378.2	375.9	372.6	370.1	368.9	368.5
37.5°	396.0	380.6	370.8	361.4	357.7	355.1	352.1	349.8	349.0	348.9	348.5
40°	373.3	360.8	352.1	344.4	342.8	338.9	336.3	334.4	334.4	334.8	334.4
42.5°	352.8	341.5	333.8	327.2	325.3	323.0	320.4	320.3	320.8	321.8	320.8
45°	321.6	313.5	308.1	304.8	301.3	299.0	298.7	299.7	300.0	300.3	301.3
47.5°	292.8	287.5	282.6	279.1	277.5	277.1	276.7	278.4	279.9	280.5	282.0
50°	275.9	269.8	265.6	263.4	262.1	261.4	262.1	264.0	265.3	266.9	267.9
52.5°	256.8	252.5	249.7	247.9	247.4	247.8	247.9	250.1	252.2	252.7	253.2
55°	230.6	227.3	226.7	223.8	225.1	224.7	226.4	227.6	229.5	231.5	231.9
57.5°	204.3	201.7	200.0	200.3	200.6	202.1	203.4	205.7	207.8	209.7	210.0
60°	186.8	185.5	184.6	184.6	185.2	187.2	188.7	191.0	192.3	193.6	194.5
62.5°	170.9	169.6	168.6	169.1	170.8	171.9	173.8	175.0	176.3	177.6	178.1
65°	145.7	145.0	146.0	146.6	147.0	148.5	150.8	151.8	153.1	153.7	155.9
67.5°	122.4	122.6	122.4	123.4	125.2	125.6	127.7	130.0	130.3	131.5	132.9
70°	106.8	107.4	108.1	108.7	110.3	110.9	112.5	113.5	114.8	115.7	116.8
72.5°	92.4	92.5	93.2	93.0	94.4	95.7	97.1	98.1	99.4	100.6	101.5
75°	71.0	71.0	71.7	72.1	73.6	75.3	74.9	75.6	76.9	78.2	78.8
77.5°	51.9	51.2	51.9	52.2	52.7	54.1	54.3	55.3	56.7	56.3	57.0
80°	39.5	38.6	39.5	39.9	39.9	41.5	41.5	42.1	43.0	42.1	43.0
82.5°	28.2	27.8	28.5	28.6	29.1	29.1	29.6	29.8	30.7	30.3	30.7
85°	14.1	13.9	14.1	13.9	14.1	14.5	14.5	14.1	14.1	14.8	13.9
87.5°	5.5	5.6	5.9	6.5	6.8	6.7	6.3	6.2	6.0	5.7	5.9
90°	5.9	7.4	9.8	13.3	16.2	16.7	16.2	15.7	14.7	15.7	16.2
92.5°	17.7	22.3	33.4	49.0	62.9	63.8	53.9	42.8	36.8	32.6	29.5
95°	36.3	48.1	70.7	113.4	170.4	192.5	168.4	128.6	98.7	78.1	67.2
97.5°	51.6	64.9	93.3	152.8	247.5	328.6	344.7	300.2	245.6	192.5	157.0
100°	61.4	75.2	101.2	161.1	267.1	387.9	458.6	448.3	387.4	320.1	260.7
102.5°	70.4	84.1	108.2	161.4	259.7	389.9	501.0	545.4	531.6	482.4	419.4
105°	83.4	97.2	120.3	164.0	245.0	363.9	494.5	596.6	652.0	658.5	642.2
107.5°	96.4	110.3	132.7	170.7	237.7	336.0	451.3	559.6	643.3	694.3	718.1
110°	105.0	119.3	140.9	176.2	236.2	322.6	424.2	527.9	615.7	678.6	718.8



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	113.3	127.9	148.8	182.2	236.6	313.9	405.4	498.8	583.2	650.3	696.5
115°	126.7	139.9	161.1	191.0	238.7	304.4	382.0	463.0	538.6	603.0	653.6
117.5°	139.1	152.8	172.4	200.4	242.2	299.8	367.3	436.1	502.5	560.9	608.3
120°	147.3	161.1	180.2	206.7	244.5	297.0	359.5	422.8	483.6	535.7	580.4
122.5°	155.6	169.7	187.7	212.2	247.3	295.5	352.8	412.2	468.0	517.2	557.6
125°	167.5	181.2	198.9	220.9	251.4	292.7	343.2	396.7	447.3	490.5	527.4
127.5°	178.0	192.1	209.3	229.1	255.6	291.0	334.4	381.5	427.3	468.0	502.0
130°	184.6	198.4	215.6	234.2	258.7	290.2	328.5	371.7	414.0	452.7	485.1
132.5°	190.9	204.7	221.0	239.4	261.9	289.8	323.7	362.3	401.4	437.0	467.4
135°	199.3	213.1	228.9	246.0	265.6	289.2	317.2	349.1	381.5	414.0	441.4
137.5°	206.8	219.6	235.1	251.1	269.0	289.1	312.5	338.6	365.8	391.4	415.4
140°	211.1	223.9	238.7	253.8	270.5	288.7	309.9	331.9	355.5	378.1	399.7
142.5°	215.1	227.0	241.4	256.2	271.7	288.7	307.1	326.4	346.5	365.9	384.0
145°	221.4	232.2	245.5	259.2	273.0	287.7	303.4	318.7	334.8	350.1	364.4
147.5°	226.8	236.3	248.8	261.0	273.4	285.9	299.7	312.7	325.5	337.3	347.8
150°	230.3	239.1	250.4	261.7	273.0	284.8	296.6	308.3	319.2	329.5	338.3
152.5°	233.8	241.9	252.0	262.1	272.2	282.8	293.9	304.0	314.1	322.8	330.5
155°	238.7	246.0	254.3	262.7	271.0	279.4	288.7	298.1	305.9	313.2	318.7
157.5°	242.8	248.9	256.0	262.7	268.8	275.9	283.9	291.1	297.6	303.8	308.1
160°	245.5	250.9	256.8	262.7	267.6	273.5	280.3	286.7	292.1	297.6	301.0
162.5°	247.9	252.1	257.2	262.3	266.4	271.6	277.2	282.4	287.1	291.7	294.3
165°	250.4	253.4	257.8	261.2	264.2	267.6	272.0	276.0	279.4	282.8	284.8
167.5°	252.6	254.4	257.7	260.5	261.9	264.2	266.9	269.8	272.4	274.7	276.6
170°	253.4	254.9	257.3	259.8	260.7	262.2	264.2	266.7	268.1	270.1	271.0
172.5°	254.2	255.2	256.9	258.6	259.2	259.8	261.4	263.1	264.2	265.7	266.3
175°	254.9	255.3	256.3	257.3	256.8	257.3	257.8	259.2	259.8	260.3	260.7
177.5°	255.3	255.3	255.7	256.5	255.7	255.3	255.7	256.5	256.5	256.9	256.9
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	802.5	801.9	801.9	799.6	801.9	801.9	802.5	805.0	805.8	806.3	805.3
5°	744.4	743.4	741.8	743.4	741.8	743.4	744.4	748.9	751.1	753.4	755.4
7.5°	687.0	683.1	682.5	678.7	682.5	683.1	687.0	689.1	693.5	698.6	703.3
10°	645.1	642.5	642.1	636.0	642.1	642.5	645.1	650.5	655.0	661.1	667.5
12.5°	613.1	606.9	608.2	604.7	608.2	606.9	613.1	613.2	618.5	622.2	632.3
15°	557.8	557.8	556.6	551.1	556.6	557.8	557.8	566.5	568.2	574.3	583.0
17.5°	518.2	517.5	514.4	516.0	514.4	517.5	518.2	524.6	525.6	533.8	541.0
20°	494.6	492.6	488.8	488.8	488.8	492.6	494.6	498.1	502.2	507.0	513.2
22.5°	472.2	472.0	468.0	469.2	468.0	472.0	472.2	475.4	479.4	484.7	489.8
25°	446.0	443.4	441.5	442.5	441.5	443.4	446.0	446.3	450.8	454.3	457.5
27.5°	421.2	419.7	419.7	417.0	419.7	419.7	421.2	422.0	424.6	426.6	429.6
30°	406.7	403.6	404.2	402.6	404.2	403.6	406.7	407.1	408.4	409.7	413.2
32.5°	390.3	389.2	388.5	387.1	388.5	389.2	390.3	390.9	393.5	394.8	397.5
35°	367.8	368.2	366.5	367.2	366.5	368.2	367.8	368.5	368.9	370.1	372.6
37.5°	348.3	349.3	348.5	348.7	348.5	349.3	348.3	348.5	348.9	349.0	349.8
40°	335.4	335.4	335.4	336.3	335.4	335.4	335.4	334.4	334.8	334.4	334.4
42.5°	323.0	322.5	322.0	321.9	322.0	322.5	323.0	320.8	321.8	320.8	320.3
45°	302.0	302.9	303.2	301.6	303.2	302.9	302.0	301.3	300.3	300.0	299.7
47.5°	282.8	282.9	282.8	284.2	282.8	282.9	282.8	282.0	280.5	279.9	278.4
50°	269.5	268.8	269.5	268.8	269.5	268.8	269.5	267.9	266.9	265.3	264.0
52.5°	255.3	255.5	255.0	254.9	255.0	255.5	255.3	253.2	252.7	252.2	250.1
55°	233.2	233.8	233.4	233.4	233.4	233.8	233.2	231.9	231.5	229.5	227.6
57.5°	210.2	210.8	211.2	209.7	211.2	210.8	210.2	210.0	209.7	207.8	205.7
60°	194.2	195.8	195.5	194.8	195.5	195.8	194.2	194.5	193.6	192.3	191.0
62.5°	179.5	180.1	180.0	179.9	180.0	180.1	179.5	178.1	177.6	176.3	175.0
65°	156.9	157.6	156.6	157.6	156.6	157.6	156.9	155.9	153.7	153.1	151.8
67.5°	132.5	132.8	133.5	133.9	133.5	132.8	132.5	132.9	131.5	130.3	130.0
70°	117.4	117.0	118.0	119.0	118.0	117.0	117.4	116.8	115.7	114.8	113.5
72.5°	101.4	102.1	101.8	102.5	101.8	102.1	101.4	101.5	100.6	99.4	98.1
75°	78.2	79.1	78.8	79.7	78.8	79.1	78.2	78.8	78.2	76.9	75.6
77.5°	56.5	56.6	56.5	57.0	56.5	56.6	56.5	57.0	56.3	56.7	55.3
80°	43.0	42.4	41.8	43.0	41.8	42.4	43.0	43.0	42.1	43.0	42.1
82.5°	30.0	30.4	29.7	29.7	29.7	30.4	30.0	30.7	30.3	30.7	29.8
85°	13.9	13.5	12.8	12.8	12.8	13.5	13.9	13.9	14.8	14.1	14.1
87.5°	5.9	5.6	5.6	5.3	5.6	5.6	5.9	5.9	5.7	6.0	6.2
90°	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2	15.7	14.7	15.7
92.5°	29.2	27.6	28.0	27.2	28.0	27.6	29.2	29.5	32.6	36.8	42.8
95°	60.9	57.0	55.4	56.0	55.4	57.0	60.9	67.2	78.1	98.7	128.6
97.5°	133.5	121.5	114.3	110.2	114.3	121.5	133.5	157.0	192.5	245.6	300.2
100°	220.0	198.9	184.6	175.8	184.6	198.9	220.0	260.7	320.1	387.4	448.3
102.5°	375.1	339.1	321.3	309.4	321.3	339.1	375.1	419.4	482.4	531.6	545.4
105°	611.8	581.3	560.3	553.4	560.3	581.3	611.8	642.2	658.5	652.0	596.6
107.5°	721.9	720.2	716.0	706.9	716.0	720.2	721.9	718.1	694.3	643.3	559.6
110°	739.9	749.3	753.7	753.2	753.7	749.3	739.9	718.8	678.6	615.7	527.9



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	725.8	741.4	749.8	752.4	749.8	741.4	725.8	696.5	650.3	583.2	498.8
115°	688.4	711.0	723.8	728.1	723.8	711.0	688.4	653.6	603.0	538.6	463.0
117.5°	643.9	667.7	681.1	684.8	681.1	667.7	643.9	608.3	560.9	502.5	436.1
120°	614.8	637.8	652.0	656.9	652.0	637.8	614.8	580.4	535.7	483.6	422.8
122.5°	588.4	611.1	623.8	627.9	623.8	611.1	588.4	557.6	517.2	468.0	412.2
125°	555.9	574.5	586.8	590.7	586.8	574.5	555.9	527.4	490.5	447.3	396.7
127.5°	526.8	544.3	554.9	558.1	554.9	544.3	526.8	502.0	468.0	427.3	381.5
130°	509.2	525.9	535.7	539.6	535.7	525.9	509.2	485.1	452.7	414.0	371.7
132.5°	491.1	507.8	516.9	520.4	516.9	507.8	491.1	467.4	437.0	401.4	362.3
135°	462.5	478.7	487.6	489.6	487.6	478.7	462.5	441.4	414.0	381.5	349.1
137.5°	434.6	448.6	456.3	459.3	456.3	448.6	434.6	415.4	391.4	365.8	338.6
140°	415.4	428.2	435.5	438.5	435.5	428.2	415.4	399.7	378.1	355.5	331.9
142.5°	398.9	410.5	417.1	417.7	417.1	410.5	398.9	384.0	365.9	346.5	326.4
145°	376.1	384.4	389.3	390.8	389.3	384.4	376.1	364.4	350.1	334.8	318.7
147.5°	357.5	364.1	367.5	368.3	367.5	364.1	357.5	347.8	337.3	325.5	312.7
150°	345.7	351.5	354.5	355.0	354.5	351.5	345.7	338.3	329.5	319.2	308.3
152.5°	336.2	341.4	343.5	343.6	343.5	341.4	336.2	330.5	322.8	314.1	304.0
155°	324.1	327.5	329.5	328.5	329.5	327.5	324.1	318.7	313.2	305.9	298.1
157.5°	311.9	314.8	315.6	315.6	315.6	314.8	311.9	308.1	303.8	297.6	291.1
160°	304.4	306.9	307.4	307.4	307.4	306.9	304.4	301.0	297.6	292.1	286.7
162.5°	297.7	299.5	299.9	299.5	299.9	299.5	297.7	294.3	291.7	287.1	282.4
165°	286.7	288.7	288.7	288.3	288.7	288.7	286.7	284.8	282.8	279.4	276.0
167.5°	277.4	278.5	278.4	277.8	278.4	278.5	277.4	276.6	274.7	272.4	269.8
170°	271.6	273.0	272.5	271.6	272.5	273.0	271.6	271.0	270.1	268.1	266.7
172.5°	266.8	267.5	267.0	266.4	267.0	267.5	266.8	266.3	265.7	264.2	263.1
175°	260.7	261.2	260.7	259.8	260.7	261.2	260.7	260.7	260.3	259.8	259.2
177.5°	256.9	256.9	256.5	255.7	256.5	256.9	256.9	256.9	256.9	256.5	256.5
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	804.0	806.8	811.2	815.8	818.6	824.1	825.6	828.2	830.5	835.9	841.5
5°	757.6	762.1	772.7	778.4	786.5	795.8	801.9	808.4	815.5	827.7	839.0
7.5°	707.8	715.3	728.5	739.3	750.8	764.1	773.8	786.5	797.0	814.2	830.8
10°	674.6	685.2	697.2	710.0	726.1	740.2	753.7	769.8	782.6	803.2	822.5
12.5°	644.8	646.4	663.4	677.6	699.6	717.0	732.6	753.3	765.9	790.4	810.7
15°	592.6	602.3	617.7	629.0	655.0	677.2	699.0	720.6	735.0	765.3	791.9
17.5°	548.7	557.6	573.4	591.9	610.5	632.6	660.9	683.6	703.3	737.8	769.4
20°	520.9	531.8	547.9	566.9	583.3	607.4	631.8	657.9	679.1	718.0	755.0
22.5°	497.2	505.8	518.8	537.5	555.5	577.6	604.3	632.7	655.0	696.9	734.4
25°	464.0	471.1	479.4	494.9	515.1	539.2	560.2	591.3	623.8	663.1	708.3
27.5°	434.0	439.0	446.4	460.0	475.7	498.3	521.5	551.0	583.8	626.3	674.2
30°	415.8	419.0	426.4	437.6	453.1	470.7	494.2	522.5	555.9	599.1	646.6
32.5°	399.8	402.8	407.6	418.4	431.7	446.9	468.0	496.3	528.1	570.5	623.2
35°	375.9	378.2	382.3	391.0	398.4	413.2	430.8	456.6	486.5	527.0	581.7
37.5°	352.1	355.1	357.7	361.4	370.8	380.6	396.0	417.7	447.0	487.9	540.0
40°	336.3	338.9	342.8	344.4	352.1	360.8	373.3	393.2	422.8	460.1	510.9
42.5°	320.4	323.0	325.3	327.2	333.8	341.5	352.8	369.9	396.1	432.4	482.7
45°	298.7	299.0	301.3	304.8	308.1	313.5	321.6	336.3	356.6	390.7	436.4
47.5°	276.7	277.1	277.5	279.1	282.6	287.5	292.8	304.9	323.0	350.3	394.7
50°	262.1	261.4	262.1	263.4	265.6	269.8	275.9	284.6	299.4	324.8	365.6
52.5°	247.9	247.8	247.4	247.9	249.7	252.5	256.8	264.2	277.5	300.8	336.8
55°	226.4	224.7	225.1	223.8	226.7	227.3	230.6	236.7	248.2	264.3	298.1
57.5°	203.4	202.1	200.6	200.3	200.0	201.7	204.3	209.1	218.0	232.1	259.5
60°	188.7	187.2	185.2	184.6	184.6	185.5	186.8	190.4	198.7	211.3	233.8
62.5°	173.8	171.9	170.8	169.1	168.6	169.6	170.9	173.4	179.4	191.2	210.6
65°	150.8	148.5	147.0	146.6	146.0	145.0	145.7	148.3	153.1	162.4	177.8
67.5°	127.7	125.6	125.2	123.4	122.4	122.6	122.4	124.7	127.5	135.5	147.1
70°	112.5	110.9	110.3	108.7	108.1	107.4	106.8	108.7	111.6	118.3	128.3
72.5°	97.1	95.7	94.4	93.0	93.2	92.5	92.4	93.5	95.9	102.1	109.8
75°	74.9	75.3	73.6	72.1	71.7	71.0	71.0	72.1	73.0	77.8	83.9
77.5°	54.3	54.1	52.7	52.2	51.9	51.2	51.9	52.5	53.0	56.3	60.8
80°	41.5	41.5	39.9	39.9	39.5	38.6	39.5	38.9	40.2	43.4	46.7
82.5°	29.6	29.1	29.1	28.6	28.5	27.8	28.2	28.8	29.4	31.6	33.5
85°	14.5	14.5	14.1	13.9	14.1	13.9	14.1	14.5	14.8	15.8	17.4
87.5°	6.3	6.7	6.8	6.5	5.9	5.6	5.5	5.6	5.9	5.8	5.8
90°	16.2	16.7	16.2	13.3	9.8	7.4	5.9	4.9	4.0	2.0	0.5
92.5°	53.9	63.8	62.9	49.0	33.4	22.3	17.7	14.4	12.1	8.6	6.0
95°	168.4	192.5	170.4	113.4	70.7	48.1	36.3	28.5	24.0	19.1	17.2
97.5°	344.7	328.6	247.5	152.8	93.3	64.9	51.6	42.5	35.8	30.7	28.0
100°	458.6	387.9	267.1	161.1	101.2	75.2	61.4	51.6	43.7	39.3	37.8
102.5°	501.0	389.9	259.7	161.4	108.2	84.1	70.4	60.2	52.3	48.0	46.8
105°	494.5	363.9	245.0	164.0	120.3	97.2	83.4	72.7	65.3	61.9	59.9
107.5°	451.3	336.0	237.7	170.7	132.7	110.3	96.4	85.8	79.0	75.6	74.0
110°	424.2	322.6	236.2	176.2	140.9	119.3	105.0	94.8	88.4	85.4	83.4



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	405.4	313.9	236.6	182.2	148.8	127.9	113.3	103.4	97.4	94.1	92.1
115°	382.0	304.4	238.7	191.0	161.1	139.9	126.7	116.8	111.0	108.1	105.6
117.5°	367.3	299.8	242.2	200.4	172.4	152.8	139.1	129.7	124.4	121.5	119.5
120°	359.5	297.0	244.5	206.7	180.2	161.1	147.3	137.5	133.0	130.1	128.1
122.5°	352.8	295.5	247.3	212.2	187.7	169.7	155.6	145.8	140.9	138.0	136.4
125°	343.2	292.7	251.4	220.9	198.9	181.2	167.5	157.6	151.7	148.8	147.3
127.5°	334.4	291.0	255.6	229.1	209.3	192.1	178.0	168.5	162.0	157.9	155.9
130°	328.5	290.2	258.7	234.2	215.6	198.4	184.6	174.8	167.9	163.0	161.1
132.5°	323.7	289.8	261.9	239.4	221.0	204.7	190.9	180.7	173.4	168.2	165.7
135°	317.2	289.2	265.6	246.0	228.9	213.1	199.3	188.0	180.7	174.8	172.8
137.5°	312.5	289.1	269.0	251.1	235.1	219.6	206.8	195.6	187.8	181.8	179.5
140°	309.9	288.7	270.5	253.8	238.7	223.9	211.1	200.4	192.5	186.6	184.6
142.5°	307.1	288.7	271.7	256.2	241.4	227.0	215.1	204.7	196.8	191.3	189.8
145°	303.4	287.7	273.0	259.2	245.5	232.2	221.4	211.6	204.2	199.3	197.4
147.5°	299.7	285.9	273.4	261.0	248.8	236.3	226.8	218.6	211.8	207.1	205.6
150°	296.6	284.8	273.0	261.7	250.4	239.1	230.3	222.9	216.5	212.6	211.1
152.5°	293.9	282.8	272.2	262.1	252.0	241.9	233.8	226.9	221.3	217.3	216.6
155°	288.7	279.4	271.0	262.7	254.3	246.0	238.7	233.2	227.8	224.9	224.4
157.5°	283.9	275.9	268.8	262.7	256.0	248.9	242.8	238.4	233.8	231.4	230.8
160°	280.3	273.5	267.6	262.7	256.8	250.9	245.5	241.6	237.6	235.7	235.2
162.5°	277.2	271.6	266.4	262.3	257.2	252.1	247.9	244.4	241.2	239.2	239.5
165°	272.0	267.6	264.2	261.2	257.8	253.4	250.4	248.0	245.0	244.0	244.5
167.5°	266.9	264.2	261.9	260.5	257.7	254.4	252.6	250.8	248.9	248.1	248.7
170°	264.2	262.2	260.7	259.8	257.3	254.9	253.4	252.4	250.9	250.4	251.4
172.5°	261.4	259.8	259.2	258.6	256.9	255.2	254.2	253.6	252.1	252.4	253.0
175°	257.8	257.3	256.8	257.3	256.3	255.3	254.9	254.9	253.8	254.3	254.9
177.5°	255.7	255.3	255.7	256.5	255.7	255.3	255.3	255.3	254.5	254.9	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	841.0	842.3	846.4	850.6	855.1	856.4	858.5	856.7	856.2	861.1	864.7
5°	843.4	849.2	860.5	870.7	879.4	885.5	892.0	894.6	899.4	906.1	914.5
7.5°	840.7	852.0	869.7	884.7	901.0	912.7	922.0	929.8	939.3	952.1	966.0
10°	837.7	852.7	874.3	892.6	912.6	927.6	940.2	952.4	966.6	984.3	1002.5
12.5°	832.0	849.9	876.8	898.5	924.1	939.0	955.9	982.2	997.5	1022.1	1047.8
15°	820.6	840.5	878.1	904.8	933.8	962.1	993.2	1018.3	1043.4	1057.9	1094.2
17.5°	803.7	832.9	874.6	905.8	942.5	987.1	1022.1	1050.6	1079.5	1102.9	1121.2
20°	790.1	821.9	869.4	906.8	950.5	998.4	1038.6	1067.6	1092.6	1112.2	1123.5
22.5°	772.8	812.9	859.2	902.9	958.7	1006.2	1048.4	1071.2	1092.1	1101.6	1106.0
25°	745.6	793.9	846.3	899.7	962.7	1012.9	1051.5	1065.3	1071.4	1062.0	1046.6
27.5°	716.4	770.2	831.5	893.6	960.3	1008.5	1036.1	1034.0	1023.6	993.4	969.3
30°	694.6	753.7	819.6	887.4	954.3	1001.3	1017.4	1001.3	977.8	944.1	909.6
32.5°	671.7	732.9	807.0	878.7	943.6	984.8	988.3	960.6	924.3	886.0	843.0
35°	637.0	703.3	783.3	859.2	920.6	946.7	931.2	882.4	839.2	786.9	728.3
37.5°	597.8	671.0	751.2	830.5	886.2	893.0	854.7	803.2	742.4	680.9	612.0
40°	568.5	646.0	728.7	808.7	857.9	850.8	801.9	745.4	673.0	597.8	533.7
42.5°	542.3	619.7	704.0	782.5	821.9	802.5	745.4	675.9	598.1	527.3	468.7
45°	496.8	576.5	662.7	738.6	761.1	726.1	650.5	573.3	496.8	437.6	391.3
47.5°	452.7	531.5	616.8	683.5	691.6	644.4	561.8	482.4	416.6	368.4	335.8
50°	420.3	499.4	583.9	643.4	640.8	583.9	499.0	423.4	368.5	329.6	307.7
52.5°	391.2	465.9	547.2	601.2	587.6	525.6	444.5	377.5	332.3	301.8	282.0
55°	345.9	415.1	492.3	535.7	510.7	441.8	373.3	319.3	285.9	263.0	247.6
57.5°	301.1	365.9	432.0	458.7	431.0	367.5	310.4	271.2	246.1	229.1	219.1
60°	273.3	329.9	388.7	411.9	378.8	322.2	277.2	242.1	221.9	208.0	199.1
62.5°	245.6	296.2	351.7	364.3	334.0	286.2	246.3	217.1	200.5	188.2	179.8
65°	207.8	249.2	291.4	299.7	271.7	234.7	203.2	184.3	169.4	160.5	153.7
67.5°	170.4	203.6	233.5	240.2	215.8	190.1	167.3	150.8	140.8	133.3	127.6
70°	148.3	174.6	199.1	204.5	184.9	162.0	144.7	131.5	122.5	116.1	110.6
72.5°	124.8	146.8	167.1	170.8	154.8	137.3	123.1	112.7	104.8	100.7	95.4
75°	95.5	108.4	124.2	125.1	114.5	103.8	92.9	86.2	82.0	76.9	74.3
77.5°	67.4	77.5	86.5	88.3	82.0	74.7	68.6	63.3	59.8	57.3	55.0
80°	51.5	59.5	63.4	65.6	61.1	56.0	52.4	48.9	46.7	45.0	43.4
82.5°	36.8	41.8	45.4	47.1	44.6	41.6	38.0	36.0	34.3	32.9	32.4
85°	18.7	20.9	23.2	23.8	23.2	21.9	20.0	20.0	18.9	18.7	18.7
87.5°	6.8	8.3	8.4	9.4	9.2	9.6	10.3	10.7	10.5	10.2	9.8
90°	2.0	4.0	4.9	5.9	7.4	9.8	13.3	16.2	16.7	16.2	15.7
92.5°	8.6	12.1	14.4	17.7	22.3	33.4	49.0	62.9	63.8	53.9	42.8
95°	19.1	24.0	28.5	36.3	48.1	70.7	113.4	170.4	192.5	168.4	128.6
97.5°	30.7	35.8	42.5	51.6	64.9	93.3	152.8	247.5	328.6	344.7	300.2
100°	39.3	43.7	51.6	61.4	75.2	101.2	161.1	267.1	387.9	458.6	448.3
102.5°	48.0	52.3	60.2	70.4	84.1	108.2	161.4	259.7	389.9	501.0	545.4
105°	61.9	65.3	72.7	83.4	97.2	120.3	164.0	245.0	363.9	494.5	596.6
107.5°	75.6	79.0	85.8	96.4	110.3	132.7	170.7	237.7	336.0	451.3	559.6
110°	85.4	88.4	94.8	105.0	119.3	140.9	176.2	236.2	322.6	424.2	527.9



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	94.1	97.4	103.4	113.3	127.9	148.8	182.2	236.6	313.9	405.4	498.8
115°	108.1	111.0	116.8	126.7	139.9	161.1	191.0	238.7	304.4	382.0	463.0
117.5°	121.5	124.4	129.7	139.1	152.8	172.4	200.4	242.2	299.8	367.3	436.1
120°	130.1	133.0	137.5	147.3	161.1	180.2	206.7	244.5	297.0	359.5	422.8
122.5°	138.0	140.9	145.8	155.6	169.7	187.7	212.2	247.3	295.5	352.8	412.2
125°	148.8	151.7	157.6	167.5	181.2	198.9	220.9	251.4	292.7	343.2	396.7
127.5°	157.9	162.0	168.5	178.0	192.1	209.3	229.1	255.6	291.0	334.4	381.5
130°	163.0	167.9	174.8	184.6	198.4	215.6	234.2	258.7	290.2	328.5	371.7
132.5°	168.2	173.4	180.7	190.9	204.7	221.0	239.4	261.9	289.8	323.7	362.3
135°	174.8	180.7	188.0	199.3	213.1	228.9	246.0	265.6	289.2	317.2	349.1
137.5°	181.8	187.8	195.6	206.8	219.6	235.1	251.1	269.0	289.1	312.5	338.6
140°	186.6	192.5	200.4	211.1	223.9	238.7	253.8	270.5	288.7	309.9	331.9
142.5°	191.3	196.8	204.7	215.1	227.0	241.4	256.2	271.7	288.7	307.1	326.4
145°	199.3	204.2	211.6	221.4	232.2	245.5	259.2	273.0	287.7	303.4	318.7
147.5°	207.1	211.8	218.6	226.8	236.3	248.8	261.0	273.4	285.9	299.7	312.7
150°	212.6	216.5	222.9	230.3	239.1	250.4	261.7	273.0	284.8	296.6	308.3
152.5°	217.3	221.3	226.9	233.8	241.9	252.0	262.1	272.2	282.8	293.9	304.0
155°	224.9	227.8	233.2	238.7	246.0	254.3	262.7	271.0	279.4	288.7	298.1
157.5°	231.4	233.8	238.4	242.8	248.9	256.0	262.7	268.8	275.9	283.9	291.1
160°	235.7	237.6	241.6	245.5	250.9	256.8	262.7	267.6	273.5	280.3	286.7
162.5°	239.2	241.2	244.4	247.9	252.1	257.2	262.3	266.4	271.6	277.2	282.4
165°	244.0	245.0	248.0	250.4	253.4	257.8	261.2	264.2	267.6	272.0	276.0
167.5°	248.1	248.9	250.8	252.6	254.4	257.7	260.5	261.9	264.2	266.9	269.8
170°	250.4	250.9	252.4	253.4	254.9	257.3	259.8	260.7	262.2	264.2	266.7
172.5°	252.4	252.1	253.6	254.2	255.2	256.9	258.6	259.2	259.8	261.4	263.1
175°	254.3	253.8	254.9	254.9	255.3	256.3	257.3	256.8	257.3	257.8	259.2
177.5°	254.9	254.5	255.3	255.3	255.3	255.7	256.5	255.7	255.3	255.7	256.5
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	867.8	871.4	871.4	871.9	876.0	875.6	875.3
5°	923.5	928.9	929.6	935.4	939.3	938.0	934.4
7.5°	976.0	986.2	993.9	998.2	1003.3	1006.4	1005.0
10°	1017.7	1032.5	1041.5	1047.6	1055.0	1060.5	1058.5
12.5°	1055.5	1073.2	1085.5	1096.0	1096.9	1104.0	1099.2
15°	1114.5	1133.2	1135.1	1142.8	1148.9	1148.2	1148.6
17.5°	1133.9	1140.0	1141.2	1141.3	1141.4	1139.2	1134.3
20°	1127.0	1124.8	1119.3	1115.2	1107.8	1106.7	1100.4
22.5°	1094.1	1086.9	1073.2	1064.2	1052.7	1049.6	1047.8
25°	1029.2	1013.5	991.6	970.8	964.9	953.7	956.9
27.5°	940.3	915.8	892.1	875.1	859.8	842.9	847.7
30°	877.8	850.2	816.7	791.0	774.6	758.5	755.6
32.5°	803.2	762.7	725.4	702.7	677.6	667.4	656.3
35°	674.6	635.1	598.1	566.3	547.9	533.7	520.9
37.5°	558.9	513.4	483.5	457.8	444.5	436.4	438.4
40°	487.2	447.3	425.4	405.8	393.6	387.8	389.1
42.5°	429.0	399.2	381.2	367.7	359.1	355.9	355.1
45°	363.0	346.3	331.5	323.8	319.6	316.1	313.8
47.5°	318.1	304.4	296.0	291.4	287.7	284.2	284.1
50°	291.0	282.0	276.2	271.4	268.5	265.9	268.2
52.5°	270.4	262.2	256.4	252.1	251.0	248.7	248.7
55°	239.9	233.4	229.3	225.4	223.5	222.2	220.6
57.5°	212.1	206.0	202.2	199.7	196.0	194.8	194.2
60°	192.3	187.4	183.6	180.4	178.7	176.2	176.2
62.5°	174.0	169.2	165.6	163.2	160.5	159.5	159.7
65°	147.6	143.7	140.2	137.6	137.0	135.1	135.7
67.5°	123.3	120.7	117.0	115.5	114.3	113.3	112.5
70°	107.1	104.5	102.5	100.7	99.7	99.7	99.7
72.5°	93.4	90.3	89.2	86.8	87.3	86.3	85.2
75°	72.3	70.4	69.5	68.4	66.9	66.9	66.9
77.5°	53.2	52.7	51.5	50.5	50.1	49.8	49.9
80°	41.2	40.8	40.2	40.2	39.5	39.3	38.6
82.5°	31.6	30.8	30.4	30.1	30.0	30.0	29.9
85°	18.0	17.4	17.4	17.7	17.0	17.0	17.4
87.5°	9.9	10.1	9.9	9.9	10.2	9.9	9.9
90°	14.7	15.7	16.2	16.2	16.2	16.2	16.2
92.5°	36.8	32.6	29.5	29.2	27.6	28.0	27.2
95°	98.7	78.1	67.2	60.9	57.0	55.4	56.0
97.5°	245.6	192.5	157.0	133.5	121.5	114.3	110.2
100°	387.4	320.1	260.7	220.0	198.9	184.6	175.8
102.5°	531.6	482.4	419.4	375.1	339.1	321.3	309.4
105°	652.0	658.5	642.2	611.8	581.3	560.3	553.4
107.5°	643.3	694.3	718.1	721.9	720.2	716.0	706.9
110°	615.7	678.6	718.8	739.9	749.3	753.7	753.2



TEST NUMBER: P331296-935

CATALOG NUMBER: S122DIP-S485D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	583.2	650.3	696.5	725.8	741.4	749.8	752.4
115°	538.6	603.0	653.6	688.4	711.0	723.8	728.1
117.5°	502.5	560.9	608.3	643.9	667.7	681.1	684.8
120°	483.6	535.7	580.4	614.8	637.8	652.0	656.9
122.5°	468.0	517.2	557.6	588.4	611.1	623.8	627.9
125°	447.3	490.5	527.4	555.9	574.5	586.8	590.7
127.5°	427.3	468.0	502.0	526.8	544.3	554.9	558.1
130°	414.0	452.7	485.1	509.2	525.9	535.7	539.6
132.5°	401.4	437.0	467.4	491.1	507.8	516.9	520.4
135°	381.5	414.0	441.4	462.5	478.7	487.6	489.6
137.5°	365.8	391.4	415.4	434.6	448.6	456.3	459.3
140°	355.5	378.1	399.7	415.4	428.2	435.5	438.5
142.5°	346.5	365.9	384.0	398.9	410.5	417.1	417.7
145°	334.8	350.1	364.4	376.1	384.4	389.3	390.8
147.5°	325.5	337.3	347.8	357.5	364.1	367.5	368.3
150°	319.2	329.5	338.3	345.7	351.5	354.5	355.0
152.5°	314.1	322.8	330.5	336.2	341.4	343.5	343.6
155°	305.9	313.2	318.7	324.1	327.5	329.5	328.5
157.5°	297.6	303.8	308.1	311.9	314.8	315.6	315.6
160°	292.1	297.6	301.0	304.4	306.9	307.4	307.4
162.5°	287.1	291.7	294.3	297.7	299.5	299.9	299.5
165°	279.4	282.8	284.8	286.7	288.7	288.7	288.3
167.5°	272.4	274.7	276.6	277.4	278.5	278.4	277.8
170°	268.1	270.1	271.0	271.6	273.0	272.5	271.6
172.5°	264.2	265.7	266.3	266.8	267.5	267.0	266.4
175°	259.8	260.3	260.7	260.7	261.2	260.7	259.8
177.5°	256.5	256.9	256.9	256.9	256.9	256.5	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3

(END OF REPORT)