

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331617-935

Luminaire Tested: **S122RDIP-S290D330U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331617-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D330U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2075.0 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	94	90	87	90	86	83	81	73	70	68	60	58	57	48	47	46	41
2	90	83	77	72	82	76	72	67	65	61	58	54	51	49	43	42	40	36
3	82	73	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	52	70	61	54	49	52	47	43	43	40	37	36	33	31	27
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	32	30	28	24
6	65	53	45	40	59	49	43	38	42	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	27	25	22	20
8	56	44	37	32	51	41	35	30	36	30	27	30	26	24	25	23	20	18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19	17
10	49	37	30	26	45	35	29	24	30	25	22	26	22	20	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9087	9087	9087	9087
5°	10149	9144	8109	9144
10°	11262	9081	7029	9081
15°	11814	8948	5538	8948
20°	10244	8751	4792	8751
25°	6716	8480	4277	8480
30°	4521	8153	3872	8153
35°	3662	7740	3493	7740
40°	3256	7290	3231	7290
45°	2948	6766	2884	6766
50°	2683	6244	2673	6244
55°	2519	5664	2488	5664
60°	2109	5134	2086	5134
65°	1780	4661	2017	4661
70°	1643	4164	1902	4164
75°	1535	3624	1759	3624
80°	1413	2985	1562	2985
85°	1315	2353	1371	2353



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	2.6
10°-20°	148.7	7.2
20°-30°	191.6	9.2
30°-40°	182.1	8.8
40°-50°	156.0	7.5
50°-60°	118.8	5.7
60°-70°	75.1	3.6
70°-80°	37.5	1.8
80°-90°	11.2	0.5
90°-100°	63.3	3.0
100°-110°	214.7	10.3
110°-120°	228.0	11.0
120°-130°	187.7	9.0
130°-140°	150.7	7.3
140°-150°	113.9	5.5
150°-160°	80.1	3.9
160°-170°	47.1	2.3
170°-180°	15.3	0.7
0°-30°	393.6	19.0
0°-40°	575.7	27.7
0°-60°	850.4	41.0
0°-90°	974.2	46.9
90°-120°	505.9	24.4
90°-150°	958.3	46.2
90°-180°	1101.0	53.1
0°-180°	2075.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	626	564	500	564	626	62
15°	707	535	331	535	707	191
25°	377	476	240	476	377	179
35°	186	393	177	393	186	119
45°	129	296	126	296	129	100
55°	90	201	88	201	90	79
65°	47	122	53	122	47	47
75°	25	58	28	58	25	26
85°	7	13	7	13	7	8
90°	10	0	10	0	10	6
95°	35	11	35	11	35	45
105°	343	37	343	37	343	332
115°	451	65	451	65	451	442
125°	366	91	366	91	366	331
135°	303	107	303	107	303	236
145°	242	122	242	122	242	154
155°	204	139	204	139	204	95
165°	179	152	179	152	179	51
175°	161	158	161	158	161	16
180°	158	158	158	158	158	



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	585.7	586.2	586.7	585.6	585.6	584.6	582.6	581.0	576.6	576.0	576.0
5°	626.2	625.9	626.6	624.1	620.6	619.7	616.0	611.1	606.1	600.5	599.3
7.5°	666.5	665.9	664.3	663.9	661.2	655.3	649.4	643.0	634.6	626.3	622.2
10°	686.9	693.4	689.4	682.6	683.9	674.8	669.9	661.4	654.4	642.0	639.4
12.5°	706.9	709.5	708.2	704.3	702.6	696.2	689.6	682.3	669.3	658.2	648.6
15°	706.8	710.5	711.5	710.3	711.3	710.9	707.4	701.4	690.0	677.9	667.3
17.5°	654.6	657.2	663.7	668.0	673.5	685.0	690.8	692.9	691.3	684.3	676.9
20°	596.2	591.9	609.8	619.0	626.8	646.4	663.2	669.7	680.0	679.8	677.9
22.5°	513.2	514.2	531.2	542.2	565.0	584.6	603.7	628.0	648.1	661.3	669.1
25°	377.0	384.5	401.5	416.4	441.8	478.2	511.3	549.6	585.7	614.3	641.5
27.5°	283.2	283.8	297.2	311.0	326.1	355.9	397.5	443.2	494.8	537.4	586.3
30°	242.5	241.3	247.0	255.5	268.4	291.4	322.7	367.6	419.1	483.3	540.4
32.5°	213.7	213.8	218.1	224.3	235.0	250.6	272.0	308.6	357.1	420.3	487.2
35°	185.8	185.6	188.7	193.2	197.7	207.7	222.4	241.5	275.0	333.8	402.3
37.5°	165.7	166.6	168.2	171.0	175.9	181.5	190.3	203.2	227.0	261.8	319.3
40°	154.5	154.9	157.0	159.4	162.3	166.6	173.8	184.3	201.6	229.4	271.5
42.5°	144.2	144.6	146.1	148.3	150.6	154.9	160.9	169.9	184.0	205.6	240.3
45°	129.1	129.1	130.4	131.4	134.0	137.8	142.8	150.2	160.0	176.0	199.1
47.5°	114.9	114.9	115.9	117.5	119.2	122.2	127.0	133.1	140.2	152.6	172.3
50°	106.8	107.0	107.5	108.9	109.9	112.6	116.4	121.7	129.1	138.7	155.1
52.5°	100.2	100.1	100.8	101.4	102.1	104.0	106.9	111.5	118.1	126.5	140.1
55°	89.5	88.8	90.0	90.9	91.5	92.3	93.8	96.8	102.5	109.5	119.7
57.5°	76.3	75.9	76.8	77.7	79.6	81.6	83.0	84.8	87.7	92.8	102.9
60°	65.3	65.3	67.1	67.7	69.8	72.6	75.3	76.9	79.8	83.1	90.6
62.5°	55.6	55.8	56.6	57.2	58.4	61.7	65.6	69.1	71.8	75.0	79.9
65°	46.6	46.9	46.9	47.4	48.1	48.9	50.5	53.2	58.1	62.6	66.3
67.5°	39.5	39.6	39.8	40.1	40.3	41.2	41.8	43.0	44.2	48.4	53.0
70°	34.8	35.4	35.2	35.6	35.8	36.2	36.9	37.5	39.3	40.3	43.0
72.5°	30.4	30.8	30.8	31.1	31.6	31.7	32.3	32.9	34.0	34.8	36.3
75°	24.6	24.5	24.6	25.1	25.2	25.4	25.4	26.2	26.8	27.6	28.6
77.5°	19.0	19.2	19.2	19.2	19.3	19.6	19.5	19.9	20.5	20.9	21.4
80°	15.2	15.4	15.2	15.4	15.7	15.8	15.7	15.8	16.4	16.8	16.8
82.5°	11.8	11.9	12.0	12.0	12.1	12.1	12.4	12.4	12.8	12.7	12.9
85°	7.1	6.9	6.9	6.9	7.1	7.2	7.1	7.1	7.2	7.2	7.2
87.5°	4.5	4.6	4.6	4.6	4.6	4.6	4.5	4.7	4.6	4.9	4.6
90°	10.1	10.1	10.1	10.1	10.1	9.7	9.1	9.7	10.1	10.3	10.1
92.5°	16.9	17.3	17.1	18.1	18.3	20.2	22.7	26.5	33.4	39.5	39.0
95°	34.7	34.4	35.3	37.7	41.7	48.4	61.1	79.7	104.4	119.2	105.6
97.5°	68.3	70.9	75.3	82.7	97.3	119.2	152.1	186.0	213.5	203.5	153.3
100°	108.9	114.4	123.2	136.3	161.5	198.4	240.0	277.8	284.1	240.3	165.5
102.5°	191.7	199.1	210.1	232.4	259.8	298.9	329.3	337.9	310.4	241.5	160.8
105°	342.9	347.1	360.2	379.0	398.0	407.9	404.0	369.6	306.3	225.4	151.8
107.5°	438.0	443.6	446.3	447.3	444.9	430.2	398.6	346.7	279.7	208.1	147.3
110°	466.7	467.0	464.3	458.5	445.4	420.4	381.5	327.0	262.9	199.8	146.4



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	466.1	464.5	459.3	449.7	431.5	402.9	361.3	309.0	251.2	194.5	146.5
115°	451.2	448.4	440.5	426.5	404.9	373.6	333.7	286.9	236.7	188.6	147.8
117.5°	424.3	422.0	413.7	398.9	376.9	347.5	311.3	270.2	227.6	185.7	150.1
120°	407.1	404.0	395.2	380.9	359.6	331.9	299.6	261.9	222.7	184.1	151.5
122.5°	389.0	386.5	378.7	364.5	345.4	320.5	289.9	255.4	218.5	183.0	153.2
125°	366.0	363.5	355.9	344.4	326.7	303.9	277.2	245.8	212.7	181.3	155.8
127.5°	345.8	343.8	337.3	326.4	311.0	290.0	264.8	236.3	207.2	180.3	158.3
130°	334.3	331.9	325.8	315.5	300.6	280.5	256.5	230.3	203.5	179.8	160.3
132.5°	322.4	320.2	314.6	304.3	289.6	270.8	248.7	224.5	200.6	179.5	162.3
135°	303.3	302.1	296.6	286.5	273.5	256.5	236.3	216.3	196.5	179.2	164.6
137.5°	284.6	282.8	277.9	269.3	257.4	242.5	226.6	209.8	193.6	179.1	166.7
140°	271.6	269.8	265.3	257.4	247.6	234.3	220.2	205.6	191.9	178.9	167.6
142.5°	258.7	258.4	254.3	247.1	237.9	226.7	214.6	202.2	190.3	178.9	168.3
145°	242.1	241.3	238.2	233.0	225.8	216.9	207.5	197.4	188.0	178.2	169.1
147.5°	228.3	227.6	225.6	221.4	215.4	209.0	201.6	193.7	185.7	177.2	169.4
150°	220.0	219.6	217.8	214.1	209.6	204.1	197.8	191.1	183.7	176.4	169.1
152.5°	212.9	212.8	211.5	208.4	204.7	200.0	194.6	188.4	182.0	175.2	168.7
155°	203.5	204.1	202.9	200.8	197.4	194.1	189.5	184.7	178.9	173.1	167.9
157.5°	195.5	195.5	195.0	193.2	190.9	188.2	184.4	180.4	175.9	170.9	166.5
160°	190.5	190.5	190.1	188.6	186.5	184.3	181.0	177.6	173.7	169.4	165.8
162.5°	185.5	185.8	185.5	184.5	182.4	180.7	177.9	175.0	171.8	168.2	165.1
165°	178.6	178.9	178.9	177.6	176.4	175.2	173.1	171.0	168.5	165.8	163.7
167.5°	172.1	172.5	172.5	171.9	171.3	170.2	168.8	167.1	165.4	163.7	162.3
170°	168.2	168.8	169.1	168.2	167.9	167.3	166.1	165.2	163.7	162.5	161.5
172.5°	165.1	165.4	165.7	165.3	165.0	164.6	163.7	163.0	162.0	161.0	160.6
175°	160.9	161.5	161.9	161.5	161.5	161.3	160.9	160.7	159.7	159.4	159.1
177.5°	158.4	158.9	159.2	159.2	159.2	159.2	158.9	158.9	158.4	158.2	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	576.4	575.1	573.9	571.2	569.7	566.6	566.2	566.0	562.0	558.0	556.9
5°	596.2	593.0	588.3	582.8	577.1	571.3	567.4	564.2	556.4	549.0	544.7
7.5°	616.0	609.3	601.2	590.9	582.2	572.6	565.3	558.9	547.8	537.1	529.9
10°	630.9	620.0	609.2	595.0	583.8	572.8	562.7	553.9	541.4	527.3	517.3
12.5°	640.2	628.1	613.3	599.3	584.9	570.9	557.3	546.0	531.3	516.8	505.0
15°	652.6	639.7	621.7	601.8	583.2	565.0	549.4	535.3	516.2	498.7	484.2
17.5°	662.9	645.1	625.8	602.7	581.2	558.1	538.0	520.0	498.6	477.6	460.5
20°	666.2	648.5	626.2	603.1	577.7	550.5	528.8	509.3	486.4	463.5	443.9
22.5°	664.1	650.4	625.6	598.0	572.0	543.5	519.0	496.3	470.9	447.5	424.9
25°	650.3	645.6	622.2	592.0	562.3	529.3	500.8	476.0	447.1	422.1	397.4
27.5°	618.1	628.3	613.7	581.6	548.5	513.2	481.2	453.0	422.9	394.8	370.2
30°	587.1	610.4	604.2	574.4	537.4	502.7	466.8	437.3	405.3	376.3	352.1
32.5°	544.8	583.2	589.3	564.4	526.2	487.9	450.4	421.0	387.5	357.1	333.4
35°	477.2	534.7	561.1	545.3	507.0	465.6	427.0	392.7	359.0	329.0	305.5
37.5°	396.7	475.0	519.0	520.1	484.9	442.0	399.8	365.8	331.4	301.9	276.5
40°	344.4	429.3	486.6	499.3	469.6	423.3	380.6	345.9	312.4	283.4	254.3
42.5°	297.5	382.0	452.5	474.6	451.0	404.9	362.1	326.0	293.3	265.9	236.1
45°	240.6	314.5	392.1	431.6	418.5	375.9	330.7	296.3	265.6	241.9	213.4
47.5°	202.9	255.0	330.2	383.6	383.4	344.5	300.0	267.1	238.6	216.4	193.3
50°	181.5	226.9	290.4	351.0	356.1	323.5	281.2	248.6	222.0	198.7	180.1
52.5°	162.2	199.7	256.8	315.0	329.4	301.1	260.1	230.0	204.1	182.7	166.9
55°	137.1	166.1	209.5	263.8	285.8	265.8	229.4	201.2	180.3	162.3	148.6
57.5°	116.0	137.7	172.5	216.3	241.8	229.3	199.2	176.3	158.4	142.2	131.4
60°	102.7	120.5	150.0	186.6	214.7	206.0	180.3	159.0	143.8	129.7	119.5
62.5°	90.1	105.5	130.8	160.5	186.2	182.6	161.7	143.8	130.4	117.6	109.0
65°	72.6	83.7	103.5	126.7	147.5	149.2	134.1	122.0	110.1	100.0	92.3
67.5°	57.8	65.1	79.0	98.6	114.1	119.7	110.5	101.2	91.7	83.9	77.2
70°	48.7	54.6	64.7	80.6	94.9	100.7	95.4	88.2	80.0	73.5	67.8
72.5°	39.4	45.2	52.7	64.3	76.5	82.9	81.0	75.9	69.2	63.8	58.5
75°	29.7	31.5	36.6	44.4	54.0	59.5	60.8	58.1	52.8	48.7	45.5
77.5°	22.0	23.1	25.5	29.5	35.8	40.7	42.7	42.4	38.7	36.4	33.4
80°	17.6	18.2	19.4	21.1	25.8	30.7	32.1	32.1	29.5	28.6	25.7
82.5°	13.3	13.8	14.6	15.5	17.7	22.0	23.5	23.8	22.2	20.9	18.6
85°	7.7	7.4	7.8	8.4	8.8	10.0	12.3	12.7	12.3	10.8	10.2
87.5°	4.3	4.0	3.7	3.4	3.4	3.4	4.0	4.6	4.1	4.0	3.7
90°	8.2	6.1	4.6	3.6	3.0	2.4	1.2	0.3	1.2	2.4	3.0
92.5°	30.4	20.7	13.8	10.9	8.9	7.6	5.3	3.7	5.3	7.6	8.9
95°	70.3	43.8	29.8	22.5	17.7	14.9	11.9	10.7	11.9	14.9	17.7
97.5°	94.7	57.8	40.2	31.9	26.3	22.2	18.9	17.3	18.9	22.2	26.3
100°	99.8	62.7	46.6	38.1	31.9	27.0	24.4	23.4	24.4	27.0	31.9
102.5°	100.0	67.1	52.2	43.7	37.3	32.5	29.7	29.0	29.7	32.5	37.3
105°	101.6	74.6	60.3	51.7	45.0	40.5	38.3	37.1	38.3	40.5	45.0
107.5°	105.8	82.2	68.4	59.8	53.1	48.9	46.8	45.9	46.8	48.9	53.1
110°	109.2	87.3	74.0	65.1	58.7	54.8	53.0	51.7	53.0	54.8	58.7



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	112.9	92.2	79.3	70.2	64.1	60.4	58.3	57.1	58.3	60.4	64.1
115°	118.3	99.8	86.7	78.5	72.4	68.8	66.9	65.4	66.9	68.8	72.4
117.5°	124.2	106.8	94.7	86.2	80.3	77.1	75.3	74.0	75.3	77.1	80.3
120°	128.1	111.7	99.8	91.3	85.2	82.5	80.6	79.4	80.6	82.5	85.2
122.5°	131.5	116.2	105.1	96.3	90.3	87.3	85.5	84.6	85.5	87.3	90.3
125°	136.9	123.2	112.3	103.8	97.6	94.0	92.2	91.3	92.2	94.0	97.6
127.5°	142.0	129.7	119.0	110.2	104.4	100.4	97.8	96.6	97.8	100.4	104.4
130°	145.1	133.5	122.9	114.4	108.3	104.0	101.0	99.8	101.0	104.0	108.3
132.5°	148.3	137.0	126.8	118.3	111.9	107.5	104.2	102.7	104.2	107.5	111.9
135°	152.4	141.8	132.0	123.6	116.5	111.9	108.3	107.1	108.3	111.9	116.5
137.5°	155.6	145.7	136.0	128.1	121.2	116.3	112.7	111.2	112.7	116.3	121.2
140°	157.3	147.8	138.7	130.8	124.2	119.2	115.6	114.4	115.6	119.2	124.2
142.5°	158.8	149.6	140.7	133.3	126.8	121.9	118.6	117.5	118.6	121.9	126.8
145°	160.7	152.1	143.9	137.2	131.1	126.6	123.6	122.3	123.6	126.6	131.1
147.5°	161.7	154.2	146.5	140.5	135.4	131.2	128.3	127.4	128.3	131.2	135.4
150°	162.1	155.2	148.2	142.7	138.1	134.1	131.7	130.8	131.7	134.1	138.1
152.5°	162.4	156.1	149.8	144.9	140.5	137.1	134.7	134.2	134.7	137.1	140.5
155°	162.7	157.6	152.4	147.8	144.5	141.1	139.3	139.1	139.3	141.1	144.5
157.5°	162.7	158.6	154.2	150.4	147.7	144.8	143.4	143.0	143.4	144.8	147.7
160°	162.7	159.1	155.5	152.1	149.6	147.2	146.0	145.7	146.0	147.2	149.6
162.5°	162.5	159.4	156.2	153.6	151.4	149.5	148.2	148.4	148.2	149.5	151.4
165°	161.9	159.7	157.0	155.2	153.6	151.8	151.2	151.5	151.2	151.8	153.6
167.5°	161.4	159.6	157.6	156.5	155.4	154.2	153.7	154.0	153.7	154.2	155.4
170°	160.9	159.4	157.9	157.0	156.4	155.5	155.2	155.8	155.2	155.5	156.4
172.5°	160.2	159.2	158.2	157.5	157.1	156.2	156.4	156.7	156.4	156.2	157.1
175°	159.4	158.8	158.2	157.9	157.9	157.3	157.6	157.9	157.6	157.3	157.9
177.5°	158.9	158.4	158.2	158.2	158.2	157.7	157.9	158.4	157.9	157.7	158.2
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	554.9	553.8	551.7	548.6	546.7	543.5	541.3	542.5	542.9	542.5	542.3
5°	540.0	535.9	530.2	524.7	519.6	514.2	511.0	509.7	507.0	505.4	504.5
7.5°	521.9	514.9	506.9	497.3	489.2	480.7	476.4	474.2	468.6	465.6	463.0
10°	508.5	497.3	489.3	476.8	469.2	458.1	450.4	450.6	443.0	438.7	435.6
12.5°	493.6	481.4	468.0	456.8	446.2	437.2	428.0	424.3	416.2	412.1	403.6
15°	469.0	454.7	440.7	425.4	414.7	400.7	387.4	371.2	358.1	346.7	343.6
17.5°	442.1	424.4	410.3	392.4	373.9	350.6	335.2	325.7	317.9	311.9	307.4
20°	423.6	405.6	390.5	363.6	338.7	322.9	311.6	304.3	296.1	289.6	286.1
22.5°	404.2	385.5	364.9	334.8	315.4	302.7	292.7	284.3	278.7	273.7	270.4
25°	376.7	356.1	322.3	301.6	285.9	272.6	265.6	260.5	254.7	247.8	244.7
27.5°	347.6	315.0	290.6	275.2	260.3	251.7	245.3	237.7	232.5	229.4	226.1
30°	325.8	293.2	274.2	257.4	246.8	237.2	229.8	225.5	220.4	215.2	213.0
32.5°	301.6	275.5	257.3	243.3	232.6	224.4	218.5	211.5	207.9	204.7	200.2
35°	271.5	251.7	235.1	223.8	213.5	206.9	200.1	196.0	189.3	186.6	184.9
37.5°	246.0	228.9	216.5	204.5	196.4	189.1	184.9	178.3	175.5	171.6	167.9
40°	231.5	214.7	202.9	193.0	184.0	178.6	173.3	168.0	163.7	162.0	157.5
42.5°	216.9	203.2	191.2	180.6	174.5	168.7	162.0	158.2	153.7	150.8	148.1
45°	196.6	184.4	174.3	165.5	158.8	152.7	148.4	142.0	139.5	133.8	131.4
47.5°	178.7	167.5	157.7	149.4	142.9	139.0	132.7	127.6	123.6	120.0	117.0
50°	166.1	156.6	147.2	139.8	134.0	128.3	121.8	119.3	113.0	111.2	109.5
52.5°	154.5	145.5	137.0	129.7	123.8	118.3	112.6	109.3	105.0	103.3	102.0
55°	138.3	129.7	121.5	115.0	109.2	103.5	100.0	95.8	93.8	92.5	90.9
57.5°	122.0	114.3	108.0	101.4	95.5	91.0	87.0	84.5	82.5	80.7	78.8
60°	111.7	104.3	98.6	92.5	86.4	82.7	79.6	76.6	74.3	71.5	70.8
62.5°	100.7	94.2	89.0	83.1	77.8	74.5	71.5	68.7	65.9	61.9	60.8
65°	85.7	80.6	75.1	70.2	65.5	62.2	57.9	54.8	53.6	53.2	53.0
67.5°	72.1	67.2	62.5	57.5	53.3	50.2	48.0	47.5	46.7	46.5	45.9
70°	62.9	58.5	53.8	49.1	44.9	44.4	43.7	42.8	41.8	41.5	41.1
72.5°	54.8	50.2	45.5	41.8	40.0	39.3	38.5	37.6	37.0	36.6	36.4
75°	42.0	37.7	34.6	33.2	32.3	31.7	30.5	30.0	29.5	28.9	28.8
77.5°	30.3	27.8	26.4	25.6	24.5	23.9	23.2	22.6	22.2	22.1	21.8
80°	23.1	21.9	20.9	19.7	19.4	18.6	18.4	17.8	18.0	17.4	17.4
82.5°	17.9	16.4	15.6	15.1	14.6	14.0	13.9	13.6	13.6	13.2	13.2
85°	9.2	8.8	8.4	8.0	8.0	7.4	7.7	7.4	7.4	7.1	6.9
87.5°	3.7	3.7	3.7	4.1	4.5	4.4	4.4	4.1	4.0	4.1	4.0
90°	3.6	4.6	6.1	8.2	10.1	10.3	10.1	9.7	9.1	9.7	10.1
92.5°	10.9	13.8	20.7	30.4	39.0	39.5	33.4	26.5	22.7	20.2	18.3
95°	22.5	29.8	43.8	70.3	105.6	119.2	104.4	79.7	61.1	48.4	41.7
97.5°	31.9	40.2	57.8	94.7	153.3	203.5	213.5	186.0	152.1	119.2	97.3
100°	38.1	46.6	62.7	99.8	165.5	240.3	284.1	277.8	240.0	198.4	161.5
102.5°	43.7	52.2	67.1	100.0	160.8	241.5	310.4	337.9	329.3	298.9	259.8
105°	51.7	60.3	74.6	101.6	151.8	225.4	306.3	369.6	404.0	407.9	398.0
107.5°	59.8	68.4	82.2	105.8	147.3	208.1	279.7	346.7	398.6	430.2	444.9
110°	65.1	74.0	87.3	109.2	146.4	199.8	262.9	327.0	381.5	420.4	445.4



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	70.2	79.3	92.2	112.9	146.5	194.5	251.2	309.0	361.3	402.9	431.5
115°	78.5	86.7	99.8	118.3	147.8	188.6	236.7	286.9	333.7	373.6	404.9
117.5°	86.2	94.7	106.8	124.2	150.1	185.7	227.6	270.2	311.3	347.5	376.9
120°	91.3	99.8	111.7	128.1	151.5	184.1	222.7	261.9	299.6	331.9	359.6
122.5°	96.3	105.1	116.2	131.5	153.2	183.0	218.5	255.4	289.9	320.5	345.4
125°	103.8	112.3	123.2	136.9	155.8	181.3	212.7	245.8	277.2	303.9	326.7
127.5°	110.2	119.0	129.7	142.0	158.3	180.3	207.2	236.3	264.8	290.0	311.0
130°	114.4	122.9	133.5	145.1	160.3	179.8	203.5	230.3	256.5	280.5	300.6
132.5°	118.3	126.8	137.0	148.3	162.3	179.5	200.6	224.5	248.7	270.8	289.6
135°	123.6	132.0	141.8	152.4	164.6	179.2	196.5	216.3	236.3	256.5	273.5
137.5°	128.1	136.0	145.7	155.6	166.7	179.1	193.6	209.8	226.6	242.5	257.4
140°	130.8	138.7	147.8	157.3	167.6	178.9	191.9	205.6	220.2	234.3	247.6
142.5°	133.3	140.7	149.6	158.8	168.3	178.9	190.3	202.2	214.6	226.7	237.9
145°	137.2	143.9	152.1	160.7	169.1	178.2	188.0	197.4	207.5	216.9	225.8
147.5°	140.5	146.5	154.2	161.7	169.4	177.2	185.7	193.7	201.6	209.0	215.4
150°	142.7	148.2	155.2	162.1	169.1	176.4	183.7	191.1	197.8	204.1	209.6
152.5°	144.9	149.8	156.1	162.4	168.7	175.2	182.0	188.4	194.6	200.0	204.7
155°	147.8	152.4	157.6	162.7	167.9	173.1	178.9	184.7	189.5	194.1	197.4
157.5°	150.4	154.2	158.6	162.7	166.5	170.9	175.9	180.4	184.4	188.2	190.9
160°	152.1	155.5	159.1	162.7	165.8	169.4	173.7	177.6	181.0	184.3	186.5
162.5°	153.6	156.2	159.4	162.5	165.1	168.2	171.8	175.0	177.9	180.7	182.4
165°	155.2	157.0	159.7	161.9	163.7	165.8	168.5	171.0	173.1	175.2	176.4
167.5°	156.5	157.6	159.6	161.4	162.3	163.7	165.4	167.1	168.8	170.2	171.3
170°	157.0	157.9	159.4	160.9	161.5	162.5	163.7	165.2	166.1	167.3	167.9
172.5°	157.5	158.2	159.2	160.2	160.6	161.0	162.0	163.0	163.7	164.6	165.0
175°	157.9	158.2	158.8	159.4	159.1	159.4	159.7	160.7	160.9	161.3	161.5
177.5°	158.2	158.2	158.4	158.9	158.4	158.2	158.4	158.9	158.9	159.2	159.2
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	540.5	540.8	540.4	540.6	540.4	540.8	540.5	542.3	542.5	542.9	542.5
5°	503.6	501.3	500.8	500.3	500.8	501.3	503.6	504.5	505.4	507.0	509.7
7.5°	459.6	459.3	458.2	456.8	458.2	459.3	459.6	463.0	465.6	468.6	474.2
10°	431.3	430.2	430.1	428.7	430.1	430.2	431.3	435.6	438.7	443.0	450.6
12.5°	398.0	391.8	391.2	387.7	391.2	391.8	398.0	403.6	412.1	416.2	424.3
15°	339.0	337.8	333.8	331.3	333.8	337.8	339.0	343.6	346.7	358.1	371.2
17.5°	305.1	301.3	300.1	299.5	300.1	301.3	305.1	307.4	311.9	317.9	325.7
20°	283.4	279.9	279.3	278.9	279.3	279.9	283.4	286.1	289.6	296.1	304.3
22.5°	268.4	264.7	263.2	262.0	263.2	264.7	268.4	270.4	273.7	278.7	284.3
25°	242.7	241.3	240.6	240.1	240.6	241.3	242.7	244.7	247.8	254.7	260.5
27.5°	222.7	219.6	219.0	218.0	219.0	219.6	222.7	226.1	229.4	232.5	237.7
30°	211.2	210.3	208.9	207.7	208.9	210.3	211.2	213.0	215.2	220.4	225.5
32.5°	197.8	196.9	195.7	195.2	195.7	196.9	197.8	200.2	204.7	207.9	211.5
35°	182.9	180.1	178.9	177.2	178.9	180.1	182.9	184.9	186.6	189.3	196.0
37.5°	167.1	165.7	164.0	164.6	164.0	165.7	167.1	167.9	171.6	175.5	178.3
40°	154.9	153.9	153.5	153.3	153.5	153.9	154.9	157.5	162.0	163.7	168.0
42.5°	145.2	142.5	141.5	141.5	141.5	142.5	145.2	148.1	150.8	153.7	158.2
45°	130.4	127.9	126.1	126.3	126.1	127.9	130.4	131.4	133.8	139.5	142.0
47.5°	115.4	115.3	114.2	114.5	114.2	115.3	115.4	117.0	120.0	123.6	127.6
50°	108.1	107.0	106.2	106.4	106.2	107.0	108.1	109.5	111.2	113.0	119.3
52.5°	101.3	100.2	99.6	100.5	99.6	100.2	101.3	102.0	103.3	105.0	109.3
55°	90.0	88.8	88.6	88.4	88.6	88.8	90.0	90.9	92.5	93.8	95.8
57.5°	77.3	76.5	75.3	74.9	75.3	76.5	77.3	78.8	80.7	82.5	84.5
60°	68.3	66.7	64.7	64.6	64.7	66.7	68.3	70.8	71.5	74.3	76.6
62.5°	59.9	59.7	59.2	59.2	59.2	59.7	59.9	60.8	61.9	65.9	68.7
65°	52.6	52.4	52.6	52.8	52.6	52.4	52.6	53.0	53.2	53.6	54.8
67.5°	45.8	45.5	45.1	45.3	45.1	45.5	45.8	45.9	46.5	46.7	47.5
70°	40.6	40.5	40.3	40.3	40.3	40.5	40.6	41.1	41.5	41.8	42.8
72.5°	35.6	35.6	35.5	35.3	35.5	35.6	35.6	36.4	36.6	37.0	37.6
75°	28.6	28.2	28.2	28.2	28.2	28.2	28.6	28.8	28.9	29.5	30.0
77.5°	21.8	21.5	21.4	21.2	21.4	21.5	21.8	21.8	22.1	22.2	22.6
80°	17.2	17.0	16.8	16.8	16.8	17.0	17.2	17.4	17.4	18.0	17.8
82.5°	13.2	12.9	12.9	12.7	12.9	12.9	13.2	13.2	13.2	13.6	13.6
85°	7.1	7.2	7.1	7.4	7.1	7.2	7.1	6.9	7.1	7.4	7.4
87.5°	4.0	3.9	4.0	3.9	4.0	3.9	4.0	4.0	4.1	4.0	4.1
90°	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1	9.7	9.1	9.7
92.5°	18.1	17.1	17.3	16.9	17.3	17.1	18.1	18.3	20.2	22.7	26.5
95°	37.7	35.3	34.4	34.7	34.4	35.3	37.7	41.7	48.4	61.1	79.7
97.5°	82.7	75.3	70.9	68.3	70.9	75.3	82.7	97.3	119.2	152.1	186.0
100°	136.3	123.2	114.4	108.9	114.4	123.2	136.3	161.5	198.4	240.0	277.8
102.5°	232.4	210.1	199.1	191.7	199.1	210.1	232.4	259.8	298.9	329.3	337.9
105°	379.0	360.2	347.1	342.9	347.1	360.2	379.0	398.0	407.9	404.0	369.6
107.5°	447.3	446.3	443.6	438.0	443.6	446.3	447.3	444.9	430.2	398.6	346.7
110°	458.5	464.3	467.0	466.7	467.0	464.3	458.5	445.4	420.4	381.5	327.0



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	449.7	459.3	464.5	466.1	464.5	459.3	449.7	431.5	402.9	361.3	309.0
115°	426.5	440.5	448.4	451.2	448.4	440.5	426.5	404.9	373.6	333.7	286.9
117.5°	398.9	413.7	422.0	424.3	422.0	413.7	398.9	376.9	347.5	311.3	270.2
120°	380.9	395.2	404.0	407.1	404.0	395.2	380.9	359.6	331.9	299.6	261.9
122.5°	364.5	378.7	386.5	389.0	386.5	378.7	364.5	345.4	320.5	289.9	255.4
125°	344.4	355.9	363.5	366.0	363.5	355.9	344.4	326.7	303.9	277.2	245.8
127.5°	326.4	337.3	343.8	345.8	343.8	337.3	326.4	311.0	290.0	264.8	236.3
130°	315.5	325.8	331.9	334.3	331.9	325.8	315.5	300.6	280.5	256.5	230.3
132.5°	304.3	314.6	320.2	322.4	320.2	314.6	304.3	289.6	270.8	248.7	224.5
135°	286.5	296.6	302.1	303.3	302.1	296.6	286.5	273.5	256.5	236.3	216.3
137.5°	269.3	277.9	282.8	284.6	282.8	277.9	269.3	257.4	242.5	226.6	209.8
140°	257.4	265.3	269.8	271.6	269.8	265.3	257.4	247.6	234.3	220.2	205.6
142.5°	247.1	254.3	258.4	258.7	258.4	254.3	247.1	237.9	226.7	214.6	202.2
145°	233.0	238.2	241.3	242.1	241.3	238.2	233.0	225.8	216.9	207.5	197.4
147.5°	221.4	225.6	227.6	228.3	227.6	225.6	221.4	215.4	209.0	201.6	193.7
150°	214.1	217.8	219.6	220.0	219.6	217.8	214.1	209.6	204.1	197.8	191.1
152.5°	208.4	211.5	212.8	212.9	212.8	211.5	208.4	204.7	200.0	194.6	188.4
155°	200.8	202.9	204.1	203.5	204.1	202.9	200.8	197.4	194.1	189.5	184.7
157.5°	193.2	195.0	195.5	195.5	195.5	195.0	193.2	190.9	188.2	184.4	180.4
160°	188.6	190.1	190.5	190.5	190.5	190.1	188.6	186.5	184.3	181.0	177.6
162.5°	184.5	185.5	185.8	185.5	185.8	185.5	184.5	182.4	180.7	177.9	175.0
165°	177.6	178.9	178.9	178.6	178.9	178.9	177.6	176.4	175.2	173.1	171.0
167.5°	171.9	172.5	172.5	172.1	172.5	172.5	171.9	171.3	170.2	168.8	167.1
170°	168.2	169.1	168.8	168.2	168.8	169.1	168.2	167.9	167.3	166.1	165.2
172.5°	165.3	165.7	165.4	165.1	165.4	165.7	165.3	165.0	164.6	163.7	163.0
175°	161.5	161.9	161.5	160.9	161.5	161.9	161.5	161.5	161.3	160.9	160.7
177.5°	159.2	159.2	158.9	158.4	158.9	159.2	159.2	159.2	159.2	158.9	158.9
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	541.3	543.5	546.7	548.6	551.7	553.8	554.9	556.9	558.0	562.0	566.0
5°	511.0	514.2	519.6	524.7	530.2	535.9	540.0	544.7	549.0	556.4	564.2
7.5°	476.4	480.7	489.2	497.3	506.9	514.9	521.9	529.9	537.1	547.8	558.9
10°	450.4	458.1	469.2	476.8	489.3	497.3	508.5	517.3	527.3	541.4	553.9
12.5°	428.0	437.2	446.2	456.8	468.0	481.4	493.6	505.0	516.8	531.3	546.0
15°	387.4	400.7	414.7	425.4	440.7	454.7	469.0	484.2	498.7	516.2	535.3
17.5°	335.2	350.6	373.9	392.4	410.3	424.4	442.1	460.5	477.6	498.6	520.0
20°	311.6	322.9	338.7	363.6	390.5	405.6	423.6	443.9	463.5	486.4	509.3
22.5°	292.7	302.7	315.4	334.8	364.9	385.5	404.2	424.9	447.5	470.9	496.3
25°	265.6	272.6	285.9	301.6	322.3	356.1	376.7	397.4	422.1	447.1	476.0
27.5°	245.3	251.7	260.3	275.2	290.6	315.0	347.6	370.2	394.8	422.9	453.0
30°	229.8	237.2	246.8	257.4	274.2	293.2	325.8	352.1	376.3	405.3	437.3
32.5°	218.5	224.4	232.6	243.3	257.3	275.5	301.6	333.4	357.1	387.5	421.0
35°	200.1	206.9	213.5	223.8	235.1	251.7	271.5	305.5	329.0	359.0	392.7
37.5°	184.9	189.1	196.4	204.5	216.5	228.9	246.0	276.5	301.9	331.4	365.8
40°	173.3	178.6	184.0	193.0	202.9	214.7	231.5	254.3	283.4	312.4	345.9
42.5°	162.0	168.7	174.5	180.6	191.2	203.2	216.9	236.1	265.9	293.3	326.0
45°	148.4	152.7	158.8	165.5	174.3	184.4	196.6	213.4	241.9	265.6	296.3
47.5°	132.7	139.0	142.9	149.4	157.7	167.5	178.7	193.3	216.4	238.6	267.1
50°	121.8	128.3	134.0	139.8	147.2	156.6	166.1	180.1	198.7	222.0	248.6
52.5°	112.6	118.3	123.8	129.7	137.0	145.5	154.5	166.9	182.7	204.1	230.0
55°	100.0	103.5	109.2	115.0	121.5	129.7	138.3	148.6	162.3	180.3	201.2
57.5°	87.0	91.0	95.5	101.4	108.0	114.3	122.0	131.4	142.2	158.4	176.3
60°	79.6	82.7	86.4	92.5	98.6	104.3	111.7	119.5	129.7	143.8	159.0
62.5°	71.5	74.5	77.8	83.1	89.0	94.2	100.7	109.0	117.6	130.4	143.8
65°	57.9	62.2	65.5	70.2	75.1	80.6	85.7	92.3	100.0	110.1	122.0
67.5°	48.0	50.2	53.3	57.5	62.5	67.2	72.1	77.2	83.9	91.7	101.2
70°	43.7	44.4	44.9	49.1	53.8	58.5	62.9	67.8	73.5	80.0	88.2
72.5°	38.5	39.3	40.0	41.8	45.5	50.2	54.8	58.5	63.8	69.2	75.9
75°	30.5	31.7	32.3	33.2	34.6	37.7	42.0	45.5	48.7	52.8	58.1
77.5°	23.2	23.9	24.5	25.6	26.4	27.8	30.3	33.4	36.4	38.7	42.4
80°	18.4	18.6	19.4	19.7	20.9	21.9	23.1	25.7	28.6	29.5	32.1
82.5°	13.9	14.0	14.6	15.1	15.6	16.4	17.9	18.6	20.9	22.2	23.8
85°	7.7	7.4	8.0	8.0	8.4	8.8	9.2	10.2	10.8	12.3	12.7
87.5°	4.4	4.4	4.5	4.1	3.7	3.7	3.7	3.7	4.0	4.1	4.6
90°	10.1	10.3	10.1	8.2	6.1	4.6	3.6	3.0	2.4	1.2	0.3
92.5°	33.4	39.5	39.0	30.4	20.7	13.8	10.9	8.9	7.6	5.3	3.7
95°	104.4	119.2	105.6	70.3	43.8	29.8	22.5	17.7	14.9	11.9	10.7
97.5°	213.5	203.5	153.3	94.7	57.8	40.2	31.9	26.3	22.2	18.9	17.3
100°	284.1	240.3	165.5	99.8	62.7	46.6	38.1	31.9	27.0	24.4	23.4
102.5°	310.4	241.5	160.8	100.0	67.1	52.2	43.7	37.3	32.5	29.7	29.0
105°	306.3	225.4	151.8	101.6	74.6	60.3	51.7	45.0	40.5	38.3	37.1
107.5°	279.7	208.1	147.3	105.8	82.2	68.4	59.8	53.1	48.9	46.8	45.9
110°	262.9	199.8	146.4	109.2	87.3	74.0	65.1	58.7	54.8	53.0	51.7



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	251.2	194.5	146.5	112.9	92.2	79.3	70.2	64.1	60.4	58.3	57.1
115°	236.7	188.6	147.8	118.3	99.8	86.7	78.5	72.4	68.8	66.9	65.4
117.5°	227.6	185.7	150.1	124.2	106.8	94.7	86.2	80.3	77.1	75.3	74.0
120°	222.7	184.1	151.5	128.1	111.7	99.8	91.3	85.2	82.5	80.6	79.4
122.5°	218.5	183.0	153.2	131.5	116.2	105.1	96.3	90.3	87.3	85.5	84.6
125°	212.7	181.3	155.8	136.9	123.2	112.3	103.8	97.6	94.0	92.2	91.3
127.5°	207.2	180.3	158.3	142.0	129.7	119.0	110.2	104.4	100.4	97.8	96.6
130°	203.5	179.8	160.3	145.1	133.5	122.9	114.4	108.3	104.0	101.0	99.8
132.5°	200.6	179.5	162.3	148.3	137.0	126.8	118.3	111.9	107.5	104.2	102.7
135°	196.5	179.2	164.6	152.4	141.8	132.0	123.6	116.5	111.9	108.3	107.1
137.5°	193.6	179.1	166.7	155.6	145.7	136.0	128.1	121.2	116.3	112.7	111.2
140°	191.9	178.9	167.6	157.3	147.8	138.7	130.8	124.2	119.2	115.6	114.4
142.5°	190.3	178.9	168.3	158.8	149.6	140.7	133.3	126.8	121.9	118.6	117.5
145°	188.0	178.2	169.1	160.7	152.1	143.9	137.2	131.1	126.6	123.6	122.3
147.5°	185.7	177.2	169.4	161.7	154.2	146.5	140.5	135.4	131.2	128.3	127.4
150°	183.7	176.4	169.1	162.1	155.2	148.2	142.7	138.1	134.1	131.7	130.8
152.5°	182.0	175.2	168.7	162.4	156.1	149.8	144.9	140.5	137.1	134.7	134.2
155°	178.9	173.1	167.9	162.7	157.6	152.4	147.8	144.5	141.1	139.3	139.1
157.5°	175.9	170.9	166.5	162.7	158.6	154.2	150.4	147.7	144.8	143.4	143.0
160°	173.7	169.4	165.8	162.7	159.1	155.5	152.1	149.6	147.2	146.0	145.7
162.5°	171.8	168.2	165.1	162.5	159.4	156.2	153.6	151.4	149.5	148.2	148.4
165°	168.5	165.8	163.7	161.9	159.7	157.0	155.2	153.6	151.8	151.2	151.5
167.5°	165.4	163.7	162.3	161.4	159.6	157.6	156.5	155.4	154.2	153.7	154.0
170°	163.7	162.5	161.5	160.9	159.4	157.9	157.0	156.4	155.5	155.2	155.8
172.5°	162.0	161.0	160.6	160.2	159.2	158.2	157.5	157.1	156.2	156.4	156.7
175°	159.7	159.4	159.1	159.4	158.8	158.2	157.9	157.9	157.3	157.6	157.9
177.5°	158.4	158.2	158.4	158.9	158.4	158.2	158.2	158.2	157.7	157.9	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	566.2	566.6	569.7	571.2	573.9	575.1	576.4	576.0	576.0	576.6	581.0
5°	567.4	571.3	577.1	582.8	588.3	593.0	596.2	599.3	600.5	606.1	611.1
7.5°	565.3	572.6	582.2	590.9	601.2	609.3	616.0	622.2	626.3	634.6	643.0
10°	562.7	572.8	583.8	595.0	609.2	620.0	630.9	639.4	642.0	654.4	661.4
12.5°	557.3	570.9	584.9	599.3	613.3	628.1	640.2	648.6	658.2	669.3	682.3
15°	549.4	565.0	583.2	601.8	621.7	639.7	652.6	667.3	677.9	690.0	701.4
17.5°	538.0	558.1	581.2	602.7	625.8	645.1	662.9	676.9	684.3	691.3	692.9
20°	528.8	550.5	577.7	603.1	626.2	648.5	666.2	677.9	679.8	680.0	669.7
22.5°	519.0	543.5	572.0	598.0	625.6	650.4	664.1	669.1	661.3	648.1	628.0
25°	500.8	529.3	562.3	592.0	622.2	645.6	650.3	641.5	614.3	585.7	549.6
27.5°	481.2	513.2	548.5	581.6	613.7	628.3	618.1	586.3	537.4	494.8	443.2
30°	466.8	502.7	537.4	574.4	604.2	610.4	587.1	540.4	483.3	419.1	367.6
32.5°	450.4	487.9	526.2	564.4	589.3	583.2	544.8	487.2	420.3	357.1	308.6
35°	427.0	465.6	507.0	545.3	561.1	534.7	477.2	402.3	333.8	275.0	241.5
37.5°	399.8	442.0	484.9	520.1	519.0	475.0	396.7	319.3	261.8	227.0	203.2
40°	380.6	423.3	469.6	499.3	486.6	429.3	344.4	271.5	229.4	201.6	184.3
42.5°	362.1	404.9	451.0	474.6	452.5	382.0	297.5	240.3	205.6	184.0	169.9
45°	330.7	375.9	418.5	431.6	392.1	314.5	240.6	199.1	176.0	160.0	150.2
47.5°	300.0	344.5	383.4	383.6	330.2	255.0	202.9	172.3	152.6	140.2	133.1
50°	281.2	323.5	356.1	351.0	290.4	226.9	181.5	155.1	138.7	129.1	121.7
52.5°	260.1	301.1	329.4	315.0	256.8	199.7	162.2	140.1	126.5	118.1	111.5
55°	229.4	265.8	285.8	263.8	209.5	166.1	137.1	119.7	109.5	102.5	96.8
57.5°	199.2	229.3	241.8	216.3	172.5	137.7	116.0	102.9	92.8	87.7	84.8
60°	180.3	206.0	214.7	186.6	150.0	120.5	102.7	90.6	83.1	79.8	76.9
62.5°	161.7	182.6	186.2	160.5	130.8	105.5	90.1	79.9	75.0	71.8	69.1
65°	134.1	149.2	147.5	126.7	103.5	83.7	72.6	66.3	62.6	58.1	53.2
67.5°	110.5	119.7	114.1	98.6	79.0	65.1	57.8	53.0	48.4	44.2	43.0
70°	95.4	100.7	94.9	80.6	64.7	54.6	48.7	43.0	40.3	39.3	37.5
72.5°	81.0	82.9	76.5	64.3	52.7	45.2	39.4	36.3	34.8	34.0	32.9
75°	60.8	59.5	54.0	44.4	36.6	31.5	29.7	28.6	27.6	26.8	26.2
77.5°	42.7	40.7	35.8	29.5	25.5	23.1	22.0	21.4	20.9	20.5	19.9
80°	32.1	30.7	25.8	21.1	19.4	18.2	17.6	16.8	16.8	16.4	15.8
82.5°	23.5	22.0	17.7	15.5	14.6	13.8	13.3	12.9	12.7	12.8	12.4
85°	12.3	10.0	8.8	8.4	7.8	7.4	7.7	7.2	7.2	7.2	7.1
87.5°	4.0	3.4	3.4	3.4	3.7	4.0	4.3	4.6	4.9	4.6	4.7
90°	1.2	2.4	3.0	3.6	4.6	6.1	8.2	10.1	10.3	10.1	9.7
92.5°	5.3	7.6	8.9	10.9	13.8	20.7	30.4	39.0	39.5	33.4	26.5
95°	11.9	14.9	17.7	22.5	29.8	43.8	70.3	105.6	119.2	104.4	79.7
97.5°	18.9	22.2	26.3	31.9	40.2	57.8	94.7	153.3	203.5	213.5	186.0
100°	24.4	27.0	31.9	38.1	46.6	62.7	99.8	165.5	240.3	284.1	277.8
102.5°	29.7	32.5	37.3	43.7	52.2	67.1	100.0	160.8	241.5	310.4	337.9
105°	38.3	40.5	45.0	51.7	60.3	74.6	101.6	151.8	225.4	306.3	369.6
107.5°	46.8	48.9	53.1	59.8	68.4	82.2	105.8	147.3	208.1	279.7	346.7
110°	53.0	54.8	58.7	65.1	74.0	87.3	109.2	146.4	199.8	262.9	327.0



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	58.3	60.4	64.1	70.2	79.3	92.2	112.9	146.5	194.5	251.2	309.0
115°	66.9	68.8	72.4	78.5	86.7	99.8	118.3	147.8	188.6	236.7	286.9
117.5°	75.3	77.1	80.3	86.2	94.7	106.8	124.2	150.1	185.7	227.6	270.2
120°	80.6	82.5	85.2	91.3	99.8	111.7	128.1	151.5	184.1	222.7	261.9
122.5°	85.5	87.3	90.3	96.3	105.1	116.2	131.5	153.2	183.0	218.5	255.4
125°	92.2	94.0	97.6	103.8	112.3	123.2	136.9	155.8	181.3	212.7	245.8
127.5°	97.8	100.4	104.4	110.2	119.0	129.7	142.0	158.3	180.3	207.2	236.3
130°	101.0	104.0	108.3	114.4	122.9	133.5	145.1	160.3	179.8	203.5	230.3
132.5°	104.2	107.5	111.9	118.3	126.8	137.0	148.3	162.3	179.5	200.6	224.5
135°	108.3	111.9	116.5	123.6	132.0	141.8	152.4	164.6	179.2	196.5	216.3
137.5°	112.7	116.3	121.2	128.1	136.0	145.7	155.6	166.7	179.1	193.6	209.8
140°	115.6	119.2	124.2	130.8	138.7	147.8	157.3	167.6	178.9	191.9	205.6
142.5°	118.6	121.9	126.8	133.3	140.7	149.6	158.8	168.3	178.9	190.3	202.2
145°	123.6	126.6	131.1	137.2	143.9	152.1	160.7	169.1	178.2	188.0	197.4
147.5°	128.3	131.2	135.4	140.5	146.5	154.2	161.7	169.4	177.2	185.7	193.7
150°	131.7	134.1	138.1	142.7	148.2	155.2	162.1	169.1	176.4	183.7	191.1
152.5°	134.7	137.1	140.5	144.9	149.8	156.1	162.4	168.7	175.2	182.0	188.4
155°	139.3	141.1	144.5	147.8	152.4	157.6	162.7	167.9	173.1	178.9	184.7
157.5°	143.4	144.8	147.7	150.4	154.2	158.6	162.7	166.5	170.9	175.9	180.4
160°	146.0	147.2	149.6	152.1	155.5	159.1	162.7	165.8	169.4	173.7	177.6
162.5°	148.2	149.5	151.4	153.6	156.2	159.4	162.5	165.1	168.2	171.8	175.0
165°	151.2	151.8	153.6	155.2	157.0	159.7	161.9	163.7	165.8	168.5	171.0
167.5°	153.7	154.2	155.4	156.5	157.6	159.6	161.4	162.3	163.7	165.4	167.1
170°	155.2	155.5	156.4	157.0	157.9	159.4	160.9	161.5	162.5	163.7	165.2
172.5°	156.4	156.2	157.1	157.5	158.2	159.2	160.2	160.6	161.0	162.0	163.0
175°	157.6	157.3	157.9	157.9	158.2	158.8	159.4	159.1	159.4	159.7	160.7
177.5°	157.9	157.7	158.2	158.2	158.2	158.4	158.9	158.4	158.2	158.4	158.9
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	582.6	584.6	585.6	585.6	586.7	586.2	585.7
5°	616.0	619.7	620.6	624.1	626.6	625.9	626.2
7.5°	649.4	655.3	661.2	663.9	664.3	665.9	666.5
10°	669.9	674.8	683.9	682.6	689.4	693.4	686.9
12.5°	689.6	696.2	702.6	704.3	708.2	709.5	706.9
15°	707.4	710.9	711.3	710.3	711.5	710.5	706.8
17.5°	690.8	685.0	673.5	668.0	663.7	657.2	654.6
20°	663.2	646.4	626.8	619.0	609.8	591.9	596.2
22.5°	603.7	584.6	565.0	542.2	531.2	514.2	513.2
25°	511.3	478.2	441.8	416.4	401.5	384.5	377.0
27.5°	397.5	355.9	326.1	311.0	297.2	283.8	283.2
30°	322.7	291.4	268.4	255.5	247.0	241.3	242.5
32.5°	272.0	250.6	235.0	224.3	218.1	213.8	213.7
35°	222.4	207.7	197.7	193.2	188.7	185.6	185.8
37.5°	190.3	181.5	175.9	171.0	168.2	166.6	165.7
40°	173.8	166.6	162.3	159.4	157.0	154.9	154.5
42.5°	160.9	154.9	150.6	148.3	146.1	144.6	144.2
45°	142.8	137.8	134.0	131.4	130.4	129.1	129.1
47.5°	127.0	122.2	119.2	117.5	115.9	114.9	114.9
50°	116.4	112.6	109.9	108.9	107.5	107.0	106.8
52.5°	106.9	104.0	102.1	101.4	100.8	100.1	100.2
55°	93.8	92.3	91.5	90.9	90.0	88.8	89.5
57.5°	83.0	81.6	79.6	77.7	76.8	75.9	76.3
60°	75.3	72.6	69.8	67.7	67.1	65.3	65.3
62.5°	65.6	61.7	58.4	57.2	56.6	55.8	55.6
65°	50.5	48.9	48.1	47.4	46.9	46.9	46.6
67.5°	41.8	41.2	40.3	40.1	39.8	39.6	39.5
70°	36.9	36.2	35.8	35.6	35.2	35.4	34.8
72.5°	32.3	31.7	31.6	31.1	30.8	30.8	30.4
75°	25.4	25.4	25.2	25.1	24.6	24.5	24.6
77.5°	19.5	19.6	19.3	19.2	19.2	19.2	19.0
80°	15.7	15.8	15.7	15.4	15.2	15.4	15.2
82.5°	12.4	12.1	12.1	12.0	12.0	11.9	11.8
85°	7.1	7.2	7.1	6.9	6.9	6.9	7.1
87.5°	4.5	4.6	4.6	4.6	4.6	4.6	4.5
90°	9.1	9.7	10.1	10.1	10.1	10.1	10.1
92.5°	22.7	20.2	18.3	18.1	17.1	17.3	16.9
95°	61.1	48.4	41.7	37.7	35.3	34.4	34.7
97.5°	152.1	119.2	97.3	82.7	75.3	70.9	68.3
100°	240.0	198.4	161.5	136.3	123.2	114.4	108.9
102.5°	329.3	298.9	259.8	232.4	210.1	199.1	191.7
105°	404.0	407.9	398.0	379.0	360.2	347.1	342.9
107.5°	398.6	430.2	444.9	447.3	446.3	443.6	438.0
110°	381.5	420.4	445.4	458.5	464.3	467.0	466.7



TEST NUMBER: P331617-935

CATALOG NUMBER: S122RDIP-S290D330U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	361.3	402.9	431.5	449.7	459.3	464.5	466.1
115°	333.7	373.6	404.9	426.5	440.5	448.4	451.2
117.5°	311.3	347.5	376.9	398.9	413.7	422.0	424.3
120°	299.6	331.9	359.6	380.9	395.2	404.0	407.1
122.5°	289.9	320.5	345.4	364.5	378.7	386.5	389.0
125°	277.2	303.9	326.7	344.4	355.9	363.5	366.0
127.5°	264.8	290.0	311.0	326.4	337.3	343.8	345.8
130°	256.5	280.5	300.6	315.5	325.8	331.9	334.3
132.5°	248.7	270.8	289.6	304.3	314.6	320.2	322.4
135°	236.3	256.5	273.5	286.5	296.6	302.1	303.3
137.5°	226.6	242.5	257.4	269.3	277.9	282.8	284.6
140°	220.2	234.3	247.6	257.4	265.3	269.8	271.6
142.5°	214.6	226.7	237.9	247.1	254.3	258.4	258.7
145°	207.5	216.9	225.8	233.0	238.2	241.3	242.1
147.5°	201.6	209.0	215.4	221.4	225.6	227.6	228.3
150°	197.8	204.1	209.6	214.1	217.8	219.6	220.0
152.5°	194.6	200.0	204.7	208.4	211.5	212.8	212.9
155°	189.5	194.1	197.4	200.8	202.9	204.1	203.5
157.5°	184.4	188.2	190.9	193.2	195.0	195.5	195.5
160°	181.0	184.3	186.5	188.6	190.1	190.5	190.5
162.5°	177.9	180.7	182.4	184.5	185.5	185.8	185.5
165°	173.1	175.2	176.4	177.6	178.9	178.9	178.6
167.5°	168.8	170.2	171.3	171.9	172.5	172.5	172.1
170°	166.1	167.3	167.9	168.2	169.1	168.8	168.2
172.5°	163.7	164.6	165.0	165.3	165.7	165.4	165.1
175°	160.9	161.3	161.5	161.5	161.9	161.5	160.9
177.5°	158.9	159.2	159.2	159.2	159.2	158.9	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2

(END OF REPORT)