

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331629-935

Luminaire Tested: **S122RDIP-S290D725U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331629-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D725U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3411.4 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	89	86	83	84	80	77	75	63	61	59	47	46	45	33	32	32	25
2	85	79	73	68	76	71	66	62	56	53	50	42	40	38	29	28	27	22
3	78	69	63	57	70	63	57	52	50	46	42	38	35	33	27	25	24	19
4	72	62	54	49	64	56	49	45	44	40	36	34	31	29	24	22	21	17
5	66	55	48	42	59	50	43	38	40	35	32	31	27	25	22	20	19	15
6	61	49	42	36	54	45	38	34	36	31	28	28	25	22	20	18	17	13
7	56	45	37	32	50	41	34	30	33	28	25	25	22	20	18	16	15	12
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	14	11
9	49	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12	10
10	45	34	27	23	41	31	25	21	25	21	18	20	17	15	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9087	9087	9087	9087
5°	10149	9144	8109	9144
10°	11262	9081	7029	9081
15°	11814	8948	5538	8948
20°	10244	8751	4792	8751
25°	6716	8480	4277	8480
30°	4521	8153	3872	8153
35°	3662	7740	3493	7740
40°	3256	7290	3231	7290
45°	2948	6766	2884	6766
50°	2683	6244	2673	6244
55°	2519	5664	2488	5664
60°	2109	5134	2086	5134
65°	1780	4661	2017	4661
70°	1643	4164	1902	4164
75°	1535	3624	1759	3624
80°	1413	2985	1562	2985
85°	1315	2353	1371	2353



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	1.6
10°-20°	148.7	4.4
20°-30°	191.6	5.6
30°-40°	182.1	5.3
40°-50°	156.0	4.6
50°-60°	118.8	3.5
60°-70°	75.1	2.2
70°-80°	37.5	1.1
80°-90°	12.9	0.4
90°-100°	139.9	4.1
100°-110°	474.9	13.9
110°-120°	504.5	14.8
120°-130°	415.3	12.2
130°-140°	333.5	9.8
140°-150°	252.0	7.4
150°-160°	177.1	5.2
160°-170°	104.3	3.1
170°-180°	33.9	1.0
0°-30°	393.6	11.5
0°-40°	575.7	16.9
0°-60°	850.4	24.9
0°-90°	975.9	28.6
90°-120°	1119.3	32.8
90°-150°	2120.1	62.1
90°-180°	2435.0	71.4
0°-180°	3411.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	626	564	500	564	626	62
15°	707	535	331	535	707	191
25°	377	476	240	476	377	179
35°	186	393	177	393	186	119
45°	129	296	126	296	129	100
55°	90	201	88	201	90	79
65°	47	122	53	122	47	47
75°	25	58	28	58	25	26
85°	7	13	7	13	7	8
90°	22	1	22	1	22	12
95°	77	24	77	24	77	100
105°	758	82	758	82	758	734
115°	998	145	998	145	998	977
125°	810	202	810	202	810	732
135°	671	237	671	237	671	521
145°	536	270	536	270	536	340
155°	450	308	450	308	450	210
165°	395	335	395	335	395	113
175°	356	349	356	349	356	35
180°	350	350	350	350	350	



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	585.7	586.2	586.7	585.6	585.6	584.6	582.6	581.0	576.6	576.0	576.0
5°	626.2	625.9	626.6	624.1	620.6	619.7	616.0	611.1	606.1	600.5	599.3
7.5°	666.5	665.9	664.3	663.9	661.2	655.3	649.4	643.0	634.6	626.3	622.2
10°	686.9	693.4	689.4	682.6	683.9	674.8	669.9	661.4	654.4	642.0	639.4
12.5°	706.9	709.5	708.2	704.3	702.6	696.2	689.6	682.3	669.3	658.2	648.6
15°	706.8	710.5	711.5	710.3	711.3	710.9	707.4	701.4	690.0	677.9	667.3
17.5°	654.6	657.2	663.7	668.0	673.5	685.0	690.8	692.9	691.3	684.3	676.9
20°	596.2	591.9	609.8	619.0	626.8	646.4	663.2	669.7	680.0	679.8	677.9
22.5°	513.2	514.2	531.2	542.2	565.0	584.6	603.7	628.0	648.1	661.3	669.1
25°	377.0	384.5	401.5	416.4	441.8	478.2	511.3	549.6	585.7	614.3	641.5
27.5°	283.2	283.8	297.2	311.0	326.1	355.9	397.5	443.2	494.8	537.4	586.3
30°	242.5	241.3	247.0	255.5	268.4	291.4	322.7	367.6	419.1	483.3	540.4
32.5°	213.7	213.8	218.1	224.3	235.0	250.6	272.0	308.6	357.1	420.3	487.2
35°	185.8	185.6	188.7	193.2	197.7	207.7	222.4	241.5	275.0	333.8	402.3
37.5°	165.7	166.6	168.2	171.0	175.9	181.5	190.3	203.2	227.0	261.8	319.3
40°	154.5	154.9	157.0	159.4	162.3	166.6	173.8	184.3	201.6	229.4	271.5
42.5°	144.2	144.6	146.1	148.3	150.6	154.9	160.9	169.9	184.0	205.6	240.3
45°	129.1	129.1	130.4	131.4	134.0	137.8	142.8	150.2	160.0	176.0	199.1
47.5°	114.9	114.9	115.9	117.5	119.2	122.2	127.0	133.1	140.2	152.6	172.3
50°	106.8	107.0	107.5	108.9	109.9	112.6	116.4	121.7	129.1	138.7	155.1
52.5°	100.2	100.1	100.8	101.4	102.1	104.0	106.9	111.5	118.1	126.5	140.1
55°	89.5	88.8	90.0	90.9	91.5	92.3	93.8	96.8	102.5	109.5	119.7
57.5°	76.3	75.9	76.8	77.7	79.6	81.6	83.0	84.8	87.7	92.8	102.9
60°	65.3	65.3	67.1	67.7	69.8	72.6	75.3	76.9	79.8	83.1	90.6
62.5°	55.6	55.8	56.6	57.2	58.4	61.7	65.6	69.1	71.8	75.0	79.9
65°	46.6	46.9	46.9	47.4	48.1	48.9	50.5	53.2	58.1	62.6	66.3
67.5°	39.5	39.6	39.8	40.1	40.3	41.2	41.8	43.0	44.2	48.4	53.0
70°	34.8	35.4	35.2	35.6	35.8	36.2	36.9	37.5	39.3	40.3	43.0
72.5°	30.4	30.8	30.8	31.1	31.6	31.7	32.3	32.9	34.0	34.8	36.3
75°	24.6	24.5	24.6	25.1	25.2	25.4	25.4	26.2	26.8	27.6	28.6
77.5°	19.0	19.2	19.2	19.2	19.3	19.6	19.5	19.9	20.5	20.9	21.4
80°	15.2	15.4	15.2	15.4	15.7	15.8	15.7	15.8	16.4	16.8	16.8
82.5°	11.8	11.9	12.0	12.0	12.1	12.1	12.4	12.4	12.8	12.7	12.9
85°	7.1	6.9	6.9	6.9	7.1	7.2	7.1	7.1	7.2	7.2	7.2
87.5°	7.0	7.1	7.1	7.1	7.1	7.0	6.7	7.1	7.1	7.4	7.1
90°	22.2	22.2	22.2	22.2	22.2	21.5	20.2	21.5	22.2	22.9	22.2
92.5°	37.3	38.4	37.8	40.0	40.6	44.7	50.4	58.7	73.9	87.5	86.3
95°	76.7	76.0	78.1	83.4	92.2	107.0	135.3	176.3	230.8	263.8	233.6
97.5°	151.0	156.7	166.5	183.0	215.2	263.8	336.7	411.5	472.5	450.4	339.2
100°	240.9	253.0	272.6	301.5	357.4	438.9	531.1	614.5	628.6	531.7	366.1
102.5°	424.0	440.4	464.8	514.2	574.9	661.2	728.7	747.5	686.7	534.4	355.9
105°	758.5	767.9	796.9	838.6	880.4	902.6	893.8	817.8	677.8	498.7	335.9
107.5°	968.9	981.5	987.2	989.5	984.3	951.7	881.7	767.2	618.6	460.5	325.9
110°	1032.4	1033.1	1027.1	1014.3	985.3	930.1	844.0	723.5	581.5	442.2	323.7



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1031.4	1027.8	1016.3	994.9	954.7	891.4	799.3	683.7	555.7	430.3	324.3
115°	998.2	992.0	974.6	943.6	895.8	826.5	738.3	634.6	523.7	417.3	327.1
117.5°	938.7	933.7	915.2	882.5	833.8	768.8	688.8	597.8	503.4	411.0	331.9
120°	900.5	893.8	874.3	842.7	795.6	734.3	663.0	579.5	492.7	407.2	335.2
122.5°	860.7	855.1	837.7	806.6	764.3	708.9	641.4	565.0	483.5	405.0	339.0
125°	809.7	804.3	787.5	761.9	722.8	672.4	613.1	543.8	470.5	401.1	344.6
127.5°	765.0	760.7	746.1	722.2	688.1	641.5	585.7	523.0	458.3	398.8	350.4
130°	739.7	734.3	720.8	697.9	665.0	620.5	567.4	509.5	450.3	397.8	354.7
132.5°	713.3	708.4	696.0	673.2	640.8	599.0	550.2	496.5	443.8	397.3	359.0
135°	671.1	668.3	656.3	634.0	605.0	567.4	523.0	478.5	434.8	396.4	364.1
137.5°	629.6	625.5	614.9	595.8	569.4	536.6	501.3	464.2	428.4	396.3	368.7
140°	601.1	597.0	586.9	569.4	547.9	518.2	487.3	455.0	424.7	395.7	370.8
142.5°	572.5	571.7	562.7	546.8	526.3	501.5	474.9	447.5	420.9	395.7	372.5
145°	535.7	533.7	527.0	515.6	499.4	479.9	459.0	436.8	415.9	394.4	374.2
147.5°	504.9	503.7	499.1	490.0	476.6	462.4	446.1	428.6	410.9	392.0	374.8
150°	486.6	485.9	481.9	473.8	463.7	451.6	437.5	422.7	406.5	390.4	374.2
152.5°	471.0	470.9	467.9	460.9	453.0	442.5	430.5	416.7	402.8	387.7	373.2
155°	450.3	451.6	448.9	444.2	436.8	429.4	419.3	408.5	395.7	383.0	371.5
157.5°	432.7	432.7	431.4	427.5	422.2	416.5	408.0	399.0	389.2	378.2	368.4
160°	421.3	421.3	420.7	417.3	412.6	407.9	400.5	393.0	384.4	374.9	366.8
162.5°	410.5	411.1	410.4	408.1	403.5	399.8	393.5	387.1	380.0	372.2	365.2
165°	395.1	395.7	395.7	393.0	390.4	387.7	383.0	378.2	372.9	366.8	362.1
167.5°	380.8	381.6	381.8	380.3	379.1	376.6	373.4	369.8	365.8	362.1	359.0
170°	372.2	373.5	374.2	372.2	371.5	370.1	367.5	365.5	362.1	359.4	357.4
172.5°	365.2	366.0	366.7	365.8	365.1	364.3	362.1	360.6	358.3	356.2	355.2
175°	356.0	357.4	358.1	357.4	357.4	356.7	356.0	355.3	353.4	352.7	352.0
177.5°	350.5	351.6	352.1	352.1	352.1	352.1	351.6	351.6	350.5	350.0	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	576.4	575.1	573.9	571.2	569.7	566.6	566.2	566.0	562.0	558.0	556.9
5°	596.2	593.0	588.3	582.8	577.1	571.3	567.4	564.2	556.4	549.0	544.7
7.5°	616.0	609.3	601.2	590.9	582.2	572.6	565.3	558.9	547.8	537.1	529.9
10°	630.9	620.0	609.2	595.0	583.8	572.8	562.7	553.9	541.4	527.3	517.3
12.5°	640.2	628.1	613.3	599.3	584.9	570.9	557.3	546.0	531.3	516.8	505.0
15°	652.6	639.7	621.7	601.8	583.2	565.0	549.4	535.3	516.2	498.7	484.2
17.5°	662.9	645.1	625.8	602.7	581.2	558.1	538.0	520.0	498.6	477.6	460.5
20°	666.2	648.5	626.2	603.1	577.7	550.5	528.8	509.3	486.4	463.5	443.9
22.5°	664.1	650.4	625.6	598.0	572.0	543.5	519.0	496.3	470.9	447.5	424.9
25°	650.3	645.6	622.2	592.0	562.3	529.3	500.8	476.0	447.1	422.1	397.4
27.5°	618.1	628.3	613.7	581.6	548.5	513.2	481.2	453.0	422.9	394.8	370.2
30°	587.1	610.4	604.2	574.4	537.4	502.7	466.8	437.3	405.3	376.3	352.1
32.5°	544.8	583.2	589.3	564.4	526.2	487.9	450.4	421.0	387.5	357.1	333.4
35°	477.2	534.7	561.1	545.3	507.0	465.6	427.0	392.7	359.0	329.0	305.5
37.5°	396.7	475.0	519.0	520.1	484.9	442.0	399.8	365.8	331.4	301.9	276.5
40°	344.4	429.3	486.6	499.3	469.6	423.3	380.6	345.9	312.4	283.4	254.3
42.5°	297.5	382.0	452.5	474.6	451.0	404.9	362.1	326.0	293.3	265.9	236.1
45°	240.6	314.5	392.1	431.6	418.5	375.9	330.7	296.3	265.6	241.9	213.4
47.5°	202.9	255.0	330.2	383.6	383.4	344.5	300.0	267.1	238.6	216.4	193.3
50°	181.5	226.9	290.4	351.0	356.1	323.5	281.2	248.6	222.0	198.7	180.1
52.5°	162.2	199.7	256.8	315.0	329.4	301.1	260.1	230.0	204.1	182.7	166.9
55°	137.1	166.1	209.5	263.8	285.8	265.8	229.4	201.2	180.3	162.3	148.6
57.5°	116.0	137.7	172.5	216.3	241.8	229.3	199.2	176.3	158.4	142.2	131.4
60°	102.7	120.5	150.0	186.6	214.7	206.0	180.3	159.0	143.8	129.7	119.5
62.5°	90.1	105.5	130.8	160.5	186.2	182.6	161.7	143.8	130.4	117.6	109.0
65°	72.6	83.7	103.5	126.7	147.5	149.2	134.1	122.0	110.1	100.0	92.3
67.5°	57.8	65.1	79.0	98.6	114.1	119.7	110.5	101.2	91.7	83.9	77.2
70°	48.7	54.6	64.7	80.6	94.9	100.7	95.4	88.2	80.0	73.5	67.8
72.5°	39.4	45.2	52.7	64.3	76.5	82.9	81.0	75.9	69.2	63.8	58.5
75°	29.7	31.5	36.6	44.4	54.0	59.5	60.8	58.1	52.8	48.7	45.5
77.5°	22.0	23.1	25.5	29.5	35.8	40.7	42.7	42.4	38.7	36.4	33.4
80°	17.6	18.2	19.4	21.1	25.8	30.7	32.1	32.1	29.5	28.6	25.7
82.5°	13.3	13.8	14.6	15.5	17.7	22.0	23.5	23.8	22.2	20.9	18.6
85°	7.7	7.4	7.8	8.4	8.8	10.0	12.3	12.7	12.3	10.8	10.2
87.5°	6.3	5.5	4.8	4.3	4.1	4.0	4.3	4.6	4.5	4.5	4.5
90°	18.2	13.4	10.1	8.1	6.7	5.4	2.7	0.7	2.7	5.4	6.7
92.5°	67.2	45.8	30.6	24.2	19.6	16.7	11.9	8.2	11.9	16.7	19.6
95°	155.5	96.9	66.0	49.8	39.0	33.0	26.3	23.6	26.3	33.0	39.0
97.5°	209.5	127.9	88.9	70.7	58.3	49.2	42.0	38.4	42.0	49.2	58.3
100°	220.8	138.6	103.0	84.1	70.7	59.9	53.8	51.8	53.8	59.9	70.7
102.5°	221.3	148.4	115.4	96.5	82.5	71.7	65.7	64.2	65.7	71.7	82.5
105°	224.8	164.9	133.3	114.4	99.6	89.5	84.8	82.1	84.8	89.5	99.6
107.5°	234.1	181.8	151.2	132.2	117.5	108.2	103.7	101.5	103.7	108.2	117.5
110°	241.6	193.1	163.6	144.0	129.9	121.1	117.1	114.4	117.1	121.1	129.9



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	249.7	204.0	175.4	155.3	141.7	133.5	129.0	126.2	129.0	133.5	141.7
115°	261.8	220.8	191.8	173.7	160.1	152.1	148.1	144.7	148.1	152.1	160.1
117.5°	274.7	236.3	209.5	190.6	177.7	170.6	166.5	163.8	166.5	170.6	177.7
120°	283.4	247.0	220.8	201.9	188.5	182.4	178.4	175.6	178.4	182.4	188.5
122.5°	290.9	257.3	232.6	213.2	199.8	193.1	189.2	187.0	189.2	193.1	199.8
125°	302.9	272.6	248.3	229.5	216.0	207.9	204.0	201.9	204.0	207.9	216.0
127.5°	314.0	286.9	263.3	243.9	231.0	222.1	216.5	213.8	216.5	222.1	231.0
130°	321.1	295.5	271.9	253.0	239.6	230.1	223.4	220.8	223.4	230.1	239.6
132.5°	328.0	303.0	280.5	261.7	247.7	237.7	230.5	227.2	230.5	237.7	247.7
135°	337.2	313.7	292.1	273.3	257.8	247.7	239.6	236.9	239.6	247.7	257.8
137.5°	344.2	322.3	301.0	283.5	268.1	257.4	249.3	246.1	249.3	257.4	268.1
140°	347.9	327.1	306.9	289.4	274.6	263.8	255.7	253.0	255.7	263.8	274.6
142.5°	351.2	330.9	311.3	294.8	280.5	269.8	262.3	260.0	262.3	269.8	280.5
145°	355.3	336.6	318.3	303.5	290.1	280.0	273.3	270.5	273.3	280.0	290.1
147.5°	357.7	341.1	324.0	310.8	299.6	290.3	283.9	281.9	283.9	290.3	299.6
150°	358.7	343.3	327.8	315.6	305.6	296.8	291.4	289.4	291.4	296.8	305.6
152.5°	359.3	345.4	331.6	320.5	310.9	303.2	297.9	297.0	297.9	303.2	310.9
155°	360.1	348.6	337.2	327.1	319.7	312.3	308.2	307.5	308.2	312.3	319.7
157.5°	360.1	350.9	341.2	332.8	326.8	320.4	317.1	316.5	317.1	320.4	326.8
160°	360.1	352.0	343.9	336.6	331.1	325.7	323.0	322.4	323.0	325.7	331.1
162.5°	359.6	352.6	345.5	339.8	334.9	330.6	327.9	328.3	327.9	330.6	334.9
165°	358.1	353.4	347.3	343.3	339.9	335.9	334.5	335.2	334.5	335.9	339.9
167.5°	357.1	353.2	348.8	346.2	343.8	341.2	340.0	340.9	340.0	341.2	343.8
170°	356.0	352.7	349.3	347.3	345.9	343.9	343.3	344.6	343.3	343.9	345.9
172.5°	354.4	352.1	349.8	348.4	347.6	345.5	345.9	346.7	345.9	345.5	347.6
175°	352.7	351.3	350.0	349.3	349.3	347.9	348.6	349.3	348.6	347.9	349.3
177.5°	351.6	350.5	350.0	350.0	350.0	348.9	349.5	350.5	349.5	348.9	350.0
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	554.9	553.8	551.7	548.6	546.7	543.5	541.3	542.5	542.9	542.5	542.3
5°	540.0	535.9	530.2	524.7	519.6	514.2	511.0	509.7	507.0	505.4	504.5
7.5°	521.9	514.9	506.9	497.3	489.2	480.7	476.4	474.2	468.6	465.6	463.0
10°	508.5	497.3	489.3	476.8	469.2	458.1	450.4	450.6	443.0	438.7	435.6
12.5°	493.6	481.4	468.0	456.8	446.2	437.2	428.0	424.3	416.2	412.1	403.6
15°	469.0	454.7	440.7	425.4	414.7	400.7	387.4	371.2	358.1	346.7	343.6
17.5°	442.1	424.4	410.3	392.4	373.9	350.6	335.2	325.7	317.9	311.9	307.4
20°	423.6	405.6	390.5	363.6	338.7	322.9	311.6	304.3	296.1	289.6	286.1
22.5°	404.2	385.5	364.9	334.8	315.4	302.7	292.7	284.3	278.7	273.7	270.4
25°	376.7	356.1	322.3	301.6	285.9	272.6	265.6	260.5	254.7	247.8	244.7
27.5°	347.6	315.0	290.6	275.2	260.3	251.7	245.3	237.7	232.5	229.4	226.1
30°	325.8	293.2	274.2	257.4	246.8	237.2	229.8	225.5	220.4	215.2	213.0
32.5°	301.6	275.5	257.3	243.3	232.6	224.4	218.5	211.5	207.9	204.7	200.2
35°	271.5	251.7	235.1	223.8	213.5	206.9	200.1	196.0	189.3	186.6	184.9
37.5°	246.0	228.9	216.5	204.5	196.4	189.1	184.9	178.3	175.5	171.6	167.9
40°	231.5	214.7	202.9	193.0	184.0	178.6	173.3	168.0	163.7	162.0	157.5
42.5°	216.9	203.2	191.2	180.6	174.5	168.7	162.0	158.2	153.7	150.8	148.1
45°	196.6	184.4	174.3	165.5	158.8	152.7	148.4	142.0	139.5	133.8	131.4
47.5°	178.7	167.5	157.7	149.4	142.9	139.0	132.7	127.6	123.6	120.0	117.0
50°	166.1	156.6	147.2	139.8	134.0	128.3	121.8	119.3	113.0	111.2	109.5
52.5°	154.5	145.5	137.0	129.7	123.8	118.3	112.6	109.3	105.0	103.3	102.0
55°	138.3	129.7	121.5	115.0	109.2	103.5	100.0	95.8	93.8	92.5	90.9
57.5°	122.0	114.3	108.0	101.4	95.5	91.0	87.0	84.5	82.5	80.7	78.8
60°	111.7	104.3	98.6	92.5	86.4	82.7	79.6	76.6	74.3	71.5	70.8
62.5°	100.7	94.2	89.0	83.1	77.8	74.5	71.5	68.7	65.9	61.9	60.8
65°	85.7	80.6	75.1	70.2	65.5	62.2	57.9	54.8	53.6	53.2	53.0
67.5°	72.1	67.2	62.5	57.5	53.3	50.2	48.0	47.5	46.7	46.5	45.9
70°	62.9	58.5	53.8	49.1	44.9	44.4	43.7	42.8	41.8	41.5	41.1
72.5°	54.8	50.2	45.5	41.8	40.0	39.3	38.5	37.6	37.0	36.6	36.4
75°	42.0	37.7	34.6	33.2	32.3	31.7	30.5	30.0	29.5	28.9	28.8
77.5°	30.3	27.8	26.4	25.6	24.5	23.9	23.2	22.6	22.2	22.1	21.8
80°	23.1	21.9	20.9	19.7	19.4	18.6	18.4	17.8	18.0	17.4	17.4
82.5°	17.9	16.4	15.6	15.1	14.6	14.0	13.9	13.6	13.6	13.2	13.2
85°	9.2	8.8	8.4	8.0	8.0	7.4	7.7	7.4	7.4	7.1	6.9
87.5°	4.6	4.8	5.2	6.1	7.0	6.9	6.8	6.5	6.2	6.5	6.5
90°	8.1	10.1	13.4	18.2	22.2	22.9	22.2	21.5	20.2	21.5	22.2
92.5°	24.2	30.6	45.8	67.2	86.3	87.5	73.9	58.7	50.4	44.7	40.6
95°	49.8	66.0	96.9	155.5	233.6	263.8	230.8	176.3	135.3	107.0	92.2
97.5°	70.7	88.9	127.9	209.5	339.2	450.4	472.5	411.5	336.7	263.8	215.2
100°	84.1	103.0	138.6	220.8	366.1	531.7	628.6	614.5	531.1	438.9	357.4
102.5°	96.5	115.4	148.4	221.3	355.9	534.4	686.7	747.5	728.7	661.2	574.9
105°	114.4	133.3	164.9	224.8	335.9	498.7	677.8	817.8	893.8	902.6	880.4
107.5°	132.2	151.2	181.8	234.1	325.9	460.5	618.6	767.2	881.7	951.7	984.3
110°	144.0	163.6	193.1	241.6	323.7	442.2	581.5	723.5	844.0	930.1	985.3



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	155.3	175.4	204.0	249.7	324.3	430.3	555.7	683.7	799.3	891.4	954.7
115°	173.7	191.8	220.8	261.8	327.1	417.3	523.7	634.6	738.3	826.5	895.8
117.5°	190.6	209.5	236.3	274.7	331.9	411.0	503.4	597.8	688.8	768.8	833.8
120°	201.9	220.8	247.0	283.4	335.2	407.2	492.7	579.5	663.0	734.3	795.6
122.5°	213.2	232.6	257.3	290.9	339.0	405.0	483.5	565.0	641.4	708.9	764.3
125°	229.5	248.3	272.6	302.9	344.6	401.1	470.5	543.8	613.1	672.4	722.8
127.5°	243.9	263.3	286.9	314.0	350.4	398.8	458.3	523.0	585.7	641.5	688.1
130°	253.0	271.9	295.5	321.1	354.7	397.8	450.3	509.5	567.4	620.5	665.0
132.5°	261.7	280.5	303.0	328.0	359.0	397.3	443.8	496.5	550.2	599.0	640.8
135°	273.3	292.1	313.7	337.2	364.1	396.4	434.8	478.5	523.0	567.4	605.0
137.5°	283.5	301.0	322.3	344.2	368.7	396.3	428.4	464.2	501.3	536.6	569.4
140°	289.4	306.9	327.1	347.9	370.8	395.7	424.7	455.0	487.3	518.2	547.9
142.5°	294.8	311.3	330.9	351.2	372.5	395.7	420.9	447.5	474.9	501.5	526.3
145°	303.5	318.3	336.6	355.3	374.2	394.4	415.9	436.8	459.0	479.9	499.4
147.5°	310.8	324.0	341.1	357.7	374.8	392.0	410.9	428.6	446.1	462.4	476.6
150°	315.6	327.8	343.3	358.7	374.2	390.4	406.5	422.7	437.5	451.6	463.7
152.5°	320.5	331.6	345.4	359.3	373.2	387.7	402.8	416.7	430.5	442.5	453.0
155°	327.1	337.2	348.6	360.1	371.5	383.0	395.7	408.5	419.3	429.4	436.8
157.5°	332.8	341.2	350.9	360.1	368.4	378.2	389.2	399.0	408.0	416.5	422.2
160°	336.6	343.9	352.0	360.1	366.8	374.9	384.4	393.0	400.5	407.9	412.6
162.5°	339.8	345.5	352.6	359.6	365.2	372.2	380.0	387.1	393.5	399.8	403.5
165°	343.3	347.3	353.4	358.1	362.1	366.8	372.9	378.2	383.0	387.7	390.4
167.5°	346.2	348.8	353.2	357.1	359.0	362.1	365.8	369.8	373.4	376.6	379.1
170°	347.3	349.3	352.7	356.0	357.4	359.4	362.1	365.5	367.5	370.1	371.5
172.5°	348.4	349.8	352.1	354.4	355.2	356.2	358.3	360.6	362.1	364.3	365.1
175°	349.3	350.0	351.3	352.7	352.0	352.7	353.4	355.3	356.0	356.7	357.4
177.5°	350.0	350.0	350.5	351.6	350.5	350.0	350.5	351.6	351.6	352.1	352.1
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	540.5	540.8	540.4	540.6	540.4	540.8	540.5	542.3	542.5	542.9	542.5
5°	503.6	501.3	500.8	500.3	500.8	501.3	503.6	504.5	505.4	507.0	509.7
7.5°	459.6	459.3	458.2	456.8	458.2	459.3	459.6	463.0	465.6	468.6	474.2
10°	431.3	430.2	430.1	428.7	430.1	430.2	431.3	435.6	438.7	443.0	450.6
12.5°	398.0	391.8	391.2	387.7	391.2	391.8	398.0	403.6	412.1	416.2	424.3
15°	339.0	337.8	333.8	331.3	333.8	337.8	339.0	343.6	346.7	358.1	371.2
17.5°	305.1	301.3	300.1	299.5	300.1	301.3	305.1	307.4	311.9	317.9	325.7
20°	283.4	279.9	279.3	278.9	279.3	279.9	283.4	286.1	289.6	296.1	304.3
22.5°	268.4	264.7	263.2	262.0	263.2	264.7	268.4	270.4	273.7	278.7	284.3
25°	242.7	241.3	240.6	240.1	240.6	241.3	242.7	244.7	247.8	254.7	260.5
27.5°	222.7	219.6	219.0	218.0	219.0	219.6	222.7	226.1	229.4	232.5	237.7
30°	211.2	210.3	208.9	207.7	208.9	210.3	211.2	213.0	215.2	220.4	225.5
32.5°	197.8	196.9	195.7	195.2	195.7	196.9	197.8	200.2	204.7	207.9	211.5
35°	182.9	180.1	178.9	177.2	178.9	180.1	182.9	184.9	186.6	189.3	196.0
37.5°	167.1	165.7	164.0	164.6	164.0	165.7	167.1	167.9	171.6	175.5	178.3
40°	154.9	153.9	153.5	153.3	153.5	153.9	154.9	157.5	162.0	163.7	168.0
42.5°	145.2	142.5	141.5	141.5	141.5	142.5	145.2	148.1	150.8	153.7	158.2
45°	130.4	127.9	126.1	126.3	126.1	127.9	130.4	131.4	133.8	139.5	142.0
47.5°	115.4	115.3	114.2	114.5	114.2	115.3	115.4	117.0	120.0	123.6	127.6
50°	108.1	107.0	106.2	106.4	106.2	107.0	108.1	109.5	111.2	113.0	119.3
52.5°	101.3	100.2	99.6	100.5	99.6	100.2	101.3	102.0	103.3	105.0	109.3
55°	90.0	88.8	88.6	88.4	88.6	88.8	90.0	90.9	92.5	93.8	95.8
57.5°	77.3	76.5	75.3	74.9	75.3	76.5	77.3	78.8	80.7	82.5	84.5
60°	68.3	66.7	64.7	64.6	64.7	66.7	68.3	70.8	71.5	74.3	76.6
62.5°	59.9	59.7	59.2	59.2	59.2	59.7	59.9	60.8	61.9	65.9	68.7
65°	52.6	52.4	52.6	52.8	52.6	52.4	52.6	53.0	53.2	53.6	54.8
67.5°	45.8	45.5	45.1	45.3	45.1	45.5	45.8	45.9	46.5	46.7	47.5
70°	40.6	40.5	40.3	40.3	40.3	40.5	40.6	41.1	41.5	41.8	42.8
72.5°	35.6	35.6	35.5	35.3	35.5	35.6	35.6	36.4	36.6	37.0	37.6
75°	28.6	28.2	28.2	28.2	28.2	28.2	28.6	28.8	28.9	29.5	30.0
77.5°	21.8	21.5	21.4	21.2	21.4	21.5	21.8	21.8	22.1	22.2	22.6
80°	17.2	17.0	16.8	16.8	16.8	17.0	17.2	17.4	17.4	18.0	17.8
82.5°	13.2	12.9	12.9	12.7	12.9	12.9	13.2	13.2	13.2	13.6	13.6
85°	7.1	7.2	7.1	7.4	7.1	7.2	7.1	6.9	7.1	7.4	7.4
87.5°	6.5	6.3	6.5	6.3	6.5	6.3	6.5	6.5	6.5	6.2	6.5
90°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	21.5	20.2	21.5
92.5°	40.0	37.8	38.4	37.3	38.4	37.8	40.0	40.6	44.7	50.4	58.7
95°	83.4	78.1	76.0	76.7	76.0	78.1	83.4	92.2	107.0	135.3	176.3
97.5°	183.0	166.5	156.7	151.0	156.7	166.5	183.0	215.2	263.8	336.7	411.5
100°	301.5	272.6	253.0	240.9	253.0	272.6	301.5	357.4	438.9	531.1	614.5
102.5°	514.2	464.8	440.4	424.0	440.4	464.8	514.2	574.9	661.2	728.7	747.5
105°	838.6	796.9	767.9	758.5	767.9	796.9	838.6	880.4	902.6	893.8	817.8
107.5°	989.5	987.2	981.5	968.9	981.5	987.2	989.5	984.3	951.7	881.7	767.2
110°	1014.3	1027.1	1033.1	1032.4	1033.1	1027.1	1014.3	985.3	930.1	844.0	723.5



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	994.9	1016.3	1027.8	1031.4	1027.8	1016.3	994.9	954.7	891.4	799.3	683.7
115°	943.6	974.6	992.0	998.2	992.0	974.6	943.6	895.8	826.5	738.3	634.6
117.5°	882.5	915.2	933.7	938.7	933.7	915.2	882.5	833.8	768.8	688.8	597.8
120°	842.7	874.3	893.8	900.5	893.8	874.3	842.7	795.6	734.3	663.0	579.5
122.5°	806.6	837.7	855.1	860.7	855.1	837.7	806.6	764.3	708.9	641.4	565.0
125°	761.9	787.5	804.3	809.7	804.3	787.5	761.9	722.8	672.4	613.1	543.8
127.5°	722.2	746.1	760.7	765.0	760.7	746.1	722.2	688.1	641.5	585.7	523.0
130°	697.9	720.8	734.3	739.7	734.3	720.8	697.9	665.0	620.5	567.4	509.5
132.5°	673.2	696.0	708.4	713.3	708.4	696.0	673.2	640.8	599.0	550.2	496.5
135°	634.0	656.3	668.3	671.1	668.3	656.3	634.0	605.0	567.4	523.0	478.5
137.5°	595.8	614.9	625.5	629.6	625.5	614.9	595.8	569.4	536.6	501.3	464.2
140°	569.4	586.9	597.0	601.1	597.0	586.9	569.4	547.9	518.2	487.3	455.0
142.5°	546.8	562.7	571.7	572.5	571.7	562.7	546.8	526.3	501.5	474.9	447.5
145°	515.6	527.0	533.7	535.7	533.7	527.0	515.6	499.4	479.9	459.0	436.8
147.5°	490.0	499.1	503.7	504.9	503.7	499.1	490.0	476.6	462.4	446.1	428.6
150°	473.8	481.9	485.9	486.6	485.9	481.9	473.8	463.7	451.6	437.5	422.7
152.5°	460.9	467.9	470.9	471.0	470.9	467.9	460.9	453.0	442.5	430.5	416.7
155°	444.2	448.9	451.6	450.3	451.6	448.9	444.2	436.8	429.4	419.3	408.5
157.5°	427.5	431.4	432.7	432.7	432.7	431.4	427.5	422.2	416.5	408.0	399.0
160°	417.3	420.7	421.3	421.3	421.3	420.7	417.3	412.6	407.9	400.5	393.0
162.5°	408.1	410.4	411.1	410.5	411.1	410.4	408.1	403.5	399.8	393.5	387.1
165°	393.0	395.7	395.7	395.1	395.7	395.7	393.0	390.4	387.7	383.0	378.2
167.5°	380.3	381.8	381.6	380.8	381.6	381.8	380.3	379.1	376.6	373.4	369.8
170°	372.2	374.2	373.5	372.2	373.5	374.2	372.2	371.5	370.1	367.5	365.5
172.5°	365.8	366.7	366.0	365.2	366.0	366.7	365.8	365.1	364.3	362.1	360.6
175°	357.4	358.1	357.4	356.0	357.4	358.1	357.4	357.4	356.7	356.0	355.3
177.5°	352.1	352.1	351.6	350.5	351.6	352.1	352.1	352.1	352.1	351.6	351.6
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	541.3	543.5	546.7	548.6	551.7	553.8	554.9	556.9	558.0	562.0	566.0
5°	511.0	514.2	519.6	524.7	530.2	535.9	540.0	544.7	549.0	556.4	564.2
7.5°	476.4	480.7	489.2	497.3	506.9	514.9	521.9	529.9	537.1	547.8	558.9
10°	450.4	458.1	469.2	476.8	489.3	497.3	508.5	517.3	527.3	541.4	553.9
12.5°	428.0	437.2	446.2	456.8	468.0	481.4	493.6	505.0	516.8	531.3	546.0
15°	387.4	400.7	414.7	425.4	440.7	454.7	469.0	484.2	498.7	516.2	535.3
17.5°	335.2	350.6	373.9	392.4	410.3	424.4	442.1	460.5	477.6	498.6	520.0
20°	311.6	322.9	338.7	363.6	390.5	405.6	423.6	443.9	463.5	486.4	509.3
22.5°	292.7	302.7	315.4	334.8	364.9	385.5	404.2	424.9	447.5	470.9	496.3
25°	265.6	272.6	285.9	301.6	322.3	356.1	376.7	397.4	422.1	447.1	476.0
27.5°	245.3	251.7	260.3	275.2	290.6	315.0	347.6	370.2	394.8	422.9	453.0
30°	229.8	237.2	246.8	257.4	274.2	293.2	325.8	352.1	376.3	405.3	437.3
32.5°	218.5	224.4	232.6	243.3	257.3	275.5	301.6	333.4	357.1	387.5	421.0
35°	200.1	206.9	213.5	223.8	235.1	251.7	271.5	305.5	329.0	359.0	392.7
37.5°	184.9	189.1	196.4	204.5	216.5	228.9	246.0	276.5	301.9	331.4	365.8
40°	173.3	178.6	184.0	193.0	202.9	214.7	231.5	254.3	283.4	312.4	345.9
42.5°	162.0	168.7	174.5	180.6	191.2	203.2	216.9	236.1	265.9	293.3	326.0
45°	148.4	152.7	158.8	165.5	174.3	184.4	196.6	213.4	241.9	265.6	296.3
47.5°	132.7	139.0	142.9	149.4	157.7	167.5	178.7	193.3	216.4	238.6	267.1
50°	121.8	128.3	134.0	139.8	147.2	156.6	166.1	180.1	198.7	222.0	248.6
52.5°	112.6	118.3	123.8	129.7	137.0	145.5	154.5	166.9	182.7	204.1	230.0
55°	100.0	103.5	109.2	115.0	121.5	129.7	138.3	148.6	162.3	180.3	201.2
57.5°	87.0	91.0	95.5	101.4	108.0	114.3	122.0	131.4	142.2	158.4	176.3
60°	79.6	82.7	86.4	92.5	98.6	104.3	111.7	119.5	129.7	143.8	159.0
62.5°	71.5	74.5	77.8	83.1	89.0	94.2	100.7	109.0	117.6	130.4	143.8
65°	57.9	62.2	65.5	70.2	75.1	80.6	85.7	92.3	100.0	110.1	122.0
67.5°	48.0	50.2	53.3	57.5	62.5	67.2	72.1	77.2	83.9	91.7	101.2
70°	43.7	44.4	44.9	49.1	53.8	58.5	62.9	67.8	73.5	80.0	88.2
72.5°	38.5	39.3	40.0	41.8	45.5	50.2	54.8	58.5	63.8	69.2	75.9
75°	30.5	31.7	32.3	33.2	34.6	37.7	42.0	45.5	48.7	52.8	58.1
77.5°	23.2	23.9	24.5	25.6	26.4	27.8	30.3	33.4	36.4	38.7	42.4
80°	18.4	18.6	19.4	19.7	20.9	21.9	23.1	25.7	28.6	29.5	32.1
82.5°	13.9	14.0	14.6	15.1	15.6	16.4	17.9	18.6	20.9	22.2	23.8
85°	7.7	7.4	8.0	8.0	8.4	8.8	9.2	10.2	10.8	12.3	12.7
87.5°	6.8	6.9	7.0	6.1	5.2	4.8	4.6	4.5	4.5	4.5	4.6
90°	22.2	22.9	22.2	18.2	13.4	10.1	8.1	6.7	5.4	2.7	0.7
92.5°	73.9	87.5	86.3	67.2	45.8	30.6	24.2	19.6	16.7	11.9	8.2
95°	230.8	263.8	233.6	155.5	96.9	66.0	49.8	39.0	33.0	26.3	23.6
97.5°	472.5	450.4	339.2	209.5	127.9	88.9	70.7	58.3	49.2	42.0	38.4
100°	628.6	531.7	366.1	220.8	138.6	103.0	84.1	70.7	59.9	53.8	51.8
102.5°	686.7	534.4	355.9	221.3	148.4	115.4	96.5	82.5	71.7	65.7	64.2
105°	677.8	498.7	335.9	224.8	164.9	133.3	114.4	99.6	89.5	84.8	82.1
107.5°	618.6	460.5	325.9	234.1	181.8	151.2	132.2	117.5	108.2	103.7	101.5
110°	581.5	442.2	323.7	241.6	193.1	163.6	144.0	129.9	121.1	117.1	114.4



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	555.7	430.3	324.3	249.7	204.0	175.4	155.3	141.7	133.5	129.0	126.2
115°	523.7	417.3	327.1	261.8	220.8	191.8	173.7	160.1	152.1	148.1	144.7
117.5°	503.4	411.0	331.9	274.7	236.3	209.5	190.6	177.7	170.6	166.5	163.8
120°	492.7	407.2	335.2	283.4	247.0	220.8	201.9	188.5	182.4	178.4	175.6
122.5°	483.5	405.0	339.0	290.9	257.3	232.6	213.2	199.8	193.1	189.2	187.0
125°	470.5	401.1	344.6	302.9	272.6	248.3	229.5	216.0	207.9	204.0	201.9
127.5°	458.3	398.8	350.4	314.0	286.9	263.3	243.9	231.0	222.1	216.5	213.8
130°	450.3	397.8	354.7	321.1	295.5	271.9	253.0	239.6	230.1	223.4	220.8
132.5°	443.8	397.3	359.0	328.0	303.0	280.5	261.7	247.7	237.7	230.5	227.2
135°	434.8	396.4	364.1	337.2	313.7	292.1	273.3	257.8	247.7	239.6	236.9
137.5°	428.4	396.3	368.7	344.2	322.3	301.0	283.5	268.1	257.4	249.3	246.1
140°	424.7	395.7	370.8	347.9	327.1	306.9	289.4	274.6	263.8	255.7	253.0
142.5°	420.9	395.7	372.5	351.2	330.9	311.3	294.8	280.5	269.8	262.3	260.0
145°	415.9	394.4	374.2	355.3	336.6	318.3	303.5	290.1	280.0	273.3	270.5
147.5°	410.9	392.0	374.8	357.7	341.1	324.0	310.8	299.6	290.3	283.9	281.9
150°	406.5	390.4	374.2	358.7	343.3	327.8	315.6	305.6	296.8	291.4	289.4
152.5°	402.8	387.7	373.2	359.3	345.4	331.6	320.5	310.9	303.2	297.9	297.0
155°	395.7	383.0	371.5	360.1	348.6	337.2	327.1	319.7	312.3	308.2	307.5
157.5°	389.2	378.2	368.4	360.1	350.9	341.2	332.8	326.8	320.4	317.1	316.5
160°	384.4	374.9	366.8	360.1	352.0	343.9	336.6	331.1	325.7	323.0	322.4
162.5°	380.0	372.2	365.2	359.6	352.6	345.5	339.8	334.9	330.6	327.9	328.3
165°	372.9	366.8	362.1	358.1	353.4	347.3	343.3	339.9	335.9	334.5	335.2
167.5°	365.8	362.1	359.0	357.1	353.2	348.8	346.2	343.8	341.2	340.0	340.9
170°	362.1	359.4	357.4	356.0	352.7	349.3	347.3	345.9	343.9	343.3	344.6
172.5°	358.3	356.2	355.2	354.4	352.1	349.8	348.4	347.6	345.5	345.9	346.7
175°	353.4	352.7	352.0	352.7	351.3	350.0	349.3	349.3	347.9	348.6	349.3
177.5°	350.5	350.0	350.5	351.6	350.5	350.0	350.0	350.0	348.9	349.5	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	566.2	566.6	569.7	571.2	573.9	575.1	576.4	576.0	576.0	576.6	581.0
5°	567.4	571.3	577.1	582.8	588.3	593.0	596.2	599.3	600.5	606.1	611.1
7.5°	565.3	572.6	582.2	590.9	601.2	609.3	616.0	622.2	626.3	634.6	643.0
10°	562.7	572.8	583.8	595.0	609.2	620.0	630.9	639.4	642.0	654.4	661.4
12.5°	557.3	570.9	584.9	599.3	613.3	628.1	640.2	648.6	658.2	669.3	682.3
15°	549.4	565.0	583.2	601.8	621.7	639.7	652.6	667.3	677.9	690.0	701.4
17.5°	538.0	558.1	581.2	602.7	625.8	645.1	662.9	676.9	684.3	691.3	692.9
20°	528.8	550.5	577.7	603.1	626.2	648.5	666.2	677.9	679.8	680.0	669.7
22.5°	519.0	543.5	572.0	598.0	625.6	650.4	664.1	669.1	661.3	648.1	628.0
25°	500.8	529.3	562.3	592.0	622.2	645.6	650.3	641.5	614.3	585.7	549.6
27.5°	481.2	513.2	548.5	581.6	613.7	628.3	618.1	586.3	537.4	494.8	443.2
30°	466.8	502.7	537.4	574.4	604.2	610.4	587.1	540.4	483.3	419.1	367.6
32.5°	450.4	487.9	526.2	564.4	589.3	583.2	544.8	487.2	420.3	357.1	308.6
35°	427.0	465.6	507.0	545.3	561.1	534.7	477.2	402.3	333.8	275.0	241.5
37.5°	399.8	442.0	484.9	520.1	519.0	475.0	396.7	319.3	261.8	227.0	203.2
40°	380.6	423.3	469.6	499.3	486.6	429.3	344.4	271.5	229.4	201.6	184.3
42.5°	362.1	404.9	451.0	474.6	452.5	382.0	297.5	240.3	205.6	184.0	169.9
45°	330.7	375.9	418.5	431.6	392.1	314.5	240.6	199.1	176.0	160.0	150.2
47.5°	300.0	344.5	383.4	383.6	330.2	255.0	202.9	172.3	152.6	140.2	133.1
50°	281.2	323.5	356.1	351.0	290.4	226.9	181.5	155.1	138.7	129.1	121.7
52.5°	260.1	301.1	329.4	315.0	256.8	199.7	162.2	140.1	126.5	118.1	111.5
55°	229.4	265.8	285.8	263.8	209.5	166.1	137.1	119.7	109.5	102.5	96.8
57.5°	199.2	229.3	241.8	216.3	172.5	137.7	116.0	102.9	92.8	87.7	84.8
60°	180.3	206.0	214.7	186.6	150.0	120.5	102.7	90.6	83.1	79.8	76.9
62.5°	161.7	182.6	186.2	160.5	130.8	105.5	90.1	79.9	75.0	71.8	69.1
65°	134.1	149.2	147.5	126.7	103.5	83.7	72.6	66.3	62.6	58.1	53.2
67.5°	110.5	119.7	114.1	98.6	79.0	65.1	57.8	53.0	48.4	44.2	43.0
70°	95.4	100.7	94.9	80.6	64.7	54.6	48.7	43.0	40.3	39.3	37.5
72.5°	81.0	82.9	76.5	64.3	52.7	45.2	39.4	36.3	34.8	34.0	32.9
75°	60.8	59.5	54.0	44.4	36.6	31.5	29.7	28.6	27.6	26.8	26.2
77.5°	42.7	40.7	35.8	29.5	25.5	23.1	22.0	21.4	20.9	20.5	19.9
80°	32.1	30.7	25.8	21.1	19.4	18.2	17.6	16.8	16.8	16.4	15.8
82.5°	23.5	22.0	17.7	15.5	14.6	13.8	13.3	12.9	12.7	12.8	12.4
85°	12.3	10.0	8.8	8.4	7.8	7.4	7.7	7.2	7.2	7.2	7.1
87.5°	4.3	4.0	4.1	4.3	4.8	5.5	6.3	7.1	7.4	7.1	7.1
90°	2.7	5.4	6.7	8.1	10.1	13.4	18.2	22.2	22.9	22.2	21.5
92.5°	11.9	16.7	19.6	24.2	30.6	45.8	67.2	86.3	87.5	73.9	58.7
95°	26.3	33.0	39.0	49.8	66.0	96.9	155.5	233.6	263.8	230.8	176.3
97.5°	42.0	49.2	58.3	70.7	88.9	127.9	209.5	339.2	450.4	472.5	411.5
100°	53.8	59.9	70.7	84.1	103.0	138.6	220.8	366.1	531.7	628.6	614.5
102.5°	65.7	71.7	82.5	96.5	115.4	148.4	221.3	355.9	534.4	686.7	747.5
105°	84.8	89.5	99.6	114.4	133.3	164.9	224.8	335.9	498.7	677.8	817.8
107.5°	103.7	108.2	117.5	132.2	151.2	181.8	234.1	325.9	460.5	618.6	767.2
110°	117.1	121.1	129.9	144.0	163.6	193.1	241.6	323.7	442.2	581.5	723.5



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	129.0	133.5	141.7	155.3	175.4	204.0	249.7	324.3	430.3	555.7	683.7
115°	148.1	152.1	160.1	173.7	191.8	220.8	261.8	327.1	417.3	523.7	634.6
117.5°	166.5	170.6	177.7	190.6	209.5	236.3	274.7	331.9	411.0	503.4	597.8
120°	178.4	182.4	188.5	201.9	220.8	247.0	283.4	335.2	407.2	492.7	579.5
122.5°	189.2	193.1	199.8	213.2	232.6	257.3	290.9	339.0	405.0	483.5	565.0
125°	204.0	207.9	216.0	229.5	248.3	272.6	302.9	344.6	401.1	470.5	543.8
127.5°	216.5	222.1	231.0	243.9	263.3	286.9	314.0	350.4	398.8	458.3	523.0
130°	223.4	230.1	239.6	253.0	271.9	295.5	321.1	354.7	397.8	450.3	509.5
132.5°	230.5	237.7	247.7	261.7	280.5	303.0	328.0	359.0	397.3	443.8	496.5
135°	239.6	247.7	257.8	273.3	292.1	313.7	337.2	364.1	396.4	434.8	478.5
137.5°	249.3	257.4	268.1	283.5	301.0	322.3	344.2	368.7	396.3	428.4	464.2
140°	255.7	263.8	274.6	289.4	306.9	327.1	347.9	370.8	395.7	424.7	455.0
142.5°	262.3	269.8	280.5	294.8	311.3	330.9	351.2	372.5	395.7	420.9	447.5
145°	273.3	280.0	290.1	303.5	318.3	336.6	355.3	374.2	394.4	415.9	436.8
147.5°	283.9	290.3	299.6	310.8	324.0	341.1	357.7	374.8	392.0	410.9	428.6
150°	291.4	296.8	305.6	315.6	327.8	343.3	358.7	374.2	390.4	406.5	422.7
152.5°	297.9	303.2	310.9	320.5	331.6	345.4	359.3	373.2	387.7	402.8	416.7
155°	308.2	312.3	319.7	327.1	337.2	348.6	360.1	371.5	383.0	395.7	408.5
157.5°	317.1	320.4	326.8	332.8	341.2	350.9	360.1	368.4	378.2	389.2	399.0
160°	323.0	325.7	331.1	336.6	343.9	352.0	360.1	366.8	374.9	384.4	393.0
162.5°	327.9	330.6	334.9	339.8	345.5	352.6	359.6	365.2	372.2	380.0	387.1
165°	334.5	335.9	339.9	343.3	347.3	353.4	358.1	362.1	366.8	372.9	378.2
167.5°	340.0	341.2	343.8	346.2	348.8	353.2	357.1	359.0	362.1	365.8	369.8
170°	343.3	343.9	345.9	347.3	349.3	352.7	356.0	357.4	359.4	362.1	365.5
172.5°	345.9	345.5	347.6	348.4	349.8	352.1	354.4	355.2	356.2	358.3	360.6
175°	348.6	347.9	349.3	349.3	350.0	351.3	352.7	352.0	352.7	353.4	355.3
177.5°	349.5	348.9	350.0	350.0	350.0	350.5	351.6	350.5	350.0	350.5	351.6
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	582.6	584.6	585.6	585.6	586.7	586.2	585.7
5°	616.0	619.7	620.6	624.1	626.6	625.9	626.2
7.5°	649.4	655.3	661.2	663.9	664.3	665.9	666.5
10°	669.9	674.8	683.9	682.6	689.4	693.4	686.9
12.5°	689.6	696.2	702.6	704.3	708.2	709.5	706.9
15°	707.4	710.9	711.3	710.3	711.5	710.5	706.8
17.5°	690.8	685.0	673.5	668.0	663.7	657.2	654.6
20°	663.2	646.4	626.8	619.0	609.8	591.9	596.2
22.5°	603.7	584.6	565.0	542.2	531.2	514.2	513.2
25°	511.3	478.2	441.8	416.4	401.5	384.5	377.0
27.5°	397.5	355.9	326.1	311.0	297.2	283.8	283.2
30°	322.7	291.4	268.4	255.5	247.0	241.3	242.5
32.5°	272.0	250.6	235.0	224.3	218.1	213.8	213.7
35°	222.4	207.7	197.7	193.2	188.7	185.6	185.8
37.5°	190.3	181.5	175.9	171.0	168.2	166.6	165.7
40°	173.8	166.6	162.3	159.4	157.0	154.9	154.5
42.5°	160.9	154.9	150.6	148.3	146.1	144.6	144.2
45°	142.8	137.8	134.0	131.4	130.4	129.1	129.1
47.5°	127.0	122.2	119.2	117.5	115.9	114.9	114.9
50°	116.4	112.6	109.9	108.9	107.5	107.0	106.8
52.5°	106.9	104.0	102.1	101.4	100.8	100.1	100.2
55°	93.8	92.3	91.5	90.9	90.0	88.8	89.5
57.5°	83.0	81.6	79.6	77.7	76.8	75.9	76.3
60°	75.3	72.6	69.8	67.7	67.1	65.3	65.3
62.5°	65.6	61.7	58.4	57.2	56.6	55.8	55.6
65°	50.5	48.9	48.1	47.4	46.9	46.9	46.6
67.5°	41.8	41.2	40.3	40.1	39.8	39.6	39.5
70°	36.9	36.2	35.8	35.6	35.2	35.4	34.8
72.5°	32.3	31.7	31.6	31.1	30.8	30.8	30.4
75°	25.4	25.4	25.2	25.1	24.6	24.5	24.6
77.5°	19.5	19.6	19.3	19.2	19.2	19.2	19.0
80°	15.7	15.8	15.7	15.4	15.2	15.4	15.2
82.5°	12.4	12.1	12.1	12.0	12.0	11.9	11.8
85°	7.1	7.2	7.1	6.9	6.9	6.9	7.1
87.5°	6.7	7.0	7.1	7.1	7.1	7.1	7.0
90°	20.2	21.5	22.2	22.2	22.2	22.2	22.2
92.5°	50.4	44.7	40.6	40.0	37.8	38.4	37.3
95°	135.3	107.0	92.2	83.4	78.1	76.0	76.7
97.5°	336.7	263.8	215.2	183.0	166.5	156.7	151.0
100°	531.1	438.9	357.4	301.5	272.6	253.0	240.9
102.5°	728.7	661.2	574.9	514.2	464.8	440.4	424.0
105°	893.8	902.6	880.4	838.6	796.9	767.9	758.5
107.5°	881.7	951.7	984.3	989.5	987.2	981.5	968.9
110°	844.0	930.1	985.3	1014.3	1027.1	1033.1	1032.4



TEST NUMBER: P331629-935

CATALOG NUMBER: S122RDIP-S290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	799.3	891.4	954.7	994.9	1016.3	1027.8	1031.4
115°	738.3	826.5	895.8	943.6	974.6	992.0	998.2
117.5°	688.8	768.8	833.8	882.5	915.2	933.7	938.7
120°	663.0	734.3	795.6	842.7	874.3	893.8	900.5
122.5°	641.4	708.9	764.3	806.6	837.7	855.1	860.7
125°	613.1	672.4	722.8	761.9	787.5	804.3	809.7
127.5°	585.7	641.5	688.1	722.2	746.1	760.7	765.0
130°	567.4	620.5	665.0	697.9	720.8	734.3	739.7
132.5°	550.2	599.0	640.8	673.2	696.0	708.4	713.3
135°	523.0	567.4	605.0	634.0	656.3	668.3	671.1
137.5°	501.3	536.6	569.4	595.8	614.9	625.5	629.6
140°	487.3	518.2	547.9	569.4	586.9	597.0	601.1
142.5°	474.9	501.5	526.3	546.8	562.7	571.7	572.5
145°	459.0	479.9	499.4	515.6	527.0	533.7	535.7
147.5°	446.1	462.4	476.6	490.0	499.1	503.7	504.9
150°	437.5	451.6	463.7	473.8	481.9	485.9	486.6
152.5°	430.5	442.5	453.0	460.9	467.9	470.9	471.0
155°	419.3	429.4	436.8	444.2	448.9	451.6	450.3
157.5°	408.0	416.5	422.2	427.5	431.4	432.7	432.7
160°	400.5	407.9	412.6	417.3	420.7	421.3	421.3
162.5°	393.5	399.8	403.5	408.1	410.4	411.1	410.5
165°	383.0	387.7	390.4	393.0	395.7	395.7	395.1
167.5°	373.4	376.6	379.1	380.3	381.8	381.6	380.8
170°	367.5	370.1	371.5	372.2	374.2	373.5	372.2
172.5°	362.1	364.3	365.1	365.8	366.7	366.0	365.2
175°	356.0	356.7	357.4	357.4	358.1	357.4	356.0
177.5°	351.6	352.1	352.1	352.1	352.1	351.6	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0

(END OF REPORT)