

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331635-935

Luminaire Tested: **S122RDIP-S290D925U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331635-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S290D925U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4086.2 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21
2	84	77	72	67	75	69	64	60	54	50	48	39	37	36	26	25	24	18
3	77	68	62	56	68	61	55	51	48	44	41	35	33	30	23	22	21	16
4	71	61	53	48	63	54	48	43	42	38	35	31	29	26	21	20	18	14
5	65	54	47	41	58	49	42	37	38	34	30	28	25	23	19	18	16	12
6	60	49	41	36	53	44	37	32	34	30	26	26	23	20	18	16	14	11
7	55	44	36	31	49	39	33	29	31	27	23	23	20	18	16	14	13	10
8	51	40	33	28	46	36	30	25	28	24	21	21	18	16	15	13	12	9
9	48	36	29	24	42	33	27	22	26	22	19	20	17	15	14	12	11	8
10	44	33	26	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9087	9087	9087	9087
5°	10149	9144	8109	9144
10°	11262	9081	7029	9081
15°	11814	8948	5538	8948
20°	10244	8751	4792	8751
25°	6716	8480	4277	8480
30°	4521	8153	3872	8153
35°	3662	7740	3493	7740
40°	3256	7290	3231	7290
45°	2948	6766	2884	6766
50°	2683	6244	2673	6244
55°	2519	5664	2488	5664
60°	2109	5134	2086	5134
65°	1780	4661	2017	4661
70°	1643	4164	1902	4164
75°	1535	3624	1759	3624
80°	1413	2985	1562	2985
85°	1315	2353	1371	2353



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	1.3
10°-20°	148.7	3.6
20°-30°	191.6	4.7
30°-40°	182.1	4.5
40°-50°	156.0	3.8
50°-60°	118.8	2.9
60°-70°	75.1	1.8
70°-80°	37.5	0.9
80°-90°	13.8	0.3
90°-100°	178.7	4.4
100°-110°	606.3	14.8
110°-120°	644.1	15.8
120°-130°	530.2	13.0
130°-140°	425.8	10.4
140°-150°	321.8	7.9
150°-160°	226.1	5.5
160°-170°	133.1	3.3
170°-180°	43.3	1.1
0°-30°	393.6	9.6
0°-40°	575.7	14.1
0°-60°	850.4	20.8
0°-90°	976.8	23.9
90°-120°	1429.1	35.0
90°-150°	2706.8	66.2
90°-180°	3109.0	76.1
0°-180°	4086.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	626	564	500	564	626	62
15°	707	535	331	535	707	191
25°	377	476	240	476	377	179
35°	186	393	177	393	186	119
45°	129	296	126	296	129	100
55°	90	201	88	201	90	79
65°	47	122	53	122	47	47
75°	25	58	28	58	25	26
85°	7	13	7	13	7	8
90°	28	1	28	1	28	15
95°	98	30	98	30	98	127
105°	968	105	968	105	968	937
115°	1274	185	1274	185	1274	1248
125°	1034	258	1034	258	1034	934
135°	857	302	857	302	857	666
145°	684	345	684	345	684	434
155°	575	393	575	393	575	268
165°	504	428	504	428	504	144
175°	455	446	455	446	455	44
180°	447	447	447	447	447	



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	585.7	586.2	586.7	585.6	585.6	584.6	582.6	581.0	576.6	576.0	576.0
5°	626.2	625.9	626.6	624.1	620.6	619.7	616.0	611.1	606.1	600.5	599.3
7.5°	666.5	665.9	664.3	663.9	661.2	655.3	649.4	643.0	634.6	626.3	622.2
10°	686.9	693.4	689.4	682.6	683.9	674.8	669.9	661.4	654.4	642.0	639.4
12.5°	706.9	709.5	708.2	704.3	702.6	696.2	689.6	682.3	669.3	658.2	648.6
15°	706.8	710.5	711.5	710.3	711.3	710.9	707.4	701.4	690.0	677.9	667.3
17.5°	654.6	657.2	663.7	668.0	673.5	685.0	690.8	692.9	691.3	684.3	676.9
20°	596.2	591.9	609.8	619.0	626.8	646.4	663.2	669.7	680.0	679.8	677.9
22.5°	513.2	514.2	531.2	542.2	565.0	584.6	603.7	628.0	648.1	661.3	669.1
25°	377.0	384.5	401.5	416.4	441.8	478.2	511.3	549.6	585.7	614.3	641.5
27.5°	283.2	283.8	297.2	311.0	326.1	355.9	397.5	443.2	494.8	537.4	586.3
30°	242.5	241.3	247.0	255.5	268.4	291.4	322.7	367.6	419.1	483.3	540.4
32.5°	213.7	213.8	218.1	224.3	235.0	250.6	272.0	308.6	357.1	420.3	487.2
35°	185.8	185.6	188.7	193.2	197.7	207.7	222.4	241.5	275.0	333.8	402.3
37.5°	165.7	166.6	168.2	171.0	175.9	181.5	190.3	203.2	227.0	261.8	319.3
40°	154.5	154.9	157.0	159.4	162.3	166.6	173.8	184.3	201.6	229.4	271.5
42.5°	144.2	144.6	146.1	148.3	150.6	154.9	160.9	169.9	184.0	205.6	240.3
45°	129.1	129.1	130.4	131.4	134.0	137.8	142.8	150.2	160.0	176.0	199.1
47.5°	114.9	114.9	115.9	117.5	119.2	122.2	127.0	133.1	140.2	152.6	172.3
50°	106.8	107.0	107.5	108.9	109.9	112.6	116.4	121.7	129.1	138.7	155.1
52.5°	100.2	100.1	100.8	101.4	102.1	104.0	106.9	111.5	118.1	126.5	140.1
55°	89.5	88.8	90.0	90.9	91.5	92.3	93.8	96.8	102.5	109.5	119.7
57.5°	76.3	75.9	76.8	77.7	79.6	81.6	83.0	84.8	87.7	92.8	102.9
60°	65.3	65.3	67.1	67.7	69.8	72.6	75.3	76.9	79.8	83.1	90.6
62.5°	55.6	55.8	56.6	57.2	58.4	61.7	65.6	69.1	71.8	75.0	79.9
65°	46.6	46.9	46.9	47.4	48.1	48.9	50.5	53.2	58.1	62.6	66.3
67.5°	39.5	39.6	39.8	40.1	40.3	41.2	41.8	43.0	44.2	48.4	53.0
70°	34.8	35.4	35.2	35.6	35.8	36.2	36.9	37.5	39.3	40.3	43.0
72.5°	30.4	30.8	30.8	31.1	31.6	31.7	32.3	32.9	34.0	34.8	36.3
75°	24.6	24.5	24.6	25.1	25.2	25.4	25.4	26.2	26.8	27.6	28.6
77.5°	19.0	19.2	19.2	19.2	19.3	19.6	19.5	19.9	20.5	20.9	21.4
80°	15.2	15.4	15.2	15.4	15.7	15.8	15.7	15.8	16.4	16.8	16.8
82.5°	11.8	11.9	12.0	12.0	12.1	12.1	12.4	12.4	12.8	12.7	12.9
85°	7.1	6.9	6.9	6.9	7.1	7.2	7.1	7.1	7.2	7.2	7.2
87.5°	8.2	8.4	8.4	8.4	8.4	8.2	7.8	8.4	8.4	8.7	8.4
90°	28.3	28.3	28.3	28.3	28.3	27.5	25.7	27.5	28.3	29.2	28.3
92.5°	47.6	49.0	48.3	51.1	51.7	57.1	64.3	74.9	94.4	111.7	110.1
95°	98.0	97.1	99.7	106.6	117.7	136.6	172.7	225.2	294.7	336.8	298.2
97.5°	192.9	200.0	212.6	233.8	274.8	336.8	429.8	525.4	603.2	575.1	433.1
100°	307.6	323.1	348.0	385.0	456.3	560.3	678.0	784.5	802.6	678.8	467.4
102.5°	541.4	562.3	593.4	656.5	734.0	844.2	930.3	954.3	876.8	682.3	454.4
105°	968.5	980.4	1017.4	1070.7	1123.9	1152.4	1141.2	1044.0	865.3	636.7	428.8
107.5°	1237.1	1253.0	1260.4	1263.3	1256.6	1215.0	1125.7	979.5	789.9	588.0	416.0
110°	1318.2	1319.1	1311.3	1294.9	1258.0	1187.6	1077.5	923.8	742.4	564.6	413.4



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1316.8	1312.2	1297.5	1270.2	1218.8	1138.1	1020.5	872.9	709.5	549.4	414.0
115°	1274.4	1266.6	1244.2	1204.7	1143.8	1055.2	942.6	810.3	668.6	532.8	417.6
117.5°	1198.5	1192.1	1168.5	1126.7	1064.5	981.5	879.4	763.2	642.7	524.7	423.8
120°	1149.8	1141.2	1116.2	1075.8	1015.7	937.5	846.4	739.9	629.0	519.9	427.9
122.5°	1098.9	1091.7	1069.4	1029.8	975.9	905.2	818.9	721.3	617.3	517.1	432.7
125°	1033.7	1026.8	1005.4	972.8	922.9	858.4	782.8	694.3	600.6	512.1	440.0
127.5°	976.7	971.2	952.6	922.0	878.6	819.1	747.8	667.7	585.2	509.2	447.4
130°	944.3	937.5	920.3	891.1	849.0	792.3	724.4	650.5	574.9	507.8	452.9
132.5°	910.7	904.5	888.7	859.5	818.0	764.7	702.4	634.0	566.6	507.1	458.3
135°	856.7	853.3	837.8	809.4	772.5	724.4	667.7	611.0	555.1	506.1	464.9
137.5°	803.8	798.7	785.1	760.7	726.9	685.0	640.0	592.5	547.0	505.9	470.7
140°	767.3	762.2	749.3	726.9	699.5	661.7	622.2	580.9	542.3	505.2	473.5
142.5°	730.9	729.9	718.4	698.1	672.0	640.3	606.3	571.3	537.4	505.2	475.5
145°	684.0	681.4	672.9	658.2	637.6	612.7	586.1	557.7	531.1	503.5	477.8
147.5°	644.6	643.1	637.2	625.6	608.6	590.3	569.6	547.2	524.5	500.5	478.5
150°	621.3	620.4	615.3	604.9	592.0	576.6	558.5	539.7	519.0	498.4	477.8
152.5°	601.3	601.2	597.4	588.4	578.3	564.9	549.6	532.1	514.2	495.0	476.4
155°	574.9	576.6	573.2	567.1	557.7	548.2	535.4	521.6	505.2	489.0	474.3
157.5°	552.3	552.3	550.8	545.8	539.2	531.8	520.9	509.4	496.9	482.8	470.4
160°	538.0	538.0	537.1	532.8	526.8	520.7	511.3	501.8	490.7	478.6	468.3
162.5°	524.2	524.9	524.0	521.1	515.1	510.4	502.3	494.3	485.2	475.2	466.2
165°	504.4	505.2	505.2	501.8	498.4	495.0	489.0	482.9	476.0	468.3	462.3
167.5°	486.2	487.2	487.4	485.5	484.0	480.9	476.7	472.1	467.1	462.3	458.3
170°	475.2	476.9	477.8	475.2	474.3	472.6	469.2	466.6	462.3	458.8	456.3
172.5°	466.2	467.3	468.1	466.9	466.1	465.0	462.3	460.4	457.5	454.8	453.6
175°	454.6	456.3	457.2	456.3	456.3	455.5	454.6	453.7	451.2	450.3	449.4
177.5°	447.5	448.9	449.6	449.6	449.6	449.6	448.9	448.9	447.5	446.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	576.4	575.1	573.9	571.2	569.7	566.6	566.2	566.0	562.0	558.0	556.9
5°	596.2	593.0	588.3	582.8	577.1	571.3	567.4	564.2	556.4	549.0	544.7
7.5°	616.0	609.3	601.2	590.9	582.2	572.6	565.3	558.9	547.8	537.1	529.9
10°	630.9	620.0	609.2	595.0	583.8	572.8	562.7	553.9	541.4	527.3	517.3
12.5°	640.2	628.1	613.3	599.3	584.9	570.9	557.3	546.0	531.3	516.8	505.0
15°	652.6	639.7	621.7	601.8	583.2	565.0	549.4	535.3	516.2	498.7	484.2
17.5°	662.9	645.1	625.8	602.7	581.2	558.1	538.0	520.0	498.6	477.6	460.5
20°	666.2	648.5	626.2	603.1	577.7	550.5	528.8	509.3	486.4	463.5	443.9
22.5°	664.1	650.4	625.6	598.0	572.0	543.5	519.0	496.3	470.9	447.5	424.9
25°	650.3	645.6	622.2	592.0	562.3	529.3	500.8	476.0	447.1	422.1	397.4
27.5°	618.1	628.3	613.7	581.6	548.5	513.2	481.2	453.0	422.9	394.8	370.2
30°	587.1	610.4	604.2	574.4	537.4	502.7	466.8	437.3	405.3	376.3	352.1
32.5°	544.8	583.2	589.3	564.4	526.2	487.9	450.4	421.0	387.5	357.1	333.4
35°	477.2	534.7	561.1	545.3	507.0	465.6	427.0	392.7	359.0	329.0	305.5
37.5°	396.7	475.0	519.0	520.1	484.9	442.0	399.8	365.8	331.4	301.9	276.5
40°	344.4	429.3	486.6	499.3	469.6	423.3	380.6	345.9	312.4	283.4	254.3
42.5°	297.5	382.0	452.5	474.6	451.0	404.9	362.1	326.0	293.3	265.9	236.1
45°	240.6	314.5	392.1	431.6	418.5	375.9	330.7	296.3	265.6	241.9	213.4
47.5°	202.9	255.0	330.2	383.6	383.4	344.5	300.0	267.1	238.6	216.4	193.3
50°	181.5	226.9	290.4	351.0	356.1	323.5	281.2	248.6	222.0	198.7	180.1
52.5°	162.2	199.7	256.8	315.0	329.4	301.1	260.1	230.0	204.1	182.7	166.9
55°	137.1	166.1	209.5	263.8	285.8	265.8	229.4	201.2	180.3	162.3	148.6
57.5°	116.0	137.7	172.5	216.3	241.8	229.3	199.2	176.3	158.4	142.2	131.4
60°	102.7	120.5	150.0	186.6	214.7	206.0	180.3	159.0	143.8	129.7	119.5
62.5°	90.1	105.5	130.8	160.5	186.2	182.6	161.7	143.8	130.4	117.6	109.0
65°	72.6	83.7	103.5	126.7	147.5	149.2	134.1	122.0	110.1	100.0	92.3
67.5°	57.8	65.1	79.0	98.6	114.1	119.7	110.5	101.2	91.7	83.9	77.2
70°	48.7	54.6	64.7	80.6	94.9	100.7	95.4	88.2	80.0	73.5	67.8
72.5°	39.4	45.2	52.7	64.3	76.5	82.9	81.0	75.9	69.2	63.8	58.5
75°	29.7	31.5	36.6	44.4	54.0	59.5	60.8	58.1	52.8	48.7	45.5
77.5°	22.0	23.1	25.5	29.5	35.8	40.7	42.7	42.4	38.7	36.4	33.4
80°	17.6	18.2	19.4	21.1	25.8	30.7	32.1	32.1	29.5	28.6	25.7
82.5°	13.3	13.8	14.6	15.5	17.7	22.0	23.5	23.8	22.2	20.9	18.6
85°	7.7	7.4	7.8	8.4	8.8	10.0	12.3	12.7	12.3	10.8	10.2
87.5°	7.3	6.3	5.4	4.7	4.6	4.3	4.5	4.7	4.6	4.8	4.8
90°	23.2	17.2	12.9	10.3	8.6	6.9	3.4	0.9	3.4	6.9	8.6
92.5°	85.8	58.5	39.0	30.9	25.1	21.4	15.2	10.5	15.2	21.4	25.1
95°	198.5	123.7	84.2	63.6	49.9	42.1	33.5	30.0	33.5	42.1	49.9
97.5°	267.4	163.2	113.6	90.2	74.4	62.8	53.6	49.0	53.6	62.8	74.4
100°	281.9	177.0	131.5	107.5	90.2	76.5	68.7	66.1	68.7	76.5	90.2
102.5°	282.6	189.4	147.3	123.2	105.4	91.6	83.9	82.0	83.9	91.6	105.4
105°	287.0	210.5	170.1	146.1	127.2	114.3	108.3	104.9	108.3	114.3	127.2
107.5°	298.9	232.2	193.0	168.8	150.1	138.2	132.3	129.6	132.3	138.2	150.1
110°	308.5	246.6	208.8	183.9	165.8	154.6	149.6	146.1	149.6	154.6	165.8



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	318.8	260.4	223.9	198.3	181.0	170.5	164.6	161.2	164.6	170.5	181.0
115°	334.2	281.9	244.9	221.7	204.5	194.2	189.1	184.8	189.1	194.2	204.5
117.5°	350.8	301.6	267.4	243.3	226.9	217.7	212.6	209.1	212.6	217.7	226.9
120°	361.8	315.4	281.9	257.8	240.6	232.9	227.7	224.3	227.7	232.9	240.6
122.5°	371.3	328.4	297.0	272.2	255.0	246.6	241.4	238.8	241.4	246.6	255.0
125°	386.7	348.0	317.1	293.0	275.9	265.5	260.4	257.8	260.4	265.5	275.9
127.5°	401.0	366.3	336.1	311.4	294.9	283.5	276.4	272.9	276.4	283.5	294.9
130°	409.9	377.2	347.2	323.1	305.9	293.9	285.2	281.9	285.2	293.9	305.9
132.5°	418.8	386.8	358.2	334.1	316.2	303.5	294.2	290.1	294.2	303.5	316.2
135°	430.5	400.5	372.9	348.9	329.1	316.2	305.9	302.5	305.9	316.2	329.1
137.5°	439.5	411.5	384.3	362.0	342.3	328.6	318.3	314.2	318.3	328.6	342.3
140°	444.3	417.6	391.8	369.5	350.6	336.8	326.6	323.1	326.6	336.8	350.6
142.5°	448.4	422.4	397.4	376.3	358.2	344.4	334.8	332.0	334.8	344.4	358.2
145°	453.7	429.6	406.5	387.5	370.4	357.5	348.9	345.4	348.9	357.5	370.4
147.5°	456.7	435.5	413.7	396.8	382.5	370.7	362.5	359.9	362.5	370.7	382.5
150°	458.0	438.2	418.4	403.0	390.1	378.9	372.0	369.5	372.0	378.9	390.1
152.5°	458.7	441.0	423.3	409.2	397.0	387.2	380.3	379.1	380.3	387.2	397.0
155°	459.7	445.1	430.5	417.6	408.2	398.7	393.6	392.7	393.6	398.7	408.2
157.5°	459.7	448.1	435.7	424.8	417.2	409.1	404.9	404.1	404.9	409.1	417.2
160°	459.7	449.4	439.1	429.6	422.8	415.9	412.5	411.6	412.5	415.9	422.8
162.5°	459.0	450.1	441.2	433.8	427.6	422.1	418.6	419.1	418.6	422.1	427.6
165°	457.2	451.2	443.4	438.2	433.9	428.8	427.1	427.9	427.1	428.8	433.9
167.5°	456.0	451.0	445.3	442.0	438.9	435.7	434.1	435.1	434.1	435.7	438.9
170°	454.6	450.3	446.0	443.4	441.7	439.1	438.2	440.0	438.2	439.1	441.7
172.5°	452.5	449.6	446.7	444.8	443.8	441.2	441.7	442.7	441.7	441.2	443.8
175°	450.3	448.6	446.9	446.0	446.0	444.3	445.1	446.0	445.1	444.3	446.0
177.5°	448.9	447.5	446.9	446.9	446.9	445.5	446.2	447.5	446.2	445.5	446.9
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	554.9	553.8	551.7	548.6	546.7	543.5	541.3	542.5	542.9	542.5	542.3
5°	540.0	535.9	530.2	524.7	519.6	514.2	511.0	509.7	507.0	505.4	504.5
7.5°	521.9	514.9	506.9	497.3	489.2	480.7	476.4	474.2	468.6	465.6	463.0
10°	508.5	497.3	489.3	476.8	469.2	458.1	450.4	450.6	443.0	438.7	435.6
12.5°	493.6	481.4	468.0	456.8	446.2	437.2	428.0	424.3	416.2	412.1	403.6
15°	469.0	454.7	440.7	425.4	414.7	400.7	387.4	371.2	358.1	346.7	343.6
17.5°	442.1	424.4	410.3	392.4	373.9	350.6	335.2	325.7	317.9	311.9	307.4
20°	423.6	405.6	390.5	363.6	338.7	322.9	311.6	304.3	296.1	289.6	286.1
22.5°	404.2	385.5	364.9	334.8	315.4	302.7	292.7	284.3	278.7	273.7	270.4
25°	376.7	356.1	322.3	301.6	285.9	272.6	265.6	260.5	254.7	247.8	244.7
27.5°	347.6	315.0	290.6	275.2	260.3	251.7	245.3	237.7	232.5	229.4	226.1
30°	325.8	293.2	274.2	257.4	246.8	237.2	229.8	225.5	220.4	215.2	213.0
32.5°	301.6	275.5	257.3	243.3	232.6	224.4	218.5	211.5	207.9	204.7	200.2
35°	271.5	251.7	235.1	223.8	213.5	206.9	200.1	196.0	189.3	186.6	184.9
37.5°	246.0	228.9	216.5	204.5	196.4	189.1	184.9	178.3	175.5	171.6	167.9
40°	231.5	214.7	202.9	193.0	184.0	178.6	173.3	168.0	163.7	162.0	157.5
42.5°	216.9	203.2	191.2	180.6	174.5	168.7	162.0	158.2	153.7	150.8	148.1
45°	196.6	184.4	174.3	165.5	158.8	152.7	148.4	142.0	139.5	133.8	131.4
47.5°	178.7	167.5	157.7	149.4	142.9	139.0	132.7	127.6	123.6	120.0	117.0
50°	166.1	156.6	147.2	139.8	134.0	128.3	121.8	119.3	113.0	111.2	109.5
52.5°	154.5	145.5	137.0	129.7	123.8	118.3	112.6	109.3	105.0	103.3	102.0
55°	138.3	129.7	121.5	115.0	109.2	103.5	100.0	95.8	93.8	92.5	90.9
57.5°	122.0	114.3	108.0	101.4	95.5	91.0	87.0	84.5	82.5	80.7	78.8
60°	111.7	104.3	98.6	92.5	86.4	82.7	79.6	76.6	74.3	71.5	70.8
62.5°	100.7	94.2	89.0	83.1	77.8	74.5	71.5	68.7	65.9	61.9	60.8
65°	85.7	80.6	75.1	70.2	65.5	62.2	57.9	54.8	53.6	53.2	53.0
67.5°	72.1	67.2	62.5	57.5	53.3	50.2	48.0	47.5	46.7	46.5	45.9
70°	62.9	58.5	53.8	49.1	44.9	44.4	43.7	42.8	41.8	41.5	41.1
72.5°	54.8	50.2	45.5	41.8	40.0	39.3	38.5	37.6	37.0	36.6	36.4
75°	42.0	37.7	34.6	33.2	32.3	31.7	30.5	30.0	29.5	28.9	28.8
77.5°	30.3	27.8	26.4	25.6	24.5	23.9	23.2	22.6	22.2	22.1	21.8
80°	23.1	21.9	20.9	19.7	19.4	18.6	18.4	17.8	18.0	17.4	17.4
82.5°	17.9	16.4	15.6	15.1	14.6	14.0	13.9	13.6	13.6	13.2	13.2
85°	9.2	8.8	8.4	8.0	8.0	7.4	7.7	7.4	7.4	7.1	6.9
87.5°	5.0	5.4	5.9	7.1	8.2	8.2	8.0	7.7	7.3	7.7	7.7
90°	10.3	12.9	17.2	23.2	28.3	29.2	28.3	27.5	25.7	27.5	28.3
92.5°	30.9	39.0	58.5	85.8	110.1	111.7	94.4	74.9	64.3	57.1	51.7
95°	63.6	84.2	123.7	198.5	298.2	336.8	294.7	225.2	172.7	136.6	117.7
97.5°	90.2	113.6	163.2	267.4	433.1	575.1	603.2	525.4	429.8	336.8	274.8
100°	107.5	131.5	177.0	281.9	467.4	678.8	802.6	784.5	678.0	560.3	456.3
102.5°	123.2	147.3	189.4	282.6	454.4	682.3	876.8	954.3	930.3	844.2	734.0
105°	146.1	170.1	210.5	287.0	428.8	636.7	865.3	1044.0	1141.2	1152.4	1123.9
107.5°	168.8	193.0	232.2	298.9	416.0	588.0	789.9	979.5	1125.7	1215.0	1256.6
110°	183.9	208.8	246.6	308.5	413.4	564.6	742.4	923.8	1077.5	1187.6	1258.0



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	198.3	223.9	260.4	318.8	414.0	549.4	709.5	872.9	1020.5	1138.1	1218.8
115°	221.7	244.9	281.9	334.2	417.6	532.8	668.6	810.3	942.6	1055.2	1143.8
117.5°	243.3	267.4	301.6	350.8	423.8	524.7	642.7	763.2	879.4	981.5	1064.5
120°	257.8	281.9	315.4	361.8	427.9	519.9	629.0	739.9	846.4	937.5	1015.7
122.5°	272.2	297.0	328.4	371.3	432.7	517.1	617.3	721.3	818.9	905.2	975.9
125°	293.0	317.1	348.0	386.7	440.0	512.1	600.6	694.3	782.8	858.4	922.9
127.5°	311.4	336.1	366.3	401.0	447.4	509.2	585.2	667.7	747.8	819.1	878.6
130°	323.1	347.2	377.2	409.9	452.9	507.8	574.9	650.5	724.4	792.3	849.0
132.5°	334.1	358.2	386.8	418.8	458.3	507.1	566.6	634.0	702.4	764.7	818.0
135°	348.9	372.9	400.5	430.5	464.9	506.1	555.1	611.0	667.7	724.4	772.5
137.5°	362.0	384.3	411.5	439.5	470.7	505.9	547.0	592.5	640.0	685.0	726.9
140°	369.5	391.8	417.6	444.3	473.5	505.2	542.3	580.9	622.2	661.7	699.5
142.5°	376.3	397.4	422.4	448.4	475.5	505.2	537.4	571.3	606.3	640.3	672.0
145°	387.5	406.5	429.6	453.7	477.8	503.5	531.1	557.7	586.1	612.7	637.6
147.5°	396.8	413.7	435.5	456.7	478.5	500.5	524.5	547.2	569.6	590.3	608.6
150°	403.0	418.4	438.2	458.0	477.8	498.4	519.0	539.7	558.5	576.6	592.0
152.5°	409.2	423.3	441.0	458.7	476.4	495.0	514.2	532.1	549.6	564.9	578.3
155°	417.6	430.5	445.1	459.7	474.3	489.0	505.2	521.6	535.4	548.2	557.7
157.5°	424.8	435.7	448.1	459.7	470.4	482.8	496.9	509.4	520.9	531.8	539.2
160°	429.6	439.1	449.4	459.7	468.3	478.6	490.7	501.8	511.3	520.7	526.8
162.5°	433.8	441.2	450.1	459.0	466.2	475.2	485.2	494.3	502.3	510.4	515.1
165°	438.2	443.4	451.2	457.2	462.3	468.3	476.0	482.9	489.0	495.0	498.4
167.5°	442.0	445.3	451.0	456.0	458.3	462.3	467.1	472.1	476.7	480.9	484.0
170°	443.4	446.0	450.3	454.6	456.3	458.8	462.3	466.6	469.2	472.6	474.3
172.5°	444.8	446.7	449.6	452.5	453.6	454.8	457.5	460.4	462.3	465.0	466.1
175°	446.0	446.9	448.6	450.3	449.4	450.3	451.2	453.7	454.6	455.5	456.3
177.5°	446.9	446.9	447.5	448.9	447.5	446.9	447.5	448.9	448.9	449.6	449.6
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	540.5	540.8	540.4	540.6	540.4	540.8	540.5	542.3	542.5	542.9	542.5
5°	503.6	501.3	500.8	500.3	500.8	501.3	503.6	504.5	505.4	507.0	509.7
7.5°	459.6	459.3	458.2	456.8	458.2	459.3	459.6	463.0	465.6	468.6	474.2
10°	431.3	430.2	430.1	428.7	430.1	430.2	431.3	435.6	438.7	443.0	450.6
12.5°	398.0	391.8	391.2	387.7	391.2	391.8	398.0	403.6	412.1	416.2	424.3
15°	339.0	337.8	333.8	331.3	333.8	337.8	339.0	343.6	346.7	358.1	371.2
17.5°	305.1	301.3	300.1	299.5	300.1	301.3	305.1	307.4	311.9	317.9	325.7
20°	283.4	279.9	279.3	278.9	279.3	279.9	283.4	286.1	289.6	296.1	304.3
22.5°	268.4	264.7	263.2	262.0	263.2	264.7	268.4	270.4	273.7	278.7	284.3
25°	242.7	241.3	240.6	240.1	240.6	241.3	242.7	244.7	247.8	254.7	260.5
27.5°	222.7	219.6	219.0	218.0	219.0	219.6	222.7	226.1	229.4	232.5	237.7
30°	211.2	210.3	208.9	207.7	208.9	210.3	211.2	213.0	215.2	220.4	225.5
32.5°	197.8	196.9	195.7	195.2	195.7	196.9	197.8	200.2	204.7	207.9	211.5
35°	182.9	180.1	178.9	177.2	178.9	180.1	182.9	184.9	186.6	189.3	196.0
37.5°	167.1	165.7	164.0	164.6	164.0	165.7	167.1	167.9	171.6	175.5	178.3
40°	154.9	153.9	153.5	153.3	153.5	153.9	154.9	157.5	162.0	163.7	168.0
42.5°	145.2	142.5	141.5	141.5	141.5	142.5	145.2	148.1	150.8	153.7	158.2
45°	130.4	127.9	126.1	126.3	126.1	127.9	130.4	131.4	133.8	139.5	142.0
47.5°	115.4	115.3	114.2	114.5	114.2	115.3	115.4	117.0	120.0	123.6	127.6
50°	108.1	107.0	106.2	106.4	106.2	107.0	108.1	109.5	111.2	113.0	119.3
52.5°	101.3	100.2	99.6	100.5	99.6	100.2	101.3	102.0	103.3	105.0	109.3
55°	90.0	88.8	88.6	88.4	88.6	88.8	90.0	90.9	92.5	93.8	95.8
57.5°	77.3	76.5	75.3	74.9	75.3	76.5	77.3	78.8	80.7	82.5	84.5
60°	68.3	66.7	64.7	64.6	64.7	66.7	68.3	70.8	71.5	74.3	76.6
62.5°	59.9	59.7	59.2	59.2	59.2	59.7	59.9	60.8	61.9	65.9	68.7
65°	52.6	52.4	52.6	52.8	52.6	52.4	52.6	53.0	53.2	53.6	54.8
67.5°	45.8	45.5	45.1	45.3	45.1	45.5	45.8	45.9	46.5	46.7	47.5
70°	40.6	40.5	40.3	40.3	40.3	40.5	40.6	41.1	41.5	41.8	42.8
72.5°	35.6	35.6	35.5	35.3	35.5	35.6	35.6	36.4	36.6	37.0	37.6
75°	28.6	28.2	28.2	28.2	28.2	28.2	28.6	28.8	28.9	29.5	30.0
77.5°	21.8	21.5	21.4	21.2	21.4	21.5	21.8	21.8	22.1	22.2	22.6
80°	17.2	17.0	16.8	16.8	16.8	17.0	17.2	17.4	17.4	18.0	17.8
82.5°	13.2	12.9	12.9	12.7	12.9	12.9	13.2	13.2	13.2	13.6	13.6
85°	7.1	7.2	7.1	7.4	7.1	7.2	7.1	6.9	7.1	7.4	7.4
87.5°	7.7	7.6	7.7	7.6	7.7	7.6	7.7	7.7	7.7	7.3	7.7
90°	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	27.5	25.7	27.5
92.5°	51.1	48.3	49.0	47.6	49.0	48.3	51.1	51.7	57.1	64.3	74.9
95°	106.6	99.7	97.1	98.0	97.1	99.7	106.6	117.7	136.6	172.7	225.2
97.5°	233.8	212.6	200.0	192.9	200.0	212.6	233.8	274.8	336.8	429.8	525.4
100°	385.0	348.0	323.1	307.6	323.1	348.0	385.0	456.3	560.3	678.0	784.5
102.5°	656.5	593.4	562.3	541.4	562.3	593.4	656.5	734.0	844.2	930.3	954.3
105°	1070.7	1017.4	980.4	968.5	980.4	1017.4	1070.7	1123.9	1152.4	1141.2	1044.0
107.5°	1263.3	1260.4	1253.0	1237.1	1253.0	1260.4	1263.3	1256.6	1215.0	1125.7	979.5
110°	1294.9	1311.3	1319.1	1318.2	1319.1	1311.3	1294.9	1258.0	1187.6	1077.5	923.8



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1270.2	1297.5	1312.2	1316.8	1312.2	1297.5	1270.2	1218.8	1138.1	1020.5	872.9
115°	1204.7	1244.2	1266.6	1274.4	1266.6	1244.2	1204.7	1143.8	1055.2	942.6	810.3
117.5°	1126.7	1168.5	1192.1	1198.5	1192.1	1168.5	1126.7	1064.5	981.5	879.4	763.2
120°	1075.8	1116.2	1141.2	1149.8	1141.2	1116.2	1075.8	1015.7	937.5	846.4	739.9
122.5°	1029.8	1069.4	1091.7	1098.9	1091.7	1069.4	1029.8	975.9	905.2	818.9	721.3
125°	972.8	1005.4	1026.8	1033.7	1026.8	1005.4	972.8	922.9	858.4	782.8	694.3
127.5°	922.0	952.6	971.2	976.7	971.2	952.6	922.0	878.6	819.1	747.8	667.7
130°	891.1	920.3	937.5	944.3	937.5	920.3	891.1	849.0	792.3	724.4	650.5
132.5°	859.5	888.7	904.5	910.7	904.5	888.7	859.5	818.0	764.7	702.4	634.0
135°	809.4	837.8	853.3	856.7	853.3	837.8	809.4	772.5	724.4	667.7	611.0
137.5°	760.7	785.1	798.7	803.8	798.7	785.1	760.7	726.9	685.0	640.0	592.5
140°	726.9	749.3	762.2	767.3	762.2	749.3	726.9	699.5	661.7	622.2	580.9
142.5°	698.1	718.4	729.9	730.9	729.9	718.4	698.1	672.0	640.3	606.3	571.3
145°	658.2	672.9	681.4	684.0	681.4	672.9	658.2	637.6	612.7	586.1	557.7
147.5°	625.6	637.2	643.1	644.6	643.1	637.2	625.6	608.6	590.3	569.6	547.2
150°	604.9	615.3	620.4	621.3	620.4	615.3	604.9	592.0	576.6	558.5	539.7
152.5°	588.4	597.4	601.2	601.3	601.2	597.4	588.4	578.3	564.9	549.6	532.1
155°	567.1	573.2	576.6	574.9	576.6	573.2	567.1	557.7	548.2	535.4	521.6
157.5°	545.8	550.8	552.3	552.3	552.3	550.8	545.8	539.2	531.8	520.9	509.4
160°	532.8	537.1	538.0	538.0	538.0	537.1	532.8	526.8	520.7	511.3	501.8
162.5°	521.1	524.0	524.9	524.2	524.9	524.0	521.1	515.1	510.4	502.3	494.3
165°	501.8	505.2	505.2	504.4	505.2	505.2	501.8	498.4	495.0	489.0	482.9
167.5°	485.5	487.4	487.2	486.2	487.2	487.4	485.5	484.0	480.9	476.7	472.1
170°	475.2	477.8	476.9	475.2	476.9	477.8	475.2	474.3	472.6	469.2	466.6
172.5°	466.9	468.1	467.3	466.2	467.3	468.1	466.9	466.1	465.0	462.3	460.4
175°	456.3	457.2	456.3	454.6	456.3	457.2	456.3	456.3	455.5	454.6	453.7
177.5°	449.6	449.6	448.9	447.5	448.9	449.6	449.6	449.6	449.6	448.9	448.9
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	541.3	543.5	546.7	548.6	551.7	553.8	554.9	556.9	558.0	562.0	566.0
5°	511.0	514.2	519.6	524.7	530.2	535.9	540.0	544.7	549.0	556.4	564.2
7.5°	476.4	480.7	489.2	497.3	506.9	514.9	521.9	529.9	537.1	547.8	558.9
10°	450.4	458.1	469.2	476.8	489.3	497.3	508.5	517.3	527.3	541.4	553.9
12.5°	428.0	437.2	446.2	456.8	468.0	481.4	493.6	505.0	516.8	531.3	546.0
15°	387.4	400.7	414.7	425.4	440.7	454.7	469.0	484.2	498.7	516.2	535.3
17.5°	335.2	350.6	373.9	392.4	410.3	424.4	442.1	460.5	477.6	498.6	520.0
20°	311.6	322.9	338.7	363.6	390.5	405.6	423.6	443.9	463.5	486.4	509.3
22.5°	292.7	302.7	315.4	334.8	364.9	385.5	404.2	424.9	447.5	470.9	496.3
25°	265.6	272.6	285.9	301.6	322.3	356.1	376.7	397.4	422.1	447.1	476.0
27.5°	245.3	251.7	260.3	275.2	290.6	315.0	347.6	370.2	394.8	422.9	453.0
30°	229.8	237.2	246.8	257.4	274.2	293.2	325.8	352.1	376.3	405.3	437.3
32.5°	218.5	224.4	232.6	243.3	257.3	275.5	301.6	333.4	357.1	387.5	421.0
35°	200.1	206.9	213.5	223.8	235.1	251.7	271.5	305.5	329.0	359.0	392.7
37.5°	184.9	189.1	196.4	204.5	216.5	228.9	246.0	276.5	301.9	331.4	365.8
40°	173.3	178.6	184.0	193.0	202.9	214.7	231.5	254.3	283.4	312.4	345.9
42.5°	162.0	168.7	174.5	180.6	191.2	203.2	216.9	236.1	265.9	293.3	326.0
45°	148.4	152.7	158.8	165.5	174.3	184.4	196.6	213.4	241.9	265.6	296.3
47.5°	132.7	139.0	142.9	149.4	157.7	167.5	178.7	193.3	216.4	238.6	267.1
50°	121.8	128.3	134.0	139.8	147.2	156.6	166.1	180.1	198.7	222.0	248.6
52.5°	112.6	118.3	123.8	129.7	137.0	145.5	154.5	166.9	182.7	204.1	230.0
55°	100.0	103.5	109.2	115.0	121.5	129.7	138.3	148.6	162.3	180.3	201.2
57.5°	87.0	91.0	95.5	101.4	108.0	114.3	122.0	131.4	142.2	158.4	176.3
60°	79.6	82.7	86.4	92.5	98.6	104.3	111.7	119.5	129.7	143.8	159.0
62.5°	71.5	74.5	77.8	83.1	89.0	94.2	100.7	109.0	117.6	130.4	143.8
65°	57.9	62.2	65.5	70.2	75.1	80.6	85.7	92.3	100.0	110.1	122.0
67.5°	48.0	50.2	53.3	57.5	62.5	67.2	72.1	77.2	83.9	91.7	101.2
70°	43.7	44.4	44.9	49.1	53.8	58.5	62.9	67.8	73.5	80.0	88.2
72.5°	38.5	39.3	40.0	41.8	45.5	50.2	54.8	58.5	63.8	69.2	75.9
75°	30.5	31.7	32.3	33.2	34.6	37.7	42.0	45.5	48.7	52.8	58.1
77.5°	23.2	23.9	24.5	25.6	26.4	27.8	30.3	33.4	36.4	38.7	42.4
80°	18.4	18.6	19.4	19.7	20.9	21.9	23.1	25.7	28.6	29.5	32.1
82.5°	13.9	14.0	14.6	15.1	15.6	16.4	17.9	18.6	20.9	22.2	23.8
85°	7.7	7.4	8.0	8.0	8.4	8.8	9.2	10.2	10.8	12.3	12.7
87.5°	8.0	8.2	8.2	7.1	5.9	5.4	5.0	4.8	4.8	4.6	4.7
90°	28.3	29.2	28.3	23.2	17.2	12.9	10.3	8.6	6.9	3.4	0.9
92.5°	94.4	111.7	110.1	85.8	58.5	39.0	30.9	25.1	21.4	15.2	10.5
95°	294.7	336.8	298.2	198.5	123.7	84.2	63.6	49.9	42.1	33.5	30.0
97.5°	603.2	575.1	433.1	267.4	163.2	113.6	90.2	74.4	62.8	53.6	49.0
100°	802.6	678.8	467.4	281.9	177.0	131.5	107.5	90.2	76.5	68.7	66.1
102.5°	876.8	682.3	454.4	282.6	189.4	147.3	123.2	105.4	91.6	83.9	82.0
105°	865.3	636.7	428.8	287.0	210.5	170.1	146.1	127.2	114.3	108.3	104.9
107.5°	789.9	588.0	416.0	298.9	232.2	193.0	168.8	150.1	138.2	132.3	129.6
110°	742.4	564.6	413.4	308.5	246.6	208.8	183.9	165.8	154.6	149.6	146.1



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	709.5	549.4	414.0	318.8	260.4	223.9	198.3	181.0	170.5	164.6	161.2
115°	668.6	532.8	417.6	334.2	281.9	244.9	221.7	204.5	194.2	189.1	184.8
117.5°	642.7	524.7	423.8	350.8	301.6	267.4	243.3	226.9	217.7	212.6	209.1
120°	629.0	519.9	427.9	361.8	315.4	281.9	257.8	240.6	232.9	227.7	224.3
122.5°	617.3	517.1	432.7	371.3	328.4	297.0	272.2	255.0	246.6	241.4	238.8
125°	600.6	512.1	440.0	386.7	348.0	317.1	293.0	275.9	265.5	260.4	257.8
127.5°	585.2	509.2	447.4	401.0	366.3	336.1	311.4	294.9	283.5	276.4	272.9
130°	574.9	507.8	452.9	409.9	377.2	347.2	323.1	305.9	293.9	285.2	281.9
132.5°	566.6	507.1	458.3	418.8	386.8	358.2	334.1	316.2	303.5	294.2	290.1
135°	555.1	506.1	464.9	430.5	400.5	372.9	348.9	329.1	316.2	305.9	302.5
137.5°	547.0	505.9	470.7	439.5	411.5	384.3	362.0	342.3	328.6	318.3	314.2
140°	542.3	505.2	473.5	444.3	417.6	391.8	369.5	350.6	336.8	326.6	323.1
142.5°	537.4	505.2	475.5	448.4	422.4	397.4	376.3	358.2	344.4	334.8	332.0
145°	531.1	503.5	477.8	453.7	429.6	406.5	387.5	370.4	357.5	348.9	345.4
147.5°	524.5	500.5	478.5	456.7	435.5	413.7	396.8	382.5	370.7	362.5	359.9
150°	519.0	498.4	477.8	458.0	438.2	418.4	403.0	390.1	378.9	372.0	369.5
152.5°	514.2	495.0	476.4	458.7	441.0	423.3	409.2	397.0	387.2	380.3	379.1
155°	505.2	489.0	474.3	459.7	445.1	430.5	417.6	408.2	398.7	393.6	392.7
157.5°	496.9	482.8	470.4	459.7	448.1	435.7	424.8	417.2	409.1	404.9	404.1
160°	490.7	478.6	468.3	459.7	449.4	439.1	429.6	422.8	415.9	412.5	411.6
162.5°	485.2	475.2	466.2	459.0	450.1	441.2	433.8	427.6	422.1	418.6	419.1
165°	476.0	468.3	462.3	457.2	451.2	443.4	438.2	433.9	428.8	427.1	427.9
167.5°	467.1	462.3	458.3	456.0	451.0	445.3	442.0	438.9	435.7	434.1	435.1
170°	462.3	458.8	456.3	454.6	450.3	446.0	443.4	441.7	439.1	438.2	440.0
172.5°	457.5	454.8	453.6	452.5	449.6	446.7	444.8	443.8	441.2	441.7	442.7
175°	451.2	450.3	449.4	450.3	448.6	446.9	446.0	446.0	444.3	445.1	446.0
177.5°	447.5	446.9	447.5	448.9	447.5	446.9	446.9	446.9	445.5	446.2	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	566.2	566.6	569.7	571.2	573.9	575.1	576.4	576.0	576.0	576.6	581.0
5°	567.4	571.3	577.1	582.8	588.3	593.0	596.2	599.3	600.5	606.1	611.1
7.5°	565.3	572.6	582.2	590.9	601.2	609.3	616.0	622.2	626.3	634.6	643.0
10°	562.7	572.8	583.8	595.0	609.2	620.0	630.9	639.4	642.0	654.4	661.4
12.5°	557.3	570.9	584.9	599.3	613.3	628.1	640.2	648.6	658.2	669.3	682.3
15°	549.4	565.0	583.2	601.8	621.7	639.7	652.6	667.3	677.9	690.0	701.4
17.5°	538.0	558.1	581.2	602.7	625.8	645.1	662.9	676.9	684.3	691.3	692.9
20°	528.8	550.5	577.7	603.1	626.2	648.5	666.2	677.9	679.8	680.0	669.7
22.5°	519.0	543.5	572.0	598.0	625.6	650.4	664.1	669.1	661.3	648.1	628.0
25°	500.8	529.3	562.3	592.0	622.2	645.6	650.3	641.5	614.3	585.7	549.6
27.5°	481.2	513.2	548.5	581.6	613.7	628.3	618.1	586.3	537.4	494.8	443.2
30°	466.8	502.7	537.4	574.4	604.2	610.4	587.1	540.4	483.3	419.1	367.6
32.5°	450.4	487.9	526.2	564.4	589.3	583.2	544.8	487.2	420.3	357.1	308.6
35°	427.0	465.6	507.0	545.3	561.1	534.7	477.2	402.3	333.8	275.0	241.5
37.5°	399.8	442.0	484.9	520.1	519.0	475.0	396.7	319.3	261.8	227.0	203.2
40°	380.6	423.3	469.6	499.3	486.6	429.3	344.4	271.5	229.4	201.6	184.3
42.5°	362.1	404.9	451.0	474.6	452.5	382.0	297.5	240.3	205.6	184.0	169.9
45°	330.7	375.9	418.5	431.6	392.1	314.5	240.6	199.1	176.0	160.0	150.2
47.5°	300.0	344.5	383.4	383.6	330.2	255.0	202.9	172.3	152.6	140.2	133.1
50°	281.2	323.5	356.1	351.0	290.4	226.9	181.5	155.1	138.7	129.1	121.7
52.5°	260.1	301.1	329.4	315.0	256.8	199.7	162.2	140.1	126.5	118.1	111.5
55°	229.4	265.8	285.8	263.8	209.5	166.1	137.1	119.7	109.5	102.5	96.8
57.5°	199.2	229.3	241.8	216.3	172.5	137.7	116.0	102.9	92.8	87.7	84.8
60°	180.3	206.0	214.7	186.6	150.0	120.5	102.7	90.6	83.1	79.8	76.9
62.5°	161.7	182.6	186.2	160.5	130.8	105.5	90.1	79.9	75.0	71.8	69.1
65°	134.1	149.2	147.5	126.7	103.5	83.7	72.6	66.3	62.6	58.1	53.2
67.5°	110.5	119.7	114.1	98.6	79.0	65.1	57.8	53.0	48.4	44.2	43.0
70°	95.4	100.7	94.9	80.6	64.7	54.6	48.7	43.0	40.3	39.3	37.5
72.5°	81.0	82.9	76.5	64.3	52.7	45.2	39.4	36.3	34.8	34.0	32.9
75°	60.8	59.5	54.0	44.4	36.6	31.5	29.7	28.6	27.6	26.8	26.2
77.5°	42.7	40.7	35.8	29.5	25.5	23.1	22.0	21.4	20.9	20.5	19.9
80°	32.1	30.7	25.8	21.1	19.4	18.2	17.6	16.8	16.8	16.4	15.8
82.5°	23.5	22.0	17.7	15.5	14.6	13.8	13.3	12.9	12.7	12.8	12.4
85°	12.3	10.0	8.8	8.4	7.8	7.4	7.7	7.2	7.2	7.2	7.1
87.5°	4.5	4.3	4.6	4.7	5.4	6.3	7.3	8.4	8.7	8.4	8.4
90°	3.4	6.9	8.6	10.3	12.9	17.2	23.2	28.3	29.2	28.3	27.5
92.5°	15.2	21.4	25.1	30.9	39.0	58.5	85.8	110.1	111.7	94.4	74.9
95°	33.5	42.1	49.9	63.6	84.2	123.7	198.5	298.2	336.8	294.7	225.2
97.5°	53.6	62.8	74.4	90.2	113.6	163.2	267.4	433.1	575.1	603.2	525.4
100°	68.7	76.5	90.2	107.5	131.5	177.0	281.9	467.4	678.8	802.6	784.5
102.5°	83.9	91.6	105.4	123.2	147.3	189.4	282.6	454.4	682.3	876.8	954.3
105°	108.3	114.3	127.2	146.1	170.1	210.5	287.0	428.8	636.7	865.3	1044.0
107.5°	132.3	138.2	150.1	168.8	193.0	232.2	298.9	416.0	588.0	789.9	979.5
110°	149.6	154.6	165.8	183.9	208.8	246.6	308.5	413.4	564.6	742.4	923.8



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	164.6	170.5	181.0	198.3	223.9	260.4	318.8	414.0	549.4	709.5	872.9
115°	189.1	194.2	204.5	221.7	244.9	281.9	334.2	417.6	532.8	668.6	810.3
117.5°	212.6	217.7	226.9	243.3	267.4	301.6	350.8	423.8	524.7	642.7	763.2
120°	227.7	232.9	240.6	257.8	281.9	315.4	361.8	427.9	519.9	629.0	739.9
122.5°	241.4	246.6	255.0	272.2	297.0	328.4	371.3	432.7	517.1	617.3	721.3
125°	260.4	265.5	275.9	293.0	317.1	348.0	386.7	440.0	512.1	600.6	694.3
127.5°	276.4	283.5	294.9	311.4	336.1	366.3	401.0	447.4	509.2	585.2	667.7
130°	285.2	293.9	305.9	323.1	347.2	377.2	409.9	452.9	507.8	574.9	650.5
132.5°	294.2	303.5	316.2	334.1	358.2	386.8	418.8	458.3	507.1	566.6	634.0
135°	305.9	316.2	329.1	348.9	372.9	400.5	430.5	464.9	506.1	555.1	611.0
137.5°	318.3	328.6	342.3	362.0	384.3	411.5	439.5	470.7	505.9	547.0	592.5
140°	326.6	336.8	350.6	369.5	391.8	417.6	444.3	473.5	505.2	542.3	580.9
142.5°	334.8	344.4	358.2	376.3	397.4	422.4	448.4	475.5	505.2	537.4	571.3
145°	348.9	357.5	370.4	387.5	406.5	429.6	453.7	477.8	503.5	531.1	557.7
147.5°	362.5	370.7	382.5	396.8	413.7	435.5	456.7	478.5	500.5	524.5	547.2
150°	372.0	378.9	390.1	403.0	418.4	438.2	458.0	477.8	498.4	519.0	539.7
152.5°	380.3	387.2	397.0	409.2	423.3	441.0	458.7	476.4	495.0	514.2	532.1
155°	393.6	398.7	408.2	417.6	430.5	445.1	459.7	474.3	489.0	505.2	521.6
157.5°	404.9	409.1	417.2	424.8	435.7	448.1	459.7	470.4	482.8	496.9	509.4
160°	412.5	415.9	422.8	429.6	439.1	449.4	459.7	468.3	478.6	490.7	501.8
162.5°	418.6	422.1	427.6	433.8	441.2	450.1	459.0	466.2	475.2	485.2	494.3
165°	427.1	428.8	433.9	438.2	443.4	451.2	457.2	462.3	468.3	476.0	482.9
167.5°	434.1	435.7	438.9	442.0	445.3	451.0	456.0	458.3	462.3	467.1	472.1
170°	438.2	439.1	441.7	443.4	446.0	450.3	454.6	456.3	458.8	462.3	466.6
172.5°	441.7	441.2	443.8	444.8	446.7	449.6	452.5	453.6	454.8	457.5	460.4
175°	445.1	444.3	446.0	446.0	446.9	448.6	450.3	449.4	450.3	451.2	453.7
177.5°	446.2	445.5	446.9	446.9	446.9	447.5	448.9	447.5	446.9	447.5	448.9
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	582.6	584.6	585.6	585.6	586.7	586.2	585.7
5°	616.0	619.7	620.6	624.1	626.6	625.9	626.2
7.5°	649.4	655.3	661.2	663.9	664.3	665.9	666.5
10°	669.9	674.8	683.9	682.6	689.4	693.4	686.9
12.5°	689.6	696.2	702.6	704.3	708.2	709.5	706.9
15°	707.4	710.9	711.3	710.3	711.5	710.5	706.8
17.5°	690.8	685.0	673.5	668.0	663.7	657.2	654.6
20°	663.2	646.4	626.8	619.0	609.8	591.9	596.2
22.5°	603.7	584.6	565.0	542.2	531.2	514.2	513.2
25°	511.3	478.2	441.8	416.4	401.5	384.5	377.0
27.5°	397.5	355.9	326.1	311.0	297.2	283.8	283.2
30°	322.7	291.4	268.4	255.5	247.0	241.3	242.5
32.5°	272.0	250.6	235.0	224.3	218.1	213.8	213.7
35°	222.4	207.7	197.7	193.2	188.7	185.6	185.8
37.5°	190.3	181.5	175.9	171.0	168.2	166.6	165.7
40°	173.8	166.6	162.3	159.4	157.0	154.9	154.5
42.5°	160.9	154.9	150.6	148.3	146.1	144.6	144.2
45°	142.8	137.8	134.0	131.4	130.4	129.1	129.1
47.5°	127.0	122.2	119.2	117.5	115.9	114.9	114.9
50°	116.4	112.6	109.9	108.9	107.5	107.0	106.8
52.5°	106.9	104.0	102.1	101.4	100.8	100.1	100.2
55°	93.8	92.3	91.5	90.9	90.0	88.8	89.5
57.5°	83.0	81.6	79.6	77.7	76.8	75.9	76.3
60°	75.3	72.6	69.8	67.7	67.1	65.3	65.3
62.5°	65.6	61.7	58.4	57.2	56.6	55.8	55.6
65°	50.5	48.9	48.1	47.4	46.9	46.9	46.6
67.5°	41.8	41.2	40.3	40.1	39.8	39.6	39.5
70°	36.9	36.2	35.8	35.6	35.2	35.4	34.8
72.5°	32.3	31.7	31.6	31.1	30.8	30.8	30.4
75°	25.4	25.4	25.2	25.1	24.6	24.5	24.6
77.5°	19.5	19.6	19.3	19.2	19.2	19.2	19.0
80°	15.7	15.8	15.7	15.4	15.2	15.4	15.2
82.5°	12.4	12.1	12.1	12.0	12.0	11.9	11.8
85°	7.1	7.2	7.1	6.9	6.9	6.9	7.1
87.5°	7.8	8.2	8.4	8.4	8.4	8.4	8.2
90°	25.7	27.5	28.3	28.3	28.3	28.3	28.3
92.5°	64.3	57.1	51.7	51.1	48.3	49.0	47.6
95°	172.7	136.6	117.7	106.6	99.7	97.1	98.0
97.5°	429.8	336.8	274.8	233.8	212.6	200.0	192.9
100°	678.0	560.3	456.3	385.0	348.0	323.1	307.6
102.5°	930.3	844.2	734.0	656.5	593.4	562.3	541.4
105°	1141.2	1152.4	1123.9	1070.7	1017.4	980.4	968.5
107.5°	1125.7	1215.0	1256.6	1263.3	1260.4	1253.0	1237.1
110°	1077.5	1187.6	1258.0	1294.9	1311.3	1319.1	1318.2



TEST NUMBER: P331635-935

CATALOG NUMBER: S122RDIP-S290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1020.5	1138.1	1218.8	1270.2	1297.5	1312.2	1316.8
115°	942.6	1055.2	1143.8	1204.7	1244.2	1266.6	1274.4
117.5°	879.4	981.5	1064.5	1126.7	1168.5	1192.1	1198.5
120°	846.4	937.5	1015.7	1075.8	1116.2	1141.2	1149.8
122.5°	818.9	905.2	975.9	1029.8	1069.4	1091.7	1098.9
125°	782.8	858.4	922.9	972.8	1005.4	1026.8	1033.7
127.5°	747.8	819.1	878.6	922.0	952.6	971.2	976.7
130°	724.4	792.3	849.0	891.1	920.3	937.5	944.3
132.5°	702.4	764.7	818.0	859.5	888.7	904.5	910.7
135°	667.7	724.4	772.5	809.4	837.8	853.3	856.7
137.5°	640.0	685.0	726.9	760.7	785.1	798.7	803.8
140°	622.2	661.7	699.5	726.9	749.3	762.2	767.3
142.5°	606.3	640.3	672.0	698.1	718.4	729.9	730.9
145°	586.1	612.7	637.6	658.2	672.9	681.4	684.0
147.5°	569.6	590.3	608.6	625.6	637.2	643.1	644.6
150°	558.5	576.6	592.0	604.9	615.3	620.4	621.3
152.5°	549.6	564.9	578.3	588.4	597.4	601.2	601.3
155°	535.4	548.2	557.7	567.1	573.2	576.6	574.9
157.5°	520.9	531.8	539.2	545.8	550.8	552.3	552.3
160°	511.3	520.7	526.8	532.8	537.1	538.0	538.0
162.5°	502.3	510.4	515.1	521.1	524.0	524.9	524.2
165°	489.0	495.0	498.4	501.8	505.2	505.2	504.4
167.5°	476.7	480.9	484.0	485.5	487.4	487.2	486.2
170°	469.2	472.6	474.3	475.2	477.8	476.9	475.2
172.5°	462.3	465.0	466.1	466.9	468.1	467.3	466.2
175°	454.6	455.5	456.3	456.3	457.2	456.3	454.6
177.5°	448.9	449.6	449.6	449.6	449.6	448.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9

(END OF REPORT)