

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331711-935

Luminaire Tested: **S122RDIP-S865D530U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331711-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D530U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4662.8 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	94	90	95	91	88	85	80	78	75	70	68	66	60	59	58	53
2	93	86	80	75	87	81	76	72	71	67	64	62	59	57	54	52	50	46
3	86	77	70	64	80	72	66	61	64	59	55	56	52	49	49	46	44	40
4	79	69	61	55	74	65	58	53	57	52	48	51	47	43	44	41	39	36
5	73	62	54	48	68	58	51	46	52	47	42	46	42	38	41	37	35	32
6	68	56	48	43	63	53	46	41	47	42	38	42	38	34	37	34	31	28
7	63	51	43	38	59	48	41	37	43	38	34	39	34	31	34	31	28	26
8	59	47	39	34	55	44	38	33	40	34	30	36	31	28	32	28	26	23
9	55	43	36	31	52	41	34	30	37	31	28	33	29	26	30	26	23	21
10	51	40	33	28	48	38	31	27	34	29	25	31	27	23	28	24	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26547	26547	26547	26547
5°	29648	26712	23686	26712
10°	32893	26525	20530	26525
15°	34511	26136	16177	26136
20°	29919	25560	13998	25560
25°	19621	24772	12497	24772
30°	13207	23815	11311	23815
35°	10697	22610	10200	22610
40°	9512	21300	9440	21300
45°	8608	19763	8426	19763
50°	7834	18239	7804	18239
55°	7367	16549	7268	16549
60°	6161	14996	6090	14996
65°	5196	13620	5891	13620
70°	4801	12161	5556	12161
75°	4492	10586	5128	10586
80°	4147	8712	4575	8712
85°	3816	6873	4020	6873



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.9	3.3
10°-20°	434.3	9.3
20°-30°	559.6	12.0
30°-40°	531.8	11.4
40°-50°	455.6	9.8
50°-60°	346.9	7.4
60°-70°	219.3	4.7
70°-80°	109.5	2.3
80°-90°	30.0	0.6
90°-100°	20.7	0.4
100°-110°	76.0	1.6
110°-120°	203.0	4.4
120°-130°	335.2	7.2
130°-140°	356.5	7.6
140°-150°	331.3	7.1
150°-160°	266.4	5.7
160°-170°	171.7	3.7
170°-180°	59.1	1.3
0°-30°	1149.8	24.7
0°-40°	1681.6	36.1
0°-60°	2484.1	53.3
0°-90°	2843.0	61.0
90°-120°	299.7	6.4
90°-150°	1322.7	28.4
90°-180°	1820.0	39.0
0°-180°	4662.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1829	1648	1461	1648	1829	181
15°	2065	1564	968	1564	2065	557
25°	1101	1390	702	1390	1101	523
35°	543	1147	518	1147	543	347
45°	377	866	369	866	377	292
55°	262	588	258	588	262	230
65°	136	356	154	356	136	138
75°	72	170	82	170	72	76
85°	21	37	22	37	21	22
90°	12	0	12	0	12	6
95°	19	29	19	29	19	18
105°	34	137	34	137	34	36
115°	37	258	37	258	37	92
125°	384	365	384	365	384	332
135°	467	452	467	452	467	360
145°	532	524	532	524	532	333
155°	578	577	578	577	578	267
165°	607	608	607	608	607	171
175°	619	622	619	622	619	59
180°	621	621	621	621	621	



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1710.9	1712.3	1713.6	1710.4	1710.4	1707.7	1701.8	1697.2	1684.4	1682.6	1682.6
5°	1829.3	1828.1	1830.4	1823.0	1812.7	1810.4	1799.6	1785.3	1770.4	1753.9	1750.4
7.5°	1946.9	1945.2	1940.6	1939.4	1931.5	1914.3	1896.8	1878.2	1853.5	1829.4	1817.2
10°	2006.3	2025.2	2013.8	1993.7	1997.8	1970.9	1956.6	1932.1	1911.5	1875.5	1867.5
12.5°	2064.9	2072.3	2068.6	2057.3	2052.2	2033.5	2014.2	1992.9	1954.9	1922.6	1894.5
15°	2064.6	2075.4	2078.3	2074.9	2077.8	2076.6	2066.3	2048.6	2015.5	1980.0	1949.2
17.5°	1912.2	1919.8	1938.5	1951.1	1967.1	2001.0	2017.7	2024.1	2019.2	1999.0	1977.3
20°	1741.3	1728.7	1781.2	1808.1	1830.9	1888.1	1937.2	1956.1	1986.3	1985.8	1980.0
22.5°	1499.0	1502.0	1551.9	1583.7	1650.5	1707.5	1763.6	1834.5	1893.1	1931.8	1954.5
25°	1101.4	1123.2	1172.9	1216.2	1290.6	1396.8	1493.3	1605.3	1711.0	1794.4	1873.8
27.5°	827.2	828.8	868.2	908.4	952.4	1039.5	1161.1	1294.8	1445.4	1569.8	1712.8
30°	708.4	705.0	721.5	746.1	783.8	851.2	942.6	1074.0	1224.3	1411.6	1578.5
32.5°	624.3	624.5	637.0	655.1	686.5	731.9	794.5	901.3	1043.3	1227.4	1423.1
35°	542.7	542.2	551.3	564.4	577.6	606.7	649.5	705.5	803.2	975.2	1175.1
37.5°	484.2	486.7	491.2	499.4	513.9	530.1	555.9	593.5	663.1	764.7	932.8
40°	451.3	452.5	458.7	465.6	474.2	486.7	507.9	538.1	589.0	670.1	792.9
42.5°	421.1	422.3	426.7	433.2	439.9	452.5	469.9	496.1	537.4	600.6	702.0
45°	377.0	377.0	381.1	383.9	391.3	402.8	417.1	438.8	467.3	514.2	581.6
47.5°	335.7	335.8	338.5	343.4	348.0	357.0	371.0	388.7	409.5	445.7	503.3
50°	311.9	312.5	314.2	318.2	321.1	329.1	339.9	355.3	377.0	405.0	453.1
52.5°	292.7	292.4	294.5	296.3	298.3	303.9	312.0	325.6	345.1	369.4	409.1
55°	261.7	259.3	262.8	265.6	267.3	269.7	274.2	282.8	299.4	319.9	349.7
57.5°	222.8	221.9	224.3	226.9	232.3	238.4	242.4	247.8	256.4	271.1	300.6
60°	190.8	190.8	196.0	197.7	204.0	212.0	220.0	224.5	233.1	242.8	264.5
62.5°	162.5	162.9	165.3	167.0	170.6	180.4	191.6	201.6	209.7	219.0	233.4
65°	136.0	137.1	137.1	138.3	140.5	142.8	147.4	155.4	169.7	182.8	193.6
67.5°	115.4	115.7	116.1	117.3	117.8	120.3	122.2	125.7	129.0	141.5	154.9
70°	101.7	103.4	102.8	104.0	104.5	105.6	108.0	109.7	114.9	117.7	125.7
72.5°	88.9	90.1	90.1	90.7	92.2	92.5	94.3	96.0	99.3	101.7	106.0
75°	72.0	71.4	72.0	73.1	73.7	74.3	74.3	76.5	78.3	80.6	83.4
77.5°	55.5	56.1	56.0	56.1	56.2	57.3	57.2	58.1	59.8	61.0	62.4
80°	44.6	45.1	44.6	45.1	45.7	46.2	45.7	46.2	48.0	49.2	49.2
82.5°	34.5	34.6	35.0	35.0	35.2	35.3	36.1	36.2	37.5	37.3	37.7
85°	20.6	20.0	20.0	20.0	20.6	21.1	20.6	20.6	21.1	21.1	21.1
87.5°	9.7	10.2	10.1	10.1	10.1	10.0	9.9	10.2	9.6	10.0	9.4
90°	12.1	12.0	11.7	11.5	11.4	11.0	10.5	10.0	9.5	9.0	8.2
92.5°	12.1	12.1	11.9	11.8	11.6	11.5	11.2	10.9	10.7	10.4	10.0
95°	19.3	19.5	19.5	19.6	19.7	19.5	19.0	18.5	18.0	17.6	16.8
97.5°	25.8	25.7	25.6	25.4	25.3	25.1	24.6	24.3	23.8	23.4	21.9
100°	30.1	29.9	29.7	29.5	29.3	28.8	28.0	27.2	26.4	25.6	23.9
102.5°	32.3	31.9	31.7	31.4	31.2	30.5	29.4	28.4	27.4	26.3	40.6
105°	34.2	33.8	33.3	33.0	32.5	31.8	30.7	29.6	28.5	27.4	54.7
107.5°	35.1	34.7	34.4	33.9	33.6	33.9	35.0	36.2	37.3	38.4	71.0
110°	35.5	35.1	34.7	34.3	33.9	38.7	48.6	58.6	68.6	78.6	107.5



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	35.8	35.6	35.2	34.9	34.6	52.6	89.0	125.4	161.9	198.4	205.4
115°	36.9	44.0	51.2	58.4	65.6	92.3	138.5	184.8	231.0	277.2	274.7
117.5°	150.4	174.1	197.7	221.3	245.0	262.3	273.5	284.7	295.9	307.0	305.4
120°	274.1	287.6	301.1	314.5	328.0	334.2	332.9	331.7	330.5	329.3	327.5
122.5°	342.0	344.7	347.2	349.9	352.5	353.4	352.8	352.0	351.3	350.6	348.6
125°	384.2	383.9	383.6	383.3	383.0	382.5	381.8	381.1	380.4	379.7	377.8
127.5°	410.8	410.7	410.7	410.6	410.5	410.0	409.0	407.9	406.9	406.0	404.5
130°	427.3	427.4	427.5	427.6	427.7	427.2	426.1	425.0	424.0	422.8	421.7
132.5°	443.5	443.6	443.7	443.8	443.8	443.5	442.6	441.6	440.7	439.7	438.6
135°	466.8	467.1	467.3	467.4	467.7	467.3	466.2	465.3	464.3	463.2	462.4
137.5°	488.2	488.5	488.8	489.1	489.5	489.2	488.2	487.2	486.3	485.3	484.2
140°	501.4	502.0	502.5	502.9	503.4	503.3	502.3	501.4	500.6	499.6	498.5
142.5°	514.4	514.9	515.4	515.9	516.4	516.3	515.4	514.6	513.8	513.0	511.7
145°	532.4	533.0	533.5	534.0	534.4	534.3	533.6	533.0	532.3	531.6	529.9
147.5°	548.4	548.8	549.2	549.7	550.0	550.0	549.5	549.0	548.5	547.9	546.2
150°	558.1	558.5	559.0	559.6	560.1	560.0	559.4	558.8	558.2	557.6	556.0
152.5°	566.4	567.0	567.7	568.3	568.9	569.0	568.4	567.8	567.2	566.6	565.1
155°	577.8	578.7	579.5	580.2	581.0	581.2	580.6	580.0	579.4	578.8	577.6
157.5°	588.3	589.1	589.9	590.6	591.5	591.5	590.8	590.1	589.4	588.8	588.0
160°	594.4	595.1	595.9	596.6	597.3	597.3	596.7	596.1	595.6	595.0	594.3
162.5°	599.5	600.4	601.2	602.1	603.0	603.0	602.4	601.7	601.0	600.3	599.8
165°	607.0	607.8	608.5	609.2	609.8	609.8	609.2	608.5	607.8	607.0	606.7
167.5°	611.8	612.7	613.6	614.5	615.4	615.5	614.8	614.1	613.4	612.7	612.4
170°	614.7	615.6	616.5	617.3	618.3	618.4	617.7	617.0	616.3	615.6	615.4
172.5°	616.8	617.8	618.6	619.6	620.4	620.5	619.8	619.1	618.5	617.8	617.5
175°	618.7	619.7	620.7	621.7	622.8	622.8	622.2	621.5	620.8	620.1	619.8
177.5°	619.9	620.6	621.3	622.1	622.8	622.8	622.3	621.7	621.2	620.6	620.5
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1683.4	1679.8	1676.6	1668.4	1664.2	1655.1	1653.7	1653.3	1641.4	1630.0	1626.8
5°	1741.3	1732.2	1718.4	1702.5	1685.8	1668.7	1657.3	1648.1	1625.3	1603.6	1591.0
7.5°	1799.6	1779.9	1756.3	1726.0	1700.7	1672.4	1651.3	1632.5	1600.1	1569.0	1548.1
10°	1843.0	1810.9	1779.5	1737.8	1705.3	1673.3	1643.6	1617.9	1581.3	1540.2	1511.1
12.5°	1869.9	1834.7	1791.4	1750.7	1708.5	1667.8	1628.1	1595.0	1552.0	1509.6	1474.9
15°	1906.3	1868.6	1816.1	1757.8	1703.6	1650.5	1604.7	1563.6	1507.6	1456.7	1414.5
17.5°	1936.2	1884.3	1827.9	1760.5	1697.6	1630.1	1571.2	1518.7	1456.4	1395.1	1345.2
20°	1945.8	1894.4	1829.3	1761.9	1687.6	1608.2	1544.7	1487.6	1420.7	1353.9	1296.8
22.5°	1939.8	1899.9	1827.4	1746.7	1670.7	1587.6	1516.0	1449.7	1375.5	1307.3	1241.0
25°	1899.5	1885.8	1817.2	1729.2	1642.4	1545.9	1463.0	1390.5	1306.0	1232.9	1160.8
27.5°	1805.5	1835.0	1792.6	1698.8	1602.3	1498.8	1405.7	1323.1	1235.4	1153.1	1081.3
30°	1715.0	1783.0	1764.7	1677.8	1569.9	1468.2	1363.7	1277.4	1183.7	1099.2	1028.3
32.5°	1591.1	1703.4	1721.3	1648.6	1537.0	1425.2	1315.7	1229.9	1132.0	1042.9	973.9
35°	1394.0	1561.9	1639.0	1592.8	1480.7	1360.2	1247.1	1147.1	1048.9	960.9	892.3
37.5°	1158.6	1387.4	1516.0	1519.2	1416.4	1291.1	1167.9	1068.7	968.1	881.8	807.5
40°	1006.0	1254.0	1421.3	1458.4	1371.7	1236.2	1111.7	1010.6	912.3	827.8	742.7
42.5°	868.9	1115.9	1321.7	1386.3	1317.2	1182.8	1057.8	952.1	856.6	776.6	689.7
45°	702.7	918.6	1145.4	1260.8	1222.5	1098.0	966.0	865.5	775.8	706.7	623.3
47.5°	592.8	744.9	964.4	1120.5	1119.8	1006.2	876.3	780.1	696.8	632.1	564.6
50°	530.1	662.7	848.3	1025.5	1040.3	944.9	821.5	726.1	648.4	580.4	526.2
52.5°	473.9	583.2	750.1	919.9	962.2	879.5	759.8	671.8	596.3	533.8	487.3
55°	400.5	485.0	611.8	770.7	834.7	776.4	670.1	587.9	526.8	474.2	434.2
57.5°	338.8	402.2	503.9	631.8	706.4	669.7	582.0	515.2	462.9	415.3	383.7
60°	299.9	351.9	438.2	545.0	627.2	601.6	526.8	464.4	419.9	378.8	349.0
62.5°	263.4	308.1	381.9	468.6	544.1	533.5	472.3	420.1	381.1	343.5	318.4
65°	212.0	244.5	302.2	370.2	430.8	435.9	391.9	356.5	321.7	292.0	269.7
67.5°	168.8	190.0	230.7	287.9	333.3	349.5	322.6	295.6	267.9	245.0	225.7
70°	142.2	159.4	189.1	235.4	277.1	294.2	278.8	257.6	233.7	214.8	198.2
72.5°	115.3	132.0	153.9	187.9	223.6	242.1	236.8	221.5	202.1	186.5	170.8
75°	86.9	92.0	106.9	129.7	157.6	173.7	177.7	169.7	154.2	142.2	133.1
77.5°	64.2	67.3	74.4	86.4	104.7	118.9	124.8	123.8	113.2	106.2	97.7
80°	51.4	53.1	56.6	61.7	75.4	89.7	93.7	93.7	86.3	83.4	74.8
82.5°	39.1	40.3	42.4	45.2	51.7	64.1	68.5	69.5	64.7	61.0	54.2
85°	22.3	21.7	22.8	24.5	25.7	29.1	36.0	37.1	36.0	31.4	29.7
87.5°	9.2	9.6	9.4	8.7	9.0	9.2	11.3	13.3	11.7	10.6	9.9
90°	7.4	6.6	5.8	4.8	3.7	2.7	1.5	0.4	1.5	2.7	3.7
92.5°	9.6	9.2	8.9	8.7	8.8	8.9	9.0	9.0	9.0	8.9	8.8
95°	16.1	15.4	14.7	16.0	19.3	22.6	25.9	29.2	25.9	22.6	19.3
97.5°	20.2	18.6	17.0	20.8	30.1	39.4	48.6	57.9	48.6	39.4	30.1
100°	22.2	20.5	18.9	24.8	38.5	52.2	65.9	79.6	65.9	52.2	38.5
102.5°	54.8	69.0	83.1	91.7	94.5	97.5	100.4	103.2	100.4	97.5	94.5
105°	82.0	109.2	136.5	148.6	145.6	142.6	139.6	136.6	139.6	142.6	145.6
107.5°	103.8	136.5	169.1	184.3	181.8	179.4	177.0	174.6	177.0	179.4	181.8
110°	136.4	165.2	194.1	207.4	205.3	203.3	201.1	199.1	201.1	203.3	205.3



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	212.6	219.7	226.9	229.5	227.6	225.8	223.9	222.1	223.9	225.8	227.6
115°	272.2	269.8	267.3	265.2	263.5	261.7	260.0	258.4	260.0	261.7	263.5
117.5°	303.7	302.0	300.2	298.4	296.5	294.6	292.7	290.8	292.7	294.6	296.5
120°	325.8	324.0	322.2	320.6	319.0	317.5	316.0	314.5	316.0	317.5	319.0
122.5°	346.6	344.7	342.8	341.0	339.4	337.9	336.2	334.7	336.2	337.9	339.4
125°	375.9	374.0	372.1	370.5	369.2	367.9	366.6	365.3	366.6	367.9	369.2
127.5°	403.1	401.7	400.3	398.8	397.4	396.0	394.5	393.0	394.5	396.0	397.4
130°	420.6	419.6	418.4	417.1	415.5	413.9	412.2	410.7	412.2	413.9	415.5
132.5°	437.6	436.4	435.3	434.1	432.7	431.4	430.0	428.7	430.0	431.4	432.7
135°	461.5	460.5	459.7	458.4	456.8	455.2	453.7	452.0	453.7	455.2	456.8
137.5°	483.3	482.2	481.2	480.1	479.0	477.9	476.7	475.7	476.7	477.9	479.0
140°	497.5	496.4	495.2	494.3	493.5	492.8	491.9	491.1	491.9	492.8	493.5
142.5°	510.4	509.2	507.9	507.0	506.2	505.5	504.8	504.0	504.8	505.5	506.2
145°	528.1	526.5	524.8	524.0	524.1	524.2	524.3	524.3	524.3	524.2	524.1
147.5°	544.6	542.9	541.2	540.5	541.0	541.3	541.7	542.1	541.7	541.3	541.0
150°	554.4	552.8	551.2	550.8	551.5	552.2	552.8	553.5	552.8	552.2	551.5
152.5°	563.6	562.1	560.5	560.2	560.9	561.7	562.5	563.3	562.5	561.7	560.9
155°	576.4	575.1	573.9	573.8	574.7	575.6	576.5	577.4	576.5	575.6	574.7
157.5°	587.1	586.3	585.5	585.4	586.2	586.9	587.7	588.4	587.7	586.9	586.2
160°	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0	594.3	593.7	593.1
162.5°	599.3	598.7	598.2	598.3	598.8	599.4	600.0	600.6	600.0	599.4	598.8
165°	606.4	606.1	605.9	606.0	606.6	607.2	607.8	608.4	607.8	607.2	606.6
167.5°	612.2	611.8	611.6	611.7	612.3	612.9	613.5	614.2	613.5	612.9	612.3
170°	615.2	615.0	614.8	615.0	615.6	616.2	616.8	617.3	616.8	616.2	615.6
172.5°	617.3	617.2	616.9	617.2	617.8	618.4	619.0	619.6	619.0	618.4	617.8
175°	619.7	619.5	619.3	619.5	620.3	621.0	621.6	622.3	621.6	621.0	620.3
177.5°	620.4	620.4	620.3	620.5	621.1	621.6	622.2	622.8	622.2	621.6	621.1
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1620.8	1617.6	1611.7	1602.6	1597.1	1587.5	1581.1	1584.8	1585.6	1584.8	1583.8
5°	1577.3	1565.3	1548.8	1532.8	1517.9	1501.9	1492.7	1488.8	1480.7	1476.2	1473.9
7.5°	1524.7	1504.0	1480.5	1452.7	1429.0	1404.2	1391.5	1385.3	1368.9	1359.9	1352.2
10°	1485.3	1452.8	1429.3	1392.8	1370.5	1337.9	1315.7	1316.2	1293.9	1281.3	1272.2
12.5°	1441.9	1406.2	1367.2	1334.3	1303.3	1277.1	1250.3	1239.4	1215.8	1203.7	1179.0
15°	1369.9	1328.3	1287.1	1242.5	1211.1	1170.5	1131.7	1084.3	1046.0	1012.9	1003.8
17.5°	1291.3	1239.7	1198.4	1146.1	1092.3	1024.1	979.0	951.5	928.4	910.9	897.9
20°	1237.4	1184.8	1140.8	1062.0	989.5	943.2	910.1	888.9	865.0	846.1	835.8
22.5°	1180.7	1125.8	1065.9	977.9	921.4	884.2	854.7	830.4	814.2	799.4	790.1
25°	1100.3	1040.3	941.5	880.9	835.2	796.3	775.8	761.0	743.8	723.8	714.6
27.5°	1015.3	919.9	848.9	803.9	760.3	735.0	716.5	694.3	679.0	670.0	660.5
30°	951.7	856.4	800.9	751.8	720.9	692.9	671.2	658.7	643.9	628.4	622.2
32.5°	880.9	804.7	751.6	710.7	679.3	655.5	638.3	618.0	607.3	597.8	584.6
35°	792.9	735.2	686.6	653.6	623.9	604.4	584.4	572.4	553.0	545.0	539.8
37.5°	718.4	668.4	632.1	597.2	573.7	552.2	539.9	520.9	512.5	501.4	490.5
40°	676.4	627.2	592.5	563.9	537.6	521.6	506.2	490.8	478.2	473.0	459.9
42.5°	633.4	593.5	558.6	527.3	509.7	492.8	473.3	461.9	448.9	440.6	432.5
45°	574.1	538.7	509.0	483.3	463.9	446.2	433.6	414.7	407.3	390.7	383.9
47.5°	522.0	489.1	460.8	436.4	417.4	405.9	387.4	372.7	360.8	350.7	341.8
50°	485.0	457.6	430.2	408.5	391.3	374.8	355.9	348.4	330.2	325.0	319.9
52.5°	451.2	425.2	400.0	378.8	361.6	345.5	328.9	319.3	306.9	301.8	298.0
55°	403.9	378.8	354.7	335.9	318.7	302.2	292.0	279.9	274.2	270.2	265.6
57.5°	356.4	333.7	315.4	296.3	279.1	265.9	254.0	246.8	240.8	235.6	230.1
60°	326.2	304.4	287.9	270.2	252.5	241.7	232.5	223.9	217.1	209.1	206.8
62.5°	294.2	275.3	260.0	242.8	227.4	217.4	208.7	200.6	192.4	180.7	177.5
65°	250.2	235.4	219.4	205.1	191.4	181.7	169.1	160.0	156.5	155.4	154.8
67.5°	210.4	196.4	182.7	168.1	155.6	146.6	140.2	138.8	136.4	135.7	134.1
70°	183.9	170.8	157.1	143.4	131.4	129.7	127.4	125.1	122.3	121.1	119.9
72.5°	160.1	146.6	132.9	121.9	116.8	114.6	112.3	110.0	108.1	106.9	106.2
75°	122.9	110.3	101.1	97.1	94.3	92.6	89.1	87.4	86.3	84.6	83.9
77.5°	88.4	81.4	77.1	74.6	71.6	69.8	67.8	66.1	64.9	64.6	63.6
80°	67.4	64.0	61.1	57.7	56.6	54.2	53.7	52.0	52.5	50.9	50.9
82.5°	52.3	48.0	45.5	44.0	42.9	41.0	40.5	39.6	39.8	38.5	38.5
85°	26.9	25.7	24.5	23.4	23.4	21.7	22.3	21.7	21.7	20.6	20.0
87.5°	9.6	9.4	8.6	8.8	9.0	8.6	8.8	8.4	8.5	8.6	8.2
90°	4.8	5.8	6.6	7.4	8.2	9.0	9.5	10.0	10.5	11.0	11.4
92.5°	8.7	8.9	9.2	9.6	10.0	10.4	10.7	10.9	11.2	11.5	11.6
95°	16.0	14.7	15.4	16.1	16.8	17.6	18.0	18.5	19.0	19.5	19.7
97.5°	20.8	17.0	18.6	20.2	21.9	23.4	23.8	24.3	24.6	25.1	25.3
100°	24.8	18.9	20.5	22.2	23.9	25.6	26.4	27.2	28.0	28.8	29.3
102.5°	91.7	83.1	69.0	54.8	40.6	26.3	27.4	28.4	29.4	30.5	31.2
105°	148.6	136.5	109.2	82.0	54.7	27.4	28.5	29.6	30.7	31.8	32.5
107.5°	184.3	169.1	136.5	103.8	71.0	38.4	37.3	36.2	35.0	33.9	33.6
110°	207.4	194.1	165.2	136.4	107.5	78.6	68.6	58.6	48.6	38.7	33.9



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	229.5	226.9	219.7	212.6	205.4	198.4	161.9	125.4	89.0	52.6	34.6
115°	265.2	267.3	269.8	272.2	274.7	277.2	231.0	184.8	138.5	92.3	65.6
117.5°	298.4	300.2	302.0	303.7	305.4	307.0	295.9	284.7	273.5	262.3	245.0
120°	320.6	322.2	324.0	325.8	327.5	329.3	330.5	331.7	332.9	334.2	328.0
122.5°	341.0	342.8	344.7	346.6	348.6	350.6	351.3	352.0	352.8	353.4	352.5
125°	370.5	372.1	374.0	375.9	377.8	379.7	380.4	381.1	381.8	382.5	383.0
127.5°	398.8	400.3	401.7	403.1	404.5	406.0	406.9	407.9	409.0	410.0	410.5
130°	417.1	418.4	419.6	420.6	421.7	422.8	424.0	425.0	426.1	427.2	427.7
132.5°	434.1	435.3	436.4	437.6	438.6	439.7	440.7	441.6	442.6	443.5	443.8
135°	458.4	459.7	460.5	461.5	462.4	463.2	464.3	465.3	466.2	467.3	467.7
137.5°	480.1	481.2	482.2	483.3	484.2	485.3	486.3	487.2	488.2	489.2	489.5
140°	494.3	495.2	496.4	497.5	498.5	499.6	500.6	501.4	502.3	503.3	503.4
142.5°	507.0	507.9	509.2	510.4	511.7	513.0	513.8	514.6	515.4	516.3	516.4
145°	524.0	524.8	526.5	528.1	529.9	531.6	532.3	533.0	533.6	534.3	534.4
147.5°	540.5	541.2	542.9	544.6	546.2	547.9	548.5	549.0	549.5	550.0	550.0
150°	550.8	551.2	552.8	554.4	556.0	557.6	558.2	558.8	559.4	560.0	560.1
152.5°	560.2	560.5	562.1	563.6	565.1	566.6	567.2	567.8	568.4	569.0	568.9
155°	573.8	573.9	575.1	576.4	577.6	578.8	579.4	580.0	580.6	581.2	581.0
157.5°	585.4	585.5	586.3	587.1	588.0	588.8	589.4	590.1	590.8	591.5	591.5
160°	592.5	592.5	593.1	593.7	594.3	595.0	595.6	596.1	596.7	597.3	597.3
162.5°	598.3	598.2	598.7	599.3	599.8	600.3	601.0	601.7	602.4	603.0	603.0
165°	606.0	605.9	606.1	606.4	606.7	607.0	607.8	608.5	609.2	609.8	609.8
167.5°	611.7	611.6	611.8	612.2	612.4	612.7	613.4	614.1	614.8	615.5	615.4
170°	615.0	614.8	615.0	615.2	615.4	615.6	616.3	617.0	617.7	618.4	618.3
172.5°	617.2	616.9	617.2	617.3	617.5	617.8	618.5	619.1	619.8	620.5	620.4
175°	619.5	619.3	619.5	619.7	619.8	620.1	620.8	621.5	622.2	622.8	622.8
177.5°	620.5	620.3	620.4	620.4	620.5	620.6	621.2	621.7	622.3	622.8	622.8
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1578.8	1579.7	1578.3	1579.2	1578.3	1579.7	1578.8	1583.8	1584.8	1585.6	1584.8
5°	1471.0	1464.2	1463.0	1461.4	1463.0	1464.2	1471.0	1473.9	1476.2	1480.7	1488.8
7.5°	1342.4	1341.4	1338.5	1334.6	1338.5	1341.4	1342.4	1352.2	1359.9	1368.9	1385.3
10°	1259.6	1256.8	1256.3	1252.2	1256.3	1256.8	1259.6	1272.2	1281.3	1293.9	1316.2
12.5°	1162.8	1144.4	1142.5	1132.5	1142.5	1144.4	1162.8	1179.0	1203.7	1215.8	1239.4
15°	990.1	986.6	975.2	967.8	975.2	986.6	990.1	1003.8	1012.9	1046.0	1084.3
17.5°	891.3	880.1	876.6	874.9	876.6	880.1	891.3	897.9	910.9	928.4	951.5
20°	827.8	817.5	815.8	814.7	815.8	817.5	827.8	835.8	846.1	865.0	888.9
22.5°	783.9	773.2	768.7	765.3	768.7	773.2	783.9	790.1	799.4	814.2	830.4
25°	708.9	705.0	702.7	701.5	702.7	705.0	708.9	714.6	723.8	743.8	761.0
27.5°	650.3	641.5	639.8	636.9	639.8	641.5	650.3	660.5	670.0	679.0	694.3
30°	617.0	614.2	610.1	606.7	610.1	614.2	617.0	622.2	628.4	643.9	658.7
32.5°	577.6	575.3	571.7	570.2	571.7	575.3	577.6	584.6	597.8	607.3	618.0
35°	534.2	526.2	522.7	517.5	522.7	526.2	534.2	539.8	545.0	553.0	572.4
37.5°	488.1	483.9	479.1	480.8	479.1	483.9	488.1	490.5	501.4	512.5	520.9
40°	452.5	449.6	448.5	447.9	448.5	449.6	452.5	459.9	473.0	478.2	490.8
42.5°	424.1	416.2	413.3	413.1	413.3	416.2	424.1	432.5	440.6	448.9	461.9
45°	381.1	373.6	368.5	369.0	368.5	373.6	381.1	383.9	390.7	407.3	414.7
47.5°	336.9	336.7	333.6	334.6	333.6	336.7	336.9	341.8	350.7	360.8	372.7
50°	315.9	312.5	310.2	310.7	310.2	312.5	315.9	319.9	325.0	330.2	348.4
52.5°	295.8	292.8	291.0	293.4	291.0	292.8	295.8	298.0	301.8	306.9	319.3
55°	262.8	259.3	258.8	258.2	258.8	259.3	262.8	265.6	270.2	274.2	279.9
57.5°	225.9	223.6	220.2	218.7	220.2	223.6	225.9	230.1	235.6	240.8	246.8
60°	199.4	194.8	189.1	188.6	189.1	194.8	199.4	206.8	209.1	217.1	223.9
62.5°	175.1	174.3	173.1	173.0	173.1	174.3	175.1	177.5	180.7	192.4	200.6
65°	153.7	153.1	153.7	154.2	153.7	153.1	153.7	154.8	155.4	156.5	160.0
67.5°	133.9	132.9	131.8	132.3	131.8	132.9	133.9	134.1	135.7	136.4	138.8
70°	118.8	118.2	117.7	117.7	117.7	118.2	118.8	119.9	121.1	122.3	125.1
72.5°	104.2	104.1	103.5	103.1	103.5	104.1	104.2	106.2	106.9	108.1	110.0
75°	83.4	82.2	82.2	82.2	82.2	82.2	83.4	83.9	84.6	86.3	87.4
77.5°	63.5	62.9	62.4	61.9	62.4	62.9	63.5	63.6	64.6	64.9	66.1
80°	50.3	49.7	49.2	49.2	49.2	49.7	50.3	50.9	50.9	52.5	52.0
82.5°	38.4	37.8	37.7	37.3	37.7	37.8	38.4	38.5	38.5	39.8	39.6
85°	20.6	21.1	20.6	21.7	20.6	21.1	20.6	20.0	20.6	21.7	21.7
87.5°	8.3	7.8	8.4	7.9	8.4	7.8	8.3	8.2	8.6	8.5	8.4
90°	11.5	11.7	12.0	12.1	12.0	11.7	11.5	11.4	11.0	10.5	10.0
92.5°	11.8	11.9	12.1	12.1	12.1	11.9	11.8	11.6	11.5	11.2	10.9
95°	19.6	19.5	19.5	19.3	19.5	19.5	19.6	19.7	19.5	19.0	18.5
97.5°	25.4	25.6	25.7	25.8	25.7	25.6	25.4	25.3	25.1	24.6	24.3
100°	29.5	29.7	29.9	30.1	29.9	29.7	29.5	29.3	28.8	28.0	27.2
102.5°	31.4	31.7	31.9	32.3	31.9	31.7	31.4	31.2	30.5	29.4	28.4
105°	33.0	33.3	33.8	34.2	33.8	33.3	33.0	32.5	31.8	30.7	29.6
107.5°	33.9	34.4	34.7	35.1	34.7	34.4	33.9	33.6	33.9	35.0	36.2
110°	34.3	34.7	35.1	35.5	35.1	34.7	34.3	33.9	38.7	48.6	58.6



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	34.9	35.2	35.6	35.8	35.6	35.2	34.9	34.6	52.6	89.0	125.4
115°	58.4	51.2	44.0	36.9	44.0	51.2	58.4	65.6	92.3	138.5	184.8
117.5°	221.3	197.7	174.1	150.4	174.1	197.7	221.3	245.0	262.3	273.5	284.7
120°	314.5	301.1	287.6	274.1	287.6	301.1	314.5	328.0	334.2	332.9	331.7
122.5°	349.9	347.2	344.7	342.0	344.7	347.2	349.9	352.5	353.4	352.8	352.0
125°	383.3	383.6	383.9	384.2	383.9	383.6	383.3	383.0	382.5	381.8	381.1
127.5°	410.6	410.7	410.7	410.8	410.7	410.7	410.6	410.5	410.0	409.0	407.9
130°	427.6	427.5	427.4	427.3	427.4	427.5	427.6	427.7	427.2	426.1	425.0
132.5°	443.8	443.7	443.6	443.5	443.6	443.7	443.8	443.8	443.5	442.6	441.6
135°	467.4	467.3	467.1	466.8	467.1	467.3	467.4	467.7	467.3	466.2	465.3
137.5°	489.1	488.8	488.5	488.2	488.5	488.8	489.1	489.5	489.2	488.2	487.2
140°	502.9	502.5	502.0	501.4	502.0	502.5	502.9	503.4	503.3	502.3	501.4
142.5°	515.9	515.4	514.9	514.4	514.9	515.4	515.9	516.4	516.3	515.4	514.6
145°	534.0	533.5	533.0	532.4	533.0	533.5	534.0	534.4	534.3	533.6	533.0
147.5°	549.7	549.2	548.8	548.4	548.8	549.2	549.7	550.0	550.0	549.5	549.0
150°	559.6	559.0	558.5	558.1	558.5	559.0	559.6	560.1	560.0	559.4	558.8
152.5°	568.3	567.7	567.0	566.4	567.0	567.7	568.3	568.9	569.0	568.4	567.8
155°	580.2	579.5	578.7	577.8	578.7	579.5	580.2	581.0	581.2	580.6	580.0
157.5°	590.6	589.9	589.1	588.3	589.1	589.9	590.6	591.5	591.5	590.8	590.1
160°	596.6	595.9	595.1	594.4	595.1	595.9	596.6	597.3	597.3	596.7	596.1
162.5°	602.1	601.2	600.4	599.5	600.4	601.2	602.1	603.0	603.0	602.4	601.7
165°	609.2	608.5	607.8	607.0	607.8	608.5	609.2	609.8	609.8	609.2	608.5
167.5°	614.5	613.6	612.7	611.8	612.7	613.6	614.5	615.4	615.5	614.8	614.1
170°	617.3	616.5	615.6	614.7	615.6	616.5	617.3	618.3	618.4	617.7	617.0
172.5°	619.6	618.6	617.8	616.8	617.8	618.6	619.6	620.4	620.5	619.8	619.1
175°	621.7	620.7	619.7	618.7	619.7	620.7	621.7	622.8	622.8	622.2	621.5
177.5°	622.1	621.3	620.6	619.9	620.6	621.3	622.1	622.8	622.8	622.3	621.7
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1581.1	1587.5	1597.1	1602.6	1611.7	1617.6	1620.8	1626.8	1630.0	1641.4	1653.3
5°	1492.7	1501.9	1517.9	1532.8	1548.8	1565.3	1577.3	1591.0	1603.6	1625.3	1648.1
7.5°	1391.5	1404.2	1429.0	1452.7	1480.5	1504.0	1524.7	1548.1	1569.0	1600.1	1632.5
10°	1315.7	1337.9	1370.5	1392.8	1429.3	1452.8	1485.3	1511.1	1540.2	1581.3	1617.9
12.5°	1250.3	1277.1	1303.3	1334.3	1367.2	1406.2	1441.9	1474.9	1509.6	1552.0	1595.0
15°	1131.7	1170.5	1211.1	1242.5	1287.1	1328.3	1369.9	1414.5	1456.7	1507.6	1563.6
17.5°	979.0	1024.1	1092.3	1146.1	1198.4	1239.7	1291.3	1345.2	1395.1	1456.4	1518.7
20°	910.1	943.2	989.5	1062.0	1140.8	1184.8	1237.4	1296.8	1353.9	1420.7	1487.6
22.5°	854.7	884.2	921.4	977.9	1065.9	1125.8	1180.7	1241.0	1307.3	1375.5	1449.7
25°	775.8	796.3	835.2	880.9	941.5	1040.3	1100.3	1160.8	1232.9	1306.0	1390.5
27.5°	716.5	735.0	760.3	803.9	848.9	919.9	1015.3	1081.3	1153.1	1235.4	1323.1
30°	671.2	692.9	720.9	751.8	800.9	856.4	951.7	1028.3	1099.2	1183.7	1277.4
32.5°	638.3	655.5	679.3	710.7	751.6	804.7	880.9	973.9	1042.9	1132.0	1229.9
35°	584.4	604.4	623.9	653.6	686.6	735.2	792.9	892.3	960.9	1048.9	1147.1
37.5°	539.9	552.2	573.7	597.2	632.1	668.4	718.4	807.5	881.8	968.1	1068.7
40°	506.2	521.6	537.6	563.9	592.5	627.2	676.4	742.7	827.8	912.3	1010.6
42.5°	473.3	492.8	509.7	527.3	558.6	593.5	633.4	689.7	776.6	856.6	952.1
45°	433.6	446.2	463.9	483.3	509.0	538.7	574.1	623.3	706.7	775.8	865.5
47.5°	387.4	405.9	417.4	436.4	460.8	489.1	522.0	564.6	632.1	696.8	780.1
50°	355.9	374.8	391.3	408.5	430.2	457.6	485.0	526.2	580.4	648.4	726.1
52.5°	328.9	345.5	361.6	378.8	400.0	425.2	451.2	487.3	533.8	596.3	671.8
55°	292.0	302.2	318.7	335.9	354.7	378.8	403.9	434.2	474.2	526.8	587.9
57.5°	254.0	265.9	279.1	296.3	315.4	333.7	356.4	383.7	415.3	462.9	515.2
60°	232.5	241.7	252.5	270.2	287.9	304.4	326.2	349.0	378.8	419.9	464.4
62.5°	208.7	217.4	227.4	242.8	260.0	275.3	294.2	318.4	343.5	381.1	420.1
65°	169.1	181.7	191.4	205.1	219.4	235.4	250.2	269.7	292.0	321.7	356.5
67.5°	140.2	146.6	155.6	168.1	182.7	196.4	210.4	225.7	245.0	267.9	295.6
70°	127.4	129.7	131.4	143.4	157.1	170.8	183.9	198.2	214.8	233.7	257.6
72.5°	112.3	114.6	116.8	121.9	132.9	146.6	160.1	170.8	186.5	202.1	221.5
75°	89.1	92.6	94.3	97.1	101.1	110.3	122.9	133.1	142.2	154.2	169.7
77.5°	67.8	69.8	71.6	74.6	77.1	81.4	88.4	97.7	106.2	113.2	123.8
80°	53.7	54.2	56.6	57.7	61.1	64.0	67.4	74.8	83.4	86.3	93.7
82.5°	40.5	41.0	42.9	44.0	45.5	48.0	52.3	54.2	61.0	64.7	69.5
85°	22.3	21.7	23.4	23.4	24.5	25.7	26.9	29.7	31.4	36.0	37.1
87.5°	8.8	8.6	9.0	8.8	8.6	9.4	9.6	9.9	10.6	11.7	13.3
90°	9.5	9.0	8.2	7.4	6.6	5.8	4.8	3.7	2.7	1.5	0.4
92.5°	10.7	10.4	10.0	9.6	9.2	8.9	8.7	8.8	8.9	9.0	9.0
95°	18.0	17.6	16.8	16.1	15.4	14.7	16.0	19.3	22.6	25.9	29.2
97.5°	23.8	23.4	21.9	20.2	18.6	17.0	20.8	30.1	39.4	48.6	57.9
100°	26.4	25.6	23.9	22.2	20.5	18.9	24.8	38.5	52.2	65.9	79.6
102.5°	27.4	26.3	40.6	54.8	69.0	83.1	91.7	94.5	97.5	100.4	103.2
105°	28.5	27.4	54.7	82.0	109.2	136.5	148.6	145.6	142.6	139.6	136.6
107.5°	37.3	38.4	71.0	103.8	136.5	169.1	184.3	181.8	179.4	177.0	174.6
110°	68.6	78.6	107.5	136.4	165.2	194.1	207.4	205.3	203.3	201.1	199.1



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	161.9	198.4	205.4	212.6	219.7	226.9	229.5	227.6	225.8	223.9	222.1
115°	231.0	277.2	274.7	272.2	269.8	267.3	265.2	263.5	261.7	260.0	258.4
117.5°	295.9	307.0	305.4	303.7	302.0	300.2	298.4	296.5	294.6	292.7	290.8
120°	330.5	329.3	327.5	325.8	324.0	322.2	320.6	319.0	317.5	316.0	314.5
122.5°	351.3	350.6	348.6	346.6	344.7	342.8	341.0	339.4	337.9	336.2	334.7
125°	380.4	379.7	377.8	375.9	374.0	372.1	370.5	369.2	367.9	366.6	365.3
127.5°	406.9	406.0	404.5	403.1	401.7	400.3	398.8	397.4	396.0	394.5	393.0
130°	424.0	422.8	421.7	420.6	419.6	418.4	417.1	415.5	413.9	412.2	410.7
132.5°	440.7	439.7	438.6	437.6	436.4	435.3	434.1	432.7	431.4	430.0	428.7
135°	464.3	463.2	462.4	461.5	460.5	459.7	458.4	456.8	455.2	453.7	452.0
137.5°	486.3	485.3	484.2	483.3	482.2	481.2	480.1	479.0	477.9	476.7	475.7
140°	500.6	499.6	498.5	497.5	496.4	495.2	494.3	493.5	492.8	491.9	491.1
142.5°	513.8	513.0	511.7	510.4	509.2	507.9	507.0	506.2	505.5	504.8	504.0
145°	532.3	531.6	529.9	528.1	526.5	524.8	524.0	524.1	524.2	524.3	524.3
147.5°	548.5	547.9	546.2	544.6	542.9	541.2	540.5	541.0	541.3	541.7	542.1
150°	558.2	557.6	556.0	554.4	552.8	551.2	550.8	551.5	552.2	552.8	553.5
152.5°	567.2	566.6	565.1	563.6	562.1	560.5	560.2	560.9	561.7	562.5	563.3
155°	579.4	578.8	577.6	576.4	575.1	573.9	573.8	574.7	575.6	576.5	577.4
157.5°	589.4	588.8	588.0	587.1	586.3	585.5	585.4	586.2	586.9	587.7	588.4
160°	595.6	595.0	594.3	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0
162.5°	601.0	600.3	599.8	599.3	598.7	598.2	598.3	598.8	599.4	600.0	600.6
165°	607.8	607.0	606.7	606.4	606.1	605.9	606.0	606.6	607.2	607.8	608.4
167.5°	613.4	612.7	612.4	612.2	611.8	611.6	611.7	612.3	612.9	613.5	614.2
170°	616.3	615.6	615.4	615.2	615.0	614.8	615.0	615.6	616.2	616.8	617.3
172.5°	618.5	617.8	617.5	617.3	617.2	616.9	617.2	617.8	618.4	619.0	619.6
175°	620.8	620.1	619.8	619.7	619.5	619.3	619.5	620.3	621.0	621.6	622.3
177.5°	621.2	620.6	620.5	620.4	620.4	620.3	620.5	621.1	621.6	622.2	622.8
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1653.7	1655.1	1664.2	1668.4	1676.6	1679.8	1683.4	1682.6	1682.6	1684.4	1697.2
5°	1657.3	1668.7	1685.8	1702.5	1718.4	1732.2	1741.3	1750.4	1753.9	1770.4	1785.3
7.5°	1651.3	1672.4	1700.7	1726.0	1756.3	1779.9	1799.6	1817.2	1829.4	1853.5	1878.2
10°	1643.6	1673.3	1705.3	1737.8	1779.5	1810.9	1843.0	1867.5	1875.5	1911.5	1932.1
12.5°	1628.1	1667.8	1708.5	1750.7	1791.4	1834.7	1869.9	1894.5	1922.6	1954.9	1992.9
15°	1604.7	1650.5	1703.6	1757.8	1816.1	1868.6	1906.3	1949.2	1980.0	2015.5	2048.6
17.5°	1571.2	1630.1	1697.6	1760.5	1827.9	1884.3	1936.2	1977.3	1999.0	2019.2	2024.1
20°	1544.7	1608.2	1687.6	1761.9	1829.3	1894.4	1945.8	1980.0	1985.8	1986.3	1956.1
22.5°	1516.0	1587.6	1670.7	1746.7	1827.4	1899.9	1939.8	1954.5	1931.8	1893.1	1834.5
25°	1463.0	1545.9	1642.4	1729.2	1817.2	1885.8	1899.5	1873.8	1794.4	1711.0	1605.3
27.5°	1405.7	1498.8	1602.3	1698.8	1792.6	1835.0	1805.5	1712.8	1569.8	1445.4	1294.8
30°	1363.7	1468.2	1569.9	1677.8	1764.7	1783.0	1715.0	1578.5	1411.6	1224.3	1074.0
32.5°	1315.7	1425.2	1537.0	1648.6	1721.3	1703.4	1591.1	1423.1	1227.4	1043.3	901.3
35°	1247.1	1360.2	1480.7	1592.8	1639.0	1561.9	1394.0	1175.1	975.2	803.2	705.5
37.5°	1167.9	1291.1	1416.4	1519.2	1516.0	1387.4	1158.6	932.8	764.7	663.1	593.5
40°	1111.7	1236.2	1371.7	1458.4	1421.3	1254.0	1006.0	792.9	670.1	589.0	538.1
42.5°	1057.8	1182.8	1317.2	1386.3	1321.7	1115.9	868.9	702.0	600.6	537.4	496.1
45°	966.0	1098.0	1222.5	1260.8	1145.4	918.6	702.7	581.6	514.2	467.3	438.8
47.5°	876.3	1006.2	1119.8	1120.5	964.4	744.9	592.8	503.3	445.7	409.5	388.7
50°	821.5	944.9	1040.3	1025.5	848.3	662.7	530.1	453.1	405.0	377.0	355.3
52.5°	759.8	879.5	962.2	919.9	750.1	583.2	473.9	409.1	369.4	345.1	325.6
55°	670.1	776.4	834.7	770.7	611.8	485.0	400.5	349.7	319.9	299.4	282.8
57.5°	582.0	669.7	706.4	631.8	503.9	402.2	338.8	300.6	271.1	256.4	247.8
60°	526.8	601.6	627.2	545.0	438.2	351.9	299.9	264.5	242.8	233.1	224.5
62.5°	472.3	533.5	544.1	468.6	381.9	308.1	263.4	233.4	219.0	209.7	201.6
65°	391.9	435.9	430.8	370.2	302.2	244.5	212.0	193.6	182.8	169.7	155.4
67.5°	322.6	349.5	333.3	287.9	230.7	190.0	168.8	154.9	141.5	129.0	125.7
70°	278.8	294.2	277.1	235.4	189.1	159.4	142.2	125.7	117.7	114.9	109.7
72.5°	236.8	242.1	223.6	187.9	153.9	132.0	115.3	106.0	101.7	99.3	96.0
75°	177.7	173.7	157.6	129.7	106.9	92.0	86.9	83.4	80.6	78.3	76.5
77.5°	124.8	118.9	104.7	86.4	74.4	67.3	64.2	62.4	61.0	59.8	58.1
80°	93.7	89.7	75.4	61.7	56.6	53.1	51.4	49.2	49.2	48.0	46.2
82.5°	68.5	64.1	51.7	45.2	42.4	40.3	39.1	37.7	37.3	37.5	36.2
85°	36.0	29.1	25.7	24.5	22.8	21.7	22.3	21.1	21.1	21.1	20.6
87.5°	11.3	9.2	9.0	8.7	9.4	9.6	9.2	9.4	10.0	9.6	10.2
90°	1.5	2.7	3.7	4.8	5.8	6.6	7.4	8.2	9.0	9.5	10.0
92.5°	9.0	8.9	8.8	8.7	8.9	9.2	9.6	10.0	10.4	10.7	10.9
95°	25.9	22.6	19.3	16.0	14.7	15.4	16.1	16.8	17.6	18.0	18.5
97.5°	48.6	39.4	30.1	20.8	17.0	18.6	20.2	21.9	23.4	23.8	24.3
100°	65.9	52.2	38.5	24.8	18.9	20.5	22.2	23.9	25.6	26.4	27.2
102.5°	100.4	97.5	94.5	91.7	83.1	69.0	54.8	40.6	26.3	27.4	28.4
105°	139.6	142.6	145.6	148.6	136.5	109.2	82.0	54.7	27.4	28.5	29.6
107.5°	177.0	179.4	181.8	184.3	169.1	136.5	103.8	71.0	38.4	37.3	36.2
110°	201.1	203.3	205.3	207.4	194.1	165.2	136.4	107.5	78.6	68.6	58.6



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	223.9	225.8	227.6	229.5	226.9	219.7	212.6	205.4	198.4	161.9	125.4
115°	260.0	261.7	263.5	265.2	267.3	269.8	272.2	274.7	277.2	231.0	184.8
117.5°	292.7	294.6	296.5	298.4	300.2	302.0	303.7	305.4	307.0	295.9	284.7
120°	316.0	317.5	319.0	320.6	322.2	324.0	325.8	327.5	329.3	330.5	331.7
122.5°	336.2	337.9	339.4	341.0	342.8	344.7	346.6	348.6	350.6	351.3	352.0
125°	366.6	367.9	369.2	370.5	372.1	374.0	375.9	377.8	379.7	380.4	381.1
127.5°	394.5	396.0	397.4	398.8	400.3	401.7	403.1	404.5	406.0	406.9	407.9
130°	412.2	413.9	415.5	417.1	418.4	419.6	420.6	421.7	422.8	424.0	425.0
132.5°	430.0	431.4	432.7	434.1	435.3	436.4	437.6	438.6	439.7	440.7	441.6
135°	453.7	455.2	456.8	458.4	459.7	460.5	461.5	462.4	463.2	464.3	465.3
137.5°	476.7	477.9	479.0	480.1	481.2	482.2	483.3	484.2	485.3	486.3	487.2
140°	491.9	492.8	493.5	494.3	495.2	496.4	497.5	498.5	499.6	500.6	501.4
142.5°	504.8	505.5	506.2	507.0	507.9	509.2	510.4	511.7	513.0	513.8	514.6
145°	524.3	524.2	524.1	524.0	524.8	526.5	528.1	529.9	531.6	532.3	533.0
147.5°	541.7	541.3	541.0	540.5	541.2	542.9	544.6	546.2	547.9	548.5	549.0
150°	552.8	552.2	551.5	550.8	551.2	552.8	554.4	556.0	557.6	558.2	558.8
152.5°	562.5	561.7	560.9	560.2	560.5	562.1	563.6	565.1	566.6	567.2	567.8
155°	576.5	575.6	574.7	573.8	573.9	575.1	576.4	577.6	578.8	579.4	580.0
157.5°	587.7	586.9	586.2	585.4	585.5	586.3	587.1	588.0	588.8	589.4	590.1
160°	594.3	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0	595.6	596.1
162.5°	600.0	599.4	598.8	598.3	598.2	598.7	599.3	599.8	600.3	601.0	601.7
165°	607.8	607.2	606.6	606.0	605.9	606.1	606.4	606.7	607.0	607.8	608.5
167.5°	613.5	612.9	612.3	611.7	611.6	611.8	612.2	612.4	612.7	613.4	614.1
170°	616.8	616.2	615.6	615.0	614.8	615.0	615.2	615.4	615.6	616.3	617.0
172.5°	619.0	618.4	617.8	617.2	616.9	617.2	617.3	617.5	617.8	618.5	619.1
175°	621.6	621.0	620.3	619.5	619.3	619.5	619.7	619.8	620.1	620.8	621.5
177.5°	622.2	621.6	621.1	620.5	620.3	620.4	620.4	620.5	620.6	621.2	621.7
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1701.8	1707.7	1710.4	1710.4	1713.6	1712.3	1710.9
5°	1799.6	1810.4	1812.7	1823.0	1830.4	1828.1	1829.3
7.5°	1896.8	1914.3	1931.5	1939.4	1940.6	1945.2	1946.9
10°	1956.6	1970.9	1997.8	1993.7	2013.8	2025.2	2006.3
12.5°	2014.2	2033.5	2052.2	2057.3	2068.6	2072.3	2064.9
15°	2066.3	2076.6	2077.8	2074.9	2078.3	2075.4	2064.6
17.5°	2017.7	2001.0	1967.1	1951.1	1938.5	1919.8	1912.2
20°	1937.2	1888.1	1830.9	1808.1	1781.2	1728.7	1741.3
22.5°	1763.6	1707.5	1650.5	1583.7	1551.9	1502.0	1499.0
25°	1493.3	1396.8	1290.6	1216.2	1172.9	1123.2	1101.4
27.5°	1161.1	1039.5	952.4	908.4	868.2	828.8	827.2
30°	942.6	851.2	783.8	746.1	721.5	705.0	708.4
32.5°	794.5	731.9	686.5	655.1	637.0	624.5	624.3
35°	649.5	606.7	577.6	564.4	551.3	542.2	542.7
37.5°	555.9	530.1	513.9	499.4	491.2	486.7	484.2
40°	507.9	486.7	474.2	465.6	458.7	452.5	451.3
42.5°	469.9	452.5	439.9	433.2	426.7	422.3	421.1
45°	417.1	402.8	391.3	383.9	381.1	377.0	377.0
47.5°	371.0	357.0	348.0	343.4	338.5	335.8	335.7
50°	339.9	329.1	321.1	318.2	314.2	312.5	311.9
52.5°	312.0	303.9	298.3	296.3	294.5	292.4	292.7
55°	274.2	269.7	267.3	265.6	262.8	259.3	261.7
57.5°	242.4	238.4	232.3	226.9	224.3	221.9	222.8
60°	220.0	212.0	204.0	197.7	196.0	190.8	190.8
62.5°	191.6	180.4	170.6	167.0	165.3	162.9	162.5
65°	147.4	142.8	140.5	138.3	137.1	137.1	136.0
67.5°	122.2	120.3	117.8	117.3	116.1	115.7	115.4
70°	108.0	105.6	104.5	104.0	102.8	103.4	101.7
72.5°	94.3	92.5	92.2	90.7	90.1	90.1	88.9
75°	74.3	74.3	73.7	73.1	72.0	71.4	72.0
77.5°	57.2	57.3	56.2	56.1	56.0	56.1	55.5
80°	45.7	46.2	45.7	45.1	44.6	45.1	44.6
82.5°	36.1	35.3	35.2	35.0	35.0	34.6	34.5
85°	20.6	21.1	20.6	20.0	20.0	20.0	20.6
87.5°	9.9	10.0	10.1	10.1	10.1	10.2	9.7
90°	10.5	11.0	11.4	11.5	11.7	12.0	12.1
92.5°	11.2	11.5	11.6	11.8	11.9	12.1	12.1
95°	19.0	19.5	19.7	19.6	19.5	19.5	19.3
97.5°	24.6	25.1	25.3	25.4	25.6	25.7	25.8
100°	28.0	28.8	29.3	29.5	29.7	29.9	30.1
102.5°	29.4	30.5	31.2	31.4	31.7	31.9	32.3
105°	30.7	31.8	32.5	33.0	33.3	33.8	34.2
107.5°	35.0	33.9	33.6	33.9	34.4	34.7	35.1
110°	48.6	38.7	33.9	34.3	34.7	35.1	35.5



TEST NUMBER: P331711-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	89.0	52.6	34.6	34.9	35.2	35.6	35.8
115°	138.5	92.3	65.6	58.4	51.2	44.0	36.9
117.5°	273.5	262.3	245.0	221.3	197.7	174.1	150.4
120°	332.9	334.2	328.0	314.5	301.1	287.6	274.1
122.5°	352.8	353.4	352.5	349.9	347.2	344.7	342.0
125°	381.8	382.5	383.0	383.3	383.6	383.9	384.2
127.5°	409.0	410.0	410.5	410.6	410.7	410.7	410.8
130°	426.1	427.2	427.7	427.6	427.5	427.4	427.3
132.5°	442.6	443.5	443.8	443.8	443.7	443.6	443.5
135°	466.2	467.3	467.7	467.4	467.3	467.1	466.8
137.5°	488.2	489.2	489.5	489.1	488.8	488.5	488.2
140°	502.3	503.3	503.4	502.9	502.5	502.0	501.4
142.5°	515.4	516.3	516.4	515.9	515.4	514.9	514.4
145°	533.6	534.3	534.4	534.0	533.5	533.0	532.4
147.5°	549.5	550.0	550.0	549.7	549.2	548.8	548.4
150°	559.4	560.0	560.1	559.6	559.0	558.5	558.1
152.5°	568.4	569.0	568.9	568.3	567.7	567.0	566.4
155°	580.6	581.2	581.0	580.2	579.5	578.7	577.8
157.5°	590.8	591.5	591.5	590.6	589.9	589.1	588.3
160°	596.7	597.3	597.3	596.6	595.9	595.1	594.4
162.5°	602.4	603.0	603.0	602.1	601.2	600.4	599.5
165°	609.2	609.8	609.8	609.2	608.5	607.8	607.0
167.5°	614.8	615.5	615.4	614.5	613.6	612.7	611.8
170°	617.7	618.4	618.3	617.3	616.5	615.6	614.7
172.5°	619.8	620.5	620.4	619.6	618.6	617.8	616.8
175°	622.2	622.8	622.8	621.7	620.7	619.7	618.7
177.5°	622.3	622.8	622.8	622.1	621.3	620.6	619.9
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0

(END OF REPORT)