

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331713-935

Luminaire Tested: **S122RDIP-S865D530U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331713-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D530U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4620.5 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	94	90	95	91	88	85	80	78	76	70	68	67	60	59	58	54
2	93	86	80	76	87	81	76	72	71	68	64	63	60	57	54	52	51	47
3	86	77	70	64	80	72	66	61	64	59	55	56	53	50	49	47	44	41
4	79	69	61	55	74	65	58	53	58	52	48	51	47	44	45	42	39	36
5	73	62	54	48	68	59	52	46	52	47	42	46	42	39	41	38	35	32
6	68	56	48	43	63	53	46	41	48	42	38	42	38	35	38	34	31	29
7	63	51	43	38	59	49	42	37	44	38	34	39	34	31	35	31	28	26
8	59	47	39	34	55	45	38	33	40	35	31	36	32	28	32	29	26	24
9	55	43	36	31	52	41	34	30	37	32	28	33	29	26	30	26	24	22
10	52	40	33	28	49	38	32	27	34	29	25	31	27	24	28	24	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26547	26547	26547	26547
5°	29648	26712	23686	26712
10°	32893	26525	20530	26525
15°	34511	26136	16177	26136
20°	29919	25560	13998	25560
25°	19621	24772	12497	24772
30°	13207	23815	11311	23815
35°	10697	22610	10200	22610
40°	9512	21300	9440	21300
45°	8608	19763	8426	19763
50°	7834	18239	7804	18239
55°	7367	16549	7268	16549
60°	6161	14996	6090	14996
65°	5196	13620	5891	13620
70°	4801	12161	5556	12161
75°	4492	10586	5128	10586
80°	4147	8712	4575	8712
85°	3816	6873	4020	6873



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.9	3.4
10°-20°	434.3	9.4
20°-30°	559.6	12.1
30°-40°	531.8	11.5
40°-50°	455.6	9.9
50°-60°	346.9	7.5
60°-70°	219.3	4.7
70°-80°	109.5	2.4
80°-90°	30.8	0.7
90°-100°	102.1	2.2
100°-110°	346.4	7.5
110°-120°	368.0	8.0
120°-130°	303.0	6.6
130°-140°	243.3	5.3
140°-150°	183.9	4.0
150°-160°	129.2	2.8
160°-170°	76.1	1.6
170°-180°	24.8	0.5
0°-30°	1149.8	24.9
0°-40°	1681.6	36.4
0°-60°	2484.1	53.8
0°-90°	2843.8	61.5
90°-120°	816.6	17.7
90°-150°	1546.7	33.5
90°-180°	1777.0	38.5
0°-180°	4620.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1829	1648	1461	1648	1829	181
15°	2065	1564	968	1564	2065	557
25°	1101	1390	702	1390	1101	523
35°	543	1147	518	1147	543	347
45°	377	866	369	866	377	292
55°	262	588	258	588	262	230
65°	136	356	154	356	136	138
75°	72	170	82	170	72	76
85°	21	37	22	37	21	22
90°	16	0	16	0	16	10
95°	56	17	56	17	56	73
105°	553	60	553	60	553	535
115°	728	106	728	106	728	713
125°	591	147	591	147	591	534
135°	490	173	490	173	490	380
145°	391	197	391	197	391	248
155°	328	224	328	224	328	153
165°	288	244	288	244	288	82
175°	260	255	260	255	260	25
180°	255	255	255	255	255	



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1710.9	1712.3	1713.6	1710.4	1710.4	1707.7	1701.8	1697.2	1684.4	1682.6	1682.6
5°	1829.3	1828.1	1830.4	1823.0	1812.7	1810.4	1799.6	1785.3	1770.4	1753.9	1750.4
7.5°	1946.9	1945.2	1940.6	1939.4	1931.5	1914.3	1896.8	1878.2	1853.5	1829.4	1817.2
10°	2006.3	2025.2	2013.8	1993.7	1997.8	1970.9	1956.6	1932.1	1911.5	1875.5	1867.5
12.5°	2064.9	2072.3	2068.6	2057.3	2052.2	2033.5	2014.2	1992.9	1954.9	1922.6	1894.5
15°	2064.6	2075.4	2078.3	2074.9	2077.8	2076.6	2066.3	2048.6	2015.5	1980.0	1949.2
17.5°	1912.2	1919.8	1938.5	1951.1	1967.1	2001.0	2017.7	2024.1	2019.2	1999.0	1977.3
20°	1741.3	1728.7	1781.2	1808.1	1830.9	1888.1	1937.2	1956.1	1986.3	1985.8	1980.0
22.5°	1499.0	1502.0	1551.9	1583.7	1650.5	1707.5	1763.6	1834.5	1893.1	1931.8	1954.5
25°	1101.4	1123.2	1172.9	1216.2	1290.6	1396.8	1493.3	1605.3	1711.0	1794.4	1873.8
27.5°	827.2	828.8	868.2	908.4	952.4	1039.5	1161.1	1294.8	1445.4	1569.8	1712.8
30°	708.4	705.0	721.5	746.1	783.8	851.2	942.6	1074.0	1224.3	1411.6	1578.5
32.5°	624.3	624.5	637.0	655.1	686.5	731.9	794.5	901.3	1043.3	1227.4	1423.1
35°	542.7	542.2	551.3	564.4	577.6	606.7	649.5	705.5	803.2	975.2	1175.1
37.5°	484.2	486.7	491.2	499.4	513.9	530.1	555.9	593.5	663.1	764.7	932.8
40°	451.3	452.5	458.7	465.6	474.2	486.7	507.9	538.1	589.0	670.1	792.9
42.5°	421.1	422.3	426.7	433.2	439.9	452.5	469.9	496.1	537.4	600.6	702.0
45°	377.0	377.0	381.1	383.9	391.3	402.8	417.1	438.8	467.3	514.2	581.6
47.5°	335.7	335.8	338.5	343.4	348.0	357.0	371.0	388.7	409.5	445.7	503.3
50°	311.9	312.5	314.2	318.2	321.1	329.1	339.9	355.3	377.0	405.0	453.1
52.5°	292.7	292.4	294.5	296.3	298.3	303.9	312.0	325.6	345.1	369.4	409.1
55°	261.7	259.3	262.8	265.6	267.3	269.7	274.2	282.8	299.4	319.9	349.7
57.5°	222.8	221.9	224.3	226.9	232.3	238.4	242.4	247.8	256.4	271.1	300.6
60°	190.8	190.8	196.0	197.7	204.0	212.0	220.0	224.5	233.1	242.8	264.5
62.5°	162.5	162.9	165.3	167.0	170.6	180.4	191.6	201.6	209.7	219.0	233.4
65°	136.0	137.1	137.1	138.3	140.5	142.8	147.4	155.4	169.7	182.8	193.6
67.5°	115.4	115.7	116.1	117.3	117.8	120.3	122.2	125.7	129.0	141.5	154.9
70°	101.7	103.4	102.8	104.0	104.5	105.6	108.0	109.7	114.9	117.7	125.7
72.5°	88.9	90.1	90.1	90.7	92.2	92.5	94.3	96.0	99.3	101.7	106.0
75°	72.0	71.4	72.0	73.1	73.7	74.3	74.3	76.5	78.3	80.6	83.4
77.5°	55.5	56.1	56.0	56.1	56.2	57.3	57.2	58.1	59.8	61.0	62.4
80°	44.6	45.1	44.6	45.1	45.7	46.2	45.7	46.2	48.0	49.2	49.2
82.5°	34.5	34.6	35.0	35.0	35.2	35.3	36.1	36.2	37.5	37.3	37.7
85°	20.6	20.0	20.0	20.0	20.6	21.1	20.6	20.6	21.1	21.1	21.1
87.5°	10.6	11.0	11.0	11.0	11.0	10.9	10.7	11.4	11.0	11.5	11.0
90°	16.2	16.2	16.2	16.2	16.2	15.7	14.7	15.7	16.2	16.7	16.2
92.5°	27.2	28.0	27.6	29.2	29.5	32.6	36.8	42.8	53.9	63.8	62.9
95°	56.0	55.4	57.0	60.9	67.2	78.1	98.7	128.6	168.4	192.5	170.4
97.5°	110.2	114.3	121.5	133.5	157.0	192.5	245.6	300.2	344.7	328.6	247.5
100°	175.8	184.6	198.9	220.0	260.7	320.1	387.4	448.3	458.6	387.9	267.1
102.5°	309.4	321.3	339.1	375.1	419.4	482.4	531.6	545.4	501.0	389.9	259.7
105°	553.4	560.3	581.3	611.8	642.2	658.5	652.0	596.6	494.5	363.9	245.0
107.5°	706.9	716.0	720.2	721.9	718.1	694.3	643.3	559.6	451.3	336.0	237.7
110°	753.2	753.7	749.3	739.9	718.8	678.6	615.7	527.9	424.2	322.6	236.2



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	752.4	749.8	741.4	725.8	696.5	650.3	583.2	498.8	405.4	313.9	236.6
115°	728.1	723.8	711.0	688.4	653.6	603.0	538.6	463.0	382.0	304.4	238.7
117.5°	684.8	681.1	667.7	643.9	608.3	560.9	502.5	436.1	367.3	299.8	242.2
120°	656.9	652.0	637.8	614.8	580.4	535.7	483.6	422.8	359.5	297.0	244.5
122.5°	627.9	623.8	611.1	588.4	557.6	517.2	468.0	412.2	352.8	295.5	247.3
125°	590.7	586.8	574.5	555.9	527.4	490.5	447.3	396.7	343.2	292.7	251.4
127.5°	558.1	554.9	544.3	526.8	502.0	468.0	427.3	381.5	334.4	291.0	255.6
130°	539.6	535.7	525.9	509.2	485.1	452.7	414.0	371.7	328.5	290.2	258.7
132.5°	520.4	516.9	507.8	491.1	467.4	437.0	401.4	362.3	323.7	289.8	261.9
135°	489.6	487.6	478.7	462.5	441.4	414.0	381.5	349.1	317.2	289.2	265.6
137.5°	459.3	456.3	448.6	434.6	415.4	391.4	365.8	338.6	312.5	289.1	269.0
140°	438.5	435.5	428.2	415.4	399.7	378.1	355.5	331.9	309.9	288.7	270.5
142.5°	417.7	417.1	410.5	398.9	384.0	365.9	346.5	326.4	307.1	288.7	271.7
145°	390.8	389.3	384.4	376.1	364.4	350.1	334.8	318.7	303.4	287.7	273.0
147.5°	368.3	367.5	364.1	357.5	347.8	337.3	325.5	312.7	299.7	285.9	273.4
150°	355.0	354.5	351.5	345.7	338.3	329.5	319.2	308.3	296.6	284.8	273.0
152.5°	343.6	343.5	341.4	336.2	330.5	322.8	314.1	304.0	293.9	282.8	272.2
155°	328.5	329.5	327.5	324.1	318.7	313.2	305.9	298.1	288.7	279.4	271.0
157.5°	315.6	315.6	314.8	311.9	308.1	303.8	297.6	291.1	283.9	275.9	268.8
160°	307.4	307.4	306.9	304.4	301.0	297.6	292.1	286.7	280.3	273.5	267.6
162.5°	299.5	299.9	299.5	297.7	294.3	291.7	287.1	282.4	277.2	271.6	266.4
165°	288.3	288.7	288.7	286.7	284.8	282.8	279.4	276.0	272.0	267.6	264.2
167.5°	277.8	278.4	278.5	277.4	276.6	274.7	272.4	269.8	266.9	264.2	261.9
170°	271.6	272.5	273.0	271.6	271.0	270.1	268.1	266.7	264.2	262.2	260.7
172.5°	266.4	267.0	267.5	266.8	266.3	265.7	264.2	263.1	261.4	259.8	259.2
175°	259.8	260.7	261.2	260.7	260.7	260.3	259.8	259.2	257.8	257.3	256.8
177.5°	255.7	256.5	256.9	256.9	256.9	256.9	256.5	256.5	255.7	255.3	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1683.4	1679.8	1676.6	1668.4	1664.2	1655.1	1653.7	1653.3	1641.4	1630.0	1626.8
5°	1741.3	1732.2	1718.4	1702.5	1685.8	1668.7	1657.3	1648.1	1625.3	1603.6	1591.0
7.5°	1799.6	1779.9	1756.3	1726.0	1700.7	1672.4	1651.3	1632.5	1600.1	1569.0	1548.1
10°	1843.0	1810.9	1779.5	1737.8	1705.3	1673.3	1643.6	1617.9	1581.3	1540.2	1511.1
12.5°	1869.9	1834.7	1791.4	1750.7	1708.5	1667.8	1628.1	1595.0	1552.0	1509.6	1474.9
15°	1906.3	1868.6	1816.1	1757.8	1703.6	1650.5	1604.7	1563.6	1507.6	1456.7	1414.5
17.5°	1936.2	1884.3	1827.9	1760.5	1697.6	1630.1	1571.2	1518.7	1456.4	1395.1	1345.2
20°	1945.8	1894.4	1829.3	1761.9	1687.6	1608.2	1544.7	1487.6	1420.7	1353.9	1296.8
22.5°	1939.8	1899.9	1827.4	1746.7	1670.7	1587.6	1516.0	1449.7	1375.5	1307.3	1241.0
25°	1899.5	1885.8	1817.2	1729.2	1642.4	1545.9	1463.0	1390.5	1306.0	1232.9	1160.8
27.5°	1805.5	1835.0	1792.6	1698.8	1602.3	1498.8	1405.7	1323.1	1235.4	1153.1	1081.3
30°	1715.0	1783.0	1764.7	1677.8	1569.9	1468.2	1363.7	1277.4	1183.7	1099.2	1028.3
32.5°	1591.1	1703.4	1721.3	1648.6	1537.0	1425.2	1315.7	1229.9	1132.0	1042.9	973.9
35°	1394.0	1561.9	1639.0	1592.8	1480.7	1360.2	1247.1	1147.1	1048.9	960.9	892.3
37.5°	1158.6	1387.4	1516.0	1519.2	1416.4	1291.1	1167.9	1068.7	968.1	881.8	807.5
40°	1006.0	1254.0	1421.3	1458.4	1371.7	1236.2	1111.7	1010.6	912.3	827.8	742.7
42.5°	868.9	1115.9	1321.7	1386.3	1317.2	1182.8	1057.8	952.1	856.6	776.6	689.7
45°	702.7	918.6	1145.4	1260.8	1222.5	1098.0	966.0	865.5	775.8	706.7	623.3
47.5°	592.8	744.9	964.4	1120.5	1119.8	1006.2	876.3	780.1	696.8	632.1	564.6
50°	530.1	662.7	848.3	1025.5	1040.3	944.9	821.5	726.1	648.4	580.4	526.2
52.5°	473.9	583.2	750.1	919.9	962.2	879.5	759.8	671.8	596.3	533.8	487.3
55°	400.5	485.0	611.8	770.7	834.7	776.4	670.1	587.9	526.8	474.2	434.2
57.5°	338.8	402.2	503.9	631.8	706.4	669.7	582.0	515.2	462.9	415.3	383.7
60°	299.9	351.9	438.2	545.0	627.2	601.6	526.8	464.4	419.9	378.8	349.0
62.5°	263.4	308.1	381.9	468.6	544.1	533.5	472.3	420.1	381.1	343.5	318.4
65°	212.0	244.5	302.2	370.2	430.8	435.9	391.9	356.5	321.7	292.0	269.7
67.5°	168.8	190.0	230.7	287.9	333.3	349.5	322.6	295.6	267.9	245.0	225.7
70°	142.2	159.4	189.1	235.4	277.1	294.2	278.8	257.6	233.7	214.8	198.2
72.5°	115.3	132.0	153.9	187.9	223.6	242.1	236.8	221.5	202.1	186.5	170.8
75°	86.9	92.0	106.9	129.7	157.6	173.7	177.7	169.7	154.2	142.2	133.1
77.5°	64.2	67.3	74.4	86.4	104.7	118.9	124.8	123.8	113.2	106.2	97.7
80°	51.4	53.1	56.6	61.7	75.4	89.7	93.7	93.7	86.3	83.4	74.8
82.5°	39.1	40.3	42.4	45.2	51.7	64.1	68.5	69.5	64.7	61.0	54.2
85°	22.3	21.7	22.8	24.5	25.7	29.1	36.0	37.1	36.0	31.4	29.7
87.5°	10.4	10.2	9.7	9.0	9.2	9.5	11.4	13.3	11.8	10.8	10.2
90°	13.3	9.8	7.4	5.9	4.9	4.0	2.0	0.5	2.0	4.0	4.9
92.5°	49.0	33.4	22.3	17.7	14.4	12.1	8.6	6.0	8.6	12.1	14.4
95°	113.4	70.7	48.1	36.3	28.5	24.0	19.1	17.2	19.1	24.0	28.5
97.5°	152.8	93.3	64.9	51.6	42.5	35.8	30.7	28.0	30.7	35.8	42.5
100°	161.1	101.2	75.2	61.4	51.6	43.7	39.3	37.8	39.3	43.7	51.6
102.5°	161.4	108.2	84.1	70.4	60.2	52.3	48.0	46.8	48.0	52.3	60.2
105°	164.0	120.3	97.2	83.4	72.7	65.3	61.9	59.9	61.9	65.3	72.7
107.5°	170.7	132.7	110.3	96.4	85.8	79.0	75.6	74.0	75.6	79.0	85.8
110°	176.2	140.9	119.3	105.0	94.8	88.4	85.4	83.4	85.4	88.4	94.8



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	182.2	148.8	127.9	113.3	103.4	97.4	94.1	92.1	94.1	97.4	103.4
115°	191.0	161.1	139.9	126.7	116.8	111.0	108.1	105.6	108.1	111.0	116.8
117.5°	200.4	172.4	152.8	139.1	129.7	124.4	121.5	119.5	121.5	124.4	129.7
120°	206.7	180.2	161.1	147.3	137.5	133.0	130.1	128.1	130.1	133.0	137.5
122.5°	212.2	187.7	169.7	155.6	145.8	140.9	138.0	136.4	138.0	140.9	145.8
125°	220.9	198.9	181.2	167.5	157.6	151.7	148.8	147.3	148.8	151.7	157.6
127.5°	229.1	209.3	192.1	178.0	168.5	162.0	157.9	155.9	157.9	162.0	168.5
130°	234.2	215.6	198.4	184.6	174.8	167.9	163.0	161.1	163.0	167.9	174.8
132.5°	239.4	221.0	204.7	190.9	180.7	173.4	168.2	165.7	168.2	173.4	180.7
135°	246.0	228.9	213.1	199.3	188.0	180.7	174.8	172.8	174.8	180.7	188.0
137.5°	251.1	235.1	219.6	206.8	195.6	187.8	181.8	179.5	181.8	187.8	195.6
140°	253.8	238.7	223.9	211.1	200.4	192.5	186.6	184.6	186.6	192.5	200.4
142.5°	256.2	241.4	227.0	215.1	204.7	196.8	191.3	189.8	191.3	196.8	204.7
145°	259.2	245.5	232.2	221.4	211.6	204.2	199.3	197.4	199.3	204.2	211.6
147.5°	261.0	248.8	236.3	226.8	218.6	211.8	207.1	205.6	207.1	211.8	218.6
150°	261.7	250.4	239.1	230.3	222.9	216.5	212.6	211.1	212.6	216.5	222.9
152.5°	262.1	252.0	241.9	233.8	226.9	221.3	217.3	216.6	217.3	221.3	226.9
155°	262.7	254.3	246.0	238.7	233.2	227.8	224.9	224.4	224.9	227.8	233.2
157.5°	262.7	256.0	248.9	242.8	238.4	233.8	231.4	230.8	231.4	233.8	238.4
160°	262.7	256.8	250.9	245.5	241.6	237.6	235.7	235.2	235.7	237.6	241.6
162.5°	262.3	257.2	252.1	247.9	244.4	241.2	239.2	239.5	239.2	241.2	244.4
165°	261.2	257.8	253.4	250.4	248.0	245.0	244.0	244.5	244.0	245.0	248.0
167.5°	260.5	257.7	254.4	252.6	250.8	248.9	248.1	248.7	248.1	248.9	250.8
170°	259.8	257.3	254.9	253.4	252.4	250.9	250.4	251.4	250.4	250.9	252.4
172.5°	258.6	256.9	255.2	254.2	253.6	252.1	252.4	253.0	252.4	252.1	253.6
175°	257.3	256.3	255.3	254.9	254.9	253.8	254.3	254.9	254.3	253.8	254.9
177.5°	256.5	255.7	255.3	255.3	255.3	254.5	254.9	255.7	254.9	254.5	255.3
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1620.8	1617.6	1611.7	1602.6	1597.1	1587.5	1581.1	1584.8	1585.6	1584.8	1583.8
5°	1577.3	1565.3	1548.8	1532.8	1517.9	1501.9	1492.7	1488.8	1480.7	1476.2	1473.9
7.5°	1524.7	1504.0	1480.5	1452.7	1429.0	1404.2	1391.5	1385.3	1368.9	1359.9	1352.2
10°	1485.3	1452.8	1429.3	1392.8	1370.5	1337.9	1315.7	1316.2	1293.9	1281.3	1272.2
12.5°	1441.9	1406.2	1367.2	1334.3	1303.3	1277.1	1250.3	1239.4	1215.8	1203.7	1179.0
15°	1369.9	1328.3	1287.1	1242.5	1211.1	1170.5	1131.7	1084.3	1046.0	1012.9	1003.8
17.5°	1291.3	1239.7	1198.4	1146.1	1092.3	1024.1	979.0	951.5	928.4	910.9	897.9
20°	1237.4	1184.8	1140.8	1062.0	989.5	943.2	910.1	888.9	865.0	846.1	835.8
22.5°	1180.7	1125.8	1065.9	977.9	921.4	884.2	854.7	830.4	814.2	799.4	790.1
25°	1100.3	1040.3	941.5	880.9	835.2	796.3	775.8	761.0	743.8	723.8	714.6
27.5°	1015.3	919.9	848.9	803.9	760.3	735.0	716.5	694.3	679.0	670.0	660.5
30°	951.7	856.4	800.9	751.8	720.9	692.9	671.2	658.7	643.9	628.4	622.2
32.5°	880.9	804.7	751.6	710.7	679.3	655.5	638.3	618.0	607.3	597.8	584.6
35°	792.9	735.2	686.6	653.6	623.9	604.4	584.4	572.4	553.0	545.0	539.8
37.5°	718.4	668.4	632.1	597.2	573.7	552.2	539.9	520.9	512.5	501.4	490.5
40°	676.4	627.2	592.5	563.9	537.6	521.6	506.2	490.8	478.2	473.0	459.9
42.5°	633.4	593.5	558.6	527.3	509.7	492.8	473.3	461.9	448.9	440.6	432.5
45°	574.1	538.7	509.0	483.3	463.9	446.2	433.6	414.7	407.3	390.7	383.9
47.5°	522.0	489.1	460.8	436.4	417.4	405.9	387.4	372.7	360.8	350.7	341.8
50°	485.0	457.6	430.2	408.5	391.3	374.8	355.9	348.4	330.2	325.0	319.9
52.5°	451.2	425.2	400.0	378.8	361.6	345.5	328.9	319.3	306.9	301.8	298.0
55°	403.9	378.8	354.7	335.9	318.7	302.2	292.0	279.9	274.2	270.2	265.6
57.5°	356.4	333.7	315.4	296.3	279.1	265.9	254.0	246.8	240.8	235.6	230.1
60°	326.2	304.4	287.9	270.2	252.5	241.7	232.5	223.9	217.1	209.1	206.8
62.5°	294.2	275.3	260.0	242.8	227.4	217.4	208.7	200.6	192.4	180.7	177.5
65°	250.2	235.4	219.4	205.1	191.4	181.7	169.1	160.0	156.5	155.4	154.8
67.5°	210.4	196.4	182.7	168.1	155.6	146.6	140.2	138.8	136.4	135.7	134.1
70°	183.9	170.8	157.1	143.4	131.4	129.7	127.4	125.1	122.3	121.1	119.9
72.5°	160.1	146.6	132.9	121.9	116.8	114.6	112.3	110.0	108.1	106.9	106.2
75°	122.9	110.3	101.1	97.1	94.3	92.6	89.1	87.4	86.3	84.6	83.9
77.5°	88.4	81.4	77.1	74.6	71.6	69.8	67.8	66.1	64.9	64.6	63.6
80°	67.4	64.0	61.1	57.7	56.6	54.2	53.7	52.0	52.5	50.9	50.9
82.5°	52.3	48.0	45.5	44.0	42.9	41.0	40.5	39.6	39.8	38.5	38.5
85°	26.9	25.7	24.5	23.4	23.4	21.7	22.3	21.7	21.7	20.6	20.0
87.5°	9.9	9.7	9.3	10.0	10.6	10.2	10.1	9.6	9.4	9.6	9.2
90°	5.9	7.4	9.8	13.3	16.2	16.7	16.2	15.7	14.7	15.7	16.2
92.5°	17.7	22.3	33.4	49.0	62.9	63.8	53.9	42.8	36.8	32.6	29.5
95°	36.3	48.1	70.7	113.4	170.4	192.5	168.4	128.6	98.7	78.1	67.2
97.5°	51.6	64.9	93.3	152.8	247.5	328.6	344.7	300.2	245.6	192.5	157.0
100°	61.4	75.2	101.2	161.1	267.1	387.9	458.6	448.3	387.4	320.1	260.7
102.5°	70.4	84.1	108.2	161.4	259.7	389.9	501.0	545.4	531.6	482.4	419.4
105°	83.4	97.2	120.3	164.0	245.0	363.9	494.5	596.6	652.0	658.5	642.2
107.5°	96.4	110.3	132.7	170.7	237.7	336.0	451.3	559.6	643.3	694.3	718.1
110°	105.0	119.3	140.9	176.2	236.2	322.6	424.2	527.9	615.7	678.6	718.8



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	113.3	127.9	148.8	182.2	236.6	313.9	405.4	498.8	583.2	650.3	696.5
115°	126.7	139.9	161.1	191.0	238.7	304.4	382.0	463.0	538.6	603.0	653.6
117.5°	139.1	152.8	172.4	200.4	242.2	299.8	367.3	436.1	502.5	560.9	608.3
120°	147.3	161.1	180.2	206.7	244.5	297.0	359.5	422.8	483.6	535.7	580.4
122.5°	155.6	169.7	187.7	212.2	247.3	295.5	352.8	412.2	468.0	517.2	557.6
125°	167.5	181.2	198.9	220.9	251.4	292.7	343.2	396.7	447.3	490.5	527.4
127.5°	178.0	192.1	209.3	229.1	255.6	291.0	334.4	381.5	427.3	468.0	502.0
130°	184.6	198.4	215.6	234.2	258.7	290.2	328.5	371.7	414.0	452.7	485.1
132.5°	190.9	204.7	221.0	239.4	261.9	289.8	323.7	362.3	401.4	437.0	467.4
135°	199.3	213.1	228.9	246.0	265.6	289.2	317.2	349.1	381.5	414.0	441.4
137.5°	206.8	219.6	235.1	251.1	269.0	289.1	312.5	338.6	365.8	391.4	415.4
140°	211.1	223.9	238.7	253.8	270.5	288.7	309.9	331.9	355.5	378.1	399.7
142.5°	215.1	227.0	241.4	256.2	271.7	288.7	307.1	326.4	346.5	365.9	384.0
145°	221.4	232.2	245.5	259.2	273.0	287.7	303.4	318.7	334.8	350.1	364.4
147.5°	226.8	236.3	248.8	261.0	273.4	285.9	299.7	312.7	325.5	337.3	347.8
150°	230.3	239.1	250.4	261.7	273.0	284.8	296.6	308.3	319.2	329.5	338.3
152.5°	233.8	241.9	252.0	262.1	272.2	282.8	293.9	304.0	314.1	322.8	330.5
155°	238.7	246.0	254.3	262.7	271.0	279.4	288.7	298.1	305.9	313.2	318.7
157.5°	242.8	248.9	256.0	262.7	268.8	275.9	283.9	291.1	297.6	303.8	308.1
160°	245.5	250.9	256.8	262.7	267.6	273.5	280.3	286.7	292.1	297.6	301.0
162.5°	247.9	252.1	257.2	262.3	266.4	271.6	277.2	282.4	287.1	291.7	294.3
165°	250.4	253.4	257.8	261.2	264.2	267.6	272.0	276.0	279.4	282.8	284.8
167.5°	252.6	254.4	257.7	260.5	261.9	264.2	266.9	269.8	272.4	274.7	276.6
170°	253.4	254.9	257.3	259.8	260.7	262.2	264.2	266.7	268.1	270.1	271.0
172.5°	254.2	255.2	256.9	258.6	259.2	259.8	261.4	263.1	264.2	265.7	266.3
175°	254.9	255.3	256.3	257.3	256.8	257.3	257.8	259.2	259.8	260.3	260.7
177.5°	255.3	255.3	255.7	256.5	255.7	255.3	255.7	256.5	256.5	256.9	256.9
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1578.8	1579.7	1578.3	1579.2	1578.3	1579.7	1578.8	1583.8	1584.8	1585.6	1584.8
5°	1471.0	1464.2	1463.0	1461.4	1463.0	1464.2	1471.0	1473.9	1476.2	1480.7	1488.8
7.5°	1342.4	1341.4	1338.5	1334.6	1338.5	1341.4	1342.4	1352.2	1359.9	1368.9	1385.3
10°	1259.6	1256.8	1256.3	1252.2	1256.3	1256.8	1259.6	1272.2	1281.3	1293.9	1316.2
12.5°	1162.8	1144.4	1142.5	1132.5	1142.5	1144.4	1162.8	1179.0	1203.7	1215.8	1239.4
15°	990.1	986.6	975.2	967.8	975.2	986.6	990.1	1003.8	1012.9	1046.0	1084.3
17.5°	891.3	880.1	876.6	874.9	876.6	880.1	891.3	897.9	910.9	928.4	951.5
20°	827.8	817.5	815.8	814.7	815.8	817.5	827.8	835.8	846.1	865.0	888.9
22.5°	783.9	773.2	768.7	765.3	768.7	773.2	783.9	790.1	799.4	814.2	830.4
25°	708.9	705.0	702.7	701.5	702.7	705.0	708.9	714.6	723.8	743.8	761.0
27.5°	650.3	641.5	639.8	636.9	639.8	641.5	650.3	660.5	670.0	679.0	694.3
30°	617.0	614.2	610.1	606.7	610.1	614.2	617.0	622.2	628.4	643.9	658.7
32.5°	577.6	575.3	571.7	570.2	571.7	575.3	577.6	584.6	597.8	607.3	618.0
35°	534.2	526.2	522.7	517.5	522.7	526.2	534.2	539.8	545.0	553.0	572.4
37.5°	488.1	483.9	479.1	480.8	479.1	483.9	488.1	490.5	501.4	512.5	520.9
40°	452.5	449.6	448.5	447.9	448.5	449.6	452.5	459.9	473.0	478.2	490.8
42.5°	424.1	416.2	413.3	413.1	413.3	416.2	424.1	432.5	440.6	448.9	461.9
45°	381.1	373.6	368.5	369.0	368.5	373.6	381.1	383.9	390.7	407.3	414.7
47.5°	336.9	336.7	333.6	334.6	333.6	336.7	336.9	341.8	350.7	360.8	372.7
50°	315.9	312.5	310.2	310.7	310.2	312.5	315.9	319.9	325.0	330.2	348.4
52.5°	295.8	292.8	291.0	293.4	291.0	292.8	295.8	298.0	301.8	306.9	319.3
55°	262.8	259.3	258.8	258.2	258.8	259.3	262.8	265.6	270.2	274.2	279.9
57.5°	225.9	223.6	220.2	218.7	220.2	223.6	225.9	230.1	235.6	240.8	246.8
60°	199.4	194.8	189.1	188.6	189.1	194.8	199.4	206.8	209.1	217.1	223.9
62.5°	175.1	174.3	173.1	173.0	173.1	174.3	175.1	177.5	180.7	192.4	200.6
65°	153.7	153.1	153.7	154.2	153.7	153.1	153.7	154.8	155.4	156.5	160.0
67.5°	133.9	132.9	131.8	132.3	131.8	132.9	133.9	134.1	135.7	136.4	138.8
70°	118.8	118.2	117.7	117.7	117.7	118.2	118.8	119.9	121.1	122.3	125.1
72.5°	104.2	104.1	103.5	103.1	103.5	104.1	104.2	106.2	106.9	108.1	110.0
75°	83.4	82.2	82.2	82.2	82.2	82.2	83.4	83.9	84.6	86.3	87.4
77.5°	63.5	62.9	62.4	61.9	62.4	62.9	63.5	63.6	64.6	64.9	66.1
80°	50.3	49.7	49.2	49.2	49.2	49.7	50.3	50.9	50.9	52.5	52.0
82.5°	38.4	37.8	37.7	37.3	37.7	37.8	38.4	38.5	38.5	39.8	39.6
85°	20.6	21.1	20.6	21.7	20.6	21.1	20.6	20.0	20.6	21.7	21.7
87.5°	9.2	8.7	9.2	8.7	9.2	8.7	9.2	9.2	9.6	9.4	9.6
90°	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2	15.7	14.7	15.7
92.5°	29.2	27.6	28.0	27.2	28.0	27.6	29.2	29.5	32.6	36.8	42.8
95°	60.9	57.0	55.4	56.0	55.4	57.0	60.9	67.2	78.1	98.7	128.6
97.5°	133.5	121.5	114.3	110.2	114.3	121.5	133.5	157.0	192.5	245.6	300.2
100°	220.0	198.9	184.6	175.8	184.6	198.9	220.0	260.7	320.1	387.4	448.3
102.5°	375.1	339.1	321.3	309.4	321.3	339.1	375.1	419.4	482.4	531.6	545.4
105°	611.8	581.3	560.3	553.4	560.3	581.3	611.8	642.2	658.5	652.0	596.6
107.5°	721.9	720.2	716.0	706.9	716.0	720.2	721.9	718.1	694.3	643.3	559.6
110°	739.9	749.3	753.7	753.2	753.7	749.3	739.9	718.8	678.6	615.7	527.9



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	725.8	741.4	749.8	752.4	749.8	741.4	725.8	696.5	650.3	583.2	498.8
115°	688.4	711.0	723.8	728.1	723.8	711.0	688.4	653.6	603.0	538.6	463.0
117.5°	643.9	667.7	681.1	684.8	681.1	667.7	643.9	608.3	560.9	502.5	436.1
120°	614.8	637.8	652.0	656.9	652.0	637.8	614.8	580.4	535.7	483.6	422.8
122.5°	588.4	611.1	623.8	627.9	623.8	611.1	588.4	557.6	517.2	468.0	412.2
125°	555.9	574.5	586.8	590.7	586.8	574.5	555.9	527.4	490.5	447.3	396.7
127.5°	526.8	544.3	554.9	558.1	554.9	544.3	526.8	502.0	468.0	427.3	381.5
130°	509.2	525.9	535.7	539.6	535.7	525.9	509.2	485.1	452.7	414.0	371.7
132.5°	491.1	507.8	516.9	520.4	516.9	507.8	491.1	467.4	437.0	401.4	362.3
135°	462.5	478.7	487.6	489.6	487.6	478.7	462.5	441.4	414.0	381.5	349.1
137.5°	434.6	448.6	456.3	459.3	456.3	448.6	434.6	415.4	391.4	365.8	338.6
140°	415.4	428.2	435.5	438.5	435.5	428.2	415.4	399.7	378.1	355.5	331.9
142.5°	398.9	410.5	417.1	417.7	417.1	410.5	398.9	384.0	365.9	346.5	326.4
145°	376.1	384.4	389.3	390.8	389.3	384.4	376.1	364.4	350.1	334.8	318.7
147.5°	357.5	364.1	367.5	368.3	367.5	364.1	357.5	347.8	337.3	325.5	312.7
150°	345.7	351.5	354.5	355.0	354.5	351.5	345.7	338.3	329.5	319.2	308.3
152.5°	336.2	341.4	343.5	343.6	343.5	341.4	336.2	330.5	322.8	314.1	304.0
155°	324.1	327.5	329.5	328.5	329.5	327.5	324.1	318.7	313.2	305.9	298.1
157.5°	311.9	314.8	315.6	315.6	315.6	314.8	311.9	308.1	303.8	297.6	291.1
160°	304.4	306.9	307.4	307.4	307.4	306.9	304.4	301.0	297.6	292.1	286.7
162.5°	297.7	299.5	299.9	299.5	299.9	299.5	297.7	294.3	291.7	287.1	282.4
165°	286.7	288.7	288.7	288.3	288.7	288.7	286.7	284.8	282.8	279.4	276.0
167.5°	277.4	278.5	278.4	277.8	278.4	278.5	277.4	276.6	274.7	272.4	269.8
170°	271.6	273.0	272.5	271.6	272.5	273.0	271.6	271.0	270.1	268.1	266.7
172.5°	266.8	267.5	267.0	266.4	267.0	267.5	266.8	266.3	265.7	264.2	263.1
175°	260.7	261.2	260.7	259.8	260.7	261.2	260.7	260.7	260.3	259.8	259.2
177.5°	256.9	256.9	256.5	255.7	256.5	256.9	256.9	256.9	256.9	256.5	256.5
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1581.1	1587.5	1597.1	1602.6	1611.7	1617.6	1620.8	1626.8	1630.0	1641.4	1653.3
5°	1492.7	1501.9	1517.9	1532.8	1548.8	1565.3	1577.3	1591.0	1603.6	1625.3	1648.1
7.5°	1391.5	1404.2	1429.0	1452.7	1480.5	1504.0	1524.7	1548.1	1569.0	1600.1	1632.5
10°	1315.7	1337.9	1370.5	1392.8	1429.3	1452.8	1485.3	1511.1	1540.2	1581.3	1617.9
12.5°	1250.3	1277.1	1303.3	1334.3	1367.2	1406.2	1441.9	1474.9	1509.6	1552.0	1595.0
15°	1131.7	1170.5	1211.1	1242.5	1287.1	1328.3	1369.9	1414.5	1456.7	1507.6	1563.6
17.5°	979.0	1024.1	1092.3	1146.1	1198.4	1239.7	1291.3	1345.2	1395.1	1456.4	1518.7
20°	910.1	943.2	989.5	1062.0	1140.8	1184.8	1237.4	1296.8	1353.9	1420.7	1487.6
22.5°	854.7	884.2	921.4	977.9	1065.9	1125.8	1180.7	1241.0	1307.3	1375.5	1449.7
25°	775.8	796.3	835.2	880.9	941.5	1040.3	1100.3	1160.8	1232.9	1306.0	1390.5
27.5°	716.5	735.0	760.3	803.9	848.9	919.9	1015.3	1081.3	1153.1	1235.4	1323.1
30°	671.2	692.9	720.9	751.8	800.9	856.4	951.7	1028.3	1099.2	1183.7	1277.4
32.5°	638.3	655.5	679.3	710.7	751.6	804.7	880.9	973.9	1042.9	1132.0	1229.9
35°	584.4	604.4	623.9	653.6	686.6	735.2	792.9	892.3	960.9	1048.9	1147.1
37.5°	539.9	552.2	573.7	597.2	632.1	668.4	718.4	807.5	881.8	968.1	1068.7
40°	506.2	521.6	537.6	563.9	592.5	627.2	676.4	742.7	827.8	912.3	1010.6
42.5°	473.3	492.8	509.7	527.3	558.6	593.5	633.4	689.7	776.6	856.6	952.1
45°	433.6	446.2	463.9	483.3	509.0	538.7	574.1	623.3	706.7	775.8	865.5
47.5°	387.4	405.9	417.4	436.4	460.8	489.1	522.0	564.6	632.1	696.8	780.1
50°	355.9	374.8	391.3	408.5	430.2	457.6	485.0	526.2	580.4	648.4	726.1
52.5°	328.9	345.5	361.6	378.8	400.0	425.2	451.2	487.3	533.8	596.3	671.8
55°	292.0	302.2	318.7	335.9	354.7	378.8	403.9	434.2	474.2	526.8	587.9
57.5°	254.0	265.9	279.1	296.3	315.4	333.7	356.4	383.7	415.3	462.9	515.2
60°	232.5	241.7	252.5	270.2	287.9	304.4	326.2	349.0	378.8	419.9	464.4
62.5°	208.7	217.4	227.4	242.8	260.0	275.3	294.2	318.4	343.5	381.1	420.1
65°	169.1	181.7	191.4	205.1	219.4	235.4	250.2	269.7	292.0	321.7	356.5
67.5°	140.2	146.6	155.6	168.1	182.7	196.4	210.4	225.7	245.0	267.9	295.6
70°	127.4	129.7	131.4	143.4	157.1	170.8	183.9	198.2	214.8	233.7	257.6
72.5°	112.3	114.6	116.8	121.9	132.9	146.6	160.1	170.8	186.5	202.1	221.5
75°	89.1	92.6	94.3	97.1	101.1	110.3	122.9	133.1	142.2	154.2	169.7
77.5°	67.8	69.8	71.6	74.6	77.1	81.4	88.4	97.7	106.2	113.2	123.8
80°	53.7	54.2	56.6	57.7	61.1	64.0	67.4	74.8	83.4	86.3	93.7
82.5°	40.5	41.0	42.9	44.0	45.5	48.0	52.3	54.2	61.0	64.7	69.5
85°	22.3	21.7	23.4	23.4	24.5	25.7	26.9	29.7	31.4	36.0	37.1
87.5°	10.1	10.2	10.6	10.0	9.3	9.7	9.9	10.2	10.8	11.8	13.3
90°	16.2	16.7	16.2	13.3	9.8	7.4	5.9	4.9	4.0	2.0	0.5
92.5°	53.9	63.8	62.9	49.0	33.4	22.3	17.7	14.4	12.1	8.6	6.0
95°	168.4	192.5	170.4	113.4	70.7	48.1	36.3	28.5	24.0	19.1	17.2
97.5°	344.7	328.6	247.5	152.8	93.3	64.9	51.6	42.5	35.8	30.7	28.0
100°	458.6	387.9	267.1	161.1	101.2	75.2	61.4	51.6	43.7	39.3	37.8
102.5°	501.0	389.9	259.7	161.4	108.2	84.1	70.4	60.2	52.3	48.0	46.8
105°	494.5	363.9	245.0	164.0	120.3	97.2	83.4	72.7	65.3	61.9	59.9
107.5°	451.3	336.0	237.7	170.7	132.7	110.3	96.4	85.8	79.0	75.6	74.0
110°	424.2	322.6	236.2	176.2	140.9	119.3	105.0	94.8	88.4	85.4	83.4



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	405.4	313.9	236.6	182.2	148.8	127.9	113.3	103.4	97.4	94.1	92.1
115°	382.0	304.4	238.7	191.0	161.1	139.9	126.7	116.8	111.0	108.1	105.6
117.5°	367.3	299.8	242.2	200.4	172.4	152.8	139.1	129.7	124.4	121.5	119.5
120°	359.5	297.0	244.5	206.7	180.2	161.1	147.3	137.5	133.0	130.1	128.1
122.5°	352.8	295.5	247.3	212.2	187.7	169.7	155.6	145.8	140.9	138.0	136.4
125°	343.2	292.7	251.4	220.9	198.9	181.2	167.5	157.6	151.7	148.8	147.3
127.5°	334.4	291.0	255.6	229.1	209.3	192.1	178.0	168.5	162.0	157.9	155.9
130°	328.5	290.2	258.7	234.2	215.6	198.4	184.6	174.8	167.9	163.0	161.1
132.5°	323.7	289.8	261.9	239.4	221.0	204.7	190.9	180.7	173.4	168.2	165.7
135°	317.2	289.2	265.6	246.0	228.9	213.1	199.3	188.0	180.7	174.8	172.8
137.5°	312.5	289.1	269.0	251.1	235.1	219.6	206.8	195.6	187.8	181.8	179.5
140°	309.9	288.7	270.5	253.8	238.7	223.9	211.1	200.4	192.5	186.6	184.6
142.5°	307.1	288.7	271.7	256.2	241.4	227.0	215.1	204.7	196.8	191.3	189.8
145°	303.4	287.7	273.0	259.2	245.5	232.2	221.4	211.6	204.2	199.3	197.4
147.5°	299.7	285.9	273.4	261.0	248.8	236.3	226.8	218.6	211.8	207.1	205.6
150°	296.6	284.8	273.0	261.7	250.4	239.1	230.3	222.9	216.5	212.6	211.1
152.5°	293.9	282.8	272.2	262.1	252.0	241.9	233.8	226.9	221.3	217.3	216.6
155°	288.7	279.4	271.0	262.7	254.3	246.0	238.7	233.2	227.8	224.9	224.4
157.5°	283.9	275.9	268.8	262.7	256.0	248.9	242.8	238.4	233.8	231.4	230.8
160°	280.3	273.5	267.6	262.7	256.8	250.9	245.5	241.6	237.6	235.7	235.2
162.5°	277.2	271.6	266.4	262.3	257.2	252.1	247.9	244.4	241.2	239.2	239.5
165°	272.0	267.6	264.2	261.2	257.8	253.4	250.4	248.0	245.0	244.0	244.5
167.5°	266.9	264.2	261.9	260.5	257.7	254.4	252.6	250.8	248.9	248.1	248.7
170°	264.2	262.2	260.7	259.8	257.3	254.9	253.4	252.4	250.9	250.4	251.4
172.5°	261.4	259.8	259.2	258.6	256.9	255.2	254.2	253.6	252.1	252.4	253.0
175°	257.8	257.3	256.8	257.3	256.3	255.3	254.9	254.9	253.8	254.3	254.9
177.5°	255.7	255.3	255.7	256.5	255.7	255.3	255.3	255.3	254.5	254.9	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1653.7	1655.1	1664.2	1668.4	1676.6	1679.8	1683.4	1682.6	1682.6	1684.4	1697.2
5°	1657.3	1668.7	1685.8	1702.5	1718.4	1732.2	1741.3	1750.4	1753.9	1770.4	1785.3
7.5°	1651.3	1672.4	1700.7	1726.0	1756.3	1779.9	1799.6	1817.2	1829.4	1853.5	1878.2
10°	1643.6	1673.3	1705.3	1737.8	1779.5	1810.9	1843.0	1867.5	1875.5	1911.5	1932.1
12.5°	1628.1	1667.8	1708.5	1750.7	1791.4	1834.7	1869.9	1894.5	1922.6	1954.9	1992.9
15°	1604.7	1650.5	1703.6	1757.8	1816.1	1868.6	1906.3	1949.2	1980.0	2015.5	2048.6
17.5°	1571.2	1630.1	1697.6	1760.5	1827.9	1884.3	1936.2	1977.3	1999.0	2019.2	2024.1
20°	1544.7	1608.2	1687.6	1761.9	1829.3	1894.4	1945.8	1980.0	1985.8	1986.3	1956.1
22.5°	1516.0	1587.6	1670.7	1746.7	1827.4	1899.9	1939.8	1954.5	1931.8	1893.1	1834.5
25°	1463.0	1545.9	1642.4	1729.2	1817.2	1885.8	1899.5	1873.8	1794.4	1711.0	1605.3
27.5°	1405.7	1498.8	1602.3	1698.8	1792.6	1835.0	1805.5	1712.8	1569.8	1445.4	1294.8
30°	1363.7	1468.2	1569.9	1677.8	1764.7	1783.0	1715.0	1578.5	1411.6	1224.3	1074.0
32.5°	1315.7	1425.2	1537.0	1648.6	1721.3	1703.4	1591.1	1423.1	1227.4	1043.3	901.3
35°	1247.1	1360.2	1480.7	1592.8	1639.0	1561.9	1394.0	1175.1	975.2	803.2	705.5
37.5°	1167.9	1291.1	1416.4	1519.2	1516.0	1387.4	1158.6	932.8	764.7	663.1	593.5
40°	1111.7	1236.2	1371.7	1458.4	1421.3	1254.0	1006.0	792.9	670.1	589.0	538.1
42.5°	1057.8	1182.8	1317.2	1386.3	1321.7	1115.9	868.9	702.0	600.6	537.4	496.1
45°	966.0	1098.0	1222.5	1260.8	1145.4	918.6	702.7	581.6	514.2	467.3	438.8
47.5°	876.3	1006.2	1119.8	1120.5	964.4	744.9	592.8	503.3	445.7	409.5	388.7
50°	821.5	944.9	1040.3	1025.5	848.3	662.7	530.1	453.1	405.0	377.0	355.3
52.5°	759.8	879.5	962.2	919.9	750.1	583.2	473.9	409.1	369.4	345.1	325.6
55°	670.1	776.4	834.7	770.7	611.8	485.0	400.5	349.7	319.9	299.4	282.8
57.5°	582.0	669.7	706.4	631.8	503.9	402.2	338.8	300.6	271.1	256.4	247.8
60°	526.8	601.6	627.2	545.0	438.2	351.9	299.9	264.5	242.8	233.1	224.5
62.5°	472.3	533.5	544.1	468.6	381.9	308.1	263.4	233.4	219.0	209.7	201.6
65°	391.9	435.9	430.8	370.2	302.2	244.5	212.0	193.6	182.8	169.7	155.4
67.5°	322.6	349.5	333.3	287.9	230.7	190.0	168.8	154.9	141.5	129.0	125.7
70°	278.8	294.2	277.1	235.4	189.1	159.4	142.2	125.7	117.7	114.9	109.7
72.5°	236.8	242.1	223.6	187.9	153.9	132.0	115.3	106.0	101.7	99.3	96.0
75°	177.7	173.7	157.6	129.7	106.9	92.0	86.9	83.4	80.6	78.3	76.5
77.5°	124.8	118.9	104.7	86.4	74.4	67.3	64.2	62.4	61.0	59.8	58.1
80°	93.7	89.7	75.4	61.7	56.6	53.1	51.4	49.2	49.2	48.0	46.2
82.5°	68.5	64.1	51.7	45.2	42.4	40.3	39.1	37.7	37.3	37.5	36.2
85°	36.0	29.1	25.7	24.5	22.8	21.7	22.3	21.1	21.1	21.1	20.6
87.5°	11.4	9.5	9.2	9.0	9.7	10.2	10.4	11.0	11.5	11.0	11.4
90°	2.0	4.0	4.9	5.9	7.4	9.8	13.3	16.2	16.7	16.2	15.7
92.5°	8.6	12.1	14.4	17.7	22.3	33.4	49.0	62.9	63.8	53.9	42.8
95°	19.1	24.0	28.5	36.3	48.1	70.7	113.4	170.4	192.5	168.4	128.6
97.5°	30.7	35.8	42.5	51.6	64.9	93.3	152.8	247.5	328.6	344.7	300.2
100°	39.3	43.7	51.6	61.4	75.2	101.2	161.1	267.1	387.9	458.6	448.3
102.5°	48.0	52.3	60.2	70.4	84.1	108.2	161.4	259.7	389.9	501.0	545.4
105°	61.9	65.3	72.7	83.4	97.2	120.3	164.0	245.0	363.9	494.5	596.6
107.5°	75.6	79.0	85.8	96.4	110.3	132.7	170.7	237.7	336.0	451.3	559.6
110°	85.4	88.4	94.8	105.0	119.3	140.9	176.2	236.2	322.6	424.2	527.9



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	94.1	97.4	103.4	113.3	127.9	148.8	182.2	236.6	313.9	405.4	498.8
115°	108.1	111.0	116.8	126.7	139.9	161.1	191.0	238.7	304.4	382.0	463.0
117.5°	121.5	124.4	129.7	139.1	152.8	172.4	200.4	242.2	299.8	367.3	436.1
120°	130.1	133.0	137.5	147.3	161.1	180.2	206.7	244.5	297.0	359.5	422.8
122.5°	138.0	140.9	145.8	155.6	169.7	187.7	212.2	247.3	295.5	352.8	412.2
125°	148.8	151.7	157.6	167.5	181.2	198.9	220.9	251.4	292.7	343.2	396.7
127.5°	157.9	162.0	168.5	178.0	192.1	209.3	229.1	255.6	291.0	334.4	381.5
130°	163.0	167.9	174.8	184.6	198.4	215.6	234.2	258.7	290.2	328.5	371.7
132.5°	168.2	173.4	180.7	190.9	204.7	221.0	239.4	261.9	289.8	323.7	362.3
135°	174.8	180.7	188.0	199.3	213.1	228.9	246.0	265.6	289.2	317.2	349.1
137.5°	181.8	187.8	195.6	206.8	219.6	235.1	251.1	269.0	289.1	312.5	338.6
140°	186.6	192.5	200.4	211.1	223.9	238.7	253.8	270.5	288.7	309.9	331.9
142.5°	191.3	196.8	204.7	215.1	227.0	241.4	256.2	271.7	288.7	307.1	326.4
145°	199.3	204.2	211.6	221.4	232.2	245.5	259.2	273.0	287.7	303.4	318.7
147.5°	207.1	211.8	218.6	226.8	236.3	248.8	261.0	273.4	285.9	299.7	312.7
150°	212.6	216.5	222.9	230.3	239.1	250.4	261.7	273.0	284.8	296.6	308.3
152.5°	217.3	221.3	226.9	233.8	241.9	252.0	262.1	272.2	282.8	293.9	304.0
155°	224.9	227.8	233.2	238.7	246.0	254.3	262.7	271.0	279.4	288.7	298.1
157.5°	231.4	233.8	238.4	242.8	248.9	256.0	262.7	268.8	275.9	283.9	291.1
160°	235.7	237.6	241.6	245.5	250.9	256.8	262.7	267.6	273.5	280.3	286.7
162.5°	239.2	241.2	244.4	247.9	252.1	257.2	262.3	266.4	271.6	277.2	282.4
165°	244.0	245.0	248.0	250.4	253.4	257.8	261.2	264.2	267.6	272.0	276.0
167.5°	248.1	248.9	250.8	252.6	254.4	257.7	260.5	261.9	264.2	266.9	269.8
170°	250.4	250.9	252.4	253.4	254.9	257.3	259.8	260.7	262.2	264.2	266.7
172.5°	252.4	252.1	253.6	254.2	255.2	256.9	258.6	259.2	259.8	261.4	263.1
175°	254.3	253.8	254.9	254.9	255.3	256.3	257.3	256.8	257.3	257.8	259.2
177.5°	254.9	254.5	255.3	255.3	255.3	255.7	256.5	255.7	255.3	255.7	256.5
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1701.8	1707.7	1710.4	1710.4	1713.6	1712.3	1710.9
5°	1799.6	1810.4	1812.7	1823.0	1830.4	1828.1	1829.3
7.5°	1896.8	1914.3	1931.5	1939.4	1940.6	1945.2	1946.9
10°	1956.6	1970.9	1997.8	1993.7	2013.8	2025.2	2006.3
12.5°	2014.2	2033.5	2052.2	2057.3	2068.6	2072.3	2064.9
15°	2066.3	2076.6	2077.8	2074.9	2078.3	2075.4	2064.6
17.5°	2017.7	2001.0	1967.1	1951.1	1938.5	1919.8	1912.2
20°	1937.2	1888.1	1830.9	1808.1	1781.2	1728.7	1741.3
22.5°	1763.6	1707.5	1650.5	1583.7	1551.9	1502.0	1499.0
25°	1493.3	1396.8	1290.6	1216.2	1172.9	1123.2	1101.4
27.5°	1161.1	1039.5	952.4	908.4	868.2	828.8	827.2
30°	942.6	851.2	783.8	746.1	721.5	705.0	708.4
32.5°	794.5	731.9	686.5	655.1	637.0	624.5	624.3
35°	649.5	606.7	577.6	564.4	551.3	542.2	542.7
37.5°	555.9	530.1	513.9	499.4	491.2	486.7	484.2
40°	507.9	486.7	474.2	465.6	458.7	452.5	451.3
42.5°	469.9	452.5	439.9	433.2	426.7	422.3	421.1
45°	417.1	402.8	391.3	383.9	381.1	377.0	377.0
47.5°	371.0	357.0	348.0	343.4	338.5	335.8	335.7
50°	339.9	329.1	321.1	318.2	314.2	312.5	311.9
52.5°	312.0	303.9	298.3	296.3	294.5	292.4	292.7
55°	274.2	269.7	267.3	265.6	262.8	259.3	261.7
57.5°	242.4	238.4	232.3	226.9	224.3	221.9	222.8
60°	220.0	212.0	204.0	197.7	196.0	190.8	190.8
62.5°	191.6	180.4	170.6	167.0	165.3	162.9	162.5
65°	147.4	142.8	140.5	138.3	137.1	137.1	136.0
67.5°	122.2	120.3	117.8	117.3	116.1	115.7	115.4
70°	108.0	105.6	104.5	104.0	102.8	103.4	101.7
72.5°	94.3	92.5	92.2	90.7	90.1	90.1	88.9
75°	74.3	74.3	73.7	73.1	72.0	71.4	72.0
77.5°	57.2	57.3	56.2	56.1	56.0	56.1	55.5
80°	45.7	46.2	45.7	45.1	44.6	45.1	44.6
82.5°	36.1	35.3	35.2	35.0	35.0	34.6	34.5
85°	20.6	21.1	20.6	20.0	20.0	20.0	20.6
87.5°	10.7	10.9	11.0	11.0	11.0	11.0	10.6
90°	14.7	15.7	16.2	16.2	16.2	16.2	16.2
92.5°	36.8	32.6	29.5	29.2	27.6	28.0	27.2
95°	98.7	78.1	67.2	60.9	57.0	55.4	56.0
97.5°	245.6	192.5	157.0	133.5	121.5	114.3	110.2
100°	387.4	320.1	260.7	220.0	198.9	184.6	175.8
102.5°	531.6	482.4	419.4	375.1	339.1	321.3	309.4
105°	652.0	658.5	642.2	611.8	581.3	560.3	553.4
107.5°	643.3	694.3	718.1	721.9	720.2	716.0	706.9
110°	615.7	678.6	718.8	739.9	749.3	753.7	753.2



TEST NUMBER: P331713-935

CATALOG NUMBER: S122RDIP-S865D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	583.2	650.3	696.5	725.8	741.4	749.8	752.4
115°	538.6	603.0	653.6	688.4	711.0	723.8	728.1
117.5°	502.5	560.9	608.3	643.9	667.7	681.1	684.8
120°	483.6	535.7	580.4	614.8	637.8	652.0	656.9
122.5°	468.0	517.2	557.6	588.4	611.1	623.8	627.9
125°	447.3	490.5	527.4	555.9	574.5	586.8	590.7
127.5°	427.3	468.0	502.0	526.8	544.3	554.9	558.1
130°	414.0	452.7	485.1	509.2	525.9	535.7	539.6
132.5°	401.4	437.0	467.4	491.1	507.8	516.9	520.4
135°	381.5	414.0	441.4	462.5	478.7	487.6	489.6
137.5°	365.8	391.4	415.4	434.6	448.6	456.3	459.3
140°	355.5	378.1	399.7	415.4	428.2	435.5	438.5
142.5°	346.5	365.9	384.0	398.9	410.5	417.1	417.7
145°	334.8	350.1	364.4	376.1	384.4	389.3	390.8
147.5°	325.5	337.3	347.8	357.5	364.1	367.5	368.3
150°	319.2	329.5	338.3	345.7	351.5	354.5	355.0
152.5°	314.1	322.8	330.5	336.2	341.4	343.5	343.6
155°	305.9	313.2	318.7	324.1	327.5	329.5	328.5
157.5°	297.6	303.8	308.1	311.9	314.8	315.6	315.6
160°	292.1	297.6	301.0	304.4	306.9	307.4	307.4
162.5°	287.1	291.7	294.3	297.7	299.5	299.9	299.5
165°	279.4	282.8	284.8	286.7	288.7	288.7	288.3
167.5°	272.4	274.7	276.6	277.4	278.5	278.4	277.8
170°	268.1	270.1	271.0	271.6	273.0	272.5	271.6
172.5°	264.2	265.7	266.3	266.8	267.5	267.0	266.4
175°	259.8	260.3	260.7	260.7	261.2	260.7	259.8
177.5°	256.5	256.9	256.9	256.9	256.9	256.5	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3

(END OF REPORT)