

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331256-840

Luminaire Tested: **S122DIP-S290D530U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331256-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D530U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3124.7 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331256-840
CATALOG NUMBER: S122DIP-S290D530U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331256-840

CATALOG NUMBER: S122DIP-S290D530U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39	39	39	39	39	39	39	39	39	39	39	39																
	1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39	33	33	33	33	33	33	33	33	33	33	33	33																
	2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33	27	27	27	27	27	27	27	27	27	27	27	27																
	3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28	23	23	23	23	23	23	23	23	23	23	23	23																
	4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20	20	20	20	20	20	20	20	20	20	20	20																
	5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17	17	17	17	17	17	17	17	17	17	17	17																
	6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15	15	15	15	15	15	15	15	15	15	15	15																
	7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16	14	14	14	14	14	14	14	14	14	14	14	14																
	8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15	12	12	12	12	12	12	12	12	12	12	12	12																
	9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11	11	11	11	11	11	11	11	11	11	11	11																
	10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10	10	10	10	10	10	10	10	10	10	10	10																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7703	7703	7703
5°	7733	7621	7666
10°	7688	7543	7581
15°	7590	7447	7438
20°	7455	7301	7290
25°	7322	7119	7119
30°	7150	6952	6893
35°	6991	6753	6654
40°	6787	6555	6431
45°	6588	6357	6202
50°	6373	6154	5935
55°	6145	5917	5695
60°	5896	5628	5422
65°	5624	5349	5100
70°	5282	4999	4763
75°	4810	4604	4492
80°	4258	4138	3924
85°	3483	3316	2983



TEST NUMBER: P331256-840

CATALOG NUMBER: S122DIP-S290D530U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.9	1.4
10°-20°	126.2	4.0
20°-30°	185.5	5.9
30°-40°	215.5	6.9
40°-50°	215.3	6.9
50°-60°	187.7	6.0
60°-70°	138.8	4.4
70°-80°	78.6	2.5
80°-90°	23.9	0.8
90°-100°	43.3	1.4
100°-110°	134.3	4.3
110°-120°	229.6	7.3
120°-130°	301.9	9.7
130°-140°	338.8	10.8
140°-150°	332.2	10.6
150°-160°	278.7	8.9
160°-170°	184.8	5.9
170°-180°	64.6	2.1
0°-30°	356.6	11.4
0°-40°	572.2	18.3
0°-60°	975.2	31.2
0°-90°	1216.5	38.9
90°-120°	407.1	13.0
90°-150°	1380.1	44.2
90°-180°	1908.0	61.1
0°-180°	3124.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	477	477	477	477	477	
5°	477	475	470	474	473	45
15°	454	451	446	447	445	128
25°	411	407	400	400	400	189
35°	355	350	343	340	338	221
45°	288	285	278	274	272	223
55°	218	215	210	205	202	195
65°	147	144	140	136	134	146
75°	77	76	74	71	72	82
85°	19	18	18	17	16	22
90°	1	8	20	19	20	3
95°	30	35	37	37	36	34
105°	124	125	127	128	128	131
115°	230	234	233	232	230	228
125°	335	340	339	337	336	299
135°	434	440	441	440	439	335
145°	526	530	534	534	532	329
155°	602	604	605	608	606	277
165°	655	654	654	658	655	185
175°	681	680	678	682	679	65
180°	682	682	682	682	682	



TEST NUMBER: P331256-840

CATALOG NUMBER: S122DIP-S290D530U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1
2.5°	479.3	478.9	478.5	478.1	477.7	477.1	476.2	475.2	474.3	473.4	474.2
5°	477.1	476.7	476.3	475.8	475.4	474.7	473.6	472.5	471.3	470.2	471.0
7.5°	472.9	472.2	471.6	471.0	470.4	469.5	468.4	467.2	466.1	464.9	465.7
10°	468.9	468.2	467.5	466.8	466.0	465.0	463.8	462.6	461.4	460.1	460.9
12.5°	463.3	462.7	462.1	461.4	460.8	459.9	458.7	457.5	456.3	455.0	455.6
15°	454.1	453.5	452.9	452.3	451.7	450.8	449.4	448.1	446.8	445.5	445.9
17.5°	442.4	441.8	441.2	440.6	440.0	439.0	437.7	436.3	434.9	433.6	434.0
20°	433.9	433.3	432.7	432.1	431.5	430.5	429.1	427.7	426.3	424.9	425.2
22.5°	425.6	424.6	423.8	422.9	422.1	421.0	419.7	418.3	417.0	415.7	415.7
25°	411.0	410.2	409.4	408.6	407.8	406.5	404.8	403.0	401.3	399.6	399.8
27.5°	394.6	393.8	393.0	392.3	391.6	390.5	389.2	387.8	386.5	385.1	384.8
30°	383.5	382.7	381.9	381.1	380.2	379.1	377.6	376.1	374.5	372.9	372.6
32.5°	371.7	371.1	370.5	369.8	369.2	368.0	366.4	364.9	363.2	361.6	361.0
35°	354.7	353.6	352.5	351.5	350.5	349.2	347.6	346.0	344.4	342.6	342.0
37.5°	335.3	334.4	333.5	332.5	331.6	330.4	328.8	327.2	325.5	323.9	323.2
40°	322.0	321.2	320.4	319.6	318.8	317.6	315.9	314.3	312.7	311.0	310.1
42.5°	309.2	308.4	307.6	306.8	306.0	304.7	303.1	301.4	299.8	298.2	297.2
45°	288.5	287.8	287.1	286.4	285.7	284.6	283.1	281.6	280.0	278.4	277.3
47.5°	268.0	267.3	266.7	266.0	265.3	264.2	262.6	261.1	259.4	257.8	256.6
50°	253.7	253.2	252.7	252.2	251.7	250.6	249.2	247.8	246.4	245.0	243.6
52.5°	239.7	239.0	238.4	237.7	237.0	236.0	234.7	233.4	232.0	230.7	229.4
55°	218.3	217.7	217.1	216.5	215.9	215.0	213.8	212.6	211.4	210.2	208.8
57.5°	196.9	196.4	195.9	195.4	194.9	194.0	192.7	191.4	190.0	188.6	187.4
60°	182.6	182.2	181.8	181.4	181.0	180.1	178.6	177.2	175.7	174.3	173.2
62.5°	168.6	167.9	167.3	166.7	166.0	165.1	164.0	163.0	161.9	160.8	159.7
65°	147.2	146.6	146.0	145.4	144.8	144.0	143.0	142.0	141.0	140.0	139.0
67.5°	125.5	125.0	124.5	124.0	123.6	122.9	121.9	121.0	120.1	119.2	118.5
70°	111.9	111.5	111.1	110.7	110.3	109.7	108.8	107.9	106.8	105.9	105.2
72.5°	98.0	97.6	97.1	96.7	96.3	95.8	95.2	94.7	94.1	93.5	92.8
75°	77.1	76.9	76.6	76.4	76.2	75.9	75.4	74.8	74.3	73.8	73.2
77.5°	58.4	58.0	57.7	57.4	57.0	56.7	56.5	56.2	56.0	55.8	55.5
80°	45.8	45.7	45.6	45.5	45.4	45.3	45.1	44.9	44.7	44.5	44.2
82.5°	34.1	34.1	34.1	34.0	34.0	33.9	33.8	33.7	33.6	33.5	33.1
85°	18.8	18.7	18.6	18.5	18.4	18.3	18.2	18.1	18.0	17.9	17.6
87.5°	6.8	6.9	7.0	7.2	7.3	7.6	8.0	8.4	8.8	9.2	8.9
90°	0.6	2.1	3.6	5.2	6.8	8.9	11.7	14.5	17.4	20.2	19.9
92.5°	10.3	11.4	12.5	13.6	14.7	15.7	16.4	17.0	17.7	18.3	18.4
95°	30.0	31.2	32.5	33.8	35.0	35.9	36.1	36.4	36.6	36.9	36.9
97.5°	54.7	55.8	57.0	58.1	59.2	60.0	60.5	61.0	61.5	62.0	62.0
100°	73.1	74.1	75.1	76.2	77.3	78.0	78.4	78.7	79.1	79.5	79.5
102.5°	92.5	93.3	94.1	94.9	95.7	96.4	96.9	97.4	97.9	98.4	98.5
105°	123.8	124.2	124.6	124.9	125.3	125.6	125.9	126.1	126.4	126.7	126.9
107.5°	155.4	155.9	156.5	157.0	157.6	157.9	157.9	157.9	157.9	157.9	158.0
110°	175.6	176.4	177.1	177.9	178.7	179.0	179.0	179.0	179.0	179.0	179.0



TEST NUMBER: P331256-840

CATALOG NUMBER: S122DIP-S290D530U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	197.7	198.5	199.2	200.1	200.9	201.2	201.1	201.0	200.9	200.8	200.5
115°	230.4	231.2	231.9	232.7	233.4	233.7	233.4	233.2	232.9	232.7	232.6
117.5°	262.9	263.9	264.9	265.9	266.9	267.1	266.4	265.6	264.9	264.2	263.9
120°	284.5	285.5	286.5	287.5	288.6	288.6	287.5	286.5	285.5	284.5	284.5
122.5°	304.3	305.5	306.8	308.0	309.2	309.4	308.7	308.0	307.3	306.6	306.3
125°	335.2	336.3	337.5	338.6	339.7	340.1	339.7	339.4	339.0	338.6	338.2
127.5°	365.2	366.7	368.1	369.6	371.0	371.5	371.1	370.6	370.2	369.7	369.2
130°	384.2	385.8	387.4	389.1	390.7	391.4	391.2	390.9	390.7	390.4	390.2
132.5°	405.3	406.7	408.0	409.4	410.7	411.4	411.5	411.5	411.6	411.6	411.1
135°	433.6	435.0	436.5	437.9	439.3	440.1	440.3	440.6	440.9	441.1	441.0
137.5°	463.4	464.6	465.7	467.0	468.1	468.8	469.2	469.5	469.8	470.1	470.0
140°	481.4	482.6	483.7	484.8	486.0	487.0	487.6	488.2	488.9	489.5	489.5
142.5°	499.9	501.0	502.2	503.3	504.4	505.2	505.7	506.1	506.5	507.0	507.1
145°	526.3	527.3	528.2	529.1	530.0	530.8	531.5	532.3	533.1	533.8	533.9
147.5°	550.0	551.0	552.1	553.2	554.2	555.0	555.5	556.0	556.5	557.1	557.3
150°	566.1	566.8	567.6	568.4	569.2	569.8	570.3	570.8	571.3	571.9	572.2
152.5°	580.4	581.2	581.9	582.7	583.4	584.1	584.7	585.3	585.9	586.6	587.0
155°	601.8	602.2	602.6	602.9	603.3	603.7	604.1	604.5	604.8	605.2	605.9
157.5°	620.1	620.4	620.6	620.9	621.2	621.4	621.6	621.9	622.1	622.3	623.2
160°	631.2	631.4	631.7	631.9	632.2	632.4	632.5	632.6	632.8	632.9	633.7
162.5°	641.3	641.4	641.4	641.5	641.5	641.6	641.7	641.9	642.0	642.1	643.0
165°	654.8	654.6	654.5	654.4	654.3	654.2	654.2	654.2	654.2	654.2	655.1
167.5°	666.0	665.7	665.3	664.9	664.5	664.3	664.3	664.3	664.2	664.2	665.1
170°	672.1	671.7	671.3	670.9	670.6	670.2	670.1	669.9	669.8	669.7	670.7
172.5°	676.2	675.8	675.4	675.0	674.7	674.4	674.3	674.2	674.0	673.9	674.8
175°	681.3	680.9	680.4	680.1	679.7	679.4	679.1	678.9	678.6	678.3	679.2
177.5°	683.4	683.0	682.7	682.4	682.1	681.9	681.7	681.5	681.3	681.1	681.7
180°	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4



TEST NUMBER: P331256-840

CATALOG NUMBER: S122DIP-S290D530U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	477.1	477.1	477.1	477.1	477.1	477.1	477.1	477.1
2.5°	475.0	475.8	476.7	477.1	476.9	476.7	476.6	476.4
5°	471.9	472.7	473.5	473.8	473.6	473.4	473.2	473.0
7.5°	466.6	467.4	468.2	468.5	468.3	468.0	467.8	467.6
10°	461.8	462.6	463.4	463.6	463.3	463.0	462.7	462.4
12.5°	456.2	456.7	457.3	457.5	457.3	457.0	456.8	456.6
15°	446.3	446.7	447.1	447.1	446.6	446.1	445.6	445.0
17.5°	434.5	435.0	435.5	435.5	434.9	434.5	434.0	433.5
20°	425.5	425.8	426.1	426.0	425.6	425.2	424.7	424.3
22.5°	415.8	415.9	415.9	415.8	415.6	415.3	415.1	414.9
25°	400.0	400.2	400.4	400.4	400.2	400.0	399.8	399.6
27.5°	384.5	384.2	383.8	383.4	382.9	382.4	382.0	381.5
30°	372.3	372.0	371.7	371.4	371.0	370.6	370.2	369.7
32.5°	360.5	359.9	359.4	358.9	358.5	358.1	357.7	357.3
35°	341.4	340.8	340.2	339.7	339.2	338.7	338.2	337.6
37.5°	322.3	321.6	320.8	320.2	319.7	319.2	318.8	318.3
40°	309.2	308.3	307.4	306.7	306.3	305.9	305.5	305.1
42.5°	296.2	295.2	294.2	293.4	292.9	292.3	291.8	291.1
45°	276.2	275.1	274.0	273.2	272.8	272.4	272.0	271.6
47.5°	255.5	254.3	253.1	252.2	251.7	251.1	250.4	249.8
50°	242.2	240.7	239.2	238.3	237.8	237.3	236.8	236.3
52.5°	228.3	227.1	225.9	225.0	224.3	223.7	223.0	222.3
55°	207.6	206.4	205.2	204.4	203.9	203.3	202.8	202.3
57.5°	186.2	185.0	183.8	183.0	182.7	182.3	181.9	181.5
60°	172.1	171.0	169.9	169.2	168.8	168.5	168.2	167.9
62.5°	158.6	157.6	156.6	155.9	155.5	155.1	154.7	154.3
65°	138.0	137.1	136.2	135.5	135.0	134.5	134.0	133.5
67.5°	117.8	117.0	116.3	115.7	115.3	114.9	114.5	114.1
70°	104.5	103.8	103.1	102.6	102.2	101.7	101.3	100.9
72.5°	92.1	91.4	90.7	90.1	89.8	89.5	89.2	88.8
75°	72.6	72.0	71.4	71.2	71.4	71.6	71.8	72.0
77.5°	55.2	54.9	54.6	54.3	54.0	53.8	53.5	53.2
80°	43.9	43.6	43.3	43.0	42.8	42.6	42.4	42.2
82.5°	32.7	32.3	31.9	31.7	31.7	31.6	31.6	31.6
85°	17.3	17.0	16.7	16.5	16.4	16.3	16.2	16.1
87.5°	8.6	8.3	8.0	7.8	7.8	7.7	7.7	7.6
90°	19.7	19.4	19.1	19.1	19.2	19.3	19.5	19.6
92.5°	18.4	18.5	18.5	18.6	18.6	18.6	18.7	18.7
95°	36.9	36.9	36.9	36.8	36.5	36.3	36.0	35.7
97.5°	62.0	62.0	62.0	61.9	61.9	61.9	61.9	61.8
100°	79.5	79.5	79.5	79.4	79.3	79.2	79.1	78.9
102.5°	98.6	98.7	98.8	98.8	98.7	98.5	98.4	98.3
105°	127.2	127.4	127.7	127.8	127.8	127.8	127.8	127.8
107.5°	158.1	158.2	158.3	158.0	157.4	156.9	156.3	155.7
110°	179.0	179.0	179.0	178.9	178.5	178.1	177.7	177.3



TEST NUMBER: P331256-840

CATALOG NUMBER: S122DIP-S290D530U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	200.2	199.9	199.5	199.2	198.9	198.6	198.3	198.1
115°	232.4	232.3	232.2	231.9	231.5	231.2	230.8	230.4
117.5°	263.6	263.3	263.0	262.7	262.3	261.9	261.5	261.1
120°	284.5	284.5	284.5	284.3	283.9	283.6	283.2	282.8
122.5°	306.0	305.7	305.4	305.1	304.8	304.5	304.3	304.0
125°	337.8	337.5	337.1	336.8	336.7	336.6	336.4	336.3
127.5°	368.8	368.3	367.9	367.4	367.0	366.6	366.2	365.8
130°	389.9	389.7	389.4	389.0	388.5	388.0	387.5	387.0
132.5°	410.5	409.9	409.4	408.9	408.5	408.1	407.7	407.3
135°	440.9	440.7	440.6	440.3	440.0	439.6	439.2	438.8
137.5°	469.9	469.8	469.7	469.4	468.9	468.4	467.9	467.4
140°	489.5	489.5	489.5	489.3	488.7	488.2	487.7	487.2
142.5°	507.2	507.3	507.4	507.2	506.6	506.1	505.6	505.1
145°	534.1	534.2	534.3	534.1	533.6	533.1	532.6	532.1
147.5°	557.6	558.0	558.3	558.2	557.6	557.1	556.6	556.1
150°	572.6	573.0	573.4	573.4	573.0	572.6	572.2	571.9
152.5°	587.5	588.0	588.5	588.5	588.0	587.5	587.0	586.6
155°	606.5	607.1	607.8	607.9	607.5	607.1	606.7	606.4
157.5°	624.0	624.9	625.8	625.9	625.3	624.7	624.1	623.4
160°	634.4	635.2	635.9	636.1	635.6	635.1	634.5	634.0
162.5°	643.8	644.7	645.6	645.7	645.1	644.5	643.9	643.3
165°	656.0	656.9	657.7	657.9	657.2	656.6	656.0	655.3
167.5°	666.0	666.9	667.8	667.9	667.2	666.6	665.9	665.2
170°	671.6	672.5	673.3	673.4	672.6	671.9	671.1	670.3
172.5°	675.7	676.6	677.4	677.5	676.8	676.0	675.2	674.5
175°	680.1	681.1	682.0	682.1	681.3	680.4	679.7	678.9
177.5°	682.3	682.9	683.5	683.5	682.9	682.3	681.7	681.1
180°	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4

(END OF REPORT)