

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331287-840

Luminaire Tested: **S122DIP-S485D330U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331287-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D330U840-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3457.8 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58	54
2	93	85	79	74	87	80	75	71	71	67	64	62	59	57	54	52	50	46
3	85	76	69	63	79	71	65	60	63	58	54	56	52	49	49	46	43	40
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35
5	72	60	52	47	67	57	50	45	51	45	41	45	41	37	40	36	33	31
6	67	55	47	41	62	52	44	39	46	40	36	41	36	33	36	33	30	27
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27	24
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22
9	54	42	34	29	50	39	33	28	36	30	26	32	27	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15844	15844	15844	15844
5°	17763	15948	14131	15948
10°	20354	15816	12231	15816
15°	22519	15527	10805	15527
20°	22175	15216	9850	15216
25°	19996	14801	9246	14801
30°	16524	14139	8804	14139
35°	12043	13448	8489	13448
40°	9619	12631	8315	12631
45°	8405	11686	8079	11686
50°	7902	10771	7920	10771
55°	7282	9841	7707	9841
60°	6675	8854	7379	8854
65°	6082	7966	7060	7966
70°	5519	7105	6590	7105
75°	4897	6145	5833	6145
80°	4203	5086	4695	5086
85°	3779	3779	2779	3779



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	2.7
10°-20°	271.7	7.9
20°-30°	394.3	11.4
30°-40°	416.1	12.0
40°-50°	368.4	10.7
50°-60°	294.0	8.5
60°-70°	199.8	5.8
70°-80°	102.5	3.0
80°-90°	26.4	0.8
90°-100°	74.2	2.1
100°-110°	251.8	7.3
110°-120°	267.5	7.7
120°-130°	220.2	6.4
130°-140°	176.8	5.1
140°-150°	133.6	3.9
150°-160°	93.9	2.7
160°-170°	55.3	1.6
170°-180°	18.0	0.5
0°-30°	759.5	22.0
0°-40°	1175.6	34.0
0°-60°	1838.0	53.2
0°-90°	2166.7	62.7
90°-120°	593.4	17.2
90°-150°	1124.0	32.5
90°-180°	1291.0	37.3
0°-180°	3457.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	981	981	981	981	981	
5°	1096	984	872	984	1096	109
15°	1347	929	646	929	1347	372
25°	1122	831	519	831	1122	507
35°	611	682	431	682	611	397
45°	368	512	354	512	368	289
55°	259	350	274	350	259	232
65°	159	208	185	208	159	158
75°	78	98	94	98	78	84
85°	20	20	15	20	20	23
90°	12	0	12	0	12	7
95°	41	12	41	12	41	53
105°	402	44	402	44	402	389
115°	529	77	529	77	529	518
125°	429	107	429	107	429	388
135°	356	126	356	126	356	276
145°	284	143	284	143	284	180
155°	239	163	239	163	239	111
165°	209	178	209	178	209	60
175°	189	185	189	185	189	18
180°	186	186	186	186	186	



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1026.6	1026.9	1027.4	1022.7	1022.1	1022.1	1017.8	1014.2	1010.0	1004.2	1004.8
5°	1096.0	1100.1	1101.7	1097.1	1090.4	1089.5	1083.2	1072.6	1062.8	1054.9	1049.2
7.5°	1178.8	1180.4	1176.8	1170.8	1165.8	1156.7	1144.8	1133.1	1116.7	1101.7	1090.6
10°	1241.5	1243.9	1237.4	1228.7	1221.5	1211.0	1193.7	1175.9	1154.5	1133.7	1117.1
12.5°	1289.2	1294.8	1286.6	1285.5	1273.1	1258.7	1238.0	1229.0	1198.8	1169.9	1152.1
15°	1347.2	1346.8	1347.6	1340.4	1331.3	1329.1	1307.2	1283.4	1240.8	1223.9	1194.4
17.5°	1330.4	1336.2	1338.8	1338.7	1338.5	1337.1	1330.0	1315.0	1293.6	1266.2	1232.2
20°	1290.6	1298.1	1299.3	1308.0	1312.8	1319.3	1321.9	1317.8	1304.5	1281.5	1252.1
22.5°	1229.0	1231.1	1234.7	1248.2	1258.8	1274.9	1283.2	1297.2	1292.1	1280.9	1256.4
25°	1122.4	1118.6	1131.8	1138.6	1163.1	1188.7	1207.2	1227.6	1245.7	1256.7	1249.5
27.5°	994.3	988.7	1008.5	1026.4	1046.3	1074.1	1102.9	1136.9	1165.2	1200.6	1212.7
30°	886.3	889.7	908.6	927.8	958.0	997.1	1029.6	1066.9	1107.3	1146.9	1174.4
32.5°	769.8	782.8	794.8	824.3	850.8	894.5	942.1	988.8	1039.2	1084.1	1126.7
35°	611.0	626.0	642.7	664.2	701.5	744.9	791.2	854.2	922.9	984.3	1034.9
37.5°	514.2	511.9	521.4	536.9	567.1	602.2	655.5	717.8	798.6	870.8	942.1
40°	456.4	454.8	461.6	475.9	499.0	524.6	571.4	626.0	701.1	789.3	874.2
42.5°	416.5	417.4	421.2	431.3	447.1	468.2	503.2	549.8	618.4	701.6	792.7
45°	368.1	370.7	374.9	379.8	388.8	406.2	425.8	459.0	513.3	582.7	672.5
47.5°	333.3	333.4	337.5	341.8	347.2	357.0	373.0	393.8	432.1	488.7	565.8
50°	314.6	311.8	314.9	318.3	324.0	330.7	341.3	360.9	386.6	432.2	496.7
52.5°	291.6	291.6	294.4	295.7	300.7	307.5	317.2	330.7	354.0	389.7	442.7
55°	258.7	260.6	262.2	264.4	268.9	273.8	281.3	290.4	308.5	335.3	374.5
57.5°	227.8	228.4	229.9	234.2	237.1	241.6	248.7	257.0	268.7	288.6	318.1
60°	206.7	206.7	209.6	211.6	215.3	219.8	225.5	233.5	244.0	260.2	284.0
62.5°	187.3	187.0	188.2	191.4	194.2	198.4	204.1	210.9	220.8	235.2	254.7
65°	159.2	158.4	160.7	161.4	164.4	168.5	173.1	180.3	188.2	198.7	216.1
67.5°	132.0	132.9	134.1	135.5	137.2	141.6	144.6	149.7	156.3	165.1	176.9
70°	116.9	116.9	116.9	118.1	120.3	122.6	125.6	129.8	136.1	143.7	154.2
72.5°	100.0	101.2	102.4	101.8	104.6	105.9	109.6	111.9	118.1	122.9	132.2
75°	78.5	78.5	78.5	80.3	81.5	82.6	84.8	87.2	90.2	96.1	101.1
77.5°	58.6	58.4	58.8	59.2	60.4	61.8	62.4	64.5	67.3	70.1	74.2
80°	45.2	46.0	46.4	47.2	47.2	47.9	48.3	50.9	52.8	54.7	57.4
82.5°	35.0	35.1	35.2	35.3	35.6	36.2	37.1	38.0	38.6	40.2	42.2
85°	20.4	20.0	20.0	20.7	20.4	20.4	21.1	21.9	21.9	22.2	23.4
87.5°	10.2	10.2	10.5	10.2	10.2	10.4	10.3	10.1	10.5	10.9	11.1
90°	11.8	11.8	11.8	11.8	11.8	11.4	10.7	11.4	11.8	12.1	11.8
92.5°	19.8	20.3	20.1	21.2	21.5	23.7	26.7	31.1	39.2	46.4	45.7
95°	40.7	40.3	41.4	44.2	48.9	56.8	71.7	93.5	122.4	139.9	123.8
97.5°	80.1	83.1	88.3	97.0	114.1	139.9	178.4	218.1	250.4	238.7	179.9
100°	127.7	134.2	144.5	159.9	189.5	232.7	281.6	325.8	333.3	281.9	194.1
102.5°	224.8	233.5	246.4	272.6	304.8	350.5	386.3	396.3	364.1	283.3	188.6
105°	402.1	407.1	422.4	444.5	466.8	478.5	473.8	433.5	359.3	264.4	178.0
107.5°	513.7	520.3	523.4	524.6	521.8	504.5	467.5	406.7	328.0	244.1	172.8
110°	547.3	547.8	544.5	537.8	522.4	493.1	447.5	383.5	308.3	234.4	171.7



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	546.7	544.8	538.8	527.5	506.1	472.5	423.7	362.4	294.6	228.1	171.9
115°	529.2	525.9	516.6	500.3	474.9	438.2	391.4	336.5	277.6	221.3	173.4
117.5°	497.7	494.9	485.2	467.9	442.0	407.6	365.2	316.9	266.9	217.8	176.0
120°	477.5	473.8	463.5	446.8	421.7	389.3	351.4	307.2	261.2	215.9	177.7
122.5°	456.3	453.3	444.1	427.6	405.2	375.9	340.0	299.5	256.3	214.7	179.7
125°	429.3	426.4	417.5	403.9	383.2	356.5	325.1	288.3	249.4	212.7	182.7
127.5°	405.6	403.2	395.6	382.8	364.8	340.1	310.5	277.2	243.0	211.5	185.7
130°	392.1	389.3	382.1	370.0	352.5	329.0	300.8	270.1	238.7	210.9	188.0
132.5°	378.2	375.6	369.0	356.9	339.7	317.6	291.6	263.3	235.3	210.6	190.4
135°	355.8	354.4	347.9	336.1	320.7	300.8	277.2	253.7	230.5	210.2	193.1
137.5°	333.8	331.6	326.0	315.9	301.8	284.5	265.8	246.1	227.1	210.1	195.5
140°	318.6	316.5	311.1	301.8	290.4	274.8	258.3	241.2	225.1	209.8	196.6
142.5°	303.5	303.1	298.3	289.8	279.0	265.9	251.8	237.2	223.2	209.8	197.4
145°	284.0	283.0	279.4	273.3	264.8	254.4	243.4	231.6	220.6	209.0	198.3
147.5°	267.7	267.0	264.6	259.7	252.7	245.1	236.5	227.2	217.8	207.8	198.6
150°	258.0	257.6	255.5	251.2	245.8	239.4	232.0	224.1	215.5	206.9	198.3
152.5°	249.7	249.6	248.0	244.4	240.1	234.6	228.2	221.0	213.5	205.5	197.8
155°	238.7	239.4	238.0	235.5	231.6	227.6	222.3	216.6	209.8	203.0	196.9
157.5°	229.3	229.3	228.7	226.6	223.9	220.8	216.3	211.6	206.3	200.5	195.3
160°	223.4	223.4	223.0	221.3	218.7	216.2	212.3	208.3	203.7	198.7	194.5
162.5°	217.6	217.9	217.6	216.4	213.9	212.0	208.6	205.2	201.5	197.3	193.6
165°	209.4	209.8	209.8	208.3	206.9	205.5	203.0	200.6	197.6	194.5	192.0
167.5°	201.9	202.3	202.4	201.6	201.0	199.7	197.9	196.0	194.0	192.0	190.4
170°	197.3	198.0	198.3	197.3	196.9	196.2	194.8	193.8	192.0	190.6	189.5
172.5°	193.6	194.0	194.4	193.9	193.5	193.1	192.0	191.2	190.0	188.8	188.3
175°	188.7	189.5	189.9	189.5	189.5	189.1	188.7	188.4	187.3	186.9	186.6
177.5°	185.8	186.4	186.7	186.7	186.7	186.7	186.4	186.4	185.8	185.5	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1006.9	1004.5	1003.0	997.6	992.8	988.0	986.4	987.0	980.4	974.1	971.4
5°	1046.2	1038.6	1031.5	1021.3	1009.3	996.0	989.3	984.0	970.8	956.4	948.2
7.5°	1081.4	1070.6	1056.7	1037.6	1020.1	999.3	986.0	974.4	955.0	934.8	922.5
10°	1102.8	1088.0	1070.4	1046.9	1025.4	1000.2	982.5	964.7	942.1	918.0	902.9
12.5°	1121.2	1101.4	1083.9	1053.9	1028.4	996.8	975.8	950.9	927.1	898.4	883.5
15°	1165.0	1128.4	1095.2	1061.3	1030.0	985.8	962.5	928.9	897.6	862.1	845.2
17.5°	1198.8	1157.7	1105.5	1062.4	1025.8	976.9	942.6	902.4	865.4	824.9	801.8
20°	1218.2	1171.0	1114.8	1063.6	1019.8	964.0	926.7	885.6	842.1	796.5	771.6
22.5°	1229.6	1180.1	1124.5	1059.0	1007.7	953.4	906.5	861.4	817.4	768.2	742.0
25°	1233.2	1188.0	1129.1	1055.2	992.6	931.2	874.5	830.8	777.7	731.6	693.6
27.5°	1215.3	1182.9	1126.3	1048.1	975.2	903.3	840.3	790.7	734.6	684.7	646.3
30°	1193.3	1174.4	1119.3	1040.9	961.3	884.0	814.7	758.4	702.7	652.1	612.9
32.5°	1159.2	1155.1	1106.7	1030.7	946.5	859.6	787.8	730.9	669.1	619.5	582.1
35°	1092.2	1110.3	1079.7	1007.7	918.7	824.9	747.1	682.3	618.1	570.6	535.5
37.5°	1002.5	1047.4	1039.5	974.1	881.1	787.0	701.1	633.4	572.3	524.3	489.9
40°	940.6	997.9	1006.2	948.5	854.6	757.7	666.8	599.3	539.7	495.9	461.2
42.5°	874.2	941.2	964.0	917.8	825.7	726.9	636.0	566.1	507.2	464.5	433.8
45°	763.0	851.6	892.7	866.3	777.3	676.2	582.7	511.8	458.3	418.3	394.5
47.5°	658.9	755.8	811.1	801.7	723.5	623.4	531.0	462.9	410.8	378.9	357.6
50°	585.3	684.9	751.6	754.7	684.9	585.7	492.9	428.8	380.9	351.1	333.8
52.5°	521.4	616.4	689.2	705.2	641.8	546.4	458.8	395.1	352.8	325.5	309.9
55°	437.9	518.2	599.0	628.3	577.4	486.9	405.8	349.6	310.0	291.1	277.6
57.5°	364.1	431.0	505.5	538.1	506.6	429.2	353.1	304.4	272.3	255.7	245.3
60°	325.1	377.9	444.2	483.1	456.0	387.0	320.5	274.2	247.8	233.1	223.3
62.5°	288.9	335.7	391.7	427.3	412.5	347.4	288.0	247.0	224.3	210.5	203.4
65°	238.3	275.3	318.7	351.5	341.7	292.3	243.7	208.5	190.5	179.6	173.9
67.5°	196.2	223.0	253.1	281.8	273.9	238.8	199.9	172.5	159.0	149.6	146.2
70°	169.8	190.1	216.8	239.8	233.5	204.8	173.9	150.5	138.8	130.9	127.4
72.5°	144.4	161.1	181.6	200.4	196.0	172.2	146.4	128.8	119.8	112.5	109.7
75°	109.0	121.8	134.3	146.7	145.6	127.1	112.0	98.5	91.3	85.6	84.5
77.5°	80.5	87.7	96.1	103.5	101.5	90.9	79.1	71.3	66.0	62.2	61.6
80°	61.5	65.6	71.7	77.0	74.3	69.8	60.4	54.7	50.9	47.2	45.6
82.5°	44.5	48.8	52.3	55.2	53.2	49.0	43.1	39.3	37.1	34.4	33.8
85°	23.4	25.7	27.2	27.9	27.2	24.5	21.9	20.4	18.5	17.4	17.0
87.5°	11.0	10.5	10.1	10.5	9.5	9.3	7.9	6.7	6.7	6.6	6.2
90°	9.6	7.2	5.4	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	35.6	24.2	16.2	12.8	10.4	8.9	6.3	4.3	6.3	8.9	10.4
95°	82.4	51.4	34.9	26.4	20.7	17.5	13.9	12.5	13.9	17.5	20.7
97.5°	111.1	67.8	47.2	37.5	30.9	26.1	22.2	20.3	22.2	26.1	30.9
100°	117.0	73.5	54.6	44.6	37.5	31.7	28.6	27.5	28.6	31.7	37.5
102.5°	117.3	78.7	61.2	51.2	43.7	38.1	34.8	34.0	34.8	38.1	43.7
105°	119.2	87.5	70.7	60.7	52.8	47.5	44.9	43.5	44.9	47.5	52.8
107.5°	124.1	96.4	80.2	70.1	62.3	57.4	54.9	53.8	54.9	57.4	62.3
110°	128.1	102.4	86.7	76.3	68.9	64.2	62.1	60.7	62.1	64.2	68.9



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	132.4	108.2	93.0	82.3	75.1	70.8	68.4	67.0	68.4	70.8	75.1
115°	138.8	117.0	101.7	92.1	84.9	80.7	78.5	76.7	78.5	80.7	84.9
117.5°	145.6	125.2	111.1	101.1	94.2	90.4	88.3	86.8	88.3	90.4	94.2
120°	150.3	131.0	117.0	107.0	99.9	96.7	94.5	93.1	94.5	96.7	99.9
122.5°	154.2	136.3	123.3	113.0	105.9	102.4	100.3	99.2	100.3	102.4	105.9
125°	160.6	144.5	131.7	121.7	114.5	110.3	108.2	107.0	108.2	110.3	114.5
127.5°	166.5	152.1	139.6	129.3	122.5	117.8	114.7	113.3	114.7	117.8	122.5
130°	170.2	156.6	144.1	134.2	127.0	122.0	118.5	117.0	118.5	122.0	127.0
132.5°	173.9	160.7	148.8	138.8	131.3	126.0	122.2	120.5	122.2	126.0	131.3
135°	178.7	166.3	154.8	144.9	136.6	131.3	127.0	125.6	127.0	131.3	136.6
137.5°	182.5	170.9	159.6	150.3	142.2	136.4	132.2	130.5	132.2	136.4	142.2
140°	184.5	173.4	162.7	153.4	145.6	139.9	135.6	134.2	135.6	139.9	145.6
142.5°	186.2	175.4	165.0	156.3	148.8	143.0	139.1	137.8	139.1	143.0	148.8
145°	188.4	178.4	168.7	161.0	153.8	148.5	144.9	143.4	144.9	148.5	153.8
147.5°	189.7	180.9	171.8	164.8	158.9	153.9	150.5	149.5	150.5	153.9	158.9
150°	190.2	182.0	173.8	167.3	162.0	157.3	154.5	153.4	154.5	157.3	162.0
152.5°	190.5	183.1	175.7	170.0	164.8	160.8	157.9	157.4	157.9	160.8	164.8
155°	190.9	184.8	178.7	173.4	169.5	165.5	163.4	163.1	163.4	165.5	169.5
157.5°	190.9	186.0	180.9	176.4	173.3	169.9	168.1	167.7	168.1	169.9	173.3
160°	190.9	186.6	182.4	178.4	175.5	172.7	171.3	170.9	171.3	172.7	175.5
162.5°	190.6	186.9	183.2	180.2	177.5	175.3	173.8	174.1	173.8	175.3	177.5
165°	189.9	187.3	184.1	182.0	180.2	178.0	177.3	177.7	177.3	178.0	180.2
167.5°	189.3	187.2	184.9	183.6	182.3	180.9	180.3	180.7	180.3	180.9	182.3
170°	188.7	186.9	185.2	184.1	183.4	182.4	182.0	182.7	182.0	182.4	183.4
172.5°	187.9	186.7	185.5	184.7	184.3	183.2	183.4	183.8	183.4	183.2	184.3
175°	186.9	186.2	185.5	185.2	185.2	184.5	184.8	185.2	184.8	184.5	185.2
177.5°	186.4	185.8	185.5	185.5	185.5	185.0	185.2	185.8	185.2	185.0	185.5
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	968.4	966.5	960.2	956.8	951.5	946.3	943.0	944.5	945.7	945.1	944.2
5°	940.6	933.4	922.5	913.0	906.3	893.8	888.6	886.0	883.6	881.0	878.4
7.5°	907.6	896.3	880.6	867.2	854.4	839.0	830.2	824.9	819.4	813.4	808.2
10°	884.0	868.2	851.6	832.7	817.7	803.7	791.2	782.9	775.4	768.2	763.0
12.5°	859.3	841.0	820.5	794.8	778.1	758.1	756.3	741.6	729.8	725.4	719.2
15°	819.9	794.3	768.2	737.7	724.5	706.4	695.1	683.8	673.6	666.4	664.5
17.5°	775.2	741.9	716.1	694.2	672.6	654.0	643.6	634.5	626.1	616.5	615.3
20°	741.0	712.5	684.2	664.9	642.7	623.8	611.0	601.9	594.7	589.1	584.2
22.5°	708.8	677.4	651.6	630.5	608.5	593.3	583.2	574.5	568.6	562.3	557.6
25°	657.0	632.5	604.2	580.5	562.3	552.5	544.2	536.6	532.9	528.8	523.5
27.5°	611.7	584.4	558.0	539.6	523.6	514.9	509.1	503.9	500.4	498.0	494.9
30°	579.7	552.1	531.4	513.3	500.1	491.4	487.7	484.6	480.5	479.0	477.5
32.5°	548.9	524.1	506.3	490.7	478.1	472.4	469.0	466.3	463.0	461.5	458.5
35°	505.3	484.6	467.3	458.6	448.4	443.5	440.9	437.1	434.1	432.6	432.2
37.5°	464.4	446.4	434.9	423.8	419.5	416.5	412.9	410.3	409.4	409.2	408.8
40°	437.9	423.1	412.9	403.9	402.0	397.5	394.5	392.2	392.2	392.6	392.2
42.5°	413.7	400.5	391.5	383.7	381.5	378.8	375.8	375.7	376.3	377.5	376.3
45°	377.2	367.7	361.3	357.5	353.4	350.7	350.3	351.5	351.8	352.2	353.4
47.5°	343.5	337.2	331.4	327.3	325.5	325.0	324.6	326.5	328.3	329.0	330.7
50°	323.6	316.4	311.5	308.9	307.4	306.6	307.4	309.6	311.1	313.1	314.2
52.5°	301.2	296.2	292.9	290.7	290.1	290.6	290.7	293.4	295.8	296.4	297.0
55°	270.4	266.6	265.9	262.5	264.0	263.6	265.5	267.0	269.2	271.6	272.0
57.5°	239.6	236.6	234.6	234.9	235.3	237.0	238.5	241.3	243.7	246.0	246.3
60°	219.1	217.6	216.5	216.5	217.2	219.5	221.4	224.0	225.5	227.0	228.1
62.5°	200.5	198.9	197.7	198.3	200.4	201.7	203.9	205.3	206.8	208.3	208.8
65°	170.9	170.1	171.3	172.0	172.4	174.2	176.9	178.0	179.6	180.3	182.9
67.5°	143.6	143.8	143.6	144.7	146.8	147.3	149.8	152.5	152.8	154.2	155.9
70°	125.2	125.9	126.7	127.4	129.4	130.1	132.0	133.1	134.6	135.7	136.9
72.5°	108.4	108.5	109.3	109.1	110.7	112.3	113.9	115.0	116.5	118.0	119.1
75°	83.3	83.3	84.1	84.5	86.3	88.3	87.9	88.7	90.2	91.7	92.4
77.5°	60.9	60.1	60.9	61.2	61.8	63.4	63.7	64.8	66.6	66.0	66.9
80°	46.4	45.2	46.4	46.8	46.8	48.7	48.7	49.4	50.5	49.4	50.5
82.5°	33.1	32.6	33.4	33.5	34.1	34.1	34.7	34.9	36.1	35.5	36.1
85°	16.6	16.3	16.6	16.3	16.6	17.0	17.0	16.6	16.6	17.4	16.3
87.5°	6.0	5.9	6.0	6.5	6.6	6.4	6.0	5.9	5.8	5.3	5.4
90°	4.2	5.4	7.2	9.6	11.8	12.1	11.8	11.4	10.7	11.4	11.8
92.5°	12.8	16.2	24.2	35.6	45.7	46.4	39.2	31.1	26.7	23.7	21.5
95°	26.4	34.9	51.4	82.4	123.8	139.9	122.4	93.5	71.7	56.8	48.9
97.5°	37.5	47.2	67.8	111.1	179.9	238.7	250.4	218.1	178.4	139.9	114.1
100°	44.6	54.6	73.5	117.0	194.1	281.9	333.3	325.8	281.6	232.7	189.5
102.5°	51.2	61.2	78.7	117.3	188.6	283.3	364.1	396.3	386.3	350.5	304.8
105°	60.7	70.7	87.5	119.2	178.0	264.4	359.3	433.5	473.8	478.5	466.8
107.5°	70.1	80.2	96.4	124.1	172.8	244.1	328.0	406.7	467.5	504.5	521.8
110°	76.3	86.7	102.4	128.1	171.7	234.4	308.3	383.5	447.5	493.1	522.4



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	82.3	93.0	108.2	132.4	171.9	228.1	294.6	362.4	423.7	472.5	506.1
115°	92.1	101.7	117.0	138.8	173.4	221.3	277.6	336.5	391.4	438.2	474.9
117.5°	101.1	111.1	125.2	145.6	176.0	217.8	266.9	316.9	365.2	407.6	442.0
120°	107.0	117.0	131.0	150.3	177.7	215.9	261.2	307.2	351.4	389.3	421.7
122.5°	113.0	123.3	136.3	154.2	179.7	214.7	256.3	299.5	340.0	375.9	405.2
125°	121.7	131.7	144.5	160.6	182.7	212.7	249.4	288.3	325.1	356.5	383.2
127.5°	129.3	139.6	152.1	166.5	185.7	211.5	243.0	277.2	310.5	340.1	364.8
130°	134.2	144.1	156.6	170.2	188.0	210.9	238.7	270.1	300.8	329.0	352.5
132.5°	138.8	148.8	160.7	173.9	190.4	210.6	235.3	263.3	291.6	317.6	339.7
135°	144.9	154.8	166.3	178.7	193.1	210.2	230.5	253.7	277.2	300.8	320.7
137.5°	150.3	159.6	170.9	182.5	195.5	210.1	227.1	246.1	265.8	284.5	301.8
140°	153.4	162.7	173.4	184.5	196.6	209.8	225.1	241.2	258.3	274.8	290.4
142.5°	156.3	165.0	175.4	186.2	197.4	209.8	223.2	237.2	251.8	265.9	279.0
145°	161.0	168.7	178.4	188.4	198.3	209.0	220.6	231.6	243.4	254.4	264.8
147.5°	164.8	171.8	180.9	189.7	198.6	207.8	217.8	227.2	236.5	245.1	252.7
150°	167.3	173.8	182.0	190.2	198.3	206.9	215.5	224.1	232.0	239.4	245.8
152.5°	170.0	175.7	183.1	190.5	197.8	205.5	213.5	221.0	228.2	234.6	240.1
155°	173.4	178.7	184.8	190.9	196.9	203.0	209.8	216.6	222.3	227.6	231.6
157.5°	176.4	180.9	186.0	190.9	195.3	200.5	206.3	211.6	216.3	220.8	223.9
160°	178.4	182.4	186.6	190.9	194.5	198.7	203.7	208.3	212.3	216.2	218.7
162.5°	180.2	183.2	186.9	190.6	193.6	197.3	201.5	205.2	208.6	212.0	213.9
165°	182.0	184.1	187.3	189.9	192.0	194.5	197.6	200.6	203.0	205.5	206.9
167.5°	183.6	184.9	187.2	189.3	190.4	192.0	194.0	196.0	197.9	199.7	201.0
170°	184.1	185.2	186.9	188.7	189.5	190.6	192.0	193.8	194.8	196.2	196.9
172.5°	184.7	185.5	186.7	187.9	188.3	188.8	190.0	191.2	192.0	193.1	193.5
175°	185.2	185.5	186.2	186.9	186.6	186.9	187.3	188.4	188.7	189.1	189.5
177.5°	185.5	185.5	185.8	186.4	185.8	185.5	185.8	186.4	186.4	186.7	186.7
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	941.2	940.6	940.6	937.9	940.6	940.6	941.2	944.2	945.1	945.7	944.5
5°	873.1	871.9	870.1	871.9	870.1	871.9	873.1	878.4	881.0	883.6	886.0
7.5°	805.8	801.2	800.5	796.1	800.5	801.2	805.8	808.2	813.4	819.4	824.9
10°	756.6	753.6	753.2	746.0	753.2	753.6	756.6	763.0	768.2	775.4	782.9
12.5°	719.1	711.9	713.4	709.2	713.4	711.9	719.1	719.2	725.4	729.8	741.6
15°	654.3	654.3	652.9	646.4	652.9	654.3	654.3	664.5	666.4	673.6	683.8
17.5°	607.8	607.0	603.4	605.2	603.4	607.0	607.8	615.3	616.5	626.1	634.5
20°	580.1	577.7	573.3	573.3	573.3	577.7	580.1	584.2	589.1	594.7	601.9
22.5°	553.8	553.6	548.9	550.4	548.9	553.6	553.8	557.6	562.3	568.6	574.5
25°	523.1	520.1	517.9	519.0	517.9	520.1	523.1	523.5	528.8	532.9	536.6
27.5°	494.0	492.3	492.2	489.1	492.2	492.3	494.0	494.9	498.0	500.4	503.9
30°	477.1	473.3	474.0	472.2	474.0	473.3	477.1	477.5	479.0	480.5	484.6
32.5°	457.8	456.5	455.7	454.0	455.7	456.5	457.8	458.5	461.5	463.0	466.3
35°	431.4	431.8	429.9	430.7	429.9	431.8	431.4	432.2	432.6	434.1	437.1
37.5°	408.5	409.7	408.8	409.0	408.8	409.7	408.5	408.8	409.2	409.4	410.3
40°	393.3	393.3	393.3	394.5	393.3	393.3	393.3	392.2	392.6	392.2	392.2
42.5°	378.9	378.3	377.7	377.6	377.7	378.3	378.9	376.3	377.5	376.3	375.7
45°	354.2	355.3	355.7	353.8	355.7	355.3	354.2	353.4	352.2	351.8	351.5
47.5°	331.7	331.8	331.7	333.4	331.7	331.8	331.7	330.7	329.0	328.3	326.5
50°	316.1	315.3	316.1	315.3	316.1	315.3	316.1	314.2	313.1	311.1	309.6
52.5°	299.4	299.6	299.1	299.0	299.1	299.6	299.4	297.0	296.4	295.8	293.4
55°	273.5	274.2	273.8	273.8	273.8	274.2	273.5	272.0	271.6	269.2	267.0
57.5°	246.5	247.2	247.7	246.0	247.7	247.2	246.5	246.3	246.0	243.7	241.3
60°	227.8	229.6	229.3	228.5	229.3	229.6	227.8	228.1	227.0	225.5	224.0
62.5°	210.6	211.3	211.2	211.1	211.2	211.3	210.6	208.8	208.3	206.8	205.3
65°	184.0	184.8	183.7	184.8	183.7	184.8	184.0	182.9	180.3	179.6	178.0
67.5°	155.4	155.7	156.5	157.0	156.5	155.7	155.4	155.9	154.2	152.8	152.5
70°	137.6	137.2	138.5	139.6	138.5	137.2	137.6	136.9	135.7	134.6	133.1
72.5°	119.0	119.8	119.4	120.3	119.4	119.8	119.0	119.1	118.0	116.5	115.0
75°	91.7	92.8	92.4	93.5	92.4	92.8	91.7	92.4	91.7	90.2	88.7
77.5°	66.2	66.3	66.2	66.9	66.2	66.3	66.2	66.9	66.0	66.6	64.8
80°	50.5	49.8	49.0	50.5	49.0	49.8	50.5	50.5	49.4	50.5	49.4
82.5°	35.1	35.6	34.8	34.8	34.8	35.6	35.1	36.1	35.5	36.1	34.9
85°	16.3	15.9	15.0	15.0	15.0	15.9	16.3	16.3	17.4	16.6	16.6
87.5°	5.4	5.0	5.0	4.7	5.0	5.0	5.4	5.4	5.3	5.8	5.9
90°	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.4	10.7	11.4
92.5°	21.2	20.1	20.3	19.8	20.3	20.1	21.2	21.5	23.7	26.7	31.1
95°	44.2	41.4	40.3	40.7	40.3	41.4	44.2	48.9	56.8	71.7	93.5
97.5°	97.0	88.3	83.1	80.1	83.1	88.3	97.0	114.1	139.9	178.4	218.1
100°	159.9	144.5	134.2	127.7	134.2	144.5	159.9	189.5	232.7	281.6	325.8
102.5°	272.6	246.4	233.5	224.8	233.5	246.4	272.6	304.8	350.5	386.3	396.3
105°	444.5	422.4	407.1	402.1	407.1	422.4	444.5	466.8	478.5	473.8	433.5
107.5°	524.6	523.4	520.3	513.7	520.3	523.4	524.6	521.8	504.5	467.5	406.7
110°	537.8	544.5	547.8	547.3	547.8	544.5	537.8	522.4	493.1	447.5	383.5



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	527.5	538.8	544.8	546.7	544.8	538.8	527.5	506.1	472.5	423.7	362.4
115°	500.3	516.6	525.9	529.2	525.9	516.6	500.3	474.9	438.2	391.4	336.5
117.5°	467.9	485.2	494.9	497.7	494.9	485.2	467.9	442.0	407.6	365.2	316.9
120°	446.8	463.5	473.8	477.5	473.8	463.5	446.8	421.7	389.3	351.4	307.2
122.5°	427.6	444.1	453.3	456.3	453.3	444.1	427.6	405.2	375.9	340.0	299.5
125°	403.9	417.5	426.4	429.3	426.4	417.5	403.9	383.2	356.5	325.1	288.3
127.5°	382.8	395.6	403.2	405.6	403.2	395.6	382.8	364.8	340.1	310.5	277.2
130°	370.0	382.1	389.3	392.1	389.3	382.1	370.0	352.5	329.0	300.8	270.1
132.5°	356.9	369.0	375.6	378.2	375.6	369.0	356.9	339.7	317.6	291.6	263.3
135°	336.1	347.9	354.4	355.8	354.4	347.9	336.1	320.7	300.8	277.2	253.7
137.5°	315.9	326.0	331.6	333.8	331.6	326.0	315.9	301.8	284.5	265.8	246.1
140°	301.8	311.1	316.5	318.6	316.5	311.1	301.8	290.4	274.8	258.3	241.2
142.5°	289.8	298.3	303.1	303.5	303.1	298.3	289.8	279.0	265.9	251.8	237.2
145°	273.3	279.4	283.0	284.0	283.0	279.4	273.3	264.8	254.4	243.4	231.6
147.5°	259.7	264.6	267.0	267.7	267.0	264.6	259.7	252.7	245.1	236.5	227.2
150°	251.2	255.5	257.6	258.0	257.6	255.5	251.2	245.8	239.4	232.0	224.1
152.5°	244.4	248.0	249.6	249.7	249.6	248.0	244.4	240.1	234.6	228.2	221.0
155°	235.5	238.0	239.4	238.7	239.4	238.0	235.5	231.6	227.6	222.3	216.6
157.5°	226.6	228.7	229.3	229.3	229.3	228.7	226.6	223.9	220.8	216.3	211.6
160°	221.3	223.0	223.4	223.4	223.4	223.0	221.3	218.7	216.2	212.3	208.3
162.5°	216.4	217.6	217.9	217.6	217.9	217.6	216.4	213.9	212.0	208.6	205.2
165°	208.3	209.8	209.8	209.4	209.8	209.8	208.3	206.9	205.5	203.0	200.6
167.5°	201.6	202.4	202.3	201.9	202.3	202.4	201.6	201.0	199.7	197.9	196.0
170°	197.3	198.3	198.0	197.3	198.0	198.3	197.3	196.9	196.2	194.8	193.8
172.5°	193.9	194.4	194.0	193.6	194.0	194.4	193.9	193.5	193.1	192.0	191.2
175°	189.5	189.9	189.5	188.7	189.5	189.9	189.5	189.5	189.1	188.7	188.4
177.5°	186.7	186.7	186.4	185.8	186.4	186.7	186.7	186.7	186.7	186.4	186.4
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	943.0	946.3	951.5	956.8	960.2	966.5	968.4	971.4	974.1	980.4	987.0
5°	888.6	893.8	906.3	913.0	922.5	933.4	940.6	948.2	956.4	970.8	984.0
7.5°	830.2	839.0	854.4	867.2	880.6	896.3	907.6	922.5	934.8	955.0	974.4
10°	791.2	803.7	817.7	832.7	851.6	868.2	884.0	902.9	918.0	942.1	964.7
12.5°	756.3	758.1	778.1	794.8	820.5	841.0	859.3	883.5	898.4	927.1	950.9
15°	695.1	706.4	724.5	737.7	768.2	794.3	819.9	845.2	862.1	897.6	928.9
17.5°	643.6	654.0	672.6	694.2	716.1	741.9	775.2	801.8	824.9	865.4	902.4
20°	611.0	623.8	642.7	664.9	684.2	712.5	741.0	771.6	796.5	842.1	885.6
22.5°	583.2	593.3	608.5	630.5	651.6	677.4	708.8	742.0	768.2	817.4	861.4
25°	544.2	552.5	562.3	580.5	604.2	632.5	657.0	693.6	731.6	777.7	830.8
27.5°	509.1	514.9	523.6	539.6	558.0	584.4	611.7	646.3	684.7	734.6	790.7
30°	487.7	491.4	500.1	513.3	531.4	552.1	579.7	612.9	652.1	702.7	758.4
32.5°	469.0	472.4	478.1	490.7	506.3	524.1	548.9	582.1	619.5	669.1	730.9
35°	440.9	443.5	448.4	458.6	467.3	484.6	505.3	535.5	570.6	618.1	682.3
37.5°	412.9	416.5	419.5	423.8	434.9	446.4	464.4	489.9	524.3	572.3	633.4
40°	394.5	397.5	402.0	403.9	412.9	423.1	437.9	461.2	495.9	539.7	599.3
42.5°	375.8	378.8	381.5	383.7	391.5	400.5	413.7	433.8	464.5	507.2	566.1
45°	350.3	350.7	353.4	357.5	361.3	367.7	377.2	394.5	418.3	458.3	511.8
47.5°	324.6	325.0	325.5	327.3	331.4	337.2	343.5	357.6	378.9	410.8	462.9
50°	307.4	306.6	307.4	308.9	311.5	316.4	323.6	333.8	351.1	380.9	428.8
52.5°	290.7	290.6	290.1	290.7	292.9	296.2	301.2	309.9	325.5	352.8	395.1
55°	265.5	263.6	264.0	262.5	265.9	266.6	270.4	277.6	291.1	310.0	349.6
57.5°	238.5	237.0	235.3	234.9	234.6	236.6	239.6	245.3	255.7	272.3	304.4
60°	221.4	219.5	217.2	216.5	216.5	217.6	219.1	223.3	233.1	247.8	274.2
62.5°	203.9	201.7	200.4	198.3	197.7	198.9	200.5	203.4	210.5	224.3	247.0
65°	176.9	174.2	172.4	172.0	171.3	170.1	170.9	173.9	179.6	190.5	208.5
67.5°	149.8	147.3	146.8	144.7	143.6	143.8	143.6	146.2	149.6	159.0	172.5
70°	132.0	130.1	129.4	127.4	126.7	125.9	125.2	127.4	130.9	138.8	150.5
72.5°	113.9	112.3	110.7	109.1	109.3	108.5	108.4	109.7	112.5	119.8	128.8
75°	87.9	88.3	86.3	84.5	84.1	83.3	83.3	84.5	85.6	91.3	98.5
77.5°	63.7	63.4	61.8	61.2	60.9	60.1	60.9	61.6	62.2	66.0	71.3
80°	48.7	48.7	46.8	46.8	46.4	45.2	46.4	45.6	47.2	50.9	54.7
82.5°	34.7	34.1	34.1	33.5	33.4	32.6	33.1	33.8	34.4	37.1	39.3
85°	17.0	17.0	16.6	16.3	16.6	16.3	16.6	17.0	17.4	18.5	20.4
87.5°	6.0	6.4	6.6	6.5	6.0	5.9	6.0	6.2	6.6	6.7	6.7
90°	11.8	12.1	11.8	9.6	7.2	5.4	4.2	3.5	2.8	1.4	0.4
92.5°	39.2	46.4	45.7	35.6	24.2	16.2	12.8	10.4	8.9	6.3	4.3
95°	122.4	139.9	123.8	82.4	51.4	34.9	26.4	20.7	17.5	13.9	12.5
97.5°	250.4	238.7	179.9	111.1	67.8	47.2	37.5	30.9	26.1	22.2	20.3
100°	333.3	281.9	194.1	117.0	73.5	54.6	44.6	37.5	31.7	28.6	27.5
102.5°	364.1	283.3	188.6	117.3	78.7	61.2	51.2	43.7	38.1	34.8	34.0
105°	359.3	264.4	178.0	119.2	87.5	70.7	60.7	52.8	47.5	44.9	43.5
107.5°	328.0	244.1	172.8	124.1	96.4	80.2	70.1	62.3	57.4	54.9	53.8
110°	308.3	234.4	171.7	128.1	102.4	86.7	76.3	68.9	64.2	62.1	60.7



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	294.6	228.1	171.9	132.4	108.2	93.0	82.3	75.1	70.8	68.4	67.0
115°	277.6	221.3	173.4	138.8	117.0	101.7	92.1	84.9	80.7	78.5	76.7
117.5°	266.9	217.8	176.0	145.6	125.2	111.1	101.1	94.2	90.4	88.3	86.8
120°	261.2	215.9	177.7	150.3	131.0	117.0	107.0	99.9	96.7	94.5	93.1
122.5°	256.3	214.7	179.7	154.2	136.3	123.3	113.0	105.9	102.4	100.3	99.2
125°	249.4	212.7	182.7	160.6	144.5	131.7	121.7	114.5	110.3	108.2	107.0
127.5°	243.0	211.5	185.7	166.5	152.1	139.6	129.3	122.5	117.8	114.7	113.3
130°	238.7	210.9	188.0	170.2	156.6	144.1	134.2	127.0	122.0	118.5	117.0
132.5°	235.3	210.6	190.4	173.9	160.7	148.8	138.8	131.3	126.0	122.2	120.5
135°	230.5	210.2	193.1	178.7	166.3	154.8	144.9	136.6	131.3	127.0	125.6
137.5°	227.1	210.1	195.5	182.5	170.9	159.6	150.3	142.2	136.4	132.2	130.5
140°	225.1	209.8	196.6	184.5	173.4	162.7	153.4	145.6	139.9	135.6	134.2
142.5°	223.2	209.8	197.4	186.2	175.4	165.0	156.3	148.8	143.0	139.1	137.8
145°	220.6	209.0	198.3	188.4	178.4	168.7	161.0	153.8	148.5	144.9	143.4
147.5°	217.8	207.8	198.6	189.7	180.9	171.8	164.8	158.9	153.9	150.5	149.5
150°	215.5	206.9	198.3	190.2	182.0	173.8	167.3	162.0	157.3	154.5	153.4
152.5°	213.5	205.5	197.8	190.5	183.1	175.7	170.0	164.8	160.8	157.9	157.4
155°	209.8	203.0	196.9	190.9	184.8	178.7	173.4	169.5	165.5	163.4	163.1
157.5°	206.3	200.5	195.3	190.9	186.0	180.9	176.4	173.3	169.9	168.1	167.7
160°	203.7	198.7	194.5	190.9	186.6	182.4	178.4	175.5	172.7	171.3	170.9
162.5°	201.5	197.3	193.6	190.6	186.9	183.2	180.2	177.5	175.3	173.8	174.1
165°	197.6	194.5	192.0	189.9	187.3	184.1	182.0	180.2	178.0	177.3	177.7
167.5°	194.0	192.0	190.4	189.3	187.2	184.9	183.6	182.3	180.9	180.3	180.7
170°	192.0	190.6	189.5	188.7	186.9	185.2	184.1	183.4	182.4	182.0	182.7
172.5°	190.0	188.8	188.3	187.9	186.7	185.5	184.7	184.3	183.2	183.4	183.8
175°	187.3	186.9	186.6	186.9	186.2	185.5	185.2	185.2	184.5	184.8	185.2
177.5°	185.8	185.5	185.8	186.4	185.8	185.5	185.5	185.5	185.0	185.2	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	986.4	988.0	992.8	997.6	1003.0	1004.5	1006.9	1004.8	1004.2	1010.0	1014.2
5°	989.3	996.0	1009.3	1021.3	1031.5	1038.6	1046.2	1049.2	1054.9	1062.8	1072.6
7.5°	986.0	999.3	1020.1	1037.6	1056.7	1070.6	1081.4	1090.6	1101.7	1116.7	1133.1
10°	982.5	1000.2	1025.4	1046.9	1070.4	1088.0	1102.8	1117.1	1133.7	1154.5	1175.9
12.5°	975.8	996.8	1028.4	1053.9	1083.9	1101.4	1121.2	1152.1	1169.9	1198.8	1229.0
15°	962.5	985.8	1030.0	1061.3	1095.2	1128.4	1165.0	1194.4	1223.9	1240.8	1283.4
17.5°	942.6	976.9	1025.8	1062.4	1105.5	1157.7	1198.8	1232.2	1266.2	1293.6	1315.0
20°	926.7	964.0	1019.8	1063.6	1114.8	1171.0	1218.2	1252.1	1281.5	1304.5	1317.8
22.5°	906.5	953.4	1007.7	1059.0	1124.5	1180.1	1229.6	1256.4	1280.9	1292.1	1297.2
25°	874.5	931.2	992.6	1055.2	1129.1	1188.0	1233.2	1249.5	1256.7	1245.7	1227.6
27.5°	840.3	903.3	975.2	1048.1	1126.3	1182.9	1215.3	1212.7	1200.6	1165.2	1136.9
30°	814.7	884.0	961.3	1040.9	1119.3	1174.4	1193.3	1174.4	1146.9	1107.3	1066.9
32.5°	787.8	859.6	946.5	1030.7	1106.7	1155.1	1159.2	1126.7	1084.1	1039.2	988.8
35°	747.1	824.9	918.7	1007.7	1079.7	1110.3	1092.2	1034.9	984.3	922.9	854.2
37.5°	701.1	787.0	881.1	974.1	1039.5	1047.4	1002.5	942.1	870.8	798.6	717.8
40°	666.8	757.7	854.6	948.5	1006.2	997.9	940.6	874.2	789.3	701.1	626.0
42.5°	636.0	726.9	825.7	917.8	964.0	941.2	874.2	792.7	701.6	618.4	549.8
45°	582.7	676.2	777.3	866.3	892.7	851.6	763.0	672.5	582.7	513.3	459.0
47.5°	531.0	623.4	723.5	801.7	811.1	755.8	658.9	565.8	488.7	432.1	393.8
50°	492.9	585.7	684.9	754.7	751.6	684.9	585.3	496.7	432.2	386.6	360.9
52.5°	458.8	546.4	641.8	705.2	689.2	616.4	521.4	442.7	389.7	354.0	330.7
55°	405.8	486.9	577.4	628.3	599.0	518.2	437.9	374.5	335.3	308.5	290.4
57.5°	353.1	429.2	506.6	538.1	505.5	431.0	364.1	318.1	288.6	268.7	257.0
60°	320.5	387.0	456.0	483.1	444.2	377.9	325.1	284.0	260.2	244.0	233.5
62.5°	288.0	347.4	412.5	427.3	391.7	335.7	288.9	254.7	235.2	220.8	210.9
65°	243.7	292.3	341.7	351.5	318.7	275.3	238.3	216.1	198.7	188.2	180.3
67.5°	199.9	238.8	273.9	281.8	253.1	223.0	196.2	176.9	165.1	156.3	149.7
70°	173.9	204.8	233.5	239.8	216.8	190.1	169.8	154.2	143.7	136.1	129.8
72.5°	146.4	172.2	196.0	200.4	181.6	161.1	144.4	132.2	122.9	118.1	111.9
75°	112.0	127.1	145.6	146.7	134.3	121.8	109.0	101.1	96.1	90.2	87.2
77.5°	79.1	90.9	101.5	103.5	96.1	87.7	80.5	74.2	70.1	67.3	64.5
80°	60.4	69.8	74.3	77.0	71.7	65.6	61.5	57.4	54.7	52.8	50.9
82.5°	43.1	49.0	53.2	55.2	52.3	48.8	44.5	42.2	40.2	38.6	38.0
85°	21.9	24.5	27.2	27.9	27.2	25.7	23.4	23.4	22.2	21.9	21.9
87.5°	7.9	9.3	9.5	10.5	10.1	10.5	11.0	11.1	10.9	10.5	10.1
90°	1.4	2.8	3.5	4.2	5.4	7.2	9.6	11.8	12.1	11.8	11.4
92.5°	6.3	8.9	10.4	12.8	16.2	24.2	35.6	45.7	46.4	39.2	31.1
95°	13.9	17.5	20.7	26.4	34.9	51.4	82.4	123.8	139.9	122.4	93.5
97.5°	22.2	26.1	30.9	37.5	47.2	67.8	111.1	179.9	238.7	250.4	218.1
100°	28.6	31.7	37.5	44.6	54.6	73.5	117.0	194.1	281.9	333.3	325.8
102.5°	34.8	38.1	43.7	51.2	61.2	78.7	117.3	188.6	283.3	364.1	396.3
105°	44.9	47.5	52.8	60.7	70.7	87.5	119.2	178.0	264.4	359.3	433.5
107.5°	54.9	57.4	62.3	70.1	80.2	96.4	124.1	172.8	244.1	328.0	406.7
110°	62.1	64.2	68.9	76.3	86.7	102.4	128.1	171.7	234.4	308.3	383.5



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	68.4	70.8	75.1	82.3	93.0	108.2	132.4	171.9	228.1	294.6	362.4
115°	78.5	80.7	84.9	92.1	101.7	117.0	138.8	173.4	221.3	277.6	336.5
117.5°	88.3	90.4	94.2	101.1	111.1	125.2	145.6	176.0	217.8	266.9	316.9
120°	94.5	96.7	99.9	107.0	117.0	131.0	150.3	177.7	215.9	261.2	307.2
122.5°	100.3	102.4	105.9	113.0	123.3	136.3	154.2	179.7	214.7	256.3	299.5
125°	108.2	110.3	114.5	121.7	131.7	144.5	160.6	182.7	212.7	249.4	288.3
127.5°	114.7	117.8	122.5	129.3	139.6	152.1	166.5	185.7	211.5	243.0	277.2
130°	118.5	122.0	127.0	134.2	144.1	156.6	170.2	188.0	210.9	238.7	270.1
132.5°	122.2	126.0	131.3	138.8	148.8	160.7	173.9	190.4	210.6	235.3	263.3
135°	127.0	131.3	136.6	144.9	154.8	166.3	178.7	193.1	210.2	230.5	253.7
137.5°	132.2	136.4	142.2	150.3	159.6	170.9	182.5	195.5	210.1	227.1	246.1
140°	135.6	139.9	145.6	153.4	162.7	173.4	184.5	196.6	209.8	225.1	241.2
142.5°	139.1	143.0	148.8	156.3	165.0	175.4	186.2	197.4	209.8	223.2	237.2
145°	144.9	148.5	153.8	161.0	168.7	178.4	188.4	198.3	209.0	220.6	231.6
147.5°	150.5	153.9	158.9	164.8	171.8	180.9	189.7	198.6	207.8	217.8	227.2
150°	154.5	157.3	162.0	167.3	173.8	182.0	190.2	198.3	206.9	215.5	224.1
152.5°	157.9	160.8	164.8	170.0	175.7	183.1	190.5	197.8	205.5	213.5	221.0
155°	163.4	165.5	169.5	173.4	178.7	184.8	190.9	196.9	203.0	209.8	216.6
157.5°	168.1	169.9	173.3	176.4	180.9	186.0	190.9	195.3	200.5	206.3	211.6
160°	171.3	172.7	175.5	178.4	182.4	186.6	190.9	194.5	198.7	203.7	208.3
162.5°	173.8	175.3	177.5	180.2	183.2	186.9	190.6	193.6	197.3	201.5	205.2
165°	177.3	178.0	180.2	182.0	184.1	187.3	189.9	192.0	194.5	197.6	200.6
167.5°	180.3	180.9	182.3	183.6	184.9	187.2	189.3	190.4	192.0	194.0	196.0
170°	182.0	182.4	183.4	184.1	185.2	186.9	188.7	189.5	190.6	192.0	193.8
172.5°	183.4	183.2	184.3	184.7	185.5	186.7	187.9	188.3	188.8	190.0	191.2
175°	184.8	184.5	185.2	185.2	185.5	186.2	186.9	186.6	186.9	187.3	188.4
177.5°	185.2	185.0	185.5	185.5	185.5	185.8	186.4	185.8	185.5	185.8	186.4
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	981.3	981.3	981.3	981.3	981.3	981.3	981.3
2.5°	1017.8	1022.1	1022.1	1022.7	1027.4	1026.9	1026.6
5°	1083.2	1089.5	1090.4	1097.1	1101.7	1100.1	1096.0
7.5°	1144.8	1156.7	1165.8	1170.8	1176.8	1180.4	1178.8
10°	1193.7	1211.0	1221.5	1228.7	1237.4	1243.9	1241.5
12.5°	1238.0	1258.7	1273.1	1285.5	1286.6	1294.8	1289.2
15°	1307.2	1329.1	1331.3	1340.4	1347.6	1346.8	1347.2
17.5°	1330.0	1337.1	1338.5	1338.7	1338.8	1336.2	1330.4
20°	1321.9	1319.3	1312.8	1308.0	1299.3	1298.1	1290.6
22.5°	1283.2	1274.9	1258.8	1248.2	1234.7	1231.1	1229.0
25°	1207.2	1188.7	1163.1	1138.6	1131.8	1118.6	1122.4
27.5°	1102.9	1074.1	1046.3	1026.4	1008.5	988.7	994.3
30°	1029.6	997.1	958.0	927.8	908.6	889.7	886.3
32.5°	942.1	894.5	850.8	824.3	794.8	782.8	769.8
35°	791.2	744.9	701.5	664.2	642.7	626.0	611.0
37.5°	655.5	602.2	567.1	536.9	521.4	511.9	514.2
40°	571.4	524.6	499.0	475.9	461.6	454.8	456.4
42.5°	503.2	468.2	447.1	431.3	421.2	417.4	416.5
45°	425.8	406.2	388.8	379.8	374.9	370.7	368.1
47.5°	373.0	357.0	347.2	341.8	337.5	333.4	333.3
50°	341.3	330.7	324.0	318.3	314.9	311.8	314.6
52.5°	317.2	307.5	300.7	295.7	294.4	291.6	291.6
55°	281.3	273.8	268.9	264.4	262.2	260.6	258.7
57.5°	248.7	241.6	237.1	234.2	229.9	228.4	227.8
60°	225.5	219.8	215.3	211.6	209.6	206.7	206.7
62.5°	204.1	198.4	194.2	191.4	188.2	187.0	187.3
65°	173.1	168.5	164.4	161.4	160.7	158.4	159.2
67.5°	144.6	141.6	137.2	135.5	134.1	132.9	132.0
70°	125.6	122.6	120.3	118.1	116.9	116.9	116.9
72.5°	109.6	105.9	104.6	101.8	102.4	101.2	100.0
75°	84.8	82.6	81.5	80.3	78.5	78.5	78.5
77.5°	62.4	61.8	60.4	59.2	58.8	58.4	58.6
80°	48.3	47.9	47.2	47.2	46.4	46.0	45.2
82.5°	37.1	36.2	35.6	35.3	35.2	35.1	35.0
85°	21.1	20.4	20.4	20.7	20.0	20.0	20.4
87.5°	10.3	10.4	10.2	10.2	10.5	10.2	10.2
90°	10.7	11.4	11.8	11.8	11.8	11.8	11.8
92.5°	26.7	23.7	21.5	21.2	20.1	20.3	19.8
95°	71.7	56.8	48.9	44.2	41.4	40.3	40.7
97.5°	178.4	139.9	114.1	97.0	88.3	83.1	80.1
100°	281.6	232.7	189.5	159.9	144.5	134.2	127.7
102.5°	386.3	350.5	304.8	272.6	246.4	233.5	224.8
105°	473.8	478.5	466.8	444.5	422.4	407.1	402.1
107.5°	467.5	504.5	521.8	524.6	523.4	520.3	513.7
110°	447.5	493.1	522.4	537.8	544.5	547.8	547.3



TEST NUMBER: P331287-840

CATALOG NUMBER: S122DIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	423.7	472.5	506.1	527.5	538.8	544.8	546.7
115°	391.4	438.2	474.9	500.3	516.6	525.9	529.2
117.5°	365.2	407.6	442.0	467.9	485.2	494.9	497.7
120°	351.4	389.3	421.7	446.8	463.5	473.8	477.5
122.5°	340.0	375.9	405.2	427.6	444.1	453.3	456.3
125°	325.1	356.5	383.2	403.9	417.5	426.4	429.3
127.5°	310.5	340.1	364.8	382.8	395.6	403.2	405.6
130°	300.8	329.0	352.5	370.0	382.1	389.3	392.1
132.5°	291.6	317.6	339.7	356.9	369.0	375.6	378.2
135°	277.2	300.8	320.7	336.1	347.9	354.4	355.8
137.5°	265.8	284.5	301.8	315.9	326.0	331.6	333.8
140°	258.3	274.8	290.4	301.8	311.1	316.5	318.6
142.5°	251.8	265.9	279.0	289.8	298.3	303.1	303.5
145°	243.4	254.4	264.8	273.3	279.4	283.0	284.0
147.5°	236.5	245.1	252.7	259.7	264.6	267.0	267.7
150°	232.0	239.4	245.8	251.2	255.5	257.6	258.0
152.5°	228.2	234.6	240.1	244.4	248.0	249.6	249.7
155°	222.3	227.6	231.6	235.5	238.0	239.4	238.7
157.5°	216.3	220.8	223.9	226.6	228.7	229.3	229.3
160°	212.3	216.2	218.7	221.3	223.0	223.4	223.4
162.5°	208.6	212.0	213.9	216.4	217.6	217.9	217.6
165°	203.0	205.5	206.9	208.3	209.8	209.8	209.4
167.5°	197.9	199.7	201.0	201.6	202.4	202.3	201.9
170°	194.8	196.2	196.9	197.3	198.3	198.0	197.3
172.5°	192.0	193.1	193.5	193.9	194.4	194.0	193.6
175°	188.7	189.1	189.5	189.5	189.9	189.5	188.7
177.5°	186.4	186.7	186.7	186.7	186.7	186.4	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5

(END OF REPORT)