

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331622-840

Luminaire Tested: **S122RDIP-S290D530U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331622-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D530U840-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3051.8 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	96	91	88	85	87	83	80	77	68	66	64	53	52	51	40	39	39	33
2	87	81	75	70	79	73	69	64	60	57	54	48	45	43	36	35	34	28
3	80	71	65	59	73	65	59	55	53	49	46	43	40	37	33	31	29	25
4	74	64	56	51	67	58	52	47	48	43	40	38	35	33	30	28	26	22
5	68	57	49	44	61	52	46	41	43	38	35	35	31	29	27	25	23	19
6	63	51	44	38	57	47	40	36	39	34	30	32	28	25	25	22	21	17
7	58	46	39	34	53	43	36	31	36	31	27	29	25	23	23	20	19	16
8	54	42	35	30	49	39	33	28	33	28	24	27	23	21	21	19	17	14
9	50	39	32	27	46	36	29	25	30	25	22	25	21	19	20	17	15	13
10	47	36	29	24	43	33	27	23	28	23	20	23	19	17	18	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10658	10658	10658	10658
5°	11904	10726	9511	10726
10°	13209	10650	8243	10650
15°	13857	10494	6496	10494
20°	12014	10263	5620	10263
25°	7878	9948	5018	9948
30°	5304	9562	4542	9562
35°	4295	9079	4096	9079
40°	3819	8553	3792	8553
45°	3457	7935	3382	7935
50°	3145	7322	3135	7322
55°	2956	6643	2919	6643
60°	2474	6022	2444	6022
65°	2086	5467	2365	5467
70°	1926	4881	2233	4881
75°	1803	4255	2059	4255
80°	1664	3505	1832	3505
85°	1538	2760	1612	2760



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.6	2.1
10°-20°	174.4	5.7
20°-30°	224.7	7.4
30°-40°	213.5	7.0
40°-50°	182.9	6.0
50°-60°	139.3	4.6
60°-70°	88.1	2.9
70°-80°	44.0	1.4
80°-90°	14.2	0.5
90°-100°	43.3	1.4
100°-110°	134.3	4.4
110°-120°	229.6	7.5
120°-130°	301.9	9.9
130°-140°	338.8	11.1
140°-150°	332.2	10.9
150°-160°	278.7	9.1
160°-170°	184.8	6.1
170°-180°	64.6	2.1
0°-30°	461.7	15.1
0°-40°	675.2	22.1
0°-60°	997.5	32.7
0°-90°	1143.7	37.5
90°-120°	407.1	13.3
90°-150°	1380.1	45.2
90°-180°	1908.0	62.5
0°-180°	3051.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	660	660	660	660	660	
5°	734	662	587	662	734	72
15°	829	628	389	628	829	224
25°	442	558	282	558	442	210
35°	218	461	208	461	218	139
45°	151	348	148	348	151	117
55°	105	236	104	236	105	92
65°	55	143	62	143	55	56
75°	29	68	33	68	29	31
85°	8	15	9	15	8	9
90°	20	1	20	1	20	9
95°	36	30	36	30	36	40
105°	128	124	128	124	128	134
115°	230	230	230	230	230	227
125°	336	335	336	335	336	300
135°	439	434	439	434	439	338
145°	532	526	532	526	532	332
155°	606	602	606	602	606	279
165°	655	655	655	655	655	185
175°	679	681	679	681	679	65
180°	682	682	682	682	682	



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	687.0	687.5	688.1	686.8	686.8	685.7	683.3	681.5	676.3	675.6	675.6
5°	734.5	734.1	735.0	732.0	727.9	726.9	722.6	716.8	710.8	704.3	702.9
7.5°	781.7	781.0	779.2	778.7	775.6	768.6	761.6	754.2	744.3	734.6	729.7
10°	805.7	813.2	808.6	800.6	802.1	791.4	785.7	775.8	767.5	753.1	749.9
12.5°	829.1	832.1	830.6	826.1	824.0	816.6	808.8	800.2	785.0	772.0	760.7
15°	829.0	833.3	834.6	833.1	834.2	833.8	829.7	822.6	809.3	795.1	782.6
17.5°	767.8	770.8	778.4	783.5	789.9	803.4	810.2	812.7	810.8	802.6	794.0
20°	699.2	694.2	715.3	726.0	735.2	758.1	777.9	785.5	797.6	797.4	795.1
22.5°	601.9	603.1	623.1	635.9	662.7	685.7	708.1	736.6	760.1	775.7	784.8
25°	442.2	451.0	470.9	488.4	518.2	560.9	599.7	644.6	687.0	720.5	752.5
27.5°	332.1	332.9	348.6	364.8	382.4	417.4	466.3	519.9	580.4	630.4	687.7
30°	284.5	283.1	289.7	299.6	314.8	341.8	378.5	431.2	491.6	566.8	633.8
32.5°	250.6	250.7	255.8	263.1	275.6	293.9	319.0	361.9	418.9	492.9	571.4
35°	217.9	217.7	221.4	226.6	231.9	243.6	260.8	283.3	322.6	391.5	471.8
37.5°	194.4	195.4	197.2	200.6	206.3	212.9	223.2	238.3	266.2	307.1	374.6
40°	181.2	181.7	184.2	186.9	190.4	195.4	203.9	216.1	236.5	269.0	318.4
42.5°	169.2	169.6	171.4	173.9	176.6	181.7	188.7	199.2	215.8	241.2	281.9
45°	151.4	151.4	153.0	154.1	157.1	161.7	167.4	176.2	187.6	206.4	233.5
47.5°	134.8	134.8	135.9	137.8	139.8	143.3	149.0	156.1	164.4	178.9	202.1
50°	125.2	125.5	126.1	127.7	129.0	132.1	136.5	142.7	151.4	162.7	181.9
52.5°	117.5	117.4	118.3	119.0	119.8	122.0	125.3	130.8	138.6	148.3	164.3
55°	105.0	104.1	105.5	106.6	107.3	108.3	110.1	113.5	120.2	128.5	140.4
57.5°	89.5	89.1	90.1	91.1	93.3	95.7	97.4	99.5	102.9	108.9	120.7
60°	76.6	76.6	78.7	79.4	81.9	85.1	88.4	90.2	93.6	97.5	106.2
62.5°	65.2	65.4	66.3	67.1	68.5	72.4	77.0	81.0	84.2	88.0	93.7
65°	54.6	55.0	55.0	55.5	56.5	57.4	59.2	62.4	68.2	73.4	77.8
67.5°	46.4	46.5	46.7	47.1	47.3	48.3	49.1	50.5	51.8	56.8	62.2
70°	40.8	41.5	41.3	41.7	42.0	42.4	43.3	44.0	46.2	47.3	50.5
72.5°	35.6	36.2	36.2	36.5	37.1	37.2	37.9	38.6	39.9	40.8	42.6
75°	28.9	28.7	28.9	29.4	29.6	29.8	29.8	30.7	31.4	32.3	33.5
77.5°	22.3	22.5	22.5	22.5	22.6	23.0	22.9	23.3	24.0	24.5	25.0
80°	17.9	18.1	17.9	18.1	18.4	18.6	18.4	18.6	19.3	19.7	19.7
82.5°	13.8	13.9	14.0	14.0	14.1	14.1	14.5	14.5	15.0	14.9	15.1
85°	8.3	8.1	8.1	8.1	8.3	8.5	8.3	8.3	8.5	8.5	8.5
87.5°	6.9	7.0	7.0	7.0	7.0	7.0	7.0	7.3	7.1	7.4	6.6
90°	19.6	19.5	19.3	19.2	19.1	19.1	19.4	19.7	19.9	20.2	17.4
92.5°	18.7	18.7	18.6	18.6	18.6	18.5	18.5	18.4	18.4	18.3	17.7
95°	35.7	36.0	36.3	36.5	36.8	36.9	36.9	36.9	36.9	36.9	36.6
97.5°	61.8	61.9	61.9	61.9	61.9	62.0	62.0	62.0	62.0	62.0	61.5
100°	78.9	79.1	79.2	79.3	79.4	79.5	79.5	79.5	79.5	79.5	79.1
102.5°	98.3	98.4	98.5	98.7	98.8	98.8	98.7	98.6	98.5	98.4	97.9
105°	127.8	127.8	127.8	127.8	127.8	127.7	127.4	127.2	126.9	126.7	126.4
107.5°	155.7	156.3	156.9	157.4	158.0	158.3	158.2	158.1	158.0	157.9	157.9
110°	177.3	177.7	178.1	178.5	178.9	179.0	179.0	179.0	179.0	179.0	179.0



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	198.1	198.3	198.6	198.9	199.2	199.5	199.9	200.2	200.5	200.8	200.9
115°	230.4	230.8	231.2	231.5	231.9	232.2	232.3	232.4	232.6	232.7	232.9
117.5°	261.1	261.5	261.9	262.3	262.7	263.0	263.3	263.6	263.9	264.2	264.9
120°	282.8	283.2	283.6	283.9	284.3	284.5	284.5	284.5	284.5	284.5	285.5
122.5°	304.0	304.3	304.5	304.8	305.1	305.4	305.7	306.0	306.3	306.6	307.3
125°	336.3	336.4	336.6	336.7	336.8	337.1	337.5	337.8	338.2	338.6	339.0
127.5°	365.8	366.2	366.6	367.0	367.4	367.9	368.3	368.8	369.2	369.7	370.2
130°	387.0	387.5	388.0	388.5	389.0	389.4	389.7	389.9	390.2	390.4	390.7
132.5°	407.3	407.7	408.1	408.5	408.9	409.4	409.9	410.5	411.1	411.6	411.6
135°	438.8	439.2	439.6	440.0	440.3	440.6	440.7	440.9	441.0	441.1	440.9
137.5°	467.4	467.9	468.4	468.9	469.4	469.7	469.8	469.9	470.0	470.1	469.8
140°	487.2	487.7	488.2	488.7	489.3	489.5	489.5	489.5	489.5	489.5	488.9
142.5°	505.1	505.6	506.1	506.6	507.2	507.4	507.3	507.2	507.1	507.0	506.5
145°	532.1	532.6	533.1	533.6	534.1	534.3	534.2	534.1	533.9	533.8	533.1
147.5°	556.1	556.6	557.1	557.6	558.2	558.3	558.0	557.6	557.3	557.1	556.5
150°	571.9	572.2	572.6	573.0	573.4	573.4	573.0	572.6	572.2	571.9	571.3
152.5°	586.6	587.0	587.5	588.0	588.5	588.5	588.0	587.5	587.0	586.6	585.9
155°	606.4	606.7	607.1	607.5	607.9	607.8	607.1	606.5	605.9	605.2	604.8
157.5°	623.4	624.1	624.7	625.3	625.9	625.8	624.9	624.0	623.2	622.3	622.1
160°	634.0	634.5	635.1	635.6	636.1	635.9	635.2	634.4	633.7	632.9	632.8
162.5°	643.3	643.9	644.5	645.1	645.7	645.6	644.7	643.8	643.0	642.1	642.0
165°	655.3	656.0	656.6	657.2	657.9	657.7	656.9	656.0	655.1	654.2	654.2
167.5°	665.2	665.9	666.6	667.2	667.9	667.8	666.9	666.0	665.1	664.2	664.2
170°	670.3	671.1	671.9	672.6	673.4	673.3	672.5	671.6	670.7	669.7	669.8
172.5°	674.5	675.2	676.0	676.8	677.5	677.4	676.6	675.7	674.8	673.9	674.0
175°	678.9	679.7	680.4	681.3	682.1	682.0	681.1	680.1	679.2	678.3	678.6
177.5°	681.1	681.7	682.3	682.9	683.5	683.5	682.9	682.3	681.7	681.1	681.3
180°	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	676.0	674.5	673.2	669.9	668.2	664.6	664.1	663.9	659.1	654.5	653.2
5°	699.2	695.5	690.0	683.6	676.9	670.0	665.5	661.8	652.6	643.9	638.8
7.5°	722.6	714.7	705.2	693.1	682.9	671.6	663.1	655.5	642.5	630.0	621.6
10°	740.0	727.2	714.6	697.8	684.7	671.9	659.9	649.6	635.0	618.4	606.7
12.5°	750.8	736.7	719.3	703.0	686.0	669.6	653.7	640.5	623.2	606.1	592.3
15°	765.5	750.3	729.2	705.8	684.1	662.7	644.4	627.8	605.4	584.9	567.9
17.5°	777.5	756.6	734.0	706.9	681.7	654.6	631.0	609.9	584.8	560.2	540.2
20°	781.3	760.6	734.5	707.4	677.6	645.7	620.3	597.3	570.5	543.6	520.7
22.5°	778.9	762.9	733.8	701.4	670.9	637.5	608.7	582.1	552.3	524.9	498.4
25°	762.8	757.2	729.7	694.4	659.5	620.8	587.4	558.4	524.4	495.0	466.2
27.5°	725.0	736.9	719.8	682.2	643.4	601.9	564.4	531.3	496.0	463.0	434.2
30°	688.6	715.9	708.6	673.7	630.4	589.6	547.5	512.9	475.3	441.3	412.9
32.5°	638.9	684.0	691.2	662.0	617.1	572.3	528.3	493.8	454.5	418.8	391.0
35°	559.7	627.1	658.1	639.5	594.6	546.1	500.8	460.6	421.1	385.9	358.3
37.5°	465.2	557.1	608.7	610.1	568.8	518.5	469.0	429.1	388.7	354.1	324.3
40°	403.9	503.5	570.8	585.6	550.8	496.4	446.4	405.8	366.4	332.3	298.2
42.5°	348.9	448.1	530.7	556.6	529.0	474.9	424.7	382.3	344.0	311.8	276.9
45°	282.2	368.9	459.9	506.2	490.9	440.9	387.9	347.5	311.5	283.8	250.2
47.5°	238.0	299.1	387.3	449.9	449.7	404.0	351.8	313.3	279.8	253.8	226.7
50°	212.9	266.1	340.6	411.7	417.7	379.4	329.8	291.5	260.3	233.1	211.3
52.5°	190.3	234.2	301.1	369.4	386.4	353.1	305.1	269.7	239.4	214.3	195.7
55°	160.8	194.8	245.7	309.4	335.2	311.7	269.0	236.0	211.5	190.4	174.3
57.5°	136.0	161.5	202.4	253.7	283.6	268.9	233.7	206.8	185.8	166.7	154.1
60°	120.5	141.3	175.9	218.8	251.9	241.6	211.5	186.5	168.6	152.1	140.2
62.5°	105.7	123.7	153.4	188.2	218.4	214.2	189.7	168.6	153.0	137.9	127.8
65°	85.1	98.2	121.4	148.7	173.0	175.0	157.3	143.1	129.2	117.2	108.3
67.5°	67.8	76.3	92.6	115.6	133.8	140.4	129.6	118.7	107.6	98.4	90.6
70°	57.2	64.0	75.9	94.5	111.3	118.2	111.9	103.4	93.8	86.2	79.6
72.5°	46.3	53.0	61.8	75.4	89.8	97.3	95.0	89.0	81.2	74.8	68.6
75°	34.8	37.0	42.9	52.1	63.3	69.8	71.3	68.2	61.9	57.2	53.4
77.5°	25.8	27.1	29.9	34.6	42.0	47.8	50.1	49.7	45.4	42.7	39.2
80°	20.6	21.3	22.7	24.7	30.3	36.1	37.7	37.7	34.6	33.5	30.1
82.5°	15.7	16.2	17.1	18.2	20.7	25.8	27.6	27.9	26.1	24.5	21.8
85°	9.0	8.7	9.2	9.9	10.3	11.7	14.4	14.9	14.4	12.6	11.9
87.5°	6.1	5.7	5.0	4.4	4.3	4.2	4.8	5.5	5.0	4.7	4.7
90°	14.5	11.7	8.9	6.8	5.2	3.6	2.1	0.6	2.1	3.6	5.2
92.5°	17.0	16.4	15.7	14.7	13.6	12.5	11.4	10.3	11.4	12.5	13.6
95°	36.4	36.1	35.9	35.0	33.8	32.5	31.2	30.0	31.2	32.5	33.8
97.5°	61.0	60.5	60.0	59.2	58.1	57.0	55.8	54.7	55.8	57.0	58.1
100°	78.7	78.4	78.0	77.3	76.2	75.1	74.1	73.1	74.1	75.1	76.2
102.5°	97.4	96.9	96.4	95.7	94.9	94.1	93.3	92.5	93.3	94.1	94.9
105°	126.1	125.9	125.6	125.3	124.9	124.6	124.2	123.8	124.2	124.6	124.9
107.5°	157.9	157.9	157.9	157.6	157.0	156.5	155.9	155.4	155.9	156.5	157.0
110°	179.0	179.0	179.0	178.7	177.9	177.1	176.4	175.6	176.4	177.1	177.9





TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	201.0	201.1	201.2	200.9	200.1	199.2	198.5	197.7	198.5	199.2	200.1
115°	233.2	233.4	233.7	233.4	232.7	231.9	231.2	230.4	231.2	231.9	232.7
117.5°	265.6	266.4	267.1	266.9	265.9	264.9	263.9	262.9	263.9	264.9	265.9
120°	286.5	287.5	288.6	288.6	287.5	286.5	285.5	284.5	285.5	286.5	287.5
122.5°	308.0	308.7	309.4	309.2	308.0	306.8	305.5	304.3	305.5	306.8	308.0
125°	339.4	339.7	340.1	339.7	338.6	337.5	336.3	335.2	336.3	337.5	338.6
127.5°	370.6	371.1	371.5	371.0	369.6	368.1	366.7	365.2	366.7	368.1	369.6
130°	390.9	391.2	391.4	390.7	389.1	387.4	385.8	384.2	385.8	387.4	389.1
132.5°	411.5	411.5	411.4	410.7	409.4	408.0	406.7	405.3	406.7	408.0	409.4
135°	440.6	440.3	440.1	439.3	437.9	436.5	435.0	433.6	435.0	436.5	437.9
137.5°	469.5	469.2	468.8	468.1	467.0	465.7	464.6	463.4	464.6	465.7	467.0
140°	488.2	487.6	487.0	486.0	484.8	483.7	482.6	481.4	482.6	483.7	484.8
142.5°	506.1	505.7	505.2	504.4	503.3	502.2	501.0	499.9	501.0	502.2	503.3
145°	532.3	531.5	530.8	530.0	529.1	528.2	527.3	526.3	527.3	528.2	529.1
147.5°	556.0	555.5	555.0	554.2	553.2	552.1	551.0	550.0	551.0	552.1	553.2
150°	570.8	570.3	569.8	569.2	568.4	567.6	566.8	566.1	566.8	567.6	568.4
152.5°	585.3	584.7	584.1	583.4	582.7	581.9	581.2	580.4	581.2	581.9	582.7
155°	604.5	604.1	603.7	603.3	602.9	602.6	602.2	601.8	602.2	602.6	602.9
157.5°	621.9	621.6	621.4	621.2	620.9	620.6	620.4	620.1	620.4	620.6	620.9
160°	632.6	632.5	632.4	632.2	631.9	631.7	631.4	631.2	631.4	631.7	631.9
162.5°	641.9	641.7	641.6	641.5	641.5	641.4	641.4	641.3	641.4	641.4	641.5
165°	654.2	654.2	654.2	654.3	654.4	654.5	654.6	654.8	654.6	654.5	654.4
167.5°	664.3	664.3	664.3	664.5	664.9	665.3	665.7	666.0	665.7	665.3	664.9
170°	669.9	670.1	670.2	670.6	670.9	671.3	671.7	672.1	671.7	671.3	670.9
172.5°	674.2	674.3	674.4	674.7	675.0	675.4	675.8	676.2	675.8	675.4	675.0
175°	678.9	679.1	679.4	679.7	680.1	680.4	680.9	681.3	680.9	680.4	680.1
177.5°	681.5	681.7	681.9	682.1	682.4	682.7	683.0	683.4	683.0	682.7	682.4
180°	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	650.9	649.5	647.1	643.5	641.3	637.4	634.9	636.3	636.7	636.3	636.0
5°	633.4	628.5	621.9	615.4	609.5	603.1	599.4	597.8	594.6	592.8	591.8
7.5°	612.2	603.9	594.5	583.3	573.8	563.8	558.8	556.2	549.7	546.1	543.0
10°	596.4	583.3	573.9	559.3	550.3	537.2	528.3	528.6	519.6	514.5	510.9
12.5°	579.0	564.6	549.0	535.7	523.3	512.8	502.0	497.7	488.2	483.3	473.4
15°	550.1	533.3	516.8	499.0	486.4	470.0	454.4	435.4	420.0	406.7	403.0
17.5°	518.6	497.8	481.2	460.2	438.6	411.2	393.1	382.0	372.8	365.8	360.5
20°	496.9	475.7	458.1	426.5	397.3	378.7	365.5	356.9	347.3	339.7	335.6
22.5°	474.1	452.1	428.0	392.6	369.9	355.1	343.3	333.5	326.9	321.0	317.2
25°	441.8	417.7	378.0	353.8	335.4	319.7	311.5	305.6	298.7	290.6	287.0
27.5°	407.7	369.4	340.8	322.8	305.3	295.2	287.7	278.8	272.7	269.0	265.2
30°	382.1	343.9	321.6	301.8	289.5	278.2	269.5	264.5	258.5	252.4	249.8
32.5°	353.8	323.2	301.7	285.4	272.8	263.2	256.3	248.1	243.9	240.0	234.8
35°	318.4	295.2	275.7	262.5	250.4	242.7	234.7	229.8	222.1	218.8	216.8
37.5°	288.5	268.4	253.9	239.8	230.4	221.8	216.8	209.1	205.8	201.3	196.9
40°	271.6	251.9	237.9	226.4	215.8	209.4	203.3	197.0	192.0	190.0	184.7
42.5°	254.4	238.3	224.3	211.8	204.7	197.8	190.1	185.5	180.3	176.9	173.7
45°	230.6	216.3	204.4	194.1	186.2	179.2	174.1	166.5	163.6	156.9	154.1
47.5°	209.6	196.4	185.0	175.2	167.6	163.0	155.6	149.7	144.9	140.8	137.2
50°	194.8	183.7	172.7	164.0	157.1	150.5	142.9	140.0	132.6	130.5	128.5
52.5°	181.2	170.7	160.7	152.1	145.2	138.8	132.1	128.2	123.2	121.2	119.7
55°	162.2	152.1	142.5	134.9	128.1	121.4	117.2	112.4	110.1	108.5	106.6
57.5°	143.1	134.0	126.6	119.0	112.0	106.7	102.0	99.1	96.7	94.6	92.4
60°	131.0	122.3	115.6	108.5	101.4	97.0	93.4	89.9	87.2	83.9	83.0
62.5°	118.2	110.5	104.4	97.5	91.3	87.4	83.8	80.6	77.3	72.6	71.3
65°	100.5	94.5	88.1	82.3	76.9	72.9	67.9	64.2	62.8	62.4	62.2
67.5°	84.5	78.9	73.3	67.5	62.5	58.9	56.2	55.7	54.7	54.5	53.8
70°	73.8	68.6	63.1	57.6	52.7	52.1	51.2	50.2	49.1	48.7	48.2
72.5°	64.3	58.9	53.3	49.0	46.9	46.0	45.1	44.1	43.4	42.9	42.7
75°	49.3	44.2	40.6	39.0	37.9	37.2	35.7	35.1	34.6	33.9	33.7
77.5°	35.5	32.6	31.0	30.0	28.8	28.1	27.3	26.6	26.1	26.0	25.5
80°	27.1	25.7	24.5	23.1	22.7	21.8	21.6	20.9	21.1	20.4	20.4
82.5°	21.0	19.3	18.3	17.7	17.2	16.5	16.3	16.0	16.0	15.5	15.5
85°	10.8	10.3	9.9	9.4	9.4	8.7	9.0	8.7	8.7	8.3	8.1
87.5°	4.8	5.0	5.3	5.9	6.4	6.8	6.8	6.5	6.5	6.4	6.2
90°	6.8	8.9	11.7	14.5	17.4	20.2	19.9	19.7	19.4	19.1	19.1
92.5°	14.7	15.7	16.4	17.0	17.7	18.3	18.4	18.4	18.5	18.5	18.6
95°	35.0	35.9	36.1	36.4	36.6	36.9	36.9	36.9	36.9	36.9	36.8
97.5°	59.2	60.0	60.5	61.0	61.5	62.0	62.0	62.0	62.0	62.0	61.9
100°	77.3	78.0	78.4	78.7	79.1	79.5	79.5	79.5	79.5	79.5	79.4
102.5°	95.7	96.4	96.9	97.4	97.9	98.4	98.5	98.6	98.7	98.8	98.8
105°	125.3	125.6	125.9	126.1	126.4	126.7	126.9	127.2	127.4	127.7	127.8
107.5°	157.6	157.9	157.9	157.9	157.9	157.9	158.0	158.1	158.2	158.3	158.0
110°	178.7	179.0	179.0	179.0	179.0	179.0	179.0	179.0	179.0	179.0	178.9



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	200.9	201.2	201.1	201.0	200.9	200.8	200.5	200.2	199.9	199.5	199.2
115°	233.4	233.7	233.4	233.2	232.9	232.7	232.6	232.4	232.3	232.2	231.9
117.5°	266.9	267.1	266.4	265.6	264.9	264.2	263.9	263.6	263.3	263.0	262.7
120°	288.6	288.6	287.5	286.5	285.5	284.5	284.5	284.5	284.5	284.5	284.3
122.5°	309.2	309.4	308.7	308.0	307.3	306.6	306.3	306.0	305.7	305.4	305.1
125°	339.7	340.1	339.7	339.4	339.0	338.6	338.2	337.8	337.5	337.1	336.8
127.5°	371.0	371.5	371.1	370.6	370.2	369.7	369.2	368.8	368.3	367.9	367.4
130°	390.7	391.4	391.2	390.9	390.7	390.4	390.2	389.9	389.7	389.4	389.0
132.5°	410.7	411.4	411.5	411.5	411.6	411.6	411.1	410.5	409.9	409.4	408.9
135°	439.3	440.1	440.3	440.6	440.9	441.1	441.0	440.9	440.7	440.6	440.3
137.5°	468.1	468.8	469.2	469.5	469.8	470.1	470.0	469.9	469.8	469.7	469.4
140°	486.0	487.0	487.6	488.2	488.9	489.5	489.5	489.5	489.5	489.5	489.3
142.5°	504.4	505.2	505.7	506.1	506.5	507.0	507.1	507.2	507.3	507.4	507.2
145°	530.0	530.8	531.5	532.3	533.1	533.8	533.9	534.1	534.2	534.3	534.1
147.5°	554.2	555.0	555.5	556.0	556.5	557.1	557.3	557.6	558.0	558.3	558.2
150°	569.2	569.8	570.3	570.8	571.3	571.9	572.2	572.6	573.0	573.4	573.4
152.5°	583.4	584.1	584.7	585.3	585.9	586.6	587.0	587.5	588.0	588.5	588.5
155°	603.3	603.7	604.1	604.5	604.8	605.2	605.9	606.5	607.1	607.8	607.9
157.5°	621.2	621.4	621.6	621.9	622.1	622.3	623.2	624.0	624.9	625.8	625.9
160°	632.2	632.4	632.5	632.6	632.8	632.9	633.7	634.4	635.2	635.9	636.1
162.5°	641.5	641.6	641.7	641.9	642.0	642.1	643.0	643.8	644.7	645.6	645.7
165°	654.3	654.2	654.2	654.2	654.2	654.2	655.1	656.0	656.9	657.7	657.9
167.5°	664.5	664.3	664.3	664.3	664.2	664.2	665.1	666.0	666.9	667.8	667.9
170°	670.6	670.2	670.1	669.9	669.8	669.7	670.7	671.6	672.5	673.3	673.4
172.5°	674.7	674.4	674.3	674.2	674.0	673.9	674.8	675.7	676.6	677.4	677.5
175°	679.7	679.4	679.1	678.9	678.6	678.3	679.2	680.1	681.1	682.0	682.1
177.5°	682.1	681.9	681.7	681.5	681.3	681.1	681.7	682.3	682.9	683.5	683.5
180°	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.0	634.3	633.8	634.1	633.8	634.3	634.0	636.0	636.3	636.7	636.3
5°	590.7	587.9	587.4	586.8	587.4	587.9	590.7	591.8	592.8	594.6	597.8
7.5°	539.1	538.7	537.5	535.8	537.5	538.7	539.1	543.0	546.1	549.7	556.2
10°	505.8	504.6	504.4	502.8	504.4	504.6	505.8	510.9	514.5	519.6	528.6
12.5°	466.9	459.5	458.8	454.7	458.8	459.5	466.9	473.4	483.3	488.2	497.7
15°	397.6	396.2	391.5	388.6	391.5	396.2	397.6	403.0	406.7	420.0	435.4
17.5°	357.9	353.4	351.9	351.3	351.9	353.4	357.9	360.5	365.8	372.8	382.0
20°	332.3	328.3	327.6	327.1	327.6	328.3	332.3	335.6	339.7	347.3	356.9
22.5°	314.8	310.4	308.7	307.3	308.7	310.4	314.8	317.2	321.0	326.9	333.5
25°	284.7	283.1	282.2	281.7	282.2	283.1	284.7	287.0	290.6	298.7	305.6
27.5°	261.2	257.6	256.9	255.7	256.9	257.6	261.2	265.2	269.0	272.7	278.8
30°	247.7	246.6	245.0	243.6	245.0	246.6	247.7	249.8	252.4	258.5	264.5
32.5°	232.0	231.0	229.5	228.9	229.5	231.0	232.0	234.8	240.0	243.9	248.1
35°	214.5	211.3	209.8	207.8	209.8	211.3	214.5	216.8	218.8	222.1	229.8
37.5°	196.0	194.3	192.4	193.1	192.4	194.3	196.0	196.9	201.3	205.8	209.1
40°	181.7	180.6	180.1	179.9	180.1	180.6	181.7	184.7	190.0	192.0	197.0
42.5°	170.3	167.1	165.9	165.9	165.9	167.1	170.3	173.7	176.9	180.3	185.5
45°	153.0	150.1	147.9	148.1	147.9	150.1	153.0	154.1	156.9	163.6	166.5
47.5°	135.3	135.2	133.9	134.3	133.9	135.2	135.3	137.2	140.8	144.9	149.7
50°	126.8	125.5	124.5	124.8	124.5	125.5	126.8	128.5	130.5	132.6	140.0
52.5°	118.8	117.5	116.8	117.9	116.8	117.5	118.8	119.7	121.2	123.2	128.2
55°	105.5	104.1	103.9	103.7	103.9	104.1	105.5	106.6	108.5	110.1	112.4
57.5°	90.7	89.8	88.4	87.9	88.4	89.8	90.7	92.4	94.6	96.7	99.1
60°	80.1	78.3	75.9	75.7	75.9	78.3	80.1	83.0	83.9	87.2	89.9
62.5°	70.3	70.0	69.5	69.5	69.5	70.0	70.3	71.3	72.6	77.3	80.6
65°	61.7	61.5	61.7	61.9	61.7	61.5	61.7	62.2	62.4	62.8	64.2
67.5°	53.7	53.3	52.9	53.1	52.9	53.3	53.7	53.8	54.5	54.7	55.7
70°	47.7	47.5	47.3	47.3	47.3	47.5	47.7	48.2	48.7	49.1	50.2
72.5°	41.8	41.8	41.6	41.4	41.6	41.8	41.8	42.7	42.9	43.4	44.1
75°	33.5	33.0	33.0	33.0	33.0	33.0	33.5	33.7	33.9	34.6	35.1
77.5°	25.5	25.2	25.0	24.8	25.0	25.2	25.5	25.5	26.0	26.1	26.6
80°	20.2	20.0	19.7	19.7	19.7	20.0	20.2	20.4	20.4	21.1	20.9
82.5°	15.5	15.1	15.1	14.9	15.1	15.1	15.5	15.5	15.5	16.0	16.0
85°	8.3	8.5	8.3	8.7	8.3	8.5	8.3	8.1	8.3	8.7	8.7
87.5°	6.3	6.1	6.3	6.2	6.3	6.1	6.3	6.2	6.4	6.5	6.5
90°	19.2	19.3	19.5	19.6	19.5	19.3	19.2	19.1	19.1	19.4	19.7
92.5°	18.6	18.6	18.7	18.7	18.7	18.6	18.6	18.6	18.5	18.5	18.4
95°	36.5	36.3	36.0	35.7	36.0	36.3	36.5	36.8	36.9	36.9	36.9
97.5°	61.9	61.9	61.9	61.8	61.9	61.9	61.9	61.9	62.0	62.0	62.0
100°	79.3	79.2	79.1	78.9	79.1	79.2	79.3	79.4	79.5	79.5	79.5
102.5°	98.7	98.5	98.4	98.3	98.4	98.5	98.7	98.8	98.8	98.7	98.6
105°	127.8	127.8	127.8	127.8	127.8	127.8	127.8	127.8	127.7	127.4	127.2
107.5°	157.4	156.9	156.3	155.7	156.3	156.9	157.4	158.0	158.3	158.2	158.1
110°	178.5	178.1	177.7	177.3	177.7	178.1	178.5	178.9	179.0	179.0	179.0



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	198.9	198.6	198.3	198.1	198.3	198.6	198.9	199.2	199.5	199.9	200.2
115°	231.5	231.2	230.8	230.4	230.8	231.2	231.5	231.9	232.2	232.3	232.4
117.5°	262.3	261.9	261.5	261.1	261.5	261.9	262.3	262.7	263.0	263.3	263.6
120°	283.9	283.6	283.2	282.8	283.2	283.6	283.9	284.3	284.5	284.5	284.5
122.5°	304.8	304.5	304.3	304.0	304.3	304.5	304.8	305.1	305.4	305.7	306.0
125°	336.7	336.6	336.4	336.3	336.4	336.6	336.7	336.8	337.1	337.5	337.8
127.5°	367.0	366.6	366.2	365.8	366.2	366.6	367.0	367.4	367.9	368.3	368.8
130°	388.5	388.0	387.5	387.0	387.5	388.0	388.5	389.0	389.4	389.7	389.9
132.5°	408.5	408.1	407.7	407.3	407.7	408.1	408.5	408.9	409.4	409.9	410.5
135°	440.0	439.6	439.2	438.8	439.2	439.6	440.0	440.3	440.6	440.7	440.9
137.5°	468.9	468.4	467.9	467.4	467.9	468.4	468.9	469.4	469.7	469.8	469.9
140°	488.7	488.2	487.7	487.2	487.7	488.2	488.7	489.3	489.5	489.5	489.5
142.5°	506.6	506.1	505.6	505.1	505.6	506.1	506.6	507.2	507.4	507.3	507.2
145°	533.6	533.1	532.6	532.1	532.6	533.1	533.6	534.1	534.3	534.2	534.1
147.5°	557.6	557.1	556.6	556.1	556.6	557.1	557.6	558.2	558.3	558.0	557.6
150°	573.0	572.6	572.2	571.9	572.2	572.6	573.0	573.4	573.4	573.0	572.6
152.5°	588.0	587.5	587.0	586.6	587.0	587.5	588.0	588.5	588.5	588.0	587.5
155°	607.5	607.1	606.7	606.4	606.7	607.1	607.5	607.9	607.8	607.1	606.5
157.5°	625.3	624.7	624.1	623.4	624.1	624.7	625.3	625.9	625.8	624.9	624.0
160°	635.6	635.1	634.5	634.0	634.5	635.1	635.6	636.1	635.9	635.2	634.4
162.5°	645.1	644.5	643.9	643.3	643.9	644.5	645.1	645.7	645.6	644.7	643.8
165°	657.2	656.6	656.0	655.3	656.0	656.6	657.2	657.9	657.7	656.9	656.0
167.5°	667.2	666.6	665.9	665.2	665.9	666.6	667.2	667.9	667.8	666.9	666.0
170°	672.6	671.9	671.1	670.3	671.1	671.9	672.6	673.4	673.3	672.5	671.6
172.5°	676.8	676.0	675.2	674.5	675.2	676.0	676.8	677.5	677.4	676.6	675.7
175°	681.3	680.4	679.7	678.9	679.7	680.4	681.3	682.1	682.0	681.1	680.1
177.5°	682.9	682.3	681.7	681.1	681.7	682.3	682.9	683.5	683.5	682.9	682.3
180°	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.9	637.4	641.3	643.5	647.1	649.5	650.9	653.2	654.5	659.1	663.9
5°	599.4	603.1	609.5	615.4	621.9	628.5	633.4	638.8	643.9	652.6	661.8
7.5°	558.8	563.8	573.8	583.3	594.5	603.9	612.2	621.6	630.0	642.5	655.5
10°	528.3	537.2	550.3	559.3	573.9	583.3	596.4	606.7	618.4	635.0	649.6
12.5°	502.0	512.8	523.3	535.7	549.0	564.6	579.0	592.3	606.1	623.2	640.5
15°	454.4	470.0	486.4	499.0	516.8	533.3	550.1	567.9	584.9	605.4	627.8
17.5°	393.1	411.2	438.6	460.2	481.2	497.8	518.6	540.2	560.2	584.8	609.9
20°	365.5	378.7	397.3	426.5	458.1	475.7	496.9	520.7	543.6	570.5	597.3
22.5°	343.3	355.1	369.9	392.6	428.0	452.1	474.1	498.4	524.9	552.3	582.1
25°	311.5	319.7	335.4	353.8	378.0	417.7	441.8	466.2	495.0	524.4	558.4
27.5°	287.7	295.2	305.3	322.8	340.8	369.4	407.7	434.2	463.0	496.0	531.3
30°	269.5	278.2	289.5	301.8	321.6	343.9	382.1	412.9	441.3	475.3	512.9
32.5°	256.3	263.2	272.8	285.4	301.7	323.2	353.8	391.0	418.8	454.5	493.8
35°	234.7	242.7	250.4	262.5	275.7	295.2	318.4	358.3	385.9	421.1	460.6
37.5°	216.8	221.8	230.4	239.8	253.9	268.4	288.5	324.3	354.1	388.7	429.1
40°	203.3	209.4	215.8	226.4	237.9	251.9	271.6	298.2	332.3	366.4	405.8
42.5°	190.1	197.8	204.7	211.8	224.3	238.3	254.4	276.9	311.8	344.0	382.3
45°	174.1	179.2	186.2	194.1	204.4	216.3	230.6	250.2	283.8	311.5	347.5
47.5°	155.6	163.0	167.6	175.2	185.0	196.4	209.6	226.7	253.8	279.8	313.3
50°	142.9	150.5	157.1	164.0	172.7	183.7	194.8	211.3	233.1	260.3	291.5
52.5°	132.1	138.8	145.2	152.1	160.7	170.7	181.2	195.7	214.3	239.4	269.7
55°	117.2	121.4	128.1	134.9	142.5	152.1	162.2	174.3	190.4	211.5	236.0
57.5°	102.0	106.7	112.0	119.0	126.6	134.0	143.1	154.1	166.7	185.8	206.8
60°	93.4	97.0	101.4	108.5	115.6	122.3	131.0	140.2	152.1	168.6	186.5
62.5°	83.8	87.4	91.3	97.5	104.4	110.5	118.2	127.8	137.9	153.0	168.6
65°	67.9	72.9	76.9	82.3	88.1	94.5	100.5	108.3	117.2	129.2	143.1
67.5°	56.2	58.9	62.5	67.5	73.3	78.9	84.5	90.6	98.4	107.6	118.7
70°	51.2	52.1	52.7	57.6	63.1	68.6	73.8	79.6	86.2	93.8	103.4
72.5°	45.1	46.0	46.9	49.0	53.3	58.9	64.3	68.6	74.8	81.2	89.0
75°	35.7	37.2	37.9	39.0	40.6	44.2	49.3	53.4	57.2	61.9	68.2
77.5°	27.3	28.1	28.8	30.0	31.0	32.6	35.5	39.2	42.7	45.4	49.7
80°	21.6	21.8	22.7	23.1	24.5	25.7	27.1	30.1	33.5	34.6	37.7
82.5°	16.3	16.5	17.2	17.7	18.3	19.3	21.0	21.8	24.5	26.1	27.9
85°	9.0	8.7	9.4	9.4	9.9	10.3	10.8	11.9	12.6	14.4	14.9
87.5°	6.8	6.8	6.4	5.9	5.3	5.0	4.8	4.7	4.7	5.0	5.5
90°	19.9	20.2	17.4	14.5	11.7	8.9	6.8	5.2	3.6	2.1	0.6
92.5°	18.4	18.3	17.7	17.0	16.4	15.7	14.7	13.6	12.5	11.4	10.3
95°	36.9	36.9	36.6	36.4	36.1	35.9	35.0	33.8	32.5	31.2	30.0
97.5°	62.0	62.0	61.5	61.0	60.5	60.0	59.2	58.1	57.0	55.8	54.7
100°	79.5	79.5	79.1	78.7	78.4	78.0	77.3	76.2	75.1	74.1	73.1
102.5°	98.5	98.4	97.9	97.4	96.9	96.4	95.7	94.9	94.1	93.3	92.5
105°	126.9	126.7	126.4	126.1	125.9	125.6	125.3	124.9	124.6	124.2	123.8
107.5°	158.0	157.9	157.9	157.9	157.9	157.9	157.6	157.0	156.5	155.9	155.4
110°	179.0	179.0	179.0	179.0	179.0	179.0	178.7	177.9	177.1	176.4	175.6



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	200.5	200.8	200.9	201.0	201.1	201.2	200.9	200.1	199.2	198.5	197.7
115°	232.6	232.7	232.9	233.2	233.4	233.7	233.4	232.7	231.9	231.2	230.4
117.5°	263.9	264.2	264.9	265.6	266.4	267.1	266.9	265.9	264.9	263.9	262.9
120°	284.5	284.5	285.5	286.5	287.5	288.6	288.6	287.5	286.5	285.5	284.5
122.5°	306.3	306.6	307.3	308.0	308.7	309.4	309.2	308.0	306.8	305.5	304.3
125°	338.2	338.6	339.0	339.4	339.7	340.1	339.7	338.6	337.5	336.3	335.2
127.5°	369.2	369.7	370.2	370.6	371.1	371.5	371.0	369.6	368.1	366.7	365.2
130°	390.2	390.4	390.7	390.9	391.2	391.4	390.7	389.1	387.4	385.8	384.2
132.5°	411.1	411.6	411.6	411.5	411.5	411.4	410.7	409.4	408.0	406.7	405.3
135°	441.0	441.1	440.9	440.6	440.3	440.1	439.3	437.9	436.5	435.0	433.6
137.5°	470.0	470.1	469.8	469.5	469.2	468.8	468.1	467.0	465.7	464.6	463.4
140°	489.5	489.5	488.9	488.2	487.6	487.0	486.0	484.8	483.7	482.6	481.4
142.5°	507.1	507.0	506.5	506.1	505.7	505.2	504.4	503.3	502.2	501.0	499.9
145°	533.9	533.8	533.1	532.3	531.5	530.8	530.0	529.1	528.2	527.3	526.3
147.5°	557.3	557.1	556.5	556.0	555.5	555.0	554.2	553.2	552.1	551.0	550.0
150°	572.2	571.9	571.3	570.8	570.3	569.8	569.2	568.4	567.6	566.8	566.1
152.5°	587.0	586.6	585.9	585.3	584.7	584.1	583.4	582.7	581.9	581.2	580.4
155°	605.9	605.2	604.8	604.5	604.1	603.7	603.3	602.9	602.6	602.2	601.8
157.5°	623.2	622.3	622.1	621.9	621.6	621.4	621.2	620.9	620.6	620.4	620.1
160°	633.7	632.9	632.8	632.6	632.5	632.4	632.2	631.9	631.7	631.4	631.2
162.5°	643.0	642.1	642.0	641.9	641.7	641.6	641.5	641.5	641.4	641.4	641.3
165°	655.1	654.2	654.2	654.2	654.2	654.2	654.3	654.4	654.5	654.6	654.8
167.5°	665.1	664.2	664.2	664.3	664.3	664.3	664.5	664.9	665.3	665.7	666.0
170°	670.7	669.7	669.8	669.9	670.1	670.2	670.6	670.9	671.3	671.7	672.1
172.5°	674.8	673.9	674.0	674.2	674.3	674.4	674.7	675.0	675.4	675.8	676.2
175°	679.2	678.3	678.6	678.9	679.1	679.4	679.7	680.1	680.4	680.9	681.3
177.5°	681.7	681.1	681.3	681.5	681.7	681.9	682.1	682.4	682.7	683.0	683.4
180°	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	664.1	664.6	668.2	669.9	673.2	674.5	676.0	675.6	675.6	676.3	681.5
5°	665.5	670.0	676.9	683.6	690.0	695.5	699.2	702.9	704.3	710.8	716.8
7.5°	663.1	671.6	682.9	693.1	705.2	714.7	722.6	729.7	734.6	744.3	754.2
10°	659.9	671.9	684.7	697.8	714.6	727.2	740.0	749.9	753.1	767.5	775.8
12.5°	653.7	669.6	686.0	703.0	719.3	736.7	750.8	760.7	772.0	785.0	800.2
15°	644.4	662.7	684.1	705.8	729.2	750.3	765.5	782.6	795.1	809.3	822.6
17.5°	631.0	654.6	681.7	706.9	734.0	756.6	777.5	794.0	802.6	810.8	812.7
20°	620.3	645.7	677.6	707.4	734.5	760.6	781.3	795.1	797.4	797.6	785.5
22.5°	608.7	637.5	670.9	701.4	733.8	762.9	778.9	784.8	775.7	760.1	736.6
25°	587.4	620.8	659.5	694.4	729.7	757.2	762.8	752.5	720.5	687.0	644.6
27.5°	564.4	601.9	643.4	682.2	719.8	736.9	725.0	687.7	630.4	580.4	519.9
30°	547.5	589.6	630.4	673.7	708.6	715.9	688.6	633.8	566.8	491.6	431.2
32.5°	528.3	572.3	617.1	662.0	691.2	684.0	638.9	571.4	492.9	418.9	361.9
35°	500.8	546.1	594.6	639.5	658.1	627.1	559.7	471.8	391.5	322.6	283.3
37.5°	469.0	518.5	568.8	610.1	608.7	557.1	465.2	374.6	307.1	266.2	238.3
40°	446.4	496.4	550.8	585.6	570.8	503.5	403.9	318.4	269.0	236.5	216.1
42.5°	424.7	474.9	529.0	556.6	530.7	448.1	348.9	281.9	241.2	215.8	199.2
45°	387.9	440.9	490.9	506.2	459.9	368.9	282.2	233.5	206.4	187.6	176.2
47.5°	351.8	404.0	449.7	449.9	387.3	299.1	238.0	202.1	178.9	164.4	156.1
50°	329.8	379.4	417.7	411.7	340.6	266.1	212.9	181.9	162.7	151.4	142.7
52.5°	305.1	353.1	386.4	369.4	301.1	234.2	190.3	164.3	148.3	138.6	130.8
55°	269.0	311.7	335.2	309.4	245.7	194.8	160.8	140.4	128.5	120.2	113.5
57.5°	233.7	268.9	283.6	253.7	202.4	161.5	136.0	120.7	108.9	102.9	99.5
60°	211.5	241.6	251.9	218.8	175.9	141.3	120.5	106.2	97.5	93.6	90.2
62.5°	189.7	214.2	218.4	188.2	153.4	123.7	105.7	93.7	88.0	84.2	81.0
65°	157.3	175.0	173.0	148.7	121.4	98.2	85.1	77.8	73.4	68.2	62.4
67.5°	129.6	140.4	133.8	115.6	92.6	76.3	67.8	62.2	56.8	51.8	50.5
70°	111.9	118.2	111.3	94.5	75.9	64.0	57.2	50.5	47.3	46.2	44.0
72.5°	95.0	97.3	89.8	75.4	61.8	53.0	46.3	42.6	40.8	39.9	38.6
75°	71.3	69.8	63.3	52.1	42.9	37.0	34.8	33.5	32.3	31.4	30.7
77.5°	50.1	47.8	42.0	34.6	29.9	27.1	25.8	25.0	24.5	24.0	23.3
80°	37.7	36.1	30.3	24.7	22.7	21.3	20.6	19.7	19.7	19.3	18.6
82.5°	27.6	25.8	20.7	18.2	17.1	16.2	15.7	15.1	14.9	15.0	14.5
85°	14.4	11.7	10.3	9.9	9.2	8.7	9.0	8.5	8.5	8.5	8.3
87.5°	4.8	4.2	4.3	4.4	5.0	5.7	6.1	6.6	7.4	7.1	7.3
90°	2.1	3.6	5.2	6.8	8.9	11.7	14.5	17.4	20.2	19.9	19.7
92.5°	11.4	12.5	13.6	14.7	15.7	16.4	17.0	17.7	18.3	18.4	18.4
95°	31.2	32.5	33.8	35.0	35.9	36.1	36.4	36.6	36.9	36.9	36.9
97.5°	55.8	57.0	58.1	59.2	60.0	60.5	61.0	61.5	62.0	62.0	62.0
100°	74.1	75.1	76.2	77.3	78.0	78.4	78.7	79.1	79.5	79.5	79.5
102.5°	93.3	94.1	94.9	95.7	96.4	96.9	97.4	97.9	98.4	98.5	98.6
105°	124.2	124.6	124.9	125.3	125.6	125.9	126.1	126.4	126.7	126.9	127.2
107.5°	155.9	156.5	157.0	157.6	157.9	157.9	157.9	157.9	157.9	158.0	158.1
110°	176.4	177.1	177.9	178.7	179.0	179.0	179.0	179.0	179.0	179.0	179.0





TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	198.5	199.2	200.1	200.9	201.2	201.1	201.0	200.9	200.8	200.5	200.2
115°	231.2	231.9	232.7	233.4	233.7	233.4	233.2	232.9	232.7	232.6	232.4
117.5°	263.9	264.9	265.9	266.9	267.1	266.4	265.6	264.9	264.2	263.9	263.6
120°	285.5	286.5	287.5	288.6	288.6	287.5	286.5	285.5	284.5	284.5	284.5
122.5°	305.5	306.8	308.0	309.2	309.4	308.7	308.0	307.3	306.6	306.3	306.0
125°	336.3	337.5	338.6	339.7	340.1	339.7	339.4	339.0	338.6	338.2	337.8
127.5°	366.7	368.1	369.6	371.0	371.5	371.1	370.6	370.2	369.7	369.2	368.8
130°	385.8	387.4	389.1	390.7	391.4	391.2	390.9	390.7	390.4	390.2	389.9
132.5°	406.7	408.0	409.4	410.7	411.4	411.5	411.5	411.6	411.6	411.1	410.5
135°	435.0	436.5	437.9	439.3	440.1	440.3	440.6	440.9	441.1	441.0	440.9
137.5°	464.6	465.7	467.0	468.1	468.8	469.2	469.5	469.8	470.1	470.0	469.9
140°	482.6	483.7	484.8	486.0	487.0	487.6	488.2	488.9	489.5	489.5	489.5
142.5°	501.0	502.2	503.3	504.4	505.2	505.7	506.1	506.5	507.0	507.1	507.2
145°	527.3	528.2	529.1	530.0	530.8	531.5	532.3	533.1	533.8	533.9	534.1
147.5°	551.0	552.1	553.2	554.2	555.0	555.5	556.0	556.5	557.1	557.3	557.6
150°	566.8	567.6	568.4	569.2	569.8	570.3	570.8	571.3	571.9	572.2	572.6
152.5°	581.2	581.9	582.7	583.4	584.1	584.7	585.3	585.9	586.6	587.0	587.5
155°	602.2	602.6	602.9	603.3	603.7	604.1	604.5	604.8	605.2	605.9	606.5
157.5°	620.4	620.6	620.9	621.2	621.4	621.6	621.9	622.1	622.3	623.2	624.0
160°	631.4	631.7	631.9	632.2	632.4	632.5	632.6	632.8	632.9	633.7	634.4
162.5°	641.4	641.4	641.5	641.5	641.6	641.7	641.9	642.0	642.1	643.0	643.8
165°	654.6	654.5	654.4	654.3	654.2	654.2	654.2	654.2	654.2	655.1	656.0
167.5°	665.7	665.3	664.9	664.5	664.3	664.3	664.3	664.2	664.2	665.1	666.0
170°	671.7	671.3	670.9	670.6	670.2	670.1	669.9	669.8	669.7	670.7	671.6
172.5°	675.8	675.4	675.0	674.7	674.4	674.3	674.2	674.0	673.9	674.8	675.7
175°	680.9	680.4	680.1	679.7	679.4	679.1	678.9	678.6	678.3	679.2	680.1
177.5°	683.0	682.7	682.4	682.1	681.9	681.7	681.5	681.3	681.1	681.7	682.3
180°	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	683.3	685.7	686.8	686.8	688.1	687.5	687.0
5°	722.6	726.9	727.9	732.0	735.0	734.1	734.5
7.5°	761.6	768.6	775.6	778.7	779.2	781.0	781.7
10°	785.7	791.4	802.1	800.6	808.6	813.2	805.7
12.5°	808.8	816.6	824.0	826.1	830.6	832.1	829.1
15°	829.7	833.8	834.2	833.1	834.6	833.3	829.0
17.5°	810.2	803.4	789.9	783.5	778.4	770.8	767.8
20°	777.9	758.1	735.2	726.0	715.3	694.2	699.2
22.5°	708.1	685.7	662.7	635.9	623.1	603.1	601.9
25°	599.7	560.9	518.2	488.4	470.9	451.0	442.2
27.5°	466.3	417.4	382.4	364.8	348.6	332.9	332.1
30°	378.5	341.8	314.8	299.6	289.7	283.1	284.5
32.5°	319.0	293.9	275.6	263.1	255.8	250.7	250.6
35°	260.8	243.6	231.9	226.6	221.4	217.7	217.9
37.5°	223.2	212.9	206.3	200.6	197.2	195.4	194.4
40°	203.9	195.4	190.4	186.9	184.2	181.7	181.2
42.5°	188.7	181.7	176.6	173.9	171.4	169.6	169.2
45°	167.4	161.7	157.1	154.1	153.0	151.4	151.4
47.5°	149.0	143.3	139.8	137.8	135.9	134.8	134.8
50°	136.5	132.1	129.0	127.7	126.1	125.5	125.2
52.5°	125.3	122.0	119.8	119.0	118.3	117.4	117.5
55°	110.1	108.3	107.3	106.6	105.5	104.1	105.0
57.5°	97.4	95.7	93.3	91.1	90.1	89.1	89.5
60°	88.4	85.1	81.9	79.4	78.7	76.6	76.6
62.5°	77.0	72.4	68.5	67.1	66.3	65.4	65.2
65°	59.2	57.4	56.5	55.5	55.0	55.0	54.6
67.5°	49.1	48.3	47.3	47.1	46.7	46.5	46.4
70°	43.3	42.4	42.0	41.7	41.3	41.5	40.8
72.5°	37.9	37.2	37.1	36.5	36.2	36.2	35.6
75°	29.8	29.8	29.6	29.4	28.9	28.7	28.9
77.5°	22.9	23.0	22.6	22.5	22.5	22.5	22.3
80°	18.4	18.6	18.4	18.1	17.9	18.1	17.9
82.5°	14.5	14.1	14.1	14.0	14.0	13.9	13.8
85°	8.3	8.5	8.3	8.1	8.1	8.1	8.3
87.5°	7.0	7.0	7.0	7.0	7.0	7.0	6.9
90°	19.4	19.1	19.1	19.2	19.3	19.5	19.6
92.5°	18.5	18.5	18.6	18.6	18.6	18.7	18.7
95°	36.9	36.9	36.8	36.5	36.3	36.0	35.7
97.5°	62.0	62.0	61.9	61.9	61.9	61.9	61.8
100°	79.5	79.5	79.4	79.3	79.2	79.1	78.9
102.5°	98.7	98.8	98.8	98.7	98.5	98.4	98.3
105°	127.4	127.7	127.8	127.8	127.8	127.8	127.8
107.5°	158.2	158.3	158.0	157.4	156.9	156.3	155.7
110°	179.0	179.0	178.9	178.5	178.1	177.7	177.3



TEST NUMBER: P331622-840

CATALOG NUMBER: S122RDIP-S290D530U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	199.9	199.5	199.2	198.9	198.6	198.3	198.1
115°	232.3	232.2	231.9	231.5	231.2	230.8	230.4
117.5°	263.3	263.0	262.7	262.3	261.9	261.5	261.1
120°	284.5	284.5	284.3	283.9	283.6	283.2	282.8
122.5°	305.7	305.4	305.1	304.8	304.5	304.3	304.0
125°	337.5	337.1	336.8	336.7	336.6	336.4	336.3
127.5°	368.3	367.9	367.4	367.0	366.6	366.2	365.8
130°	389.7	389.4	389.0	388.5	388.0	387.5	387.0
132.5°	409.9	409.4	408.9	408.5	408.1	407.7	407.3
135°	440.7	440.6	440.3	440.0	439.6	439.2	438.8
137.5°	469.8	469.7	469.4	468.9	468.4	467.9	467.4
140°	489.5	489.5	489.3	488.7	488.2	487.7	487.2
142.5°	507.3	507.4	507.2	506.6	506.1	505.6	505.1
145°	534.2	534.3	534.1	533.6	533.1	532.6	532.1
147.5°	558.0	558.3	558.2	557.6	557.1	556.6	556.1
150°	573.0	573.4	573.4	573.0	572.6	572.2	571.9
152.5°	588.0	588.5	588.5	588.0	587.5	587.0	586.6
155°	607.1	607.8	607.9	607.5	607.1	606.7	606.4
157.5°	624.9	625.8	625.9	625.3	624.7	624.1	623.4
160°	635.2	635.9	636.1	635.6	635.1	634.5	634.0
162.5°	644.7	645.6	645.7	645.1	644.5	643.9	643.3
165°	656.9	657.7	657.9	657.2	656.6	656.0	655.3
167.5°	666.9	667.8	667.9	667.2	666.6	665.9	665.2
170°	672.5	673.3	673.4	672.6	671.9	671.1	670.3
172.5°	676.6	677.4	677.5	676.8	676.0	675.2	674.5
175°	681.1	682.0	682.1	681.3	680.4	679.7	678.9
177.5°	682.9	683.5	683.5	682.9	682.3	681.7	681.1
180°	682.4	682.4	682.4	682.4	682.4	682.4	682.4

(END OF REPORT)