

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331647-840

Luminaire Tested: **S122RDIP-S485D330U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331647-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D330U840-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3168.5 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	101	97	93	90	94	91	87	85	79	77	75	68	67	65	59	57	56	52
2	93	86	80	75	86	80	75	71	70	67	63	61	58	56	53	51	49	45
3	85	76	69	64	79	72	66	61	63	58	54	55	52	49	48	45	43	39
4	78	68	61	55	73	64	58	52	57	52	47	50	46	43	43	40	38	35
5	72	61	54	48	68	58	51	46	51	46	42	45	41	38	40	36	34	31
6	67	56	48	42	63	53	46	41	47	41	37	41	37	34	36	33	30	28
7	62	51	43	38	58	48	41	36	43	37	33	38	34	30	34	30	27	25
8	58	46	39	34	55	44	37	33	39	34	30	35	31	27	31	28	25	23
9	55	43	35	31	51	41	34	29	36	31	27	33	28	25	29	25	23	21
10	51	39	32	28	48	38	31	27	34	29	25	30	26	23	27	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17525	17525	17525	17525
5°	19571	17634	15635	17634
10°	21713	17510	13554	17510
15°	22781	17254	10678	17254
20°	19749	16873	9241	16873
25°	12953	16352	8250	16352
30°	8720	15720	7467	15720
35°	7062	14927	6733	14927
40°	6279	14060	6232	14060
45°	5683	13047	5562	13047
50°	5172	12039	5152	12039
55°	4861	10925	4799	10925
60°	4066	9901	4017	9901
65°	3431	8989	3889	8989
70°	3172	8030	3668	8030
75°	2969	6987	3387	6987
80°	2734	5746	3013	5746
85°	2501	4539	2649	4539



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.9	3.2
10°-20°	286.7	9.0
20°-30°	369.4	11.7
30°-40°	351.1	11.1
40°-50°	300.7	9.5
50°-60°	229.0	7.2
60°-70°	144.8	4.6
70°-80°	72.3	2.3
80°-90°	20.5	0.6
90°-100°	74.2	2.3
100°-110°	251.8	7.9
110°-120°	267.5	8.4
120°-130°	220.2	6.9
130°-140°	176.8	5.6
140°-150°	133.6	4.2
150°-160°	93.9	3.0
160°-170°	55.3	1.7
170°-180°	18.0	0.6
0°-30°	759.0	24.0
0°-40°	1110.1	35.0
0°-60°	1639.8	51.8
0°-90°	1877.4	59.3
90°-120°	593.4	18.7
90°-150°	1124.0	35.5
90°-180°	1291.0	40.7
0°-180°	3168.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1085	1085	1085	1085	1085	
5°	1208	1088	965	1088	1208	119
15°	1363	1032	639	1032	1363	368
25°	727	918	463	918	727	345
35°	358	757	342	757	358	229
45°	249	571	244	571	249	193
55°	173	388	170	388	173	152
65°	90	235	102	235	90	91
75°	48	112	54	112	48	50
85°	14	24	14	24	14	15
90°	12	0	12	0	12	7
95°	41	12	41	12	41	53
105°	402	44	402	44	402	389
115°	529	77	529	77	529	518
125°	429	107	429	107	429	388
135°	356	126	356	126	356	276
145°	284	143	284	143	284	180
155°	239	163	239	163	239	111
165°	209	178	209	178	209	60
175°	189	185	189	185	189	18
180°	186	186	186	186	186	



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1129.4	1130.3	1131.3	1129.1	1129.1	1127.3	1123.4	1120.3	1111.9	1110.6	1110.6
5°	1207.5	1206.8	1208.3	1203.4	1196.6	1195.1	1187.9	1178.5	1168.7	1157.7	1155.5
7.5°	1285.3	1284.1	1281.1	1280.2	1275.1	1263.6	1252.1	1239.8	1223.6	1207.6	1199.6
10°	1324.4	1336.9	1329.4	1316.2	1318.8	1301.1	1291.6	1275.5	1261.8	1238.1	1232.8
12.5°	1363.0	1368.0	1365.5	1358.1	1354.7	1342.4	1329.7	1315.6	1290.5	1269.2	1250.6
15°	1362.9	1370.1	1372.0	1369.7	1371.6	1370.8	1364.0	1352.3	1330.5	1307.1	1286.8
17.5°	1262.3	1267.3	1279.6	1288.0	1298.6	1320.9	1331.9	1336.3	1332.9	1319.6	1305.3
20°	1149.4	1141.1	1175.9	1193.6	1208.7	1246.4	1278.8	1291.2	1311.2	1310.9	1307.1
22.5°	989.6	991.5	1024.4	1045.4	1089.5	1127.2	1164.2	1211.0	1249.7	1275.3	1290.2
25°	727.1	741.4	774.3	802.8	851.9	922.1	985.8	1059.8	1129.4	1184.6	1237.0
27.5°	546.0	547.1	573.1	599.7	628.7	686.2	766.5	854.7	954.2	1036.2	1130.6
30°	467.7	465.3	476.4	492.5	517.5	561.9	622.3	709.0	808.2	931.9	1042.0
32.5°	412.1	412.2	420.5	432.5	453.1	483.1	524.5	594.9	688.7	810.3	939.4
35°	358.3	357.9	364.0	372.6	381.2	400.5	428.8	465.7	530.3	643.8	775.8
37.5°	319.6	321.3	324.3	329.7	339.2	349.9	367.0	391.7	437.7	504.8	615.7
40°	297.9	298.7	302.9	307.4	313.1	321.3	335.3	355.3	388.8	442.3	523.4
42.5°	278.0	278.7	281.8	285.9	290.3	298.7	310.2	327.5	354.8	396.5	463.4
45°	248.9	248.9	251.6	253.4	258.3	265.9	275.3	289.6	308.5	339.4	384.0
47.5°	221.6	221.7	223.4	226.6	229.7	235.6	244.9	256.6	270.3	294.3	332.2
50°	205.9	206.3	207.4	210.1	212.0	217.2	224.4	234.6	248.9	267.4	299.0
52.5°	193.2	193.0	194.4	195.6	196.8	200.7	206.0	215.0	227.8	243.9	270.1
55°	172.7	171.2	173.5	175.3	176.5	178.0	181.0	186.7	197.6	211.2	230.8
57.5°	147.0	146.4	148.0	149.8	153.3	157.4	160.0	163.6	169.3	178.9	198.4
60°	125.9	125.9	129.4	130.5	134.6	139.9	145.2	148.2	153.9	160.3	174.6
62.5°	107.2	107.6	109.2	110.3	112.6	119.1	126.5	133.1	138.5	144.6	154.1
65°	89.8	90.5	90.5	91.3	92.8	94.3	97.3	102.6	112.0	120.7	127.8
67.5°	76.1	76.4	76.6	77.4	77.8	79.4	80.6	83.0	85.1	93.4	102.3
70°	67.2	68.3	67.9	68.7	69.0	69.8	71.3	72.4	75.8	77.7	83.0
72.5°	58.7	59.5	59.5	59.9	60.9	61.0	62.2	63.3	65.5	67.2	70.0
75°	47.6	47.2	47.6	48.3	48.7	49.0	49.0	50.5	51.7	53.2	55.0
77.5°	36.7	37.1	37.0	37.1	37.1	37.8	37.7	38.4	39.5	40.3	41.2
80°	29.4	29.8	29.4	29.8	30.2	30.5	30.2	30.5	31.7	32.4	32.4
82.5°	22.8	22.8	23.1	23.1	23.2	23.3	23.8	23.9	24.7	24.5	24.8
85°	13.5	13.2	13.2	13.2	13.5	13.9	13.5	13.5	13.9	13.9	13.9
87.5°	7.2	7.5	7.5	7.5	7.5	7.4	7.3	7.7	7.5	7.9	7.5
90°	11.8	11.8	11.8	11.8	11.8	11.4	10.7	11.4	11.8	12.1	11.8
92.5°	19.8	20.3	20.1	21.2	21.5	23.7	26.7	31.1	39.2	46.4	45.7
95°	40.7	40.3	41.4	44.2	48.9	56.8	71.7	93.5	122.4	139.9	123.8
97.5°	80.1	83.1	88.3	97.0	114.1	139.9	178.4	218.1	250.4	238.7	179.9
100°	127.7	134.2	144.5	159.9	189.5	232.7	281.6	325.8	333.3	281.9	194.1
102.5°	224.8	233.5	246.4	272.6	304.8	350.5	386.3	396.3	364.1	283.3	188.6
105°	402.1	407.1	422.4	444.5	466.8	478.5	473.8	433.5	359.3	264.4	178.0
107.5°	513.7	520.3	523.4	524.6	521.8	504.5	467.5	406.7	328.0	244.1	172.8
110°	547.3	547.8	544.5	537.8	522.4	493.1	447.5	383.5	308.3	234.4	171.7



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	546.7	544.8	538.8	527.5	506.1	472.5	423.7	362.4	294.6	228.1	171.9
115°	529.2	525.9	516.6	500.3	474.9	438.2	391.4	336.5	277.6	221.3	173.4
117.5°	497.7	494.9	485.2	467.9	442.0	407.6	365.2	316.9	266.9	217.8	176.0
120°	477.5	473.8	463.5	446.8	421.7	389.3	351.4	307.2	261.2	215.9	177.7
122.5°	456.3	453.3	444.1	427.6	405.2	375.9	340.0	299.5	256.3	214.7	179.7
125°	429.3	426.4	417.5	403.9	383.2	356.5	325.1	288.3	249.4	212.7	182.7
127.5°	405.6	403.2	395.6	382.8	364.8	340.1	310.5	277.2	243.0	211.5	185.7
130°	392.1	389.3	382.1	370.0	352.5	329.0	300.8	270.1	238.7	210.9	188.0
132.5°	378.2	375.6	369.0	356.9	339.7	317.6	291.6	263.3	235.3	210.6	190.4
135°	355.8	354.4	347.9	336.1	320.7	300.8	277.2	253.7	230.5	210.2	193.1
137.5°	333.8	331.6	326.0	315.9	301.8	284.5	265.8	246.1	227.1	210.1	195.5
140°	318.6	316.5	311.1	301.8	290.4	274.8	258.3	241.2	225.1	209.8	196.6
142.5°	303.5	303.1	298.3	289.8	279.0	265.9	251.8	237.2	223.2	209.8	197.4
145°	284.0	283.0	279.4	273.3	264.8	254.4	243.4	231.6	220.6	209.0	198.3
147.5°	267.7	267.0	264.6	259.7	252.7	245.1	236.5	227.2	217.8	207.8	198.6
150°	258.0	257.6	255.5	251.2	245.8	239.4	232.0	224.1	215.5	206.9	198.3
152.5°	249.7	249.6	248.0	244.4	240.1	234.6	228.2	221.0	213.5	205.5	197.8
155°	238.7	239.4	238.0	235.5	231.6	227.6	222.3	216.6	209.8	203.0	196.9
157.5°	229.3	229.3	228.7	226.6	223.9	220.8	216.3	211.6	206.3	200.5	195.3
160°	223.4	223.4	223.0	221.3	218.7	216.2	212.3	208.3	203.7	198.7	194.5
162.5°	217.6	217.9	217.6	216.4	213.9	212.0	208.6	205.2	201.5	197.3	193.6
165°	209.4	209.8	209.8	208.3	206.9	205.5	203.0	200.6	197.6	194.5	192.0
167.5°	201.9	202.3	202.4	201.6	201.0	199.7	197.9	196.0	194.0	192.0	190.4
170°	197.3	198.0	198.3	197.3	196.9	196.2	194.8	193.8	192.0	190.6	189.5
172.5°	193.6	194.0	194.4	193.9	193.5	193.1	192.0	191.2	190.0	188.8	188.3
175°	188.7	189.5	189.9	189.5	189.5	189.1	188.7	188.4	187.3	186.9	186.6
177.5°	185.8	186.4	186.7	186.7	186.7	186.7	186.4	186.4	185.8	185.5	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1111.3	1108.9	1106.8	1101.4	1098.6	1092.6	1091.7	1091.4	1083.6	1076.0	1073.9
5°	1149.4	1143.5	1134.4	1123.8	1112.9	1101.6	1094.0	1088.0	1072.9	1058.5	1050.3
7.5°	1187.9	1175.0	1159.3	1139.3	1122.7	1104.0	1090.1	1077.6	1056.2	1035.7	1021.9
10°	1216.6	1195.5	1174.8	1147.2	1125.7	1104.6	1085.0	1068.0	1043.9	1016.7	997.4
12.5°	1234.4	1211.1	1182.6	1155.7	1127.8	1101.0	1074.7	1052.9	1024.6	996.5	973.6
15°	1258.5	1233.6	1198.9	1160.4	1124.6	1089.5	1059.3	1032.2	995.2	961.7	933.7
17.5°	1278.2	1243.9	1206.6	1162.2	1120.6	1076.1	1037.2	1002.5	961.4	920.9	888.1
20°	1284.4	1250.5	1207.5	1163.1	1114.0	1061.6	1019.8	982.0	937.9	893.7	856.1
22.5°	1280.5	1254.2	1206.3	1153.1	1102.9	1048.0	1000.8	956.9	908.1	863.0	819.3
25°	1253.9	1244.9	1199.6	1141.6	1084.2	1020.5	965.8	917.9	862.1	813.9	766.3
27.5°	1191.8	1211.4	1183.4	1121.5	1057.7	989.4	928.0	873.4	815.5	761.1	713.8
30°	1132.2	1177.0	1164.9	1107.6	1036.3	969.2	900.2	843.2	781.4	725.6	678.8
32.5°	1050.4	1124.5	1136.3	1088.3	1014.6	940.8	868.5	811.8	747.3	688.4	642.9
35°	920.2	1031.1	1082.0	1051.4	977.4	898.0	823.2	757.3	692.4	634.3	589.1
37.5°	764.9	915.8	1000.8	1002.9	935.0	852.3	771.0	705.5	639.0	582.1	533.1
40°	664.1	827.8	938.3	962.8	905.4	816.1	733.9	667.1	602.3	546.4	490.3
42.5°	573.6	736.7	872.5	915.1	869.6	780.8	698.3	628.5	565.4	512.6	455.2
45°	463.8	606.4	756.1	832.3	807.1	724.8	637.7	571.4	512.1	466.5	411.4
47.5°	391.3	491.8	636.6	739.7	739.2	664.2	578.6	514.9	460.0	417.3	372.6
50°	349.9	437.5	560.1	676.9	686.7	623.8	542.3	479.3	428.1	383.1	347.3
52.5°	312.9	385.0	495.1	607.2	635.1	580.6	501.6	443.4	393.6	352.3	321.6
55°	264.4	320.1	403.9	508.8	551.0	512.5	442.3	388.1	347.7	313.1	286.6
57.5°	223.6	265.5	332.6	417.1	466.3	442.0	384.3	340.1	305.6	274.2	253.4
60°	198.0	232.3	289.2	359.8	414.0	397.1	347.7	306.6	277.2	250.0	230.5
62.5°	173.9	203.4	252.2	309.4	359.2	352.1	311.8	277.3	251.6	226.8	210.3
65°	139.9	161.4	199.4	244.4	284.4	287.7	258.7	235.3	212.3	192.7	178.0
67.5°	111.4	125.4	152.3	190.1	220.0	230.8	213.0	195.1	176.8	161.7	149.0
70°	93.9	105.2	124.8	155.4	182.9	194.2	184.0	170.1	154.2	141.8	130.9
72.5°	76.1	87.2	101.6	124.0	147.6	159.9	156.3	146.2	133.4	123.1	112.8
75°	57.4	60.7	70.5	85.6	104.1	114.6	117.2	112.0	101.8	93.9	87.9
77.5°	42.4	44.4	49.1	57.1	69.1	78.5	82.4	81.8	74.7	70.2	64.5
80°	33.9	35.0	37.4	40.7	49.8	59.2	61.8	61.8	57.0	55.0	49.4
82.5°	25.8	26.7	28.0	29.9	34.1	42.3	45.2	45.8	42.7	40.3	35.9
85°	14.7	14.3	15.0	16.3	17.0	19.2	23.7	24.5	23.7	20.7	19.6
87.5°	7.1	6.9	6.5	6.0	6.2	6.3	7.6	8.8	7.9	7.2	6.8
90°	9.6	7.2	5.4	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	35.6	24.2	16.2	12.8	10.4	8.9	6.3	4.3	6.3	8.9	10.4
95°	82.4	51.4	34.9	26.4	20.7	17.5	13.9	12.5	13.9	17.5	20.7
97.5°	111.1	67.8	47.2	37.5	30.9	26.1	22.2	20.3	22.2	26.1	30.9
100°	117.0	73.5	54.6	44.6	37.5	31.7	28.6	27.5	28.6	31.7	37.5
102.5°	117.3	78.7	61.2	51.2	43.7	38.1	34.8	34.0	34.8	38.1	43.7
105°	119.2	87.5	70.7	60.7	52.8	47.5	44.9	43.5	44.9	47.5	52.8
107.5°	124.1	96.4	80.2	70.1	62.3	57.4	54.9	53.8	54.9	57.4	62.3
110°	128.1	102.4	86.7	76.3	68.9	64.2	62.1	60.7	62.1	64.2	68.9



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	132.4	108.2	93.0	82.3	75.1	70.8	68.4	67.0	68.4	70.8	75.1
115°	138.8	117.0	101.7	92.1	84.9	80.7	78.5	76.7	78.5	80.7	84.9
117.5°	145.6	125.2	111.1	101.1	94.2	90.4	88.3	86.8	88.3	90.4	94.2
120°	150.3	131.0	117.0	107.0	99.9	96.7	94.5	93.1	94.5	96.7	99.9
122.5°	154.2	136.3	123.3	113.0	105.9	102.4	100.3	99.2	100.3	102.4	105.9
125°	160.6	144.5	131.7	121.7	114.5	110.3	108.2	107.0	108.2	110.3	114.5
127.5°	166.5	152.1	139.6	129.3	122.5	117.8	114.7	113.3	114.7	117.8	122.5
130°	170.2	156.6	144.1	134.2	127.0	122.0	118.5	117.0	118.5	122.0	127.0
132.5°	173.9	160.7	148.8	138.8	131.3	126.0	122.2	120.5	122.2	126.0	131.3
135°	178.7	166.3	154.8	144.9	136.6	131.3	127.0	125.6	127.0	131.3	136.6
137.5°	182.5	170.9	159.6	150.3	142.2	136.4	132.2	130.5	132.2	136.4	142.2
140°	184.5	173.4	162.7	153.4	145.6	139.9	135.6	134.2	135.6	139.9	145.6
142.5°	186.2	175.4	165.0	156.3	148.8	143.0	139.1	137.8	139.1	143.0	148.8
145°	188.4	178.4	168.7	161.0	153.8	148.5	144.9	143.4	144.9	148.5	153.8
147.5°	189.7	180.9	171.8	164.8	158.9	153.9	150.5	149.5	150.5	153.9	158.9
150°	190.2	182.0	173.8	167.3	162.0	157.3	154.5	153.4	154.5	157.3	162.0
152.5°	190.5	183.1	175.7	170.0	164.8	160.8	157.9	157.4	157.9	160.8	164.8
155°	190.9	184.8	178.7	173.4	169.5	165.5	163.4	163.1	163.4	165.5	169.5
157.5°	190.9	186.0	180.9	176.4	173.3	169.9	168.1	167.7	168.1	169.9	173.3
160°	190.9	186.6	182.4	178.4	175.5	172.7	171.3	170.9	171.3	172.7	175.5
162.5°	190.6	186.9	183.2	180.2	177.5	175.3	173.8	174.1	173.8	175.3	177.5
165°	189.9	187.3	184.1	182.0	180.2	178.0	177.3	177.7	177.3	178.0	180.2
167.5°	189.3	187.2	184.9	183.6	182.3	180.9	180.3	180.7	180.3	180.9	182.3
170°	188.7	186.9	185.2	184.1	183.4	182.4	182.0	182.7	182.0	182.4	183.4
172.5°	187.9	186.7	185.5	184.7	184.3	183.2	183.4	183.8	183.4	183.2	184.3
175°	186.9	186.2	185.5	185.2	185.2	184.5	184.8	185.2	184.8	184.5	185.2
177.5°	186.4	185.8	185.5	185.5	185.5	185.0	185.2	185.8	185.2	185.0	185.5
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1070.0	1067.8	1063.9	1057.9	1054.3	1047.9	1043.7	1046.1	1046.7	1046.1	1045.5
5°	1041.3	1033.3	1022.4	1011.8	1002.0	991.5	985.4	982.8	977.4	974.5	973.0
7.5°	1006.4	992.8	977.3	959.0	943.3	927.0	918.6	914.4	903.6	897.8	892.6
10°	980.5	959.0	943.5	919.4	904.7	883.2	868.5	868.9	854.1	845.9	839.8
12.5°	951.9	928.3	902.5	880.8	860.4	843.1	825.4	818.2	802.5	794.6	778.3
15°	904.3	876.8	849.7	820.2	799.5	772.7	747.1	715.8	690.5	668.6	662.6
17.5°	852.4	818.4	791.1	756.6	721.0	676.0	646.3	628.1	612.9	601.4	592.8
20°	816.9	782.1	753.2	701.0	653.2	622.6	600.8	586.8	571.0	558.6	551.7
22.5°	779.4	743.3	703.7	645.5	608.2	583.7	564.2	548.2	537.5	527.8	521.6
25°	726.3	686.7	621.5	581.5	551.4	525.7	512.1	502.3	491.0	477.8	471.8
27.5°	670.2	607.2	560.4	530.7	501.9	485.2	473.0	458.4	448.3	442.3	436.1
30°	628.2	565.3	528.8	496.2	475.9	457.5	443.1	434.8	425.1	414.9	410.7
32.5°	581.5	531.2	496.1	469.2	448.5	432.7	421.4	408.0	400.9	394.7	386.0
35°	523.4	485.3	453.3	431.4	411.8	399.0	385.8	377.9	365.1	359.8	356.4
37.5°	474.2	441.2	417.3	394.3	378.7	364.6	356.5	343.9	338.3	330.9	323.8
40°	446.5	414.0	391.1	372.2	354.9	344.3	334.2	324.0	315.7	312.3	303.6
42.5°	418.2	391.7	368.7	348.1	336.5	325.3	312.5	305.0	296.3	290.8	285.5
45°	379.0	355.7	336.0	319.0	306.2	294.6	286.2	273.8	268.9	257.9	253.4
47.5°	344.6	322.9	304.2	288.0	275.5	267.9	255.8	246.0	238.2	231.5	225.7
50°	320.1	302.1	284.0	269.6	258.3	247.4	235.0	230.0	217.9	214.6	211.2
52.5°	297.8	280.6	264.1	250.0	238.7	228.1	217.1	210.8	202.6	199.1	196.7
55°	266.6	250.0	234.2	221.8	210.5	199.4	192.7	184.8	181.0	178.3	175.3
57.5°	235.2	220.4	208.1	195.6	184.2	175.5	167.6	162.9	159.0	155.5	151.9
60°	215.3	201.0	190.1	178.3	166.7	159.6	153.5	147.8	143.3	138.0	136.5
62.5°	194.2	181.7	171.7	160.3	150.1	143.5	137.8	132.5	127.0	119.4	117.2
65°	165.2	155.4	144.8	135.4	126.3	120.0	111.6	105.6	103.3	102.6	102.2
67.5°	139.0	129.7	120.6	111.0	102.7	96.7	92.5	91.6	90.1	89.6	88.6
70°	121.4	112.8	103.7	94.6	86.7	85.6	84.1	82.6	80.7	80.0	79.2
72.5°	105.7	96.7	87.8	80.5	77.1	75.6	74.1	72.6	71.4	70.6	70.2
75°	81.1	72.8	66.8	64.1	62.2	61.1	58.9	57.7	57.0	55.8	55.4
77.5°	58.4	53.7	50.9	49.3	47.3	46.0	44.8	43.6	42.8	42.6	42.0
80°	44.5	42.2	40.4	38.1	37.4	35.9	35.4	34.3	34.7	33.5	33.5
82.5°	34.5	31.7	30.1	29.1	28.3	27.1	26.7	26.2	26.3	25.4	25.4
85°	17.8	17.0	16.3	15.5	15.5	14.3	14.7	14.3	14.3	13.5	13.2
87.5°	6.6	6.5	6.3	6.8	7.2	7.0	6.9	6.5	6.4	6.5	6.3
90°	4.2	5.4	7.2	9.6	11.8	12.1	11.8	11.4	10.7	11.4	11.8
92.5°	12.8	16.2	24.2	35.6	45.7	46.4	39.2	31.1	26.7	23.7	21.5
95°	26.4	34.9	51.4	82.4	123.8	139.9	122.4	93.5	71.7	56.8	48.9
97.5°	37.5	47.2	67.8	111.1	179.9	238.7	250.4	218.1	178.4	139.9	114.1
100°	44.6	54.6	73.5	117.0	194.1	281.9	333.3	325.8	281.6	232.7	189.5
102.5°	51.2	61.2	78.7	117.3	188.6	283.3	364.1	396.3	386.3	350.5	304.8
105°	60.7	70.7	87.5	119.2	178.0	264.4	359.3	433.5	473.8	478.5	466.8
107.5°	70.1	80.2	96.4	124.1	172.8	244.1	328.0	406.7	467.5	504.5	521.8
110°	76.3	86.7	102.4	128.1	171.7	234.4	308.3	383.5	447.5	493.1	522.4



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	82.3	93.0	108.2	132.4	171.9	228.1	294.6	362.4	423.7	472.5	506.1
115°	92.1	101.7	117.0	138.8	173.4	221.3	277.6	336.5	391.4	438.2	474.9
117.5°	101.1	111.1	125.2	145.6	176.0	217.8	266.9	316.9	365.2	407.6	442.0
120°	107.0	117.0	131.0	150.3	177.7	215.9	261.2	307.2	351.4	389.3	421.7
122.5°	113.0	123.3	136.3	154.2	179.7	214.7	256.3	299.5	340.0	375.9	405.2
125°	121.7	131.7	144.5	160.6	182.7	212.7	249.4	288.3	325.1	356.5	383.2
127.5°	129.3	139.6	152.1	166.5	185.7	211.5	243.0	277.2	310.5	340.1	364.8
130°	134.2	144.1	156.6	170.2	188.0	210.9	238.7	270.1	300.8	329.0	352.5
132.5°	138.8	148.8	160.7	173.9	190.4	210.6	235.3	263.3	291.6	317.6	339.7
135°	144.9	154.8	166.3	178.7	193.1	210.2	230.5	253.7	277.2	300.8	320.7
137.5°	150.3	159.6	170.9	182.5	195.5	210.1	227.1	246.1	265.8	284.5	301.8
140°	153.4	162.7	173.4	184.5	196.6	209.8	225.1	241.2	258.3	274.8	290.4
142.5°	156.3	165.0	175.4	186.2	197.4	209.8	223.2	237.2	251.8	265.9	279.0
145°	161.0	168.7	178.4	188.4	198.3	209.0	220.6	231.6	243.4	254.4	264.8
147.5°	164.8	171.8	180.9	189.7	198.6	207.8	217.8	227.2	236.5	245.1	252.7
150°	167.3	173.8	182.0	190.2	198.3	206.9	215.5	224.1	232.0	239.4	245.8
152.5°	170.0	175.7	183.1	190.5	197.8	205.5	213.5	221.0	228.2	234.6	240.1
155°	173.4	178.7	184.8	190.9	196.9	203.0	209.8	216.6	222.3	227.6	231.6
157.5°	176.4	180.9	186.0	190.9	195.3	200.5	206.3	211.6	216.3	220.8	223.9
160°	178.4	182.4	186.6	190.9	194.5	198.7	203.7	208.3	212.3	216.2	218.7
162.5°	180.2	183.2	186.9	190.6	193.6	197.3	201.5	205.2	208.6	212.0	213.9
165°	182.0	184.1	187.3	189.9	192.0	194.5	197.6	200.6	203.0	205.5	206.9
167.5°	183.6	184.9	187.2	189.3	190.4	192.0	194.0	196.0	197.9	199.7	201.0
170°	184.1	185.2	186.9	188.7	189.5	190.6	192.0	193.8	194.8	196.2	196.9
172.5°	184.7	185.5	186.7	187.9	188.3	188.8	190.0	191.2	192.0	193.1	193.5
175°	185.2	185.5	186.2	186.9	186.6	186.9	187.3	188.4	188.7	189.1	189.5
177.5°	185.5	185.5	185.8	186.4	185.8	185.5	185.8	186.4	186.4	186.7	186.7
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1042.2	1042.8	1041.9	1042.5	1041.9	1042.8	1042.2	1045.5	1046.1	1046.7	1046.1
5°	971.1	966.5	965.8	964.7	965.8	966.5	971.1	973.0	974.5	977.4	982.8
7.5°	886.2	885.4	883.6	880.9	883.6	885.4	886.2	892.6	897.8	903.6	914.4
10°	831.5	829.7	829.3	826.7	829.3	829.7	831.5	839.8	845.9	854.1	868.9
12.5°	767.6	755.5	754.2	747.6	754.2	755.5	767.6	778.3	794.6	802.5	818.2
15°	653.6	651.3	643.8	638.8	643.8	651.3	653.6	662.6	668.6	690.5	715.8
17.5°	588.3	581.0	578.7	577.6	578.7	581.0	588.3	592.8	601.4	612.9	628.1
20°	546.4	539.7	538.6	537.8	538.6	539.7	546.4	551.7	558.6	571.0	586.8
22.5°	517.5	510.4	507.5	505.2	507.5	510.4	517.5	521.6	527.8	537.5	548.2
25°	468.0	465.3	463.8	463.1	463.8	465.3	468.0	471.8	477.8	491.0	502.3
27.5°	429.3	423.5	422.3	420.4	422.3	423.5	429.3	436.1	442.3	448.3	458.4
30°	407.3	405.4	402.7	400.5	402.7	405.4	407.3	410.7	414.9	425.1	434.8
32.5°	381.3	379.8	377.4	376.4	377.4	379.8	381.3	386.0	394.7	400.9	408.0
35°	352.6	347.3	345.1	341.6	345.1	347.3	352.6	356.4	359.8	365.1	377.9
37.5°	322.2	319.4	316.3	317.4	316.3	319.4	322.2	323.8	330.9	338.3	343.9
40°	298.7	296.8	296.0	295.7	296.0	296.8	298.7	303.6	312.3	315.7	324.0
42.5°	279.9	274.8	272.8	272.8	272.8	274.8	279.9	285.5	290.8	296.3	305.0
45°	251.6	246.6	243.3	243.6	243.3	246.6	251.6	253.4	257.9	268.9	273.8
47.5°	222.5	222.3	220.2	220.9	220.2	222.3	222.5	225.7	231.5	238.2	246.0
50°	208.5	206.3	204.8	205.1	204.8	206.3	208.5	211.2	214.6	217.9	230.0
52.5°	195.3	193.3	192.1	193.7	192.1	193.3	195.3	196.7	199.1	202.6	210.8
55°	173.5	171.2	170.9	170.5	170.9	171.2	173.5	175.3	178.3	181.0	184.8
57.5°	149.2	147.6	145.3	144.4	145.3	147.6	149.2	151.9	155.5	159.0	162.9
60°	131.6	128.6	124.8	124.4	124.8	128.6	131.6	136.5	138.0	143.3	147.8
62.5°	115.6	115.0	114.3	114.2	114.3	115.0	115.6	117.2	119.4	127.0	132.5
65°	101.5	101.1	101.5	101.8	101.5	101.1	101.5	102.2	102.6	103.3	105.6
67.5°	88.4	87.8	87.1	87.4	87.1	87.8	88.4	88.6	89.6	90.1	91.6
70°	78.5	78.1	77.7	77.7	77.7	78.1	78.5	79.2	80.0	80.7	82.6
72.5°	68.8	68.7	68.4	68.1	68.4	68.7	68.8	70.2	70.6	71.4	72.6
75°	55.0	54.3	54.3	54.3	54.3	54.3	55.0	55.4	55.8	57.0	57.7
77.5°	41.9	41.6	41.2	40.9	41.2	41.6	41.9	42.0	42.6	42.8	43.6
80°	33.2	32.8	32.4	32.4	32.4	32.8	33.2	33.5	33.5	34.7	34.3
82.5°	25.3	24.9	24.8	24.5	24.8	24.9	25.3	25.4	25.4	26.3	26.2
85°	13.5	13.9	13.5	14.3	13.5	13.9	13.5	13.2	13.5	14.3	14.3
87.5°	6.3	6.0	6.3	6.0	6.3	6.0	6.3	6.3	6.5	6.4	6.5
90°	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.4	10.7	11.4
92.5°	21.2	20.1	20.3	19.8	20.3	20.1	21.2	21.5	23.7	26.7	31.1
95°	44.2	41.4	40.3	40.7	40.3	41.4	44.2	48.9	56.8	71.7	93.5
97.5°	97.0	88.3	83.1	80.1	83.1	88.3	97.0	114.1	139.9	178.4	218.1
100°	159.9	144.5	134.2	127.7	134.2	144.5	159.9	189.5	232.7	281.6	325.8
102.5°	272.6	246.4	233.5	224.8	233.5	246.4	272.6	304.8	350.5	386.3	396.3
105°	444.5	422.4	407.1	402.1	407.1	422.4	444.5	466.8	478.5	473.8	433.5
107.5°	524.6	523.4	520.3	513.7	520.3	523.4	524.6	521.8	504.5	467.5	406.7
110°	537.8	544.5	547.8	547.3	547.8	544.5	537.8	522.4	493.1	447.5	383.5



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	527.5	538.8	544.8	546.7	544.8	538.8	527.5	506.1	472.5	423.7	362.4
115°	500.3	516.6	525.9	529.2	525.9	516.6	500.3	474.9	438.2	391.4	336.5
117.5°	467.9	485.2	494.9	497.7	494.9	485.2	467.9	442.0	407.6	365.2	316.9
120°	446.8	463.5	473.8	477.5	473.8	463.5	446.8	421.7	389.3	351.4	307.2
122.5°	427.6	444.1	453.3	456.3	453.3	444.1	427.6	405.2	375.9	340.0	299.5
125°	403.9	417.5	426.4	429.3	426.4	417.5	403.9	383.2	356.5	325.1	288.3
127.5°	382.8	395.6	403.2	405.6	403.2	395.6	382.8	364.8	340.1	310.5	277.2
130°	370.0	382.1	389.3	392.1	389.3	382.1	370.0	352.5	329.0	300.8	270.1
132.5°	356.9	369.0	375.6	378.2	375.6	369.0	356.9	339.7	317.6	291.6	263.3
135°	336.1	347.9	354.4	355.8	354.4	347.9	336.1	320.7	300.8	277.2	253.7
137.5°	315.9	326.0	331.6	333.8	331.6	326.0	315.9	301.8	284.5	265.8	246.1
140°	301.8	311.1	316.5	318.6	316.5	311.1	301.8	290.4	274.8	258.3	241.2
142.5°	289.8	298.3	303.1	303.5	303.1	298.3	289.8	279.0	265.9	251.8	237.2
145°	273.3	279.4	283.0	284.0	283.0	279.4	273.3	264.8	254.4	243.4	231.6
147.5°	259.7	264.6	267.0	267.7	267.0	264.6	259.7	252.7	245.1	236.5	227.2
150°	251.2	255.5	257.6	258.0	257.6	255.5	251.2	245.8	239.4	232.0	224.1
152.5°	244.4	248.0	249.6	249.7	249.6	248.0	244.4	240.1	234.6	228.2	221.0
155°	235.5	238.0	239.4	238.7	239.4	238.0	235.5	231.6	227.6	222.3	216.6
157.5°	226.6	228.7	229.3	229.3	229.3	228.7	226.6	223.9	220.8	216.3	211.6
160°	221.3	223.0	223.4	223.4	223.4	223.0	221.3	218.7	216.2	212.3	208.3
162.5°	216.4	217.6	217.9	217.6	217.9	217.6	216.4	213.9	212.0	208.6	205.2
165°	208.3	209.8	209.8	209.4	209.8	209.8	208.3	206.9	205.5	203.0	200.6
167.5°	201.6	202.4	202.3	201.9	202.3	202.4	201.6	201.0	199.7	197.9	196.0
170°	197.3	198.3	198.0	197.3	198.0	198.3	197.3	196.9	196.2	194.8	193.8
172.5°	193.9	194.4	194.0	193.6	194.0	194.4	193.9	193.5	193.1	192.0	191.2
175°	189.5	189.9	189.5	188.7	189.5	189.9	189.5	189.5	189.1	188.7	188.4
177.5°	186.7	186.7	186.4	185.8	186.4	186.7	186.7	186.7	186.7	186.4	186.4
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1043.7	1047.9	1054.3	1057.9	1063.9	1067.8	1070.0	1073.9	1076.0	1083.6	1091.4
5°	985.4	991.5	1002.0	1011.8	1022.4	1033.3	1041.3	1050.3	1058.5	1072.9	1088.0
7.5°	918.6	927.0	943.3	959.0	977.3	992.8	1006.4	1021.9	1035.7	1056.2	1077.6
10°	868.5	883.2	904.7	919.4	943.5	959.0	980.5	997.4	1016.7	1043.9	1068.0
12.5°	825.4	843.1	860.4	880.8	902.5	928.3	951.9	973.6	996.5	1024.6	1052.9
15°	747.1	772.7	799.5	820.2	849.7	876.8	904.3	933.7	961.7	995.2	1032.2
17.5°	646.3	676.0	721.0	756.6	791.1	818.4	852.4	888.1	920.9	961.4	1002.5
20°	600.8	622.6	653.2	701.0	753.2	782.1	816.9	856.1	893.7	937.9	982.0
22.5°	564.2	583.7	608.2	645.5	703.7	743.3	779.4	819.3	863.0	908.1	956.9
25°	512.1	525.7	551.4	581.5	621.5	686.7	726.3	766.3	813.9	862.1	917.9
27.5°	473.0	485.2	501.9	530.7	560.4	607.2	670.2	713.8	761.1	815.5	873.4
30°	443.1	457.5	475.9	496.2	528.8	565.3	628.2	678.8	725.6	781.4	843.2
32.5°	421.4	432.7	448.5	469.2	496.1	531.2	581.5	642.9	688.4	747.3	811.8
35°	385.8	399.0	411.8	431.4	453.3	485.3	523.4	589.1	634.3	692.4	757.3
37.5°	356.5	364.6	378.7	394.3	417.3	441.2	474.2	533.1	582.1	639.0	705.5
40°	334.2	344.3	354.9	372.2	391.1	414.0	446.5	490.3	546.4	602.3	667.1
42.5°	312.5	325.3	336.5	348.1	368.7	391.7	418.2	455.2	512.6	565.4	628.5
45°	286.2	294.6	306.2	319.0	336.0	355.7	379.0	411.4	466.5	512.1	571.4
47.5°	255.8	267.9	275.5	288.0	304.2	322.9	344.6	372.6	417.3	460.0	514.9
50°	235.0	247.4	258.3	269.6	284.0	302.1	320.1	347.3	383.1	428.1	479.3
52.5°	217.1	228.1	238.7	250.0	264.1	280.6	297.8	321.6	352.3	393.6	443.4
55°	192.7	199.4	210.5	221.8	234.2	250.0	266.6	286.6	313.1	347.7	388.1
57.5°	167.6	175.5	184.2	195.6	208.1	220.4	235.2	253.4	274.2	305.6	340.1
60°	153.5	159.6	166.7	178.3	190.1	201.0	215.3	230.5	250.0	277.2	306.6
62.5°	137.8	143.5	150.1	160.3	171.7	181.7	194.2	210.3	226.8	251.6	277.3
65°	111.6	120.0	126.3	135.4	144.8	155.4	165.2	178.0	192.7	212.3	235.3
67.5°	92.5	96.7	102.7	111.0	120.6	129.7	139.0	149.0	161.7	176.8	195.1
70°	84.1	85.6	86.7	94.6	103.7	112.8	121.4	130.9	141.8	154.2	170.1
72.5°	74.1	75.6	77.1	80.5	87.8	96.7	105.7	112.8	123.1	133.4	146.2
75°	58.9	61.1	62.2	64.1	66.8	72.8	81.1	87.9	93.9	101.8	112.0
77.5°	44.8	46.0	47.3	49.3	50.9	53.7	58.4	64.5	70.2	74.7	81.8
80°	35.4	35.9	37.4	38.1	40.4	42.2	44.5	49.4	55.0	57.0	61.8
82.5°	26.7	27.1	28.3	29.1	30.1	31.7	34.5	35.9	40.3	42.7	45.8
85°	14.7	14.3	15.5	15.5	16.3	17.0	17.8	19.6	20.7	23.7	24.5
87.5°	6.9	7.0	7.2	6.8	6.3	6.5	6.6	6.8	7.2	7.9	8.8
90°	11.8	12.1	11.8	9.6	7.2	5.4	4.2	3.5	2.8	1.4	0.4
92.5°	39.2	46.4	45.7	35.6	24.2	16.2	12.8	10.4	8.9	6.3	4.3
95°	122.4	139.9	123.8	82.4	51.4	34.9	26.4	20.7	17.5	13.9	12.5
97.5°	250.4	238.7	179.9	111.1	67.8	47.2	37.5	30.9	26.1	22.2	20.3
100°	333.3	281.9	194.1	117.0	73.5	54.6	44.6	37.5	31.7	28.6	27.5
102.5°	364.1	283.3	188.6	117.3	78.7	61.2	51.2	43.7	38.1	34.8	34.0
105°	359.3	264.4	178.0	119.2	87.5	70.7	60.7	52.8	47.5	44.9	43.5
107.5°	328.0	244.1	172.8	124.1	96.4	80.2	70.1	62.3	57.4	54.9	53.8
110°	308.3	234.4	171.7	128.1	102.4	86.7	76.3	68.9	64.2	62.1	60.7



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	294.6	228.1	171.9	132.4	108.2	93.0	82.3	75.1	70.8	68.4	67.0
115°	277.6	221.3	173.4	138.8	117.0	101.7	92.1	84.9	80.7	78.5	76.7
117.5°	266.9	217.8	176.0	145.6	125.2	111.1	101.1	94.2	90.4	88.3	86.8
120°	261.2	215.9	177.7	150.3	131.0	117.0	107.0	99.9	96.7	94.5	93.1
122.5°	256.3	214.7	179.7	154.2	136.3	123.3	113.0	105.9	102.4	100.3	99.2
125°	249.4	212.7	182.7	160.6	144.5	131.7	121.7	114.5	110.3	108.2	107.0
127.5°	243.0	211.5	185.7	166.5	152.1	139.6	129.3	122.5	117.8	114.7	113.3
130°	238.7	210.9	188.0	170.2	156.6	144.1	134.2	127.0	122.0	118.5	117.0
132.5°	235.3	210.6	190.4	173.9	160.7	148.8	138.8	131.3	126.0	122.2	120.5
135°	230.5	210.2	193.1	178.7	166.3	154.8	144.9	136.6	131.3	127.0	125.6
137.5°	227.1	210.1	195.5	182.5	170.9	159.6	150.3	142.2	136.4	132.2	130.5
140°	225.1	209.8	196.6	184.5	173.4	162.7	153.4	145.6	139.9	135.6	134.2
142.5°	223.2	209.8	197.4	186.2	175.4	165.0	156.3	148.8	143.0	139.1	137.8
145°	220.6	209.0	198.3	188.4	178.4	168.7	161.0	153.8	148.5	144.9	143.4
147.5°	217.8	207.8	198.6	189.7	180.9	171.8	164.8	158.9	153.9	150.5	149.5
150°	215.5	206.9	198.3	190.2	182.0	173.8	167.3	162.0	157.3	154.5	153.4
152.5°	213.5	205.5	197.8	190.5	183.1	175.7	170.0	164.8	160.8	157.9	157.4
155°	209.8	203.0	196.9	190.9	184.8	178.7	173.4	169.5	165.5	163.4	163.1
157.5°	206.3	200.5	195.3	190.9	186.0	180.9	176.4	173.3	169.9	168.1	167.7
160°	203.7	198.7	194.5	190.9	186.6	182.4	178.4	175.5	172.7	171.3	170.9
162.5°	201.5	197.3	193.6	190.6	186.9	183.2	180.2	177.5	175.3	173.8	174.1
165°	197.6	194.5	192.0	189.9	187.3	184.1	182.0	180.2	178.0	177.3	177.7
167.5°	194.0	192.0	190.4	189.3	187.2	184.9	183.6	182.3	180.9	180.3	180.7
170°	192.0	190.6	189.5	188.7	186.9	185.2	184.1	183.4	182.4	182.0	182.7
172.5°	190.0	188.8	188.3	187.9	186.7	185.5	184.7	184.3	183.2	183.4	183.8
175°	187.3	186.9	186.6	186.9	186.2	185.5	185.2	185.2	184.5	184.8	185.2
177.5°	185.8	185.5	185.8	186.4	185.8	185.5	185.5	185.5	185.0	185.2	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1091.7	1092.6	1098.6	1101.4	1106.8	1108.9	1111.3	1110.6	1110.6	1111.9	1120.3
5°	1094.0	1101.6	1112.9	1123.8	1134.4	1143.5	1149.4	1155.5	1157.7	1168.7	1178.5
7.5°	1090.1	1104.0	1122.7	1139.3	1159.3	1175.0	1187.9	1199.6	1207.6	1223.6	1239.8
10°	1085.0	1104.6	1125.7	1147.2	1174.8	1195.5	1216.6	1232.8	1238.1	1261.8	1275.5
12.5°	1074.7	1101.0	1127.8	1155.7	1182.6	1211.1	1234.4	1250.6	1269.2	1290.5	1315.6
15°	1059.3	1089.5	1124.6	1160.4	1198.9	1233.6	1258.5	1286.8	1307.1	1330.5	1352.3
17.5°	1037.2	1076.1	1120.6	1162.2	1206.6	1243.9	1278.2	1305.3	1319.6	1332.9	1336.3
20°	1019.8	1061.6	1114.0	1163.1	1207.5	1250.5	1284.4	1307.1	1310.9	1311.2	1291.2
22.5°	1000.8	1048.0	1102.9	1153.1	1206.3	1254.2	1280.5	1290.2	1275.3	1249.7	1211.0
25°	965.8	1020.5	1084.2	1141.6	1199.6	1244.9	1253.9	1237.0	1184.6	1129.4	1059.8
27.5°	928.0	989.4	1057.7	1121.5	1183.4	1211.4	1191.8	1130.6	1036.2	954.2	854.7
30°	900.2	969.2	1036.3	1107.6	1164.9	1177.0	1132.2	1042.0	931.9	808.2	709.0
32.5°	868.5	940.8	1014.6	1088.3	1136.3	1124.5	1050.4	939.4	810.3	688.7	594.9
35°	823.2	898.0	977.4	1051.4	1082.0	1031.1	920.2	775.8	643.8	530.3	465.7
37.5°	771.0	852.3	935.0	1002.9	1000.8	915.8	764.9	615.7	504.8	437.7	391.7
40°	733.9	816.1	905.4	962.8	938.3	827.8	664.1	523.4	442.3	388.8	355.3
42.5°	698.3	780.8	869.6	915.1	872.5	736.7	573.6	463.4	396.5	354.8	327.5
45°	637.7	724.8	807.1	832.3	756.1	606.4	463.8	384.0	339.4	308.5	289.6
47.5°	578.6	664.2	739.2	739.7	636.6	491.8	391.3	332.2	294.3	270.3	256.6
50°	542.3	623.8	686.7	676.9	560.1	437.5	349.9	299.0	267.4	248.9	234.6
52.5°	501.6	580.6	635.1	607.2	495.1	385.0	312.9	270.1	243.9	227.8	215.0
55°	442.3	512.5	551.0	508.8	403.9	320.1	264.4	230.8	211.2	197.6	186.7
57.5°	384.3	442.0	466.3	417.1	332.6	265.5	223.6	198.4	178.9	169.3	163.6
60°	347.7	397.1	414.0	359.8	289.2	232.3	198.0	174.6	160.3	153.9	148.2
62.5°	311.8	352.1	359.2	309.4	252.2	203.4	173.9	154.1	144.6	138.5	133.1
65°	258.7	287.7	284.4	244.4	199.4	161.4	139.9	127.8	120.7	112.0	102.6
67.5°	213.0	230.8	220.0	190.1	152.3	125.4	111.4	102.3	93.4	85.1	83.0
70°	184.0	194.2	182.9	155.4	124.8	105.2	93.9	83.0	77.7	75.8	72.4
72.5°	156.3	159.9	147.6	124.0	101.6	87.2	76.1	70.0	67.2	65.5	63.3
75°	117.2	114.6	104.1	85.6	70.5	60.7	57.4	55.0	53.2	51.7	50.5
77.5°	82.4	78.5	69.1	57.1	49.1	44.4	42.4	41.2	40.3	39.5	38.4
80°	61.8	59.2	49.8	40.7	37.4	35.0	33.9	32.4	32.4	31.7	30.5
82.5°	45.2	42.3	34.1	29.9	28.0	26.7	25.8	24.8	24.5	24.7	23.9
85°	23.7	19.2	17.0	16.3	15.0	14.3	14.7	13.9	13.9	13.9	13.5
87.5°	7.6	6.3	6.2	6.0	6.5	6.9	7.1	7.5	7.9	7.5	7.7
90°	1.4	2.8	3.5	4.2	5.4	7.2	9.6	11.8	12.1	11.8	11.4
92.5°	6.3	8.9	10.4	12.8	16.2	24.2	35.6	45.7	46.4	39.2	31.1
95°	13.9	17.5	20.7	26.4	34.9	51.4	82.4	123.8	139.9	122.4	93.5
97.5°	22.2	26.1	30.9	37.5	47.2	67.8	111.1	179.9	238.7	250.4	218.1
100°	28.6	31.7	37.5	44.6	54.6	73.5	117.0	194.1	281.9	333.3	325.8
102.5°	34.8	38.1	43.7	51.2	61.2	78.7	117.3	188.6	283.3	364.1	396.3
105°	44.9	47.5	52.8	60.7	70.7	87.5	119.2	178.0	264.4	359.3	433.5
107.5°	54.9	57.4	62.3	70.1	80.2	96.4	124.1	172.8	244.1	328.0	406.7
110°	62.1	64.2	68.9	76.3	86.7	102.4	128.1	171.7	234.4	308.3	383.5



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	68.4	70.8	75.1	82.3	93.0	108.2	132.4	171.9	228.1	294.6	362.4
115°	78.5	80.7	84.9	92.1	101.7	117.0	138.8	173.4	221.3	277.6	336.5
117.5°	88.3	90.4	94.2	101.1	111.1	125.2	145.6	176.0	217.8	266.9	316.9
120°	94.5	96.7	99.9	107.0	117.0	131.0	150.3	177.7	215.9	261.2	307.2
122.5°	100.3	102.4	105.9	113.0	123.3	136.3	154.2	179.7	214.7	256.3	299.5
125°	108.2	110.3	114.5	121.7	131.7	144.5	160.6	182.7	212.7	249.4	288.3
127.5°	114.7	117.8	122.5	129.3	139.6	152.1	166.5	185.7	211.5	243.0	277.2
130°	118.5	122.0	127.0	134.2	144.1	156.6	170.2	188.0	210.9	238.7	270.1
132.5°	122.2	126.0	131.3	138.8	148.8	160.7	173.9	190.4	210.6	235.3	263.3
135°	127.0	131.3	136.6	144.9	154.8	166.3	178.7	193.1	210.2	230.5	253.7
137.5°	132.2	136.4	142.2	150.3	159.6	170.9	182.5	195.5	210.1	227.1	246.1
140°	135.6	139.9	145.6	153.4	162.7	173.4	184.5	196.6	209.8	225.1	241.2
142.5°	139.1	143.0	148.8	156.3	165.0	175.4	186.2	197.4	209.8	223.2	237.2
145°	144.9	148.5	153.8	161.0	168.7	178.4	188.4	198.3	209.0	220.6	231.6
147.5°	150.5	153.9	158.9	164.8	171.8	180.9	189.7	198.6	207.8	217.8	227.2
150°	154.5	157.3	162.0	167.3	173.8	182.0	190.2	198.3	206.9	215.5	224.1
152.5°	157.9	160.8	164.8	170.0	175.7	183.1	190.5	197.8	205.5	213.5	221.0
155°	163.4	165.5	169.5	173.4	178.7	184.8	190.9	196.9	203.0	209.8	216.6
157.5°	168.1	169.9	173.3	176.4	180.9	186.0	190.9	195.3	200.5	206.3	211.6
160°	171.3	172.7	175.5	178.4	182.4	186.6	190.9	194.5	198.7	203.7	208.3
162.5°	173.8	175.3	177.5	180.2	183.2	186.9	190.6	193.6	197.3	201.5	205.2
165°	177.3	178.0	180.2	182.0	184.1	187.3	189.9	192.0	194.5	197.6	200.6
167.5°	180.3	180.9	182.3	183.6	184.9	187.2	189.3	190.4	192.0	194.0	196.0
170°	182.0	182.4	183.4	184.1	185.2	186.9	188.7	189.5	190.6	192.0	193.8
172.5°	183.4	183.2	184.3	184.7	185.5	186.7	187.9	188.3	188.8	190.0	191.2
175°	184.8	184.5	185.2	185.2	185.5	186.2	186.9	186.6	186.9	187.3	188.4
177.5°	185.2	185.0	185.5	185.5	185.5	185.8	186.4	185.8	185.5	185.8	186.4
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1123.4	1127.3	1129.1	1129.1	1131.3	1130.3	1129.4
5°	1187.9	1195.1	1196.6	1203.4	1208.3	1206.8	1207.5
7.5°	1252.1	1263.6	1275.1	1280.2	1281.1	1284.1	1285.3
10°	1291.6	1301.1	1318.8	1316.2	1329.4	1336.9	1324.4
12.5°	1329.7	1342.4	1354.7	1358.1	1365.5	1368.0	1363.0
15°	1364.0	1370.8	1371.6	1369.7	1372.0	1370.1	1362.9
17.5°	1331.9	1320.9	1298.6	1288.0	1279.6	1267.3	1262.3
20°	1278.8	1246.4	1208.7	1193.6	1175.9	1141.1	1149.4
22.5°	1164.2	1127.2	1089.5	1045.4	1024.4	991.5	989.6
25°	985.8	922.1	851.9	802.8	774.3	741.4	727.1
27.5°	766.5	686.2	628.7	599.7	573.1	547.1	546.0
30°	622.3	561.9	517.5	492.5	476.4	465.3	467.7
32.5°	524.5	483.1	453.1	432.5	420.5	412.2	412.1
35°	428.8	400.5	381.2	372.6	364.0	357.9	358.3
37.5°	367.0	349.9	339.2	329.7	324.3	321.3	319.6
40°	335.3	321.3	313.1	307.4	302.9	298.7	297.9
42.5°	310.2	298.7	290.3	285.9	281.8	278.7	278.0
45°	275.3	265.9	258.3	253.4	251.6	248.9	248.9
47.5°	244.9	235.6	229.7	226.6	223.4	221.7	221.6
50°	224.4	217.2	212.0	210.1	207.4	206.3	205.9
52.5°	206.0	200.7	196.8	195.6	194.4	193.0	193.2
55°	181.0	178.0	176.5	175.3	173.5	171.2	172.7
57.5°	160.0	157.4	153.3	149.8	148.0	146.4	147.0
60°	145.2	139.9	134.6	130.5	129.4	125.9	125.9
62.5°	126.5	119.1	112.6	110.3	109.2	107.6	107.2
65°	97.3	94.3	92.8	91.3	90.5	90.5	89.8
67.5°	80.6	79.4	77.8	77.4	76.6	76.4	76.1
70°	71.3	69.8	69.0	68.7	67.9	68.3	67.2
72.5°	62.2	61.0	60.9	59.9	59.5	59.5	58.7
75°	49.0	49.0	48.7	48.3	47.6	47.2	47.6
77.5°	37.7	37.8	37.1	37.1	37.0	37.1	36.7
80°	30.2	30.5	30.2	29.8	29.4	29.8	29.4
82.5°	23.8	23.3	23.2	23.1	23.1	22.8	22.8
85°	13.5	13.9	13.5	13.2	13.2	13.2	13.5
87.5°	7.3	7.4	7.5	7.5	7.5	7.5	7.2
90°	10.7	11.4	11.8	11.8	11.8	11.8	11.8
92.5°	26.7	23.7	21.5	21.2	20.1	20.3	19.8
95°	71.7	56.8	48.9	44.2	41.4	40.3	40.7
97.5°	178.4	139.9	114.1	97.0	88.3	83.1	80.1
100°	281.6	232.7	189.5	159.9	144.5	134.2	127.7
102.5°	386.3	350.5	304.8	272.6	246.4	233.5	224.8
105°	473.8	478.5	466.8	444.5	422.4	407.1	402.1
107.5°	467.5	504.5	521.8	524.6	523.4	520.3	513.7
110°	447.5	493.1	522.4	537.8	544.5	547.8	547.3



TEST NUMBER: P331647-840

CATALOG NUMBER: S122RDIP-S485D330U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	423.7	472.5	506.1	527.5	538.8	544.8	546.7
115°	391.4	438.2	474.9	500.3	516.6	525.9	529.2
117.5°	365.2	407.6	442.0	467.9	485.2	494.9	497.7
120°	351.4	389.3	421.7	446.8	463.5	473.8	477.5
122.5°	340.0	375.9	405.2	427.6	444.1	453.3	456.3
125°	325.1	356.5	383.2	403.9	417.5	426.4	429.3
127.5°	310.5	340.1	364.8	382.8	395.6	403.2	405.6
130°	300.8	329.0	352.5	370.0	382.1	389.3	392.1
132.5°	291.6	317.6	339.7	356.9	369.0	375.6	378.2
135°	277.2	300.8	320.7	336.1	347.9	354.4	355.8
137.5°	265.8	284.5	301.8	315.9	326.0	331.6	333.8
140°	258.3	274.8	290.4	301.8	311.1	316.5	318.6
142.5°	251.8	265.9	279.0	289.8	298.3	303.1	303.5
145°	243.4	254.4	264.8	273.3	279.4	283.0	284.0
147.5°	236.5	245.1	252.7	259.7	264.6	267.0	267.7
150°	232.0	239.4	245.8	251.2	255.5	257.6	258.0
152.5°	228.2	234.6	240.1	244.4	248.0	249.6	249.7
155°	222.3	227.6	231.6	235.5	238.0	239.4	238.7
157.5°	216.3	220.8	223.9	226.6	228.7	229.3	229.3
160°	212.3	216.2	218.7	221.3	223.0	223.4	223.4
162.5°	208.6	212.0	213.9	216.4	217.6	217.9	217.6
165°	203.0	205.5	206.9	208.3	209.8	209.8	209.4
167.5°	197.9	199.7	201.0	201.6	202.4	202.3	201.9
170°	194.8	196.2	196.9	197.3	198.3	198.0	197.3
172.5°	192.0	193.1	193.5	193.9	194.4	194.0	193.6
175°	188.7	189.1	189.5	189.5	189.9	189.5	188.7
177.5°	186.4	186.7	186.7	186.7	186.7	186.4	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5

(END OF REPORT)