

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331659-840

Luminaire Tested: **S122RDIP-S485D725U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331659-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D725U840-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4735.9 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	19
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17525	17525	17525	17525
5°	19571	17634	15635	17634
10°	21713	17510	13554	17510
15°	22781	17254	10678	17254
20°	19749	16873	9241	16873
25°	12953	16352	8250	16352
30°	8720	15720	7467	15720
35°	7062	14927	6733	14927
40°	6279	14060	6232	14060
45°	5683	13047	5562	13047
50°	5172	12039	5152	12039
55°	4861	10925	4799	10925
60°	4066	9901	4017	9901
65°	3431	8989	3889	8989
70°	3172	8030	3668	8030
75°	2969	6987	3387	6987
80°	2734	5746	3013	5746
85°	2501	4539	2649	4539



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.9	2.2
10°-20°	286.7	6.1
20°-30°	369.4	7.8
30°-40°	351.1	7.4
40°-50°	300.7	6.4
50°-60°	229.0	4.8
60°-70°	144.8	3.1
70°-80°	72.3	1.5
80°-90°	22.5	0.5
90°-100°	164.1	3.5
100°-110°	557.0	11.8
110°-120°	591.7	12.5
120°-130°	487.1	10.3
130°-140°	391.2	8.3
140°-150°	295.6	6.2
150°-160°	207.7	4.4
160°-170°	122.3	2.6
170°-180°	39.8	0.8
0°-30°	759.0	16.0
0°-40°	1110.1	23.4
0°-60°	1639.8	34.6
0°-90°	1879.4	39.7
90°-120°	1312.8	27.7
90°-150°	2486.7	52.5
90°-180°	2856.0	60.3
0°-180°	4735.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1085	1085	1085	1085	1085	
5°	1208	1088	965	1088	1208	119
15°	1363	1032	639	1032	1363	368
25°	727	918	463	918	727	345
35°	358	757	342	757	358	229
45°	249	571	244	571	249	193
55°	173	388	170	388	173	152
65°	90	235	102	235	90	91
75°	48	112	54	112	48	50
85°	14	24	14	24	14	15
90°	26	1	26	1	26	15
95°	90	28	90	28	90	117
105°	890	96	890	96	890	861
115°	1171	170	1171	170	1171	1146
125°	950	237	950	237	950	858
135°	787	278	787	278	787	611
145°	628	317	628	317	628	399
155°	528	361	528	361	528	246
165°	463	393	463	393	463	132
175°	418	410	418	410	418	41
180°	410	410	410	410	410	



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1129.4	1130.3	1131.3	1129.1	1129.1	1127.3	1123.4	1120.3	1111.9	1110.6	1110.6
5°	1207.5	1206.8	1208.3	1203.4	1196.6	1195.1	1187.9	1178.5	1168.7	1157.7	1155.5
7.5°	1285.3	1284.1	1281.1	1280.2	1275.1	1263.6	1252.1	1239.8	1223.6	1207.6	1199.6
10°	1324.4	1336.9	1329.4	1316.2	1318.8	1301.1	1291.6	1275.5	1261.8	1238.1	1232.8
12.5°	1363.0	1368.0	1365.5	1358.1	1354.7	1342.4	1329.7	1315.6	1290.5	1269.2	1250.6
15°	1362.9	1370.1	1372.0	1369.7	1371.6	1370.8	1364.0	1352.3	1330.5	1307.1	1286.8
17.5°	1262.3	1267.3	1279.6	1288.0	1298.6	1320.9	1331.9	1336.3	1332.9	1319.6	1305.3
20°	1149.4	1141.1	1175.9	1193.6	1208.7	1246.4	1278.8	1291.2	1311.2	1310.9	1307.1
22.5°	989.6	991.5	1024.4	1045.4	1089.5	1127.2	1164.2	1211.0	1249.7	1275.3	1290.2
25°	727.1	741.4	774.3	802.8	851.9	922.1	985.8	1059.8	1129.4	1184.6	1237.0
27.5°	546.0	547.1	573.1	599.7	628.7	686.2	766.5	854.7	954.2	1036.2	1130.6
30°	467.7	465.3	476.4	492.5	517.5	561.9	622.3	709.0	808.2	931.9	1042.0
32.5°	412.1	412.2	420.5	432.5	453.1	483.1	524.5	594.9	688.7	810.3	939.4
35°	358.3	357.9	364.0	372.6	381.2	400.5	428.8	465.7	530.3	643.8	775.8
37.5°	319.6	321.3	324.3	329.7	339.2	349.9	367.0	391.7	437.7	504.8	615.7
40°	297.9	298.7	302.9	307.4	313.1	321.3	335.3	355.3	388.8	442.3	523.4
42.5°	278.0	278.7	281.8	285.9	290.3	298.7	310.2	327.5	354.8	396.5	463.4
45°	248.9	248.9	251.6	253.4	258.3	265.9	275.3	289.6	308.5	339.4	384.0
47.5°	221.6	221.7	223.4	226.6	229.7	235.6	244.9	256.6	270.3	294.3	332.2
50°	205.9	206.3	207.4	210.1	212.0	217.2	224.4	234.6	248.9	267.4	299.0
52.5°	193.2	193.0	194.4	195.6	196.8	200.7	206.0	215.0	227.8	243.9	270.1
55°	172.7	171.2	173.5	175.3	176.5	178.0	181.0	186.7	197.6	211.2	230.8
57.5°	147.0	146.4	148.0	149.8	153.3	157.4	160.0	163.6	169.3	178.9	198.4
60°	125.9	125.9	129.4	130.5	134.6	139.9	145.2	148.2	153.9	160.3	174.6
62.5°	107.2	107.6	109.2	110.3	112.6	119.1	126.5	133.1	138.5	144.6	154.1
65°	89.8	90.5	90.5	91.3	92.8	94.3	97.3	102.6	112.0	120.7	127.8
67.5°	76.1	76.4	76.6	77.4	77.8	79.4	80.6	83.0	85.1	93.4	102.3
70°	67.2	68.3	67.9	68.7	69.0	69.8	71.3	72.4	75.8	77.7	83.0
72.5°	58.7	59.5	59.5	59.9	60.9	61.0	62.2	63.3	65.5	67.2	70.0
75°	47.6	47.2	47.6	48.3	48.7	49.0	49.0	50.5	51.7	53.2	55.0
77.5°	36.7	37.1	37.0	37.1	37.1	37.8	37.7	38.4	39.5	40.3	41.2
80°	29.4	29.8	29.4	29.8	30.2	30.5	30.2	30.5	31.7	32.4	32.4
82.5°	22.8	22.8	23.1	23.1	23.2	23.3	23.8	23.9	24.7	24.5	24.8
85°	13.5	13.2	13.2	13.2	13.5	13.9	13.5	13.5	13.9	13.9	13.9
87.5°	10.0	10.3	10.3	10.3	10.3	10.2	9.9	10.5	10.3	10.8	10.3
90°	26.1	26.1	26.1	26.1	26.1	25.2	23.7	25.2	26.1	26.9	26.1
92.5°	43.7	45.0	44.3	46.9	47.6	52.4	59.1	68.9	86.6	102.6	101.2
95°	90.0	89.2	91.6	97.9	108.2	125.5	158.6	206.8	270.7	309.4	274.0
97.5°	177.1	183.8	195.3	214.7	252.5	309.4	394.9	482.6	554.2	528.3	397.9
100°	282.6	296.8	319.7	353.7	419.2	514.7	622.9	720.7	737.3	623.6	429.4
102.5°	497.4	516.5	545.1	603.1	674.3	775.5	854.6	876.8	805.5	626.8	417.5
105°	889.7	900.7	934.6	983.6	1032.6	1058.6	1048.3	959.2	795.0	584.9	393.9
107.5°	1136.4	1151.1	1157.9	1160.6	1154.5	1116.2	1034.1	899.8	725.6	540.1	382.2
110°	1210.9	1211.7	1204.7	1189.6	1155.7	1091.0	990.0	848.6	682.1	518.7	379.7



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1209.7	1205.5	1192.0	1166.9	1119.7	1045.5	937.5	801.9	651.8	504.7	380.3
115°	1170.7	1163.6	1143.1	1106.7	1050.7	969.4	866.0	744.4	614.2	489.5	383.6
117.5°	1101.1	1095.1	1073.5	1035.1	978.0	901.7	807.9	701.1	590.5	482.0	389.3
120°	1056.2	1048.3	1025.4	988.4	933.1	861.2	777.6	679.6	577.8	477.6	393.1
122.5°	1009.5	1002.9	982.5	946.0	896.5	831.5	752.3	662.7	567.1	475.0	397.6
125°	949.7	943.3	923.6	893.6	847.8	788.6	719.1	637.8	551.8	470.5	404.1
127.5°	897.3	892.2	875.1	847.1	807.1	752.5	686.9	613.4	537.6	467.8	411.0
130°	867.6	861.2	845.5	818.6	779.9	727.8	665.5	597.5	528.2	466.6	416.1
132.5°	836.6	830.9	816.4	789.6	751.5	702.6	645.3	582.4	520.6	466.0	421.1
135°	787.1	783.9	769.7	743.7	709.6	665.5	613.4	561.3	510.0	464.9	427.1
137.5°	738.4	733.7	721.2	698.8	667.8	629.3	587.9	544.4	502.5	464.8	432.4
140°	705.0	700.2	688.3	667.8	642.6	607.8	571.6	533.6	498.2	464.1	434.9
142.5°	671.5	670.6	659.9	641.4	617.3	588.2	557.0	524.8	493.7	464.1	436.9
145°	628.3	626.0	618.1	604.7	585.7	562.9	538.4	512.3	487.9	462.6	438.9
147.5°	592.2	590.8	585.4	574.7	559.1	542.3	523.2	502.7	481.9	459.8	439.6
150°	570.8	570.0	565.2	555.7	543.9	529.7	513.1	495.7	476.8	457.9	438.9
152.5°	552.4	552.3	548.8	540.6	531.3	519.0	504.9	488.8	472.4	454.7	437.7
155°	528.2	529.7	526.5	521.0	512.3	503.6	491.8	479.2	464.1	449.2	435.8
157.5°	507.5	507.5	506.0	501.4	495.2	488.5	478.6	468.0	456.5	443.5	432.1
160°	494.1	494.1	493.4	489.5	483.9	478.4	469.7	461.0	450.8	439.7	430.2
162.5°	481.5	482.2	481.4	478.7	473.2	468.9	461.5	454.0	445.7	436.6	428.4
165°	463.4	464.1	464.1	461.0	457.9	454.7	449.2	443.6	437.4	430.2	424.7
167.5°	446.7	447.6	447.8	446.1	444.6	441.7	438.0	433.7	429.1	424.7	421.1
170°	436.6	438.1	438.9	436.6	435.8	434.1	431.0	428.7	424.7	421.5	419.2
172.5°	428.4	429.3	430.1	429.0	428.2	427.3	424.7	422.9	420.3	417.8	416.7
175°	417.6	419.2	420.0	419.2	419.2	418.4	417.6	416.8	414.4	413.6	412.8
177.5°	411.1	412.4	413.0	413.0	413.0	413.0	412.4	412.4	411.1	410.5	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1111.3	1108.9	1106.8	1101.4	1098.6	1092.6	1091.7	1091.4	1083.6	1076.0	1073.9
5°	1149.4	1143.5	1134.4	1123.8	1112.9	1101.6	1094.0	1088.0	1072.9	1058.5	1050.3
7.5°	1187.9	1175.0	1159.3	1139.3	1122.7	1104.0	1090.1	1077.6	1056.2	1035.7	1021.9
10°	1216.6	1195.5	1174.8	1147.2	1125.7	1104.6	1085.0	1068.0	1043.9	1016.7	997.4
12.5°	1234.4	1211.1	1182.6	1155.7	1127.8	1101.0	1074.7	1052.9	1024.6	996.5	973.6
15°	1258.5	1233.6	1198.9	1160.4	1124.6	1089.5	1059.3	1032.2	995.2	961.7	933.7
17.5°	1278.2	1243.9	1206.6	1162.2	1120.6	1076.1	1037.2	1002.5	961.4	920.9	888.1
20°	1284.4	1250.5	1207.5	1163.1	1114.0	1061.6	1019.8	982.0	937.9	893.7	856.1
22.5°	1280.5	1254.2	1206.3	1153.1	1102.9	1048.0	1000.8	956.9	908.1	863.0	819.3
25°	1253.9	1244.9	1199.6	1141.6	1084.2	1020.5	965.8	917.9	862.1	813.9	766.3
27.5°	1191.8	1211.4	1183.4	1121.5	1057.7	989.4	928.0	873.4	815.5	761.1	713.8
30°	1132.2	1177.0	1164.9	1107.6	1036.3	969.2	900.2	843.2	781.4	725.6	678.8
32.5°	1050.4	1124.5	1136.3	1088.3	1014.6	940.8	868.5	811.8	747.3	688.4	642.9
35°	920.2	1031.1	1082.0	1051.4	977.4	898.0	823.2	757.3	692.4	634.3	589.1
37.5°	764.9	915.8	1000.8	1002.9	935.0	852.3	771.0	705.5	639.0	582.1	533.1
40°	664.1	827.8	938.3	962.8	905.4	816.1	733.9	667.1	602.3	546.4	490.3
42.5°	573.6	736.7	872.5	915.1	869.6	780.8	698.3	628.5	565.4	512.6	455.2
45°	463.8	606.4	756.1	832.3	807.1	724.8	637.7	571.4	512.1	466.5	411.4
47.5°	391.3	491.8	636.6	739.7	739.2	664.2	578.6	514.9	460.0	417.3	372.6
50°	349.9	437.5	560.1	676.9	686.7	623.8	542.3	479.3	428.1	383.1	347.3
52.5°	312.9	385.0	495.1	607.2	635.1	580.6	501.6	443.4	393.6	352.3	321.6
55°	264.4	320.1	403.9	508.8	551.0	512.5	442.3	388.1	347.7	313.1	286.6
57.5°	223.6	265.5	332.6	417.1	466.3	442.0	384.3	340.1	305.6	274.2	253.4
60°	198.0	232.3	289.2	359.8	414.0	397.1	347.7	306.6	277.2	250.0	230.5
62.5°	173.9	203.4	252.2	309.4	359.2	352.1	311.8	277.3	251.6	226.8	210.3
65°	139.9	161.4	199.4	244.4	284.4	287.7	258.7	235.3	212.3	192.7	178.0
67.5°	111.4	125.4	152.3	190.1	220.0	230.8	213.0	195.1	176.8	161.7	149.0
70°	93.9	105.2	124.8	155.4	182.9	194.2	184.0	170.1	154.2	141.8	130.9
72.5°	76.1	87.2	101.6	124.0	147.6	159.9	156.3	146.2	133.4	123.1	112.8
75°	57.4	60.7	70.5	85.6	104.1	114.6	117.2	112.0	101.8	93.9	87.9
77.5°	42.4	44.4	49.1	57.1	69.1	78.5	82.4	81.8	74.7	70.2	64.5
80°	33.9	35.0	37.4	40.7	49.8	59.2	61.8	61.8	57.0	55.0	49.4
82.5°	25.8	26.7	28.0	29.9	34.1	42.3	45.2	45.8	42.7	40.3	35.9
85°	14.7	14.3	15.0	16.3	17.0	19.2	23.7	24.5	23.7	20.7	19.6
87.5°	9.4	8.6	7.8	7.1	7.0	7.0	7.9	8.9	8.2	7.9	7.6
90°	21.3	15.8	11.8	9.5	7.9	6.4	3.1	0.8	3.1	6.4	7.9
92.5°	78.8	53.7	35.9	28.4	23.0	19.6	13.9	9.6	13.9	19.6	23.0
95°	182.4	113.7	77.4	58.4	45.7	38.7	30.8	27.7	30.8	38.7	45.7
97.5°	245.7	150.0	104.3	82.9	68.4	57.7	49.3	45.0	49.3	57.7	68.4
100°	258.9	162.6	120.8	98.7	82.9	70.3	63.1	60.8	63.1	70.3	82.9
102.5°	259.5	174.0	135.3	113.2	96.7	84.1	77.1	75.3	77.1	84.1	96.7
105°	263.7	193.4	156.3	134.2	116.8	105.0	99.5	96.3	99.5	105.0	116.8
107.5°	274.6	213.3	177.3	155.0	137.8	126.9	121.6	119.1	121.6	126.9	137.8
110°	283.4	226.5	191.9	169.0	152.4	142.1	137.3	134.2	137.3	142.1	152.4



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	292.9	239.2	205.7	182.2	166.2	156.6	151.3	148.0	151.3	156.6	166.2
115°	307.1	258.9	225.0	203.7	187.8	178.4	173.7	169.8	173.7	178.4	187.8
117.5°	322.2	277.1	245.7	223.6	208.4	200.1	195.3	192.2	195.3	200.1	208.4
120°	332.3	289.7	258.9	236.8	221.1	213.9	209.2	206.0	209.2	213.9	221.1
122.5°	341.2	301.7	272.9	250.0	234.3	226.5	221.9	219.3	221.9	226.5	234.3
125°	355.3	319.7	291.2	269.2	253.4	243.9	239.2	236.8	239.2	243.9	253.4
127.5°	368.3	336.5	308.8	286.1	270.9	260.5	253.9	250.7	253.9	260.5	270.9
130°	376.6	346.6	318.9	296.8	281.0	269.9	262.1	258.9	262.1	269.9	281.0
132.5°	384.8	355.4	329.0	306.9	290.5	278.8	270.3	266.5	270.3	278.8	290.5
135°	395.5	367.9	342.6	320.5	302.4	290.5	281.0	277.9	281.0	290.5	302.4
137.5°	403.7	378.0	353.0	332.5	314.5	301.8	292.4	288.6	292.4	301.8	314.5
140°	408.1	383.6	360.0	339.4	322.0	309.4	299.9	296.8	299.9	309.4	322.0
142.5°	411.9	388.1	365.1	345.8	329.0	316.4	307.6	305.0	307.6	316.4	329.0
145°	416.8	394.8	373.3	356.0	340.2	328.4	320.5	317.3	320.5	328.4	340.2
147.5°	419.5	400.1	380.0	364.6	351.4	340.5	333.0	330.6	333.0	340.5	351.4
150°	420.7	402.6	384.5	370.2	358.4	348.1	341.8	339.4	341.8	348.1	358.4
152.5°	421.4	405.2	388.9	375.9	364.7	355.7	349.4	348.3	349.4	355.7	364.7
155°	422.3	408.9	395.5	383.6	375.0	366.3	361.5	360.7	361.5	366.3	375.0
157.5°	422.3	411.6	400.2	390.3	383.3	375.8	371.9	371.2	371.9	375.8	383.3
160°	422.3	412.8	403.3	394.8	388.4	382.0	378.9	378.1	378.9	382.0	388.4
162.5°	421.7	413.5	405.3	398.5	392.8	387.8	384.6	385.1	384.6	387.8	392.8
165°	420.0	414.4	407.4	402.6	398.7	393.9	392.3	393.1	392.3	393.9	398.7
167.5°	418.9	414.2	409.1	406.1	403.2	400.2	398.8	399.8	398.8	400.2	403.2
170°	417.6	413.6	409.7	407.4	405.8	403.3	402.6	404.1	402.6	403.3	405.8
172.5°	415.7	413.0	410.3	408.6	407.7	405.3	405.8	406.7	405.8	405.3	407.7
175°	413.6	412.0	410.5	409.7	409.7	408.1	408.9	409.7	408.9	408.1	409.7
177.5°	412.4	411.1	410.5	410.5	410.5	409.2	409.9	411.1	409.9	409.2	410.5
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1070.0	1067.8	1063.9	1057.9	1054.3	1047.9	1043.7	1046.1	1046.7	1046.1	1045.5
5°	1041.3	1033.3	1022.4	1011.8	1002.0	991.5	985.4	982.8	977.4	974.5	973.0
7.5°	1006.4	992.8	977.3	959.0	943.3	927.0	918.6	914.4	903.6	897.8	892.6
10°	980.5	959.0	943.5	919.4	904.7	883.2	868.5	868.9	854.1	845.9	839.8
12.5°	951.9	928.3	902.5	880.8	860.4	843.1	825.4	818.2	802.5	794.6	778.3
15°	904.3	876.8	849.7	820.2	799.5	772.7	747.1	715.8	690.5	668.6	662.6
17.5°	852.4	818.4	791.1	756.6	721.0	676.0	646.3	628.1	612.9	601.4	592.8
20°	816.9	782.1	753.2	701.0	653.2	622.6	600.8	586.8	571.0	558.6	551.7
22.5°	779.4	743.3	703.7	645.5	608.2	583.7	564.2	548.2	537.5	527.8	521.6
25°	726.3	686.7	621.5	581.5	551.4	525.7	512.1	502.3	491.0	477.8	471.8
27.5°	670.2	607.2	560.4	530.7	501.9	485.2	473.0	458.4	448.3	442.3	436.1
30°	628.2	565.3	528.8	496.2	475.9	457.5	443.1	434.8	425.1	414.9	410.7
32.5°	581.5	531.2	496.1	469.2	448.5	432.7	421.4	408.0	400.9	394.7	386.0
35°	523.4	485.3	453.3	431.4	411.8	399.0	385.8	377.9	365.1	359.8	356.4
37.5°	474.2	441.2	417.3	394.3	378.7	364.6	356.5	343.9	338.3	330.9	323.8
40°	446.5	414.0	391.1	372.2	354.9	344.3	334.2	324.0	315.7	312.3	303.6
42.5°	418.2	391.7	368.7	348.1	336.5	325.3	312.5	305.0	296.3	290.8	285.5
45°	379.0	355.7	336.0	319.0	306.2	294.6	286.2	273.8	268.9	257.9	253.4
47.5°	344.6	322.9	304.2	288.0	275.5	267.9	255.8	246.0	238.2	231.5	225.7
50°	320.1	302.1	284.0	269.6	258.3	247.4	235.0	230.0	217.9	214.6	211.2
52.5°	297.8	280.6	264.1	250.0	238.7	228.1	217.1	210.8	202.6	199.1	196.7
55°	266.6	250.0	234.2	221.8	210.5	199.4	192.7	184.8	181.0	178.3	175.3
57.5°	235.2	220.4	208.1	195.6	184.2	175.5	167.6	162.9	159.0	155.5	151.9
60°	215.3	201.0	190.1	178.3	166.7	159.6	153.5	147.8	143.3	138.0	136.5
62.5°	194.2	181.7	171.7	160.3	150.1	143.5	137.8	132.5	127.0	119.4	117.2
65°	165.2	155.4	144.8	135.4	126.3	120.0	111.6	105.6	103.3	102.6	102.2
67.5°	139.0	129.7	120.6	111.0	102.7	96.7	92.5	91.6	90.1	89.6	88.6
70°	121.4	112.8	103.7	94.6	86.7	85.6	84.1	82.6	80.7	80.0	79.2
72.5°	105.7	96.7	87.8	80.5	77.1	75.6	74.1	72.6	71.4	70.6	70.2
75°	81.1	72.8	66.8	64.1	62.2	61.1	58.9	57.7	57.0	55.8	55.4
77.5°	58.4	53.7	50.9	49.3	47.3	46.0	44.8	43.6	42.8	42.6	42.0
80°	44.5	42.2	40.4	38.1	37.4	35.9	35.4	34.3	34.7	33.5	33.5
82.5°	34.5	31.7	30.1	29.1	28.3	27.1	26.7	26.2	26.3	25.4	25.4
85°	17.8	17.0	16.3	15.5	15.5	14.3	14.7	14.3	14.3	13.5	13.2
87.5°	7.7	7.8	8.0	9.1	10.0	9.9	9.7	9.3	9.0	9.3	9.1
90°	9.5	11.8	15.8	21.3	26.1	26.9	26.1	25.2	23.7	25.2	26.1
92.5°	28.4	35.9	53.7	78.8	101.2	102.6	86.6	68.9	59.1	52.4	47.6
95°	58.4	77.4	113.7	182.4	274.0	309.4	270.7	206.8	158.6	125.5	108.2
97.5°	82.9	104.3	150.0	245.7	397.9	528.3	554.2	482.6	394.9	309.4	252.5
100°	98.7	120.8	162.6	258.9	429.4	623.6	737.3	720.7	622.9	514.7	419.2
102.5°	113.2	135.3	174.0	259.5	417.5	626.8	805.5	876.8	854.6	775.5	674.3
105°	134.2	156.3	193.4	263.7	393.9	584.9	795.0	959.2	1048.3	1058.6	1032.6
107.5°	155.0	177.3	213.3	274.6	382.2	540.1	725.6	899.8	1034.1	1116.2	1154.5
110°	169.0	191.9	226.5	283.4	379.7	518.7	682.1	848.6	990.0	1091.0	1155.7



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.2	205.7	239.2	292.9	380.3	504.7	651.8	801.9	937.5	1045.5	1119.7
115°	203.7	225.0	258.9	307.1	383.6	489.5	614.2	744.4	866.0	969.4	1050.7
117.5°	223.6	245.7	277.1	322.2	389.3	482.0	590.5	701.1	807.9	901.7	978.0
120°	236.8	258.9	289.7	332.3	393.1	477.6	577.8	679.6	777.6	861.2	933.1
122.5°	250.0	272.9	301.7	341.2	397.6	475.0	567.1	662.7	752.3	831.5	896.5
125°	269.2	291.2	319.7	355.3	404.1	470.5	551.8	637.8	719.1	788.6	847.8
127.5°	286.1	308.8	336.5	368.3	411.0	467.8	537.6	613.4	686.9	752.5	807.1
130°	296.8	318.9	346.6	376.6	416.1	466.6	528.2	597.5	665.5	727.8	779.9
132.5°	306.9	329.0	355.4	384.8	421.1	466.0	520.6	582.4	645.3	702.6	751.5
135°	320.5	342.6	367.9	395.5	427.1	464.9	510.0	561.3	613.4	665.5	709.6
137.5°	332.5	353.0	378.0	403.7	432.4	464.8	502.5	544.4	587.9	629.3	667.8
140°	339.4	360.0	383.6	408.1	434.9	464.1	498.2	533.6	571.6	607.8	642.6
142.5°	345.8	365.1	388.1	411.9	436.9	464.1	493.7	524.8	557.0	588.2	617.3
145°	356.0	373.3	394.8	416.8	438.9	462.6	487.9	512.3	538.4	562.9	585.7
147.5°	364.6	380.0	400.1	419.5	439.6	459.8	481.9	502.7	523.2	542.3	559.1
150°	370.2	384.5	402.6	420.7	438.9	457.9	476.8	495.7	513.1	529.7	543.9
152.5°	375.9	388.9	405.2	421.4	437.7	454.7	472.4	488.8	504.9	519.0	531.3
155°	383.6	395.5	408.9	422.3	435.8	449.2	464.1	479.2	491.8	503.6	512.3
157.5°	390.3	400.2	411.6	422.3	432.1	443.5	456.5	468.0	478.6	488.5	495.2
160°	394.8	403.3	412.8	422.3	430.2	439.7	450.8	461.0	469.7	478.4	483.9
162.5°	398.5	405.3	413.5	421.7	428.4	436.6	445.7	454.0	461.5	468.9	473.2
165°	402.6	407.4	414.4	420.0	424.7	430.2	437.4	443.6	449.2	454.7	457.9
167.5°	406.1	409.1	414.2	418.9	421.1	424.7	429.1	433.7	438.0	441.7	444.6
170°	407.4	409.7	413.6	417.6	419.2	421.5	424.7	428.7	431.0	434.1	435.8
172.5°	408.6	410.3	413.0	415.7	416.7	417.8	420.3	422.9	424.7	427.3	428.2
175°	409.7	410.5	412.0	413.6	412.8	413.6	414.4	416.8	417.6	418.4	419.2
177.5°	410.5	410.5	411.1	412.4	411.1	410.5	411.1	412.4	412.4	413.0	413.0
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1042.2	1042.8	1041.9	1042.5	1041.9	1042.8	1042.2	1045.5	1046.1	1046.7	1046.1
5°	971.1	966.5	965.8	964.7	965.8	966.5	971.1	973.0	974.5	977.4	982.8
7.5°	886.2	885.4	883.6	880.9	883.6	885.4	886.2	892.6	897.8	903.6	914.4
10°	831.5	829.7	829.3	826.7	829.3	829.7	831.5	839.8	845.9	854.1	868.9
12.5°	767.6	755.5	754.2	747.6	754.2	755.5	767.6	778.3	794.6	802.5	818.2
15°	653.6	651.3	643.8	638.8	643.8	651.3	653.6	662.6	668.6	690.5	715.8
17.5°	588.3	581.0	578.7	577.6	578.7	581.0	588.3	592.8	601.4	612.9	628.1
20°	546.4	539.7	538.6	537.8	538.6	539.7	546.4	551.7	558.6	571.0	586.8
22.5°	517.5	510.4	507.5	505.2	507.5	510.4	517.5	521.6	527.8	537.5	548.2
25°	468.0	465.3	463.8	463.1	463.8	465.3	468.0	471.8	477.8	491.0	502.3
27.5°	429.3	423.5	422.3	420.4	422.3	423.5	429.3	436.1	442.3	448.3	458.4
30°	407.3	405.4	402.7	400.5	402.7	405.4	407.3	410.7	414.9	425.1	434.8
32.5°	381.3	379.8	377.4	376.4	377.4	379.8	381.3	386.0	394.7	400.9	408.0
35°	352.6	347.3	345.1	341.6	345.1	347.3	352.6	356.4	359.8	365.1	377.9
37.5°	322.2	319.4	316.3	317.4	316.3	319.4	322.2	323.8	330.9	338.3	343.9
40°	298.7	296.8	296.0	295.7	296.0	296.8	298.7	303.6	312.3	315.7	324.0
42.5°	279.9	274.8	272.8	272.8	272.8	274.8	279.9	285.5	290.8	296.3	305.0
45°	251.6	246.6	243.3	243.6	243.3	246.6	251.6	253.4	257.9	268.9	273.8
47.5°	222.5	222.3	220.2	220.9	220.2	222.3	222.5	225.7	231.5	238.2	246.0
50°	208.5	206.3	204.8	205.1	204.8	206.3	208.5	211.2	214.6	217.9	230.0
52.5°	195.3	193.3	192.1	193.7	192.1	193.3	195.3	196.7	199.1	202.6	210.8
55°	173.5	171.2	170.9	170.5	170.9	171.2	173.5	175.3	178.3	181.0	184.8
57.5°	149.2	147.6	145.3	144.4	145.3	147.6	149.2	151.9	155.5	159.0	162.9
60°	131.6	128.6	124.8	124.4	124.8	128.6	131.6	136.5	138.0	143.3	147.8
62.5°	115.6	115.0	114.3	114.2	114.3	115.0	115.6	117.2	119.4	127.0	132.5
65°	101.5	101.1	101.5	101.8	101.5	101.1	101.5	102.2	102.6	103.3	105.6
67.5°	88.4	87.8	87.1	87.4	87.1	87.8	88.4	88.6	89.6	90.1	91.6
70°	78.5	78.1	77.7	77.7	77.7	78.1	78.5	79.2	80.0	80.7	82.6
72.5°	68.8	68.7	68.4	68.1	68.4	68.7	68.8	70.2	70.6	71.4	72.6
75°	55.0	54.3	54.3	54.3	54.3	54.3	55.0	55.4	55.8	57.0	57.7
77.5°	41.9	41.6	41.2	40.9	41.2	41.6	41.9	42.0	42.6	42.8	43.6
80°	33.2	32.8	32.4	32.4	32.4	32.8	33.2	33.5	33.5	34.7	34.3
82.5°	25.3	24.9	24.8	24.5	24.8	24.9	25.3	25.4	25.4	26.3	26.2
85°	13.5	13.9	13.5	14.3	13.5	13.9	13.5	13.2	13.5	14.3	14.3
87.5°	9.1	8.8	9.1	8.8	9.1	8.8	9.1	9.1	9.3	9.0	9.3
90°	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	25.2	23.7	25.2
92.5°	46.9	44.3	45.0	43.7	45.0	44.3	46.9	47.6	52.4	59.1	68.9
95°	97.9	91.6	89.2	90.0	89.2	91.6	97.9	108.2	125.5	158.6	206.8
97.5°	214.7	195.3	183.8	177.1	183.8	195.3	214.7	252.5	309.4	394.9	482.6
100°	353.7	319.7	296.8	282.6	296.8	319.7	353.7	419.2	514.7	622.9	720.7
102.5°	603.1	545.1	516.5	497.4	516.5	545.1	603.1	674.3	775.5	854.6	876.8
105°	983.6	934.6	900.7	889.7	900.7	934.6	983.6	1032.6	1058.6	1048.3	959.2
107.5°	1160.6	1157.9	1151.1	1136.4	1151.1	1157.9	1160.6	1154.5	1116.2	1034.1	899.8
110°	1189.6	1204.7	1211.7	1210.9	1211.7	1204.7	1189.6	1155.7	1091.0	990.0	848.6



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1166.9	1192.0	1205.5	1209.7	1205.5	1192.0	1166.9	1119.7	1045.5	937.5	801.9
115°	1106.7	1143.1	1163.6	1170.7	1163.6	1143.1	1106.7	1050.7	969.4	866.0	744.4
117.5°	1035.1	1073.5	1095.1	1101.1	1095.1	1073.5	1035.1	978.0	901.7	807.9	701.1
120°	988.4	1025.4	1048.3	1056.2	1048.3	1025.4	988.4	933.1	861.2	777.6	679.6
122.5°	946.0	982.5	1002.9	1009.5	1002.9	982.5	946.0	896.5	831.5	752.3	662.7
125°	893.6	923.6	943.3	949.7	943.3	923.6	893.6	847.8	788.6	719.1	637.8
127.5°	847.1	875.1	892.2	897.3	892.2	875.1	847.1	807.1	752.5	686.9	613.4
130°	818.6	845.5	861.2	867.6	861.2	845.5	818.6	779.9	727.8	665.5	597.5
132.5°	789.6	816.4	830.9	836.6	830.9	816.4	789.6	751.5	702.6	645.3	582.4
135°	743.7	769.7	783.9	787.1	783.9	769.7	743.7	709.6	665.5	613.4	561.3
137.5°	698.8	721.2	733.7	738.4	733.7	721.2	698.8	667.8	629.3	587.9	544.4
140°	667.8	688.3	700.2	705.0	700.2	688.3	667.8	642.6	607.8	571.6	533.6
142.5°	641.4	659.9	670.6	671.5	670.6	659.9	641.4	617.3	588.2	557.0	524.8
145°	604.7	618.1	626.0	628.3	626.0	618.1	604.7	585.7	562.9	538.4	512.3
147.5°	574.7	585.4	590.8	592.2	590.8	585.4	574.7	559.1	542.3	523.2	502.7
150°	555.7	565.2	570.0	570.8	570.0	565.2	555.7	543.9	529.7	513.1	495.7
152.5°	540.6	548.8	552.3	552.4	552.3	548.8	540.6	531.3	519.0	504.9	488.8
155°	521.0	526.5	529.7	528.2	529.7	526.5	521.0	512.3	503.6	491.8	479.2
157.5°	501.4	506.0	507.5	507.5	507.5	506.0	501.4	495.2	488.5	478.6	468.0
160°	489.5	493.4	494.1	494.1	494.1	493.4	489.5	483.9	478.4	469.7	461.0
162.5°	478.7	481.4	482.2	481.5	482.2	481.4	478.7	473.2	468.9	461.5	454.0
165°	461.0	464.1	464.1	463.4	464.1	464.1	461.0	457.9	454.7	449.2	443.6
167.5°	446.1	447.8	447.6	446.7	447.6	447.8	446.1	444.6	441.7	438.0	433.7
170°	436.6	438.9	438.1	436.6	438.1	438.9	436.6	435.8	434.1	431.0	428.7
172.5°	429.0	430.1	429.3	428.4	429.3	430.1	429.0	428.2	427.3	424.7	422.9
175°	419.2	420.0	419.2	417.6	419.2	420.0	419.2	419.2	418.4	417.6	416.8
177.5°	413.0	413.0	412.4	411.1	412.4	413.0	413.0	413.0	413.0	412.4	412.4
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1043.7	1047.9	1054.3	1057.9	1063.9	1067.8	1070.0	1073.9	1076.0	1083.6	1091.4
5°	985.4	991.5	1002.0	1011.8	1022.4	1033.3	1041.3	1050.3	1058.5	1072.9	1088.0
7.5°	918.6	927.0	943.3	959.0	977.3	992.8	1006.4	1021.9	1035.7	1056.2	1077.6
10°	868.5	883.2	904.7	919.4	943.5	959.0	980.5	997.4	1016.7	1043.9	1068.0
12.5°	825.4	843.1	860.4	880.8	902.5	928.3	951.9	973.6	996.5	1024.6	1052.9
15°	747.1	772.7	799.5	820.2	849.7	876.8	904.3	933.7	961.7	995.2	1032.2
17.5°	646.3	676.0	721.0	756.6	791.1	818.4	852.4	888.1	920.9	961.4	1002.5
20°	600.8	622.6	653.2	701.0	753.2	782.1	816.9	856.1	893.7	937.9	982.0
22.5°	564.2	583.7	608.2	645.5	703.7	743.3	779.4	819.3	863.0	908.1	956.9
25°	512.1	525.7	551.4	581.5	621.5	686.7	726.3	766.3	813.9	862.1	917.9
27.5°	473.0	485.2	501.9	530.7	560.4	607.2	670.2	713.8	761.1	815.5	873.4
30°	443.1	457.5	475.9	496.2	528.8	565.3	628.2	678.8	725.6	781.4	843.2
32.5°	421.4	432.7	448.5	469.2	496.1	531.2	581.5	642.9	688.4	747.3	811.8
35°	385.8	399.0	411.8	431.4	453.3	485.3	523.4	589.1	634.3	692.4	757.3
37.5°	356.5	364.6	378.7	394.3	417.3	441.2	474.2	533.1	582.1	639.0	705.5
40°	334.2	344.3	354.9	372.2	391.1	414.0	446.5	490.3	546.4	602.3	667.1
42.5°	312.5	325.3	336.5	348.1	368.7	391.7	418.2	455.2	512.6	565.4	628.5
45°	286.2	294.6	306.2	319.0	336.0	355.7	379.0	411.4	466.5	512.1	571.4
47.5°	255.8	267.9	275.5	288.0	304.2	322.9	344.6	372.6	417.3	460.0	514.9
50°	235.0	247.4	258.3	269.6	284.0	302.1	320.1	347.3	383.1	428.1	479.3
52.5°	217.1	228.1	238.7	250.0	264.1	280.6	297.8	321.6	352.3	393.6	443.4
55°	192.7	199.4	210.5	221.8	234.2	250.0	266.6	286.6	313.1	347.7	388.1
57.5°	167.6	175.5	184.2	195.6	208.1	220.4	235.2	253.4	274.2	305.6	340.1
60°	153.5	159.6	166.7	178.3	190.1	201.0	215.3	230.5	250.0	277.2	306.6
62.5°	137.8	143.5	150.1	160.3	171.7	181.7	194.2	210.3	226.8	251.6	277.3
65°	111.6	120.0	126.3	135.4	144.8	155.4	165.2	178.0	192.7	212.3	235.3
67.5°	92.5	96.7	102.7	111.0	120.6	129.7	139.0	149.0	161.7	176.8	195.1
70°	84.1	85.6	86.7	94.6	103.7	112.8	121.4	130.9	141.8	154.2	170.1
72.5°	74.1	75.6	77.1	80.5	87.8	96.7	105.7	112.8	123.1	133.4	146.2
75°	58.9	61.1	62.2	64.1	66.8	72.8	81.1	87.9	93.9	101.8	112.0
77.5°	44.8	46.0	47.3	49.3	50.9	53.7	58.4	64.5	70.2	74.7	81.8
80°	35.4	35.9	37.4	38.1	40.4	42.2	44.5	49.4	55.0	57.0	61.8
82.5°	26.7	27.1	28.3	29.1	30.1	31.7	34.5	35.9	40.3	42.7	45.8
85°	14.7	14.3	15.5	15.5	16.3	17.0	17.8	19.6	20.7	23.7	24.5
87.5°	9.7	9.9	10.0	9.1	8.0	7.8	7.7	7.6	7.9	8.2	8.9
90°	26.1	26.9	26.1	21.3	15.8	11.8	9.5	7.9	6.4	3.1	0.8
92.5°	86.6	102.6	101.2	78.8	53.7	35.9	28.4	23.0	19.6	13.9	9.6
95°	270.7	309.4	274.0	182.4	113.7	77.4	58.4	45.7	38.7	30.8	27.7
97.5°	554.2	528.3	397.9	245.7	150.0	104.3	82.9	68.4	57.7	49.3	45.0
100°	737.3	623.6	429.4	258.9	162.6	120.8	98.7	82.9	70.3	63.1	60.8
102.5°	805.5	626.8	417.5	259.5	174.0	135.3	113.2	96.7	84.1	77.1	75.3
105°	795.0	584.9	393.9	263.7	193.4	156.3	134.2	116.8	105.0	99.5	96.3
107.5°	725.6	540.1	382.2	274.6	213.3	177.3	155.0	137.8	126.9	121.6	119.1
110°	682.1	518.7	379.7	283.4	226.5	191.9	169.0	152.4	142.1	137.3	134.2



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	651.8	504.7	380.3	292.9	239.2	205.7	182.2	166.2	156.6	151.3	148.0
115°	614.2	489.5	383.6	307.1	258.9	225.0	203.7	187.8	178.4	173.7	169.8
117.5°	590.5	482.0	389.3	322.2	277.1	245.7	223.6	208.4	200.1	195.3	192.2
120°	577.8	477.6	393.1	332.3	289.7	258.9	236.8	221.1	213.9	209.2	206.0
122.5°	567.1	475.0	397.6	341.2	301.7	272.9	250.0	234.3	226.5	221.9	219.3
125°	551.8	470.5	404.1	355.3	319.7	291.2	269.2	253.4	243.9	239.2	236.8
127.5°	537.6	467.8	411.0	368.3	336.5	308.8	286.1	270.9	260.5	253.9	250.7
130°	528.2	466.6	416.1	376.6	346.6	318.9	296.8	281.0	269.9	262.1	258.9
132.5°	520.6	466.0	421.1	384.8	355.4	329.0	306.9	290.5	278.8	270.3	266.5
135°	510.0	464.9	427.1	395.5	367.9	342.6	320.5	302.4	290.5	281.0	277.9
137.5°	502.5	464.8	432.4	403.7	378.0	353.0	332.5	314.5	301.8	292.4	288.6
140°	498.2	464.1	434.9	408.1	383.6	360.0	339.4	322.0	309.4	299.9	296.8
142.5°	493.7	464.1	436.9	411.9	388.1	365.1	345.8	329.0	316.4	307.6	305.0
145°	487.9	462.6	438.9	416.8	394.8	373.3	356.0	340.2	328.4	320.5	317.3
147.5°	481.9	459.8	439.6	419.5	400.1	380.0	364.6	351.4	340.5	333.0	330.6
150°	476.8	457.9	438.9	420.7	402.6	384.5	370.2	358.4	348.1	341.8	339.4
152.5°	472.4	454.7	437.7	421.4	405.2	388.9	375.9	364.7	355.7	349.4	348.3
155°	464.1	449.2	435.8	422.3	408.9	395.5	383.6	375.0	366.3	361.5	360.7
157.5°	456.5	443.5	432.1	422.3	411.6	400.2	390.3	383.3	375.8	371.9	371.2
160°	450.8	439.7	430.2	422.3	412.8	403.3	394.8	388.4	382.0	378.9	378.1
162.5°	445.7	436.6	428.4	421.7	413.5	405.3	398.5	392.8	387.8	384.6	385.1
165°	437.4	430.2	424.7	420.0	414.4	407.4	402.6	398.7	393.9	392.3	393.1
167.5°	429.1	424.7	421.1	418.9	414.2	409.1	406.1	403.2	400.2	398.8	399.8
170°	424.7	421.5	419.2	417.6	413.6	409.7	407.4	405.8	403.3	402.6	404.1
172.5°	420.3	417.8	416.7	415.7	413.0	410.3	408.6	407.7	405.3	405.8	406.7
175°	414.4	413.6	412.8	413.6	412.0	410.5	409.7	409.7	408.1	408.9	409.7
177.5°	411.1	410.5	411.1	412.4	411.1	410.5	410.5	410.5	409.2	409.9	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1091.7	1092.6	1098.6	1101.4	1106.8	1108.9	1111.3	1110.6	1110.6	1111.9	1120.3
5°	1094.0	1101.6	1112.9	1123.8	1134.4	1143.5	1149.4	1155.5	1157.7	1168.7	1178.5
7.5°	1090.1	1104.0	1122.7	1139.3	1159.3	1175.0	1187.9	1199.6	1207.6	1223.6	1239.8
10°	1085.0	1104.6	1125.7	1147.2	1174.8	1195.5	1216.6	1232.8	1238.1	1261.8	1275.5
12.5°	1074.7	1101.0	1127.8	1155.7	1182.6	1211.1	1234.4	1250.6	1269.2	1290.5	1315.6
15°	1059.3	1089.5	1124.6	1160.4	1198.9	1233.6	1258.5	1286.8	1307.1	1330.5	1352.3
17.5°	1037.2	1076.1	1120.6	1162.2	1206.6	1243.9	1278.2	1305.3	1319.6	1332.9	1336.3
20°	1019.8	1061.6	1114.0	1163.1	1207.5	1250.5	1284.4	1307.1	1310.9	1311.2	1291.2
22.5°	1000.8	1048.0	1102.9	1153.1	1206.3	1254.2	1280.5	1290.2	1275.3	1249.7	1211.0
25°	965.8	1020.5	1084.2	1141.6	1199.6	1244.9	1253.9	1237.0	1184.6	1129.4	1059.8
27.5°	928.0	989.4	1057.7	1121.5	1183.4	1211.4	1191.8	1130.6	1036.2	954.2	854.7
30°	900.2	969.2	1036.3	1107.6	1164.9	1177.0	1132.2	1042.0	931.9	808.2	709.0
32.5°	868.5	940.8	1014.6	1088.3	1136.3	1124.5	1050.4	939.4	810.3	688.7	594.9
35°	823.2	898.0	977.4	1051.4	1082.0	1031.1	920.2	775.8	643.8	530.3	465.7
37.5°	771.0	852.3	935.0	1002.9	1000.8	915.8	764.9	615.7	504.8	437.7	391.7
40°	733.9	816.1	905.4	962.8	938.3	827.8	664.1	523.4	442.3	388.8	355.3
42.5°	698.3	780.8	869.6	915.1	872.5	736.7	573.6	463.4	396.5	354.8	327.5
45°	637.7	724.8	807.1	832.3	756.1	606.4	463.8	384.0	339.4	308.5	289.6
47.5°	578.6	664.2	739.2	739.7	636.6	491.8	391.3	332.2	294.3	270.3	256.6
50°	542.3	623.8	686.7	676.9	560.1	437.5	349.9	299.0	267.4	248.9	234.6
52.5°	501.6	580.6	635.1	607.2	495.1	385.0	312.9	270.1	243.9	227.8	215.0
55°	442.3	512.5	551.0	508.8	403.9	320.1	264.4	230.8	211.2	197.6	186.7
57.5°	384.3	442.0	466.3	417.1	332.6	265.5	223.6	198.4	178.9	169.3	163.6
60°	347.7	397.1	414.0	359.8	289.2	232.3	198.0	174.6	160.3	153.9	148.2
62.5°	311.8	352.1	359.2	309.4	252.2	203.4	173.9	154.1	144.6	138.5	133.1
65°	258.7	287.7	284.4	244.4	199.4	161.4	139.9	127.8	120.7	112.0	102.6
67.5°	213.0	230.8	220.0	190.1	152.3	125.4	111.4	102.3	93.4	85.1	83.0
70°	184.0	194.2	182.9	155.4	124.8	105.2	93.9	83.0	77.7	75.8	72.4
72.5°	156.3	159.9	147.6	124.0	101.6	87.2	76.1	70.0	67.2	65.5	63.3
75°	117.2	114.6	104.1	85.6	70.5	60.7	57.4	55.0	53.2	51.7	50.5
77.5°	82.4	78.5	69.1	57.1	49.1	44.4	42.4	41.2	40.3	39.5	38.4
80°	61.8	59.2	49.8	40.7	37.4	35.0	33.9	32.4	32.4	31.7	30.5
82.5°	45.2	42.3	34.1	29.9	28.0	26.7	25.8	24.8	24.5	24.7	23.9
85°	23.7	19.2	17.0	16.3	15.0	14.3	14.7	13.9	13.9	13.9	13.5
87.5°	7.9	7.0	7.0	7.1	7.8	8.6	9.4	10.3	10.8	10.3	10.5
90°	3.1	6.4	7.9	9.5	11.8	15.8	21.3	26.1	26.9	26.1	25.2
92.5°	13.9	19.6	23.0	28.4	35.9	53.7	78.8	101.2	102.6	86.6	68.9
95°	30.8	38.7	45.7	58.4	77.4	113.7	182.4	274.0	309.4	270.7	206.8
97.5°	49.3	57.7	68.4	82.9	104.3	150.0	245.7	397.9	528.3	554.2	482.6
100°	63.1	70.3	82.9	98.7	120.8	162.6	258.9	429.4	623.6	737.3	720.7
102.5°	77.1	84.1	96.7	113.2	135.3	174.0	259.5	417.5	626.8	805.5	876.8
105°	99.5	105.0	116.8	134.2	156.3	193.4	263.7	393.9	584.9	795.0	959.2
107.5°	121.6	126.9	137.8	155.0	177.3	213.3	274.6	382.2	540.1	725.6	899.8
110°	137.3	142.1	152.4	169.0	191.9	226.5	283.4	379.7	518.7	682.1	848.6



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	151.3	156.6	166.2	182.2	205.7	239.2	292.9	380.3	504.7	651.8	801.9
115°	173.7	178.4	187.8	203.7	225.0	258.9	307.1	383.6	489.5	614.2	744.4
117.5°	195.3	200.1	208.4	223.6	245.7	277.1	322.2	389.3	482.0	590.5	701.1
120°	209.2	213.9	221.1	236.8	258.9	289.7	332.3	393.1	477.6	577.8	679.6
122.5°	221.9	226.5	234.3	250.0	272.9	301.7	341.2	397.6	475.0	567.1	662.7
125°	239.2	243.9	253.4	269.2	291.2	319.7	355.3	404.1	470.5	551.8	637.8
127.5°	253.9	260.5	270.9	286.1	308.8	336.5	368.3	411.0	467.8	537.6	613.4
130°	262.1	269.9	281.0	296.8	318.9	346.6	376.6	416.1	466.6	528.2	597.5
132.5°	270.3	278.8	290.5	306.9	329.0	355.4	384.8	421.1	466.0	520.6	582.4
135°	281.0	290.5	302.4	320.5	342.6	367.9	395.5	427.1	464.9	510.0	561.3
137.5°	292.4	301.8	314.5	332.5	353.0	378.0	403.7	432.4	464.8	502.5	544.4
140°	299.9	309.4	322.0	339.4	360.0	383.6	408.1	434.9	464.1	498.2	533.6
142.5°	307.6	316.4	329.0	345.8	365.1	388.1	411.9	436.9	464.1	493.7	524.8
145°	320.5	328.4	340.2	356.0	373.3	394.8	416.8	438.9	462.6	487.9	512.3
147.5°	333.0	340.5	351.4	364.6	380.0	400.1	419.5	439.6	459.8	481.9	502.7
150°	341.8	348.1	358.4	370.2	384.5	402.6	420.7	438.9	457.9	476.8	495.7
152.5°	349.4	355.7	364.7	375.9	388.9	405.2	421.4	437.7	454.7	472.4	488.8
155°	361.5	366.3	375.0	383.6	395.5	408.9	422.3	435.8	449.2	464.1	479.2
157.5°	371.9	375.8	383.3	390.3	400.2	411.6	422.3	432.1	443.5	456.5	468.0
160°	378.9	382.0	388.4	394.8	403.3	412.8	422.3	430.2	439.7	450.8	461.0
162.5°	384.6	387.8	392.8	398.5	405.3	413.5	421.7	428.4	436.6	445.7	454.0
165°	392.3	393.9	398.7	402.6	407.4	414.4	420.0	424.7	430.2	437.4	443.6
167.5°	398.8	400.2	403.2	406.1	409.1	414.2	418.9	421.1	424.7	429.1	433.7
170°	402.6	403.3	405.8	407.4	409.7	413.6	417.6	419.2	421.5	424.7	428.7
172.5°	405.8	405.3	407.7	408.6	410.3	413.0	415.7	416.7	417.8	420.3	422.9
175°	408.9	408.1	409.7	409.7	410.5	412.0	413.6	412.8	413.6	414.4	416.8
177.5°	409.9	409.2	410.5	410.5	410.5	411.1	412.4	411.1	410.5	411.1	412.4
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1123.4	1127.3	1129.1	1129.1	1131.3	1130.3	1129.4
5°	1187.9	1195.1	1196.6	1203.4	1208.3	1206.8	1207.5
7.5°	1252.1	1263.6	1275.1	1280.2	1281.1	1284.1	1285.3
10°	1291.6	1301.1	1318.8	1316.2	1329.4	1336.9	1324.4
12.5°	1329.7	1342.4	1354.7	1358.1	1365.5	1368.0	1363.0
15°	1364.0	1370.8	1371.6	1369.7	1372.0	1370.1	1362.9
17.5°	1331.9	1320.9	1298.6	1288.0	1279.6	1267.3	1262.3
20°	1278.8	1246.4	1208.7	1193.6	1175.9	1141.1	1149.4
22.5°	1164.2	1127.2	1089.5	1045.4	1024.4	991.5	989.6
25°	985.8	922.1	851.9	802.8	774.3	741.4	727.1
27.5°	766.5	686.2	628.7	599.7	573.1	547.1	546.0
30°	622.3	561.9	517.5	492.5	476.4	465.3	467.7
32.5°	524.5	483.1	453.1	432.5	420.5	412.2	412.1
35°	428.8	400.5	381.2	372.6	364.0	357.9	358.3
37.5°	367.0	349.9	339.2	329.7	324.3	321.3	319.6
40°	335.3	321.3	313.1	307.4	302.9	298.7	297.9
42.5°	310.2	298.7	290.3	285.9	281.8	278.7	278.0
45°	275.3	265.9	258.3	253.4	251.6	248.9	248.9
47.5°	244.9	235.6	229.7	226.6	223.4	221.7	221.6
50°	224.4	217.2	212.0	210.1	207.4	206.3	205.9
52.5°	206.0	200.7	196.8	195.6	194.4	193.0	193.2
55°	181.0	178.0	176.5	175.3	173.5	171.2	172.7
57.5°	160.0	157.4	153.3	149.8	148.0	146.4	147.0
60°	145.2	139.9	134.6	130.5	129.4	125.9	125.9
62.5°	126.5	119.1	112.6	110.3	109.2	107.6	107.2
65°	97.3	94.3	92.8	91.3	90.5	90.5	89.8
67.5°	80.6	79.4	77.8	77.4	76.6	76.4	76.1
70°	71.3	69.8	69.0	68.7	67.9	68.3	67.2
72.5°	62.2	61.0	60.9	59.9	59.5	59.5	58.7
75°	49.0	49.0	48.7	48.3	47.6	47.2	47.6
77.5°	37.7	37.8	37.1	37.1	37.0	37.1	36.7
80°	30.2	30.5	30.2	29.8	29.4	29.8	29.4
82.5°	23.8	23.3	23.2	23.1	23.1	22.8	22.8
85°	13.5	13.9	13.5	13.2	13.2	13.2	13.5
87.5°	9.9	10.2	10.3	10.3	10.3	10.3	10.0
90°	23.7	25.2	26.1	26.1	26.1	26.1	26.1
92.5°	59.1	52.4	47.6	46.9	44.3	45.0	43.7
95°	158.6	125.5	108.2	97.9	91.6	89.2	90.0
97.5°	394.9	309.4	252.5	214.7	195.3	183.8	177.1
100°	622.9	514.7	419.2	353.7	319.7	296.8	282.6
102.5°	854.6	775.5	674.3	603.1	545.1	516.5	497.4
105°	1048.3	1058.6	1032.6	983.6	934.6	900.7	889.7
107.5°	1034.1	1116.2	1154.5	1160.6	1157.9	1151.1	1136.4
110°	990.0	1091.0	1155.7	1189.6	1204.7	1211.7	1210.9



TEST NUMBER: P331659-840

CATALOG NUMBER: S122RDIP-S485D725U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	937.5	1045.5	1119.7	1166.9	1192.0	1205.5	1209.7
115°	866.0	969.4	1050.7	1106.7	1143.1	1163.6	1170.7
117.5°	807.9	901.7	978.0	1035.1	1073.5	1095.1	1101.1
120°	777.6	861.2	933.1	988.4	1025.4	1048.3	1056.2
122.5°	752.3	831.5	896.5	946.0	982.5	1002.9	1009.5
125°	719.1	788.6	847.8	893.6	923.6	943.3	949.7
127.5°	686.9	752.5	807.1	847.1	875.1	892.2	897.3
130°	665.5	727.8	779.9	818.6	845.5	861.2	867.6
132.5°	645.3	702.6	751.5	789.6	816.4	830.9	836.6
135°	613.4	665.5	709.6	743.7	769.7	783.9	787.1
137.5°	587.9	629.3	667.8	698.8	721.2	733.7	738.4
140°	571.6	607.8	642.6	667.8	688.3	700.2	705.0
142.5°	557.0	588.2	617.3	641.4	659.9	670.6	671.5
145°	538.4	562.9	585.7	604.7	618.1	626.0	628.3
147.5°	523.2	542.3	559.1	574.7	585.4	590.8	592.2
150°	513.1	529.7	543.9	555.7	565.2	570.0	570.8
152.5°	504.9	519.0	531.3	540.6	548.8	552.3	552.4
155°	491.8	503.6	512.3	521.0	526.5	529.7	528.2
157.5°	478.6	488.5	495.2	501.4	506.0	507.5	507.5
160°	469.7	478.4	483.9	489.5	493.4	494.1	494.1
162.5°	461.5	468.9	473.2	478.7	481.4	482.2	481.5
165°	449.2	454.7	457.9	461.0	464.1	464.1	463.4
167.5°	438.0	441.7	444.6	446.1	447.8	447.6	446.7
170°	431.0	434.1	435.8	436.6	438.9	438.1	436.6
172.5°	424.7	427.3	428.2	429.0	430.1	429.3	428.4
175°	417.6	418.4	419.2	419.2	420.0	419.2	417.6
177.5°	412.4	413.0	413.0	413.0	413.0	412.4	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5

(END OF REPORT)