

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331695-840

Luminaire Tested: **S122RDIP-S675D925U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331695-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S675D925U840-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6215.6 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	89	86	88	85	81	79	70	68	66	56	55	53	43	43	42	36
2	88	81	76	71	80	75	70	66	62	58	55	50	48	46	39	38	36	31
3	81	72	65	60	74	66	60	56	55	51	47	45	42	39	35	33	32	27
4	74	64	57	51	68	59	53	48	49	45	41	40	37	34	32	30	28	24
5	69	58	50	44	63	53	47	42	45	40	36	37	33	30	29	27	25	21
6	63	52	44	39	58	48	41	36	40	35	32	33	30	27	27	24	22	19
7	59	47	40	34	54	44	37	32	37	32	28	31	27	24	25	22	20	17
8	55	43	36	31	50	40	33	29	34	29	25	28	24	22	23	20	18	16
9	51	39	32	27	47	37	30	26	31	26	23	26	22	20	21	19	17	15
10	48	36	29	25	44	34	28	23	29	24	21	24	21	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23954	23954	23954	23954
5°	26752	24104	21371	24104
10°	29681	23935	18525	23935
15°	31141	23584	14596	23584
20°	26996	23063	12631	23063
25°	17706	22352	11277	22352
30°	11917	21490	10206	21490
35°	9652	20402	9207	20402
40°	8585	19220	8517	19220
45°	7768	17831	7606	17831
50°	7068	16458	7043	16458
55°	6646	14933	6559	14933
60°	5561	13533	5493	13533
65°	4688	12287	5318	12287
70°	4334	10976	5013	10976
75°	4049	9551	4629	9551
80°	3738	7857	4119	7857
85°	3446	6206	3631	6206



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.6	2.3
10°-20°	391.9	6.3
20°-30°	505.0	8.1
30°-40°	479.9	7.7
40°-50°	411.1	6.6
50°-60°	313.0	5.0
60°-70°	197.9	3.2
70°-80°	98.8	1.6
80°-90°	30.4	0.5
90°-100°	209.6	3.4
100°-110°	711.1	11.4
110°-120°	755.5	12.2
120°-130°	621.9	10.0
130°-140°	499.4	8.0
140°-150°	377.4	6.1
150°-160°	265.2	4.3
160°-170°	156.1	2.5
170°-180°	50.8	0.8
0°-30°	1037.5	16.7
0°-40°	1517.4	24.4
0°-60°	2241.5	36.1
0°-90°	2568.7	41.3
90°-120°	1676.1	27.0
90°-150°	3174.8	51.1
90°-180°	3647.0	58.7
0°-180°	6215.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1484	1484	1484	1484	1484	
5°	1651	1487	1319	1487	1651	163
15°	1863	1411	873	1411	1863	503
25°	994	1255	633	1255	994	472
35°	490	1035	467	1035	490	313
45°	340	781	333	781	340	263
55°	236	530	233	530	236	207
65°	123	322	139	322	123	125
75°	65	153	74	153	65	69
85°	19	34	20	34	19	21
90°	33	1	33	1	33	19
95°	115	35	115	35	115	149
105°	1136	123	1136	123	1136	1099
115°	1495	217	1495	217	1495	1464
125°	1212	302	1212	302	1212	1096
135°	1005	355	1005	355	1005	781
145°	802	405	802	405	802	510
155°	674	461	674	461	674	315
165°	592	502	592	502	592	169
175°	533	523	533	523	533	52
180°	524	524	524	524	524	



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1543.8	1545.0	1546.3	1543.4	1543.4	1540.9	1535.5	1531.5	1519.8	1518.2	1518.2
5°	1650.6	1649.5	1651.6	1645.0	1635.7	1633.6	1623.8	1610.9	1597.5	1582.6	1579.4
7.5°	1756.8	1755.2	1751.1	1750.0	1742.8	1727.3	1711.5	1694.8	1672.4	1650.7	1639.8
10°	1810.4	1827.5	1817.1	1799.1	1802.7	1778.5	1765.5	1743.4	1724.8	1692.3	1685.2
12.5°	1863.2	1869.9	1866.6	1856.3	1851.7	1834.9	1817.6	1798.3	1764.0	1734.8	1709.5
15°	1863.0	1872.8	1875.3	1872.3	1874.8	1873.8	1864.5	1848.6	1818.7	1786.7	1758.9
17.5°	1725.5	1732.2	1749.2	1760.6	1775.0	1805.5	1820.6	1826.4	1822.0	1803.8	1784.2
20°	1571.2	1559.8	1607.3	1631.5	1652.1	1703.6	1748.0	1765.0	1792.3	1791.8	1786.7
22.5°	1352.6	1355.3	1400.3	1429.1	1489.2	1540.8	1591.3	1655.4	1708.2	1743.1	1763.6
25°	993.9	1013.5	1058.3	1097.5	1164.5	1260.4	1347.5	1448.6	1543.9	1619.1	1690.8
27.5°	746.4	747.9	783.5	819.6	859.4	938.0	1047.6	1168.3	1304.2	1416.4	1545.5
30°	639.2	636.1	651.1	673.3	707.2	768.1	850.5	969.2	1104.7	1273.7	1424.3
32.5°	563.3	563.5	574.8	591.2	619.5	660.5	716.9	813.2	941.4	1107.6	1284.0
35°	489.7	489.2	497.5	509.3	521.2	547.4	586.1	636.6	724.8	879.9	1060.4
37.5°	437.0	439.2	443.2	450.6	463.7	478.4	501.6	535.5	598.2	690.0	841.7
40°	407.3	408.3	413.9	420.1	427.9	439.2	458.3	485.5	531.5	604.7	715.5
42.5°	380.0	381.0	385.1	390.8	396.9	408.3	424.0	447.7	484.8	542.0	633.4
45°	340.2	340.2	343.9	346.4	353.1	363.5	376.3	395.9	421.7	463.9	524.7
47.5°	302.9	303.0	305.4	309.8	314.1	322.0	334.8	350.7	369.5	402.2	454.1
50°	281.4	282.0	283.5	287.1	289.7	296.9	306.7	320.6	340.2	365.5	408.8
52.5°	264.2	263.8	265.8	267.3	269.1	274.3	281.6	293.9	311.3	333.4	369.2
55°	236.1	234.0	237.1	239.7	241.3	243.3	247.4	255.2	270.1	288.7	315.5
57.5°	201.1	200.3	202.4	204.8	209.6	215.2	218.6	223.6	231.4	244.7	271.2
60°	172.2	172.2	176.8	178.3	184.0	191.3	198.4	202.6	210.4	219.0	238.6
62.5°	146.6	147.0	149.2	150.8	153.9	162.8	172.9	182.0	189.2	197.6	210.7
65°	122.7	123.7	123.7	124.7	126.8	128.9	133.0	140.2	153.1	164.9	174.7
67.5°	104.1	104.4	104.7	105.7	106.3	108.6	110.2	113.4	116.4	127.6	139.8
70°	91.8	93.3	92.8	93.8	94.3	95.3	97.5	99.0	103.6	106.2	113.4
72.5°	80.2	81.3	81.2	81.9	83.2	83.4	85.0	86.6	89.6	91.8	95.6
75°	64.9	64.4	64.9	65.9	66.4	67.1	67.1	69.1	70.6	72.7	75.2
77.5°	50.1	50.6	50.5	50.6	50.7	51.6	51.5	52.5	54.0	55.0	56.2
80°	40.2	40.7	40.2	40.7	41.2	41.7	41.2	41.7	43.3	44.3	44.3
82.5°	31.1	31.2	31.5	31.6	31.7	31.8	32.6	32.7	33.8	33.6	34.0
85°	18.6	18.1	18.1	18.1	18.6	19.1	18.6	18.6	19.1	19.1	19.1
87.5°	13.2	13.6	13.6	13.6	13.6	13.4	13.0	13.8	13.6	14.2	13.6
90°	33.2	33.2	33.2	33.2	33.2	32.2	30.2	32.2	33.2	34.2	33.2
92.5°	55.8	57.5	56.7	59.9	60.7	67.0	75.4	87.9	110.7	131.0	129.2
95°	114.9	113.9	116.9	125.0	138.0	160.3	202.6	264.1	345.7	395.1	349.7
97.5°	226.2	234.6	249.3	274.2	322.3	395.1	504.1	616.2	707.5	674.5	508.0
100°	360.8	379.0	408.2	451.5	535.2	657.1	795.2	920.2	941.4	796.2	548.3
102.5°	635.0	659.5	696.0	770.0	860.9	990.2	1091.2	1119.3	1028.4	800.2	533.0
105°	1135.9	1149.9	1193.4	1255.8	1318.3	1351.6	1338.5	1224.6	1014.9	746.8	502.9
107.5°	1451.0	1469.7	1478.3	1481.8	1473.9	1425.1	1320.3	1148.8	926.5	689.6	488.0
110°	1546.1	1547.1	1538.0	1518.8	1475.5	1392.9	1263.8	1083.5	870.8	662.2	484.8



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1544.5	1539.0	1521.9	1489.9	1429.6	1334.8	1197.0	1023.8	832.1	644.4	485.5
115°	1494.7	1485.6	1459.4	1413.0	1341.5	1237.7	1105.6	950.4	784.2	624.9	489.8
117.5°	1405.7	1398.2	1370.5	1321.5	1248.6	1151.1	1031.5	895.1	753.9	615.4	497.1
120°	1348.6	1338.5	1309.2	1261.8	1191.3	1099.5	992.8	867.8	737.8	609.8	501.9
122.5°	1288.9	1280.4	1254.4	1207.8	1144.6	1061.7	960.5	846.0	724.1	606.5	507.6
125°	1212.4	1204.4	1179.2	1140.9	1082.5	1006.8	918.2	814.4	704.5	600.7	516.0
127.5°	1145.6	1139.1	1117.3	1081.5	1030.5	960.7	877.1	783.2	686.4	597.2	524.7
130°	1107.6	1099.5	1079.4	1045.2	995.8	929.3	849.6	763.0	674.3	595.6	531.2
132.5°	1068.1	1060.9	1042.4	1008.0	959.5	897.0	823.8	743.6	664.6	594.8	537.6
135°	1004.8	1000.8	982.7	949.4	906.1	849.6	783.2	716.6	651.1	593.6	545.2
137.5°	942.8	936.8	920.8	892.2	852.6	803.4	750.6	695.0	641.6	593.4	552.1
140°	900.0	894.0	878.9	852.6	820.4	776.1	729.7	681.4	636.0	592.6	555.3
142.5°	857.3	856.1	842.6	818.8	788.2	751.0	711.1	670.0	630.4	592.6	557.7
145°	802.2	799.2	789.2	772.0	747.8	718.6	687.4	654.1	622.9	590.6	560.4
147.5°	756.1	754.3	747.4	733.8	713.8	692.4	668.0	641.8	615.2	587.0	561.2
150°	728.7	727.7	721.6	709.5	694.4	676.3	655.1	633.0	608.7	584.6	560.4
152.5°	705.3	705.1	700.6	690.1	678.3	662.6	644.6	624.1	603.1	580.6	558.8
155°	674.3	676.3	672.3	665.2	654.1	643.0	627.9	611.8	592.6	573.5	556.3
157.5°	647.8	647.8	646.0	640.2	632.4	623.7	611.0	597.4	582.8	566.2	551.7
160°	631.0	631.0	630.0	624.9	617.8	610.8	599.7	588.5	575.5	561.4	549.3
162.5°	614.8	615.6	614.6	611.2	604.1	598.6	589.2	579.8	569.1	557.3	546.8
165°	591.6	592.6	592.6	588.5	584.6	580.6	573.5	566.4	558.4	549.3	542.2
167.5°	570.3	571.5	571.7	569.5	567.6	564.0	559.2	553.7	547.9	542.2	537.6
170°	557.3	559.4	560.4	557.3	556.3	554.3	550.3	547.2	542.2	538.2	535.2
172.5°	546.8	548.1	549.1	547.6	546.6	545.4	542.2	540.0	536.6	533.4	532.0
175°	533.2	535.2	536.2	535.2	535.2	534.2	533.2	532.2	529.2	528.2	527.1
177.5°	524.9	526.5	527.4	527.4	527.4	527.4	526.5	526.5	524.9	524.1	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1519.0	1515.7	1512.9	1505.4	1501.8	1493.5	1492.3	1491.9	1481.1	1470.8	1467.9
5°	1571.2	1563.0	1550.5	1536.1	1521.2	1505.7	1495.4	1487.2	1466.5	1446.9	1435.6
7.5°	1623.8	1606.1	1584.7	1557.4	1534.6	1509.0	1490.1	1473.1	1443.8	1415.7	1396.8
10°	1662.9	1634.1	1605.8	1568.1	1538.7	1509.8	1483.1	1459.9	1426.8	1389.8	1363.4
12.5°	1687.3	1655.6	1616.5	1579.6	1541.7	1504.9	1469.1	1439.3	1400.5	1362.1	1330.9
15°	1720.2	1686.2	1638.7	1586.2	1537.2	1489.2	1448.0	1410.9	1360.4	1314.5	1276.4
17.5°	1747.1	1700.3	1649.3	1588.5	1531.9	1470.9	1417.7	1370.4	1314.1	1258.8	1213.9
20°	1755.8	1709.4	1650.6	1589.7	1522.8	1451.1	1393.9	1342.3	1282.0	1221.7	1170.1
22.5°	1750.4	1714.3	1648.9	1576.2	1507.5	1432.5	1367.9	1308.1	1241.2	1179.6	1119.8
25°	1714.0	1701.6	1639.8	1560.3	1482.1	1394.9	1320.2	1254.7	1178.4	1112.5	1047.4
27.5°	1629.1	1655.9	1617.5	1533.0	1445.8	1352.4	1268.4	1193.9	1114.7	1040.5	975.7
30°	1547.5	1608.8	1592.4	1514.0	1416.5	1324.8	1230.5	1152.7	1068.1	991.8	927.9
32.5°	1435.7	1537.1	1553.2	1487.6	1386.8	1286.1	1187.2	1109.7	1021.5	941.1	878.8
35°	1257.8	1409.4	1478.9	1437.1	1336.2	1227.4	1125.3	1035.1	946.4	867.1	805.2
37.5°	1045.5	1251.9	1367.9	1370.9	1278.1	1165.0	1053.9	964.3	873.5	795.6	728.7
40°	907.8	1131.5	1282.5	1316.1	1237.7	1115.5	1003.1	911.9	823.2	746.9	670.1
42.5°	784.1	1006.9	1192.7	1250.9	1188.6	1067.2	954.5	859.1	773.0	700.7	622.3
45°	634.1	828.9	1033.6	1137.7	1103.2	990.8	871.7	780.9	700.0	637.6	562.4
47.5°	534.8	672.2	870.2	1011.1	1010.5	907.9	790.7	703.9	628.8	570.4	509.4
50°	478.4	597.9	765.5	925.3	938.7	852.6	741.2	655.2	585.1	523.7	474.7
52.5°	427.7	526.2	676.8	830.0	868.2	793.7	685.6	606.1	538.1	481.7	439.7
55°	361.3	437.7	552.1	695.4	753.2	700.5	604.7	530.5	475.2	427.9	391.7
57.5°	305.7	362.9	454.7	570.2	637.3	604.3	525.1	464.8	417.7	374.8	346.3
60°	270.6	317.5	395.4	491.8	566.0	542.8	475.2	419.1	378.9	341.7	315.0
62.5°	237.6	277.9	344.7	422.9	491.0	481.4	426.2	379.1	343.9	310.0	287.3
65°	191.3	220.7	272.7	334.1	388.7	393.3	353.7	321.6	290.2	263.4	243.3
67.5°	152.3	171.5	208.1	259.8	300.7	315.4	291.1	266.7	241.8	221.1	203.6
70°	128.4	143.8	170.7	212.4	250.0	265.5	251.6	232.5	210.9	193.8	178.8
72.5°	104.0	119.1	138.9	169.5	201.8	218.4	213.6	200.0	182.4	168.2	154.1
75°	78.4	83.0	96.4	117.0	142.3	156.7	160.4	153.1	139.2	128.4	120.1
77.5°	58.0	60.7	67.2	78.0	94.4	107.3	112.6	111.8	102.2	95.8	88.2
80°	46.4	48.0	51.0	55.6	68.1	80.9	84.5	84.5	77.9	75.2	67.6
82.5°	35.2	36.4	38.3	40.8	46.6	57.9	61.9	62.7	58.5	55.0	49.0
85°	20.1	19.6	20.6	22.1	23.2	26.3	32.5	33.5	32.5	28.4	26.8
87.5°	12.4	11.4	10.4	9.4	9.4	9.5	10.7	12.1	11.1	10.7	10.3
90°	27.2	20.2	15.1	12.1	10.1	8.1	4.0	1.0	4.0	8.1	10.1
92.5°	100.6	68.6	45.7	36.3	29.4	25.0	17.8	12.3	17.8	25.0	29.4
95°	232.8	145.1	98.8	74.6	58.5	49.4	39.3	35.2	39.3	49.4	58.5
97.5°	313.7	191.5	133.2	105.8	87.3	73.6	62.9	57.5	62.9	73.6	87.3
100°	330.6	207.6	154.2	126.0	105.8	89.7	80.6	77.6	80.6	89.7	105.8
102.5°	331.4	222.2	172.8	144.5	123.6	107.4	98.4	96.1	98.4	107.4	123.6
105°	336.6	246.9	199.5	171.4	149.2	134.0	127.0	123.0	127.0	134.0	149.2
107.5°	350.5	272.4	226.4	197.9	176.0	162.1	155.2	152.0	155.2	162.1	176.0
110°	361.8	289.2	244.9	215.7	194.5	181.4	175.4	171.4	175.4	181.4	194.5



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	374.0	305.4	262.7	232.6	212.3	200.0	193.1	189.0	193.1	200.0	212.3
115°	392.0	330.6	287.2	260.0	239.8	227.8	221.8	216.7	221.8	227.8	239.8
117.5°	411.4	353.8	313.7	285.4	266.1	255.4	249.3	245.3	249.3	255.4	266.1
120°	424.3	369.9	330.6	302.4	282.2	273.2	267.1	263.1	267.1	273.2	282.2
122.5°	435.6	385.2	348.3	319.3	299.1	289.2	283.2	280.0	283.2	289.2	299.1
125°	453.5	408.2	371.9	343.7	323.6	311.4	305.4	302.4	305.4	311.4	323.6
127.5°	470.3	429.6	394.3	365.3	345.9	332.5	324.2	320.1	324.2	332.5	345.9
130°	480.8	442.4	407.2	379.0	358.8	344.7	334.6	330.6	334.6	344.7	358.8
132.5°	491.2	453.7	420.1	391.8	370.9	356.0	345.1	340.2	345.1	356.0	370.9
135°	504.9	469.7	437.4	409.2	386.0	370.9	358.8	354.8	358.8	370.9	386.0
137.5°	515.4	482.6	450.7	424.5	401.5	385.4	373.3	368.5	373.3	385.4	401.5
140°	521.1	489.8	459.6	433.4	411.2	395.1	383.0	379.0	383.0	395.1	411.2
142.5°	525.9	495.4	466.1	441.4	420.1	403.9	392.6	389.4	392.6	403.9	420.1
145°	532.2	503.9	476.8	454.5	434.4	419.3	409.2	405.2	409.2	419.3	434.4
147.5°	535.6	510.8	485.2	465.4	448.7	434.7	425.2	422.1	425.2	434.7	448.7
150°	537.1	514.0	490.8	472.7	457.6	444.4	436.4	433.4	436.4	444.4	457.6
152.5°	538.0	517.3	496.4	480.0	465.6	454.1	446.1	444.6	446.1	454.1	465.6
155°	539.2	522.1	504.9	489.8	478.8	467.7	461.6	460.6	461.6	467.7	478.8
157.5°	539.2	525.5	511.0	498.3	489.4	479.8	474.9	473.9	474.9	479.8	489.4
160°	539.2	527.1	515.0	503.9	495.8	487.8	483.8	482.8	483.8	487.8	495.8
162.5°	538.4	528.0	517.5	508.8	501.5	495.0	491.0	491.6	491.0	495.0	501.5
165°	536.2	529.2	520.1	514.0	509.0	502.9	500.9	501.9	500.9	502.9	509.0
167.5°	534.8	529.0	522.3	518.5	514.8	511.0	509.2	510.4	509.2	511.0	514.8
170°	533.2	528.2	523.1	520.1	518.1	515.0	514.0	516.0	514.0	515.0	518.1
172.5°	530.8	527.4	523.9	521.7	520.5	517.5	518.1	519.3	518.1	517.5	520.5
175°	528.2	526.1	524.1	523.1	523.1	521.1	522.1	523.1	522.1	521.1	523.1
177.5°	526.5	524.9	524.1	524.1	524.1	522.5	523.3	524.9	523.3	522.5	524.1
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1462.6	1459.7	1454.3	1446.0	1441.1	1432.4	1426.6	1430.0	1430.8	1430.0	1429.2
5°	1423.3	1412.4	1397.5	1383.0	1369.7	1355.2	1347.0	1343.3	1336.2	1332.0	1330.0
7.5°	1375.7	1357.1	1336.0	1310.8	1289.4	1267.1	1255.7	1249.9	1235.2	1227.2	1220.1
10°	1340.3	1310.9	1289.8	1256.8	1236.7	1207.3	1187.2	1187.7	1167.6	1156.2	1148.0
12.5°	1301.1	1268.8	1233.7	1204.0	1176.0	1152.5	1128.2	1118.4	1097.0	1086.1	1063.9
15°	1236.2	1198.5	1161.4	1121.2	1092.9	1056.2	1021.2	978.4	943.8	913.9	905.7
17.5°	1165.2	1118.6	1081.4	1034.2	985.6	924.0	883.4	858.6	837.8	822.0	810.2
20°	1116.5	1069.1	1029.5	958.3	892.8	851.1	821.2	802.1	780.4	763.5	754.2
22.5°	1065.4	1015.9	961.8	882.4	831.4	797.9	771.2	749.3	734.7	721.3	713.0
25°	992.8	938.7	849.5	794.9	753.7	718.6	700.0	686.6	671.2	653.1	644.9
27.5°	916.1	830.0	766.0	725.4	686.0	663.2	646.5	626.5	612.7	604.6	596.0
30°	858.8	772.7	722.8	678.4	650.6	625.3	605.7	594.4	581.0	567.0	561.4
32.5°	794.9	726.1	678.2	641.3	613.0	591.5	576.0	557.6	548.0	539.4	527.6
35°	715.5	663.5	619.7	589.8	562.9	545.4	527.4	516.5	499.0	491.8	487.2
37.5°	648.2	603.1	570.5	538.9	517.7	498.3	487.3	470.0	462.4	452.4	442.6
40°	610.4	566.0	534.5	508.8	485.0	470.6	456.8	442.8	431.4	426.9	415.0
42.5°	571.6	535.5	504.0	475.7	459.9	444.6	427.1	416.9	405.1	397.6	390.2
45°	518.1	486.1	459.3	436.1	418.6	402.6	391.2	374.3	367.6	352.5	346.4
47.5°	471.1	441.3	415.8	393.7	376.6	366.2	349.6	336.3	325.6	316.4	308.5
50°	437.7	412.9	388.2	368.6	353.1	338.2	321.1	314.5	297.9	293.3	288.7
52.5°	407.2	383.6	360.9	341.7	326.3	311.7	296.8	288.0	276.9	272.3	268.9
55°	364.5	341.7	320.1	303.1	287.6	272.7	263.4	252.6	247.4	243.8	239.7
57.5°	321.5	301.1	284.6	267.3	251.8	239.9	229.1	222.7	217.3	212.6	207.6
60°	294.4	274.8	259.8	243.8	227.8	218.0	209.8	202.1	195.9	188.6	186.6
62.5°	265.5	248.3	234.7	219.0	205.2	196.2	188.3	181.1	173.6	163.1	160.2
65°	225.8	212.4	197.9	185.1	172.7	163.9	152.6	144.3	141.3	140.2	139.7
67.5°	190.0	177.2	164.8	151.7	140.4	132.3	126.5	125.2	123.1	122.5	121.1
70°	166.0	154.1	141.8	129.4	118.6	117.0	114.9	112.9	110.3	109.3	108.3
72.5°	144.5	132.3	119.9	110.0	105.3	103.4	101.4	99.3	97.6	96.5	95.8
75°	110.8	99.5	91.3	87.7	85.0	83.5	80.4	78.9	77.9	76.2	75.7
77.5°	79.8	73.4	69.6	67.4	64.6	63.0	61.2	59.7	58.6	58.3	57.5
80°	60.8	57.8	55.1	52.1	51.0	49.0	48.5	47.0	47.5	45.8	45.8
82.5°	47.3	43.3	41.1	39.7	38.7	37.1	36.5	35.7	35.9	34.7	34.7
85°	24.2	23.2	22.1	21.1	21.1	19.6	20.1	19.6	19.6	18.6	18.1
87.5°	10.3	10.4	10.6	12.0	13.2	13.0	12.8	12.2	11.8	12.2	12.0
90°	12.1	15.1	20.2	27.2	33.2	34.2	33.2	32.2	30.2	32.2	33.2
92.5°	36.3	45.7	68.6	100.6	129.2	131.0	110.7	87.9	75.4	67.0	60.7
95°	74.6	98.8	145.1	232.8	349.7	395.1	345.7	264.1	202.6	160.3	138.0
97.5°	105.8	133.2	191.5	313.7	508.0	674.5	707.5	616.2	504.1	395.1	322.3
100°	126.0	154.2	207.6	330.6	548.3	796.2	941.4	920.2	795.2	657.1	535.2
102.5°	144.5	172.8	222.2	331.4	533.0	800.2	1028.4	1119.3	1091.2	990.2	860.9
105°	171.4	199.5	246.9	336.6	502.9	746.8	1014.9	1224.6	1338.5	1351.6	1318.3
107.5°	197.9	226.4	272.4	350.5	488.0	689.6	926.5	1148.8	1320.3	1425.1	1473.9
110°	215.7	244.9	289.2	361.8	484.8	662.2	870.8	1083.5	1263.8	1392.9	1475.5



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	232.6	262.7	305.4	374.0	485.5	644.4	832.1	1023.8	1197.0	1334.8	1429.6
115°	260.0	287.2	330.6	392.0	489.8	624.9	784.2	950.4	1105.6	1237.7	1341.5
117.5°	285.4	313.7	353.8	411.4	497.1	615.4	753.9	895.1	1031.5	1151.1	1248.6
120°	302.4	330.6	369.9	424.3	501.9	609.8	737.8	867.8	992.8	1099.5	1191.3
122.5°	319.3	348.3	385.2	435.6	507.6	606.5	724.1	846.0	960.5	1061.7	1144.6
125°	343.7	371.9	408.2	453.5	516.0	600.7	704.5	814.4	918.2	1006.8	1082.5
127.5°	365.3	394.3	429.6	470.3	524.7	597.2	686.4	783.2	877.1	960.7	1030.5
130°	379.0	407.2	442.4	480.8	531.2	595.6	674.3	763.0	849.6	929.3	995.8
132.5°	391.8	420.1	453.7	491.2	537.6	594.8	664.6	743.6	823.8	897.0	959.5
135°	409.2	437.4	469.7	504.9	545.2	593.6	651.1	716.6	783.2	849.6	906.1
137.5°	424.5	450.7	482.6	515.4	552.1	593.4	641.6	695.0	750.6	803.4	852.6
140°	433.4	459.6	489.8	521.1	555.3	592.6	636.0	681.4	729.7	776.1	820.4
142.5°	441.4	466.1	495.4	525.9	557.7	592.6	630.4	670.0	711.1	751.0	788.2
145°	454.5	476.8	503.9	532.2	560.4	590.6	622.9	654.1	687.4	718.6	747.8
147.5°	465.4	485.2	510.8	535.6	561.2	587.0	615.2	641.8	668.0	692.4	713.8
150°	472.7	490.8	514.0	537.1	560.4	584.6	608.7	633.0	655.1	676.3	694.4
152.5°	480.0	496.4	517.3	538.0	558.8	580.6	603.1	624.1	644.6	662.6	678.3
155°	489.8	504.9	522.1	539.2	556.3	573.5	592.6	611.8	627.9	643.0	654.1
157.5°	498.3	511.0	525.5	539.2	551.7	566.2	582.8	597.4	611.0	623.7	632.4
160°	503.9	515.0	527.1	539.2	549.3	561.4	575.5	588.5	599.7	610.8	617.8
162.5°	508.8	517.5	528.0	538.4	546.8	557.3	569.1	579.8	589.2	598.6	604.1
165°	514.0	520.1	529.2	536.2	542.2	549.3	558.4	566.4	573.5	580.6	584.6
167.5°	518.5	522.3	529.0	534.8	537.6	542.2	547.9	553.7	559.2	564.0	567.6
170°	520.1	523.1	528.2	533.2	535.2	538.2	542.2	547.2	550.3	554.3	556.3
172.5°	521.7	523.9	527.4	530.8	532.0	533.4	536.6	540.0	542.2	545.4	546.6
175°	523.1	524.1	526.1	528.2	527.1	528.2	529.2	532.2	533.2	534.2	535.2
177.5°	524.1	524.1	524.9	526.5	524.9	524.1	524.9	526.5	526.5	527.4	527.4
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1424.6	1425.4	1424.2	1425.0	1424.2	1425.4	1424.6	1429.2	1430.0	1430.8	1430.0
5°	1327.4	1321.2	1320.2	1318.6	1320.2	1321.2	1327.4	1330.0	1332.0	1336.2	1343.3
7.5°	1211.3	1210.3	1207.8	1204.2	1207.8	1210.3	1211.3	1220.1	1227.2	1235.2	1249.9
10°	1136.6	1134.1	1133.6	1129.9	1133.6	1134.1	1136.6	1148.0	1156.2	1167.6	1187.7
12.5°	1049.2	1032.6	1030.9	1021.9	1030.9	1032.6	1049.2	1063.9	1086.1	1097.0	1118.4
15°	893.3	890.3	879.9	873.2	879.9	890.3	893.3	905.7	913.9	943.8	978.4
17.5°	804.3	794.2	790.9	789.5	790.9	794.2	804.3	810.2	822.0	837.8	858.6
20°	746.9	737.7	736.1	735.1	736.1	737.7	746.9	754.2	763.5	780.4	802.1
22.5°	707.3	697.6	693.7	690.5	693.7	697.6	707.3	713.0	721.3	734.7	749.3
25°	639.7	636.1	634.1	633.0	634.1	636.1	639.7	644.9	653.1	671.2	686.6
27.5°	586.8	578.9	577.3	574.7	577.3	578.9	586.8	596.0	604.6	612.7	626.5
30°	556.7	554.1	550.6	547.4	550.6	554.1	556.7	561.4	567.0	581.0	594.4
32.5°	521.3	519.1	515.9	514.4	515.9	519.1	521.3	527.6	539.4	548.0	557.6
35°	482.0	474.7	471.7	467.1	471.7	474.7	482.0	487.2	491.8	499.0	516.5
37.5°	440.4	436.7	432.3	433.8	432.3	436.7	440.4	442.6	452.4	462.4	470.0
40°	408.3	405.7	404.7	404.1	404.7	405.7	408.3	415.0	426.9	431.4	442.8
42.5°	382.7	375.6	372.9	372.8	372.9	375.6	382.7	390.2	397.6	405.1	416.9
45°	343.9	337.1	332.4	333.1	332.4	337.1	343.9	346.4	352.5	367.6	374.3
47.5°	304.1	303.9	300.9	301.8	300.9	303.9	304.1	308.5	316.4	325.6	336.3
50°	285.1	282.0	279.9	280.4	279.9	282.0	285.1	288.7	293.3	297.9	314.5
52.5°	266.9	264.3	262.6	264.8	262.6	264.3	266.9	268.9	272.3	276.9	288.0
55°	237.1	234.0	233.5	233.0	233.5	234.0	237.1	239.7	243.8	247.4	252.6
57.5°	203.8	201.8	198.6	197.3	198.6	201.8	203.8	207.6	212.6	217.3	222.7
60°	179.9	175.8	170.7	170.1	170.7	175.8	179.9	186.6	188.6	195.9	202.1
62.5°	158.0	157.2	156.2	156.1	156.2	157.2	158.0	160.2	163.1	173.6	181.1
65°	138.7	138.1	138.7	139.2	138.7	138.1	138.7	139.7	140.2	141.3	144.3
67.5°	120.9	119.9	119.0	119.4	119.0	119.9	120.9	121.1	122.5	123.1	125.2
70°	107.2	106.7	106.2	106.2	106.2	106.7	107.2	108.3	109.3	110.3	112.9
72.5°	94.0	93.9	93.4	93.0	93.4	93.9	94.0	95.8	96.5	97.6	99.3
75°	75.2	74.2	74.2	74.2	74.2	74.2	75.2	75.7	76.2	77.9	78.9
77.5°	57.4	56.9	56.2	55.8	56.2	56.9	57.4	57.5	58.3	58.6	59.7
80°	45.3	44.8	44.3	44.3	44.3	44.8	45.3	45.8	45.8	47.5	47.0
82.5°	34.6	34.1	34.0	33.6	34.0	34.1	34.6	34.7	34.7	35.9	35.7
85°	18.6	19.1	18.6	19.6	18.6	19.1	18.6	18.1	18.6	19.6	19.6
87.5°	12.0	11.6	12.0	11.6	12.0	11.6	12.0	12.0	12.2	11.8	12.2
90°	33.2	33.2	33.2	33.2	33.2	33.2	33.2	33.2	32.2	30.2	32.2
92.5°	59.9	56.7	57.5	55.8	57.5	56.7	59.9	60.7	67.0	75.4	87.9
95°	125.0	116.9	113.9	114.9	113.9	116.9	125.0	138.0	160.3	202.6	264.1
97.5°	274.2	249.3	234.6	226.2	234.6	249.3	274.2	322.3	395.1	504.1	616.2
100°	451.5	408.2	379.0	360.8	379.0	408.2	451.5	535.2	657.1	795.2	920.2
102.5°	770.0	696.0	659.5	635.0	659.5	696.0	770.0	860.9	990.2	1091.2	1119.3
105°	1255.8	1193.4	1149.9	1135.9	1149.9	1193.4	1255.8	1318.3	1351.6	1338.5	1224.6
107.5°	1481.8	1478.3	1469.7	1451.0	1469.7	1478.3	1481.8	1473.9	1425.1	1320.3	1148.8
110°	1518.8	1538.0	1547.1	1546.1	1547.1	1538.0	1518.8	1475.5	1392.9	1263.8	1083.5



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1489.9	1521.9	1539.0	1544.5	1539.0	1521.9	1489.9	1429.6	1334.8	1197.0	1023.8
115°	1413.0	1459.4	1485.6	1494.7	1485.6	1459.4	1413.0	1341.5	1237.7	1105.6	950.4
117.5°	1321.5	1370.5	1398.2	1405.7	1398.2	1370.5	1321.5	1248.6	1151.1	1031.5	895.1
120°	1261.8	1309.2	1338.5	1348.6	1338.5	1309.2	1261.8	1191.3	1099.5	992.8	867.8
122.5°	1207.8	1254.4	1280.4	1288.9	1280.4	1254.4	1207.8	1144.6	1061.7	960.5	846.0
125°	1140.9	1179.2	1204.4	1212.4	1204.4	1179.2	1140.9	1082.5	1006.8	918.2	814.4
127.5°	1081.5	1117.3	1139.1	1145.6	1139.1	1117.3	1081.5	1030.5	960.7	877.1	783.2
130°	1045.2	1079.4	1099.5	1107.6	1099.5	1079.4	1045.2	995.8	929.3	849.6	763.0
132.5°	1008.0	1042.4	1060.9	1068.1	1060.9	1042.4	1008.0	959.5	897.0	823.8	743.6
135°	949.4	982.7	1000.8	1004.8	1000.8	982.7	949.4	906.1	849.6	783.2	716.6
137.5°	892.2	920.8	936.8	942.8	936.8	920.8	892.2	852.6	803.4	750.6	695.0
140°	852.6	878.9	894.0	900.0	894.0	878.9	852.6	820.4	776.1	729.7	681.4
142.5°	818.8	842.6	856.1	857.3	856.1	842.6	818.8	788.2	751.0	711.1	670.0
145°	772.0	789.2	799.2	802.2	799.2	789.2	772.0	747.8	718.6	687.4	654.1
147.5°	733.8	747.4	754.3	756.1	754.3	747.4	733.8	713.8	692.4	668.0	641.8
150°	709.5	721.6	727.7	728.7	727.7	721.6	709.5	694.4	676.3	655.1	633.0
152.5°	690.1	700.6	705.1	705.3	705.1	700.6	690.1	678.3	662.6	644.6	624.1
155°	665.2	672.3	676.3	674.3	676.3	672.3	665.2	654.1	643.0	627.9	611.8
157.5°	640.2	646.0	647.8	647.8	647.8	646.0	640.2	632.4	623.7	611.0	597.4
160°	624.9	630.0	631.0	631.0	631.0	630.0	624.9	617.8	610.8	599.7	588.5
162.5°	611.2	614.6	615.6	614.8	615.6	614.6	611.2	604.1	598.6	589.2	579.8
165°	588.5	592.6	592.6	591.6	592.6	592.6	588.5	584.6	580.6	573.5	566.4
167.5°	569.5	571.7	571.5	570.3	571.5	571.7	569.5	567.6	564.0	559.2	553.7
170°	557.3	560.4	559.4	557.3	559.4	560.4	557.3	556.3	554.3	550.3	547.2
172.5°	547.6	549.1	548.1	546.8	548.1	549.1	547.6	546.6	545.4	542.2	540.0
175°	535.2	536.2	535.2	533.2	535.2	536.2	535.2	535.2	534.2	533.2	532.2
177.5°	527.4	527.4	526.5	524.9	526.5	527.4	527.4	527.4	527.4	526.5	526.5
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1426.6	1432.4	1441.1	1446.0	1454.3	1459.7	1462.6	1467.9	1470.8	1481.1	1491.9
5°	1347.0	1355.2	1369.7	1383.0	1397.5	1412.4	1423.3	1435.6	1446.9	1466.5	1487.2
7.5°	1255.7	1267.1	1289.4	1310.8	1336.0	1357.1	1375.7	1396.8	1415.7	1443.8	1473.1
10°	1187.2	1207.3	1236.7	1256.8	1289.8	1310.9	1340.3	1363.4	1389.8	1426.8	1459.9
12.5°	1128.2	1152.5	1176.0	1204.0	1233.7	1268.8	1301.1	1330.9	1362.1	1400.5	1439.3
15°	1021.2	1056.2	1092.9	1121.2	1161.4	1198.5	1236.2	1276.4	1314.5	1360.4	1410.9
17.5°	883.4	924.0	985.6	1034.2	1081.4	1118.6	1165.2	1213.9	1258.8	1314.1	1370.4
20°	821.2	851.1	892.8	958.3	1029.5	1069.1	1116.5	1170.1	1221.7	1282.0	1342.3
22.5°	771.2	797.9	831.4	882.4	961.8	1015.9	1065.4	1119.8	1179.6	1241.2	1308.1
25°	700.0	718.6	753.7	794.9	849.5	938.7	992.8	1047.4	1112.5	1178.4	1254.7
27.5°	646.5	663.2	686.0	725.4	766.0	830.0	916.1	975.7	1040.5	1114.7	1193.9
30°	605.7	625.3	650.6	678.4	722.8	772.7	858.8	927.9	991.8	1068.1	1152.7
32.5°	576.0	591.5	613.0	641.3	678.2	726.1	794.9	878.8	941.1	1021.5	1109.7
35°	527.4	545.4	562.9	589.8	619.7	663.5	715.5	805.2	867.1	946.4	1035.1
37.5°	487.3	498.3	517.7	538.9	570.5	603.1	648.2	728.7	795.6	873.5	964.3
40°	456.8	470.6	485.0	508.8	534.5	566.0	610.4	670.1	746.9	823.2	911.9
42.5°	427.1	444.6	459.9	475.7	504.0	535.5	571.6	622.3	700.7	773.0	859.1
45°	391.2	402.6	418.6	436.1	459.3	486.1	518.1	562.4	637.6	700.0	780.9
47.5°	349.6	366.2	376.6	393.7	415.8	441.3	471.1	509.4	570.4	628.8	703.9
50°	321.1	338.2	353.1	368.6	388.2	412.9	437.7	474.7	523.7	585.1	655.2
52.5°	296.8	311.7	326.3	341.7	360.9	383.6	407.2	439.7	481.7	538.1	606.1
55°	263.4	272.7	287.6	303.1	320.1	341.7	364.5	391.7	427.9	475.2	530.5
57.5°	229.1	239.9	251.8	267.3	284.6	301.1	321.5	346.3	374.8	417.7	464.8
60°	209.8	218.0	227.8	243.8	259.8	274.8	294.4	315.0	341.7	378.9	419.1
62.5°	188.3	196.2	205.2	219.0	234.7	248.3	265.5	287.3	310.0	343.9	379.1
65°	152.6	163.9	172.7	185.1	197.9	212.4	225.8	243.3	263.4	290.2	321.6
67.5°	126.5	132.3	140.4	151.7	164.8	177.2	190.0	203.6	221.1	241.8	266.7
70°	114.9	117.0	118.6	129.4	141.8	154.1	166.0	178.8	193.8	210.9	232.5
72.5°	101.4	103.4	105.3	110.0	119.9	132.3	144.5	154.1	168.2	182.4	200.0
75°	80.4	83.5	85.0	87.7	91.3	99.5	110.8	120.1	128.4	139.2	153.1
77.5°	61.2	63.0	64.6	67.4	69.6	73.4	79.8	88.2	95.8	102.2	111.8
80°	48.5	49.0	51.0	52.1	55.1	57.8	60.8	67.6	75.2	77.9	84.5
82.5°	36.5	37.1	38.7	39.7	41.1	43.3	47.3	49.0	55.0	58.5	62.7
85°	20.1	19.6	21.1	21.1	22.1	23.2	24.2	26.8	28.4	32.5	33.5
87.5°	12.8	13.0	13.2	12.0	10.6	10.4	10.3	10.3	10.7	11.1	12.1
90°	33.2	34.2	33.2	27.2	20.2	15.1	12.1	10.1	8.1	4.0	1.0
92.5°	110.7	131.0	129.2	100.6	68.6	45.7	36.3	29.4	25.0	17.8	12.3
95°	345.7	395.1	349.7	232.8	145.1	98.8	74.6	58.5	49.4	39.3	35.2
97.5°	707.5	674.5	508.0	313.7	191.5	133.2	105.8	87.3	73.6	62.9	57.5
100°	941.4	796.2	548.3	330.6	207.6	154.2	126.0	105.8	89.7	80.6	77.6
102.5°	1028.4	800.2	533.0	331.4	222.2	172.8	144.5	123.6	107.4	98.4	96.1
105°	1014.9	746.8	502.9	336.6	246.9	199.5	171.4	149.2	134.0	127.0	123.0
107.5°	926.5	689.6	488.0	350.5	272.4	226.4	197.9	176.0	162.1	155.2	152.0
110°	870.8	662.2	484.8	361.8	289.2	244.9	215.7	194.5	181.4	175.4	171.4



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	832.1	644.4	485.5	374.0	305.4	262.7	232.6	212.3	200.0	193.1	189.0
115°	784.2	624.9	489.8	392.0	330.6	287.2	260.0	239.8	227.8	221.8	216.7
117.5°	753.9	615.4	497.1	411.4	353.8	313.7	285.4	266.1	255.4	249.3	245.3
120°	737.8	609.8	501.9	424.3	369.9	330.6	302.4	282.2	273.2	267.1	263.1
122.5°	724.1	606.5	507.6	435.6	385.2	348.3	319.3	299.1	289.2	283.2	280.0
125°	704.5	600.7	516.0	453.5	408.2	371.9	343.7	323.6	311.4	305.4	302.4
127.5°	686.4	597.2	524.7	470.3	429.6	394.3	365.3	345.9	332.5	324.2	320.1
130°	674.3	595.6	531.2	480.8	442.4	407.2	379.0	358.8	344.7	334.6	330.6
132.5°	664.6	594.8	537.6	491.2	453.7	420.1	391.8	370.9	356.0	345.1	340.2
135°	651.1	593.6	545.2	504.9	469.7	437.4	409.2	386.0	370.9	358.8	354.8
137.5°	641.6	593.4	552.1	515.4	482.6	450.7	424.5	401.5	385.4	373.3	368.5
140°	636.0	592.6	555.3	521.1	489.8	459.6	433.4	411.2	395.1	383.0	379.0
142.5°	630.4	592.6	557.7	525.9	495.4	466.1	441.4	420.1	403.9	392.6	389.4
145°	622.9	590.6	560.4	532.2	503.9	476.8	454.5	434.4	419.3	409.2	405.2
147.5°	615.2	587.0	561.2	535.6	510.8	485.2	465.4	448.7	434.7	425.2	422.1
150°	608.7	584.6	560.4	537.1	514.0	490.8	472.7	457.6	444.4	436.4	433.4
152.5°	603.1	580.6	558.8	538.0	517.3	496.4	480.0	465.6	454.1	446.1	444.6
155°	592.6	573.5	556.3	539.2	522.1	504.9	489.8	478.8	467.7	461.6	460.6
157.5°	582.8	566.2	551.7	539.2	525.5	511.0	498.3	489.4	479.8	474.9	473.9
160°	575.5	561.4	549.3	539.2	527.1	515.0	503.9	495.8	487.8	483.8	482.8
162.5°	569.1	557.3	546.8	538.4	528.0	517.5	508.8	501.5	495.0	491.0	491.6
165°	558.4	549.3	542.2	536.2	529.2	520.1	514.0	509.0	502.9	500.9	501.9
167.5°	547.9	542.2	537.6	534.8	529.0	522.3	518.5	514.8	511.0	509.2	510.4
170°	542.2	538.2	535.2	533.2	528.2	523.1	520.1	518.1	515.0	514.0	516.0
172.5°	536.6	533.4	532.0	530.8	527.4	523.9	521.7	520.5	517.5	518.1	519.3
175°	529.2	528.2	527.1	528.2	526.1	524.1	523.1	523.1	521.1	522.1	523.1
177.5°	524.9	524.1	524.9	526.5	524.9	524.1	524.1	524.1	522.5	523.3	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1492.3	1493.5	1501.8	1505.4	1512.9	1515.7	1519.0	1518.2	1518.2	1519.8	1531.5
5°	1495.4	1505.7	1521.2	1536.1	1550.5	1563.0	1571.2	1579.4	1582.6	1597.5	1610.9
7.5°	1490.1	1509.0	1534.6	1557.4	1584.7	1606.1	1623.8	1639.8	1650.7	1672.4	1694.8
10°	1483.1	1509.8	1538.7	1568.1	1605.8	1634.1	1662.9	1685.2	1692.3	1724.8	1743.4
12.5°	1469.1	1504.9	1541.7	1579.6	1616.5	1655.6	1687.3	1709.5	1734.8	1764.0	1798.3
15°	1448.0	1489.2	1537.2	1586.2	1638.7	1686.2	1720.2	1758.9	1786.7	1818.7	1848.6
17.5°	1417.7	1470.9	1531.9	1588.5	1649.3	1700.3	1747.1	1784.2	1803.8	1822.0	1826.4
20°	1393.9	1451.1	1522.8	1589.7	1650.6	1709.4	1755.8	1786.7	1791.8	1792.3	1765.0
22.5°	1367.9	1432.5	1507.5	1576.2	1648.9	1714.3	1750.4	1763.6	1743.1	1708.2	1655.4
25°	1320.2	1394.9	1482.1	1560.3	1639.8	1701.6	1714.0	1690.8	1619.1	1543.9	1448.6
27.5°	1268.4	1352.4	1445.8	1533.0	1617.5	1655.9	1629.1	1545.5	1416.4	1304.2	1168.3
30°	1230.5	1324.8	1416.5	1514.0	1592.4	1608.8	1547.5	1424.3	1273.7	1104.7	969.2
32.5°	1187.2	1286.1	1386.8	1487.6	1553.2	1537.1	1435.7	1284.0	1107.6	941.4	813.2
35°	1125.3	1227.4	1336.2	1437.1	1478.9	1409.4	1257.8	1060.4	879.9	724.8	636.6
37.5°	1053.9	1165.0	1278.1	1370.9	1367.9	1251.9	1045.5	841.7	690.0	598.2	535.5
40°	1003.1	1115.5	1237.7	1316.1	1282.5	1131.5	907.8	715.5	604.7	531.5	485.5
42.5°	954.5	1067.2	1188.6	1250.9	1192.7	1006.9	784.1	633.4	542.0	484.8	447.7
45°	871.7	990.8	1103.2	1137.7	1033.6	828.9	634.1	524.7	463.9	421.7	395.9
47.5°	790.7	907.9	1010.5	1011.1	870.2	672.2	534.8	454.1	402.2	369.5	350.7
50°	741.2	852.6	938.7	925.3	765.5	597.9	478.4	408.8	365.5	340.2	320.6
52.5°	685.6	793.7	868.2	830.0	676.8	526.2	427.7	369.2	333.4	311.3	293.9
55°	604.7	700.5	753.2	695.4	552.1	437.7	361.3	315.5	288.7	270.1	255.2
57.5°	525.1	604.3	637.3	570.2	454.7	362.9	305.7	271.2	244.7	231.4	223.6
60°	475.2	542.8	566.0	491.8	395.4	317.5	270.6	238.6	219.0	210.4	202.6
62.5°	426.2	481.4	491.0	422.9	344.7	277.9	237.6	210.7	197.6	189.2	182.0
65°	353.7	393.3	388.7	334.1	272.7	220.7	191.3	174.7	164.9	153.1	140.2
67.5°	291.1	315.4	300.7	259.8	208.1	171.5	152.3	139.8	127.6	116.4	113.4
70°	251.6	265.5	250.0	212.4	170.7	143.8	128.4	113.4	106.2	103.6	99.0
72.5°	213.6	218.4	201.8	169.5	138.9	119.1	104.0	95.6	91.8	89.6	86.6
75°	160.4	156.7	142.3	117.0	96.4	83.0	78.4	75.2	72.7	70.6	69.1
77.5°	112.6	107.3	94.4	78.0	67.2	60.7	58.0	56.2	55.0	54.0	52.5
80°	84.5	80.9	68.1	55.6	51.0	48.0	46.4	44.3	44.3	43.3	41.7
82.5°	61.9	57.9	46.6	40.8	38.3	36.4	35.2	34.0	33.6	33.8	32.7
85°	32.5	26.3	23.2	22.1	20.6	19.6	20.1	19.1	19.1	19.1	18.6
87.5°	10.7	9.5	9.4	9.4	10.4	11.4	12.4	13.6	14.2	13.6	13.8
90°	4.0	8.1	10.1	12.1	15.1	20.2	27.2	33.2	34.2	33.2	32.2
92.5°	17.8	25.0	29.4	36.3	45.7	68.6	100.6	129.2	131.0	110.7	87.9
95°	39.3	49.4	58.5	74.6	98.8	145.1	232.8	349.7	395.1	345.7	264.1
97.5°	62.9	73.6	87.3	105.8	133.2	191.5	313.7	508.0	674.5	707.5	616.2
100°	80.6	89.7	105.8	126.0	154.2	207.6	330.6	548.3	796.2	941.4	920.2
102.5°	98.4	107.4	123.6	144.5	172.8	222.2	331.4	533.0	800.2	1028.4	1119.3
105°	127.0	134.0	149.2	171.4	199.5	246.9	336.6	502.9	746.8	1014.9	1224.6
107.5°	155.2	162.1	176.0	197.9	226.4	272.4	350.5	488.0	689.6	926.5	1148.8
110°	175.4	181.4	194.5	215.7	244.9	289.2	361.8	484.8	662.2	870.8	1083.5



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	193.1	200.0	212.3	232.6	262.7	305.4	374.0	485.5	644.4	832.1	1023.8
115°	221.8	227.8	239.8	260.0	287.2	330.6	392.0	489.8	624.9	784.2	950.4
117.5°	249.3	255.4	266.1	285.4	313.7	353.8	411.4	497.1	615.4	753.9	895.1
120°	267.1	273.2	282.2	302.4	330.6	369.9	424.3	501.9	609.8	737.8	867.8
122.5°	283.2	289.2	299.1	319.3	348.3	385.2	435.6	507.6	606.5	724.1	846.0
125°	305.4	311.4	323.6	343.7	371.9	408.2	453.5	516.0	600.7	704.5	814.4
127.5°	324.2	332.5	345.9	365.3	394.3	429.6	470.3	524.7	597.2	686.4	783.2
130°	334.6	344.7	358.8	379.0	407.2	442.4	480.8	531.2	595.6	674.3	763.0
132.5°	345.1	356.0	370.9	391.8	420.1	453.7	491.2	537.6	594.8	664.6	743.6
135°	358.8	370.9	386.0	409.2	437.4	469.7	504.9	545.2	593.6	651.1	716.6
137.5°	373.3	385.4	401.5	424.5	450.7	482.6	515.4	552.1	593.4	641.6	695.0
140°	383.0	395.1	411.2	433.4	459.6	489.8	521.1	555.3	592.6	636.0	681.4
142.5°	392.6	403.9	420.1	441.4	466.1	495.4	525.9	557.7	592.6	630.4	670.0
145°	409.2	419.3	434.4	454.5	476.8	503.9	532.2	560.4	590.6	622.9	654.1
147.5°	425.2	434.7	448.7	465.4	485.2	510.8	535.6	561.2	587.0	615.2	641.8
150°	436.4	444.4	457.6	472.7	490.8	514.0	537.1	560.4	584.6	608.7	633.0
152.5°	446.1	454.1	465.6	480.0	496.4	517.3	538.0	558.8	580.6	603.1	624.1
155°	461.6	467.7	478.8	489.8	504.9	522.1	539.2	556.3	573.5	592.6	611.8
157.5°	474.9	479.8	489.4	498.3	511.0	525.5	539.2	551.7	566.2	582.8	597.4
160°	483.8	487.8	495.8	503.9	515.0	527.1	539.2	549.3	561.4	575.5	588.5
162.5°	491.0	495.0	501.5	508.8	517.5	528.0	538.4	546.8	557.3	569.1	579.8
165°	500.9	502.9	509.0	514.0	520.1	529.2	536.2	542.2	549.3	558.4	566.4
167.5°	509.2	511.0	514.8	518.5	522.3	529.0	534.8	537.6	542.2	547.9	553.7
170°	514.0	515.0	518.1	520.1	523.1	528.2	533.2	535.2	538.2	542.2	547.2
172.5°	518.1	517.5	520.5	521.7	523.9	527.4	530.8	532.0	533.4	536.6	540.0
175°	522.1	521.1	523.1	523.1	524.1	526.1	528.2	527.1	528.2	529.2	532.2
177.5°	523.3	522.5	524.1	524.1	524.1	524.9	526.5	524.9	524.1	524.9	526.5
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6
2.5°	1535.5	1540.9	1543.4	1543.4	1546.3	1545.0	1543.8
5°	1623.8	1633.6	1635.7	1645.0	1651.6	1649.5	1650.6
7.5°	1711.5	1727.3	1742.8	1750.0	1751.1	1755.2	1756.8
10°	1765.5	1778.5	1802.7	1799.1	1817.1	1827.5	1810.4
12.5°	1817.6	1834.9	1851.7	1856.3	1866.6	1869.9	1863.2
15°	1864.5	1873.8	1874.8	1872.3	1875.3	1872.8	1863.0
17.5°	1820.6	1805.5	1775.0	1760.6	1749.2	1732.2	1725.5
20°	1748.0	1703.6	1652.1	1631.5	1607.3	1559.8	1571.2
22.5°	1591.3	1540.8	1489.2	1429.1	1400.3	1355.3	1352.6
25°	1347.5	1260.4	1164.5	1097.5	1058.3	1013.5	993.9
27.5°	1047.6	938.0	859.4	819.6	783.5	747.9	746.4
30°	850.5	768.1	707.2	673.3	651.1	636.1	639.2
32.5°	716.9	660.5	619.5	591.2	574.8	563.5	563.3
35°	586.1	547.4	521.2	509.3	497.5	489.2	489.7
37.5°	501.6	478.4	463.7	450.6	443.2	439.2	437.0
40°	458.3	439.2	427.9	420.1	413.9	408.3	407.3
42.5°	424.0	408.3	396.9	390.8	385.1	381.0	380.0
45°	376.3	363.5	353.1	346.4	343.9	340.2	340.2
47.5°	334.8	322.0	314.1	309.8	305.4	303.0	302.9
50°	306.7	296.9	289.7	287.1	283.5	282.0	281.4
52.5°	281.6	274.3	269.1	267.3	265.8	263.8	264.2
55°	247.4	243.3	241.3	239.7	237.1	234.0	236.1
57.5°	218.6	215.2	209.6	204.8	202.4	200.3	201.1
60°	198.4	191.3	184.0	178.3	176.8	172.2	172.2
62.5°	172.9	162.8	153.9	150.8	149.2	147.0	146.6
65°	133.0	128.9	126.8	124.7	123.7	123.7	122.7
67.5°	110.2	108.6	106.3	105.7	104.7	104.4	104.1
70°	97.5	95.3	94.3	93.8	92.8	93.3	91.8
72.5°	85.0	83.4	83.2	81.9	81.2	81.3	80.2
75°	67.1	67.1	66.4	65.9	64.9	64.4	64.9
77.5°	51.5	51.6	50.7	50.6	50.5	50.6	50.1
80°	41.2	41.7	41.2	40.7	40.2	40.7	40.2
82.5°	32.6	31.8	31.7	31.6	31.5	31.2	31.1
85°	18.6	19.1	18.6	18.1	18.1	18.1	18.6
87.5°	13.0	13.4	13.6	13.6	13.6	13.6	13.2
90°	30.2	32.2	33.2	33.2	33.2	33.2	33.2
92.5°	75.4	67.0	60.7	59.9	56.7	57.5	55.8
95°	202.6	160.3	138.0	125.0	116.9	113.9	114.9
97.5°	504.1	395.1	322.3	274.2	249.3	234.6	226.2
100°	795.2	657.1	535.2	451.5	408.2	379.0	360.8
102.5°	1091.2	990.2	860.9	770.0	696.0	659.5	635.0
105°	1338.5	1351.6	1318.3	1255.8	1193.4	1149.9	1135.9
107.5°	1320.3	1425.1	1473.9	1481.8	1478.3	1469.7	1451.0
110°	1263.8	1392.9	1475.5	1518.8	1538.0	1547.1	1546.1



TEST NUMBER: P331695-840

CATALOG NUMBER: S122RDIP-S675D925U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1197.0	1334.8	1429.6	1489.9	1521.9	1539.0	1544.5
115°	1105.6	1237.7	1341.5	1413.0	1459.4	1485.6	1494.7
117.5°	1031.5	1151.1	1248.6	1321.5	1370.5	1398.2	1405.7
120°	992.8	1099.5	1191.3	1261.8	1309.2	1338.5	1348.6
122.5°	960.5	1061.7	1144.6	1207.8	1254.4	1280.4	1288.9
125°	918.2	1006.8	1082.5	1140.9	1179.2	1204.4	1212.4
127.5°	877.1	960.7	1030.5	1081.5	1117.3	1139.1	1145.6
130°	849.6	929.3	995.8	1045.2	1079.4	1099.5	1107.6
132.5°	823.8	897.0	959.5	1008.0	1042.4	1060.9	1068.1
135°	783.2	849.6	906.1	949.4	982.7	1000.8	1004.8
137.5°	750.6	803.4	852.6	892.2	920.8	936.8	942.8
140°	729.7	776.1	820.4	852.6	878.9	894.0	900.0
142.5°	711.1	751.0	788.2	818.8	842.6	856.1	857.3
145°	687.4	718.6	747.8	772.0	789.2	799.2	802.2
147.5°	668.0	692.4	713.8	733.8	747.4	754.3	756.1
150°	655.1	676.3	694.4	709.5	721.6	727.7	728.7
152.5°	644.6	662.6	678.3	690.1	700.6	705.1	705.3
155°	627.9	643.0	654.1	665.2	672.3	676.3	674.3
157.5°	611.0	623.7	632.4	640.2	646.0	647.8	647.8
160°	599.7	610.8	617.8	624.9	630.0	631.0	631.0
162.5°	589.2	598.6	604.1	611.2	614.6	615.6	614.8
165°	573.5	580.6	584.6	588.5	592.6	592.6	591.6
167.5°	559.2	564.0	567.6	569.5	571.7	571.5	570.3
170°	550.3	554.3	556.3	557.3	560.4	559.4	557.3
172.5°	542.2	545.4	546.6	547.6	549.1	548.1	546.8
175°	533.2	534.2	535.2	535.2	536.2	535.2	533.2
177.5°	526.5	527.4	527.4	527.4	527.4	526.5	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1

(END OF REPORT)