

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331714-840

Luminaire Tested: **S122RDIP-S865D530U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331714-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S865D530U840-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5181.7 lumens  
Efficiency: N/A  
Efficacy: 106.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331714-840

CATALOG NUMBER: S122RDIP-S865D530U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331714-840

CATALOG NUMBER: S122RDIP-S865D530U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59								
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	56	55	51								
2	92	85	79	74	85	79	74	70	69	65	62	60	57	55	51	49	47	43								
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37								
4	77	67	59	53	72	63	56	51	55	50	45	48	44	41	42	38	36	33								
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32	29								
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	34	31	28	25								
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23								
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21								
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	23	21	19								
10	50	38	31	26	46	36	29	25	32	27	23	28	24	21	25	22	19	17								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	23909	23909	23909
5°	24000	23608	23738
10°	23815	23222	23023
15°	23542	22534	21884
20°	23163	21551	20469
25°	22775	20436	19099
30°	22236	19287	17339
35°	21711	18039	15794
40°	21182	16750	14010
45°	20562	15299	12392
50°	19926	13835	10803
55°	19277	12262	9278
60°	18519	10601	7702
65°	17662	8909	7014
70°	16636	7336	6449
75°	15384	6687	6014
80°	13575	5979	5486
85°	10689	4705	4705



TEST NUMBER: P331714-840

CATALOG NUMBER: S122RDIP-S865D530U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.6	2.7
10°-20°	380.6	7.3
20°-30°	534.4	10.3
30°-40°	582.7	11.2
40°-50°	535.8	10.3
50°-60°	420.8	8.1
60°-70°	274.4	5.3
70°-80°	141.5	2.7
80°-90°	38.5	0.7
90°-100°	24.3	0.5
100°-110°	89.1	1.7
110°-120°	238.2	4.6
120°-130°	393.1	7.6
130°-140°	418.1	8.1
140°-150°	388.6	7.5
150°-160°	312.4	6.0
160°-170°	201.3	3.9
170°-180°	69.3	1.3
0°-30°	1053.6	20.3
0°-40°	1636.3	31.6
0°-60°	2593.0	50.0
0°-90°	3047.3	58.8
90°-120°	351.5	6.8
90°-150°	1551.4	29.9
90°-180°	2134.0	41.2
0°-180°	5181.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1481	1481	1481	1481	1481	
5°	1481	1473	1457	1468	1465	140
15°	1408	1392	1348	1323	1309	397
25°	1278	1233	1147	1094	1072	588
35°	1102	1030	915	834	801	689
45°	900	808	670	578	543	695
55°	685	578	436	358	330	612
65°	462	353	233	190	184	458
75°	247	155	107	98	96	261
85°	58	31	25	25	25	68
90°	0	6	10	13	14	4
95°	34	18	21	23	23	42
105°	160	167	32	38	40	171
115°	303	312	325	93	43	298
125°	428	436	445	449	451	382
135°	530	538	543	548	548	409
145°	615	615	624	627	624	385
155°	677	673	679	682	678	312
165°	714	711	712	715	712	202
175°	730	726	727	730	726	69
180°	728	728	728	728	728	



TEST NUMBER: P331714-840

CATALOG NUMBER: S122RDIP-S865D530U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1486.1	1484.9	1483.7	1482.5	1481.4	1479.5	1476.8	1474.2	1471.6	1468.9	1471.4
5°	1480.8	1479.3	1477.7	1476.2	1474.8	1472.1	1468.2	1464.4	1460.5	1456.6	1459.3
7.5°	1465.4	1463.6	1461.8	1460.0	1458.0	1454.9	1450.4	1445.8	1441.3	1436.7	1437.5
10°	1452.6	1450.5	1448.4	1446.3	1444.2	1440.3	1434.3	1428.4	1422.4	1416.4	1415.5
12.5°	1436.5	1433.9	1431.4	1428.9	1426.2	1421.2	1413.5	1405.9	1398.3	1390.7	1389.1
15°	1408.4	1405.1	1401.8	1398.6	1395.2	1388.6	1378.5	1368.4	1358.2	1348.1	1342.4
17.5°	1373.8	1368.8	1363.8	1358.8	1353.8	1344.8	1331.8	1318.8	1305.9	1292.8	1286.2
20°	1348.1	1342.1	1336.2	1330.2	1324.2	1313.8	1298.9	1284.0	1269.2	1254.3	1246.8
22.5°	1320.2	1313.5	1306.9	1300.2	1293.5	1281.8	1265.0	1248.2	1231.4	1214.6	1205.0
25°	1278.4	1268.9	1259.3	1249.8	1240.3	1225.7	1206.0	1186.4	1166.7	1147.1	1134.9
27.5°	1228.0	1217.6	1207.3	1196.9	1186.6	1170.3	1148.1	1126.0	1103.8	1081.7	1067.4
30°	1192.7	1181.3	1170.0	1158.7	1147.4	1129.8	1106.0	1082.2	1058.3	1034.5	1019.4
32.5°	1158.3	1145.1	1131.9	1118.6	1105.4	1086.7	1062.4	1038.0	1013.8	989.5	972.2
35°	1101.5	1086.3	1071.2	1055.9	1040.8	1020.1	993.8	967.7	941.5	915.2	896.5
37.5°	1044.7	1028.0	1011.4	994.6	978.0	955.6	927.8	899.8	871.9	843.9	823.2
40°	1005.0	987.1	969.3	951.4	933.5	910.2	881.3	852.4	823.5	794.7	773.5
42.5°	964.3	945.4	926.7	907.9	889.0	864.6	834.9	805.0	775.2	745.3	723.5
45°	900.5	880.5	860.6	840.6	820.7	795.1	763.9	732.6	701.3	670.0	648.8
47.5°	838.3	817.2	796.1	774.9	753.8	727.0	694.8	662.5	630.2	597.9	576.9
50°	793.3	772.1	751.0	729.8	708.7	681.8	649.0	616.2	583.5	550.8	530.2
52.5°	749.3	727.2	705.2	683.1	661.0	633.9	601.9	569.8	537.8	505.7	485.8
55°	684.8	661.6	638.3	615.1	591.9	564.1	532.0	499.8	467.7	435.6	417.7
57.5°	618.5	594.7	570.9	547.0	523.3	495.9	464.9	434.0	403.1	372.2	355.9
60°	573.5	549.7	525.9	502.1	478.3	451.0	420.3	389.6	359.0	328.3	313.2
62.5°	529.6	505.7	481.9	458.1	434.2	407.8	378.5	349.3	320.0	290.7	276.3
65°	462.3	438.2	414.0	389.9	365.9	340.3	313.6	286.8	259.9	233.2	223.1
67.5°	397.5	373.5	349.6	325.6	301.6	277.6	253.6	229.4	205.3	181.2	176.5
70°	352.4	329.2	306.0	282.8	259.5	237.6	217.1	196.5	176.0	155.4	152.5
72.5°	309.5	287.3	265.0	242.8	220.5	201.1	184.6	168.0	151.6	135.1	132.6
75°	246.6	225.7	204.9	184.0	163.2	147.7	137.5	127.4	117.3	107.2	105.1
77.5°	184.7	166.3	148.0	129.8	111.5	100.0	95.0	90.2	85.3	80.4	79.2
80°	146.0	130.9	115.7	100.5	85.3	76.2	73.2	70.3	67.3	64.3	63.1
82.5°	110.7	98.9	86.9	75.1	63.3	56.4	54.3	52.3	50.3	48.3	47.6
85°	57.7	51.4	45.1	38.9	32.6	29.1	28.2	27.3	26.4	25.4	25.4
87.5°	17.3	15.7	13.9	12.3	10.7	9.9	10.1	10.3	10.5	10.7	10.6
90°	0.5	1.8	3.1	4.3	5.7	6.8	7.8	8.7	9.6	10.5	11.1
92.5°	10.6	10.5	10.4	10.3	10.2	10.4	10.8	11.3	11.7	12.2	12.5
95°	34.2	30.4	26.6	22.6	18.8	17.3	18.1	18.9	19.7	20.6	21.1
97.5°	68.0	57.1	46.3	35.3	24.4	19.9	21.8	23.7	25.7	27.5	28.0
100°	93.3	77.3	61.2	45.1	29.1	22.1	24.0	26.1	28.1	30.0	31.0
102.5°	121.1	117.8	114.3	110.9	107.6	97.5	80.9	64.2	47.6	30.9	32.1
105°	160.2	163.7	167.2	170.8	174.3	160.1	128.1	96.1	64.1	32.1	33.4
107.5°	204.8	207.6	210.5	213.3	216.1	198.3	160.1	121.7	83.3	45.0	43.7
110°	233.5	235.9	238.4	240.9	243.3	227.6	193.8	160.0	126.0	92.2	80.5



TEST NUMBER: P331714-840

CATALOG NUMBER: S122RDIP-S865D530U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	260.4	262.7	264.8	267.0	269.1	266.1	257.7	249.3	241.0	232.7	189.9
115°	303.1	305.0	307.0	309.0	311.0	313.5	316.4	319.3	322.2	325.2	270.9
117.5°	341.1	343.4	345.6	347.8	350.0	352.1	354.2	356.2	358.2	360.1	347.1
120°	368.9	370.6	372.4	374.2	376.0	377.9	380.0	382.1	384.2	386.3	387.7
122.5°	392.5	394.4	396.3	398.1	399.9	402.0	404.2	406.6	408.9	411.2	412.0
125°	428.5	430.0	431.5	433.0	434.5	436.5	438.7	440.9	443.1	445.4	446.2
127.5°	461.0	462.7	464.4	466.1	467.8	469.5	471.1	472.8	474.4	476.2	477.3
130°	481.7	483.5	485.4	487.4	489.2	490.8	492.1	493.3	494.6	495.9	497.3
132.5°	502.8	504.3	505.9	507.6	509.2	510.6	511.9	513.2	514.4	515.7	516.8
135°	530.2	532.1	533.9	535.8	537.7	539.2	540.2	541.3	542.3	543.3	544.5
137.5°	558.0	559.2	560.5	561.8	563.1	564.4	565.6	566.8	567.9	569.2	570.4
140°	576.0	576.9	577.9	578.9	579.8	580.9	582.2	583.5	584.7	586.0	587.1
142.5°	591.2	592.1	592.9	593.7	594.6	595.7	597.2	598.6	600.2	601.7	602.6
145°	615.0	614.9	614.8	614.7	614.6	615.5	617.5	619.5	621.5	623.5	624.3
147.5°	635.8	635.3	634.9	634.5	634.0	634.8	636.7	638.7	640.7	642.7	643.3
150°	649.2	648.4	647.6	646.8	646.0	646.5	648.4	650.3	652.2	654.0	654.7
152.5°	660.7	659.7	658.8	657.9	657.0	657.4	659.2	661.1	662.8	664.6	665.3
155°	677.2	676.2	675.1	674.1	673.0	673.2	674.6	676.0	677.4	678.8	679.5
157.5°	690.1	689.3	688.4	687.5	686.6	686.7	687.6	688.6	689.6	690.6	691.4
160°	697.8	697.1	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8	698.5
162.5°	704.5	703.8	703.1	702.4	701.8	701.7	702.3	702.9	703.5	704.1	704.9
165°	713.6	712.9	712.2	711.4	710.7	710.6	710.9	711.2	711.7	712.0	712.9
167.5°	720.3	719.6	718.9	718.2	717.5	717.3	717.6	718.0	718.3	718.6	719.4
170°	724.1	723.5	722.8	722.1	721.3	721.0	721.3	721.5	721.8	722.1	722.9
172.5°	726.7	726.0	725.3	724.6	723.9	723.6	723.9	724.1	724.3	724.6	725.4
175°	729.9	729.1	728.3	727.5	726.6	726.4	726.6	726.8	727.0	727.3	728.1
177.5°	730.4	729.8	729.1	728.5	727.8	727.5	727.6	727.7	727.8	727.9	728.6
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331714-840

CATALOG NUMBER: S122RDIP-S865D530U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1473.7	1476.1	1478.4	1479.5	1478.9	1478.4	1478.0	1477.5
5°	1462.0	1464.6	1467.3	1468.2	1467.3	1466.4	1465.5	1464.6
7.5°	1438.4	1439.1	1439.9	1439.5	1437.9	1436.4	1434.8	1433.3
10°	1414.6	1413.7	1412.8	1411.5	1409.7	1408.0	1406.1	1404.3
12.5°	1387.5	1385.8	1384.2	1382.0	1379.0	1376.0	1373.0	1370.1
15°	1336.8	1331.1	1325.4	1321.1	1318.2	1315.1	1312.2	1309.2
17.5°	1279.4	1272.6	1266.0	1260.0	1254.9	1249.8	1244.7	1239.5
20°	1239.4	1231.9	1224.5	1217.5	1210.9	1204.4	1197.8	1191.3
22.5°	1195.5	1185.9	1176.3	1169.0	1164.2	1159.2	1154.4	1149.5
25°	1122.7	1110.4	1098.2	1089.8	1085.4	1081.0	1076.5	1072.1
27.5°	1053.2	1038.9	1024.7	1014.1	1007.0	999.9	992.8	985.7
30°	1004.1	989.0	973.7	962.1	954.1	946.0	938.1	930.0
32.5°	954.8	937.5	920.2	907.7	900.2	892.6	885.0	877.5
35°	877.7	859.0	840.2	827.6	821.0	814.5	807.9	801.3
37.5°	802.6	781.9	761.3	747.2	739.7	732.2	724.7	717.2
40°	752.3	731.2	710.0	695.6	687.9	680.1	672.4	664.7
42.5°	701.7	679.7	657.9	643.2	635.7	628.2	620.7	613.2
45°	627.7	606.6	585.4	571.3	564.1	557.0	549.9	542.7
47.5°	555.8	534.8	513.8	500.1	493.6	487.1	480.6	474.1
50°	509.7	489.1	468.6	455.1	448.9	442.6	436.4	430.1
52.5°	466.1	446.3	426.4	413.6	407.8	402.0	396.3	390.5
55°	399.8	381.9	364.1	352.2	346.6	340.9	335.3	329.6
57.5°	339.5	323.2	306.8	296.2	291.4	286.6	281.9	277.1
60°	297.9	282.8	267.5	257.6	252.8	248.0	243.3	238.5
62.5°	261.9	247.4	232.9	224.2	221.4	218.5	215.6	212.8
65°	212.9	202.8	192.7	187.1	186.2	185.4	184.5	183.6
67.5°	171.9	167.2	162.6	159.8	158.9	157.8	156.9	156.0
70°	149.5	146.5	143.5	141.5	140.3	139.1	137.8	136.6
72.5°	130.1	127.5	125.0	123.5	122.7	122.0	121.3	120.6
75°	103.0	101.0	98.9	97.7	97.4	97.0	96.7	96.4
77.5°	78.1	76.9	75.6	74.8	74.3	73.8	73.4	72.9
80°	61.9	60.8	59.6	59.0	59.0	59.0	59.0	59.0
82.5°	46.9	46.0	45.3	45.0	45.0	45.0	45.0	45.0
85°	25.4	25.4	25.4	25.4	25.4	25.4	25.4	25.4
87.5°	10.4	10.3	10.2	10.2	10.2	10.3	10.3	10.3
90°	11.7	12.3	12.9	13.3	13.5	13.7	14.0	14.2
92.5°	12.8	13.1	13.4	13.6	13.8	13.9	14.1	14.2
95°	21.7	22.3	22.9	23.1	23.0	22.9	22.8	22.6
97.5°	28.5	28.9	29.4	29.7	29.8	30.0	30.1	30.3
100°	31.9	32.8	33.8	34.3	34.6	34.8	35.0	35.3
102.5°	33.3	34.5	35.7	36.6	36.9	37.2	37.5	37.9
105°	34.7	36.1	37.3	38.2	38.7	39.1	39.6	40.1
107.5°	42.4	41.1	39.8	39.4	39.8	40.3	40.7	41.2
110°	68.8	57.1	45.3	39.8	40.2	40.7	41.2	41.6





TEST NUMBER: P331714-840

CATALOG NUMBER: S122RDIP-S865D530U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	147.1	104.4	61.7	40.6	40.9	41.3	41.7	42.0
115°	216.7	162.5	108.3	77.0	68.5	60.1	51.6	43.2
117.5°	334.0	320.8	307.7	287.3	259.5	231.9	204.2	176.4
120°	389.1	390.5	391.9	384.8	368.9	353.1	337.3	321.4
122.5°	412.8	413.7	414.5	413.4	410.4	407.3	404.2	401.1
125°	447.0	447.8	448.6	449.2	449.6	449.9	450.3	450.6
127.5°	478.5	479.7	480.9	481.5	481.6	481.7	481.7	481.8
130°	498.5	499.8	501.1	501.7	501.5	501.4	501.3	501.2
132.5°	518.0	519.1	520.2	520.6	520.5	520.4	520.3	520.2
135°	545.7	546.8	548.1	548.6	548.3	548.1	547.9	547.5
137.5°	571.5	572.6	573.8	574.1	573.7	573.3	573.0	572.6
140°	588.1	589.2	590.3	590.5	589.9	589.4	588.8	588.1
142.5°	603.6	604.5	605.5	605.7	605.1	604.5	603.9	603.3
145°	625.1	625.9	626.7	626.8	626.3	625.7	625.1	624.5
147.5°	643.9	644.5	645.1	645.1	644.7	644.2	643.7	643.2
150°	655.4	656.1	656.8	656.9	656.3	655.7	655.1	654.6
152.5°	666.0	666.7	667.4	667.3	666.6	665.8	665.0	664.3
155°	680.2	681.0	681.7	681.5	680.5	679.6	678.7	677.7
157.5°	692.2	693.0	693.8	693.8	692.8	691.9	690.9	690.0
160°	699.1	699.8	700.5	700.5	699.7	698.9	698.0	697.2
162.5°	705.7	706.5	707.3	707.2	706.2	705.2	704.2	703.2
165°	713.7	714.5	715.3	715.3	714.5	713.7	712.9	712.0
167.5°	720.2	721.1	722.0	721.9	720.7	719.7	718.6	717.6
170°	723.7	724.5	725.3	725.2	724.1	723.1	722.1	720.9
172.5°	726.2	727.0	727.8	727.7	726.7	725.6	724.6	723.5
175°	728.9	729.7	730.5	730.4	729.2	728.0	726.9	725.7
177.5°	729.2	729.9	730.5	730.4	729.6	728.7	727.9	727.1
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)