

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331727-840

Luminaire Tested: **S122RDIP-S865D925U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331727-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S865D925U840-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6389.6 lumens  
Efficiency: N/A  
Efficacy: 105.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331727-840

CATALOG NUMBER: S122RDIP-S865D925U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331727-840

CATALOG NUMBER: S122RDIP-S865D925U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48
1	98	94	90	87	90	86	83	80	73	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	67	64	60	57	53	51	48	43	41	40	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	39	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	32	29	26	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	23909	23909	23909
5°	24000	23608	23738
10°	23815	23222	23023
15°	23542	22534	21884
20°	23163	21551	20469
25°	22775	20436	19099
30°	22236	19287	17339
35°	21711	18039	15794
40°	21182	16750	14010
45°	20562	15299	12392
50°	19926	13835	10803
55°	19277	12262	9278
60°	18519	10601	7702
65°	17662	8909	7014
70°	16636	7336	6449
75°	15384	6687	6014
80°	13575	5979	5486
85°	10689	4705	4705



TEST NUMBER: P331727-840

CATALOG NUMBER: S122RDIP-S865D925U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.6	2.2
10°-20°	380.6	6.0
20°-30°	534.4	8.4
30°-40°	582.7	9.1
40°-50°	535.8	8.4
50°-60°	420.8	6.6
60°-70°	274.4	4.3
70°-80°	141.5	2.2
80°-90°	41.5	0.6
90°-100°	75.7	1.2
100°-110°	235.0	3.7
110°-120°	401.8	6.3
120°-130°	528.3	8.3
130°-140°	593.0	9.3
140°-150°	581.4	9.1
150°-160°	487.7	7.6
160°-170°	323.5	5.1
170°-180°	113.0	1.8
0°-30°	1053.6	16.5
0°-40°	1636.3	25.6
0°-60°	2593.0	40.6
0°-90°	3050.2	47.7
90°-120°	712.5	11.2
90°-150°	2415.2	37.8
90°-180°	3339.0	52.3
0°-180°	6389.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1481	1481	1481	1481	1481	
5°	1481	1473	1457	1468	1465	140
15°	1408	1392	1348	1323	1309	397
25°	1278	1233	1147	1094	1072	588
35°	1102	1030	915	834	801	689
45°	900	808	670	578	543	695
55°	685	578	436	358	330	612
65°	462	353	233	190	184	458
75°	247	155	107	98	96	261
85°	58	31	25	25	25	68
90°	1	14	35	33	34	5
95°	52	62	64	64	62	60
105°	217	220	222	224	224	229
115°	403	409	407	406	403	399
125°	586	595	593	590	588	524
135°	759	769	772	771	768	586
145°	921	928	934	935	931	575
155°	1053	1056	1059	1064	1061	485
165°	1146	1145	1145	1151	1147	323
175°	1192	1189	1187	1194	1188	113
180°	1194	1194	1194	1194	1194	



TEST NUMBER: P331727-840

CATALOG NUMBER: S122RDIP-S865D925U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1486.1	1484.9	1483.7	1482.5	1481.4	1479.5	1476.8	1474.2	1471.6	1468.9	1471.4
5°	1480.8	1479.3	1477.7	1476.2	1474.8	1472.1	1468.2	1464.4	1460.5	1456.6	1459.3
7.5°	1465.4	1463.6	1461.8	1460.0	1458.0	1454.9	1450.4	1445.8	1441.3	1436.7	1437.5
10°	1452.6	1450.5	1448.4	1446.3	1444.2	1440.3	1434.3	1428.4	1422.4	1416.4	1415.5
12.5°	1436.5	1433.9	1431.4	1428.9	1426.2	1421.2	1413.5	1405.9	1398.3	1390.7	1389.1
15°	1408.4	1405.1	1401.8	1398.6	1395.2	1388.6	1378.5	1368.4	1358.2	1348.1	1342.4
17.5°	1373.8	1368.8	1363.8	1358.8	1353.8	1344.8	1331.8	1318.8	1305.9	1292.8	1286.2
20°	1348.1	1342.1	1336.2	1330.2	1324.2	1313.8	1298.9	1284.0	1269.2	1254.3	1246.8
22.5°	1320.2	1313.5	1306.9	1300.2	1293.5	1281.8	1265.0	1248.2	1231.4	1214.6	1205.0
25°	1278.4	1268.9	1259.3	1249.8	1240.3	1225.7	1206.0	1186.4	1166.7	1147.1	1134.9
27.5°	1228.0	1217.6	1207.3	1196.9	1186.6	1170.3	1148.1	1126.0	1103.8	1081.7	1067.4
30°	1192.7	1181.3	1170.0	1158.7	1147.4	1129.8	1106.0	1082.2	1058.3	1034.5	1019.4
32.5°	1158.3	1145.1	1131.9	1118.6	1105.4	1086.7	1062.4	1038.0	1013.8	989.5	972.2
35°	1101.5	1086.3	1071.2	1055.9	1040.8	1020.1	993.8	967.7	941.5	915.2	896.5
37.5°	1044.7	1028.0	1011.4	994.6	978.0	955.6	927.8	899.8	871.9	843.9	823.2
40°	1005.0	987.1	969.3	951.4	933.5	910.2	881.3	852.4	823.5	794.7	773.5
42.5°	964.3	945.4	926.7	907.9	889.0	864.6	834.9	805.0	775.2	745.3	723.5
45°	900.5	880.5	860.6	840.6	820.7	795.1	763.9	732.6	701.3	670.0	648.8
47.5°	838.3	817.2	796.1	774.9	753.8	727.0	694.8	662.5	630.2	597.9	576.9
50°	793.3	772.1	751.0	729.8	708.7	681.8	649.0	616.2	583.5	550.8	530.2
52.5°	749.3	727.2	705.2	683.1	661.0	633.9	601.9	569.8	537.8	505.7	485.8
55°	684.8	661.6	638.3	615.1	591.9	564.1	532.0	499.8	467.7	435.6	417.7
57.5°	618.5	594.7	570.9	547.0	523.3	495.9	464.9	434.0	403.1	372.2	355.9
60°	573.5	549.7	525.9	502.1	478.3	451.0	420.3	389.6	359.0	328.3	313.2
62.5°	529.6	505.7	481.9	458.1	434.2	407.8	378.5	349.3	320.0	290.7	276.3
65°	462.3	438.2	414.0	389.9	365.9	340.3	313.6	286.8	259.9	233.2	223.1
67.5°	397.5	373.5	349.6	325.6	301.6	277.6	253.6	229.4	205.3	181.2	176.5
70°	352.4	329.2	306.0	282.8	259.5	237.6	217.1	196.5	176.0	155.4	152.5
72.5°	309.5	287.3	265.0	242.8	220.5	201.1	184.6	168.0	151.6	135.1	132.6
75°	246.6	225.7	204.9	184.0	163.2	147.7	137.5	127.4	117.3	107.2	105.1
77.5°	184.7	166.3	148.0	129.8	111.5	100.0	95.0	90.2	85.3	80.4	79.2
80°	146.0	130.9	115.7	100.5	85.3	76.2	73.2	70.3	67.3	64.3	63.1
82.5°	110.7	98.9	86.9	75.1	63.3	56.4	54.3	52.3	50.3	48.3	47.6
85°	57.7	51.4	45.1	38.9	32.6	29.1	28.2	27.3	26.4	25.4	25.4
87.5°	17.4	16.0	14.6	13.2	11.9	11.7	12.7	13.6	14.6	15.7	15.3
90°	1.0	3.7	6.4	9.1	11.7	15.6	20.5	25.4	30.3	35.2	34.8
92.5°	18.0	19.9	21.9	23.8	25.9	27.4	28.6	29.7	30.9	32.0	32.1
95°	52.4	54.6	56.9	59.1	61.4	62.7	63.1	63.6	64.0	64.5	64.5
97.5°	95.7	97.8	99.7	101.7	103.6	105.0	105.9	106.7	107.6	108.5	108.5
100°	127.9	129.8	131.6	133.4	135.1	136.4	137.0	137.7	138.5	139.1	139.1
102.5°	161.9	163.3	164.7	166.1	167.5	168.7	169.6	170.5	171.3	172.2	172.3
105°	216.7	217.3	218.0	218.7	219.3	219.9	220.4	220.9	221.3	221.7	222.2
107.5°	271.9	272.9	273.9	274.9	275.9	276.3	276.3	276.3	276.3	276.3	276.5
110°	307.4	308.7	310.0	311.4	312.8	313.5	313.5	313.5	313.5	313.5	313.5



TEST NUMBER: P331727-840

CATALOG NUMBER: S122RDIP-S865D925U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	346.1	347.4	348.8	350.1	351.4	352.0	351.8	351.6	351.5	351.3	350.8
115°	403.1	404.5	405.8	407.2	408.5	408.9	408.5	408.1	407.6	407.2	407.0
117.5°	460.0	461.7	463.5	465.3	467.2	467.4	466.2	464.8	463.6	462.4	461.8
120°	497.9	499.7	501.4	503.2	505.0	505.0	503.2	501.4	499.7	497.9	497.9
122.5°	532.5	534.6	536.8	539.0	541.1	541.6	540.3	539.1	537.9	536.5	536.0
125°	586.5	588.5	590.6	592.6	594.6	595.3	594.6	593.9	593.3	592.6	591.9
127.5°	639.1	641.7	644.3	646.8	649.3	650.3	649.4	648.6	647.8	647.0	646.2
130°	672.2	675.1	678.0	681.0	683.9	685.1	684.6	684.2	683.8	683.3	682.9
132.5°	709.3	711.7	714.1	716.4	718.8	720.0	720.1	720.2	720.2	720.3	719.4
135°	758.9	761.3	763.8	766.3	768.7	770.2	770.6	771.0	771.5	771.9	771.7
137.5°	811.1	813.0	815.1	817.1	819.1	820.4	821.0	821.6	822.2	822.7	822.6
140°	842.5	844.6	846.6	848.6	850.6	852.1	853.2	854.3	855.6	856.7	856.7
142.5°	874.7	876.8	878.8	880.8	882.8	884.2	884.9	885.8	886.5	887.3	887.5
145°	921.1	922.7	924.2	925.8	927.4	928.9	930.2	931.5	932.9	934.2	934.4
147.5°	962.4	964.3	966.2	968.1	970.0	971.4	972.3	973.1	974.0	974.9	975.4
150°	990.7	992.0	993.3	994.7	996.0	997.1	998.0	999.0	999.9	1000.8	1001.4
152.5°	1015.6	1017.0	1018.3	1019.7	1021.1	1022.3	1023.3	1024.4	1025.4	1026.5	1027.4
155°	1053.2	1053.8	1054.5	1055.2	1055.8	1056.5	1057.2	1057.8	1058.5	1059.1	1060.4
157.5°	1085.2	1085.6	1086.1	1086.5	1087.0	1087.4	1087.8	1088.2	1088.6	1089.0	1090.6
160°	1104.6	1105.0	1105.4	1105.9	1106.3	1106.7	1106.9	1107.1	1107.3	1107.5	1108.9
162.5°	1122.3	1122.4	1122.5	1122.6	1122.7	1122.8	1123.1	1123.3	1123.5	1123.7	1125.2
165°	1145.9	1145.7	1145.4	1145.2	1145.0	1144.9	1144.9	1144.9	1144.9	1144.9	1146.4
167.5°	1165.6	1165.0	1164.3	1163.6	1163.0	1162.6	1162.6	1162.5	1162.5	1162.4	1164.0
170°	1176.1	1175.4	1174.8	1174.1	1173.4	1173.0	1172.8	1172.6	1172.3	1172.0	1173.7
172.5°	1183.4	1182.7	1182.0	1181.3	1180.6	1180.2	1180.0	1179.7	1179.5	1179.3	1180.9
175°	1192.2	1191.5	1190.8	1190.2	1189.5	1189.0	1188.5	1188.1	1187.6	1187.2	1188.7
177.5°	1195.9	1195.3	1194.8	1194.3	1193.7	1193.3	1192.9	1192.5	1192.1	1191.8	1192.9
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3



TEST NUMBER: P331727-840

CATALOG NUMBER: S122RDIP-S865D925U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8	1480.8
2.5°	1473.7	1476.1	1478.4	1479.5	1478.9	1478.4	1478.0	1477.5
5°	1462.0	1464.6	1467.3	1468.2	1467.3	1466.4	1465.5	1464.6
7.5°	1438.4	1439.1	1439.9	1439.5	1437.9	1436.4	1434.8	1433.3
10°	1414.6	1413.7	1412.8	1411.5	1409.7	1408.0	1406.1	1404.3
12.5°	1387.5	1385.8	1384.2	1382.0	1379.0	1376.0	1373.0	1370.1
15°	1336.8	1331.1	1325.4	1321.1	1318.2	1315.1	1312.2	1309.2
17.5°	1279.4	1272.6	1266.0	1260.0	1254.9	1249.8	1244.7	1239.5
20°	1239.4	1231.9	1224.5	1217.5	1210.9	1204.4	1197.8	1191.3
22.5°	1195.5	1185.9	1176.3	1169.0	1164.2	1159.2	1154.4	1149.5
25°	1122.7	1110.4	1098.2	1089.8	1085.4	1081.0	1076.5	1072.1
27.5°	1053.2	1038.9	1024.7	1014.1	1007.0	999.9	992.8	985.7
30°	1004.1	989.0	973.7	962.1	954.1	946.0	938.1	930.0
32.5°	954.8	937.5	920.2	907.7	900.2	892.6	885.0	877.5
35°	877.7	859.0	840.2	827.6	821.0	814.5	807.9	801.3
37.5°	802.6	781.9	761.3	747.2	739.7	732.2	724.7	717.2
40°	752.3	731.2	710.0	695.6	687.9	680.1	672.4	664.7
42.5°	701.7	679.7	657.9	643.2	635.7	628.2	620.7	613.2
45°	627.7	606.6	585.4	571.3	564.1	557.0	549.9	542.7
47.5°	555.8	534.8	513.8	500.1	493.6	487.1	480.6	474.1
50°	509.7	489.1	468.6	455.1	448.9	442.6	436.4	430.1
52.5°	466.1	446.3	426.4	413.6	407.8	402.0	396.3	390.5
55°	399.8	381.9	364.1	352.2	346.6	340.9	335.3	329.6
57.5°	339.5	323.2	306.8	296.2	291.4	286.6	281.9	277.1
60°	297.9	282.8	267.5	257.6	252.8	248.0	243.3	238.5
62.5°	261.9	247.4	232.9	224.2	221.4	218.5	215.6	212.8
65°	212.9	202.8	192.7	187.1	186.2	185.4	184.5	183.6
67.5°	171.9	167.2	162.6	159.8	158.9	157.8	156.9	156.0
70°	149.5	146.5	143.5	141.5	140.3	139.1	137.8	136.6
72.5°	130.1	127.5	125.0	123.5	122.7	122.0	121.3	120.6
75°	103.0	101.0	98.9	97.7	97.4	97.0	96.7	96.4
77.5°	78.1	76.9	75.6	74.8	74.3	73.8	73.4	72.9
80°	61.9	60.8	59.6	59.0	59.0	59.0	59.0	59.0
82.5°	46.9	46.0	45.3	45.0	45.0	45.0	45.0	45.0
85°	25.4	25.4	25.4	25.4	25.4	25.4	25.4	25.4
87.5°	14.9	14.6	14.3	14.1	14.2	14.2	14.3	14.3
90°	34.3	33.9	33.5	33.3	33.6	33.8	34.0	34.2
92.5°	32.2	32.3	32.4	32.5	32.5	32.5	32.6	32.6
95°	64.5	64.5	64.5	64.2	63.8	63.4	62.9	62.5
97.5°	108.5	108.5	108.5	108.5	108.4	108.4	108.3	108.3
100°	139.1	139.1	139.1	139.0	138.8	138.6	138.3	138.0
102.5°	172.5	172.7	172.9	172.8	172.6	172.4	172.2	172.0
105°	222.6	223.1	223.5	223.7	223.7	223.7	223.7	223.7
107.5°	276.7	276.9	277.0	276.6	275.6	274.6	273.6	272.5
110°	313.5	313.5	313.5	313.1	312.5	311.7	311.0	310.4





TEST NUMBER: P331727-840

CATALOG NUMBER: S122RDIP-S865D925U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	350.2	349.7	349.2	348.6	348.2	347.7	347.2	346.7
115°	406.7	406.5	406.3	405.8	405.2	404.5	403.7	403.1
117.5°	461.3	460.8	460.2	459.6	459.0	458.3	457.6	457.0
120°	497.9	497.9	497.9	497.6	496.9	496.1	495.5	494.8
122.5°	535.4	534.9	534.4	533.9	533.4	532.9	532.4	531.9
125°	591.3	590.6	589.9	589.5	589.3	589.0	588.8	588.5
127.5°	645.4	644.6	643.8	643.0	642.3	641.6	640.9	640.2
130°	682.4	682.0	681.5	680.9	679.9	679.0	678.1	677.2
132.5°	718.4	717.4	716.4	715.6	714.9	714.2	713.5	712.8
135°	771.5	771.3	771.0	770.6	769.9	769.3	768.6	767.9
137.5°	822.4	822.2	822.0	821.5	820.6	819.7	818.8	817.9
140°	856.7	856.7	856.7	856.2	855.3	854.3	853.5	852.6
142.5°	887.7	887.8	888.0	887.7	886.8	885.9	884.9	884.0
145°	934.6	934.9	935.1	934.8	933.9	933.0	932.1	931.2
147.5°	975.9	976.4	976.9	976.7	975.9	975.0	974.2	973.3
150°	1002.1	1002.8	1003.4	1003.4	1002.8	1002.1	1001.4	1000.8
152.5°	1028.2	1029.1	1030.0	1030.0	1029.1	1028.2	1027.4	1026.5
155°	1061.5	1062.6	1063.7	1063.9	1063.2	1062.6	1061.9	1061.2
157.5°	1092.1	1093.6	1095.1	1095.3	1094.3	1093.2	1092.1	1091.1
160°	1110.2	1111.6	1113.0	1113.2	1112.3	1111.4	1110.4	1109.5
162.5°	1126.7	1128.2	1129.7	1130.0	1128.9	1127.8	1126.8	1125.7
165°	1148.0	1149.5	1151.1	1151.3	1150.2	1149.1	1148.0	1146.9
167.5°	1165.5	1167.1	1168.6	1168.8	1167.7	1166.5	1165.4	1164.2
170°	1175.2	1176.8	1178.3	1178.4	1177.1	1175.8	1174.4	1173.1
172.5°	1182.5	1184.1	1185.6	1185.7	1184.4	1183.1	1181.6	1180.3
175°	1190.3	1191.8	1193.5	1193.6	1192.2	1190.8	1189.5	1188.2
177.5°	1194.0	1195.1	1196.1	1196.1	1195.1	1194.0	1192.9	1191.8
180°	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3	1194.3

(END OF REPORT)