

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331249-940

Luminaire Tested: **S122DIP-S290D530U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331249-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D530U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3049.1 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28				
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24				
4	73	63	55	50	66	57	51	46	47	43	39	38	35	32	29	27	25	21				
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22	19				
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	22	20	17				
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18	15				
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13				
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12				
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	1.6
10°-20°	145.9	4.8
20°-30°	211.8	6.9
30°-40°	223.5	7.3
40°-50°	197.9	6.5
50°-60°	157.9	5.2
60°-70°	107.3	3.5
70°-80°	55.0	1.8
80°-90°	14.8	0.5
90°-100°	21.5	0.7
100°-110°	78.7	2.6
110°-120°	210.3	6.9
120°-130°	347.1	11.4
130°-140°	369.2	12.1
140°-150°	343.1	11.3
150°-160°	275.9	9.0
160°-170°	177.8	5.8
170°-180°	61.2	2.0
0°-30°	407.9	13.4
0°-40°	631.4	20.7
0°-60°	987.2	32.4
0°-90°	1164.4	38.2
90°-120°	310.4	10.2
90°-150°	1369.9	44.9
90°-180°	1885.0	61.8
0°-180°	3049.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	12
90°	13	0	13	0	13	6
95°	20	30	20	30	20	19
105°	35	141	35	141	35	37
115°	38	268	38	268	38	96
125°	398	378	398	378	398	344
135°	484	468	484	468	484	373
145°	551	543	551	543	551	345
155°	598	598	598	598	598	276
165°	629	630	629	630	629	177
175°	641	644	641	644	641	61
180°	643	643	643	643	643	



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	6.7	6.7	6.8	6.6	6.6	6.7	6.5	6.2	6.3	6.4	6.4
90°	12.6	12.4	12.1	11.9	11.8	11.4	10.9	10.3	9.8	9.3	8.5
92.5°	12.6	12.5	12.3	12.2	12.0	11.9	11.6	11.3	11.1	10.8	10.3
95°	20.0	20.2	20.2	20.3	20.4	20.2	19.7	19.2	18.6	18.2	17.4
97.5°	26.8	26.6	26.5	26.3	26.2	25.9	25.5	25.1	24.7	24.3	22.6
100°	31.2	30.9	30.8	30.6	30.3	29.9	29.0	28.2	27.4	26.5	24.8
102.5°	33.4	33.1	32.8	32.5	32.3	31.6	30.5	29.4	28.4	27.3	42.0
105°	35.4	35.0	34.5	34.2	33.7	32.9	31.8	30.7	29.5	28.4	56.6
107.5°	36.4	35.9	35.6	35.1	34.8	35.1	36.3	37.5	38.6	39.8	73.6
110°	36.7	36.4	35.9	35.5	35.1	40.0	50.4	60.7	71.1	81.4	111.3



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	37.1	36.8	36.5	36.1	35.8	54.5	92.2	129.9	167.6	205.5	212.8
115°	38.2	45.6	53.1	60.5	67.9	95.6	143.5	191.4	239.2	287.1	284.5
117.5°	155.8	180.3	204.7	229.2	253.7	271.7	283.3	294.9	306.5	318.0	316.3
120°	283.8	297.8	311.8	325.7	339.7	346.1	344.8	343.6	342.3	341.1	339.2
122.5°	354.2	357.0	359.6	362.4	365.1	366.0	365.3	364.5	363.8	363.1	361.1
125°	397.9	397.6	397.3	397.0	396.6	396.1	395.4	394.7	394.0	393.2	391.3
127.5°	425.4	425.3	425.3	425.3	425.2	424.6	423.6	422.5	421.4	420.4	418.9
130°	442.6	442.6	442.7	442.8	443.0	442.5	441.3	440.1	439.1	437.9	436.8
132.5°	459.3	459.4	459.5	459.6	459.7	459.3	458.3	457.4	456.4	455.4	454.2
135°	483.5	483.8	483.9	484.1	484.4	483.9	482.9	481.9	480.8	479.7	478.8
137.5°	505.6	506.0	506.2	506.6	506.9	506.7	505.6	504.6	503.6	502.6	501.5
140°	519.3	519.9	520.4	520.8	521.4	521.2	520.2	519.3	518.4	517.5	516.3
142.5°	532.7	533.2	533.8	534.3	534.8	534.7	533.8	533.0	532.1	531.3	529.9
145°	551.4	552.0	552.5	553.0	553.5	553.4	552.7	552.0	551.3	550.5	548.8
147.5°	567.9	568.4	568.8	569.3	569.6	569.6	569.1	568.6	568.0	567.5	565.7
150°	578.0	578.5	579.0	579.5	580.1	580.0	579.3	578.7	578.1	577.5	575.9
152.5°	586.6	587.2	587.9	588.6	589.2	589.3	588.7	588.1	587.5	586.8	585.2
155°	598.4	599.3	600.1	600.9	601.7	601.9	601.3	600.7	600.0	599.4	598.2
157.5°	609.3	610.1	610.9	611.7	612.6	612.6	611.9	611.2	610.5	609.8	608.9
160°	615.6	616.4	617.2	617.9	618.6	618.6	618.0	617.3	616.8	616.2	615.5
162.5°	620.9	621.8	622.7	623.6	624.5	624.6	623.8	623.1	622.4	621.7	621.2
165°	628.7	629.5	630.2	630.9	631.6	631.6	630.9	630.2	629.5	628.7	628.4
167.5°	633.6	634.5	635.5	636.4	637.4	637.5	636.8	636.0	635.3	634.5	634.3
170°	636.6	637.6	638.5	639.4	640.3	640.4	639.7	639.0	638.3	637.6	637.3
172.5°	638.8	639.8	640.7	641.7	642.6	642.7	641.9	641.2	640.5	639.8	639.5
175°	640.8	641.9	642.8	643.9	645.0	645.1	644.4	643.6	642.9	642.2	641.9
177.5°	642.0	642.7	643.5	644.3	645.0	645.1	644.5	643.9	643.4	642.7	642.7
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	6.4	6.2	6.1	6.2	5.4	5.3	4.4	3.7	3.7	3.7	3.7
90°	7.7	6.9	6.0	5.0	3.8	2.8	1.6	0.4	1.6	2.8	3.8
92.5°	10.0	9.5	9.2	9.0	9.1	9.2	9.3	9.4	9.3	9.2	9.1
95°	16.7	16.0	15.2	16.6	20.0	23.5	26.8	30.2	26.8	23.5	20.0
97.5°	21.0	19.3	17.6	21.6	31.2	40.8	50.4	60.0	50.4	40.8	31.2
100°	23.0	21.2	19.5	25.7	39.9	54.0	68.2	82.4	68.2	54.0	39.9
102.5°	56.7	71.4	86.1	95.0	97.9	100.9	104.0	106.9	104.0	100.9	97.9
105°	84.9	113.1	141.3	153.9	150.8	147.7	144.5	141.4	144.5	147.7	150.8
107.5°	107.5	141.3	175.1	190.8	188.3	185.8	183.3	180.8	183.3	185.8	188.3
110°	141.2	171.1	201.0	214.8	212.7	210.5	208.3	206.2	208.3	210.5	212.7



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	220.2	227.6	235.0	237.6	235.8	233.8	231.9	230.0	231.9	233.8	235.8
115°	282.0	279.4	276.8	274.6	272.9	271.1	269.3	267.6	269.3	271.1	272.9
117.5°	314.5	312.7	310.9	309.1	307.1	305.1	303.2	301.2	303.2	305.1	307.1
120°	337.4	335.6	333.7	332.0	330.4	328.9	327.3	325.7	327.3	328.9	330.4
122.5°	359.0	357.0	355.0	353.1	351.5	349.9	348.2	346.6	348.2	349.9	351.5
125°	389.3	387.4	385.4	383.7	382.4	381.0	379.7	378.4	379.7	381.0	382.4
127.5°	417.5	416.0	414.6	413.0	411.5	410.1	408.6	407.1	408.6	410.1	411.5
130°	435.6	434.5	433.4	431.9	430.3	428.6	427.0	425.3	427.0	428.6	430.3
132.5°	453.2	452.0	450.8	449.6	448.2	446.7	445.3	444.0	445.3	446.7	448.2
135°	478.0	477.0	476.1	474.7	473.1	471.4	469.8	468.1	469.8	471.4	473.1
137.5°	500.5	499.4	498.4	497.2	496.1	494.9	493.7	492.7	493.7	494.9	496.1
140°	515.2	514.1	512.9	511.9	511.1	510.3	509.4	508.6	509.4	510.3	511.1
142.5°	528.6	527.4	526.0	525.0	524.2	523.5	522.8	522.0	522.8	523.5	524.2
145°	547.0	545.3	543.5	542.7	542.8	542.9	543.0	543.1	543.0	542.9	542.8
147.5°	564.0	562.2	560.5	559.8	560.3	560.6	561.0	561.4	561.0	560.6	560.3
150°	574.2	572.6	570.9	570.4	571.1	571.9	572.6	573.3	572.6	571.9	571.1
152.5°	583.7	582.1	580.5	580.1	580.9	581.8	582.6	583.4	582.6	581.8	580.9
155°	596.9	595.7	594.4	594.2	595.2	596.1	597.1	598.0	597.1	596.1	595.2
157.5°	608.1	607.2	606.4	606.3	607.1	607.9	608.7	609.4	608.7	607.9	607.1
160°	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2	615.5	614.9	614.3
162.5°	620.6	620.1	619.6	619.6	620.2	620.8	621.4	622.1	621.4	620.8	620.2
165°	628.0	627.8	627.5	627.6	628.2	628.8	629.5	630.1	629.5	628.8	628.2
167.5°	634.0	633.6	633.4	633.6	634.2	634.8	635.4	636.1	635.4	634.8	634.2
170°	637.1	636.9	636.7	636.9	637.6	638.2	638.8	639.4	638.8	638.2	637.6
172.5°	639.4	639.2	638.9	639.2	639.8	640.4	641.1	641.7	641.1	640.4	639.8
175°	641.8	641.6	641.4	641.6	642.4	643.1	643.8	644.5	643.8	643.1	642.4
177.5°	642.6	642.5	642.4	642.7	643.3	643.8	644.4	645.0	644.4	643.8	643.3
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	3.7	3.8	3.8	3.9	3.9	3.9	3.9	4.0	4.1	3.9	3.9
90°	5.0	6.0	6.9	7.7	8.5	9.3	9.8	10.3	10.9	11.4	11.8
92.5°	9.0	9.2	9.5	10.0	10.3	10.8	11.1	11.3	11.6	11.9	12.0
95°	16.6	15.2	16.0	16.7	17.4	18.2	18.6	19.2	19.7	20.2	20.4
97.5°	21.6	17.6	19.3	21.0	22.6	24.3	24.7	25.1	25.5	25.9	26.2
100°	25.7	19.5	21.2	23.0	24.8	26.5	27.4	28.2	29.0	29.9	30.3
102.5°	95.0	86.1	71.4	56.7	42.0	27.3	28.4	29.4	30.5	31.6	32.3
105°	153.9	141.3	113.1	84.9	56.6	28.4	29.5	30.7	31.8	32.9	33.7
107.5°	190.8	175.1	141.3	107.5	73.6	39.8	38.6	37.5	36.3	35.1	34.8
110°	214.8	201.0	171.1	141.2	111.3	81.4	71.1	60.7	50.4	40.0	35.1



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.6	235.0	227.6	220.2	212.8	205.5	167.6	129.9	92.2	54.5	35.8
115°	274.6	276.8	279.4	282.0	284.5	287.1	239.2	191.4	143.5	95.6	67.9
117.5°	309.1	310.9	312.7	314.5	316.3	318.0	306.5	294.9	283.3	271.7	253.7
120°	332.0	333.7	335.6	337.4	339.2	341.1	342.3	343.6	344.8	346.1	339.7
122.5°	353.1	355.0	357.0	359.0	361.1	363.1	363.8	364.5	365.3	366.0	365.1
125°	383.7	385.4	387.4	389.3	391.3	393.2	394.0	394.7	395.4	396.1	396.6
127.5°	413.0	414.6	416.0	417.5	418.9	420.4	421.4	422.5	423.6	424.6	425.2
130°	431.9	433.4	434.5	435.6	436.8	437.9	439.1	440.1	441.3	442.5	443.0
132.5°	449.6	450.8	452.0	453.2	454.2	455.4	456.4	457.4	458.3	459.3	459.7
135°	474.7	476.1	477.0	478.0	478.8	479.7	480.8	481.9	482.9	483.9	484.4
137.5°	497.2	498.4	499.4	500.5	501.5	502.6	503.6	504.6	505.6	506.7	506.9
140°	511.9	512.9	514.1	515.2	516.3	517.5	518.4	519.3	520.2	521.2	521.4
142.5°	525.0	526.0	527.4	528.6	529.9	531.3	532.1	533.0	533.8	534.7	534.8
145°	542.7	543.5	545.3	547.0	548.8	550.5	551.3	552.0	552.7	553.4	553.5
147.5°	559.8	560.5	562.2	564.0	565.7	567.5	568.0	568.6	569.1	569.6	569.6
150°	570.4	570.9	572.6	574.2	575.9	577.5	578.1	578.7	579.3	580.0	580.1
152.5°	580.1	580.5	582.1	583.7	585.2	586.8	587.5	588.1	588.7	589.3	589.2
155°	594.2	594.4	595.7	596.9	598.2	599.4	600.0	600.7	601.3	601.9	601.7
157.5°	606.3	606.4	607.2	608.1	608.9	609.8	610.5	611.2	611.9	612.6	612.6
160°	613.7	613.7	614.3	614.9	615.5	616.2	616.8	617.3	618.0	618.6	618.6
162.5°	619.6	619.6	620.1	620.6	621.2	621.7	622.4	623.1	623.8	624.6	624.5
165°	627.6	627.5	627.8	628.0	628.4	628.7	629.5	630.2	630.9	631.6	631.6
167.5°	633.6	633.4	633.6	634.0	634.3	634.5	635.3	636.0	636.8	637.5	637.4
170°	636.9	636.7	636.9	637.1	637.3	637.6	638.3	639.0	639.7	640.4	640.3
172.5°	639.2	638.9	639.2	639.4	639.5	639.8	640.5	641.2	641.9	642.7	642.6
175°	641.6	641.4	641.6	641.8	641.9	642.2	642.9	643.6	644.4	645.1	645.0
177.5°	642.7	642.4	642.5	642.6	642.7	642.7	643.4	643.9	644.5	645.1	645.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	4.0	3.9	3.9	3.8	3.9	3.9	4.0	3.9	3.9	4.1	4.0
90°	11.9	12.1	12.4	12.6	12.4	12.1	11.9	11.8	11.4	10.9	10.3
92.5°	12.2	12.3	12.5	12.6	12.5	12.3	12.2	12.0	11.9	11.6	11.3
95°	20.3	20.2	20.2	20.0	20.2	20.2	20.3	20.4	20.2	19.7	19.2
97.5°	26.3	26.5	26.6	26.8	26.6	26.5	26.3	26.2	25.9	25.5	25.1
100°	30.6	30.8	30.9	31.2	30.9	30.8	30.6	30.3	29.9	29.0	28.2
102.5°	32.5	32.8	33.1	33.4	33.1	32.8	32.5	32.3	31.6	30.5	29.4
105°	34.2	34.5	35.0	35.4	35.0	34.5	34.2	33.7	32.9	31.8	30.7
107.5°	35.1	35.6	35.9	36.4	35.9	35.6	35.1	34.8	35.1	36.3	37.5
110°	35.5	35.9	36.4	36.7	36.4	35.9	35.5	35.1	40.0	50.4	60.7



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	36.1	36.5	36.8	37.1	36.8	36.5	36.1	35.8	54.5	92.2	129.9
115°	60.5	53.1	45.6	38.2	45.6	53.1	60.5	67.9	95.6	143.5	191.4
117.5°	229.2	204.7	180.3	155.8	180.3	204.7	229.2	253.7	271.7	283.3	294.9
120°	325.7	311.8	297.8	283.8	297.8	311.8	325.7	339.7	346.1	344.8	343.6
122.5°	362.4	359.6	357.0	354.2	357.0	359.6	362.4	365.1	366.0	365.3	364.5
125°	397.0	397.3	397.6	397.9	397.6	397.3	397.0	396.6	396.1	395.4	394.7
127.5°	425.3	425.3	425.3	425.4	425.3	425.3	425.3	425.2	424.6	423.6	422.5
130°	442.8	442.7	442.6	442.6	442.6	442.7	442.8	443.0	442.5	441.3	440.1
132.5°	459.6	459.5	459.4	459.3	459.4	459.5	459.6	459.7	459.3	458.3	457.4
135°	484.1	483.9	483.8	483.5	483.8	483.9	484.1	484.4	483.9	482.9	481.9
137.5°	506.6	506.2	506.0	505.6	506.0	506.2	506.6	506.9	506.7	505.6	504.6
140°	520.8	520.4	519.9	519.3	519.9	520.4	520.8	521.4	521.2	520.2	519.3
142.5°	534.3	533.8	533.2	532.7	533.2	533.8	534.3	534.8	534.7	533.8	533.0
145°	553.0	552.5	552.0	551.4	552.0	552.5	553.0	553.5	553.4	552.7	552.0
147.5°	569.3	568.8	568.4	567.9	568.4	568.8	569.3	569.6	569.6	569.1	568.6
150°	579.5	579.0	578.5	578.0	578.5	579.0	579.5	580.1	580.0	579.3	578.7
152.5°	588.6	587.9	587.2	586.6	587.2	587.9	588.6	589.2	589.3	588.7	588.1
155°	600.9	600.1	599.3	598.4	599.3	600.1	600.9	601.7	601.9	601.3	600.7
157.5°	611.7	610.9	610.1	609.3	610.1	610.9	611.7	612.6	612.6	611.9	611.2
160°	617.9	617.2	616.4	615.6	616.4	617.2	617.9	618.6	618.6	618.0	617.3
162.5°	623.6	622.7	621.8	620.9	621.8	622.7	623.6	624.5	624.6	623.8	623.1
165°	630.9	630.2	629.5	628.7	629.5	630.2	630.9	631.6	631.6	630.9	630.2
167.5°	636.4	635.5	634.5	633.6	634.5	635.5	636.4	637.4	637.5	636.8	636.0
170°	639.4	638.5	637.6	636.6	637.6	638.5	639.4	640.3	640.4	639.7	639.0
172.5°	641.7	640.7	639.8	638.8	639.8	640.7	641.7	642.6	642.7	641.9	641.2
175°	643.9	642.8	641.9	640.8	641.9	642.8	643.9	645.0	645.1	644.4	643.6
177.5°	644.3	643.5	642.7	642.0	642.7	643.5	644.3	645.0	645.1	644.5	643.9
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	3.9	3.9	3.9	3.9	3.8	3.8	3.7	3.7	3.7	3.7	3.7
90°	9.8	9.3	8.5	7.7	6.9	6.0	5.0	3.8	2.8	1.6	0.4
92.5°	11.1	10.8	10.3	10.0	9.5	9.2	9.0	9.1	9.2	9.3	9.4
95°	18.6	18.2	17.4	16.7	16.0	15.2	16.6	20.0	23.5	26.8	30.2
97.5°	24.7	24.3	22.6	21.0	19.3	17.6	21.6	31.2	40.8	50.4	60.0
100°	27.4	26.5	24.8	23.0	21.2	19.5	25.7	39.9	54.0	68.2	82.4
102.5°	28.4	27.3	42.0	56.7	71.4	86.1	95.0	97.9	100.9	104.0	106.9
105°	29.5	28.4	56.6	84.9	113.1	141.3	153.9	150.8	147.7	144.5	141.4
107.5°	38.6	39.8	73.6	107.5	141.3	175.1	190.8	188.3	185.8	183.3	180.8
110°	71.1	81.4	111.3	141.2	171.1	201.0	214.8	212.7	210.5	208.3	206.2



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	167.6	205.5	212.8	220.2	227.6	235.0	237.6	235.8	233.8	231.9	230.0
115°	239.2	287.1	284.5	282.0	279.4	276.8	274.6	272.9	271.1	269.3	267.6
117.5°	306.5	318.0	316.3	314.5	312.7	310.9	309.1	307.1	305.1	303.2	301.2
120°	342.3	341.1	339.2	337.4	335.6	333.7	332.0	330.4	328.9	327.3	325.7
122.5°	363.8	363.1	361.1	359.0	357.0	355.0	353.1	351.5	349.9	348.2	346.6
125°	394.0	393.2	391.3	389.3	387.4	385.4	383.7	382.4	381.0	379.7	378.4
127.5°	421.4	420.4	418.9	417.5	416.0	414.6	413.0	411.5	410.1	408.6	407.1
130°	439.1	437.9	436.8	435.6	434.5	433.4	431.9	430.3	428.6	427.0	425.3
132.5°	456.4	455.4	454.2	453.2	452.0	450.8	449.6	448.2	446.7	445.3	444.0
135°	480.8	479.7	478.8	478.0	477.0	476.1	474.7	473.1	471.4	469.8	468.1
137.5°	503.6	502.6	501.5	500.5	499.4	498.4	497.2	496.1	494.9	493.7	492.7
140°	518.4	517.5	516.3	515.2	514.1	512.9	511.9	511.1	510.3	509.4	508.6
142.5°	532.1	531.3	529.9	528.6	527.4	526.0	525.0	524.2	523.5	522.8	522.0
145°	551.3	550.5	548.8	547.0	545.3	543.5	542.7	542.8	542.9	543.0	543.1
147.5°	568.0	567.5	565.7	564.0	562.2	560.5	559.8	560.3	560.6	561.0	561.4
150°	578.1	577.5	575.9	574.2	572.6	570.9	570.4	571.1	571.9	572.6	573.3
152.5°	587.5	586.8	585.2	583.7	582.1	580.5	580.1	580.9	581.8	582.6	583.4
155°	600.0	599.4	598.2	596.9	595.7	594.4	594.2	595.2	596.1	597.1	598.0
157.5°	610.5	609.8	608.9	608.1	607.2	606.4	606.3	607.1	607.9	608.7	609.4
160°	616.8	616.2	615.5	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2
162.5°	622.4	621.7	621.2	620.6	620.1	619.6	619.6	620.2	620.8	621.4	622.1
165°	629.5	628.7	628.4	628.0	627.8	627.5	627.6	628.2	628.8	629.5	630.1
167.5°	635.3	634.5	634.3	634.0	633.6	633.4	633.6	634.2	634.8	635.4	636.1
170°	638.3	637.6	637.3	637.1	636.9	636.7	636.9	637.6	638.2	638.8	639.4
172.5°	640.5	639.8	639.5	639.4	639.2	638.9	639.2	639.8	640.4	641.1	641.7
175°	642.9	642.2	641.9	641.8	641.6	641.4	641.6	642.4	643.1	643.8	644.5
177.5°	643.4	642.7	642.7	642.6	642.5	642.4	642.7	643.3	643.8	644.4	645.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	4.4	5.3	5.4	6.2	6.1	6.2	6.4	6.4	6.4	6.3	6.2
90°	1.6	2.8	3.8	5.0	6.0	6.9	7.7	8.5	9.3	9.8	10.3
92.5°	9.3	9.2	9.1	9.0	9.2	9.5	10.0	10.3	10.8	11.1	11.3
95°	26.8	23.5	20.0	16.6	15.2	16.0	16.7	17.4	18.2	18.6	19.2
97.5°	50.4	40.8	31.2	21.6	17.6	19.3	21.0	22.6	24.3	24.7	25.1
100°	68.2	54.0	39.9	25.7	19.5	21.2	23.0	24.8	26.5	27.4	28.2
102.5°	104.0	100.9	97.9	95.0	86.1	71.4	56.7	42.0	27.3	28.4	29.4
105°	144.5	147.7	150.8	153.9	141.3	113.1	84.9	56.6	28.4	29.5	30.7
107.5°	183.3	185.8	188.3	190.8	175.1	141.3	107.5	73.6	39.8	38.6	37.5
110°	208.3	210.5	212.7	214.8	201.0	171.1	141.2	111.3	81.4	71.1	60.7



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	231.9	233.8	235.8	237.6	235.0	227.6	220.2	212.8	205.5	167.6	129.9
115°	269.3	271.1	272.9	274.6	276.8	279.4	282.0	284.5	287.1	239.2	191.4
117.5°	303.2	305.1	307.1	309.1	310.9	312.7	314.5	316.3	318.0	306.5	294.9
120°	327.3	328.9	330.4	332.0	333.7	335.6	337.4	339.2	341.1	342.3	343.6
122.5°	348.2	349.9	351.5	353.1	355.0	357.0	359.0	361.1	363.1	363.8	364.5
125°	379.7	381.0	382.4	383.7	385.4	387.4	389.3	391.3	393.2	394.0	394.7
127.5°	408.6	410.1	411.5	413.0	414.6	416.0	417.5	418.9	420.4	421.4	422.5
130°	427.0	428.6	430.3	431.9	433.4	434.5	435.6	436.8	437.9	439.1	440.1
132.5°	445.3	446.7	448.2	449.6	450.8	452.0	453.2	454.2	455.4	456.4	457.4
135°	469.8	471.4	473.1	474.7	476.1	477.0	478.0	478.8	479.7	480.8	481.9
137.5°	493.7	494.9	496.1	497.2	498.4	499.4	500.5	501.5	502.6	503.6	504.6
140°	509.4	510.3	511.1	511.9	512.9	514.1	515.2	516.3	517.5	518.4	519.3
142.5°	522.8	523.5	524.2	525.0	526.0	527.4	528.6	529.9	531.3	532.1	533.0
145°	543.0	542.9	542.8	542.7	543.5	545.3	547.0	548.8	550.5	551.3	552.0
147.5°	561.0	560.6	560.3	559.8	560.5	562.2	564.0	565.7	567.5	568.0	568.6
150°	572.6	571.9	571.1	570.4	570.9	572.6	574.2	575.9	577.5	578.1	578.7
152.5°	582.6	581.8	580.9	580.1	580.5	582.1	583.7	585.2	586.8	587.5	588.1
155°	597.1	596.1	595.2	594.2	594.4	595.7	596.9	598.2	599.4	600.0	600.7
157.5°	608.7	607.9	607.1	606.3	606.4	607.2	608.1	608.9	609.8	610.5	611.2
160°	615.5	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2	616.8	617.3
162.5°	621.4	620.8	620.2	619.6	619.6	620.1	620.6	621.2	621.7	622.4	623.1
165°	629.5	628.8	628.2	627.6	627.5	627.8	628.0	628.4	628.7	629.5	630.2
167.5°	635.4	634.8	634.2	633.6	633.4	633.6	634.0	634.3	634.5	635.3	636.0
170°	638.8	638.2	637.6	636.9	636.7	636.9	637.1	637.3	637.6	638.3	639.0
172.5°	641.1	640.4	639.8	639.2	638.9	639.2	639.4	639.5	639.8	640.5	641.2
175°	643.8	643.1	642.4	641.6	641.4	641.6	641.8	641.9	642.2	642.9	643.6
177.5°	644.4	643.8	643.3	642.7	642.4	642.5	642.6	642.7	642.7	643.4	643.9
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	6.5	6.7	6.6	6.6	6.8	6.7	6.7
90°	10.9	11.4	11.8	11.9	12.1	12.4	12.6
92.5°	11.6	11.9	12.0	12.2	12.3	12.5	12.6
95°	19.7	20.2	20.4	20.3	20.2	20.2	20.0
97.5°	25.5	25.9	26.2	26.3	26.5	26.6	26.8
100°	29.0	29.9	30.3	30.6	30.8	30.9	31.2
102.5°	30.5	31.6	32.3	32.5	32.8	33.1	33.4
105°	31.8	32.9	33.7	34.2	34.5	35.0	35.4
107.5°	36.3	35.1	34.8	35.1	35.6	35.9	36.4
110°	50.4	40.0	35.1	35.5	35.9	36.4	36.7



TEST NUMBER: P331249-940

CATALOG NUMBER: S122DIP-S290D530U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	92.2	54.5	35.8	36.1	36.5	36.8	37.1
115°	143.5	95.6	67.9	60.5	53.1	45.6	38.2
117.5°	283.3	271.7	253.7	229.2	204.7	180.3	155.8
120°	344.8	346.1	339.7	325.7	311.8	297.8	283.8
122.5°	365.3	366.0	365.1	362.4	359.6	357.0	354.2
125°	395.4	396.1	396.6	397.0	397.3	397.6	397.9
127.5°	423.6	424.6	425.2	425.3	425.3	425.3	425.4
130°	441.3	442.5	443.0	442.8	442.7	442.6	442.6
132.5°	458.3	459.3	459.7	459.6	459.5	459.4	459.3
135°	482.9	483.9	484.4	484.1	483.9	483.8	483.5
137.5°	505.6	506.7	506.9	506.6	506.2	506.0	505.6
140°	520.2	521.2	521.4	520.8	520.4	519.9	519.3
142.5°	533.8	534.7	534.8	534.3	533.8	533.2	532.7
145°	552.7	553.4	553.5	553.0	552.5	552.0	551.4
147.5°	569.1	569.6	569.6	569.3	568.8	568.4	567.9
150°	579.3	580.0	580.1	579.5	579.0	578.5	578.0
152.5°	588.7	589.3	589.2	588.6	587.9	587.2	586.6
155°	601.3	601.9	601.7	600.9	600.1	599.3	598.4
157.5°	611.9	612.6	612.6	611.7	610.9	610.1	609.3
160°	618.0	618.6	618.6	617.9	617.2	616.4	615.6
162.5°	623.8	624.6	624.5	623.6	622.7	621.8	620.9
165°	630.9	631.6	631.6	630.9	630.2	629.5	628.7
167.5°	636.8	637.5	637.4	636.4	635.5	634.5	633.6
170°	639.7	640.4	640.3	639.4	638.5	637.6	636.6
172.5°	641.9	642.7	642.6	641.7	640.7	639.8	638.8
175°	644.4	645.1	645.0	643.9	642.8	641.9	640.8
177.5°	644.5	645.1	645.0	644.3	643.5	642.7	642.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1

(END OF REPORT)