

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331269-940

Luminaire Tested: **S122DIP-S290D925U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331269-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D925U940-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4387.3 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	27	26	25	20
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22	17
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15	11
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10
8	51	39	32	27	46	36	29	25	28	24	20	22	19	16	15	13	12	9
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	1.1
10°-20°	145.9	3.3
20°-30°	211.8	4.8
30°-40°	223.5	5.1
40°-50°	197.9	4.5
50°-60°	157.9	3.6
60°-70°	107.3	2.4
70°-80°	55.0	1.3
80°-90°	17.4	0.4
90°-100°	185.0	4.2
100°-110°	627.9	14.3
110°-120°	667.1	15.2
120°-130°	549.1	12.5
130°-140°	441.0	10.1
140°-150°	333.2	7.6
150°-160°	234.2	5.3
160°-170°	137.9	3.1
170°-180°	44.9	1.0
0°-30°	407.9	9.3
0°-40°	631.4	14.4
0°-60°	987.2	22.5
0°-90°	1167.0	26.6
90°-120°	1480.0	33.7
90°-150°	2803.4	63.9
90°-180°	3220.0	73.4
0°-180°	4387.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	13
90°	29	1	29	1	29	16
95°	102	31	102	31	102	132
105°	1003	109	1003	109	1003	970
115°	1320	191	1320	191	1320	1292
125°	1071	267	1071	267	1071	967
135°	887	313	887	313	887	689
145°	708	358	708	358	708	450
155°	595	407	595	407	595	278
165°	522	443	522	443	522	149
175°	471	462	471	462	471	46
180°	463	463	463	463	463	



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	10.1	10.1	10.3	10.1	10.1	10.1	9.7	9.9	10.3	10.6	10.6
90°	29.3	29.3	29.3	29.3	29.3	28.4	26.7	28.4	29.3	30.2	29.3
92.5°	49.3	50.7	50.0	52.9	53.6	59.1	66.6	77.6	97.7	115.7	114.0
95°	101.5	100.6	103.3	110.4	121.9	141.5	178.9	233.2	305.2	348.8	308.8
97.5°	199.7	207.1	220.2	242.1	284.6	348.8	445.1	544.1	624.7	595.6	448.5
100°	318.6	334.7	360.4	398.7	472.6	580.2	702.1	812.5	831.3	703.0	484.1
102.5°	560.7	582.4	614.6	679.9	760.2	874.3	963.5	988.4	908.1	706.6	470.6
105°	1003.0	1015.4	1053.7	1108.8	1164.0	1193.5	1181.9	1081.3	896.2	659.4	444.1
107.5°	1281.2	1297.7	1305.4	1308.4	1301.5	1258.4	1165.8	1014.4	818.1	608.9	430.9
110°	1365.2	1366.1	1358.1	1341.1	1302.9	1229.9	1116.0	956.7	768.9	584.7	428.1



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1363.8	1359.0	1343.8	1315.5	1262.3	1178.7	1056.9	904.0	734.8	569.0	428.7
115°	1319.8	1311.8	1288.6	1247.7	1184.5	1092.9	976.2	839.2	692.4	551.8	432.5
117.5°	1241.3	1234.6	1210.1	1166.9	1102.5	1016.5	910.8	790.4	665.7	543.4	438.9
120°	1190.8	1181.9	1156.0	1114.2	1052.0	970.9	876.6	766.2	651.5	538.4	443.2
122.5°	1138.1	1130.6	1107.6	1066.5	1010.7	937.5	848.1	747.0	639.4	535.6	448.2
125°	1070.6	1063.5	1041.3	1007.5	955.8	889.0	810.7	719.1	622.1	530.4	455.7
127.5°	1011.6	1005.8	986.6	954.9	909.9	848.3	774.5	691.5	606.1	527.4	463.3
130°	978.0	970.9	953.1	922.9	879.3	820.6	750.2	673.7	595.4	525.9	469.0
132.5°	943.2	936.7	920.4	890.1	847.2	792.0	727.5	656.6	586.8	525.2	474.7
135°	887.3	883.7	867.7	838.3	800.0	750.2	691.5	632.8	574.9	524.1	481.4
137.5°	832.5	827.2	813.1	787.8	752.9	709.4	662.8	613.7	566.5	524.0	487.5
140°	794.7	789.4	776.1	752.9	724.4	685.3	644.4	601.6	561.6	523.3	490.4
142.5°	757.0	755.9	744.0	723.0	696.0	663.2	627.9	591.7	556.6	523.3	492.5
145°	708.4	705.7	696.9	681.7	660.3	634.5	607.0	577.6	550.0	521.5	494.8
147.5°	667.6	666.0	660.0	647.9	630.3	611.4	589.9	566.7	543.2	518.4	495.5
150°	643.5	642.6	637.2	626.5	613.1	597.2	578.5	558.9	537.5	516.2	494.8
152.5°	622.8	622.6	618.7	609.4	599.0	585.1	569.2	551.1	532.5	512.6	493.4
155°	595.4	597.2	593.6	587.4	577.6	567.8	554.5	540.2	523.3	506.4	491.2
157.5°	572.0	572.0	570.4	565.3	558.4	550.7	539.5	527.5	514.6	500.0	487.1
160°	557.1	557.1	556.2	551.8	545.5	539.3	529.5	519.7	508.2	495.7	485.0
162.5°	542.9	543.6	542.7	539.7	533.4	528.6	520.2	511.9	502.5	492.1	482.9
165°	522.4	523.3	523.3	519.7	516.2	512.6	506.4	500.2	493.0	485.0	478.8
167.5°	503.5	504.6	504.8	502.8	501.2	498.0	493.7	488.9	483.8	478.8	474.7
170°	492.1	493.9	494.8	492.1	491.2	489.5	485.9	483.2	478.8	475.2	472.6
172.5°	482.9	483.9	484.8	483.6	482.7	481.6	478.8	476.8	473.9	471.0	469.8
175°	470.8	472.6	473.5	472.6	472.6	471.7	470.8	469.9	467.3	466.4	465.5
177.5°	463.5	464.9	465.7	465.7	465.7	465.7	464.9	464.9	463.5	462.8	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	9.6	8.4	7.5	7.3	6.5	6.2	4.7	3.7	4.1	4.6	4.7
90°	24.0	17.8	13.4	10.7	8.9	7.1	3.6	0.9	3.6	7.1	8.9
92.5°	88.8	60.5	40.4	32.0	25.9	22.1	15.7	10.9	15.7	22.1	25.9
95°	205.5	128.1	87.2	65.9	51.6	43.6	34.7	31.1	34.7	43.6	51.6
97.5°	277.0	169.1	117.6	93.5	77.0	65.0	55.6	50.7	55.6	65.0	77.0
100°	291.9	183.3	136.2	111.3	93.5	79.2	71.2	68.5	71.2	79.2	93.5
102.5°	292.7	196.2	152.6	127.6	109.1	94.9	86.9	84.9	86.9	94.9	109.1
105°	297.2	218.0	176.2	151.3	131.7	118.3	112.2	108.6	112.2	118.3	131.7
107.5°	309.5	240.5	199.9	174.8	155.4	143.1	137.1	134.2	137.1	143.1	155.4
110°	319.5	255.4	216.2	190.5	171.7	160.2	154.9	151.3	154.9	160.2	171.7



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	330.2	269.7	231.9	205.4	187.4	176.6	170.5	166.9	170.5	176.6	187.4
115°	346.2	291.9	253.6	229.6	211.8	201.2	195.8	191.4	195.8	201.2	211.8
117.5°	363.3	312.4	277.0	252.0	235.0	225.5	220.2	216.6	220.2	225.5	235.0
120°	374.7	326.6	291.9	267.0	249.1	241.2	235.9	232.3	235.9	241.2	249.1
122.5°	384.6	340.1	307.6	282.0	264.1	255.4	250.0	247.3	250.0	255.4	264.1
125°	400.5	360.4	328.4	303.4	285.7	275.0	269.7	267.0	269.7	275.0	285.7
127.5°	415.3	379.3	348.1	322.5	305.4	293.6	286.2	282.7	286.2	293.6	305.4
130°	424.5	390.7	359.5	334.7	316.8	304.3	295.4	291.9	295.4	304.3	316.8
132.5°	433.7	400.6	371.0	346.0	327.5	314.3	304.7	300.4	304.7	314.3	327.5
135°	445.9	414.7	386.2	361.3	340.8	327.5	316.8	313.3	316.8	327.5	340.8
137.5°	455.1	426.1	398.0	374.9	354.5	340.3	329.7	325.4	329.7	340.3	354.5
140°	460.1	432.5	405.8	382.7	363.1	348.8	338.2	334.7	338.2	348.8	363.1
142.5°	464.4	437.5	411.5	389.8	371.0	356.7	346.7	343.8	346.7	356.7	371.0
145°	469.9	445.0	421.0	401.4	383.6	370.2	361.3	357.8	361.3	370.2	383.6
147.5°	473.0	451.0	428.5	411.0	396.2	383.9	375.4	372.7	375.4	383.9	396.2
150°	474.3	453.9	433.4	417.4	404.0	392.4	385.3	382.7	385.3	392.4	404.0
152.5°	475.0	456.7	438.4	423.8	411.2	401.0	393.9	392.6	393.9	401.0	411.2
155°	476.1	461.0	445.9	432.5	422.8	413.0	407.6	406.7	407.6	413.0	422.8
157.5°	476.1	464.0	451.2	440.0	432.1	423.7	419.4	418.5	419.4	423.7	432.1
160°	476.1	465.5	454.8	445.0	437.8	430.7	427.2	426.3	427.2	430.7	437.8
162.5°	475.4	466.2	456.9	449.2	442.8	437.1	433.5	434.1	433.5	437.1	442.8
165°	473.5	467.3	459.2	453.9	449.4	444.1	442.3	443.2	442.3	444.1	449.4
167.5°	472.3	467.1	461.2	457.8	454.6	451.2	449.6	450.7	449.6	451.2	454.6
170°	470.8	466.4	461.9	459.2	457.4	454.8	453.9	455.7	453.9	454.8	457.4
172.5°	468.7	465.7	462.6	460.7	459.6	456.9	457.4	458.5	457.4	456.9	459.6
175°	466.4	464.6	462.8	461.9	461.9	460.1	461.0	461.9	461.0	460.1	461.9
177.5°	464.9	463.5	462.8	462.8	462.8	461.4	462.1	463.5	462.1	461.4	462.8
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	4.9	5.3	6.0	7.2	8.1	8.1	7.8	7.7	7.3	7.3	7.5
90°	10.7	13.4	17.8	24.0	29.3	30.2	29.3	28.4	26.7	28.4	29.3
92.5°	32.0	40.4	60.5	88.8	114.0	115.7	97.7	77.6	66.6	59.1	53.6
95°	65.9	87.2	128.1	205.5	308.8	348.8	305.2	233.2	178.9	141.5	121.9
97.5°	93.5	117.6	169.1	277.0	448.5	595.6	624.7	544.1	445.1	348.8	284.6
100°	111.3	136.2	183.3	291.9	484.1	703.0	831.3	812.5	702.1	580.2	472.6
102.5°	127.6	152.6	196.2	292.7	470.6	706.6	908.1	988.4	963.5	874.3	760.2
105°	151.3	176.2	218.0	297.2	444.1	659.4	896.2	1081.3	1181.9	1193.5	1164.0
107.5°	174.8	199.9	240.5	309.5	430.9	608.9	818.1	1014.4	1165.8	1258.4	1301.5
110°	190.5	216.2	255.4	319.5	428.1	584.7	768.9	956.7	1116.0	1229.9	1302.9



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	205.4	231.9	269.7	330.2	428.7	569.0	734.8	904.0	1056.9	1178.7	1262.3
115°	229.6	253.6	291.9	346.2	432.5	551.8	692.4	839.2	976.2	1092.9	1184.5
117.5°	252.0	277.0	312.4	363.3	438.9	543.4	665.7	790.4	910.8	1016.5	1102.5
120°	267.0	291.9	326.6	374.7	443.2	538.4	651.5	766.2	876.6	970.9	1052.0
122.5°	282.0	307.6	340.1	384.6	448.2	535.6	639.4	747.0	848.1	937.5	1010.7
125°	303.4	328.4	360.4	400.5	455.7	530.4	622.1	719.1	810.7	889.0	955.8
127.5°	322.5	348.1	379.3	415.3	463.3	527.4	606.1	691.5	774.5	848.3	909.9
130°	334.7	359.5	390.7	424.5	469.0	525.9	595.4	673.7	750.2	820.6	879.3
132.5°	346.0	371.0	400.6	433.7	474.7	525.2	586.8	656.6	727.5	792.0	847.2
135°	361.3	386.2	414.7	445.9	481.4	524.1	574.9	632.8	691.5	750.2	800.0
137.5°	374.9	398.0	426.1	455.1	487.5	524.0	566.5	613.7	662.8	709.4	752.9
140°	382.7	405.8	432.5	460.1	490.4	523.3	561.6	601.6	644.4	685.3	724.4
142.5°	389.8	411.5	437.5	464.4	492.5	523.3	556.6	591.7	627.9	663.2	696.0
145°	401.4	421.0	445.0	469.9	494.8	521.5	550.0	577.6	607.0	634.5	660.3
147.5°	411.0	428.5	451.0	473.0	495.5	518.4	543.2	566.7	589.9	611.4	630.3
150°	417.4	433.4	453.9	474.3	494.8	516.2	537.5	558.9	578.5	597.2	613.1
152.5°	423.8	438.4	456.7	475.0	493.4	512.6	532.5	551.1	569.2	585.1	599.0
155°	432.5	445.9	461.0	476.1	491.2	506.4	523.3	540.2	554.5	567.8	577.6
157.5°	440.0	451.2	464.0	476.1	487.1	500.0	514.6	527.5	539.5	550.7	558.4
160°	445.0	454.8	465.5	476.1	485.0	495.7	508.2	519.7	529.5	539.3	545.5
162.5°	449.2	456.9	466.2	475.4	482.9	492.1	502.5	511.9	520.2	528.6	533.4
165°	453.9	459.2	467.3	473.5	478.8	485.0	493.0	500.2	506.4	512.6	516.2
167.5°	457.8	461.2	467.1	472.3	474.7	478.8	483.8	488.9	493.7	498.0	501.2
170°	459.2	461.9	466.4	470.8	472.6	475.2	478.8	483.2	485.9	489.5	491.2
172.5°	460.7	462.6	465.7	468.7	469.8	471.0	473.9	476.8	478.8	481.6	482.7
175°	461.9	462.8	464.6	466.4	465.5	466.4	467.3	469.9	470.8	471.7	472.6
177.5°	462.8	462.8	463.5	464.9	463.5	462.8	463.5	464.9	464.9	465.7	465.7
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	7.5	7.3	7.3	7.1	7.3	7.3	7.5	7.5	7.3	7.3	7.7
90°	29.3	29.3	29.3	29.3	29.3	29.3	29.3	29.3	28.4	26.7	28.4
92.5°	52.9	50.0	50.7	49.3	50.7	50.0	52.9	53.6	59.1	66.6	77.6
95°	110.4	103.3	100.6	101.5	100.6	103.3	110.4	121.9	141.5	178.9	233.2
97.5°	242.1	220.2	207.1	199.7	207.1	220.2	242.1	284.6	348.8	445.1	544.1
100°	398.7	360.4	334.7	318.6	334.7	360.4	398.7	472.6	580.2	702.1	812.5
102.5°	679.9	614.6	582.4	560.7	582.4	614.6	679.9	760.2	874.3	963.5	988.4
105°	1108.8	1053.7	1015.4	1003.0	1015.4	1053.7	1108.8	1164.0	1193.5	1181.9	1081.3
107.5°	1308.4	1305.4	1297.7	1281.2	1297.7	1305.4	1308.4	1301.5	1258.4	1165.8	1014.4
110°	1341.1	1358.1	1366.1	1365.2	1366.1	1358.1	1341.1	1302.9	1229.9	1116.0	956.7



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1315.5	1343.8	1359.0	1363.8	1359.0	1343.8	1315.5	1262.3	1178.7	1056.9	904.0
115°	1247.7	1288.6	1311.8	1319.8	1311.8	1288.6	1247.7	1184.5	1092.9	976.2	839.2
117.5°	1166.9	1210.1	1234.6	1241.3	1234.6	1210.1	1166.9	1102.5	1016.5	910.8	790.4
120°	1114.2	1156.0	1181.9	1190.8	1181.9	1156.0	1114.2	1052.0	970.9	876.6	766.2
122.5°	1066.5	1107.6	1130.6	1138.1	1130.6	1107.6	1066.5	1010.7	937.5	848.1	747.0
125°	1007.5	1041.3	1063.5	1070.6	1063.5	1041.3	1007.5	955.8	889.0	810.7	719.1
127.5°	954.9	986.6	1005.8	1011.6	1005.8	986.6	954.9	909.9	848.3	774.5	691.5
130°	922.9	953.1	970.9	978.0	970.9	953.1	922.9	879.3	820.6	750.2	673.7
132.5°	890.1	920.4	936.7	943.2	936.7	920.4	890.1	847.2	792.0	727.5	656.6
135°	838.3	867.7	883.7	887.3	883.7	867.7	838.3	800.0	750.2	691.5	632.8
137.5°	787.8	813.1	827.2	832.5	827.2	813.1	787.8	752.9	709.4	662.8	613.7
140°	752.9	776.1	789.4	794.7	789.4	776.1	752.9	724.4	685.3	644.4	601.6
142.5°	723.0	744.0	755.9	757.0	755.9	744.0	723.0	696.0	663.2	627.9	591.7
145°	681.7	696.9	705.7	708.4	705.7	696.9	681.7	660.3	634.5	607.0	577.6
147.5°	647.9	660.0	666.0	667.6	666.0	660.0	647.9	630.3	611.4	589.9	566.7
150°	626.5	637.2	642.6	643.5	642.6	637.2	626.5	613.1	597.2	578.5	558.9
152.5°	609.4	618.7	622.6	622.8	622.6	618.7	609.4	599.0	585.1	569.2	551.1
155°	587.4	593.6	597.2	595.4	597.2	593.6	587.4	577.6	567.8	554.5	540.2
157.5°	565.3	570.4	572.0	572.0	572.0	570.4	565.3	558.4	550.7	539.5	527.5
160°	551.8	556.2	557.1	557.1	557.1	556.2	551.8	545.5	539.3	529.5	519.7
162.5°	539.7	542.7	543.6	542.9	543.6	542.7	539.7	533.4	528.6	520.2	511.9
165°	519.7	523.3	523.3	522.4	523.3	523.3	519.7	516.2	512.6	506.4	500.2
167.5°	502.8	504.8	504.6	503.5	504.6	504.8	502.8	501.2	498.0	493.7	488.9
170°	492.1	494.8	493.9	492.1	493.9	494.8	492.1	491.2	489.5	485.9	483.2
172.5°	483.6	484.8	483.9	482.9	483.9	484.8	483.6	482.7	481.6	478.8	476.8
175°	472.6	473.5	472.6	470.8	472.6	473.5	472.6	472.6	471.7	470.8	469.9
177.5°	465.7	465.7	464.9	463.5	464.9	465.7	465.7	465.7	465.7	464.9	464.9
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	7.8	8.1	8.1	7.2	6.0	5.3	4.9	4.7	4.6	4.1	3.7
90°	29.3	30.2	29.3	24.0	17.8	13.4	10.7	8.9	7.1	3.6	0.9
92.5°	97.7	115.7	114.0	88.8	60.5	40.4	32.0	25.9	22.1	15.7	10.9
95°	305.2	348.8	308.8	205.5	128.1	87.2	65.9	51.6	43.6	34.7	31.1
97.5°	624.7	595.6	448.5	277.0	169.1	117.6	93.5	77.0	65.0	55.6	50.7
100°	831.3	703.0	484.1	291.9	183.3	136.2	111.3	93.5	79.2	71.2	68.5
102.5°	908.1	706.6	470.6	292.7	196.2	152.6	127.6	109.1	94.9	86.9	84.9
105°	896.2	659.4	444.1	297.2	218.0	176.2	151.3	131.7	118.3	112.2	108.6
107.5°	818.1	608.9	430.9	309.5	240.5	199.9	174.8	155.4	143.1	137.1	134.2
110°	768.9	584.7	428.1	319.5	255.4	216.2	190.5	171.7	160.2	154.9	151.3



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	734.8	569.0	428.7	330.2	269.7	231.9	205.4	187.4	176.6	170.5	166.9
115°	692.4	551.8	432.5	346.2	291.9	253.6	229.6	211.8	201.2	195.8	191.4
117.5°	665.7	543.4	438.9	363.3	312.4	277.0	252.0	235.0	225.5	220.2	216.6
120°	651.5	538.4	443.2	374.7	326.6	291.9	267.0	249.1	241.2	235.9	232.3
122.5°	639.4	535.6	448.2	384.6	340.1	307.6	282.0	264.1	255.4	250.0	247.3
125°	622.1	530.4	455.7	400.5	360.4	328.4	303.4	285.7	275.0	269.7	267.0
127.5°	606.1	527.4	463.3	415.3	379.3	348.1	322.5	305.4	293.6	286.2	282.7
130°	595.4	525.9	469.0	424.5	390.7	359.5	334.7	316.8	304.3	295.4	291.9
132.5°	586.8	525.2	474.7	433.7	400.6	371.0	346.0	327.5	314.3	304.7	300.4
135°	574.9	524.1	481.4	445.9	414.7	386.2	361.3	340.8	327.5	316.8	313.3
137.5°	566.5	524.0	487.5	455.1	426.1	398.0	374.9	354.5	340.3	329.7	325.4
140°	561.6	523.3	490.4	460.1	432.5	405.8	382.7	363.1	348.8	338.2	334.7
142.5°	556.6	523.3	492.5	464.4	437.5	411.5	389.8	371.0	356.7	346.7	343.8
145°	550.0	521.5	494.8	469.9	445.0	421.0	401.4	383.6	370.2	361.3	357.8
147.5°	543.2	518.4	495.5	473.0	451.0	428.5	411.0	396.2	383.9	375.4	372.7
150°	537.5	516.2	494.8	474.3	453.9	433.4	417.4	404.0	392.4	385.3	382.7
152.5°	532.5	512.6	493.4	475.0	456.7	438.4	423.8	411.2	401.0	393.9	392.6
155°	523.3	506.4	491.2	476.1	461.0	445.9	432.5	422.8	413.0	407.6	406.7
157.5°	514.6	500.0	487.1	476.1	464.0	451.2	440.0	432.1	423.7	419.4	418.5
160°	508.2	495.7	485.0	476.1	465.5	454.8	445.0	437.8	430.7	427.2	426.3
162.5°	502.5	492.1	482.9	475.4	466.2	456.9	449.2	442.8	437.1	433.5	434.1
165°	493.0	485.0	478.8	473.5	467.3	459.2	453.9	449.4	444.1	442.3	443.2
167.5°	483.8	478.8	474.7	472.3	467.1	461.2	457.8	454.6	451.2	449.6	450.7
170°	478.8	475.2	472.6	470.8	466.4	461.9	459.2	457.4	454.8	453.9	455.7
172.5°	473.9	471.0	469.8	468.7	465.7	462.6	460.7	459.6	456.9	457.4	458.5
175°	467.3	466.4	465.5	466.4	464.6	462.8	461.9	461.9	460.1	461.0	461.9
177.5°	463.5	462.8	463.5	464.9	463.5	462.8	462.8	462.8	461.4	462.1	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	4.7	6.2	6.5	7.3	7.5	8.4	9.6	10.6	10.6	10.3	9.9
90°	3.6	7.1	8.9	10.7	13.4	17.8	24.0	29.3	30.2	29.3	28.4
92.5°	15.7	22.1	25.9	32.0	40.4	60.5	88.8	114.0	115.7	97.7	77.6
95°	34.7	43.6	51.6	65.9	87.2	128.1	205.5	308.8	348.8	305.2	233.2
97.5°	55.6	65.0	77.0	93.5	117.6	169.1	277.0	448.5	595.6	624.7	544.1
100°	71.2	79.2	93.5	111.3	136.2	183.3	291.9	484.1	703.0	831.3	812.5
102.5°	86.9	94.9	109.1	127.6	152.6	196.2	292.7	470.6	706.6	908.1	988.4
105°	112.2	118.3	131.7	151.3	176.2	218.0	297.2	444.1	659.4	896.2	1081.3
107.5°	137.1	143.1	155.4	174.8	199.9	240.5	309.5	430.9	608.9	818.1	1014.4
110°	154.9	160.2	171.7	190.5	216.2	255.4	319.5	428.1	584.7	768.9	956.7



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	170.5	176.6	187.4	205.4	231.9	269.7	330.2	428.7	569.0	734.8	904.0
115°	195.8	201.2	211.8	229.6	253.6	291.9	346.2	432.5	551.8	692.4	839.2
117.5°	220.2	225.5	235.0	252.0	277.0	312.4	363.3	438.9	543.4	665.7	790.4
120°	235.9	241.2	249.1	267.0	291.9	326.6	374.7	443.2	538.4	651.5	766.2
122.5°	250.0	255.4	264.1	282.0	307.6	340.1	384.6	448.2	535.6	639.4	747.0
125°	269.7	275.0	285.7	303.4	328.4	360.4	400.5	455.7	530.4	622.1	719.1
127.5°	286.2	293.6	305.4	322.5	348.1	379.3	415.3	463.3	527.4	606.1	691.5
130°	295.4	304.3	316.8	334.7	359.5	390.7	424.5	469.0	525.9	595.4	673.7
132.5°	304.7	314.3	327.5	346.0	371.0	400.6	433.7	474.7	525.2	586.8	656.6
135°	316.8	327.5	340.8	361.3	386.2	414.7	445.9	481.4	524.1	574.9	632.8
137.5°	329.7	340.3	354.5	374.9	398.0	426.1	455.1	487.5	524.0	566.5	613.7
140°	338.2	348.8	363.1	382.7	405.8	432.5	460.1	490.4	523.3	561.6	601.6
142.5°	346.7	356.7	371.0	389.8	411.5	437.5	464.4	492.5	523.3	556.6	591.7
145°	361.3	370.2	383.6	401.4	421.0	445.0	469.9	494.8	521.5	550.0	577.6
147.5°	375.4	383.9	396.2	411.0	428.5	451.0	473.0	495.5	518.4	543.2	566.7
150°	385.3	392.4	404.0	417.4	433.4	453.9	474.3	494.8	516.2	537.5	558.9
152.5°	393.9	401.0	411.2	423.8	438.4	456.7	475.0	493.4	512.6	532.5	551.1
155°	407.6	413.0	422.8	432.5	445.9	461.0	476.1	491.2	506.4	523.3	540.2
157.5°	419.4	423.7	432.1	440.0	451.2	464.0	476.1	487.1	500.0	514.6	527.5
160°	427.2	430.7	437.8	445.0	454.8	465.5	476.1	485.0	495.7	508.2	519.7
162.5°	433.5	437.1	442.8	449.2	456.9	466.2	475.4	482.9	492.1	502.5	511.9
165°	442.3	444.1	449.4	453.9	459.2	467.3	473.5	478.8	485.0	493.0	500.2
167.5°	449.6	451.2	454.6	457.8	461.2	467.1	472.3	474.7	478.8	483.8	488.9
170°	453.9	454.8	457.4	459.2	461.9	466.4	470.8	472.6	475.2	478.8	483.2
172.5°	457.4	456.9	459.6	460.7	462.6	465.7	468.7	469.8	471.0	473.9	476.8
175°	461.0	460.1	461.9	461.9	462.8	464.6	466.4	465.5	466.4	467.3	469.9
177.5°	462.1	461.4	462.8	462.8	462.8	463.5	464.9	463.5	462.8	463.5	464.9
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	9.7	10.1	10.1	10.1	10.3	10.1	10.1
90°	26.7	28.4	29.3	29.3	29.3	29.3	29.3
92.5°	66.6	59.1	53.6	52.9	50.0	50.7	49.3
95°	178.9	141.5	121.9	110.4	103.3	100.6	101.5
97.5°	445.1	348.8	284.6	242.1	220.2	207.1	199.7
100°	702.1	580.2	472.6	398.7	360.4	334.7	318.6
102.5°	963.5	874.3	760.2	679.9	614.6	582.4	560.7
105°	1181.9	1193.5	1164.0	1108.8	1053.7	1015.4	1003.0
107.5°	1165.8	1258.4	1301.5	1308.4	1305.4	1297.7	1281.2
110°	1116.0	1229.9	1302.9	1341.1	1358.1	1366.1	1365.2



TEST NUMBER: P331269-940

CATALOG NUMBER: S122DIP-S290D925U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1056.9	1178.7	1262.3	1315.5	1343.8	1359.0	1363.8
115°	976.2	1092.9	1184.5	1247.7	1288.6	1311.8	1319.8
117.5°	910.8	1016.5	1102.5	1166.9	1210.1	1234.6	1241.3
120°	876.6	970.9	1052.0	1114.2	1156.0	1181.9	1190.8
122.5°	848.1	937.5	1010.7	1066.5	1107.6	1130.6	1138.1
125°	810.7	889.0	955.8	1007.5	1041.3	1063.5	1070.6
127.5°	774.5	848.3	909.9	954.9	986.6	1005.8	1011.6
130°	750.2	820.6	879.3	922.9	953.1	970.9	978.0
132.5°	727.5	792.0	847.2	890.1	920.4	936.7	943.2
135°	691.5	750.2	800.0	838.3	867.7	883.7	887.3
137.5°	662.8	709.4	752.9	787.8	813.1	827.2	832.5
140°	644.4	685.3	724.4	752.9	776.1	789.4	794.7
142.5°	627.9	663.2	696.0	723.0	744.0	755.9	757.0
145°	607.0	634.5	660.3	681.7	696.9	705.7	708.4
147.5°	589.9	611.4	630.3	647.9	660.0	666.0	667.6
150°	578.5	597.2	613.1	626.5	637.2	642.6	643.5
152.5°	569.2	585.1	599.0	609.4	618.7	622.6	622.8
155°	554.5	567.8	577.6	587.4	593.6	597.2	595.4
157.5°	539.5	550.7	558.4	565.3	570.4	572.0	572.0
160°	529.5	539.3	545.5	551.8	556.2	557.1	557.1
162.5°	520.2	528.6	533.4	539.7	542.7	543.6	542.9
165°	506.4	512.6	516.2	519.7	523.3	523.3	522.4
167.5°	493.7	498.0	501.2	502.8	504.8	504.6	503.5
170°	485.9	489.5	491.2	492.1	494.8	493.9	492.1
172.5°	478.8	481.6	482.7	483.6	484.8	483.9	482.9
175°	470.8	471.7	472.6	472.6	473.5	472.6	470.8
177.5°	464.9	465.7	465.7	465.7	465.7	464.9	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8

(END OF REPORT)