

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331287-940

Luminaire Tested: **S122DIP-S485D330U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331287-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D330U940-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3053.2 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63				
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58	54				
2	93	85	79	74	87	80	75	71	71	67	64	62	59	57	54	52	50	46				
3	85	76	69	63	79	71	65	60	63	58	54	56	52	49	49	46	43	40				
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35				
5	72	60	52	47	67	57	50	45	51	45	41	45	41	37	40	36	33	31				
6	67	55	47	41	62	52	44	39	46	40	36	41	36	33	36	33	30	27				
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27	24				
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22				
9	54	42	34	29	50	39	33	28	36	30	26	32	27	24	29	25	22	20				
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13990	13990	13990	13990
5°	15686	14083	12478	14083
10°	17974	13967	10799	13967
15°	19883	13710	9541	13710
20°	19581	13435	8698	13435
25°	17655	13069	8165	13069
30°	14590	12486	7774	12486
35°	10634	11874	7496	11874
40°	8494	11152	7341	11152
45°	7421	10319	7133	10319
50°	6978	9510	6993	9510
55°	6432	8690	6804	8690
60°	5893	7818	6516	7818
65°	5368	7033	6235	7033
70°	4877	6274	5816	6274
75°	4323	5421	5153	5421
80°	3710	4491	4147	4491
85°	3335	3335	2464	3335



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	2.7
10°-20°	239.9	7.9
20°-30°	348.2	11.4
30°-40°	367.4	12.0
40°-50°	325.3	10.7
50°-60°	259.6	8.5
60°-70°	176.5	5.8
70°-80°	90.5	3.0
80°-90°	23.3	0.8
90°-100°	65.5	2.1
100°-110°	222.3	7.3
110°-120°	236.2	7.7
120°-130°	194.4	6.4
130°-140°	156.1	5.1
140°-150°	118.0	3.9
150°-160°	82.9	2.7
160°-170°	48.8	1.6
170°-180°	15.9	0.5
0°-30°	670.6	22.0
0°-40°	1038.0	34.0
0°-60°	1623.0	53.2
0°-90°	1913.2	62.7
90°-120°	524.0	17.2
90°-150°	992.5	32.5
90°-180°	1140.0	37.3
0°-180°	3053.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	866	866	866	866	866	
5°	968	869	770	869	968	97
15°	1190	820	571	820	1190	328
25°	991	734	458	734	991	448
35°	540	602	380	602	540	351
45°	325	452	312	452	325	256
55°	228	309	242	309	228	205
65°	140	184	163	184	140	140
75°	69	87	83	87	69	74
85°	18	18	13	18	18	20
90°	10	0	10	0	10	6
95°	36	11	36	11	36	47
105°	355	38	355	38	355	344
115°	467	68	467	68	467	458
125°	379	94	379	94	379	343
135°	314	111	314	111	314	244
145°	251	127	251	127	251	159
155°	211	144	211	144	211	98
165°	185	157	185	157	185	53
175°	167	164	167	164	167	16
180°	164	164	164	164	164	



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	906.5	906.8	907.2	903.0	902.5	902.5	898.8	895.5	891.8	886.7	887.3
5°	967.8	971.4	972.8	968.8	962.8	962.1	956.4	947.1	938.4	931.5	926.5
7.5°	1040.9	1042.3	1039.1	1033.8	1029.4	1021.4	1010.8	1000.5	986.1	972.8	963.0
10°	1096.3	1098.3	1092.6	1084.9	1078.6	1069.3	1054.0	1038.3	1019.4	1001.0	986.4
12.5°	1138.4	1143.4	1136.0	1135.1	1124.2	1111.4	1093.1	1085.2	1058.5	1033.0	1017.3
15°	1189.5	1189.2	1189.9	1183.6	1175.5	1173.6	1154.2	1133.3	1095.6	1080.7	1054.6
17.5°	1174.7	1179.8	1182.1	1182.1	1181.9	1180.6	1174.4	1161.2	1142.3	1118.0	1088.1
20°	1139.6	1146.2	1147.3	1154.9	1159.2	1164.9	1167.2	1163.6	1151.9	1131.6	1105.6
22.5°	1085.2	1087.1	1090.2	1102.2	1111.5	1125.7	1133.1	1145.4	1140.9	1131.0	1109.4
25°	991.0	987.7	999.3	1005.4	1027.0	1049.6	1066.0	1084.0	1099.9	1109.6	1103.3
27.5°	878.0	873.0	890.5	906.3	923.9	948.4	973.8	1003.9	1028.9	1060.2	1070.9
30°	782.6	785.6	802.3	819.2	845.9	880.5	909.1	942.1	977.8	1012.7	1037.0
32.5°	679.8	691.3	701.8	727.8	751.3	789.9	831.9	873.1	917.6	957.3	994.9
35°	539.5	552.8	567.5	586.5	619.4	657.7	698.7	754.3	814.9	869.2	913.8
37.5°	454.1	452.0	460.4	474.1	500.8	531.7	578.8	633.8	705.2	768.9	831.9
40°	403.0	401.6	407.6	420.3	440.6	463.2	504.5	552.8	619.1	697.0	772.0
42.5°	367.7	368.5	371.9	380.8	394.8	413.4	444.3	485.4	546.1	619.5	700.0
45°	325.0	327.3	331.0	335.4	343.3	358.6	375.9	405.3	453.3	514.5	593.8
47.5°	294.3	294.4	298.0	301.8	306.6	315.2	329.4	347.8	381.6	431.5	499.6
50°	277.8	275.4	278.0	281.1	286.1	292.0	301.4	318.7	341.3	381.7	438.5
52.5°	257.5	257.5	259.9	261.1	265.6	271.5	280.1	292.0	312.5	344.1	390.9
55°	228.5	230.2	231.5	233.4	237.5	241.7	248.4	256.5	272.4	296.0	330.6
57.5°	201.2	201.7	203.0	206.8	209.4	213.3	219.6	226.9	237.3	254.9	280.9
60°	182.5	182.5	185.1	186.8	190.1	194.1	199.1	206.2	215.4	229.8	250.7
62.5°	165.4	165.1	166.2	169.0	171.5	175.2	180.2	186.2	194.9	207.7	224.9
65°	140.5	139.9	141.9	142.5	145.2	148.8	152.8	159.2	166.2	175.5	190.8
67.5°	116.5	117.3	118.4	119.7	121.2	125.0	127.7	132.2	138.0	145.8	156.2
70°	103.3	103.3	103.3	104.2	106.2	108.3	110.9	114.6	120.2	126.9	136.2
72.5°	88.3	89.3	90.4	89.9	92.4	93.5	96.8	98.8	104.2	108.5	116.7
75°	69.3	69.3	69.3	70.9	72.0	72.9	74.9	77.0	79.6	84.9	89.3
77.5°	51.7	51.5	51.9	52.3	53.3	54.6	55.1	57.0	59.4	61.9	65.5
80°	39.9	40.7	40.9	41.6	41.6	42.3	42.6	44.9	46.6	48.3	50.6
82.5°	30.9	31.0	31.1	31.2	31.5	31.9	32.7	33.5	34.1	35.5	37.3
85°	18.0	17.7	17.7	18.3	18.0	18.0	18.6	19.4	19.4	19.6	20.7
87.5°	9.0	9.0	9.3	9.0	9.0	9.2	9.1	8.9	9.3	9.6	9.8
90°	10.4	10.4	10.4	10.4	10.4	10.1	9.5	10.1	10.4	10.7	10.4
92.5°	17.5	17.9	17.7	18.7	19.0	21.0	23.5	27.5	34.6	40.9	40.4
95°	35.9	35.6	36.6	39.1	43.2	50.1	63.3	82.6	108.1	123.5	109.3
97.5°	70.7	73.4	77.9	85.7	100.8	123.5	157.6	192.6	221.1	210.8	158.8
100°	112.8	118.5	127.6	141.2	167.3	205.5	248.6	287.7	294.3	248.9	171.4
102.5°	198.5	206.2	217.6	240.7	269.1	309.5	341.1	349.9	321.5	250.1	166.6
105°	355.1	359.4	373.0	392.5	412.1	422.5	418.4	382.8	317.3	233.4	157.2
107.5°	453.6	459.4	462.2	463.2	460.7	445.5	412.8	359.1	289.6	215.5	152.6
110°	483.3	483.7	480.8	474.8	461.3	435.4	395.1	338.7	272.2	207.0	151.6



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	482.8	481.1	475.7	465.7	446.9	417.2	374.2	320.0	260.1	201.4	151.8
115°	467.3	464.4	456.2	441.8	419.4	386.9	345.6	297.1	245.1	195.4	153.1
117.5°	439.4	437.0	428.5	413.1	390.3	359.9	322.4	279.8	235.7	192.3	155.4
120°	421.6	418.4	409.3	394.5	372.4	343.8	310.3	271.3	230.6	190.6	156.9
122.5°	402.9	400.3	392.2	377.6	357.8	331.9	300.2	264.5	226.3	189.6	158.6
125°	379.1	376.5	368.6	356.7	338.4	314.8	287.0	254.6	220.3	187.8	161.3
127.5°	358.1	356.1	349.3	338.0	322.1	300.3	274.2	244.8	214.5	186.7	164.0
130°	346.3	343.8	337.4	326.7	311.3	290.5	265.6	238.5	210.8	186.2	166.0
132.5°	333.9	331.6	325.8	315.1	300.0	280.4	257.5	232.5	207.8	185.9	168.1
135°	314.1	312.9	307.2	296.8	283.2	265.6	244.8	224.0	203.5	185.6	170.5
137.5°	294.7	292.8	287.8	278.9	266.5	251.2	234.7	217.3	200.5	185.5	172.6
140°	281.3	279.5	274.7	266.5	256.5	242.6	228.1	212.9	198.8	185.3	173.6
142.5°	268.0	267.6	263.4	255.9	246.4	234.8	222.3	209.5	197.1	185.3	174.3
145°	250.7	249.9	246.7	241.3	233.8	224.6	214.9	204.5	194.7	184.6	175.1
147.5°	236.4	235.8	233.6	229.3	223.1	216.4	208.8	200.6	192.3	183.5	175.4
150°	227.8	227.5	225.6	221.8	217.0	211.4	204.8	197.9	190.3	182.7	175.1
152.5°	220.5	220.4	219.0	215.8	212.0	207.1	201.5	195.1	188.5	181.5	174.7
155°	210.8	211.4	210.2	207.9	204.5	201.0	196.3	191.3	185.3	179.2	173.9
157.5°	202.5	202.5	202.0	200.1	197.7	194.9	191.0	186.8	182.2	177.0	172.5
160°	197.2	197.2	196.9	195.4	193.1	190.9	187.4	184.0	179.9	175.5	171.7
162.5°	192.2	192.4	192.2	191.1	188.9	187.2	184.2	181.2	177.9	174.2	170.9
165°	184.9	185.3	185.3	184.0	182.7	181.5	179.2	177.1	174.5	171.7	169.5
167.5°	178.3	178.6	178.7	178.0	177.5	176.3	174.8	173.1	171.3	169.5	168.1
170°	174.2	174.9	175.1	174.2	173.9	173.3	172.0	171.1	169.5	168.3	167.3
172.5°	170.9	171.3	171.7	171.2	170.9	170.5	169.5	168.8	167.7	166.7	166.3
175°	166.7	167.3	167.6	167.3	167.3	167.0	166.7	166.4	165.4	165.1	164.8
177.5°	164.1	164.6	164.9	164.9	164.9	164.9	164.6	164.6	164.1	163.8	164.1
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	889.1	887.0	885.6	880.9	876.6	872.4	871.0	871.6	865.7	860.1	857.7
5°	923.8	917.1	910.8	901.8	891.2	879.5	873.5	868.9	857.2	844.5	837.2
7.5°	954.8	945.3	933.1	916.2	900.7	882.3	870.7	860.4	843.3	825.5	814.6
10°	973.7	960.7	945.1	924.4	905.4	883.2	867.5	851.9	831.9	810.6	797.3
12.5°	990.0	972.5	957.1	930.6	908.1	880.2	861.7	839.6	818.6	793.3	780.2
15°	1028.7	996.4	967.1	937.1	909.5	870.5	849.9	820.2	792.6	761.3	746.3
17.5°	1058.5	1022.3	976.2	938.1	905.8	862.6	832.3	796.8	764.1	728.3	708.0
20°	1075.7	1034.0	984.4	939.1	900.4	851.2	818.2	781.9	743.6	703.3	681.4
22.5°	1085.7	1042.1	992.9	935.1	889.8	841.9	800.4	760.6	721.8	678.3	655.2
25°	1089.0	1049.0	997.0	931.7	876.5	822.2	772.2	733.6	686.7	646.0	612.4
27.5°	1073.1	1044.5	994.5	925.5	861.1	797.6	742.0	698.2	648.6	604.6	570.7
30°	1053.6	1037.0	988.4	919.1	848.8	780.6	719.3	669.7	620.5	575.8	541.2
32.5°	1023.6	1019.9	977.2	910.1	835.8	759.0	695.6	645.4	590.8	547.0	514.0
35°	964.4	980.4	953.4	889.8	811.2	728.3	659.7	602.4	545.8	503.8	472.9
37.5°	885.2	924.9	917.8	860.1	778.0	694.9	619.1	559.3	505.3	463.0	432.6
40°	830.5	881.2	888.5	837.5	754.7	669.1	588.8	529.1	476.5	437.9	407.2
42.5°	772.0	831.1	851.2	810.4	729.1	641.9	561.6	499.9	447.8	410.2	383.1
45°	673.7	752.0	788.3	764.9	686.3	597.1	514.5	451.9	404.7	369.3	348.3
47.5°	581.8	667.4	716.2	707.9	638.8	550.5	468.9	408.8	362.7	334.6	315.8
50°	516.8	604.8	663.7	666.4	604.8	517.2	435.2	378.6	336.4	310.0	294.7
52.5°	460.4	544.3	608.6	622.7	566.7	482.5	405.1	348.8	311.6	287.4	273.7
55°	386.6	457.5	528.9	554.8	509.9	429.9	358.3	308.7	273.8	257.1	245.1
57.5°	321.5	380.6	446.4	475.1	447.4	379.0	311.8	268.8	240.4	225.8	216.6
60°	287.0	333.7	392.3	426.6	402.6	341.7	283.0	242.1	218.8	205.8	197.2
62.5°	255.1	296.4	345.9	377.3	364.3	306.7	254.3	218.1	198.0	185.8	179.6
65°	210.4	243.1	281.4	310.4	301.8	258.1	215.2	184.1	168.2	158.5	153.6
67.5°	173.3	196.9	223.5	248.8	241.8	210.9	176.5	152.3	140.4	132.1	129.1
70°	149.9	167.8	191.5	211.8	206.2	180.8	153.6	132.9	122.5	115.6	112.5
72.5°	127.5	142.2	160.3	176.9	173.1	152.0	129.3	113.7	105.8	99.3	96.8
75°	96.2	107.5	118.6	129.6	128.6	112.3	98.9	86.9	80.6	75.6	74.6
77.5°	71.1	77.4	84.9	91.4	89.6	80.3	69.8	63.0	58.3	54.9	54.4
80°	54.3	58.0	63.3	67.9	65.6	61.6	53.3	48.3	44.9	41.6	40.3
82.5°	39.3	43.1	46.2	48.8	47.0	43.2	38.1	34.7	32.7	30.4	29.9
85°	20.7	22.6	24.0	24.6	24.0	21.7	19.4	18.0	16.3	15.3	15.0
87.5°	9.7	9.3	8.9	9.3	8.4	8.2	7.0	5.9	5.9	5.8	5.4
90°	8.5	6.3	4.7	3.7	3.1	2.5	1.2	0.4	1.2	2.5	3.1
92.5°	31.5	21.4	14.3	11.3	9.2	7.8	5.5	3.8	5.5	7.8	9.2
95°	72.8	45.4	30.9	23.3	18.3	15.4	12.3	11.1	12.3	15.4	18.3
97.5°	98.1	59.8	41.6	33.1	27.3	23.0	19.6	17.9	19.6	23.0	27.3
100°	103.3	64.9	48.2	39.4	33.1	28.0	25.2	24.3	25.2	28.0	33.1
102.5°	103.6	69.5	54.0	45.2	38.6	33.6	30.8	30.1	30.8	33.6	38.6
105°	105.2	77.2	62.4	53.6	46.6	41.9	39.7	38.4	39.7	41.9	46.6
107.5°	109.6	85.2	70.8	61.9	55.0	50.6	48.5	47.5	48.5	50.6	55.0
110°	113.1	90.4	76.6	67.4	60.8	56.7	54.8	53.6	54.8	56.7	60.8



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	116.9	95.5	82.1	72.7	66.3	62.5	60.4	59.1	60.4	62.5	66.3
115°	122.5	103.3	89.8	81.3	75.0	71.2	69.3	67.8	69.3	71.2	75.0
117.5°	128.6	110.6	98.1	89.3	83.2	79.8	77.9	76.7	77.9	79.8	83.2
120°	132.7	115.7	103.3	94.5	88.2	85.4	83.5	82.2	83.5	85.4	88.2
122.5°	136.2	120.4	108.9	99.8	93.5	90.4	88.5	87.6	88.5	90.4	93.5
125°	141.8	127.6	116.3	107.5	101.1	97.4	95.5	94.5	95.5	97.4	101.1
127.5°	147.0	134.3	123.2	114.1	108.2	104.0	101.3	100.0	101.3	104.0	108.2
130°	150.3	138.3	127.2	118.5	112.2	107.7	104.6	103.3	104.6	107.7	112.2
132.5°	153.6	141.9	131.3	122.5	115.9	111.3	107.9	106.4	107.9	111.3	115.9
135°	157.8	146.9	136.7	128.0	120.6	115.9	112.2	110.9	112.2	115.9	120.6
137.5°	161.1	150.9	140.9	132.7	125.6	120.5	116.7	115.2	116.7	120.5	125.6
140°	162.9	153.1	143.7	135.5	128.6	123.5	119.8	118.5	119.8	123.5	128.6
142.5°	164.4	154.9	145.7	138.0	131.3	126.3	122.8	121.7	122.8	126.3	131.3
145°	166.4	157.6	149.0	142.1	135.8	131.1	128.0	126.6	128.0	131.1	135.8
147.5°	167.5	159.7	151.7	145.5	140.3	135.9	132.9	132.0	132.9	135.9	140.3
150°	167.9	160.7	153.5	147.8	143.0	138.9	136.4	135.5	136.4	138.9	143.0
152.5°	168.2	161.7	155.2	150.1	145.5	142.0	139.5	139.0	139.5	142.0	145.5
155°	168.5	163.2	157.8	153.1	149.6	146.2	144.3	144.0	144.3	146.2	149.6
157.5°	168.5	164.3	159.7	155.8	153.0	150.0	148.5	148.1	148.5	150.0	153.0
160°	168.5	164.8	161.0	157.6	155.0	152.5	151.2	150.9	151.2	152.5	155.0
162.5°	168.3	165.1	161.8	159.1	156.8	154.8	153.5	153.7	153.5	154.8	156.8
165°	167.6	165.4	162.6	160.7	159.1	157.2	156.6	156.9	156.6	157.2	159.1
167.5°	167.2	165.3	163.3	162.1	161.0	159.7	159.2	159.5	159.2	159.7	161.0
170°	166.7	165.1	163.5	162.6	161.9	161.0	160.7	161.3	160.7	161.0	161.9
172.5°	165.9	164.9	163.8	163.1	162.7	161.8	161.9	162.3	161.9	161.8	162.7
175°	165.1	164.4	163.8	163.5	163.5	162.9	163.2	163.5	163.2	162.9	163.5
177.5°	164.6	164.1	163.8	163.8	163.8	163.4	163.5	164.1	163.5	163.4	163.8
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	855.1	853.5	847.8	844.9	840.2	835.6	832.7	834.0	835.1	834.6	833.7
5°	830.5	824.2	814.6	806.2	800.2	789.3	784.6	782.3	780.2	777.9	775.6
7.5°	801.4	791.4	777.6	765.7	754.5	740.8	733.1	728.3	723.5	718.3	713.6
10°	780.6	766.6	752.0	735.3	722.0	709.6	698.7	691.3	684.7	678.3	673.7
12.5°	758.8	742.6	724.5	701.8	687.1	669.4	667.8	654.9	644.4	640.5	635.1
15°	724.0	701.3	678.3	651.4	639.7	623.8	613.8	603.8	594.8	588.4	586.7
17.5°	684.5	655.1	632.3	613.0	593.9	577.5	568.3	560.3	552.9	544.4	543.3
20°	654.3	629.1	604.1	587.1	567.5	550.8	539.5	531.5	525.1	520.1	515.9
22.5°	625.9	598.2	575.3	556.7	537.3	523.9	515.0	507.3	502.0	496.5	492.4
25°	580.1	558.5	533.5	512.6	496.5	487.9	480.5	473.9	470.6	466.9	462.3
27.5°	540.1	516.0	492.7	476.4	462.4	454.7	449.5	445.0	441.8	439.7	437.0
30°	511.8	487.5	469.2	453.3	441.6	433.9	430.6	427.9	424.3	422.9	421.6
32.5°	484.6	462.8	447.1	433.3	422.1	417.1	414.1	411.7	408.8	407.5	404.8
35°	446.2	427.9	412.6	404.9	395.9	391.6	389.3	385.9	383.3	382.0	381.7
37.5°	410.1	394.1	384.1	374.3	370.4	367.7	364.6	362.3	361.5	361.3	361.0
40°	386.6	373.6	364.6	356.7	355.0	351.0	348.3	346.3	346.3	346.7	346.3
42.5°	365.3	353.7	345.7	338.9	336.9	334.5	331.8	331.7	332.3	333.3	332.3
45°	333.1	324.7	319.1	315.7	312.0	309.7	309.3	310.4	310.7	311.0	312.0
47.5°	303.3	297.7	292.7	289.0	287.4	287.0	286.6	288.3	289.9	290.5	292.0
50°	285.7	279.4	275.1	272.8	271.4	270.7	271.4	273.4	274.7	276.4	277.4
52.5°	266.0	261.5	258.6	256.7	256.2	256.6	256.7	259.0	261.2	261.7	262.3
55°	238.8	235.4	234.8	231.8	233.1	232.7	234.4	235.8	237.7	239.8	240.1
57.5°	211.6	208.9	207.1	207.4	207.8	209.3	210.6	213.0	215.2	217.2	217.5
60°	193.5	192.2	191.2	191.2	191.8	193.9	195.5	197.8	199.1	200.5	201.4
62.5°	177.0	175.7	174.6	175.1	176.9	178.1	180.0	181.3	182.6	184.0	184.4
65°	150.9	150.2	151.2	151.9	152.2	153.8	156.2	157.2	158.5	159.2	161.5
67.5°	126.8	127.0	126.8	127.8	129.7	130.1	132.2	134.6	134.9	136.2	137.7
70°	110.6	111.2	111.9	112.5	114.2	114.9	116.5	117.5	118.9	119.8	120.9
72.5°	95.7	95.8	96.5	96.3	97.7	99.2	100.6	101.6	102.9	104.2	105.1
75°	73.6	73.6	74.3	74.6	76.2	77.9	77.6	78.3	79.6	81.0	81.6
77.5°	53.8	53.1	53.8	54.0	54.6	56.0	56.3	57.2	58.8	58.3	59.0
80°	40.9	39.9	40.9	41.3	41.3	43.0	43.0	43.6	44.6	43.6	44.6
82.5°	29.2	28.8	29.5	29.6	30.1	30.1	30.7	30.9	31.8	31.4	31.8
85°	14.6	14.4	14.6	14.4	14.6	15.0	15.0	14.6	14.6	15.3	14.4
87.5°	5.3	5.2	5.3	5.7	5.8	5.6	5.3	5.2	5.1	4.6	4.7
90°	3.7	4.7	6.3	8.5	10.4	10.7	10.4	10.1	9.5	10.1	10.4
92.5°	11.3	14.3	21.4	31.5	40.4	40.9	34.6	27.5	23.5	21.0	19.0
95°	23.3	30.9	45.4	72.8	109.3	123.5	108.1	82.6	63.3	50.1	43.2
97.5°	33.1	41.6	59.8	98.1	158.8	210.8	221.1	192.6	157.6	123.5	100.8
100°	39.4	48.2	64.9	103.3	171.4	248.9	294.3	287.7	248.6	205.5	167.3
102.5°	45.2	54.0	69.5	103.6	166.6	250.1	321.5	349.9	341.1	309.5	269.1
105°	53.6	62.4	77.2	105.2	157.2	233.4	317.3	382.8	418.4	422.5	412.1
107.5°	61.9	70.8	85.2	109.6	152.6	215.5	289.6	359.1	412.8	445.5	460.7
110°	67.4	76.6	90.4	113.1	151.6	207.0	272.2	338.7	395.1	435.4	461.3



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	72.7	82.1	95.5	116.9	151.8	201.4	260.1	320.0	374.2	417.2	446.9
115°	81.3	89.8	103.3	122.5	153.1	195.4	245.1	297.1	345.6	386.9	419.4
117.5°	89.3	98.1	110.6	128.6	155.4	192.3	235.7	279.8	322.4	359.9	390.3
120°	94.5	103.3	115.7	132.7	156.9	190.6	230.6	271.3	310.3	343.8	372.4
122.5°	99.8	108.9	120.4	136.2	158.6	189.6	226.3	264.5	300.2	331.9	357.8
125°	107.5	116.3	127.6	141.8	161.3	187.8	220.3	254.6	287.0	314.8	338.4
127.5°	114.1	123.2	134.3	147.0	164.0	186.7	214.5	244.8	274.2	300.3	322.1
130°	118.5	127.2	138.3	150.3	166.0	186.2	210.8	238.5	265.6	290.5	311.3
132.5°	122.5	131.3	141.9	153.6	168.1	185.9	207.8	232.5	257.5	280.4	300.0
135°	128.0	136.7	146.9	157.8	170.5	185.6	203.5	224.0	244.8	265.6	283.2
137.5°	132.7	140.9	150.9	161.1	172.6	185.5	200.5	217.3	234.7	251.2	266.5
140°	135.5	143.7	153.1	162.9	173.6	185.3	198.8	212.9	228.1	242.6	256.5
142.5°	138.0	145.7	154.9	164.4	174.3	185.3	197.1	209.5	222.3	234.8	246.4
145°	142.1	149.0	157.6	166.4	175.1	184.6	194.7	204.5	214.9	224.6	233.8
147.5°	145.5	151.7	159.7	167.5	175.4	183.5	192.3	200.6	208.8	216.4	223.1
150°	147.8	153.5	160.7	167.9	175.1	182.7	190.3	197.9	204.8	211.4	217.0
152.5°	150.1	155.2	161.7	168.2	174.7	181.5	188.5	195.1	201.5	207.1	212.0
155°	153.1	157.8	163.2	168.5	173.9	179.2	185.3	191.3	196.3	201.0	204.5
157.5°	155.8	159.7	164.3	168.5	172.5	177.0	182.2	186.8	191.0	194.9	197.7
160°	157.6	161.0	164.8	168.5	171.7	175.5	179.9	184.0	187.4	190.9	193.1
162.5°	159.1	161.8	165.1	168.3	170.9	174.2	177.9	181.2	184.2	187.2	188.9
165°	160.7	162.6	165.4	167.6	169.5	171.7	174.5	177.1	179.2	181.5	182.7
167.5°	162.1	163.3	165.3	167.2	168.1	169.5	171.3	173.1	174.8	176.3	177.5
170°	162.6	163.5	165.1	166.7	167.3	168.3	169.5	171.1	172.0	173.3	173.9
172.5°	163.1	163.8	164.9	165.9	166.3	166.7	167.7	168.8	169.5	170.5	170.9
175°	163.5	163.8	164.4	165.1	164.8	165.1	165.4	166.4	166.7	167.0	167.3
177.5°	163.8	163.8	164.1	164.6	164.1	163.8	164.1	164.6	164.6	164.9	164.9
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	831.1	830.5	830.5	828.1	830.5	830.5	831.1	833.7	834.6	835.1	834.0
5°	771.0	769.9	768.3	769.9	768.3	769.9	771.0	775.6	777.9	780.2	782.3
7.5°	711.5	707.5	706.9	702.9	706.9	707.5	711.5	713.6	718.3	723.5	728.3
10°	668.1	665.4	665.0	658.7	665.0	665.4	668.1	673.7	678.3	684.7	691.3
12.5°	635.0	628.6	629.9	626.2	629.9	628.6	635.0	635.1	640.5	644.4	654.9
15°	577.7	577.7	576.5	570.8	576.5	577.7	577.7	586.7	588.4	594.8	603.8
17.5°	536.7	536.0	532.8	534.4	532.8	536.0	536.7	543.3	544.4	552.9	560.3
20°	512.2	510.1	506.2	506.2	506.2	510.1	512.2	515.9	520.1	525.1	531.5
22.5°	489.0	488.8	484.6	486.0	484.6	488.8	489.0	492.4	496.5	502.0	507.3
25°	461.9	459.2	457.3	458.3	457.3	459.2	461.9	462.3	466.9	470.6	473.9
27.5°	436.2	434.7	434.6	431.9	434.6	434.7	436.2	437.0	439.7	441.8	445.0
30°	421.2	417.9	418.6	417.0	418.6	417.9	421.2	421.6	422.9	424.3	427.9
32.5°	404.2	403.1	402.3	400.9	402.3	403.1	404.2	404.8	407.5	408.8	411.7
35°	380.9	381.3	379.6	380.3	379.6	381.3	380.9	381.7	382.0	383.3	385.9
37.5°	360.7	361.8	361.0	361.1	361.0	361.8	360.7	361.0	361.3	361.5	362.3
40°	347.3	347.3	347.3	348.3	347.3	347.3	347.3	346.3	346.7	346.3	346.3
42.5°	334.6	334.0	333.5	333.4	333.5	334.0	334.6	332.3	333.3	332.3	331.7
45°	312.7	313.7	314.1	312.4	314.1	313.7	312.7	312.0	311.0	310.7	310.4
47.5°	292.9	293.0	292.9	294.4	292.9	293.0	292.9	292.0	290.5	289.9	288.3
50°	279.1	278.4	279.1	278.4	279.1	278.4	279.1	277.4	276.4	274.7	273.4
52.5°	264.4	264.6	264.1	264.0	264.1	264.6	264.4	262.3	261.7	261.2	259.0
55°	241.5	242.1	241.7	241.7	241.7	242.1	241.5	240.1	239.8	237.7	235.8
57.5°	217.7	218.3	218.7	217.2	218.7	218.3	217.7	217.5	217.2	215.2	213.0
60°	201.2	202.8	202.5	201.8	202.5	202.8	201.2	201.4	200.5	199.1	197.8
62.5°	185.9	186.5	186.5	186.4	186.5	186.5	185.9	184.4	184.0	182.6	181.3
65°	162.5	163.2	162.2	163.2	162.2	163.2	162.5	161.5	159.2	158.5	157.2
67.5°	137.2	137.5	138.2	138.7	138.2	137.5	137.2	137.7	136.2	134.9	134.6
70°	121.5	121.2	122.3	123.2	122.3	121.2	121.5	120.9	119.8	118.9	117.5
72.5°	105.0	105.8	105.4	106.2	105.4	105.8	105.0	105.1	104.2	102.9	101.6
75°	81.0	81.9	81.6	82.6	81.6	81.9	81.0	81.6	81.0	79.6	78.3
77.5°	58.5	58.6	58.5	59.0	58.5	58.6	58.5	59.0	58.3	58.8	57.2
80°	44.6	44.0	43.2	44.6	43.2	44.0	44.6	44.6	43.6	44.6	43.6
82.5°	31.0	31.5	30.8	30.8	30.8	31.5	31.0	31.8	31.4	31.8	30.9
85°	14.4	14.0	13.3	13.3	13.3	14.0	14.4	14.4	15.3	14.6	14.6
87.5°	4.7	4.5	4.5	4.2	4.5	4.5	4.7	4.7	4.6	5.1	5.2
90°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.1	9.5	10.1
92.5°	18.7	17.7	17.9	17.5	17.9	17.7	18.7	19.0	21.0	23.5	27.5
95°	39.1	36.6	35.6	35.9	35.6	36.6	39.1	43.2	50.1	63.3	82.6
97.5°	85.7	77.9	73.4	70.7	73.4	77.9	85.7	100.8	123.5	157.6	192.6
100°	141.2	127.6	118.5	112.8	118.5	127.6	141.2	167.3	205.5	248.6	287.7
102.5°	240.7	217.6	206.2	198.5	206.2	217.6	240.7	269.1	309.5	341.1	349.9
105°	392.5	373.0	359.4	355.1	359.4	373.0	392.5	412.1	422.5	418.4	382.8
107.5°	463.2	462.2	459.4	453.6	459.4	462.2	463.2	460.7	445.5	412.8	359.1
110°	474.8	480.8	483.7	483.3	483.7	480.8	474.8	461.3	435.4	395.1	338.7



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	465.7	475.7	481.1	482.8	481.1	475.7	465.7	446.9	417.2	374.2	320.0
115°	441.8	456.2	464.4	467.3	464.4	456.2	441.8	419.4	386.9	345.6	297.1
117.5°	413.1	428.5	437.0	439.4	437.0	428.5	413.1	390.3	359.9	322.4	279.8
120°	394.5	409.3	418.4	421.6	418.4	409.3	394.5	372.4	343.8	310.3	271.3
122.5°	377.6	392.2	400.3	402.9	400.3	392.2	377.6	357.8	331.9	300.2	264.5
125°	356.7	368.6	376.5	379.1	376.5	368.6	356.7	338.4	314.8	287.0	254.6
127.5°	338.0	349.3	356.1	358.1	356.1	349.3	338.0	322.1	300.3	274.2	244.8
130°	326.7	337.4	343.8	346.3	343.8	337.4	326.7	311.3	290.5	265.6	238.5
132.5°	315.1	325.8	331.6	333.9	331.6	325.8	315.1	300.0	280.4	257.5	232.5
135°	296.8	307.2	312.9	314.1	312.9	307.2	296.8	283.2	265.6	244.8	224.0
137.5°	278.9	287.8	292.8	294.7	292.8	287.8	278.9	266.5	251.2	234.7	217.3
140°	266.5	274.7	279.5	281.3	279.5	274.7	266.5	256.5	242.6	228.1	212.9
142.5°	255.9	263.4	267.6	268.0	267.6	263.4	255.9	246.4	234.8	222.3	209.5
145°	241.3	246.7	249.9	250.7	249.9	246.7	241.3	233.8	224.6	214.9	204.5
147.5°	229.3	233.6	235.8	236.4	235.8	233.6	229.3	223.1	216.4	208.8	200.6
150°	221.8	225.6	227.5	227.8	227.5	225.6	221.8	217.0	211.4	204.8	197.9
152.5°	215.8	219.0	220.4	220.5	220.4	219.0	215.8	212.0	207.1	201.5	195.1
155°	207.9	210.2	211.4	210.8	211.4	210.2	207.9	204.5	201.0	196.3	191.3
157.5°	200.1	202.0	202.5	202.5	202.5	202.0	200.1	197.7	194.9	191.0	186.8
160°	195.4	196.9	197.2	197.2	197.2	196.9	195.4	193.1	190.9	187.4	184.0
162.5°	191.1	192.2	192.4	192.2	192.4	192.2	191.1	188.9	187.2	184.2	181.2
165°	184.0	185.3	185.3	184.9	185.3	185.3	184.0	182.7	181.5	179.2	177.1
167.5°	178.0	178.7	178.6	178.3	178.6	178.7	178.0	177.5	176.3	174.8	173.1
170°	174.2	175.1	174.9	174.2	174.9	175.1	174.2	173.9	173.3	172.0	171.1
172.5°	171.2	171.7	171.3	170.9	171.3	171.7	171.2	170.9	170.5	169.5	168.8
175°	167.3	167.6	167.3	166.7	167.3	167.6	167.3	167.3	167.0	166.7	166.4
177.5°	164.9	164.9	164.6	164.1	164.6	164.9	164.9	164.9	164.9	164.6	164.6
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	832.7	835.6	840.2	844.9	847.8	853.5	855.1	857.7	860.1	865.7	871.6
5°	784.6	789.3	800.2	806.2	814.6	824.2	830.5	837.2	844.5	857.2	868.9
7.5°	733.1	740.8	754.5	765.7	777.6	791.4	801.4	814.6	825.5	843.3	860.4
10°	698.7	709.6	722.0	735.3	752.0	766.6	780.6	797.3	810.6	831.9	851.9
12.5°	667.8	669.4	687.1	701.8	724.5	742.6	758.8	780.2	793.3	818.6	839.6
15°	613.8	623.8	639.7	651.4	678.3	701.3	724.0	746.3	761.3	792.6	820.2
17.5°	568.3	577.5	593.9	613.0	632.3	655.1	684.5	708.0	728.3	764.1	796.8
20°	539.5	550.8	567.5	587.1	604.1	629.1	654.3	681.4	703.3	743.6	781.9
22.5°	515.0	523.9	537.3	556.7	575.3	598.2	625.9	655.2	678.3	721.8	760.6
25°	480.5	487.9	496.5	512.6	533.5	558.5	580.1	612.4	646.0	686.7	733.6
27.5°	449.5	454.7	462.4	476.4	492.7	516.0	540.1	570.7	604.6	648.6	698.2
30°	430.6	433.9	441.6	453.3	469.2	487.5	511.8	541.2	575.8	620.5	669.7
32.5°	414.1	417.1	422.1	433.3	447.1	462.8	484.6	514.0	547.0	590.8	645.4
35°	389.3	391.6	395.9	404.9	412.6	427.9	446.2	472.9	503.8	545.8	602.4
37.5°	364.6	367.7	370.4	374.3	384.1	394.1	410.1	432.6	463.0	505.3	559.3
40°	348.3	351.0	355.0	356.7	364.6	373.6	386.6	407.2	437.9	476.5	529.1
42.5°	331.8	334.5	336.9	338.9	345.7	353.7	365.3	383.1	410.2	447.8	499.9
45°	309.3	309.7	312.0	315.7	319.1	324.7	333.1	348.3	369.3	404.7	451.9
47.5°	286.6	287.0	287.4	289.0	292.7	297.7	303.3	315.8	334.6	362.7	408.8
50°	271.4	270.7	271.4	272.8	275.1	279.4	285.7	294.7	310.0	336.4	378.6
52.5°	256.7	256.6	256.2	256.7	258.6	261.5	266.0	273.7	287.4	311.6	348.8
55°	234.4	232.7	233.1	231.8	234.8	235.4	238.8	245.1	257.1	273.8	308.7
57.5°	210.6	209.3	207.8	207.4	207.1	208.9	211.6	216.6	225.8	240.4	268.8
60°	195.5	193.9	191.8	191.2	191.2	192.2	193.5	197.2	205.8	218.8	242.1
62.5°	180.0	178.1	176.9	175.1	174.6	175.7	177.0	179.6	185.8	198.0	218.1
65°	156.2	153.8	152.2	151.9	151.2	150.2	150.9	153.6	158.5	168.2	184.1
67.5°	132.2	130.1	129.7	127.8	126.8	127.0	126.8	129.1	132.1	140.4	152.3
70°	116.5	114.9	114.2	112.5	111.9	111.2	110.6	112.5	115.6	122.5	132.9
72.5°	100.6	99.2	97.7	96.3	96.5	95.8	95.7	96.8	99.3	105.8	113.7
75°	77.6	77.9	76.2	74.6	74.3	73.6	73.6	74.6	75.6	80.6	86.9
77.5°	56.3	56.0	54.6	54.0	53.8	53.1	53.8	54.4	54.9	58.3	63.0
80°	43.0	43.0	41.3	41.3	40.9	39.9	40.9	40.3	41.6	44.9	48.3
82.5°	30.7	30.1	30.1	29.6	29.5	28.8	29.2	29.9	30.4	32.7	34.7
85°	15.0	15.0	14.6	14.4	14.6	14.4	14.6	15.0	15.3	16.3	18.0
87.5°	5.3	5.6	5.8	5.7	5.3	5.2	5.3	5.4	5.8	5.9	5.9
90°	10.4	10.7	10.4	8.5	6.3	4.7	3.7	3.1	2.5	1.2	0.4
92.5°	34.6	40.9	40.4	31.5	21.4	14.3	11.3	9.2	7.8	5.5	3.8
95°	108.1	123.5	109.3	72.8	45.4	30.9	23.3	18.3	15.4	12.3	11.1
97.5°	221.1	210.8	158.8	98.1	59.8	41.6	33.1	27.3	23.0	19.6	17.9
100°	294.3	248.9	171.4	103.3	64.9	48.2	39.4	33.1	28.0	25.2	24.3
102.5°	321.5	250.1	166.6	103.6	69.5	54.0	45.2	38.6	33.6	30.8	30.1
105°	317.3	233.4	157.2	105.2	77.2	62.4	53.6	46.6	41.9	39.7	38.4
107.5°	289.6	215.5	152.6	109.6	85.2	70.8	61.9	55.0	50.6	48.5	47.5
110°	272.2	207.0	151.6	113.1	90.4	76.6	67.4	60.8	56.7	54.8	53.6



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.1	201.4	151.8	116.9	95.5	82.1	72.7	66.3	62.5	60.4	59.1
115°	245.1	195.4	153.1	122.5	103.3	89.8	81.3	75.0	71.2	69.3	67.8
117.5°	235.7	192.3	155.4	128.6	110.6	98.1	89.3	83.2	79.8	77.9	76.7
120°	230.6	190.6	156.9	132.7	115.7	103.3	94.5	88.2	85.4	83.5	82.2
122.5°	226.3	189.6	158.6	136.2	120.4	108.9	99.8	93.5	90.4	88.5	87.6
125°	220.3	187.8	161.3	141.8	127.6	116.3	107.5	101.1	97.4	95.5	94.5
127.5°	214.5	186.7	164.0	147.0	134.3	123.2	114.1	108.2	104.0	101.3	100.0
130°	210.8	186.2	166.0	150.3	138.3	127.2	118.5	112.2	107.7	104.6	103.3
132.5°	207.8	185.9	168.1	153.6	141.9	131.3	122.5	115.9	111.3	107.9	106.4
135°	203.5	185.6	170.5	157.8	146.9	136.7	128.0	120.6	115.9	112.2	110.9
137.5°	200.5	185.5	172.6	161.1	150.9	140.9	132.7	125.6	120.5	116.7	115.2
140°	198.8	185.3	173.6	162.9	153.1	143.7	135.5	128.6	123.5	119.8	118.5
142.5°	197.1	185.3	174.3	164.4	154.9	145.7	138.0	131.3	126.3	122.8	121.7
145°	194.7	184.6	175.1	166.4	157.6	149.0	142.1	135.8	131.1	128.0	126.6
147.5°	192.3	183.5	175.4	167.5	159.7	151.7	145.5	140.3	135.9	132.9	132.0
150°	190.3	182.7	175.1	167.9	160.7	153.5	147.8	143.0	138.9	136.4	135.5
152.5°	188.5	181.5	174.7	168.2	161.7	155.2	150.1	145.5	142.0	139.5	139.0
155°	185.3	179.2	173.9	168.5	163.2	157.8	153.1	149.6	146.2	144.3	144.0
157.5°	182.2	177.0	172.5	168.5	164.3	159.7	155.8	153.0	150.0	148.5	148.1
160°	179.9	175.5	171.7	168.5	164.8	161.0	157.6	155.0	152.5	151.2	150.9
162.5°	177.9	174.2	170.9	168.3	165.1	161.8	159.1	156.8	154.8	153.5	153.7
165°	174.5	171.7	169.5	167.6	165.4	162.6	160.7	159.1	157.2	156.6	156.9
167.5°	171.3	169.5	168.1	167.2	165.3	163.3	162.1	161.0	159.7	159.2	159.5
170°	169.5	168.3	167.3	166.7	165.1	163.5	162.6	161.9	161.0	160.7	161.3
172.5°	167.7	166.7	166.3	165.9	164.9	163.8	163.1	162.7	161.8	161.9	162.3
175°	165.4	165.1	164.8	165.1	164.4	163.8	163.5	163.5	162.9	163.2	163.5
177.5°	164.1	163.8	164.1	164.6	164.1	163.8	163.8	163.8	163.4	163.5	164.1
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	871.0	872.4	876.6	880.9	885.6	887.0	889.1	887.3	886.7	891.8	895.5
5°	873.5	879.5	891.2	901.8	910.8	917.1	923.8	926.5	931.5	938.4	947.1
7.5°	870.7	882.3	900.7	916.2	933.1	945.3	954.8	963.0	972.8	986.1	1000.5
10°	867.5	883.2	905.4	924.4	945.1	960.7	973.7	986.4	1001.0	1019.4	1038.3
12.5°	861.7	880.2	908.1	930.6	957.1	972.5	990.0	1017.3	1033.0	1058.5	1085.2
15°	849.9	870.5	909.5	937.1	967.1	996.4	1028.7	1054.6	1080.7	1095.6	1133.3
17.5°	832.3	862.6	905.8	938.1	976.2	1022.3	1058.5	1088.1	1118.0	1142.3	1161.2
20°	818.2	851.2	900.4	939.1	984.4	1034.0	1075.7	1105.6	1131.6	1151.9	1163.6
22.5°	800.4	841.9	889.8	935.1	992.9	1042.1	1085.7	1109.4	1131.0	1140.9	1145.4
25°	772.2	822.2	876.5	931.7	997.0	1049.0	1089.0	1103.3	1109.6	1099.9	1084.0
27.5°	742.0	797.6	861.1	925.5	994.5	1044.5	1073.1	1070.9	1060.2	1028.9	1003.9
30°	719.3	780.6	848.8	919.1	988.4	1037.0	1053.6	1037.0	1012.7	977.8	942.1
32.5°	695.6	759.0	835.8	910.1	977.2	1019.9	1023.6	994.9	957.3	917.6	873.1
35°	659.7	728.3	811.2	889.8	953.4	980.4	964.4	913.8	869.2	814.9	754.3
37.5°	619.1	694.9	778.0	860.1	917.8	924.9	885.2	831.9	768.9	705.2	633.8
40°	588.8	669.1	754.7	837.5	888.5	881.2	830.5	772.0	697.0	619.1	552.8
42.5°	561.6	641.9	729.1	810.4	851.2	831.1	772.0	700.0	619.5	546.1	485.4
45°	514.5	597.1	686.3	764.9	788.3	752.0	673.7	593.8	514.5	453.3	405.3
47.5°	468.9	550.5	638.8	707.9	716.2	667.4	581.8	499.6	431.5	381.6	347.8
50°	435.2	517.2	604.8	666.4	663.7	604.8	516.8	438.5	381.7	341.3	318.7
52.5°	405.1	482.5	566.7	622.7	608.6	544.3	460.4	390.9	344.1	312.5	292.0
55°	358.3	429.9	509.9	554.8	528.9	457.5	386.6	330.6	296.0	272.4	256.5
57.5°	311.8	379.0	447.4	475.1	446.4	380.6	321.5	280.9	254.9	237.3	226.9
60°	283.0	341.7	402.6	426.6	392.3	333.7	287.0	250.7	229.8	215.4	206.2
62.5°	254.3	306.7	364.3	377.3	345.9	296.4	255.1	224.9	207.7	194.9	186.2
65°	215.2	258.1	301.8	310.4	281.4	243.1	210.4	190.8	175.5	166.2	159.2
67.5°	176.5	210.9	241.8	248.8	223.5	196.9	173.3	156.2	145.8	138.0	132.2
70°	153.6	180.8	206.2	211.8	191.5	167.8	149.9	136.2	126.9	120.2	114.6
72.5°	129.3	152.0	173.1	176.9	160.3	142.2	127.5	116.7	108.5	104.2	98.8
75°	98.9	112.3	128.6	129.6	118.6	107.5	96.2	89.3	84.9	79.6	77.0
77.5°	69.8	80.3	89.6	91.4	84.9	77.4	71.1	65.5	61.9	59.4	57.0
80°	53.3	61.6	65.6	67.9	63.3	58.0	54.3	50.6	48.3	46.6	44.9
82.5°	38.1	43.2	47.0	48.8	46.2	43.1	39.3	37.3	35.5	34.1	33.5
85°	19.4	21.7	24.0	24.6	24.0	22.6	20.7	20.7	19.6	19.4	19.4
87.5°	7.0	8.2	8.4	9.3	8.9	9.3	9.7	9.8	9.6	9.3	8.9
90°	1.2	2.5	3.1	3.7	4.7	6.3	8.5	10.4	10.7	10.4	10.1
92.5°	5.5	7.8	9.2	11.3	14.3	21.4	31.5	40.4	40.9	34.6	27.5
95°	12.3	15.4	18.3	23.3	30.9	45.4	72.8	109.3	123.5	108.1	82.6
97.5°	19.6	23.0	27.3	33.1	41.6	59.8	98.1	158.8	210.8	221.1	192.6
100°	25.2	28.0	33.1	39.4	48.2	64.9	103.3	171.4	248.9	294.3	287.7
102.5°	30.8	33.6	38.6	45.2	54.0	69.5	103.6	166.6	250.1	321.5	349.9
105°	39.7	41.9	46.6	53.6	62.4	77.2	105.2	157.2	233.4	317.3	382.8
107.5°	48.5	50.6	55.0	61.9	70.8	85.2	109.6	152.6	215.5	289.6	359.1
110°	54.8	56.7	60.8	67.4	76.6	90.4	113.1	151.6	207.0	272.2	338.7



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	60.4	62.5	66.3	72.7	82.1	95.5	116.9	151.8	201.4	260.1	320.0
115°	69.3	71.2	75.0	81.3	89.8	103.3	122.5	153.1	195.4	245.1	297.1
117.5°	77.9	79.8	83.2	89.3	98.1	110.6	128.6	155.4	192.3	235.7	279.8
120°	83.5	85.4	88.2	94.5	103.3	115.7	132.7	156.9	190.6	230.6	271.3
122.5°	88.5	90.4	93.5	99.8	108.9	120.4	136.2	158.6	189.6	226.3	264.5
125°	95.5	97.4	101.1	107.5	116.3	127.6	141.8	161.3	187.8	220.3	254.6
127.5°	101.3	104.0	108.2	114.1	123.2	134.3	147.0	164.0	186.7	214.5	244.8
130°	104.6	107.7	112.2	118.5	127.2	138.3	150.3	166.0	186.2	210.8	238.5
132.5°	107.9	111.3	115.9	122.5	131.3	141.9	153.6	168.1	185.9	207.8	232.5
135°	112.2	115.9	120.6	128.0	136.7	146.9	157.8	170.5	185.6	203.5	224.0
137.5°	116.7	120.5	125.6	132.7	140.9	150.9	161.1	172.6	185.5	200.5	217.3
140°	119.8	123.5	128.6	135.5	143.7	153.1	162.9	173.6	185.3	198.8	212.9
142.5°	122.8	126.3	131.3	138.0	145.7	154.9	164.4	174.3	185.3	197.1	209.5
145°	128.0	131.1	135.8	142.1	149.0	157.6	166.4	175.1	184.6	194.7	204.5
147.5°	132.9	135.9	140.3	145.5	151.7	159.7	167.5	175.4	183.5	192.3	200.6
150°	136.4	138.9	143.0	147.8	153.5	160.7	167.9	175.1	182.7	190.3	197.9
152.5°	139.5	142.0	145.5	150.1	155.2	161.7	168.2	174.7	181.5	188.5	195.1
155°	144.3	146.2	149.6	153.1	157.8	163.2	168.5	173.9	179.2	185.3	191.3
157.5°	148.5	150.0	153.0	155.8	159.7	164.3	168.5	172.5	177.0	182.2	186.8
160°	151.2	152.5	155.0	157.6	161.0	164.8	168.5	171.7	175.5	179.9	184.0
162.5°	153.5	154.8	156.8	159.1	161.8	165.1	168.3	170.9	174.2	177.9	181.2
165°	156.6	157.2	159.1	160.7	162.6	165.4	167.6	169.5	171.7	174.5	177.1
167.5°	159.2	159.7	161.0	162.1	163.3	165.3	167.2	168.1	169.5	171.3	173.1
170°	160.7	161.0	161.9	162.6	163.5	165.1	166.7	167.3	168.3	169.5	171.1
172.5°	161.9	161.8	162.7	163.1	163.8	164.9	165.9	166.3	166.7	167.7	168.8
175°	163.2	162.9	163.5	163.5	163.8	164.4	165.1	164.8	165.1	165.4	166.4
177.5°	163.5	163.4	163.8	163.8	163.8	164.1	164.6	164.1	163.8	164.1	164.6
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	866.5	866.5	866.5	866.5	866.5	866.5	866.5
2.5°	898.8	902.5	902.5	903.0	907.2	906.8	906.5
5°	956.4	962.1	962.8	968.8	972.8	971.4	967.8
7.5°	1010.8	1021.4	1029.4	1033.8	1039.1	1042.3	1040.9
10°	1054.0	1069.3	1078.6	1084.9	1092.6	1098.3	1096.3
12.5°	1093.1	1111.4	1124.2	1135.1	1136.0	1143.4	1138.4
15°	1154.2	1173.6	1175.5	1183.6	1189.9	1189.2	1189.5
17.5°	1174.4	1180.6	1181.9	1182.1	1182.1	1179.8	1174.7
20°	1167.2	1164.9	1159.2	1154.9	1147.3	1146.2	1139.6
22.5°	1133.1	1125.7	1111.5	1102.2	1090.2	1087.1	1085.2
25°	1066.0	1049.6	1027.0	1005.4	999.3	987.7	991.0
27.5°	973.8	948.4	923.9	906.3	890.5	873.0	878.0
30°	909.1	880.5	845.9	819.2	802.3	785.6	782.6
32.5°	831.9	789.9	751.3	727.8	701.8	691.3	679.8
35°	698.7	657.7	619.4	586.5	567.5	552.8	539.5
37.5°	578.8	531.7	500.8	474.1	460.4	452.0	454.1
40°	504.5	463.2	440.6	420.3	407.6	401.6	403.0
42.5°	444.3	413.4	394.8	380.8	371.9	368.5	367.7
45°	375.9	358.6	343.3	335.4	331.0	327.3	325.0
47.5°	329.4	315.2	306.6	301.8	298.0	294.4	294.3
50°	301.4	292.0	286.1	281.1	278.0	275.4	277.8
52.5°	280.1	271.5	265.6	261.1	259.9	257.5	257.5
55°	248.4	241.7	237.5	233.4	231.5	230.2	228.5
57.5°	219.6	213.3	209.4	206.8	203.0	201.7	201.2
60°	199.1	194.1	190.1	186.8	185.1	182.5	182.5
62.5°	180.2	175.2	171.5	169.0	166.2	165.1	165.4
65°	152.8	148.8	145.2	142.5	141.9	139.9	140.5
67.5°	127.7	125.0	121.2	119.7	118.4	117.3	116.5
70°	110.9	108.3	106.2	104.2	103.3	103.3	103.3
72.5°	96.8	93.5	92.4	89.9	90.4	89.3	88.3
75°	74.9	72.9	72.0	70.9	69.3	69.3	69.3
77.5°	55.1	54.6	53.3	52.3	51.9	51.5	51.7
80°	42.6	42.3	41.6	41.6	40.9	40.7	39.9
82.5°	32.7	31.9	31.5	31.2	31.1	31.0	30.9
85°	18.6	18.0	18.0	18.3	17.7	17.7	18.0
87.5°	9.1	9.2	9.0	9.0	9.3	9.0	9.0
90°	9.5	10.1	10.4	10.4	10.4	10.4	10.4
92.5°	23.5	21.0	19.0	18.7	17.7	17.9	17.5
95°	63.3	50.1	43.2	39.1	36.6	35.6	35.9
97.5°	157.6	123.5	100.8	85.7	77.9	73.4	70.7
100°	248.6	205.5	167.3	141.2	127.6	118.5	112.8
102.5°	341.1	309.5	269.1	240.7	217.6	206.2	198.5
105°	418.4	422.5	412.1	392.5	373.0	359.4	355.1
107.5°	412.8	445.5	460.7	463.2	462.2	459.4	453.6
110°	395.1	435.4	461.3	474.8	480.8	483.7	483.3



TEST NUMBER: P331287-940

CATALOG NUMBER: S122DIP-S485D330U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	374.2	417.2	446.9	465.7	475.7	481.1	482.8
115°	345.6	386.9	419.4	441.8	456.2	464.4	467.3
117.5°	322.4	359.9	390.3	413.1	428.5	437.0	439.4
120°	310.3	343.8	372.4	394.5	409.3	418.4	421.6
122.5°	300.2	331.9	357.8	377.6	392.2	400.3	402.9
125°	287.0	314.8	338.4	356.7	368.6	376.5	379.1
127.5°	274.2	300.3	322.1	338.0	349.3	356.1	358.1
130°	265.6	290.5	311.3	326.7	337.4	343.8	346.3
132.5°	257.5	280.4	300.0	315.1	325.8	331.6	333.9
135°	244.8	265.6	283.2	296.8	307.2	312.9	314.1
137.5°	234.7	251.2	266.5	278.9	287.8	292.8	294.7
140°	228.1	242.6	256.5	266.5	274.7	279.5	281.3
142.5°	222.3	234.8	246.4	255.9	263.4	267.6	268.0
145°	214.9	224.6	233.8	241.3	246.7	249.9	250.7
147.5°	208.8	216.4	223.1	229.3	233.6	235.8	236.4
150°	204.8	211.4	217.0	221.8	225.6	227.5	227.8
152.5°	201.5	207.1	212.0	215.8	219.0	220.4	220.5
155°	196.3	201.0	204.5	207.9	210.2	211.4	210.8
157.5°	191.0	194.9	197.7	200.1	202.0	202.5	202.5
160°	187.4	190.9	193.1	195.4	196.9	197.2	197.2
162.5°	184.2	187.2	188.9	191.1	192.2	192.4	192.2
165°	179.2	181.5	182.7	184.0	185.3	185.3	184.9
167.5°	174.8	176.3	177.5	178.0	178.7	178.6	178.3
170°	172.0	173.3	173.9	174.2	175.1	174.9	174.2
172.5°	169.5	170.5	170.9	171.2	171.7	171.3	170.9
175°	166.7	167.0	167.3	167.3	167.6	167.3	166.7
177.5°	164.6	164.9	164.9	164.9	164.9	164.6	164.1
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8

(END OF REPORT)